

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333593-940

Luminaire Tested: **S125RDIP-S1090D810U940-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333593-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIP-S1090D810U940-4F0-1E-UDD-A1  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1090 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 810 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6300.7 lumens  
Efficiency: N/A  
Efficacy: 115.8 lumens/watt  
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 54.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333593-940

CATALOG NUMBER: S125RDIP-S1090D810U940-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P333593-940

CATALOG NUMBER: S125RDIP-S1090D810U940-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	102	102	102	102	89	89	89	77	77	77	66	66	66	60
1	101	96	93	89	94	90	87	84	79	77	74	68	67	65	59	58	56	52
2	92	85	79	74	86	80	74	70	70	66	62	61	58	55	52	50	48	44
3	84	75	68	62	79	70	64	59	62	57	53	54	50	47	47	44	42	38
4	77	67	59	53	72	63	56	50	55	50	45	48	44	41	42	39	36	33
5	71	60	51	46	66	56	49	44	50	44	39	44	39	36	38	35	32	29
6	66	54	46	40	61	51	43	38	45	39	35	40	35	31	35	31	28	25
7	61	49	41	35	57	46	39	34	41	35	31	36	31	28	32	28	25	23
8	56	44	36	31	53	42	35	30	37	31	27	33	28	25	29	25	22	20
9	53	40	33	28	49	38	31	27	34	29	25	30	26	22	27	23	20	18
10	49	37	30	25	46	35	29	24	32	26	22	28	24	20	25	21	19	17

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	9469	9469	9469	9469
5°	10893	9481	8373	9481
10°	12496	9433	7389	9433
15°	13497	9336	6567	9336
20°	14882	9224	6064	9224
25°	17224	9075	5627	9075
30°	18744	8918	5341	8918
35°	15811	8736	5077	8736
40°	11042	8408	4850	8408
45°	8191	7965	4629	7965
50°	6531	7504	4439	7504
55°	5543	6933	4270	6933
60°	4790	6421	3995	6421
65°	4268	5868	3440	5868
70°	3750	5374	3136	5374
75°	3244	4654	2944	4654
80°	2462	3916	2462	3916
85°	2045	3083	2319	3083



TEST NUMBER: P333593-940

CATALOG NUMBER: S125RDIP-S1090D810U940-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	140.6	2.2
10°-20°	412.0	6.5
20°-30°	653.3	10.4
30°-40°	787.8	12.5
40°-50°	703.5	11.2
50°-60°	539.5	8.6
60°-70°	350.6	5.6
70°-80°	170.5	2.7
80°-90°	42.6	0.7
90°-100°	60.0	1.0
100°-110°	177.2	2.8
110°-120°	300.2	4.8
120°-130°	395.0	6.3
130°-140°	442.6	7.0
140°-150°	433.8	6.9
150°-160°	364.4	5.8
160°-170°	242.2	3.8
170°-180°	84.8	1.3
0°-30°	1205.9	19.1
0°-40°	1993.7	31.6
0°-60°	3236.7	51.4
0°-90°	3800.4	60.3
90°-120°	537.4	8.5
90°-150°	1808.9	28.7
90°-180°	2500.0	39.7
0°-180°	6300.7	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1466	1466	1466	1466	1466	
5°	1680	1462	1292	1462	1680	168
15°	2019	1396	982	1396	2019	578
25°	2417	1274	790	1274	2417	1110
35°	2005	1108	644	1108	2005	1211
45°	897	872	507	872	897	716
55°	492	616	379	616	492	447
65°	279	384	225	384	279	278
75°	130	186	118	186	130	138
85°	28	42	31	42	28	32
90°	17	1	17	1	17	11
95°	60	45	60	45	60	61
105°	173	159	173	159	173	183
115°	303	300	303	300	303	300
125°	441	438	441	438	441	394
135°	572	570	572	570	572	442
145°	694	691	694	691	694	433
155°	791	791	791	791	791	364
165°	858	860	858	860	858	242
175°	890	894	890	894	890	85
180°	896	896	896	896	896	



TEST NUMBER: P333593-940

CATALOG NUMBER: S125RDIP-S1090D810U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2
2.5°	1542.2	1541.2	1543.2	1537.8	1538.4	1530.2	1530.2	1523.9	1515.7	1509.5	1506.5
5°	1680.3	1681.6	1679.2	1670.2	1664.1	1655.1	1644.8	1626.8	1611.8	1597.3	1585.9
7.5°	1822.7	1823.5	1815.5	1812.8	1797.6	1786.5	1763.8	1739.2	1717.4	1689.8	1668.6
10°	1905.5	1904.9	1896.4	1889.8	1876.6	1859.8	1837.5	1808.6	1781.5	1751.4	1722.5
12.5°	1953.6	1952.0	1949.4	1941.3	1929.0	1914.1	1895.2	1866.8	1833.4	1800.5	1766.8
15°	2018.7	2014.4	2006.6	1996.4	1978.9	1961.4	1940.4	1915.1	1883.2	1845.8	1814.6
17.5°	2099.0	2099.2	2087.1	2072.9	2049.2	2018.4	1985.8	1945.1	1901.8	1860.7	1827.4
20°	2165.4	2163.6	2151.6	2124.0	2096.9	2058.3	2021.1	1971.0	1918.1	1864.6	1823.0
22.5°	2260.8	2256.1	2243.5	2207.3	2165.3	2115.7	2058.6	1997.5	1933.5	1872.7	1818.2
25°	2417.1	2413.4	2388.7	2346.6	2287.7	2211.2	2136.5	2052.9	1960.9	1880.8	1814.6
27.5°	2523.9	2520.0	2501.7	2466.7	2412.3	2331.8	2230.8	2119.0	2004.0	1893.9	1798.5
30°	2513.4	2522.4	2520.0	2503.7	2462.8	2390.6	2297.3	2171.5	2034.9	1905.5	1791.7
32.5°	2362.1	2370.3	2391.4	2423.3	2425.7	2396.8	2327.1	2211.0	2069.6	1922.4	1786.5
35°	2005.4	2016.2	2057.2	2121.6	2205.8	2276.2	2290.6	2228.0	2101.0	1942.8	1778.5
37.5°	1541.7	1600.9	1635.4	1703.2	1830.5	1960.0	2084.6	2130.5	2076.3	1934.4	1765.6
40°	1309.7	1324.1	1385.5	1461.9	1569.1	1703.9	1881.4	2009.6	2013.8	1915.1	1745.3
42.5°	1120.9	1139.2	1181.3	1242.3	1334.1	1468.9	1652.3	1821.3	1899.7	1862.2	1718.9
45°	896.8	910.6	941.3	988.3	1058.6	1170.0	1327.7	1523.3	1678.6	1739.4	1647.9
47.5°	736.6	744.1	770.9	806.6	858.7	939.9	1061.9	1231.7	1418.0	1548.5	1535.7
50°	650.0	658.4	678.9	706.0	749.9	818.5	916.1	1057.5	1249.5	1408.9	1440.8
52.5°	582.6	589.6	602.4	627.9	664.2	716.9	795.7	923.6	1096.4	1266.0	1339.7
55°	492.3	497.1	507.4	521.8	550.7	588.6	656.7	745.1	884.8	1055.6	1164.0
57.5°	417.9	420.4	426.9	440.2	460.2	487.9	537.0	612.0	712.1	866.0	985.6
60°	370.8	373.2	381.6	390.6	406.3	431.5	470.0	522.4	618.7	745.7	866.7
62.5°	333.1	334.7	338.2	347.2	361.0	380.5	410.8	453.5	530.1	641.7	755.9
65°	279.3	279.8	281.1	288.3	296.7	311.1	331.0	361.1	418.9	503.2	604.2
67.5°	227.5	228.4	232.6	235.1	243.9	251.5	263.1	286.1	326.8	383.6	462.3
70°	198.6	198.0	202.2	205.3	208.2	217.3	225.1	243.8	269.0	312.4	378.0
72.5°	171.7	170.0	171.9	173.0	176.9	183.1	190.9	202.3	221.9	251.7	301.9
75°	130.0	130.6	130.6	131.8	134.8	137.2	139.6	145.6	156.5	176.4	203.4
77.5°	91.2	90.2	92.8	93.2	95.0	97.6	99.7	102.1	106.6	114.7	128.7
80°	66.2	66.2	66.8	68.6	68.0	69.2	72.2	74.6	80.1	84.9	89.7
82.5°	50.8	50.3	50.9	51.3	51.2	52.3	53.4	53.9	56.0	58.4	61.7
85°	27.6	27.6	28.3	28.3	28.9	28.9	29.5	29.5	29.5	30.1	30.7
87.5°	13.9	13.4	12.8	12.7	13.1	13.9	13.3	12.7	12.5	12.3	12.6
90°	16.8	16.2	15.8	15.3	14.9	14.3	13.5	12.7	11.9	11.1	10.1
92.5°	32.9	32.5	32.2	31.9	31.6	30.9	29.9	28.8	27.8	26.8	25.4
95°	59.9	59.7	59.4	59.0	58.8	58.1	57.0	55.8	54.8	53.7	52.2
97.5°	91.0	90.8	90.5	90.3	90.2	89.6	88.5	87.6	86.5	85.5	83.4
100°	114.3	114.0	113.7	113.4	113.2	112.3	110.8	109.5	108.1	106.6	104.7
102.5°	137.8	137.3	136.9	136.5	136.1	135.1	133.6	132.1	130.5	129.0	128.0
105°	172.9	172.5	172.0	171.6	171.0	170.4	169.4	168.5	167.6	166.7	165.7
107.5°	208.9	208.9	208.9	209.0	209.0	208.8	208.3	207.9	207.4	207.0	206.3
110°	235.7	235.9	235.9	236.1	236.3	236.1	235.7	235.2	234.8	234.3	233.8



TEST NUMBER: P333593-940

CATALOG NUMBER: S125RDIP-S1090D810U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	261.9	262.2	262.4	262.7	263.1	263.1	262.8	262.6	262.4	262.2	261.6
115°	303.4	303.4	303.6	303.8	303.9	304.1	304.3	304.4	304.5	304.7	304.4
117.5°	343.8	344.4	345.0	345.6	346.3	346.5	346.3	346.3	346.1	346.0	345.7
120°	371.7	372.3	372.9	373.5	374.2	374.4	374.4	374.4	374.4	374.4	374.3
122.5°	399.6	400.0	400.6	401.0	401.5	401.8	402.0	402.1	402.2	402.3	401.9
125°	441.4	441.6	441.7	441.8	442.0	442.2	442.6	442.8	443.2	443.4	443.3
127.5°	481.5	481.9	482.1	482.5	482.8	483.0	483.1	483.3	483.5	483.7	483.5
130°	508.3	508.6	508.9	509.3	509.5	509.8	510.0	510.1	510.2	510.4	510.1
132.5°	533.4	533.9	534.3	534.8	535.1	535.5	535.6	535.7	535.9	536.1	536.1
135°	572.5	573.1	573.7	574.4	575.0	575.2	575.2	575.2	575.2	575.2	575.1
137.5°	610.6	611.4	612.2	613.0	613.8	614.0	613.9	613.7	613.5	613.3	613.0
140°	635.3	636.0	636.8	637.6	638.3	638.6	638.2	637.9	637.7	637.3	636.9
142.5°	658.6	659.4	660.2	660.9	661.7	662.0	661.8	661.6	661.5	661.3	660.7
145°	693.8	694.3	694.7	695.2	695.6	695.9	695.9	695.9	695.9	695.9	695.4
147.5°	723.8	724.9	725.9	726.9	728.0	728.3	728.0	727.5	727.2	726.8	726.5
150°	746.1	746.4	746.7	747.0	747.3	747.5	747.5	747.5	747.5	747.5	746.9
152.5°	764.5	765.1	765.6	766.2	766.7	766.8	766.4	766.1	765.7	765.4	765.1
155°	790.7	791.5	792.3	793.0	793.8	793.9	793.3	792.6	792.0	791.4	791.2
157.5°	812.6	813.6	814.7	815.6	816.7	816.9	816.3	815.6	815.0	814.4	814.2
160°	827.7	828.4	829.2	830.0	830.8	830.8	830.2	829.6	829.0	828.4	828.2
162.5°	840.5	841.4	842.3	843.2	844.1	844.2	843.5	842.7	842.0	841.2	841.2
165°	857.6	858.5	859.5	860.4	861.4	861.5	860.9	860.3	859.7	859.1	858.9
167.5°	871.3	872.3	873.3	874.2	875.1	875.2	874.2	873.3	872.4	871.5	871.5
170°	878.6	879.7	880.7	881.8	882.9	883.0	882.1	881.1	880.2	879.2	879.2
172.5°	884.7	885.6	886.6	887.6	888.6	888.6	887.6	886.7	885.7	884.8	884.8
175°	890.5	891.5	892.6	893.7	894.7	894.8	893.9	893.0	892.1	891.1	891.1
177.5°	893.8	894.7	895.5	896.3	897.2	897.3	896.5	895.8	895.1	894.3	894.5
180°	896.0	896.0	896.0	896.0	896.0	896.0	896.0	896.0	896.0	896.0	896.0



TEST NUMBER: P333593-940

CATALOG NUMBER: S125RDIP-S1090D810U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2
2.5°	1506.5	1503.2	1496.9	1491.1	1483.9	1477.7	1473.4	1468.0	1461.3	1453.1	1446.4
5°	1573.2	1560.0	1542.6	1527.5	1508.2	1493.2	1477.6	1462.5	1447.4	1428.2	1411.3
7.5°	1647.2	1619.8	1593.2	1559.8	1529.5	1502.4	1476.3	1450.0	1424.2	1396.9	1370.6
10°	1692.4	1659.3	1622.6	1580.5	1541.9	1505.2	1471.5	1438.4	1403.6	1372.8	1339.7
12.5°	1734.8	1692.0	1650.0	1596.9	1550.6	1505.7	1462.9	1421.6	1384.3	1344.4	1308.9
15°	1773.1	1730.9	1684.0	1619.0	1554.6	1500.4	1449.8	1396.3	1350.0	1305.4	1265.7
17.5°	1787.9	1743.7	1689.2	1626.7	1556.3	1488.2	1423.0	1364.3	1309.7	1257.8	1213.2
20°	1782.1	1739.4	1683.4	1623.8	1548.5	1477.6	1407.1	1342.1	1281.4	1226.5	1179.0
22.5°	1768.1	1723.9	1669.9	1607.0	1535.5	1460.2	1385.0	1315.6	1252.0	1195.2	1143.4
25°	1747.2	1687.0	1631.7	1570.2	1502.3	1427.6	1350.0	1273.5	1205.5	1147.7	1091.2
27.5°	1725.4	1650.3	1579.8	1518.9	1447.0	1380.4	1305.6	1227.2	1155.7	1096.8	1038.8
30°	1705.7	1621.4	1543.7	1474.5	1406.5	1343.4	1272.3	1195.9	1122.5	1061.7	1002.7
32.5°	1681.1	1591.5	1506.2	1426.4	1360.8	1298.1	1233.8	1160.7	1089.2	1026.5	966.6
35°	1650.3	1536.0	1443.2	1358.3	1285.6	1224.8	1167.0	1108.0	1036.4	971.4	913.0
37.5°	1609.8	1480.1	1372.8	1280.4	1203.5	1142.5	1096.9	1043.0	977.7	915.4	861.2
40°	1585.3	1439.7	1322.2	1230.8	1150.1	1085.7	1043.0	997.3	937.7	879.3	825.1
42.5°	1552.6	1402.6	1271.2	1175.9	1094.8	1032.8	989.5	949.6	899.6	844.6	786.6
45°	1488.4	1330.7	1192.8	1090.6	1008.7	947.9	907.6	872.1	834.2	783.6	733.1
47.5°	1404.8	1255.7	1111.5	999.8	919.6	863.2	824.0	796.0	768.9	725.9	676.8
50°	1337.9	1194.1	1053.2	944.9	859.4	805.8	769.2	746.9	722.2	683.1	642.2
52.5°	1258.9	1130.5	992.6	881.8	801.2	751.0	715.7	693.5	673.2	641.2	602.2
55°	1134.5	1022.0	895.5	795.0	721.0	670.5	636.8	615.7	603.7	576.6	545.9
57.5°	990.9	910.3	798.8	701.9	636.4	586.5	561.8	543.9	530.2	511.1	489.5
60°	890.7	834.2	734.2	642.2	582.0	534.4	512.2	497.1	484.5	468.2	451.4
62.5°	789.2	748.0	661.1	582.0	526.6	486.8	465.9	452.4	437.8	426.9	410.5
65°	653.0	616.3	556.1	494.1	443.0	411.1	396.0	384.0	375.0	362.9	351.5
67.5°	508.0	493.0	451.5	408.8	372.0	343.7	330.6	322.3	311.4	304.2	296.3
70°	418.9	411.7	382.2	353.9	319.6	300.3	288.3	284.6	271.4	264.2	258.8
72.5°	339.9	336.5	319.6	300.0	275.8	259.0	247.8	243.8	235.3	229.5	226.0
75°	232.9	234.2	231.1	218.5	209.5	198.6	189.0	186.5	180.6	175.8	172.7
77.5°	147.3	153.5	153.7	153.1	149.5	142.9	138.9	137.1	131.2	129.4	128.7
80°	101.1	107.7	113.8	113.2	111.9	110.1	107.1	105.3	102.3	100.5	99.3
82.5°	67.4	73.6	78.6	81.9	81.6	79.8	77.8	77.0	76.3	75.0	74.7
85°	31.9	33.1	34.9	39.1	42.1	42.7	42.1	41.6	39.7	40.3	40.9
87.5°	12.8	12.7	12.9	12.7	11.9	14.1	15.3	15.5	14.8	14.1	13.4
90°	9.0	7.9	6.8	5.6	4.5	3.2	2.0	0.7	2.0	3.2	4.5
92.5°	24.1	22.7	21.4	20.3	19.4	18.6	17.7	16.9	17.7	18.6	19.4
95°	50.6	49.0	47.5	46.5	46.3	45.9	45.7	45.3	45.7	45.9	46.3
97.5°	81.2	79.1	77.0	75.8	75.7	75.5	75.4	75.3	75.4	75.5	75.7
100°	102.6	100.7	98.6	97.6	97.6	97.6	97.6	97.6	97.6	97.6	97.6
102.5°	127.0	125.9	124.9	124.1	123.5	122.9	122.3	121.6	122.3	122.9	123.5
105°	164.8	163.9	162.9	162.1	161.3	160.5	159.8	159.0	159.8	160.5	161.3
107.5°	205.5	204.8	204.1	203.4	202.6	201.8	201.0	200.3	201.0	201.8	202.6
110°	233.4	232.9	232.5	231.8	231.0	230.2	229.5	228.7	229.5	230.2	231.0





TEST NUMBER: P333593-940

CATALOG NUMBER: S125RDIP-S1090D810U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	261.0	260.4	259.8	259.3	259.0	258.5	258.2	257.7	258.2	258.5	259.0
115°	304.1	303.8	303.4	303.0	302.4	301.8	301.1	300.5	301.1	301.8	302.4
117.5°	345.4	345.2	344.9	344.6	344.3	344.0	343.8	343.5	343.8	344.0	344.3
120°	374.2	374.0	373.8	373.4	372.6	371.8	371.0	370.2	371.0	371.8	372.6
122.5°	401.5	401.1	400.7	400.4	400.1	399.8	399.6	399.2	399.6	399.8	400.1
125°	443.2	443.0	442.8	442.3	441.4	440.4	439.5	438.5	439.5	440.4	441.4
127.5°	483.2	483.0	482.9	482.5	482.0	481.4	481.0	480.5	481.0	481.4	482.0
130°	509.8	509.4	509.2	508.6	507.8	507.1	506.3	505.5	506.3	507.1	507.8
132.5°	536.2	536.3	536.3	535.7	534.4	533.2	531.9	530.7	531.9	533.2	534.4
135°	575.0	574.8	574.6	574.1	573.2	572.2	571.3	570.3	571.3	572.2	573.2
137.5°	612.6	612.3	612.0	611.4	610.5	609.6	608.7	607.8	608.7	609.6	610.5
140°	636.4	635.9	635.4	634.8	634.1	633.3	632.5	631.8	632.5	633.3	634.1
142.5°	660.1	659.5	659.0	658.4	657.6	657.0	656.4	655.8	656.4	657.0	657.6
145°	694.9	694.5	694.0	693.5	692.9	692.2	691.6	691.0	691.6	692.2	692.9
147.5°	726.1	725.8	725.3	725.0	724.7	724.3	724.0	723.6	724.0	724.3	724.7
150°	746.3	745.6	745.0	744.8	744.9	745.1	745.2	745.4	745.2	745.1	744.9
152.5°	764.8	764.6	764.4	764.1	763.9	763.7	763.5	763.2	763.5	763.7	763.9
155°	791.1	790.9	790.8	790.7	790.7	790.7	790.7	790.7	790.7	790.7	790.7
157.5°	814.1	814.0	813.8	813.9	814.2	814.6	814.9	815.3	814.9	814.6	814.2
160°	828.0	827.9	827.8	827.9	828.4	828.8	829.3	829.7	829.3	828.8	828.4
162.5°	841.2	841.1	841.1	841.2	841.6	841.9	842.2	842.6	842.2	841.9	841.6
165°	858.7	858.5	858.4	858.5	858.8	859.2	859.4	859.8	859.4	859.2	858.8
167.5°	871.5	871.5	871.5	871.7	872.4	873.0	873.6	874.2	873.6	873.0	872.4
170°	879.2	879.2	879.2	879.6	880.2	880.8	881.5	882.1	881.5	880.8	880.2
172.5°	884.8	884.8	884.8	885.1	885.7	886.4	887.0	887.6	887.0	886.4	885.7
175°	891.1	891.1	891.1	891.4	892.1	892.7	893.3	893.9	893.3	892.7	892.1
177.5°	894.6	894.7	894.8	895.1	895.6	896.2	896.6	897.2	896.6	896.2	895.6
180°	896.0	896.0	896.0	896.0	896.0	896.0	896.0	896.0	896.0	896.0	896.0



TEST NUMBER: P333593-940

CATALOG NUMBER: S125RDIP-S1090D810U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2
2.5°	1441.5	1434.9	1430.0	1420.4	1413.6	1410.8	1405.4	1404.0	1409.3	1405.4	1405.0
5°	1398.7	1381.3	1367.4	1353.5	1338.5	1328.9	1314.5	1312.1	1308.4	1303.0	1301.8
7.5°	1347.3	1324.5	1306.7	1283.9	1264.0	1248.0	1229.9	1221.4	1216.7	1209.7	1200.3
10°	1312.6	1285.6	1261.5	1238.6	1214.0	1194.1	1176.0	1162.2	1153.2	1144.7	1141.1
12.5°	1278.4	1250.9	1220.0	1192.4	1164.8	1142.5	1122.6	1113.6	1103.6	1093.7	1085.3
15°	1225.4	1188.7	1154.9	1123.0	1099.6	1075.5	1056.2	1043.0	1028.0	1023.8	1007.5
17.5°	1169.0	1133.0	1093.6	1060.0	1032.8	1006.3	985.1	970.1	958.8	943.3	935.8
20°	1133.9	1091.2	1052.7	1022.0	991.8	960.6	938.9	926.2	915.4	902.8	896.8
22.5°	1096.4	1054.5	1015.1	979.1	948.5	917.7	902.3	889.2	876.9	865.2	857.3
25°	1041.2	999.1	957.5	920.2	888.3	866.0	848.0	832.9	826.3	814.9	806.5
27.5°	986.7	941.9	898.8	861.6	836.6	814.6	799.8	787.8	775.9	765.9	758.6
30°	951.5	905.8	858.8	829.4	802.9	781.8	765.5	754.1	745.1	736.1	730.7
32.5°	916.4	869.2	827.5	795.7	770.6	752.4	735.7	724.8	715.2	705.3	698.8
35°	860.1	811.9	778.2	746.9	722.2	705.3	693.9	678.3	670.5	663.3	656.7
37.5°	807.7	762.9	726.5	699.0	677.5	660.8	646.0	637.6	627.9	621.4	615.9
40°	769.2	728.3	695.2	666.3	650.6	632.0	618.1	607.3	600.0	591.7	585.6
42.5°	734.5	696.4	664.3	638.3	618.8	603.1	589.7	578.9	569.7	563.7	558.7
45°	685.5	647.6	616.3	592.2	574.2	559.1	545.3	539.8	527.8	520.6	518.2
47.5°	634.8	600.9	570.7	548.5	530.0	515.8	502.7	491.7	485.1	478.0	474.1
50°	600.7	568.1	539.8	518.2	500.2	484.5	472.4	465.2	456.2	449.6	444.8
52.5°	566.5	536.4	508.1	487.4	471.7	456.1	442.6	435.4	426.9	422.6	419.3
55°	517.6	485.7	461.6	441.1	424.9	410.5	397.8	390.6	385.2	380.9	379.8
57.5°	462.3	436.9	414.6	396.1	379.2	365.7	354.6	347.8	343.0	342.3	338.8
60°	426.1	403.2	382.8	362.9	348.5	335.8	326.2	318.3	313.5	313.0	311.7
62.5°	390.0	368.1	349.1	331.6	318.6	306.5	297.3	288.6	285.6	282.7	280.0
65°	336.4	316.6	301.0	287.0	273.2	263.0	254.0	248.6	241.9	238.4	231.8
67.5°	283.8	268.4	253.4	241.7	230.9	221.1	213.7	205.6	201.2	198.2	193.4
70°	249.1	237.1	222.1	209.5	201.0	193.2	187.2	178.2	175.1	172.7	170.3
72.5°	216.4	205.8	193.2	183.0	174.5	167.2	160.2	156.0	153.0	150.6	149.2
75°	170.3	160.1	149.3	142.0	136.0	130.0	126.4	123.4	122.2	121.5	119.1
77.5°	125.1	119.7	111.0	105.2	101.2	98.8	95.6	94.0	93.9	91.2	90.4
80°	95.7	92.6	85.4	83.0	80.1	77.7	75.8	72.9	69.8	68.6	66.8
82.5°	71.2	68.1	65.3	61.3	58.9	57.4	55.6	54.5	54.9	53.2	52.3
85°	37.9	34.9	33.7	33.1	31.9	33.1	32.5	31.9	31.3	30.7	31.3
87.5°	13.2	13.4	13.1	14.4	13.1	13.8	13.9	13.6	13.7	13.9	13.6
90°	5.6	6.8	7.9	9.0	10.1	11.1	11.9	12.7	13.5	14.3	14.9
92.5°	20.3	21.4	22.7	24.1	25.4	26.8	27.8	28.8	29.9	30.9	31.6
95°	46.5	47.5	49.0	50.6	52.2	53.7	54.8	55.8	57.0	58.1	58.8
97.5°	75.8	77.0	79.1	81.2	83.4	85.5	86.5	87.6	88.5	89.6	90.2
100°	97.6	98.6	100.7	102.6	104.7	106.6	108.1	109.5	110.8	112.3	113.2
102.5°	124.1	124.9	125.9	127.0	128.0	129.0	130.5	132.1	133.6	135.1	136.1
105°	162.1	162.9	163.9	164.8	165.7	166.7	167.6	168.5	169.4	170.4	171.0
107.5°	203.4	204.1	204.8	205.5	206.3	207.0	207.4	207.9	208.3	208.8	209.0
110°	231.8	232.5	232.9	233.4	233.8	234.3	234.8	235.2	235.7	236.1	236.3



TEST NUMBER: P333593-940

CATALOG NUMBER: S125RDIP-S1090D810U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	259.3	259.8	260.4	261.0	261.6	262.2	262.4	262.6	262.8	263.1	263.1
115°	303.0	303.4	303.8	304.1	304.4	304.7	304.5	304.4	304.3	304.1	303.9
117.5°	344.6	344.9	345.2	345.4	345.7	346.0	346.1	346.3	346.3	346.5	346.3
120°	373.4	373.8	374.0	374.2	374.3	374.4	374.4	374.4	374.4	374.4	374.2
122.5°	400.4	400.7	401.1	401.5	401.9	402.3	402.2	402.1	402.0	401.8	401.5
125°	442.3	442.8	443.0	443.2	443.3	443.4	443.2	442.8	442.6	442.2	442.0
127.5°	482.5	482.9	483.0	483.2	483.5	483.7	483.5	483.3	483.1	483.0	482.8
130°	508.6	509.2	509.4	509.8	510.1	510.4	510.2	510.1	510.0	509.8	509.5
132.5°	535.7	536.3	536.3	536.2	536.1	536.1	535.9	535.7	535.6	535.5	535.1
135°	574.1	574.6	574.8	575.0	575.1	575.2	575.2	575.2	575.2	575.2	575.0
137.5°	611.4	612.0	612.3	612.6	613.0	613.3	613.5	613.7	613.9	614.0	613.8
140°	634.8	635.4	635.9	636.4	636.9	637.3	637.7	637.9	638.2	638.6	638.3
142.5°	658.4	659.0	659.5	660.1	660.7	661.3	661.5	661.6	661.8	662.0	661.7
145°	693.5	694.0	694.5	694.9	695.4	695.9	695.9	695.9	695.9	695.9	695.6
147.5°	725.0	725.3	725.8	726.1	726.5	726.8	727.2	727.5	728.0	728.3	728.0
150°	744.8	745.0	745.6	746.3	746.9	747.5	747.5	747.5	747.5	747.5	747.3
152.5°	764.1	764.4	764.6	764.8	765.1	765.4	765.7	766.1	766.4	766.8	766.7
155°	790.7	790.8	790.9	791.1	791.2	791.4	792.0	792.6	793.3	793.9	793.8
157.5°	813.9	813.8	814.0	814.1	814.2	814.4	815.0	815.6	816.3	816.9	816.7
160°	827.9	827.8	827.9	828.0	828.2	828.4	829.0	829.6	830.2	830.8	830.8
162.5°	841.2	841.1	841.1	841.2	841.2	841.2	842.0	842.7	843.5	844.2	844.1
165°	858.5	858.4	858.5	858.7	858.9	859.1	859.7	860.3	860.9	861.5	861.4
167.5°	871.7	871.5	871.5	871.5	871.5	871.5	872.4	873.3	874.2	875.2	875.1
170°	879.6	879.2	879.2	879.2	879.2	879.2	880.2	881.1	882.1	883.0	882.9
172.5°	885.1	884.8	884.8	884.8	884.8	884.8	885.7	886.7	887.6	888.6	888.6
175°	891.4	891.1	891.1	891.1	891.1	891.1	892.1	893.0	893.9	894.8	894.7
177.5°	895.1	894.8	894.7	894.6	894.5	894.3	895.1	895.8	896.5	897.3	897.2
180°	896.0	896.0	896.0	896.0	896.0	896.0	896.0	896.0	896.0	896.0	896.0



TEST NUMBER: P333593-940

CATALOG NUMBER: S125RDIP-S1090D810U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2
2.5°	1404.4	1399.2	1397.8	1399.6	1397.8	1399.2	1404.4	1405.0	1405.4	1409.3	1404.0
5°	1295.8	1289.8	1292.8	1291.6	1292.8	1289.8	1295.8	1301.8	1303.0	1308.4	1312.1
7.5°	1200.2	1192.8	1184.8	1187.3	1184.8	1192.8	1200.2	1200.3	1209.7	1216.7	1221.4
10°	1133.3	1127.3	1123.6	1126.7	1123.6	1127.3	1133.3	1141.1	1144.7	1153.2	1162.2
12.5°	1076.9	1073.4	1070.2	1068.9	1070.2	1073.4	1076.9	1085.3	1093.7	1103.6	1113.6
15°	1000.3	993.1	990.1	982.2	990.1	993.1	1000.3	1007.5	1023.8	1028.0	1043.0
17.5°	929.6	927.2	919.4	916.1	919.4	927.2	929.6	935.8	943.3	958.8	970.1
20°	887.7	885.3	877.5	882.3	877.5	885.3	887.7	896.8	902.8	915.4	926.2
22.5°	853.1	847.7	845.3	843.8	845.3	847.7	853.1	857.3	865.2	876.9	889.2
25°	804.1	796.2	793.3	789.6	793.3	796.2	804.1	806.5	814.9	826.3	832.9
27.5°	755.2	751.0	747.0	746.1	747.0	751.0	755.2	758.6	765.9	775.9	787.8
30°	723.4	719.3	716.2	716.2	716.2	719.3	723.4	730.7	736.1	745.1	754.1
32.5°	695.0	691.8	688.8	688.3	688.8	691.8	695.0	698.8	705.3	715.2	724.8
35°	653.6	648.8	647.6	644.0	647.6	648.8	653.6	656.7	663.3	670.5	678.3
37.5°	610.6	606.6	606.5	606.2	606.5	606.6	610.6	615.9	621.4	627.9	637.6
40°	583.2	580.1	579.6	575.3	579.6	580.1	583.2	585.6	591.7	600.0	607.3
42.5°	553.8	552.2	550.2	548.4	550.2	552.2	553.8	558.7	563.7	569.7	578.9
45°	514.0	509.8	509.8	506.8	509.8	509.8	514.0	518.2	520.6	527.8	539.8
47.5°	472.8	469.6	469.9	466.8	469.9	469.6	472.8	474.1	478.0	485.1	491.7
50°	445.4	443.5	443.0	441.8	443.0	443.5	445.4	444.8	449.6	456.2	465.2
52.5°	417.9	417.1	419.4	416.7	419.4	417.1	417.9	419.3	422.6	426.9	435.4
55°	380.9	379.2	382.8	379.2	382.8	379.2	380.9	379.8	380.9	385.2	390.6
57.5°	338.5	336.8	340.0	338.2	340.0	336.8	338.5	338.8	342.3	343.0	347.8
60°	310.6	306.9	308.7	309.3	308.7	306.9	310.6	311.7	313.0	313.5	318.3
62.5°	277.3	275.2	276.5	273.8	276.5	275.2	277.3	280.0	282.7	285.6	288.6
65°	230.5	228.7	226.3	225.1	226.3	228.7	230.5	231.8	238.4	241.9	248.6
67.5°	193.7	189.3	189.2	190.2	189.2	189.3	193.7	193.4	198.2	201.2	205.6
70°	166.7	166.7	166.1	166.1	166.1	166.7	166.7	170.3	172.7	175.1	178.2
72.5°	147.9	147.5	146.3	145.9	146.3	147.5	147.9	149.2	150.6	153.0	156.0
75°	119.1	119.8	118.6	118.0	118.6	119.8	119.1	119.1	121.5	122.2	123.4
77.5°	88.0	85.4	86.8	85.4	86.8	85.4	88.0	90.4	91.2	93.9	94.0
80°	66.8	66.2	68.0	66.2	68.0	66.2	66.8	66.8	68.6	69.8	72.9
82.5°	52.9	52.3	53.1	51.7	53.1	52.3	52.9	52.3	53.2	54.9	54.5
85°	31.9	31.3	30.7	31.3	30.7	31.3	31.9	31.3	30.7	31.3	31.9
87.5°	14.2	13.7	13.8	13.9	13.8	13.7	14.2	13.6	13.9	13.7	13.6
90°	15.3	15.8	16.2	16.8	16.2	15.8	15.3	14.9	14.3	13.5	12.7
92.5°	31.9	32.2	32.5	32.9	32.5	32.2	31.9	31.6	30.9	29.9	28.8
95°	59.0	59.4	59.7	59.9	59.7	59.4	59.0	58.8	58.1	57.0	55.8
97.5°	90.3	90.5	90.8	91.0	90.8	90.5	90.3	90.2	89.6	88.5	87.6
100°	113.4	113.7	114.0	114.3	114.0	113.7	113.4	113.2	112.3	110.8	109.5
102.5°	136.5	136.9	137.3	137.8	137.3	136.9	136.5	136.1	135.1	133.6	132.1
105°	171.6	172.0	172.5	172.9	172.5	172.0	171.6	171.0	170.4	169.4	168.5
107.5°	209.0	208.9	208.9	208.9	208.9	208.9	209.0	209.0	208.8	208.3	207.9
110°	236.1	235.9	235.9	235.7	235.9	235.9	236.1	236.3	236.1	235.7	235.2



TEST NUMBER: P333593-940

CATALOG NUMBER: S125RDIP-S1090D810U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	262.7	262.4	262.2	261.9	262.2	262.4	262.7	263.1	263.1	262.8	262.6
115°	303.8	303.6	303.4	303.4	303.4	303.6	303.8	303.9	304.1	304.3	304.4
117.5°	345.6	345.0	344.4	343.8	344.4	345.0	345.6	346.3	346.5	346.3	346.3
120°	373.5	372.9	372.3	371.7	372.3	372.9	373.5	374.2	374.4	374.4	374.4
122.5°	401.0	400.6	400.0	399.6	400.0	400.6	401.0	401.5	401.8	402.0	402.1
125°	441.8	441.7	441.6	441.4	441.6	441.7	441.8	442.0	442.2	442.6	442.8
127.5°	482.5	482.1	481.9	481.5	481.9	482.1	482.5	482.8	483.0	483.1	483.3
130°	509.3	508.9	508.6	508.3	508.6	508.9	509.3	509.5	509.8	510.0	510.1
132.5°	534.8	534.3	533.9	533.4	533.9	534.3	534.8	535.1	535.5	535.6	535.7
135°	574.4	573.7	573.1	572.5	573.1	573.7	574.4	575.0	575.2	575.2	575.2
137.5°	613.0	612.2	611.4	610.6	611.4	612.2	613.0	613.8	614.0	613.9	613.7
140°	637.6	636.8	636.0	635.3	636.0	636.8	637.6	638.3	638.6	638.2	637.9
142.5°	660.9	660.2	659.4	658.6	659.4	660.2	660.9	661.7	662.0	661.8	661.6
145°	695.2	694.7	694.3	693.8	694.3	694.7	695.2	695.6	695.9	695.9	695.9
147.5°	726.9	725.9	724.9	723.8	724.9	725.9	726.9	728.0	728.3	728.0	727.5
150°	747.0	746.7	746.4	746.1	746.4	746.7	747.0	747.3	747.5	747.5	747.5
152.5°	766.2	765.6	765.1	764.5	765.1	765.6	766.2	766.7	766.8	766.4	766.1
155°	793.0	792.3	791.5	790.7	791.5	792.3	793.0	793.8	793.9	793.3	792.6
157.5°	815.6	814.7	813.6	812.6	813.6	814.7	815.6	816.7	816.9	816.3	815.6
160°	830.0	829.2	828.4	827.7	828.4	829.2	830.0	830.8	830.8	830.2	829.6
162.5°	843.2	842.3	841.4	840.5	841.4	842.3	843.2	844.1	844.2	843.5	842.7
165°	860.4	859.5	858.5	857.6	858.5	859.5	860.4	861.4	861.5	860.9	860.3
167.5°	874.2	873.3	872.3	871.3	872.3	873.3	874.2	875.1	875.2	874.2	873.3
170°	881.8	880.7	879.7	878.6	879.7	880.7	881.8	882.9	883.0	882.1	881.1
172.5°	887.6	886.6	885.6	884.7	885.6	886.6	887.6	888.6	888.6	887.6	886.7
175°	893.7	892.6	891.5	890.5	891.5	892.6	893.7	894.7	894.8	893.9	893.0
177.5°	896.3	895.5	894.7	893.8	894.7	895.5	896.3	897.2	897.3	896.5	895.8
180°	896.0	896.0	896.0	896.0	896.0	896.0	896.0	896.0	896.0	896.0	896.0



TEST NUMBER: P333593-940

CATALOG NUMBER: S125RDIP-S1090D810U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2
2.5°	1405.4	1410.8	1413.6	1420.4	1430.0	1434.9	1441.5	1446.4	1453.1	1461.3	1468.0
5°	1314.5	1328.9	1338.5	1353.5	1367.4	1381.3	1398.7	1411.3	1428.2	1447.4	1462.5
7.5°	1229.9	1248.0	1264.0	1283.9	1306.7	1324.5	1347.3	1370.6	1396.9	1424.2	1450.0
10°	1176.0	1194.1	1214.0	1238.6	1261.5	1285.6	1312.6	1339.7	1372.8	1403.6	1438.4
12.5°	1122.6	1142.5	1164.8	1192.4	1220.0	1250.9	1278.4	1308.9	1344.4	1384.3	1421.6
15°	1056.2	1075.5	1099.6	1123.0	1154.9	1188.7	1225.4	1265.7	1305.4	1350.0	1396.3
17.5°	985.1	1006.3	1032.8	1060.0	1093.6	1133.0	1169.0	1213.2	1257.8	1309.7	1364.3
20°	938.9	960.6	991.8	1022.0	1052.7	1091.2	1133.9	1179.0	1226.5	1281.4	1342.1
22.5°	902.3	917.7	948.5	979.1	1015.1	1054.5	1096.4	1143.4	1195.2	1252.0	1315.6
25°	848.0	866.0	888.3	920.2	957.5	999.1	1041.2	1091.2	1147.7	1205.5	1273.5
27.5°	799.8	814.6	836.6	861.6	898.8	941.9	986.7	1038.8	1096.8	1155.7	1227.2
30°	765.5	781.8	802.9	829.4	858.8	905.8	951.5	1002.7	1061.7	1122.5	1195.9
32.5°	735.7	752.4	770.6	795.7	827.5	869.2	916.4	966.6	1026.5	1089.2	1160.7
35°	693.9	705.3	722.2	746.9	778.2	811.9	860.1	913.0	971.4	1036.4	1108.0
37.5°	646.0	660.8	677.5	699.0	726.5	762.9	807.7	861.2	915.4	977.7	1043.0
40°	618.1	632.0	650.6	666.3	695.2	728.3	769.2	825.1	879.3	937.7	997.3
42.5°	589.7	603.1	618.8	638.3	664.3	696.4	734.5	786.6	844.6	899.6	949.6
45°	545.3	559.1	574.2	592.2	616.3	647.6	685.5	733.1	783.6	834.2	872.1
47.5°	502.7	515.8	530.0	548.5	570.7	600.9	634.8	676.8	725.9	768.9	796.0
50°	472.4	484.5	500.2	518.2	539.8	568.1	600.7	642.2	683.1	722.2	746.9
52.5°	442.6	456.1	471.7	487.4	508.1	536.4	566.5	602.2	641.2	673.2	693.5
55°	397.8	410.5	424.9	441.1	461.6	485.7	517.6	545.9	576.6	603.7	615.7
57.5°	354.6	365.7	379.2	396.1	414.6	436.9	462.3	489.5	511.1	530.2	543.9
60°	326.2	335.8	348.5	362.9	382.8	403.2	426.1	451.4	468.2	484.5	497.1
62.5°	297.3	306.5	318.6	331.6	349.1	368.1	390.0	410.5	426.9	437.8	452.4
65°	254.0	263.0	273.2	287.0	301.0	316.6	336.4	351.5	362.9	375.0	384.0
67.5°	213.7	221.1	230.9	241.7	253.4	268.4	283.8	296.3	304.2	311.4	322.3
70°	187.2	193.2	201.0	209.5	222.1	237.1	249.1	258.8	264.2	271.4	284.6
72.5°	160.2	167.2	174.5	183.0	193.2	205.8	216.4	226.0	229.5	235.3	243.8
75°	126.4	130.0	136.0	142.0	149.3	160.1	170.3	172.7	175.8	180.6	186.5
77.5°	95.6	98.8	101.2	105.2	111.0	119.7	125.1	128.7	129.4	131.2	137.1
80°	75.8	77.7	80.1	83.0	85.4	92.6	95.7	99.3	100.5	102.3	105.3
82.5°	55.6	57.4	58.9	61.3	65.3	68.1	71.2	74.7	75.0	76.3	77.0
85°	32.5	33.1	31.9	33.1	33.7	34.9	37.9	40.9	40.3	39.7	41.6
87.5°	13.9	13.8	13.1	14.4	13.1	13.4	13.2	13.4	14.1	14.8	15.5
90°	11.9	11.1	10.1	9.0	7.9	6.8	5.6	4.5	3.2	2.0	0.7
92.5°	27.8	26.8	25.4	24.1	22.7	21.4	20.3	19.4	18.6	17.7	16.9
95°	54.8	53.7	52.2	50.6	49.0	47.5	46.5	46.3	45.9	45.7	45.3
97.5°	86.5	85.5	83.4	81.2	79.1	77.0	75.8	75.7	75.5	75.4	75.3
100°	108.1	106.6	104.7	102.6	100.7	98.6	97.6	97.6	97.6	97.6	97.6
102.5°	130.5	129.0	128.0	127.0	125.9	124.9	124.1	123.5	122.9	122.3	121.6
105°	167.6	166.7	165.7	164.8	163.9	162.9	162.1	161.3	160.5	159.8	159.0
107.5°	207.4	207.0	206.3	205.5	204.8	204.1	203.4	202.6	201.8	201.0	200.3
110°	234.8	234.3	233.8	233.4	232.9	232.5	231.8	231.0	230.2	229.5	228.7



TEST NUMBER: P333593-940

CATALOG NUMBER: S125RDIP-S1090D810U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	262.4	262.2	261.6	261.0	260.4	259.8	259.3	259.0	258.5	258.2	257.7
115°	304.5	304.7	304.4	304.1	303.8	303.4	303.0	302.4	301.8	301.1	300.5
117.5°	346.1	346.0	345.7	345.4	345.2	344.9	344.6	344.3	344.0	343.8	343.5
120°	374.4	374.4	374.3	374.2	374.0	373.8	373.4	372.6	371.8	371.0	370.2
122.5°	402.2	402.3	401.9	401.5	401.1	400.7	400.4	400.1	399.8	399.6	399.2
125°	443.2	443.4	443.3	443.2	443.0	442.8	442.3	441.4	440.4	439.5	438.5
127.5°	483.5	483.7	483.5	483.2	483.0	482.9	482.5	482.0	481.4	481.0	480.5
130°	510.2	510.4	510.1	509.8	509.4	509.2	508.6	507.8	507.1	506.3	505.5
132.5°	535.9	536.1	536.1	536.2	536.3	536.3	535.7	534.4	533.2	531.9	530.7
135°	575.2	575.2	575.1	575.0	574.8	574.6	574.1	573.2	572.2	571.3	570.3
137.5°	613.5	613.3	613.0	612.6	612.3	612.0	611.4	610.5	609.6	608.7	607.8
140°	637.7	637.3	636.9	636.4	635.9	635.4	634.8	634.1	633.3	632.5	631.8
142.5°	661.5	661.3	660.7	660.1	659.5	659.0	658.4	657.6	657.0	656.4	655.8
145°	695.9	695.9	695.4	694.9	694.5	694.0	693.5	692.9	692.2	691.6	691.0
147.5°	727.2	726.8	726.5	726.1	725.8	725.3	725.0	724.7	724.3	724.0	723.6
150°	747.5	747.5	746.9	746.3	745.6	745.0	744.8	744.9	745.1	745.2	745.4
152.5°	765.7	765.4	765.1	764.8	764.6	764.4	764.1	763.9	763.7	763.5	763.2
155°	792.0	791.4	791.2	791.1	790.9	790.8	790.7	790.7	790.7	790.7	790.7
157.5°	815.0	814.4	814.2	814.1	814.0	813.8	813.9	814.2	814.6	814.9	815.3
160°	829.0	828.4	828.2	828.0	827.9	827.8	827.9	828.4	828.8	829.3	829.7
162.5°	842.0	841.2	841.2	841.2	841.1	841.1	841.2	841.6	841.9	842.2	842.6
165°	859.7	859.1	858.9	858.7	858.5	858.4	858.5	858.8	859.2	859.4	859.8
167.5°	872.4	871.5	871.5	871.5	871.5	871.5	871.7	872.4	873.0	873.6	874.2
170°	880.2	879.2	879.2	879.2	879.2	879.2	879.6	880.2	880.8	881.5	882.1
172.5°	885.7	884.8	884.8	884.8	884.8	884.8	885.1	885.7	886.4	887.0	887.6
175°	892.1	891.1	891.1	891.1	891.1	891.1	891.4	892.1	892.7	893.3	893.9
177.5°	895.1	894.3	894.5	894.6	894.7	894.8	895.1	895.6	896.2	896.6	897.2
180°	896.0	896.0	896.0	896.0	896.0	896.0	896.0	896.0	896.0	896.0	896.0



TEST NUMBER: P333593-940

CATALOG NUMBER: S125RDIP-S1090D810U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2
2.5°	1473.4	1477.7	1483.9	1491.1	1496.9	1503.2	1506.5	1506.5	1509.5	1515.7	1523.9
5°	1477.6	1493.2	1508.2	1527.5	1542.6	1560.0	1573.2	1585.9	1597.3	1611.8	1626.8
7.5°	1476.3	1502.4	1529.5	1559.8	1593.2	1619.8	1647.2	1668.6	1689.8	1717.4	1739.2
10°	1471.5	1505.2	1541.9	1580.5	1622.6	1659.3	1692.4	1722.5	1751.4	1781.5	1808.6
12.5°	1462.9	1505.7	1550.6	1596.9	1650.0	1692.0	1734.8	1766.8	1800.5	1833.4	1866.8
15°	1449.8	1500.4	1554.6	1619.0	1684.0	1730.9	1773.1	1814.6	1845.8	1883.2	1915.1
17.5°	1423.0	1488.2	1556.3	1626.7	1689.2	1743.7	1787.9	1827.4	1860.7	1901.8	1945.1
20°	1407.1	1477.6	1548.5	1623.8	1683.4	1739.4	1782.1	1823.0	1864.6	1918.1	1971.0
22.5°	1385.0	1460.2	1535.5	1607.0	1669.9	1723.9	1768.1	1818.2	1872.7	1933.5	1997.5
25°	1350.0	1427.6	1502.3	1570.2	1631.7	1687.0	1747.2	1814.6	1880.8	1960.9	2052.9
27.5°	1305.6	1380.4	1447.0	1518.9	1579.8	1650.3	1725.4	1798.5	1893.9	2004.0	2119.0
30°	1272.3	1343.4	1406.5	1474.5	1543.7	1621.4	1705.7	1791.7	1905.5	2034.9	2171.5
32.5°	1233.8	1298.1	1360.8	1426.4	1506.2	1591.5	1681.1	1786.5	1922.4	2069.6	2211.0
35°	1167.0	1224.8	1285.6	1358.3	1443.2	1536.0	1650.3	1778.5	1942.8	2101.0	2228.0
37.5°	1096.9	1142.5	1203.5	1280.4	1372.8	1480.1	1609.8	1765.6	1934.4	2076.3	2130.5
40°	1043.0	1085.7	1150.1	1230.8	1322.2	1439.7	1585.3	1745.3	1915.1	2013.8	2009.6
42.5°	989.5	1032.8	1094.8	1175.9	1271.2	1402.6	1552.6	1718.9	1862.2	1899.7	1821.3
45°	907.6	947.9	1008.7	1090.6	1192.8	1330.7	1488.4	1647.9	1739.4	1678.6	1523.3
47.5°	824.0	863.2	919.6	999.8	1111.5	1255.7	1404.8	1535.7	1548.5	1418.0	1231.7
50°	769.2	805.8	859.4	944.9	1053.2	1194.1	1337.9	1440.8	1408.9	1249.5	1057.5
52.5°	715.7	751.0	801.2	881.8	992.6	1130.5	1258.9	1339.7	1266.0	1096.4	923.6
55°	636.8	670.5	721.0	795.0	895.5	1022.0	1134.5	1164.0	1055.6	884.8	745.1
57.5°	561.8	586.5	636.4	701.9	798.8	910.3	990.9	985.6	866.0	712.1	612.0
60°	512.2	534.4	582.0	642.2	734.2	834.2	890.7	866.7	745.7	618.7	522.4
62.5°	465.9	486.8	526.6	582.0	661.1	748.0	789.2	755.9	641.7	530.1	453.5
65°	396.0	411.1	443.0	494.1	556.1	616.3	653.0	604.2	503.2	418.9	361.1
67.5°	330.6	343.7	372.0	408.8	451.5	493.0	508.0	462.3	383.6	326.8	286.1
70°	288.3	300.3	319.6	353.9	382.2	411.7	418.9	378.0	312.4	269.0	243.8
72.5°	247.8	259.0	275.8	300.0	319.6	336.5	339.9	301.9	251.7	221.9	202.3
75°	189.0	198.6	209.5	218.5	231.1	234.2	232.9	203.4	176.4	156.5	145.6
77.5°	138.9	142.9	149.5	153.1	153.7	153.5	147.3	128.7	114.7	106.6	102.1
80°	107.1	110.1	111.9	113.2	113.8	107.7	101.1	89.7	84.9	80.1	74.6
82.5°	77.8	79.8	81.6	81.9	78.6	73.6	67.4	61.7	58.4	56.0	53.9
85°	42.1	42.7	42.1	39.1	34.9	33.1	31.9	30.7	30.1	29.5	29.5
87.5°	15.3	14.1	11.9	12.7	12.9	12.7	12.8	12.6	12.3	12.5	12.7
90°	2.0	3.2	4.5	5.6	6.8	7.9	9.0	10.1	11.1	11.9	12.7
92.5°	17.7	18.6	19.4	20.3	21.4	22.7	24.1	25.4	26.8	27.8	28.8
95°	45.7	45.9	46.3	46.5	47.5	49.0	50.6	52.2	53.7	54.8	55.8
97.5°	75.4	75.5	75.7	75.8	77.0	79.1	81.2	83.4	85.5	86.5	87.6
100°	97.6	97.6	97.6	97.6	98.6	100.7	102.6	104.7	106.6	108.1	109.5
102.5°	122.3	122.9	123.5	124.1	124.9	125.9	127.0	128.0	129.0	130.5	132.1
105°	159.8	160.5	161.3	162.1	162.9	163.9	164.8	165.7	166.7	167.6	168.5
107.5°	201.0	201.8	202.6	203.4	204.1	204.8	205.5	206.3	207.0	207.4	207.9
110°	229.5	230.2	231.0	231.8	232.5	232.9	233.4	233.8	234.3	234.8	235.2





TEST NUMBER: P333593-940

CATALOG NUMBER: S125RDIP-S1090D810U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	258.2	258.5	259.0	259.3	259.8	260.4	261.0	261.6	262.2	262.4	262.6
115°	301.1	301.8	302.4	303.0	303.4	303.8	304.1	304.4	304.7	304.5	304.4
117.5°	343.8	344.0	344.3	344.6	344.9	345.2	345.4	345.7	346.0	346.1	346.3
120°	371.0	371.8	372.6	373.4	373.8	374.0	374.2	374.3	374.4	374.4	374.4
122.5°	399.6	399.8	400.1	400.4	400.7	401.1	401.5	401.9	402.3	402.2	402.1
125°	439.5	440.4	441.4	442.3	442.8	443.0	443.2	443.3	443.4	443.2	442.8
127.5°	481.0	481.4	482.0	482.5	482.9	483.0	483.2	483.5	483.7	483.5	483.3
130°	506.3	507.1	507.8	508.6	509.2	509.4	509.8	510.1	510.4	510.2	510.1
132.5°	531.9	533.2	534.4	535.7	536.3	536.3	536.2	536.1	536.1	535.9	535.7
135°	571.3	572.2	573.2	574.1	574.6	574.8	575.0	575.1	575.2	575.2	575.2
137.5°	608.7	609.6	610.5	611.4	612.0	612.3	612.6	613.0	613.3	613.5	613.7
140°	632.5	633.3	634.1	634.8	635.4	635.9	636.4	636.9	637.3	637.7	637.9
142.5°	656.4	657.0	657.6	658.4	659.0	659.5	660.1	660.7	661.3	661.5	661.6
145°	691.6	692.2	692.9	693.5	694.0	694.5	694.9	695.4	695.9	695.9	695.9
147.5°	724.0	724.3	724.7	725.0	725.3	725.8	726.1	726.5	726.8	727.2	727.5
150°	745.2	745.1	744.9	744.8	745.0	745.6	746.3	746.9	747.5	747.5	747.5
152.5°	763.5	763.7	763.9	764.1	764.4	764.6	764.8	765.1	765.4	765.7	766.1
155°	790.7	790.7	790.7	790.7	790.8	790.9	791.1	791.2	791.4	792.0	792.6
157.5°	814.9	814.6	814.2	813.9	813.8	814.0	814.1	814.2	814.4	815.0	815.6
160°	829.3	828.8	828.4	827.9	827.8	827.9	828.0	828.2	828.4	829.0	829.6
162.5°	842.2	841.9	841.6	841.2	841.1	841.1	841.2	841.2	841.2	842.0	842.7
165°	859.4	859.2	858.8	858.5	858.4	858.5	858.7	858.9	859.1	859.7	860.3
167.5°	873.6	873.0	872.4	871.7	871.5	871.5	871.5	871.5	871.5	872.4	873.3
170°	881.5	880.8	880.2	879.6	879.2	879.2	879.2	879.2	879.2	880.2	881.1
172.5°	887.0	886.4	885.7	885.1	884.8	884.8	884.8	884.8	884.8	885.7	886.7
175°	893.3	892.7	892.1	891.4	891.1	891.1	891.1	891.1	891.1	892.1	893.0
177.5°	896.6	896.2	895.6	895.1	894.8	894.7	894.6	894.5	894.3	895.1	895.8
180°	896.0	896.0	896.0	896.0	896.0	896.0	896.0	896.0	896.0	896.0	896.0



TEST NUMBER: P333593-940

CATALOG NUMBER: S125RDIP-S1090D810U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2
2.5°	1530.2	1530.2	1538.4	1537.8	1543.2	1541.2	1542.2
5°	1644.8	1655.1	1664.1	1670.2	1679.2	1681.6	1680.3
7.5°	1763.8	1786.5	1797.6	1812.8	1815.5	1823.5	1822.7
10°	1837.5	1859.8	1876.6	1889.8	1896.4	1904.9	1905.5
12.5°	1895.2	1914.1	1929.0	1941.3	1949.4	1952.0	1953.6
15°	1940.4	1961.4	1978.9	1996.4	2006.6	2014.4	2018.7
17.5°	1985.8	2018.4	2049.2	2072.9	2087.1	2099.2	2099.0
20°	2021.1	2058.3	2096.9	2124.0	2151.6	2163.6	2165.4
22.5°	2058.6	2115.7	2165.3	2207.3	2243.5	2256.1	2260.8
25°	2136.5	2211.2	2287.7	2346.6	2388.7	2413.4	2417.1
27.5°	2230.8	2331.8	2412.3	2466.7	2501.7	2520.0	2523.9
30°	2297.3	2390.6	2462.8	2503.7	2520.0	2522.4	2513.4
32.5°	2327.1	2396.8	2425.7	2423.3	2391.4	2370.3	2362.1
35°	2290.6	2276.2	2205.8	2121.6	2057.2	2016.2	2005.4
37.5°	2084.6	1960.0	1830.5	1703.2	1635.4	1600.9	1541.7
40°	1881.4	1703.9	1569.1	1461.9	1385.5	1324.1	1309.7
42.5°	1652.3	1468.9	1334.1	1242.3	1181.3	1139.2	1120.9
45°	1327.7	1170.0	1058.6	988.3	941.3	910.6	896.8
47.5°	1061.9	939.9	858.7	806.6	770.9	744.1	736.6
50°	916.1	818.5	749.9	706.0	678.9	658.4	650.0
52.5°	795.7	716.9	664.2	627.9	602.4	589.6	582.6
55°	656.7	588.6	550.7	521.8	507.4	497.1	492.3
57.5°	537.0	487.9	460.2	440.2	426.9	420.4	417.9
60°	470.0	431.5	406.3	390.6	381.6	373.2	370.8
62.5°	410.8	380.5	361.0	347.2	338.2	334.7	333.1
65°	331.0	311.1	296.7	288.3	281.1	279.8	279.3
67.5°	263.1	251.5	243.9	235.1	232.6	228.4	227.5
70°	225.1	217.3	208.2	205.3	202.2	198.0	198.6
72.5°	190.9	183.1	176.9	173.0	171.9	170.0	171.7
75°	139.6	137.2	134.8	131.8	130.6	130.6	130.0
77.5°	99.7	97.6	95.0	93.2	92.8	90.2	91.2
80°	72.2	69.2	68.0	68.6	66.8	66.2	66.2
82.5°	53.4	52.3	51.2	51.3	50.9	50.3	50.8
85°	29.5	28.9	28.9	28.3	28.3	27.6	27.6
87.5°	13.3	13.9	13.1	12.7	12.8	13.4	13.9
90°	13.5	14.3	14.9	15.3	15.8	16.2	16.8
92.5°	29.9	30.9	31.6	31.9	32.2	32.5	32.9
95°	57.0	58.1	58.8	59.0	59.4	59.7	59.9
97.5°	88.5	89.6	90.2	90.3	90.5	90.8	91.0
100°	110.8	112.3	113.2	113.4	113.7	114.0	114.3
102.5°	133.6	135.1	136.1	136.5	136.9	137.3	137.8
105°	169.4	170.4	171.0	171.6	172.0	172.5	172.9
107.5°	208.3	208.8	209.0	209.0	208.9	208.9	208.9
110°	235.7	236.1	236.3	236.1	235.9	235.9	235.7



TEST NUMBER: P333593-940

CATALOG NUMBER: S125RDIP-S1090D810U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	262.8	263.1	263.1	262.7	262.4	262.2	261.9
115°	304.3	304.1	303.9	303.8	303.6	303.4	303.4
117.5°	346.3	346.5	346.3	345.6	345.0	344.4	343.8
120°	374.4	374.4	374.2	373.5	372.9	372.3	371.7
122.5°	402.0	401.8	401.5	401.0	400.6	400.0	399.6
125°	442.6	442.2	442.0	441.8	441.7	441.6	441.4
127.5°	483.1	483.0	482.8	482.5	482.1	481.9	481.5
130°	510.0	509.8	509.5	509.3	508.9	508.6	508.3
132.5°	535.6	535.5	535.1	534.8	534.3	533.9	533.4
135°	575.2	575.2	575.0	574.4	573.7	573.1	572.5
137.5°	613.9	614.0	613.8	613.0	612.2	611.4	610.6
140°	638.2	638.6	638.3	637.6	636.8	636.0	635.3
142.5°	661.8	662.0	661.7	660.9	660.2	659.4	658.6
145°	695.9	695.9	695.6	695.2	694.7	694.3	693.8
147.5°	728.0	728.3	728.0	726.9	725.9	724.9	723.8
150°	747.5	747.5	747.3	747.0	746.7	746.4	746.1
152.5°	766.4	766.8	766.7	766.2	765.6	765.1	764.5
155°	793.3	793.9	793.8	793.0	792.3	791.5	790.7
157.5°	816.3	816.9	816.7	815.6	814.7	813.6	812.6
160°	830.2	830.8	830.8	830.0	829.2	828.4	827.7
162.5°	843.5	844.2	844.1	843.2	842.3	841.4	840.5
165°	860.9	861.5	861.4	860.4	859.5	858.5	857.6
167.5°	874.2	875.2	875.1	874.2	873.3	872.3	871.3
170°	882.1	883.0	882.9	881.8	880.7	879.7	878.6
172.5°	887.6	888.6	888.6	887.6	886.6	885.6	884.7
175°	893.9	894.8	894.7	893.7	892.6	891.5	890.5
177.5°	896.5	897.3	897.2	896.3	895.5	894.7	893.8
180°	896.0	896.0	896.0	896.0	896.0	896.0	896.0

(END OF REPORT)