

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331366-930

Luminaire Tested: **SA2XXDIP-C675D1080U930-4F0-1E-UDD-A**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331366-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C675D1080U930-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1080 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5902.3 lumens
Efficiency: N/A
Efficacy: 103.7 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 56.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331366-930
CATALOG NUMBER: SA2XXDIP-C675D1080U930-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331366-930

CATALOG NUMBER: SA2XXDIP-C675D1080U930-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	47	47	47	41				41
1	96	92	88	85	87	84	81	78	69	67	65	55	54	52	42	42	41	35				35
2	88	81	75	70	80	74	69	65	61	57	54	49	46	44	38	36	35	30				30
3	80	71	64	59	73	65	59	54	54	50	46	44	41	38	34	32	30	26				26
4	74	63	56	50	67	58	51	46	48	43	40	39	36	33	31	28	26	22				22
5	68	57	49	43	61	52	45	40	43	38	34	35	32	29	28	25	23	20				20
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	25	23	21	18				18
7	58	46	38	33	53	42	36	31	36	30	27	29	25	22	23	20	18	16				16
8	54	42	34	29	49	39	32	27	32	27	24	27	23	20	21	19	17	14				14
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	20	17	15	13				13
10	47	35	28	23	43	32	26	22	27	23	19	23	19	16	18	16	14	12				12

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	17486	17486	17486	17486
5°	19603	17598	15595	17598
10°	22463	17454	13496	17454
15°	24849	17135	11925	17135
20°	24471	16790	10869	16790
25°	22066	16335	10203	16335
30°	18233	15605	9715	15605
35°	13291	14840	9368	14840
40°	10614	13940	9177	13940
45°	9275	12896	8914	12896
50°	8719	11886	8741	11886
55°	8037	10860	8504	10860
60°	7363	9771	8147	9771
65°	6709	8795	7790	8795
70°	6090	7841	7270	7841
75°	5402	6775	6438	6775
80°	4649	5607	5188	5607
85°	4168	4168	3075	4168



TEST NUMBER: P331366-930

CATALOG NUMBER: SA2XXDIP-C675D1080U930-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	103.1	1.7
10°-20°	299.8	5.1
20°-30°	435.1	7.4
30°-40°	459.2	7.8
40°-50°	406.6	6.9
50°-60°	324.5	5.5
60°-70°	220.5	3.7
70°-80°	113.1	1.9
80°-90°	30.2	0.5
90°-100°	40.0	0.7
100°-110°	146.5	2.5
110°-120°	391.7	6.6
120°-130°	646.5	11.0
130°-140°	687.6	11.6
140°-150°	639.1	10.8
150°-160°	513.8	8.7
160°-170°	331.1	5.6
170°-180°	114.0	1.9
0°-30°	838.1	14.2
0°-40°	1297.3	22.0
0°-60°	2028.3	34.4
0°-90°	2392.1	40.5
90°-120°	578.1	9.8
90°-150°	2551.3	43.2
90°-180°	3510.0	59.5
0°-180°	5902.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1083	1083	1083	1083	1083	
5°	1210	1086	962	1086	1210	121
15°	1487	1025	713	1025	1487	410
25°	1239	917	573	917	1239	560
35°	674	753	475	753	674	439
45°	406	565	390	565	406	319
55°	286	386	302	386	286	256
65°	176	230	204	230	176	175
75°	87	109	103	109	87	93
85°	22	22	17	22	22	25
90°	23	1	23	1	23	11
95°	37	56	37	56	37	35
105°	66	264	66	264	66	68
115°	71	498	71	498	71	178
125°	741	705	741	705	741	641
135°	900	872	900	872	900	694
145°	1027	1012	1027	1012	1027	642
155°	1115	1114	1115	1114	1115	514
165°	1171	1174	1171	1174	1171	331
175°	1193	1200	1193	1200	1193	114
180°	1198	1198	1198	1198	1198	



TEST NUMBER: P331366-930

CATALOG NUMBER: SA2XXDIP-C675D1080U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0
2.5°	1132.9	1133.2	1133.9	1128.5	1127.9	1127.9	1123.2	1119.2	1114.6	1108.2	1108.9
5°	1209.5	1214.1	1215.7	1210.7	1203.2	1202.4	1195.3	1183.7	1172.8	1164.1	1157.9
7.5°	1300.9	1302.7	1298.6	1292.0	1286.5	1276.5	1263.3	1250.4	1232.3	1215.8	1203.5
10°	1370.1	1372.6	1365.5	1356.0	1348.1	1336.4	1317.3	1297.7	1274.0	1251.1	1232.7
12.5°	1422.7	1428.9	1419.8	1418.5	1405.0	1389.0	1366.2	1356.3	1322.9	1291.0	1271.4
15°	1486.6	1486.2	1487.1	1479.2	1469.2	1466.6	1442.5	1416.3	1369.3	1350.5	1318.1
17.5°	1468.2	1474.5	1477.4	1477.3	1477.1	1475.5	1467.8	1451.2	1427.7	1397.3	1359.8
20°	1424.2	1432.6	1433.8	1443.4	1448.8	1455.9	1458.7	1454.2	1439.7	1414.2	1381.8
22.5°	1356.3	1358.6	1362.5	1377.4	1389.2	1406.9	1416.2	1431.6	1426.0	1413.6	1386.4
25°	1238.6	1234.4	1249.0	1256.5	1283.5	1311.8	1332.3	1354.7	1374.7	1386.7	1378.8
27.5°	1097.2	1091.0	1112.8	1132.7	1154.7	1185.4	1217.2	1254.7	1285.9	1324.9	1338.3
30°	978.0	981.8	1002.7	1023.9	1057.1	1100.4	1136.2	1177.5	1222.0	1265.7	1296.0
32.5°	849.5	864.0	877.1	909.6	938.9	987.2	1039.7	1091.2	1146.7	1196.4	1243.4
35°	674.3	690.9	709.2	733.0	774.1	822.0	873.2	942.6	1018.5	1086.3	1142.1
37.5°	567.5	564.8	575.4	592.5	625.9	664.5	723.4	792.1	881.3	961.0	1039.7
40°	503.6	501.9	509.4	525.2	550.7	578.9	630.6	690.9	773.7	871.1	964.7
42.5°	459.7	460.6	464.8	476.0	493.3	516.7	555.3	606.7	682.5	774.2	874.8
45°	406.2	409.1	413.7	419.1	429.1	448.3	469.9	506.5	566.5	643.0	742.1
47.5°	367.8	367.9	372.5	377.2	383.2	394.0	411.6	434.6	476.9	539.2	624.4
50°	347.1	344.2	347.6	351.2	357.5	365.0	376.7	398.3	426.6	477.0	548.1
52.5°	321.8	321.9	324.9	326.3	331.9	339.3	350.0	365.0	390.6	430.0	488.5
55°	285.5	287.6	289.3	291.7	296.8	302.1	310.5	320.5	340.5	370.0	413.3
57.5°	251.4	252.0	253.7	258.4	261.6	266.6	274.5	283.6	296.6	318.5	351.0
60°	228.0	228.0	231.4	233.5	237.7	242.6	248.9	257.6	269.3	287.1	313.4
62.5°	206.8	206.4	207.7	211.2	214.3	219.0	225.3	232.7	243.6	259.5	281.1
65°	175.6	174.8	177.3	178.1	181.5	186.1	191.0	198.9	207.7	219.3	238.5
67.5°	145.7	146.7	148.0	149.6	151.4	156.2	159.6	165.2	172.5	182.2	195.2
70°	129.0	129.0	129.0	130.3	132.7	135.3	138.6	143.2	150.3	158.6	170.2
72.5°	110.4	111.7	113.0	112.3	115.4	116.9	120.9	123.5	130.3	135.6	145.9
75°	86.6	86.6	86.6	88.6	89.9	91.2	93.7	96.1	99.5	106.2	111.5
77.5°	64.6	64.4	64.8	65.3	66.7	68.2	68.9	71.2	74.3	77.3	81.9
80°	50.0	50.8	51.2	52.0	52.0	52.8	53.2	56.2	58.3	60.3	63.3
82.5°	38.6	38.8	38.9	39.1	39.4	39.9	40.9	41.9	42.6	44.4	46.6
85°	22.5	22.1	22.1	22.9	22.5	22.5	23.3	24.1	24.1	24.5	25.8
87.5°	13.4	13.3	13.5	13.1	13.0	13.2	13.0	12.5	12.6	12.8	12.8
90°	23.4	23.0	22.7	22.3	21.9	21.2	20.2	19.2	18.3	17.4	15.8
92.5°	23.4	23.2	22.9	22.7	22.5	22.1	21.6	21.1	20.6	20.1	19.3
95°	37.3	37.4	37.7	37.8	38.1	37.7	36.7	35.7	34.7	33.8	32.4
97.5°	49.7	49.5	49.3	49.1	48.8	48.3	47.5	46.8	46.0	45.2	42.2
100°	58.0	57.7	57.3	56.9	56.5	55.6	54.1	52.5	51.0	49.4	46.1
102.5°	62.2	61.7	61.1	60.6	60.1	58.8	56.8	54.8	52.8	50.8	78.2
105°	65.9	65.1	64.3	63.6	62.8	61.3	59.2	57.1	55.0	52.8	105.4
107.5°	67.8	67.0	66.2	65.5	64.7	65.4	67.5	69.7	71.8	74.0	137.1
110°	68.5	67.7	66.9	66.1	65.4	74.6	93.9	113.2	132.4	151.6	207.3



TEST NUMBER: P331366-930

CATALOG NUMBER: SA2XXDIP-C675D1080U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	69.1	68.6	67.9	67.3	66.7	101.5	171.8	242.1	312.3	382.5	396.3
115°	71.1	85.0	98.8	112.7	126.5	178.1	267.3	356.4	445.6	534.8	529.9
117.5°	290.2	335.7	381.3	426.9	472.5	506.1	527.6	549.2	570.7	592.3	589.0
120°	528.7	554.6	580.7	606.7	632.7	644.6	642.2	639.9	637.6	635.3	631.9
122.5°	659.7	664.8	669.8	674.9	679.9	681.8	680.4	679.0	677.6	676.2	672.5
125°	741.0	740.5	739.9	739.3	738.7	737.8	736.4	735.1	733.7	732.4	728.7
127.5°	792.3	792.2	792.1	792.0	791.9	790.8	788.9	786.9	785.0	783.0	780.2
130°	824.3	824.4	824.6	824.8	825.0	824.0	821.9	819.8	817.7	815.5	813.4
132.5°	855.4	855.7	855.8	856.0	856.2	855.4	853.6	851.7	849.9	848.2	846.0
135°	900.5	900.9	901.2	901.6	902.0	901.2	899.4	897.4	895.5	893.6	891.9
137.5°	941.6	942.2	942.9	943.5	944.2	943.5	941.7	939.8	937.9	936.0	934.1
140°	967.3	968.2	969.1	970.1	971.1	970.7	969.0	967.3	965.5	963.8	961.6
142.5°	992.2	993.2	994.1	995.1	996.1	995.7	994.2	992.5	991.0	989.4	987.0
145°	1027.0	1028.0	1029.0	1030.0	1030.9	1030.7	1029.3	1028.0	1026.6	1025.3	1022.1
147.5°	1057.7	1058.5	1059.3	1060.1	1060.9	1060.9	1059.9	1058.8	1057.9	1056.9	1053.6
150°	1076.4	1077.4	1078.4	1079.3	1080.3	1080.2	1079.0	1077.9	1076.8	1075.5	1072.5
152.5°	1092.4	1093.6	1094.9	1096.2	1097.5	1097.6	1096.4	1095.2	1094.1	1092.9	1090.0
155°	1114.6	1116.1	1117.7	1119.2	1120.7	1121.0	1119.8	1118.6	1117.4	1116.3	1114.0
157.5°	1134.8	1136.4	1137.8	1139.4	1140.8	1140.9	1139.6	1138.3	1137.0	1135.7	1134.1
160°	1146.6	1148.0	1149.3	1150.7	1152.0	1152.1	1151.0	1149.8	1148.7	1147.5	1146.4
162.5°	1156.3	1158.0	1159.7	1161.3	1162.9	1163.2	1161.8	1160.5	1159.2	1157.9	1156.9
165°	1170.9	1172.2	1173.6	1174.9	1176.3	1176.3	1174.9	1173.6	1172.2	1170.9	1170.4
167.5°	1180.1	1181.9	1183.6	1185.3	1187.0	1187.2	1185.9	1184.5	1183.2	1181.9	1181.3
170°	1185.6	1187.4	1189.1	1190.8	1192.5	1192.8	1191.4	1190.1	1188.7	1187.4	1187.0
172.5°	1189.8	1191.6	1193.3	1195.0	1196.8	1196.9	1195.6	1194.3	1192.9	1191.6	1191.2
175°	1193.4	1195.4	1197.3	1199.2	1201.2	1201.4	1200.1	1198.7	1197.4	1196.0	1195.6
177.5°	1195.7	1197.1	1198.5	1199.9	1201.3	1201.4	1200.3	1199.2	1198.2	1197.1	1196.9
180°	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8



TEST NUMBER: P331366-930

CATALOG NUMBER: SA2XXDIP-C675D1080U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0
2.5°	1111.3	1108.6	1106.9	1100.9	1095.6	1090.3	1088.6	1089.2	1082.0	1075.0	1072.0
5°	1154.5	1146.2	1138.3	1127.1	1113.8	1099.2	1091.7	1085.8	1071.3	1055.5	1046.4
7.5°	1193.4	1181.5	1166.2	1145.0	1125.7	1102.8	1088.2	1075.3	1053.9	1031.7	1018.0
10°	1217.0	1200.7	1181.1	1155.4	1131.6	1103.8	1084.2	1064.6	1039.7	1013.0	996.4
12.5°	1237.3	1215.4	1196.1	1163.0	1135.0	1100.1	1076.8	1049.3	1023.0	991.4	975.1
15°	1285.6	1245.3	1208.6	1171.2	1136.6	1087.9	1062.2	1025.1	990.5	951.5	932.7
17.5°	1323.0	1277.7	1219.9	1172.3	1132.0	1078.2	1040.2	995.9	955.0	910.3	884.8
20°	1344.3	1292.2	1230.3	1173.7	1125.4	1063.8	1022.6	977.2	929.4	879.0	851.5
22.5°	1357.0	1302.3	1241.0	1168.7	1112.1	1052.1	1000.3	950.6	902.0	847.7	818.9
25°	1361.0	1311.0	1246.1	1164.5	1095.4	1027.6	965.2	916.9	858.2	807.4	765.4
27.5°	1341.2	1305.4	1242.9	1156.7	1076.2	996.9	927.3	872.6	810.7	755.5	713.3
30°	1316.9	1296.0	1235.3	1148.7	1060.9	975.6	898.9	837.0	775.3	719.6	676.3
32.5°	1279.2	1274.7	1221.3	1137.3	1044.6	948.6	869.4	806.7	738.4	683.6	642.4
35°	1205.3	1225.3	1191.6	1112.1	1013.8	910.2	824.5	752.9	682.2	629.7	591.0
37.5°	1106.3	1155.8	1147.0	1075.1	972.4	868.5	773.8	699.0	631.5	578.6	540.6
40°	1038.0	1101.2	1110.4	1046.8	943.1	836.2	735.8	661.4	595.6	547.3	509.0
42.5°	964.7	1038.7	1063.8	1012.8	911.1	802.2	701.9	624.7	559.6	512.7	478.7
45°	842.0	939.8	985.1	956.0	857.8	746.2	643.0	564.8	505.6	461.5	435.4
47.5°	727.2	834.1	895.0	884.8	798.4	687.9	586.0	510.9	453.3	418.1	394.6
50°	646.0	755.8	829.5	832.8	755.8	646.4	544.0	473.2	420.4	387.5	368.4
52.5°	575.4	680.2	760.6	778.2	708.2	603.1	506.4	435.9	389.4	359.1	342.0
55°	483.2	571.9	660.9	693.4	637.2	537.3	447.8	385.8	342.1	321.3	306.3
57.5°	401.7	475.6	557.9	593.8	559.1	473.6	389.7	335.9	300.4	282.2	270.7
60°	358.7	417.0	490.2	533.1	503.2	427.1	353.8	302.6	273.5	257.2	246.4
62.5°	318.8	370.4	432.4	471.6	455.3	383.4	317.8	272.6	247.4	232.2	224.5
65°	263.0	303.9	351.7	387.9	377.1	322.5	268.9	230.2	210.2	198.1	191.8
67.5°	216.6	246.1	279.2	311.0	302.2	263.6	220.5	190.4	175.5	165.1	161.3
70°	187.3	209.8	239.3	264.7	257.6	226.0	191.8	166.1	153.2	144.4	140.6
72.5°	159.3	177.8	200.3	221.1	216.3	190.0	161.6	142.1	132.2	124.1	121.0
75°	120.3	134.4	148.1	161.9	160.6	140.2	123.6	108.6	100.7	94.5	93.2
77.5°	88.8	96.7	106.1	114.2	111.9	100.3	87.2	78.7	72.8	68.6	68.0
80°	67.8	72.4	79.1	84.9	82.0	77.0	66.6	60.3	56.2	52.0	50.4
82.5°	49.2	53.8	57.8	60.9	58.7	54.1	47.6	43.4	40.8	38.1	37.3
85°	25.8	28.3	30.0	30.8	30.0	27.1	24.1	22.5	20.4	19.2	18.8
87.5°	12.8	12.6	12.2	12.6	11.1	10.7	8.9	7.5	7.6	7.7	7.4
90°	14.3	12.7	11.2	9.4	7.3	5.1	3.0	0.9	3.0	5.1	7.3
92.5°	18.6	17.8	17.0	16.7	17.0	17.1	17.3	17.5	17.3	17.1	17.0
95°	31.1	29.8	28.4	30.9	37.3	43.6	50.0	56.3	50.0	43.6	37.3
97.5°	39.0	35.9	32.8	40.2	58.0	76.0	93.9	111.8	93.9	76.0	58.0
100°	42.9	39.5	36.3	47.9	74.3	100.6	127.0	153.4	127.0	100.6	74.3
102.5°	105.6	133.0	160.4	176.8	182.4	188.0	193.6	199.2	193.6	188.0	182.4
105°	158.0	210.6	263.2	286.6	280.8	275.0	269.3	263.5	269.3	275.0	280.8
107.5°	200.2	263.2	326.3	355.5	350.7	346.1	341.4	336.8	341.4	346.1	350.7
110°	263.0	318.6	374.3	400.1	396.1	392.1	388.0	383.9	388.0	392.1	396.1



TEST NUMBER: P331366-930

CATALOG NUMBER: SA2XXDIP-C675D1080U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	410.1	423.8	437.6	442.6	439.0	435.5	431.9	428.4	431.9	435.5	439.0
115°	525.1	520.3	515.5	511.4	508.2	504.9	501.7	498.4	501.7	504.9	508.2
117.5°	585.7	582.4	579.0	575.6	571.9	568.3	564.6	560.9	564.6	568.3	571.9
120°	628.4	624.9	621.4	618.2	615.4	612.5	609.6	606.7	609.6	612.5	615.4
122.5°	668.6	664.9	661.1	657.7	654.7	651.6	648.6	645.6	648.6	651.6	654.7
125°	725.0	721.4	717.7	714.6	712.2	709.6	707.1	704.7	707.1	709.6	712.2
127.5°	777.5	774.8	772.0	769.3	766.5	763.8	761.0	758.2	761.0	763.8	766.5
130°	811.3	809.2	807.1	804.5	801.4	798.3	795.2	792.1	795.2	798.3	801.4
132.5°	843.9	841.8	839.7	837.3	834.7	832.1	829.5	826.8	829.5	832.1	834.7
135°	890.1	888.4	886.6	884.2	881.2	878.1	875.0	871.9	875.0	878.1	881.2
137.5°	932.1	930.2	928.1	926.1	924.0	921.8	919.7	917.5	919.7	921.8	924.0
140°	959.5	957.4	955.3	953.5	951.9	950.4	948.8	947.3	948.8	950.4	951.9
142.5°	984.6	982.1	979.7	977.8	976.4	975.0	973.6	972.2	973.6	975.0	976.4
145°	1018.7	1015.5	1012.2	1010.6	1010.9	1011.1	1011.2	1011.5	1011.2	1011.1	1010.9
147.5°	1050.4	1047.2	1043.9	1042.7	1043.4	1044.2	1044.9	1045.6	1044.9	1044.2	1043.4
150°	1069.4	1066.3	1063.2	1062.4	1063.7	1065.1	1066.4	1067.8	1066.4	1065.1	1063.7
152.5°	1087.0	1084.1	1081.2	1080.5	1082.0	1083.5	1085.0	1086.5	1085.0	1083.5	1082.0
155°	1111.7	1109.4	1107.1	1106.8	1108.5	1110.3	1112.0	1113.7	1112.0	1110.3	1108.5
157.5°	1132.5	1130.9	1129.3	1129.2	1130.7	1132.1	1133.6	1135.1	1133.6	1132.1	1130.7
160°	1145.2	1144.0	1142.9	1142.9	1144.0	1145.2	1146.4	1147.5	1146.4	1145.2	1144.0
162.5°	1155.9	1154.9	1153.9	1154.0	1155.1	1156.3	1157.5	1158.6	1157.5	1156.3	1155.1
165°	1169.8	1169.1	1168.6	1168.9	1170.0	1171.2	1172.3	1173.5	1172.3	1171.2	1170.0
167.5°	1180.7	1180.2	1179.7	1180.0	1181.1	1182.3	1183.5	1184.6	1183.5	1182.3	1181.1
170°	1186.6	1186.3	1185.9	1186.3	1187.4	1188.5	1189.7	1190.8	1189.7	1188.5	1187.4
172.5°	1190.7	1190.4	1190.0	1190.4	1191.6	1192.7	1193.8	1195.0	1193.8	1192.7	1191.6
175°	1195.3	1194.9	1194.5	1195.0	1196.4	1197.7	1199.1	1200.4	1199.1	1197.7	1196.4
177.5°	1196.8	1196.6	1196.5	1196.9	1198.0	1199.1	1200.2	1201.3	1200.2	1199.1	1198.0
180°	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8



TEST NUMBER: P331366-930

CATALOG NUMBER: SA2XXDIP-C675D1080U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0
2.5°	1068.6	1066.7	1059.6	1056.0	1049.9	1044.3	1040.6	1042.4	1043.7	1043.0	1042.0
5°	1038.0	1030.0	1018.0	1007.6	1000.1	986.3	980.6	977.6	975.2	972.2	969.3
7.5°	1001.5	989.0	971.8	956.9	942.9	925.9	916.2	910.3	904.3	897.7	891.9
10°	975.6	958.1	939.8	918.9	902.3	886.9	873.2	864.1	855.7	847.8	842.0
12.5°	948.3	928.1	905.5	877.0	858.7	836.7	834.5	818.4	805.4	800.5	793.7
15°	904.8	876.5	847.8	814.1	799.5	779.5	767.0	754.6	743.3	735.4	733.4
17.5°	855.4	818.8	790.3	766.1	742.2	721.7	710.2	700.2	691.0	680.4	679.0
20°	817.8	786.2	755.0	733.8	709.2	688.4	674.3	664.2	656.3	650.1	644.7
22.5°	782.2	747.5	719.0	695.8	671.6	654.8	643.6	634.0	627.4	620.4	615.4
25°	725.0	698.0	666.8	640.5	620.5	609.8	600.5	592.2	588.1	583.5	577.7
27.5°	675.0	644.9	615.7	595.4	577.9	568.3	561.7	556.1	552.2	549.5	546.3
30°	639.7	609.3	586.4	566.5	551.9	542.3	538.2	534.8	530.3	528.6	526.9
32.5°	605.8	578.4	558.8	541.4	527.6	521.3	517.5	514.5	510.9	509.2	505.9
35°	557.7	534.8	515.7	506.1	494.9	489.4	486.6	482.3	479.1	477.4	477.0
37.5°	512.5	492.6	480.0	467.7	463.0	459.7	455.7	452.8	451.8	451.6	451.2
40°	483.2	467.0	455.8	445.7	443.7	438.6	435.4	432.8	432.8	433.3	432.8
42.5°	456.6	442.0	432.1	423.5	421.0	418.0	414.7	414.5	415.2	416.6	415.2
45°	416.2	405.8	398.7	394.5	390.0	387.0	386.6	387.9	388.3	388.7	390.0
47.5°	379.0	372.2	365.7	361.2	359.1	358.7	358.2	360.4	362.3	363.1	365.0
50°	357.1	349.2	343.8	340.9	339.2	338.3	339.2	341.7	343.3	345.4	346.7
52.5°	332.5	326.9	323.1	320.9	320.2	320.7	320.9	323.8	326.4	327.1	327.8
55°	298.4	294.2	293.4	289.7	291.3	290.9	293.0	294.6	297.2	299.6	300.1
57.5°	264.5	261.1	258.9	259.2	259.7	261.5	263.3	266.2	268.9	271.5	271.7
60°	241.8	240.1	238.9	238.9	239.7	242.2	244.3	247.2	248.9	250.5	251.8
62.5°	221.2	219.5	218.3	218.9	221.1	222.6	225.0	226.6	228.2	229.9	230.5
65°	188.5	187.7	189.0	189.8	190.2	192.2	195.2	196.4	198.1	198.9	201.9
67.5°	158.5	158.7	158.5	159.6	162.1	162.6	165.3	168.2	168.5	170.2	172.0
70°	138.2	139.0	139.8	140.6	142.8	143.6	145.7	146.9	148.5	149.9	151.1
72.5°	119.5	119.7	120.5	120.3	122.1	123.9	125.7	126.9	128.6	130.2	131.4
75°	92.0	92.0	92.8	93.2	95.3	97.4	96.9	97.8	99.5	101.1	102.0
77.5°	67.2	66.3	67.2	67.6	68.2	70.0	70.4	71.5	73.4	72.8	73.8
80°	51.2	50.0	51.2	51.6	51.6	53.7	53.7	54.5	55.8	54.5	55.8
82.5°	36.5	36.0	36.9	36.9	37.6	37.7	38.4	38.6	39.8	39.2	39.8
85°	18.3	17.9	18.3	17.9	18.3	18.8	18.8	18.3	18.3	19.2	17.9
87.5°	7.5	7.6	7.5	7.8	7.8	7.8	7.7	7.8	8.1	7.6	7.7
90°	9.4	11.2	12.7	14.3	15.8	17.4	18.3	19.2	20.2	21.2	21.9
92.5°	16.7	17.0	17.8	18.6	19.3	20.1	20.6	21.1	21.6	22.1	22.5
95°	30.9	28.4	29.8	31.1	32.4	33.8	34.7	35.7	36.7	37.7	38.1
97.5°	40.2	32.8	35.9	39.0	42.2	45.2	46.0	46.8	47.5	48.3	48.8
100°	47.9	36.3	39.5	42.9	46.1	49.4	51.0	52.5	54.1	55.6	56.5
102.5°	176.8	160.4	133.0	105.6	78.2	50.8	52.8	54.8	56.8	58.8	60.1
105°	286.6	263.2	210.6	158.0	105.4	52.8	55.0	57.1	59.2	61.3	62.8
107.5°	355.5	326.3	263.2	200.2	137.1	74.0	71.8	69.7	67.5	65.4	64.7
110°	400.1	374.3	318.6	263.0	207.3	151.6	132.4	113.2	93.9	74.6	65.4



TEST NUMBER: P331366-930

CATALOG NUMBER: SA2XXDIP-C675D1080U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	442.6	437.6	423.8	410.1	396.3	382.5	312.3	242.1	171.8	101.5	66.7
115°	511.4	515.5	520.3	525.1	529.9	534.8	445.6	356.4	267.3	178.1	126.5
117.5°	575.6	579.0	582.4	585.7	589.0	592.3	570.7	549.2	527.6	506.1	472.5
120°	618.2	621.4	624.9	628.4	631.9	635.3	637.6	639.9	642.2	644.6	632.7
122.5°	657.7	661.1	664.9	668.6	672.5	676.2	677.6	679.0	680.4	681.8	679.9
125°	714.6	717.7	721.4	725.0	728.7	732.4	733.7	735.1	736.4	737.8	738.7
127.5°	769.3	772.0	774.8	777.5	780.2	783.0	785.0	786.9	788.9	790.8	791.9
130°	804.5	807.1	809.2	811.3	813.4	815.5	817.7	819.8	821.9	824.0	825.0
132.5°	837.3	839.7	841.8	843.9	846.0	848.2	849.9	851.7	853.6	855.4	856.2
135°	884.2	886.6	888.4	890.1	891.9	893.6	895.5	897.4	899.4	901.2	902.0
137.5°	926.1	928.1	930.2	932.1	934.1	936.0	937.9	939.8	941.7	943.5	944.2
140°	953.5	955.3	957.4	959.5	961.6	963.8	965.5	967.3	969.0	970.7	971.1
142.5°	977.8	979.7	982.1	984.6	987.0	989.4	991.0	992.5	994.2	995.7	996.1
145°	1010.6	1012.2	1015.5	1018.7	1022.1	1025.3	1026.6	1028.0	1029.3	1030.7	1030.9
147.5°	1042.7	1043.9	1047.2	1050.4	1053.6	1056.9	1057.9	1058.8	1059.9	1060.9	1060.9
150°	1062.4	1063.2	1066.3	1069.4	1072.5	1075.5	1076.8	1077.9	1079.0	1080.2	1080.3
152.5°	1080.5	1081.2	1084.1	1087.0	1090.0	1092.9	1094.1	1095.2	1096.4	1097.6	1097.5
155°	1106.8	1107.1	1109.4	1111.7	1114.0	1116.3	1117.4	1118.6	1119.8	1121.0	1120.7
157.5°	1129.2	1129.3	1130.9	1132.5	1134.1	1135.7	1137.0	1138.3	1139.6	1140.9	1140.8
160°	1142.9	1142.9	1144.0	1145.2	1146.4	1147.5	1148.7	1149.8	1151.0	1152.1	1152.0
162.5°	1154.0	1153.9	1154.9	1155.9	1156.9	1157.9	1159.2	1160.5	1161.8	1163.2	1162.9
165°	1168.9	1168.6	1169.1	1169.8	1170.4	1170.9	1172.2	1173.6	1174.9	1176.3	1176.3
167.5°	1180.0	1179.7	1180.2	1180.7	1181.3	1181.9	1183.2	1184.5	1185.9	1187.2	1187.0
170°	1186.3	1185.9	1186.3	1186.6	1187.0	1187.4	1188.7	1190.1	1191.4	1192.8	1192.5
172.5°	1190.4	1190.0	1190.4	1190.7	1191.2	1191.6	1192.9	1194.3	1195.6	1196.9	1196.8
175°	1195.0	1194.5	1194.9	1195.3	1195.6	1196.0	1197.4	1198.7	1200.1	1201.4	1201.2
177.5°	1196.9	1196.5	1196.6	1196.8	1196.9	1197.1	1198.2	1199.2	1200.3	1201.4	1201.3
180°	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8



TEST NUMBER: P331366-930

CATALOG NUMBER: SA2XXDIP-C675D1080U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0
2.5°	1038.7	1038.0	1038.0	1035.0	1038.0	1038.0	1038.7	1042.0	1043.0	1043.7	1042.4
5°	963.5	962.2	960.2	962.2	960.2	962.2	963.5	969.3	972.2	975.2	977.6
7.5°	889.2	884.2	883.5	878.5	883.5	884.2	889.2	891.9	897.7	904.3	910.3
10°	834.9	831.5	831.1	823.2	831.1	831.5	834.9	842.0	847.8	855.7	864.1
12.5°	793.6	785.6	787.2	782.6	787.2	785.6	793.6	793.7	800.5	805.4	818.4
15°	722.1	722.1	720.4	713.4	720.4	722.1	722.1	733.4	735.4	743.3	754.6
17.5°	670.7	669.9	665.9	667.9	665.9	669.9	670.7	679.0	680.4	691.0	700.2
20°	640.1	637.6	632.6	632.6	632.6	637.6	640.1	644.7	650.1	656.3	664.2
22.5°	611.1	611.0	605.7	607.3	605.7	611.0	611.1	615.4	620.4	627.4	634.0
25°	577.2	574.0	571.4	572.7	571.4	574.0	577.2	577.7	583.5	588.1	592.2
27.5°	545.1	543.3	543.2	539.7	543.2	543.3	545.1	546.3	549.5	552.2	556.1
30°	526.5	522.4	523.2	521.1	523.2	522.4	526.5	526.9	528.6	530.3	534.8
32.5°	505.2	503.7	502.9	501.1	502.9	503.7	505.2	505.9	509.2	510.9	514.5
35°	476.1	476.5	474.5	475.3	474.5	476.5	476.1	477.0	477.4	479.1	482.3
37.5°	450.8	452.1	451.1	451.3	451.1	452.1	450.8	451.2	451.6	451.8	452.8
40°	434.1	434.1	434.1	435.4	434.1	434.1	434.1	432.8	433.3	432.8	432.8
42.5°	418.1	417.4	416.8	416.7	416.8	417.4	418.1	415.2	416.6	415.2	414.5
45°	390.8	392.1	392.5	390.4	392.5	392.1	390.8	390.0	388.7	388.3	387.9
47.5°	366.1	366.2	366.1	367.9	366.1	366.2	366.1	365.0	363.1	362.3	360.4
50°	348.8	348.0	348.8	348.0	348.8	348.0	348.8	346.7	345.4	343.3	341.7
52.5°	330.4	330.6	330.1	330.0	330.1	330.6	330.4	327.8	327.1	326.4	323.8
55°	301.7	302.6	302.1	302.1	302.1	302.6	301.7	300.1	299.6	297.2	294.6
57.5°	272.1	272.8	273.4	271.5	273.4	272.8	272.1	271.7	271.5	268.9	266.2
60°	251.4	253.5	253.1	252.3	253.1	253.5	251.4	251.8	250.5	248.9	247.2
62.5°	232.4	233.2	233.1	232.9	233.1	233.2	232.4	230.5	229.9	228.2	226.6
65°	203.1	203.9	202.7	203.9	202.7	203.9	203.1	201.9	198.9	198.1	196.4
67.5°	171.5	171.8	172.8	173.3	172.8	171.8	171.5	172.0	170.2	168.5	168.2
70°	151.9	151.5	152.7	154.0	152.7	151.5	151.9	151.1	149.9	148.5	146.9
72.5°	131.3	132.2	131.8	132.6	131.8	132.2	131.3	131.4	130.2	128.6	126.9
75°	101.1	102.4	102.0	103.2	102.0	102.4	101.1	102.0	101.1	99.5	97.8
77.5°	73.1	73.2	73.1	73.8	73.1	73.2	73.1	73.8	72.8	73.4	71.5
80°	55.8	55.0	54.1	55.8	54.1	55.0	55.8	55.8	54.5	55.8	54.5
82.5°	38.8	39.3	38.5	38.5	38.5	39.3	38.8	39.8	39.2	39.8	38.6
85°	17.9	17.4	16.6	16.6	16.6	17.4	17.9	17.9	19.2	18.3	18.3
87.5°	7.7	7.5	7.6	7.3	7.6	7.5	7.7	7.7	7.6	8.1	7.8
90°	22.3	22.7	23.0	23.4	23.0	22.7	22.3	21.9	21.2	20.2	19.2
92.5°	22.7	22.9	23.2	23.4	23.2	22.9	22.7	22.5	22.1	21.6	21.1
95°	37.8	37.7	37.4	37.3	37.4	37.7	37.8	38.1	37.7	36.7	35.7
97.5°	49.1	49.3	49.5	49.7	49.5	49.3	49.1	48.8	48.3	47.5	46.8
100°	56.9	57.3	57.7	58.0	57.7	57.3	56.9	56.5	55.6	54.1	52.5
102.5°	60.6	61.1	61.7	62.2	61.7	61.1	60.6	60.1	58.8	56.8	54.8
105°	63.6	64.3	65.1	65.9	65.1	64.3	63.6	62.8	61.3	59.2	57.1
107.5°	65.5	66.2	67.0	67.8	67.0	66.2	65.5	64.7	65.4	67.5	69.7
110°	66.1	66.9	67.7	68.5	67.7	66.9	66.1	65.4	74.6	93.9	113.2



TEST NUMBER: P331366-930

CATALOG NUMBER: SA2XXDIP-C675D1080U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	67.3	67.9	68.6	69.1	68.6	67.9	67.3	66.7	101.5	171.8	242.1
115°	112.7	98.8	85.0	71.1	85.0	98.8	112.7	126.5	178.1	267.3	356.4
117.5°	426.9	381.3	335.7	290.2	335.7	381.3	426.9	472.5	506.1	527.6	549.2
120°	606.7	580.7	554.6	528.7	554.6	580.7	606.7	632.7	644.6	642.2	639.9
122.5°	674.9	669.8	664.8	659.7	664.8	669.8	674.9	679.9	681.8	680.4	679.0
125°	739.3	739.9	740.5	741.0	740.5	739.9	739.3	738.7	737.8	736.4	735.1
127.5°	792.0	792.1	792.2	792.3	792.2	792.1	792.0	791.9	790.8	788.9	786.9
130°	824.8	824.6	824.4	824.3	824.4	824.6	824.8	825.0	824.0	821.9	819.8
132.5°	856.0	855.8	855.7	855.4	855.7	855.8	856.0	856.2	855.4	853.6	851.7
135°	901.6	901.2	900.9	900.5	900.9	901.2	901.6	902.0	901.2	899.4	897.4
137.5°	943.5	942.9	942.2	941.6	942.2	942.9	943.5	944.2	943.5	941.7	939.8
140°	970.1	969.1	968.2	967.3	968.2	969.1	970.1	971.1	970.7	969.0	967.3
142.5°	995.1	994.1	993.2	992.2	993.2	994.1	995.1	996.1	995.7	994.2	992.5
145°	1030.0	1029.0	1028.0	1027.0	1028.0	1029.0	1030.0	1030.9	1030.7	1029.3	1028.0
147.5°	1060.1	1059.3	1058.5	1057.7	1058.5	1059.3	1060.1	1060.9	1060.9	1059.9	1058.8
150°	1079.3	1078.4	1077.4	1076.4	1077.4	1078.4	1079.3	1080.3	1080.2	1079.0	1077.9
152.5°	1096.2	1094.9	1093.6	1092.4	1093.6	1094.9	1096.2	1097.5	1097.6	1096.4	1095.2
155°	1119.2	1117.7	1116.1	1114.6	1116.1	1117.7	1119.2	1120.7	1121.0	1119.8	1118.6
157.5°	1139.4	1137.8	1136.4	1134.8	1136.4	1137.8	1139.4	1140.8	1140.9	1139.6	1138.3
160°	1150.7	1149.3	1148.0	1146.6	1148.0	1149.3	1150.7	1152.0	1152.1	1151.0	1149.8
162.5°	1161.3	1159.7	1158.0	1156.3	1158.0	1159.7	1161.3	1162.9	1163.2	1161.8	1160.5
165°	1174.9	1173.6	1172.2	1170.9	1172.2	1173.6	1174.9	1176.3	1176.3	1174.9	1173.6
167.5°	1185.3	1183.6	1181.9	1180.1	1181.9	1183.6	1185.3	1187.0	1187.2	1185.9	1184.5
170°	1190.8	1189.1	1187.4	1185.6	1187.4	1189.1	1190.8	1192.5	1192.8	1191.4	1190.1
172.5°	1195.0	1193.3	1191.6	1189.8	1191.6	1193.3	1195.0	1196.8	1196.9	1195.6	1194.3
175°	1199.2	1197.3	1195.4	1193.4	1195.4	1197.3	1199.2	1201.2	1201.4	1200.1	1198.7
177.5°	1199.9	1198.5	1197.1	1195.7	1197.1	1198.5	1199.9	1201.3	1201.4	1200.3	1199.2
180°	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8



TEST NUMBER: P331366-930
 CATALOG NUMBER: SA2XXDIP-C675D1080U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0
2.5°	1040.6	1044.3	1049.9	1056.0	1059.6	1066.7	1068.6	1072.0	1075.0	1082.0	1089.2
5°	980.6	986.3	1000.1	1007.6	1018.0	1030.0	1038.0	1046.4	1055.5	1071.3	1085.8
7.5°	916.2	925.9	942.9	956.9	971.8	989.0	1001.5	1018.0	1031.7	1053.9	1075.3
10°	873.2	886.9	902.3	918.9	939.8	958.1	975.6	996.4	1013.0	1039.7	1064.6
12.5°	834.5	836.7	858.7	877.0	905.5	928.1	948.3	975.1	991.4	1023.0	1049.3
15°	767.0	779.5	799.5	814.1	847.8	876.5	904.8	932.7	951.5	990.5	1025.1
17.5°	710.2	721.7	742.2	766.1	790.3	818.8	855.4	884.8	910.3	955.0	995.9
20°	674.3	688.4	709.2	733.8	755.0	786.2	817.8	851.5	879.0	929.4	977.2
22.5°	643.6	654.8	671.6	695.8	719.0	747.5	782.2	818.9	847.7	902.0	950.6
25°	600.5	609.8	620.5	640.5	666.8	698.0	725.0	765.4	807.4	858.2	916.9
27.5°	561.7	568.3	577.9	595.4	615.7	644.9	675.0	713.3	755.5	810.7	872.6
30°	538.2	542.3	551.9	566.5	586.4	609.3	639.7	676.3	719.6	775.3	837.0
32.5°	517.5	521.3	527.6	541.4	558.8	578.4	605.8	642.4	683.6	738.4	806.7
35°	486.6	489.4	494.9	506.1	515.7	534.8	557.7	591.0	629.7	682.2	752.9
37.5°	455.7	459.7	463.0	467.7	480.0	492.6	512.5	540.6	578.6	631.5	699.0
40°	435.4	438.6	443.7	445.7	455.8	467.0	483.2	509.0	547.3	595.6	661.4
42.5°	414.7	418.0	421.0	423.5	432.1	442.0	456.6	478.7	512.7	559.6	624.7
45°	386.6	387.0	390.0	394.5	398.7	405.8	416.2	435.4	461.5	505.6	564.8
47.5°	358.2	358.7	359.1	361.2	365.7	372.2	379.0	394.6	418.1	453.3	510.9
50°	339.2	338.3	339.2	340.9	343.8	349.2	357.1	368.4	387.5	420.4	473.2
52.5°	320.9	320.7	320.2	320.9	323.1	326.9	332.5	342.0	359.1	389.4	435.9
55°	293.0	290.9	291.3	289.7	293.4	294.2	298.4	306.3	321.3	342.1	385.8
57.5°	263.3	261.5	259.7	259.2	258.9	261.1	264.5	270.7	282.2	300.4	335.9
60°	244.3	242.2	239.7	238.9	238.9	240.1	241.8	246.4	257.2	273.5	302.6
62.5°	225.0	222.6	221.1	218.9	218.3	219.5	221.2	224.5	232.2	247.4	272.6
65°	195.2	192.2	190.2	189.8	189.0	187.7	188.5	191.8	198.1	210.2	230.2
67.5°	165.3	162.6	162.1	159.6	158.5	158.7	158.5	161.3	165.1	175.5	190.4
70°	145.7	143.6	142.8	140.6	139.8	139.0	138.2	140.6	144.4	153.2	166.1
72.5°	125.7	123.9	122.1	120.3	120.5	119.7	119.5	121.0	124.1	132.2	142.1
75°	96.9	97.4	95.3	93.2	92.8	92.0	92.0	93.2	94.5	100.7	108.6
77.5°	70.4	70.0	68.2	67.6	67.2	66.3	67.2	68.0	68.6	72.8	78.7
80°	53.7	53.7	51.6	51.6	51.2	50.0	51.2	50.4	52.0	56.2	60.3
82.5°	38.4	37.7	37.6	36.9	36.9	36.0	36.5	37.3	38.1	40.8	43.4
85°	18.8	18.8	18.3	17.9	18.3	17.9	18.3	18.8	19.2	20.4	22.5
87.5°	7.7	7.8	7.8	7.8	7.5	7.6	7.5	7.4	7.7	7.6	7.5
90°	18.3	17.4	15.8	14.3	12.7	11.2	9.4	7.3	5.1	3.0	0.9
92.5°	20.6	20.1	19.3	18.6	17.8	17.0	16.7	17.0	17.1	17.3	17.5
95°	34.7	33.8	32.4	31.1	29.8	28.4	30.9	37.3	43.6	50.0	56.3
97.5°	46.0	45.2	42.2	39.0	35.9	32.8	40.2	58.0	76.0	93.9	111.8
100°	51.0	49.4	46.1	42.9	39.5	36.3	47.9	74.3	100.6	127.0	153.4
102.5°	52.8	50.8	78.2	105.6	133.0	160.4	176.8	182.4	188.0	193.6	199.2
105°	55.0	52.8	105.4	158.0	210.6	263.2	286.6	280.8	275.0	269.3	263.5
107.5°	71.8	74.0	137.1	200.2	263.2	326.3	355.5	350.7	346.1	341.4	336.8
110°	132.4	151.6	207.3	263.0	318.6	374.3	400.1	396.1	392.1	388.0	383.9



TEST NUMBER: P331366-930

CATALOG NUMBER: SA2XXDIP-C675D1080U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	312.3	382.5	396.3	410.1	423.8	437.6	442.6	439.0	435.5	431.9	428.4
115°	445.6	534.8	529.9	525.1	520.3	515.5	511.4	508.2	504.9	501.7	498.4
117.5°	570.7	592.3	589.0	585.7	582.4	579.0	575.6	571.9	568.3	564.6	560.9
120°	637.6	635.3	631.9	628.4	624.9	621.4	618.2	615.4	612.5	609.6	606.7
122.5°	677.6	676.2	672.5	668.6	664.9	661.1	657.7	654.7	651.6	648.6	645.6
125°	733.7	732.4	728.7	725.0	721.4	717.7	714.6	712.2	709.6	707.1	704.7
127.5°	785.0	783.0	780.2	777.5	774.8	772.0	769.3	766.5	763.8	761.0	758.2
130°	817.7	815.5	813.4	811.3	809.2	807.1	804.5	801.4	798.3	795.2	792.1
132.5°	849.9	848.2	846.0	843.9	841.8	839.7	837.3	834.7	832.1	829.5	826.8
135°	895.5	893.6	891.9	890.1	888.4	886.6	884.2	881.2	878.1	875.0	871.9
137.5°	937.9	936.0	934.1	932.1	930.2	928.1	926.1	924.0	921.8	919.7	917.5
140°	965.5	963.8	961.6	959.5	957.4	955.3	953.5	951.9	950.4	948.8	947.3
142.5°	991.0	989.4	987.0	984.6	982.1	979.7	977.8	976.4	975.0	973.6	972.2
145°	1026.6	1025.3	1022.1	1018.7	1015.5	1012.2	1010.6	1010.9	1011.1	1011.2	1011.5
147.5°	1057.9	1056.9	1053.6	1050.4	1047.2	1043.9	1042.7	1043.4	1044.2	1044.9	1045.6
150°	1076.8	1075.5	1072.5	1069.4	1066.3	1063.2	1062.4	1063.7	1065.1	1066.4	1067.8
152.5°	1094.1	1092.9	1090.0	1087.0	1084.1	1081.2	1080.5	1082.0	1083.5	1085.0	1086.5
155°	1117.4	1116.3	1114.0	1111.7	1109.4	1107.1	1106.8	1108.5	1110.3	1112.0	1113.7
157.5°	1137.0	1135.7	1134.1	1132.5	1130.9	1129.3	1129.2	1130.7	1132.1	1133.6	1135.1
160°	1148.7	1147.5	1146.4	1145.2	1144.0	1142.9	1142.9	1144.0	1145.2	1146.4	1147.5
162.5°	1159.2	1157.9	1156.9	1155.9	1154.9	1153.9	1154.0	1155.1	1156.3	1157.5	1158.6
165°	1172.2	1170.9	1170.4	1169.8	1169.1	1168.6	1168.9	1170.0	1171.2	1172.3	1173.5
167.5°	1183.2	1181.9	1181.3	1180.7	1180.2	1179.7	1180.0	1181.1	1182.3	1183.5	1184.6
170°	1188.7	1187.4	1187.0	1186.6	1186.3	1185.9	1186.3	1187.4	1188.5	1189.7	1190.8
172.5°	1192.9	1191.6	1191.2	1190.7	1190.4	1190.0	1190.4	1191.6	1192.7	1193.8	1195.0
175°	1197.4	1196.0	1195.6	1195.3	1194.9	1194.5	1195.0	1196.4	1197.7	1199.1	1200.4
177.5°	1198.2	1197.1	1196.9	1196.8	1196.6	1196.5	1196.9	1198.0	1199.1	1200.2	1201.3
180°	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8



TEST NUMBER: P331366-930
 CATALOG NUMBER: SA2XXDIP-C675D1080U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0
2.5°	1088.6	1090.3	1095.6	1100.9	1106.9	1108.6	1111.3	1108.9	1108.2	1114.6	1119.2
5°	1091.7	1099.2	1113.8	1127.1	1138.3	1146.2	1154.5	1157.9	1164.1	1172.8	1183.7
7.5°	1088.2	1102.8	1125.7	1145.0	1166.2	1181.5	1193.4	1203.5	1215.8	1232.3	1250.4
10°	1084.2	1103.8	1131.6	1155.4	1181.1	1200.7	1217.0	1232.7	1251.1	1274.0	1297.7
12.5°	1076.8	1100.1	1135.0	1163.0	1196.1	1215.4	1237.3	1271.4	1291.0	1322.9	1356.3
15°	1062.2	1087.9	1136.6	1171.2	1208.6	1245.3	1285.6	1318.1	1350.5	1369.3	1416.3
17.5°	1040.2	1078.2	1132.0	1172.3	1219.9	1277.7	1323.0	1359.8	1397.3	1427.7	1451.2
20°	1022.6	1063.8	1125.4	1173.7	1230.3	1292.2	1344.3	1381.8	1414.2	1439.7	1454.2
22.5°	1000.3	1052.1	1112.1	1168.7	1241.0	1302.3	1357.0	1386.4	1413.6	1426.0	1431.6
25°	965.2	1027.6	1095.4	1164.5	1246.1	1311.0	1361.0	1378.8	1386.7	1374.7	1354.7
27.5°	927.3	996.9	1076.2	1156.7	1242.9	1305.4	1341.2	1338.3	1324.9	1285.9	1254.7
30°	898.9	975.6	1060.9	1148.7	1235.3	1296.0	1316.9	1296.0	1265.7	1222.0	1177.5
32.5°	869.4	948.6	1044.6	1137.3	1221.3	1274.7	1279.2	1243.4	1196.4	1146.7	1091.2
35°	824.5	910.2	1013.8	1112.1	1191.6	1225.3	1205.3	1142.1	1086.3	1018.5	942.6
37.5°	773.8	868.5	972.4	1075.1	1147.0	1155.8	1106.3	1039.7	961.0	881.3	792.1
40°	735.8	836.2	943.1	1046.8	1110.4	1101.2	1038.0	964.7	871.1	773.7	690.9
42.5°	701.9	802.2	911.1	1012.8	1063.8	1038.7	964.7	874.8	774.2	682.5	606.7
45°	643.0	746.2	857.8	956.0	985.1	939.8	842.0	742.1	643.0	566.5	506.5
47.5°	586.0	687.9	798.4	884.8	895.0	834.1	727.2	624.4	539.2	476.9	434.6
50°	544.0	646.4	755.8	832.8	829.5	755.8	646.0	548.1	477.0	426.6	398.3
52.5°	506.4	603.1	708.2	778.2	760.6	680.2	575.4	488.5	430.0	390.6	365.0
55°	447.8	537.3	637.2	693.4	660.9	571.9	483.2	413.3	370.0	340.5	320.5
57.5°	389.7	473.6	559.1	593.8	557.9	475.6	401.7	351.0	318.5	296.6	283.6
60°	353.8	427.1	503.2	533.1	490.2	417.0	358.7	313.4	287.1	269.3	257.6
62.5°	317.8	383.4	455.3	471.6	432.4	370.4	318.8	281.1	259.5	243.6	232.7
65°	268.9	322.5	377.1	387.9	351.7	303.9	263.0	238.5	219.3	207.7	198.9
67.5°	220.5	263.6	302.2	311.0	279.2	246.1	216.6	195.2	182.2	172.5	165.2
70°	191.8	226.0	257.6	264.7	239.3	209.8	187.3	170.2	158.6	150.3	143.2
72.5°	161.6	190.0	216.3	221.1	200.3	177.8	159.3	145.9	135.6	130.3	123.5
75°	123.6	140.2	160.6	161.9	148.1	134.4	120.3	111.5	106.2	99.5	96.1
77.5°	87.2	100.3	111.9	114.2	106.1	96.7	88.8	81.9	77.3	74.3	71.2
80°	66.6	77.0	82.0	84.9	79.1	72.4	67.8	63.3	60.3	58.3	56.2
82.5°	47.6	54.1	58.7	60.9	57.8	53.8	49.2	46.6	44.4	42.6	41.9
85°	24.1	27.1	30.0	30.8	30.0	28.3	25.8	25.8	24.5	24.1	24.1
87.5°	8.9	10.7	11.1	12.6	12.2	12.6	12.8	12.8	12.8	12.6	12.5
90°	3.0	5.1	7.3	9.4	11.2	12.7	14.3	15.8	17.4	18.3	19.2
92.5°	17.3	17.1	17.0	16.7	17.0	17.8	18.6	19.3	20.1	20.6	21.1
95°	50.0	43.6	37.3	30.9	28.4	29.8	31.1	32.4	33.8	34.7	35.7
97.5°	93.9	76.0	58.0	40.2	32.8	35.9	39.0	42.2	45.2	46.0	46.8
100°	127.0	100.6	74.3	47.9	36.3	39.5	42.9	46.1	49.4	51.0	52.5
102.5°	193.6	188.0	182.4	176.8	160.4	133.0	105.6	78.2	50.8	52.8	54.8
105°	269.3	275.0	280.8	286.6	263.2	210.6	158.0	105.4	52.8	55.0	57.1
107.5°	341.4	346.1	350.7	355.5	326.3	263.2	200.2	137.1	74.0	71.8	69.7
110°	388.0	392.1	396.1	400.1	374.3	318.6	263.0	207.3	151.6	132.4	113.2



TEST NUMBER: P331366-930

CATALOG NUMBER: SA2XXDIP-C675D1080U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	431.9	435.5	439.0	442.6	437.6	423.8	410.1	396.3	382.5	312.3	242.1
115°	501.7	504.9	508.2	511.4	515.5	520.3	525.1	529.9	534.8	445.6	356.4
117.5°	564.6	568.3	571.9	575.6	579.0	582.4	585.7	589.0	592.3	570.7	549.2
120°	609.6	612.5	615.4	618.2	621.4	624.9	628.4	631.9	635.3	637.6	639.9
122.5°	648.6	651.6	654.7	657.7	661.1	664.9	668.6	672.5	676.2	677.6	679.0
125°	707.1	709.6	712.2	714.6	717.7	721.4	725.0	728.7	732.4	733.7	735.1
127.5°	761.0	763.8	766.5	769.3	772.0	774.8	777.5	780.2	783.0	785.0	786.9
130°	795.2	798.3	801.4	804.5	807.1	809.2	811.3	813.4	815.5	817.7	819.8
132.5°	829.5	832.1	834.7	837.3	839.7	841.8	843.9	846.0	848.2	849.9	851.7
135°	875.0	878.1	881.2	884.2	886.6	888.4	890.1	891.9	893.6	895.5	897.4
137.5°	919.7	921.8	924.0	926.1	928.1	930.2	932.1	934.1	936.0	937.9	939.8
140°	948.8	950.4	951.9	953.5	955.3	957.4	959.5	961.6	963.8	965.5	967.3
142.5°	973.6	975.0	976.4	977.8	979.7	982.1	984.6	987.0	989.4	991.0	992.5
145°	1011.2	1011.1	1010.9	1010.6	1012.2	1015.5	1018.7	1022.1	1025.3	1026.6	1028.0
147.5°	1044.9	1044.2	1043.4	1042.7	1043.9	1047.2	1050.4	1053.6	1056.9	1057.9	1058.8
150°	1066.4	1065.1	1063.7	1062.4	1063.2	1066.3	1069.4	1072.5	1075.5	1076.8	1077.9
152.5°	1085.0	1083.5	1082.0	1080.5	1081.2	1084.1	1087.0	1090.0	1092.9	1094.1	1095.2
155°	1112.0	1110.3	1108.5	1106.8	1107.1	1109.4	1111.7	1114.0	1116.3	1117.4	1118.6
157.5°	1133.6	1132.1	1130.7	1129.2	1129.3	1130.9	1132.5	1134.1	1135.7	1137.0	1138.3
160°	1146.4	1145.2	1144.0	1142.9	1142.9	1144.0	1145.2	1146.4	1147.5	1148.7	1149.8
162.5°	1157.5	1156.3	1155.1	1154.0	1153.9	1154.9	1155.9	1156.9	1157.9	1159.2	1160.5
165°	1172.3	1171.2	1170.0	1168.9	1168.6	1169.1	1169.8	1170.4	1170.9	1172.2	1173.6
167.5°	1183.5	1182.3	1181.1	1180.0	1179.7	1180.2	1180.7	1181.3	1181.9	1183.2	1184.5
170°	1189.7	1188.5	1187.4	1186.3	1185.9	1186.3	1186.6	1187.0	1187.4	1188.7	1190.1
172.5°	1193.8	1192.7	1191.6	1190.4	1190.0	1190.4	1190.7	1191.2	1191.6	1192.9	1194.3
175°	1199.1	1197.7	1196.4	1195.0	1194.5	1194.9	1195.3	1195.6	1196.0	1197.4	1198.7
177.5°	1200.2	1199.1	1198.0	1196.9	1196.5	1196.6	1196.8	1196.9	1197.1	1198.2	1199.2
180°	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8



TEST NUMBER: P331366-930

CATALOG NUMBER: SA2XXDIP-C675D1080U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0
2.5°	1123.2	1127.9	1127.9	1128.5	1133.9	1133.2	1132.9
5°	1195.3	1202.4	1203.2	1210.7	1215.7	1214.1	1209.5
7.5°	1263.3	1276.5	1286.5	1292.0	1298.6	1302.7	1300.9
10°	1317.3	1336.4	1348.1	1356.0	1365.5	1372.6	1370.1
12.5°	1366.2	1389.0	1405.0	1418.5	1419.8	1428.9	1422.7
15°	1442.5	1466.6	1469.2	1479.2	1487.1	1486.2	1486.6
17.5°	1467.8	1475.5	1477.1	1477.3	1477.4	1474.5	1468.2
20°	1458.7	1455.9	1448.8	1443.4	1433.8	1432.6	1424.2
22.5°	1416.2	1406.9	1389.2	1377.4	1362.5	1358.6	1356.3
25°	1332.3	1311.8	1283.5	1256.5	1249.0	1234.4	1238.6
27.5°	1217.2	1185.4	1154.7	1132.7	1112.8	1091.0	1097.2
30°	1136.2	1100.4	1057.1	1023.9	1002.7	981.8	978.0
32.5°	1039.7	987.2	938.9	909.6	877.1	864.0	849.5
35°	873.2	822.0	774.1	733.0	709.2	690.9	674.3
37.5°	723.4	664.5	625.9	592.5	575.4	564.8	567.5
40°	630.6	578.9	550.7	525.2	509.4	501.9	503.6
42.5°	555.3	516.7	493.3	476.0	464.8	460.6	459.7
45°	469.9	448.3	429.1	419.1	413.7	409.1	406.2
47.5°	411.6	394.0	383.2	377.2	372.5	367.9	367.8
50°	376.7	365.0	357.5	351.2	347.6	344.2	347.1
52.5°	350.0	339.3	331.9	326.3	324.9	321.9	321.8
55°	310.5	302.1	296.8	291.7	289.3	287.6	285.5
57.5°	274.5	266.6	261.6	258.4	253.7	252.0	251.4
60°	248.9	242.6	237.7	233.5	231.4	228.0	228.0
62.5°	225.3	219.0	214.3	211.2	207.7	206.4	206.8
65°	191.0	186.1	181.5	178.1	177.3	174.8	175.6
67.5°	159.6	156.2	151.4	149.6	148.0	146.7	145.7
70°	138.6	135.3	132.7	130.3	129.0	129.0	129.0
72.5°	120.9	116.9	115.4	112.3	113.0	111.7	110.4
75°	93.7	91.2	89.9	88.6	86.6	86.6	86.6
77.5°	68.9	68.2	66.7	65.3	64.8	64.4	64.6
80°	53.2	52.8	52.0	52.0	51.2	50.8	50.0
82.5°	40.9	39.9	39.4	39.1	38.9	38.8	38.6
85°	23.3	22.5	22.5	22.9	22.1	22.1	22.5
87.5°	13.0	13.2	13.0	13.1	13.5	13.3	13.4
90°	20.2	21.2	21.9	22.3	22.7	23.0	23.4
92.5°	21.6	22.1	22.5	22.7	22.9	23.2	23.4
95°	36.7	37.7	38.1	37.8	37.7	37.4	37.3
97.5°	47.5	48.3	48.8	49.1	49.3	49.5	49.7
100°	54.1	55.6	56.5	56.9	57.3	57.7	58.0
102.5°	56.8	58.8	60.1	60.6	61.1	61.7	62.2
105°	59.2	61.3	62.8	63.6	64.3	65.1	65.9
107.5°	67.5	65.4	64.7	65.5	66.2	67.0	67.8
110°	93.9	74.6	65.4	66.1	66.9	67.7	68.5



TEST NUMBER: P331366-930

CATALOG NUMBER: SA2XXDIP-C675D1080U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	171.8	101.5	66.7	67.3	67.9	68.6	69.1
115°	267.3	178.1	126.5	112.7	98.8	85.0	71.1
117.5°	527.6	506.1	472.5	426.9	381.3	335.7	290.2
120°	642.2	644.6	632.7	606.7	580.7	554.6	528.7
122.5°	680.4	681.8	679.9	674.9	669.8	664.8	659.7
125°	736.4	737.8	738.7	739.3	739.9	740.5	741.0
127.5°	788.9	790.8	791.9	792.0	792.1	792.2	792.3
130°	821.9	824.0	825.0	824.8	824.6	824.4	824.3
132.5°	853.6	855.4	856.2	856.0	855.8	855.7	855.4
135°	899.4	901.2	902.0	901.6	901.2	900.9	900.5
137.5°	941.7	943.5	944.2	943.5	942.9	942.2	941.6
140°	969.0	970.7	971.1	970.1	969.1	968.2	967.3
142.5°	994.2	995.7	996.1	995.1	994.1	993.2	992.2
145°	1029.3	1030.7	1030.9	1030.0	1029.0	1028.0	1027.0
147.5°	1059.9	1060.9	1060.9	1060.1	1059.3	1058.5	1057.7
150°	1079.0	1080.2	1080.3	1079.3	1078.4	1077.4	1076.4
152.5°	1096.4	1097.6	1097.5	1096.2	1094.9	1093.6	1092.4
155°	1119.8	1121.0	1120.7	1119.2	1117.7	1116.1	1114.6
157.5°	1139.6	1140.9	1140.8	1139.4	1137.8	1136.4	1134.8
160°	1151.0	1152.1	1152.0	1150.7	1149.3	1148.0	1146.6
162.5°	1161.8	1163.2	1162.9	1161.3	1159.7	1158.0	1156.3
165°	1174.9	1176.3	1176.3	1174.9	1173.6	1172.2	1170.9
167.5°	1185.9	1187.2	1187.0	1185.3	1183.6	1181.9	1180.1
170°	1191.4	1192.8	1192.5	1190.8	1189.1	1187.4	1185.6
172.5°	1195.6	1196.9	1196.8	1195.0	1193.3	1191.6	1189.8
175°	1200.1	1201.4	1201.2	1199.2	1197.3	1195.4	1193.4
177.5°	1200.3	1201.4	1201.3	1199.9	1198.5	1197.1	1195.7
180°	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8

(END OF REPORT)