

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333594-940

Luminaire Tested: **S125RDIP-S1090D810U940-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333594-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIP-S1090D810U940-4F0-1E-UDD-A4  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1090 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 810 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6393.8 lumens  
Efficiency: N/A  
Efficacy: 117.5 lumens/watt  
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 54.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333594-940

CATALOG NUMBER: S125RDIP-S1090D810U940-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P333594-940

CATALOG NUMBER: S125RDIP-S1090D810U940-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	89	89	89	76	76	76	65	65	65	59
1	100	96	92	89	94	90	87	84	79	76	74	68	66	65	58	57	56	51
2	92	85	79	74	86	79	74	70	69	65	62	60	57	55	52	50	48	44
3	84	75	68	62	78	70	64	59	62	57	53	54	50	47	46	43	41	37
4	77	66	59	53	72	62	56	50	55	50	45	48	44	40	42	38	36	32
5	71	59	51	45	66	56	49	43	49	44	39	43	39	35	38	34	31	28
6	65	53	45	40	61	50	43	38	45	39	34	39	35	31	34	31	28	25
7	61	48	40	35	57	46	38	33	41	35	30	36	31	28	31	28	25	22
8	56	44	36	31	53	42	35	30	37	31	27	33	28	25	29	25	22	20
9	52	40	33	28	49	38	31	27	34	28	24	30	26	22	27	23	20	18
10	49	37	30	25	46	35	28	24	31	26	22	28	23	20	25	21	18	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	9469	9469	9469	9469
5°	10893	9481	8373	9481
10°	12496	9433	7389	9433
15°	13497	9336	6567	9336
20°	14882	9224	6064	9224
25°	17224	9075	5627	9075
30°	18744	8918	5341	8918
35°	15811	8736	5077	8736
40°	11042	8408	4850	8408
45°	8191	7965	4629	7965
50°	6531	7504	4439	7504
55°	5543	6933	4270	6933
60°	4790	6421	3995	6421
65°	4268	5868	3440	5868
70°	3750	5374	3136	5374
75°	3244	4654	2944	4654
80°	2462	3916	2462	3916
85°	2045	3083	2319	3083



TEST NUMBER: P333594-940

CATALOG NUMBER: S125RDIP-S1090D810U940-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	140.6	2.2
10°-20°	412.0	6.4
20°-30°	653.3	10.2
30°-40°	787.8	12.3
40°-50°	703.5	11.0
50°-60°	539.5	8.4
60°-70°	350.6	5.5
70°-80°	170.5	2.7
80°-90°	42.6	0.7
90°-100°	250.7	3.9
100°-110°	538.9	8.4
110°-120°	505.7	7.9
120°-130°	409.8	6.4
130°-140°	328.9	5.1
140°-150°	248.2	3.9
150°-160°	174.7	2.7
160°-170°	103.0	1.6
170°-180°	33.5	0.5
0°-30°	1205.9	18.9
0°-40°	1993.7	31.2
0°-60°	3236.7	50.6
0°-90°	3800.4	59.4
90°-120°	1295.2	20.3
90°-150°	2282.2	35.7
90°-180°	2593.0	40.6
0°-180°	6393.8	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1466	1466	1466	1466	1466	
5°	1680	1462	1292	1462	1680	168
15°	2019	1396	982	1396	2019	578
25°	2417	1274	790	1274	2417	1110
35°	2005	1108	644	1108	2005	1211
45°	897	872	507	872	897	716
55°	492	616	379	616	492	447
65°	279	384	225	384	279	278
75°	130	186	118	186	130	138
85°	28	42	31	42	28	32
90°	16	1	16	1	16	12
95°	164	23	164	23	164	232
105°	924	79	924	79	924	918
115°	1029	141	1029	141	1029	1005
125°	811	195	811	195	811	734
135°	674	229	674	229	674	522
145°	531	266	531	266	531	338
155°	446	304	446	304	446	208
165°	390	332	390	332	390	112
175°	351	345	351	345	351	34
180°	346	346	346	346	346	



TEST NUMBER: P333594-940

CATALOG NUMBER: S125RDIP-S1090D810U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2
2.5°	1542.2	1541.2	1543.2	1537.8	1538.4	1530.2	1530.2	1523.9	1515.7	1509.5	1506.5
5°	1680.3	1681.6	1679.2	1670.2	1664.1	1655.1	1644.8	1626.8	1611.8	1597.3	1585.9
7.5°	1822.7	1823.5	1815.5	1812.8	1797.6	1786.5	1763.8	1739.2	1717.4	1689.8	1668.6
10°	1905.5	1904.9	1896.4	1889.8	1876.6	1859.8	1837.5	1808.6	1781.5	1751.4	1722.5
12.5°	1953.6	1952.0	1949.4	1941.3	1929.0	1914.1	1895.2	1866.8	1833.4	1800.5	1766.8
15°	2018.7	2014.4	2006.6	1996.4	1978.9	1961.4	1940.4	1915.1	1883.2	1845.8	1814.6
17.5°	2099.0	2099.2	2087.1	2072.9	2049.2	2018.4	1985.8	1945.1	1901.8	1860.7	1827.4
20°	2165.4	2163.6	2151.6	2124.0	2096.9	2058.3	2021.1	1971.0	1918.1	1864.6	1823.0
22.5°	2260.8	2256.1	2243.5	2207.3	2165.3	2115.7	2058.6	1997.5	1933.5	1872.7	1818.2
25°	2417.1	2413.4	2388.7	2346.6	2287.7	2211.2	2136.5	2052.9	1960.9	1880.8	1814.6
27.5°	2523.9	2520.0	2501.7	2466.7	2412.3	2331.8	2230.8	2119.0	2004.0	1893.9	1798.5
30°	2513.4	2522.4	2520.0	2503.7	2462.8	2390.6	2297.3	2171.5	2034.9	1905.5	1791.7
32.5°	2362.1	2370.3	2391.4	2423.3	2425.7	2396.8	2327.1	2211.0	2069.6	1922.4	1786.5
35°	2005.4	2016.2	2057.2	2121.6	2205.8	2276.2	2290.6	2228.0	2101.0	1942.8	1778.5
37.5°	1541.7	1600.9	1635.4	1703.2	1830.5	1960.0	2084.6	2130.5	2076.3	1934.4	1765.6
40°	1309.7	1324.1	1385.5	1461.9	1569.1	1703.9	1881.4	2009.6	2013.8	1915.1	1745.3
42.5°	1120.9	1139.2	1181.3	1242.3	1334.1	1468.9	1652.3	1821.3	1899.7	1862.2	1718.9
45°	896.8	910.6	941.3	988.3	1058.6	1170.0	1327.7	1523.3	1678.6	1739.4	1647.9
47.5°	736.6	744.1	770.9	806.6	858.7	939.9	1061.9	1231.7	1418.0	1548.5	1535.7
50°	650.0	658.4	678.9	706.0	749.9	818.5	916.1	1057.5	1249.5	1408.9	1440.8
52.5°	582.6	589.6	602.4	627.9	664.2	716.9	795.7	923.6	1096.4	1266.0	1339.7
55°	492.3	497.1	507.4	521.8	550.7	588.6	656.7	745.1	884.8	1055.6	1164.0
57.5°	417.9	420.4	426.9	440.2	460.2	487.9	537.0	612.0	712.1	866.0	985.6
60°	370.8	373.2	381.6	390.6	406.3	431.5	470.0	522.4	618.7	745.7	866.7
62.5°	333.1	334.7	338.2	347.2	361.0	380.5	410.8	453.5	530.1	641.7	755.9
65°	279.3	279.8	281.1	288.3	296.7	311.1	331.0	361.1	418.9	503.2	604.2
67.5°	227.5	228.4	232.6	235.1	243.9	251.5	263.1	286.1	326.8	383.6	462.3
70°	198.6	198.0	202.2	205.3	208.2	217.3	225.1	243.8	269.0	312.4	378.0
72.5°	171.7	170.0	171.9	173.0	176.9	183.1	190.9	202.3	221.9	251.7	301.9
75°	130.0	130.6	130.6	131.8	134.8	137.2	139.6	145.6	156.5	176.4	203.4
77.5°	91.2	90.2	92.8	93.2	95.0	97.6	99.7	102.1	106.6	114.7	128.7
80°	66.2	66.2	66.8	68.6	68.0	69.2	72.2	74.6	80.1	84.9	89.7
82.5°	50.8	50.3	50.9	51.3	51.2	52.3	53.4	53.9	56.0	58.4	61.7
85°	27.6	27.6	28.3	28.3	28.9	28.9	29.5	29.5	29.5	30.1	30.7
87.5°	13.8	13.3	12.7	12.7	13.2	13.8	13.3	12.7	12.5	12.3	12.6
90°	16.1	16.1	15.3	15.3	15.3	13.9	13.3	12.6	11.9	11.1	9.7
92.5°	44.5	45.6	46.5	48.2	57.2	67.5	89.7	123.6	182.0	224.8	228.4
95°	163.8	175.0	180.6	201.5	251.0	309.6	395.3	501.3	604.5	617.8	504.1
97.5°	396.0	404.9	425.2	464.2	507.3	588.7	672.3	746.6	764.8	659.7	450.1
100°	543.9	555.0	580.8	631.0	679.1	751.6	823.4	857.6	803.9	629.6	401.6
102.5°	708.9	717.3	745.3	781.0	832.5	881.5	916.1	894.9	780.5	576.6	364.8
105°	923.8	932.2	946.1	969.1	991.5	999.2	968.5	872.9	705.6	505.5	329.1
107.5°	1037.9	1043.5	1048.0	1048.2	1036.9	1000.5	921.8	794.2	629.2	456.6	314.1
110°	1075.8	1075.8	1070.9	1057.7	1026.3	967.1	868.7	736.3	585.7	433.6	309.6



TEST NUMBER: P333594-940

CATALOG NUMBER: S125RDIP-S1090D810U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1071.4	1066.3	1054.2	1031.4	985.6	915.7	816.3	690.5	553.3	420.3	309.6
115°	1029.1	1020.0	1000.5	967.1	912.7	836.7	741.2	633.1	518.0	405.8	311.7
117.5°	955.0	949.5	930.1	895.5	841.2	771.4	689.1	596.0	497.0	398.7	316.3
120°	907.0	901.5	882.7	849.2	797.6	736.3	659.6	575.9	485.3	395.3	320.7
122.5°	864.7	859.7	840.9	810.2	764.2	706.7	638.4	560.9	475.2	392.5	324.6
125°	810.8	803.9	788.5	760.0	720.9	670.7	610.1	539.0	461.5	389.1	331.2
127.5°	764.8	761.8	747.3	722.0	686.6	639.6	583.0	516.7	449.0	387.4	338.6
130°	739.8	735.6	721.7	698.7	663.8	618.4	564.1	502.7	440.7	386.3	343.0
132.5°	714.6	709.9	697.1	674.0	639.2	595.6	546.2	488.7	434.0	386.3	348.0
135°	673.5	669.3	656.7	633.7	603.1	563.4	518.7	470.6	426.0	386.3	354.9
137.5°	629.6	625.0	613.4	592.5	565.0	531.3	494.2	455.3	418.9	387.1	361.1
140°	598.9	595.4	585.0	566.9	541.0	511.8	479.7	446.9	415.5	387.6	363.9
142.5°	570.4	567.6	557.7	542.3	520.4	495.0	467.4	439.7	412.8	388.3	365.6
145°	531.3	528.5	520.8	509.0	492.2	473.4	451.8	430.2	408.6	387.6	367.5
147.5°	498.1	496.9	492.4	482.9	469.7	455.4	438.8	421.2	404.2	385.8	368.1
150°	479.7	479.0	476.2	467.9	457.4	444.8	431.6	416.3	400.9	384.1	368.1
152.5°	465.2	464.5	461.7	455.0	446.2	436.5	424.4	410.6	397.0	381.9	367.6
155°	445.5	444.8	442.7	437.8	430.9	423.2	413.5	402.3	390.5	377.9	366.0
157.5°	427.9	428.1	426.1	422.1	416.7	410.6	403.1	394.0	384.3	373.7	364.3
160°	416.3	417.0	415.5	412.1	407.2	402.3	395.3	388.3	379.3	371.0	362.6
162.5°	405.6	405.8	405.5	402.6	398.8	394.5	388.6	382.2	374.8	367.6	360.9
165°	390.5	390.5	390.5	389.1	386.3	382.8	378.6	373.7	368.1	362.6	358.4
167.5°	376.5	376.7	377.2	375.9	374.5	372.0	368.8	365.6	361.6	357.7	354.5
170°	368.1	368.8	368.8	368.1	366.8	365.3	363.3	361.1	357.7	354.9	352.8
172.5°	360.3	361.1	362.1	360.9	360.6	359.8	358.2	356.1	353.7	351.5	350.5
175°	350.7	351.4	352.8	352.1	352.1	352.1	350.7	350.7	348.6	347.9	347.9
177.5°	345.8	345.8	347.5	347.0	347.5	347.5	347.5	347.0	346.3	345.8	345.8
180°	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8



TEST NUMBER: P333594-940

CATALOG NUMBER: S125RDIP-S1090D810U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2
2.5°	1506.5	1503.2	1496.9	1491.1	1483.9	1477.7	1473.4	1468.0	1461.3	1453.1	1446.4
5°	1573.2	1560.0	1542.6	1527.5	1508.2	1493.2	1477.6	1462.5	1447.4	1428.2	1411.3
7.5°	1647.2	1619.8	1593.2	1559.8	1529.5	1502.4	1476.3	1450.0	1424.2	1396.9	1370.6
10°	1692.4	1659.3	1622.6	1580.5	1541.9	1505.2	1471.5	1438.4	1403.6	1372.8	1339.7
12.5°	1734.8	1692.0	1650.0	1596.9	1550.6	1505.7	1462.9	1421.6	1384.3	1344.4	1308.9
15°	1773.1	1730.9	1684.0	1619.0	1554.6	1500.4	1449.8	1396.3	1350.0	1305.4	1265.7
17.5°	1787.9	1743.7	1689.2	1626.7	1556.3	1488.2	1423.0	1364.3	1309.7	1257.8	1213.2
20°	1782.1	1739.4	1683.4	1623.8	1548.5	1477.6	1407.1	1342.1	1281.4	1226.5	1179.0
22.5°	1768.1	1723.9	1669.9	1607.0	1535.5	1460.2	1385.0	1315.6	1252.0	1195.2	1143.4
25°	1747.2	1687.0	1631.7	1570.2	1502.3	1427.6	1350.0	1273.5	1205.5	1147.7	1091.2
27.5°	1725.4	1650.3	1579.8	1518.9	1447.0	1380.4	1305.6	1227.2	1155.7	1096.8	1038.8
30°	1705.7	1621.4	1543.7	1474.5	1406.5	1343.4	1272.3	1195.9	1122.5	1061.7	1002.7
32.5°	1681.1	1591.5	1506.2	1426.4	1360.8	1298.1	1233.8	1160.7	1089.2	1026.5	966.6
35°	1650.3	1536.0	1443.2	1358.3	1285.6	1224.8	1167.0	1108.0	1036.4	971.4	913.0
37.5°	1609.8	1480.1	1372.8	1280.4	1203.5	1142.5	1096.9	1043.0	977.7	915.4	861.2
40°	1585.3	1439.7	1322.2	1230.8	1150.1	1085.7	1043.0	997.3	937.7	879.3	825.1
42.5°	1552.6	1402.6	1271.2	1175.9	1094.8	1032.8	989.5	949.6	899.6	844.6	786.6
45°	1488.4	1330.7	1192.8	1090.6	1008.7	947.9	907.6	872.1	834.2	783.6	733.1
47.5°	1404.8	1255.7	1111.5	999.8	919.6	863.2	824.0	796.0	768.9	725.9	676.8
50°	1337.9	1194.1	1053.2	944.9	859.4	805.8	769.2	746.9	722.2	683.1	642.2
52.5°	1258.9	1130.5	992.6	881.8	801.2	751.0	715.7	693.5	673.2	641.2	602.2
55°	1134.5	1022.0	895.5	795.0	721.0	670.5	636.8	615.7	603.7	576.6	545.9
57.5°	990.9	910.3	798.8	701.9	636.4	586.5	561.8	543.9	530.2	511.1	489.5
60°	890.7	834.2	734.2	642.2	582.0	534.4	512.2	497.1	484.5	468.2	451.4
62.5°	789.2	748.0	661.1	582.0	526.6	486.8	465.9	452.4	437.8	426.9	410.5
65°	653.0	616.3	556.1	494.1	443.0	411.1	396.0	384.0	375.0	362.9	351.5
67.5°	508.0	493.0	451.5	408.8	372.0	343.7	330.6	322.3	311.4	304.2	296.3
70°	418.9	411.7	382.2	353.9	319.6	300.3	288.3	284.6	271.4	264.2	258.8
72.5°	339.9	336.5	319.6	300.0	275.8	259.0	247.8	243.8	235.3	229.5	226.0
75°	232.9	234.2	231.1	218.5	209.5	198.6	189.0	186.5	180.6	175.8	172.7
77.5°	147.3	153.5	153.7	153.1	149.5	142.9	138.9	137.1	131.2	129.4	128.7
80°	101.1	107.7	113.8	113.2	111.9	110.1	107.1	105.3	102.3	100.5	99.3
82.5°	67.4	73.6	78.6	81.9	81.6	79.8	77.8	77.0	76.3	75.0	74.7
85°	31.9	33.1	34.9	39.1	42.1	42.7	42.1	41.6	39.7	40.3	40.9
87.5°	12.9	12.6	12.9	12.7	11.9	14.0	15.2	15.5	14.7	14.0	13.4
90°	9.1	7.7	7.0	5.6	4.2	2.8	1.4	0.7	1.4	2.8	4.2
92.5°	159.1	95.2	57.2	36.8	24.8	16.1	10.3	8.5	10.3	16.1	24.8
95°	311.7	158.3	83.6	52.3	36.9	29.2	23.7	23.0	23.7	29.2	36.9
97.5°	248.8	136.3	87.0	64.4	50.6	43.0	39.1	38.2	39.1	43.0	50.6
100°	225.9	135.3	94.8	73.9	60.6	53.0	50.2	48.8	50.2	53.0	60.6
102.5°	216.4	140.3	104.3	83.9	71.8	63.6	61.3	60.5	61.3	63.6	71.8
105°	212.7	150.6	119.9	100.4	89.3	82.3	78.8	78.8	78.8	82.3	89.3
107.5°	219.1	165.9	136.3	118.7	107.1	101.4	98.0	96.7	98.0	101.4	107.1
110°	225.2	177.1	148.5	130.4	119.9	113.6	110.8	109.5	110.8	113.6	119.9





TEST NUMBER: P333594-940

CATALOG NUMBER: S125RDIP-S1090D810U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	233.0	187.7	160.2	142.7	132.2	125.9	123.7	122.3	123.7	125.9	132.2
115°	244.7	204.3	178.5	161.0	150.6	144.4	142.2	140.8	142.2	144.4	150.6
117.5°	258.2	221.3	196.9	180.0	168.2	161.9	159.7	157.6	159.7	161.9	168.2
120°	267.1	233.5	209.2	191.7	179.9	173.6	170.9	168.7	170.9	173.6	179.9
122.5°	277.1	245.3	220.9	203.5	190.5	184.2	182.0	180.5	182.0	184.2	190.5
125°	290.7	260.7	237.7	219.6	206.3	200.1	196.6	195.2	196.6	200.1	206.3
127.5°	303.3	275.7	253.5	235.4	221.3	213.4	208.9	206.8	208.9	213.4	221.3
130°	311.7	285.2	263.6	245.4	230.8	221.7	216.2	214.0	216.2	221.7	230.8
132.5°	318.9	294.1	272.5	254.3	239.2	229.0	222.3	219.6	222.3	229.0	239.2
135°	329.1	306.1	284.5	265.6	251.0	239.9	231.5	228.7	231.5	239.9	251.0
137.5°	336.6	314.6	294.9	275.5	261.2	250.0	242.2	240.1	242.2	250.0	261.2
140°	341.6	320.7	300.5	281.7	268.4	257.3	248.9	246.8	248.9	257.3	268.4
142.5°	344.5	324.6	305.5	287.8	275.1	263.9	256.2	254.6	256.2	263.9	275.1
145°	348.6	331.2	313.1	297.0	284.5	274.7	267.7	266.4	267.7	274.7	284.5
147.5°	351.2	335.4	319.5	305.4	294.5	285.4	279.5	278.6	279.5	285.4	294.5
150°	352.8	338.1	322.8	310.9	301.2	292.1	287.2	285.9	287.2	292.1	301.2
152.5°	353.9	340.9	326.7	316.0	306.7	298.8	294.5	293.6	294.5	298.8	306.7
155°	354.9	343.8	331.9	322.1	315.1	308.2	304.0	304.0	304.0	308.2	315.1
157.5°	355.6	346.1	335.9	328.5	322.4	316.4	313.1	313.2	313.1	316.4	322.4
160°	355.6	347.2	338.1	331.9	326.3	321.5	318.6	319.3	318.6	321.5	326.3
162.5°	355.0	348.3	340.4	335.2	330.7	326.5	323.7	324.3	323.7	326.5	330.7
165°	354.2	348.6	343.0	338.9	336.1	332.6	330.5	331.9	330.5	332.6	336.1
167.5°	352.5	348.6	344.0	341.3	339.4	337.4	336.2	336.9	336.2	337.4	339.4
170°	351.4	348.6	345.1	343.0	341.6	340.3	339.6	340.3	339.6	340.3	341.6
172.5°	350.3	348.0	345.1	344.1	343.3	341.9	341.3	342.5	341.3	341.9	343.3
175°	348.6	347.2	345.1	345.1	345.1	344.5	343.8	345.1	343.8	344.5	345.1
177.5°	347.0	346.3	345.3	345.3	345.8	345.3	345.3	346.3	345.3	345.3	345.8
180°	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8



TEST NUMBER: P333594-940

CATALOG NUMBER: S125RDIP-S1090D810U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2
2.5°	1441.5	1434.9	1430.0	1420.4	1413.6	1410.8	1405.4	1404.0	1409.3	1405.4	1405.0
5°	1398.7	1381.3	1367.4	1353.5	1338.5	1328.9	1314.5	1312.1	1308.4	1303.0	1301.8
7.5°	1347.3	1324.5	1306.7	1283.9	1264.0	1248.0	1229.9	1221.4	1216.7	1209.7	1200.3
10°	1312.6	1285.6	1261.5	1238.6	1214.0	1194.1	1176.0	1162.2	1153.2	1144.7	1141.1
12.5°	1278.4	1250.9	1220.0	1192.4	1164.8	1142.5	1122.6	1113.6	1103.6	1093.7	1085.3
15°	1225.4	1188.7	1154.9	1123.0	1099.6	1075.5	1056.2	1043.0	1028.0	1023.8	1007.5
17.5°	1169.0	1133.0	1093.6	1060.0	1032.8	1006.3	985.1	970.1	958.8	943.3	935.8
20°	1133.9	1091.2	1052.7	1022.0	991.8	960.6	938.9	926.2	915.4	902.8	896.8
22.5°	1096.4	1054.5	1015.1	979.1	948.5	917.7	902.3	889.2	876.9	865.2	857.3
25°	1041.2	999.1	957.5	920.2	888.3	866.0	848.0	832.9	826.3	814.9	806.5
27.5°	986.7	941.9	898.8	861.6	836.6	814.6	799.8	787.8	775.9	765.9	758.6
30°	951.5	905.8	858.8	829.4	802.9	781.8	765.5	754.1	745.1	736.1	730.7
32.5°	916.4	869.2	827.5	795.7	770.6	752.4	735.7	724.8	715.2	705.3	698.8
35°	860.1	811.9	778.2	746.9	722.2	705.3	693.9	678.3	670.5	663.3	656.7
37.5°	807.7	762.9	726.5	699.0	677.5	660.8	646.0	637.6	627.9	621.4	615.9
40°	769.2	728.3	695.2	666.3	650.6	632.0	618.1	607.3	600.0	591.7	585.6
42.5°	734.5	696.4	664.3	638.3	618.8	603.1	589.7	578.9	569.7	563.7	558.7
45°	685.5	647.6	616.3	592.2	574.2	559.1	545.3	539.8	527.8	520.6	518.2
47.5°	634.8	600.9	570.7	548.5	530.0	515.8	502.7	491.7	485.1	478.0	474.1
50°	600.7	568.1	539.8	518.2	500.2	484.5	472.4	465.2	456.2	449.6	444.8
52.5°	566.5	536.4	508.1	487.4	471.7	456.1	442.6	435.4	426.9	422.6	419.3
55°	517.6	485.7	461.6	441.1	424.9	410.5	397.8	390.6	385.2	380.9	379.8
57.5°	462.3	436.9	414.6	396.1	379.2	365.7	354.6	347.8	343.0	342.3	338.8
60°	426.1	403.2	382.8	362.9	348.5	335.8	326.2	318.3	313.5	313.0	311.7
62.5°	390.0	368.1	349.1	331.6	318.6	306.5	297.3	288.6	285.6	282.7	280.0
65°	336.4	316.6	301.0	287.0	273.2	263.0	254.0	248.6	241.9	238.4	231.8
67.5°	283.8	268.4	253.4	241.7	230.9	221.1	213.7	205.6	201.2	198.2	193.4
70°	249.1	237.1	222.1	209.5	201.0	193.2	187.2	178.2	175.1	172.7	170.3
72.5°	216.4	205.8	193.2	183.0	174.5	167.2	160.2	156.0	153.0	150.6	149.2
75°	170.3	160.1	149.3	142.0	136.0	130.0	126.4	123.4	122.2	121.5	119.1
77.5°	125.1	119.7	111.0	105.2	101.2	98.8	95.6	94.0	93.9	91.2	90.4
80°	95.7	92.6	85.4	83.0	80.1	77.7	75.8	72.9	69.8	68.6	66.8
82.5°	71.2	68.1	65.3	61.3	58.9	57.4	55.6	54.5	54.9	53.2	52.3
85°	37.9	34.9	33.7	33.1	31.9	33.1	32.5	31.9	31.3	30.7	31.3
87.5°	13.1	13.5	13.1	14.4	13.0	13.8	13.9	13.6	13.7	13.8	13.6
90°	5.6	7.0	7.7	9.1	9.7	11.1	11.9	12.6	13.3	13.9	15.3
92.5°	36.8	57.2	95.2	159.1	228.4	224.8	182.0	123.6	89.7	67.5	57.2
95°	52.3	83.6	158.3	311.7	504.1	617.8	604.5	501.3	395.3	309.6	251.0
97.5°	64.4	87.0	136.3	248.8	450.1	659.7	764.8	746.6	672.3	588.7	507.3
100°	73.9	94.8	135.3	225.9	401.6	629.6	803.9	857.6	823.4	751.6	679.1
102.5°	83.9	104.3	140.3	216.4	364.8	576.6	780.5	894.9	916.1	881.5	832.5
105°	100.4	119.9	150.6	212.7	329.1	505.5	705.6	872.9	968.5	999.2	991.5
107.5°	118.7	136.3	165.9	219.1	314.1	456.6	629.2	794.2	921.8	1000.5	1036.9
110°	130.4	148.5	177.1	225.2	309.6	433.6	585.7	736.3	868.7	967.1	1026.3



TEST NUMBER: P333594-940

CATALOG NUMBER: S125RDIP-S1090D810U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	142.7	160.2	187.7	233.0	309.6	420.3	553.3	690.5	816.3	915.7	985.6
115°	161.0	178.5	204.3	244.7	311.7	405.8	518.0	633.1	741.2	836.7	912.7
117.5°	180.0	196.9	221.3	258.2	316.3	398.7	497.0	596.0	689.1	771.4	841.2
120°	191.7	209.2	233.5	267.1	320.7	395.3	485.3	575.9	659.6	736.3	797.6
122.5°	203.5	220.9	245.3	277.1	324.6	392.5	475.2	560.9	638.4	706.7	764.2
125°	219.6	237.7	260.7	290.7	331.2	389.1	461.5	539.0	610.1	670.7	720.9
127.5°	235.4	253.5	275.7	303.3	338.6	387.4	449.0	516.7	583.0	639.6	686.6
130°	245.4	263.6	285.2	311.7	343.0	386.3	440.7	502.7	564.1	618.4	663.8
132.5°	254.3	272.5	294.1	318.9	348.0	386.3	434.0	488.7	546.2	595.6	639.2
135°	265.6	284.5	306.1	329.1	354.9	386.3	426.0	470.6	518.7	563.4	603.1
137.5°	275.5	294.9	314.6	336.6	361.1	387.1	418.9	455.3	494.2	531.3	565.0
140°	281.7	300.5	320.7	341.6	363.9	387.6	415.5	446.9	479.7	511.8	541.0
142.5°	287.8	305.5	324.6	344.5	365.6	388.3	412.8	439.7	467.4	495.0	520.4
145°	297.0	313.1	331.2	348.6	367.5	387.6	408.6	430.2	451.8	473.4	492.2
147.5°	305.4	319.5	335.4	351.2	368.1	385.8	404.2	421.2	438.8	455.4	469.7
150°	310.9	322.8	338.1	352.8	368.1	384.1	400.9	416.3	431.6	444.8	457.4
152.5°	316.0	326.7	340.9	353.9	367.6	381.9	397.0	410.6	424.4	436.5	446.2
155°	322.1	331.9	343.8	354.9	366.0	377.9	390.5	402.3	413.5	423.2	430.9
157.5°	328.5	335.9	346.1	355.6	364.3	373.7	384.3	394.0	403.1	410.6	416.7
160°	331.9	338.1	347.2	355.6	362.6	371.0	379.3	388.3	395.3	402.3	407.2
162.5°	335.2	340.4	348.3	355.0	360.9	367.6	374.8	382.2	388.6	394.5	398.8
165°	338.9	343.0	348.6	354.2	358.4	362.6	368.1	373.7	378.6	382.8	386.3
167.5°	341.3	344.0	348.6	352.5	354.5	357.7	361.6	365.6	368.8	372.0	374.5
170°	343.0	345.1	348.6	351.4	352.8	354.9	357.7	361.1	363.3	365.3	366.8
172.5°	344.1	345.1	348.0	350.3	350.5	351.5	353.7	356.1	358.2	359.8	360.6
175°	345.1	345.1	347.2	348.6	347.9	347.9	348.6	350.7	350.7	352.1	352.1
177.5°	345.3	345.3	346.3	347.0	345.8	345.8	346.3	347.0	347.5	347.5	347.5
180°	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8



TEST NUMBER: P333594-940

CATALOG NUMBER: S125RDIP-S1090D810U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2
2.5°	1404.4	1399.2	1397.8	1399.6	1397.8	1399.2	1404.4	1405.0	1405.4	1409.3	1404.0
5°	1295.8	1289.8	1292.8	1291.6	1292.8	1289.8	1295.8	1301.8	1303.0	1308.4	1312.1
7.5°	1200.2	1192.8	1184.8	1187.3	1184.8	1192.8	1200.2	1200.3	1209.7	1216.7	1221.4
10°	1133.3	1127.3	1123.6	1126.7	1123.6	1127.3	1133.3	1141.1	1144.7	1153.2	1162.2
12.5°	1076.9	1073.4	1070.2	1068.9	1070.2	1073.4	1076.9	1085.3	1093.7	1103.6	1113.6
15°	1000.3	993.1	990.1	982.2	990.1	993.1	1000.3	1007.5	1023.8	1028.0	1043.0
17.5°	929.6	927.2	919.4	916.1	919.4	927.2	929.6	935.8	943.3	958.8	970.1
20°	887.7	885.3	877.5	882.3	877.5	885.3	887.7	896.8	902.8	915.4	926.2
22.5°	853.1	847.7	845.3	843.8	845.3	847.7	853.1	857.3	865.2	876.9	889.2
25°	804.1	796.2	793.3	789.6	793.3	796.2	804.1	806.5	814.9	826.3	832.9
27.5°	755.2	751.0	747.0	746.1	747.0	751.0	755.2	758.6	765.9	775.9	787.8
30°	723.4	719.3	716.2	716.2	716.2	719.3	723.4	730.7	736.1	745.1	754.1
32.5°	695.0	691.8	688.8	688.3	688.8	691.8	695.0	698.8	705.3	715.2	724.8
35°	653.6	648.8	647.6	644.0	647.6	648.8	653.6	656.7	663.3	670.5	678.3
37.5°	610.6	606.6	606.5	606.2	606.5	606.6	610.6	615.9	621.4	627.9	637.6
40°	583.2	580.1	579.6	575.3	579.6	580.1	583.2	585.6	591.7	600.0	607.3
42.5°	553.8	552.2	550.2	548.4	550.2	552.2	553.8	558.7	563.7	569.7	578.9
45°	514.0	509.8	509.8	506.8	509.8	509.8	514.0	518.2	520.6	527.8	539.8
47.5°	472.8	469.6	469.9	466.8	469.9	469.6	472.8	474.1	478.0	485.1	491.7
50°	445.4	443.5	443.0	441.8	443.0	443.5	445.4	444.8	449.6	456.2	465.2
52.5°	417.9	417.1	419.4	416.7	419.4	417.1	417.9	419.3	422.6	426.9	435.4
55°	380.9	379.2	382.8	379.2	382.8	379.2	380.9	379.8	380.9	385.2	390.6
57.5°	338.5	336.8	340.0	338.2	340.0	336.8	338.5	338.8	342.3	343.0	347.8
60°	310.6	306.9	308.7	309.3	308.7	306.9	310.6	311.7	313.0	313.5	318.3
62.5°	277.3	275.2	276.5	273.8	276.5	275.2	277.3	280.0	282.7	285.6	288.6
65°	230.5	228.7	226.3	225.1	226.3	228.7	230.5	231.8	238.4	241.9	248.6
67.5°	193.7	189.3	189.2	190.2	189.2	189.3	193.7	193.4	198.2	201.2	205.6
70°	166.7	166.7	166.1	166.1	166.1	166.7	166.7	170.3	172.7	175.1	178.2
72.5°	147.9	147.5	146.3	145.9	146.3	147.5	147.9	149.2	150.6	153.0	156.0
75°	119.1	119.8	118.6	118.0	118.6	119.8	119.1	119.1	121.5	122.2	123.4
77.5°	88.0	85.4	86.8	85.4	86.8	85.4	88.0	90.4	91.2	93.9	94.0
80°	66.8	66.2	68.0	66.2	68.0	66.2	66.8	66.8	68.6	69.8	72.9
82.5°	52.9	52.3	53.1	51.7	53.1	52.3	52.9	52.3	53.2	54.9	54.5
85°	31.9	31.3	30.7	31.3	30.7	31.3	31.9	31.3	30.7	31.3	31.9
87.5°	14.2	13.6	13.8	13.8	13.8	13.6	14.2	13.6	13.8	13.7	13.6
90°	15.3	15.3	16.1	16.1	16.1	15.3	15.3	15.3	13.9	13.3	12.6
92.5°	48.2	46.5	45.6	44.5	45.6	46.5	48.2	57.2	67.5	89.7	123.6
95°	201.5	180.6	175.0	163.8	175.0	180.6	201.5	251.0	309.6	395.3	501.3
97.5°	464.2	425.2	404.9	396.0	404.9	425.2	464.2	507.3	588.7	672.3	746.6
100°	631.0	580.8	555.0	543.9	555.0	580.8	631.0	679.1	751.6	823.4	857.6
102.5°	781.0	745.3	717.3	708.9	717.3	745.3	781.0	832.5	881.5	916.1	894.9
105°	969.1	946.1	932.2	923.8	932.2	946.1	969.1	991.5	999.2	968.5	872.9
107.5°	1048.2	1048.0	1043.5	1037.9	1043.5	1048.0	1048.2	1036.9	1000.5	921.8	794.2
110°	1057.7	1070.9	1075.8	1075.8	1075.8	1070.9	1057.7	1026.3	967.1	868.7	736.3



TEST NUMBER: P333594-940

CATALOG NUMBER: S125RDIP-S1090D810U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1031.4	1054.2	1066.3	1071.4	1066.3	1054.2	1031.4	985.6	915.7	816.3	690.5
115°	967.1	1000.5	1020.0	1029.1	1020.0	1000.5	967.1	912.7	836.7	741.2	633.1
117.5°	895.5	930.1	949.5	955.0	949.5	930.1	895.5	841.2	771.4	689.1	596.0
120°	849.2	882.7	901.5	907.0	901.5	882.7	849.2	797.6	736.3	659.6	575.9
122.5°	810.2	840.9	859.7	864.7	859.7	840.9	810.2	764.2	706.7	638.4	560.9
125°	760.0	788.5	803.9	810.8	803.9	788.5	760.0	720.9	670.7	610.1	539.0
127.5°	722.0	747.3	761.8	764.8	761.8	747.3	722.0	686.6	639.6	583.0	516.7
130°	698.7	721.7	735.6	739.8	735.6	721.7	698.7	663.8	618.4	564.1	502.7
132.5°	674.0	697.1	709.9	714.6	709.9	697.1	674.0	639.2	595.6	546.2	488.7
135°	633.7	656.7	669.3	673.5	669.3	656.7	633.7	603.1	563.4	518.7	470.6
137.5°	592.5	613.4	625.0	629.6	625.0	613.4	592.5	565.0	531.3	494.2	455.3
140°	566.9	585.0	595.4	598.9	595.4	585.0	566.9	541.0	511.8	479.7	446.9
142.5°	542.3	557.7	567.6	570.4	567.6	557.7	542.3	520.4	495.0	467.4	439.7
145°	509.0	520.8	528.5	531.3	528.5	520.8	509.0	492.2	473.4	451.8	430.2
147.5°	482.9	492.4	496.9	498.1	496.9	492.4	482.9	469.7	455.4	438.8	421.2
150°	467.9	476.2	479.0	479.7	479.0	476.2	467.9	457.4	444.8	431.6	416.3
152.5°	455.0	461.7	464.5	465.2	464.5	461.7	455.0	446.2	436.5	424.4	410.6
155°	437.8	442.7	444.8	445.5	444.8	442.7	437.8	430.9	423.2	413.5	402.3
157.5°	422.1	426.1	428.1	427.9	428.1	426.1	422.1	416.7	410.6	403.1	394.0
160°	412.1	415.5	417.0	416.3	417.0	415.5	412.1	407.2	402.3	395.3	388.3
162.5°	402.6	405.5	405.8	405.6	405.8	405.5	402.6	398.8	394.5	388.6	382.2
165°	389.1	390.5	390.5	390.5	390.5	390.5	389.1	386.3	382.8	378.6	373.7
167.5°	375.9	377.2	376.7	376.5	376.7	377.2	375.9	374.5	372.0	368.8	365.6
170°	368.1	368.8	368.8	368.1	368.8	368.8	368.1	366.8	365.3	363.3	361.1
172.5°	360.9	362.1	361.1	360.3	361.1	362.1	360.9	360.6	359.8	358.2	356.1
175°	352.1	352.8	351.4	350.7	351.4	352.8	352.1	352.1	352.1	350.7	350.7
177.5°	347.0	347.5	345.8	345.8	345.8	347.5	347.0	347.5	347.5	347.5	347.0
180°	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8



TEST NUMBER: P333594-940

CATALOG NUMBER: S125RDIP-S1090D810U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2
2.5°	1405.4	1410.8	1413.6	1420.4	1430.0	1434.9	1441.5	1446.4	1453.1	1461.3	1468.0
5°	1314.5	1328.9	1338.5	1353.5	1367.4	1381.3	1398.7	1411.3	1428.2	1447.4	1462.5
7.5°	1229.9	1248.0	1264.0	1283.9	1306.7	1324.5	1347.3	1370.6	1396.9	1424.2	1450.0
10°	1176.0	1194.1	1214.0	1238.6	1261.5	1285.6	1312.6	1339.7	1372.8	1403.6	1438.4
12.5°	1122.6	1142.5	1164.8	1192.4	1220.0	1250.9	1278.4	1308.9	1344.4	1384.3	1421.6
15°	1056.2	1075.5	1099.6	1123.0	1154.9	1188.7	1225.4	1265.7	1305.4	1350.0	1396.3
17.5°	985.1	1006.3	1032.8	1060.0	1093.6	1133.0	1169.0	1213.2	1257.8	1309.7	1364.3
20°	938.9	960.6	991.8	1022.0	1052.7	1091.2	1133.9	1179.0	1226.5	1281.4	1342.1
22.5°	902.3	917.7	948.5	979.1	1015.1	1054.5	1096.4	1143.4	1195.2	1252.0	1315.6
25°	848.0	866.0	888.3	920.2	957.5	999.1	1041.2	1091.2	1147.7	1205.5	1273.5
27.5°	799.8	814.6	836.6	861.6	898.8	941.9	986.7	1038.8	1096.8	1155.7	1227.2
30°	765.5	781.8	802.9	829.4	858.8	905.8	951.5	1002.7	1061.7	1122.5	1195.9
32.5°	735.7	752.4	770.6	795.7	827.5	869.2	916.4	966.6	1026.5	1089.2	1160.7
35°	693.9	705.3	722.2	746.9	778.2	811.9	860.1	913.0	971.4	1036.4	1108.0
37.5°	646.0	660.8	677.5	699.0	726.5	762.9	807.7	861.2	915.4	977.7	1043.0
40°	618.1	632.0	650.6	666.3	695.2	728.3	769.2	825.1	879.3	937.7	997.3
42.5°	589.7	603.1	618.8	638.3	664.3	696.4	734.5	786.6	844.6	899.6	949.6
45°	545.3	559.1	574.2	592.2	616.3	647.6	685.5	733.1	783.6	834.2	872.1
47.5°	502.7	515.8	530.0	548.5	570.7	600.9	634.8	676.8	725.9	768.9	796.0
50°	472.4	484.5	500.2	518.2	539.8	568.1	600.7	642.2	683.1	722.2	746.9
52.5°	442.6	456.1	471.7	487.4	508.1	536.4	566.5	602.2	641.2	673.2	693.5
55°	397.8	410.5	424.9	441.1	461.6	485.7	517.6	545.9	576.6	603.7	615.7
57.5°	354.6	365.7	379.2	396.1	414.6	436.9	462.3	489.5	511.1	530.2	543.9
60°	326.2	335.8	348.5	362.9	382.8	403.2	426.1	451.4	468.2	484.5	497.1
62.5°	297.3	306.5	318.6	331.6	349.1	368.1	390.0	410.5	426.9	437.8	452.4
65°	254.0	263.0	273.2	287.0	301.0	316.6	336.4	351.5	362.9	375.0	384.0
67.5°	213.7	221.1	230.9	241.7	253.4	268.4	283.8	296.3	304.2	311.4	322.3
70°	187.2	193.2	201.0	209.5	222.1	237.1	249.1	258.8	264.2	271.4	284.6
72.5°	160.2	167.2	174.5	183.0	193.2	205.8	216.4	226.0	229.5	235.3	243.8
75°	126.4	130.0	136.0	142.0	149.3	160.1	170.3	172.7	175.8	180.6	186.5
77.5°	95.6	98.8	101.2	105.2	111.0	119.7	125.1	128.7	129.4	131.2	137.1
80°	75.8	77.7	80.1	83.0	85.4	92.6	95.7	99.3	100.5	102.3	105.3
82.5°	55.6	57.4	58.9	61.3	65.3	68.1	71.2	74.7	75.0	76.3	77.0
85°	32.5	33.1	31.9	33.1	33.7	34.9	37.9	40.9	40.3	39.7	41.6
87.5°	13.9	13.8	13.0	14.4	13.1	13.5	13.1	13.4	14.0	14.7	15.5
90°	11.9	11.1	9.7	9.1	7.7	7.0	5.6	4.2	2.8	1.4	0.7
92.5°	182.0	224.8	228.4	159.1	95.2	57.2	36.8	24.8	16.1	10.3	8.5
95°	604.5	617.8	504.1	311.7	158.3	83.6	52.3	36.9	29.2	23.7	23.0
97.5°	764.8	659.7	450.1	248.8	136.3	87.0	64.4	50.6	43.0	39.1	38.2
100°	803.9	629.6	401.6	225.9	135.3	94.8	73.9	60.6	53.0	50.2	48.8
102.5°	780.5	576.6	364.8	216.4	140.3	104.3	83.9	71.8	63.6	61.3	60.5
105°	705.6	505.5	329.1	212.7	150.6	119.9	100.4	89.3	82.3	78.8	78.8
107.5°	629.2	456.6	314.1	219.1	165.9	136.3	118.7	107.1	101.4	98.0	96.7
110°	585.7	433.6	309.6	225.2	177.1	148.5	130.4	119.9	113.6	110.8	109.5



TEST NUMBER: P333594-940

CATALOG NUMBER: S125RDIP-S1090D810U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	553.3	420.3	309.6	233.0	187.7	160.2	142.7	132.2	125.9	123.7	122.3
115°	518.0	405.8	311.7	244.7	204.3	178.5	161.0	150.6	144.4	142.2	140.8
117.5°	497.0	398.7	316.3	258.2	221.3	196.9	180.0	168.2	161.9	159.7	157.6
120°	485.3	395.3	320.7	267.1	233.5	209.2	191.7	179.9	173.6	170.9	168.7
122.5°	475.2	392.5	324.6	277.1	245.3	220.9	203.5	190.5	184.2	182.0	180.5
125°	461.5	389.1	331.2	290.7	260.7	237.7	219.6	206.3	200.1	196.6	195.2
127.5°	449.0	387.4	338.6	303.3	275.7	253.5	235.4	221.3	213.4	208.9	206.8
130°	440.7	386.3	343.0	311.7	285.2	263.6	245.4	230.8	221.7	216.2	214.0
132.5°	434.0	386.3	348.0	318.9	294.1	272.5	254.3	239.2	229.0	222.3	219.6
135°	426.0	386.3	354.9	329.1	306.1	284.5	265.6	251.0	239.9	231.5	228.7
137.5°	418.9	387.1	361.1	336.6	314.6	294.9	275.5	261.2	250.0	242.2	240.1
140°	415.5	387.6	363.9	341.6	320.7	300.5	281.7	268.4	257.3	248.9	246.8
142.5°	412.8	388.3	365.6	344.5	324.6	305.5	287.8	275.1	263.9	256.2	254.6
145°	408.6	387.6	367.5	348.6	331.2	313.1	297.0	284.5	274.7	267.7	266.4
147.5°	404.2	385.8	368.1	351.2	335.4	319.5	305.4	294.5	285.4	279.5	278.6
150°	400.9	384.1	368.1	352.8	338.1	322.8	310.9	301.2	292.1	287.2	285.9
152.5°	397.0	381.9	367.6	353.9	340.9	326.7	316.0	306.7	298.8	294.5	293.6
155°	390.5	377.9	366.0	354.9	343.8	331.9	322.1	315.1	308.2	304.0	304.0
157.5°	384.3	373.7	364.3	355.6	346.1	335.9	328.5	322.4	316.4	313.1	313.2
160°	379.3	371.0	362.6	355.6	347.2	338.1	331.9	326.3	321.5	318.6	319.3
162.5°	374.8	367.6	360.9	355.0	348.3	340.4	335.2	330.7	326.5	323.7	324.3
165°	368.1	362.6	358.4	354.2	348.6	343.0	338.9	336.1	332.6	330.5	331.9
167.5°	361.6	357.7	354.5	352.5	348.6	344.0	341.3	339.4	337.4	336.2	336.9
170°	357.7	354.9	352.8	351.4	348.6	345.1	343.0	341.6	340.3	339.6	340.3
172.5°	353.7	351.5	350.5	350.3	348.0	345.1	344.1	343.3	341.9	341.3	342.5
175°	348.6	347.9	347.9	348.6	347.2	345.1	345.1	345.1	344.5	343.8	345.1
177.5°	346.3	345.8	345.8	347.0	346.3	345.3	345.3	345.8	345.3	345.3	346.3
180°	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8



TEST NUMBER: P333594-940

CATALOG NUMBER: S125RDIP-S1090D810U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2
2.5°	1473.4	1477.7	1483.9	1491.1	1496.9	1503.2	1506.5	1506.5	1509.5	1515.7	1523.9
5°	1477.6	1493.2	1508.2	1527.5	1542.6	1560.0	1573.2	1585.9	1597.3	1611.8	1626.8
7.5°	1476.3	1502.4	1529.5	1559.8	1593.2	1619.8	1647.2	1668.6	1689.8	1717.4	1739.2
10°	1471.5	1505.2	1541.9	1580.5	1622.6	1659.3	1692.4	1722.5	1751.4	1781.5	1808.6
12.5°	1462.9	1505.7	1550.6	1596.9	1650.0	1692.0	1734.8	1766.8	1800.5	1833.4	1866.8
15°	1449.8	1500.4	1554.6	1619.0	1684.0	1730.9	1773.1	1814.6	1845.8	1883.2	1915.1
17.5°	1423.0	1488.2	1556.3	1626.7	1689.2	1743.7	1787.9	1827.4	1860.7	1901.8	1945.1
20°	1407.1	1477.6	1548.5	1623.8	1683.4	1739.4	1782.1	1823.0	1864.6	1918.1	1971.0
22.5°	1385.0	1460.2	1535.5	1607.0	1669.9	1723.9	1768.1	1818.2	1872.7	1933.5	1997.5
25°	1350.0	1427.6	1502.3	1570.2	1631.7	1687.0	1747.2	1814.6	1880.8	1960.9	2052.9
27.5°	1305.6	1380.4	1447.0	1518.9	1579.8	1650.3	1725.4	1798.5	1893.9	2004.0	2119.0
30°	1272.3	1343.4	1406.5	1474.5	1543.7	1621.4	1705.7	1791.7	1905.5	2034.9	2171.5
32.5°	1233.8	1298.1	1360.8	1426.4	1506.2	1591.5	1681.1	1786.5	1922.4	2069.6	2211.0
35°	1167.0	1224.8	1285.6	1358.3	1443.2	1536.0	1650.3	1778.5	1942.8	2101.0	2228.0
37.5°	1096.9	1142.5	1203.5	1280.4	1372.8	1480.1	1609.8	1765.6	1934.4	2076.3	2130.5
40°	1043.0	1085.7	1150.1	1230.8	1322.2	1439.7	1585.3	1745.3	1915.1	2013.8	2009.6
42.5°	989.5	1032.8	1094.8	1175.9	1271.2	1402.6	1552.6	1718.9	1862.2	1899.7	1821.3
45°	907.6	947.9	1008.7	1090.6	1192.8	1330.7	1488.4	1647.9	1739.4	1678.6	1523.3
47.5°	824.0	863.2	919.6	999.8	1111.5	1255.7	1404.8	1535.7	1548.5	1418.0	1231.7
50°	769.2	805.8	859.4	944.9	1053.2	1194.1	1337.9	1440.8	1408.9	1249.5	1057.5
52.5°	715.7	751.0	801.2	881.8	992.6	1130.5	1258.9	1339.7	1266.0	1096.4	923.6
55°	636.8	670.5	721.0	795.0	895.5	1022.0	1134.5	1164.0	1055.6	884.8	745.1
57.5°	561.8	586.5	636.4	701.9	798.8	910.3	990.9	985.6	866.0	712.1	612.0
60°	512.2	534.4	582.0	642.2	734.2	834.2	890.7	866.7	745.7	618.7	522.4
62.5°	465.9	486.8	526.6	582.0	661.1	748.0	789.2	755.9	641.7	530.1	453.5
65°	396.0	411.1	443.0	494.1	556.1	616.3	653.0	604.2	503.2	418.9	361.1
67.5°	330.6	343.7	372.0	408.8	451.5	493.0	508.0	462.3	383.6	326.8	286.1
70°	288.3	300.3	319.6	353.9	382.2	411.7	418.9	378.0	312.4	269.0	243.8
72.5°	247.8	259.0	275.8	300.0	319.6	336.5	339.9	301.9	251.7	221.9	202.3
75°	189.0	198.6	209.5	218.5	231.1	234.2	232.9	203.4	176.4	156.5	145.6
77.5°	138.9	142.9	149.5	153.1	153.7	153.5	147.3	128.7	114.7	106.6	102.1
80°	107.1	110.1	111.9	113.2	113.8	107.7	101.1	89.7	84.9	80.1	74.6
82.5°	77.8	79.8	81.6	81.9	78.6	73.6	67.4	61.7	58.4	56.0	53.9
85°	42.1	42.7	42.1	39.1	34.9	33.1	31.9	30.7	30.1	29.5	29.5
87.5°	15.2	14.0	11.9	12.7	12.9	12.6	12.9	12.6	12.3	12.5	12.7
90°	1.4	2.8	4.2	5.6	7.0	7.7	9.1	9.7	11.1	11.9	12.6
92.5°	10.3	16.1	24.8	36.8	57.2	95.2	159.1	228.4	224.8	182.0	123.6
95°	23.7	29.2	36.9	52.3	83.6	158.3	311.7	504.1	617.8	604.5	501.3
97.5°	39.1	43.0	50.6	64.4	87.0	136.3	248.8	450.1	659.7	764.8	746.6
100°	50.2	53.0	60.6	73.9	94.8	135.3	225.9	401.6	629.6	803.9	857.6
102.5°	61.3	63.6	71.8	83.9	104.3	140.3	216.4	364.8	576.6	780.5	894.9
105°	78.8	82.3	89.3	100.4	119.9	150.6	212.7	329.1	505.5	705.6	872.9
107.5°	98.0	101.4	107.1	118.7	136.3	165.9	219.1	314.1	456.6	629.2	794.2
110°	110.8	113.6	119.9	130.4	148.5	177.1	225.2	309.6	433.6	585.7	736.3





TEST NUMBER: P333594-940

CATALOG NUMBER: S125RDIP-S1090D810U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	123.7	125.9	132.2	142.7	160.2	187.7	233.0	309.6	420.3	553.3	690.5
115°	142.2	144.4	150.6	161.0	178.5	204.3	244.7	311.7	405.8	518.0	633.1
117.5°	159.7	161.9	168.2	180.0	196.9	221.3	258.2	316.3	398.7	497.0	596.0
120°	170.9	173.6	179.9	191.7	209.2	233.5	267.1	320.7	395.3	485.3	575.9
122.5°	182.0	184.2	190.5	203.5	220.9	245.3	277.1	324.6	392.5	475.2	560.9
125°	196.6	200.1	206.3	219.6	237.7	260.7	290.7	331.2	389.1	461.5	539.0
127.5°	208.9	213.4	221.3	235.4	253.5	275.7	303.3	338.6	387.4	449.0	516.7
130°	216.2	221.7	230.8	245.4	263.6	285.2	311.7	343.0	386.3	440.7	502.7
132.5°	222.3	229.0	239.2	254.3	272.5	294.1	318.9	348.0	386.3	434.0	488.7
135°	231.5	239.9	251.0	265.6	284.5	306.1	329.1	354.9	386.3	426.0	470.6
137.5°	242.2	250.0	261.2	275.5	294.9	314.6	336.6	361.1	387.1	418.9	455.3
140°	248.9	257.3	268.4	281.7	300.5	320.7	341.6	363.9	387.6	415.5	446.9
142.5°	256.2	263.9	275.1	287.8	305.5	324.6	344.5	365.6	388.3	412.8	439.7
145°	267.7	274.7	284.5	297.0	313.1	331.2	348.6	367.5	387.6	408.6	430.2
147.5°	279.5	285.4	294.5	305.4	319.5	335.4	351.2	368.1	385.8	404.2	421.2
150°	287.2	292.1	301.2	310.9	322.8	338.1	352.8	368.1	384.1	400.9	416.3
152.5°	294.5	298.8	306.7	316.0	326.7	340.9	353.9	367.6	381.9	397.0	410.6
155°	304.0	308.2	315.1	322.1	331.9	343.8	354.9	366.0	377.9	390.5	402.3
157.5°	313.1	316.4	322.4	328.5	335.9	346.1	355.6	364.3	373.7	384.3	394.0
160°	318.6	321.5	326.3	331.9	338.1	347.2	355.6	362.6	371.0	379.3	388.3
162.5°	323.7	326.5	330.7	335.2	340.4	348.3	355.0	360.9	367.6	374.8	382.2
165°	330.5	332.6	336.1	338.9	343.0	348.6	354.2	358.4	362.6	368.1	373.7
167.5°	336.2	337.4	339.4	341.3	344.0	348.6	352.5	354.5	357.7	361.6	365.6
170°	339.6	340.3	341.6	343.0	345.1	348.6	351.4	352.8	354.9	357.7	361.1
172.5°	341.3	341.9	343.3	344.1	345.1	348.0	350.3	350.5	351.5	353.7	356.1
175°	343.8	344.5	345.1	345.1	345.1	347.2	348.6	347.9	347.9	348.6	350.7
177.5°	345.3	345.3	345.8	345.3	345.3	346.3	347.0	345.8	345.8	346.3	347.0
180°	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8



TEST NUMBER: P333594-940

CATALOG NUMBER: S125RDIP-S1090D810U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2
2.5°	1530.2	1530.2	1538.4	1537.8	1543.2	1541.2	1542.2
5°	1644.8	1655.1	1664.1	1670.2	1679.2	1681.6	1680.3
7.5°	1763.8	1786.5	1797.6	1812.8	1815.5	1823.5	1822.7
10°	1837.5	1859.8	1876.6	1889.8	1896.4	1904.9	1905.5
12.5°	1895.2	1914.1	1929.0	1941.3	1949.4	1952.0	1953.6
15°	1940.4	1961.4	1978.9	1996.4	2006.6	2014.4	2018.7
17.5°	1985.8	2018.4	2049.2	2072.9	2087.1	2099.2	2099.0
20°	2021.1	2058.3	2096.9	2124.0	2151.6	2163.6	2165.4
22.5°	2058.6	2115.7	2165.3	2207.3	2243.5	2256.1	2260.8
25°	2136.5	2211.2	2287.7	2346.6	2388.7	2413.4	2417.1
27.5°	2230.8	2331.8	2412.3	2466.7	2501.7	2520.0	2523.9
30°	2297.3	2390.6	2462.8	2503.7	2520.0	2522.4	2513.4
32.5°	2327.1	2396.8	2425.7	2423.3	2391.4	2370.3	2362.1
35°	2290.6	2276.2	2205.8	2121.6	2057.2	2016.2	2005.4
37.5°	2084.6	1960.0	1830.5	1703.2	1635.4	1600.9	1541.7
40°	1881.4	1703.9	1569.1	1461.9	1385.5	1324.1	1309.7
42.5°	1652.3	1468.9	1334.1	1242.3	1181.3	1139.2	1120.9
45°	1327.7	1170.0	1058.6	988.3	941.3	910.6	896.8
47.5°	1061.9	939.9	858.7	806.6	770.9	744.1	736.6
50°	916.1	818.5	749.9	706.0	678.9	658.4	650.0
52.5°	795.7	716.9	664.2	627.9	602.4	589.6	582.6
55°	656.7	588.6	550.7	521.8	507.4	497.1	492.3
57.5°	537.0	487.9	460.2	440.2	426.9	420.4	417.9
60°	470.0	431.5	406.3	390.6	381.6	373.2	370.8
62.5°	410.8	380.5	361.0	347.2	338.2	334.7	333.1
65°	331.0	311.1	296.7	288.3	281.1	279.8	279.3
67.5°	263.1	251.5	243.9	235.1	232.6	228.4	227.5
70°	225.1	217.3	208.2	205.3	202.2	198.0	198.6
72.5°	190.9	183.1	176.9	173.0	171.9	170.0	171.7
75°	139.6	137.2	134.8	131.8	130.6	130.6	130.0
77.5°	99.7	97.6	95.0	93.2	92.8	90.2	91.2
80°	72.2	69.2	68.0	68.6	66.8	66.2	66.2
82.5°	53.4	52.3	51.2	51.3	50.9	50.3	50.8
85°	29.5	28.9	28.9	28.3	28.3	27.6	27.6
87.5°	13.3	13.8	13.2	12.7	12.7	13.3	13.8
90°	13.3	13.9	15.3	15.3	15.3	16.1	16.1
92.5°	89.7	67.5	57.2	48.2	46.5	45.6	44.5
95°	395.3	309.6	251.0	201.5	180.6	175.0	163.8
97.5°	672.3	588.7	507.3	464.2	425.2	404.9	396.0
100°	823.4	751.6	679.1	631.0	580.8	555.0	543.9
102.5°	916.1	881.5	832.5	781.0	745.3	717.3	708.9
105°	968.5	999.2	991.5	969.1	946.1	932.2	923.8
107.5°	921.8	1000.5	1036.9	1048.2	1048.0	1043.5	1037.9
110°	868.7	967.1	1026.3	1057.7	1070.9	1075.8	1075.8



TEST NUMBER: P333594-940

CATALOG NUMBER: S125RDIP-S1090D810U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	816.3	915.7	985.6	1031.4	1054.2	1066.3	1071.4
115°	741.2	836.7	912.7	967.1	1000.5	1020.0	1029.1
117.5°	689.1	771.4	841.2	895.5	930.1	949.5	955.0
120°	659.6	736.3	797.6	849.2	882.7	901.5	907.0
122.5°	638.4	706.7	764.2	810.2	840.9	859.7	864.7
125°	610.1	670.7	720.9	760.0	788.5	803.9	810.8
127.5°	583.0	639.6	686.6	722.0	747.3	761.8	764.8
130°	564.1	618.4	663.8	698.7	721.7	735.6	739.8
132.5°	546.2	595.6	639.2	674.0	697.1	709.9	714.6
135°	518.7	563.4	603.1	633.7	656.7	669.3	673.5
137.5°	494.2	531.3	565.0	592.5	613.4	625.0	629.6
140°	479.7	511.8	541.0	566.9	585.0	595.4	598.9
142.5°	467.4	495.0	520.4	542.3	557.7	567.6	570.4
145°	451.8	473.4	492.2	509.0	520.8	528.5	531.3
147.5°	438.8	455.4	469.7	482.9	492.4	496.9	498.1
150°	431.6	444.8	457.4	467.9	476.2	479.0	479.7
152.5°	424.4	436.5	446.2	455.0	461.7	464.5	465.2
155°	413.5	423.2	430.9	437.8	442.7	444.8	445.5
157.5°	403.1	410.6	416.7	422.1	426.1	428.1	427.9
160°	395.3	402.3	407.2	412.1	415.5	417.0	416.3
162.5°	388.6	394.5	398.8	402.6	405.5	405.8	405.6
165°	378.6	382.8	386.3	389.1	390.5	390.5	390.5
167.5°	368.8	372.0	374.5	375.9	377.2	376.7	376.5
170°	363.3	365.3	366.8	368.1	368.8	368.8	368.1
172.5°	358.2	359.8	360.6	360.9	362.1	361.1	360.3
175°	350.7	352.1	352.1	352.1	352.8	351.4	350.7
177.5°	347.5	347.5	347.5	347.0	347.5	345.8	345.8
180°	345.8	345.8	345.8	345.8	345.8	345.8	345.8

(END OF REPORT)