

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331331-930

Luminaire Tested: **SA2XXDIP-C675D330U930-4F0-1E-UDD-A1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331331-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C675D330U930-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 330 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3345.0 lumens
Efficiency: N/A
Efficacy: 95.6 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 35
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331331-930
CATALOG NUMBER: SA2XXDIP-C675D330U930-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331331-930

CATALOG NUMBER: SA2XXDIP-C675D330U930-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	76	76	76	71				
1	103	99	95	92	98	94	91	88	85	82	80	76	74	72	68	67	65	62				
2	95	87	81	76	89	83	78	73	75	71	67	68	64	62	61	58	56	53				
3	87	77	70	64	82	74	67	62	67	62	57	60	56	53	55	51	49	45				
4	80	69	61	55	75	66	59	53	60	54	50	54	50	46	49	46	43	40				
5	74	62	54	48	70	59	52	46	54	48	43	49	44	40	45	41	38	35				
6	68	56	48	42	65	54	46	41	49	43	38	45	40	36	41	37	33	31				
7	63	51	43	37	60	49	42	36	45	39	34	41	36	32	38	33	30	28				
8	59	47	39	34	56	45	38	33	41	35	31	38	33	29	35	30	27	25				
9	55	43	35	30	52	41	34	29	38	32	28	35	30	26	32	28	25	23				
10	52	40	32	27	49	38	31	27	35	29	25	32	27	24	30	26	23	21				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	17486	17486	17486	17486
5°	19603	17598	15595	17598
10°	22463	17454	13496	17454
15°	24849	17135	11925	17135
20°	24471	16790	10869	16790
25°	22066	16335	10203	16335
30°	18233	15605	9715	15605
35°	13291	14840	9368	14840
40°	10614	13940	9177	13940
45°	9275	12896	8914	12896
50°	8719	11886	8741	11886
55°	8037	10860	8504	10860
60°	7363	9771	8147	9771
65°	6709	8795	7790	8795
70°	6090	7841	7270	7841
75°	5402	6775	6438	6775
80°	4649	5607	5188	5607
85°	4168	4168	3075	4168



TEST NUMBER: P331331-930

CATALOG NUMBER: SA2XXDIP-C675D330U930-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	103.1	3.1
10°-20°	299.8	9.0
20°-30°	435.1	13.0
30°-40°	459.2	13.7
40°-50°	406.6	12.2
50°-60°	324.5	9.7
60°-70°	220.5	6.6
70°-80°	113.1	3.4
80°-90°	28.6	0.9
90°-100°	21.6	0.6
100°-110°	67.2	2.0
110°-120°	114.8	3.4
120°-130°	151.0	4.5
130°-140°	169.5	5.1
140°-150°	166.2	5.0
150°-160°	139.4	4.2
160°-170°	92.4	2.8
170°-180°	32.3	1.0
0°-30°	838.1	25.1
0°-40°	1297.3	38.8
0°-60°	2028.3	60.6
0°-90°	2390.6	71.5
90°-120°	203.6	6.1
90°-150°	690.3	20.6
90°-180°	954.0	28.5
0°-180°	3345.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1083	1083	1083	1083	1083	
5°	1210	1086	962	1086	1210	121
15°	1487	1025	713	1025	1487	410
25°	1239	917	573	917	1239	560
35°	674	753	475	753	674	439
45°	406	565	390	565	406	319
55°	286	386	302	386	286	256
65°	176	230	204	230	176	175
75°	87	109	103	109	87	93
85°	22	22	17	22	22	25
90°	10	0	10	0	10	5
95°	18	15	18	15	18	20
105°	64	62	64	62	64	67
115°	115	115	115	115	115	114
125°	168	168	168	168	168	150
135°	220	217	220	217	220	169
145°	266	263	266	263	266	166
155°	303	301	303	301	303	140
165°	328	328	328	328	328	92
175°	340	341	340	341	340	32
180°	341	341	341	341	341	



TEST NUMBER: P331331-930

CATALOG NUMBER: SA2XXDIP-C675D330U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0
2.5°	1132.9	1133.2	1133.9	1128.5	1127.9	1127.9	1123.2	1119.2	1114.6	1108.2	1108.9
5°	1209.5	1214.1	1215.7	1210.7	1203.2	1202.4	1195.3	1183.7	1172.8	1164.1	1157.9
7.5°	1300.9	1302.7	1298.6	1292.0	1286.5	1276.5	1263.3	1250.4	1232.3	1215.8	1203.5
10°	1370.1	1372.6	1365.5	1356.0	1348.1	1336.4	1317.3	1297.7	1274.0	1251.1	1232.7
12.5°	1422.7	1428.9	1419.8	1418.5	1405.0	1389.0	1366.2	1356.3	1322.9	1291.0	1271.4
15°	1486.6	1486.2	1487.1	1479.2	1469.2	1466.6	1442.5	1416.3	1369.3	1350.5	1318.1
17.5°	1468.2	1474.5	1477.4	1477.3	1477.1	1475.5	1467.8	1451.2	1427.7	1397.3	1359.8
20°	1424.2	1432.6	1433.8	1443.4	1448.8	1455.9	1458.7	1454.2	1439.7	1414.2	1381.8
22.5°	1356.3	1358.6	1362.5	1377.4	1389.2	1406.9	1416.2	1431.6	1426.0	1413.6	1386.4
25°	1238.6	1234.4	1249.0	1256.5	1283.5	1311.8	1332.3	1354.7	1374.7	1386.7	1378.8
27.5°	1097.2	1091.0	1112.8	1132.7	1154.7	1185.4	1217.2	1254.7	1285.9	1324.9	1338.3
30°	978.0	981.8	1002.7	1023.9	1057.1	1100.4	1136.2	1177.5	1222.0	1265.7	1296.0
32.5°	849.5	864.0	877.1	909.6	938.9	987.2	1039.7	1091.2	1146.7	1196.4	1243.4
35°	674.3	690.9	709.2	733.0	774.1	822.0	873.2	942.6	1018.5	1086.3	1142.1
37.5°	567.5	564.8	575.4	592.5	625.9	664.5	723.4	792.1	881.3	961.0	1039.7
40°	503.6	501.9	509.4	525.2	550.7	578.9	630.6	690.9	773.7	871.1	964.7
42.5°	459.7	460.6	464.8	476.0	493.3	516.7	555.3	606.7	682.5	774.2	874.8
45°	406.2	409.1	413.7	419.1	429.1	448.3	469.9	506.5	566.5	643.0	742.1
47.5°	367.8	367.9	372.5	377.2	383.2	394.0	411.6	434.6	476.9	539.2	624.4
50°	347.1	344.2	347.6	351.2	357.5	365.0	376.7	398.3	426.6	477.0	548.1
52.5°	321.8	321.9	324.9	326.3	331.9	339.3	350.0	365.0	390.6	430.0	488.5
55°	285.5	287.6	289.3	291.7	296.8	302.1	310.5	320.5	340.5	370.0	413.3
57.5°	251.4	252.0	253.7	258.4	261.6	266.6	274.5	283.6	296.6	318.5	351.0
60°	228.0	228.0	231.4	233.5	237.7	242.6	248.9	257.6	269.3	287.1	313.4
62.5°	206.8	206.4	207.7	211.2	214.3	219.0	225.3	232.7	243.6	259.5	281.1
65°	175.6	174.8	177.3	178.1	181.5	186.1	191.0	198.9	207.7	219.3	238.5
67.5°	145.7	146.7	148.0	149.6	151.4	156.2	159.6	165.2	172.5	182.2	195.2
70°	129.0	129.0	129.0	130.3	132.7	135.3	138.6	143.2	150.3	158.6	170.2
72.5°	110.4	111.7	113.0	112.3	115.4	116.9	120.9	123.5	130.3	135.6	145.9
75°	86.6	86.6	86.6	88.6	89.9	91.2	93.7	96.1	99.5	106.2	111.5
77.5°	64.6	64.4	64.8	65.3	66.7	68.2	68.9	71.2	74.3	77.3	81.9
80°	50.0	50.8	51.2	52.0	52.0	52.8	53.2	56.2	58.3	60.3	63.3
82.5°	38.6	38.8	38.9	39.1	39.4	39.9	40.9	41.9	42.6	44.4	46.6
85°	22.5	22.1	22.1	22.9	22.5	22.5	23.3	24.1	24.1	24.5	25.8
87.5°	10.6	10.6	10.9	10.6	10.6	10.9	10.9	10.6	11.0	11.3	11.4
90°	9.8	9.7	9.7	9.6	9.5	9.5	9.7	9.9	9.9	10.1	8.6
92.5°	9.3	9.3	9.3	9.3	9.3	9.3	9.2	9.2	9.2	9.1	8.8
95°	17.9	18.0	18.1	18.3	18.3	18.4	18.4	18.4	18.4	18.4	18.3
97.5°	30.9	31.0	31.0	31.0	31.0	31.0	31.0	31.0	31.0	31.0	30.7
100°	39.5	39.5	39.6	39.6	39.7	39.8	39.8	39.8	39.8	39.8	39.5
102.5°	49.2	49.2	49.2	49.3	49.4	49.4	49.3	49.3	49.2	49.2	48.9
105°	63.9	63.9	63.9	63.9	63.9	63.9	63.8	63.6	63.5	63.3	63.3
107.5°	77.9	78.2	78.5	78.8	79.1	79.2	79.2	79.1	79.0	79.0	79.0
110°	88.7	88.9	89.1	89.3	89.5	89.6	89.6	89.6	89.6	89.6	89.6



TEST NUMBER: P331331-930

CATALOG NUMBER: SA2XXDIP-C675D330U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	99.1	99.2	99.4	99.5	99.6	99.8	100.0	100.1	100.3	100.4	100.4
115°	115.2	115.4	115.6	115.8	116.0	116.1	116.2	116.3	116.3	116.3	116.5
117.5°	130.6	130.8	131.0	131.2	131.3	131.5	131.7	131.8	132.0	132.2	132.5
120°	141.5	141.6	141.8	142.0	142.2	142.3	142.3	142.3	142.3	142.3	142.8
122.5°	152.1	152.1	152.3	152.5	152.6	152.7	152.9	153.0	153.2	153.4	153.7
125°	168.2	168.3	168.4	168.4	168.4	168.6	168.8	169.0	169.2	169.3	169.6
127.5°	183.0	183.2	183.4	183.6	183.8	184.0	184.3	184.5	184.7	184.9	185.2
130°	193.6	193.8	194.0	194.4	194.6	194.8	194.9	195.0	195.2	195.3	195.4
132.5°	203.7	203.9	204.2	204.3	204.6	204.8	205.0	205.3	205.6	205.9	205.9
135°	219.5	219.7	219.9	220.0	220.3	220.4	220.5	220.5	220.5	220.6	220.5
137.5°	233.7	234.1	234.3	234.6	234.8	235.0	235.0	235.1	235.1	235.1	235.0
140°	243.7	243.9	244.2	244.4	244.7	244.8	244.8	244.8	244.8	244.8	244.5
142.5°	252.7	252.9	253.2	253.5	253.7	253.8	253.7	253.7	253.6	253.6	253.4
145°	266.1	266.4	266.7	266.9	267.2	267.3	267.2	267.2	267.1	267.0	266.6
147.5°	278.2	278.4	278.7	278.9	279.2	279.2	279.1	278.9	278.8	278.7	278.4
150°	286.0	286.3	286.4	286.6	286.8	286.8	286.6	286.4	286.3	286.0	285.8
152.5°	293.4	293.7	293.9	294.2	294.4	294.4	294.2	293.9	293.7	293.4	293.1
155°	303.3	303.5	303.7	303.9	304.1	304.0	303.7	303.4	303.0	302.7	302.6
157.5°	311.9	312.2	312.4	312.7	313.1	313.0	312.6	312.1	311.7	311.3	311.1
160°	317.2	317.4	317.6	317.9	318.1	318.1	317.7	317.3	316.9	316.6	316.5
162.5°	321.7	322.0	322.4	322.7	322.9	322.9	322.5	322.0	321.6	321.1	321.1
165°	327.8	328.1	328.4	328.7	329.1	329.0	328.6	328.1	327.7	327.2	327.2
167.5°	332.7	333.0	333.4	333.8	334.1	334.0	333.5	333.1	332.6	332.2	332.2
170°	335.3	335.7	336.1	336.5	336.8	336.8	336.3	335.9	335.4	335.0	335.1
172.5°	337.4	337.8	338.1	338.5	338.9	338.8	338.4	337.9	337.5	337.0	337.1
175°	339.6	340.0	340.4	340.8	341.1	341.1	340.6	340.2	339.7	339.3	339.4
177.5°	340.6	341.0	341.3	341.5	341.9	341.9	341.5	341.3	341.0	340.6	340.7
180°	341.4	341.4	341.4	341.4	341.4	341.4	341.4	341.4	341.4	341.4	341.4



TEST NUMBER: P331331-930

CATALOG NUMBER: SA2XXDIP-C675D330U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0
2.5°	1111.3	1108.6	1106.9	1100.9	1095.6	1090.3	1088.6	1089.2	1082.0	1075.0	1072.0
5°	1154.5	1146.2	1138.3	1127.1	1113.8	1099.2	1091.7	1085.8	1071.3	1055.5	1046.4
7.5°	1193.4	1181.5	1166.2	1145.0	1125.7	1102.8	1088.2	1075.3	1053.9	1031.7	1018.0
10°	1217.0	1200.7	1181.1	1155.4	1131.6	1103.8	1084.2	1064.6	1039.7	1013.0	996.4
12.5°	1237.3	1215.4	1196.1	1163.0	1135.0	1100.1	1076.8	1049.3	1023.0	991.4	975.1
15°	1285.6	1245.3	1208.6	1171.2	1136.6	1087.9	1062.2	1025.1	990.5	951.5	932.7
17.5°	1323.0	1277.7	1219.9	1172.3	1132.0	1078.2	1040.2	995.9	955.0	910.3	884.8
20°	1344.3	1292.2	1230.3	1173.7	1125.4	1063.8	1022.6	977.2	929.4	879.0	851.5
22.5°	1357.0	1302.3	1241.0	1168.7	1112.1	1052.1	1000.3	950.6	902.0	847.7	818.9
25°	1361.0	1311.0	1246.1	1164.5	1095.4	1027.6	965.2	916.9	858.2	807.4	765.4
27.5°	1341.2	1305.4	1242.9	1156.7	1076.2	996.9	927.3	872.6	810.7	755.5	713.3
30°	1316.9	1296.0	1235.3	1148.7	1060.9	975.6	898.9	837.0	775.3	719.6	676.3
32.5°	1279.2	1274.7	1221.3	1137.3	1044.6	948.6	869.4	806.7	738.4	683.6	642.4
35°	1205.3	1225.3	1191.6	1112.1	1013.8	910.2	824.5	752.9	682.2	629.7	591.0
37.5°	1106.3	1155.8	1147.0	1075.1	972.4	868.5	773.8	699.0	631.5	578.6	540.6
40°	1038.0	1101.2	1110.4	1046.8	943.1	836.2	735.8	661.4	595.6	547.3	509.0
42.5°	964.7	1038.7	1063.8	1012.8	911.1	802.2	701.9	624.7	559.6	512.7	478.7
45°	842.0	939.8	985.1	956.0	857.8	746.2	643.0	564.8	505.6	461.5	435.4
47.5°	727.2	834.1	895.0	884.8	798.4	687.9	586.0	510.9	453.3	418.1	394.6
50°	646.0	755.8	829.5	832.8	755.8	646.4	544.0	473.2	420.4	387.5	368.4
52.5°	575.4	680.2	760.6	778.2	708.2	603.1	506.4	435.9	389.4	359.1	342.0
55°	483.2	571.9	660.9	693.4	637.2	537.3	447.8	385.8	342.1	321.3	306.3
57.5°	401.7	475.6	557.9	593.8	559.1	473.6	389.7	335.9	300.4	282.2	270.7
60°	358.7	417.0	490.2	533.1	503.2	427.1	353.8	302.6	273.5	257.2	246.4
62.5°	318.8	370.4	432.4	471.6	455.3	383.4	317.8	272.6	247.4	232.2	224.5
65°	263.0	303.9	351.7	387.9	377.1	322.5	268.9	230.2	210.2	198.1	191.8
67.5°	216.6	246.1	279.2	311.0	302.2	263.6	220.5	190.4	175.5	165.1	161.3
70°	187.3	209.8	239.3	264.7	257.6	226.0	191.8	166.1	153.2	144.4	140.6
72.5°	159.3	177.8	200.3	221.1	216.3	190.0	161.6	142.1	132.2	124.1	121.0
75°	120.3	134.4	148.1	161.9	160.6	140.2	123.6	108.6	100.7	94.5	93.2
77.5°	88.8	96.7	106.1	114.2	111.9	100.3	87.2	78.7	72.8	68.6	68.0
80°	67.8	72.4	79.1	84.9	82.0	77.0	66.6	60.3	56.2	52.0	50.4
82.5°	49.2	53.8	57.8	60.9	58.7	54.1	47.6	43.4	40.8	38.1	37.3
85°	25.8	28.3	30.0	30.8	30.0	27.1	24.1	22.5	20.4	19.2	18.8
87.5°	11.4	11.2	10.8	11.3	10.2	10.0	8.6	7.4	7.2	7.0	6.5
90°	7.3	5.9	4.5	3.3	2.6	1.8	1.1	0.3	1.1	1.8	2.6
92.5°	8.5	8.2	7.8	7.4	6.8	6.3	5.7	5.1	5.7	6.3	6.8
95°	18.2	18.0	17.9	17.5	16.9	16.2	15.7	15.0	15.7	16.2	16.9
97.5°	30.5	30.2	30.0	29.6	29.0	28.5	28.0	27.4	28.0	28.5	29.0
100°	39.4	39.1	39.0	38.6	38.2	37.6	37.1	36.6	37.1	37.6	38.2
102.5°	48.7	48.4	48.3	47.9	47.5	47.0	46.6	46.2	46.6	47.0	47.5
105°	63.1	63.0	62.9	62.7	62.5	62.3	62.1	62.0	62.1	62.3	62.5
107.5°	79.0	79.0	79.0	78.8	78.6	78.3	78.0	77.7	78.0	78.3	78.6
110°	89.6	89.6	89.6	89.4	89.0	88.6	88.2	87.9	88.2	88.6	89.0



TEST NUMBER: P331331-930

CATALOG NUMBER: SA2XXDIP-C675D330U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	100.5	100.5	100.6	100.4	100.0	99.7	99.3	98.9	99.3	99.7	100.0
115°	116.6	116.8	116.9	116.8	116.3	116.0	115.6	115.2	115.6	116.0	116.3
117.5°	132.9	133.2	133.6	133.5	133.0	132.5	132.0	131.4	132.0	132.5	133.0
120°	143.3	143.8	144.3	144.3	143.8	143.3	142.8	142.3	142.8	143.3	143.8
122.5°	154.1	154.4	154.8	154.7	154.0	153.4	152.8	152.2	152.8	153.4	154.0
125°	169.7	169.9	170.2	169.9	169.3	168.8	168.2	167.6	168.2	168.8	169.3
127.5°	185.4	185.6	185.8	185.6	184.8	184.2	183.4	182.7	183.4	184.2	184.8
130°	195.6	195.7	195.8	195.4	194.6	193.8	193.0	192.2	193.0	193.8	194.6
132.5°	205.9	205.8	205.8	205.5	204.7	204.1	203.4	202.8	203.4	204.1	204.7
135°	220.4	220.3	220.1	219.7	219.0	218.3	217.6	216.9	217.6	218.3	219.0
137.5°	234.8	234.6	234.5	234.2	233.6	232.9	232.4	231.8	232.4	232.9	233.6
140°	244.2	243.9	243.5	243.1	242.6	242.0	241.4	240.8	241.4	242.0	242.6
142.5°	253.2	252.9	252.7	252.3	251.8	251.2	250.6	250.1	250.6	251.2	251.8
145°	266.3	265.9	265.5	265.1	264.6	264.2	263.7	263.3	263.7	264.2	264.6
147.5°	278.2	277.9	277.6	277.2	276.7	276.1	275.7	275.1	275.7	276.1	276.7
150°	285.5	285.3	285.0	284.7	284.3	283.9	283.6	283.2	283.6	283.9	284.3
152.5°	292.8	292.4	292.2	291.8	291.5	291.1	290.7	290.3	290.7	291.1	291.5
155°	302.3	302.1	302.0	301.7	301.6	301.4	301.2	301.0	301.2	301.4	301.6
157.5°	311.0	311.0	310.8	310.7	310.5	310.4	310.3	310.1	310.3	310.4	310.5
160°	316.4	316.3	316.3	316.2	316.1	315.9	315.8	315.7	315.8	315.9	316.1
162.5°	321.1	321.0	320.9	320.9	320.8	320.8	320.8	320.7	320.8	320.8	320.8
165°	327.2	327.2	327.2	327.3	327.3	327.3	327.4	327.5	327.4	327.3	327.3
167.5°	332.2	332.2	332.3	332.4	332.6	332.8	333.0	333.1	333.0	332.8	332.6
170°	335.1	335.2	335.3	335.4	335.6	335.7	336.0	336.1	336.0	335.7	335.6
172.5°	337.2	337.3	337.3	337.5	337.6	337.9	338.0	338.2	338.0	337.9	337.6
175°	339.6	339.7	339.8	340.0	340.1	340.4	340.6	340.8	340.6	340.4	340.1
177.5°	340.9	341.0	341.0	341.2	341.4	341.4	341.6	341.8	341.6	341.4	341.4
180°	341.4	341.4	341.4	341.4	341.4	341.4	341.4	341.4	341.4	341.4	341.4



TEST NUMBER: P331331-930

CATALOG NUMBER: SA2XXDIP-C675D330U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0
2.5°	1068.6	1066.7	1059.6	1056.0	1049.9	1044.3	1040.6	1042.4	1043.7	1043.0	1042.0
5°	1038.0	1030.0	1018.0	1007.6	1000.1	986.3	980.6	977.6	975.2	972.2	969.3
7.5°	1001.5	989.0	971.8	956.9	942.9	925.9	916.2	910.3	904.3	897.7	891.9
10°	975.6	958.1	939.8	918.9	902.3	886.9	873.2	864.1	855.7	847.8	842.0
12.5°	948.3	928.1	905.5	877.0	858.7	836.7	834.5	818.4	805.4	800.5	793.7
15°	904.8	876.5	847.8	814.1	799.5	779.5	767.0	754.6	743.3	735.4	733.4
17.5°	855.4	818.8	790.3	766.1	742.2	721.7	710.2	700.2	691.0	680.4	679.0
20°	817.8	786.2	755.0	733.8	709.2	688.4	674.3	664.2	656.3	650.1	644.7
22.5°	782.2	747.5	719.0	695.8	671.6	654.8	643.6	634.0	627.4	620.4	615.4
25°	725.0	698.0	666.8	640.5	620.5	609.8	600.5	592.2	588.1	583.5	577.7
27.5°	675.0	644.9	615.7	595.4	577.9	568.3	561.7	556.1	552.2	549.5	546.3
30°	639.7	609.3	586.4	566.5	551.9	542.3	538.2	534.8	530.3	528.6	526.9
32.5°	605.8	578.4	558.8	541.4	527.6	521.3	517.5	514.5	510.9	509.2	505.9
35°	557.7	534.8	515.7	506.1	494.9	489.4	486.6	482.3	479.1	477.4	477.0
37.5°	512.5	492.6	480.0	467.7	463.0	459.7	455.7	452.8	451.8	451.6	451.2
40°	483.2	467.0	455.8	445.7	443.7	438.6	435.4	432.8	432.8	433.3	432.8
42.5°	456.6	442.0	432.1	423.5	421.0	418.0	414.7	414.5	415.2	416.6	415.2
45°	416.2	405.8	398.7	394.5	390.0	387.0	386.6	387.9	388.3	388.7	390.0
47.5°	379.0	372.2	365.7	361.2	359.1	358.7	358.2	360.4	362.3	363.1	365.0
50°	357.1	349.2	343.8	340.9	339.2	338.3	339.2	341.7	343.3	345.4	346.7
52.5°	332.5	326.9	323.1	320.9	320.2	320.7	320.9	323.8	326.4	327.1	327.8
55°	298.4	294.2	293.4	289.7	291.3	290.9	293.0	294.6	297.2	299.6	300.1
57.5°	264.5	261.1	258.9	259.2	259.7	261.5	263.3	266.2	268.9	271.5	271.7
60°	241.8	240.1	238.9	238.9	239.7	242.2	244.3	247.2	248.9	250.5	251.8
62.5°	221.2	219.5	218.3	218.9	221.1	222.6	225.0	226.6	228.2	229.9	230.5
65°	188.5	187.7	189.0	189.8	190.2	192.2	195.2	196.4	198.1	198.9	201.9
67.5°	158.5	158.7	158.5	159.6	162.1	162.6	165.3	168.2	168.5	170.2	172.0
70°	138.2	139.0	139.8	140.6	142.8	143.6	145.7	146.9	148.5	149.9	151.1
72.5°	119.5	119.7	120.5	120.3	122.1	123.9	125.7	126.9	128.6	130.2	131.4
75°	92.0	92.0	92.8	93.2	95.3	97.4	96.9	97.8	99.5	101.1	102.0
77.5°	67.2	66.3	67.2	67.6	68.2	70.0	70.4	71.5	73.4	72.8	73.8
80°	51.2	50.0	51.2	51.6	51.6	53.7	53.7	54.5	55.8	54.5	55.8
82.5°	36.5	36.0	36.9	36.9	37.6	37.7	38.4	38.6	39.8	39.2	39.8
85°	18.3	17.9	18.3	17.9	18.3	18.8	18.8	18.3	18.3	19.2	17.9
87.5°	6.4	6.2	6.2	6.4	6.4	6.4	6.0	6.0	6.0	5.2	5.2
90°	3.3	4.5	5.9	7.3	8.6	10.1	9.9	9.9	9.7	9.5	9.5
92.5°	7.4	7.8	8.2	8.5	8.8	9.1	9.2	9.2	9.2	9.3	9.3
95°	17.5	17.9	18.0	18.2	18.3	18.4	18.4	18.4	18.4	18.4	18.3
97.5°	29.6	30.0	30.2	30.5	30.7	31.0	31.0	31.0	31.0	31.0	31.0
100°	38.6	39.0	39.1	39.4	39.5	39.8	39.8	39.8	39.8	39.8	39.7
102.5°	47.9	48.3	48.4	48.7	48.9	49.2	49.2	49.3	49.3	49.4	49.4
105°	62.7	62.9	63.0	63.1	63.3	63.3	63.5	63.6	63.8	63.9	63.9
107.5°	78.8	79.0	79.0	79.0	79.0	79.0	79.0	79.1	79.2	79.2	79.1
110°	89.4	89.6	89.6	89.6	89.6	89.6	89.6	89.6	89.6	89.6	89.5



TEST NUMBER: P331331-930

CATALOG NUMBER: SA2XXDIP-C675D330U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	100.4	100.6	100.5	100.5	100.4	100.4	100.3	100.1	100.0	99.8	99.6
115°	116.8	116.9	116.8	116.6	116.5	116.3	116.3	116.3	116.2	116.1	116.0
117.5°	133.5	133.6	133.2	132.9	132.5	132.2	132.0	131.8	131.7	131.5	131.3
120°	144.3	144.3	143.8	143.3	142.8	142.3	142.3	142.3	142.3	142.3	142.2
122.5°	154.7	154.8	154.4	154.1	153.7	153.4	153.2	153.0	152.9	152.7	152.6
125°	169.9	170.2	169.9	169.7	169.6	169.3	169.2	169.0	168.8	168.6	168.4
127.5°	185.6	185.8	185.6	185.4	185.2	184.9	184.7	184.5	184.3	184.0	183.8
130°	195.4	195.8	195.7	195.6	195.4	195.3	195.2	195.0	194.9	194.8	194.6
132.5°	205.5	205.8	205.8	205.9	205.9	205.9	205.6	205.3	205.0	204.8	204.6
135°	219.7	220.1	220.3	220.4	220.5	220.6	220.5	220.5	220.5	220.4	220.3
137.5°	234.2	234.5	234.6	234.8	235.0	235.1	235.1	235.1	235.0	235.0	234.8
140°	243.1	243.5	243.9	244.2	244.5	244.8	244.8	244.8	244.8	244.8	244.7
142.5°	252.3	252.7	252.9	253.2	253.4	253.6	253.6	253.7	253.7	253.8	253.7
145°	265.1	265.5	265.9	266.3	266.6	267.0	267.1	267.2	267.2	267.3	267.2
147.5°	277.2	277.6	277.9	278.2	278.4	278.7	278.8	278.9	279.1	279.2	279.2
150°	284.7	285.0	285.3	285.5	285.8	286.0	286.3	286.4	286.6	286.8	286.8
152.5°	291.8	292.2	292.4	292.8	293.1	293.4	293.7	293.9	294.2	294.4	294.4
155°	301.7	302.0	302.1	302.3	302.6	302.7	303.0	303.4	303.7	304.0	304.1
157.5°	310.7	310.8	311.0	311.0	311.1	311.3	311.7	312.1	312.6	313.0	313.1
160°	316.2	316.3	316.3	316.4	316.5	316.6	316.9	317.3	317.7	318.1	318.1
162.5°	320.9	320.9	321.0	321.1	321.1	321.1	321.6	322.0	322.5	322.9	322.9
165°	327.3	327.2	327.2	327.2	327.2	327.2	327.7	328.1	328.6	329.0	329.1
167.5°	332.4	332.3	332.2	332.2	332.2	332.2	332.6	333.1	333.5	334.0	334.1
170°	335.4	335.3	335.2	335.1	335.1	335.0	335.4	335.9	336.3	336.8	336.8
172.5°	337.5	337.3	337.3	337.2	337.1	337.0	337.5	337.9	338.4	338.8	338.9
175°	340.0	339.8	339.7	339.6	339.4	339.3	339.7	340.2	340.6	341.1	341.1
177.5°	341.2	341.0	341.0	340.9	340.7	340.6	341.0	341.3	341.5	341.9	341.9
180°	341.4	341.4	341.4	341.4	341.4	341.4	341.4	341.4	341.4	341.4	341.4



TEST NUMBER: P331331-930

CATALOG NUMBER: SA2XXDIP-C675D330U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0
2.5°	1038.7	1038.0	1038.0	1035.0	1038.0	1038.0	1038.7	1042.0	1043.0	1043.7	1042.4
5°	963.5	962.2	960.2	962.2	960.2	962.2	963.5	969.3	972.2	975.2	977.6
7.5°	889.2	884.2	883.5	878.5	883.5	884.2	889.2	891.9	897.7	904.3	910.3
10°	834.9	831.5	831.1	823.2	831.1	831.5	834.9	842.0	847.8	855.7	864.1
12.5°	793.6	785.6	787.2	782.6	787.2	785.6	793.6	793.7	800.5	805.4	818.4
15°	722.1	722.1	720.4	713.4	720.4	722.1	722.1	733.4	735.4	743.3	754.6
17.5°	670.7	669.9	665.9	667.9	665.9	669.9	670.7	679.0	680.4	691.0	700.2
20°	640.1	637.6	632.6	632.6	632.6	637.6	640.1	644.7	650.1	656.3	664.2
22.5°	611.1	611.0	605.7	607.3	605.7	611.0	611.1	615.4	620.4	627.4	634.0
25°	577.2	574.0	571.4	572.7	571.4	574.0	577.2	577.7	583.5	588.1	592.2
27.5°	545.1	543.3	543.2	539.7	543.2	543.3	545.1	546.3	549.5	552.2	556.1
30°	526.5	522.4	523.2	521.1	523.2	522.4	526.5	526.9	528.6	530.3	534.8
32.5°	505.2	503.7	502.9	501.1	502.9	503.7	505.2	505.9	509.2	510.9	514.5
35°	476.1	476.5	474.5	475.3	474.5	476.5	476.1	477.0	477.4	479.1	482.3
37.5°	450.8	452.1	451.1	451.3	451.1	452.1	450.8	451.2	451.6	451.8	452.8
40°	434.1	434.1	434.1	435.4	434.1	434.1	434.1	432.8	433.3	432.8	432.8
42.5°	418.1	417.4	416.8	416.7	416.8	417.4	418.1	415.2	416.6	415.2	414.5
45°	390.8	392.1	392.5	390.4	392.5	392.1	390.8	390.0	388.7	388.3	387.9
47.5°	366.1	366.2	366.1	367.9	366.1	366.2	366.1	365.0	363.1	362.3	360.4
50°	348.8	348.0	348.8	348.0	348.8	348.0	348.8	346.7	345.4	343.3	341.7
52.5°	330.4	330.6	330.1	330.0	330.1	330.6	330.4	327.8	327.1	326.4	323.8
55°	301.7	302.6	302.1	302.1	302.1	302.6	301.7	300.1	299.6	297.2	294.6
57.5°	272.1	272.8	273.4	271.5	273.4	272.8	272.1	271.7	271.5	268.9	266.2
60°	251.4	253.5	253.1	252.3	253.1	253.5	251.4	251.8	250.5	248.9	247.2
62.5°	232.4	233.2	233.1	232.9	233.1	233.2	232.4	230.5	229.9	228.2	226.6
65°	203.1	203.9	202.7	203.9	202.7	203.9	203.1	201.9	198.9	198.1	196.4
67.5°	171.5	171.8	172.8	173.3	172.8	171.8	171.5	172.0	170.2	168.5	168.2
70°	151.9	151.5	152.7	154.0	152.7	151.5	151.9	151.1	149.9	148.5	146.9
72.5°	131.3	132.2	131.8	132.6	131.8	132.2	131.3	131.4	130.2	128.6	126.9
75°	101.1	102.4	102.0	103.2	102.0	102.4	101.1	102.0	101.1	99.5	97.8
77.5°	73.1	73.2	73.1	73.8	73.1	73.2	73.1	73.8	72.8	73.4	71.5
80°	55.8	55.0	54.1	55.8	54.1	55.0	55.8	55.8	54.5	55.8	54.5
82.5°	38.8	39.3	38.5	38.5	38.5	39.3	38.8	39.8	39.2	39.8	38.6
85°	17.9	17.4	16.6	16.6	16.6	17.4	17.9	17.9	19.2	18.3	18.3
87.5°	5.2	4.9	5.0	4.6	5.0	4.9	5.2	5.2	5.2	6.0	6.0
90°	9.6	9.7	9.7	9.8	9.7	9.7	9.6	9.5	9.5	9.7	9.9
92.5°	9.3	9.3	9.3	9.3	9.3	9.3	9.3	9.3	9.3	9.2	9.2
95°	18.3	18.1	18.0	17.9	18.0	18.1	18.3	18.3	18.4	18.4	18.4
97.5°	31.0	31.0	31.0	30.9	31.0	31.0	31.0	31.0	31.0	31.0	31.0
100°	39.6	39.6	39.5	39.5	39.5	39.6	39.6	39.7	39.8	39.8	39.8
102.5°	49.3	49.2	49.2	49.2	49.2	49.2	49.3	49.4	49.4	49.3	49.3
105°	63.9	63.9	63.9	63.9	63.9	63.9	63.9	63.9	63.9	63.8	63.6
107.5°	78.8	78.5	78.2	77.9	78.2	78.5	78.8	79.1	79.2	79.2	79.1
110°	89.3	89.1	88.9	88.7	88.9	89.1	89.3	89.5	89.6	89.6	89.6



TEST NUMBER: P331331-930

CATALOG NUMBER: SA2XXDIP-C675D330U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	99.5	99.4	99.2	99.1	99.2	99.4	99.5	99.6	99.8	100.0	100.1
115°	115.8	115.6	115.4	115.2	115.4	115.6	115.8	116.0	116.1	116.2	116.3
117.5°	131.2	131.0	130.8	130.6	130.8	131.0	131.2	131.3	131.5	131.7	131.8
120°	142.0	141.8	141.6	141.5	141.6	141.8	142.0	142.2	142.3	142.3	142.3
122.5°	152.5	152.3	152.1	152.1	152.1	152.3	152.5	152.6	152.7	152.9	153.0
125°	168.4	168.4	168.3	168.2	168.3	168.4	168.4	168.4	168.6	168.8	169.0
127.5°	183.6	183.4	183.2	183.0	183.2	183.4	183.6	183.8	184.0	184.3	184.5
130°	194.4	194.0	193.8	193.6	193.8	194.0	194.4	194.6	194.8	194.9	195.0
132.5°	204.3	204.2	203.9	203.7	203.9	204.2	204.3	204.6	204.8	205.0	205.3
135°	220.0	219.9	219.7	219.5	219.7	219.9	220.0	220.3	220.4	220.5	220.5
137.5°	234.6	234.3	234.1	233.7	234.1	234.3	234.6	234.8	235.0	235.0	235.1
140°	244.4	244.2	243.9	243.7	243.9	244.2	244.4	244.7	244.8	244.8	244.8
142.5°	253.5	253.2	252.9	252.7	252.9	253.2	253.5	253.7	253.8	253.7	253.7
145°	266.9	266.7	266.4	266.1	266.4	266.7	266.9	267.2	267.3	267.2	267.2
147.5°	278.9	278.7	278.4	278.2	278.4	278.7	278.9	279.2	279.2	279.1	278.9
150°	286.6	286.4	286.3	286.0	286.3	286.4	286.6	286.8	286.8	286.6	286.4
152.5°	294.2	293.9	293.7	293.4	293.7	293.9	294.2	294.4	294.4	294.2	293.9
155°	303.9	303.7	303.5	303.3	303.5	303.7	303.9	304.1	304.0	303.7	303.4
157.5°	312.7	312.4	312.2	311.9	312.2	312.4	312.7	313.1	313.0	312.6	312.1
160°	317.9	317.6	317.4	317.2	317.4	317.6	317.9	318.1	318.1	317.7	317.3
162.5°	322.7	322.4	322.0	321.7	322.0	322.4	322.7	322.9	322.9	322.5	322.0
165°	328.7	328.4	328.1	327.8	328.1	328.4	328.7	329.1	329.0	328.6	328.1
167.5°	333.8	333.4	333.0	332.7	333.0	333.4	333.8	334.1	334.0	333.5	333.1
170°	336.5	336.1	335.7	335.3	335.7	336.1	336.5	336.8	336.8	336.3	335.9
172.5°	338.5	338.1	337.8	337.4	337.8	338.1	338.5	338.9	338.8	338.4	337.9
175°	340.8	340.4	340.0	339.6	340.0	340.4	340.8	341.1	341.1	340.6	340.2
177.5°	341.5	341.3	341.0	340.6	341.0	341.3	341.5	341.9	341.9	341.5	341.3
180°	341.4	341.4	341.4	341.4	341.4	341.4	341.4	341.4	341.4	341.4	341.4



TEST NUMBER: P331331-930

CATALOG NUMBER: SA2XXDIP-C675D330U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0
2.5°	1040.6	1044.3	1049.9	1056.0	1059.6	1066.7	1068.6	1072.0	1075.0	1082.0	1089.2
5°	980.6	986.3	1000.1	1007.6	1018.0	1030.0	1038.0	1046.4	1055.5	1071.3	1085.8
7.5°	916.2	925.9	942.9	956.9	971.8	989.0	1001.5	1018.0	1031.7	1053.9	1075.3
10°	873.2	886.9	902.3	918.9	939.8	958.1	975.6	996.4	1013.0	1039.7	1064.6
12.5°	834.5	836.7	858.7	877.0	905.5	928.1	948.3	975.1	991.4	1023.0	1049.3
15°	767.0	779.5	799.5	814.1	847.8	876.5	904.8	932.7	951.5	990.5	1025.1
17.5°	710.2	721.7	742.2	766.1	790.3	818.8	855.4	884.8	910.3	955.0	995.9
20°	674.3	688.4	709.2	733.8	755.0	786.2	817.8	851.5	879.0	929.4	977.2
22.5°	643.6	654.8	671.6	695.8	719.0	747.5	782.2	818.9	847.7	902.0	950.6
25°	600.5	609.8	620.5	640.5	666.8	698.0	725.0	765.4	807.4	858.2	916.9
27.5°	561.7	568.3	577.9	595.4	615.7	644.9	675.0	713.3	755.5	810.7	872.6
30°	538.2	542.3	551.9	566.5	586.4	609.3	639.7	676.3	719.6	775.3	837.0
32.5°	517.5	521.3	527.6	541.4	558.8	578.4	605.8	642.4	683.6	738.4	806.7
35°	486.6	489.4	494.9	506.1	515.7	534.8	557.7	591.0	629.7	682.2	752.9
37.5°	455.7	459.7	463.0	467.7	480.0	492.6	512.5	540.6	578.6	631.5	699.0
40°	435.4	438.6	443.7	445.7	455.8	467.0	483.2	509.0	547.3	595.6	661.4
42.5°	414.7	418.0	421.0	423.5	432.1	442.0	456.6	478.7	512.7	559.6	624.7
45°	386.6	387.0	390.0	394.5	398.7	405.8	416.2	435.4	461.5	505.6	564.8
47.5°	358.2	358.7	359.1	361.2	365.7	372.2	379.0	394.6	418.1	453.3	510.9
50°	339.2	338.3	339.2	340.9	343.8	349.2	357.1	368.4	387.5	420.4	473.2
52.5°	320.9	320.7	320.2	320.9	323.1	326.9	332.5	342.0	359.1	389.4	435.9
55°	293.0	290.9	291.3	289.7	293.4	294.2	298.4	306.3	321.3	342.1	385.8
57.5°	263.3	261.5	259.7	259.2	258.9	261.1	264.5	270.7	282.2	300.4	335.9
60°	244.3	242.2	239.7	238.9	238.9	240.1	241.8	246.4	257.2	273.5	302.6
62.5°	225.0	222.6	221.1	218.9	218.3	219.5	221.2	224.5	232.2	247.4	272.6
65°	195.2	192.2	190.2	189.8	189.0	187.7	188.5	191.8	198.1	210.2	230.2
67.5°	165.3	162.6	162.1	159.6	158.5	158.7	158.5	161.3	165.1	175.5	190.4
70°	145.7	143.6	142.8	140.6	139.8	139.0	138.2	140.6	144.4	153.2	166.1
72.5°	125.7	123.9	122.1	120.3	120.5	119.7	119.5	121.0	124.1	132.2	142.1
75°	96.9	97.4	95.3	93.2	92.8	92.0	92.0	93.2	94.5	100.7	108.6
77.5°	70.4	70.0	68.2	67.6	67.2	66.3	67.2	68.0	68.6	72.8	78.7
80°	53.7	53.7	51.6	51.6	51.2	50.0	51.2	50.4	52.0	56.2	60.3
82.5°	38.4	37.7	37.6	36.9	36.9	36.0	36.5	37.3	38.1	40.8	43.4
85°	18.8	18.8	18.3	17.9	18.3	17.9	18.3	18.8	19.2	20.4	22.5
87.5°	6.0	6.4	6.4	6.4	6.2	6.2	6.4	6.5	7.0	7.2	7.4
90°	9.9	10.1	8.6	7.3	5.9	4.5	3.3	2.6	1.8	1.1	0.3
92.5°	9.2	9.1	8.8	8.5	8.2	7.8	7.4	6.8	6.3	5.7	5.1
95°	18.4	18.4	18.3	18.2	18.0	17.9	17.5	16.9	16.2	15.7	15.0
97.5°	31.0	31.0	30.7	30.5	30.2	30.0	29.6	29.0	28.5	28.0	27.4
100°	39.8	39.8	39.5	39.4	39.1	39.0	38.6	38.2	37.6	37.1	36.6
102.5°	49.2	49.2	48.9	48.7	48.4	48.3	47.9	47.5	47.0	46.6	46.2
105°	63.5	63.3	63.3	63.1	63.0	62.9	62.7	62.5	62.3	62.1	62.0
107.5°	79.0	79.0	79.0	79.0	79.0	79.0	78.8	78.6	78.3	78.0	77.7
110°	89.6	89.6	89.6	89.6	89.6	89.6	89.4	89.0	88.6	88.2	87.9



TEST NUMBER: P331331-930

CATALOG NUMBER: SA2XXDIP-C675D330U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	100.3	100.4	100.4	100.5	100.5	100.6	100.4	100.0	99.7	99.3	98.9
115°	116.3	116.3	116.5	116.6	116.8	116.9	116.8	116.3	116.0	115.6	115.2
117.5°	132.0	132.2	132.5	132.9	133.2	133.6	133.5	133.0	132.5	132.0	131.4
120°	142.3	142.3	142.8	143.3	143.8	144.3	144.3	143.8	143.3	142.8	142.3
122.5°	153.2	153.4	153.7	154.1	154.4	154.8	154.7	154.0	153.4	152.8	152.2
125°	169.2	169.3	169.6	169.7	169.9	170.2	169.9	169.3	168.8	168.2	167.6
127.5°	184.7	184.9	185.2	185.4	185.6	185.8	185.6	184.8	184.2	183.4	182.7
130°	195.2	195.3	195.4	195.6	195.7	195.8	195.4	194.6	193.8	193.0	192.2
132.5°	205.6	205.9	205.9	205.9	205.8	205.8	205.5	204.7	204.1	203.4	202.8
135°	220.5	220.6	220.5	220.4	220.3	220.1	219.7	219.0	218.3	217.6	216.9
137.5°	235.1	235.1	235.0	234.8	234.6	234.5	234.2	233.6	232.9	232.4	231.8
140°	244.8	244.8	244.5	244.2	243.9	243.5	243.1	242.6	242.0	241.4	240.8
142.5°	253.6	253.6	253.4	253.2	252.9	252.7	252.3	251.8	251.2	250.6	250.1
145°	267.1	267.0	266.6	266.3	265.9	265.5	265.1	264.6	264.2	263.7	263.3
147.5°	278.8	278.7	278.4	278.2	277.9	277.6	277.2	276.7	276.1	275.7	275.1
150°	286.3	286.0	285.8	285.5	285.3	285.0	284.7	284.3	283.9	283.6	283.2
152.5°	293.7	293.4	293.1	292.8	292.4	292.2	291.8	291.5	291.1	290.7	290.3
155°	303.0	302.7	302.6	302.3	302.1	302.0	301.7	301.6	301.4	301.2	301.0
157.5°	311.7	311.3	311.1	311.0	311.0	310.8	310.7	310.5	310.4	310.3	310.1
160°	316.9	316.6	316.5	316.4	316.3	316.3	316.2	316.1	315.9	315.8	315.7
162.5°	321.6	321.1	321.1	321.1	321.0	320.9	320.9	320.8	320.8	320.8	320.7
165°	327.7	327.2	327.2	327.2	327.2	327.2	327.3	327.3	327.3	327.4	327.5
167.5°	332.6	332.2	332.2	332.2	332.2	332.3	332.4	332.6	332.8	333.0	333.1
170°	335.4	335.0	335.1	335.1	335.2	335.3	335.4	335.6	335.7	336.0	336.1
172.5°	337.5	337.0	337.1	337.2	337.3	337.3	337.5	337.6	337.9	338.0	338.2
175°	339.7	339.3	339.4	339.6	339.7	339.8	340.0	340.1	340.4	340.6	340.8
177.5°	341.0	340.6	340.7	340.9	341.0	341.0	341.2	341.4	341.4	341.6	341.8
180°	341.4	341.4	341.4	341.4	341.4	341.4	341.4	341.4	341.4	341.4	341.4



TEST NUMBER: P331331-930

CATALOG NUMBER: SA2XXDIP-C675D330U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0
2.5°	1088.6	1090.3	1095.6	1100.9	1106.9	1108.6	1111.3	1108.9	1108.2	1114.6	1119.2
5°	1091.7	1099.2	1113.8	1127.1	1138.3	1146.2	1154.5	1157.9	1164.1	1172.8	1183.7
7.5°	1088.2	1102.8	1125.7	1145.0	1166.2	1181.5	1193.4	1203.5	1215.8	1232.3	1250.4
10°	1084.2	1103.8	1131.6	1155.4	1181.1	1200.7	1217.0	1232.7	1251.1	1274.0	1297.7
12.5°	1076.8	1100.1	1135.0	1163.0	1196.1	1215.4	1237.3	1271.4	1291.0	1322.9	1356.3
15°	1062.2	1087.9	1136.6	1171.2	1208.6	1245.3	1285.6	1318.1	1350.5	1369.3	1416.3
17.5°	1040.2	1078.2	1132.0	1172.3	1219.9	1277.7	1323.0	1359.8	1397.3	1427.7	1451.2
20°	1022.6	1063.8	1125.4	1173.7	1230.3	1292.2	1344.3	1381.8	1414.2	1439.7	1454.2
22.5°	1000.3	1052.1	1112.1	1168.7	1241.0	1302.3	1357.0	1386.4	1413.6	1426.0	1431.6
25°	965.2	1027.6	1095.4	1164.5	1246.1	1311.0	1361.0	1378.8	1386.7	1374.7	1354.7
27.5°	927.3	996.9	1076.2	1156.7	1242.9	1305.4	1341.2	1338.3	1324.9	1285.9	1254.7
30°	898.9	975.6	1060.9	1148.7	1235.3	1296.0	1316.9	1296.0	1265.7	1222.0	1177.5
32.5°	869.4	948.6	1044.6	1137.3	1221.3	1274.7	1279.2	1243.4	1196.4	1146.7	1091.2
35°	824.5	910.2	1013.8	1112.1	1191.6	1225.3	1205.3	1142.1	1086.3	1018.5	942.6
37.5°	773.8	868.5	972.4	1075.1	1147.0	1155.8	1106.3	1039.7	961.0	881.3	792.1
40°	735.8	836.2	943.1	1046.8	1110.4	1101.2	1038.0	964.7	871.1	773.7	690.9
42.5°	701.9	802.2	911.1	1012.8	1063.8	1038.7	964.7	874.8	774.2	682.5	606.7
45°	643.0	746.2	857.8	956.0	985.1	939.8	842.0	742.1	643.0	566.5	506.5
47.5°	586.0	687.9	798.4	884.8	895.0	834.1	727.2	624.4	539.2	476.9	434.6
50°	544.0	646.4	755.8	832.8	829.5	755.8	646.0	548.1	477.0	426.6	398.3
52.5°	506.4	603.1	708.2	778.2	760.6	680.2	575.4	488.5	430.0	390.6	365.0
55°	447.8	537.3	637.2	693.4	660.9	571.9	483.2	413.3	370.0	340.5	320.5
57.5°	389.7	473.6	559.1	593.8	557.9	475.6	401.7	351.0	318.5	296.6	283.6
60°	353.8	427.1	503.2	533.1	490.2	417.0	358.7	313.4	287.1	269.3	257.6
62.5°	317.8	383.4	455.3	471.6	432.4	370.4	318.8	281.1	259.5	243.6	232.7
65°	268.9	322.5	377.1	387.9	351.7	303.9	263.0	238.5	219.3	207.7	198.9
67.5°	220.5	263.6	302.2	311.0	279.2	246.1	216.6	195.2	182.2	172.5	165.2
70°	191.8	226.0	257.6	264.7	239.3	209.8	187.3	170.2	158.6	150.3	143.2
72.5°	161.6	190.0	216.3	221.1	200.3	177.8	159.3	145.9	135.6	130.3	123.5
75°	123.6	140.2	160.6	161.9	148.1	134.4	120.3	111.5	106.2	99.5	96.1
77.5°	87.2	100.3	111.9	114.2	106.1	96.7	88.8	81.9	77.3	74.3	71.2
80°	66.6	77.0	82.0	84.9	79.1	72.4	67.8	63.3	60.3	58.3	56.2
82.5°	47.6	54.1	58.7	60.9	57.8	53.8	49.2	46.6	44.4	42.6	41.9
85°	24.1	27.1	30.0	30.8	30.0	28.3	25.8	25.8	24.5	24.1	24.1
87.5°	8.6	10.0	10.2	11.3	10.8	11.2	11.4	11.4	11.3	11.0	10.6
90°	1.1	1.8	2.6	3.3	4.5	5.9	7.3	8.6	10.1	9.9	9.9
92.5°	5.7	6.3	6.8	7.4	7.8	8.2	8.5	8.8	9.1	9.2	9.2
95°	15.7	16.2	16.9	17.5	17.9	18.0	18.2	18.3	18.4	18.4	18.4
97.5°	28.0	28.5	29.0	29.6	30.0	30.2	30.5	30.7	31.0	31.0	31.0
100°	37.1	37.6	38.2	38.6	39.0	39.1	39.4	39.5	39.8	39.8	39.8
102.5°	46.6	47.0	47.5	47.9	48.3	48.4	48.7	48.9	49.2	49.2	49.3
105°	62.1	62.3	62.5	62.7	62.9	63.0	63.1	63.3	63.3	63.5	63.6
107.5°	78.0	78.3	78.6	78.8	79.0	79.0	79.0	79.0	79.0	79.0	79.1
110°	88.2	88.6	89.0	89.4	89.6	89.6	89.6	89.6	89.6	89.6	89.6



TEST NUMBER: P331331-930

CATALOG NUMBER: SA2XXDIP-C675D330U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	99.3	99.7	100.0	100.4	100.6	100.5	100.5	100.4	100.4	100.3	100.1
115°	115.6	116.0	116.3	116.8	116.9	116.8	116.6	116.5	116.3	116.3	116.3
117.5°	132.0	132.5	133.0	133.5	133.6	133.2	132.9	132.5	132.2	132.0	131.8
120°	142.8	143.3	143.8	144.3	144.3	143.8	143.3	142.8	142.3	142.3	142.3
122.5°	152.8	153.4	154.0	154.7	154.8	154.4	154.1	153.7	153.4	153.2	153.0
125°	168.2	168.8	169.3	169.9	170.2	169.9	169.7	169.6	169.3	169.2	169.0
127.5°	183.4	184.2	184.8	185.6	185.8	185.6	185.4	185.2	184.9	184.7	184.5
130°	193.0	193.8	194.6	195.4	195.8	195.7	195.6	195.4	195.3	195.2	195.0
132.5°	203.4	204.1	204.7	205.5	205.8	205.8	205.9	205.9	205.9	205.6	205.3
135°	217.6	218.3	219.0	219.7	220.1	220.3	220.4	220.5	220.6	220.5	220.5
137.5°	232.4	232.9	233.6	234.2	234.5	234.6	234.8	235.0	235.1	235.1	235.1
140°	241.4	242.0	242.6	243.1	243.5	243.9	244.2	244.5	244.8	244.8	244.8
142.5°	250.6	251.2	251.8	252.3	252.7	252.9	253.2	253.4	253.6	253.6	253.7
145°	263.7	264.2	264.6	265.1	265.5	265.9	266.3	266.6	267.0	267.1	267.2
147.5°	275.7	276.1	276.7	277.2	277.6	277.9	278.2	278.4	278.7	278.8	278.9
150°	283.6	283.9	284.3	284.7	285.0	285.3	285.5	285.8	286.0	286.3	286.4
152.5°	290.7	291.1	291.5	291.8	292.2	292.4	292.8	293.1	293.4	293.7	293.9
155°	301.2	301.4	301.6	301.7	302.0	302.1	302.3	302.6	302.7	303.0	303.4
157.5°	310.3	310.4	310.5	310.7	310.8	311.0	311.0	311.1	311.3	311.7	312.1
160°	315.8	315.9	316.1	316.2	316.3	316.3	316.4	316.5	316.6	316.9	317.3
162.5°	320.8	320.8	320.8	320.9	320.9	321.0	321.1	321.1	321.1	321.6	322.0
165°	327.4	327.3	327.3	327.3	327.2	327.2	327.2	327.2	327.2	327.7	328.1
167.5°	333.0	332.8	332.6	332.4	332.3	332.2	332.2	332.2	332.2	332.6	333.1
170°	336.0	335.7	335.6	335.4	335.3	335.2	335.1	335.1	335.0	335.4	335.9
172.5°	338.0	337.9	337.6	337.5	337.3	337.3	337.2	337.1	337.0	337.5	337.9
175°	340.6	340.4	340.1	340.0	339.8	339.7	339.6	339.4	339.3	339.7	340.2
177.5°	341.6	341.4	341.4	341.2	341.0	341.0	340.9	340.7	340.6	341.0	341.3
180°	341.4	341.4	341.4	341.4	341.4	341.4	341.4	341.4	341.4	341.4	341.4



TEST NUMBER: P331331-930

CATALOG NUMBER: SA2XXDIP-C675D330U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0
2.5°	1123.2	1127.9	1127.9	1128.5	1133.9	1133.2	1132.9
5°	1195.3	1202.4	1203.2	1210.7	1215.7	1214.1	1209.5
7.5°	1263.3	1276.5	1286.5	1292.0	1298.6	1302.7	1300.9
10°	1317.3	1336.4	1348.1	1356.0	1365.5	1372.6	1370.1
12.5°	1366.2	1389.0	1405.0	1418.5	1419.8	1428.9	1422.7
15°	1442.5	1466.6	1469.2	1479.2	1487.1	1486.2	1486.6
17.5°	1467.8	1475.5	1477.1	1477.3	1477.4	1474.5	1468.2
20°	1458.7	1455.9	1448.8	1443.4	1433.8	1432.6	1424.2
22.5°	1416.2	1406.9	1389.2	1377.4	1362.5	1358.6	1356.3
25°	1332.3	1311.8	1283.5	1256.5	1249.0	1234.4	1238.6
27.5°	1217.2	1185.4	1154.7	1132.7	1112.8	1091.0	1097.2
30°	1136.2	1100.4	1057.1	1023.9	1002.7	981.8	978.0
32.5°	1039.7	987.2	938.9	909.6	877.1	864.0	849.5
35°	873.2	822.0	774.1	733.0	709.2	690.9	674.3
37.5°	723.4	664.5	625.9	592.5	575.4	564.8	567.5
40°	630.6	578.9	550.7	525.2	509.4	501.9	503.6
42.5°	555.3	516.7	493.3	476.0	464.8	460.6	459.7
45°	469.9	448.3	429.1	419.1	413.7	409.1	406.2
47.5°	411.6	394.0	383.2	377.2	372.5	367.9	367.8
50°	376.7	365.0	357.5	351.2	347.6	344.2	347.1
52.5°	350.0	339.3	331.9	326.3	324.9	321.9	321.8
55°	310.5	302.1	296.8	291.7	289.3	287.6	285.5
57.5°	274.5	266.6	261.6	258.4	253.7	252.0	251.4
60°	248.9	242.6	237.7	233.5	231.4	228.0	228.0
62.5°	225.3	219.0	214.3	211.2	207.7	206.4	206.8
65°	191.0	186.1	181.5	178.1	177.3	174.8	175.6
67.5°	159.6	156.2	151.4	149.6	148.0	146.7	145.7
70°	138.6	135.3	132.7	130.3	129.0	129.0	129.0
72.5°	120.9	116.9	115.4	112.3	113.0	111.7	110.4
75°	93.7	91.2	89.9	88.6	86.6	86.6	86.6
77.5°	68.9	68.2	66.7	65.3	64.8	64.4	64.6
80°	53.2	52.8	52.0	52.0	51.2	50.8	50.0
82.5°	40.9	39.9	39.4	39.1	38.9	38.8	38.6
85°	23.3	22.5	22.5	22.9	22.1	22.1	22.5
87.5°	10.9	10.9	10.6	10.6	10.9	10.6	10.6
90°	9.7	9.5	9.5	9.6	9.7	9.7	9.8
92.5°	9.2	9.3	9.3	9.3	9.3	9.3	9.3
95°	18.4	18.4	18.3	18.3	18.1	18.0	17.9
97.5°	31.0	31.0	31.0	31.0	31.0	31.0	30.9
100°	39.8	39.8	39.7	39.6	39.6	39.5	39.5
102.5°	49.3	49.4	49.4	49.3	49.2	49.2	49.2
105°	63.8	63.9	63.9	63.9	63.9	63.9	63.9
107.5°	79.2	79.2	79.1	78.8	78.5	78.2	77.9
110°	89.6	89.6	89.5	89.3	89.1	88.9	88.7



TEST NUMBER: P331331-930

CATALOG NUMBER: SA2XXDIP-C675D330U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	100.0	99.8	99.6	99.5	99.4	99.2	99.1
115°	116.2	116.1	116.0	115.8	115.6	115.4	115.2
117.5°	131.7	131.5	131.3	131.2	131.0	130.8	130.6
120°	142.3	142.3	142.2	142.0	141.8	141.6	141.5
122.5°	152.9	152.7	152.6	152.5	152.3	152.1	152.1
125°	168.8	168.6	168.4	168.4	168.4	168.3	168.2
127.5°	184.3	184.0	183.8	183.6	183.4	183.2	183.0
130°	194.9	194.8	194.6	194.4	194.0	193.8	193.6
132.5°	205.0	204.8	204.6	204.3	204.2	203.9	203.7
135°	220.5	220.4	220.3	220.0	219.9	219.7	219.5
137.5°	235.0	235.0	234.8	234.6	234.3	234.1	233.7
140°	244.8	244.8	244.7	244.4	244.2	243.9	243.7
142.5°	253.7	253.8	253.7	253.5	253.2	252.9	252.7
145°	267.2	267.3	267.2	266.9	266.7	266.4	266.1
147.5°	279.1	279.2	279.2	278.9	278.7	278.4	278.2
150°	286.6	286.8	286.8	286.6	286.4	286.3	286.0
152.5°	294.2	294.4	294.4	294.2	293.9	293.7	293.4
155°	303.7	304.0	304.1	303.9	303.7	303.5	303.3
157.5°	312.6	313.0	313.1	312.7	312.4	312.2	311.9
160°	317.7	318.1	318.1	317.9	317.6	317.4	317.2
162.5°	322.5	322.9	322.9	322.7	322.4	322.0	321.7
165°	328.6	329.0	329.1	328.7	328.4	328.1	327.8
167.5°	333.5	334.0	334.1	333.8	333.4	333.0	332.7
170°	336.3	336.8	336.8	336.5	336.1	335.7	335.3
172.5°	338.4	338.8	338.9	338.5	338.1	337.8	337.4
175°	340.6	341.1	341.1	340.8	340.4	340.0	339.6
177.5°	341.5	341.9	341.9	341.5	341.3	341.0	340.6
180°	341.4	341.4	341.4	341.4	341.4	341.4	341.4

(END OF REPORT)