

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333628-940

Luminaire Tested: **S125RDIP-S1270D1035U940-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333628-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S1270D1035U940-4F0-1E-UDD-A
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1035 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8077.8 lumens
Efficiency: N/A
Efficacy: 120.9 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 66.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333628-940

CATALOG NUMBER: S125RDIP-S1270D1035U940-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P333628-940

CATALOG NUMBER: S125RDIP-S1270D1035U940-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	86	86	86	72	72	72	60	60	60	54
1	99	95	91	88	92	88	85	82	76	74	71	64	63	61	54	53	52	47
2	91	84	78	73	84	78	73	68	67	63	60	57	54	52	48	46	44	40
3	83	74	67	61	77	69	63	57	59	55	51	51	47	44	43	40	38	34
4	76	66	58	52	70	61	54	49	53	48	44	46	41	38	38	36	33	30
5	70	59	51	45	65	55	48	42	48	42	38	41	37	33	35	32	29	26
6	65	53	45	39	60	49	42	37	43	37	33	37	33	29	32	28	26	23
7	60	48	40	34	55	45	38	33	39	33	29	34	29	26	29	25	23	20
8	55	43	36	30	51	41	34	29	36	30	26	31	27	23	27	23	21	18
9	52	40	32	27	48	37	30	26	33	27	23	29	24	21	25	21	19	16
10	48	36	29	24	45	34	28	23	30	25	21	26	22	19	23	19	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10936	10936	10936	10936
5°	12582	10950	9671	10950
10°	14432	10895	8533	10895
15°	15588	10783	7585	10783
20°	17189	10654	7003	10654
25°	19892	10481	6499	10481
30°	21647	10300	6169	10300
35°	18260	10089	5864	10089
40°	12752	9711	5602	9711
45°	9460	9199	5345	9199
50°	7543	8667	5126	8667
55°	6402	8007	4931	8007
60°	5531	7417	4615	7417
65°	4928	6776	3972	6776
70°	4330	6209	3622	6209
75°	3748	5375	3401	5375
80°	2841	4523	2841	4523
85°	2371	3557	2675	3557



TEST NUMBER: P333628-940

CATALOG NUMBER: S125RDIP-S1270D1035U940-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	162.4	2.0
10°-20°	475.9	5.9
20°-30°	754.5	9.3
30°-40°	909.8	11.3
40°-50°	812.5	10.1
50°-60°	623.1	7.7
60°-70°	404.9	5.0
70°-80°	196.9	2.4
80°-90°	49.5	0.6
90°-100°	43.6	0.5
100°-110°	269.0	3.3
110°-120°	487.9	6.0
120°-130°	626.1	7.8
130°-140°	673.4	8.3
140°-150°	632.1	7.8
150°-160°	511.3	6.3
160°-170°	330.7	4.1
170°-180°	114.1	1.4
0°-30°	1392.7	17.2
0°-40°	2302.6	28.5
0°-60°	3738.2	46.3
0°-90°	4389.5	54.3
90°-120°	800.5	9.9
90°-150°	2732.2	33.8
90°-180°	3688.0	45.7
0°-180°	8077.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1693	1693	1693	1693	1693	
5°	1941	1689	1492	1689	1941	194
15°	2331	1613	1134	1613	2331	668
25°	2792	1471	912	1471	2792	1282
35°	2316	1280	744	1280	2316	1399
45°	1036	1007	585	1007	1036	826
55°	569	711	438	711	569	516
65°	322	443	260	443	322	321
75°	150	215	136	215	150	160
85°	32	48	36	48	32	37
90°	21	1	21	1	21	11
95°	19	51	19	51	19	15
105°	264	262	264	262	264	239
115°	488	492	488	492	488	484
125°	699	699	699	699	699	622
135°	868	872	868	872	868	670
145°	1008	1011	1008	1011	1008	630
155°	1105	1113	1105	1113	1105	509
165°	1168	1174	1168	1174	1168	330
175°	1196	1201	1196	1201	1196	114
180°	1201	1201	1201	1201	1201	



TEST NUMBER: P333628-940

CATALOG NUMBER: S125RDIP-S1270D1035U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3
2.5°	1781.1	1780.0	1782.3	1776.1	1776.6	1767.2	1767.2	1760.0	1750.5	1743.3	1740.0
5°	1940.7	1942.1	1939.3	1928.9	1922.0	1911.6	1899.7	1878.8	1861.4	1844.8	1831.6
7.5°	2105.1	2106.0	2096.9	2093.6	2076.1	2063.3	2037.0	2008.7	1983.5	1951.6	1927.1
10°	2200.7	2200.0	2190.2	2182.6	2167.3	2147.9	2122.2	2088.7	2057.5	2022.8	1989.4
12.5°	2256.3	2254.5	2251.4	2242.1	2227.9	2210.7	2188.9	2156.1	2117.5	2079.5	2040.5
15°	2331.4	2326.5	2317.5	2305.6	2285.5	2265.3	2241.0	2211.8	2175.0	2131.9	2095.7
17.5°	2424.2	2424.4	2410.5	2394.1	2366.7	2331.1	2293.6	2246.4	2196.4	2148.9	2110.5
20°	2501.0	2498.8	2485.0	2453.0	2421.7	2377.2	2334.1	2276.4	2215.3	2153.4	2105.4
22.5°	2611.1	2605.7	2591.2	2549.2	2500.7	2443.4	2377.5	2307.0	2233.1	2162.8	2099.9
25°	2791.5	2787.3	2758.9	2710.2	2642.0	2553.8	2467.6	2371.0	2264.7	2172.2	2095.7
27.5°	2915.0	2910.4	2889.2	2848.8	2786.0	2693.1	2576.4	2447.3	2314.5	2187.4	2077.1
30°	2902.7	2913.1	2910.4	2891.6	2844.4	2760.9	2653.2	2507.9	2350.1	2200.7	2069.3
32.5°	2728.1	2737.5	2761.9	2798.7	2801.5	2768.1	2687.7	2553.5	2390.1	2220.2	2063.2
35°	2316.0	2328.6	2375.9	2450.2	2547.5	2628.9	2645.5	2573.3	2426.6	2243.8	2054.1
37.5°	1780.6	1849.0	1888.7	1967.0	2114.1	2263.7	2407.5	2460.5	2398.1	2234.1	2039.2
40°	1512.5	1529.2	1600.1	1688.4	1812.1	1967.8	2172.9	2320.9	2325.8	2211.8	2015.8
42.5°	1294.6	1315.7	1364.3	1434.9	1540.8	1696.5	1908.2	2103.5	2194.1	2150.6	1985.2
45°	1035.7	1051.7	1087.2	1141.4	1222.7	1351.3	1533.4	1759.3	1938.7	2008.8	1903.2
47.5°	850.8	859.4	890.3	931.6	991.8	1085.5	1226.5	1422.5	1637.6	1788.5	1773.6
50°	750.7	760.5	784.1	815.4	866.1	945.3	1057.9	1221.3	1443.1	1627.2	1664.1
52.5°	672.9	680.9	695.6	725.2	767.1	828.0	918.9	1066.7	1266.2	1462.0	1547.3
55°	568.6	574.2	585.9	602.6	636.1	679.8	758.3	860.5	1021.8	1219.2	1344.3
57.5°	482.7	485.4	492.9	508.4	531.5	563.5	620.2	706.8	822.4	1000.2	1138.3
60°	428.2	431.0	440.7	451.1	469.2	498.4	542.9	603.3	714.5	861.2	1000.9
62.5°	384.8	386.5	390.7	401.1	417.0	439.4	474.5	523.8	612.2	741.1	873.1
65°	322.5	323.2	324.6	333.0	342.7	359.4	382.3	417.1	483.8	581.1	697.9
67.5°	262.8	263.7	268.6	271.5	281.7	290.4	303.9	330.5	377.5	443.1	533.9
70°	229.3	228.7	233.5	237.0	240.5	250.9	259.9	281.5	310.7	360.8	436.5
72.5°	198.2	196.4	198.5	199.7	204.4	211.4	220.5	233.7	256.2	290.7	348.7
75°	150.2	150.9	150.9	152.2	155.7	158.5	161.2	168.2	180.7	203.7	235.0
77.5°	105.4	104.2	107.2	107.6	109.7	112.7	115.1	117.9	123.1	132.5	148.6
80°	76.4	76.4	77.1	79.3	78.6	79.9	83.4	86.2	92.5	98.0	103.5
82.5°	58.7	58.1	58.8	59.2	59.1	60.5	61.7	62.2	64.6	67.4	71.3
85°	32.0	32.0	32.6	32.6	33.3	33.3	34.1	34.1	34.1	34.8	35.5
87.5°	16.5	15.9	15.2	15.1	15.5	16.4	15.7	14.9	14.7	14.5	14.8
90°	21.4	20.8	20.2	19.6	19.0	18.2	17.2	16.2	15.2	14.3	12.8
92.5°	20.0	19.7	19.4	19.1	18.8	18.2	17.2	16.2	15.2	14.3	13.0
95°	18.7	18.7	18.7	18.7	18.7	18.2	17.2	16.2	15.2	14.3	21.8
97.5°	18.7	18.7	18.7	18.7	18.7	21.5	27.1	32.6	38.3	43.8	58.7
100°	18.7	19.5	20.2	21.0	21.8	37.0	66.5	95.9	125.5	154.9	154.1
102.5°	112.0	125.5	138.9	152.4	165.9	175.3	180.9	186.5	192.1	197.7	197.2
105°	264.4	264.7	264.8	265.0	265.2	265.3	265.3	265.3	265.3	265.3	265.3
107.5°	333.3	333.9	334.6	335.1	335.7	336.0	336.0	335.9	335.9	335.8	335.5
110°	381.0	380.8	380.7	380.5	380.3	380.5	381.0	381.7	382.3	382.8	382.5



TEST NUMBER: P333628-940

CATALOG NUMBER: S125RDIP-S1270D1035U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	423.8	424.1	424.4	424.6	424.9	425.4	426.1	427.0	427.7	428.5	428.2
115°	487.9	489.1	490.3	491.5	492.7	493.7	494.5	495.3	496.1	496.8	496.6
117.5°	556.2	556.8	557.3	557.9	558.3	559.1	560.2	561.2	562.2	563.2	562.5
120°	598.3	599.3	600.3	601.3	602.3	603.0	603.3	603.8	604.1	604.6	604.0
122.5°	638.2	639.4	640.5	641.7	642.7	643.5	644.0	644.4	644.7	645.2	644.9
125°	698.9	699.5	700.1	700.7	701.3	702.0	702.8	703.6	704.4	705.2	705.2
127.5°	750.0	751.5	753.0	754.4	755.9	756.8	757.2	757.7	758.1	758.6	758.7
130°	787.0	788.1	789.1	790.1	791.0	791.8	792.4	793.0	793.6	794.2	794.0
132.5°	821.3	822.2	823.2	824.2	825.2	825.7	825.9	826.0	826.1	826.3	826.7
135°	868.1	869.2	870.5	871.6	872.8	873.6	874.1	874.4	874.8	875.2	875.6
137.5°	915.1	916.1	917.1	918.2	919.2	919.7	919.6	919.5	919.4	919.4	919.7
140°	942.9	944.1	945.2	946.5	947.6	948.0	947.6	947.3	946.8	946.5	946.6
142.5°	969.2	970.4	971.6	972.8	974.0	974.6	974.5	974.4	974.3	974.2	973.9
145°	1007.9	1009.1	1010.2	1011.5	1012.6	1013.1	1012.9	1012.7	1012.5	1012.4	1012.4
147.5°	1039.7	1041.2	1042.6	1044.0	1045.4	1046.1	1045.8	1045.5	1045.4	1045.1	1044.8
150°	1060.4	1061.9	1063.5	1065.1	1066.8	1067.3	1066.9	1066.6	1066.1	1065.8	1065.3
152.5°	1079.6	1081.0	1082.4	1083.9	1085.3	1085.8	1085.5	1085.0	1084.7	1084.2	1083.9
155°	1104.9	1106.5	1108.0	1109.6	1111.3	1111.8	1111.2	1110.5	1110.0	1109.4	1108.9
157.5°	1126.1	1127.7	1129.3	1130.9	1132.5	1132.9	1132.3	1131.7	1131.0	1130.4	1130.3
160°	1139.6	1141.2	1142.8	1144.4	1145.9	1146.4	1145.6	1144.8	1144.0	1143.2	1143.0
162.5°	1151.7	1153.5	1155.2	1157.0	1158.7	1159.0	1157.9	1156.8	1155.7	1154.6	1154.4
165°	1168.1	1169.7	1171.3	1172.9	1174.5	1174.7	1173.5	1172.2	1171.1	1169.9	1169.7
167.5°	1179.6	1181.3	1183.1	1184.9	1186.7	1186.9	1185.4	1184.0	1182.6	1181.2	1180.9
170°	1186.0	1187.8	1189.5	1191.2	1193.0	1193.2	1191.6	1190.0	1188.4	1186.9	1186.6
172.5°	1190.3	1191.9	1193.7	1195.5	1197.3	1197.5	1196.1	1194.6	1193.2	1191.8	1191.4
175°	1195.7	1197.5	1199.3	1201.0	1202.8	1202.9	1201.4	1199.8	1198.2	1196.6	1196.4
177.5°	1198.9	1200.2	1201.5	1202.7	1204.0	1204.1	1203.0	1201.8	1200.8	1199.6	1199.5
180°	1201.0	1201.0	1201.0	1201.0	1201.0	1201.0	1201.0	1201.0	1201.0	1201.0	1201.0



TEST NUMBER: P333628-940

CATALOG NUMBER: S125RDIP-S1270D1035U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3
2.5°	1740.0	1736.1	1728.8	1722.2	1713.9	1706.6	1701.6	1695.5	1687.7	1678.3	1670.4
5°	1816.9	1801.7	1781.5	1764.2	1742.0	1724.6	1706.5	1689.1	1671.7	1649.5	1630.0
7.5°	1902.4	1870.8	1840.0	1801.4	1766.4	1735.1	1705.0	1674.6	1644.8	1613.3	1582.9
10°	1954.6	1916.4	1874.0	1825.3	1780.8	1738.5	1699.5	1661.3	1621.0	1585.6	1547.3
12.5°	2003.6	1954.2	1905.7	1844.2	1790.8	1739.0	1689.5	1641.8	1598.7	1552.7	1511.7
15°	2047.7	1999.1	1944.9	1869.8	1795.5	1732.9	1674.5	1612.7	1559.1	1507.7	1461.8
17.5°	2064.8	2013.8	1950.9	1878.7	1797.4	1718.7	1643.5	1575.7	1512.7	1452.8	1401.1
20°	2058.2	2008.8	1944.2	1875.4	1788.5	1706.5	1625.1	1550.1	1479.9	1416.6	1361.7
22.5°	2042.1	1991.0	1928.6	1855.9	1773.4	1686.5	1599.6	1519.5	1445.9	1380.5	1320.5
25°	2017.9	1948.4	1884.5	1813.5	1735.0	1648.8	1559.1	1470.8	1392.3	1325.5	1260.3
27.5°	1992.7	1905.9	1824.6	1754.2	1671.2	1594.3	1507.8	1417.3	1334.7	1266.8	1199.7
30°	1969.9	1872.6	1782.9	1703.0	1624.4	1551.5	1469.5	1381.2	1296.4	1226.2	1158.1
32.5°	1941.5	1838.1	1739.5	1647.3	1571.6	1499.2	1425.0	1340.6	1258.0	1185.5	1116.3
35°	1905.9	1773.9	1666.9	1568.9	1484.7	1414.5	1347.8	1279.7	1196.9	1121.9	1054.4
37.5°	1859.2	1709.4	1585.6	1478.7	1390.1	1319.6	1266.9	1204.6	1129.1	1057.2	994.7
40°	1830.9	1662.7	1527.1	1421.5	1328.3	1253.9	1204.6	1151.8	1083.0	1015.6	953.0
42.5°	1793.1	1619.9	1468.2	1358.1	1264.4	1192.8	1142.9	1096.7	1039.0	975.5	908.5
45°	1719.0	1536.9	1377.7	1259.5	1165.0	1094.8	1048.2	1007.2	963.4	905.0	846.6
47.5°	1622.5	1450.3	1283.7	1154.7	1062.1	996.9	951.7	919.4	888.1	838.4	781.7
50°	1545.2	1379.1	1216.4	1091.3	992.6	930.8	888.3	862.6	834.1	788.9	741.6
52.5°	1454.0	1305.6	1146.4	1018.4	925.3	867.4	826.6	800.9	777.4	740.6	695.5
55°	1310.3	1180.3	1034.3	918.2	832.8	774.4	735.4	711.1	697.2	665.9	630.4
57.5°	1144.4	1051.2	922.6	810.7	735.0	677.3	648.8	628.1	612.4	590.3	565.3
60°	1028.8	963.4	848.0	741.6	672.2	617.2	591.6	574.2	559.5	540.8	521.3
62.5°	911.4	863.9	763.5	672.2	608.2	562.2	538.1	522.5	505.6	492.9	474.0
65°	754.2	711.8	642.3	570.7	511.6	474.7	457.4	443.4	433.0	419.1	405.9
67.5°	586.7	569.4	521.5	472.1	429.7	396.9	381.9	372.2	359.6	351.3	342.2
70°	483.8	475.5	441.4	408.8	369.1	346.9	333.0	328.8	313.5	305.1	298.9
72.5°	392.6	388.7	369.1	346.4	318.5	299.0	286.2	281.5	271.8	265.1	261.1
75°	269.0	270.4	266.9	252.4	241.9	229.3	218.3	215.4	208.6	203.0	199.5
77.5°	170.1	177.3	177.5	176.8	172.6	165.1	160.4	158.4	151.5	149.5	148.6
80°	116.8	124.4	131.3	130.6	129.3	127.2	123.8	121.6	118.2	116.1	114.7
82.5°	77.8	85.0	90.8	94.5	94.3	92.2	89.8	88.8	88.1	86.6	86.3
85°	36.8	38.3	40.3	45.2	48.7	49.3	48.7	48.0	45.8	46.5	47.3
87.5°	15.1	14.8	15.1	14.8	13.9	16.4	17.7	18.0	17.2	16.4	15.6
90°	11.5	10.1	8.7	7.2	5.6	4.0	2.5	0.9	2.5	4.0	5.6
92.5°	11.8	10.5	9.4	9.3	10.3	11.5	12.6	13.7	12.6	11.5	10.3
95°	29.2	36.8	44.3	48.4	49.0	49.6	50.1	50.7	50.1	49.6	49.0
97.5°	73.6	88.5	103.3	110.2	109.1	108.1	107.0	105.9	107.0	108.1	109.1
100°	153.4	152.6	151.8	151.1	150.4	149.9	149.3	148.6	149.3	149.9	150.4
102.5°	196.7	196.3	195.7	195.1	194.4	193.7	192.9	192.2	192.9	193.7	194.4
105°	265.3	265.3	265.3	264.9	264.1	263.3	262.5	261.7	262.5	263.3	264.1
107.5°	335.0	334.7	334.2	334.0	334.0	334.0	334.0	334.0	334.0	334.0	334.0
110°	382.1	381.7	381.3	381.0	381.0	381.0	381.0	381.0	381.0	381.0	381.0



TEST NUMBER: P333628-940

CATALOG NUMBER: S125RDIP-S1270D1035U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	427.9	427.8	427.5	427.1	426.7	426.1	425.7	425.3	425.7	426.1	426.7
115°	496.4	496.2	496.1	495.4	494.5	493.5	492.5	491.5	492.5	493.5	494.5
117.5°	561.7	561.0	560.3	559.9	559.9	559.9	560.0	560.0	560.0	559.9	559.9
120°	603.3	602.8	602.2	602.0	602.2	602.4	602.5	602.8	602.5	602.4	602.2
122.5°	644.6	644.4	644.0	643.5	642.7	642.0	641.2	640.5	641.2	642.0	642.7
125°	705.2	705.2	705.2	704.5	703.1	701.7	700.3	698.9	700.3	701.7	703.1
127.5°	758.8	758.9	759.0	758.6	757.6	756.6	755.6	754.7	755.6	756.6	757.6
130°	793.8	793.6	793.4	792.8	791.8	790.9	789.9	788.8	789.9	790.9	791.8
132.5°	827.2	827.5	828.0	827.6	826.4	825.4	824.2	823.0	824.2	825.4	826.4
135°	876.0	876.4	876.8	876.4	875.2	874.1	872.8	871.6	872.8	874.1	875.2
137.5°	920.1	920.4	920.8	920.4	919.4	918.4	917.4	916.3	917.4	918.4	919.4
140°	946.8	947.0	947.3	947.1	946.7	946.4	945.9	945.6	945.9	946.4	946.7
142.5°	973.7	973.4	973.1	972.9	972.6	972.4	972.1	971.9	972.1	972.4	972.6
145°	1012.4	1012.4	1012.4	1012.1	1011.7	1011.3	1010.9	1010.6	1010.9	1011.3	1011.7
147.5°	1044.6	1044.4	1044.1	1044.0	1044.1	1044.2	1044.3	1044.4	1044.3	1044.2	1044.1
150°	1065.0	1064.5	1064.2	1064.2	1064.5	1065.0	1065.3	1065.8	1065.3	1065.0	1064.5
152.5°	1083.4	1083.1	1082.7	1082.9	1083.8	1084.7	1085.6	1086.4	1085.6	1084.7	1083.8
155°	1108.6	1108.2	1107.8	1108.2	1109.4	1110.5	1111.8	1112.9	1111.8	1110.5	1109.4
157.5°	1130.3	1130.2	1130.2	1130.6	1131.3	1132.0	1132.7	1133.4	1132.7	1132.0	1131.3
160°	1142.8	1142.6	1142.4	1142.9	1144.1	1145.3	1146.5	1147.6	1146.5	1145.3	1144.1
162.5°	1154.2	1154.0	1153.8	1154.3	1155.5	1156.6	1157.9	1159.0	1157.9	1156.6	1155.5
165°	1169.5	1169.3	1169.1	1169.7	1170.8	1172.0	1173.1	1174.4	1173.1	1172.0	1170.8
167.5°	1180.7	1180.5	1180.4	1180.9	1182.1	1183.3	1184.5	1185.8	1184.5	1183.3	1182.1
170°	1186.4	1186.2	1186.1	1186.6	1188.0	1189.4	1190.8	1192.1	1190.8	1189.4	1188.0
172.5°	1191.1	1190.7	1190.4	1190.9	1192.3	1193.6	1195.1	1196.4	1195.1	1193.6	1192.3
175°	1196.2	1196.1	1195.9	1196.3	1197.5	1198.7	1199.9	1201.0	1199.9	1198.7	1197.5
177.5°	1199.4	1199.2	1199.0	1199.4	1200.3	1201.3	1202.3	1203.2	1202.3	1201.3	1200.3
180°	1201.0	1201.0	1201.0	1201.0	1201.0	1201.0	1201.0	1201.0	1201.0	1201.0	1201.0



TEST NUMBER: P333628-940

CATALOG NUMBER: S125RDIP-S1270D1035U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3
2.5°	1664.9	1657.2	1651.5	1640.4	1632.6	1629.3	1623.2	1621.5	1627.6	1623.2	1622.6
5°	1615.4	1595.3	1579.3	1563.3	1545.9	1534.8	1518.1	1515.3	1511.2	1504.9	1503.5
7.5°	1556.0	1529.8	1509.2	1482.8	1459.8	1441.4	1420.5	1410.6	1405.2	1397.1	1386.3
10°	1516.0	1484.7	1457.0	1430.5	1402.0	1379.1	1358.3	1342.2	1331.8	1322.1	1317.9
12.5°	1476.5	1444.7	1409.1	1377.2	1345.3	1319.6	1296.5	1286.1	1274.5	1263.1	1253.4
15°	1415.2	1372.8	1333.9	1297.1	1270.0	1242.2	1219.9	1204.6	1187.2	1182.4	1163.6
17.5°	1350.1	1308.6	1263.0	1224.2	1192.8	1162.2	1137.7	1120.3	1107.3	1089.4	1080.8
20°	1309.6	1260.3	1215.8	1180.3	1145.5	1109.4	1084.3	1069.8	1057.2	1042.7	1035.7
22.5°	1266.2	1218.0	1172.3	1130.8	1095.5	1059.9	1042.1	1027.0	1012.7	999.3	990.1
25°	1202.6	1153.9	1105.9	1062.8	1026.0	1000.2	979.4	962.0	954.4	941.2	931.4
27.5°	1139.5	1087.8	1038.0	995.1	966.2	940.8	923.6	909.9	896.1	884.6	876.1
30°	1098.9	1046.2	991.9	957.9	927.3	902.9	884.1	870.9	860.5	850.1	843.8
32.5°	1058.4	1003.9	955.7	918.9	890.0	869.0	849.7	837.0	826.1	814.5	807.2
35°	993.3	937.7	898.8	862.6	834.1	814.7	801.5	783.4	774.4	766.0	758.3
37.5°	932.8	881.1	839.0	807.3	782.6	763.2	746.1	736.4	725.2	717.7	711.4
40°	888.3	841.1	802.8	769.5	751.4	729.9	713.9	701.3	693.0	683.3	676.4
42.5°	848.3	804.4	767.2	737.3	714.7	696.5	681.1	668.5	658.0	651.0	645.2
45°	791.8	748.0	711.8	683.9	663.2	645.8	629.7	623.5	609.6	601.3	598.5
47.5°	733.2	694.0	659.1	633.5	612.1	595.7	580.7	567.9	560.3	552.1	547.6
50°	693.8	656.2	623.5	598.5	577.7	559.5	545.6	537.3	526.9	519.2	513.7
52.5°	654.2	619.5	586.8	562.8	544.8	526.7	511.2	502.8	492.9	488.1	484.2
55°	597.8	561.0	533.2	509.5	490.7	474.0	459.5	451.1	444.9	440.0	438.6
57.5°	533.9	504.6	478.8	457.5	438.0	422.3	409.6	401.6	396.1	395.4	391.2
60°	492.1	465.7	442.1	419.1	402.4	387.9	376.7	367.7	362.1	361.4	360.1
62.5°	450.4	425.1	403.1	383.0	368.0	353.9	343.4	333.2	329.9	326.5	323.3
65°	388.5	365.6	347.6	331.5	315.6	303.7	293.4	287.0	279.5	275.3	267.6
67.5°	327.8	310.0	292.7	279.2	266.6	255.4	246.7	237.5	232.3	229.0	223.4
70°	287.8	273.8	256.5	241.9	232.2	223.1	216.2	205.7	202.2	199.5	196.7
72.5°	249.9	237.7	223.1	211.3	201.6	193.1	185.0	180.1	176.7	173.9	172.3
75°	196.7	184.9	172.4	164.1	157.1	150.2	146.0	142.5	141.1	140.4	137.6
77.5°	144.5	138.2	128.1	121.5	116.9	114.1	110.4	108.6	108.4	105.4	104.4
80°	110.5	107.0	98.7	95.9	92.5	89.7	87.6	84.1	80.6	79.3	77.1
82.5°	82.1	78.6	75.3	70.9	67.9	66.3	64.2	63.0	63.4	61.4	60.5
85°	43.8	40.3	39.0	38.3	36.8	38.3	37.5	36.8	36.1	35.5	36.1
87.5°	15.3	15.6	15.3	16.8	15.3	16.2	16.4	16.1	16.2	16.4	16.1
90°	7.2	8.7	10.1	11.5	12.8	14.3	15.2	16.2	17.2	18.2	19.0
92.5°	9.3	9.4	10.5	11.8	13.0	14.3	15.2	16.2	17.2	18.2	18.8
95°	48.4	44.3	36.8	29.2	21.8	14.3	15.2	16.2	17.2	18.2	18.7
97.5°	110.2	103.3	88.5	73.6	58.7	43.8	38.3	32.6	27.1	21.5	18.7
100°	151.1	151.8	152.6	153.4	154.1	154.9	125.5	95.9	66.5	37.0	21.8
102.5°	195.1	195.7	196.3	196.7	197.2	197.7	192.1	186.5	180.9	175.3	165.9
105°	264.9	265.3	265.3	265.3	265.3	265.3	265.3	265.3	265.3	265.3	265.2
107.5°	334.0	334.2	334.7	335.0	335.5	335.8	335.9	335.9	336.0	336.0	335.7
110°	381.0	381.3	381.7	382.1	382.5	382.8	382.3	381.7	381.0	380.5	380.3



TEST NUMBER: P333628-940

CATALOG NUMBER: S125RDIP-S1270D1035U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	427.1	427.5	427.8	427.9	428.2	428.5	427.7	427.0	426.1	425.4	424.9
115°	495.4	496.1	496.2	496.4	496.6	496.8	496.1	495.3	494.5	493.7	492.7
117.5°	559.9	560.3	561.0	561.7	562.5	563.2	562.2	561.2	560.2	559.1	558.3
120°	602.0	602.2	602.8	603.3	604.0	604.6	604.1	603.8	603.3	603.0	602.3
122.5°	643.5	644.0	644.4	644.6	644.9	645.2	644.7	644.4	644.0	643.5	642.7
125°	704.5	705.2	705.2	705.2	705.2	705.2	704.4	703.6	702.8	702.0	701.3
127.5°	758.6	759.0	758.9	758.8	758.7	758.6	758.1	757.7	757.2	756.8	755.9
130°	792.8	793.4	793.6	793.8	794.0	794.2	793.6	793.0	792.4	791.8	791.0
132.5°	827.6	828.0	827.5	827.2	826.7	826.3	826.1	826.0	825.9	825.7	825.2
135°	876.4	876.8	876.4	876.0	875.6	875.2	874.8	874.4	874.1	873.6	872.8
137.5°	920.4	920.8	920.4	920.1	919.7	919.4	919.4	919.5	919.6	919.7	919.2
140°	947.1	947.3	947.0	946.8	946.6	946.5	946.8	947.3	947.6	948.0	947.6
142.5°	972.9	973.1	973.4	973.7	973.9	974.2	974.3	974.4	974.5	974.6	974.0
145°	1012.1	1012.4	1012.4	1012.4	1012.4	1012.4	1012.5	1012.7	1012.9	1013.1	1012.6
147.5°	1044.0	1044.1	1044.4	1044.6	1044.8	1045.1	1045.4	1045.5	1045.8	1046.1	1045.4
150°	1064.2	1064.2	1064.5	1065.0	1065.3	1065.8	1066.1	1066.6	1066.9	1067.3	1066.8
152.5°	1082.9	1082.7	1083.1	1083.4	1083.9	1084.2	1084.7	1085.0	1085.5	1085.8	1085.3
155°	1108.2	1107.8	1108.2	1108.6	1108.9	1109.4	1110.0	1110.5	1111.2	1111.8	1111.3
157.5°	1130.6	1130.2	1130.2	1130.3	1130.3	1130.4	1131.0	1131.7	1132.3	1132.9	1132.5
160°	1142.9	1142.4	1142.6	1142.8	1143.0	1143.2	1144.0	1144.8	1145.6	1146.4	1145.9
162.5°	1154.3	1153.8	1154.0	1154.2	1154.4	1154.6	1155.7	1156.8	1157.9	1159.0	1158.7
165°	1169.7	1169.1	1169.3	1169.5	1169.7	1169.9	1171.1	1172.2	1173.5	1174.7	1174.5
167.5°	1180.9	1180.4	1180.5	1180.7	1180.9	1181.2	1182.6	1184.0	1185.4	1186.9	1186.7
170°	1186.6	1186.1	1186.2	1186.4	1186.6	1186.9	1188.4	1190.0	1191.6	1193.2	1193.0
172.5°	1190.9	1190.4	1190.7	1191.1	1191.4	1191.8	1193.2	1194.6	1196.1	1197.5	1197.3
175°	1196.3	1195.9	1196.1	1196.2	1196.4	1196.6	1198.2	1199.8	1201.4	1202.9	1202.8
177.5°	1199.4	1199.0	1199.2	1199.4	1199.5	1199.6	1200.8	1201.8	1203.0	1204.1	1204.0
180°	1201.0	1201.0	1201.0	1201.0	1201.0	1201.0	1201.0	1201.0	1201.0	1201.0	1201.0



TEST NUMBER: P333628-940

CATALOG NUMBER: S125RDIP-S1270D1035U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3
2.5°	1622.1	1616.0	1614.3	1616.5	1614.3	1616.0	1622.1	1622.6	1623.2	1627.6	1621.5
5°	1496.6	1489.6	1493.1	1491.7	1493.1	1489.6	1496.6	1503.5	1504.9	1511.2	1515.3
7.5°	1386.2	1377.5	1368.3	1371.3	1368.3	1377.5	1386.2	1386.3	1397.1	1405.2	1410.6
10°	1308.9	1301.9	1297.7	1301.2	1297.7	1301.9	1308.9	1317.9	1322.1	1331.8	1342.2
12.5°	1243.8	1239.7	1236.0	1234.5	1236.0	1239.7	1243.8	1253.4	1263.1	1274.5	1286.1
15°	1155.2	1146.9	1143.4	1134.4	1143.4	1146.9	1155.2	1163.6	1182.4	1187.2	1204.6
17.5°	1073.6	1070.9	1061.8	1057.9	1061.8	1070.9	1073.6	1080.8	1089.4	1107.3	1120.3
20°	1025.3	1022.5	1013.4	1019.0	1013.4	1022.5	1025.3	1035.7	1042.7	1057.2	1069.8
22.5°	985.3	979.1	976.2	974.6	976.2	979.1	985.3	990.1	999.3	1012.7	1027.0
25°	928.6	919.6	916.1	912.0	916.1	919.6	928.6	931.4	941.2	954.4	962.0
27.5°	872.2	867.4	862.7	861.7	862.7	867.4	872.2	876.1	884.6	896.1	909.9
30°	835.5	830.6	827.2	827.2	827.2	830.6	835.5	843.8	850.1	860.5	870.9
32.5°	802.7	799.0	795.5	795.0	795.5	799.0	802.7	807.2	814.5	826.1	837.0
35°	754.9	749.3	748.0	743.8	748.0	749.3	754.9	758.3	766.0	774.4	783.4
37.5°	705.3	700.6	700.5	700.1	700.5	700.6	705.3	711.4	717.7	725.2	736.4
40°	673.5	670.0	669.4	664.5	669.4	670.0	673.5	676.4	683.3	693.0	701.3
42.5°	639.6	637.8	635.4	633.4	635.4	637.8	639.6	645.2	651.0	658.0	668.5
45°	593.6	588.7	588.7	585.2	588.7	588.7	593.6	598.5	601.3	609.6	623.5
47.5°	546.1	542.3	542.7	539.1	542.7	542.3	546.1	547.6	552.1	560.3	567.9
50°	514.3	512.3	511.6	510.2	511.6	512.3	514.3	513.7	519.2	526.9	537.3
52.5°	482.7	481.7	484.4	481.3	484.4	481.7	482.7	484.2	488.1	492.9	502.8
55°	440.0	437.9	442.1	437.9	442.1	437.9	440.0	438.6	440.0	444.9	451.1
57.5°	390.9	389.0	392.7	390.7	392.7	389.0	390.9	391.2	395.4	396.1	401.6
60°	358.6	354.5	356.6	357.3	356.6	354.5	358.6	360.1	361.4	362.1	367.7
62.5°	320.3	317.8	319.3	316.1	319.3	317.8	320.3	323.3	326.5	329.9	333.2
65°	266.3	264.1	261.4	259.9	261.4	264.1	266.3	267.6	275.3	279.5	287.0
67.5°	223.6	218.6	218.6	219.6	218.6	218.6	223.6	223.4	229.0	232.3	237.5
70°	192.5	192.5	191.8	191.8	191.8	192.5	192.5	196.7	199.5	202.2	205.7
72.5°	170.9	170.3	169.1	168.5	169.1	170.3	170.9	172.3	173.9	176.7	180.1
75°	137.6	138.3	137.0	136.3	137.0	138.3	137.6	137.6	140.4	141.1	142.5
77.5°	101.7	98.7	100.2	98.7	100.2	98.7	101.7	104.4	105.4	108.4	108.6
80°	77.1	76.4	78.6	76.4	78.6	76.4	77.1	77.1	79.3	80.6	84.1
82.5°	61.0	60.4	61.3	59.7	61.3	60.4	61.0	60.5	61.4	63.4	63.0
85°	36.8	36.1	35.5	36.1	35.5	36.1	36.8	36.1	35.5	36.1	36.8
87.5°	16.7	16.2	16.4	16.5	16.4	16.2	16.7	16.1	16.4	16.2	16.1
90°	19.6	20.2	20.8	21.4	20.8	20.2	19.6	19.0	18.2	17.2	16.2
92.5°	19.1	19.4	19.7	20.0	19.7	19.4	19.1	18.8	18.2	17.2	16.2
95°	18.7	18.7	18.7	18.7	18.7	18.7	18.7	18.7	18.2	17.2	16.2
97.5°	18.7	18.7	18.7	18.7	18.7	18.7	18.7	18.7	21.5	27.1	32.6
100°	21.0	20.2	19.5	18.7	19.5	20.2	21.0	21.8	37.0	66.5	95.9
102.5°	152.4	138.9	125.5	112.0	125.5	138.9	152.4	165.9	175.3	180.9	186.5
105°	265.0	264.8	264.7	264.4	264.7	264.8	265.0	265.2	265.3	265.3	265.3
107.5°	335.1	334.6	333.9	333.3	333.9	334.6	335.1	335.7	336.0	336.0	335.9
110°	380.5	380.7	380.8	381.0	380.8	380.7	380.5	380.3	380.5	381.0	381.7



TEST NUMBER: P333628-940

CATALOG NUMBER: S125RDIP-S1270D1035U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	424.6	424.4	424.1	423.8	424.1	424.4	424.6	424.9	425.4	426.1	427.0
115°	491.5	490.3	489.1	487.9	489.1	490.3	491.5	492.7	493.7	494.5	495.3
117.5°	557.9	557.3	556.8	556.2	556.8	557.3	557.9	558.3	559.1	560.2	561.2
120°	601.3	600.3	599.3	598.3	599.3	600.3	601.3	602.3	603.0	603.3	603.8
122.5°	641.7	640.5	639.4	638.2	639.4	640.5	641.7	642.7	643.5	644.0	644.4
125°	700.7	700.1	699.5	698.9	699.5	700.1	700.7	701.3	702.0	702.8	703.6
127.5°	754.4	753.0	751.5	750.0	751.5	753.0	754.4	755.9	756.8	757.2	757.7
130°	790.1	789.1	788.1	787.0	788.1	789.1	790.1	791.0	791.8	792.4	793.0
132.5°	824.2	823.2	822.2	821.3	822.2	823.2	824.2	825.2	825.7	825.9	826.0
135°	871.6	870.5	869.2	868.1	869.2	870.5	871.6	872.8	873.6	874.1	874.4
137.5°	918.2	917.1	916.1	915.1	916.1	917.1	918.2	919.2	919.7	919.6	919.5
140°	946.5	945.2	944.1	942.9	944.1	945.2	946.5	947.6	948.0	947.6	947.3
142.5°	972.8	971.6	970.4	969.2	970.4	971.6	972.8	974.0	974.6	974.5	974.4
145°	1011.5	1010.2	1009.1	1007.9	1009.1	1010.2	1011.5	1012.6	1013.1	1012.9	1012.7
147.5°	1044.0	1042.6	1041.2	1039.7	1041.2	1042.6	1044.0	1045.4	1046.1	1045.8	1045.5
150°	1065.1	1063.5	1061.9	1060.4	1061.9	1063.5	1065.1	1066.8	1067.3	1066.9	1066.6
152.5°	1083.9	1082.4	1081.0	1079.6	1081.0	1082.4	1083.9	1085.3	1085.8	1085.5	1085.0
155°	1109.6	1108.0	1106.5	1104.9	1106.5	1108.0	1109.6	1111.3	1111.8	1111.2	1110.5
157.5°	1130.9	1129.3	1127.7	1126.1	1127.7	1129.3	1130.9	1132.5	1132.9	1132.3	1131.7
160°	1144.4	1142.8	1141.2	1139.6	1141.2	1142.8	1144.4	1145.9	1146.4	1145.6	1144.8
162.5°	1157.0	1155.2	1153.5	1151.7	1153.5	1155.2	1157.0	1158.7	1159.0	1157.9	1156.8
165°	1172.9	1171.3	1169.7	1168.1	1169.7	1171.3	1172.9	1174.5	1174.7	1173.5	1172.2
167.5°	1184.9	1183.1	1181.3	1179.6	1181.3	1183.1	1184.9	1186.7	1186.9	1185.4	1184.0
170°	1191.2	1189.5	1187.8	1186.0	1187.8	1189.5	1191.2	1193.0	1193.2	1191.6	1190.0
172.5°	1195.5	1193.7	1191.9	1190.3	1191.9	1193.7	1195.5	1197.3	1197.5	1196.1	1194.6
175°	1201.0	1199.3	1197.5	1195.7	1197.5	1199.3	1201.0	1202.8	1202.9	1201.4	1199.8
177.5°	1202.7	1201.5	1200.2	1198.9	1200.2	1201.5	1202.7	1204.0	1204.1	1203.0	1201.8
180°	1201.0	1201.0	1201.0	1201.0	1201.0	1201.0	1201.0	1201.0	1201.0	1201.0	1201.0



TEST NUMBER: P333628-940

CATALOG NUMBER: S125RDIP-S1270D1035U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3
2.5°	1623.2	1629.3	1632.6	1640.4	1651.5	1657.2	1664.9	1670.4	1678.3	1687.7	1695.5
5°	1518.1	1534.8	1545.9	1563.3	1579.3	1595.3	1615.4	1630.0	1649.5	1671.7	1689.1
7.5°	1420.5	1441.4	1459.8	1482.8	1509.2	1529.8	1556.0	1582.9	1613.3	1644.8	1674.6
10°	1358.3	1379.1	1402.0	1430.5	1457.0	1484.7	1516.0	1547.3	1585.6	1621.0	1661.3
12.5°	1296.5	1319.6	1345.3	1377.2	1409.1	1444.7	1476.5	1511.7	1552.7	1598.7	1641.8
15°	1219.9	1242.2	1270.0	1297.1	1333.9	1372.8	1415.2	1461.8	1507.7	1559.1	1612.7
17.5°	1137.7	1162.2	1192.8	1224.2	1263.0	1308.6	1350.1	1401.1	1452.8	1512.7	1575.7
20°	1084.3	1109.4	1145.5	1180.3	1215.8	1260.3	1309.6	1361.7	1416.6	1479.9	1550.1
22.5°	1042.1	1059.9	1095.5	1130.8	1172.3	1218.0	1266.2	1320.5	1380.5	1445.9	1519.5
25°	979.4	1000.2	1026.0	1062.8	1105.9	1153.9	1202.6	1260.3	1325.5	1392.3	1470.8
27.5°	923.6	940.8	966.2	995.1	1038.0	1087.8	1139.5	1199.7	1266.8	1334.7	1417.3
30°	884.1	902.9	927.3	957.9	991.9	1046.2	1098.9	1158.1	1226.2	1296.4	1381.2
32.5°	849.7	869.0	890.0	918.9	955.7	1003.9	1058.4	1116.3	1185.5	1258.0	1340.6
35°	801.5	814.7	834.1	862.6	898.8	937.7	993.3	1054.4	1121.9	1196.9	1279.7
37.5°	746.1	763.2	782.6	807.3	839.0	881.1	932.8	994.7	1057.2	1129.1	1204.6
40°	713.9	729.9	751.4	769.5	802.8	841.1	888.3	953.0	1015.6	1083.0	1151.8
42.5°	681.1	696.5	714.7	737.3	767.2	804.4	848.3	908.5	975.5	1039.0	1096.7
45°	629.7	645.8	663.2	683.9	711.8	748.0	791.8	846.6	905.0	963.4	1007.2
47.5°	580.7	595.7	612.1	633.5	659.1	694.0	733.2	781.7	838.4	888.1	919.4
50°	545.6	559.5	577.7	598.5	623.5	656.2	693.8	741.6	788.9	834.1	862.6
52.5°	511.2	526.7	544.8	562.8	586.8	619.5	654.2	695.5	740.6	777.4	800.9
55°	459.5	474.0	490.7	509.5	533.2	561.0	597.8	630.4	665.9	697.2	711.1
57.5°	409.6	422.3	438.0	457.5	478.8	504.6	533.9	565.3	590.3	612.4	628.1
60°	376.7	387.9	402.4	419.1	442.1	465.7	492.1	521.3	540.8	559.5	574.2
62.5°	343.4	353.9	368.0	383.0	403.1	425.1	450.4	474.0	492.9	505.6	522.5
65°	293.4	303.7	315.6	331.5	347.6	365.6	388.5	405.9	419.1	433.0	443.4
67.5°	246.7	255.4	266.6	279.2	292.7	310.0	327.8	342.2	351.3	359.6	372.2
70°	216.2	223.1	232.2	241.9	256.5	273.8	287.8	298.9	305.1	313.5	328.8
72.5°	185.0	193.1	201.6	211.3	223.1	237.7	249.9	261.1	265.1	271.8	281.5
75°	146.0	150.2	157.1	164.1	172.4	184.9	196.7	199.5	203.0	208.6	215.4
77.5°	110.4	114.1	116.9	121.5	128.1	138.2	144.5	148.6	149.5	151.5	158.4
80°	87.6	89.7	92.5	95.9	98.7	107.0	110.5	114.7	116.1	118.2	121.6
82.5°	64.2	66.3	67.9	70.9	75.3	78.6	82.1	86.3	86.6	88.1	88.8
85°	37.5	38.3	36.8	38.3	39.0	40.3	43.8	47.3	46.5	45.8	48.0
87.5°	16.4	16.2	15.3	16.8	15.3	15.6	15.3	15.6	16.4	17.2	18.0
90°	15.2	14.3	12.8	11.5	10.1	8.7	7.2	5.6	4.0	2.5	0.9
92.5°	15.2	14.3	13.0	11.8	10.5	9.4	9.3	10.3	11.5	12.6	13.7
95°	15.2	14.3	21.8	29.2	36.8	44.3	48.4	49.0	49.6	50.1	50.7
97.5°	38.3	43.8	58.7	73.6	88.5	103.3	110.2	109.1	108.1	107.0	105.9
100°	125.5	154.9	154.1	153.4	152.6	151.8	151.1	150.4	149.9	149.3	148.6
102.5°	192.1	197.7	197.2	196.7	196.3	195.7	195.1	194.4	193.7	192.9	192.2
105°	265.3	265.3	265.3	265.3	265.3	265.3	264.9	264.1	263.3	262.5	261.7
107.5°	335.9	335.8	335.5	335.0	334.7	334.2	334.0	334.0	334.0	334.0	334.0
110°	382.3	382.8	382.5	382.1	381.7	381.3	381.0	381.0	381.0	381.0	381.0



TEST NUMBER: P333628-940

CATALOG NUMBER: S125RDIP-S1270D1035U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	427.7	428.5	428.2	427.9	427.8	427.5	427.1	426.7	426.1	425.7	425.3
115°	496.1	496.8	496.6	496.4	496.2	496.1	495.4	494.5	493.5	492.5	491.5
117.5°	562.2	563.2	562.5	561.7	561.0	560.3	559.9	559.9	559.9	560.0	560.0
120°	604.1	604.6	604.0	603.3	602.8	602.2	602.0	602.2	602.4	602.5	602.8
122.5°	644.7	645.2	644.9	644.6	644.4	644.0	643.5	642.7	642.0	641.2	640.5
125°	704.4	705.2	705.2	705.2	705.2	705.2	704.5	703.1	701.7	700.3	698.9
127.5°	758.1	758.6	758.7	758.8	758.9	759.0	758.6	757.6	756.6	755.6	754.7
130°	793.6	794.2	794.0	793.8	793.6	793.4	792.8	791.8	790.9	789.9	788.8
132.5°	826.1	826.3	826.7	827.2	827.5	828.0	827.6	826.4	825.4	824.2	823.0
135°	874.8	875.2	875.6	876.0	876.4	876.8	876.4	875.2	874.1	872.8	871.6
137.5°	919.4	919.4	919.7	920.1	920.4	920.8	920.4	919.4	918.4	917.4	916.3
140°	946.8	946.5	946.6	946.8	947.0	947.3	947.1	946.7	946.4	945.9	945.6
142.5°	974.3	974.2	973.9	973.7	973.4	973.1	972.9	972.6	972.4	972.1	971.9
145°	1012.5	1012.4	1012.4	1012.4	1012.4	1012.4	1012.1	1011.7	1011.3	1010.9	1010.6
147.5°	1045.4	1045.1	1044.8	1044.6	1044.4	1044.1	1044.0	1044.1	1044.2	1044.3	1044.4
150°	1066.1	1065.8	1065.3	1065.0	1064.5	1064.2	1064.2	1064.5	1065.0	1065.3	1065.8
152.5°	1084.7	1084.2	1083.9	1083.4	1083.1	1082.7	1082.9	1083.8	1084.7	1085.6	1086.4
155°	1110.0	1109.4	1108.9	1108.6	1108.2	1107.8	1108.2	1109.4	1110.5	1111.8	1112.9
157.5°	1131.0	1130.4	1130.3	1130.3	1130.2	1130.2	1130.6	1131.3	1132.0	1132.7	1133.4
160°	1144.0	1143.2	1143.0	1142.8	1142.6	1142.4	1142.9	1144.1	1145.3	1146.5	1147.6
162.5°	1155.7	1154.6	1154.4	1154.2	1154.0	1153.8	1154.3	1155.5	1156.6	1157.9	1159.0
165°	1171.1	1169.9	1169.7	1169.5	1169.3	1169.1	1169.7	1170.8	1172.0	1173.1	1174.4
167.5°	1182.6	1181.2	1180.9	1180.7	1180.5	1180.4	1180.9	1182.1	1183.3	1184.5	1185.8
170°	1188.4	1186.9	1186.6	1186.4	1186.2	1186.1	1186.6	1188.0	1189.4	1190.8	1192.1
172.5°	1193.2	1191.8	1191.4	1191.1	1190.7	1190.4	1190.9	1192.3	1193.6	1195.1	1196.4
175°	1198.2	1196.6	1196.4	1196.2	1196.1	1195.9	1196.3	1197.5	1198.7	1199.9	1201.0
177.5°	1200.8	1199.6	1199.5	1199.4	1199.2	1199.0	1199.4	1200.3	1201.3	1202.3	1203.2
180°	1201.0	1201.0	1201.0	1201.0	1201.0	1201.0	1201.0	1201.0	1201.0	1201.0	1201.0



TEST NUMBER: P333628-940

CATALOG NUMBER: S125RDIP-S1270D1035U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3
2.5°	1701.6	1706.6	1713.9	1722.2	1728.8	1736.1	1740.0	1740.0	1743.3	1750.5	1760.0
5°	1706.5	1724.6	1742.0	1764.2	1781.5	1801.7	1816.9	1831.6	1844.8	1861.4	1878.8
7.5°	1705.0	1735.1	1766.4	1801.4	1840.0	1870.8	1902.4	1927.1	1951.6	1983.5	2008.7
10°	1699.5	1738.5	1780.8	1825.3	1874.0	1916.4	1954.6	1989.4	2022.8	2057.5	2088.7
12.5°	1689.5	1739.0	1790.8	1844.2	1905.7	1954.2	2003.6	2040.5	2079.5	2117.5	2156.1
15°	1674.5	1732.9	1795.5	1869.8	1944.9	1999.1	2047.7	2095.7	2131.9	2175.0	2211.8
17.5°	1643.5	1718.7	1797.4	1878.7	1950.9	2013.8	2064.8	2110.5	2148.9	2196.4	2246.4
20°	1625.1	1706.5	1788.5	1875.4	1944.2	2008.8	2058.2	2105.4	2153.4	2215.3	2276.4
22.5°	1599.6	1686.5	1773.4	1855.9	1928.6	1991.0	2042.1	2099.9	2162.8	2233.1	2307.0
25°	1559.1	1648.8	1735.0	1813.5	1884.5	1948.4	2017.9	2095.7	2172.2	2264.7	2371.0
27.5°	1507.8	1594.3	1671.2	1754.2	1824.6	1905.9	1992.7	2077.1	2187.4	2314.5	2447.3
30°	1469.5	1551.5	1624.4	1703.0	1782.9	1872.6	1969.9	2069.3	2200.7	2350.1	2507.9
32.5°	1425.0	1499.2	1571.6	1647.3	1739.5	1838.1	1941.5	2063.2	2220.2	2390.1	2553.5
35°	1347.8	1414.5	1484.7	1568.9	1666.9	1773.9	1905.9	2054.1	2243.8	2426.6	2573.3
37.5°	1266.9	1319.6	1390.1	1478.7	1585.6	1709.4	1859.2	2039.2	2234.1	2398.1	2460.5
40°	1204.6	1253.9	1328.3	1421.5	1527.1	1662.7	1830.9	2015.8	2211.8	2325.8	2320.9
42.5°	1142.9	1192.8	1264.4	1358.1	1468.2	1619.9	1793.1	1985.2	2150.6	2194.1	2103.5
45°	1048.2	1094.8	1165.0	1259.5	1377.7	1536.9	1719.0	1903.2	2008.8	1938.7	1759.3
47.5°	951.7	996.9	1062.1	1154.7	1283.7	1450.3	1622.5	1773.6	1788.5	1637.6	1422.5
50°	888.3	930.8	992.6	1091.3	1216.4	1379.1	1545.2	1664.1	1627.2	1443.1	1221.3
52.5°	826.6	867.4	925.3	1018.4	1146.4	1305.6	1454.0	1547.3	1462.0	1266.2	1066.7
55°	735.4	774.4	832.8	918.2	1034.3	1180.3	1310.3	1344.3	1219.2	1021.8	860.5
57.5°	648.8	677.3	735.0	810.7	922.6	1051.2	1144.4	1138.3	1000.2	822.4	706.8
60°	591.6	617.2	672.2	741.6	848.0	963.4	1028.8	1000.9	861.2	714.5	603.3
62.5°	538.1	562.2	608.2	672.2	763.5	863.9	911.4	873.1	741.1	612.2	523.8
65°	457.4	474.7	511.6	570.7	642.3	711.8	754.2	697.9	581.1	483.8	417.1
67.5°	381.9	396.9	429.7	472.1	521.5	569.4	586.7	533.9	443.1	377.5	330.5
70°	333.0	346.9	369.1	408.8	441.4	475.5	483.8	436.5	360.8	310.7	281.5
72.5°	286.2	299.0	318.5	346.4	369.1	388.7	392.6	348.7	290.7	256.2	233.7
75°	218.3	229.3	241.9	252.4	266.9	270.4	269.0	235.0	203.7	180.7	168.2
77.5°	160.4	165.1	172.6	176.8	177.5	177.3	170.1	148.6	132.5	123.1	117.9
80°	123.8	127.2	129.3	130.6	131.3	124.4	116.8	103.5	98.0	92.5	86.2
82.5°	89.8	92.2	94.3	94.5	90.8	85.0	77.8	71.3	67.4	64.6	62.2
85°	48.7	49.3	48.7	45.2	40.3	38.3	36.8	35.5	34.8	34.1	34.1
87.5°	17.7	16.4	13.9	14.8	15.1	14.8	15.1	14.8	14.5	14.7	14.9
90°	2.5	4.0	5.6	7.2	8.7	10.1	11.5	12.8	14.3	15.2	16.2
92.5°	12.6	11.5	10.3	9.3	9.4	10.5	11.8	13.0	14.3	15.2	16.2
95°	50.1	49.6	49.0	48.4	44.3	36.8	29.2	21.8	14.3	15.2	16.2
97.5°	107.0	108.1	109.1	110.2	103.3	88.5	73.6	58.7	43.8	38.3	32.6
100°	149.3	149.9	150.4	151.1	151.8	152.6	153.4	154.1	154.9	125.5	95.9
102.5°	192.9	193.7	194.4	195.1	195.7	196.3	196.7	197.2	197.7	192.1	186.5
105°	262.5	263.3	264.1	264.9	265.3	265.3	265.3	265.3	265.3	265.3	265.3
107.5°	334.0	334.0	334.0	334.0	334.2	334.7	335.0	335.5	335.8	335.9	335.9
110°	381.0	381.0	381.0	381.0	381.3	381.7	382.1	382.5	382.8	382.3	381.7



TEST NUMBER: P333628-940

CATALOG NUMBER: S125RDIP-S1270D1035U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	425.7	426.1	426.7	427.1	427.5	427.8	427.9	428.2	428.5	427.7	427.0
115°	492.5	493.5	494.5	495.4	496.1	496.2	496.4	496.6	496.8	496.1	495.3
117.5°	560.0	559.9	559.9	559.9	560.3	561.0	561.7	562.5	563.2	562.2	561.2
120°	602.5	602.4	602.2	602.0	602.2	602.8	603.3	604.0	604.6	604.1	603.8
122.5°	641.2	642.0	642.7	643.5	644.0	644.4	644.6	644.9	645.2	644.7	644.4
125°	700.3	701.7	703.1	704.5	705.2	705.2	705.2	705.2	705.2	704.4	703.6
127.5°	755.6	756.6	757.6	758.6	759.0	758.9	758.8	758.7	758.6	758.1	757.7
130°	789.9	790.9	791.8	792.8	793.4	793.6	793.8	794.0	794.2	793.6	793.0
132.5°	824.2	825.4	826.4	827.6	828.0	827.5	827.2	826.7	826.3	826.1	826.0
135°	872.8	874.1	875.2	876.4	876.8	876.4	876.0	875.6	875.2	874.8	874.4
137.5°	917.4	918.4	919.4	920.4	920.8	920.4	920.1	919.7	919.4	919.4	919.5
140°	945.9	946.4	946.7	947.1	947.3	947.0	946.8	946.6	946.5	946.8	947.3
142.5°	972.1	972.4	972.6	972.9	973.1	973.4	973.7	973.9	974.2	974.3	974.4
145°	1010.9	1011.3	1011.7	1012.1	1012.4	1012.4	1012.4	1012.4	1012.4	1012.5	1012.7
147.5°	1044.3	1044.2	1044.1	1044.0	1044.1	1044.4	1044.6	1044.8	1045.1	1045.4	1045.5
150°	1065.3	1065.0	1064.5	1064.2	1064.2	1064.5	1065.0	1065.3	1065.8	1066.1	1066.6
152.5°	1085.6	1084.7	1083.8	1082.9	1082.7	1083.1	1083.4	1083.9	1084.2	1084.7	1085.0
155°	1111.8	1110.5	1109.4	1108.2	1107.8	1108.2	1108.6	1108.9	1109.4	1110.0	1110.5
157.5°	1132.7	1132.0	1131.3	1130.6	1130.2	1130.2	1130.3	1130.3	1130.4	1131.0	1131.7
160°	1146.5	1145.3	1144.1	1142.9	1142.4	1142.6	1142.8	1143.0	1143.2	1144.0	1144.8
162.5°	1157.9	1156.6	1155.5	1154.3	1153.8	1154.0	1154.2	1154.4	1154.6	1155.7	1156.8
165°	1173.1	1172.0	1170.8	1169.7	1169.1	1169.3	1169.5	1169.7	1169.9	1171.1	1172.2
167.5°	1184.5	1183.3	1182.1	1180.9	1180.4	1180.5	1180.7	1180.9	1181.2	1182.6	1184.0
170°	1190.8	1189.4	1188.0	1186.6	1186.1	1186.2	1186.4	1186.6	1186.9	1188.4	1190.0
172.5°	1195.1	1193.6	1192.3	1190.9	1190.4	1190.7	1191.1	1191.4	1191.8	1193.2	1194.6
175°	1199.9	1198.7	1197.5	1196.3	1195.9	1196.1	1196.2	1196.4	1196.6	1198.2	1199.8
177.5°	1202.3	1201.3	1200.3	1199.4	1199.0	1199.2	1199.4	1199.5	1199.6	1200.8	1201.8
180°	1201.0	1201.0	1201.0	1201.0	1201.0	1201.0	1201.0	1201.0	1201.0	1201.0	1201.0



TEST NUMBER: P333628-940

CATALOG NUMBER: S125RDIP-S1270D1035U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3
2.5°	1767.2	1767.2	1776.6	1776.1	1782.3	1780.0	1781.1
5°	1899.7	1911.6	1922.0	1928.9	1939.3	1942.1	1940.7
7.5°	2037.0	2063.3	2076.1	2093.6	2096.9	2106.0	2105.1
10°	2122.2	2147.9	2167.3	2182.6	2190.2	2200.0	2200.7
12.5°	2188.9	2210.7	2227.9	2242.1	2251.4	2254.5	2256.3
15°	2241.0	2265.3	2285.5	2305.6	2317.5	2326.5	2331.4
17.5°	2293.6	2331.1	2366.7	2394.1	2410.5	2424.4	2424.2
20°	2334.1	2377.2	2421.7	2453.0	2485.0	2498.8	2501.0
22.5°	2377.5	2443.4	2500.7	2549.2	2591.2	2605.7	2611.1
25°	2467.6	2553.8	2642.0	2710.2	2758.9	2787.3	2791.5
27.5°	2576.4	2693.1	2786.0	2848.8	2889.2	2910.4	2915.0
30°	2653.2	2760.9	2844.4	2891.6	2910.4	2913.1	2902.7
32.5°	2687.7	2768.1	2801.5	2798.7	2761.9	2737.5	2728.1
35°	2645.5	2628.9	2547.5	2450.2	2375.9	2328.6	2316.0
37.5°	2407.5	2263.7	2114.1	1967.0	1888.7	1849.0	1780.6
40°	2172.9	1967.8	1812.1	1688.4	1600.1	1529.2	1512.5
42.5°	1908.2	1696.5	1540.8	1434.9	1364.3	1315.7	1294.6
45°	1533.4	1351.3	1222.7	1141.4	1087.2	1051.7	1035.7
47.5°	1226.5	1085.5	991.8	931.6	890.3	859.4	850.8
50°	1057.9	945.3	866.1	815.4	784.1	760.5	750.7
52.5°	918.9	828.0	767.1	725.2	695.6	680.9	672.9
55°	758.3	679.8	636.1	602.6	585.9	574.2	568.6
57.5°	620.2	563.5	531.5	508.4	492.9	485.4	482.7
60°	542.9	498.4	469.2	451.1	440.7	431.0	428.2
62.5°	474.5	439.4	417.0	401.1	390.7	386.5	384.8
65°	382.3	359.4	342.7	333.0	324.6	323.2	322.5
67.5°	303.9	290.4	281.7	271.5	268.6	263.7	262.8
70°	259.9	250.9	240.5	237.0	233.5	228.7	229.3
72.5°	220.5	211.4	204.4	199.7	198.5	196.4	198.2
75°	161.2	158.5	155.7	152.2	150.9	150.9	150.2
77.5°	115.1	112.7	109.7	107.6	107.2	104.2	105.4
80°	83.4	79.9	78.6	79.3	77.1	76.4	76.4
82.5°	61.7	60.5	59.1	59.2	58.8	58.1	58.7
85°	34.1	33.3	33.3	32.6	32.6	32.0	32.0
87.5°	15.7	16.4	15.5	15.1	15.2	15.9	16.5
90°	17.2	18.2	19.0	19.6	20.2	20.8	21.4
92.5°	17.2	18.2	18.8	19.1	19.4	19.7	20.0
95°	17.2	18.2	18.7	18.7	18.7	18.7	18.7
97.5°	27.1	21.5	18.7	18.7	18.7	18.7	18.7
100°	66.5	37.0	21.8	21.0	20.2	19.5	18.7
102.5°	180.9	175.3	165.9	152.4	138.9	125.5	112.0
105°	265.3	265.3	265.2	265.0	264.8	264.7	264.4
107.5°	336.0	336.0	335.7	335.1	334.6	333.9	333.3
110°	381.0	380.5	380.3	380.5	380.7	380.8	381.0



TEST NUMBER: P333628-940

CATALOG NUMBER: S125RDIP-S1270D1035U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	426.1	425.4	424.9	424.6	424.4	424.1	423.8
115°	494.5	493.7	492.7	491.5	490.3	489.1	487.9
117.5°	560.2	559.1	558.3	557.9	557.3	556.8	556.2
120°	603.3	603.0	602.3	601.3	600.3	599.3	598.3
122.5°	644.0	643.5	642.7	641.7	640.5	639.4	638.2
125°	702.8	702.0	701.3	700.7	700.1	699.5	698.9
127.5°	757.2	756.8	755.9	754.4	753.0	751.5	750.0
130°	792.4	791.8	791.0	790.1	789.1	788.1	787.0
132.5°	825.9	825.7	825.2	824.2	823.2	822.2	821.3
135°	874.1	873.6	872.8	871.6	870.5	869.2	868.1
137.5°	919.6	919.7	919.2	918.2	917.1	916.1	915.1
140°	947.6	948.0	947.6	946.5	945.2	944.1	942.9
142.5°	974.5	974.6	974.0	972.8	971.6	970.4	969.2
145°	1012.9	1013.1	1012.6	1011.5	1010.2	1009.1	1007.9
147.5°	1045.8	1046.1	1045.4	1044.0	1042.6	1041.2	1039.7
150°	1066.9	1067.3	1066.8	1065.1	1063.5	1061.9	1060.4
152.5°	1085.5	1085.8	1085.3	1083.9	1082.4	1081.0	1079.6
155°	1111.2	1111.8	1111.3	1109.6	1108.0	1106.5	1104.9
157.5°	1132.3	1132.9	1132.5	1130.9	1129.3	1127.7	1126.1
160°	1145.6	1146.4	1145.9	1144.4	1142.8	1141.2	1139.6
162.5°	1157.9	1159.0	1158.7	1157.0	1155.2	1153.5	1151.7
165°	1173.5	1174.7	1174.5	1172.9	1171.3	1169.7	1168.1
167.5°	1185.4	1186.9	1186.7	1184.9	1183.1	1181.3	1179.6
170°	1191.6	1193.2	1193.0	1191.2	1189.5	1187.8	1186.0
172.5°	1196.1	1197.5	1197.3	1195.5	1193.7	1191.9	1190.3
175°	1201.4	1202.9	1202.8	1201.0	1199.3	1197.5	1195.7
177.5°	1203.0	1204.1	1204.0	1202.7	1201.5	1200.2	1198.9
180°	1201.0	1201.0	1201.0	1201.0	1201.0	1201.0	1201.0

(END OF REPORT)