

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333631-940

Luminaire Tested: **S125RDIP-S1270D1035U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333631-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S1270D1035U940-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1035 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8039.4 lumens
Efficiency: N/A
Efficacy: 120.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 66.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333631-940

CATALOG NUMBER: S125RDIP-S1270D1035U940-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333631-940

CATALOG NUMBER: S125RDIP-S1270D1035U940-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	86	86	86	72	72	72	60	60	60	54
1	99	95	91	87	92	88	85	82	75	73	71	64	62	61	53	52	51	46
2	90	83	77	72	84	77	72	67	66	62	59	56	54	51	47	45	43	39
3	82	73	66	60	76	68	62	57	59	54	50	50	46	43	42	39	37	33
4	76	65	57	51	70	61	54	48	52	47	43	45	41	37	38	35	32	29
5	69	58	50	44	64	54	47	42	47	41	37	40	36	33	34	31	28	25
6	64	52	44	38	59	49	41	36	42	37	32	36	32	29	31	28	25	22
7	59	47	39	34	55	44	37	32	38	33	29	33	29	25	28	25	22	20
8	55	43	35	30	51	40	33	28	35	30	25	30	26	23	26	23	20	18
9	51	39	32	27	48	37	30	25	32	27	23	28	24	20	24	21	18	16
10	48	36	29	24	45	34	27	23	30	24	21	26	22	19	22	19	16	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11889	11889	11889
5°	11916	11780	11852
10°	11825	11671	11671
15°	11685	11433	11340
20°	11504	11103	10970
25°	11294	10779	10541
30°	11032	10399	10068
35°	10764	10008	9536
40°	10514	9599	9014
45°	10209	9143	8444
50°	9904	8647	7850
55°	9549	8172	7218
60°	9195	7596	6536
65°	8775	6927	5757
70°	8295	6090	4962
75°	7633	5133	4127
80°	6721	4032	3466
85°	5669	3298	3090



TEST NUMBER: P333631-940

CATALOG NUMBER: S125RDIP-S1270D1035U940-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	173.1	2.2
10°-20°	483.7	6.0
20°-30°	701.4	8.7
30°-40°	799.4	9.9
40°-50°	779.2	9.7
50°-60°	655.9	8.2
60°-70°	459.8	5.7
70°-80°	236.3	2.9
80°-90°	62.2	0.8
90°-100°	43.6	0.5
100°-110°	269.0	3.3
110°-120°	487.9	6.1
120°-130°	626.1	7.8
130°-140°	673.4	8.4
140°-150°	632.1	7.9
150°-160°	511.3	6.4
160°-170°	330.7	4.1
170°-180°	114.1	1.4
0°-30°	1358.2	16.9
0°-40°	2157.6	26.8
0°-60°	3592.8	44.7
0°-90°	4351.1	54.1
90°-120°	800.5	10.0
90°-150°	2732.2	34.0
90°-180°	3688.0	45.9
0°-180°	8039.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1841	1841	1841	1841	1841	
5°	1838	1832	1817	1830	1828	174
15°	1748	1738	1710	1708	1696	492
25°	1585	1562	1513	1495	1479	729
35°	1365	1330	1269	1230	1210	854
45°	1118	1075	1001	947	924	862
55°	848	802	726	665	641	758
65°	574	525	453	400	377	569
75°	306	263	206	176	165	324
85°	76	52	44	43	42	86
90°	1	8	14	19	21	6
95°	51	46	14	18	19	65
105°	262	265	265	265	264	277
115°	492	496	497	493	488	487
125°	699	705	705	702	699	624
135°	872	877	875	873	868	672
145°	1011	1012	1012	1013	1008	632
155°	1113	1108	1109	1112	1105	513
165°	1174	1169	1170	1175	1168	332
175°	1201	1196	1197	1203	1196	114
180°	1201	1201	1201	1201	1201	



TEST NUMBER: P333631-940

CATALOG NUMBER: S125RDIP-S1270D1035U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1840.8	1840.8	1840.8	1840.8	1840.8	1840.8	1840.8	1840.8	1840.8	1840.8	1840.8
2.5°	1844.1	1843.3	1842.5	1841.8	1841.1	1839.5	1837.0	1834.5	1832.1	1829.6	1832.1
5°	1838.0	1836.7	1835.5	1834.2	1833.0	1830.7	1827.3	1823.9	1820.5	1817.1	1820.2
7.5°	1819.9	1818.7	1817.6	1816.3	1815.2	1812.6	1808.5	1804.4	1800.4	1796.3	1798.4
10°	1803.2	1802.2	1801.3	1800.5	1799.5	1796.9	1792.5	1788.2	1783.9	1779.6	1780.5
12.5°	1784.3	1783.2	1781.9	1780.7	1779.6	1776.1	1770.3	1764.5	1758.6	1752.8	1753.5
15°	1747.6	1745.7	1743.9	1742.0	1740.2	1736.0	1729.5	1723.1	1716.5	1710.0	1709.8
17.5°	1706.1	1703.3	1700.5	1697.6	1694.8	1689.3	1681.1	1672.9	1664.8	1656.6	1655.1
20°	1673.9	1670.8	1667.7	1664.6	1661.5	1655.0	1645.2	1635.3	1625.4	1615.5	1614.0
22.5°	1638.3	1635.2	1632.1	1629.1	1625.9	1619.3	1608.8	1598.5	1588.0	1577.7	1574.7
25°	1584.9	1580.3	1575.7	1571.0	1566.4	1558.4	1546.9	1535.5	1524.0	1512.6	1508.6
27.5°	1523.8	1518.1	1512.5	1506.9	1501.3	1492.4	1480.1	1467.8	1455.6	1443.4	1437.8
30°	1479.3	1473.4	1467.5	1461.7	1455.8	1446.4	1433.3	1420.4	1407.4	1394.5	1387.3
32.5°	1435.9	1429.1	1422.2	1415.3	1408.5	1398.4	1385.2	1372.0	1358.7	1345.5	1337.7
35°	1365.3	1357.8	1350.4	1343.0	1335.6	1324.9	1311.0	1297.2	1283.3	1269.4	1260.3
37.5°	1296.0	1287.0	1278.0	1269.0	1259.9	1248.2	1233.9	1219.6	1205.2	1190.9	1180.2
40°	1247.1	1237.8	1228.5	1219.2	1210.1	1197.9	1183.1	1168.3	1153.4	1138.6	1126.9
42.5°	1196.0	1186.4	1176.9	1167.3	1157.9	1145.4	1130.2	1114.8	1099.5	1084.1	1072.9
45°	1117.8	1108.8	1099.8	1090.9	1081.9	1069.0	1052.0	1035.0	1018.0	1001.0	988.6
47.5°	1036.9	1027.4	1018.0	1008.5	999.1	985.8	968.7	951.5	934.4	917.3	904.6
50°	985.7	975.5	965.3	955.1	944.9	931.0	913.4	895.8	878.2	860.6	847.6
52.5°	930.1	919.6	909.2	898.8	888.3	874.8	858.2	841.6	824.9	808.3	794.3
55°	848.1	838.2	828.3	818.4	808.5	795.0	777.7	760.4	743.1	725.8	711.9
57.5°	765.2	754.7	744.0	733.5	722.9	709.4	692.7	675.9	659.2	642.6	629.0
60°	711.9	701.0	690.2	679.4	668.6	654.8	638.1	621.4	604.8	588.1	574.5
62.5°	655.1	644.8	634.5	624.1	613.9	600.2	583.3	566.3	549.4	532.4	519.9
65°	574.2	563.7	553.2	542.7	532.2	518.7	502.4	486.0	469.6	453.3	440.9
67.5°	493.8	483.3	472.8	462.4	451.8	438.7	423.0	407.3	391.6	375.9	364.6
70°	439.3	428.8	418.3	407.8	397.3	384.3	368.9	353.5	338.0	322.5	313.0
72.5°	385.9	375.7	365.4	355.2	344.9	332.5	318.1	303.6	289.2	274.7	265.9
75°	305.9	296.6	287.3	278.0	268.8	257.7	244.7	231.8	218.7	205.7	198.9
77.5°	226.3	218.9	211.5	204.1	196.7	187.8	177.4	167.0	156.7	146.2	141.5
80°	180.7	173.3	165.9	158.5	151.1	143.0	134.4	125.7	117.1	108.4	105.7
82.5°	136.3	129.6	122.9	116.2	109.6	103.3	97.3	91.4	85.4	79.5	78.2
85°	76.5	70.9	65.4	59.7	54.2	50.6	49.1	47.6	46.0	44.5	44.1
87.5°	25.8	24.3	22.9	21.5	20.1	19.4	19.4	19.4	19.5	19.5	19.7
90°	0.9	2.5	4.0	5.6	7.2	8.7	10.1	11.5	12.8	14.3	15.2
92.5°	13.7	12.6	11.5	10.3	9.3	9.4	10.5	11.8	13.0	14.3	15.2
95°	50.7	50.1	49.6	49.0	48.4	44.3	36.8	29.2	21.8	14.3	15.2
97.5°	105.9	107.0	108.1	109.1	110.2	103.3	88.5	73.6	58.7	43.8	38.3
100°	148.6	149.3	149.9	150.4	151.1	151.8	152.6	153.4	154.1	154.9	125.5
102.5°	192.2	192.9	193.7	194.4	195.1	195.7	196.3	196.7	197.2	197.7	192.1
105°	261.7	262.5	263.3	264.1	264.9	265.3	265.3	265.3	265.3	265.3	265.3
107.5°	334.0	334.0	334.0	334.0	334.0	334.2	334.7	335.0	335.5	335.8	335.9
110°	381.0	381.0	381.0	381.0	381.0	381.3	381.7	382.1	382.5	382.8	382.3



TEST NUMBER: P333631-940

CATALOG NUMBER: S125RDIP-S1270D1035U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	425.3	425.7	426.1	426.7	427.1	427.5	427.8	427.9	428.2	428.5	427.7
115°	491.5	492.5	493.5	494.5	495.4	496.1	496.2	496.4	496.6	496.8	496.1
117.5°	560.0	560.0	559.9	559.9	559.9	560.3	561.0	561.7	562.5	563.2	562.2
120°	602.8	602.5	602.4	602.2	602.0	602.2	602.8	603.3	604.0	604.6	604.1
122.5°	640.5	641.2	642.0	642.7	643.5	644.0	644.4	644.6	644.9	645.2	644.7
125°	698.9	700.3	701.7	703.1	704.5	705.2	705.2	705.2	705.2	705.2	704.4
127.5°	754.7	755.6	756.6	757.6	758.6	759.0	758.9	758.8	758.7	758.6	758.1
130°	788.8	789.9	790.9	791.8	792.8	793.4	793.6	793.8	794.0	794.2	793.6
132.5°	823.0	824.2	825.4	826.4	827.6	828.0	827.5	827.2	826.7	826.3	826.1
135°	871.6	872.8	874.1	875.2	876.4	876.8	876.4	876.0	875.6	875.2	874.8
137.5°	916.3	917.4	918.4	919.4	920.4	920.8	920.4	920.1	919.7	919.4	919.4
140°	945.6	945.9	946.4	946.7	947.1	947.3	947.0	946.8	946.6	946.5	946.8
142.5°	971.9	972.1	972.4	972.6	972.9	973.1	973.4	973.7	973.9	974.2	974.3
145°	1010.6	1010.9	1011.3	1011.7	1012.1	1012.4	1012.4	1012.4	1012.4	1012.4	1012.5
147.5°	1044.4	1044.3	1044.2	1044.1	1044.0	1044.1	1044.4	1044.6	1044.8	1045.1	1045.4
150°	1065.8	1065.3	1065.0	1064.5	1064.2	1064.2	1064.5	1065.0	1065.3	1065.8	1066.1
152.5°	1086.4	1085.6	1084.7	1083.8	1082.9	1082.7	1083.1	1083.4	1083.9	1084.2	1084.7
155°	1112.9	1111.8	1110.5	1109.4	1108.2	1107.8	1108.2	1108.6	1108.9	1109.4	1110.0
157.5°	1133.4	1132.7	1132.0	1131.3	1130.6	1130.2	1130.2	1130.3	1130.3	1130.4	1131.0
160°	1147.6	1146.5	1145.3	1144.1	1142.9	1142.4	1142.6	1142.8	1143.0	1143.2	1144.0
162.5°	1159.0	1157.9	1156.6	1155.5	1154.3	1153.8	1154.0	1154.2	1154.4	1154.6	1155.7
165°	1174.4	1173.1	1172.0	1170.8	1169.7	1169.1	1169.3	1169.5	1169.7	1169.9	1171.1
167.5°	1185.8	1184.5	1183.3	1182.1	1180.9	1180.4	1180.5	1180.7	1180.9	1181.2	1182.6
170°	1192.1	1190.8	1189.4	1188.0	1186.6	1186.1	1186.2	1186.4	1186.6	1186.9	1188.4
172.5°	1196.4	1195.1	1193.6	1192.3	1190.9	1190.4	1190.7	1191.1	1191.4	1191.8	1193.2
175°	1201.0	1199.9	1198.7	1197.5	1196.3	1195.9	1196.1	1196.2	1196.4	1196.6	1198.2
177.5°	1203.2	1202.3	1201.3	1200.3	1199.4	1199.0	1199.2	1199.4	1199.5	1199.6	1200.8
180°	1201.0	1201.0	1201.0	1201.0	1201.0	1201.0	1201.0	1201.0	1201.0	1201.0	1201.0



TEST NUMBER: P333631-940

CATALOG NUMBER: S125RDIP-S1270D1035U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1840.8	1840.8	1840.8	1840.8	1840.8	1840.8	1840.8	1840.8
2.5°	1834.5	1837.0	1839.5	1840.6	1840.4	1840.1	1839.9	1839.6
5°	1823.3	1826.4	1829.4	1830.7	1830.1	1829.4	1828.8	1828.2
7.5°	1800.5	1802.8	1804.9	1805.6	1804.9	1804.3	1803.6	1803.0
10°	1781.4	1782.4	1783.2	1783.2	1782.4	1781.4	1780.5	1779.6
12.5°	1754.3	1754.9	1755.6	1755.2	1753.8	1752.4	1751.0	1749.5
15°	1709.4	1709.1	1708.8	1707.3	1704.5	1701.7	1698.9	1696.1
17.5°	1653.6	1652.0	1650.5	1648.6	1646.3	1644.0	1641.7	1639.4
20°	1612.4	1610.9	1609.4	1607.1	1604.4	1601.6	1598.8	1596.1
22.5°	1571.6	1568.6	1565.6	1562.9	1560.7	1558.4	1556.0	1553.8
25°	1504.6	1500.6	1496.6	1492.8	1489.4	1486.0	1482.6	1479.3
27.5°	1432.2	1426.6	1420.9	1416.5	1413.2	1409.9	1406.6	1403.4
30°	1380.3	1373.1	1366.0	1361.1	1358.3	1355.5	1352.7	1350.0
32.5°	1329.8	1322.0	1314.1	1308.4	1304.9	1301.4	1297.9	1294.3
35°	1251.4	1242.4	1233.5	1226.8	1222.5	1218.2	1213.9	1209.5
37.5°	1169.4	1158.7	1147.9	1140.4	1136.2	1132.0	1127.8	1123.6
40°	1115.2	1103.4	1091.7	1084.0	1080.2	1076.6	1072.8	1069.2
42.5°	1061.7	1050.4	1039.2	1030.8	1025.4	1019.9	1014.5	1009.1
45°	976.2	963.9	951.5	943.1	938.4	933.8	929.2	924.5
47.5°	891.9	879.1	866.4	857.5	852.3	847.2	842.0	837.0
50°	834.6	821.6	808.7	799.9	795.2	790.6	786.0	781.3
52.5°	780.3	766.4	752.4	743.2	738.5	733.9	729.2	724.6
55°	697.9	684.0	670.1	660.7	655.8	650.8	645.9	641.0
57.5°	615.4	601.8	588.2	579.3	574.8	570.4	566.1	561.7
60°	560.9	547.3	533.7	524.6	520.0	515.3	510.7	506.0
62.5°	507.3	494.6	482.1	473.4	468.8	464.1	459.5	454.9
65°	428.6	416.2	403.8	395.3	390.7	386.0	381.4	376.7
67.5°	353.3	342.0	330.7	323.2	319.5	315.8	312.1	308.4
70°	303.4	293.8	284.3	277.6	273.8	270.2	266.4	262.8
72.5°	257.1	248.3	239.3	233.7	231.2	228.8	226.3	223.8
75°	192.2	185.4	178.6	174.1	171.9	169.8	167.6	165.4
77.5°	136.7	132.0	127.2	124.0	122.4	120.8	119.2	117.6
80°	102.9	100.1	97.3	95.6	95.0	94.3	93.8	93.2
82.5°	77.0	75.6	74.4	73.5	73.1	72.8	72.4	72.1
85°	43.9	43.6	43.2	43.0	42.6	42.4	42.0	41.7
87.5°	19.9	20.2	20.3	20.3	20.2	20.1	20.0	19.9
90°	16.2	17.2	18.2	19.0	19.6	20.2	20.8	21.4
92.5°	16.2	17.2	18.2	18.8	19.1	19.4	19.7	20.0
95°	16.2	17.2	18.2	18.7	18.7	18.7	18.7	18.7
97.5°	32.6	27.1	21.5	18.7	18.7	18.7	18.7	18.7
100°	95.9	66.5	37.0	21.8	21.0	20.2	19.5	18.7
102.5°	186.5	180.9	175.3	165.9	152.4	138.9	125.5	112.0
105°	265.3	265.3	265.3	265.2	265.0	264.8	264.7	264.4
107.5°	335.9	336.0	336.0	335.7	335.1	334.6	333.9	333.3
110°	381.7	381.0	380.5	380.3	380.5	380.7	380.8	381.0



TEST NUMBER: P333631-940

CATALOG NUMBER: S125RDIP-S1270D1035U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	427.0	426.1	425.4	424.9	424.6	424.4	424.1	423.8
115°	495.3	494.5	493.7	492.7	491.5	490.3	489.1	487.9
117.5°	561.2	560.2	559.1	558.3	557.9	557.3	556.8	556.2
120°	603.8	603.3	603.0	602.3	601.3	600.3	599.3	598.3
122.5°	644.4	644.0	643.5	642.7	641.7	640.5	639.4	638.2
125°	703.6	702.8	702.0	701.3	700.7	700.1	699.5	698.9
127.5°	757.7	757.2	756.8	755.9	754.4	753.0	751.5	750.0
130°	793.0	792.4	791.8	791.0	790.1	789.1	788.1	787.0
132.5°	826.0	825.9	825.7	825.2	824.2	823.2	822.2	821.3
135°	874.4	874.1	873.6	872.8	871.6	870.5	869.2	868.1
137.5°	919.5	919.6	919.7	919.2	918.2	917.1	916.1	915.1
140°	947.3	947.6	948.0	947.6	946.5	945.2	944.1	942.9
142.5°	974.4	974.5	974.6	974.0	972.8	971.6	970.4	969.2
145°	1012.7	1012.9	1013.1	1012.6	1011.5	1010.2	1009.1	1007.9
147.5°	1045.5	1045.8	1046.1	1045.4	1044.0	1042.6	1041.2	1039.7
150°	1066.6	1066.9	1067.3	1066.8	1065.1	1063.5	1061.9	1060.4
152.5°	1085.0	1085.5	1085.8	1085.3	1083.9	1082.4	1081.0	1079.6
155°	1110.5	1111.2	1111.8	1111.3	1109.6	1108.0	1106.5	1104.9
157.5°	1131.7	1132.3	1132.9	1132.5	1130.9	1129.3	1127.7	1126.1
160°	1144.8	1145.6	1146.4	1145.9	1144.4	1142.8	1141.2	1139.6
162.5°	1156.8	1157.9	1159.0	1158.7	1157.0	1155.2	1153.5	1151.7
165°	1172.2	1173.5	1174.7	1174.5	1172.9	1171.3	1169.7	1168.1
167.5°	1184.0	1185.4	1186.9	1186.7	1184.9	1183.1	1181.3	1179.6
170°	1190.0	1191.6	1193.2	1193.0	1191.2	1189.5	1187.8	1186.0
172.5°	1194.6	1196.1	1197.5	1197.3	1195.5	1193.7	1191.9	1190.3
175°	1199.8	1201.4	1202.9	1202.8	1201.0	1199.3	1197.5	1195.7
177.5°	1201.8	1203.0	1204.1	1204.0	1202.7	1201.5	1200.2	1198.9
180°	1201.0	1201.0	1201.0	1201.0	1201.0	1201.0	1201.0	1201.0

(END OF REPORT)