

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331348-930

Luminaire Tested: **SA2XXDIP-C675D725U930-4F0-1E-UDD-A**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331348-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXDIP-C675D725U930-4F0-1E-UDD-A  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 725 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4753.2 lumens  
Efficiency: N/A  
Efficacy: 103.6 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 45.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331348-930  
CATALOG NUMBER: SA2XXDIP-C675D725U930-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P331348-930

CATALOG NUMBER: SA2XXDIP-C675D725U930-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	84	84	84	69	69	69	56	56	56	50
1	98	94	90	87	91	87	84	81	74	72	70	62	60	59	51	50	49	43
2	90	83	77	72	83	77	72	67	65	62	58	55	52	50	45	43	42	37
3	82	73	66	61	76	68	62	57	58	53	50	49	46	43	40	38	36	32
4	76	65	57	52	70	61	54	49	52	47	43	44	40	37	36	34	31	28
5	70	58	50	45	64	54	47	42	47	41	37	40	36	32	33	30	28	25
6	64	52	45	39	59	49	42	37	42	37	33	36	32	29	30	27	25	22
7	60	48	40	34	55	44	37	33	38	33	29	33	29	26	28	25	22	20
8	55	43	36	31	51	41	34	29	35	30	26	30	26	23	26	22	20	18
9	52	40	32	27	48	37	31	26	32	27	23	28	24	21	24	20	18	16
10	48	36	29	25	45	34	28	23	30	25	21	26	22	19	22	19	17	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	17486	17486	17486	17486
5°	19603	17598	15595	17598
10°	22463	17454	13496	17454
15°	24849	17135	11925	17135
20°	24471	16790	10869	16790
25°	22066	16335	10203	16335
30°	18233	15605	9715	15605
35°	13291	14840	9368	14840
40°	10614	13940	9177	13940
45°	9275	12896	8914	12896
50°	8719	11886	8741	11886
55°	8037	10860	8504	10860
60°	7363	9771	8147	9771
65°	6709	8795	7790	8795
70°	6090	7841	7270	7841
75°	5402	6775	6438	6775
80°	4649	5607	5188	5607
85°	4168	4168	3075	4168



TEST NUMBER: P331348-930

CATALOG NUMBER: SA2XXDIP-C675D725U930-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	103.1	2.2
10°-20°	299.8	6.3
20°-30°	435.1	9.2
30°-40°	459.2	9.7
40°-50°	406.6	8.6
50°-60°	324.5	6.8
60°-70°	220.5	4.6
70°-80°	113.1	2.4
80°-90°	29.2	0.6
90°-100°	26.9	0.6
100°-110°	98.6	2.1
110°-120°	263.5	5.5
120°-130°	435.0	9.2
130°-140°	462.7	9.7
140°-150°	430.0	9.0
150°-160°	345.7	7.3
160°-170°	222.8	4.7
170°-180°	76.7	1.6
0°-30°	838.1	17.6
0°-40°	1297.3	27.3
0°-60°	2028.3	42.7
0°-90°	2391.2	50.3
90°-120°	389.0	8.2
90°-150°	1716.8	36.1
90°-180°	2362.0	49.7
0°-180°	4753.2	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1083	1083	1083	1083	1083	
5°	1210	1086	962	1086	1210	121
15°	1487	1025	713	1025	1487	410
25°	1239	917	573	917	1239	560
35°	674	753	475	753	674	439
45°	406	565	390	565	406	319
55°	286	386	302	386	286	256
65°	176	230	204	230	176	175
75°	87	109	103	109	87	93
85°	22	22	17	22	22	25
90°	16	1	16	1	16	8
95°	25	38	25	38	25	23
105°	44	177	44	177	44	46
115°	48	335	48	335	48	120
125°	499	474	499	474	499	431
135°	606	587	606	587	606	467
145°	691	681	691	681	691	432
155°	750	749	750	749	750	346
165°	788	790	788	790	788	222
175°	803	808	803	808	803	76
180°	806	806	806	806	806	



TEST NUMBER: P331348-930

CATALOG NUMBER: SA2XXDIP-C675D725U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0
2.5°	1132.9	1133.2	1133.9	1128.5	1127.9	1127.9	1123.2	1119.2	1114.6	1108.2	1108.9
5°	1209.5	1214.1	1215.7	1210.7	1203.2	1202.4	1195.3	1183.7	1172.8	1164.1	1157.9
7.5°	1300.9	1302.7	1298.6	1292.0	1286.5	1276.5	1263.3	1250.4	1232.3	1215.8	1203.5
10°	1370.1	1372.6	1365.5	1356.0	1348.1	1336.4	1317.3	1297.7	1274.0	1251.1	1232.7
12.5°	1422.7	1428.9	1419.8	1418.5	1405.0	1389.0	1366.2	1356.3	1322.9	1291.0	1271.4
15°	1486.6	1486.2	1487.1	1479.2	1469.2	1466.6	1442.5	1416.3	1369.3	1350.5	1318.1
17.5°	1468.2	1474.5	1477.4	1477.3	1477.1	1475.5	1467.8	1451.2	1427.7	1397.3	1359.8
20°	1424.2	1432.6	1433.8	1443.4	1448.8	1455.9	1458.7	1454.2	1439.7	1414.2	1381.8
22.5°	1356.3	1358.6	1362.5	1377.4	1389.2	1406.9	1416.2	1431.6	1426.0	1413.6	1386.4
25°	1238.6	1234.4	1249.0	1256.5	1283.5	1311.8	1332.3	1354.7	1374.7	1386.7	1378.8
27.5°	1097.2	1091.0	1112.8	1132.7	1154.7	1185.4	1217.2	1254.7	1285.9	1324.9	1338.3
30°	978.0	981.8	1002.7	1023.9	1057.1	1100.4	1136.2	1177.5	1222.0	1265.7	1296.0
32.5°	849.5	864.0	877.1	909.6	938.9	987.2	1039.7	1091.2	1146.7	1196.4	1243.4
35°	674.3	690.9	709.2	733.0	774.1	822.0	873.2	942.6	1018.5	1086.3	1142.1
37.5°	567.5	564.8	575.4	592.5	625.9	664.5	723.4	792.1	881.3	961.0	1039.7
40°	503.6	501.9	509.4	525.2	550.7	578.9	630.6	690.9	773.7	871.1	964.7
42.5°	459.7	460.6	464.8	476.0	493.3	516.7	555.3	606.7	682.5	774.2	874.8
45°	406.2	409.1	413.7	419.1	429.1	448.3	469.9	506.5	566.5	643.0	742.1
47.5°	367.8	367.9	372.5	377.2	383.2	394.0	411.6	434.6	476.9	539.2	624.4
50°	347.1	344.2	347.6	351.2	357.5	365.0	376.7	398.3	426.6	477.0	548.1
52.5°	321.8	321.9	324.9	326.3	331.9	339.3	350.0	365.0	390.6	430.0	488.5
55°	285.5	287.6	289.3	291.7	296.8	302.1	310.5	320.5	340.5	370.0	413.3
57.5°	251.4	252.0	253.7	258.4	261.6	266.6	274.5	283.6	296.6	318.5	351.0
60°	228.0	228.0	231.4	233.5	237.7	242.6	248.9	257.6	269.3	287.1	313.4
62.5°	206.8	206.4	207.7	211.2	214.3	219.0	225.3	232.7	243.6	259.5	281.1
65°	175.6	174.8	177.3	178.1	181.5	186.1	191.0	198.9	207.7	219.3	238.5
67.5°	145.7	146.7	148.0	149.6	151.4	156.2	159.6	165.2	172.5	182.2	195.2
70°	129.0	129.0	129.0	130.3	132.7	135.3	138.6	143.2	150.3	158.6	170.2
72.5°	110.4	111.7	113.0	112.3	115.4	116.9	120.9	123.5	130.3	135.6	145.9
75°	86.6	86.6	86.6	88.6	89.9	91.2	93.7	96.1	99.5	106.2	111.5
77.5°	64.6	64.4	64.8	65.3	66.7	68.2	68.9	71.2	74.3	77.3	81.9
80°	50.0	50.8	51.2	52.0	52.0	52.8	53.2	56.2	58.3	60.3	63.3
82.5°	38.6	38.8	38.9	39.1	39.4	39.9	40.9	41.9	42.6	44.4	46.6
85°	22.5	22.1	22.1	22.9	22.5	22.5	23.3	24.1	24.1	24.5	25.8
87.5°	11.8	11.7	12.1	11.7	11.6	11.8	11.7	11.3	11.4	11.7	11.8
90°	15.7	15.5	15.2	15.0	14.7	14.3	13.6	13.0	12.3	11.7	10.6
92.5°	15.7	15.6	15.4	15.2	15.2	14.8	14.5	14.2	13.9	13.5	13.0
95°	25.1	25.2	25.4	25.4	25.6	25.4	24.7	24.1	23.4	22.7	21.9
97.5°	33.5	33.3	33.2	33.0	32.9	32.5	32.0	31.5	31.0	30.4	28.4
100°	39.1	38.8	38.6	38.3	38.1	37.4	36.4	35.3	34.2	33.3	31.1
102.5°	41.9	41.5	41.2	40.8	40.4	39.5	38.2	36.9	35.5	34.2	52.6
105°	44.4	43.8	43.3	42.8	42.2	41.3	39.9	38.4	37.0	35.5	70.9
107.5°	45.6	45.1	44.6	44.0	43.5	44.0	45.4	46.9	48.3	49.8	92.2
110°	46.1	45.6	45.0	44.5	44.0	50.2	63.2	76.1	89.1	102.1	139.5



TEST NUMBER: P331348-930  
 CATALOG NUMBER: SA2XXDIP-C675D725U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	46.6	46.1	45.7	45.3	44.8	68.3	115.6	162.9	210.2	257.4	266.7
115°	47.9	57.2	66.4	75.8	85.1	119.8	179.9	239.9	299.9	359.9	356.6
117.5°	195.3	225.9	256.6	287.2	317.9	340.5	355.0	369.6	384.1	398.6	396.3
120°	355.8	373.2	390.8	408.2	425.7	433.7	432.2	430.6	429.0	427.5	425.2
122.5°	443.9	447.4	450.7	454.1	457.5	458.8	457.8	456.9	455.9	455.0	452.5
125°	498.6	498.2	497.9	497.5	497.1	496.4	495.5	494.6	493.7	492.8	490.3
127.5°	533.2	533.1	533.0	533.0	532.9	532.1	530.8	529.5	528.2	526.8	525.1
130°	554.6	554.7	554.9	555.1	555.1	554.5	553.1	551.6	550.2	548.8	547.4
132.5°	575.6	575.8	575.9	576.0	576.2	575.6	574.4	573.2	571.9	570.7	569.3
135°	605.9	606.2	606.5	606.7	607.0	606.5	605.2	603.9	602.6	601.3	600.1
137.5°	633.6	634.1	634.5	635.0	635.4	635.0	633.7	632.4	631.1	629.9	628.5
140°	650.9	651.5	652.2	652.8	653.5	653.2	652.0	650.9	649.7	648.6	647.1
142.5°	667.6	668.3	669.0	669.6	670.3	670.0	669.0	667.9	666.8	665.8	664.1
145°	691.1	691.8	692.4	693.1	693.7	693.6	692.7	691.8	690.9	689.9	687.7
147.5°	711.8	712.3	712.8	713.4	714.0	713.9	713.2	712.5	711.8	711.2	709.0
150°	724.3	725.0	725.6	726.3	726.9	726.8	726.1	725.3	724.6	723.7	721.7
152.5°	735.1	736.0	736.8	737.7	738.5	738.6	737.8	736.9	736.2	735.4	733.4
155°	750.0	751.1	752.1	753.1	754.2	754.3	753.5	752.8	752.0	751.1	749.6
157.5°	763.7	764.7	765.6	766.7	767.7	767.8	766.9	766.0	765.2	764.3	763.1
160°	771.6	772.5	773.4	774.3	775.2	775.3	774.5	773.7	773.0	772.2	771.4
162.5°	778.1	779.3	780.3	781.5	782.6	782.7	781.8	780.9	780.1	779.2	778.5
165°	787.9	788.8	789.7	790.7	791.6	791.6	790.7	789.7	788.8	787.9	787.5
167.5°	794.1	795.2	796.5	797.6	798.7	798.9	798.0	797.1	796.1	795.2	794.9
170°	797.9	799.0	800.1	801.4	802.5	802.7	801.7	800.8	799.9	799.0	798.7
172.5°	800.6	801.8	803.0	804.1	805.3	805.4	804.5	803.6	802.7	801.8	801.5
175°	803.1	804.4	805.7	807.0	808.3	808.5	807.6	806.7	805.8	804.9	804.5
177.5°	804.6	805.5	806.5	807.4	808.4	808.5	807.7	807.0	806.2	805.5	805.4
180°	806.0	806.0	806.0	806.0	806.0	806.0	806.0	806.0	806.0	806.0	806.0



TEST NUMBER: P331348-930  
 CATALOG NUMBER: SA2XXDIP-C675D725U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0
2.5°	1111.3	1108.6	1106.9	1100.9	1095.6	1090.3	1088.6	1089.2	1082.0	1075.0	1072.0
5°	1154.5	1146.2	1138.3	1127.1	1113.8	1099.2	1091.7	1085.8	1071.3	1055.5	1046.4
7.5°	1193.4	1181.5	1166.2	1145.0	1125.7	1102.8	1088.2	1075.3	1053.9	1031.7	1018.0
10°	1217.0	1200.7	1181.1	1155.4	1131.6	1103.8	1084.2	1064.6	1039.7	1013.0	996.4
12.5°	1237.3	1215.4	1196.1	1163.0	1135.0	1100.1	1076.8	1049.3	1023.0	991.4	975.1
15°	1285.6	1245.3	1208.6	1171.2	1136.6	1087.9	1062.2	1025.1	990.5	951.5	932.7
17.5°	1323.0	1277.7	1219.9	1172.3	1132.0	1078.2	1040.2	995.9	955.0	910.3	884.8
20°	1344.3	1292.2	1230.3	1173.7	1125.4	1063.8	1022.6	977.2	929.4	879.0	851.5
22.5°	1357.0	1302.3	1241.0	1168.7	1112.1	1052.1	1000.3	950.6	902.0	847.7	818.9
25°	1361.0	1311.0	1246.1	1164.5	1095.4	1027.6	965.2	916.9	858.2	807.4	765.4
27.5°	1341.2	1305.4	1242.9	1156.7	1076.2	996.9	927.3	872.6	810.7	755.5	713.3
30°	1316.9	1296.0	1235.3	1148.7	1060.9	975.6	898.9	837.0	775.3	719.6	676.3
32.5°	1279.2	1274.7	1221.3	1137.3	1044.6	948.6	869.4	806.7	738.4	683.6	642.4
35°	1205.3	1225.3	1191.6	1112.1	1013.8	910.2	824.5	752.9	682.2	629.7	591.0
37.5°	1106.3	1155.8	1147.0	1075.1	972.4	868.5	773.8	699.0	631.5	578.6	540.6
40°	1038.0	1101.2	1110.4	1046.8	943.1	836.2	735.8	661.4	595.6	547.3	509.0
42.5°	964.7	1038.7	1063.8	1012.8	911.1	802.2	701.9	624.7	559.6	512.7	478.7
45°	842.0	939.8	985.1	956.0	857.8	746.2	643.0	564.8	505.6	461.5	435.4
47.5°	727.2	834.1	895.0	884.8	798.4	687.9	586.0	510.9	453.3	418.1	394.6
50°	646.0	755.8	829.5	832.8	755.8	646.4	544.0	473.2	420.4	387.5	368.4
52.5°	575.4	680.2	760.6	778.2	708.2	603.1	506.4	435.9	389.4	359.1	342.0
55°	483.2	571.9	660.9	693.4	637.2	537.3	447.8	385.8	342.1	321.3	306.3
57.5°	401.7	475.6	557.9	593.8	559.1	473.6	389.7	335.9	300.4	282.2	270.7
60°	358.7	417.0	490.2	533.1	503.2	427.1	353.8	302.6	273.5	257.2	246.4
62.5°	318.8	370.4	432.4	471.6	455.3	383.4	317.8	272.6	247.4	232.2	224.5
65°	263.0	303.9	351.7	387.9	377.1	322.5	268.9	230.2	210.2	198.1	191.8
67.5°	216.6	246.1	279.2	311.0	302.2	263.6	220.5	190.4	175.5	165.1	161.3
70°	187.3	209.8	239.3	264.7	257.6	226.0	191.8	166.1	153.2	144.4	140.6
72.5°	159.3	177.8	200.3	221.1	216.3	190.0	161.6	142.1	132.2	124.1	121.0
75°	120.3	134.4	148.1	161.9	160.6	140.2	123.6	108.6	100.7	94.5	93.2
77.5°	88.8	96.7	106.1	114.2	111.9	100.3	87.2	78.7	72.8	68.6	68.0
80°	67.8	72.4	79.1	84.9	82.0	77.0	66.6	60.3	56.2	52.0	50.4
82.5°	49.2	53.8	57.8	60.9	58.7	54.1	47.6	43.4	40.8	38.1	37.3
85°	25.8	28.3	30.0	30.8	30.0	27.1	24.1	22.5	20.4	19.2	18.8
87.5°	11.9	11.7	11.5	11.9	10.6	10.4	8.7	7.4	7.4	7.3	6.9
90°	9.6	8.6	7.5	6.3	4.9	3.4	2.0	0.6	2.0	3.4	4.9
92.5°	12.5	12.0	11.5	11.3	11.4	11.5	11.7	11.7	11.7	11.5	11.4
95°	21.0	20.1	19.1	20.8	25.1	29.4	33.7	37.9	33.7	29.4	25.1
97.5°	26.3	24.1	22.0	27.0	39.1	51.1	63.2	75.3	63.2	51.1	39.1
100°	28.9	26.7	24.5	32.2	50.0	67.8	85.4	103.2	85.4	67.8	50.0
102.5°	71.0	89.4	107.9	119.0	122.8	126.5	130.3	134.0	130.3	126.5	122.8
105°	106.3	141.7	177.1	192.8	189.0	185.1	181.2	177.3	181.2	185.1	189.0
107.5°	134.7	177.1	219.6	239.2	236.0	232.9	229.8	226.7	229.8	232.9	236.0
110°	177.0	214.4	251.8	269.2	266.5	263.8	261.1	258.4	261.1	263.8	266.5





TEST NUMBER: P331348-930

CATALOG NUMBER: SA2XXDIP-C675D725U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	275.9	285.2	294.4	297.8	295.5	293.0	290.7	288.2	290.7	293.0	295.5
115°	353.4	350.1	346.9	344.1	341.9	339.7	337.5	335.3	337.5	339.7	341.9
117.5°	394.1	391.9	389.6	387.3	384.8	382.4	379.9	377.5	379.9	382.4	384.8
120°	422.8	420.5	418.2	416.0	414.1	412.1	410.2	408.2	410.2	412.1	414.1
122.5°	450.0	447.4	444.8	442.5	440.5	438.5	436.4	434.4	436.4	438.5	440.5
125°	487.9	485.4	483.0	480.9	479.2	477.5	475.8	474.2	475.8	477.5	479.2
127.5°	523.2	521.4	519.5	517.6	515.8	514.0	512.1	510.2	512.1	514.0	515.8
130°	545.9	544.5	543.1	541.4	539.2	537.2	535.2	533.0	535.2	537.2	539.2
132.5°	567.9	566.5	565.0	563.5	561.7	559.9	558.2	556.4	558.2	559.9	561.7
135°	598.9	597.8	596.6	595.0	593.0	590.8	588.8	586.7	588.8	590.8	593.0
137.5°	627.2	625.9	624.6	623.2	621.7	620.3	618.8	617.4	618.8	620.3	621.7
140°	645.7	644.2	642.9	641.6	640.6	639.5	638.5	637.5	638.5	639.5	640.6
142.5°	662.5	660.9	659.3	657.9	657.0	656.2	655.2	654.3	655.2	656.2	657.0
145°	685.5	683.3	681.1	680.1	680.2	680.4	680.4	680.6	680.4	680.4	680.2
147.5°	706.8	704.7	702.5	701.6	702.1	702.6	703.1	703.6	703.1	702.6	702.1
150°	719.6	717.5	715.5	714.9	715.8	716.7	717.6	718.5	717.6	716.7	715.8
152.5°	731.5	729.5	727.6	727.1	728.1	729.1	730.1	731.1	730.1	729.1	728.1
155°	748.0	746.5	744.9	744.8	745.9	747.1	748.3	749.4	748.3	747.1	745.9
157.5°	762.1	761.0	759.9	759.9	760.8	761.8	762.8	763.8	762.8	761.8	760.8
160°	770.6	769.8	769.1	769.1	769.8	770.6	771.4	772.2	771.4	770.6	769.8
162.5°	777.8	777.1	776.5	776.5	777.3	778.1	778.9	779.7	778.9	778.1	777.3
165°	787.2	786.8	786.4	786.5	787.3	788.1	788.9	789.7	788.9	788.1	787.3
167.5°	794.5	794.2	793.8	794.0	794.8	795.6	796.4	797.1	796.4	795.6	794.8
170°	798.5	798.3	797.9	798.3	799.0	799.8	800.5	801.4	800.5	799.8	799.0
172.5°	801.3	801.0	800.8	801.0	801.8	802.6	803.3	804.1	803.3	802.6	801.8
175°	804.3	804.0	803.8	804.1	805.0	805.9	806.8	807.7	806.8	805.9	805.0
177.5°	805.4	805.2	805.1	805.4	806.2	806.9	807.6	808.4	807.6	806.9	806.2
180°	806.0	806.0	806.0	806.0	806.0	806.0	806.0	806.0	806.0	806.0	806.0



TEST NUMBER: P331348-930

CATALOG NUMBER: SA2XXDIP-C675D725U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0
2.5°	1068.6	1066.7	1059.6	1056.0	1049.9	1044.3	1040.6	1042.4	1043.7	1043.0	1042.0
5°	1038.0	1030.0	1018.0	1007.6	1000.1	986.3	980.6	977.6	975.2	972.2	969.3
7.5°	1001.5	989.0	971.8	956.9	942.9	925.9	916.2	910.3	904.3	897.7	891.9
10°	975.6	958.1	939.8	918.9	902.3	886.9	873.2	864.1	855.7	847.8	842.0
12.5°	948.3	928.1	905.5	877.0	858.7	836.7	834.5	818.4	805.4	800.5	793.7
15°	904.8	876.5	847.8	814.1	799.5	779.5	767.0	754.6	743.3	735.4	733.4
17.5°	855.4	818.8	790.3	766.1	742.2	721.7	710.2	700.2	691.0	680.4	679.0
20°	817.8	786.2	755.0	733.8	709.2	688.4	674.3	664.2	656.3	650.1	644.7
22.5°	782.2	747.5	719.0	695.8	671.6	654.8	643.6	634.0	627.4	620.4	615.4
25°	725.0	698.0	666.8	640.5	620.5	609.8	600.5	592.2	588.1	583.5	577.7
27.5°	675.0	644.9	615.7	595.4	577.9	568.3	561.7	556.1	552.2	549.5	546.3
30°	639.7	609.3	586.4	566.5	551.9	542.3	538.2	534.8	530.3	528.6	526.9
32.5°	605.8	578.4	558.8	541.4	527.6	521.3	517.5	514.5	510.9	509.2	505.9
35°	557.7	534.8	515.7	506.1	494.9	489.4	486.6	482.3	479.1	477.4	477.0
37.5°	512.5	492.6	480.0	467.7	463.0	459.7	455.7	452.8	451.8	451.6	451.2
40°	483.2	467.0	455.8	445.7	443.7	438.6	435.4	432.8	432.8	433.3	432.8
42.5°	456.6	442.0	432.1	423.5	421.0	418.0	414.7	414.5	415.2	416.6	415.2
45°	416.2	405.8	398.7	394.5	390.0	387.0	386.6	387.9	388.3	388.7	390.0
47.5°	379.0	372.2	365.7	361.2	359.1	358.7	358.2	360.4	362.3	363.1	365.0
50°	357.1	349.2	343.8	340.9	339.2	338.3	339.2	341.7	343.3	345.4	346.7
52.5°	332.5	326.9	323.1	320.9	320.2	320.7	320.9	323.8	326.4	327.1	327.8
55°	298.4	294.2	293.4	289.7	291.3	290.9	293.0	294.6	297.2	299.6	300.1
57.5°	264.5	261.1	258.9	259.2	259.7	261.5	263.3	266.2	268.9	271.5	271.7
60°	241.8	240.1	238.9	238.9	239.7	242.2	244.3	247.2	248.9	250.5	251.8
62.5°	221.2	219.5	218.3	218.9	221.1	222.6	225.0	226.6	228.2	229.9	230.5
65°	188.5	187.7	189.0	189.8	190.2	192.2	195.2	196.4	198.1	198.9	201.9
67.5°	158.5	158.7	158.5	159.6	162.1	162.6	165.3	168.2	168.5	170.2	172.0
70°	138.2	139.0	139.8	140.6	142.8	143.6	145.7	146.9	148.5	149.9	151.1
72.5°	119.5	119.7	120.5	120.3	122.1	123.9	125.7	126.9	128.6	130.2	131.4
75°	92.0	92.0	92.8	93.2	95.3	97.4	96.9	97.8	99.5	101.1	102.0
77.5°	67.2	66.3	67.2	67.6	68.2	70.0	70.4	71.5	73.4	72.8	73.8
80°	51.2	50.0	51.2	51.6	51.6	53.7	53.7	54.5	55.8	54.5	55.8
82.5°	36.5	36.0	36.9	36.9	37.6	37.7	38.4	38.6	39.8	39.2	39.8
85°	18.3	17.9	18.3	17.9	18.3	18.8	18.8	18.3	18.3	19.2	17.9
87.5°	6.9	6.8	6.7	6.9	6.8	6.7	6.4	6.6	6.7	6.2	6.3
90°	6.3	7.5	8.6	9.6	10.6	11.7	12.3	13.0	13.6	14.3	14.7
92.5°	11.3	11.5	12.0	12.5	13.0	13.5	13.9	14.2	14.5	14.8	15.2
95°	20.8	19.1	20.1	21.0	21.9	22.7	23.4	24.1	24.7	25.4	25.6
97.5°	27.0	22.0	24.1	26.3	28.4	30.4	31.0	31.5	32.0	32.5	32.9
100°	32.2	24.5	26.7	28.9	31.1	33.3	34.2	35.3	36.4	37.4	38.1
102.5°	119.0	107.9	89.4	71.0	52.6	34.2	35.5	36.9	38.2	39.5	40.4
105°	192.8	177.1	141.7	106.3	70.9	35.5	37.0	38.4	39.9	41.3	42.2
107.5°	239.2	219.6	177.1	134.7	92.2	49.8	48.3	46.9	45.4	44.0	43.5
110°	269.2	251.8	214.4	177.0	139.5	102.1	89.1	76.1	63.2	50.2	44.0



TEST NUMBER: P331348-930

CATALOG NUMBER: SA2XXDIP-C675D725U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	297.8	294.4	285.2	275.9	266.7	257.4	210.2	162.9	115.6	68.3	44.8
115°	344.1	346.9	350.1	353.4	356.6	359.9	299.9	239.9	179.9	119.8	85.1
117.5°	387.3	389.6	391.9	394.1	396.3	398.6	384.1	369.6	355.0	340.5	317.9
120°	416.0	418.2	420.5	422.8	425.2	427.5	429.0	430.6	432.2	433.7	425.7
122.5°	442.5	444.8	447.4	450.0	452.5	455.0	455.9	456.9	457.8	458.8	457.5
125°	480.9	483.0	485.4	487.9	490.3	492.8	493.7	494.6	495.5	496.4	497.1
127.5°	517.6	519.5	521.4	523.2	525.1	526.8	528.2	529.5	530.8	532.1	532.9
130°	541.4	543.1	544.5	545.9	547.4	548.8	550.2	551.6	553.1	554.5	555.1
132.5°	563.5	565.0	566.5	567.9	569.3	570.7	571.9	573.2	574.4	575.6	576.2
135°	595.0	596.6	597.8	598.9	600.1	601.3	602.6	603.9	605.2	606.5	607.0
137.5°	623.2	624.6	625.9	627.2	628.5	629.9	631.1	632.4	633.7	635.0	635.4
140°	641.6	642.9	644.2	645.7	647.1	648.6	649.7	650.9	652.0	653.2	653.5
142.5°	657.9	659.3	660.9	662.5	664.1	665.8	666.8	667.9	669.0	670.0	670.3
145°	680.1	681.1	683.3	685.5	687.7	689.9	690.9	691.8	692.7	693.6	693.7
147.5°	701.6	702.5	704.7	706.8	709.0	711.2	711.8	712.5	713.2	713.9	714.0
150°	714.9	715.5	717.5	719.6	721.7	723.7	724.6	725.3	726.1	726.8	726.9
152.5°	727.1	727.6	729.5	731.5	733.4	735.4	736.2	736.9	737.8	738.6	738.5
155°	744.8	744.9	746.5	748.0	749.6	751.1	752.0	752.8	753.5	754.3	754.2
157.5°	759.9	759.9	761.0	762.1	763.1	764.3	765.2	766.0	766.9	767.8	767.7
160°	769.1	769.1	769.8	770.6	771.4	772.2	773.0	773.7	774.5	775.3	775.2
162.5°	776.5	776.5	777.1	777.8	778.5	779.2	780.1	780.9	781.8	782.7	782.6
165°	786.5	786.4	786.8	787.2	787.5	787.9	788.8	789.7	790.7	791.6	791.6
167.5°	794.0	793.8	794.2	794.5	794.9	795.2	796.1	797.1	798.0	798.9	798.7
170°	798.3	797.9	798.3	798.5	798.7	799.0	799.9	800.8	801.7	802.7	802.5
172.5°	801.0	800.8	801.0	801.3	801.5	801.8	802.7	803.6	804.5	805.4	805.3
175°	804.1	803.8	804.0	804.3	804.5	804.9	805.8	806.7	807.6	808.5	808.3
177.5°	805.4	805.1	805.2	805.4	805.4	805.5	806.2	807.0	807.7	808.5	808.4
180°	806.0	806.0	806.0	806.0	806.0	806.0	806.0	806.0	806.0	806.0	806.0



TEST NUMBER: P331348-930

CATALOG NUMBER: SA2XXDIP-C675D725U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0
2.5°	1038.7	1038.0	1038.0	1035.0	1038.0	1038.0	1038.7	1042.0	1043.0	1043.7	1042.4
5°	963.5	962.2	960.2	962.2	960.2	962.2	963.5	969.3	972.2	975.2	977.6
7.5°	889.2	884.2	883.5	878.5	883.5	884.2	889.2	891.9	897.7	904.3	910.3
10°	834.9	831.5	831.1	823.2	831.1	831.5	834.9	842.0	847.8	855.7	864.1
12.5°	793.6	785.6	787.2	782.6	787.2	785.6	793.6	793.7	800.5	805.4	818.4
15°	722.1	722.1	720.4	713.4	720.4	722.1	722.1	733.4	735.4	743.3	754.6
17.5°	670.7	669.9	665.9	667.9	665.9	669.9	670.7	679.0	680.4	691.0	700.2
20°	640.1	637.6	632.6	632.6	632.6	637.6	640.1	644.7	650.1	656.3	664.2
22.5°	611.1	611.0	605.7	607.3	605.7	611.0	611.1	615.4	620.4	627.4	634.0
25°	577.2	574.0	571.4	572.7	571.4	574.0	577.2	577.7	583.5	588.1	592.2
27.5°	545.1	543.3	543.2	539.7	543.2	543.3	545.1	546.3	549.5	552.2	556.1
30°	526.5	522.4	523.2	521.1	523.2	522.4	526.5	526.9	528.6	530.3	534.8
32.5°	505.2	503.7	502.9	501.1	502.9	503.7	505.2	505.9	509.2	510.9	514.5
35°	476.1	476.5	474.5	475.3	474.5	476.5	476.1	477.0	477.4	479.1	482.3
37.5°	450.8	452.1	451.1	451.3	451.1	452.1	450.8	451.2	451.6	451.8	452.8
40°	434.1	434.1	434.1	435.4	434.1	434.1	434.1	432.8	433.3	432.8	432.8
42.5°	418.1	417.4	416.8	416.7	416.8	417.4	418.1	415.2	416.6	415.2	414.5
45°	390.8	392.1	392.5	390.4	392.5	392.1	390.8	390.0	388.7	388.3	387.9
47.5°	366.1	366.2	366.1	367.9	366.1	366.2	366.1	365.0	363.1	362.3	360.4
50°	348.8	348.0	348.8	348.0	348.8	348.0	348.8	346.7	345.4	343.3	341.7
52.5°	330.4	330.6	330.1	330.0	330.1	330.6	330.4	327.8	327.1	326.4	323.8
55°	301.7	302.6	302.1	302.1	302.1	302.6	301.7	300.1	299.6	297.2	294.6
57.5°	272.1	272.8	273.4	271.5	273.4	272.8	272.1	271.7	271.5	268.9	266.2
60°	251.4	253.5	253.1	252.3	253.1	253.5	251.4	251.8	250.5	248.9	247.2
62.5°	232.4	233.2	233.1	232.9	233.1	233.2	232.4	230.5	229.9	228.2	226.6
65°	203.1	203.9	202.7	203.9	202.7	203.9	203.1	201.9	198.9	198.1	196.4
67.5°	171.5	171.8	172.8	173.3	172.8	171.8	171.5	172.0	170.2	168.5	168.2
70°	151.9	151.5	152.7	154.0	152.7	151.5	151.9	151.1	149.9	148.5	146.9
72.5°	131.3	132.2	131.8	132.6	131.8	132.2	131.3	131.4	130.2	128.6	126.9
75°	101.1	102.4	102.0	103.2	102.0	102.4	101.1	102.0	101.1	99.5	97.8
77.5°	73.1	73.2	73.1	73.8	73.1	73.2	73.1	73.8	72.8	73.4	71.5
80°	55.8	55.0	54.1	55.8	54.1	55.0	55.8	55.8	54.5	55.8	54.5
82.5°	38.8	39.3	38.5	38.5	38.5	39.3	38.8	39.8	39.2	39.8	38.6
85°	17.9	17.4	16.6	16.6	16.6	17.4	17.9	17.9	19.2	18.3	18.3
87.5°	6.4	6.0	6.1	5.8	6.1	6.0	6.4	6.3	6.2	6.7	6.6
90°	15.0	15.2	15.5	15.7	15.5	15.2	15.0	14.7	14.3	13.6	13.0
92.5°	15.2	15.4	15.6	15.7	15.6	15.4	15.2	15.2	14.8	14.5	14.2
95°	25.4	25.4	25.2	25.1	25.2	25.4	25.4	25.6	25.4	24.7	24.1
97.5°	33.0	33.2	33.3	33.5	33.3	33.2	33.0	32.9	32.5	32.0	31.5
100°	38.3	38.6	38.8	39.1	38.8	38.6	38.3	38.1	37.4	36.4	35.3
102.5°	40.8	41.2	41.5	41.9	41.5	41.2	40.8	40.4	39.5	38.2	36.9
105°	42.8	43.3	43.8	44.4	43.8	43.3	42.8	42.2	41.3	39.9	38.4
107.5°	44.0	44.6	45.1	45.6	45.1	44.6	44.0	43.5	44.0	45.4	46.9
110°	44.5	45.0	45.6	46.1	45.6	45.0	44.5	44.0	50.2	63.2	76.1



TEST NUMBER: P331348-930  
 CATALOG NUMBER: SA2XXDIP-C675D725U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	45.3	45.7	46.1	46.6	46.1	45.7	45.3	44.8	68.3	115.6	162.9
115°	75.8	66.4	57.2	47.9	57.2	66.4	75.8	85.1	119.8	179.9	239.9
117.5°	287.2	256.6	225.9	195.3	225.9	256.6	287.2	317.9	340.5	355.0	369.6
120°	408.2	390.8	373.2	355.8	373.2	390.8	408.2	425.7	433.7	432.2	430.6
122.5°	454.1	450.7	447.4	443.9	447.4	450.7	454.1	457.5	458.8	457.8	456.9
125°	497.5	497.9	498.2	498.6	498.2	497.9	497.5	497.1	496.4	495.5	494.6
127.5°	533.0	533.0	533.1	533.2	533.1	533.0	533.0	532.9	532.1	530.8	529.5
130°	555.1	554.9	554.7	554.6	554.7	554.9	555.1	555.1	554.5	553.1	551.6
132.5°	576.0	575.9	575.8	575.6	575.8	575.9	576.0	576.2	575.6	574.4	573.2
135°	606.7	606.5	606.2	605.9	606.2	606.5	606.7	607.0	606.5	605.2	603.9
137.5°	635.0	634.5	634.1	633.6	634.1	634.5	635.0	635.4	635.0	633.7	632.4
140°	652.8	652.2	651.5	650.9	651.5	652.2	652.8	653.5	653.2	652.0	650.9
142.5°	669.6	669.0	668.3	667.6	668.3	669.0	669.6	670.3	670.0	669.0	667.9
145°	693.1	692.4	691.8	691.1	691.8	692.4	693.1	693.7	693.6	692.7	691.8
147.5°	713.4	712.8	712.3	711.8	712.3	712.8	713.4	714.0	713.9	713.2	712.5
150°	726.3	725.6	725.0	724.3	725.0	725.6	726.3	726.9	726.8	726.1	725.3
152.5°	737.7	736.8	736.0	735.1	736.0	736.8	737.7	738.5	738.6	737.8	736.9
155°	753.1	752.1	751.1	750.0	751.1	752.1	753.1	754.2	754.3	753.5	752.8
157.5°	766.7	765.6	764.7	763.7	764.7	765.6	766.7	767.7	767.8	766.9	766.0
160°	774.3	773.4	772.5	771.6	772.5	773.4	774.3	775.2	775.3	774.5	773.7
162.5°	781.5	780.3	779.3	778.1	779.3	780.3	781.5	782.6	782.7	781.8	780.9
165°	790.7	789.7	788.8	787.9	788.8	789.7	790.7	791.6	791.6	790.7	789.7
167.5°	797.6	796.5	795.2	794.1	795.2	796.5	797.6	798.7	798.9	798.0	797.1
170°	801.4	800.1	799.0	797.9	799.0	800.1	801.4	802.5	802.7	801.7	800.8
172.5°	804.1	803.0	801.8	800.6	801.8	803.0	804.1	805.3	805.4	804.5	803.6
175°	807.0	805.7	804.4	803.1	804.4	805.7	807.0	808.3	808.5	807.6	806.7
177.5°	807.4	806.5	805.5	804.6	805.5	806.5	807.4	808.4	808.5	807.7	807.0
180°	806.0	806.0	806.0	806.0	806.0	806.0	806.0	806.0	806.0	806.0	806.0



TEST NUMBER: P331348-930

CATALOG NUMBER: SA2XXDIP-C675D725U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0
2.5°	1040.6	1044.3	1049.9	1056.0	1059.6	1066.7	1068.6	1072.0	1075.0	1082.0	1089.2
5°	980.6	986.3	1000.1	1007.6	1018.0	1030.0	1038.0	1046.4	1055.5	1071.3	1085.8
7.5°	916.2	925.9	942.9	956.9	971.8	989.0	1001.5	1018.0	1031.7	1053.9	1075.3
10°	873.2	886.9	902.3	918.9	939.8	958.1	975.6	996.4	1013.0	1039.7	1064.6
12.5°	834.5	836.7	858.7	877.0	905.5	928.1	948.3	975.1	991.4	1023.0	1049.3
15°	767.0	779.5	799.5	814.1	847.8	876.5	904.8	932.7	951.5	990.5	1025.1
17.5°	710.2	721.7	742.2	766.1	790.3	818.8	855.4	884.8	910.3	955.0	995.9
20°	674.3	688.4	709.2	733.8	755.0	786.2	817.8	851.5	879.0	929.4	977.2
22.5°	643.6	654.8	671.6	695.8	719.0	747.5	782.2	818.9	847.7	902.0	950.6
25°	600.5	609.8	620.5	640.5	666.8	698.0	725.0	765.4	807.4	858.2	916.9
27.5°	561.7	568.3	577.9	595.4	615.7	644.9	675.0	713.3	755.5	810.7	872.6
30°	538.2	542.3	551.9	566.5	586.4	609.3	639.7	676.3	719.6	775.3	837.0
32.5°	517.5	521.3	527.6	541.4	558.8	578.4	605.8	642.4	683.6	738.4	806.7
35°	486.6	489.4	494.9	506.1	515.7	534.8	557.7	591.0	629.7	682.2	752.9
37.5°	455.7	459.7	463.0	467.7	480.0	492.6	512.5	540.6	578.6	631.5	699.0
40°	435.4	438.6	443.7	445.7	455.8	467.0	483.2	509.0	547.3	595.6	661.4
42.5°	414.7	418.0	421.0	423.5	432.1	442.0	456.6	478.7	512.7	559.6	624.7
45°	386.6	387.0	390.0	394.5	398.7	405.8	416.2	435.4	461.5	505.6	564.8
47.5°	358.2	358.7	359.1	361.2	365.7	372.2	379.0	394.6	418.1	453.3	510.9
50°	339.2	338.3	339.2	340.9	343.8	349.2	357.1	368.4	387.5	420.4	473.2
52.5°	320.9	320.7	320.2	320.9	323.1	326.9	332.5	342.0	359.1	389.4	435.9
55°	293.0	290.9	291.3	289.7	293.4	294.2	298.4	306.3	321.3	342.1	385.8
57.5°	263.3	261.5	259.7	259.2	258.9	261.1	264.5	270.7	282.2	300.4	335.9
60°	244.3	242.2	239.7	238.9	238.9	240.1	241.8	246.4	257.2	273.5	302.6
62.5°	225.0	222.6	221.1	218.9	218.3	219.5	221.2	224.5	232.2	247.4	272.6
65°	195.2	192.2	190.2	189.8	189.0	187.7	188.5	191.8	198.1	210.2	230.2
67.5°	165.3	162.6	162.1	159.6	158.5	158.7	158.5	161.3	165.1	175.5	190.4
70°	145.7	143.6	142.8	140.6	139.8	139.0	138.2	140.6	144.4	153.2	166.1
72.5°	125.7	123.9	122.1	120.3	120.5	119.7	119.5	121.0	124.1	132.2	142.1
75°	96.9	97.4	95.3	93.2	92.8	92.0	92.0	93.2	94.5	100.7	108.6
77.5°	70.4	70.0	68.2	67.6	67.2	66.3	67.2	68.0	68.6	72.8	78.7
80°	53.7	53.7	51.6	51.6	51.2	50.0	51.2	50.4	52.0	56.2	60.3
82.5°	38.4	37.7	37.6	36.9	36.9	36.0	36.5	37.3	38.1	40.8	43.4
85°	18.8	18.8	18.3	17.9	18.3	17.9	18.3	18.8	19.2	20.4	22.5
87.5°	6.4	6.7	6.8	6.9	6.7	6.8	6.9	6.9	7.3	7.4	7.4
90°	12.3	11.7	10.6	9.6	8.6	7.5	6.3	4.9	3.4	2.0	0.6
92.5°	13.9	13.5	13.0	12.5	12.0	11.5	11.3	11.4	11.5	11.7	11.7
95°	23.4	22.7	21.9	21.0	20.1	19.1	20.8	25.1	29.4	33.7	37.9
97.5°	31.0	30.4	28.4	26.3	24.1	22.0	27.0	39.1	51.1	63.2	75.3
100°	34.2	33.3	31.1	28.9	26.7	24.5	32.2	50.0	67.8	85.4	103.2
102.5°	35.5	34.2	52.6	71.0	89.4	107.9	119.0	122.8	126.5	130.3	134.0
105°	37.0	35.5	70.9	106.3	141.7	177.1	192.8	189.0	185.1	181.2	177.3
107.5°	48.3	49.8	92.2	134.7	177.1	219.6	239.2	236.0	232.9	229.8	226.7
110°	89.1	102.1	139.5	177.0	214.4	251.8	269.2	266.5	263.8	261.1	258.4



TEST NUMBER: P331348-930

CATALOG NUMBER: SA2XXDIP-C675D725U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	210.2	257.4	266.7	275.9	285.2	294.4	297.8	295.5	293.0	290.7	288.2
115°	299.9	359.9	356.6	353.4	350.1	346.9	344.1	341.9	339.7	337.5	335.3
117.5°	384.1	398.6	396.3	394.1	391.9	389.6	387.3	384.8	382.4	379.9	377.5
120°	429.0	427.5	425.2	422.8	420.5	418.2	416.0	414.1	412.1	410.2	408.2
122.5°	455.9	455.0	452.5	450.0	447.4	444.8	442.5	440.5	438.5	436.4	434.4
125°	493.7	492.8	490.3	487.9	485.4	483.0	480.9	479.2	477.5	475.8	474.2
127.5°	528.2	526.8	525.1	523.2	521.4	519.5	517.6	515.8	514.0	512.1	510.2
130°	550.2	548.8	547.4	545.9	544.5	543.1	541.4	539.2	537.2	535.2	533.0
132.5°	571.9	570.7	569.3	567.9	566.5	565.0	563.5	561.7	559.9	558.2	556.4
135°	602.6	601.3	600.1	598.9	597.8	596.6	595.0	593.0	590.8	588.8	586.7
137.5°	631.1	629.9	628.5	627.2	625.9	624.6	623.2	621.7	620.3	618.8	617.4
140°	649.7	648.6	647.1	645.7	644.2	642.9	641.6	640.6	639.5	638.5	637.5
142.5°	666.8	665.8	664.1	662.5	660.9	659.3	657.9	657.0	656.2	655.2	654.3
145°	690.9	689.9	687.7	685.5	683.3	681.1	680.1	680.2	680.4	680.4	680.6
147.5°	711.8	711.2	709.0	706.8	704.7	702.5	701.6	702.1	702.6	703.1	703.6
150°	724.6	723.7	721.7	719.6	717.5	715.5	714.9	715.8	716.7	717.6	718.5
152.5°	736.2	735.4	733.4	731.5	729.5	727.6	727.1	728.1	729.1	730.1	731.1
155°	752.0	751.1	749.6	748.0	746.5	744.9	744.8	745.9	747.1	748.3	749.4
157.5°	765.2	764.3	763.1	762.1	761.0	759.9	759.9	760.8	761.8	762.8	763.8
160°	773.0	772.2	771.4	770.6	769.8	769.1	769.1	769.8	770.6	771.4	772.2
162.5°	780.1	779.2	778.5	777.8	777.1	776.5	776.5	777.3	778.1	778.9	779.7
165°	788.8	787.9	787.5	787.2	786.8	786.4	786.5	787.3	788.1	788.9	789.7
167.5°	796.1	795.2	794.9	794.5	794.2	793.8	794.0	794.8	795.6	796.4	797.1
170°	799.9	799.0	798.7	798.5	798.3	797.9	798.3	799.0	799.8	800.5	801.4
172.5°	802.7	801.8	801.5	801.3	801.0	800.8	801.0	801.8	802.6	803.3	804.1
175°	805.8	804.9	804.5	804.3	804.0	803.8	804.1	805.0	805.9	806.8	807.7
177.5°	806.2	805.5	805.4	805.4	805.2	805.1	805.4	806.2	806.9	807.6	808.4
180°	806.0	806.0	806.0	806.0	806.0	806.0	806.0	806.0	806.0	806.0	806.0



TEST NUMBER: P331348-930

CATALOG NUMBER: SA2XXDIP-C675D725U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0
2.5°	1088.6	1090.3	1095.6	1100.9	1106.9	1108.6	1111.3	1108.9	1108.2	1114.6	1119.2
5°	1091.7	1099.2	1113.8	1127.1	1138.3	1146.2	1154.5	1157.9	1164.1	1172.8	1183.7
7.5°	1088.2	1102.8	1125.7	1145.0	1166.2	1181.5	1193.4	1203.5	1215.8	1232.3	1250.4
10°	1084.2	1103.8	1131.6	1155.4	1181.1	1200.7	1217.0	1232.7	1251.1	1274.0	1297.7
12.5°	1076.8	1100.1	1135.0	1163.0	1196.1	1215.4	1237.3	1271.4	1291.0	1322.9	1356.3
15°	1062.2	1087.9	1136.6	1171.2	1208.6	1245.3	1285.6	1318.1	1350.5	1369.3	1416.3
17.5°	1040.2	1078.2	1132.0	1172.3	1219.9	1277.7	1323.0	1359.8	1397.3	1427.7	1451.2
20°	1022.6	1063.8	1125.4	1173.7	1230.3	1292.2	1344.3	1381.8	1414.2	1439.7	1454.2
22.5°	1000.3	1052.1	1112.1	1168.7	1241.0	1302.3	1357.0	1386.4	1413.6	1426.0	1431.6
25°	965.2	1027.6	1095.4	1164.5	1246.1	1311.0	1361.0	1378.8	1386.7	1374.7	1354.7
27.5°	927.3	996.9	1076.2	1156.7	1242.9	1305.4	1341.2	1338.3	1324.9	1285.9	1254.7
30°	898.9	975.6	1060.9	1148.7	1235.3	1296.0	1316.9	1296.0	1265.7	1222.0	1177.5
32.5°	869.4	948.6	1044.6	1137.3	1221.3	1274.7	1279.2	1243.4	1196.4	1146.7	1091.2
35°	824.5	910.2	1013.8	1112.1	1191.6	1225.3	1205.3	1142.1	1086.3	1018.5	942.6
37.5°	773.8	868.5	972.4	1075.1	1147.0	1155.8	1106.3	1039.7	961.0	881.3	792.1
40°	735.8	836.2	943.1	1046.8	1110.4	1101.2	1038.0	964.7	871.1	773.7	690.9
42.5°	701.9	802.2	911.1	1012.8	1063.8	1038.7	964.7	874.8	774.2	682.5	606.7
45°	643.0	746.2	857.8	956.0	985.1	939.8	842.0	742.1	643.0	566.5	506.5
47.5°	586.0	687.9	798.4	884.8	895.0	834.1	727.2	624.4	539.2	476.9	434.6
50°	544.0	646.4	755.8	832.8	829.5	755.8	646.0	548.1	477.0	426.6	398.3
52.5°	506.4	603.1	708.2	778.2	760.6	680.2	575.4	488.5	430.0	390.6	365.0
55°	447.8	537.3	637.2	693.4	660.9	571.9	483.2	413.3	370.0	340.5	320.5
57.5°	389.7	473.6	559.1	593.8	557.9	475.6	401.7	351.0	318.5	296.6	283.6
60°	353.8	427.1	503.2	533.1	490.2	417.0	358.7	313.4	287.1	269.3	257.6
62.5°	317.8	383.4	455.3	471.6	432.4	370.4	318.8	281.1	259.5	243.6	232.7
65°	268.9	322.5	377.1	387.9	351.7	303.9	263.0	238.5	219.3	207.7	198.9
67.5°	220.5	263.6	302.2	311.0	279.2	246.1	216.6	195.2	182.2	172.5	165.2
70°	191.8	226.0	257.6	264.7	239.3	209.8	187.3	170.2	158.6	150.3	143.2
72.5°	161.6	190.0	216.3	221.1	200.3	177.8	159.3	145.9	135.6	130.3	123.5
75°	123.6	140.2	160.6	161.9	148.1	134.4	120.3	111.5	106.2	99.5	96.1
77.5°	87.2	100.3	111.9	114.2	106.1	96.7	88.8	81.9	77.3	74.3	71.2
80°	66.6	77.0	82.0	84.9	79.1	72.4	67.8	63.3	60.3	58.3	56.2
82.5°	47.6	54.1	58.7	60.9	57.8	53.8	49.2	46.6	44.4	42.6	41.9
85°	24.1	27.1	30.0	30.8	30.0	28.3	25.8	25.8	24.5	24.1	24.1
87.5°	8.7	10.4	10.6	11.9	11.5	11.7	11.9	11.8	11.7	11.4	11.3
90°	2.0	3.4	4.9	6.3	7.5	8.6	9.6	10.6	11.7	12.3	13.0
92.5°	11.7	11.5	11.4	11.3	11.5	12.0	12.5	13.0	13.5	13.9	14.2
95°	33.7	29.4	25.1	20.8	19.1	20.1	21.0	21.9	22.7	23.4	24.1
97.5°	63.2	51.1	39.1	27.0	22.0	24.1	26.3	28.4	30.4	31.0	31.5
100°	85.4	67.8	50.0	32.2	24.5	26.7	28.9	31.1	33.3	34.2	35.3
102.5°	130.3	126.5	122.8	119.0	107.9	89.4	71.0	52.6	34.2	35.5	36.9
105°	181.2	185.1	189.0	192.8	177.1	141.7	106.3	70.9	35.5	37.0	38.4
107.5°	229.8	232.9	236.0	239.2	219.6	177.1	134.7	92.2	49.8	48.3	46.9
110°	261.1	263.8	266.5	269.2	251.8	214.4	177.0	139.5	102.1	89.1	76.1





TEST NUMBER: P331348-930

CATALOG NUMBER: SA2XXDIP-C675D725U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	290.7	293.0	295.5	297.8	294.4	285.2	275.9	266.7	257.4	210.2	162.9
115°	337.5	339.7	341.9	344.1	346.9	350.1	353.4	356.6	359.9	299.9	239.9
117.5°	379.9	382.4	384.8	387.3	389.6	391.9	394.1	396.3	398.6	384.1	369.6
120°	410.2	412.1	414.1	416.0	418.2	420.5	422.8	425.2	427.5	429.0	430.6
122.5°	436.4	438.5	440.5	442.5	444.8	447.4	450.0	452.5	455.0	455.9	456.9
125°	475.8	477.5	479.2	480.9	483.0	485.4	487.9	490.3	492.8	493.7	494.6
127.5°	512.1	514.0	515.8	517.6	519.5	521.4	523.2	525.1	526.8	528.2	529.5
130°	535.2	537.2	539.2	541.4	543.1	544.5	545.9	547.4	548.8	550.2	551.6
132.5°	558.2	559.9	561.7	563.5	565.0	566.5	567.9	569.3	570.7	571.9	573.2
135°	588.8	590.8	593.0	595.0	596.6	597.8	598.9	600.1	601.3	602.6	603.9
137.5°	618.8	620.3	621.7	623.2	624.6	625.9	627.2	628.5	629.9	631.1	632.4
140°	638.5	639.5	640.6	641.6	642.9	644.2	645.7	647.1	648.6	649.7	650.9
142.5°	655.2	656.2	657.0	657.9	659.3	660.9	662.5	664.1	665.8	666.8	667.9
145°	680.4	680.4	680.2	680.1	681.1	683.3	685.5	687.7	689.9	690.9	691.8
147.5°	703.1	702.6	702.1	701.6	702.5	704.7	706.8	709.0	711.2	711.8	712.5
150°	717.6	716.7	715.8	714.9	715.5	717.5	719.6	721.7	723.7	724.6	725.3
152.5°	730.1	729.1	728.1	727.1	727.6	729.5	731.5	733.4	735.4	736.2	736.9
155°	748.3	747.1	745.9	744.8	744.9	746.5	748.0	749.6	751.1	752.0	752.8
157.5°	762.8	761.8	760.8	759.9	759.9	761.0	762.1	763.1	764.3	765.2	766.0
160°	771.4	770.6	769.8	769.1	769.1	769.8	770.6	771.4	772.2	773.0	773.7
162.5°	778.9	778.1	777.3	776.5	776.5	777.1	777.8	778.5	779.2	780.1	780.9
165°	788.9	788.1	787.3	786.5	786.4	786.8	787.2	787.5	787.9	788.8	789.7
167.5°	796.4	795.6	794.8	794.0	793.8	794.2	794.5	794.9	795.2	796.1	797.1
170°	800.5	799.8	799.0	798.3	797.9	798.3	798.5	798.7	799.0	799.9	800.8
172.5°	803.3	802.6	801.8	801.0	800.8	801.0	801.3	801.5	801.8	802.7	803.6
175°	806.8	805.9	805.0	804.1	803.8	804.0	804.3	804.5	804.9	805.8	806.7
177.5°	807.6	806.9	806.2	805.4	805.1	805.2	805.4	805.4	805.5	806.2	807.0
180°	806.0	806.0	806.0	806.0	806.0	806.0	806.0	806.0	806.0	806.0	806.0



TEST NUMBER: P331348-930

CATALOG NUMBER: SA2XXDIP-C675D725U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0
2.5°	1123.2	1127.9	1127.9	1128.5	1133.9	1133.2	1132.9
5°	1195.3	1202.4	1203.2	1210.7	1215.7	1214.1	1209.5
7.5°	1263.3	1276.5	1286.5	1292.0	1298.6	1302.7	1300.9
10°	1317.3	1336.4	1348.1	1356.0	1365.5	1372.6	1370.1
12.5°	1366.2	1389.0	1405.0	1418.5	1419.8	1428.9	1422.7
15°	1442.5	1466.6	1469.2	1479.2	1487.1	1486.2	1486.6
17.5°	1467.8	1475.5	1477.1	1477.3	1477.4	1474.5	1468.2
20°	1458.7	1455.9	1448.8	1443.4	1433.8	1432.6	1424.2
22.5°	1416.2	1406.9	1389.2	1377.4	1362.5	1358.6	1356.3
25°	1332.3	1311.8	1283.5	1256.5	1249.0	1234.4	1238.6
27.5°	1217.2	1185.4	1154.7	1132.7	1112.8	1091.0	1097.2
30°	1136.2	1100.4	1057.1	1023.9	1002.7	981.8	978.0
32.5°	1039.7	987.2	938.9	909.6	877.1	864.0	849.5
35°	873.2	822.0	774.1	733.0	709.2	690.9	674.3
37.5°	723.4	664.5	625.9	592.5	575.4	564.8	567.5
40°	630.6	578.9	550.7	525.2	509.4	501.9	503.6
42.5°	555.3	516.7	493.3	476.0	464.8	460.6	459.7
45°	469.9	448.3	429.1	419.1	413.7	409.1	406.2
47.5°	411.6	394.0	383.2	377.2	372.5	367.9	367.8
50°	376.7	365.0	357.5	351.2	347.6	344.2	347.1
52.5°	350.0	339.3	331.9	326.3	324.9	321.9	321.8
55°	310.5	302.1	296.8	291.7	289.3	287.6	285.5
57.5°	274.5	266.6	261.6	258.4	253.7	252.0	251.4
60°	248.9	242.6	237.7	233.5	231.4	228.0	228.0
62.5°	225.3	219.0	214.3	211.2	207.7	206.4	206.8
65°	191.0	186.1	181.5	178.1	177.3	174.8	175.6
67.5°	159.6	156.2	151.4	149.6	148.0	146.7	145.7
70°	138.6	135.3	132.7	130.3	129.0	129.0	129.0
72.5°	120.9	116.9	115.4	112.3	113.0	111.7	110.4
75°	93.7	91.2	89.9	88.6	86.6	86.6	86.6
77.5°	68.9	68.2	66.7	65.3	64.8	64.4	64.6
80°	53.2	52.8	52.0	52.0	51.2	50.8	50.0
82.5°	40.9	39.9	39.4	39.1	38.9	38.8	38.6
85°	23.3	22.5	22.5	22.9	22.1	22.1	22.5
87.5°	11.7	11.8	11.6	11.7	12.1	11.7	11.8
90°	13.6	14.3	14.7	15.0	15.2	15.5	15.7
92.5°	14.5	14.8	15.2	15.2	15.4	15.6	15.7
95°	24.7	25.4	25.6	25.4	25.4	25.2	25.1
97.5°	32.0	32.5	32.9	33.0	33.2	33.3	33.5
100°	36.4	37.4	38.1	38.3	38.6	38.8	39.1
102.5°	38.2	39.5	40.4	40.8	41.2	41.5	41.9
105°	39.9	41.3	42.2	42.8	43.3	43.8	44.4
107.5°	45.4	44.0	43.5	44.0	44.6	45.1	45.6
110°	63.2	50.2	44.0	44.5	45.0	45.6	46.1



TEST NUMBER: P331348-930  
 CATALOG NUMBER: SA2XXDIP-C675D725U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	115.6	68.3	44.8	45.3	45.7	46.1	46.6
115°	179.9	119.8	85.1	75.8	66.4	57.2	47.9
117.5°	355.0	340.5	317.9	287.2	256.6	225.9	195.3
120°	432.2	433.7	425.7	408.2	390.8	373.2	355.8
122.5°	457.8	458.8	457.5	454.1	450.7	447.4	443.9
125°	495.5	496.4	497.1	497.5	497.9	498.2	498.6
127.5°	530.8	532.1	532.9	533.0	533.0	533.1	533.2
130°	553.1	554.5	555.1	555.1	554.9	554.7	554.6
132.5°	574.4	575.6	576.2	576.0	575.9	575.8	575.6
135°	605.2	606.5	607.0	606.7	606.5	606.2	605.9
137.5°	633.7	635.0	635.4	635.0	634.5	634.1	633.6
140°	652.0	653.2	653.5	652.8	652.2	651.5	650.9
142.5°	669.0	670.0	670.3	669.6	669.0	668.3	667.6
145°	692.7	693.6	693.7	693.1	692.4	691.8	691.1
147.5°	713.2	713.9	714.0	713.4	712.8	712.3	711.8
150°	726.1	726.8	726.9	726.3	725.6	725.0	724.3
152.5°	737.8	738.6	738.5	737.7	736.8	736.0	735.1
155°	753.5	754.3	754.2	753.1	752.1	751.1	750.0
157.5°	766.9	767.8	767.7	766.7	765.6	764.7	763.7
160°	774.5	775.3	775.2	774.3	773.4	772.5	771.6
162.5°	781.8	782.7	782.6	781.5	780.3	779.3	778.1
165°	790.7	791.6	791.6	790.7	789.7	788.8	787.9
167.5°	798.0	798.9	798.7	797.6	796.5	795.2	794.1
170°	801.7	802.7	802.5	801.4	800.1	799.0	797.9
172.5°	804.5	805.4	805.3	804.1	803.0	801.8	800.6
175°	807.6	808.5	808.3	807.0	805.7	804.4	803.1
177.5°	807.7	808.5	808.4	807.4	806.5	805.5	804.6
180°	806.0	806.0	806.0	806.0	806.0	806.0	806.0

(END OF REPORT)