

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331414-930

Luminaire Tested: **SA2XXDIP-C865D1080U930-4F0-1E-UDD-D**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331414-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C865D1080U930-4F0-1E-UDD-D
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, DROP SATIN WHITE DIFFUSER
UPLIGHT 1080 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6361.0 lumens
Efficiency: N/A
Efficacy: 97.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.32 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.08')
CIE Type: Semi-Indirect


Input Watts (W): 65.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331414-930

CATALOG NUMBER: SA2XXDIP-C865D1080U930-4F0-1E-UDD-D

Luminous Intensity Polar Plot





TEST NUMBER: P331414-930

CATALOG NUMBER: SA2XXDIP-C865D1080U930-4F0-1E-UDD-D

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47	40
1	94	90	85	81	85	81	78	74	66	64	61	52	50	49	39	38	37	31
2	85	77	71	65	77	70	65	60	57	53	50	45	42	40	34	32	30	25
3	78	68	60	54	70	62	55	50	50	45	41	40	36	33	30	27	25	21
4	71	60	51	45	64	54	47	42	44	39	35	35	31	28	26	24	21	17
5	65	53	45	38	58	48	41	35	39	34	30	31	27	24	24	21	18	15
6	59	47	39	33	54	43	36	31	35	30	26	28	24	21	21	18	16	13
7	55	42	34	29	50	39	32	27	32	26	22	25	21	18	19	16	14	11
8	51	38	31	25	46	35	28	23	29	24	20	23	19	16	18	15	13	10
9	47	35	27	22	43	32	25	21	26	21	18	21	17	14	16	13	11	9
10	44	32	25	20	40	29	23	18	24	19	16	20	16	13	15	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12053	12053	12053
5°	12111	11602	11558
10°	12036	11258	11133
15°	11869	10896	10685
20°	11659	10507	10254
25°	11452	10132	9863
30°	11160	9747	9469
35°	10866	9375	9193
40°	10556	9059	8916
45°	10260	8774	8678
50°	9944	8519	8446
55°	9611	8242	8208
60°	9207	7957	7957
65°	8784	7620	7658
70°	8310	7260	7336
75°	7704	6907	7041
80°	6744	6545	6739
85°	5835	6234	6508



TEST NUMBER: P331414-930

CATALOG NUMBER: SA2XXDIP-C865D1080U930-4F0-1E-UDD-D

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	70.7	1.1
10°-20°	202.8	3.2
20°-30°	307.4	4.8
30°-40°	374.4	5.9
40°-50°	402.8	6.3
50°-60°	391.1	6.1
60°-70°	341.5	5.4
70°-80°	262.9	4.1
80°-90°	179.4	2.8
90°-100°	161.5	2.5
100°-110°	235.3	3.7
110°-120°	450.3	7.1
120°-130°	679.2	10.7
130°-140°	701.3	11.0
140°-150°	641.4	10.1
150°-160°	513.8	8.1
160°-170°	331.1	5.2
170°-180°	114.0	1.8
0°-30°	580.9	9.1
0°-40°	955.3	15.0
0°-60°	1749.2	27.5
0°-90°	2533.0	39.8
90°-120°	847.1	13.3
90°-150°	2869.1	45.1
90°-180°	3828.0	60.2
0°-180°	6361.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	746	746	746	746	746	
5°	749	745	739	745	744	71
15°	714	716	716	725	725	201
25°	649	657	666	679	683	298
35°	559	578	598	621	630	349
45°	459	488	526	558	570	354
55°	352	392	447	484	500	314
65°	240	294	357	400	415	239
75°	133	194	263	308	324	141
85°	39	106	175	219	236	42
90°	12	84	160	206	222	10
95°	65	90	158	202	216	76
105°	269	313	146	192	209	288
115°	503	532	600	249	180	494
125°	707	720	769	803	817	630
135°	873	887	906	936	944	674
145°	1012	1011	1025	1037	1039	633
155°	1114	1107	1116	1121	1115	513
165°	1174	1169	1171	1176	1171	331
175°	1200	1195	1196	1201	1193	114
180°	1198	1198	1198	1198	1198	



TEST NUMBER: P331414-930

CATALOG NUMBER: SA2XXDIP-C865D1080U930-4F0-1E-UDD-D

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	746.5	746.5	746.5	746.5	746.5	746.5	746.5	746.5	746.5	746.5	746.5
2.5°	750.8	750.2	749.7	749.1	748.5	747.5	746.2	744.9	743.5	742.2	743.1
5°	748.6	748.0	747.2	746.5	745.8	744.7	743.2	741.8	740.4	738.9	740.4
7.5°	741.9	741.4	740.9	740.5	740.0	739.2	738.1	737.0	735.9	734.8	736.5
10°	736.8	736.3	735.8	735.3	734.8	734.3	733.5	732.8	732.1	731.3	733.3
12.5°	728.1	728.2	728.3	728.4	728.5	728.2	727.7	727.2	726.7	726.1	728.1
15°	714.0	714.5	715.0	715.5	715.9	716.2	716.2	716.2	716.2	716.2	718.4
17.5°	695.9	696.8	697.9	698.9	699.9	700.7	701.6	702.3	703.1	703.8	706.1
20°	683.7	684.9	686.2	687.4	688.5	689.7	690.6	691.5	692.5	693.5	696.1
22.5°	670.7	672.1	673.5	674.9	676.3	677.7	679.1	680.4	681.8	683.1	685.7
25°	649.1	650.8	652.5	654.2	655.8	657.8	659.9	662.1	664.2	666.4	669.3
27.5°	623.1	625.9	628.6	631.4	634.1	636.7	639.3	641.9	644.4	646.9	650.6
30°	605.8	608.9	612.1	615.2	618.3	621.5	624.6	627.7	630.9	634.0	637.8
32.5°	586.8	590.3	593.8	597.4	600.9	604.5	608.1	611.9	615.6	619.2	623.7
35°	559.3	563.4	567.5	571.6	575.7	580.0	584.6	589.1	593.7	598.3	603.6
37.5°	529.5	534.2	538.9	543.6	548.3	553.6	559.5	565.5	571.4	577.3	583.2
40°	509.6	514.9	520.2	525.5	530.7	536.6	543.1	549.6	556.1	562.6	568.8
42.5°	490.5	495.8	501.1	506.4	511.7	518.0	525.5	533.0	540.4	547.9	554.6
45°	458.7	465.2	471.7	478.2	484.7	492.1	500.5	509.0	517.4	525.8	533.2
47.5°	427.3	434.4	441.5	448.6	455.6	464.1	473.9	483.8	493.7	503.5	511.3
50°	405.7	413.1	420.6	428.0	435.5	444.7	455.4	466.3	477.1	488.0	496.1
52.5°	384.9	392.7	400.6	408.5	416.3	425.9	437.3	448.7	460.1	471.5	479.8
55°	351.6	360.3	368.9	377.6	386.2	396.8	409.3	421.8	434.3	446.8	455.4
57.5°	318.7	328.5	338.3	348.0	357.8	369.0	381.7	394.5	407.2	420.0	429.3
60°	295.4	305.7	316.0	326.4	336.7	348.7	362.4	376.1	389.8	403.6	412.7
62.5°	274.6	285.3	296.0	306.7	317.5	329.7	343.4	357.1	370.8	384.5	394.2
65°	240.2	251.9	263.7	275.5	287.3	300.3	314.5	328.6	342.8	357.0	366.9
67.5°	208.6	220.9	233.2	245.5	257.8	271.3	285.8	300.3	314.8	329.3	339.2
70°	186.1	198.6	211.1	223.6	236.1	249.8	264.7	279.6	294.5	309.4	319.8
72.5°	165.3	178.2	191.1	204.0	216.9	230.8	246.0	261.1	276.1	291.2	301.4
75°	133.1	146.5	160.0	173.5	186.9	201.4	216.7	232.1	247.5	262.9	273.2
77.5°	101.9	116.0	130.1	144.1	158.2	173.1	188.7	204.4	220.0	235.6	245.9
80°	81.1	95.8	110.5	125.1	139.8	154.9	170.6	186.2	201.8	217.4	227.6
82.5°	63.8	78.3	92.8	107.2	121.7	136.9	152.7	168.5	184.3	200.2	210.3
85°	39.0	53.9	68.7	83.6	98.6	113.7	129.1	144.5	159.9	175.3	185.4
87.5°	21.4	36.1	50.9	65.6	80.4	95.6	111.3	127.0	142.7	158.4	168.4
90°	11.7	27.7	43.8	59.8	75.9	92.5	109.3	126.3	143.2	160.1	170.7
92.5°	27.5	40.3	53.1	65.8	78.6	92.8	108.4	123.9	139.6	155.2	165.0
95°	65.0	70.0	74.8	79.8	84.8	95.1	110.9	126.7	142.4	158.2	168.3
97.5°	119.4	111.5	103.6	95.8	87.9	92.5	109.4	126.5	143.4	160.4	170.0
100°	160.9	143.5	126.0	108.5	91.0	90.7	107.4	124.1	140.9	157.6	168.0
102.5°	205.9	208.4	210.9	213.5	216.1	210.2	195.8	181.6	167.2	153.0	163.6
105°	268.9	281.6	294.4	307.1	319.9	306.2	266.1	226.1	186.0	145.9	156.5
107.5°	342.0	352.2	362.5	372.7	382.9	362.6	311.4	260.3	209.3	158.2	164.1
110°	388.2	397.1	406.0	414.8	423.7	406.2	362.3	318.4	274.5	230.6	219.1



TEST NUMBER: P331414-930

CATALOG NUMBER: SA2XXDIP-C865D1080U930-4F0-1E-UDD-D

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	432.7	440.3	447.9	455.5	463.2	465.7	463.1	460.6	458.0	455.5	392.9
115°	502.7	508.6	514.5	520.4	526.4	537.1	552.8	568.4	584.0	599.7	517.7
117.5°	564.2	569.6	574.9	580.3	585.7	595.1	608.4	621.7	635.0	648.3	633.9
120°	609.9	613.8	617.7	621.5	625.3	633.8	646.9	660.0	673.0	686.2	695.2
122.5°	648.7	652.2	655.6	659.0	662.5	670.6	683.4	696.2	709.1	721.9	729.8
125°	706.8	709.3	711.8	714.3	716.8	723.7	735.1	746.4	757.8	769.2	777.0
127.5°	760.3	762.9	765.4	767.9	770.5	776.2	785.1	794.1	803.1	812.0	819.9
130°	794.3	797.2	800.0	802.8	805.7	810.7	817.8	825.0	832.2	839.4	847.3
132.5°	829.0	831.4	833.7	836.2	838.5	842.7	848.7	854.8	860.7	866.7	874.2
135°	872.9	876.0	879.1	882.2	885.3	888.9	893.1	897.2	901.3	905.5	912.4
137.5°	918.6	920.7	922.8	924.9	927.0	929.6	932.6	935.6	938.7	941.7	947.9
140°	948.4	949.7	951.0	952.3	953.6	955.5	958.1	960.7	963.4	966.0	971.5
142.5°	973.3	974.5	975.7	976.8	978.0	979.7	982.3	984.8	987.3	989.9	994.5
145°	1011.5	1011.2	1011.1	1010.9	1010.6	1012.2	1015.5	1018.7	1022.1	1025.3	1028.1
147.5°	1045.6	1044.9	1044.2	1043.4	1042.7	1043.9	1047.2	1050.4	1053.6	1056.9	1058.0
150°	1067.8	1066.4	1065.1	1063.7	1062.4	1063.2	1066.3	1069.4	1072.5	1075.5	1076.8
152.5°	1086.5	1085.0	1083.5	1082.0	1080.5	1081.2	1084.1	1087.0	1090.0	1092.9	1094.1
155°	1113.7	1112.0	1110.3	1108.5	1106.8	1107.1	1109.4	1111.7	1114.0	1116.3	1117.4
157.5°	1135.1	1133.6	1132.1	1130.7	1129.2	1129.3	1130.9	1132.5	1134.1	1135.7	1137.0
160°	1147.5	1146.4	1145.2	1144.0	1142.9	1142.9	1144.0	1145.2	1146.4	1147.5	1148.7
162.5°	1158.6	1157.5	1156.3	1155.1	1154.0	1153.9	1154.9	1155.9	1156.9	1157.9	1159.2
165°	1173.5	1172.3	1171.2	1170.0	1168.9	1168.6	1169.1	1169.8	1170.4	1170.9	1172.2
167.5°	1184.6	1183.5	1182.3	1181.1	1180.0	1179.7	1180.2	1180.7	1181.3	1181.9	1183.2
170°	1190.8	1189.7	1188.5	1187.4	1186.3	1185.9	1186.3	1186.6	1187.0	1187.4	1188.7
172.5°	1195.0	1193.8	1192.7	1191.6	1190.4	1190.0	1190.4	1190.7	1191.2	1191.6	1192.9
175°	1200.4	1199.1	1197.7	1196.4	1195.0	1194.5	1194.9	1195.3	1195.6	1196.0	1197.4
177.5°	1201.3	1200.2	1199.1	1198.0	1196.9	1196.5	1196.6	1196.8	1196.9	1197.1	1198.2
180°	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8



TEST NUMBER: P331414-930

CATALOG NUMBER: SA2XXDIP-C865D1080U930-4F0-1E-UDD-D

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	746.5	746.5	746.5	746.5	746.5	746.5	746.5	746.5
2.5°	744.0	745.0	746.0	746.3	745.9	745.5	745.1	744.8
5°	741.8	743.2	744.7	745.3	745.0	744.8	744.5	744.3
7.5°	738.3	740.0	741.8	742.5	742.2	742.0	741.8	741.5
10°	735.2	737.1	739.1	739.9	739.6	739.4	739.2	738.9
12.5°	730.0	731.9	733.9	734.7	734.4	734.2	733.9	733.7
15°	720.5	722.7	724.9	725.8	725.5	725.3	725.0	724.9
17.5°	708.4	710.6	712.9	714.0	714.0	714.0	714.0	714.0
20°	698.8	701.4	704.0	705.4	705.4	705.4	705.4	705.4
22.5°	688.4	691.0	693.7	695.2	695.5	695.9	696.3	696.8
25°	672.2	675.1	678.0	679.8	680.4	681.2	681.9	682.7
27.5°	654.3	657.9	661.5	663.7	664.2	664.7	665.3	665.8
30°	641.6	645.5	649.4	651.7	652.3	653.1	653.8	654.5
32.5°	628.1	632.5	636.9	639.8	641.1	642.4	643.7	645.0
35°	608.9	614.2	619.5	622.9	624.6	626.3	627.9	629.7
37.5°	589.0	594.8	600.7	604.5	606.3	608.1	609.9	611.7
40°	575.0	581.3	587.6	591.7	593.9	596.1	598.3	600.5
42.5°	561.5	568.3	575.2	579.7	581.8	584.0	586.1	588.3
45°	540.7	548.1	555.6	560.5	563.0	565.3	567.8	570.1
47.5°	519.1	526.8	534.7	539.9	542.5	545.2	547.8	550.5
50°	504.3	512.4	520.7	526.0	528.6	531.3	533.9	536.6
52.5°	488.2	496.6	504.9	510.5	513.4	516.2	519.0	521.9
55°	464.1	472.8	481.4	487.3	490.4	493.6	496.7	499.8
57.5°	438.6	447.9	457.3	463.6	466.7	469.9	473.0	476.2
60°	421.8	431.0	440.1	446.3	449.7	453.1	456.4	459.8
62.5°	403.9	413.6	423.3	429.8	432.9	436.1	439.3	442.5
65°	376.7	386.6	396.5	402.9	406.0	409.2	412.3	415.4
67.5°	349.2	359.1	369.2	375.8	379.0	382.3	385.6	388.8
70°	330.1	340.4	350.7	357.3	360.3	363.1	366.1	368.9
72.5°	311.5	321.6	331.8	338.6	342.1	345.5	349.0	352.5
75°	283.6	293.9	304.3	311.0	314.1	317.2	320.3	323.5
77.5°	256.2	266.5	276.8	283.6	287.0	290.3	293.8	297.1
80°	237.7	247.8	257.9	264.6	267.9	271.3	274.7	278.0
82.5°	220.4	230.4	240.5	247.2	250.4	253.5	256.7	259.8
85°	195.4	205.5	215.6	222.4	225.8	229.1	232.4	235.9
87.5°	178.4	188.4	198.4	205.0	208.1	211.2	214.4	217.6
90°	181.3	191.8	202.4	209.4	212.6	215.9	219.2	222.5
92.5°	175.0	184.9	194.9	201.4	204.5	207.6	210.7	213.8
95°	178.4	188.5	198.6	205.0	207.7	210.4	213.1	215.8
97.5°	179.7	189.3	199.0	205.4	208.5	211.5	214.6	217.7
100°	178.5	188.9	199.3	206.0	209.1	212.1	215.2	218.2
102.5°	174.3	185.1	195.8	202.7	205.9	209.0	212.2	215.4
105°	167.0	177.5	188.0	195.0	198.4	201.9	205.3	208.6
107.5°	170.0	175.9	181.9	186.5	190.0	193.4	196.8	200.2
110°	207.5	195.9	184.4	180.3	183.7	187.1	190.5	194.0



TEST NUMBER: P331414-930

CATALOG NUMBER: SA2XXDIP-C865D1080U930-4F0-1E-UDD-D

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	330.4	267.7	205.2	175.5	178.8	182.1	185.3	188.6
115°	435.8	353.8	271.8	225.3	214.0	202.8	191.6	180.3
117.5°	619.5	605.0	590.5	561.7	518.6	475.5	432.4	389.3
120°	704.3	713.3	722.3	715.2	691.8	668.5	645.1	621.7
122.5°	737.7	745.6	753.6	756.1	753.3	750.6	747.8	745.0
125°	784.8	792.6	800.5	805.8	808.5	811.3	814.0	816.8
127.5°	827.9	835.8	843.7	848.7	851.0	853.2	855.4	857.7
130°	855.2	863.0	870.9	875.7	877.4	879.2	880.9	882.6
132.5°	881.5	888.9	896.3	900.9	902.6	904.3	906.0	907.8
135°	919.4	926.4	933.4	937.6	939.1	940.7	942.2	943.8
137.5°	954.3	960.6	966.9	970.5	971.5	972.5	973.5	974.4
140°	977.1	982.7	988.2	991.3	991.7	992.2	992.7	993.2
142.5°	999.1	1003.8	1008.4	1011.0	1011.2	1011.5	1011.8	1012.1
145°	1030.9	1033.6	1036.5	1038.0	1038.2	1038.4	1038.7	1038.9
147.5°	1059.2	1060.5	1061.6	1062.1	1061.8	1061.7	1061.4	1061.2
150°	1077.9	1079.0	1080.2	1080.3	1079.3	1078.4	1077.4	1076.4
152.5°	1095.2	1096.4	1097.6	1097.5	1096.2	1094.9	1093.6	1092.4
155°	1118.6	1119.8	1121.0	1120.7	1119.2	1117.7	1116.1	1114.6
157.5°	1138.3	1139.6	1140.9	1140.8	1139.4	1137.8	1136.4	1134.8
160°	1149.8	1151.0	1152.1	1152.0	1150.7	1149.3	1148.0	1146.6
162.5°	1160.5	1161.8	1163.2	1162.9	1161.3	1159.7	1158.0	1156.3
165°	1173.6	1174.9	1176.3	1176.3	1174.9	1173.6	1172.2	1170.9
167.5°	1184.5	1185.9	1187.2	1187.0	1185.3	1183.6	1181.9	1180.1
170°	1190.1	1191.4	1192.8	1192.5	1190.8	1189.1	1187.4	1185.6
172.5°	1194.3	1195.6	1196.9	1196.8	1195.0	1193.3	1191.6	1189.8
175°	1198.7	1200.1	1201.4	1201.2	1199.2	1197.3	1195.4	1193.4
177.5°	1199.2	1200.3	1201.4	1201.3	1199.9	1198.5	1197.1	1195.7
180°	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8

(END OF REPORT)