

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333514-940

Luminaire Tested: **S125RDIP-S375D1205U940-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333514-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S375D1205U940-4F0-1E-UDD-A
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1205 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5596.4 lumens
Efficiency: N/A
Efficacy: 132.6 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 42.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333514-940

CATALOG NUMBER: S125RDIP-S375D1205U940-4F0-1E-UDD-A

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - · - · 90°-270° - · - · 135°-315°



TEST NUMBER: P333514-940

CATALOG NUMBER: S125RDIP-S375D1205U940-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	68	68	68	49	49	49	32	32	32	23
1	92	88	84	81	82	78	75	73	60	58	56	43	42	41	28	28	27	20
2	84	77	71	66	74	69	64	60	53	50	47	38	36	35	25	24	23	17
3	77	68	61	55	68	60	55	50	47	43	40	34	32	29	22	21	20	15
4	70	60	52	47	62	53	47	42	41	37	34	30	28	25	20	18	17	13
5	64	53	46	40	57	48	41	36	37	32	29	27	24	22	18	16	15	11
6	59	48	40	34	52	43	36	31	33	29	25	25	21	19	16	15	13	10
7	54	43	35	30	48	38	32	27	30	25	22	22	19	17	15	13	12	9
8	50	39	31	26	45	35	28	24	27	23	19	20	17	15	14	12	10	8
9	47	35	28	23	42	32	25	21	25	20	17	19	15	13	13	11	9	7
10	44	32	25	21	39	29	23	19	23	18	15	17	14	12	12	10	8	6

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	3241	3241	3241	3241
5°	3729	3246	2867	3246
10°	4278	3229	2530	3229
15°	4621	3196	2249	3196
20°	5096	3158	2076	3158
25°	5897	3107	1927	3107
30°	6416	3053	1829	3053
35°	5412	2990	1738	2990
40°	3780	2878	1661	2878
45°	2804	2726	1585	2726
50°	2237	2569	1519	2569
55°	1897	2374	1462	2374
60°	1639	2198	1368	2198
65°	1461	2008	1177	2008
70°	1284	1841	1074	1841
75°	1110	1592	1008	1592
80°	841	1339	841	1339
85°	704	1052	793	1052



TEST NUMBER: P333514-940

CATALOG NUMBER: S125RDIP-S375D1205U940-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.1	0.9
10°-20°	141.1	2.5
20°-30°	223.6	4.0
30°-40°	269.7	4.8
40°-50°	240.9	4.3
50°-60°	184.7	3.3
60°-70°	120.0	2.1
70°-80°	58.3	1.0
80°-90°	16.8	0.3
90°-100°	50.8	0.9
100°-110°	313.1	5.6
110°-120°	567.9	10.1
120°-130°	728.8	13.0
130°-140°	783.9	14.0
140°-150°	735.8	13.1
150°-160°	595.2	10.6
160°-170°	384.9	6.9
170°-180°	132.8	2.4
0°-30°	412.8	7.4
0°-40°	682.5	12.2
0°-60°	1108.1	19.8
0°-90°	1303.3	23.3
90°-120°	931.8	16.6
90°-150°	3180.2	56.8
90°-180°	4293.0	76.7
0°-180°	5596.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	502	502	502	502	502	
5°	575	501	442	501	575	57
15°	691	478	336	478	691	198
25°	828	436	270	436	828	380
35°	686	379	220	379	686	415
45°	307	298	174	298	307	245
55°	168	211	130	211	168	153
65°	96	131	77	131	96	95
75°	44	64	40	64	44	47
85°	10	14	11	14	10	12
90°	25	1	25	1	25	11
95°	22	59	22	59	22	18
105°	308	305	308	305	308	278
115°	568	572	568	572	568	564
125°	814	814	814	814	814	724
135°	1010	1015	1010	1015	1010	780
145°	1173	1176	1173	1176	1173	733
155°	1286	1295	1286	1295	1286	593
165°	1360	1367	1360	1367	1360	384
175°	1392	1398	1392	1398	1392	132
180°	1398	1398	1398	1398	1398	



TEST NUMBER: P333514-940

CATALOG NUMBER: S125RDIP-S375D1205U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9
2.5°	528.0	527.6	528.3	526.5	526.6	523.9	523.9	521.7	518.9	516.7	515.8
5°	575.2	575.7	574.9	571.8	569.7	566.6	563.1	557.0	551.8	546.8	543.0
7.5°	624.0	624.3	621.5	620.6	615.4	611.6	603.9	595.4	588.0	578.5	571.2
10°	652.4	652.1	649.3	646.9	642.5	636.7	629.0	619.2	609.9	599.6	589.7
12.5°	668.8	668.2	667.4	664.6	660.4	655.3	648.8	639.1	627.7	616.4	604.8
15°	691.1	689.6	687.0	683.4	677.4	671.5	664.3	655.7	644.7	632.0	621.3
17.5°	718.6	718.6	714.5	709.6	701.5	691.0	679.8	665.9	651.0	637.0	625.6
20°	741.4	740.7	736.6	727.1	717.8	704.6	691.9	674.8	656.7	638.3	624.1
22.5°	774.0	772.4	768.1	755.6	741.3	724.2	704.7	683.9	661.9	641.1	622.4
25°	827.5	826.3	817.8	803.3	783.2	757.0	731.5	702.8	671.3	643.9	621.3
27.5°	864.1	862.7	856.4	844.5	825.8	798.3	763.8	725.4	686.1	648.4	615.7
30°	860.4	863.5	862.7	857.1	843.1	818.4	786.5	743.4	696.6	652.4	613.4
32.5°	808.7	811.5	818.7	829.6	830.5	820.6	796.7	756.9	708.5	658.1	611.5
35°	686.5	690.3	704.3	726.3	755.2	779.3	784.2	762.8	719.3	665.1	608.9
37.5°	527.8	548.0	559.9	583.1	626.7	671.0	713.6	729.3	710.9	662.2	604.5
40°	448.4	453.3	474.3	500.5	537.2	583.3	644.1	688.0	689.4	655.7	597.5
42.5°	383.7	390.0	404.4	425.3	456.7	502.8	565.6	623.6	650.3	637.5	588.4
45°	307.0	311.7	322.3	338.3	362.4	400.6	454.5	521.5	574.6	595.5	564.2
47.5°	252.2	254.8	263.9	276.2	294.0	321.7	363.6	421.7	485.4	530.1	525.8
50°	222.6	225.4	232.4	241.7	256.7	280.2	313.6	362.0	427.8	482.3	493.3
52.5°	199.5	201.9	206.3	215.0	227.4	245.4	272.4	316.2	375.3	433.4	458.7
55°	168.5	170.2	173.7	178.6	188.5	201.5	224.8	255.1	302.9	361.4	398.5
57.5°	143.1	143.9	146.2	150.7	157.6	167.0	183.9	209.5	243.8	296.5	337.4
60°	126.9	127.8	130.6	133.8	139.1	147.8	161.0	178.9	211.8	255.3	296.7
62.5°	114.0	114.6	115.8	118.9	123.6	130.3	140.6	155.2	181.5	219.7	258.8
65°	95.6	95.8	96.2	98.7	101.6	106.6	113.3	123.6	143.4	172.3	206.9
67.5°	77.8	78.2	79.6	80.5	83.5	86.1	90.1	97.9	111.9	131.3	158.3
70°	68.0	67.8	69.2	70.3	71.2	74.4	77.0	83.5	92.1	106.9	129.4
72.5°	58.8	58.2	58.9	59.2	60.5	62.7	65.4	69.3	76.0	86.1	103.3
75°	44.5	44.7	44.7	45.1	46.2	47.0	47.8	49.8	53.6	60.4	69.6
77.5°	31.2	30.9	31.7	31.9	32.5	33.4	34.2	35.0	36.5	39.2	44.1
80°	22.6	22.6	22.8	23.5	23.3	23.7	24.7	25.6	27.4	29.1	30.7
82.5°	17.4	17.2	17.4	17.6	17.5	17.9	18.3	18.5	19.2	20.0	21.1
85°	9.5	9.5	9.7	9.7	9.9	9.9	10.1	10.1	10.1	10.3	10.5
87.5°	8.6	8.3	8.0	7.8	7.8	8.0	7.7	7.2	7.0	6.8	6.6
90°	24.9	24.2	23.5	22.8	22.1	21.2	20.1	18.9	17.7	16.6	15.0
92.5°	23.2	22.9	22.6	22.2	21.9	21.2	20.1	18.9	17.7	16.6	15.2
95°	21.8	21.8	21.8	21.8	21.8	21.2	20.1	18.9	17.7	16.6	25.3
97.5°	21.8	21.8	21.8	21.8	21.8	25.0	31.5	38.0	44.5	51.0	68.3
100°	21.8	22.6	23.6	24.5	25.4	43.1	77.4	111.7	146.0	180.3	179.4
102.5°	130.4	146.1	161.7	177.4	193.1	204.1	210.6	217.0	223.6	230.1	229.5
105°	307.8	308.0	308.3	308.4	308.7	308.8	308.8	308.8	308.8	308.8	308.8
107.5°	388.0	388.7	389.4	390.0	390.7	391.1	391.0	391.0	390.9	390.9	390.5
110°	443.5	443.4	443.1	442.8	442.6	442.8	443.5	444.3	445.0	445.6	445.1



TEST NUMBER: P333514-940

CATALOG NUMBER: S125RDIP-S375D1205U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	493.3	493.7	493.9	494.3	494.5	495.2	496.1	497.0	497.8	498.6	498.4
115°	567.9	569.3	570.7	572.0	573.5	574.6	575.5	576.4	577.4	578.3	578.0
117.5°	647.5	648.1	648.7	649.3	649.9	650.8	652.0	653.2	654.4	655.6	654.7
120°	696.4	697.6	698.7	699.9	701.1	701.9	702.3	702.8	703.2	703.6	702.9
122.5°	742.9	744.2	745.5	746.8	748.1	749.1	749.6	750.0	750.5	750.9	750.6
125°	813.5	814.2	814.9	815.6	816.3	817.1	818.0	818.9	819.8	820.7	820.7
127.5°	873.0	874.7	876.4	878.2	879.9	880.9	881.5	881.9	882.4	883.0	883.1
130°	916.1	917.3	918.5	919.5	920.7	921.7	922.3	923.0	923.7	924.4	924.2
132.5°	955.9	957.1	958.2	959.4	960.6	961.2	961.3	961.4	961.6	961.7	962.2
135°	1010.4	1011.8	1013.2	1014.6	1015.9	1016.9	1017.4	1017.8	1018.2	1018.7	1019.1
137.5°	1065.1	1066.3	1067.6	1068.7	1070.0	1070.5	1070.4	1070.3	1070.2	1070.1	1070.5
140°	1097.5	1098.9	1100.3	1101.6	1103.0	1103.5	1103.0	1102.5	1102.1	1101.6	1101.9
142.5°	1128.2	1129.5	1131.0	1132.3	1133.7	1134.3	1134.3	1134.2	1134.1	1134.0	1133.6
145°	1173.1	1174.5	1175.9	1177.2	1178.7	1179.2	1179.0	1178.8	1178.6	1178.3	1178.3
147.5°	1210.2	1211.9	1213.5	1215.2	1216.8	1217.5	1217.3	1217.0	1216.7	1216.5	1216.2
150°	1234.3	1236.1	1238.0	1239.8	1241.6	1242.3	1241.9	1241.4	1240.9	1240.5	1240.0
152.5°	1256.7	1258.3	1260.0	1261.6	1263.3	1263.9	1263.5	1262.9	1262.5	1262.0	1261.6
155°	1286.1	1287.9	1289.8	1291.6	1293.4	1294.1	1293.3	1292.6	1292.0	1291.3	1290.8
157.5°	1310.7	1312.6	1314.5	1316.3	1318.1	1318.7	1317.9	1317.2	1316.4	1315.7	1315.7
160°	1326.5	1328.4	1330.2	1332.0	1333.9	1334.4	1333.4	1332.5	1331.6	1330.6	1330.4
162.5°	1340.6	1342.6	1344.6	1346.7	1348.7	1349.1	1347.8	1346.5	1345.2	1343.9	1343.7
165°	1359.7	1361.5	1363.3	1365.2	1367.0	1367.3	1365.9	1364.5	1363.2	1361.7	1361.5
167.5°	1373.0	1375.0	1377.1	1379.1	1381.3	1381.4	1379.7	1378.1	1376.4	1374.8	1374.6
170°	1380.4	1382.5	1384.6	1386.6	1388.7	1388.8	1387.0	1385.1	1383.3	1381.4	1381.2
172.5°	1385.4	1387.4	1389.6	1391.6	1393.7	1393.8	1392.2	1390.5	1388.9	1387.2	1386.8
175°	1391.8	1393.8	1396.0	1398.0	1400.1	1400.2	1398.4	1396.5	1394.6	1392.9	1392.6
177.5°	1395.5	1397.0	1398.5	1400.0	1401.4	1401.5	1400.3	1398.9	1397.7	1396.3	1396.2
180°	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0



TEST NUMBER: P333514-940

CATALOG NUMBER: S125RDIP-S375D1205U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9
2.5°	515.8	514.6	512.5	510.5	508.0	505.9	504.4	502.6	500.2	497.5	495.2
5°	538.6	534.0	528.1	522.9	516.3	511.2	505.9	500.7	495.5	488.9	483.1
7.5°	563.9	554.6	545.5	534.0	523.6	514.3	505.4	496.4	487.6	478.2	469.2
10°	579.4	568.0	555.5	541.1	527.9	515.3	503.8	492.4	480.5	470.0	458.7
12.5°	593.9	579.3	564.9	546.7	530.8	515.5	500.8	486.7	473.9	460.3	448.1
15°	607.0	592.5	576.5	554.3	532.2	513.6	496.3	478.0	462.2	446.9	433.3
17.5°	612.1	596.9	578.3	556.9	532.8	509.4	487.1	467.1	448.4	430.6	415.4
20°	610.1	595.5	576.3	555.9	530.1	505.9	481.7	459.5	438.6	419.9	403.7
22.5°	605.3	590.2	571.7	550.1	525.7	499.9	474.1	450.4	428.6	409.2	391.5
25°	598.2	577.6	558.6	537.5	514.2	488.7	462.2	436.0	412.7	392.9	373.5
27.5°	590.7	565.0	540.8	520.0	495.3	472.6	446.9	420.1	395.7	375.5	355.6
30°	583.9	555.1	528.5	504.8	481.5	459.9	435.6	409.4	384.2	363.5	343.3
32.5°	575.5	544.8	515.7	488.3	465.8	444.4	422.4	397.3	372.9	351.4	330.9
35°	565.0	525.8	494.1	465.0	440.1	419.3	399.5	379.3	354.8	332.5	312.5
37.5°	551.2	506.7	470.0	438.4	412.1	391.2	375.5	357.0	334.7	313.4	294.9
40°	542.7	492.8	452.7	421.3	393.8	371.7	357.0	341.4	321.0	301.0	282.5
42.5°	531.5	480.2	435.2	402.6	374.8	353.6	338.8	325.1	308.0	289.2	269.3
45°	509.5	455.6	408.4	373.4	345.4	324.5	310.7	298.5	285.6	268.2	250.9
47.5°	481.0	429.9	380.5	342.2	314.9	295.5	282.1	272.5	263.2	248.5	231.8
50°	458.1	408.8	360.6	323.5	294.3	275.9	263.3	255.7	247.3	233.9	219.8
52.5°	431.0	387.0	339.8	301.9	274.3	257.1	245.0	237.4	230.4	219.5	206.2
55°	388.4	349.8	306.6	272.2	246.8	229.5	218.0	210.8	206.7	197.4	186.9
57.5°	339.2	311.7	273.5	240.3	217.8	200.8	192.3	186.2	181.6	175.0	167.6
60°	305.0	285.6	251.4	219.8	199.2	183.0	175.3	170.2	165.9	160.3	154.5
62.5°	270.2	256.1	226.3	199.2	180.3	166.7	159.5	154.9	149.9	146.2	140.5
65°	223.6	211.0	190.4	169.2	151.7	140.7	135.5	131.4	128.4	124.2	120.3
67.5°	173.9	168.8	154.5	139.9	127.3	117.6	113.2	110.3	106.6	104.2	101.5
70°	143.4	140.9	130.8	121.2	109.4	102.8	98.7	97.5	92.9	90.4	88.6
72.5°	116.4	115.2	109.4	102.7	94.4	88.6	84.9	83.5	80.5	78.6	77.4
75°	79.7	80.2	79.1	74.8	71.7	68.0	64.7	63.8	61.8	60.2	59.1
77.5°	50.5	52.5	52.6	52.4	51.2	49.0	47.5	46.9	44.9	44.3	44.1
80°	34.6	36.9	39.0	38.7	38.3	37.7	36.6	36.0	35.0	34.4	34.0
82.5°	23.1	25.1	26.9	28.0	27.9	27.3	26.7	26.3	26.1	25.7	25.6
85°	10.9	11.3	11.9	13.4	14.4	14.6	14.4	14.2	13.6	13.8	14.0
87.5°	6.4	6.2	6.0	5.6	5.1	5.5	5.7	5.4	5.5	5.5	5.6
90°	13.4	11.8	10.2	8.4	6.6	4.7	2.9	1.1	2.9	4.7	6.6
92.5°	13.7	12.3	10.9	10.8	12.1	13.4	14.7	16.0	14.7	13.4	12.1
95°	34.1	42.8	51.6	56.3	57.0	57.7	58.4	59.0	58.4	57.7	57.0
97.5°	85.6	102.9	120.3	128.3	127.1	125.8	124.6	123.3	124.6	125.8	127.1
100°	178.5	177.5	176.6	175.8	175.1	174.4	173.8	173.1	173.8	174.4	175.1
102.5°	229.0	228.4	227.8	227.1	226.2	225.4	224.5	223.6	224.5	225.4	226.2
105°	308.8	308.8	308.8	308.4	307.5	306.5	305.6	304.7	305.6	306.5	307.5
107.5°	389.9	389.5	389.1	388.9	388.9	388.9	388.9	388.9	388.9	388.9	388.9
110°	444.7	444.3	443.8	443.5	443.5	443.5	443.5	443.5	443.5	443.5	443.5



TEST NUMBER: P333514-940

CATALOG NUMBER: S125RDIP-S375D1205U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	498.1	497.8	497.6	497.1	496.6	496.1	495.5	495.0	495.5	496.1	496.6
115°	577.8	577.6	577.4	576.7	575.5	574.4	573.2	572.0	573.2	574.4	575.5
117.5°	653.8	653.0	652.1	651.7	651.8	651.8	651.8	651.8	651.8	651.8	651.8
120°	702.3	701.6	700.9	700.7	700.9	701.2	701.3	701.6	701.3	701.2	700.9
122.5°	750.3	749.9	749.7	749.0	748.1	747.3	746.5	745.6	746.5	747.3	748.1
125°	820.7	820.7	820.7	819.9	818.3	816.7	815.1	813.5	815.1	816.7	818.3
127.5°	883.2	883.3	883.5	883.0	881.8	880.7	879.6	878.4	879.6	880.7	881.8
130°	924.0	923.7	923.5	922.8	921.7	920.5	919.4	918.2	919.4	920.5	921.7
132.5°	962.7	963.2	963.8	963.3	962.0	960.6	959.3	958.0	959.3	960.6	962.0
135°	1019.7	1020.1	1020.6	1020.1	1018.7	1017.4	1015.9	1014.6	1015.9	1017.4	1018.7
137.5°	1070.9	1071.4	1071.7	1071.4	1070.1	1069.0	1067.8	1066.6	1067.8	1069.0	1070.1
140°	1102.1	1102.3	1102.5	1102.4	1102.0	1101.5	1101.1	1100.5	1101.1	1101.5	1102.0
142.5°	1133.3	1133.0	1132.7	1132.4	1132.1	1131.8	1131.5	1131.2	1131.5	1131.8	1132.1
145°	1178.3	1178.3	1178.3	1178.0	1177.6	1177.1	1176.7	1176.3	1176.7	1177.1	1177.6
147.5°	1215.8	1215.6	1215.3	1215.2	1215.3	1215.4	1215.5	1215.6	1215.5	1215.4	1215.3
150°	1239.6	1239.1	1238.7	1238.7	1239.1	1239.6	1240.0	1240.5	1240.0	1239.6	1239.1
152.5°	1261.1	1260.7	1260.2	1260.4	1261.5	1262.5	1263.6	1264.5	1263.6	1262.5	1261.5
155°	1290.3	1289.9	1289.4	1289.9	1291.3	1292.6	1294.1	1295.4	1294.1	1292.6	1291.3
157.5°	1315.6	1315.6	1315.5	1315.9	1316.8	1317.6	1318.4	1319.3	1318.4	1317.6	1316.8
160°	1330.2	1330.0	1329.7	1330.3	1331.7	1333.1	1334.4	1335.9	1334.4	1333.1	1331.7
162.5°	1343.5	1343.2	1343.0	1343.5	1345.0	1346.3	1347.7	1349.1	1347.7	1346.3	1345.0
165°	1361.3	1361.0	1360.8	1361.4	1362.8	1364.1	1365.6	1366.9	1365.6	1364.1	1362.8
167.5°	1374.3	1374.1	1373.9	1374.5	1375.9	1377.3	1378.8	1380.2	1378.8	1377.3	1375.9
170°	1381.0	1380.7	1380.5	1381.2	1382.8	1384.4	1386.1	1387.7	1386.1	1384.4	1382.8
172.5°	1386.4	1386.0	1385.5	1386.2	1387.8	1389.4	1391.0	1392.6	1391.0	1389.4	1387.8
175°	1392.4	1392.1	1391.9	1392.5	1393.8	1395.3	1396.6	1398.0	1396.6	1395.3	1393.8
177.5°	1396.0	1395.8	1395.6	1396.1	1397.2	1398.3	1399.4	1400.5	1399.4	1398.3	1397.2
180°	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0



TEST NUMBER: P333514-940

CATALOG NUMBER: S125RDIP-S375D1205U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9
2.5°	493.5	491.2	489.5	486.2	483.9	483.0	481.2	480.6	482.5	481.2	481.0
5°	478.8	472.9	468.1	463.4	458.3	455.0	450.0	449.2	447.9	446.1	445.7
7.5°	461.3	453.4	447.4	439.5	432.7	427.2	421.1	418.1	416.5	414.1	410.9
10°	449.4	440.1	431.9	424.0	415.6	408.8	402.6	397.9	394.8	391.9	390.7
12.5°	437.7	428.2	417.7	408.2	398.8	391.2	384.3	381.2	377.8	374.4	371.6
15°	419.5	407.0	395.4	384.5	376.5	368.2	361.6	357.0	352.0	350.4	344.9
17.5°	400.2	387.9	374.3	362.9	353.6	344.5	337.2	332.1	328.2	322.9	320.4
20°	388.2	373.5	360.3	349.8	339.6	328.9	321.5	317.1	313.4	309.1	307.0
22.5°	375.3	361.1	347.5	335.2	324.8	314.1	308.9	304.4	300.2	296.2	293.5
25°	356.4	342.1	327.8	315.0	304.2	296.5	290.3	285.2	282.9	279.0	276.1
27.5°	337.8	322.4	307.7	295.0	286.4	278.8	273.8	269.7	265.6	262.3	259.7
30°	325.7	310.1	294.0	283.9	274.8	267.7	262.1	258.2	255.1	252.0	250.1
32.5°	313.7	297.6	283.3	272.4	263.9	257.6	251.9	248.1	244.9	241.5	239.2
35°	294.4	277.9	266.4	255.7	247.3	241.5	237.6	232.2	229.5	227.0	224.8
37.5°	276.5	261.2	248.7	239.3	231.9	226.2	221.1	218.3	215.0	212.8	210.9
40°	263.3	249.3	238.0	228.1	222.7	216.3	211.6	207.9	205.5	202.5	200.5
42.5°	251.5	238.4	227.4	218.6	211.9	206.4	201.9	198.1	195.0	193.0	191.3
45°	234.7	221.7	211.0	202.8	196.5	191.5	186.6	184.9	180.7	178.3	177.4
47.5°	217.3	205.7	195.4	187.8	181.5	176.6	172.1	168.4	166.0	163.6	162.3
50°	205.6	194.5	184.9	177.4	171.2	165.9	161.8	159.3	156.1	153.9	152.3
52.5°	193.9	183.6	174.0	166.8	161.5	156.1	151.5	149.1	146.2	144.7	143.6
55°	177.2	166.3	158.0	151.1	145.4	140.5	136.2	133.8	131.9	130.5	130.0
57.5°	158.3	149.6	142.0	135.6	129.8	125.2	121.4	119.0	117.4	117.2	115.9
60°	145.9	138.0	131.1	124.2	119.3	114.9	111.6	109.0	107.4	107.2	106.7
62.5°	133.5	126.0	119.5	113.5	109.1	105.0	101.7	98.8	97.8	96.8	95.9
65°	115.2	108.3	103.0	98.3	93.5	90.1	86.9	85.1	82.8	81.6	79.4
67.5°	97.2	91.9	86.8	82.8	79.0	75.7	73.1	70.4	68.8	67.9	66.3
70°	85.3	81.1	76.1	71.7	68.8	66.2	64.1	61.0	59.9	59.1	58.3
72.5°	74.1	70.4	66.2	62.6	59.7	57.2	54.8	53.4	52.3	51.5	51.1
75°	58.3	54.8	51.1	48.6	46.5	44.5	43.2	42.3	41.8	41.6	40.8
77.5°	42.8	40.9	38.0	36.0	34.7	33.8	32.7	32.2	32.1	31.2	30.9
80°	32.7	31.7	29.2	28.4	27.4	26.6	25.9	25.0	23.9	23.5	22.8
82.5°	24.3	23.4	22.3	21.0	20.2	19.6	19.1	18.6	18.8	18.2	17.9
85°	13.0	11.9	11.5	11.3	10.9	11.3	11.1	10.9	10.7	10.5	10.7
87.5°	5.8	6.2	6.3	7.0	6.8	7.3	7.5	7.6	7.8	8.0	8.0
90°	8.4	10.2	11.8	13.4	15.0	16.6	17.7	18.9	20.1	21.2	22.1
92.5°	10.8	10.9	12.3	13.7	15.2	16.6	17.7	18.9	20.1	21.2	21.9
95°	56.3	51.6	42.8	34.1	25.3	16.6	17.7	18.9	20.1	21.2	21.8
97.5°	128.3	120.3	102.9	85.6	68.3	51.0	44.5	38.0	31.5	25.0	21.8
100°	175.8	176.6	177.5	178.5	179.4	180.3	146.0	111.7	77.4	43.1	25.4
102.5°	227.1	227.8	228.4	229.0	229.5	230.1	223.6	217.0	210.6	204.1	193.1
105°	308.4	308.8	308.8	308.8	308.8	308.8	308.8	308.8	308.8	308.8	308.7
107.5°	388.9	389.1	389.5	389.9	390.5	390.9	390.9	391.0	391.0	391.1	390.7
110°	443.5	443.8	444.3	444.7	445.1	445.6	445.0	444.3	443.5	442.8	442.6



TEST NUMBER: P333514-940

CATALOG NUMBER: S125RDIP-S375D1205U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	497.1	497.6	497.8	498.1	498.4	498.6	497.8	497.0	496.1	495.2	494.5
115°	576.7	577.4	577.6	577.8	578.0	578.3	577.4	576.4	575.5	574.6	573.5
117.5°	651.7	652.1	653.0	653.8	654.7	655.6	654.4	653.2	652.0	650.8	649.9
120°	700.7	700.9	701.6	702.3	702.9	703.6	703.2	702.8	702.3	701.9	701.1
122.5°	749.0	749.7	749.9	750.3	750.6	750.9	750.5	750.0	749.6	749.1	748.1
125°	819.9	820.7	820.7	820.7	820.7	820.7	819.8	818.9	818.0	817.1	816.3
127.5°	883.0	883.5	883.3	883.2	883.1	883.0	882.4	881.9	881.5	880.9	879.9
130°	922.8	923.5	923.7	924.0	924.2	924.4	923.7	923.0	922.3	921.7	920.7
132.5°	963.3	963.8	963.2	962.7	962.2	961.7	961.6	961.4	961.3	961.2	960.6
135°	1020.1	1020.6	1020.1	1019.7	1019.1	1018.7	1018.2	1017.8	1017.4	1016.9	1015.9
137.5°	1071.4	1071.7	1071.4	1070.9	1070.5	1070.1	1070.2	1070.3	1070.4	1070.5	1070.0
140°	1102.4	1102.5	1102.3	1102.1	1101.9	1101.6	1102.1	1102.5	1103.0	1103.5	1103.0
142.5°	1132.4	1132.7	1133.0	1133.3	1133.6	1134.0	1134.1	1134.2	1134.3	1134.3	1133.7
145°	1178.0	1178.3	1178.3	1178.3	1178.3	1178.3	1178.6	1178.8	1179.0	1179.2	1178.7
147.5°	1215.2	1215.3	1215.6	1215.8	1216.2	1216.5	1216.7	1217.0	1217.3	1217.5	1216.8
150°	1238.7	1238.7	1239.1	1239.6	1240.0	1240.5	1240.9	1241.4	1241.9	1242.3	1241.6
152.5°	1260.4	1260.2	1260.7	1261.1	1261.6	1262.0	1262.5	1262.9	1263.5	1263.9	1263.3
155°	1289.9	1289.4	1289.9	1290.3	1290.8	1291.3	1292.0	1292.6	1293.3	1294.1	1293.4
157.5°	1315.9	1315.5	1315.6	1315.6	1315.7	1315.7	1316.4	1317.2	1317.9	1318.7	1318.1
160°	1330.3	1329.7	1330.0	1330.2	1330.4	1330.6	1331.6	1332.5	1333.4	1334.4	1333.9
162.5°	1343.5	1343.0	1343.2	1343.5	1343.7	1343.9	1345.2	1346.5	1347.8	1349.1	1348.7
165°	1361.4	1360.8	1361.0	1361.3	1361.5	1361.7	1363.2	1364.5	1365.9	1367.3	1367.0
167.5°	1374.5	1373.9	1374.1	1374.3	1374.6	1374.8	1376.4	1378.1	1379.7	1381.4	1381.3
170°	1381.2	1380.5	1380.7	1381.0	1381.2	1381.4	1383.3	1385.1	1387.0	1388.8	1388.7
172.5°	1386.2	1385.5	1386.0	1386.4	1386.8	1387.2	1388.9	1390.5	1392.2	1393.8	1393.7
175°	1392.5	1391.9	1392.1	1392.4	1392.6	1392.9	1394.6	1396.5	1398.4	1400.2	1400.1
177.5°	1396.1	1395.6	1395.8	1396.0	1396.2	1396.3	1397.7	1398.9	1400.3	1401.5	1401.4
180°	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0



TEST NUMBER: P333514-940

CATALOG NUMBER: S125RDIP-S375D1205U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9
2.5°	480.8	479.0	478.5	479.2	478.5	479.0	480.8	481.0	481.2	482.5	480.6
5°	443.6	441.6	442.6	442.2	442.6	441.6	443.6	445.7	446.1	447.9	449.2
7.5°	410.9	408.3	405.6	406.4	405.6	408.3	410.9	410.9	414.1	416.5	418.1
10°	388.0	385.9	384.7	385.8	384.7	385.9	388.0	390.7	391.9	394.8	397.9
12.5°	368.7	367.5	366.4	366.0	366.4	367.5	368.7	371.6	374.4	377.8	381.2
15°	342.4	340.0	338.9	336.3	338.9	340.0	342.4	344.9	350.4	352.0	357.0
17.5°	318.3	317.4	314.8	313.6	314.8	317.4	318.3	320.4	322.9	328.2	332.1
20°	303.9	303.1	300.4	302.0	300.4	303.1	303.9	307.0	309.1	313.4	317.1
22.5°	292.0	290.3	289.4	288.9	289.4	290.3	292.0	293.5	296.2	300.2	304.4
25°	275.3	272.6	271.5	270.4	271.5	272.6	275.3	276.1	279.0	282.9	285.2
27.5°	258.5	257.1	255.7	255.4	255.7	257.1	258.5	259.7	262.3	265.6	269.7
30°	247.6	246.2	245.2	245.2	245.2	246.2	247.6	250.1	252.0	255.1	258.2
32.5°	237.9	236.8	235.8	235.6	235.8	236.8	237.9	239.2	241.5	244.9	248.1
35°	223.7	222.1	221.7	220.4	221.7	222.1	223.7	224.8	227.0	229.5	232.2
37.5°	209.0	207.7	207.7	207.5	207.7	207.7	209.0	210.9	212.8	215.0	218.3
40°	199.7	198.6	198.4	197.0	198.4	198.6	199.7	200.5	202.5	205.5	207.9
42.5°	189.6	189.0	188.3	187.7	188.3	189.0	189.6	191.3	193.0	195.0	198.1
45°	175.9	174.5	174.5	173.5	174.5	174.5	175.9	177.4	178.3	180.7	184.9
47.5°	161.8	160.8	160.9	159.8	160.9	160.8	161.8	162.3	163.6	166.0	168.4
50°	152.5	151.9	151.7	151.2	151.7	151.9	152.5	152.3	153.9	156.1	159.3
52.5°	143.1	142.8	143.6	142.7	143.6	142.8	143.1	143.6	144.7	146.2	149.1
55°	130.5	129.8	131.1	129.8	131.1	129.8	130.5	130.0	130.5	131.9	133.8
57.5°	115.9	115.3	116.5	115.8	116.5	115.3	115.9	115.9	117.2	117.4	119.0
60°	106.3	105.0	105.7	105.9	105.7	105.0	106.3	106.7	107.2	107.4	109.0
62.5°	95.0	94.2	94.7	93.7	94.7	94.2	95.0	95.9	96.8	97.8	98.8
65°	78.9	78.3	77.5	77.0	77.5	78.3	78.9	79.4	81.6	82.8	85.1
67.5°	66.3	64.8	64.7	65.1	64.7	64.8	66.3	66.3	67.9	68.8	70.4
70°	57.1	57.1	56.9	56.9	56.9	57.1	57.1	58.3	59.1	59.9	61.0
72.5°	50.6	50.5	50.1	49.9	50.1	50.5	50.6	51.1	51.5	52.3	53.4
75°	40.8	41.0	40.6	40.4	40.6	41.0	40.8	40.8	41.6	41.8	42.3
77.5°	30.1	29.2	29.7	29.2	29.7	29.2	30.1	30.9	31.2	32.1	32.2
80°	22.8	22.6	23.3	22.6	23.3	22.6	22.8	22.8	23.5	23.9	25.0
82.5°	18.1	17.9	18.2	17.7	18.2	17.9	18.1	17.9	18.2	18.8	18.6
85°	10.9	10.7	10.5	10.7	10.5	10.7	10.9	10.7	10.5	10.7	10.9
87.5°	8.4	8.3	8.5	8.6	8.5	8.3	8.4	8.0	8.0	7.8	7.6
90°	22.8	23.5	24.2	24.9	24.2	23.5	22.8	22.1	21.2	20.1	18.9
92.5°	22.2	22.6	22.9	23.2	22.9	22.6	22.2	21.9	21.2	20.1	18.9
95°	21.8	21.8	21.8	21.8	21.8	21.8	21.8	21.8	21.2	20.1	18.9
97.5°	21.8	21.8	21.8	21.8	21.8	21.8	21.8	21.8	25.0	31.5	38.0
100°	24.5	23.6	22.6	21.8	22.6	23.6	24.5	25.4	43.1	77.4	111.7
102.5°	177.4	161.7	146.1	130.4	146.1	161.7	177.4	193.1	204.1	210.6	217.0
105°	308.4	308.3	308.0	307.8	308.0	308.3	308.4	308.7	308.8	308.8	308.8
107.5°	390.0	389.4	388.7	388.0	388.7	389.4	390.0	390.7	391.1	391.0	391.0
110°	442.8	443.1	443.4	443.5	443.4	443.1	442.8	442.6	442.8	443.5	444.3



TEST NUMBER: P333514-940

CATALOG NUMBER: S125RDIP-S375D1205U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	494.3	493.9	493.7	493.3	493.7	493.9	494.3	494.5	495.2	496.1	497.0
115°	572.0	570.7	569.3	567.9	569.3	570.7	572.0	573.5	574.6	575.5	576.4
117.5°	649.3	648.7	648.1	647.5	648.1	648.7	649.3	649.9	650.8	652.0	653.2
120°	699.9	698.7	697.6	696.4	697.6	698.7	699.9	701.1	701.9	702.3	702.8
122.5°	746.8	745.5	744.2	742.9	744.2	745.5	746.8	748.1	749.1	749.6	750.0
125°	815.6	814.9	814.2	813.5	814.2	814.9	815.6	816.3	817.1	818.0	818.9
127.5°	878.2	876.4	874.7	873.0	874.7	876.4	878.2	879.9	880.9	881.5	881.9
130°	919.5	918.5	917.3	916.1	917.3	918.5	919.5	920.7	921.7	922.3	923.0
132.5°	959.4	958.2	957.1	955.9	957.1	958.2	959.4	960.6	961.2	961.3	961.4
135°	1014.6	1013.2	1011.8	1010.4	1011.8	1013.2	1014.6	1015.9	1016.9	1017.4	1017.8
137.5°	1068.7	1067.6	1066.3	1065.1	1066.3	1067.6	1068.7	1070.0	1070.5	1070.4	1070.3
140°	1101.6	1100.3	1098.9	1097.5	1098.9	1100.3	1101.6	1103.0	1103.5	1103.0	1102.5
142.5°	1132.3	1131.0	1129.5	1128.2	1129.5	1131.0	1132.3	1133.7	1134.3	1134.3	1134.2
145°	1177.2	1175.9	1174.5	1173.1	1174.5	1175.9	1177.2	1178.7	1179.2	1179.0	1178.8
147.5°	1215.2	1213.5	1211.9	1210.2	1211.9	1213.5	1215.2	1216.8	1217.5	1217.3	1217.0
150°	1239.8	1238.0	1236.1	1234.3	1236.1	1238.0	1239.8	1241.6	1242.3	1241.9	1241.4
152.5°	1261.6	1260.0	1258.3	1256.7	1258.3	1260.0	1261.6	1263.3	1263.9	1263.5	1262.9
155°	1291.6	1289.8	1287.9	1286.1	1287.9	1289.8	1291.6	1293.4	1294.1	1293.3	1292.6
157.5°	1316.3	1314.5	1312.6	1310.7	1312.6	1314.5	1316.3	1318.1	1318.7	1317.9	1317.2
160°	1332.0	1330.2	1328.4	1326.5	1328.4	1330.2	1332.0	1333.9	1334.4	1333.4	1332.5
162.5°	1346.7	1344.6	1342.6	1340.6	1342.6	1344.6	1346.7	1348.7	1349.1	1347.8	1346.5
165°	1365.2	1363.3	1361.5	1359.7	1361.5	1363.3	1365.2	1367.0	1367.3	1365.9	1364.5
167.5°	1379.1	1377.1	1375.0	1373.0	1375.0	1377.1	1379.1	1381.3	1381.4	1379.7	1378.1
170°	1386.6	1384.6	1382.5	1380.4	1382.5	1384.6	1386.6	1388.7	1388.8	1387.0	1385.1
172.5°	1391.6	1389.6	1387.4	1385.4	1387.4	1389.6	1391.6	1393.7	1393.8	1392.2	1390.5
175°	1398.0	1396.0	1393.8	1391.8	1393.8	1396.0	1398.0	1400.1	1400.2	1398.4	1396.5
177.5°	1400.0	1398.5	1397.0	1395.5	1397.0	1398.5	1400.0	1401.4	1401.5	1400.3	1398.9
180°	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0



TEST NUMBER: P333514-940

CATALOG NUMBER: S125RDIP-S375D1205U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9
2.5°	481.2	483.0	483.9	486.2	489.5	491.2	493.5	495.2	497.5	500.2	502.6
5°	450.0	455.0	458.3	463.4	468.1	472.9	478.8	483.1	488.9	495.5	500.7
7.5°	421.1	427.2	432.7	439.5	447.4	453.4	461.3	469.2	478.2	487.6	496.4
10°	402.6	408.8	415.6	424.0	431.9	440.1	449.4	458.7	470.0	480.5	492.4
12.5°	384.3	391.2	398.8	408.2	417.7	428.2	437.7	448.1	460.3	473.9	486.7
15°	361.6	368.2	376.5	384.5	395.4	407.0	419.5	433.3	446.9	462.2	478.0
17.5°	337.2	344.5	353.6	362.9	374.3	387.9	400.2	415.4	430.6	448.4	467.1
20°	321.5	328.9	339.6	349.8	360.3	373.5	388.2	403.7	419.9	438.6	459.5
22.5°	308.9	314.1	324.8	335.2	347.5	361.1	375.3	391.5	409.2	428.6	450.4
25°	290.3	296.5	304.2	315.0	327.8	342.1	356.4	373.5	392.9	412.7	436.0
27.5°	273.8	278.8	286.4	295.0	307.7	322.4	337.8	355.6	375.5	395.7	420.1
30°	262.1	267.7	274.8	283.9	294.0	310.1	325.7	343.3	363.5	384.2	409.4
32.5°	251.9	257.6	263.9	272.4	283.3	297.6	313.7	330.9	351.4	372.9	397.3
35°	237.6	241.5	247.3	255.7	266.4	277.9	294.4	312.5	332.5	354.8	379.3
37.5°	221.1	226.2	231.9	239.3	248.7	261.2	276.5	294.9	313.4	334.7	357.0
40°	211.6	216.3	222.7	228.1	238.0	249.3	263.3	282.5	301.0	321.0	341.4
42.5°	201.9	206.4	211.9	218.6	227.4	238.4	251.5	269.3	289.2	308.0	325.1
45°	186.6	191.5	196.5	202.8	211.0	221.7	234.7	250.9	268.2	285.6	298.5
47.5°	172.1	176.6	181.5	187.8	195.4	205.7	217.3	231.8	248.5	263.2	272.5
50°	161.8	165.9	171.2	177.4	184.9	194.5	205.6	219.8	233.9	247.3	255.7
52.5°	151.5	156.1	161.5	166.8	174.0	183.6	193.9	206.2	219.5	230.4	237.4
55°	136.2	140.5	145.4	151.1	158.0	166.3	177.2	186.9	197.4	206.7	210.8
57.5°	121.4	125.2	129.8	135.6	142.0	149.6	158.3	167.6	175.0	181.6	186.2
60°	111.6	114.9	119.3	124.2	131.1	138.0	145.9	154.5	160.3	165.9	170.2
62.5°	101.7	105.0	109.1	113.5	119.5	126.0	133.5	140.5	146.2	149.9	154.9
65°	86.9	90.1	93.5	98.3	103.0	108.3	115.2	120.3	124.2	128.4	131.4
67.5°	73.1	75.7	79.0	82.8	86.8	91.9	97.2	101.5	104.2	106.6	110.3
70°	64.1	66.2	68.8	71.7	76.1	81.1	85.3	88.6	90.4	92.9	97.5
72.5°	54.8	57.2	59.7	62.6	66.2	70.4	74.1	77.4	78.6	80.5	83.5
75°	43.2	44.5	46.5	48.6	51.1	54.8	58.3	59.1	60.2	61.8	63.8
77.5°	32.7	33.8	34.7	36.0	38.0	40.9	42.8	44.1	44.3	44.9	46.9
80°	25.9	26.6	27.4	28.4	29.2	31.7	32.7	34.0	34.4	35.0	36.0
82.5°	19.1	19.6	20.2	21.0	22.3	23.4	24.3	25.6	25.7	26.1	26.3
85°	11.1	11.3	10.9	11.3	11.5	11.9	13.0	14.0	13.8	13.6	14.2
87.5°	7.5	7.3	6.8	7.0	6.3	6.2	5.8	5.6	5.5	5.5	5.4
90°	17.7	16.6	15.0	13.4	11.8	10.2	8.4	6.6	4.7	2.9	1.1
92.5°	17.7	16.6	15.2	13.7	12.3	10.9	10.8	12.1	13.4	14.7	16.0
95°	17.7	16.6	25.3	34.1	42.8	51.6	56.3	57.0	57.7	58.4	59.0
97.5°	44.5	51.0	68.3	85.6	102.9	120.3	128.3	127.1	125.8	124.6	123.3
100°	146.0	180.3	179.4	178.5	177.5	176.6	175.8	175.1	174.4	173.8	173.1
102.5°	223.6	230.1	229.5	229.0	228.4	227.8	227.1	226.2	225.4	224.5	223.6
105°	308.8	308.8	308.8	308.8	308.8	308.8	308.4	307.5	306.5	305.6	304.7
107.5°	390.9	390.9	390.5	389.9	389.5	389.1	388.9	388.9	388.9	388.9	388.9
110°	445.0	445.6	445.1	444.7	444.3	443.8	443.5	443.5	443.5	443.5	443.5



TEST NUMBER: P333514-940

CATALOG NUMBER: S125RDIP-S375D1205U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	497.8	498.6	498.4	498.1	497.8	497.6	497.1	496.6	496.1	495.5	495.0
115°	577.4	578.3	578.0	577.8	577.6	577.4	576.7	575.5	574.4	573.2	572.0
117.5°	654.4	655.6	654.7	653.8	653.0	652.1	651.7	651.8	651.8	651.8	651.8
120°	703.2	703.6	702.9	702.3	701.6	700.9	700.7	700.9	701.2	701.3	701.6
122.5°	750.5	750.9	750.6	750.3	749.9	749.7	749.0	748.1	747.3	746.5	745.6
125°	819.8	820.7	820.7	820.7	820.7	820.7	819.9	818.3	816.7	815.1	813.5
127.5°	882.4	883.0	883.1	883.2	883.3	883.5	883.0	881.8	880.7	879.6	878.4
130°	923.7	924.4	924.2	924.0	923.7	923.5	922.8	921.7	920.5	919.4	918.2
132.5°	961.6	961.7	962.2	962.7	963.2	963.8	963.3	962.0	960.6	959.3	958.0
135°	1018.2	1018.7	1019.1	1019.7	1020.1	1020.6	1020.1	1018.7	1017.4	1015.9	1014.6
137.5°	1070.2	1070.1	1070.5	1070.9	1071.4	1071.7	1071.4	1070.1	1069.0	1067.8	1066.6
140°	1102.1	1101.6	1101.9	1102.1	1102.3	1102.5	1102.4	1102.0	1101.5	1101.1	1100.5
142.5°	1134.1	1134.0	1133.6	1133.3	1133.0	1132.7	1132.4	1132.1	1131.8	1131.5	1131.2
145°	1178.6	1178.3	1178.3	1178.3	1178.3	1178.3	1178.0	1177.6	1177.1	1176.7	1176.3
147.5°	1216.7	1216.5	1216.2	1215.8	1215.6	1215.3	1215.2	1215.3	1215.4	1215.5	1215.6
150°	1240.9	1240.5	1240.0	1239.6	1239.1	1238.7	1238.7	1239.1	1239.6	1240.0	1240.5
152.5°	1262.5	1262.0	1261.6	1261.1	1260.7	1260.2	1260.4	1261.5	1262.5	1263.6	1264.5
155°	1292.0	1291.3	1290.8	1290.3	1289.9	1289.4	1289.9	1291.3	1292.6	1294.1	1295.4
157.5°	1316.4	1315.7	1315.7	1315.6	1315.6	1315.5	1315.9	1316.8	1317.6	1318.4	1319.3
160°	1331.6	1330.6	1330.4	1330.2	1330.0	1329.7	1330.3	1331.7	1333.1	1334.4	1335.9
162.5°	1345.2	1343.9	1343.7	1343.5	1343.2	1343.0	1343.5	1345.0	1346.3	1347.7	1349.1
165°	1363.2	1361.7	1361.5	1361.3	1361.0	1360.8	1361.4	1362.8	1364.1	1365.6	1366.9
167.5°	1376.4	1374.8	1374.6	1374.3	1374.1	1373.9	1374.5	1375.9	1377.3	1378.8	1380.2
170°	1383.3	1381.4	1381.2	1381.0	1380.7	1380.5	1381.2	1382.8	1384.4	1386.1	1387.7
172.5°	1388.9	1387.2	1386.8	1386.4	1386.0	1385.5	1386.2	1387.8	1389.4	1391.0	1392.6
175°	1394.6	1392.9	1392.6	1392.4	1392.1	1391.9	1392.5	1393.8	1395.3	1396.6	1398.0
177.5°	1397.7	1396.3	1396.2	1396.0	1395.8	1395.6	1396.1	1397.2	1398.3	1399.4	1400.5
180°	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0



TEST NUMBER: P333514-940

CATALOG NUMBER: S125RDIP-S375D1205U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9
2.5°	504.4	505.9	508.0	510.5	512.5	514.6	515.8	515.8	516.7	518.9	521.7
5°	505.9	511.2	516.3	522.9	528.1	534.0	538.6	543.0	546.8	551.8	557.0
7.5°	505.4	514.3	523.6	534.0	545.5	554.6	563.9	571.2	578.5	588.0	595.4
10°	503.8	515.3	527.9	541.1	555.5	568.0	579.4	589.7	599.6	609.9	619.2
12.5°	500.8	515.5	530.8	546.7	564.9	579.3	593.9	604.8	616.4	627.7	639.1
15°	496.3	513.6	532.2	554.3	576.5	592.5	607.0	621.3	632.0	644.7	655.7
17.5°	487.1	509.4	532.8	556.9	578.3	596.9	612.1	625.6	637.0	651.0	665.9
20°	481.7	505.9	530.1	555.9	576.3	595.5	610.1	624.1	638.3	656.7	674.8
22.5°	474.1	499.9	525.7	550.1	571.7	590.2	605.3	622.4	641.1	661.9	683.9
25°	462.2	488.7	514.2	537.5	558.6	577.6	598.2	621.3	643.9	671.3	702.8
27.5°	446.9	472.6	495.3	520.0	540.8	565.0	590.7	615.7	648.4	686.1	725.4
30°	435.6	459.9	481.5	504.8	528.5	555.1	583.9	613.4	652.4	696.6	743.4
32.5°	422.4	444.4	465.8	488.3	515.7	544.8	575.5	611.5	658.1	708.5	756.9
35°	399.5	419.3	440.1	465.0	494.1	525.8	565.0	608.9	665.1	719.3	762.8
37.5°	375.5	391.2	412.1	438.4	470.0	506.7	551.2	604.5	662.2	710.9	729.3
40°	357.0	371.7	393.8	421.3	452.7	492.8	542.7	597.5	655.7	689.4	688.0
42.5°	338.8	353.6	374.8	402.6	435.2	480.2	531.5	588.4	637.5	650.3	623.6
45°	310.7	324.5	345.4	373.4	408.4	455.6	509.5	564.2	595.5	574.6	521.5
47.5°	282.1	295.5	314.9	342.2	380.5	429.9	481.0	525.8	530.1	485.4	421.7
50°	263.3	275.9	294.3	323.5	360.6	408.8	458.1	493.3	482.3	427.8	362.0
52.5°	245.0	257.1	274.3	301.9	339.8	387.0	431.0	458.7	433.4	375.3	316.2
55°	218.0	229.5	246.8	272.2	306.6	349.8	388.4	398.5	361.4	302.9	255.1
57.5°	192.3	200.8	217.8	240.3	273.5	311.7	339.2	337.4	296.5	243.8	209.5
60°	175.3	183.0	199.2	219.8	251.4	285.6	305.0	296.7	255.3	211.8	178.9
62.5°	159.5	166.7	180.3	199.2	226.3	256.1	270.2	258.8	219.7	181.5	155.2
65°	135.5	140.7	151.7	169.2	190.4	211.0	223.6	206.9	172.3	143.4	123.6
67.5°	113.2	117.6	127.3	139.9	154.5	168.8	173.9	158.3	131.3	111.9	97.9
70°	98.7	102.8	109.4	121.2	130.8	140.9	143.4	129.4	106.9	92.1	83.5
72.5°	84.9	88.6	94.4	102.7	109.4	115.2	116.4	103.3	86.1	76.0	69.3
75°	64.7	68.0	71.7	74.8	79.1	80.2	79.7	69.6	60.4	53.6	49.8
77.5°	47.5	49.0	51.2	52.4	52.6	52.5	50.5	44.1	39.2	36.5	35.0
80°	36.6	37.7	38.3	38.7	39.0	36.9	34.6	30.7	29.1	27.4	25.6
82.5°	26.7	27.3	27.9	28.0	26.9	25.1	23.1	21.1	20.0	19.2	18.5
85°	14.4	14.6	14.4	13.4	11.9	11.3	10.9	10.5	10.3	10.1	10.1
87.5°	5.7	5.5	5.1	5.6	6.0	6.2	6.4	6.6	6.8	7.0	7.2
90°	2.9	4.7	6.6	8.4	10.2	11.8	13.4	15.0	16.6	17.7	18.9
92.5°	14.7	13.4	12.1	10.8	10.9	12.3	13.7	15.2	16.6	17.7	18.9
95°	58.4	57.7	57.0	56.3	51.6	42.8	34.1	25.3	16.6	17.7	18.9
97.5°	124.6	125.8	127.1	128.3	120.3	102.9	85.6	68.3	51.0	44.5	38.0
100°	173.8	174.4	175.1	175.8	176.6	177.5	178.5	179.4	180.3	146.0	111.7
102.5°	224.5	225.4	226.2	227.1	227.8	228.4	229.0	229.5	230.1	223.6	217.0
105°	305.6	306.5	307.5	308.4	308.8	308.8	308.8	308.8	308.8	308.8	308.8
107.5°	388.9	388.9	388.9	388.9	389.1	389.5	389.9	390.5	390.9	390.9	391.0
110°	443.5	443.5	443.5	443.5	443.8	444.3	444.7	445.1	445.6	445.0	444.3



TEST NUMBER: P333514-940

CATALOG NUMBER: S125RDIP-S375D1205U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	495.5	496.1	496.6	497.1	497.6	497.8	498.1	498.4	498.6	497.8	497.0
115°	573.2	574.4	575.5	576.7	577.4	577.6	577.8	578.0	578.3	577.4	576.4
117.5°	651.8	651.8	651.8	651.7	652.1	653.0	653.8	654.7	655.6	654.4	653.2
120°	701.3	701.2	700.9	700.7	700.9	701.6	702.3	702.9	703.6	703.2	702.8
122.5°	746.5	747.3	748.1	749.0	749.7	749.9	750.3	750.6	750.9	750.5	750.0
125°	815.1	816.7	818.3	819.9	820.7	820.7	820.7	820.7	820.7	819.8	818.9
127.5°	879.6	880.7	881.8	883.0	883.5	883.3	883.2	883.1	883.0	882.4	881.9
130°	919.4	920.5	921.7	922.8	923.5	923.7	924.0	924.2	924.4	923.7	923.0
132.5°	959.3	960.6	962.0	963.3	963.8	963.2	962.7	962.2	961.7	961.6	961.4
135°	1015.9	1017.4	1018.7	1020.1	1020.6	1020.1	1019.7	1019.1	1018.7	1018.2	1017.8
137.5°	1067.8	1069.0	1070.1	1071.4	1071.7	1071.4	1070.9	1070.5	1070.1	1070.2	1070.3
140°	1101.1	1101.5	1102.0	1102.4	1102.5	1102.3	1102.1	1101.9	1101.6	1102.1	1102.5
142.5°	1131.5	1131.8	1132.1	1132.4	1132.7	1133.0	1133.3	1133.6	1134.0	1134.1	1134.2
145°	1176.7	1177.1	1177.6	1178.0	1178.3	1178.3	1178.3	1178.3	1178.3	1178.6	1178.8
147.5°	1215.5	1215.4	1215.3	1215.2	1215.3	1215.6	1215.8	1216.2	1216.5	1216.7	1217.0
150°	1240.0	1239.6	1239.1	1238.7	1238.7	1239.1	1239.6	1240.0	1240.5	1240.9	1241.4
152.5°	1263.6	1262.5	1261.5	1260.4	1260.2	1260.7	1261.1	1261.6	1262.0	1262.5	1262.9
155°	1294.1	1292.6	1291.3	1289.9	1289.4	1289.9	1290.3	1290.8	1291.3	1292.0	1292.6
157.5°	1318.4	1317.6	1316.8	1315.9	1315.5	1315.6	1315.6	1315.7	1315.7	1316.4	1317.2
160°	1334.4	1333.1	1331.7	1330.3	1329.7	1330.0	1330.2	1330.4	1330.6	1331.6	1332.5
162.5°	1347.7	1346.3	1345.0	1343.5	1343.0	1343.2	1343.5	1343.7	1343.9	1345.2	1346.5
165°	1365.6	1364.1	1362.8	1361.4	1360.8	1361.0	1361.3	1361.5	1361.7	1363.2	1364.5
167.5°	1378.8	1377.3	1375.9	1374.5	1373.9	1374.1	1374.3	1374.6	1374.8	1376.4	1378.1
170°	1386.1	1384.4	1382.8	1381.2	1380.5	1380.7	1381.0	1381.2	1381.4	1383.3	1385.1
172.5°	1391.0	1389.4	1387.8	1386.2	1385.5	1386.0	1386.4	1386.8	1387.2	1388.9	1390.5
175°	1396.6	1395.3	1393.8	1392.5	1391.9	1392.1	1392.4	1392.6	1392.9	1394.6	1396.5
177.5°	1399.4	1398.3	1397.2	1396.1	1395.6	1395.8	1396.0	1396.2	1396.3	1397.7	1398.9
180°	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0



TEST NUMBER: P333514-940

CATALOG NUMBER: S125RDIP-S375D1205U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	501.9	501.9	501.9	501.9	501.9	501.9	501.9
2.5°	523.9	523.9	526.6	526.5	528.3	527.6	528.0
5°	563.1	566.6	569.7	571.8	574.9	575.7	575.2
7.5°	603.9	611.6	615.4	620.6	621.5	624.3	624.0
10°	629.0	636.7	642.5	646.9	649.3	652.1	652.4
12.5°	648.8	655.3	660.4	664.6	667.4	668.2	668.8
15°	664.3	671.5	677.4	683.4	687.0	689.6	691.1
17.5°	679.8	691.0	701.5	709.6	714.5	718.6	718.6
20°	691.9	704.6	717.8	727.1	736.6	740.7	741.4
22.5°	704.7	724.2	741.3	755.6	768.1	772.4	774.0
25°	731.5	757.0	783.2	803.3	817.8	826.3	827.5
27.5°	763.8	798.3	825.8	844.5	856.4	862.7	864.1
30°	786.5	818.4	843.1	857.1	862.7	863.5	860.4
32.5°	796.7	820.6	830.5	829.6	818.7	811.5	808.7
35°	784.2	779.3	755.2	726.3	704.3	690.3	686.5
37.5°	713.6	671.0	626.7	583.1	559.9	548.0	527.8
40°	644.1	583.3	537.2	500.5	474.3	453.3	448.4
42.5°	565.6	502.8	456.7	425.3	404.4	390.0	383.7
45°	454.5	400.6	362.4	338.3	322.3	311.7	307.0
47.5°	363.6	321.7	294.0	276.2	263.9	254.8	252.2
50°	313.6	280.2	256.7	241.7	232.4	225.4	222.6
52.5°	272.4	245.4	227.4	215.0	206.3	201.9	199.5
55°	224.8	201.5	188.5	178.6	173.7	170.2	168.5
57.5°	183.9	167.0	157.6	150.7	146.2	143.9	143.1
60°	161.0	147.8	139.1	133.8	130.6	127.8	126.9
62.5°	140.6	130.3	123.6	118.9	115.8	114.6	114.0
65°	113.3	106.6	101.6	98.7	96.2	95.8	95.6
67.5°	90.1	86.1	83.5	80.5	79.6	78.2	77.8
70°	77.0	74.4	71.2	70.3	69.2	67.8	68.0
72.5°	65.4	62.7	60.5	59.2	58.9	58.2	58.8
75°	47.8	47.0	46.2	45.1	44.7	44.7	44.5
77.5°	34.2	33.4	32.5	31.9	31.7	30.9	31.2
80°	24.7	23.7	23.3	23.5	22.8	22.6	22.6
82.5°	18.3	17.9	17.5	17.6	17.4	17.2	17.4
85°	10.1	9.9	9.9	9.7	9.7	9.5	9.5
87.5°	7.7	8.0	7.8	7.8	8.0	8.3	8.6
90°	20.1	21.2	22.1	22.8	23.5	24.2	24.9
92.5°	20.1	21.2	21.9	22.2	22.6	22.9	23.2
95°	20.1	21.2	21.8	21.8	21.8	21.8	21.8
97.5°	31.5	25.0	21.8	21.8	21.8	21.8	21.8
100°	77.4	43.1	25.4	24.5	23.6	22.6	21.8
102.5°	210.6	204.1	193.1	177.4	161.7	146.1	130.4
105°	308.8	308.8	308.7	308.4	308.3	308.0	307.8
107.5°	391.0	391.1	390.7	390.0	389.4	388.7	388.0
110°	443.5	442.8	442.6	442.8	443.1	443.4	443.5



TEST NUMBER: P333514-940

CATALOG NUMBER: S125RDIP-S375D1205U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	496.1	495.2	494.5	494.3	493.9	493.7	493.3
115°	575.5	574.6	573.5	572.0	570.7	569.3	567.9
117.5°	652.0	650.8	649.9	649.3	648.7	648.1	647.5
120°	702.3	701.9	701.1	699.9	698.7	697.6	696.4
122.5°	749.6	749.1	748.1	746.8	745.5	744.2	742.9
125°	818.0	817.1	816.3	815.6	814.9	814.2	813.5
127.5°	881.5	880.9	879.9	878.2	876.4	874.7	873.0
130°	922.3	921.7	920.7	919.5	918.5	917.3	916.1
132.5°	961.3	961.2	960.6	959.4	958.2	957.1	955.9
135°	1017.4	1016.9	1015.9	1014.6	1013.2	1011.8	1010.4
137.5°	1070.4	1070.5	1070.0	1068.7	1067.6	1066.3	1065.1
140°	1103.0	1103.5	1103.0	1101.6	1100.3	1098.9	1097.5
142.5°	1134.3	1134.3	1133.7	1132.3	1131.0	1129.5	1128.2
145°	1179.0	1179.2	1178.7	1177.2	1175.9	1174.5	1173.1
147.5°	1217.3	1217.5	1216.8	1215.2	1213.5	1211.9	1210.2
150°	1241.9	1242.3	1241.6	1239.8	1238.0	1236.1	1234.3
152.5°	1263.5	1263.9	1263.3	1261.6	1260.0	1258.3	1256.7
155°	1293.3	1294.1	1293.4	1291.6	1289.8	1287.9	1286.1
157.5°	1317.9	1318.7	1318.1	1316.3	1314.5	1312.6	1310.7
160°	1333.4	1334.4	1333.9	1332.0	1330.2	1328.4	1326.5
162.5°	1347.8	1349.1	1348.7	1346.7	1344.6	1342.6	1340.6
165°	1365.9	1367.3	1367.0	1365.2	1363.3	1361.5	1359.7
167.5°	1379.7	1381.4	1381.3	1379.1	1377.1	1375.0	1373.0
170°	1387.0	1388.8	1388.7	1386.6	1384.6	1382.5	1380.4
172.5°	1392.2	1393.8	1393.7	1391.6	1389.6	1387.4	1385.4
175°	1398.4	1400.2	1400.1	1398.0	1396.0	1393.8	1391.8
177.5°	1400.3	1401.5	1401.4	1400.0	1398.5	1397.0	1395.5
180°	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0

(END OF REPORT)