

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333494-940

Luminaire Tested: **S125RDIP-S375D365U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333494-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S375D365U940-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 365 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2420.0 lumens
Efficiency: N/A
Efficacy: 119.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 20.3
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333494-940

CATALOG NUMBER: S125RDIP-S375D365U940-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333494-940

CATALOG NUMBER: S125RDIP-S375D365U940-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59	53
1	99	95	91	87	91	88	84	81	75	73	70	63	62	60	53	52	50	45
2	90	83	77	72	83	77	72	67	66	62	59	56	53	51	47	45	43	38
3	82	73	66	60	76	68	62	56	58	54	50	50	46	43	41	39	37	33
4	75	65	57	51	70	60	53	48	52	47	42	44	40	37	37	34	32	28
5	69	58	50	44	64	54	47	41	47	41	37	40	36	32	34	30	28	25
6	64	52	44	38	59	49	41	36	42	36	32	36	32	28	31	27	25	22
7	59	47	39	33	55	44	37	32	38	33	28	33	28	25	28	25	22	19
8	55	43	35	30	51	40	33	28	35	29	25	30	26	22	26	22	20	17
9	51	39	32	26	47	37	30	25	32	27	23	28	23	20	24	20	18	16
10	48	36	29	24	44	34	27	23	30	24	21	26	21	18	22	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3524	3524	3524
5°	3532	3492	3513
10°	3505	3459	3459
15°	3463	3389	3361
20°	3410	3291	3252
25°	3348	3195	3125
30°	3270	3082	2984
35°	3191	2967	2827
40°	3117	2845	2672
45°	3027	2711	2503
50°	2936	2563	2327
55°	2831	2422	2139
60°	2725	2251	1938
65°	2601	2054	1705
70°	2459	1805	1469
75°	2263	1522	1223
80°	1993	1194	1027
85°	1675	978	919



TEST NUMBER: P333494-940

CATALOG NUMBER: S125RDIP-S375D365U940-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	51.3	2.1
10°-20°	143.4	5.9
20°-30°	207.9	8.6
30°-40°	237.0	9.8
40°-50°	231.0	9.5
50°-60°	194.4	8.0
60°-70°	136.3	5.6
70°-80°	70.1	2.9
80°-90°	18.6	0.8
90°-100°	27.1	1.1
100°-110°	80.1	3.3
110°-120°	135.7	5.6
120°-130°	178.6	7.4
130°-140°	200.1	8.3
140°-150°	196.1	8.1
150°-160°	164.7	6.8
160°-170°	109.5	4.5
170°-180°	38.3	1.6
0°-30°	402.6	16.6
0°-40°	639.6	26.4
0°-60°	1065.0	44.0
0°-90°	1289.9	53.3
90°-120°	242.9	10.0
90°-150°	817.6	33.8
90°-180°	1130.0	46.7
0°-180°	2420.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	546	546	546	546	546	
5°	545	543	539	542	542	52
15°	518	515	507	506	503	146
25°	470	463	448	443	438	216
35°	405	394	376	365	359	253
45°	331	319	297	281	274	256
55°	251	238	215	197	190	225
65°	170	156	134	118	112	169
75°	91	78	61	52	49	96
85°	23	16	13	13	12	25
90°	0	3	5	7	8	2
95°	20	21	24	26	27	22
105°	72	74	75	77	78	77
115°	136	137	138	137	137	134
125°	198	200	200	200	200	177
135°	258	260	260	260	259	199
145°	312	314	314	314	314	195
155°	357	357	358	359	357	165
165°	389	388	388	389	388	110
175°	404	403	403	404	402	38
180°	405	405	405	405	405	



TEST NUMBER: P333494-940

CATALOG NUMBER: S125RDIP-S375D365U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	545.6	545.6	545.6	545.6	545.6	545.6	545.6	545.6	545.6	545.6	545.6
2.5°	546.6	546.4	546.2	546.0	545.7	545.3	544.6	543.8	543.1	542.3	543.1
5°	544.8	544.5	544.1	543.7	543.3	542.7	541.6	540.6	539.7	538.6	539.6
7.5°	539.5	539.1	538.8	538.4	538.1	537.3	536.1	534.8	533.7	532.4	533.1
10°	534.5	534.2	534.0	533.7	533.4	532.6	531.4	530.0	528.8	527.5	527.8
12.5°	528.9	528.5	528.2	527.9	527.5	526.5	524.8	523.1	521.3	519.6	519.8
15°	518.0	517.5	516.9	516.4	515.9	514.6	512.6	510.8	508.8	506.9	506.8
17.5°	505.8	504.9	504.1	503.2	502.4	500.8	498.3	495.9	493.5	491.1	490.6
20°	496.1	495.3	494.4	493.5	492.5	490.6	487.7	484.7	481.8	478.8	478.4
22.5°	485.6	484.7	483.8	482.9	482.0	480.0	476.9	473.9	470.7	467.7	466.8
25°	469.8	468.4	467.1	465.7	464.3	461.9	458.5	455.1	451.7	448.4	447.2
27.5°	451.7	450.0	448.4	446.7	445.0	442.4	438.7	435.1	431.5	427.8	426.1
30°	438.5	436.8	435.0	433.3	431.5	428.7	424.9	421.1	417.2	413.3	411.3
32.5°	425.6	423.6	421.6	419.5	417.5	414.6	410.6	406.7	402.8	398.9	396.5
35°	404.7	402.5	400.3	398.1	395.9	392.7	388.6	384.5	380.4	376.3	373.6
37.5°	384.1	381.5	378.8	376.1	373.4	370.0	365.8	361.5	357.3	353.0	349.8
40°	369.7	366.9	364.2	361.4	358.6	355.1	350.7	346.3	341.9	337.5	334.0
42.5°	354.5	351.7	348.8	346.1	343.2	339.6	335.0	330.5	325.9	321.4	318.1
45°	331.4	328.7	326.0	323.3	320.7	316.8	311.8	306.8	301.8	296.8	293.0
47.5°	307.4	304.5	301.8	298.9	296.1	292.2	287.1	282.0	277.0	271.9	268.1
50°	292.2	289.2	286.1	283.1	280.1	276.0	270.7	265.6	260.3	255.1	251.3
52.5°	275.7	272.6	269.5	266.4	263.3	259.3	254.4	249.4	244.5	239.6	235.5
55°	251.4	248.4	245.5	242.6	239.7	235.7	230.5	225.3	220.3	215.1	211.0
57.5°	226.9	223.7	220.5	217.4	214.3	210.3	205.3	200.4	195.5	190.5	186.5
60°	211.0	207.8	204.6	201.3	198.1	194.1	189.1	184.2	179.2	174.3	170.3
62.5°	194.2	191.1	188.1	185.0	181.9	177.9	172.9	167.9	162.8	157.8	154.1
65°	170.2	167.1	164.0	160.9	157.7	153.7	148.9	144.1	139.2	134.4	130.7
67.5°	146.4	143.3	140.2	137.1	133.9	130.0	125.4	120.7	116.1	111.5	108.1
70°	130.2	127.2	124.0	120.9	117.8	114.0	109.3	104.8	100.2	95.6	92.7
72.5°	114.4	111.4	108.3	105.3	102.3	98.5	94.3	90.0	85.7	81.4	78.8
75°	90.7	87.9	85.2	82.4	79.7	76.4	72.5	68.7	64.8	61.0	58.9
77.5°	67.1	64.9	62.7	60.5	58.3	55.6	52.6	49.5	46.5	43.3	41.9
80°	53.6	51.4	49.2	47.0	44.8	42.4	39.9	37.3	34.7	32.1	31.3
82.5°	40.4	38.4	36.5	34.4	32.5	30.6	28.9	27.1	25.3	23.5	23.2
85°	22.6	21.0	19.4	17.7	16.1	15.0	14.5	14.1	13.6	13.2	13.1
87.5°	7.7	7.2	6.9	6.4	6.1	5.9	5.9	5.9	5.9	6.0	6.1
90°	0.4	0.9	1.4	2.0	2.6	3.1	3.6	4.1	4.5	5.1	5.4
92.5°	7.7	8.0	8.4	8.8	9.2	9.7	10.3	10.9	11.5	12.1	12.6
95°	20.5	20.6	20.8	20.9	21.0	21.5	22.2	22.8	23.5	24.3	24.8
97.5°	34.1	34.1	34.2	34.2	34.2	34.8	35.8	36.7	37.6	38.6	39.1
100°	44.1	44.1	44.1	44.1	44.1	44.6	45.5	46.4	47.3	48.2	48.9
102.5°	54.9	55.3	55.6	55.8	56.1	56.4	56.9	57.3	57.9	58.3	59.0
105°	71.9	72.2	72.6	72.9	73.3	73.7	74.1	74.5	74.9	75.3	75.7
107.5°	90.5	90.9	91.2	91.6	91.9	92.3	92.6	92.9	93.2	93.5	93.7
110°	103.3	103.7	104.1	104.4	104.8	105.0	105.2	105.5	105.7	105.9	106.1



TEST NUMBER: P333494-940

CATALOG NUMBER: S125RDIP-S375D365U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	116.5	116.6	116.8	117.0	117.2	117.4	117.7	118.0	118.2	118.5	118.6
115°	135.8	136.1	136.4	136.7	137.0	137.1	137.3	137.4	137.6	137.8	137.7
117.5°	155.2	155.3	155.5	155.6	155.8	155.9	156.0	156.1	156.2	156.4	156.4
120°	167.4	167.7	168.1	168.4	168.7	169.0	169.1	169.1	169.2	169.2	169.2
122.5°	180.5	180.6	180.7	180.8	180.9	181.1	181.3	181.5	181.6	181.8	181.8
125°	198.2	198.7	199.1	199.5	199.9	200.2	200.3	200.3	200.4	200.5	200.3
127.5°	217.1	217.4	217.7	217.8	218.1	218.3	218.4	218.5	218.6	218.6	218.6
130°	228.5	228.8	229.2	229.5	229.9	230.2	230.2	230.4	230.6	230.7	230.6
132.5°	239.9	240.4	241.0	241.6	242.1	242.5	242.4	242.4	242.4	242.3	242.2
135°	257.8	258.2	258.7	259.0	259.5	259.8	259.8	259.8	259.9	260.0	260.0
137.5°	274.7	275.1	275.5	275.9	276.3	276.6	276.8	276.9	277.1	277.2	277.3
140°	285.5	285.9	286.2	286.6	287.0	287.2	287.4	287.7	287.8	288.0	288.2
142.5°	296.4	296.7	296.9	297.3	297.6	297.8	298.1	298.4	298.6	298.9	299.0
145°	312.4	312.6	312.9	313.2	313.4	313.7	313.9	314.1	314.3	314.5	314.5
147.5°	327.1	327.3	327.3	327.5	327.7	327.9	328.1	328.2	328.3	328.5	328.7
150°	336.9	336.9	336.8	336.7	336.6	336.7	337.0	337.3	337.6	337.9	337.9
152.5°	345.0	345.1	345.2	345.3	345.4	345.4	345.6	345.7	345.8	345.9	346.1
155°	357.4	357.4	357.4	357.4	357.4	357.4	357.5	357.6	357.7	357.8	358.0
157.5°	368.5	368.4	368.2	368.0	367.9	367.8	367.9	368.0	368.0	368.1	368.4
160°	375.1	374.9	374.6	374.4	374.3	374.2	374.3	374.3	374.3	374.4	374.7
162.5°	380.8	380.7	380.6	380.4	380.2	380.1	380.1	380.2	380.2	380.2	380.6
165°	388.6	388.4	388.3	388.2	388.1	388.0	388.1	388.2	388.3	388.3	388.6
167.5°	395.1	394.8	394.6	394.3	394.0	393.9	393.9	393.9	393.9	393.9	394.3
170°	398.7	398.4	398.1	397.9	397.5	397.4	397.4	397.4	397.4	397.4	397.9
172.5°	401.2	400.9	400.6	400.4	400.1	399.9	399.9	399.9	399.9	399.9	400.4
175°	404.0	403.8	403.5	403.2	403.0	402.8	402.8	402.8	402.8	402.8	403.2
177.5°	405.5	405.3	405.0	404.8	404.6	404.5	404.4	404.4	404.3	404.2	404.6
180°	405.0	405.0	405.0	405.0	405.0	405.0	405.0	405.0	405.0	405.0	405.0



TEST NUMBER: P333494-940

CATALOG NUMBER: S125RDIP-S375D365U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	545.6	545.6	545.6	545.6	545.6	545.6	545.6	545.6
2.5°	543.8	544.6	545.3	545.6	545.5	545.5	545.4	545.3
5°	540.5	541.4	542.2	542.7	542.5	542.2	542.1	541.9
7.5°	533.7	534.4	535.0	535.2	535.0	534.8	534.7	534.4
10°	528.1	528.3	528.6	528.6	528.3	528.1	527.8	527.5
12.5°	520.0	520.2	520.4	520.3	519.9	519.4	519.1	518.6
15°	506.7	506.6	506.5	506.0	505.2	504.4	503.6	502.7
17.5°	490.2	489.7	489.3	488.7	488.0	487.3	486.6	486.0
20°	478.0	477.5	477.1	476.4	475.5	474.7	473.9	473.1
22.5°	465.8	464.9	464.0	463.2	462.6	461.9	461.3	460.6
25°	446.0	444.8	443.6	442.6	441.5	440.5	439.5	438.5
27.5°	424.5	422.8	421.2	419.9	418.9	417.9	417.0	416.0
30°	409.1	407.1	404.9	403.5	402.6	401.8	401.0	400.2
32.5°	394.2	391.9	389.5	387.9	386.8	385.8	384.7	383.7
35°	371.0	368.3	365.6	363.6	362.4	361.1	359.8	358.6
37.5°	346.6	343.5	340.3	338.0	336.8	335.6	334.3	333.1
40°	330.6	327.1	323.6	321.3	320.2	319.1	318.0	316.9
42.5°	314.7	311.4	308.0	305.6	304.0	302.3	300.7	299.1
45°	289.4	285.7	282.0	279.6	278.2	276.8	275.4	274.0
47.5°	264.4	260.6	256.8	254.1	252.6	251.1	249.6	248.1
50°	247.4	243.5	239.7	237.1	235.8	234.3	233.0	231.6
52.5°	231.3	227.2	223.0	220.3	218.9	217.6	216.2	214.8
55°	206.9	202.8	198.7	195.8	194.4	192.9	191.5	190.0
57.5°	182.4	178.4	174.3	171.7	170.4	169.1	167.8	166.5
60°	166.3	162.2	158.2	155.5	154.1	152.8	151.4	150.0
62.5°	150.3	146.6	142.9	140.4	138.9	137.6	136.3	134.8
65°	127.0	123.3	119.7	117.2	115.8	114.4	113.1	111.6
67.5°	104.7	101.4	98.0	95.8	94.7	93.6	92.5	91.4
70°	90.0	87.1	84.3	82.3	81.1	80.1	79.0	77.8
72.5°	76.2	73.6	71.0	69.3	68.6	67.9	67.1	66.3
75°	57.0	54.9	53.0	51.6	51.0	50.3	49.7	49.0
77.5°	40.6	39.1	37.7	36.7	36.3	35.8	35.3	34.9
80°	30.5	29.7	28.9	28.4	28.2	28.0	27.8	27.6
82.5°	22.8	22.4	22.0	21.8	21.7	21.6	21.5	21.3
85°	13.0	12.9	12.8	12.8	12.7	12.6	12.5	12.4
87.5°	6.1	6.2	6.2	6.2	6.2	6.2	6.2	6.2
90°	5.7	6.1	6.4	6.7	7.0	7.1	7.3	7.6
92.5°	13.0	13.5	13.9	14.3	14.4	14.5	14.7	14.9
95°	25.2	25.8	26.2	26.6	26.7	26.8	26.9	27.1
97.5°	39.6	40.0	40.5	40.8	40.8	40.9	41.0	41.1
100°	49.5	50.1	50.7	51.1	51.3	51.5	51.5	51.7
102.5°	59.7	60.4	61.1	61.5	61.7	61.9	62.1	62.2
105°	76.2	76.6	77.0	77.3	77.5	77.8	77.9	78.2
107.5°	94.0	94.2	94.3	94.5	94.4	94.4	94.4	94.4
110°	106.3	106.6	106.7	106.8	106.7	106.6	106.6	106.6



TEST NUMBER: P333494-940

CATALOG NUMBER: S125RDIP-S375D365U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	118.7	118.8	118.9	118.9	118.8	118.6	118.5	118.4
115°	137.6	137.5	137.4	137.4	137.3	137.2	137.1	137.1
117.5°	156.5	156.6	156.6	156.5	156.2	156.0	155.7	155.3
120°	169.2	169.2	169.2	169.1	168.8	168.5	168.3	168.0
122.5°	181.7	181.6	181.6	181.5	181.3	181.0	180.8	180.6
125°	200.2	200.0	199.9	199.7	199.7	199.7	199.6	199.5
127.5°	218.5	218.4	218.3	218.2	218.1	217.9	217.8	217.7
130°	230.6	230.5	230.4	230.3	230.2	230.1	229.9	229.8
132.5°	242.2	242.1	242.0	241.9	241.7	241.5	241.3	241.1
135°	260.0	260.0	260.0	259.8	259.6	259.3	259.0	258.8
137.5°	277.4	277.5	277.6	277.4	277.1	276.7	276.3	276.0
140°	288.4	288.5	288.6	288.6	288.2	287.8	287.5	287.1
142.5°	299.1	299.2	299.3	299.1	298.7	298.4	298.1	297.7
145°	314.5	314.5	314.5	314.4	314.2	314.0	313.8	313.6
147.5°	328.9	329.0	329.2	329.0	328.6	328.1	327.6	327.2
150°	337.9	337.9	337.9	337.8	337.7	337.5	337.3	337.2
152.5°	346.3	346.4	346.6	346.5	346.3	346.1	345.8	345.5
155°	358.3	358.6	358.8	358.8	358.5	358.1	357.8	357.4
157.5°	368.6	369.0	369.3	369.2	368.7	368.2	367.7	367.3
160°	375.0	375.2	375.5	375.5	375.1	374.8	374.4	374.1
162.5°	380.8	381.2	381.6	381.6	381.1	380.7	380.3	379.9
165°	388.9	389.1	389.4	389.3	388.9	388.5	388.1	387.6
167.5°	394.8	395.1	395.6	395.6	395.1	394.7	394.2	393.9
170°	398.2	398.7	399.1	399.0	398.6	398.1	397.6	397.1
172.5°	400.8	401.2	401.6	401.6	401.2	400.7	400.3	399.8
175°	403.6	404.0	404.5	404.4	403.9	403.4	403.0	402.4
177.5°	404.9	405.3	405.6	405.6	405.2	404.7	404.4	403.9
180°	405.0	405.0	405.0	405.0	405.0	405.0	405.0	405.0

(END OF REPORT)