

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331381-930

Luminaire Tested: **SA2XXDIP-C865D330U930-4F0-1E-UDD-F**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331381-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C865D330U930-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 330 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3931.0 lumens
Efficiency: N/A
Efficacy: 90.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 43.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331381-930
CATALOG NUMBER: SA2XXDIP-C865D330U930-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331381-930

CATALOG NUMBER: SA2XXDIP-C865D330U930-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									20
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR	0	113	113	113	113	107	107	107	107	96	96	96	86	86	86	77	77	77	77	73	73	73	73	61	61	61	61	61	61	61																
	1	103	98	94	91	97	94	90	87	84	82	79	76	74	72	68	67	65	65	61	61	61	61	51	51	51	51	51	51	51																
	2	94	86	80	74	89	82	76	71	74	69	66	67	63	60	60	57	55	55	51	51	51	51	44	44	44	44	44	44	44																
	3	86	76	68	62	81	72	65	60	65	60	55	59	55	51	53	50	47	47	44	44	44	44	37	37	37	37	37	37	37																
	4	78	67	59	53	74	64	57	51	58	52	47	53	48	44	48	44	40	43	39	35	35	32	32	32	32	32	32	32	32																
	5	72	60	51	45	68	57	50	44	52	46	41	47	42	38	43	39	35	39	35	31	31	29	29	29	29	29	29	29	29																
	6	67	54	45	39	63	52	44	38	47	41	36	43	38	33	39	35	31	36	31	28	28	25	25	25	25	25	25	25	25																
	7	62	49	41	35	58	47	39	34	43	36	32	39	34	30	36	31	28	33	28	25	25	23	23	23	23	23	23	23	23																
	8	57	44	36	31	54	43	35	30	39	33	28	36	30	27	33	28	25	33	28	25	25	23	23	23	23	23	23	23	23																
	9	53	41	33	28	51	39	32	27	36	30	25	33	28	24	30	26	22	30	26	22	22	20	20	20	20	20	20	20	20																
	10	50	38	30	25	48	36	29	24	33	27	23	31	25	22	28	24	20	28	24	20	20	19	19	19	19	19	19	19	19																

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	18166	18166	18166
5°	18235	17973	18078
10°	18126	17790	17879
15°	17904	17560	17541
20°	17584	17213	17194
25°	17268	16787	16787
30°	16861	16397	16257
35°	16484	15928	15693
40°	16008	15460	15163
45°	15536	14995	14625
50°	15028	14511	13996
55°	14494	13948	13430
60°	13905	13275	12788
65°	13268	12607	12027
70°	12463	11797	11235
75°	11335	10861	10593
80°	10060	9754	9252
85°	8225	7818	7003



TEST NUMBER: P331381-930

CATALOG NUMBER: SA2XXDIP-C865D330U930-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	105.8	2.7
10°-20°	297.7	7.6
20°-30°	437.6	11.1
30°-40°	508.3	12.9
40°-50°	507.7	12.9
50°-60°	442.8	11.3
60°-70°	327.4	8.3
70°-80°	185.4	4.7
80°-90°	50.8	1.3
90°-100°	12.1	0.3
100°-110°	44.6	1.1
110°-120°	119.1	3.0
120°-130°	196.6	5.0
130°-140°	209.1	5.3
140°-150°	194.4	4.9
150°-160°	156.3	4.0
160°-170°	100.7	2.6
170°-180°	34.7	0.9
0°-30°	841.1	21.4
0°-40°	1349.3	34.3
0°-60°	2299.8	58.5
0°-90°	2863.4	72.8
90°-120°	175.8	4.5
90°-150°	776.0	19.7
90°-180°	1068.0	27.2
0°-180°	3931.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1125	1125	1125	1125	1125	
5°	1125	1120	1109	1117	1115	107
15°	1071	1064	1050	1054	1049	301
25°	969	960	942	944	942	446
35°	836	825	808	802	796	522
45°	680	672	657	645	640	525
55°	515	508	496	483	477	460
65°	347	341	330	320	315	343
75°	182	179	174	168	170	194
85°	44	43	42	39	38	51
90°	0	3	5	7	7	3
95°	17	9	10	12	11	21
105°	80	84	16	19	20	86
115°	152	156	163	46	22	149
125°	214	218	223	225	225	191
135°	265	269	272	274	274	205
145°	308	308	312	314	312	192
155°	339	337	340	341	339	156
165°	357	356	356	358	356	101
175°	365	363	364	365	363	35
180°	364	364	364	364	364	



TEST NUMBER: P331381-930

CATALOG NUMBER: SA2XXDIP-C865D330U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1
2.5°	1130.3	1129.4	1128.4	1127.5	1126.5	1124.9	1122.8	1120.7	1118.6	1116.5	1118.4
5°	1125.1	1124.1	1123.2	1122.3	1121.3	1119.5	1116.9	1114.2	1111.6	1108.9	1110.8
7.5°	1115.2	1113.7	1112.2	1110.7	1109.2	1107.1	1104.4	1101.7	1099.0	1096.3	1098.3
10°	1105.6	1104.0	1102.3	1100.6	1098.9	1096.7	1093.7	1090.9	1088.0	1085.1	1087.0
12.5°	1092.7	1091.2	1089.7	1088.2	1086.7	1084.5	1081.7	1078.7	1075.9	1073.0	1074.3
15°	1071.1	1069.6	1068.1	1066.7	1065.3	1063.0	1059.9	1056.7	1053.6	1050.5	1051.4
17.5°	1043.3	1041.9	1040.5	1039.0	1037.5	1035.3	1032.1	1028.9	1025.7	1022.5	1023.7
20°	1023.4	1022.0	1020.6	1019.1	1017.7	1015.3	1011.9	1008.5	1005.2	1001.8	1002.5
22.5°	1003.6	1001.5	999.5	997.4	995.5	992.9	989.7	986.5	983.3	980.2	980.3
25°	969.3	967.4	965.5	963.6	961.6	958.6	954.6	950.5	946.4	942.3	942.8
27.5°	930.4	928.7	926.9	925.2	923.5	921.0	917.8	914.5	911.3	908.1	907.4
30°	904.4	902.5	900.6	898.7	896.7	894.0	890.4	886.8	883.1	879.5	878.8
32.5°	876.8	875.2	873.7	872.1	870.6	867.9	864.1	860.3	856.6	852.7	851.4
35°	836.3	833.9	831.4	829.1	826.6	823.5	819.7	815.9	812.0	808.1	806.7
37.5°	790.6	788.5	786.4	784.2	782.2	779.2	775.3	771.5	767.6	763.8	762.0
40°	759.5	757.6	755.6	753.7	751.8	748.9	745.0	741.2	737.4	733.5	731.3
42.5°	729.2	727.2	725.3	723.4	721.5	718.6	714.8	710.9	707.0	703.2	700.8
45°	680.4	678.8	677.1	675.5	673.8	671.1	667.5	663.9	660.3	656.7	654.0
47.5°	632.0	630.5	628.8	627.3	625.7	623.0	619.2	615.5	611.7	608.0	605.2
50°	598.3	597.0	595.9	594.7	593.5	591.2	587.8	584.4	581.1	577.7	574.4
52.5°	565.4	563.8	562.2	560.6	559.1	556.7	553.5	550.3	547.1	544.0	541.2
55°	514.9	513.6	512.1	510.6	509.2	507.0	504.2	501.2	498.4	495.5	492.6
57.5°	464.3	463.2	462.0	460.9	459.7	457.5	454.4	451.2	448.0	444.8	442.1
60°	430.6	429.6	428.7	427.7	426.7	424.6	421.2	417.8	414.5	411.1	408.5
62.5°	397.7	396.2	394.6	393.1	391.5	389.5	386.9	384.3	381.6	379.1	376.7
65°	347.3	345.8	344.4	342.9	341.5	339.6	337.2	334.8	332.4	330.0	327.8
67.5°	296.0	294.8	293.7	292.5	291.4	289.8	287.6	285.4	283.2	281.0	279.4
70°	264.0	263.0	262.0	261.1	260.2	258.5	256.4	254.2	252.1	249.9	248.3
72.5°	231.1	230.2	229.2	228.2	227.2	226.1	224.7	223.3	221.8	220.5	218.8
75°	181.7	181.2	180.8	180.3	179.9	179.0	177.8	176.6	175.4	174.1	172.8
77.5°	137.6	136.8	136.0	135.2	134.4	133.7	133.2	132.7	132.2	131.8	131.0
80°	108.2	107.9	107.7	107.5	107.2	106.9	106.4	105.9	105.4	104.9	104.2
82.5°	80.5	80.5	80.4	80.3	80.3	80.1	79.8	79.6	79.2	79.0	78.0
85°	44.4	44.1	43.9	43.6	43.4	43.1	42.9	42.6	42.4	42.2	41.5
87.5°	15.7	15.4	15.1	14.8	14.6	14.3	14.0	13.8	13.5	13.2	12.6
90°	0.2	0.9	1.5	2.2	2.9	3.4	3.8	4.3	4.8	5.3	5.5
92.5°	5.3	5.3	5.2	5.1	5.1	5.2	5.4	5.6	5.9	6.1	6.3
95°	17.1	15.2	13.3	11.3	9.4	8.6	9.0	9.5	9.9	10.3	10.6
97.5°	34.0	28.5	23.1	17.7	12.2	9.9	10.9	11.8	12.8	13.8	14.0
100°	46.6	38.6	30.6	22.6	14.6	11.0	12.1	13.0	14.0	15.0	15.5
102.5°	60.6	58.9	57.2	55.5	53.8	48.8	40.4	32.1	23.8	15.4	16.1
105°	80.1	81.9	83.6	85.4	87.2	80.1	64.1	48.1	32.0	16.1	16.7
107.5°	102.4	103.9	105.3	106.7	108.1	99.2	80.1	60.9	41.7	22.5	21.9
110°	116.8	118.0	119.3	120.5	121.7	113.8	96.9	80.0	63.0	46.1	40.3



TEST NUMBER: P331381-930

CATALOG NUMBER: SA2XXDIP-C865D330U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	130.3	131.3	132.5	133.5	134.6	133.1	128.9	124.7	120.5	116.3	95.0
115°	151.6	152.5	153.6	154.6	155.6	156.8	158.2	159.7	161.2	162.7	135.5
117.5°	170.6	171.7	172.8	174.0	175.0	176.1	177.2	178.1	179.1	180.2	173.6
120°	184.5	185.4	186.3	187.2	188.0	189.0	190.0	191.1	192.2	193.2	194.0
122.5°	196.3	197.3	198.2	199.1	200.1	201.1	202.2	203.3	204.6	205.7	206.1
125°	214.3	215.1	215.8	216.6	217.4	218.3	219.4	220.5	221.6	222.7	223.1
127.5°	230.6	231.5	232.3	233.2	234.0	234.8	235.6	236.5	237.3	238.1	238.7
130°	240.9	241.9	242.8	243.8	244.7	245.5	246.1	246.8	247.4	248.1	248.7
132.5°	251.5	252.3	253.1	253.9	254.7	255.4	256.0	256.7	257.3	258.0	258.5
135°	265.2	266.1	267.1	268.0	269.0	269.7	270.2	270.8	271.3	271.8	272.4
137.5°	279.1	279.7	280.4	281.0	281.7	282.3	282.9	283.5	284.1	284.7	285.3
140°	288.1	288.6	289.0	289.5	290.0	290.6	291.2	291.9	292.5	293.1	293.7
142.5°	295.7	296.1	296.5	297.0	297.4	298.0	298.7	299.5	300.2	300.9	301.4
145°	307.6	307.6	307.5	307.4	307.4	307.9	308.8	309.9	310.9	311.9	312.3
147.5°	318.0	317.8	317.6	317.3	317.2	317.5	318.5	319.5	320.5	321.5	321.7
150°	324.7	324.3	323.9	323.5	323.1	323.4	324.3	325.3	326.2	327.2	327.5
152.5°	330.4	330.0	329.5	329.1	328.6	328.8	329.7	330.6	331.5	332.4	332.7
155°	338.8	338.2	337.7	337.1	336.6	336.7	337.5	338.1	338.8	339.5	339.9
157.5°	345.2	344.8	344.3	343.9	343.4	343.5	344.0	344.5	345.0	345.4	345.8
160°	349.0	348.7	348.3	348.0	347.6	347.6	348.0	348.3	348.7	349.0	349.4
162.5°	352.4	352.0	351.7	351.3	351.0	351.0	351.2	351.6	351.9	352.2	352.6
165°	356.9	356.6	356.2	355.9	355.6	355.5	355.6	355.8	356.0	356.1	356.5
167.5°	360.3	360.0	359.6	359.2	358.9	358.8	359.0	359.1	359.3	359.5	359.9
170°	362.2	361.8	361.5	361.2	360.8	360.7	360.8	360.9	361.0	361.2	361.6
172.5°	363.5	363.1	362.7	362.4	362.1	361.9	362.1	362.2	362.3	362.4	362.8
175°	365.1	364.7	364.3	363.9	363.5	363.3	363.5	363.5	363.7	363.8	364.2
177.5°	365.3	365.0	364.7	364.4	364.0	363.9	363.9	364.0	364.0	364.1	364.4
180°	364.3	364.3	364.3	364.3	364.3	364.3	364.3	364.3	364.3	364.3	364.3



TEST NUMBER: P331381-930
 CATALOG NUMBER: SA2XXDIP-C865D330U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1
2.5°	1120.3	1122.3	1124.1	1124.9	1124.5	1124.1	1123.8	1123.4
5°	1112.7	1114.7	1116.6	1117.3	1116.9	1116.4	1115.9	1115.4
7.5°	1100.2	1102.1	1104.1	1104.7	1104.2	1103.7	1103.2	1102.6
10°	1088.9	1090.9	1092.8	1093.4	1092.7	1091.9	1091.2	1090.5
12.5°	1075.7	1077.0	1078.4	1078.8	1078.2	1077.7	1077.2	1076.7
15°	1052.4	1053.4	1054.3	1054.2	1053.0	1051.8	1050.6	1049.4
17.5°	1024.7	1025.9	1027.0	1027.0	1025.8	1024.7	1023.5	1022.4
20°	1003.2	1004.0	1004.7	1004.5	1003.6	1002.7	1001.7	1000.7
22.5°	980.5	980.6	980.7	980.6	979.9	979.3	978.8	978.2
25°	943.3	943.7	944.2	944.2	943.7	943.3	942.8	942.3
27.5°	906.7	906.0	905.2	904.3	903.1	902.0	900.8	899.7
30°	878.1	877.4	876.7	875.8	874.9	873.9	872.9	872.0
32.5°	850.1	848.8	847.5	846.4	845.5	844.5	843.5	842.5
35°	805.3	803.8	802.4	801.0	799.9	798.7	797.4	796.2
37.5°	760.3	758.5	756.7	755.2	754.1	752.9	751.8	750.6
40°	729.2	727.0	724.9	723.3	722.4	721.4	720.4	719.4
42.5°	698.5	696.1	693.8	691.9	690.6	689.3	687.9	686.6
45°	651.4	648.7	646.1	644.3	643.4	642.4	641.4	640.5
47.5°	602.4	599.7	596.9	594.8	593.4	592.0	590.6	589.2
50°	571.0	567.6	564.3	562.0	560.8	559.5	558.4	557.2
52.5°	538.3	535.6	532.8	530.6	529.0	527.4	525.9	524.2
55°	489.8	486.8	484.0	481.9	480.7	479.5	478.3	477.1
57.5°	439.2	436.3	433.5	431.6	430.7	429.8	428.9	428.0
60°	405.9	403.2	400.6	398.8	398.1	397.4	396.6	396.0
62.5°	374.1	371.7	369.2	367.6	366.6	365.7	364.8	363.9
65°	325.6	323.5	321.3	319.6	318.5	317.2	316.0	314.8
67.5°	277.7	276.0	274.3	273.0	272.1	271.1	270.1	269.1
70°	246.5	244.8	243.2	241.8	240.9	239.9	239.0	238.0
72.5°	217.1	215.4	213.8	212.5	211.7	211.0	210.2	209.5
75°	171.3	169.8	168.4	168.0	168.4	168.9	169.3	169.8
77.5°	130.4	129.6	128.9	128.2	127.5	126.9	126.2	125.5
80°	103.5	102.8	102.1	101.4	100.9	100.5	100.0	99.5
82.5°	77.1	76.2	75.3	74.8	74.7	74.6	74.5	74.4
85°	40.8	40.0	39.3	38.8	38.6	38.3	38.1	37.8
87.5°	12.1	11.6	11.1	10.8	10.6	10.4	10.3	10.1
90°	5.9	6.1	6.4	6.7	6.8	6.8	7.0	7.1
92.5°	6.4	6.6	6.7	6.8	6.9	7.0	7.0	7.1
95°	10.8	11.2	11.4	11.6	11.5	11.4	11.4	11.3
97.5°	14.3	14.4	14.7	14.8	14.9	15.0	15.1	15.2
100°	16.0	16.5	16.9	17.2	17.3	17.4	17.5	17.7
102.5°	16.6	17.3	17.9	18.3	18.4	18.6	18.8	18.9
105°	17.4	18.0	18.7	19.1	19.3	19.6	19.8	20.1
107.5°	21.2	20.5	19.9	19.6	19.9	20.1	20.4	20.6
110°	34.4	28.5	22.7	19.9	20.1	20.4	20.6	20.8



TEST NUMBER: P331381-930

CATALOG NUMBER: SA2XXDIP-C865D330U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	73.6	52.3	30.9	20.3	20.5	20.6	20.9	21.0
115°	108.4	81.3	54.1	38.5	34.2	30.1	25.8	21.6
117.5°	167.1	160.5	153.9	143.7	129.9	116.0	102.2	88.3
120°	194.6	195.3	196.0	192.4	184.5	176.6	168.7	160.8
122.5°	206.5	206.9	207.3	206.8	205.3	203.7	202.2	200.6
125°	223.6	224.0	224.4	224.7	224.9	225.0	225.2	225.3
127.5°	239.4	239.9	240.5	240.8	240.9	240.9	240.9	241.0
130°	249.3	250.0	250.6	250.9	250.9	250.8	250.8	250.7
132.5°	259.1	259.6	260.2	260.4	260.3	260.3	260.2	260.2
135°	273.0	273.5	274.1	274.3	274.3	274.1	274.0	273.9
137.5°	285.8	286.4	287.0	287.1	287.0	286.8	286.6	286.4
140°	294.2	294.7	295.2	295.4	295.1	294.8	294.5	294.2
142.5°	301.9	302.4	302.9	303.0	302.6	302.4	302.1	301.7
145°	312.7	313.1	313.5	313.6	313.2	313.0	312.7	312.3
147.5°	322.0	322.4	322.7	322.7	322.5	322.2	322.0	321.7
150°	327.8	328.2	328.6	328.6	328.3	328.0	327.7	327.4
152.5°	333.1	333.5	333.8	333.8	333.4	333.0	332.6	332.2
155°	340.2	340.6	341.0	340.9	340.4	340.0	339.5	339.0
157.5°	346.3	346.7	347.0	347.0	346.5	346.1	345.6	345.2
160°	349.8	350.1	350.4	350.4	350.0	349.6	349.2	348.8
162.5°	352.9	353.4	353.8	353.8	353.2	352.7	352.2	351.7
165°	356.9	357.3	357.8	357.8	357.3	356.9	356.5	356.1
167.5°	360.3	360.7	361.1	361.0	360.5	360.0	359.5	358.9
170°	362.0	362.4	362.8	362.7	362.2	361.7	361.2	360.6
172.5°	363.2	363.6	364.0	364.0	363.5	363.0	362.4	361.9
175°	364.6	365.0	365.4	365.3	364.8	364.2	363.5	363.0
177.5°	364.8	365.1	365.4	365.3	364.9	364.5	364.1	363.7
180°	364.3	364.3	364.3	364.3	364.3	364.3	364.3	364.3

(END OF REPORT)