

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331383-930

Luminaire Tested: **SA2XXDIP-C865D330U930-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331383-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXDIP-C865D330U930-4F0-1E-UDD-F4  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 330 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3906.2 lumens  
Efficiency: N/A  
Efficacy: 89.8 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 43.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331383-930

CATALOG NUMBER: SA2XXDIP-C865D330U930-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P331383-930

CATALOG NUMBER: SA2XXDIP-C865D330U930-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	113	113	113	113	107	107	107	107	96	96	96	87	87	87	78	78	78	73
1	103	99	94	91	98	94	90	87	85	82	79	76	74	72	69	67	66	62
2	94	86	80	74	89	82	76	71	74	70	66	67	63	60	60	58	55	52
3	86	76	68	62	81	72	65	60	65	60	55	59	55	51	54	50	47	44
4	78	67	59	53	74	64	57	51	58	52	47	53	48	44	48	44	41	38
5	72	60	52	45	68	57	50	44	52	46	41	48	42	38	43	39	35	33
6	67	54	46	39	63	52	44	38	47	41	36	43	38	34	39	35	31	29
7	62	49	41	35	58	47	39	34	43	36	32	39	34	30	36	31	28	25
8	57	45	36	31	54	43	35	30	39	33	28	36	31	27	33	28	25	23
9	54	41	33	28	51	39	32	27	36	30	26	33	28	24	30	26	23	21
10	50	38	30	25	48	36	29	24	33	27	23	31	26	22	28	24	21	19

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	18166	18166	18166
5°	18235	17973	18078
10°	18126	17790	17879
15°	17904	17560	17541
20°	17584	17213	17194
25°	17268	16787	16787
30°	16861	16397	16257
35°	16484	15928	15693
40°	16008	15460	15163
45°	15536	14995	14625
50°	15028	14511	13996
55°	14494	13948	13430
60°	13905	13275	12788
65°	13268	12607	12027
70°	12463	11797	11235
75°	11335	10861	10593
80°	10060	9754	9252
85°	8225	7818	7003



TEST NUMBER: P331383-930

CATALOG NUMBER: SA2XXDIP-C865D330U930-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	105.8	2.7
10°-20°	297.7	7.6
20°-30°	437.6	11.2
30°-40°	508.3	13.0
40°-50°	507.7	13.0
50°-60°	442.8	11.3
60°-70°	327.4	8.4
70°-80°	185.4	4.7
80°-90°	51.2	1.3
90°-100°	59.9	1.5
100°-110°	203.2	5.2
110°-120°	215.9	5.5
120°-130°	177.7	4.6
130°-140°	142.7	3.7
140°-150°	107.9	2.8
150°-160°	75.8	1.9
160°-170°	44.6	1.1
170°-180°	14.5	0.4
0°-30°	841.1	21.5
0°-40°	1349.3	34.5
0°-60°	2299.8	58.9
0°-90°	2863.8	73.3
90°-120°	479.1	12.3
90°-150°	907.4	23.2
90°-180°	1042.0	26.7
0°-180°	3906.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1125	1125	1125	1125	1125	
5°	1125	1120	1109	1117	1115	107
15°	1071	1064	1050	1054	1049	301
25°	969	960	942	944	942	446
35°	836	825	808	802	796	522
45°	680	672	657	645	640	525
55°	515	508	496	483	477	460
65°	347	341	330	320	315	343
75°	182	179	174	168	170	194
85°	44	43	42	39	38	51
90°	0	4	10	9	10	3
95°	10	25	113	43	33	11
105°	35	53	213	382	325	37
115°	62	78	179	369	427	61
125°	86	102	172	299	347	77
135°	101	121	170	251	287	78
145°	116	133	169	210	229	73
155°	132	142	164	185	193	61
165°	144	148	157	166	169	40
175°	150	150	151	153	152	14
180°	150	150	150	150	150	



TEST NUMBER: P331383-930  
 CATALOG NUMBER: SA2XXDIP-C865D330U930-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1
2.5°	1130.3	1129.4	1128.4	1127.5	1126.5	1124.9	1122.8	1120.7	1118.6	1116.5	1118.4
5°	1125.1	1124.1	1123.2	1122.3	1121.3	1119.5	1116.9	1114.2	1111.6	1108.9	1110.8
7.5°	1115.2	1113.7	1112.2	1110.7	1109.2	1107.1	1104.4	1101.7	1099.0	1096.3	1098.3
10°	1105.6	1104.0	1102.3	1100.6	1098.9	1096.7	1093.7	1090.9	1088.0	1085.1	1087.0
12.5°	1092.7	1091.2	1089.7	1088.2	1086.7	1084.5	1081.7	1078.7	1075.9	1073.0	1074.3
15°	1071.1	1069.6	1068.1	1066.7	1065.3	1063.0	1059.9	1056.7	1053.6	1050.5	1051.4
17.5°	1043.3	1041.9	1040.5	1039.0	1037.5	1035.3	1032.1	1028.9	1025.7	1022.5	1023.7
20°	1023.4	1022.0	1020.6	1019.1	1017.7	1015.3	1011.9	1008.5	1005.2	1001.8	1002.5
22.5°	1003.6	1001.5	999.5	997.4	995.5	992.9	989.7	986.5	983.3	980.2	980.3
25°	969.3	967.4	965.5	963.6	961.6	958.6	954.6	950.5	946.4	942.3	942.8
27.5°	930.4	928.7	926.9	925.2	923.5	921.0	917.8	914.5	911.3	908.1	907.4
30°	904.4	902.5	900.6	898.7	896.7	894.0	890.4	886.8	883.1	879.5	878.8
32.5°	876.8	875.2	873.7	872.1	870.6	867.9	864.1	860.3	856.6	852.7	851.4
35°	836.3	833.9	831.4	829.1	826.6	823.5	819.7	815.9	812.0	808.1	806.7
37.5°	790.6	788.5	786.4	784.2	782.2	779.2	775.3	771.5	767.6	763.8	762.0
40°	759.5	757.6	755.6	753.7	751.8	748.9	745.0	741.2	737.4	733.5	731.3
42.5°	729.2	727.2	725.3	723.4	721.5	718.6	714.8	710.9	707.0	703.2	700.8
45°	680.4	678.8	677.1	675.5	673.8	671.1	667.5	663.9	660.3	656.7	654.0
47.5°	632.0	630.5	628.8	627.3	625.7	623.0	619.2	615.5	611.7	608.0	605.2
50°	598.3	597.0	595.9	594.7	593.5	591.2	587.8	584.4	581.1	577.7	574.4
52.5°	565.4	563.8	562.2	560.6	559.1	556.7	553.5	550.3	547.1	544.0	541.2
55°	514.9	513.6	512.1	510.6	509.2	507.0	504.2	501.2	498.4	495.5	492.6
57.5°	464.3	463.2	462.0	460.9	459.7	457.5	454.4	451.2	448.0	444.8	442.1
60°	430.6	429.6	428.7	427.7	426.7	424.6	421.2	417.8	414.5	411.1	408.5
62.5°	397.7	396.2	394.6	393.1	391.5	389.5	386.9	384.3	381.6	379.1	376.7
65°	347.3	345.8	344.4	342.9	341.5	339.6	337.2	334.8	332.4	330.0	327.8
67.5°	296.0	294.8	293.7	292.5	291.4	289.8	287.6	285.4	283.2	281.0	279.4
70°	264.0	263.0	262.0	261.1	260.2	258.5	256.4	254.2	252.1	249.9	248.3
72.5°	231.1	230.2	229.2	228.2	227.2	226.1	224.7	223.3	221.8	220.5	218.8
75°	181.7	181.2	180.8	180.3	179.9	179.0	177.8	176.6	175.4	174.1	172.8
77.5°	137.6	136.8	136.0	135.2	134.4	133.7	133.2	132.7	132.2	131.8	131.0
80°	108.2	107.9	107.7	107.5	107.2	106.9	106.4	105.9	105.4	104.9	104.2
82.5°	80.5	80.5	80.4	80.3	80.3	80.1	79.8	79.6	79.2	79.0	78.0
85°	44.4	44.1	43.9	43.6	43.4	43.1	42.9	42.6	42.4	42.2	41.5
87.5°	15.7	15.4	15.2	15.0	14.8	14.5	14.4	14.4	14.4	14.1	13.5
90°	0.3	1.1	2.3	2.9	3.4	4.3	5.8	7.7	9.5	9.8	9.5
92.5°	3.5	5.1	7.2	8.4	10.4	13.0	19.6	28.8	36.9	37.4	31.6
95°	10.1	11.3	14.1	16.7	21.3	28.2	41.5	66.5	100.0	112.9	98.8
97.5°	16.4	17.9	21.0	24.9	30.2	38.1	54.7	89.7	145.2	192.7	202.2
100°	22.2	23.1	25.6	30.2	36.0	44.1	59.4	94.5	156.7	227.6	269.0
102.5°	27.5	28.1	30.7	35.3	41.3	49.4	63.5	94.7	152.3	228.7	293.9
105°	35.1	36.3	38.3	42.6	49.0	57.1	70.6	96.2	143.7	213.4	290.1
107.5°	43.5	44.4	46.3	50.3	56.6	64.7	77.9	100.2	139.5	197.1	264.8
110°	49.0	50.1	51.9	55.6	61.6	70.0	82.7	103.4	138.6	189.2	248.9



TEST NUMBER: P331383-930

CATALOG NUMBER: SA2XXDIP-C865D330U930-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	54.1	55.2	57.2	60.7	66.4	75.1	87.3	106.9	138.8	184.2	237.8
115°	62.0	63.3	65.1	68.6	74.4	82.1	94.5	112.0	140.0	178.6	224.1
117.5°	70.1	71.3	73.0	76.1	81.6	89.7	101.1	117.6	142.1	175.9	215.5
120°	75.2	76.3	78.1	80.6	86.4	94.5	105.7	121.3	143.5	174.3	210.8
122.5°	80.1	81.0	82.7	85.5	91.2	99.5	110.1	124.5	145.0	173.3	206.9
125°	86.4	87.3	89.0	92.5	98.2	106.3	116.7	129.6	147.5	171.7	201.4
127.5°	91.5	92.6	95.1	98.9	104.4	112.7	122.8	134.4	149.9	170.7	196.2
130°	94.5	95.6	98.5	102.6	108.4	116.3	126.5	137.4	151.8	170.2	192.7
132.5°	97.3	98.7	101.7	106.0	112.0	120.1	129.7	140.4	153.7	170.0	190.0
135°	101.4	102.6	106.0	110.3	117.0	125.0	134.3	144.3	155.9	169.7	186.1
137.5°	105.3	106.7	110.1	114.8	121.3	128.8	137.9	147.3	157.8	169.6	183.4
140°	108.4	109.5	112.9	117.6	123.8	131.3	140.0	149.0	158.7	169.4	181.7
142.5°	111.3	112.3	115.4	120.1	126.2	133.2	141.6	150.3	159.4	169.4	180.2
145°	115.8	117.0	119.8	124.2	130.0	136.2	144.1	152.1	160.1	168.8	178.1
147.5°	120.7	121.5	124.3	128.2	133.1	138.7	146.0	153.1	160.4	167.8	175.9
150°	123.8	124.7	127.0	130.8	135.1	140.3	146.9	153.5	160.1	167.1	174.0
152.5°	127.1	127.5	129.8	133.1	137.2	141.9	147.8	153.8	159.7	165.9	172.4
155°	131.7	131.9	133.6	136.8	140.0	144.3	149.2	154.1	159.0	163.9	169.4
157.5°	135.4	135.7	137.1	139.9	142.4	146.0	150.2	154.1	157.7	161.8	166.6
160°	137.9	138.3	139.4	141.7	144.1	147.2	150.7	154.1	157.0	160.5	164.4
162.5°	140.6	140.3	141.5	143.3	145.4	147.9	150.9	153.8	156.3	159.3	162.7
165°	143.5	143.2	143.7	145.4	146.9	148.6	151.2	153.3	155.0	157.0	159.6
167.5°	145.9	145.5	146.0	147.2	148.2	149.3	151.2	152.9	153.7	155.0	156.6
170°	147.5	146.9	147.2	148.1	148.6	149.5	150.9	152.4	153.0	153.8	155.0
172.5°	148.4	148.1	147.9	148.8	149.1	149.8	150.7	151.7	152.1	152.5	153.4
175°	149.5	149.2	149.0	149.5	149.5	149.8	150.3	150.9	150.7	150.9	151.2
177.5°	150.0	149.5	149.4	149.8	149.8	149.8	150.0	150.5	150.0	149.8	150.0
180°	149.8	149.8	149.8	149.8	149.8	149.8	149.8	149.8	149.8	149.8	149.8



TEST NUMBER: P331383-930

CATALOG NUMBER: SA2XXDIP-C865D330U930-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1
2.5°	1120.3	1122.3	1124.1	1124.9	1124.5	1124.1	1123.8	1123.4
5°	1112.7	1114.7	1116.6	1117.3	1116.9	1116.4	1115.9	1115.4
7.5°	1100.2	1102.1	1104.1	1104.7	1104.2	1103.7	1103.2	1102.6
10°	1088.9	1090.9	1092.8	1093.4	1092.7	1091.9	1091.2	1090.5
12.5°	1075.7	1077.0	1078.4	1078.8	1078.2	1077.7	1077.2	1076.7
15°	1052.4	1053.4	1054.3	1054.2	1053.0	1051.8	1050.6	1049.4
17.5°	1024.7	1025.9	1027.0	1027.0	1025.8	1024.7	1023.5	1022.4
20°	1003.2	1004.0	1004.7	1004.5	1003.6	1002.7	1001.7	1000.7
22.5°	980.5	980.6	980.7	980.6	979.9	979.3	978.8	978.2
25°	943.3	943.7	944.2	944.2	943.7	943.3	942.8	942.3
27.5°	906.7	906.0	905.2	904.3	903.1	902.0	900.8	899.7
30°	878.1	877.4	876.7	875.8	874.9	873.9	872.9	872.0
32.5°	850.1	848.8	847.5	846.4	845.5	844.5	843.5	842.5
35°	805.3	803.8	802.4	801.0	799.9	798.7	797.4	796.2
37.5°	760.3	758.5	756.7	755.2	754.1	752.9	751.8	750.6
40°	729.2	727.0	724.9	723.3	722.4	721.4	720.4	719.4
42.5°	698.5	696.1	693.8	691.9	690.6	689.3	687.9	686.6
45°	651.4	648.7	646.1	644.3	643.4	642.4	641.4	640.5
47.5°	602.4	599.7	596.9	594.8	593.4	592.0	590.6	589.2
50°	571.0	567.6	564.3	562.0	560.8	559.5	558.4	557.2
52.5°	538.3	535.6	532.8	530.6	529.0	527.4	525.9	524.2
55°	489.8	486.8	484.0	481.9	480.7	479.5	478.3	477.1
57.5°	439.2	436.3	433.5	431.6	430.7	429.8	428.9	428.0
60°	405.9	403.2	400.6	398.8	398.1	397.4	396.6	396.0
62.5°	374.1	371.7	369.2	367.6	366.6	365.7	364.8	363.9
65°	325.6	323.5	321.3	319.6	318.5	317.2	316.0	314.8
67.5°	277.7	276.0	274.3	273.0	272.1	271.1	270.1	269.1
70°	246.5	244.8	243.2	241.8	240.9	239.9	239.0	238.0
72.5°	217.1	215.4	213.8	212.5	211.7	211.0	210.2	209.5
75°	171.3	169.8	168.4	168.0	168.4	168.9	169.3	169.8
77.5°	130.4	129.6	128.9	128.2	127.5	126.9	126.2	125.5
80°	103.5	102.8	102.1	101.4	100.9	100.5	100.0	99.5
82.5°	77.1	76.2	75.3	74.8	74.7	74.6	74.5	74.4
85°	40.8	40.0	39.3	38.8	38.6	38.3	38.1	37.8
87.5°	12.8	12.1	11.7	11.3	11.2	10.9	10.8	10.5
90°	9.2	8.6	9.2	9.5	9.5	9.5	9.5	9.5
92.5°	25.1	21.5	19.2	17.4	17.1	16.2	16.4	16.0
95°	75.5	57.9	45.8	39.5	35.7	33.4	32.5	32.9
97.5°	176.1	144.1	112.9	92.1	78.4	71.3	67.1	64.7
100°	263.0	227.3	187.8	153.0	129.1	116.7	108.4	103.1
102.5°	319.9	311.9	283.0	246.1	220.0	198.9	188.5	181.5
105°	350.0	382.5	386.3	376.8	358.9	341.0	328.6	324.7
107.5°	328.3	377.4	407.3	421.3	423.5	422.6	420.0	414.7
110°	309.7	361.3	398.1	421.8	434.1	439.6	442.2	441.9





TEST NUMBER: P331383-930

CATALOG NUMBER: SA2XXDIP-C865D330U930-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	292.6	342.1	381.5	408.6	425.8	435.0	439.9	441.4
115°	271.7	316.0	353.8	383.4	403.9	417.1	424.6	427.2
117.5°	255.8	294.8	329.1	356.9	377.7	391.8	399.6	401.8
120°	248.0	283.7	314.3	340.5	360.7	374.2	382.5	385.5
122.5°	241.8	274.5	303.5	327.1	345.2	358.6	366.0	368.4
125°	232.8	262.4	287.8	309.4	326.1	337.0	344.2	346.6
127.5°	223.8	250.7	274.6	294.5	309.1	319.4	325.5	327.4
130°	218.1	242.9	265.6	284.6	298.7	308.5	314.3	316.6
132.5°	212.5	235.5	256.4	274.3	288.1	297.9	303.2	305.3
135°	204.8	223.8	242.9	258.9	271.3	280.9	286.1	287.2
137.5°	198.7	214.6	229.7	243.7	255.0	263.2	267.7	269.5
140°	194.7	208.6	221.8	234.5	243.7	251.2	255.5	257.2
142.5°	191.5	203.3	214.7	225.3	234.0	240.8	244.7	245.0
145°	186.9	196.5	205.4	213.8	220.6	225.6	228.4	229.3
147.5°	183.4	190.9	197.9	204.0	209.7	213.6	215.6	216.1
150°	180.9	187.3	193.3	198.4	202.8	206.3	208.0	208.3
152.5°	178.4	184.3	189.4	193.9	197.3	200.2	201.5	201.6
155°	174.9	179.4	183.8	186.9	190.1	192.2	193.3	192.7
157.5°	170.8	174.6	178.2	180.8	183.0	184.7	185.2	185.2
160°	168.2	171.4	174.6	176.6	178.6	180.0	180.3	180.3
162.5°	165.7	168.4	171.1	172.7	174.7	175.7	175.9	175.7
165°	161.9	163.9	165.9	167.1	168.2	169.4	169.4	169.1
167.5°	158.2	159.8	161.2	162.2	162.7	163.4	163.3	163.0
170°	156.5	157.3	158.4	159.0	159.3	160.1	159.9	159.3
172.5°	154.3	155.0	155.9	156.2	156.5	156.9	156.6	156.3
175°	152.1	152.4	152.7	153.0	153.0	153.3	153.0	152.4
177.5°	150.5	150.5	150.7	150.7	150.7	150.7	150.5	150.0
180°	149.8	149.8	149.8	149.8	149.8	149.8	149.8	149.8

(END OF REPORT)