

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331390-930

Luminaire Tested: **SA2XXDIP-C865D530U930-4F0-1E-UDD-F**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331390-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C865D530U930-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 530 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4587.1 lumens
Efficiency: N/A
Efficacy: 94.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 48.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331390-930
CATALOG NUMBER: SA2XXDIP-C865D530U930-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331390-930

CATALOG NUMBER: SA2XXDIP-C865D530U930-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	68	68	68	62
1	101	96	92	89	94	90	87	84	79	77	74	69	67	65	60	58	57	53
2	92	84	78	72	86	79	73	69	69	65	61	61	57	55	53	50	48	44
3	84	74	66	60	78	70	63	57	61	56	52	54	50	46	47	44	41	37
4	77	65	57	51	71	62	54	49	54	49	44	48	43	40	42	38	35	32
5	70	58	50	44	66	55	48	42	49	43	38	43	38	34	38	34	31	28
6	65	52	44	38	61	50	42	37	44	38	33	39	34	30	34	30	27	24
7	60	47	39	34	56	45	37	32	40	34	29	35	30	27	31	27	24	22
8	56	43	35	30	52	41	34	29	37	31	26	32	28	24	29	25	22	19
9	52	39	32	27	49	37	30	26	34	28	24	30	25	22	26	22	20	18
10	49	36	29	24	46	34	28	23	31	25	21	28	23	20	25	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	18166	18166	18166
5°	18235	17973	18078
10°	18126	17790	17879
15°	17904	17560	17541
20°	17584	17213	17194
25°	17268	16787	16787
30°	16861	16397	16257
35°	16484	15928	15693
40°	16008	15460	15163
45°	15536	14995	14625
50°	15028	14511	13996
55°	14494	13948	13430
60°	13905	13275	12788
65°	13268	12607	12027
70°	12463	11797	11235
75°	11335	10861	10593
80°	10060	9754	9252
85°	8225	7818	7003



TEST NUMBER: P331390-930

CATALOG NUMBER: SA2XXDIP-C865D530U930-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	105.8	2.3
10°-20°	297.7	6.5
20°-30°	437.6	9.5
30°-40°	508.3	11.1
40°-50°	507.7	11.1
50°-60°	442.8	9.7
60°-70°	327.4	7.1
70°-80°	185.4	4.0
80°-90°	51.3	1.1
90°-100°	19.6	0.4
100°-110°	71.9	1.6
110°-120°	192.3	4.2
120°-130°	317.4	6.9
130°-140°	337.5	7.4
140°-150°	313.7	6.8
150°-160°	252.2	5.5
160°-170°	162.5	3.5
170°-180°	55.9	1.2
0°-30°	841.1	18.3
0°-40°	1349.3	29.4
0°-60°	2299.8	50.1
0°-90°	2863.9	62.4
90°-120°	283.8	6.2
90°-150°	1252.5	27.3
90°-180°	1723.0	37.6
0°-180°	4587.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1125	1125	1125	1125	1125	
5°	1125	1120	1109	1117	1115	107
15°	1071	1064	1050	1054	1049	301
25°	969	960	942	944	942	446
35°	836	825	808	802	796	522
45°	680	672	657	645	640	525
55°	515	508	496	483	477	460
65°	347	341	330	320	315	343
75°	182	179	174	168	170	194
85°	44	43	42	39	38	51
90°	0	5	8	11	12	3
95°	28	15	17	19	18	34
105°	129	135	26	30	32	138
115°	245	252	262	75	35	241
125°	346	352	360	362	364	308
135°	428	435	439	443	442	330
145°	496	497	503	506	504	310
155°	547	543	548	550	547	252
165°	576	574	575	578	575	163
175°	589	586	587	590	586	56
180°	588	588	588	588	588	



TEST NUMBER: P331390-930

CATALOG NUMBER: SA2XXDIP-C865D530U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1
2.5°	1130.3	1129.4	1128.4	1127.5	1126.5	1124.9	1122.8	1120.7	1118.6	1116.5	1118.4
5°	1125.1	1124.1	1123.2	1122.3	1121.3	1119.5	1116.9	1114.2	1111.6	1108.9	1110.8
7.5°	1115.2	1113.7	1112.2	1110.7	1109.2	1107.1	1104.4	1101.7	1099.0	1096.3	1098.3
10°	1105.6	1104.0	1102.3	1100.6	1098.9	1096.7	1093.7	1090.9	1088.0	1085.1	1087.0
12.5°	1092.7	1091.2	1089.7	1088.2	1086.7	1084.5	1081.7	1078.7	1075.9	1073.0	1074.3
15°	1071.1	1069.6	1068.1	1066.7	1065.3	1063.0	1059.9	1056.7	1053.6	1050.5	1051.4
17.5°	1043.3	1041.9	1040.5	1039.0	1037.5	1035.3	1032.1	1028.9	1025.7	1022.5	1023.7
20°	1023.4	1022.0	1020.6	1019.1	1017.7	1015.3	1011.9	1008.5	1005.2	1001.8	1002.5
22.5°	1003.6	1001.5	999.5	997.4	995.5	992.9	989.7	986.5	983.3	980.2	980.3
25°	969.3	967.4	965.5	963.6	961.6	958.6	954.6	950.5	946.4	942.3	942.8
27.5°	930.4	928.7	926.9	925.2	923.5	921.0	917.8	914.5	911.3	908.1	907.4
30°	904.4	902.5	900.6	898.7	896.7	894.0	890.4	886.8	883.1	879.5	878.8
32.5°	876.8	875.2	873.7	872.1	870.6	867.9	864.1	860.3	856.6	852.7	851.4
35°	836.3	833.9	831.4	829.1	826.6	823.5	819.7	815.9	812.0	808.1	806.7
37.5°	790.6	788.5	786.4	784.2	782.2	779.2	775.3	771.5	767.6	763.8	762.0
40°	759.5	757.6	755.6	753.7	751.8	748.9	745.0	741.2	737.4	733.5	731.3
42.5°	729.2	727.2	725.3	723.4	721.5	718.6	714.8	710.9	707.0	703.2	700.8
45°	680.4	678.8	677.1	675.5	673.8	671.1	667.5	663.9	660.3	656.7	654.0
47.5°	632.0	630.5	628.8	627.3	625.7	623.0	619.2	615.5	611.7	608.0	605.2
50°	598.3	597.0	595.9	594.7	593.5	591.2	587.8	584.4	581.1	577.7	574.4
52.5°	565.4	563.8	562.2	560.6	559.1	556.7	553.5	550.3	547.1	544.0	541.2
55°	514.9	513.6	512.1	510.6	509.2	507.0	504.2	501.2	498.4	495.5	492.6
57.5°	464.3	463.2	462.0	460.9	459.7	457.5	454.4	451.2	448.0	444.8	442.1
60°	430.6	429.6	428.7	427.7	426.7	424.6	421.2	417.8	414.5	411.1	408.5
62.5°	397.7	396.2	394.6	393.1	391.5	389.5	386.9	384.3	381.6	379.1	376.7
65°	347.3	345.8	344.4	342.9	341.5	339.6	337.2	334.8	332.4	330.0	327.8
67.5°	296.0	294.8	293.7	292.5	291.4	289.8	287.6	285.4	283.2	281.0	279.4
70°	264.0	263.0	262.0	261.1	260.2	258.5	256.4	254.2	252.1	249.9	248.3
72.5°	231.1	230.2	229.2	228.2	227.2	226.1	224.7	223.3	221.8	220.5	218.8
75°	181.7	181.2	180.8	180.3	179.9	179.0	177.8	176.6	175.4	174.1	172.8
77.5°	137.6	136.8	136.0	135.2	134.4	133.7	133.2	132.7	132.2	131.8	131.0
80°	108.2	107.9	107.7	107.5	107.2	106.9	106.4	105.9	105.4	104.9	104.2
82.5°	80.5	80.5	80.4	80.3	80.3	80.1	79.8	79.6	79.2	79.0	78.0
85°	44.4	44.1	43.9	43.6	43.4	43.1	42.9	42.6	42.4	42.2	41.5
87.5°	15.7	15.5	15.3	15.2	14.9	14.8	14.5	14.3	14.0	13.8	13.4
90°	0.4	1.5	2.5	3.5	4.6	5.5	6.3	7.0	7.7	8.5	9.0
92.5°	8.6	8.5	8.4	8.3	8.2	8.4	8.7	9.1	9.5	9.9	10.1
95°	27.6	24.5	21.4	18.3	15.2	13.9	14.6	15.2	15.9	16.6	17.0
97.5°	54.9	46.1	37.3	28.5	19.7	16.1	17.6	19.2	20.7	22.2	22.6
100°	75.3	62.4	49.4	36.4	23.5	17.9	19.4	21.0	22.7	24.2	25.0
102.5°	97.8	95.1	92.3	89.5	86.8	78.7	65.3	51.9	38.4	24.9	25.9
105°	129.3	132.2	135.0	137.9	140.7	129.2	103.4	77.6	51.8	25.9	27.0
107.5°	165.3	167.6	169.9	172.2	174.5	160.1	129.2	98.2	67.3	36.4	35.3
110°	188.5	190.5	192.5	194.4	196.4	183.8	156.5	129.1	101.7	74.4	65.0



TEST NUMBER: P331390-930

CATALOG NUMBER: SA2XXDIP-C865D530U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	210.3	212.1	213.8	215.6	217.3	214.8	208.1	201.3	194.5	187.8	153.3
115°	244.7	246.2	247.9	249.5	251.1	253.1	255.4	257.8	260.2	262.5	218.7
117.5°	275.4	277.2	279.0	280.8	282.6	284.3	285.9	287.6	289.2	290.7	280.2
120°	297.8	299.2	300.7	302.1	303.5	305.1	306.8	308.5	310.1	311.9	313.0
122.5°	316.9	318.4	319.9	321.4	322.9	324.6	326.4	328.2	330.1	332.0	332.6
125°	345.9	347.2	348.4	349.6	350.8	352.4	354.2	356.0	357.8	359.5	360.2
127.5°	372.2	373.6	375.0	376.3	377.6	379.0	380.3	381.7	383.0	384.4	385.3
130°	388.9	390.4	391.9	393.5	394.9	396.2	397.3	398.3	399.3	400.4	401.5
132.5°	405.9	407.2	408.5	409.8	411.1	412.2	413.3	414.3	415.3	416.4	417.3
135°	428.0	429.6	431.0	432.6	434.1	435.3	436.1	437.0	437.8	438.6	439.6
137.5°	450.5	451.4	452.5	453.6	454.6	455.7	456.6	457.6	458.5	459.5	460.5
140°	465.0	465.8	466.6	467.3	468.1	469.0	470.0	471.1	472.1	473.1	474.0
142.5°	477.3	478.0	478.7	479.3	480.0	480.9	482.2	483.3	484.5	485.8	486.5
145°	496.5	496.4	496.4	496.3	496.2	496.9	498.6	500.1	501.7	503.4	504.0
147.5°	513.3	512.9	512.6	512.3	511.8	512.5	514.0	515.7	517.2	518.9	519.3
150°	524.2	523.5	522.9	522.2	521.5	522.0	523.5	525.0	526.5	528.0	528.6
152.5°	533.4	532.6	531.9	531.2	530.4	530.8	532.2	533.7	535.1	536.5	537.1
155°	546.7	545.9	545.0	544.2	543.3	543.5	544.6	545.8	546.9	548.0	548.6
157.5°	557.2	556.5	555.8	555.1	554.3	554.4	555.1	556.0	556.8	557.6	558.2
160°	563.4	562.8	562.2	561.7	561.1	561.1	561.7	562.2	562.8	563.4	563.9
162.5°	568.8	568.2	567.6	567.0	566.6	566.5	567.0	567.4	567.9	568.4	569.1
165°	576.1	575.5	574.9	574.4	573.8	573.7	574.0	574.2	574.5	574.8	575.5
167.5°	581.6	581.0	580.4	579.8	579.3	579.1	579.4	579.7	579.9	580.2	580.8
170°	584.6	584.1	583.5	582.9	582.4	582.1	582.4	582.5	582.7	582.9	583.6
172.5°	586.7	586.1	585.5	585.0	584.4	584.2	584.4	584.6	584.7	585.0	585.6
175°	589.3	588.6	588.0	587.3	586.6	586.4	586.6	586.8	586.9	587.2	587.8
177.5°	589.7	589.2	588.6	588.2	587.6	587.3	587.4	587.5	587.6	587.7	588.2
180°	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0



TEST NUMBER: P331390-930

CATALOG NUMBER: SA2XXDIP-C865D530U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1
2.5°	1120.3	1122.3	1124.1	1124.9	1124.5	1124.1	1123.8	1123.4
5°	1112.7	1114.7	1116.6	1117.3	1116.9	1116.4	1115.9	1115.4
7.5°	1100.2	1102.1	1104.1	1104.7	1104.2	1103.7	1103.2	1102.6
10°	1088.9	1090.9	1092.8	1093.4	1092.7	1091.9	1091.2	1090.5
12.5°	1075.7	1077.0	1078.4	1078.8	1078.2	1077.7	1077.2	1076.7
15°	1052.4	1053.4	1054.3	1054.2	1053.0	1051.8	1050.6	1049.4
17.5°	1024.7	1025.9	1027.0	1027.0	1025.8	1024.7	1023.5	1022.4
20°	1003.2	1004.0	1004.7	1004.5	1003.6	1002.7	1001.7	1000.7
22.5°	980.5	980.6	980.7	980.6	979.9	979.3	978.8	978.2
25°	943.3	943.7	944.2	944.2	943.7	943.3	942.8	942.3
27.5°	906.7	906.0	905.2	904.3	903.1	902.0	900.8	899.7
30°	878.1	877.4	876.7	875.8	874.9	873.9	872.9	872.0
32.5°	850.1	848.8	847.5	846.4	845.5	844.5	843.5	842.5
35°	805.3	803.8	802.4	801.0	799.9	798.7	797.4	796.2
37.5°	760.3	758.5	756.7	755.2	754.1	752.9	751.8	750.6
40°	729.2	727.0	724.9	723.3	722.4	721.4	720.4	719.4
42.5°	698.5	696.1	693.8	691.9	690.6	689.3	687.9	686.6
45°	651.4	648.7	646.1	644.3	643.4	642.4	641.4	640.5
47.5°	602.4	599.7	596.9	594.8	593.4	592.0	590.6	589.2
50°	571.0	567.6	564.3	562.0	560.8	559.5	558.4	557.2
52.5°	538.3	535.6	532.8	530.6	529.0	527.4	525.9	524.2
55°	489.8	486.8	484.0	481.9	480.7	479.5	478.3	477.1
57.5°	439.2	436.3	433.5	431.6	430.7	429.8	428.9	428.0
60°	405.9	403.2	400.6	398.8	398.1	397.4	396.6	396.0
62.5°	374.1	371.7	369.2	367.6	366.6	365.7	364.8	363.9
65°	325.6	323.5	321.3	319.6	318.5	317.2	316.0	314.8
67.5°	277.7	276.0	274.3	273.0	272.1	271.1	270.1	269.1
70°	246.5	244.8	243.2	241.8	240.9	239.9	239.0	238.0
72.5°	217.1	215.4	213.8	212.5	211.7	211.0	210.2	209.5
75°	171.3	169.8	168.4	168.0	168.4	168.9	169.3	169.8
77.5°	130.4	129.6	128.9	128.2	127.5	126.9	126.2	125.5
80°	103.5	102.8	102.1	101.4	100.9	100.5	100.0	99.5
82.5°	77.1	76.2	75.3	74.8	74.7	74.6	74.5	74.4
85°	40.8	40.0	39.3	38.8	38.6	38.3	38.1	37.8
87.5°	12.9	12.4	11.9	11.6	11.4	11.3	11.1	10.9
90°	9.5	9.9	10.4	10.8	10.9	11.1	11.3	11.5
92.5°	10.4	10.6	10.8	11.0	11.2	11.3	11.4	11.5
95°	17.5	18.0	18.5	18.7	18.6	18.5	18.4	18.3
97.5°	23.0	23.3	23.7	24.0	24.1	24.2	24.3	24.5
100°	25.8	26.5	27.3	27.7	28.0	28.1	28.3	28.5
102.5°	26.9	27.9	28.9	29.5	29.8	30.0	30.2	30.6
105°	28.0	29.1	30.1	30.8	31.2	31.6	32.0	32.4
107.5°	34.2	33.2	32.1	31.8	32.1	32.5	32.9	33.3
110°	55.5	46.1	36.6	32.1	32.4	32.9	33.3	33.6



TEST NUMBER: P331390-930

CATALOG NUMBER: SA2XXDIP-C865D530U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	118.8	84.3	49.8	32.8	33.0	33.3	33.7	33.9
115°	175.0	131.2	87.4	62.1	55.3	48.5	41.7	34.9
117.5°	269.6	259.0	248.4	232.0	209.5	187.2	164.9	142.4
120°	314.1	315.3	316.4	310.6	297.8	285.1	272.3	259.5
122.5°	333.3	334.0	334.7	333.8	331.3	328.8	326.4	323.8
125°	360.9	361.5	362.2	362.6	363.0	363.2	363.5	363.8
127.5°	386.3	387.3	388.2	388.7	388.8	388.9	388.9	389.0
130°	402.4	403.5	404.6	405.0	404.9	404.8	404.7	404.6
132.5°	418.2	419.1	420.0	420.3	420.2	420.1	420.0	420.0
135°	440.6	441.5	442.5	442.9	442.6	442.5	442.3	442.1
137.5°	461.4	462.3	463.3	463.5	463.2	462.8	462.6	462.3
140°	474.8	475.6	476.5	476.7	476.2	475.8	475.3	474.8
142.5°	487.3	488.0	488.9	489.0	488.5	488.0	487.5	487.1
145°	504.7	505.3	506.0	506.1	505.6	505.2	504.7	504.2
147.5°	519.8	520.3	520.8	520.8	520.5	520.1	519.7	519.3
150°	529.1	529.7	530.3	530.4	529.9	529.4	528.9	528.5
152.5°	537.7	538.3	538.8	538.7	538.2	537.5	536.9	536.3
155°	549.2	549.8	550.3	550.2	549.4	548.7	548.0	547.1
157.5°	558.8	559.5	560.1	560.1	559.3	558.6	557.8	557.1
160°	564.4	565.0	565.6	565.6	564.9	564.3	563.5	562.9
162.5°	569.7	570.4	571.0	571.0	570.1	569.3	568.5	567.7
165°	576.2	576.8	577.5	577.5	576.8	576.2	575.5	574.8
167.5°	581.5	582.2	582.9	582.8	581.9	581.1	580.2	579.4
170°	584.2	584.9	585.5	585.5	584.6	583.8	582.9	582.0
172.5°	586.3	586.9	587.6	587.5	586.7	585.8	585.0	584.1
175°	588.5	589.1	589.8	589.7	588.7	587.7	586.9	585.9
177.5°	588.7	589.3	589.8	589.7	589.1	588.3	587.7	587.0
180°	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0

(END OF REPORT)