

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333545-940

Luminaire Tested: **S125RDIP-S610D1205U940-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333545-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S610D1205U940-4F0-1E-UDD-A1
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1205 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5856.3 lumens
Efficiency: N/A
Efficacy: 118.5 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 49.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333545-940

CATALOG NUMBER: S125RDIP-S610D1205U940-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P333545-940

CATALOG NUMBER: S125RDIP-S610D1205U940-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44	37
1	95	91	87	84	86	83	79	77	67	65	63	52	51	50	39	38	38	31
2	87	80	74	69	78	73	68	63	59	55	52	46	44	42	35	33	32	27
3	79	70	63	58	72	64	58	53	52	48	44	41	38	36	31	29	28	23
4	73	62	55	49	66	57	50	45	46	42	38	37	33	31	28	26	24	20
5	67	55	48	42	60	51	44	39	42	37	33	33	30	27	25	23	21	17
6	61	50	42	36	55	45	39	34	37	32	29	30	26	23	23	20	18	15
7	57	45	37	32	51	41	34	30	34	29	25	27	23	21	21	18	16	14
8	53	41	33	28	48	37	31	26	31	26	22	25	21	18	19	17	15	12
9	49	37	30	25	44	34	28	23	28	23	20	23	19	17	18	15	13	11
10	46	34	27	22	41	31	25	21	26	21	18	21	17	15	16	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	5329	5329	5329	5329
5°	6131	5336	4713	5336
10°	7033	5309	4158	5309
15°	7596	5255	3697	5255
20°	8377	5192	3413	5192
25°	9694	5108	3167	5108
30°	10549	5020	3006	5020
35°	8898	4917	2858	4917
40°	6214	4731	2731	4731
45°	4610	4483	2606	4483
50°	3676	4224	2498	4224
55°	3120	3902	2403	3902
60°	2696	3614	2250	3614
65°	2402	3304	1936	3304
70°	2111	3025	1766	3025
75°	1827	2620	1657	2620
80°	1387	2205	1387	2205
85°	1156	1734	1312	1734



TEST NUMBER: P333545-940

CATALOG NUMBER: S125RDIP-S610D1205U940-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	79.1	1.4
10°-20°	231.9	4.0
20°-30°	367.7	6.3
30°-40°	443.4	7.6
40°-50°	396.0	6.8
50°-60°	303.6	5.2
60°-70°	197.3	3.4
70°-80°	95.9	1.6
80°-90°	25.8	0.4
90°-100°	89.2	1.5
100°-110°	263.4	4.5
110°-120°	446.1	7.6
120°-130°	587.0	10.0
130°-140°	657.8	11.2
140°-150°	644.7	11.0
150°-160°	541.5	9.2
160°-170°	359.9	6.1
170°-180°	126.0	2.2
0°-30°	678.7	11.6
0°-40°	1122.1	19.2
0°-60°	1821.7	31.1
0°-90°	2140.8	36.6
90°-120°	798.6	13.6
90°-150°	2688.1	45.9
90°-180°	3716.0	63.5
0°-180°	5856.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	825	825	825	825	825	
5°	946	823	727	823	946	94
15°	1136	786	553	786	1136	326
25°	1360	717	444	717	1360	625
35°	1129	624	362	624	1129	682
45°	505	491	285	491	505	403
55°	277	346	213	346	277	251
65°	157	216	127	216	157	156
75°	73	105	66	105	73	78
85°	16	23	18	23	16	19
90°	25	1	25	1	25	15
95°	89	67	89	67	89	91
105°	257	236	257	236	257	272
115°	451	447	451	447	451	446
125°	656	652	656	652	656	586
135°	851	848	851	848	851	656
145°	1031	1027	1031	1027	1031	644
155°	1175	1175	1175	1175	1175	541
165°	1274	1278	1274	1278	1274	359
175°	1323	1328	1323	1328	1323	126
180°	1332	1332	1332	1332	1332	



TEST NUMBER: P333545-940

CATALOG NUMBER: S125RDIP-S610D1205U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2
2.5°	868.0	867.5	868.5	865.5	865.9	861.2	861.2	857.6	853.1	849.5	847.9
5°	945.7	946.5	945.0	940.0	936.6	931.5	925.8	915.6	907.1	899.0	892.6
7.5°	1025.8	1026.3	1021.8	1020.3	1011.7	1005.5	992.7	978.9	966.6	951.0	939.1
10°	1072.5	1072.1	1067.4	1063.6	1056.1	1046.7	1034.1	1017.9	1002.6	985.7	969.5
12.5°	1099.6	1098.7	1097.2	1092.6	1085.7	1077.3	1066.7	1050.7	1031.9	1013.3	994.4
15°	1136.1	1133.7	1129.4	1123.6	1113.7	1103.9	1092.1	1077.9	1059.9	1038.9	1021.3
17.5°	1181.3	1181.4	1174.7	1166.7	1153.3	1136.0	1117.7	1094.8	1070.3	1047.2	1028.5
20°	1218.8	1217.7	1210.9	1195.4	1180.2	1158.5	1137.5	1109.4	1079.6	1049.4	1026.0
22.5°	1272.4	1269.8	1262.8	1242.2	1218.6	1190.7	1158.6	1124.3	1088.2	1054.0	1023.3
25°	1360.4	1358.3	1344.4	1320.7	1287.5	1244.5	1202.5	1155.4	1103.6	1058.5	1021.3
27.5°	1420.5	1418.3	1408.0	1388.3	1357.6	1312.4	1255.5	1192.7	1127.9	1066.0	1012.2
30°	1414.5	1419.6	1418.3	1409.2	1386.1	1345.4	1293.0	1222.2	1145.2	1072.5	1008.4
32.5°	1329.5	1334.0	1345.9	1363.9	1365.2	1349.0	1309.7	1244.4	1164.8	1081.9	1005.4
35°	1128.6	1134.8	1157.8	1194.0	1241.4	1281.1	1289.2	1254.0	1182.5	1093.4	1000.9
37.5°	867.7	901.1	920.4	958.6	1030.2	1103.1	1173.2	1199.1	1168.7	1088.7	993.7
40°	737.1	745.2	779.8	822.8	883.1	958.9	1058.9	1131.0	1133.4	1077.9	982.3
42.5°	630.9	641.1	664.9	699.2	750.8	826.7	929.9	1025.1	1069.2	1048.0	967.4
45°	504.7	512.5	529.8	556.2	595.8	658.5	747.3	857.4	944.8	978.9	927.5
47.5°	414.6	418.8	433.8	454.0	483.3	529.0	597.6	693.2	798.1	871.6	864.3
50°	365.9	370.6	382.1	397.3	422.0	460.7	515.6	595.1	703.2	793.0	810.9
52.5°	327.9	331.8	339.0	353.5	373.8	403.5	447.8	519.9	617.1	712.5	754.0
55°	277.1	279.8	285.5	293.6	310.0	331.3	369.5	419.4	497.9	594.1	655.1
57.5°	235.2	236.6	240.2	247.7	259.0	274.6	302.2	344.5	400.8	487.4	554.7
60°	208.7	210.0	214.7	219.8	228.6	242.9	264.6	294.0	348.2	419.7	487.8
62.5°	187.5	188.3	190.4	195.5	203.1	214.2	231.2	255.3	298.4	361.1	425.4
65°	157.2	157.5	158.2	162.3	167.0	175.1	186.3	203.2	235.8	283.2	340.1
67.5°	128.0	128.5	130.9	132.3	137.2	141.5	148.1	161.0	184.0	215.9	260.1
70°	111.8	111.5	113.8	115.5	117.2	122.3	126.7	137.1	151.4	175.8	212.8
72.5°	96.6	95.8	96.8	97.4	99.6	103.1	107.5	113.9	124.8	141.7	169.9
75°	73.2	73.5	73.5	74.2	75.9	77.2	78.6	81.9	88.1	99.2	114.5
77.5°	51.4	50.8	52.3	52.4	53.4	54.9	56.1	57.4	59.9	64.6	72.4
80°	37.3	37.3	37.6	38.6	38.3	39.0	40.7	42.0	45.0	47.8	50.5
82.5°	28.6	28.4	28.6	28.9	28.8	29.4	30.1	30.3	31.5	32.8	34.8
85°	15.6	15.6	16.0	16.0	16.2	16.2	16.6	16.6	16.6	16.9	17.3
87.5°	11.0	10.5	10.1	10.0	10.1	10.4	10.0	9.5	9.3	9.0	8.9
90°	24.9	24.2	23.5	22.8	22.1	21.2	20.1	18.9	17.7	16.6	15.0
92.5°	48.9	48.4	47.9	47.3	46.9	45.8	44.3	42.8	41.3	39.8	37.8
95°	89.1	88.6	88.2	87.7	87.3	86.2	84.6	83.0	81.4	79.8	77.5
97.5°	135.1	134.8	134.6	134.3	134.0	133.1	131.6	130.1	128.6	127.1	123.9
100°	170.0	169.5	169.0	168.5	168.1	166.8	164.8	162.6	160.6	158.5	155.5
102.5°	204.7	204.1	203.5	202.9	202.2	200.7	198.5	196.2	193.9	191.7	190.2
105°	257.0	256.3	255.6	254.9	254.2	253.2	251.8	250.4	249.1	247.6	246.3
107.5°	310.4	310.5	310.6	310.6	310.7	310.3	309.6	308.9	308.3	307.6	306.5
110°	350.3	350.4	350.7	350.9	351.2	350.9	350.3	349.6	348.8	348.1	347.5



TEST NUMBER: P333545-940

CATALOG NUMBER: S125RDIP-S610D1205U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	389.2	389.6	390.0	390.5	390.8	390.9	390.6	390.3	389.9	389.6	388.7
115°	450.8	450.9	451.2	451.5	451.7	451.9	452.1	452.4	452.6	452.8	452.4
117.5°	510.9	511.8	512.7	513.6	514.5	514.9	514.7	514.5	514.3	514.2	513.7
120°	552.3	553.2	554.1	555.1	556.0	556.4	556.4	556.4	556.4	556.4	556.2
122.5°	593.8	594.5	595.2	595.9	596.7	597.2	597.4	597.5	597.7	597.9	597.3
125°	655.9	656.1	656.4	656.7	656.8	657.2	657.6	658.1	658.5	659.1	658.8
127.5°	715.6	716.0	716.5	717.0	717.5	717.8	718.0	718.3	718.5	718.7	718.5
130°	755.4	755.8	756.3	756.8	757.2	757.6	757.8	758.0	758.3	758.5	758.0
132.5°	792.7	793.4	794.0	794.6	795.3	795.7	795.9	796.2	796.4	796.7	796.7
135°	850.7	851.7	852.6	853.5	854.4	854.9	854.9	854.9	854.9	854.9	854.6
137.5°	907.5	908.7	909.8	911.0	912.1	912.6	912.3	912.0	911.7	911.4	911.0
140°	944.0	945.1	946.3	947.4	948.6	949.0	948.5	948.0	947.5	947.1	946.4
142.5°	978.8	980.0	981.1	982.2	983.4	983.8	983.6	983.3	983.0	982.8	981.9
145°	1031.0	1031.7	1032.4	1033.1	1033.8	1034.1	1034.1	1034.1	1034.1	1034.1	1033.4
147.5°	1075.6	1077.2	1078.7	1080.3	1081.8	1082.4	1081.8	1081.3	1080.7	1080.1	1079.6
150°	1108.8	1109.2	1109.6	1110.1	1110.6	1110.8	1110.8	1110.8	1110.8	1110.8	1109.9
152.5°	1136.1	1136.9	1137.7	1138.6	1139.4	1139.5	1139.0	1138.4	1137.9	1137.4	1137.0
155°	1175.1	1176.3	1177.3	1178.5	1179.6	1179.8	1178.8	1177.9	1177.1	1176.1	1175.9
157.5°	1207.6	1209.2	1210.7	1212.2	1213.7	1214.0	1213.1	1212.1	1211.2	1210.3	1210.1
160°	1230.0	1231.1	1232.3	1233.4	1234.6	1234.7	1233.8	1232.9	1231.9	1231.0	1230.8
162.5°	1249.0	1250.4	1251.7	1253.0	1254.4	1254.5	1253.4	1252.3	1251.2	1250.1	1250.0
165°	1274.5	1275.9	1277.3	1278.7	1280.1	1280.3	1279.3	1278.4	1277.6	1276.6	1276.4
167.5°	1294.9	1296.3	1297.7	1299.1	1300.6	1300.6	1299.2	1297.8	1296.5	1295.0	1295.0
170°	1305.6	1307.2	1308.9	1310.5	1312.1	1312.2	1310.8	1309.4	1308.1	1306.6	1306.6
172.5°	1314.7	1316.2	1317.6	1319.0	1320.4	1320.4	1319.1	1317.7	1316.3	1314.9	1314.9
175°	1323.2	1324.8	1326.5	1328.1	1329.7	1329.8	1328.4	1327.0	1325.6	1324.3	1324.3
177.5°	1328.2	1329.5	1330.8	1332.1	1333.4	1333.5	1332.4	1331.2	1330.2	1329.0	1329.2
180°	1331.5	1331.5	1331.5	1331.5	1331.5	1331.5	1331.5	1331.5	1331.5	1331.5	1331.5



TEST NUMBER: P333545-940

CATALOG NUMBER: S125RDIP-S610D1205U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2
2.5°	847.9	846.1	842.5	839.3	835.2	831.7	829.2	826.3	822.4	817.9	814.0
5°	885.5	878.0	868.2	859.7	848.9	840.4	831.6	823.1	814.7	803.8	794.3
7.5°	927.0	911.7	896.7	877.9	860.8	845.5	830.9	816.1	801.6	786.2	771.3
10°	952.5	933.9	913.2	889.5	867.8	847.2	828.2	809.6	790.0	772.7	754.0
12.5°	976.3	952.3	928.7	898.8	872.7	847.5	823.3	800.1	779.1	756.7	736.6
15°	997.9	974.2	947.8	911.2	874.9	844.5	816.0	785.9	759.8	734.7	712.4
17.5°	1006.2	981.4	950.7	915.5	875.9	837.6	800.9	767.9	737.2	707.9	682.8
20°	1003.0	978.9	947.4	913.9	871.6	831.6	791.9	755.4	721.1	690.4	663.6
22.5°	995.1	970.3	939.9	904.5	864.2	821.8	779.5	740.5	704.6	672.7	643.5
25°	983.4	949.5	918.3	883.8	845.5	803.5	759.8	716.8	678.5	646.0	614.1
27.5°	971.1	928.8	889.2	854.8	814.4	776.9	734.8	690.7	650.4	617.3	584.7
30°	960.0	912.6	868.9	829.9	791.7	756.1	716.0	673.1	631.8	597.5	564.4
32.5°	946.2	895.7	847.7	802.8	765.9	730.6	694.4	653.3	613.1	577.7	544.0
35°	928.8	864.4	812.3	764.6	723.5	689.3	656.8	623.6	583.3	546.7	513.9
37.5°	906.1	833.0	772.7	720.6	677.4	643.0	617.4	587.0	550.3	515.2	484.7
40°	892.2	810.3	744.2	692.7	647.3	611.1	587.0	561.2	527.7	494.9	464.4
42.5°	873.8	789.4	715.5	661.8	616.2	581.3	557.0	534.5	506.3	475.4	442.7
45°	837.7	748.9	671.4	613.8	567.8	533.5	510.8	490.8	469.5	441.0	412.6
47.5°	790.7	706.8	625.5	562.7	517.5	485.8	463.8	448.0	432.7	408.6	380.9
50°	753.0	672.1	592.8	531.8	483.8	453.5	432.9	420.4	406.4	384.5	361.4
52.5°	708.6	636.3	558.7	496.3	450.9	422.7	402.8	390.3	378.8	360.9	338.9
55°	638.6	575.2	504.0	447.5	405.8	377.4	358.4	346.5	339.7	324.5	307.2
57.5°	557.7	512.3	449.6	395.0	358.2	330.0	316.2	306.1	298.5	287.7	275.4
60°	501.3	469.5	413.2	361.4	327.5	300.8	288.3	279.8	272.7	263.5	254.0
62.5°	444.2	421.0	372.1	327.5	296.4	273.9	262.3	254.6	246.4	240.2	231.0
65°	367.6	346.9	313.0	278.1	249.3	231.4	222.9	216.2	211.1	204.3	197.8
67.5°	285.9	277.5	254.1	230.1	209.4	193.4	186.1	181.4	175.2	171.2	166.7
70°	235.8	231.7	215.1	199.2	179.9	169.1	162.3	160.2	152.8	148.7	145.6
72.5°	191.4	189.4	179.9	168.8	155.2	145.7	139.5	137.1	132.4	129.2	127.2
75°	131.1	131.8	130.1	123.0	117.9	111.8	106.4	105.0	101.7	98.9	97.2
77.5°	82.9	86.4	86.5	86.1	84.2	80.4	78.2	77.1	73.8	72.9	72.4
80°	56.9	60.6	64.0	63.7	63.0	62.0	60.3	59.3	57.6	56.5	55.9
82.5°	37.9	41.4	44.2	46.1	45.9	44.9	43.8	43.2	43.0	42.2	42.1
85°	17.9	18.6	19.6	22.0	23.7	24.1	23.7	23.4	22.4	22.7	23.0
87.5°	8.9	8.6	8.6	8.2	7.6	8.6	9.0	8.9	8.7	8.6	8.4
90°	13.4	11.8	10.2	8.4	6.6	4.7	2.9	1.1	2.9	4.7	6.6
92.5°	35.8	33.9	31.8	30.2	29.0	27.6	26.4	25.1	26.4	27.6	29.0
95°	75.2	72.9	70.5	69.2	68.8	68.3	67.8	67.3	67.8	68.3	68.8
97.5°	120.6	117.5	114.3	112.6	112.4	112.3	112.1	111.9	112.1	112.3	112.4
100°	152.6	149.5	146.6	145.1	145.1	145.1	145.1	145.1	145.1	145.1	145.1
102.5°	188.7	187.2	185.7	184.4	183.5	182.5	181.6	180.7	181.6	182.5	183.5
105°	244.9	243.5	242.1	240.9	239.7	238.5	237.4	236.2	237.4	238.5	239.7
107.5°	305.4	304.3	303.3	302.2	301.0	299.9	298.7	297.6	298.7	299.9	301.0
110°	346.8	346.1	345.4	344.5	343.3	342.1	341.0	339.9	341.0	342.1	343.3



TEST NUMBER: P333545-940

CATALOG NUMBER: S125RDIP-S610D1205U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	387.9	387.0	386.1	385.4	384.8	384.1	383.6	383.0	383.6	384.1	384.8
115°	451.9	451.5	450.9	450.3	449.3	448.4	447.5	446.6	447.5	448.4	449.3
117.5°	513.4	512.9	512.5	512.1	511.7	511.3	510.9	510.4	510.9	511.3	511.7
120°	556.0	555.7	555.5	554.8	553.7	552.5	551.3	550.2	551.3	552.5	553.7
122.5°	596.7	596.1	595.5	594.9	594.6	594.1	593.8	593.3	593.8	594.1	594.6
125°	658.5	658.4	658.1	657.3	655.9	654.5	653.2	651.8	653.2	654.5	655.9
127.5°	718.2	717.9	717.6	717.1	716.3	715.5	714.7	714.0	714.7	715.5	716.3
130°	757.6	757.2	756.7	755.8	754.7	753.6	752.4	751.3	752.4	753.6	754.7
132.5°	796.8	796.9	797.0	796.1	794.2	792.4	790.4	788.5	790.4	792.4	794.2
135°	854.4	854.2	854.0	853.2	851.8	850.4	849.0	847.7	849.0	850.4	851.8
137.5°	910.4	909.9	909.5	908.5	907.1	905.8	904.5	903.1	904.5	905.8	907.1
140°	945.7	945.0	944.3	943.4	942.3	941.1	940.0	938.8	940.0	941.1	942.3
142.5°	981.0	980.1	979.3	978.3	977.3	976.4	975.4	974.5	975.4	976.4	977.3
145°	1032.8	1032.1	1031.4	1030.6	1029.7	1028.8	1027.8	1026.9	1027.8	1028.8	1029.7
147.5°	1079.1	1078.5	1077.9	1077.4	1076.9	1076.4	1075.8	1075.4	1075.8	1076.4	1076.9
150°	1108.9	1108.0	1107.1	1106.8	1107.1	1107.2	1107.5	1107.7	1107.5	1107.2	1107.1
152.5°	1136.6	1136.2	1135.9	1135.5	1135.2	1134.9	1134.5	1134.3	1134.5	1134.9	1135.2
155°	1175.6	1175.5	1175.2	1175.1	1175.1	1175.1	1175.1	1175.1	1175.1	1175.1	1175.1
157.5°	1209.9	1209.6	1209.3	1209.5	1210.1	1210.5	1211.0	1211.6	1211.0	1210.5	1210.1
160°	1230.6	1230.3	1230.1	1230.3	1231.0	1231.7	1232.4	1233.1	1232.4	1231.7	1231.0
162.5°	1250.0	1249.9	1249.9	1250.1	1250.6	1251.2	1251.7	1252.1	1251.7	1251.2	1250.6
165°	1276.1	1275.9	1275.7	1275.8	1276.3	1276.8	1277.2	1277.6	1277.2	1276.8	1276.3
167.5°	1295.0	1295.0	1295.0	1295.5	1296.5	1297.4	1298.2	1299.2	1298.2	1297.4	1296.5
170°	1306.6	1306.6	1306.6	1307.2	1308.1	1308.9	1309.9	1310.8	1309.9	1308.9	1308.1
172.5°	1314.9	1314.9	1314.9	1315.5	1316.3	1317.2	1318.2	1319.1	1318.2	1317.2	1316.3
175°	1324.3	1324.3	1324.3	1324.7	1325.6	1326.6	1327.5	1328.4	1327.5	1326.6	1325.6
177.5°	1329.5	1329.6	1329.8	1330.3	1331.0	1331.7	1332.5	1333.2	1332.5	1331.7	1331.0
180°	1331.5	1331.5	1331.5	1331.5	1331.5	1331.5	1331.5	1331.5	1331.5	1331.5	1331.5



TEST NUMBER: P333545-940

CATALOG NUMBER: S125RDIP-S610D1205U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2
2.5°	811.4	807.5	804.9	799.4	795.6	794.0	791.0	790.2	793.2	791.0	790.8
5°	787.2	777.4	769.6	761.8	753.3	748.0	739.8	738.4	736.4	733.3	732.7
7.5°	758.3	745.5	735.5	722.6	711.4	702.4	692.2	687.4	684.7	680.8	675.6
10°	738.8	723.5	710.0	697.1	683.2	672.1	661.9	654.1	649.0	644.3	642.2
12.5°	719.5	704.0	686.7	671.1	655.6	643.0	631.8	626.7	621.1	615.5	610.8
15°	689.6	669.0	650.1	632.0	618.8	605.3	594.5	587.0	578.5	576.2	567.0
17.5°	658.0	637.7	615.5	596.6	581.3	566.3	554.5	546.0	539.6	530.8	526.6
20°	638.2	614.1	592.5	575.2	558.2	540.6	528.4	521.3	515.2	508.1	504.7
22.5°	617.1	593.5	571.3	551.1	533.9	516.5	507.8	500.4	493.6	487.0	482.5
25°	586.0	562.3	539.0	517.9	500.0	487.4	477.2	468.8	465.1	458.6	453.9
27.5°	555.4	530.1	505.9	484.9	470.8	458.4	450.1	443.4	436.7	431.1	427.0
30°	535.6	509.8	483.4	466.8	451.8	440.1	430.9	424.5	419.4	414.3	411.3
32.5°	515.8	489.2	465.7	447.8	433.7	423.5	414.1	407.9	402.5	396.9	393.3
35°	484.0	456.9	438.0	420.4	406.4	397.0	390.6	381.7	377.4	373.3	369.5
37.5°	454.6	429.4	408.8	393.4	381.4	371.9	363.6	358.8	353.5	349.8	346.7
40°	432.9	409.8	391.3	375.0	366.1	355.7	347.9	341.8	337.7	333.0	329.6
42.5°	413.4	392.0	373.9	359.3	348.3	339.4	331.9	325.8	320.7	317.3	314.4
45°	385.8	364.4	346.9	333.3	323.2	314.7	306.9	303.8	297.0	293.0	291.7
47.5°	357.3	338.2	321.2	308.7	298.3	290.3	282.9	276.8	273.0	269.0	266.9
50°	338.0	319.8	303.8	291.7	281.5	272.7	265.9	261.8	256.7	253.1	250.3
52.5°	318.8	301.8	286.0	274.3	265.5	256.7	249.1	245.0	240.2	237.8	235.9
55°	291.3	273.4	259.8	248.3	239.2	231.0	223.9	219.8	216.8	214.5	213.7
57.5°	260.1	245.9	233.4	222.9	213.5	205.8	199.6	195.7	193.1	192.7	190.6
60°	239.8	226.9	215.4	204.3	196.1	189.0	183.6	179.2	176.5	176.1	175.5
62.5°	219.5	207.1	196.4	186.6	179.3	172.5	167.4	162.4	160.8	159.1	157.6
65°	189.3	178.2	169.3	161.6	153.8	148.0	142.9	139.9	136.2	134.1	130.5
67.5°	159.7	151.1	142.6	136.1	129.9	124.5	120.3	115.7	113.2	111.6	108.9
70°	140.3	133.5	125.0	117.9	113.2	108.7	105.3	100.2	98.5	97.2	95.9
72.5°	121.8	115.8	108.7	103.0	98.3	94.1	90.2	87.8	86.1	84.7	83.9
75°	95.9	90.1	84.0	79.9	76.6	73.2	71.2	69.5	68.8	68.4	67.1
77.5°	70.4	67.3	62.4	59.2	57.0	55.6	53.8	52.9	52.9	51.4	50.9
80°	53.9	52.2	48.1	46.7	45.0	43.7	42.7	41.0	39.3	38.6	37.6
82.5°	40.0	38.3	36.7	34.5	33.2	32.3	31.3	30.7	30.9	30.0	29.4
85°	21.3	19.6	19.0	18.6	17.9	18.6	18.3	17.9	17.7	17.3	17.7
87.5°	8.5	8.8	8.8	9.7	9.2	9.8	10.1	10.0	10.3	10.4	10.3
90°	8.4	10.2	11.8	13.4	15.0	16.6	17.7	18.9	20.1	21.2	22.1
92.5°	30.2	31.8	33.9	35.8	37.8	39.8	41.3	42.8	44.3	45.8	46.9
95°	69.2	70.5	72.9	75.2	77.5	79.8	81.4	83.0	84.6	86.2	87.3
97.5°	112.6	114.3	117.5	120.6	123.9	127.1	128.6	130.1	131.6	133.1	134.0
100°	145.1	146.6	149.5	152.6	155.5	158.5	160.6	162.6	164.8	166.8	168.1
102.5°	184.4	185.7	187.2	188.7	190.2	191.7	193.9	196.2	198.5	200.7	202.2
105°	240.9	242.1	243.5	244.9	246.3	247.6	249.1	250.4	251.8	253.2	254.2
107.5°	302.2	303.3	304.3	305.4	306.5	307.6	308.3	308.9	309.6	310.3	310.7
110°	344.5	345.4	346.1	346.8	347.5	348.1	348.8	349.6	350.3	350.9	351.2



TEST NUMBER: P333545-940

CATALOG NUMBER: S125RDIP-S610D1205U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	385.4	386.1	387.0	387.9	388.7	389.6	389.9	390.3	390.6	390.9	390.8
115°	450.3	450.9	451.5	451.9	452.4	452.8	452.6	452.4	452.1	451.9	451.7
117.5°	512.1	512.5	512.9	513.4	513.7	514.2	514.3	514.5	514.7	514.9	514.5
120°	554.8	555.5	555.7	556.0	556.2	556.4	556.4	556.4	556.4	556.4	556.0
122.5°	594.9	595.5	596.1	596.7	597.3	597.9	597.7	597.5	597.4	597.2	596.7
125°	657.3	658.1	658.4	658.5	658.8	659.1	658.5	658.1	657.6	657.2	656.8
127.5°	717.1	717.6	717.9	718.2	718.5	718.7	718.5	718.3	718.0	717.8	717.5
130°	755.8	756.7	757.2	757.6	758.0	758.5	758.3	758.0	757.8	757.6	757.2
132.5°	796.1	797.0	796.9	796.8	796.7	796.7	796.4	796.2	795.9	795.7	795.3
135°	853.2	854.0	854.2	854.4	854.6	854.9	854.9	854.9	854.9	854.9	854.4
137.5°	908.5	909.5	909.9	910.4	911.0	911.4	911.7	912.0	912.3	912.6	912.1
140°	943.4	944.3	945.0	945.7	946.4	947.1	947.5	948.0	948.5	949.0	948.6
142.5°	978.3	979.3	980.1	981.0	981.9	982.8	983.0	983.3	983.6	983.8	983.4
145°	1030.6	1031.4	1032.1	1032.8	1033.4	1034.1	1034.1	1034.1	1034.1	1034.1	1033.8
147.5°	1077.4	1077.9	1078.5	1079.1	1079.6	1080.1	1080.7	1081.3	1081.8	1082.4	1081.8
150°	1106.8	1107.1	1108.0	1108.9	1109.9	1110.8	1110.8	1110.8	1110.8	1110.8	1110.6
152.5°	1135.5	1135.9	1136.2	1136.6	1137.0	1137.4	1137.9	1138.4	1139.0	1139.5	1139.4
155°	1175.1	1175.2	1175.5	1175.6	1175.9	1176.1	1177.1	1177.9	1178.8	1179.8	1179.6
157.5°	1209.5	1209.3	1209.6	1209.9	1210.1	1210.3	1211.2	1212.1	1213.1	1214.0	1213.7
160°	1230.3	1230.1	1230.3	1230.6	1230.8	1231.0	1231.9	1232.9	1233.8	1234.7	1234.6
162.5°	1250.1	1249.9	1249.9	1250.0	1250.0	1250.1	1251.2	1252.3	1253.4	1254.5	1254.4
165°	1275.8	1275.7	1275.9	1276.1	1276.4	1276.6	1277.6	1278.4	1279.3	1280.3	1280.1
167.5°	1295.5	1295.0	1295.0	1295.0	1295.0	1295.0	1296.5	1297.8	1299.2	1300.6	1300.6
170°	1307.2	1306.6	1306.6	1306.6	1306.6	1306.6	1308.1	1309.4	1310.8	1312.2	1312.1
172.5°	1315.5	1314.9	1314.9	1314.9	1314.9	1314.9	1316.3	1317.7	1319.1	1320.4	1320.4
175°	1324.7	1324.3	1324.3	1324.3	1324.3	1324.3	1325.6	1327.0	1328.4	1329.8	1329.7
177.5°	1330.3	1329.8	1329.6	1329.5	1329.2	1329.0	1330.2	1331.2	1332.4	1333.5	1333.4
180°	1331.5	1331.5	1331.5	1331.5	1331.5	1331.5	1331.5	1331.5	1331.5	1331.5	1331.5



TEST NUMBER: P333545-940

CATALOG NUMBER: S125RDIP-S610D1205U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2
2.5°	790.5	787.5	786.7	787.7	786.7	787.5	790.5	790.8	791.0	793.2	790.2
5°	729.3	725.9	727.6	726.9	727.6	725.9	729.3	732.7	733.3	736.4	738.4
7.5°	675.5	671.3	666.8	668.2	666.8	671.3	675.5	675.6	680.8	684.7	687.4
10°	637.8	634.5	632.4	634.1	632.4	634.5	637.8	642.2	644.3	649.0	654.1
12.5°	606.1	604.1	602.4	601.6	602.4	604.1	606.1	610.8	615.5	621.1	626.7
15°	562.9	558.9	557.2	552.9	557.2	558.9	562.9	567.0	576.2	578.5	587.0
17.5°	523.2	521.8	517.5	515.6	517.5	521.8	523.2	526.6	530.8	539.6	546.0
20°	499.6	498.3	493.9	496.6	493.9	498.3	499.6	504.7	508.1	515.2	521.3
22.5°	480.1	477.2	475.7	474.9	475.7	477.2	480.1	482.5	487.0	493.6	500.4
25°	452.5	448.2	446.5	444.4	446.5	448.2	452.5	453.9	458.6	465.1	468.8
27.5°	425.1	422.7	420.4	419.9	420.4	422.7	425.1	427.0	431.1	436.7	443.4
30°	407.2	404.7	403.1	403.1	403.1	404.7	407.2	411.3	414.3	419.4	424.5
32.5°	391.2	389.3	387.6	387.4	387.6	389.3	391.2	393.3	396.9	402.5	407.9
35°	367.8	365.2	364.4	362.5	364.4	365.2	367.8	369.5	373.3	377.4	381.7
37.5°	343.7	341.4	341.3	341.2	341.3	341.4	343.7	346.7	349.8	353.5	358.8
40°	328.2	326.5	326.2	323.9	326.2	326.5	328.2	329.6	333.0	337.7	341.8
42.5°	311.7	310.9	309.7	308.6	309.7	310.9	311.7	314.4	317.3	320.7	325.8
45°	289.3	287.0	287.0	285.3	287.0	287.0	289.3	291.7	293.0	297.0	303.8
47.5°	266.1	264.3	264.5	262.7	264.5	264.3	266.1	266.9	269.0	273.0	276.8
50°	250.7	249.7	249.3	248.6	249.3	249.7	250.7	250.3	253.1	256.7	261.8
52.5°	235.2	234.8	236.0	234.5	236.0	234.8	235.2	235.9	237.8	240.2	245.0
55°	214.5	213.4	215.4	213.4	215.4	213.4	214.5	213.7	214.5	216.8	219.8
57.5°	190.5	189.6	191.4	190.4	191.4	189.6	190.5	190.6	192.7	193.1	195.7
60°	174.8	172.7	173.8	174.2	173.8	172.7	174.8	175.5	176.1	176.5	179.2
62.5°	156.0	154.9	155.6	154.1	155.6	154.9	156.0	157.6	159.1	160.8	162.4
65°	129.7	128.8	127.3	126.7	127.3	128.8	129.7	130.5	134.1	136.2	139.9
67.5°	109.0	106.6	106.5	107.0	106.5	106.6	109.0	108.9	111.6	113.2	115.7
70°	93.8	93.8	93.5	93.5	93.5	93.8	93.8	95.9	97.2	98.5	100.2
72.5°	83.3	83.0	82.4	82.1	82.4	83.0	83.3	83.9	84.7	86.1	87.8
75°	67.1	67.4	66.7	66.4	66.7	67.4	67.1	67.1	68.4	68.8	69.5
77.5°	49.5	48.1	48.9	48.1	48.9	48.1	49.5	50.9	51.4	52.9	52.9
80°	37.6	37.3	38.3	37.3	38.3	37.3	37.6	37.6	38.6	39.3	41.0
82.5°	29.8	29.4	29.9	29.2	29.9	29.4	29.8	29.4	30.0	30.9	30.7
85°	17.9	17.7	17.3	17.7	17.3	17.7	17.9	17.7	17.3	17.7	17.9
87.5°	10.8	10.7	10.8	11.0	10.8	10.7	10.8	10.3	10.4	10.3	10.0
90°	22.8	23.5	24.2	24.9	24.2	23.5	22.8	22.1	21.2	20.1	18.9
92.5°	47.3	47.9	48.4	48.9	48.4	47.9	47.3	46.9	45.8	44.3	42.8
95°	87.7	88.2	88.6	89.1	88.6	88.2	87.7	87.3	86.2	84.6	83.0
97.5°	134.3	134.6	134.8	135.1	134.8	134.6	134.3	134.0	133.1	131.6	130.1
100°	168.5	169.0	169.5	170.0	169.5	169.0	168.5	168.1	166.8	164.8	162.6
102.5°	202.9	203.5	204.1	204.7	204.1	203.5	202.9	202.2	200.7	198.5	196.2
105°	254.9	255.6	256.3	257.0	256.3	255.6	254.9	254.2	253.2	251.8	250.4
107.5°	310.6	310.6	310.5	310.4	310.5	310.6	310.6	310.7	310.3	309.6	308.9
110°	350.9	350.7	350.4	350.3	350.4	350.7	350.9	351.2	350.9	350.3	349.6



TEST NUMBER: P333545-940

CATALOG NUMBER: S125RDIP-S610D1205U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	390.5	390.0	389.6	389.2	389.6	390.0	390.5	390.8	390.9	390.6	390.3
115°	451.5	451.2	450.9	450.8	450.9	451.2	451.5	451.7	451.9	452.1	452.4
117.5°	513.6	512.7	511.8	510.9	511.8	512.7	513.6	514.5	514.9	514.7	514.5
120°	555.1	554.1	553.2	552.3	553.2	554.1	555.1	556.0	556.4	556.4	556.4
122.5°	595.9	595.2	594.5	593.8	594.5	595.2	595.9	596.7	597.2	597.4	597.5
125°	656.7	656.4	656.1	655.9	656.1	656.4	656.7	656.8	657.2	657.6	658.1
127.5°	717.0	716.5	716.0	715.6	716.0	716.5	717.0	717.5	717.8	718.0	718.3
130°	756.8	756.3	755.8	755.4	755.8	756.3	756.8	757.2	757.6	757.8	758.0
132.5°	794.6	794.0	793.4	792.7	793.4	794.0	794.6	795.3	795.7	795.9	796.2
135°	853.5	852.6	851.7	850.7	851.7	852.6	853.5	854.4	854.9	854.9	854.9
137.5°	911.0	909.8	908.7	907.5	908.7	909.8	911.0	912.1	912.6	912.3	912.0
140°	947.4	946.3	945.1	944.0	945.1	946.3	947.4	948.6	949.0	948.5	948.0
142.5°	982.2	981.1	980.0	978.8	980.0	981.1	982.2	983.4	983.8	983.6	983.3
145°	1033.1	1032.4	1031.7	1031.0	1031.7	1032.4	1033.1	1033.8	1034.1	1034.1	1034.1
147.5°	1080.3	1078.7	1077.2	1075.6	1077.2	1078.7	1080.3	1081.8	1082.4	1081.8	1081.3
150°	1110.1	1109.6	1109.2	1108.8	1109.2	1109.6	1110.1	1110.6	1110.8	1110.8	1110.8
152.5°	1138.6	1137.7	1136.9	1136.1	1136.9	1137.7	1138.6	1139.4	1139.5	1139.0	1138.4
155°	1178.5	1177.3	1176.3	1175.1	1176.3	1177.3	1178.5	1179.6	1179.8	1178.8	1177.9
157.5°	1212.2	1210.7	1209.2	1207.6	1209.2	1210.7	1212.2	1213.7	1214.0	1213.1	1212.1
160°	1233.4	1232.3	1231.1	1230.0	1231.1	1232.3	1233.4	1234.6	1234.7	1233.8	1232.9
162.5°	1253.0	1251.7	1250.4	1249.0	1250.4	1251.7	1253.0	1254.4	1254.5	1253.4	1252.3
165°	1278.7	1277.3	1275.9	1274.5	1275.9	1277.3	1278.7	1280.1	1280.3	1279.3	1278.4
167.5°	1299.1	1297.7	1296.3	1294.9	1296.3	1297.7	1299.1	1300.6	1300.6	1299.2	1297.8
170°	1310.5	1308.9	1307.2	1305.6	1307.2	1308.9	1310.5	1312.1	1312.2	1310.8	1309.4
172.5°	1319.0	1317.6	1316.2	1314.7	1316.2	1317.6	1319.0	1320.4	1320.4	1319.1	1317.7
175°	1328.1	1326.5	1324.8	1323.2	1324.8	1326.5	1328.1	1329.7	1329.8	1328.4	1327.0
177.5°	1332.1	1330.8	1329.5	1328.2	1329.5	1330.8	1332.1	1333.4	1333.5	1332.4	1331.2
180°	1331.5	1331.5	1331.5	1331.5	1331.5	1331.5	1331.5	1331.5	1331.5	1331.5	1331.5



TEST NUMBER: P333545-940

CATALOG NUMBER: S125RDIP-S610D1205U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2
2.5°	791.0	794.0	795.6	799.4	804.9	807.5	811.4	814.0	817.9	822.4	826.3
5°	739.8	748.0	753.3	761.8	769.6	777.4	787.2	794.3	803.8	814.7	823.1
7.5°	692.2	702.4	711.4	722.6	735.5	745.5	758.3	771.3	786.2	801.6	816.1
10°	661.9	672.1	683.2	697.1	710.0	723.5	738.8	754.0	772.7	790.0	809.6
12.5°	631.8	643.0	655.6	671.1	686.7	704.0	719.5	736.6	756.7	779.1	800.1
15°	594.5	605.3	618.8	632.0	650.1	669.0	689.6	712.4	734.7	759.8	785.9
17.5°	554.5	566.3	581.3	596.6	615.5	637.7	658.0	682.8	707.9	737.2	767.9
20°	528.4	540.6	558.2	575.2	592.5	614.1	638.2	663.6	690.4	721.1	755.4
22.5°	507.8	516.5	533.9	551.1	571.3	593.5	617.1	643.5	672.7	704.6	740.5
25°	477.2	487.4	500.0	517.9	539.0	562.3	586.0	614.1	646.0	678.5	716.8
27.5°	450.1	458.4	470.8	484.9	505.9	530.1	555.4	584.7	617.3	650.4	690.7
30°	430.9	440.1	451.8	466.8	483.4	509.8	535.6	564.4	597.5	631.8	673.1
32.5°	414.1	423.5	433.7	447.8	465.7	489.2	515.8	544.0	577.7	613.1	653.3
35°	390.6	397.0	406.4	420.4	438.0	456.9	484.0	513.9	546.7	583.3	623.6
37.5°	363.6	371.9	381.4	393.4	408.8	429.4	454.6	484.7	515.2	550.3	587.0
40°	347.9	355.7	366.1	375.0	391.3	409.8	432.9	464.4	494.9	527.7	561.2
42.5°	331.9	339.4	348.3	359.3	373.9	392.0	413.4	442.7	475.4	506.3	534.5
45°	306.9	314.7	323.2	333.3	346.9	364.4	385.8	412.6	441.0	469.5	490.8
47.5°	282.9	290.3	298.3	308.7	321.2	338.2	357.3	380.9	408.6	432.7	448.0
50°	265.9	272.7	281.5	291.7	303.8	319.8	338.0	361.4	384.5	406.4	420.4
52.5°	249.1	256.7	265.5	274.3	286.0	301.8	318.8	338.9	360.9	378.8	390.3
55°	223.9	231.0	239.2	248.3	259.8	273.4	291.3	307.2	324.5	339.7	346.5
57.5°	199.6	205.8	213.5	222.9	233.4	245.9	260.1	275.4	287.7	298.5	306.1
60°	183.6	189.0	196.1	204.3	215.4	226.9	239.8	254.0	263.5	272.7	279.8
62.5°	167.4	172.5	179.3	186.6	196.4	207.1	219.5	231.0	240.2	246.4	254.6
65°	142.9	148.0	153.8	161.6	169.3	178.2	189.3	197.8	204.3	211.1	216.2
67.5°	120.3	124.5	129.9	136.1	142.6	151.1	159.7	166.7	171.2	175.2	181.4
70°	105.3	108.7	113.2	117.9	125.0	133.5	140.3	145.6	148.7	152.8	160.2
72.5°	90.2	94.1	98.3	103.0	108.7	115.8	121.8	127.2	129.2	132.4	137.1
75°	71.2	73.2	76.6	79.9	84.0	90.1	95.9	97.2	98.9	101.7	105.0
77.5°	53.8	55.6	57.0	59.2	62.4	67.3	70.4	72.4	72.9	73.8	77.1
80°	42.7	43.7	45.0	46.7	48.1	52.2	53.9	55.9	56.5	57.6	59.3
82.5°	31.3	32.3	33.2	34.5	36.7	38.3	40.0	42.1	42.2	43.0	43.2
85°	18.3	18.6	17.9	18.6	19.0	19.6	21.3	23.0	22.7	22.4	23.4
87.5°	10.1	9.8	9.2	9.7	8.8	8.8	8.5	8.4	8.6	8.7	8.9
90°	17.7	16.6	15.0	13.4	11.8	10.2	8.4	6.6	4.7	2.9	1.1
92.5°	41.3	39.8	37.8	35.8	33.9	31.8	30.2	29.0	27.6	26.4	25.1
95°	81.4	79.8	77.5	75.2	72.9	70.5	69.2	68.8	68.3	67.8	67.3
97.5°	128.6	127.1	123.9	120.6	117.5	114.3	112.6	112.4	112.3	112.1	111.9
100°	160.6	158.5	155.5	152.6	149.5	146.6	145.1	145.1	145.1	145.1	145.1
102.5°	193.9	191.7	190.2	188.7	187.2	185.7	184.4	183.5	182.5	181.6	180.7
105°	249.1	247.6	246.3	244.9	243.5	242.1	240.9	239.7	238.5	237.4	236.2
107.5°	308.3	307.6	306.5	305.4	304.3	303.3	302.2	301.0	299.9	298.7	297.6
110°	348.8	348.1	347.5	346.8	346.1	345.4	344.5	343.3	342.1	341.0	339.9



TEST NUMBER: P333545-940

CATALOG NUMBER: S125RDIP-S610D1205U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	389.9	389.6	388.7	387.9	387.0	386.1	385.4	384.8	384.1	383.6	383.0
115°	452.6	452.8	452.4	451.9	451.5	450.9	450.3	449.3	448.4	447.5	446.6
117.5°	514.3	514.2	513.7	513.4	512.9	512.5	512.1	511.7	511.3	510.9	510.4
120°	556.4	556.4	556.2	556.0	555.7	555.5	554.8	553.7	552.5	551.3	550.2
122.5°	597.7	597.9	597.3	596.7	596.1	595.5	594.9	594.6	594.1	593.8	593.3
125°	658.5	659.1	658.8	658.5	658.4	658.1	657.3	655.9	654.5	653.2	651.8
127.5°	718.5	718.7	718.5	718.2	717.9	717.6	717.1	716.3	715.5	714.7	714.0
130°	758.3	758.5	758.0	757.6	757.2	756.7	755.8	754.7	753.6	752.4	751.3
132.5°	796.4	796.7	796.7	796.8	796.9	797.0	796.1	794.2	792.4	790.4	788.5
135°	854.9	854.9	854.6	854.4	854.2	854.0	853.2	851.8	850.4	849.0	847.7
137.5°	911.7	911.4	911.0	910.4	909.9	909.5	908.5	907.1	905.8	904.5	903.1
140°	947.5	947.1	946.4	945.7	945.0	944.3	943.4	942.3	941.1	940.0	938.8
142.5°	983.0	982.8	981.9	981.0	980.1	979.3	978.3	977.3	976.4	975.4	974.5
145°	1034.1	1034.1	1033.4	1032.8	1032.1	1031.4	1030.6	1029.7	1028.8	1027.8	1026.9
147.5°	1080.7	1080.1	1079.6	1079.1	1078.5	1077.9	1077.4	1076.9	1076.4	1075.8	1075.4
150°	1110.8	1110.8	1109.9	1108.9	1108.0	1107.1	1106.8	1107.1	1107.2	1107.5	1107.7
152.5°	1137.9	1137.4	1137.0	1136.6	1136.2	1135.9	1135.5	1135.2	1134.9	1134.5	1134.3
155°	1177.1	1176.1	1175.9	1175.6	1175.5	1175.2	1175.1	1175.1	1175.1	1175.1	1175.1
157.5°	1211.2	1210.3	1210.1	1209.9	1209.6	1209.3	1209.5	1210.1	1210.5	1211.0	1211.6
160°	1231.9	1231.0	1230.8	1230.6	1230.3	1230.1	1230.3	1231.0	1231.7	1232.4	1233.1
162.5°	1251.2	1250.1	1250.0	1250.0	1249.9	1249.9	1250.1	1250.6	1251.2	1251.7	1252.1
165°	1277.6	1276.6	1276.4	1276.1	1275.9	1275.7	1275.8	1276.3	1276.8	1277.2	1277.6
167.5°	1296.5	1295.0	1295.0	1295.0	1295.0	1295.0	1295.5	1296.5	1297.4	1298.2	1299.2
170°	1308.1	1306.6	1306.6	1306.6	1306.6	1306.6	1307.2	1308.1	1308.9	1309.9	1310.8
172.5°	1316.3	1314.9	1314.9	1314.9	1314.9	1314.9	1315.5	1316.3	1317.2	1318.2	1319.1
175°	1325.6	1324.3	1324.3	1324.3	1324.3	1324.3	1324.7	1325.6	1326.6	1327.5	1328.4
177.5°	1330.2	1329.0	1329.2	1329.5	1329.6	1329.8	1330.3	1331.0	1331.7	1332.5	1333.2
180°	1331.5	1331.5	1331.5	1331.5	1331.5	1331.5	1331.5	1331.5	1331.5	1331.5	1331.5



TEST NUMBER: P333545-940

CATALOG NUMBER: S125RDIP-S610D1205U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2
2.5°	829.2	831.7	835.2	839.3	842.5	846.1	847.9	847.9	849.5	853.1	857.6
5°	831.6	840.4	848.9	859.7	868.2	878.0	885.5	892.6	899.0	907.1	915.6
7.5°	830.9	845.5	860.8	877.9	896.7	911.7	927.0	939.1	951.0	966.6	978.9
10°	828.2	847.2	867.8	889.5	913.2	933.9	952.5	969.5	985.7	1002.6	1017.9
12.5°	823.3	847.5	872.7	898.8	928.7	952.3	976.3	994.4	1013.3	1031.9	1050.7
15°	816.0	844.5	874.9	911.2	947.8	974.2	997.9	1021.3	1038.9	1059.9	1077.9
17.5°	800.9	837.6	875.9	915.5	950.7	981.4	1006.2	1028.5	1047.2	1070.3	1094.8
20°	791.9	831.6	871.6	913.9	947.4	978.9	1003.0	1026.0	1049.4	1079.6	1109.4
22.5°	779.5	821.8	864.2	904.5	939.9	970.3	995.1	1023.3	1054.0	1088.2	1124.3
25°	759.8	803.5	845.5	883.8	918.3	949.5	983.4	1021.3	1058.5	1103.6	1155.4
27.5°	734.8	776.9	814.4	854.8	889.2	928.8	971.1	1012.2	1066.0	1127.9	1192.7
30°	716.0	756.1	791.7	829.9	868.9	912.6	960.0	1008.4	1072.5	1145.2	1222.2
32.5°	694.4	730.6	765.9	802.8	847.7	895.7	946.2	1005.4	1081.9	1164.8	1244.4
35°	656.8	689.3	723.5	764.6	812.3	864.4	928.8	1000.9	1093.4	1182.5	1254.0
37.5°	617.4	643.0	677.4	720.6	772.7	833.0	906.1	993.7	1088.7	1168.7	1199.1
40°	587.0	611.1	647.3	692.7	744.2	810.3	892.2	982.3	1077.9	1133.4	1131.0
42.5°	557.0	581.3	616.2	661.8	715.5	789.4	873.8	967.4	1048.0	1069.2	1025.1
45°	510.8	533.5	567.8	613.8	671.4	748.9	837.7	927.5	978.9	944.8	857.4
47.5°	463.8	485.8	517.5	562.7	625.5	706.8	790.7	864.3	871.6	798.1	693.2
50°	432.9	453.5	483.8	531.8	592.8	672.1	753.0	810.9	793.0	703.2	595.1
52.5°	402.8	422.7	450.9	496.3	558.7	636.3	708.6	754.0	712.5	617.1	519.9
55°	358.4	377.4	405.8	447.5	504.0	575.2	638.6	655.1	594.1	497.9	419.4
57.5°	316.2	330.0	358.2	395.0	449.6	512.3	557.7	554.7	487.4	400.8	344.5
60°	288.3	300.8	327.5	361.4	413.2	469.5	501.3	487.8	419.7	348.2	294.0
62.5°	262.3	273.9	296.4	327.5	372.1	421.0	444.2	425.4	361.1	298.4	255.3
65°	222.9	231.4	249.3	278.1	313.0	346.9	367.6	340.1	283.2	235.8	203.2
67.5°	186.1	193.4	209.4	230.1	254.1	277.5	285.9	260.1	215.9	184.0	161.0
70°	162.3	169.1	179.9	199.2	215.1	231.7	235.8	212.8	175.8	151.4	137.1
72.5°	139.5	145.7	155.2	168.8	179.9	189.4	191.4	169.9	141.7	124.8	113.9
75°	106.4	111.8	117.9	123.0	130.1	131.8	131.1	114.5	99.2	88.1	81.9
77.5°	78.2	80.4	84.2	86.1	86.5	86.4	82.9	72.4	64.6	59.9	57.4
80°	60.3	62.0	63.0	63.7	64.0	60.6	56.9	50.5	47.8	45.0	42.0
82.5°	43.8	44.9	45.9	46.1	44.2	41.4	37.9	34.8	32.8	31.5	30.3
85°	23.7	24.1	23.7	22.0	19.6	18.6	17.9	17.3	16.9	16.6	16.6
87.5°	9.0	8.6	7.6	8.2	8.6	8.6	8.9	8.9	9.0	9.3	9.5
90°	2.9	4.7	6.6	8.4	10.2	11.8	13.4	15.0	16.6	17.7	18.9
92.5°	26.4	27.6	29.0	30.2	31.8	33.9	35.8	37.8	39.8	41.3	42.8
95°	67.8	68.3	68.8	69.2	70.5	72.9	75.2	77.5	79.8	81.4	83.0
97.5°	112.1	112.3	112.4	112.6	114.3	117.5	120.6	123.9	127.1	128.6	130.1
100°	145.1	145.1	145.1	145.1	146.6	149.5	152.6	155.5	158.5	160.6	162.6
102.5°	181.6	182.5	183.5	184.4	185.7	187.2	188.7	190.2	191.7	193.9	196.2
105°	237.4	238.5	239.7	240.9	242.1	243.5	244.9	246.3	247.6	249.1	250.4
107.5°	298.7	299.9	301.0	302.2	303.3	304.3	305.4	306.5	307.6	308.3	308.9
110°	341.0	342.1	343.3	344.5	345.4	346.1	346.8	347.5	348.1	348.8	349.6



TEST NUMBER: P333545-940

CATALOG NUMBER: S125RDIP-S610D1205U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	383.6	384.1	384.8	385.4	386.1	387.0	387.9	388.7	389.6	389.9	390.3
115°	447.5	448.4	449.3	450.3	450.9	451.5	451.9	452.4	452.8	452.6	452.4
117.5°	510.9	511.3	511.7	512.1	512.5	512.9	513.4	513.7	514.2	514.3	514.5
120°	551.3	552.5	553.7	554.8	555.5	555.7	556.0	556.2	556.4	556.4	556.4
122.5°	593.8	594.1	594.6	594.9	595.5	596.1	596.7	597.3	597.9	597.7	597.5
125°	653.2	654.5	655.9	657.3	658.1	658.4	658.5	658.8	659.1	658.5	658.1
127.5°	714.7	715.5	716.3	717.1	717.6	717.9	718.2	718.5	718.7	718.5	718.3
130°	752.4	753.6	754.7	755.8	756.7	757.2	757.6	758.0	758.5	758.3	758.0
132.5°	790.4	792.4	794.2	796.1	797.0	796.9	796.8	796.7	796.7	796.4	796.2
135°	849.0	850.4	851.8	853.2	854.0	854.2	854.4	854.6	854.9	854.9	854.9
137.5°	904.5	905.8	907.1	908.5	909.5	909.9	910.4	911.0	911.4	911.7	912.0
140°	940.0	941.1	942.3	943.4	944.3	945.0	945.7	946.4	947.1	947.5	948.0
142.5°	975.4	976.4	977.3	978.3	979.3	980.1	981.0	981.9	982.8	983.0	983.3
145°	1027.8	1028.8	1029.7	1030.6	1031.4	1032.1	1032.8	1033.4	1034.1	1034.1	1034.1
147.5°	1075.8	1076.4	1076.9	1077.4	1077.9	1078.5	1079.1	1079.6	1080.1	1080.7	1081.3
150°	1107.5	1107.2	1107.1	1106.8	1107.1	1108.0	1108.9	1109.9	1110.8	1110.8	1110.8
152.5°	1134.5	1134.9	1135.2	1135.5	1135.9	1136.2	1136.6	1137.0	1137.4	1137.9	1138.4
155°	1175.1	1175.1	1175.1	1175.1	1175.2	1175.5	1175.6	1175.9	1176.1	1177.1	1177.9
157.5°	1211.0	1210.5	1210.1	1209.5	1209.3	1209.6	1209.9	1210.1	1210.3	1211.2	1212.1
160°	1232.4	1231.7	1231.0	1230.3	1230.1	1230.3	1230.6	1230.8	1231.0	1231.9	1232.9
162.5°	1251.7	1251.2	1250.6	1250.1	1249.9	1249.9	1250.0	1250.0	1250.1	1251.2	1252.3
165°	1277.2	1276.8	1276.3	1275.8	1275.7	1275.9	1276.1	1276.4	1276.6	1277.6	1278.4
167.5°	1298.2	1297.4	1296.5	1295.5	1295.0	1295.0	1295.0	1295.0	1295.0	1296.5	1297.8
170°	1309.9	1308.9	1308.1	1307.2	1306.6	1306.6	1306.6	1306.6	1306.6	1308.1	1309.4
172.5°	1318.2	1317.2	1316.3	1315.5	1314.9	1314.9	1314.9	1314.9	1314.9	1316.3	1317.7
175°	1327.5	1326.6	1325.6	1324.7	1324.3	1324.3	1324.3	1324.3	1324.3	1325.6	1327.0
177.5°	1332.5	1331.7	1331.0	1330.3	1329.8	1329.6	1329.5	1329.2	1329.0	1330.2	1331.2
180°	1331.5	1331.5	1331.5	1331.5	1331.5	1331.5	1331.5	1331.5	1331.5	1331.5	1331.5



TEST NUMBER: P333545-940

CATALOG NUMBER: S125RDIP-S610D1205U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	825.2	825.2	825.2	825.2	825.2	825.2	825.2
2.5°	861.2	861.2	865.9	865.5	868.5	867.5	868.0
5°	925.8	931.5	936.6	940.0	945.0	946.5	945.7
7.5°	992.7	1005.5	1011.7	1020.3	1021.8	1026.3	1025.8
10°	1034.1	1046.7	1056.1	1063.6	1067.4	1072.1	1072.5
12.5°	1066.7	1077.3	1085.7	1092.6	1097.2	1098.7	1099.6
15°	1092.1	1103.9	1113.7	1123.6	1129.4	1133.7	1136.1
17.5°	1117.7	1136.0	1153.3	1166.7	1174.7	1181.4	1181.3
20°	1137.5	1158.5	1180.2	1195.4	1210.9	1217.7	1218.8
22.5°	1158.6	1190.7	1218.6	1242.2	1262.8	1269.8	1272.4
25°	1202.5	1244.5	1287.5	1320.7	1344.4	1358.3	1360.4
27.5°	1255.5	1312.4	1357.6	1388.3	1408.0	1418.3	1420.5
30°	1293.0	1345.4	1386.1	1409.2	1418.3	1419.6	1414.5
32.5°	1309.7	1349.0	1365.2	1363.9	1345.9	1334.0	1329.5
35°	1289.2	1281.1	1241.4	1194.0	1157.8	1134.8	1128.6
37.5°	1173.2	1103.1	1030.2	958.6	920.4	901.1	867.7
40°	1058.9	958.9	883.1	822.8	779.8	745.2	737.1
42.5°	929.9	826.7	750.8	699.2	664.9	641.1	630.9
45°	747.3	658.5	595.8	556.2	529.8	512.5	504.7
47.5°	597.6	529.0	483.3	454.0	433.8	418.8	414.6
50°	515.6	460.7	422.0	397.3	382.1	370.6	365.9
52.5°	447.8	403.5	373.8	353.5	339.0	331.8	327.9
55°	369.5	331.3	310.0	293.6	285.5	279.8	277.1
57.5°	302.2	274.6	259.0	247.7	240.2	236.6	235.2
60°	264.6	242.9	228.6	219.8	214.7	210.0	208.7
62.5°	231.2	214.2	203.1	195.5	190.4	188.3	187.5
65°	186.3	175.1	167.0	162.3	158.2	157.5	157.2
67.5°	148.1	141.5	137.2	132.3	130.9	128.5	128.0
70°	126.7	122.3	117.2	115.5	113.8	111.5	111.8
72.5°	107.5	103.1	99.6	97.4	96.8	95.8	96.6
75°	78.6	77.2	75.9	74.2	73.5	73.5	73.2
77.5°	56.1	54.9	53.4	52.4	52.3	50.8	51.4
80°	40.7	39.0	38.3	38.6	37.6	37.3	37.3
82.5°	30.1	29.4	28.8	28.9	28.6	28.4	28.6
85°	16.6	16.2	16.2	16.0	16.0	15.6	15.6
87.5°	10.0	10.4	10.1	10.0	10.1	10.5	11.0
90°	20.1	21.2	22.1	22.8	23.5	24.2	24.9
92.5°	44.3	45.8	46.9	47.3	47.9	48.4	48.9
95°	84.6	86.2	87.3	87.7	88.2	88.6	89.1
97.5°	131.6	133.1	134.0	134.3	134.6	134.8	135.1
100°	164.8	166.8	168.1	168.5	169.0	169.5	170.0
102.5°	198.5	200.7	202.2	202.9	203.5	204.1	204.7
105°	251.8	253.2	254.2	254.9	255.6	256.3	257.0
107.5°	309.6	310.3	310.7	310.6	310.6	310.5	310.4
110°	350.3	350.9	351.2	350.9	350.7	350.4	350.3



TEST NUMBER: P333545-940

CATALOG NUMBER: S125RDIP-S610D1205U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	390.6	390.9	390.8	390.5	390.0	389.6	389.2
115°	452.1	451.9	451.7	451.5	451.2	450.9	450.8
117.5°	514.7	514.9	514.5	513.6	512.7	511.8	510.9
120°	556.4	556.4	556.0	555.1	554.1	553.2	552.3
122.5°	597.4	597.2	596.7	595.9	595.2	594.5	593.8
125°	657.6	657.2	656.8	656.7	656.4	656.1	655.9
127.5°	718.0	717.8	717.5	717.0	716.5	716.0	715.6
130°	757.8	757.6	757.2	756.8	756.3	755.8	755.4
132.5°	795.9	795.7	795.3	794.6	794.0	793.4	792.7
135°	854.9	854.9	854.4	853.5	852.6	851.7	850.7
137.5°	912.3	912.6	912.1	911.0	909.8	908.7	907.5
140°	948.5	949.0	948.6	947.4	946.3	945.1	944.0
142.5°	983.6	983.8	983.4	982.2	981.1	980.0	978.8
145°	1034.1	1034.1	1033.8	1033.1	1032.4	1031.7	1031.0
147.5°	1081.8	1082.4	1081.8	1080.3	1078.7	1077.2	1075.6
150°	1110.8	1110.8	1110.6	1110.1	1109.6	1109.2	1108.8
152.5°	1139.0	1139.5	1139.4	1138.6	1137.7	1136.9	1136.1
155°	1178.8	1179.8	1179.6	1178.5	1177.3	1176.3	1175.1
157.5°	1213.1	1214.0	1213.7	1212.2	1210.7	1209.2	1207.6
160°	1233.8	1234.7	1234.6	1233.4	1232.3	1231.1	1230.0
162.5°	1253.4	1254.5	1254.4	1253.0	1251.7	1250.4	1249.0
165°	1279.3	1280.3	1280.1	1278.7	1277.3	1275.9	1274.5
167.5°	1299.2	1300.6	1300.6	1299.1	1297.7	1296.3	1294.9
170°	1310.8	1312.2	1312.1	1310.5	1308.9	1307.2	1305.6
172.5°	1319.1	1320.4	1320.4	1319.0	1317.6	1316.2	1314.7
175°	1328.4	1329.8	1329.7	1328.1	1326.5	1324.8	1323.2
177.5°	1332.4	1333.5	1333.4	1332.1	1330.8	1329.5	1328.2
180°	1331.5	1331.5	1331.5	1331.5	1331.5	1331.5	1331.5

(END OF REPORT)