

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333574-940

Luminaire Tested: **S125RDIP-S850D1205U940-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333574-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S850D1205U940-4F0-1E-UDD-A
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1205 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7218.2 lumens
Efficiency: N/A
Efficacy: 126.9 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 56.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333574-940

CATALOG NUMBER: S125RDIP-S850D1205U940-4F0-1E-UDD-A

Luminous Intensity Polar Plot



59% Up

41% Dn



TEST NUMBER: P333574-940

CATALOG NUMBER: S125RDIP-S850D1205U940-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	47	47	47	41																												
1	96	92	88	85	87	84	81	78	69	67	65	55	54	52	42	42	41	35																												
2	88	81	75	70	80	74	69	64	61	57	54	49	46	44	38	36	35	30																												
3	80	71	64	58	73	65	59	54	54	49	46	43	40	38	34	32	30	25																												
4	73	63	55	50	67	58	51	46	48	43	39	39	35	32	30	28	26	22																												
5	67	56	48	43	61	52	45	40	43	38	34	35	31	28	27	25	23	19																												
6	62	50	43	37	56	46	39	34	39	33	30	32	28	25	25	22	20	17																												
7	57	45	38	32	52	42	35	30	35	30	26	29	25	22	23	20	18	15																												
8	53	41	34	29	48	38	31	27	32	27	23	26	22	20	21	18	16	14																												
9	49	38	30	25	45	35	28	24	29	24	21	24	20	18	19	16	14	12																												
10	46	34	27	23	42	32	26	21	27	22	19	22	18	16	18	15	13	11																												

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	7284	7284	7284	7284
5°	8381	7295	6442	7295
10°	9613	7257	5684	7257
15°	10384	7182	5052	7182
20°	11450	7096	4665	7096
25°	13251	6981	4329	6981
30°	14420	6861	4109	6861
35°	12163	6720	3906	6720
40°	8494	6468	3731	6468
45°	6301	6128	3561	6128
50°	5025	5773	3414	5773
55°	4264	5334	3284	5334
60°	3685	4941	3074	4941
65°	3283	4514	2647	4514
70°	2885	4135	2413	4135
75°	2495	3583	2266	3583
80°	1893	3016	1893	3016
85°	1578	2364	1786	2364



TEST NUMBER: P333574-940

CATALOG NUMBER: S125RDIP-S850D1205U940-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	108.2	1.5
10°-20°	317.0	4.4
20°-30°	502.6	7.0
30°-40°	606.1	8.4
40°-50°	541.2	7.5
50°-60°	415.1	5.8
60°-70°	269.7	3.7
70°-80°	131.1	1.8
80°-90°	34.2	0.5
90°-100°	50.8	0.7
100°-110°	313.1	4.3
110°-120°	567.9	7.9
120°-130°	728.8	10.1
130°-140°	783.9	10.9
140°-150°	735.8	10.2
150°-160°	595.2	8.2
160°-170°	384.9	5.3
170°-180°	132.8	1.8
0°-30°	927.7	12.9
0°-40°	1533.8	21.2
0°-60°	2490.1	34.5
0°-90°	2925.2	40.5
90°-120°	931.8	12.9
90°-150°	3180.2	44.1
90°-180°	4293.0	59.5
0°-180°	7218.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1128	1128	1128	1128	1128	
5°	1293	1125	994	1125	1293	129
15°	1553	1074	756	1074	1553	445
25°	1860	980	608	980	1860	854
35°	1543	852	495	852	1543	932
45°	690	671	390	671	690	550
55°	379	474	292	474	379	344
65°	215	295	173	295	215	214
75°	100	144	91	144	100	106
85°	21	32	24	32	21	25
90°	25	1	25	1	25	12
95°	22	59	22	59	22	18
105°	308	305	308	305	308	278
115°	568	572	568	572	568	564
125°	814	814	814	814	814	724
135°	1010	1015	1010	1015	1010	780
145°	1173	1176	1173	1176	1173	733
155°	1286	1295	1286	1295	1286	593
165°	1360	1367	1360	1367	1360	384
175°	1392	1398	1392	1398	1392	132
180°	1398	1398	1398	1398	1398	



TEST NUMBER: P333574-940

CATALOG NUMBER: S125RDIP-S850D1205U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9
2.5°	1186.4	1185.7	1187.2	1183.1	1183.5	1177.1	1177.1	1172.3	1166.1	1161.3	1159.0
5°	1292.7	1293.7	1291.8	1284.9	1280.2	1273.3	1265.4	1251.5	1239.9	1228.9	1220.0
7.5°	1402.2	1402.8	1396.8	1394.6	1383.0	1374.4	1356.9	1338.0	1321.2	1299.9	1283.7
10°	1465.9	1465.4	1459.0	1453.8	1443.7	1430.7	1413.6	1391.3	1370.6	1347.4	1325.2
12.5°	1503.0	1501.7	1499.7	1493.5	1484.1	1472.6	1458.0	1436.2	1410.5	1385.2	1359.2
15°	1553.0	1549.7	1543.7	1535.8	1522.4	1509.0	1492.8	1473.4	1448.8	1420.0	1396.0
17.5°	1614.8	1614.9	1605.7	1594.7	1576.5	1552.8	1527.8	1496.4	1463.0	1431.5	1405.8
20°	1666.0	1664.6	1655.3	1634.0	1613.2	1583.5	1554.8	1516.4	1475.6	1434.4	1402.5
22.5°	1739.3	1735.7	1726.1	1698.1	1665.8	1627.6	1583.7	1536.8	1487.5	1440.7	1398.8
25°	1859.5	1856.7	1837.7	1805.4	1760.0	1701.1	1643.7	1579.4	1508.5	1447.0	1396.0
27.5°	1941.7	1938.7	1924.6	1897.6	1855.8	1793.9	1716.2	1630.2	1541.8	1457.1	1383.6
30°	1933.6	1940.5	1938.7	1926.2	1894.7	1839.2	1767.4	1670.6	1565.5	1465.9	1378.4
32.5°	1817.2	1823.5	1839.8	1864.3	1866.2	1844.0	1790.3	1700.9	1592.1	1478.9	1374.3
35°	1542.7	1551.1	1582.6	1632.2	1696.9	1751.1	1762.3	1714.1	1616.4	1494.6	1368.2
37.5°	1186.1	1231.6	1258.1	1310.3	1408.2	1507.9	1603.7	1639.0	1597.4	1488.2	1358.3
40°	1007.5	1018.6	1065.9	1124.7	1207.1	1310.8	1447.4	1546.0	1549.3	1473.4	1342.7
42.5°	862.3	876.4	908.8	955.7	1026.4	1130.1	1271.0	1401.2	1461.5	1432.6	1322.4
45°	689.9	700.5	724.2	760.3	814.5	900.1	1021.5	1171.9	1291.4	1338.1	1267.7
47.5°	566.8	572.5	593.1	620.5	660.7	723.1	817.0	947.6	1090.9	1191.3	1181.4
50°	500.1	506.6	522.3	543.1	576.9	629.7	704.7	813.5	961.3	1084.0	1108.5
52.5°	448.2	453.6	463.4	483.1	511.0	551.5	612.1	710.5	843.5	973.9	1030.6
55°	378.7	382.5	390.3	401.4	423.7	452.8	505.2	573.2	680.6	812.2	895.5
57.5°	321.6	323.3	328.4	338.7	354.0	375.3	413.1	470.8	547.9	666.3	758.2
60°	285.3	287.0	293.6	300.5	312.5	332.0	361.6	401.9	476.0	573.6	666.7
62.5°	256.4	257.4	260.2	267.2	277.7	292.7	316.0	348.9	407.9	493.7	581.6
65°	214.8	215.3	216.2	221.8	228.3	239.4	254.7	277.8	322.3	387.1	464.8
67.5°	175.0	175.7	178.9	180.8	187.6	193.4	202.4	220.2	251.5	295.2	355.6
70°	152.8	152.3	155.6	157.9	160.2	167.1	173.2	187.5	207.0	240.3	290.8
72.5°	132.1	130.8	132.2	133.0	136.2	140.9	146.9	155.7	170.7	193.6	232.3
75°	100.0	100.5	100.5	101.4	103.7	105.6	107.5	112.1	120.4	135.6	156.5
77.5°	70.2	69.5	71.4	71.7	73.0	75.1	76.7	78.6	81.9	88.3	99.0
80°	50.9	50.9	51.4	52.8	52.3	53.2	55.6	57.4	61.6	65.3	69.0
82.5°	39.1	38.7	39.1	39.4	39.3	40.3	41.1	41.5	43.1	44.9	47.5
85°	21.3	21.3	21.8	21.8	22.2	22.2	22.6	22.6	22.6	23.2	23.6
87.5°	13.1	12.6	12.1	11.9	12.2	12.8	12.1	11.6	11.3	11.1	11.1
90°	24.9	24.2	23.5	22.8	22.1	21.2	20.1	18.9	17.7	16.6	15.0
92.5°	23.2	22.9	22.6	22.2	21.9	21.2	20.1	18.9	17.7	16.6	15.2
95°	21.8	21.8	21.8	21.8	21.8	21.2	20.1	18.9	17.7	16.6	25.3
97.5°	21.8	21.8	21.8	21.8	21.8	25.0	31.5	38.0	44.5	51.0	68.3
100°	21.8	22.6	23.6	24.5	25.4	43.1	77.4	111.7	146.0	180.3	179.4
102.5°	130.4	146.1	161.7	177.4	193.1	204.1	210.6	217.0	223.6	230.1	229.5
105°	307.8	308.0	308.3	308.4	308.7	308.8	308.8	308.8	308.8	308.8	308.8
107.5°	388.0	388.7	389.4	390.0	390.7	391.1	391.0	391.0	390.9	390.9	390.5
110°	443.5	443.4	443.1	442.8	442.6	442.8	443.5	444.3	445.0	445.6	445.1



TEST NUMBER: P333574-940

CATALOG NUMBER: S125RDIP-S850D1205U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	493.3	493.7	493.9	494.3	494.5	495.2	496.1	497.0	497.8	498.6	498.4
115°	567.9	569.3	570.7	572.0	573.5	574.6	575.5	576.4	577.4	578.3	578.0
117.5°	647.5	648.1	648.7	649.3	649.9	650.8	652.0	653.2	654.4	655.6	654.7
120°	696.4	697.6	698.7	699.9	701.1	701.9	702.3	702.8	703.2	703.6	702.9
122.5°	742.9	744.2	745.5	746.8	748.1	749.1	749.6	750.0	750.5	750.9	750.6
125°	813.5	814.2	814.9	815.6	816.3	817.1	818.0	818.9	819.8	820.7	820.7
127.5°	873.0	874.7	876.4	878.2	879.9	880.9	881.5	881.9	882.4	883.0	883.1
130°	916.1	917.3	918.5	919.5	920.7	921.7	922.3	923.0	923.7	924.4	924.2
132.5°	955.9	957.1	958.2	959.4	960.6	961.2	961.3	961.4	961.6	961.7	962.2
135°	1010.4	1011.8	1013.2	1014.6	1015.9	1016.9	1017.4	1017.8	1018.2	1018.7	1019.1
137.5°	1065.1	1066.3	1067.6	1068.7	1070.0	1070.5	1070.4	1070.3	1070.2	1070.1	1070.5
140°	1097.5	1098.9	1100.3	1101.6	1103.0	1103.5	1103.0	1102.5	1102.1	1101.6	1101.9
142.5°	1128.2	1129.5	1131.0	1132.3	1133.7	1134.3	1134.3	1134.2	1134.1	1134.0	1133.6
145°	1173.1	1174.5	1175.9	1177.2	1178.7	1179.2	1179.0	1178.8	1178.6	1178.3	1178.3
147.5°	1210.2	1211.9	1213.5	1215.2	1216.8	1217.5	1217.3	1217.0	1216.7	1216.5	1216.2
150°	1234.3	1236.1	1238.0	1239.8	1241.6	1242.3	1241.9	1241.4	1240.9	1240.5	1240.0
152.5°	1256.7	1258.3	1260.0	1261.6	1263.3	1263.9	1263.5	1262.9	1262.5	1262.0	1261.6
155°	1286.1	1287.9	1289.8	1291.6	1293.4	1294.1	1293.3	1292.6	1292.0	1291.3	1290.8
157.5°	1310.7	1312.6	1314.5	1316.3	1318.1	1318.7	1317.9	1317.2	1316.4	1315.7	1315.7
160°	1326.5	1328.4	1330.2	1332.0	1333.9	1334.4	1333.4	1332.5	1331.6	1330.6	1330.4
162.5°	1340.6	1342.6	1344.6	1346.7	1348.7	1349.1	1347.8	1346.5	1345.2	1343.9	1343.7
165°	1359.7	1361.5	1363.3	1365.2	1367.0	1367.3	1365.9	1364.5	1363.2	1361.7	1361.5
167.5°	1373.0	1375.0	1377.1	1379.1	1381.3	1381.4	1379.7	1378.1	1376.4	1374.8	1374.6
170°	1380.4	1382.5	1384.6	1386.6	1388.7	1388.8	1387.0	1385.1	1383.3	1381.4	1381.2
172.5°	1385.4	1387.4	1389.6	1391.6	1393.7	1393.8	1392.2	1390.5	1388.9	1387.2	1386.8
175°	1391.8	1393.8	1396.0	1398.0	1400.1	1400.2	1398.4	1396.5	1394.6	1392.9	1392.6
177.5°	1395.5	1397.0	1398.5	1400.0	1401.4	1401.5	1400.3	1398.9	1397.7	1396.3	1396.2
180°	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0



TEST NUMBER: P333574-940

CATALOG NUMBER: S125RDIP-S850D1205U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9
2.5°	1159.0	1156.5	1151.6	1147.2	1141.7	1136.8	1133.5	1129.4	1124.2	1117.9	1112.8
5°	1210.3	1200.2	1186.7	1175.2	1160.3	1148.8	1136.8	1125.2	1113.6	1098.8	1085.7
7.5°	1267.2	1246.2	1225.7	1200.0	1176.6	1155.7	1135.8	1115.5	1095.7	1074.7	1054.4
10°	1302.0	1276.6	1248.3	1215.8	1186.2	1158.0	1132.1	1106.6	1079.8	1056.1	1030.6
12.5°	1334.6	1301.7	1269.4	1228.5	1192.9	1158.4	1125.4	1093.7	1065.0	1034.3	1007.0
15°	1364.1	1331.7	1295.6	1245.5	1196.0	1154.3	1115.4	1074.2	1038.6	1004.3	973.7
17.5°	1375.5	1341.5	1299.5	1251.4	1197.3	1144.9	1094.8	1049.5	1007.6	967.7	933.4
20°	1371.0	1338.1	1295.0	1249.2	1191.3	1136.8	1082.5	1032.5	985.8	943.6	907.0
22.5°	1360.2	1326.2	1284.7	1236.3	1181.3	1123.4	1065.5	1012.2	963.1	919.5	879.7
25°	1344.2	1297.9	1255.3	1208.0	1155.7	1098.3	1038.6	979.7	927.5	883.0	839.5
27.5°	1327.4	1269.6	1215.4	1168.5	1113.2	1061.9	1004.4	944.1	889.1	843.8	799.2
30°	1312.2	1247.4	1187.7	1134.4	1082.1	1033.5	978.8	920.0	863.5	816.8	771.4
32.5°	1293.3	1224.4	1158.8	1097.3	1046.9	998.6	949.2	893.0	837.9	789.7	743.6
35°	1269.6	1181.6	1110.4	1045.0	989.0	942.3	897.8	852.4	797.3	747.3	702.4
37.5°	1238.5	1138.6	1056.1	985.1	926.0	879.0	843.9	802.5	752.2	704.3	662.5
40°	1219.6	1107.5	1017.3	946.9	884.8	835.3	802.5	767.2	721.4	676.5	634.8
42.5°	1194.4	1079.1	978.0	904.6	842.2	794.5	761.3	730.6	692.1	649.8	605.2
45°	1145.0	1023.8	917.7	839.0	776.1	729.2	698.2	670.9	641.8	602.9	563.9
47.5°	1080.8	966.1	855.1	769.2	707.5	664.1	634.0	612.4	591.6	558.5	520.7
50°	1029.3	918.6	810.3	726.9	661.2	620.0	591.7	574.6	555.6	525.5	494.0
52.5°	968.6	869.8	763.6	678.4	616.4	577.7	550.6	533.5	517.8	493.3	463.3
55°	872.8	786.2	688.9	611.6	554.7	515.8	489.9	473.7	464.4	443.5	420.0
57.5°	762.3	700.3	614.5	539.9	489.6	451.2	432.2	418.4	408.0	393.2	376.6
60°	685.3	641.8	564.9	494.0	447.7	411.2	394.0	382.5	372.7	360.3	347.2
62.5°	607.1	575.4	508.5	447.7	405.1	374.5	358.5	348.0	336.8	328.4	315.8
65°	502.4	474.1	427.8	380.1	340.8	316.2	304.7	295.4	288.5	279.2	270.4
67.5°	390.7	379.3	347.3	314.5	286.2	264.4	254.4	247.9	239.6	234.0	228.0
70°	322.3	316.7	294.0	272.2	245.8	231.0	221.8	219.0	208.8	203.3	199.1
72.5°	261.5	259.0	245.8	230.8	212.1	199.2	190.6	187.5	181.0	176.6	173.9
75°	179.1	180.1	177.8	168.1	161.1	152.8	145.3	143.6	138.9	135.2	132.9
77.5°	113.3	118.1	118.2	117.8	115.0	109.9	106.8	105.5	100.9	99.5	99.0
80°	77.8	82.8	87.5	87.0	86.1	84.7	82.4	81.1	78.7	77.3	76.4
82.5°	51.9	56.6	60.5	63.0	62.8	61.4	59.8	59.2	58.7	57.7	57.5
85°	24.5	25.5	26.8	30.1	32.4	32.9	32.4	31.9	30.6	31.0	31.5
87.5°	11.2	10.9	10.9	10.6	9.8	11.3	12.0	12.0	11.7	11.3	11.0
90°	13.4	11.8	10.2	8.4	6.6	4.7	2.9	1.1	2.9	4.7	6.6
92.5°	13.7	12.3	10.9	10.8	12.1	13.4	14.7	16.0	14.7	13.4	12.1
95°	34.1	42.8	51.6	56.3	57.0	57.7	58.4	59.0	58.4	57.7	57.0
97.5°	85.6	102.9	120.3	128.3	127.1	125.8	124.6	123.3	124.6	125.8	127.1
100°	178.5	177.5	176.6	175.8	175.1	174.4	173.8	173.1	173.8	174.4	175.1
102.5°	229.0	228.4	227.8	227.1	226.2	225.4	224.5	223.6	224.5	225.4	226.2
105°	308.8	308.8	308.8	308.4	307.5	306.5	305.6	304.7	305.6	306.5	307.5
107.5°	389.9	389.5	389.1	388.9	388.9	388.9	388.9	388.9	388.9	388.9	388.9
110°	444.7	444.3	443.8	443.5	443.5	443.5	443.5	443.5	443.5	443.5	443.5



TEST NUMBER: P333574-940

CATALOG NUMBER: S125RDIP-S850D1205U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	498.1	497.8	497.6	497.1	496.6	496.1	495.5	495.0	495.5	496.1	496.6
115°	577.8	577.6	577.4	576.7	575.5	574.4	573.2	572.0	573.2	574.4	575.5
117.5°	653.8	653.0	652.1	651.7	651.8	651.8	651.8	651.8	651.8	651.8	651.8
120°	702.3	701.6	700.9	700.7	700.9	701.2	701.3	701.6	701.3	701.2	700.9
122.5°	750.3	749.9	749.7	749.0	748.1	747.3	746.5	745.6	746.5	747.3	748.1
125°	820.7	820.7	820.7	819.9	818.3	816.7	815.1	813.5	815.1	816.7	818.3
127.5°	883.2	883.3	883.5	883.0	881.8	880.7	879.6	878.4	879.6	880.7	881.8
130°	924.0	923.7	923.5	922.8	921.7	920.5	919.4	918.2	919.4	920.5	921.7
132.5°	962.7	963.2	963.8	963.3	962.0	960.6	959.3	958.0	959.3	960.6	962.0
135°	1019.7	1020.1	1020.6	1020.1	1018.7	1017.4	1015.9	1014.6	1015.9	1017.4	1018.7
137.5°	1070.9	1071.4	1071.7	1071.4	1070.1	1069.0	1067.8	1066.6	1067.8	1069.0	1070.1
140°	1102.1	1102.3	1102.5	1102.4	1102.0	1101.5	1101.1	1100.5	1101.1	1101.5	1102.0
142.5°	1133.3	1133.0	1132.7	1132.4	1132.1	1131.8	1131.5	1131.2	1131.5	1131.8	1132.1
145°	1178.3	1178.3	1178.3	1178.0	1177.6	1177.1	1176.7	1176.3	1176.7	1177.1	1177.6
147.5°	1215.8	1215.6	1215.3	1215.2	1215.3	1215.4	1215.5	1215.6	1215.5	1215.4	1215.3
150°	1239.6	1239.1	1238.7	1238.7	1239.1	1239.6	1240.0	1240.5	1240.0	1239.6	1239.1
152.5°	1261.1	1260.7	1260.2	1260.4	1261.5	1262.5	1263.6	1264.5	1263.6	1262.5	1261.5
155°	1290.3	1289.9	1289.4	1289.9	1291.3	1292.6	1294.1	1295.4	1294.1	1292.6	1291.3
157.5°	1315.6	1315.6	1315.5	1315.9	1316.8	1317.6	1318.4	1319.3	1318.4	1317.6	1316.8
160°	1330.2	1330.0	1329.7	1330.3	1331.7	1333.1	1334.4	1335.9	1334.4	1333.1	1331.7
162.5°	1343.5	1343.2	1343.0	1343.5	1345.0	1346.3	1347.7	1349.1	1347.7	1346.3	1345.0
165°	1361.3	1361.0	1360.8	1361.4	1362.8	1364.1	1365.6	1366.9	1365.6	1364.1	1362.8
167.5°	1374.3	1374.1	1373.9	1374.5	1375.9	1377.3	1378.8	1380.2	1378.8	1377.3	1375.9
170°	1381.0	1380.7	1380.5	1381.2	1382.8	1384.4	1386.1	1387.7	1386.1	1384.4	1382.8
172.5°	1386.4	1386.0	1385.5	1386.2	1387.8	1389.4	1391.0	1392.6	1391.0	1389.4	1387.8
175°	1392.4	1392.1	1391.9	1392.5	1393.8	1395.3	1396.6	1398.0	1396.6	1395.3	1393.8
177.5°	1396.0	1395.8	1395.6	1396.1	1397.2	1398.3	1399.4	1400.5	1399.4	1398.3	1397.2
180°	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0



TEST NUMBER: P333574-940

CATALOG NUMBER: S125RDIP-S850D1205U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9
2.5°	1109.0	1103.8	1100.1	1092.7	1087.5	1085.3	1081.3	1080.1	1084.2	1081.3	1080.8
5°	1076.0	1062.7	1052.0	1041.3	1029.7	1022.3	1011.2	1009.4	1006.6	1002.5	1001.5
7.5°	1036.5	1019.0	1005.3	987.7	972.4	960.1	946.2	939.7	936.0	930.7	923.5
10°	1009.9	989.0	970.4	952.9	933.9	918.6	904.7	894.1	887.2	880.7	877.9
12.5°	983.6	962.3	938.6	917.3	896.2	879.0	863.6	856.7	849.0	841.4	834.9
15°	942.7	914.4	888.5	864.0	846.0	827.4	812.6	802.5	790.9	787.6	775.1
17.5°	899.4	871.6	841.3	815.5	794.5	774.2	757.9	746.3	737.6	725.7	719.9
20°	872.4	839.5	809.9	786.2	763.0	739.0	722.3	712.6	704.3	694.6	689.9
22.5°	843.5	811.3	781.0	753.2	729.7	706.1	694.2	684.0	674.6	665.7	659.5
25°	801.0	768.7	736.6	707.9	683.4	666.3	652.4	640.8	635.7	627.0	620.5
27.5°	759.1	724.6	691.4	662.9	643.6	626.7	615.3	606.1	596.9	589.2	583.6
30°	732.0	696.9	660.8	638.0	617.7	601.5	589.0	580.1	573.2	566.2	562.1
32.5°	705.0	668.7	636.7	612.1	592.8	578.9	566.0	557.6	550.3	542.6	537.7
35°	661.6	624.6	598.7	574.6	555.6	542.7	533.9	521.8	515.8	510.2	505.2
37.5°	621.3	586.9	558.8	537.8	521.3	508.4	497.0	490.5	483.1	478.1	473.9
40°	591.7	560.3	534.8	512.6	500.5	486.2	475.5	467.2	461.6	455.1	450.5
42.5°	565.1	535.8	511.0	491.1	476.1	464.0	453.7	445.3	438.3	433.6	429.8
45°	527.4	498.2	474.1	455.6	441.8	430.2	419.5	415.4	406.1	400.6	398.7
47.5°	488.4	462.3	439.1	422.0	407.8	396.8	386.8	378.3	373.2	367.7	364.8
50°	462.1	437.1	415.4	398.7	384.8	372.7	363.5	357.9	351.0	345.9	342.1
52.5°	435.8	412.7	390.9	375.0	362.9	350.9	340.5	334.9	328.4	325.1	322.5
55°	398.2	373.6	355.2	339.4	326.9	315.8	306.0	300.5	296.3	293.1	292.1
57.5°	355.6	336.2	319.0	304.8	291.8	281.3	272.8	267.5	263.9	263.3	260.6
60°	327.8	310.2	294.4	279.2	268.0	258.3	250.9	245.0	241.2	240.8	239.9
62.5°	300.1	283.2	268.6	255.1	245.1	235.8	228.7	221.9	219.7	217.4	215.4
65°	258.9	243.5	231.5	220.9	210.2	202.3	195.4	191.2	186.1	183.3	178.3
67.5°	218.4	206.5	194.9	185.9	177.6	170.1	164.3	158.2	154.7	152.5	148.8
70°	191.7	182.4	170.9	161.1	154.6	148.6	144.0	137.1	134.7	132.9	131.0
72.5°	166.5	158.4	148.6	140.8	134.3	128.6	123.2	120.0	117.7	115.8	114.8
75°	131.0	123.1	114.9	109.2	104.7	100.0	97.2	94.9	94.0	93.5	91.7
77.5°	96.2	92.0	85.3	81.0	77.8	76.1	73.6	72.3	72.2	70.2	69.6
80°	73.7	71.3	65.7	63.9	61.6	59.7	58.3	56.0	53.7	52.8	51.4
82.5°	54.8	52.4	50.2	47.3	45.3	44.1	42.8	41.9	42.3	40.9	40.3
85°	29.2	26.8	25.9	25.5	24.5	25.5	25.0	24.5	24.1	23.6	24.1
87.5°	11.0	11.3	11.2	12.3	11.5	12.2	12.4	12.3	12.5	12.8	12.6
90°	8.4	10.2	11.8	13.4	15.0	16.6	17.7	18.9	20.1	21.2	22.1
92.5°	10.8	10.9	12.3	13.7	15.2	16.6	17.7	18.9	20.1	21.2	21.9
95°	56.3	51.6	42.8	34.1	25.3	16.6	17.7	18.9	20.1	21.2	21.8
97.5°	128.3	120.3	102.9	85.6	68.3	51.0	44.5	38.0	31.5	25.0	21.8
100°	175.8	176.6	177.5	178.5	179.4	180.3	146.0	111.7	77.4	43.1	25.4
102.5°	227.1	227.8	228.4	229.0	229.5	230.1	223.6	217.0	210.6	204.1	193.1
105°	308.4	308.8	308.8	308.8	308.8	308.8	308.8	308.8	308.8	308.8	308.7
107.5°	388.9	389.1	389.5	389.9	390.5	390.9	390.9	391.0	391.0	391.1	390.7
110°	443.5	443.8	444.3	444.7	445.1	445.6	445.0	444.3	443.5	442.8	442.6



TEST NUMBER: P333574-940

CATALOG NUMBER: S125RDIP-S850D1205U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	497.1	497.6	497.8	498.1	498.4	498.6	497.8	497.0	496.1	495.2	494.5
115°	576.7	577.4	577.6	577.8	578.0	578.3	577.4	576.4	575.5	574.6	573.5
117.5°	651.7	652.1	653.0	653.8	654.7	655.6	654.4	653.2	652.0	650.8	649.9
120°	700.7	700.9	701.6	702.3	702.9	703.6	703.2	702.8	702.3	701.9	701.1
122.5°	749.0	749.7	749.9	750.3	750.6	750.9	750.5	750.0	749.6	749.1	748.1
125°	819.9	820.7	820.7	820.7	820.7	820.7	819.8	818.9	818.0	817.1	816.3
127.5°	883.0	883.5	883.3	883.2	883.1	883.0	882.4	881.9	881.5	880.9	879.9
130°	922.8	923.5	923.7	924.0	924.2	924.4	923.7	923.0	922.3	921.7	920.7
132.5°	963.3	963.8	963.2	962.7	962.2	961.7	961.6	961.4	961.3	961.2	960.6
135°	1020.1	1020.6	1020.1	1019.7	1019.1	1018.7	1018.2	1017.8	1017.4	1016.9	1015.9
137.5°	1071.4	1071.7	1071.4	1070.9	1070.5	1070.1	1070.2	1070.3	1070.4	1070.5	1070.0
140°	1102.4	1102.5	1102.3	1102.1	1101.9	1101.6	1102.1	1102.5	1103.0	1103.5	1103.0
142.5°	1132.4	1132.7	1133.0	1133.3	1133.6	1134.0	1134.1	1134.2	1134.3	1134.3	1133.7
145°	1178.0	1178.3	1178.3	1178.3	1178.3	1178.3	1178.6	1178.8	1179.0	1179.2	1178.7
147.5°	1215.2	1215.3	1215.6	1215.8	1216.2	1216.5	1216.7	1217.0	1217.3	1217.5	1216.8
150°	1238.7	1238.7	1239.1	1239.6	1240.0	1240.5	1240.9	1241.4	1241.9	1242.3	1241.6
152.5°	1260.4	1260.2	1260.7	1261.1	1261.6	1262.0	1262.5	1262.9	1263.5	1263.9	1263.3
155°	1289.9	1289.4	1289.9	1290.3	1290.8	1291.3	1292.0	1292.6	1293.3	1294.1	1293.4
157.5°	1315.9	1315.5	1315.6	1315.6	1315.7	1315.7	1316.4	1317.2	1317.9	1318.7	1318.1
160°	1330.3	1329.7	1330.0	1330.2	1330.4	1330.6	1331.6	1332.5	1333.4	1334.4	1333.9
162.5°	1343.5	1343.0	1343.2	1343.5	1343.7	1343.9	1345.2	1346.5	1347.8	1349.1	1348.7
165°	1361.4	1360.8	1361.0	1361.3	1361.5	1361.7	1363.2	1364.5	1365.9	1367.3	1367.0
167.5°	1374.5	1373.9	1374.1	1374.3	1374.6	1374.8	1376.4	1378.1	1379.7	1381.4	1381.3
170°	1381.2	1380.5	1380.7	1381.0	1381.2	1381.4	1383.3	1385.1	1387.0	1388.8	1388.7
172.5°	1386.2	1385.5	1386.0	1386.4	1386.8	1387.2	1388.9	1390.5	1392.2	1393.8	1393.7
175°	1392.5	1391.9	1392.1	1392.4	1392.6	1392.9	1394.6	1396.5	1398.4	1400.2	1400.1
177.5°	1396.1	1395.6	1395.8	1396.0	1396.2	1396.3	1397.7	1398.9	1400.3	1401.5	1401.4
180°	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0



TEST NUMBER: P333574-940

CATALOG NUMBER: S125RDIP-S850D1205U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9
2.5°	1080.5	1076.5	1075.3	1076.8	1075.3	1076.5	1080.5	1080.8	1081.3	1084.2	1080.1
5°	996.8	992.3	994.5	993.6	994.5	992.3	996.8	1001.5	1002.5	1006.6	1009.4
7.5°	923.4	917.6	911.5	913.5	911.5	917.6	923.4	923.5	930.7	936.0	939.7
10°	871.8	867.3	864.4	866.7	864.4	867.3	871.8	877.9	880.7	887.2	894.1
12.5°	828.5	825.7	823.3	822.3	823.3	825.7	828.5	834.9	841.4	849.0	856.7
15°	769.5	764.0	761.7	755.6	761.7	764.0	769.5	775.1	787.6	790.9	802.5
17.5°	715.2	713.4	707.3	704.7	707.3	713.4	715.2	719.9	725.7	737.6	746.3
20°	683.0	681.1	675.1	678.8	675.1	681.1	683.0	689.9	694.6	704.3	712.6
22.5°	656.3	652.2	650.2	649.2	650.2	652.2	656.3	659.5	665.7	674.6	684.0
25°	618.6	612.6	610.3	607.5	610.3	612.6	618.6	620.5	627.0	635.7	640.8
27.5°	581.0	577.7	574.7	574.0	574.7	577.7	581.0	583.6	589.2	596.9	606.1
30°	556.5	553.3	551.0	551.0	551.0	553.3	556.5	562.1	566.2	573.2	580.1
32.5°	534.7	532.2	529.9	529.5	529.9	532.2	534.7	537.7	542.6	550.3	557.6
35°	502.8	499.2	498.2	495.4	498.2	499.2	502.8	505.2	510.2	515.8	521.8
37.5°	469.8	466.7	466.6	466.4	466.6	466.7	469.8	473.9	478.1	483.1	490.5
40°	448.7	446.4	445.9	442.6	445.9	446.4	448.7	450.5	455.1	461.6	467.2
42.5°	426.1	424.9	423.3	421.9	423.3	424.9	426.1	429.8	433.6	438.3	445.3
45°	395.4	392.2	392.2	389.9	392.2	392.2	395.4	398.7	400.6	406.1	415.4
47.5°	363.7	361.2	361.5	359.1	361.5	361.2	363.7	364.8	367.7	373.2	378.3
50°	342.6	341.3	340.8	339.8	340.8	341.3	342.6	342.1	345.9	351.0	357.9
52.5°	321.6	320.8	322.6	320.6	322.6	320.8	321.6	322.5	325.1	328.4	334.9
55°	293.1	291.7	294.4	291.7	294.4	291.7	293.1	292.1	293.1	296.3	300.5
57.5°	260.4	259.1	261.6	260.2	261.6	259.1	260.4	260.6	263.3	263.9	267.5
60°	238.9	236.1	237.6	238.0	237.6	236.1	238.9	239.9	240.8	241.2	245.0
62.5°	213.4	211.7	212.7	210.6	212.7	211.7	213.4	215.4	217.4	219.7	221.9
65°	177.4	175.9	174.1	173.2	174.1	175.9	177.4	178.3	183.3	186.1	191.2
67.5°	149.0	145.7	145.6	146.3	145.6	145.7	149.0	148.8	152.5	154.7	158.2
70°	128.2	128.2	127.8	127.8	127.8	128.2	128.2	131.0	132.9	134.7	137.1
72.5°	113.8	113.4	112.6	112.3	112.6	113.4	113.8	114.8	115.8	117.7	120.0
75°	91.7	92.1	91.2	90.8	91.2	92.1	91.7	91.7	93.5	94.0	94.9
77.5°	67.7	65.7	66.8	65.7	66.8	65.7	67.7	69.6	70.2	72.2	72.3
80°	51.4	50.9	52.3	50.9	52.3	50.9	51.4	51.4	52.8	53.7	56.0
82.5°	40.7	40.2	40.8	39.9	40.8	40.2	40.7	40.3	40.9	42.3	41.9
85°	24.5	24.1	23.6	24.1	23.6	24.1	24.5	24.1	23.6	24.1	24.5
87.5°	13.1	12.8	13.0	13.1	13.0	12.8	13.1	12.6	12.8	12.5	12.3
90°	22.8	23.5	24.2	24.9	24.2	23.5	22.8	22.1	21.2	20.1	18.9
92.5°	22.2	22.6	22.9	23.2	22.9	22.6	22.2	21.9	21.2	20.1	18.9
95°	21.8	21.8	21.8	21.8	21.8	21.8	21.8	21.8	21.2	20.1	18.9
97.5°	21.8	21.8	21.8	21.8	21.8	21.8	21.8	21.8	25.0	31.5	38.0
100°	24.5	23.6	22.6	21.8	22.6	23.6	24.5	25.4	43.1	77.4	111.7
102.5°	177.4	161.7	146.1	130.4	146.1	161.7	177.4	193.1	204.1	210.6	217.0
105°	308.4	308.3	308.0	307.8	308.0	308.3	308.4	308.7	308.8	308.8	308.8
107.5°	390.0	389.4	388.7	388.0	388.7	389.4	390.0	390.7	391.1	391.0	391.0
110°	442.8	443.1	443.4	443.5	443.4	443.1	442.8	442.6	442.8	443.5	444.3



TEST NUMBER: P333574-940

CATALOG NUMBER: S125RDIP-S850D1205U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	494.3	493.9	493.7	493.3	493.7	493.9	494.3	494.5	495.2	496.1	497.0
115°	572.0	570.7	569.3	567.9	569.3	570.7	572.0	573.5	574.6	575.5	576.4
117.5°	649.3	648.7	648.1	647.5	648.1	648.7	649.3	649.9	650.8	652.0	653.2
120°	699.9	698.7	697.6	696.4	697.6	698.7	699.9	701.1	701.9	702.3	702.8
122.5°	746.8	745.5	744.2	742.9	744.2	745.5	746.8	748.1	749.1	749.6	750.0
125°	815.6	814.9	814.2	813.5	814.2	814.9	815.6	816.3	817.1	818.0	818.9
127.5°	878.2	876.4	874.7	873.0	874.7	876.4	878.2	879.9	880.9	881.5	881.9
130°	919.5	918.5	917.3	916.1	917.3	918.5	919.5	920.7	921.7	922.3	923.0
132.5°	959.4	958.2	957.1	955.9	957.1	958.2	959.4	960.6	961.2	961.3	961.4
135°	1014.6	1013.2	1011.8	1010.4	1011.8	1013.2	1014.6	1015.9	1016.9	1017.4	1017.8
137.5°	1068.7	1067.6	1066.3	1065.1	1066.3	1067.6	1068.7	1070.0	1070.5	1070.4	1070.3
140°	1101.6	1100.3	1098.9	1097.5	1098.9	1100.3	1101.6	1103.0	1103.5	1103.0	1102.5
142.5°	1132.3	1131.0	1129.5	1128.2	1129.5	1131.0	1132.3	1133.7	1134.3	1134.3	1134.2
145°	1177.2	1175.9	1174.5	1173.1	1174.5	1175.9	1177.2	1178.7	1179.2	1179.0	1178.8
147.5°	1215.2	1213.5	1211.9	1210.2	1211.9	1213.5	1215.2	1216.8	1217.5	1217.3	1217.0
150°	1239.8	1238.0	1236.1	1234.3	1236.1	1238.0	1239.8	1241.6	1242.3	1241.9	1241.4
152.5°	1261.6	1260.0	1258.3	1256.7	1258.3	1260.0	1261.6	1263.3	1263.9	1263.5	1262.9
155°	1291.6	1289.8	1287.9	1286.1	1287.9	1289.8	1291.6	1293.4	1294.1	1293.3	1292.6
157.5°	1316.3	1314.5	1312.6	1310.7	1312.6	1314.5	1316.3	1318.1	1318.7	1317.9	1317.2
160°	1332.0	1330.2	1328.4	1326.5	1328.4	1330.2	1332.0	1333.9	1334.4	1333.4	1332.5
162.5°	1346.7	1344.6	1342.6	1340.6	1342.6	1344.6	1346.7	1348.7	1349.1	1347.8	1346.5
165°	1365.2	1363.3	1361.5	1359.7	1361.5	1363.3	1365.2	1367.0	1367.3	1365.9	1364.5
167.5°	1379.1	1377.1	1375.0	1373.0	1375.0	1377.1	1379.1	1381.3	1381.4	1379.7	1378.1
170°	1386.6	1384.6	1382.5	1380.4	1382.5	1384.6	1386.6	1388.7	1388.8	1387.0	1385.1
172.5°	1391.6	1389.6	1387.4	1385.4	1387.4	1389.6	1391.6	1393.7	1393.8	1392.2	1390.5
175°	1398.0	1396.0	1393.8	1391.8	1393.8	1396.0	1398.0	1400.1	1400.2	1398.4	1396.5
177.5°	1400.0	1398.5	1397.0	1395.5	1397.0	1398.5	1400.0	1401.4	1401.5	1400.3	1398.9
180°	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0



TEST NUMBER: P333574-940

CATALOG NUMBER: S125RDIP-S850D1205U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9
2.5°	1081.3	1085.3	1087.5	1092.7	1100.1	1103.8	1109.0	1112.8	1117.9	1124.2	1129.4
5°	1011.2	1022.3	1029.7	1041.3	1052.0	1062.7	1076.0	1085.7	1098.8	1113.6	1125.2
7.5°	946.2	960.1	972.4	987.7	1005.3	1019.0	1036.5	1054.4	1074.7	1095.7	1115.5
10°	904.7	918.6	933.9	952.9	970.4	989.0	1009.9	1030.6	1056.1	1079.8	1106.6
12.5°	863.6	879.0	896.2	917.3	938.6	962.3	983.6	1007.0	1034.3	1065.0	1093.7
15°	812.6	827.4	846.0	864.0	888.5	914.4	942.7	973.7	1004.3	1038.6	1074.2
17.5°	757.9	774.2	794.5	815.5	841.3	871.6	899.4	933.4	967.7	1007.6	1049.5
20°	722.3	739.0	763.0	786.2	809.9	839.5	872.4	907.0	943.6	985.8	1032.5
22.5°	694.2	706.1	729.7	753.2	781.0	811.3	843.5	879.7	919.5	963.1	1012.2
25°	652.4	666.3	683.4	707.9	736.6	768.7	801.0	839.5	883.0	927.5	979.7
27.5°	615.3	626.7	643.6	662.9	691.4	724.6	759.1	799.2	843.8	889.1	944.1
30°	589.0	601.5	617.7	638.0	660.8	696.9	732.0	771.4	816.8	863.5	920.0
32.5°	566.0	578.9	592.8	612.1	636.7	668.7	705.0	743.6	789.7	837.9	893.0
35°	533.9	542.7	555.6	574.6	598.7	624.6	661.6	702.4	747.3	797.3	852.4
37.5°	497.0	508.4	521.3	537.8	558.8	586.9	621.3	662.5	704.3	752.2	802.5
40°	475.5	486.2	500.5	512.6	534.8	560.3	591.7	634.8	676.5	721.4	767.2
42.5°	453.7	464.0	476.1	491.1	511.0	535.8	565.1	605.2	649.8	692.1	730.6
45°	419.5	430.2	441.8	455.6	474.1	498.2	527.4	563.9	602.9	641.8	670.9
47.5°	386.8	396.8	407.8	422.0	439.1	462.3	488.4	520.7	558.5	591.6	612.4
50°	363.5	372.7	384.8	398.7	415.4	437.1	462.1	494.0	525.5	555.6	574.6
52.5°	340.5	350.9	362.9	375.0	390.9	412.7	435.8	463.3	493.3	517.8	533.5
55°	306.0	315.8	326.9	339.4	355.2	373.6	398.2	420.0	443.5	464.4	473.7
57.5°	272.8	281.3	291.8	304.8	319.0	336.2	355.6	376.6	393.2	408.0	418.4
60°	250.9	258.3	268.0	279.2	294.4	310.2	327.8	347.2	360.3	372.7	382.5
62.5°	228.7	235.8	245.1	255.1	268.6	283.2	300.1	315.8	328.4	336.8	348.0
65°	195.4	202.3	210.2	220.9	231.5	243.5	258.9	270.4	279.2	288.5	295.4
67.5°	164.3	170.1	177.6	185.9	194.9	206.5	218.4	228.0	234.0	239.6	247.9
70°	144.0	148.6	154.6	161.1	170.9	182.4	191.7	199.1	203.3	208.8	219.0
72.5°	123.2	128.6	134.3	140.8	148.6	158.4	166.5	173.9	176.6	181.0	187.5
75°	97.2	100.0	104.7	109.2	114.9	123.1	131.0	132.9	135.2	138.9	143.6
77.5°	73.6	76.1	77.8	81.0	85.3	92.0	96.2	99.0	99.5	100.9	105.5
80°	58.3	59.7	61.6	63.9	65.7	71.3	73.7	76.4	77.3	78.7	81.1
82.5°	42.8	44.1	45.3	47.3	50.2	52.4	54.8	57.5	57.7	58.7	59.2
85°	25.0	25.5	24.5	25.5	25.9	26.8	29.2	31.5	31.0	30.6	31.9
87.5°	12.4	12.2	11.5	12.3	11.2	11.3	11.0	11.0	11.3	11.7	12.0
90°	17.7	16.6	15.0	13.4	11.8	10.2	8.4	6.6	4.7	2.9	1.1
92.5°	17.7	16.6	15.2	13.7	12.3	10.9	10.8	12.1	13.4	14.7	16.0
95°	17.7	16.6	25.3	34.1	42.8	51.6	56.3	57.0	57.7	58.4	59.0
97.5°	44.5	51.0	68.3	85.6	102.9	120.3	128.3	127.1	125.8	124.6	123.3
100°	146.0	180.3	179.4	178.5	177.5	176.6	175.8	175.1	174.4	173.8	173.1
102.5°	223.6	230.1	229.5	229.0	228.4	227.8	227.1	226.2	225.4	224.5	223.6
105°	308.8	308.8	308.8	308.8	308.8	308.8	308.4	307.5	306.5	305.6	304.7
107.5°	390.9	390.9	390.5	389.9	389.5	389.1	388.9	388.9	388.9	388.9	388.9
110°	445.0	445.6	445.1	444.7	444.3	443.8	443.5	443.5	443.5	443.5	443.5



TEST NUMBER: P333574-940

CATALOG NUMBER: S125RDIP-S850D1205U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	497.8	498.6	498.4	498.1	497.8	497.6	497.1	496.6	496.1	495.5	495.0
115°	577.4	578.3	578.0	577.8	577.6	577.4	576.7	575.5	574.4	573.2	572.0
117.5°	654.4	655.6	654.7	653.8	653.0	652.1	651.7	651.8	651.8	651.8	651.8
120°	703.2	703.6	702.9	702.3	701.6	700.9	700.7	700.9	701.2	701.3	701.6
122.5°	750.5	750.9	750.6	750.3	749.9	749.7	749.0	748.1	747.3	746.5	745.6
125°	819.8	820.7	820.7	820.7	820.7	820.7	819.9	818.3	816.7	815.1	813.5
127.5°	882.4	883.0	883.1	883.2	883.3	883.5	883.0	881.8	880.7	879.6	878.4
130°	923.7	924.4	924.2	924.0	923.7	923.5	922.8	921.7	920.5	919.4	918.2
132.5°	961.6	961.7	962.2	962.7	963.2	963.8	963.3	962.0	960.6	959.3	958.0
135°	1018.2	1018.7	1019.1	1019.7	1020.1	1020.6	1020.1	1018.7	1017.4	1015.9	1014.6
137.5°	1070.2	1070.1	1070.5	1070.9	1071.4	1071.7	1071.4	1070.1	1069.0	1067.8	1066.6
140°	1102.1	1101.6	1101.9	1102.1	1102.3	1102.5	1102.4	1102.0	1101.5	1101.1	1100.5
142.5°	1134.1	1134.0	1133.6	1133.3	1133.0	1132.7	1132.4	1132.1	1131.8	1131.5	1131.2
145°	1178.6	1178.3	1178.3	1178.3	1178.3	1178.3	1178.0	1177.6	1177.1	1176.7	1176.3
147.5°	1216.7	1216.5	1216.2	1215.8	1215.6	1215.3	1215.2	1215.3	1215.4	1215.5	1215.6
150°	1240.9	1240.5	1240.0	1239.6	1239.1	1238.7	1238.7	1239.1	1239.6	1240.0	1240.5
152.5°	1262.5	1262.0	1261.6	1261.1	1260.7	1260.2	1260.4	1261.5	1262.5	1263.6	1264.5
155°	1292.0	1291.3	1290.8	1290.3	1289.9	1289.4	1289.9	1291.3	1292.6	1294.1	1295.4
157.5°	1316.4	1315.7	1315.7	1315.6	1315.6	1315.5	1315.9	1316.8	1317.6	1318.4	1319.3
160°	1331.6	1330.6	1330.4	1330.2	1330.0	1329.7	1330.3	1331.7	1333.1	1334.4	1335.9
162.5°	1345.2	1343.9	1343.7	1343.5	1343.2	1343.0	1343.5	1345.0	1346.3	1347.7	1349.1
165°	1363.2	1361.7	1361.5	1361.3	1361.0	1360.8	1361.4	1362.8	1364.1	1365.6	1366.9
167.5°	1376.4	1374.8	1374.6	1374.3	1374.1	1373.9	1374.5	1375.9	1377.3	1378.8	1380.2
170°	1383.3	1381.4	1381.2	1381.0	1380.7	1380.5	1381.2	1382.8	1384.4	1386.1	1387.7
172.5°	1388.9	1387.2	1386.8	1386.4	1386.0	1385.5	1386.2	1387.8	1389.4	1391.0	1392.6
175°	1394.6	1392.9	1392.6	1392.4	1392.1	1391.9	1392.5	1393.8	1395.3	1396.6	1398.0
177.5°	1397.7	1396.3	1396.2	1396.0	1395.8	1395.6	1396.1	1397.2	1398.3	1399.4	1400.5
180°	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0



TEST NUMBER: P333574-940

CATALOG NUMBER: S125RDIP-S850D1205U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9
2.5°	1133.5	1136.8	1141.7	1147.2	1151.6	1156.5	1159.0	1159.0	1161.3	1166.1	1172.3
5°	1136.8	1148.8	1160.3	1175.2	1186.7	1200.2	1210.3	1220.0	1228.9	1239.9	1251.5
7.5°	1135.8	1155.7	1176.6	1200.0	1225.7	1246.2	1267.2	1283.7	1299.9	1321.2	1338.0
10°	1132.1	1158.0	1186.2	1215.8	1248.3	1276.6	1302.0	1325.2	1347.4	1370.6	1391.3
12.5°	1125.4	1158.4	1192.9	1228.5	1269.4	1301.7	1334.6	1359.2	1385.2	1410.5	1436.2
15°	1115.4	1154.3	1196.0	1245.5	1295.6	1331.7	1364.1	1396.0	1420.0	1448.8	1473.4
17.5°	1094.8	1144.9	1197.3	1251.4	1299.5	1341.5	1375.5	1405.8	1431.5	1463.0	1496.4
20°	1082.5	1136.8	1191.3	1249.2	1295.0	1338.1	1371.0	1402.5	1434.4	1475.6	1516.4
22.5°	1065.5	1123.4	1181.3	1236.3	1284.7	1326.2	1360.2	1398.8	1440.7	1487.5	1536.8
25°	1038.6	1098.3	1155.7	1208.0	1255.3	1297.9	1344.2	1396.0	1447.0	1508.5	1579.4
27.5°	1004.4	1061.9	1113.2	1168.5	1215.4	1269.6	1327.4	1383.6	1457.1	1541.8	1630.2
30°	978.8	1033.5	1082.1	1134.4	1187.7	1247.4	1312.2	1378.4	1465.9	1565.5	1670.6
32.5°	949.2	998.6	1046.9	1097.3	1158.8	1224.4	1293.3	1374.3	1478.9	1592.1	1700.9
35°	897.8	942.3	989.0	1045.0	1110.4	1181.6	1269.6	1368.2	1494.6	1616.4	1714.1
37.5°	843.9	879.0	926.0	985.1	1056.1	1138.6	1238.5	1358.3	1488.2	1597.4	1639.0
40°	802.5	835.3	884.8	946.9	1017.3	1107.5	1219.6	1342.7	1473.4	1549.3	1546.0
42.5°	761.3	794.5	842.2	904.6	978.0	1079.1	1194.4	1322.4	1432.6	1461.5	1401.2
45°	698.2	729.2	776.1	839.0	917.7	1023.8	1145.0	1267.7	1338.1	1291.4	1171.9
47.5°	634.0	664.1	707.5	769.2	855.1	966.1	1080.8	1181.4	1191.3	1090.9	947.6
50°	591.7	620.0	661.2	726.9	810.3	918.6	1029.3	1108.5	1084.0	961.3	813.5
52.5°	550.6	577.7	616.4	678.4	763.6	869.8	968.6	1030.6	973.9	843.5	710.5
55°	489.9	515.8	554.7	611.6	688.9	786.2	872.8	895.5	812.2	680.6	573.2
57.5°	432.2	451.2	489.6	539.9	614.5	700.3	762.3	758.2	666.3	547.9	470.8
60°	394.0	411.2	447.7	494.0	564.9	641.8	685.3	666.7	573.6	476.0	401.9
62.5°	358.5	374.5	405.1	447.7	508.5	575.4	607.1	581.6	493.7	407.9	348.9
65°	304.7	316.2	340.8	380.1	427.8	474.1	502.4	464.8	387.1	322.3	277.8
67.5°	254.4	264.4	286.2	314.5	347.3	379.3	390.7	355.6	295.2	251.5	220.2
70°	221.8	231.0	245.8	272.2	294.0	316.7	322.3	290.8	240.3	207.0	187.5
72.5°	190.6	199.2	212.1	230.8	245.8	259.0	261.5	232.3	193.6	170.7	155.7
75°	145.3	152.8	161.1	168.1	177.8	180.1	179.1	156.5	135.6	120.4	112.1
77.5°	106.8	109.9	115.0	117.8	118.2	118.1	113.3	99.0	88.3	81.9	78.6
80°	82.4	84.7	86.1	87.0	87.5	82.8	77.8	69.0	65.3	61.6	57.4
82.5°	59.8	61.4	62.8	63.0	60.5	56.6	51.9	47.5	44.9	43.1	41.5
85°	32.4	32.9	32.4	30.1	26.8	25.5	24.5	23.6	23.2	22.6	22.6
87.5°	12.0	11.3	9.8	10.6	10.9	10.9	11.2	11.1	11.1	11.3	11.6
90°	2.9	4.7	6.6	8.4	10.2	11.8	13.4	15.0	16.6	17.7	18.9
92.5°	14.7	13.4	12.1	10.8	10.9	12.3	13.7	15.2	16.6	17.7	18.9
95°	58.4	57.7	57.0	56.3	51.6	42.8	34.1	25.3	16.6	17.7	18.9
97.5°	124.6	125.8	127.1	128.3	120.3	102.9	85.6	68.3	51.0	44.5	38.0
100°	173.8	174.4	175.1	175.8	176.6	177.5	178.5	179.4	180.3	146.0	111.7
102.5°	224.5	225.4	226.2	227.1	227.8	228.4	229.0	229.5	230.1	223.6	217.0
105°	305.6	306.5	307.5	308.4	308.8	308.8	308.8	308.8	308.8	308.8	308.8
107.5°	388.9	388.9	388.9	388.9	389.1	389.5	389.9	390.5	390.9	390.9	391.0
110°	443.5	443.5	443.5	443.5	443.8	444.3	444.7	445.1	445.6	445.0	444.3



TEST NUMBER: P333574-940

CATALOG NUMBER: S125RDIP-S850D1205U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	495.5	496.1	496.6	497.1	497.6	497.8	498.1	498.4	498.6	497.8	497.0
115°	573.2	574.4	575.5	576.7	577.4	577.6	577.8	578.0	578.3	577.4	576.4
117.5°	651.8	651.8	651.8	651.7	652.1	653.0	653.8	654.7	655.6	654.4	653.2
120°	701.3	701.2	700.9	700.7	700.9	701.6	702.3	702.9	703.6	703.2	702.8
122.5°	746.5	747.3	748.1	749.0	749.7	749.9	750.3	750.6	750.9	750.5	750.0
125°	815.1	816.7	818.3	819.9	820.7	820.7	820.7	820.7	820.7	819.8	818.9
127.5°	879.6	880.7	881.8	883.0	883.5	883.3	883.2	883.1	883.0	882.4	881.9
130°	919.4	920.5	921.7	922.8	923.5	923.7	924.0	924.2	924.4	923.7	923.0
132.5°	959.3	960.6	962.0	963.3	963.8	963.2	962.7	962.2	961.7	961.6	961.4
135°	1015.9	1017.4	1018.7	1020.1	1020.6	1020.1	1019.7	1019.1	1018.7	1018.2	1017.8
137.5°	1067.8	1069.0	1070.1	1071.4	1071.7	1071.4	1070.9	1070.5	1070.1	1070.2	1070.3
140°	1101.1	1101.5	1102.0	1102.4	1102.5	1102.3	1102.1	1101.9	1101.6	1102.1	1102.5
142.5°	1131.5	1131.8	1132.1	1132.4	1132.7	1133.0	1133.3	1133.6	1134.0	1134.1	1134.2
145°	1176.7	1177.1	1177.6	1178.0	1178.3	1178.3	1178.3	1178.3	1178.3	1178.6	1178.8
147.5°	1215.5	1215.4	1215.3	1215.2	1215.3	1215.6	1215.8	1216.2	1216.5	1216.7	1217.0
150°	1240.0	1239.6	1239.1	1238.7	1238.7	1239.1	1239.6	1240.0	1240.5	1240.9	1241.4
152.5°	1263.6	1262.5	1261.5	1260.4	1260.2	1260.7	1261.1	1261.6	1262.0	1262.5	1262.9
155°	1294.1	1292.6	1291.3	1289.9	1289.4	1289.9	1290.3	1290.8	1291.3	1292.0	1292.6
157.5°	1318.4	1317.6	1316.8	1315.9	1315.5	1315.6	1315.6	1315.7	1315.7	1316.4	1317.2
160°	1334.4	1333.1	1331.7	1330.3	1329.7	1330.0	1330.2	1330.4	1330.6	1331.6	1332.5
162.5°	1347.7	1346.3	1345.0	1343.5	1343.0	1343.2	1343.5	1343.7	1343.9	1345.2	1346.5
165°	1365.6	1364.1	1362.8	1361.4	1360.8	1361.0	1361.3	1361.5	1361.7	1363.2	1364.5
167.5°	1378.8	1377.3	1375.9	1374.5	1373.9	1374.1	1374.3	1374.6	1374.8	1376.4	1378.1
170°	1386.1	1384.4	1382.8	1381.2	1380.5	1380.7	1381.0	1381.2	1381.4	1383.3	1385.1
172.5°	1391.0	1389.4	1387.8	1386.2	1385.5	1386.0	1386.4	1386.8	1387.2	1388.9	1390.5
175°	1396.6	1395.3	1393.8	1392.5	1391.9	1392.1	1392.4	1392.6	1392.9	1394.6	1396.5
177.5°	1399.4	1398.3	1397.2	1396.1	1395.6	1395.8	1396.0	1396.2	1396.3	1397.7	1398.9
180°	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0



TEST NUMBER: P333574-940

CATALOG NUMBER: S125RDIP-S850D1205U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9
2.5°	1177.1	1177.1	1183.5	1183.1	1187.2	1185.7	1186.4
5°	1265.4	1273.3	1280.2	1284.9	1291.8	1293.7	1292.7
7.5°	1356.9	1374.4	1383.0	1394.6	1396.8	1402.8	1402.2
10°	1413.6	1430.7	1443.7	1453.8	1459.0	1465.4	1465.9
12.5°	1458.0	1472.6	1484.1	1493.5	1499.7	1501.7	1503.0
15°	1492.8	1509.0	1522.4	1535.8	1543.7	1549.7	1553.0
17.5°	1527.8	1552.8	1576.5	1594.7	1605.7	1614.9	1614.8
20°	1554.8	1583.5	1613.2	1634.0	1655.3	1664.6	1666.0
22.5°	1583.7	1627.6	1665.8	1698.1	1726.1	1735.7	1739.3
25°	1643.7	1701.1	1760.0	1805.4	1837.7	1856.7	1859.5
27.5°	1716.2	1793.9	1855.8	1897.6	1924.6	1938.7	1941.7
30°	1767.4	1839.2	1894.7	1926.2	1938.7	1940.5	1933.6
32.5°	1790.3	1844.0	1866.2	1864.3	1839.8	1823.5	1817.2
35°	1762.3	1751.1	1696.9	1632.2	1582.6	1551.1	1542.7
37.5°	1603.7	1507.9	1408.2	1310.3	1258.1	1231.6	1186.1
40°	1447.4	1310.8	1207.1	1124.7	1065.9	1018.6	1007.5
42.5°	1271.0	1130.1	1026.4	955.7	908.8	876.4	862.3
45°	1021.5	900.1	814.5	760.3	724.2	700.5	689.9
47.5°	817.0	723.1	660.7	620.5	593.1	572.5	566.8
50°	704.7	629.7	576.9	543.1	522.3	506.6	500.1
52.5°	612.1	551.5	511.0	483.1	463.4	453.6	448.2
55°	505.2	452.8	423.7	401.4	390.3	382.5	378.7
57.5°	413.1	375.3	354.0	338.7	328.4	323.3	321.6
60°	361.6	332.0	312.5	300.5	293.6	287.0	285.3
62.5°	316.0	292.7	277.7	267.2	260.2	257.4	256.4
65°	254.7	239.4	228.3	221.8	216.2	215.3	214.8
67.5°	202.4	193.4	187.6	180.8	178.9	175.7	175.0
70°	173.2	167.1	160.2	157.9	155.6	152.3	152.8
72.5°	146.9	140.9	136.2	133.0	132.2	130.8	132.1
75°	107.5	105.6	103.7	101.4	100.5	100.5	100.0
77.5°	76.7	75.1	73.0	71.7	71.4	69.5	70.2
80°	55.6	53.2	52.3	52.8	51.4	50.9	50.9
82.5°	41.1	40.3	39.3	39.4	39.1	38.7	39.1
85°	22.6	22.2	22.2	21.8	21.8	21.3	21.3
87.5°	12.1	12.8	12.2	11.9	12.1	12.6	13.1
90°	20.1	21.2	22.1	22.8	23.5	24.2	24.9
92.5°	20.1	21.2	21.9	22.2	22.6	22.9	23.2
95°	20.1	21.2	21.8	21.8	21.8	21.8	21.8
97.5°	31.5	25.0	21.8	21.8	21.8	21.8	21.8
100°	77.4	43.1	25.4	24.5	23.6	22.6	21.8
102.5°	210.6	204.1	193.1	177.4	161.7	146.1	130.4
105°	308.8	308.8	308.7	308.4	308.3	308.0	307.8
107.5°	391.0	391.1	390.7	390.0	389.4	388.7	388.0
110°	443.5	442.8	442.6	442.8	443.1	443.4	443.5



TEST NUMBER: P333574-940

CATALOG NUMBER: S125RDIP-S850D1205U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	496.1	495.2	494.5	494.3	493.9	493.7	493.3
115°	575.5	574.6	573.5	572.0	570.7	569.3	567.9
117.5°	652.0	650.8	649.9	649.3	648.7	648.1	647.5
120°	702.3	701.9	701.1	699.9	698.7	697.6	696.4
122.5°	749.6	749.1	748.1	746.8	745.5	744.2	742.9
125°	818.0	817.1	816.3	815.6	814.9	814.2	813.5
127.5°	881.5	880.9	879.9	878.2	876.4	874.7	873.0
130°	922.3	921.7	920.7	919.5	918.5	917.3	916.1
132.5°	961.3	961.2	960.6	959.4	958.2	957.1	955.9
135°	1017.4	1016.9	1015.9	1014.6	1013.2	1011.8	1010.4
137.5°	1070.4	1070.5	1070.0	1068.7	1067.6	1066.3	1065.1
140°	1103.0	1103.5	1103.0	1101.6	1100.3	1098.9	1097.5
142.5°	1134.3	1134.3	1133.7	1132.3	1131.0	1129.5	1128.2
145°	1179.0	1179.2	1178.7	1177.2	1175.9	1174.5	1173.1
147.5°	1217.3	1217.5	1216.8	1215.2	1213.5	1211.9	1210.2
150°	1241.9	1242.3	1241.6	1239.8	1238.0	1236.1	1234.3
152.5°	1263.5	1263.9	1263.3	1261.6	1260.0	1258.3	1256.7
155°	1293.3	1294.1	1293.4	1291.6	1289.8	1287.9	1286.1
157.5°	1317.9	1318.7	1318.1	1316.3	1314.5	1312.6	1310.7
160°	1333.4	1334.4	1333.9	1332.0	1330.2	1328.4	1326.5
162.5°	1347.8	1349.1	1348.7	1346.7	1344.6	1342.6	1340.6
165°	1365.9	1367.3	1367.0	1365.2	1363.3	1361.5	1359.7
167.5°	1379.7	1381.4	1381.3	1379.1	1377.1	1375.0	1373.0
170°	1387.0	1388.8	1388.7	1386.6	1384.6	1382.5	1380.4
172.5°	1392.2	1393.8	1393.7	1391.6	1389.6	1387.4	1385.4
175°	1398.4	1400.2	1400.1	1398.0	1396.0	1393.8	1391.8
177.5°	1400.3	1401.5	1401.4	1400.0	1398.5	1397.0	1395.5
180°	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0

(END OF REPORT)