

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331403-930

Luminaire Tested: **SA2XXDIP-C865D925U930-4F0-1E-UDD-A1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331403-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C865D925U930-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 925 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5805.4 lumens
Efficiency: N/A
Efficacy: 96.0 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 60.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331403-930

CATALOG NUMBER: SA2XXDIP-C865D925U930-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331403-930

CATALOG NUMBER: SA2XXDIP-C865D925U930-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59	54
1	99	95	91	88	92	88	85	82	76	73	71	64	62	61	53	52	51	46
2	91	83	78	73	84	78	73	68	67	63	60	57	54	52	48	46	44	39
3	83	74	67	61	77	69	63	58	59	55	51	51	47	44	43	40	38	34
4	76	66	58	52	70	61	55	49	53	48	44	45	42	38	38	36	33	30
5	70	59	51	45	65	55	48	43	48	42	38	41	37	34	35	32	29	26
6	65	53	45	39	60	50	43	37	43	38	34	37	33	30	32	29	26	23
7	60	48	40	35	56	45	38	33	39	34	30	34	30	27	29	26	23	21
8	56	44	36	31	52	41	34	30	36	31	27	31	27	24	27	24	21	19
9	52	40	33	28	48	38	31	27	33	28	24	29	25	22	25	22	19	17
10	49	37	30	25	45	35	28	24	31	25	22	27	23	20	23	20	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	22727	22727	22727	22727
5°	25480	22875	20272	22875
10°	29198	22689	17544	22689
15°	32301	22272	15499	22272
20°	31809	21825	14129	21825
25°	28682	21232	13261	21232
30°	23702	20282	12629	20282
35°	17274	19291	12177	19291
40°	13797	18120	11927	18120
45°	12056	16762	11586	16762
50°	11333	15450	11359	15450
55°	10446	14117	11054	14117
60°	9571	12700	10585	12700
65°	8722	11427	10128	11427
70°	7917	10192	9451	10192
75°	7018	8808	8372	8808
80°	6034	7290	6741	7290
85°	5409	5409	4001	5409



TEST NUMBER: P331403-930

CATALOG NUMBER: SA2XXDIP-C865D925U930-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	134.1	2.3
10°-20°	389.7	6.7
20°-30°	565.6	9.7
30°-40°	596.9	10.3
40°-50°	528.5	9.1
50°-60°	421.7	7.3
60°-70°	286.7	4.9
70°-80°	147.0	2.5
80°-90°	39.3	0.7
90°-100°	61.1	1.1
100°-110°	189.8	3.3
110°-120°	324.3	5.6
120°-130°	426.5	7.3
130°-140°	478.7	8.2
140°-150°	469.4	8.1
150°-160°	393.7	6.8
160°-170°	261.1	4.5
170°-180°	91.3	1.6
0°-30°	1089.4	18.8
0°-40°	1686.3	29.0
0°-60°	2636.5	45.4
0°-90°	3109.4	53.6
90°-120°	575.2	9.9
90°-150°	1949.8	33.6
90°-180°	2696.0	46.4
0°-180°	5805.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1408	1408	1408	1408	1408	
5°	1572	1411	1251	1411	1572	157
15°	1932	1332	927	1332	1932	533
25°	1610	1192	744	1192	1610	728
35°	876	979	618	979	876	570
45°	528	734	507	734	528	415
55°	371	502	393	502	371	333
65°	228	299	265	299	228	227
75°	112	141	134	141	112	120
85°	29	29	22	29	29	33
90°	28	1	28	1	28	13
95°	50	42	50	42	50	56
105°	181	175	181	175	181	190
115°	326	326	326	326	326	321
125°	475	474	475	474	475	424
135°	620	613	620	613	620	477
145°	752	744	752	744	752	469
155°	857	850	857	850	857	394
165°	926	925	926	925	926	261
175°	959	962	959	962	959	91
180°	964	964	964	964	964	



TEST NUMBER: P331403-930
 CATALOG NUMBER: SA2XXDIP-C865D925U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6
2.5°	1472.6	1473.0	1473.9	1467.0	1466.1	1466.1	1460.0	1454.8	1448.8	1440.6	1441.4
5°	1572.1	1578.1	1580.2	1573.8	1564.0	1562.9	1553.7	1538.6	1524.5	1513.1	1505.0
7.5°	1690.9	1693.3	1688.0	1679.4	1672.2	1659.2	1642.1	1625.4	1601.9	1580.4	1564.3
10°	1780.9	1784.2	1775.0	1762.5	1752.2	1737.1	1712.2	1686.8	1656.0	1626.2	1602.4
12.5°	1849.3	1857.3	1845.5	1843.9	1826.3	1805.5	1775.9	1763.0	1719.6	1678.1	1652.6
15°	1932.4	1931.9	1933.0	1922.6	1909.7	1906.4	1875.1	1841.0	1779.9	1755.5	1713.4
17.5°	1908.4	1916.6	1920.4	1920.3	1919.9	1917.9	1907.9	1886.4	1855.7	1816.2	1767.5
20°	1851.3	1862.1	1863.7	1876.2	1883.2	1892.4	1896.1	1890.2	1871.3	1838.3	1796.1
22.5°	1763.0	1766.0	1771.1	1790.5	1805.7	1828.8	1840.8	1860.8	1853.5	1837.4	1802.1
25°	1610.0	1604.6	1623.5	1633.2	1668.4	1705.2	1731.7	1760.9	1786.9	1802.5	1792.3
27.5°	1426.3	1418.1	1446.5	1472.3	1500.9	1540.8	1582.1	1630.8	1671.4	1722.2	1739.6
30°	1271.3	1276.2	1303.3	1330.8	1374.1	1430.4	1476.9	1530.5	1588.4	1645.1	1684.7
32.5°	1104.2	1123.0	1140.1	1182.3	1220.5	1283.2	1351.4	1418.4	1490.5	1555.1	1616.2
35°	876.4	898.1	921.9	952.7	1006.2	1068.4	1135.0	1225.3	1323.8	1412.0	1484.5
37.5°	737.7	734.3	747.9	770.1	813.5	863.7	940.4	1029.6	1145.5	1249.1	1351.4
40°	654.6	652.4	662.2	682.7	715.8	752.5	819.6	898.1	1005.7	1132.3	1254.0
42.5°	597.5	598.8	604.1	618.6	641.3	671.6	721.8	788.6	887.1	1006.3	1137.2
45°	528.0	531.8	537.8	544.8	557.7	582.6	610.7	658.4	736.3	835.8	964.6
47.5°	478.0	478.1	484.2	490.3	498.1	512.1	535.0	564.9	619.9	700.9	811.6
50°	451.2	447.4	451.8	456.6	464.7	474.4	489.6	517.7	554.5	620.0	712.5
52.5°	418.3	418.4	422.3	424.1	431.4	441.2	454.9	474.4	507.8	559.0	635.0
55°	371.1	373.8	376.0	379.2	385.7	392.7	403.6	416.5	442.5	480.9	537.2
57.5°	326.8	327.6	329.8	336.0	340.1	346.6	356.9	368.6	385.5	413.9	456.2
60°	296.4	296.4	300.8	303.5	308.9	315.4	323.5	334.8	350.0	373.2	407.4
62.5°	268.8	268.3	270.0	274.5	278.6	284.7	292.8	302.4	316.7	337.4	365.4
65°	228.3	227.2	230.5	231.5	235.9	241.8	248.3	258.6	269.9	285.1	310.0
67.5°	189.3	190.6	192.4	194.4	196.8	203.1	207.4	214.7	224.3	236.8	253.7
70°	167.7	167.7	167.7	169.3	172.6	175.9	180.2	186.1	195.3	206.1	221.3
72.5°	143.5	145.2	146.9	145.9	150.1	152.1	157.2	160.5	169.3	176.3	189.6
75°	112.5	112.5	112.5	115.2	116.8	118.5	121.7	125.0	129.3	137.9	145.0
77.5°	84.0	83.7	84.3	85.0	86.7	88.6	89.6	92.5	96.5	100.5	106.5
80°	64.9	66.0	66.5	67.6	67.6	68.7	69.2	73.1	75.7	78.4	82.3
82.5°	50.2	50.4	50.5	50.7	51.2	51.9	53.2	54.5	55.4	57.6	60.6
85°	29.2	28.7	28.7	29.8	29.2	29.2	30.3	31.4	31.4	31.9	33.5
87.5°	16.8	16.7	17.1	16.7	16.6	17.1	17.2	16.8	17.3	17.8	17.4
90°	27.6	27.5	27.3	27.1	26.9	27.1	27.4	27.7	28.1	28.5	24.5
92.5°	26.3	26.3	26.3	26.3	26.3	26.2	26.1	26.0	25.9	25.8	24.9
95°	50.5	50.8	51.2	51.5	51.9	52.1	52.1	52.1	52.1	52.1	51.7
97.5°	87.4	87.4	87.5	87.5	87.6	87.6	87.6	87.6	87.6	87.6	86.8
100°	111.5	111.6	111.9	112.0	112.2	112.3	112.3	112.3	112.3	112.3	111.8
102.5°	138.8	139.0	139.2	139.3	139.5	139.6	139.4	139.3	139.1	139.0	138.3
105°	180.6	180.6	180.6	180.6	180.6	180.4	180.1	179.7	179.4	179.0	178.6
107.5°	220.0	220.9	221.7	222.5	223.3	223.6	223.6	223.4	223.2	223.1	223.1
110°	250.6	251.1	251.7	252.3	252.7	253.1	253.1	253.1	253.1	253.1	253.1



TEST NUMBER: P331403-930

CATALOG NUMBER: SA2XXDIP-C865D925U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	279.9	280.3	280.7	281.1	281.4	281.9	282.3	282.7	283.2	283.6	283.8
115°	325.5	326.0	326.5	327.1	327.6	328.0	328.2	328.3	328.6	328.7	329.1
117.5°	368.9	369.4	370.0	370.6	371.0	371.5	372.0	372.4	372.8	373.3	374.3
120°	399.5	400.1	400.6	401.1	401.7	401.9	401.9	401.9	401.9	401.9	403.4
122.5°	429.4	429.8	430.2	430.6	431.0	431.5	431.9	432.3	432.8	433.2	434.2
125°	475.2	475.3	475.5	475.7	475.9	476.2	476.8	477.4	477.8	478.4	479.0
127.5°	516.8	517.4	518.0	518.5	519.1	519.8	520.4	521.1	521.7	522.4	523.0
130°	546.7	547.5	548.2	548.9	549.7	550.2	550.6	550.9	551.3	551.6	552.0
132.5°	575.4	576.0	576.6	577.2	577.7	578.4	579.2	580.0	580.8	581.6	581.5
135°	620.0	620.5	621.1	621.6	622.2	622.5	622.7	622.9	623.1	623.2	622.9
137.5°	660.3	661.0	661.8	662.5	663.2	663.7	663.8	664.0	664.1	664.2	663.8
140°	688.4	689.1	689.7	690.5	691.2	691.6	691.6	691.6	691.6	691.6	690.7
142.5°	713.7	714.4	715.2	715.9	716.6	716.9	716.7	716.6	716.5	716.3	715.7
145°	751.8	752.5	753.3	754.0	754.7	755.0	754.8	754.6	754.4	754.2	753.2
147.5°	785.8	786.5	787.2	787.9	788.6	788.7	788.3	787.9	787.5	787.1	786.4
150°	808.0	808.5	809.0	809.6	810.1	810.1	809.6	809.0	808.5	808.0	807.2
152.5°	828.8	829.5	830.1	830.8	831.5	831.5	830.8	830.1	829.5	828.8	827.9
155°	856.7	857.3	857.9	858.3	858.9	858.8	857.9	857.0	856.1	855.1	854.6
157.5°	880.8	881.7	882.6	883.5	884.3	884.1	882.9	881.7	880.4	879.2	878.9
160°	895.8	896.5	897.2	898.0	898.7	898.5	897.4	896.3	895.3	894.1	894.0
162.5°	908.8	909.7	910.5	911.4	912.3	912.1	910.9	909.6	908.4	907.2	907.0
165°	925.9	926.8	927.7	928.6	929.5	929.4	928.1	926.8	925.5	924.3	924.3
167.5°	939.9	940.9	941.8	942.7	943.6	943.5	942.2	940.9	939.7	938.4	938.5
170°	947.1	948.1	949.3	950.3	951.4	951.3	950.1	948.8	947.5	946.2	946.4
172.5°	952.9	954.0	955.1	956.2	957.2	957.2	955.9	954.6	953.4	952.1	952.3
175°	959.3	960.3	961.4	962.5	963.6	963.5	962.2	961.0	959.7	958.5	958.8
177.5°	962.2	963.0	963.9	964.8	965.6	965.6	964.8	963.9	963.0	962.2	962.5
180°	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2

TEST NUMBER: P331403-930

CATALOG NUMBER: SA2XXDIP-C865D925U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6
2.5°	1444.5	1441.0	1438.8	1431.0	1424.1	1417.2	1415.0	1415.8	1406.4	1397.3	1393.3
5°	1500.7	1489.9	1479.6	1465.0	1447.7	1428.7	1419.0	1411.4	1392.5	1372.0	1360.1
7.5°	1551.1	1535.6	1515.9	1488.4	1463.1	1433.4	1414.5	1397.7	1370.0	1341.0	1323.2
10°	1581.8	1560.7	1535.3	1501.8	1471.0	1434.7	1409.2	1383.9	1351.4	1316.8	1295.1
12.5°	1608.3	1579.8	1554.8	1511.7	1475.3	1430.0	1399.8	1363.9	1329.8	1288.7	1267.5
15°	1671.1	1618.6	1571.0	1522.3	1477.4	1414.1	1380.6	1332.4	1287.5	1236.7	1212.4
17.5°	1719.7	1660.8	1585.8	1523.9	1471.5	1401.4	1352.2	1294.5	1241.4	1183.2	1150.1
20°	1747.4	1679.8	1599.1	1525.6	1462.8	1382.7	1329.2	1270.2	1208.0	1142.6	1106.9
22.5°	1763.8	1692.7	1613.0	1519.1	1445.5	1367.6	1300.2	1235.6	1172.6	1101.9	1064.5
25°	1769.0	1704.1	1619.8	1513.7	1423.9	1335.7	1254.6	1191.8	1115.5	1049.5	994.9
27.5°	1743.3	1696.7	1615.6	1503.5	1398.9	1295.8	1205.3	1134.2	1053.8	982.1	927.2
30°	1711.7	1684.7	1605.7	1493.1	1379.0	1268.1	1168.6	1087.9	1007.9	935.4	879.1
32.5°	1662.8	1656.9	1587.5	1478.4	1357.8	1233.1	1130.0	1048.6	959.9	888.6	834.9
35°	1566.7	1592.7	1548.8	1445.5	1317.8	1183.2	1071.7	978.7	886.7	818.5	768.2
37.5°	1437.9	1502.4	1490.9	1397.3	1264.0	1128.9	1005.8	908.6	820.9	752.1	702.7
40°	1349.2	1431.4	1443.3	1360.6	1225.9	1086.9	956.5	859.7	774.1	711.4	661.6
42.5°	1254.0	1350.1	1382.7	1316.5	1184.3	1042.7	912.3	812.0	727.4	666.4	622.2
45°	1094.5	1221.6	1280.5	1242.7	1115.0	970.0	835.8	734.1	657.3	600.0	565.9
47.5°	945.2	1084.1	1163.4	1150.1	1037.8	894.2	761.6	664.0	589.2	543.5	513.0
50°	839.6	982.4	1078.2	1082.6	982.4	840.2	707.1	615.1	546.4	503.7	478.7
52.5°	747.9	884.2	988.6	1011.5	920.6	783.9	658.2	566.6	506.1	466.8	444.6
55°	628.1	743.3	859.1	901.3	828.3	698.4	582.1	501.5	444.7	417.7	398.2
57.5°	522.2	618.2	725.1	771.8	726.8	615.6	506.5	436.6	390.4	366.8	351.9
60°	466.4	542.1	637.3	693.0	654.0	555.1	459.8	393.3	355.5	334.4	320.2
62.5°	414.4	481.5	562.0	612.9	591.7	498.4	413.1	354.3	321.6	301.9	291.7
65°	341.9	394.9	457.1	504.2	490.2	419.2	349.5	299.1	273.2	257.5	249.4
67.5°	281.5	319.8	363.0	404.2	392.9	342.7	286.6	247.4	228.1	214.6	209.7
70°	243.4	272.6	311.0	344.1	334.8	293.8	249.4	215.9	199.1	187.8	182.9
72.5°	207.1	231.1	260.4	287.4	281.2	247.0	210.0	184.7	171.8	161.3	157.4
75°	156.4	174.7	192.6	210.4	208.8	182.3	160.7	141.2	130.9	122.8	121.2
77.5°	115.4	125.7	137.9	148.5	145.5	130.4	113.4	102.2	94.7	89.3	88.4
80°	88.2	94.2	102.8	110.4	106.6	100.1	86.6	78.4	73.1	67.6	65.5
82.5°	63.9	69.9	75.1	79.2	76.3	70.2	61.9	56.3	53.2	49.4	48.6
85°	33.5	36.8	39.0	40.0	39.0	35.1	31.4	29.2	26.5	24.9	24.4
87.5°	17.1	16.3	15.5	15.7	14.0	13.6	11.4	9.7	9.7	9.7	9.3
90°	20.5	16.6	12.6	9.5	7.3	5.1	3.0	0.8	3.0	5.1	7.3
92.5°	24.0	23.1	22.1	20.9	19.2	17.7	16.1	14.5	16.1	17.7	19.2
95°	51.4	51.0	50.6	49.6	47.7	45.9	44.1	42.3	44.1	45.9	47.7
97.5°	86.2	85.5	84.8	83.6	82.1	80.5	78.9	77.3	78.9	80.5	82.1
100°	111.2	110.6	110.1	109.1	107.7	106.2	104.8	103.3	104.8	106.2	107.7
102.5°	137.6	136.9	136.2	135.3	134.1	133.0	131.8	130.7	131.8	133.0	134.1
105°	178.3	177.9	177.6	177.1	176.6	176.0	175.5	175.0	175.5	176.0	176.6
107.5°	223.1	223.1	223.1	222.7	221.9	221.1	220.3	219.5	220.3	221.1	221.9
110°	253.1	253.1	253.1	252.5	251.4	250.3	249.2	248.2	249.2	250.3	251.4



TEST NUMBER: P331403-930

CATALOG NUMBER: SA2XXDIP-C865D925U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	283.9	284.1	284.2	283.7	282.7	281.6	280.5	279.4	280.5	281.6	282.7
115°	329.5	329.8	330.1	329.8	328.7	327.6	326.5	325.5	326.5	327.6	328.7
117.5°	375.3	376.3	377.3	377.2	375.7	374.2	372.8	371.4	372.8	374.2	375.7
120°	404.8	406.3	407.7	407.7	406.3	404.8	403.4	401.9	403.4	404.8	406.3
122.5°	435.2	436.2	437.2	436.8	435.1	433.4	431.6	429.9	431.6	433.4	435.1
125°	479.5	480.0	480.6	480.0	478.4	476.8	475.2	473.5	475.2	476.8	478.4
127.5°	523.7	524.3	525.0	524.2	522.2	520.2	518.0	516.0	518.0	520.2	522.2
130°	552.4	552.7	553.1	552.1	549.8	547.4	545.0	542.7	545.0	547.4	549.8
132.5°	581.5	581.4	581.3	580.3	578.4	576.5	574.5	572.7	574.5	576.5	578.4
135°	622.5	622.2	621.8	620.6	618.6	616.6	614.7	612.7	614.7	616.6	618.6
137.5°	663.3	662.8	662.3	661.3	659.7	658.0	656.4	654.8	656.4	658.0	659.7
140°	689.7	688.8	687.9	686.7	685.1	683.5	681.8	680.2	681.8	683.5	685.1
142.5°	715.1	714.4	713.9	712.7	711.1	709.5	707.8	706.2	707.8	709.5	711.1
145°	752.0	751.0	749.9	748.7	747.5	746.2	744.9	743.6	744.9	746.2	747.5
147.5°	785.6	785.0	784.2	783.1	781.5	780.1	778.5	777.0	778.5	780.1	781.5
150°	806.5	805.8	805.0	804.1	803.1	801.9	800.9	799.8	800.9	801.9	803.1
152.5°	827.0	826.1	825.3	824.3	823.2	822.1	821.1	819.9	821.1	822.1	823.2
155°	854.0	853.5	853.0	852.4	851.9	851.3	850.8	850.3	850.8	851.3	851.9
157.5°	878.6	878.2	877.9	877.6	877.2	876.9	876.4	876.1	876.4	876.9	877.2
160°	893.8	893.6	893.5	893.2	892.8	892.4	892.1	891.8	892.1	892.4	892.8
162.5°	906.9	906.7	906.4	906.4	906.3	906.2	906.1	906.0	906.1	906.2	906.3
165°	924.3	924.3	924.3	924.4	924.5	924.7	925.0	925.1	925.0	924.7	924.5
167.5°	938.5	938.6	938.6	938.9	939.4	940.0	940.5	941.0	940.5	940.0	939.4
170°	946.6	946.8	947.0	947.3	947.9	948.4	948.9	949.5	948.9	948.4	947.9
172.5°	952.4	952.7	952.8	953.2	953.7	954.3	954.8	955.4	954.8	954.3	953.7
175°	959.2	959.5	959.9	960.3	960.9	961.4	962.0	962.5	962.0	961.4	960.9
177.5°	962.8	963.0	963.4	963.7	964.2	964.6	965.0	965.5	965.0	964.6	964.2
180°	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2



TEST NUMBER: P331403-930

CATALOG NUMBER: SA2XXDIP-C865D925U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6
2.5°	1389.0	1386.4	1377.4	1372.6	1364.8	1357.5	1352.7	1354.9	1356.6	1355.7	1354.5
5°	1349.2	1339.0	1323.2	1309.7	1300.0	1282.1	1274.6	1270.8	1267.5	1263.7	1260.0
7.5°	1301.9	1285.6	1263.1	1243.8	1225.6	1203.5	1190.8	1183.2	1175.5	1166.9	1159.4
10°	1268.1	1245.4	1221.6	1194.5	1172.9	1152.8	1135.0	1123.1	1112.3	1102.0	1094.5
12.5°	1232.6	1206.4	1177.0	1140.0	1116.1	1087.5	1084.8	1063.8	1046.9	1040.6	1031.7
15°	1176.2	1139.3	1102.0	1058.2	1039.3	1013.3	997.0	980.8	966.2	955.9	953.2
17.5°	1112.0	1064.4	1027.2	995.7	964.7	938.1	923.2	910.2	898.1	884.4	882.6
20°	1063.1	1021.9	981.4	953.7	921.9	894.8	876.4	863.4	853.1	845.1	838.0
22.5°	1016.8	971.8	934.6	904.4	872.9	851.1	836.6	824.0	815.5	806.5	799.9
25°	942.4	907.3	866.7	832.6	806.6	792.6	780.6	769.8	764.4	758.5	750.9
27.5°	877.3	838.3	800.4	774.0	751.1	738.7	730.3	722.8	717.8	714.3	710.0
30°	831.5	792.0	762.2	736.3	717.4	704.9	699.5	695.2	689.3	687.1	684.9
32.5°	787.3	751.8	726.4	703.8	685.7	677.7	672.7	668.8	664.1	661.9	657.6
35°	725.0	695.2	670.3	657.9	643.3	636.2	632.4	627.0	622.6	620.5	620.0
37.5°	666.2	640.3	623.9	608.0	601.8	597.5	592.3	588.6	587.3	586.9	586.4
40°	628.1	607.0	592.4	579.4	576.7	570.2	565.9	562.6	562.6	563.2	562.6
42.5°	593.5	574.5	561.7	550.4	547.2	543.4	539.1	538.8	539.7	541.5	539.7
45°	541.0	527.5	518.3	512.8	506.9	503.1	502.6	504.2	504.8	505.3	506.9
47.5°	492.8	483.7	475.4	469.4	466.8	466.2	465.5	468.4	471.0	472.0	474.4
50°	464.1	453.9	446.9	443.0	440.9	439.9	440.9	444.2	446.3	449.0	450.6
52.5°	432.1	424.9	420.0	417.1	416.2	416.9	417.1	420.8	424.3	425.2	426.0
55°	387.9	382.5	381.4	376.5	378.7	378.1	380.8	383.0	386.3	389.6	390.0
57.5°	343.7	339.4	336.5	337.0	337.6	340.0	342.3	346.0	349.5	352.9	353.3
60°	314.3	312.2	310.5	310.5	311.6	314.9	317.6	321.3	323.5	325.7	327.3
62.5°	287.5	285.4	283.7	284.5	287.4	289.3	292.4	294.5	296.7	298.8	299.6
65°	245.1	244.0	245.6	246.7	247.2	250.0	253.7	255.4	257.5	258.6	262.4
67.5°	206.0	206.2	206.0	207.5	210.7	211.3	214.9	218.7	219.1	221.2	223.6
70°	179.6	180.7	181.8	182.9	185.6	186.6	189.3	190.9	193.1	194.8	196.4
72.5°	155.4	155.6	156.7	156.5	158.7	161.1	163.4	165.0	167.1	169.3	170.8
75°	119.5	119.5	120.7	121.2	123.9	126.6	126.0	127.1	129.3	131.4	132.6
77.5°	87.3	86.1	87.3	87.9	88.7	91.0	91.4	92.9	95.4	94.7	95.9
80°	66.5	64.9	66.5	67.1	67.1	69.8	69.8	70.8	72.5	70.8	72.5
82.5°	47.5	46.7	47.9	48.0	48.9	49.0	49.9	50.1	51.7	51.0	51.7
85°	23.8	23.2	23.8	23.2	23.8	24.4	24.4	23.8	23.8	24.9	23.2
87.5°	9.3	9.5	9.8	10.6	10.9	11.3	10.8	10.8	10.7	9.7	9.7
90°	9.5	12.6	16.6	20.5	24.5	28.5	28.1	27.7	27.4	27.1	26.9
92.5°	20.9	22.1	23.1	24.0	24.9	25.8	25.9	26.0	26.1	26.2	26.3
95°	49.6	50.6	51.0	51.4	51.7	52.1	52.1	52.1	52.1	52.1	51.9
97.5°	83.6	84.8	85.5	86.2	86.8	87.6	87.6	87.6	87.6	87.6	87.6
100°	109.1	110.1	110.6	111.2	111.8	112.3	112.3	112.3	112.3	112.3	112.2
102.5°	135.3	136.2	136.9	137.6	138.3	139.0	139.1	139.3	139.4	139.6	139.5
105°	177.1	177.6	177.9	178.3	178.6	179.0	179.4	179.7	180.1	180.4	180.6
107.5°	222.7	223.1	223.1	223.1	223.1	223.1	223.2	223.4	223.6	223.6	223.3
110°	252.5	253.1	253.1	253.1	253.1	253.1	253.1	253.1	253.1	253.1	252.7



TEST NUMBER: P331403-930

CATALOG NUMBER: SA2XXDIP-C865D925U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	283.7	284.2	284.1	283.9	283.8	283.6	283.2	282.7	282.3	281.9	281.4
115°	329.8	330.1	329.8	329.5	329.1	328.7	328.6	328.3	328.2	328.0	327.6
117.5°	377.2	377.3	376.3	375.3	374.3	373.3	372.8	372.4	372.0	371.5	371.0
120°	407.7	407.7	406.3	404.8	403.4	401.9	401.9	401.9	401.9	401.9	401.7
122.5°	436.8	437.2	436.2	435.2	434.2	433.2	432.8	432.3	431.9	431.5	431.0
125°	480.0	480.6	480.0	479.5	479.0	478.4	477.8	477.4	476.8	476.2	475.9
127.5°	524.2	525.0	524.3	523.7	523.0	522.4	521.7	521.1	520.4	519.8	519.1
130°	552.1	553.1	552.7	552.4	552.0	551.6	551.3	550.9	550.6	550.2	549.7
132.5°	580.3	581.3	581.4	581.5	581.5	581.6	580.8	580.0	579.2	578.4	577.7
135°	620.6	621.8	622.2	622.5	622.9	623.2	623.1	622.9	622.7	622.5	622.2
137.5°	661.3	662.3	662.8	663.3	663.8	664.2	664.1	664.0	663.8	663.7	663.2
140°	686.7	687.9	688.8	689.7	690.7	691.6	691.6	691.6	691.6	691.6	691.2
142.5°	712.7	713.9	714.4	715.1	715.7	716.3	716.5	716.6	716.7	716.9	716.6
145°	748.7	749.9	751.0	752.0	753.2	754.2	754.4	754.6	754.8	755.0	754.7
147.5°	783.1	784.2	785.0	785.6	786.4	787.1	787.5	787.9	788.3	788.7	788.6
150°	804.1	805.0	805.8	806.5	807.2	808.0	808.5	809.0	809.6	810.1	810.1
152.5°	824.3	825.3	826.1	827.0	827.9	828.8	829.5	830.1	830.8	831.5	831.5
155°	852.4	853.0	853.5	854.0	854.6	855.1	856.1	857.0	857.9	858.8	858.9
157.5°	877.6	877.9	878.2	878.6	878.9	879.2	880.4	881.7	882.9	884.1	884.3
160°	893.2	893.5	893.6	893.8	894.0	894.1	895.3	896.3	897.4	898.5	898.7
162.5°	906.4	906.4	906.7	906.9	907.0	907.2	908.4	909.6	910.9	912.1	912.3
165°	924.4	924.3	924.3	924.3	924.3	924.3	925.5	926.8	928.1	929.4	929.5
167.5°	938.9	938.6	938.6	938.5	938.5	938.4	939.7	940.9	942.2	943.5	943.6
170°	947.3	947.0	946.8	946.6	946.4	946.2	947.5	948.8	950.1	951.3	951.4
172.5°	953.2	952.8	952.7	952.4	952.3	952.1	953.4	954.6	955.9	957.2	957.2
175°	960.3	959.9	959.5	959.2	958.8	958.5	959.7	961.0	962.2	963.5	963.6
177.5°	963.7	963.4	963.0	962.8	962.5	962.2	963.0	963.9	964.8	965.6	965.6
180°	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2



TEST NUMBER: P331403-930

CATALOG NUMBER: SA2XXDIP-C865D925U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6
2.5°	1350.1	1349.2	1349.2	1345.3	1349.2	1349.2	1350.1	1354.5	1355.7	1356.6	1354.9
5°	1252.4	1250.8	1248.1	1250.8	1248.1	1250.8	1252.4	1260.0	1263.7	1267.5	1270.8
7.5°	1155.8	1149.2	1148.3	1141.9	1148.3	1149.2	1155.8	1159.4	1166.9	1175.5	1183.2
10°	1085.2	1080.9	1080.4	1070.1	1080.4	1080.9	1085.2	1094.5	1102.0	1112.3	1123.1
12.5°	1031.6	1021.2	1023.2	1017.2	1023.2	1021.2	1031.6	1031.7	1040.6	1046.9	1063.8
15°	938.7	938.7	936.5	927.2	936.5	938.7	938.7	953.2	955.9	966.2	980.8
17.5°	871.9	870.7	865.6	868.2	865.6	870.7	871.9	882.6	884.4	898.1	910.2
20°	832.0	828.8	822.3	822.3	822.3	828.8	832.0	838.0	845.1	853.1	863.4
22.5°	794.4	794.2	787.3	789.4	787.3	794.2	794.4	799.9	806.5	815.5	824.0
25°	750.3	746.0	742.8	744.4	742.8	746.0	750.3	750.9	758.5	764.4	769.8
27.5°	708.6	706.2	706.0	701.6	706.0	706.2	708.6	710.0	714.3	717.8	722.8
30°	684.4	679.0	680.0	677.4	680.0	679.0	684.4	684.9	687.1	689.3	695.2
32.5°	656.6	654.7	653.6	651.3	653.6	654.7	656.6	657.6	661.9	664.1	668.8
35°	618.9	619.5	616.7	617.8	616.7	619.5	618.9	620.0	620.5	622.6	627.0
37.5°	585.9	587.6	586.4	586.7	586.4	587.6	585.9	586.4	586.9	587.3	588.6
40°	564.3	564.3	564.3	565.9	564.3	564.3	564.3	562.6	563.2	562.6	562.6
42.5°	543.5	542.6	541.8	541.6	541.8	542.6	543.5	539.7	541.5	539.7	538.8
45°	508.0	509.6	510.1	507.4	510.1	509.6	508.0	506.9	505.3	504.8	504.2
47.5°	475.9	476.1	475.9	478.3	475.9	476.1	475.9	474.4	472.0	471.0	468.4
50°	453.4	452.2	453.4	452.2	453.4	452.2	453.4	450.6	449.0	446.3	444.2
52.5°	429.6	429.7	429.1	428.9	429.1	429.7	429.6	426.0	425.2	424.3	420.8
55°	392.2	393.3	392.7	392.7	392.7	393.3	392.2	390.0	389.6	386.3	383.0
57.5°	353.6	354.6	355.3	352.9	355.3	354.6	353.6	353.3	352.9	349.5	346.0
60°	326.8	329.5	328.9	327.8	328.9	329.5	326.8	327.3	325.7	323.5	321.3
62.5°	302.1	303.0	303.0	302.7	303.0	303.0	302.1	299.6	298.8	296.7	294.5
65°	264.0	265.1	263.4	265.1	263.4	265.1	264.0	262.4	258.6	257.5	255.4
67.5°	223.0	223.3	224.5	225.3	224.5	223.3	223.0	223.6	221.2	219.1	218.7
70°	197.5	196.9	198.5	200.2	198.5	196.9	197.5	196.4	194.8	193.1	190.9
72.5°	170.6	171.8	171.3	172.4	171.3	171.8	170.6	170.8	169.3	167.1	165.0
75°	131.4	133.1	132.6	134.2	132.6	133.1	131.4	132.6	131.4	129.3	127.1
77.5°	95.0	95.2	95.0	95.9	95.0	95.2	95.0	95.9	94.7	95.4	92.9
80°	72.5	71.4	70.4	72.5	70.4	71.4	72.5	72.5	70.8	72.5	70.8
82.5°	50.4	51.0	50.0	50.0	50.0	51.0	50.4	51.7	51.0	51.7	50.1
85°	23.2	22.7	21.6	21.6	21.6	22.7	23.2	23.2	24.9	23.8	23.8
87.5°	9.8	9.4	9.4	9.0	9.4	9.4	9.8	9.7	9.7	10.7	10.8
90°	27.1	27.3	27.5	27.6	27.5	27.3	27.1	26.9	27.1	27.4	27.7
92.5°	26.3	26.3	26.3	26.3	26.3	26.3	26.3	26.3	26.2	26.1	26.0
95°	51.5	51.2	50.8	50.5	50.8	51.2	51.5	51.9	52.1	52.1	52.1
97.5°	87.5	87.5	87.4	87.4	87.4	87.5	87.5	87.6	87.6	87.6	87.6
100°	112.0	111.9	111.6	111.5	111.6	111.9	112.0	112.2	112.3	112.3	112.3
102.5°	139.3	139.2	139.0	138.8	139.0	139.2	139.3	139.5	139.6	139.4	139.3
105°	180.6	180.6	180.6	180.6	180.6	180.6	180.6	180.6	180.4	180.1	179.7
107.5°	222.5	221.7	220.9	220.0	220.9	221.7	222.5	223.3	223.6	223.6	223.4
110°	252.3	251.7	251.1	250.6	251.1	251.7	252.3	252.7	253.1	253.1	253.1



TEST NUMBER: P331403-930

CATALOG NUMBER: SA2XXDIP-C865D925U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	281.1	280.7	280.3	279.9	280.3	280.7	281.1	281.4	281.9	282.3	282.7
115°	327.1	326.5	326.0	325.5	326.0	326.5	327.1	327.6	328.0	328.2	328.3
117.5°	370.6	370.0	369.4	368.9	369.4	370.0	370.6	371.0	371.5	372.0	372.4
120°	401.1	400.6	400.1	399.5	400.1	400.6	401.1	401.7	401.9	401.9	401.9
122.5°	430.6	430.2	429.8	429.4	429.8	430.2	430.6	431.0	431.5	431.9	432.3
125°	475.7	475.5	475.3	475.2	475.3	475.5	475.7	475.9	476.2	476.8	477.4
127.5°	518.5	518.0	517.4	516.8	517.4	518.0	518.5	519.1	519.8	520.4	521.1
130°	548.9	548.2	547.5	546.7	547.5	548.2	548.9	549.7	550.2	550.6	550.9
132.5°	577.2	576.6	576.0	575.4	576.0	576.6	577.2	577.7	578.4	579.2	580.0
135°	621.6	621.1	620.5	620.0	620.5	621.1	621.6	622.2	622.5	622.7	622.9
137.5°	662.5	661.8	661.0	660.3	661.0	661.8	662.5	663.2	663.7	663.8	664.0
140°	690.5	689.7	689.1	688.4	689.1	689.7	690.5	691.2	691.6	691.6	691.6
142.5°	715.9	715.2	714.4	713.7	714.4	715.2	715.9	716.6	716.9	716.7	716.6
145°	754.0	753.3	752.5	751.8	752.5	753.3	754.0	754.7	755.0	754.8	754.6
147.5°	787.9	787.2	786.5	785.8	786.5	787.2	787.9	788.6	788.7	788.3	787.9
150°	809.6	809.0	808.5	808.0	808.5	809.0	809.6	810.1	810.1	809.6	809.0
152.5°	830.8	830.1	829.5	828.8	829.5	830.1	830.8	831.5	831.5	830.8	830.1
155°	858.3	857.9	857.3	856.7	857.3	857.9	858.3	858.9	858.8	857.9	857.0
157.5°	883.5	882.6	881.7	880.8	881.7	882.6	883.5	884.3	884.1	882.9	881.7
160°	898.0	897.2	896.5	895.8	896.5	897.2	898.0	898.7	898.5	897.4	896.3
162.5°	911.4	910.5	909.7	908.8	909.7	910.5	911.4	912.3	912.1	910.9	909.6
165°	928.6	927.7	926.8	925.9	926.8	927.7	928.6	929.5	929.4	928.1	926.8
167.5°	942.7	941.8	940.9	939.9	940.9	941.8	942.7	943.6	943.5	942.2	940.9
170°	950.3	949.3	948.1	947.1	948.1	949.3	950.3	951.4	951.3	950.1	948.8
172.5°	956.2	955.1	954.0	952.9	954.0	955.1	956.2	957.2	957.2	955.9	954.6
175°	962.5	961.4	960.3	959.3	960.3	961.4	962.5	963.6	963.5	962.2	961.0
177.5°	964.8	963.9	963.0	962.2	963.0	963.9	964.8	965.6	965.6	964.8	963.9
180°	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2



TEST NUMBER: P331403-930
 CATALOG NUMBER: SA2XXDIP-C865D925U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6
2.5°	1352.7	1357.5	1364.8	1372.6	1377.4	1386.4	1389.0	1393.3	1397.3	1406.4	1415.8
5°	1274.6	1282.1	1300.0	1309.7	1323.2	1339.0	1349.2	1360.1	1372.0	1392.5	1411.4
7.5°	1190.8	1203.5	1225.6	1243.8	1263.1	1285.6	1301.9	1323.2	1341.0	1370.0	1397.7
10°	1135.0	1152.8	1172.9	1194.5	1221.6	1245.4	1268.1	1295.1	1316.8	1351.4	1383.9
12.5°	1084.8	1087.5	1116.1	1140.0	1177.0	1206.4	1232.6	1267.5	1288.7	1329.8	1363.9
15°	997.0	1013.3	1039.3	1058.2	1102.0	1139.3	1176.2	1212.4	1236.7	1287.5	1332.4
17.5°	923.2	938.1	964.7	995.7	1027.2	1064.4	1112.0	1150.1	1183.2	1241.4	1294.5
20°	876.4	894.8	921.9	953.7	981.4	1021.9	1063.1	1106.9	1142.6	1208.0	1270.2
22.5°	836.6	851.1	872.9	904.4	934.6	971.8	1016.8	1064.5	1101.9	1172.6	1235.6
25°	780.6	792.6	806.6	832.6	866.7	907.3	942.4	994.9	1049.5	1115.5	1191.8
27.5°	730.3	738.7	751.1	774.0	800.4	838.3	877.3	927.2	982.1	1053.8	1134.2
30°	699.5	704.9	717.4	736.3	762.2	792.0	831.5	879.1	935.4	1007.9	1087.9
32.5°	672.7	677.7	685.7	703.8	726.4	751.8	787.3	834.9	888.6	959.9	1048.6
35°	632.4	636.2	643.3	657.9	670.3	695.2	725.0	768.2	818.5	886.7	978.7
37.5°	592.3	597.5	601.8	608.0	623.9	640.3	666.2	702.7	752.1	820.9	908.6
40°	565.9	570.2	576.7	579.4	592.4	607.0	628.1	661.6	711.4	774.1	859.7
42.5°	539.1	543.4	547.2	550.4	561.7	574.5	593.5	622.2	666.4	727.4	812.0
45°	502.6	503.1	506.9	512.8	518.3	527.5	541.0	565.9	600.0	657.3	734.1
47.5°	465.5	466.2	466.8	469.4	475.4	483.7	492.8	513.0	543.5	589.2	664.0
50°	440.9	439.9	440.9	443.0	446.9	453.9	464.1	478.7	503.7	546.4	615.1
52.5°	417.1	416.9	416.2	417.1	420.0	424.9	432.1	444.6	466.8	506.1	566.6
55°	380.8	378.1	378.7	376.5	381.4	382.5	387.9	398.2	417.7	444.7	501.5
57.5°	342.3	340.0	337.6	337.0	336.5	339.4	343.7	351.9	366.8	390.4	436.6
60°	317.6	314.9	311.6	310.5	310.5	312.2	314.3	320.2	334.4	355.5	393.3
62.5°	292.4	289.3	287.4	284.5	283.7	285.4	287.5	291.7	301.9	321.6	354.3
65°	253.7	250.0	247.2	246.7	245.6	244.0	245.1	249.4	257.5	273.2	299.1
67.5°	214.9	211.3	210.7	207.5	206.0	206.2	206.0	209.7	214.6	228.1	247.4
70°	189.3	186.6	185.6	182.9	181.8	180.7	179.6	182.9	187.8	199.1	215.9
72.5°	163.4	161.1	158.7	156.5	156.7	155.6	155.4	157.4	161.3	171.8	184.7
75°	126.0	126.6	123.9	121.2	120.7	119.5	119.5	121.2	122.8	130.9	141.2
77.5°	91.4	91.0	88.7	87.9	87.3	86.1	87.3	88.4	89.3	94.7	102.2
80°	69.8	69.8	67.1	67.1	66.5	64.9	66.5	65.5	67.6	73.1	78.4
82.5°	49.9	49.0	48.9	48.0	47.9	46.7	47.5	48.6	49.4	53.2	56.3
85°	24.4	24.4	23.8	23.2	23.8	23.2	23.8	24.4	24.9	26.5	29.2
87.5°	10.8	11.3	10.9	10.6	9.8	9.5	9.3	9.3	9.7	9.7	9.7
90°	28.1	28.5	24.5	20.5	16.6	12.6	9.5	7.3	5.1	3.0	0.8
92.5°	25.9	25.8	24.9	24.0	23.1	22.1	20.9	19.2	17.7	16.1	14.5
95°	52.1	52.1	51.7	51.4	51.0	50.6	49.6	47.7	45.9	44.1	42.3
97.5°	87.6	87.6	86.8	86.2	85.5	84.8	83.6	82.1	80.5	78.9	77.3
100°	112.3	112.3	111.8	111.2	110.6	110.1	109.1	107.7	106.2	104.8	103.3
102.5°	139.1	139.0	138.3	137.6	136.9	136.2	135.3	134.1	133.0	131.8	130.7
105°	179.4	179.0	178.6	178.3	177.9	177.6	177.1	176.6	176.0	175.5	175.0
107.5°	223.2	223.1	223.1	223.1	223.1	223.1	222.7	221.9	221.1	220.3	219.5
110°	253.1	253.1	253.1	253.1	253.1	253.1	252.5	251.4	250.3	249.2	248.2



TEST NUMBER: P331403-930

CATALOG NUMBER: SA2XXDIP-C865D925U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	283.2	283.6	283.8	283.9	284.1	284.2	283.7	282.7	281.6	280.5	279.4
115°	328.6	328.7	329.1	329.5	329.8	330.1	329.8	328.7	327.6	326.5	325.5
117.5°	372.8	373.3	374.3	375.3	376.3	377.3	377.2	375.7	374.2	372.8	371.4
120°	401.9	401.9	403.4	404.8	406.3	407.7	407.7	406.3	404.8	403.4	401.9
122.5°	432.8	433.2	434.2	435.2	436.2	437.2	436.8	435.1	433.4	431.6	429.9
125°	477.8	478.4	479.0	479.5	480.0	480.6	480.0	478.4	476.8	475.2	473.5
127.5°	521.7	522.4	523.0	523.7	524.3	525.0	524.2	522.2	520.2	518.0	516.0
130°	551.3	551.6	552.0	552.4	552.7	553.1	552.1	549.8	547.4	545.0	542.7
132.5°	580.8	581.6	581.5	581.5	581.4	581.3	580.3	578.4	576.5	574.5	572.7
135°	623.1	623.2	622.9	622.5	622.2	621.8	620.6	618.6	616.6	614.7	612.7
137.5°	664.1	664.2	663.8	663.3	662.8	662.3	661.3	659.7	658.0	656.4	654.8
140°	691.6	691.6	690.7	689.7	688.8	687.9	686.7	685.1	683.5	681.8	680.2
142.5°	716.5	716.3	715.7	715.1	714.4	713.9	712.7	711.1	709.5	707.8	706.2
145°	754.4	754.2	753.2	752.0	751.0	749.9	748.7	747.5	746.2	744.9	743.6
147.5°	787.5	787.1	786.4	785.6	785.0	784.2	783.1	781.5	780.1	778.5	777.0
150°	808.5	808.0	807.2	806.5	805.8	805.0	804.1	803.1	801.9	800.9	799.8
152.5°	829.5	828.8	827.9	827.0	826.1	825.3	824.3	823.2	822.1	821.1	819.9
155°	856.1	855.1	854.6	854.0	853.5	853.0	852.4	851.9	851.3	850.8	850.3
157.5°	880.4	879.2	878.9	878.6	878.2	877.9	877.6	877.2	876.9	876.4	876.1
160°	895.3	894.1	894.0	893.8	893.6	893.5	893.2	892.8	892.4	892.1	891.8
162.5°	908.4	907.2	907.0	906.9	906.7	906.4	906.4	906.3	906.2	906.1	906.0
165°	925.5	924.3	924.3	924.3	924.3	924.3	924.4	924.5	924.7	925.0	925.1
167.5°	939.7	938.4	938.5	938.5	938.6	938.6	938.9	939.4	940.0	940.5	941.0
170°	947.5	946.2	946.4	946.6	946.8	947.0	947.3	947.9	948.4	948.9	949.5
172.5°	953.4	952.1	952.3	952.4	952.7	952.8	953.2	953.7	954.3	954.8	955.4
175°	959.7	958.5	958.8	959.2	959.5	959.9	960.3	960.9	961.4	962.0	962.5
177.5°	963.0	962.2	962.5	962.8	963.0	963.4	963.7	964.2	964.6	965.0	965.5
180°	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2



TEST NUMBER: P331403-930

CATALOG NUMBER: SA2XXDIP-C865D925U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6
2.5°	1415.0	1417.2	1424.1	1431.0	1438.8	1441.0	1444.5	1441.4	1440.6	1448.8	1454.8
5°	1419.0	1428.7	1447.7	1465.0	1479.6	1489.9	1500.7	1505.0	1513.1	1524.5	1538.6
7.5°	1414.5	1433.4	1463.1	1488.4	1515.9	1535.6	1551.1	1564.3	1580.4	1601.9	1625.4
10°	1409.2	1434.7	1471.0	1501.8	1535.3	1560.7	1581.8	1602.4	1626.2	1656.0	1686.8
12.5°	1399.8	1430.0	1475.3	1511.7	1554.8	1579.8	1608.3	1652.6	1678.1	1719.6	1763.0
15°	1380.6	1414.1	1477.4	1522.3	1571.0	1618.6	1671.1	1713.4	1755.5	1779.9	1841.0
17.5°	1352.2	1401.4	1471.5	1523.9	1585.8	1660.8	1719.7	1767.5	1816.2	1855.7	1886.4
20°	1329.2	1382.7	1462.8	1525.6	1599.1	1679.8	1747.4	1796.1	1838.3	1871.3	1890.2
22.5°	1300.2	1367.6	1445.5	1519.1	1613.0	1692.7	1763.8	1802.1	1837.4	1853.5	1860.8
25°	1254.6	1335.7	1423.9	1513.7	1619.8	1704.1	1769.0	1792.3	1802.5	1786.9	1760.9
27.5°	1205.3	1295.8	1398.9	1503.5	1615.6	1696.7	1743.3	1739.6	1722.2	1671.4	1630.8
30°	1168.6	1268.1	1379.0	1493.1	1605.7	1684.7	1711.7	1684.7	1645.1	1588.4	1530.5
32.5°	1130.0	1233.1	1357.8	1478.4	1587.5	1656.9	1662.8	1616.2	1555.1	1490.5	1418.4
35°	1071.7	1183.2	1317.8	1445.5	1548.8	1592.7	1566.7	1484.5	1412.0	1323.8	1225.3
37.5°	1005.8	1128.9	1264.0	1397.3	1490.9	1502.4	1437.9	1351.4	1249.1	1145.5	1029.6
40°	956.5	1086.9	1225.9	1360.6	1443.3	1431.4	1349.2	1254.0	1132.3	1005.7	898.1
42.5°	912.3	1042.7	1184.3	1316.5	1382.7	1350.1	1254.0	1137.2	1006.3	887.1	788.6
45°	835.8	970.0	1115.0	1242.7	1280.5	1221.6	1094.5	964.6	835.8	736.3	658.4
47.5°	761.6	894.2	1037.8	1150.1	1163.4	1084.1	945.2	811.6	700.9	619.9	564.9
50°	707.1	840.2	982.4	1082.6	1078.2	982.4	839.6	712.5	620.0	554.5	517.7
52.5°	658.2	783.9	920.6	1011.5	988.6	884.2	747.9	635.0	559.0	507.8	474.4
55°	582.1	698.4	828.3	901.3	859.1	743.3	628.1	537.2	480.9	442.5	416.5
57.5°	506.5	615.6	726.8	771.8	725.1	618.2	522.2	456.2	413.9	385.5	368.6
60°	459.8	555.1	654.0	693.0	637.3	542.1	466.4	407.4	373.2	350.0	334.8
62.5°	413.1	498.4	591.7	612.9	562.0	481.5	414.4	365.4	337.4	316.7	302.4
65°	349.5	419.2	490.2	504.2	457.1	394.9	341.9	310.0	285.1	269.9	258.6
67.5°	286.6	342.7	392.9	404.2	363.0	319.8	281.5	253.7	236.8	224.3	214.7
70°	249.4	293.8	334.8	344.1	311.0	272.6	243.4	221.3	206.1	195.3	186.1
72.5°	210.0	247.0	281.2	287.4	260.4	231.1	207.1	189.6	176.3	169.3	160.5
75°	160.7	182.3	208.8	210.4	192.6	174.7	156.4	145.0	137.9	129.3	125.0
77.5°	113.4	130.4	145.5	148.5	137.9	125.7	115.4	106.5	100.5	96.5	92.5
80°	86.6	100.1	106.6	110.4	102.8	94.2	88.2	82.3	78.4	75.7	73.1
82.5°	61.9	70.2	76.3	79.2	75.1	69.9	63.9	60.6	57.6	55.4	54.5
85°	31.4	35.1	39.0	40.0	39.0	36.8	33.5	33.5	31.9	31.4	31.4
87.5°	11.4	13.6	14.0	15.7	15.5	16.3	17.1	17.4	17.8	17.3	16.8
90°	3.0	5.1	7.3	9.5	12.6	16.6	20.5	24.5	28.5	28.1	27.7
92.5°	16.1	17.7	19.2	20.9	22.1	23.1	24.0	24.9	25.8	25.9	26.0
95°	44.1	45.9	47.7	49.6	50.6	51.0	51.4	51.7	52.1	52.1	52.1
97.5°	78.9	80.5	82.1	83.6	84.8	85.5	86.2	86.8	87.6	87.6	87.6
100°	104.8	106.2	107.7	109.1	110.1	110.6	111.2	111.8	112.3	112.3	112.3
102.5°	131.8	133.0	134.1	135.3	136.2	136.9	137.6	138.3	139.0	139.1	139.3
105°	175.5	176.0	176.6	177.1	177.6	177.9	178.3	178.6	179.0	179.4	179.7
107.5°	220.3	221.1	221.9	222.7	223.1	223.1	223.1	223.1	223.1	223.2	223.4
110°	249.2	250.3	251.4	252.5	253.1	253.1	253.1	253.1	253.1	253.1	253.1



TEST NUMBER: P331403-930

CATALOG NUMBER: SA2XXDIP-C865D925U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	280.5	281.6	282.7	283.7	284.2	284.1	283.9	283.8	283.6	283.2	282.7
115°	326.5	327.6	328.7	329.8	330.1	329.8	329.5	329.1	328.7	328.6	328.3
117.5°	372.8	374.2	375.7	377.2	377.3	376.3	375.3	374.3	373.3	372.8	372.4
120°	403.4	404.8	406.3	407.7	407.7	406.3	404.8	403.4	401.9	401.9	401.9
122.5°	431.6	433.4	435.1	436.8	437.2	436.2	435.2	434.2	433.2	432.8	432.3
125°	475.2	476.8	478.4	480.0	480.6	480.0	479.5	479.0	478.4	477.8	477.4
127.5°	518.0	520.2	522.2	524.2	525.0	524.3	523.7	523.0	522.4	521.7	521.1
130°	545.0	547.4	549.8	552.1	553.1	552.7	552.4	552.0	551.6	551.3	550.9
132.5°	574.5	576.5	578.4	580.3	581.3	581.4	581.5	581.5	581.6	580.8	580.0
135°	614.7	616.6	618.6	620.6	621.8	622.2	622.5	622.9	623.2	623.1	622.9
137.5°	656.4	658.0	659.7	661.3	662.3	662.8	663.3	663.8	664.2	664.1	664.0
140°	681.8	683.5	685.1	686.7	687.9	688.8	689.7	690.7	691.6	691.6	691.6
142.5°	707.8	709.5	711.1	712.7	713.9	714.4	715.1	715.7	716.3	716.5	716.6
145°	744.9	746.2	747.5	748.7	749.9	751.0	752.0	753.2	754.2	754.4	754.6
147.5°	778.5	780.1	781.5	783.1	784.2	785.0	785.6	786.4	787.1	787.5	787.9
150°	800.9	801.9	803.1	804.1	805.0	805.8	806.5	807.2	808.0	808.5	809.0
152.5°	821.1	822.1	823.2	824.3	825.3	826.1	827.0	827.9	828.8	829.5	830.1
155°	850.8	851.3	851.9	852.4	853.0	853.5	854.0	854.6	855.1	856.1	857.0
157.5°	876.4	876.9	877.2	877.6	877.9	878.2	878.6	878.9	879.2	880.4	881.7
160°	892.1	892.4	892.8	893.2	893.5	893.6	893.8	894.0	894.1	895.3	896.3
162.5°	906.1	906.2	906.3	906.4	906.4	906.7	906.9	907.0	907.2	908.4	909.6
165°	925.0	924.7	924.5	924.4	924.3	924.3	924.3	924.3	924.3	925.5	926.8
167.5°	940.5	940.0	939.4	938.9	938.6	938.6	938.5	938.5	938.4	939.7	940.9
170°	948.9	948.4	947.9	947.3	947.0	946.8	946.6	946.4	946.2	947.5	948.8
172.5°	954.8	954.3	953.7	953.2	952.8	952.7	952.4	952.3	952.1	953.4	954.6
175°	962.0	961.4	960.9	960.3	959.9	959.5	959.2	958.8	958.5	959.7	961.0
177.5°	965.0	964.6	964.2	963.7	963.4	963.0	962.8	962.5	962.2	963.0	963.9
180°	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2



TEST NUMBER: P331403-930

CATALOG NUMBER: SA2XXDIP-C865D925U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6
2.5°	1460.0	1466.1	1466.1	1467.0	1473.9	1473.0	1472.6
5°	1553.7	1562.9	1564.0	1573.8	1580.2	1578.1	1572.1
7.5°	1642.1	1659.2	1672.2	1679.4	1688.0	1693.3	1690.9
10°	1712.2	1737.1	1752.2	1762.5	1775.0	1784.2	1780.9
12.5°	1775.9	1805.5	1826.3	1843.9	1845.5	1857.3	1849.3
15°	1875.1	1906.4	1909.7	1922.6	1933.0	1931.9	1932.4
17.5°	1907.9	1917.9	1919.9	1920.3	1920.4	1916.6	1908.4
20°	1896.1	1892.4	1883.2	1876.2	1863.7	1862.1	1851.3
22.5°	1840.8	1828.8	1805.7	1790.5	1771.1	1766.0	1763.0
25°	1731.7	1705.2	1668.4	1633.2	1623.5	1604.6	1610.0
27.5°	1582.1	1540.8	1500.9	1472.3	1446.5	1418.1	1426.3
30°	1476.9	1430.4	1374.1	1330.8	1303.3	1276.2	1271.3
32.5°	1351.4	1283.2	1220.5	1182.3	1140.1	1123.0	1104.2
35°	1135.0	1068.4	1006.2	952.7	921.9	898.1	876.4
37.5°	940.4	863.7	813.5	770.1	747.9	734.3	737.7
40°	819.6	752.5	715.8	682.7	662.2	652.4	654.6
42.5°	721.8	671.6	641.3	618.6	604.1	598.8	597.5
45°	610.7	582.6	557.7	544.8	537.8	531.8	528.0
47.5°	535.0	512.1	498.1	490.3	484.2	478.1	478.0
50°	489.6	474.4	464.7	456.6	451.8	447.4	451.2
52.5°	454.9	441.2	431.4	424.1	422.3	418.4	418.3
55°	403.6	392.7	385.7	379.2	376.0	373.8	371.1
57.5°	356.9	346.6	340.1	336.0	329.8	327.6	326.8
60°	323.5	315.4	308.9	303.5	300.8	296.4	296.4
62.5°	292.8	284.7	278.6	274.5	270.0	268.3	268.8
65°	248.3	241.8	235.9	231.5	230.5	227.2	228.3
67.5°	207.4	203.1	196.8	194.4	192.4	190.6	189.3
70°	180.2	175.9	172.6	169.3	167.7	167.7	167.7
72.5°	157.2	152.1	150.1	145.9	146.9	145.2	143.5
75°	121.7	118.5	116.8	115.2	112.5	112.5	112.5
77.5°	89.6	88.6	86.7	85.0	84.3	83.7	84.0
80°	69.2	68.7	67.6	67.6	66.5	66.0	64.9
82.5°	53.2	51.9	51.2	50.7	50.5	50.4	50.2
85°	30.3	29.2	29.2	29.8	28.7	28.7	29.2
87.5°	17.2	17.1	16.6	16.7	17.1	16.7	16.8
90°	27.4	27.1	26.9	27.1	27.3	27.5	27.6
92.5°	26.1	26.2	26.3	26.3	26.3	26.3	26.3
95°	52.1	52.1	51.9	51.5	51.2	50.8	50.5
97.5°	87.6	87.6	87.6	87.5	87.5	87.4	87.4
100°	112.3	112.3	112.2	112.0	111.9	111.6	111.5
102.5°	139.4	139.6	139.5	139.3	139.2	139.0	138.8
105°	180.1	180.4	180.6	180.6	180.6	180.6	180.6
107.5°	223.6	223.6	223.3	222.5	221.7	220.9	220.0
110°	253.1	253.1	252.7	252.3	251.7	251.1	250.6



TEST NUMBER: P331403-930

CATALOG NUMBER: SA2XXDIP-C865D925U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	282.3	281.9	281.4	281.1	280.7	280.3	279.9
115°	328.2	328.0	327.6	327.1	326.5	326.0	325.5
117.5°	372.0	371.5	371.0	370.6	370.0	369.4	368.9
120°	401.9	401.9	401.7	401.1	400.6	400.1	399.5
122.5°	431.9	431.5	431.0	430.6	430.2	429.8	429.4
125°	476.8	476.2	475.9	475.7	475.5	475.3	475.2
127.5°	520.4	519.8	519.1	518.5	518.0	517.4	516.8
130°	550.6	550.2	549.7	548.9	548.2	547.5	546.7
132.5°	579.2	578.4	577.7	577.2	576.6	576.0	575.4
135°	622.7	622.5	622.2	621.6	621.1	620.5	620.0
137.5°	663.8	663.7	663.2	662.5	661.8	661.0	660.3
140°	691.6	691.6	691.2	690.5	689.7	689.1	688.4
142.5°	716.7	716.9	716.6	715.9	715.2	714.4	713.7
145°	754.8	755.0	754.7	754.0	753.3	752.5	751.8
147.5°	788.3	788.7	788.6	787.9	787.2	786.5	785.8
150°	809.6	810.1	810.1	809.6	809.0	808.5	808.0
152.5°	830.8	831.5	831.5	830.8	830.1	829.5	828.8
155°	857.9	858.8	858.9	858.3	857.9	857.3	856.7
157.5°	882.9	884.1	884.3	883.5	882.6	881.7	880.8
160°	897.4	898.5	898.7	898.0	897.2	896.5	895.8
162.5°	910.9	912.1	912.3	911.4	910.5	909.7	908.8
165°	928.1	929.4	929.5	928.6	927.7	926.8	925.9
167.5°	942.2	943.5	943.6	942.7	941.8	940.9	939.9
170°	950.1	951.3	951.4	950.3	949.3	948.1	947.1
172.5°	955.9	957.2	957.2	956.2	955.1	954.0	952.9
175°	962.2	963.5	963.6	962.5	961.4	960.3	959.3
177.5°	964.8	965.6	965.6	964.8	963.9	963.0	962.2
180°	964.2	964.2	964.2	964.2	964.2	964.2	964.2

(END OF REPORT)