

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331764-930

Luminaire Tested: **SA2XXRDIP-C1005D1080U930-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331764-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C1005D1080U930-4F0-1E-UDD-F4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1080 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6271.2 lumens
Efficiency: N/A
Efficacy: 87.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 71.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331764-930
CATALOG NUMBER: SA2XXRDIP-C1005D1080U930-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P331764-930

CATALOG NUMBER: SA2XXRDIP-C1005D1080U930-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	45	45	45
1	97	93	89	86	89	85	82	79	71	69	67	58	57	55	46	45	45	39	39	39
2	89	82	76	71	81	75	70	66	63	59	56	52	49	47	41	40	38	33	33	33
3	81	72	65	60	74	67	60	56	56	51	48	46	43	40	37	35	33	29	29	29
4	75	64	57	51	68	59	53	47	50	45	41	41	38	35	33	31	29	25	25	25
5	69	57	50	44	63	53	46	41	45	40	36	37	34	30	30	28	25	22	22	22
6	63	52	44	38	58	48	41	36	41	35	31	34	30	27	28	25	23	20	20	20
7	59	47	39	34	54	43	36	32	37	32	28	31	27	24	25	22	20	18	18	18
8	54	42	35	30	50	39	33	28	34	29	25	28	24	21	23	20	18	16	16	16
9	51	39	32	27	47	36	30	25	31	26	22	26	22	19	22	19	17	14	14	14
10	47	36	29	24	44	33	27	23	29	24	20	24	20	18	20	17	15	13	13	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	22291	22291	22291
5°	22376	22013	22135
10°	22207	21653	21469
15°	21951	21010	20404
20°	21596	20094	19086
25°	21235	19053	17808
30°	20734	17984	16168
35°	20243	16821	14728
40°	19751	15616	13061
45°	19173	14266	11556
50°	18580	12901	10073
55°	17973	11431	8653
60°	17270	9884	7182
65°	16466	8306	6541
70°	15512	6845	6014
75°	14342	6238	5608
80°	12664	5579	5114
85°	9948	4390	4390



TEST NUMBER: P331764-930

CATALOG NUMBER: SA2XXRDIP-C1005D1080U930-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	129.2	2.1
10°-20°	354.8	5.7
20°-30°	498.3	7.9
30°-40°	543.4	8.7
40°-50°	499.6	8.0
50°-60°	392.4	6.3
60°-70°	255.8	4.1
70°-80°	131.9	2.1
80°-90°	38.6	0.6
90°-100°	196.9	3.1
100°-110°	668.2	10.7
110°-120°	709.9	11.3
120°-130°	584.4	9.3
130°-140°	469.3	7.5
140°-150°	354.6	5.7
150°-160°	249.2	4.0
160°-170°	146.7	2.3
170°-180°	47.8	0.8
0°-30°	982.4	15.7
0°-40°	1525.7	24.3
0°-60°	2417.7	38.6
0°-90°	2844.1	45.4
90°-120°	1575.1	25.1
90°-150°	2983.4	47.6
90°-180°	3427.0	54.6
0°-180°	6271.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1381	1381	1381	1381	1381	
5°	1381	1374	1358	1369	1366	131
15°	1313	1298	1257	1234	1221	370
25°	1192	1150	1070	1020	1000	548
35°	1027	961	853	778	747	642
45°	840	753	625	539	506	648
55°	638	539	406	334	307	570
65°	431	329	217	177	171	427
75°	230	145	100	92	90	243
85°	54	29	24	24	24	63
90°	1	13	32	31	31	4
95°	33	81	371	140	108	35
105°	116	174	702	1254	1067	123
115°	204	257	587	1212	1405	202
125°	284	336	564	982	1139	252
135°	333	398	558	825	944	258
145°	381	438	555	689	754	239
155°	433	467	539	609	634	199
165°	472	486	516	547	556	133
175°	492	492	496	502	501	47
180°	492	492	492	492	492	



TEST NUMBER: P331764-930

CATALOG NUMBER: SA2XXRDIP-C1005D1080U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1380.6	1380.6	1380.6	1380.6	1380.6	1380.6	1380.6	1380.6	1380.6	1380.6	1380.6
2.5°	1385.7	1384.5	1383.4	1382.3	1381.2	1379.4	1377.0	1374.6	1372.1	1369.7	1371.9
5°	1380.6	1379.2	1377.9	1376.5	1375.1	1372.6	1369.0	1365.4	1361.8	1358.2	1360.7
7.5°	1366.4	1364.7	1363.0	1361.2	1359.5	1356.6	1352.3	1348.1	1343.9	1339.7	1340.4
10°	1354.5	1352.5	1350.5	1348.6	1346.6	1342.9	1337.3	1331.8	1326.2	1320.7	1319.9
12.5°	1339.5	1337.0	1334.6	1332.3	1329.9	1325.1	1318.0	1310.9	1303.8	1296.7	1295.2
15°	1313.2	1310.1	1307.1	1304.0	1301.0	1294.7	1285.3	1275.9	1266.4	1256.9	1251.7
17.5°	1280.9	1276.3	1271.6	1267.0	1262.3	1253.9	1241.8	1229.7	1217.6	1205.5	1199.2
20°	1256.9	1251.4	1245.9	1240.3	1234.8	1225.1	1211.1	1197.3	1183.4	1169.5	1162.5
22.5°	1230.9	1224.7	1218.5	1212.4	1206.1	1195.1	1179.5	1163.8	1148.2	1132.5	1123.6
25°	1192.0	1183.1	1174.2	1165.3	1156.4	1142.9	1124.5	1106.2	1087.9	1069.5	1058.2
27.5°	1145.0	1135.4	1125.7	1116.1	1106.4	1091.2	1070.6	1049.9	1029.2	1008.6	995.3
30°	1112.1	1101.5	1091.0	1080.4	1069.8	1053.4	1031.2	1009.0	986.8	964.6	950.4
32.5°	1080.0	1067.7	1055.4	1043.1	1030.7	1013.3	990.6	967.9	945.3	922.6	906.4
35°	1027.0	1012.9	998.7	984.6	970.5	951.1	926.7	902.3	877.8	853.4	835.9
37.5°	974.1	958.5	943.0	927.4	911.9	891.1	865.0	839.0	812.9	786.9	767.7
40°	937.1	920.5	903.8	887.1	870.5	848.6	821.7	794.8	767.8	740.9	721.2
42.5°	899.1	881.6	864.1	846.4	828.9	806.2	778.4	750.6	722.8	695.0	674.6
45°	839.7	821.0	802.4	783.8	765.2	741.4	712.2	683.1	653.9	624.8	605.0
47.5°	781.6	762.0	742.2	722.5	702.8	677.9	647.8	617.7	587.6	557.5	537.9
50°	739.7	720.0	700.3	680.5	660.8	635.7	605.2	574.6	544.0	513.6	494.4
52.5°	698.7	678.1	657.5	636.9	616.3	591.1	561.2	531.3	501.4	471.6	453.1
55°	638.5	616.9	595.2	573.5	551.9	526.0	496.0	466.0	436.1	406.1	389.4
57.5°	576.7	554.6	532.3	510.1	487.9	462.4	433.6	404.7	375.9	347.1	331.8
60°	534.8	512.6	490.3	468.1	445.9	420.5	391.9	363.3	334.7	306.1	292.0
62.5°	493.8	471.6	449.4	427.1	405.0	380.2	352.9	325.6	298.4	271.2	257.6
65°	431.0	408.5	386.1	363.6	341.1	317.4	292.4	267.4	242.4	217.4	208.0
67.5°	370.6	348.3	326.0	303.6	281.3	258.9	236.4	213.9	191.4	168.9	164.6
70°	328.6	307.0	285.3	263.7	242.0	221.6	202.4	183.3	164.1	145.0	142.2
72.5°	288.6	267.8	247.1	226.3	205.5	187.4	172.1	156.7	141.3	126.0	123.6
75°	229.9	210.4	191.0	171.6	152.1	137.7	128.2	118.9	109.4	100.0	98.0
77.5°	172.2	155.2	138.1	121.1	104.0	93.2	88.6	84.1	79.5	75.0	73.9
80°	136.2	122.1	107.9	93.7	79.6	71.1	68.3	65.6	62.8	60.0	58.9
82.5°	103.2	92.1	81.1	70.0	59.0	52.5	50.6	48.8	46.9	45.0	44.4
85°	53.7	47.9	42.1	36.2	30.4	27.1	26.3	25.4	24.5	23.7	23.7
87.5°	16.1	15.0	13.9	12.6	11.2	10.8	11.8	13.1	14.3	14.4	14.0
90°	1.0	3.8	7.6	9.5	11.3	14.2	18.9	25.6	31.2	32.2	31.2
92.5°	11.6	16.6	23.5	27.6	34.1	43.0	64.4	94.5	121.4	123.1	104.0
95°	33.2	36.9	46.4	55.0	70.1	92.8	136.4	218.7	328.6	371.3	324.9
97.5°	54.0	59.1	69.1	82.0	99.5	125.2	179.9	294.7	477.4	633.8	664.9
100°	72.9	75.7	84.3	99.5	118.4	144.9	195.1	310.6	515.2	748.2	884.6
102.5°	90.3	92.5	100.9	116.1	135.8	162.3	208.7	311.4	500.8	752.0	966.5
105°	115.5	119.4	126.0	140.1	161.0	187.5	232.0	316.3	472.6	701.8	953.7
107.5°	142.8	145.9	152.3	165.3	186.1	212.7	255.9	329.4	458.6	648.0	870.6
110°	161.0	164.8	170.5	182.8	202.7	230.2	271.8	340.0	455.6	622.2	818.3



TEST NUMBER: P331764-930

CATALOG NUMBER: SA2XXRDIP-C1005D1080U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	177.7	181.5	187.9	199.4	218.6	246.8	287.0	351.4	456.3	605.6	782.0
115°	203.7	208.4	214.0	225.4	244.3	269.9	310.6	368.4	460.3	587.2	736.9
117.5°	230.6	234.3	240.0	250.1	268.2	294.7	332.4	386.6	467.1	578.3	708.4
120°	247.2	250.9	256.7	265.2	284.1	310.6	347.6	398.8	471.7	573.0	693.2
122.5°	263.1	266.1	271.8	281.1	300.0	327.3	362.0	409.4	477.0	570.0	680.4
125°	284.1	287.0	292.7	304.0	322.9	349.5	383.6	426.2	484.9	564.5	662.0
127.5°	300.8	304.6	312.6	325.1	343.2	370.5	403.7	441.9	493.1	561.3	645.0
130°	310.6	314.5	323.9	337.2	356.1	382.6	415.8	451.8	499.1	559.7	633.7
132.5°	319.8	324.3	334.5	348.5	368.3	394.8	426.4	461.6	505.2	559.0	624.5
135°	333.4	337.2	348.5	362.7	384.5	411.1	441.3	474.5	512.4	557.8	611.8
137.5°	346.3	350.8	362.2	377.3	398.9	423.5	453.5	484.4	518.9	557.7	602.9
140°	356.1	359.9	371.3	386.5	407.2	431.9	460.3	489.7	521.9	556.9	597.6
142.5°	366.0	369.0	379.6	394.8	414.8	438.0	465.6	494.2	524.2	556.9	592.3
145°	380.7	384.5	394.0	408.2	427.1	448.0	473.5	500.1	526.6	555.0	585.3
147.5°	396.6	399.5	408.5	421.7	437.4	455.9	480.0	503.3	527.3	551.6	578.1
150°	407.2	410.1	417.7	430.0	444.2	461.2	483.1	504.8	526.6	549.3	572.0
152.5°	417.8	419.2	426.7	437.6	451.0	466.5	486.1	505.6	525.1	545.5	566.7
155°	432.8	433.7	439.4	449.9	460.3	474.5	490.6	506.7	522.8	538.9	556.9
157.5°	445.3	446.3	450.9	459.9	468.2	480.2	493.8	506.7	518.4	532.1	547.6
160°	453.6	454.6	458.4	465.9	473.5	484.0	495.4	506.7	516.2	527.6	540.8
162.5°	462.0	461.5	465.2	471.2	478.1	486.2	496.1	506.0	513.9	523.7	534.8
165°	471.7	470.8	472.6	478.3	483.1	488.7	497.3	503.9	509.6	516.2	524.7
167.5°	479.6	478.5	480.2	483.8	487.2	490.8	497.0	502.6	505.2	509.6	514.9
170°	484.9	483.1	484.0	486.8	488.7	491.5	496.3	501.0	502.9	505.7	509.6
172.5°	488.0	486.8	486.2	489.1	490.2	492.3	495.5	498.7	499.9	501.2	504.3
175°	491.5	490.6	489.7	491.5	491.5	492.5	494.4	496.3	495.4	496.3	497.3
177.5°	493.3	491.7	491.0	492.5	492.5	492.5	493.3	494.8	493.3	492.5	493.3
180°	492.5	492.5	492.5	492.5	492.5	492.5	492.5	492.5	492.5	492.5	492.5



TEST NUMBER: P331764-930

CATALOG NUMBER: SA2XXRDIP-C1005D1080U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1380.6	1380.6	1380.6	1380.6	1380.6	1380.6	1380.6	1380.6
2.5°	1374.1	1376.3	1378.6	1379.4	1379.0	1378.6	1378.1	1377.7
5°	1363.2	1365.7	1368.2	1369.0	1368.2	1367.3	1366.5	1365.7
7.5°	1341.1	1341.8	1342.6	1342.2	1340.8	1339.3	1337.9	1336.4
10°	1319.0	1318.2	1317.4	1316.1	1314.4	1312.8	1311.1	1309.5
12.5°	1293.7	1292.2	1290.7	1288.6	1285.8	1283.0	1280.3	1277.5
15°	1246.4	1241.1	1235.8	1231.8	1229.1	1226.3	1223.5	1220.7
17.5°	1192.9	1186.7	1180.4	1174.8	1170.1	1165.3	1160.5	1155.8
20°	1155.6	1148.7	1141.7	1135.2	1129.1	1123.0	1116.9	1110.8
22.5°	1114.7	1105.7	1096.7	1090.0	1085.5	1080.9	1076.4	1071.8
25°	1046.8	1035.4	1024.0	1016.3	1012.0	1007.9	1003.7	999.6
27.5°	982.0	968.7	955.4	945.5	938.9	932.3	925.7	919.1
30°	936.3	922.1	907.9	897.2	889.7	882.2	874.7	867.2
32.5°	890.3	874.2	857.9	846.4	839.4	832.3	825.2	818.2
35°	818.4	801.0	783.4	771.6	765.5	759.4	753.3	747.2
37.5°	748.4	729.1	709.8	696.7	689.7	682.7	675.7	668.7
40°	701.5	681.8	662.1	648.7	641.4	634.1	627.0	619.7
42.5°	654.2	633.8	613.4	599.7	592.7	585.7	578.8	571.8
45°	585.3	565.6	545.8	532.7	526.0	519.3	512.7	506.1
47.5°	518.3	498.7	479.1	466.3	460.2	454.2	448.1	442.1
50°	475.2	456.1	436.9	424.4	418.6	412.7	406.9	401.0
52.5°	434.6	416.0	397.6	385.6	380.3	374.9	369.5	364.1
55°	372.8	356.1	339.4	328.5	323.2	317.9	312.7	307.4
57.5°	316.6	301.3	286.0	276.1	271.7	267.3	262.9	258.4
60°	277.8	263.7	249.5	240.2	235.7	231.3	226.8	222.4
62.5°	244.2	230.6	217.2	209.0	206.4	203.7	201.1	198.4
65°	198.5	189.1	179.6	174.5	173.7	172.8	172.0	171.2
67.5°	160.3	156.0	151.6	149.0	148.1	147.2	146.3	145.4
70°	139.4	136.6	133.9	131.9	130.8	129.6	128.6	127.4
72.5°	121.3	119.0	116.6	115.1	114.5	113.8	113.1	112.4
75°	96.0	94.2	92.2	91.1	90.8	90.5	90.3	89.9
77.5°	72.7	71.7	70.5	69.7	69.3	68.9	68.4	68.0
80°	57.7	56.7	55.5	55.0	55.0	55.0	55.0	55.0
82.5°	43.6	43.0	42.3	42.0	42.0	42.0	42.0	42.0
85°	23.7	23.7	23.7	23.7	23.7	23.7	23.7	23.7
87.5°	13.6	13.0	13.2	13.2	13.2	13.2	13.2	13.2
90°	30.3	28.5	30.3	31.2	31.2	31.2	31.2	31.2
92.5°	82.6	70.8	62.9	57.0	56.3	53.2	54.0	52.5
95°	248.2	190.4	150.6	129.7	117.4	109.9	107.0	107.9
97.5°	579.0	473.8	371.3	302.9	257.6	234.3	220.5	212.5
100°	864.7	747.3	617.5	502.9	424.3	383.6	356.1	339.1
102.5°	1051.9	1025.3	930.4	809.0	723.6	654.1	619.8	596.7
105°	1150.7	1257.8	1270.1	1238.8	1180.1	1121.4	1080.7	1067.4
107.5°	1079.5	1240.7	1339.2	1385.0	1392.4	1389.2	1381.0	1363.4
110°	1018.1	1187.6	1308.9	1386.6	1427.3	1445.3	1453.8	1452.9



TEST NUMBER: P331764-930

CATALOG NUMBER: SA2XXRDIP-C1005D1080U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	962.1	1124.8	1254.3	1343.4	1400.0	1430.1	1446.3	1451.3
115°	893.2	1039.0	1163.0	1260.6	1327.9	1371.4	1396.0	1404.6
117.5°	841.2	969.3	1081.8	1173.3	1241.9	1287.8	1313.9	1321.0
120°	815.5	932.9	1033.3	1119.5	1185.8	1230.3	1257.8	1267.2
122.5°	795.0	902.6	997.7	1075.5	1135.0	1178.8	1203.2	1211.1
125°	765.2	862.8	946.2	1017.2	1072.1	1108.2	1131.8	1139.4
127.5°	735.9	824.2	902.8	968.3	1016.3	1049.9	1070.4	1076.5
130°	717.0	798.4	873.3	935.7	982.2	1014.4	1033.3	1040.9
132.5°	698.8	774.2	842.9	901.6	947.3	979.5	996.9	1003.7
135°	673.4	735.9	798.4	851.4	892.2	923.4	940.4	944.3
137.5°	653.1	705.4	755.0	801.3	838.4	865.3	880.3	885.9
140°	640.3	685.7	729.3	770.9	801.3	825.9	840.1	845.8
142.5°	629.7	668.3	705.8	740.6	769.4	791.8	804.5	805.6
145°	614.7	646.0	675.3	702.8	725.5	741.6	751.1	753.9
147.5°	603.2	627.8	650.7	670.7	689.5	702.4	708.8	710.5
150°	594.8	615.6	635.5	652.6	666.8	678.2	683.8	684.8
152.5°	586.4	605.8	622.6	637.4	648.6	658.4	662.6	662.8
155°	574.9	590.0	604.2	614.7	625.1	631.7	635.5	633.7
157.5°	561.4	574.1	586.0	594.2	601.6	607.1	608.8	608.8
160°	553.1	563.5	574.0	580.6	587.2	591.9	592.9	592.9
162.5°	544.8	553.7	562.6	567.7	574.3	577.6	578.5	577.7
165°	532.3	538.9	545.5	549.3	553.1	556.9	556.9	556.0
167.5°	520.3	525.5	530.0	533.5	535.1	537.2	537.0	535.9
170°	514.3	517.1	520.9	522.8	523.7	526.6	525.6	523.7
172.5°	507.4	509.6	512.6	513.7	514.7	516.0	515.0	513.9
175°	500.1	501.0	502.0	502.9	502.9	503.9	502.9	501.0
177.5°	494.8	494.8	495.5	495.5	495.5	495.5	494.8	493.3
180°	492.5	492.5	492.5	492.5	492.5	492.5	492.5	492.5

(END OF REPORT)