

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333563-940

Luminaire Tested: **S125RDIP-S850D810U940-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333563-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S850D810U940-4F0-1E-UDD-A1
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 810 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5424.4 lumens
Efficiency: N/A
Efficacy: 118.2 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 45.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333563-940

CATALOG NUMBER: S125RDIP-S850D810U940-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P333563-940

CATALOG NUMBER: S125RDIP-S850D810U940-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	86	86	86	72	72	72	60	60	60	54
1	99	95	91	88	92	88	85	82	76	73	71	64	63	61	54	52	51	46
2	91	83	77	72	84	78	72	68	67	63	60	57	54	52	48	46	44	40
3	83	74	67	61	77	69	62	57	59	55	51	51	47	44	43	40	38	34
4	76	65	58	52	70	61	54	49	53	48	43	45	41	38	38	35	33	29
5	70	58	50	45	65	55	48	42	47	42	38	41	37	33	35	31	29	26
6	64	53	45	39	60	49	42	37	43	37	33	37	33	29	31	28	25	23
7	60	48	40	34	55	45	37	32	39	33	29	34	29	26	29	25	23	20
8	55	43	36	30	51	41	34	29	36	30	26	31	26	23	26	23	20	18
9	52	39	32	27	48	37	30	26	33	27	23	28	24	21	24	21	18	16
10	48	36	29	24	45	34	28	23	30	25	21	26	22	19	23	19	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	7284	7284	7284	7284
5°	8381	7295	6442	7295
10°	9613	7257	5684	7257
15°	10384	7182	5052	7182
20°	11450	7096	4665	7096
25°	13251	6981	4329	6981
30°	14420	6861	4109	6861
35°	12163	6720	3906	6720
40°	8494	6468	3731	6468
45°	6301	6128	3561	6128
50°	5025	5773	3414	5773
55°	4264	5334	3284	5334
60°	3685	4941	3074	4941
65°	3283	4514	2647	4514
70°	2885	4135	2413	4135
75°	2495	3583	2266	3583
80°	1893	3016	1893	3016
85°	1578	2364	1786	2364



TEST NUMBER: P333563-940

CATALOG NUMBER: S125RDIP-S850D810U940-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	108.2	2.0
10°-20°	317.0	5.8
20°-30°	502.6	9.3
30°-40°	606.1	11.2
40°-50°	541.2	10.0
50°-60°	415.1	7.7
60°-70°	269.7	5.0
70°-80°	131.1	2.4
80°-90°	33.3	0.6
90°-100°	60.0	1.1
100°-110°	177.2	3.3
110°-120°	300.2	5.5
120°-130°	395.0	7.3
130°-140°	442.6	8.2
140°-150°	433.8	8.0
150°-160°	364.4	6.7
160°-170°	242.2	4.5
170°-180°	84.8	1.6
0°-30°	927.7	17.1
0°-40°	1533.8	28.3
0°-60°	2490.1	45.9
0°-90°	2924.2	53.9
90°-120°	537.4	9.9
90°-150°	1808.9	33.3
90°-180°	2500.0	46.1
0°-180°	5424.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1128	1128	1128	1128	1128	
5°	1293	1125	994	1125	1293	129
15°	1553	1074	756	1074	1553	445
25°	1860	980	608	980	1860	854
35°	1543	852	495	852	1543	932
45°	690	671	390	671	690	550
55°	379	474	292	474	379	344
65°	215	295	173	295	215	214
75°	100	144	91	144	100	106
85°	21	32	24	32	21	25
90°	17	1	17	1	17	11
95°	60	45	60	45	60	61
105°	173	159	173	159	173	183
115°	303	300	303	300	303	300
125°	441	438	441	438	441	394
135°	572	570	572	570	572	442
145°	694	691	694	691	694	433
155°	791	791	791	791	791	364
165°	858	860	858	860	858	242
175°	890	894	890	894	890	85
180°	896	896	896	896	896	



TEST NUMBER: P333563-940

CATALOG NUMBER: S125RDIP-S850D810U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9
2.5°	1186.4	1185.7	1187.2	1183.1	1183.5	1177.1	1177.1	1172.3	1166.1	1161.3	1159.0
5°	1292.7	1293.7	1291.8	1284.9	1280.2	1273.3	1265.4	1251.5	1239.9	1228.9	1220.0
7.5°	1402.2	1402.8	1396.8	1394.6	1383.0	1374.4	1356.9	1338.0	1321.2	1299.9	1283.7
10°	1465.9	1465.4	1459.0	1453.8	1443.7	1430.7	1413.6	1391.3	1370.6	1347.4	1325.2
12.5°	1503.0	1501.7	1499.7	1493.5	1484.1	1472.6	1458.0	1436.2	1410.5	1385.2	1359.2
15°	1553.0	1549.7	1543.7	1535.8	1522.4	1509.0	1492.8	1473.4	1448.8	1420.0	1396.0
17.5°	1614.8	1614.9	1605.7	1594.7	1576.5	1552.8	1527.8	1496.4	1463.0	1431.5	1405.8
20°	1666.0	1664.6	1655.3	1634.0	1613.2	1583.5	1554.8	1516.4	1475.6	1434.4	1402.5
22.5°	1739.3	1735.7	1726.1	1698.1	1665.8	1627.6	1583.7	1536.8	1487.5	1440.7	1398.8
25°	1859.5	1856.7	1837.7	1805.4	1760.0	1701.1	1643.7	1579.4	1508.5	1447.0	1396.0
27.5°	1941.7	1938.7	1924.6	1897.6	1855.8	1793.9	1716.2	1630.2	1541.8	1457.1	1383.6
30°	1933.6	1940.5	1938.7	1926.2	1894.7	1839.2	1767.4	1670.6	1565.5	1465.9	1378.4
32.5°	1817.2	1823.5	1839.8	1864.3	1866.2	1844.0	1790.3	1700.9	1592.1	1478.9	1374.3
35°	1542.7	1551.1	1582.6	1632.2	1696.9	1751.1	1762.3	1714.1	1616.4	1494.6	1368.2
37.5°	1186.1	1231.6	1258.1	1310.3	1408.2	1507.9	1603.7	1639.0	1597.4	1488.2	1358.3
40°	1007.5	1018.6	1065.9	1124.7	1207.1	1310.8	1447.4	1546.0	1549.3	1473.4	1342.7
42.5°	862.3	876.4	908.8	955.7	1026.4	1130.1	1271.0	1401.2	1461.5	1432.6	1322.4
45°	689.9	700.5	724.2	760.3	814.5	900.1	1021.5	1171.9	1291.4	1338.1	1267.7
47.5°	566.8	572.5	593.1	620.5	660.7	723.1	817.0	947.6	1090.9	1191.3	1181.4
50°	500.1	506.6	522.3	543.1	576.9	629.7	704.7	813.5	961.3	1084.0	1108.5
52.5°	448.2	453.6	463.4	483.1	511.0	551.5	612.1	710.5	843.5	973.9	1030.6
55°	378.7	382.5	390.3	401.4	423.7	452.8	505.2	573.2	680.6	812.2	895.5
57.5°	321.6	323.3	328.4	338.7	354.0	375.3	413.1	470.8	547.9	666.3	758.2
60°	285.3	287.0	293.6	300.5	312.5	332.0	361.6	401.9	476.0	573.6	666.7
62.5°	256.4	257.4	260.2	267.2	277.7	292.7	316.0	348.9	407.9	493.7	581.6
65°	214.8	215.3	216.2	221.8	228.3	239.4	254.7	277.8	322.3	387.1	464.8
67.5°	175.0	175.7	178.9	180.8	187.6	193.4	202.4	220.2	251.5	295.2	355.6
70°	152.8	152.3	155.6	157.9	160.2	167.1	173.2	187.5	207.0	240.3	290.8
72.5°	132.1	130.8	132.2	133.0	136.2	140.9	146.9	155.7	170.7	193.6	232.3
75°	100.0	100.5	100.5	101.4	103.7	105.6	107.5	112.1	120.4	135.6	156.5
77.5°	70.2	69.5	71.4	71.7	73.0	75.1	76.7	78.6	81.9	88.3	99.0
80°	50.9	50.9	51.4	52.8	52.3	53.2	55.6	57.4	61.6	65.3	69.0
82.5°	39.1	38.7	39.1	39.4	39.3	40.3	41.1	41.5	43.1	44.9	47.5
85°	21.3	21.3	21.8	21.8	22.2	22.2	22.6	22.6	22.6	23.2	23.6
87.5°	11.5	11.1	10.6	10.4	10.8	11.4	10.9	10.3	10.2	10.0	10.2
90°	16.8	16.2	15.8	15.3	14.9	14.3	13.5	12.7	11.9	11.1	10.1
92.5°	32.9	32.5	32.2	31.9	31.6	30.9	29.9	28.8	27.8	26.8	25.4
95°	59.9	59.7	59.4	59.0	58.8	58.1	57.0	55.8	54.8	53.7	52.2
97.5°	91.0	90.8	90.5	90.3	90.2	89.6	88.5	87.6	86.5	85.5	83.4
100°	114.3	114.0	113.7	113.4	113.2	112.3	110.8	109.5	108.1	106.6	104.7
102.5°	137.8	137.3	136.9	136.5	136.1	135.1	133.6	132.1	130.5	129.0	128.0
105°	172.9	172.5	172.0	171.6	171.0	170.4	169.4	168.5	167.6	166.7	165.7
107.5°	208.9	208.9	208.9	209.0	209.0	208.8	208.3	207.9	207.4	207.0	206.3
110°	235.7	235.9	235.9	236.1	236.3	236.1	235.7	235.2	234.8	234.3	233.8



TEST NUMBER: P333563-940

CATALOG NUMBER: S125RDIP-S850D810U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	261.9	262.2	262.4	262.7	263.1	263.1	262.8	262.6	262.4	262.2	261.6
115°	303.4	303.4	303.6	303.8	303.9	304.1	304.3	304.4	304.5	304.7	304.4
117.5°	343.8	344.4	345.0	345.6	346.3	346.5	346.3	346.3	346.1	346.0	345.7
120°	371.7	372.3	372.9	373.5	374.2	374.4	374.4	374.4	374.4	374.4	374.3
122.5°	399.6	400.0	400.6	401.0	401.5	401.8	402.0	402.1	402.2	402.3	401.9
125°	441.4	441.6	441.7	441.8	442.0	442.2	442.6	442.8	443.2	443.4	443.3
127.5°	481.5	481.9	482.1	482.5	482.8	483.0	483.1	483.3	483.5	483.7	483.5
130°	508.3	508.6	508.9	509.3	509.5	509.8	510.0	510.1	510.2	510.4	510.1
132.5°	533.4	533.9	534.3	534.8	535.1	535.5	535.6	535.7	535.9	536.1	536.1
135°	572.5	573.1	573.7	574.4	575.0	575.2	575.2	575.2	575.2	575.2	575.1
137.5°	610.6	611.4	612.2	613.0	613.8	614.0	613.9	613.7	613.5	613.3	613.0
140°	635.3	636.0	636.8	637.6	638.3	638.6	638.2	637.9	637.7	637.3	636.9
142.5°	658.6	659.4	660.2	660.9	661.7	662.0	661.8	661.6	661.5	661.3	660.7
145°	693.8	694.3	694.7	695.2	695.6	695.9	695.9	695.9	695.9	695.9	695.4
147.5°	723.8	724.9	725.9	726.9	728.0	728.3	728.0	727.5	727.2	726.8	726.5
150°	746.1	746.4	746.7	747.0	747.3	747.5	747.5	747.5	747.5	747.5	746.9
152.5°	764.5	765.1	765.6	766.2	766.7	766.8	766.4	766.1	765.7	765.4	765.1
155°	790.7	791.5	792.3	793.0	793.8	793.9	793.3	792.6	792.0	791.4	791.2
157.5°	812.6	813.6	814.7	815.6	816.7	816.9	816.3	815.6	815.0	814.4	814.2
160°	827.7	828.4	829.2	830.0	830.8	830.8	830.2	829.6	829.0	828.4	828.2
162.5°	840.5	841.4	842.3	843.2	844.1	844.2	843.5	842.7	842.0	841.2	841.2
165°	857.6	858.5	859.5	860.4	861.4	861.5	860.9	860.3	859.7	859.1	858.9
167.5°	871.3	872.3	873.3	874.2	875.1	875.2	874.2	873.3	872.4	871.5	871.5
170°	878.6	879.7	880.7	881.8	882.9	883.0	882.1	881.1	880.2	879.2	879.2
172.5°	884.7	885.6	886.6	887.6	888.6	888.6	887.6	886.7	885.7	884.8	884.8
175°	890.5	891.5	892.6	893.7	894.7	894.8	893.9	893.0	892.1	891.1	891.1
177.5°	893.8	894.7	895.5	896.3	897.2	897.3	896.5	895.8	895.1	894.3	894.5
180°	896.0	896.0	896.0	896.0	896.0	896.0	896.0	896.0	896.0	896.0	896.0



TEST NUMBER: P333563-940

CATALOG NUMBER: S125RDIP-S850D810U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9
2.5°	1159.0	1156.5	1151.6	1147.2	1141.7	1136.8	1133.5	1129.4	1124.2	1117.9	1112.8
5°	1210.3	1200.2	1186.7	1175.2	1160.3	1148.8	1136.8	1125.2	1113.6	1098.8	1085.7
7.5°	1267.2	1246.2	1225.7	1200.0	1176.6	1155.7	1135.8	1115.5	1095.7	1074.7	1054.4
10°	1302.0	1276.6	1248.3	1215.8	1186.2	1158.0	1132.1	1106.6	1079.8	1056.1	1030.6
12.5°	1334.6	1301.7	1269.4	1228.5	1192.9	1158.4	1125.4	1093.7	1065.0	1034.3	1007.0
15°	1364.1	1331.7	1295.6	1245.5	1196.0	1154.3	1115.4	1074.2	1038.6	1004.3	973.7
17.5°	1375.5	1341.5	1299.5	1251.4	1197.3	1144.9	1094.8	1049.5	1007.6	967.7	933.4
20°	1371.0	1338.1	1295.0	1249.2	1191.3	1136.8	1082.5	1032.5	985.8	943.6	907.0
22.5°	1360.2	1326.2	1284.7	1236.3	1181.3	1123.4	1065.5	1012.2	963.1	919.5	879.7
25°	1344.2	1297.9	1255.3	1208.0	1155.7	1098.3	1038.6	979.7	927.5	883.0	839.5
27.5°	1327.4	1269.6	1215.4	1168.5	1113.2	1061.9	1004.4	944.1	889.1	843.8	799.2
30°	1312.2	1247.4	1187.7	1134.4	1082.1	1033.5	978.8	920.0	863.5	816.8	771.4
32.5°	1293.3	1224.4	1158.8	1097.3	1046.9	998.6	949.2	893.0	837.9	789.7	743.6
35°	1269.6	1181.6	1110.4	1045.0	989.0	942.3	897.8	852.4	797.3	747.3	702.4
37.5°	1238.5	1138.6	1056.1	985.1	926.0	879.0	843.9	802.5	752.2	704.3	662.5
40°	1219.6	1107.5	1017.3	946.9	884.8	835.3	802.5	767.2	721.4	676.5	634.8
42.5°	1194.4	1079.1	978.0	904.6	842.2	794.5	761.3	730.6	692.1	649.8	605.2
45°	1145.0	1023.8	917.7	839.0	776.1	729.2	698.2	670.9	641.8	602.9	563.9
47.5°	1080.8	966.1	855.1	769.2	707.5	664.1	634.0	612.4	591.6	558.5	520.7
50°	1029.3	918.6	810.3	726.9	661.2	620.0	591.7	574.6	555.6	525.5	494.0
52.5°	968.6	869.8	763.6	678.4	616.4	577.7	550.6	533.5	517.8	493.3	463.3
55°	872.8	786.2	688.9	611.6	554.7	515.8	489.9	473.7	464.4	443.5	420.0
57.5°	762.3	700.3	614.5	539.9	489.6	451.2	432.2	418.4	408.0	393.2	376.6
60°	685.3	641.8	564.9	494.0	447.7	411.2	394.0	382.5	372.7	360.3	347.2
62.5°	607.1	575.4	508.5	447.7	405.1	374.5	358.5	348.0	336.8	328.4	315.8
65°	502.4	474.1	427.8	380.1	340.8	316.2	304.7	295.4	288.5	279.2	270.4
67.5°	390.7	379.3	347.3	314.5	286.2	264.4	254.4	247.9	239.6	234.0	228.0
70°	322.3	316.7	294.0	272.2	245.8	231.0	221.8	219.0	208.8	203.3	199.1
72.5°	261.5	259.0	245.8	230.8	212.1	199.2	190.6	187.5	181.0	176.6	173.9
75°	179.1	180.1	177.8	168.1	161.1	152.8	145.3	143.6	138.9	135.2	132.9
77.5°	113.3	118.1	118.2	117.8	115.0	109.9	106.8	105.5	100.9	99.5	99.0
80°	77.8	82.8	87.5	87.0	86.1	84.7	82.4	81.1	78.7	77.3	76.4
82.5°	51.9	56.6	60.5	63.0	62.8	61.4	59.8	59.2	58.7	57.7	57.5
85°	24.5	25.5	26.8	30.1	32.4	32.9	32.4	31.9	30.6	31.0	31.5
87.5°	10.3	10.1	10.3	10.0	9.4	11.0	11.9	11.9	11.5	11.0	10.5
90°	9.0	7.9	6.8	5.6	4.5	3.2	2.0	0.7	2.0	3.2	4.5
92.5°	24.1	22.7	21.4	20.3	19.4	18.6	17.7	16.9	17.7	18.6	19.4
95°	50.6	49.0	47.5	46.5	46.3	45.9	45.7	45.3	45.7	45.9	46.3
97.5°	81.2	79.1	77.0	75.8	75.7	75.5	75.4	75.3	75.4	75.5	75.7
100°	102.6	100.7	98.6	97.6	97.6	97.6	97.6	97.6	97.6	97.6	97.6
102.5°	127.0	125.9	124.9	124.1	123.5	122.9	122.3	121.6	122.3	122.9	123.5
105°	164.8	163.9	162.9	162.1	161.3	160.5	159.8	159.0	159.8	160.5	161.3
107.5°	205.5	204.8	204.1	203.4	202.6	201.8	201.0	200.3	201.0	201.8	202.6
110°	233.4	232.9	232.5	231.8	231.0	230.2	229.5	228.7	229.5	230.2	231.0



TEST NUMBER: P333563-940

CATALOG NUMBER: S125RDIP-S850D810U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	261.0	260.4	259.8	259.3	259.0	258.5	258.2	257.7	258.2	258.5	259.0
115°	304.1	303.8	303.4	303.0	302.4	301.8	301.1	300.5	301.1	301.8	302.4
117.5°	345.4	345.2	344.9	344.6	344.3	344.0	343.8	343.5	343.8	344.0	344.3
120°	374.2	374.0	373.8	373.4	372.6	371.8	371.0	370.2	371.0	371.8	372.6
122.5°	401.5	401.1	400.7	400.4	400.1	399.8	399.6	399.2	399.6	399.8	400.1
125°	443.2	443.0	442.8	442.3	441.4	440.4	439.5	438.5	439.5	440.4	441.4
127.5°	483.2	483.0	482.9	482.5	482.0	481.4	481.0	480.5	481.0	481.4	482.0
130°	509.8	509.4	509.2	508.6	507.8	507.1	506.3	505.5	506.3	507.1	507.8
132.5°	536.2	536.3	536.3	535.7	534.4	533.2	531.9	530.7	531.9	533.2	534.4
135°	575.0	574.8	574.6	574.1	573.2	572.2	571.3	570.3	571.3	572.2	573.2
137.5°	612.6	612.3	612.0	611.4	610.5	609.6	608.7	607.8	608.7	609.6	610.5
140°	636.4	635.9	635.4	634.8	634.1	633.3	632.5	631.8	632.5	633.3	634.1
142.5°	660.1	659.5	659.0	658.4	657.6	657.0	656.4	655.8	656.4	657.0	657.6
145°	694.9	694.5	694.0	693.5	692.9	692.2	691.6	691.0	691.6	692.2	692.9
147.5°	726.1	725.8	725.3	725.0	724.7	724.3	724.0	723.6	724.0	724.3	724.7
150°	746.3	745.6	745.0	744.8	744.9	745.1	745.2	745.4	745.2	745.1	744.9
152.5°	764.8	764.6	764.4	764.1	763.9	763.7	763.5	763.2	763.5	763.7	763.9
155°	791.1	790.9	790.8	790.7	790.7	790.7	790.7	790.7	790.7	790.7	790.7
157.5°	814.1	814.0	813.8	813.9	814.2	814.6	814.9	815.3	814.9	814.6	814.2
160°	828.0	827.9	827.8	827.9	828.4	828.8	829.3	829.7	829.3	828.8	828.4
162.5°	841.2	841.1	841.1	841.2	841.6	841.9	842.2	842.6	842.2	841.9	841.6
165°	858.7	858.5	858.4	858.5	858.8	859.2	859.4	859.8	859.4	859.2	858.8
167.5°	871.5	871.5	871.5	871.7	872.4	873.0	873.6	874.2	873.6	873.0	872.4
170°	879.2	879.2	879.2	879.6	880.2	880.8	881.5	882.1	881.5	880.8	880.2
172.5°	884.8	884.8	884.8	885.1	885.7	886.4	887.0	887.6	887.0	886.4	885.7
175°	891.1	891.1	891.1	891.4	892.1	892.7	893.3	893.9	893.3	892.7	892.1
177.5°	894.6	894.7	894.8	895.1	895.6	896.2	896.6	897.2	896.6	896.2	895.6
180°	896.0	896.0	896.0	896.0	896.0	896.0	896.0	896.0	896.0	896.0	896.0



TEST NUMBER: P333563-940

CATALOG NUMBER: S125RDIP-S850D810U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9
2.5°	1109.0	1103.8	1100.1	1092.7	1087.5	1085.3	1081.3	1080.1	1084.2	1081.3	1080.8
5°	1076.0	1062.7	1052.0	1041.3	1029.7	1022.3	1011.2	1009.4	1006.6	1002.5	1001.5
7.5°	1036.5	1019.0	1005.3	987.7	972.4	960.1	946.2	939.7	936.0	930.7	923.5
10°	1009.9	989.0	970.4	952.9	933.9	918.6	904.7	894.1	887.2	880.7	877.9
12.5°	983.6	962.3	938.6	917.3	896.2	879.0	863.6	856.7	849.0	841.4	834.9
15°	942.7	914.4	888.5	864.0	846.0	827.4	812.6	802.5	790.9	787.6	775.1
17.5°	899.4	871.6	841.3	815.5	794.5	774.2	757.9	746.3	737.6	725.7	719.9
20°	872.4	839.5	809.9	786.2	763.0	739.0	722.3	712.6	704.3	694.6	689.9
22.5°	843.5	811.3	781.0	753.2	729.7	706.1	694.2	684.0	674.6	665.7	659.5
25°	801.0	768.7	736.6	707.9	683.4	666.3	652.4	640.8	635.7	627.0	620.5
27.5°	759.1	724.6	691.4	662.9	643.6	626.7	615.3	606.1	596.9	589.2	583.6
30°	732.0	696.9	660.8	638.0	617.7	601.5	589.0	580.1	573.2	566.2	562.1
32.5°	705.0	668.7	636.7	612.1	592.8	578.9	566.0	557.6	550.3	542.6	537.7
35°	661.6	624.6	598.7	574.6	555.6	542.7	533.9	521.8	515.8	510.2	505.2
37.5°	621.3	586.9	558.8	537.8	521.3	508.4	497.0	490.5	483.1	478.1	473.9
40°	591.7	560.3	534.8	512.6	500.5	486.2	475.5	467.2	461.6	455.1	450.5
42.5°	565.1	535.8	511.0	491.1	476.1	464.0	453.7	445.3	438.3	433.6	429.8
45°	527.4	498.2	474.1	455.6	441.8	430.2	419.5	415.4	406.1	400.6	398.7
47.5°	488.4	462.3	439.1	422.0	407.8	396.8	386.8	378.3	373.2	367.7	364.8
50°	462.1	437.1	415.4	398.7	384.8	372.7	363.5	357.9	351.0	345.9	342.1
52.5°	435.8	412.7	390.9	375.0	362.9	350.9	340.5	334.9	328.4	325.1	322.5
55°	398.2	373.6	355.2	339.4	326.9	315.8	306.0	300.5	296.3	293.1	292.1
57.5°	355.6	336.2	319.0	304.8	291.8	281.3	272.8	267.5	263.9	263.3	260.6
60°	327.8	310.2	294.4	279.2	268.0	258.3	250.9	245.0	241.2	240.8	239.9
62.5°	300.1	283.2	268.6	255.1	245.1	235.8	228.7	221.9	219.7	217.4	215.4
65°	258.9	243.5	231.5	220.9	210.2	202.3	195.4	191.2	186.1	183.3	178.3
67.5°	218.4	206.5	194.9	185.9	177.6	170.1	164.3	158.2	154.7	152.5	148.8
70°	191.7	182.4	170.9	161.1	154.6	148.6	144.0	137.1	134.7	132.9	131.0
72.5°	166.5	158.4	148.6	140.8	134.3	128.6	123.2	120.0	117.7	115.8	114.8
75°	131.0	123.1	114.9	109.2	104.7	100.0	97.2	94.9	94.0	93.5	91.7
77.5°	96.2	92.0	85.3	81.0	77.8	76.1	73.6	72.3	72.2	70.2	69.6
80°	73.7	71.3	65.7	63.9	61.6	59.7	58.3	56.0	53.7	52.8	51.4
82.5°	54.8	52.4	50.2	47.3	45.3	44.1	42.8	41.9	42.3	40.9	40.3
85°	29.2	26.8	25.9	25.5	24.5	25.5	25.0	24.5	24.1	23.6	24.1
87.5°	10.4	10.6	10.4	11.4	10.5	11.1	11.2	11.1	11.2	11.4	11.1
90°	5.6	6.8	7.9	9.0	10.1	11.1	11.9	12.7	13.5	14.3	14.9
92.5°	20.3	21.4	22.7	24.1	25.4	26.8	27.8	28.8	29.9	30.9	31.6
95°	46.5	47.5	49.0	50.6	52.2	53.7	54.8	55.8	57.0	58.1	58.8
97.5°	75.8	77.0	79.1	81.2	83.4	85.5	86.5	87.6	88.5	89.6	90.2
100°	97.6	98.6	100.7	102.6	104.7	106.6	108.1	109.5	110.8	112.3	113.2
102.5°	124.1	124.9	125.9	127.0	128.0	129.0	130.5	132.1	133.6	135.1	136.1
105°	162.1	162.9	163.9	164.8	165.7	166.7	167.6	168.5	169.4	170.4	171.0
107.5°	203.4	204.1	204.8	205.5	206.3	207.0	207.4	207.9	208.3	208.8	209.0
110°	231.8	232.5	232.9	233.4	233.8	234.3	234.8	235.2	235.7	236.1	236.3



TEST NUMBER: P333563-940

CATALOG NUMBER: S125RDIP-S850D810U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	259.3	259.8	260.4	261.0	261.6	262.2	262.4	262.6	262.8	263.1	263.1
115°	303.0	303.4	303.8	304.1	304.4	304.7	304.5	304.4	304.3	304.1	303.9
117.5°	344.6	344.9	345.2	345.4	345.7	346.0	346.1	346.3	346.3	346.5	346.3
120°	373.4	373.8	374.0	374.2	374.3	374.4	374.4	374.4	374.4	374.4	374.2
122.5°	400.4	400.7	401.1	401.5	401.9	402.3	402.2	402.1	402.0	401.8	401.5
125°	442.3	442.8	443.0	443.2	443.3	443.4	443.2	442.8	442.6	442.2	442.0
127.5°	482.5	482.9	483.0	483.2	483.5	483.7	483.5	483.3	483.1	483.0	482.8
130°	508.6	509.2	509.4	509.8	510.1	510.4	510.2	510.1	510.0	509.8	509.5
132.5°	535.7	536.3	536.3	536.2	536.1	536.1	535.9	535.7	535.6	535.5	535.1
135°	574.1	574.6	574.8	575.0	575.1	575.2	575.2	575.2	575.2	575.2	575.0
137.5°	611.4	612.0	612.3	612.6	613.0	613.3	613.5	613.7	613.9	614.0	613.8
140°	634.8	635.4	635.9	636.4	636.9	637.3	637.7	637.9	638.2	638.6	638.3
142.5°	658.4	659.0	659.5	660.1	660.7	661.3	661.5	661.6	661.8	662.0	661.7
145°	693.5	694.0	694.5	694.9	695.4	695.9	695.9	695.9	695.9	695.9	695.6
147.5°	725.0	725.3	725.8	726.1	726.5	726.8	727.2	727.5	728.0	728.3	728.0
150°	744.8	745.0	745.6	746.3	746.9	747.5	747.5	747.5	747.5	747.5	747.3
152.5°	764.1	764.4	764.6	764.8	765.1	765.4	765.7	766.1	766.4	766.8	766.7
155°	790.7	790.8	790.9	791.1	791.2	791.4	792.0	792.6	793.3	793.9	793.8
157.5°	813.9	813.8	814.0	814.1	814.2	814.4	815.0	815.6	816.3	816.9	816.7
160°	827.9	827.8	827.9	828.0	828.2	828.4	829.0	829.6	830.2	830.8	830.8
162.5°	841.2	841.1	841.1	841.2	841.2	841.2	842.0	842.7	843.5	844.2	844.1
165°	858.5	858.4	858.5	858.7	858.9	859.1	859.7	860.3	860.9	861.5	861.4
167.5°	871.7	871.5	871.5	871.5	871.5	871.5	872.4	873.3	874.2	875.2	875.1
170°	879.6	879.2	879.2	879.2	879.2	879.2	880.2	881.1	882.1	883.0	882.9
172.5°	885.1	884.8	884.8	884.8	884.8	884.8	885.7	886.7	887.6	888.6	888.6
175°	891.4	891.1	891.1	891.1	891.1	891.1	892.1	893.0	893.9	894.8	894.7
177.5°	895.1	894.8	894.7	894.6	894.5	894.3	895.1	895.8	896.5	897.3	897.2
180°	896.0	896.0	896.0	896.0	896.0	896.0	896.0	896.0	896.0	896.0	896.0



TEST NUMBER: P333563-940

CATALOG NUMBER: S125RDIP-S850D810U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9
2.5°	1080.5	1076.5	1075.3	1076.8	1075.3	1076.5	1080.5	1080.8	1081.3	1084.2	1080.1
5°	996.8	992.3	994.5	993.6	994.5	992.3	996.8	1001.5	1002.5	1006.6	1009.4
7.5°	923.4	917.6	911.5	913.5	911.5	917.6	923.4	923.5	930.7	936.0	939.7
10°	871.8	867.3	864.4	866.7	864.4	867.3	871.8	877.9	880.7	887.2	894.1
12.5°	828.5	825.7	823.3	822.3	823.3	825.7	828.5	834.9	841.4	849.0	856.7
15°	769.5	764.0	761.7	755.6	761.7	764.0	769.5	775.1	787.6	790.9	802.5
17.5°	715.2	713.4	707.3	704.7	707.3	713.4	715.2	719.9	725.7	737.6	746.3
20°	683.0	681.1	675.1	678.8	675.1	681.1	683.0	689.9	694.6	704.3	712.6
22.5°	656.3	652.2	650.2	649.2	650.2	652.2	656.3	659.5	665.7	674.6	684.0
25°	618.6	612.6	610.3	607.5	610.3	612.6	618.6	620.5	627.0	635.7	640.8
27.5°	581.0	577.7	574.7	574.0	574.7	577.7	581.0	583.6	589.2	596.9	606.1
30°	556.5	553.3	551.0	551.0	551.0	553.3	556.5	562.1	566.2	573.2	580.1
32.5°	534.7	532.2	529.9	529.5	529.9	532.2	534.7	537.7	542.6	550.3	557.6
35°	502.8	499.2	498.2	495.4	498.2	499.2	502.8	505.2	510.2	515.8	521.8
37.5°	469.8	466.7	466.6	466.4	466.6	466.7	469.8	473.9	478.1	483.1	490.5
40°	448.7	446.4	445.9	442.6	445.9	446.4	448.7	450.5	455.1	461.6	467.2
42.5°	426.1	424.9	423.3	421.9	423.3	424.9	426.1	429.8	433.6	438.3	445.3
45°	395.4	392.2	392.2	389.9	392.2	392.2	395.4	398.7	400.6	406.1	415.4
47.5°	363.7	361.2	361.5	359.1	361.5	361.2	363.7	364.8	367.7	373.2	378.3
50°	342.6	341.3	340.8	339.8	340.8	341.3	342.6	342.1	345.9	351.0	357.9
52.5°	321.6	320.8	322.6	320.6	322.6	320.8	321.6	322.5	325.1	328.4	334.9
55°	293.1	291.7	294.4	291.7	294.4	291.7	293.1	292.1	293.1	296.3	300.5
57.5°	260.4	259.1	261.6	260.2	261.6	259.1	260.4	260.6	263.3	263.9	267.5
60°	238.9	236.1	237.6	238.0	237.6	236.1	238.9	239.9	240.8	241.2	245.0
62.5°	213.4	211.7	212.7	210.6	212.7	211.7	213.4	215.4	217.4	219.7	221.9
65°	177.4	175.9	174.1	173.2	174.1	175.9	177.4	178.3	183.3	186.1	191.2
67.5°	149.0	145.7	145.6	146.3	145.6	145.7	149.0	148.8	152.5	154.7	158.2
70°	128.2	128.2	127.8	127.8	127.8	128.2	128.2	131.0	132.9	134.7	137.1
72.5°	113.8	113.4	112.6	112.3	112.6	113.4	113.8	114.8	115.8	117.7	120.0
75°	91.7	92.1	91.2	90.8	91.2	92.1	91.7	91.7	93.5	94.0	94.9
77.5°	67.7	65.7	66.8	65.7	66.8	65.7	67.7	69.6	70.2	72.2	72.3
80°	51.4	50.9	52.3	50.9	52.3	50.9	51.4	51.4	52.8	53.7	56.0
82.5°	40.7	40.2	40.8	39.9	40.8	40.2	40.7	40.3	40.9	42.3	41.9
85°	24.5	24.1	23.6	24.1	23.6	24.1	24.5	24.1	23.6	24.1	24.5
87.5°	11.6	11.3	11.4	11.5	11.4	11.3	11.6	11.1	11.4	11.2	11.1
90°	15.3	15.8	16.2	16.8	16.2	15.8	15.3	14.9	14.3	13.5	12.7
92.5°	31.9	32.2	32.5	32.9	32.5	32.2	31.9	31.6	30.9	29.9	28.8
95°	59.0	59.4	59.7	59.9	59.7	59.4	59.0	58.8	58.1	57.0	55.8
97.5°	90.3	90.5	90.8	91.0	90.8	90.5	90.3	90.2	89.6	88.5	87.6
100°	113.4	113.7	114.0	114.3	114.0	113.7	113.4	113.2	112.3	110.8	109.5
102.5°	136.5	136.9	137.3	137.8	137.3	136.9	136.5	136.1	135.1	133.6	132.1
105°	171.6	172.0	172.5	172.9	172.5	172.0	171.6	171.0	170.4	169.4	168.5
107.5°	209.0	208.9	208.9	208.9	208.9	208.9	209.0	209.0	208.8	208.3	207.9
110°	236.1	235.9	235.9	235.7	235.9	235.9	236.1	236.3	236.1	235.7	235.2



TEST NUMBER: P333563-940

CATALOG NUMBER: S125RDIP-S850D810U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	262.7	262.4	262.2	261.9	262.2	262.4	262.7	263.1	263.1	262.8	262.6
115°	303.8	303.6	303.4	303.4	303.4	303.6	303.8	303.9	304.1	304.3	304.4
117.5°	345.6	345.0	344.4	343.8	344.4	345.0	345.6	346.3	346.5	346.3	346.3
120°	373.5	372.9	372.3	371.7	372.3	372.9	373.5	374.2	374.4	374.4	374.4
122.5°	401.0	400.6	400.0	399.6	400.0	400.6	401.0	401.5	401.8	402.0	402.1
125°	441.8	441.7	441.6	441.4	441.6	441.7	441.8	442.0	442.2	442.6	442.8
127.5°	482.5	482.1	481.9	481.5	481.9	482.1	482.5	482.8	483.0	483.1	483.3
130°	509.3	508.9	508.6	508.3	508.6	508.9	509.3	509.5	509.8	510.0	510.1
132.5°	534.8	534.3	533.9	533.4	533.9	534.3	534.8	535.1	535.5	535.6	535.7
135°	574.4	573.7	573.1	572.5	573.1	573.7	574.4	575.0	575.2	575.2	575.2
137.5°	613.0	612.2	611.4	610.6	611.4	612.2	613.0	613.8	614.0	613.9	613.7
140°	637.6	636.8	636.0	635.3	636.0	636.8	637.6	638.3	638.6	638.2	637.9
142.5°	660.9	660.2	659.4	658.6	659.4	660.2	660.9	661.7	662.0	661.8	661.6
145°	695.2	694.7	694.3	693.8	694.3	694.7	695.2	695.6	695.9	695.9	695.9
147.5°	726.9	725.9	724.9	723.8	724.9	725.9	726.9	728.0	728.3	728.0	727.5
150°	747.0	746.7	746.4	746.1	746.4	746.7	747.0	747.3	747.5	747.5	747.5
152.5°	766.2	765.6	765.1	764.5	765.1	765.6	766.2	766.7	766.8	766.4	766.1
155°	793.0	792.3	791.5	790.7	791.5	792.3	793.0	793.8	793.9	793.3	792.6
157.5°	815.6	814.7	813.6	812.6	813.6	814.7	815.6	816.7	816.9	816.3	815.6
160°	830.0	829.2	828.4	827.7	828.4	829.2	830.0	830.8	830.8	830.2	829.6
162.5°	843.2	842.3	841.4	840.5	841.4	842.3	843.2	844.1	844.2	843.5	842.7
165°	860.4	859.5	858.5	857.6	858.5	859.5	860.4	861.4	861.5	860.9	860.3
167.5°	874.2	873.3	872.3	871.3	872.3	873.3	874.2	875.1	875.2	874.2	873.3
170°	881.8	880.7	879.7	878.6	879.7	880.7	881.8	882.9	883.0	882.1	881.1
172.5°	887.6	886.6	885.6	884.7	885.6	886.6	887.6	888.6	888.6	887.6	886.7
175°	893.7	892.6	891.5	890.5	891.5	892.6	893.7	894.7	894.8	893.9	893.0
177.5°	896.3	895.5	894.7	893.8	894.7	895.5	896.3	897.2	897.3	896.5	895.8
180°	896.0	896.0	896.0	896.0	896.0	896.0	896.0	896.0	896.0	896.0	896.0



TEST NUMBER: P333563-940

CATALOG NUMBER: S125RDIP-S850D810U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9
2.5°	1081.3	1085.3	1087.5	1092.7	1100.1	1103.8	1109.0	1112.8	1117.9	1124.2	1129.4
5°	1011.2	1022.3	1029.7	1041.3	1052.0	1062.7	1076.0	1085.7	1098.8	1113.6	1125.2
7.5°	946.2	960.1	972.4	987.7	1005.3	1019.0	1036.5	1054.4	1074.7	1095.7	1115.5
10°	904.7	918.6	933.9	952.9	970.4	989.0	1009.9	1030.6	1056.1	1079.8	1106.6
12.5°	863.6	879.0	896.2	917.3	938.6	962.3	983.6	1007.0	1034.3	1065.0	1093.7
15°	812.6	827.4	846.0	864.0	888.5	914.4	942.7	973.7	1004.3	1038.6	1074.2
17.5°	757.9	774.2	794.5	815.5	841.3	871.6	899.4	933.4	967.7	1007.6	1049.5
20°	722.3	739.0	763.0	786.2	809.9	839.5	872.4	907.0	943.6	985.8	1032.5
22.5°	694.2	706.1	729.7	753.2	781.0	811.3	843.5	879.7	919.5	963.1	1012.2
25°	652.4	666.3	683.4	707.9	736.6	768.7	801.0	839.5	883.0	927.5	979.7
27.5°	615.3	626.7	643.6	662.9	691.4	724.6	759.1	799.2	843.8	889.1	944.1
30°	589.0	601.5	617.7	638.0	660.8	696.9	732.0	771.4	816.8	863.5	920.0
32.5°	566.0	578.9	592.8	612.1	636.7	668.7	705.0	743.6	789.7	837.9	893.0
35°	533.9	542.7	555.6	574.6	598.7	624.6	661.6	702.4	747.3	797.3	852.4
37.5°	497.0	508.4	521.3	537.8	558.8	586.9	621.3	662.5	704.3	752.2	802.5
40°	475.5	486.2	500.5	512.6	534.8	560.3	591.7	634.8	676.5	721.4	767.2
42.5°	453.7	464.0	476.1	491.1	511.0	535.8	565.1	605.2	649.8	692.1	730.6
45°	419.5	430.2	441.8	455.6	474.1	498.2	527.4	563.9	602.9	641.8	670.9
47.5°	386.8	396.8	407.8	422.0	439.1	462.3	488.4	520.7	558.5	591.6	612.4
50°	363.5	372.7	384.8	398.7	415.4	437.1	462.1	494.0	525.5	555.6	574.6
52.5°	340.5	350.9	362.9	375.0	390.9	412.7	435.8	463.3	493.3	517.8	533.5
55°	306.0	315.8	326.9	339.4	355.2	373.6	398.2	420.0	443.5	464.4	473.7
57.5°	272.8	281.3	291.8	304.8	319.0	336.2	355.6	376.6	393.2	408.0	418.4
60°	250.9	258.3	268.0	279.2	294.4	310.2	327.8	347.2	360.3	372.7	382.5
62.5°	228.7	235.8	245.1	255.1	268.6	283.2	300.1	315.8	328.4	336.8	348.0
65°	195.4	202.3	210.2	220.9	231.5	243.5	258.9	270.4	279.2	288.5	295.4
67.5°	164.3	170.1	177.6	185.9	194.9	206.5	218.4	228.0	234.0	239.6	247.9
70°	144.0	148.6	154.6	161.1	170.9	182.4	191.7	199.1	203.3	208.8	219.0
72.5°	123.2	128.6	134.3	140.8	148.6	158.4	166.5	173.9	176.6	181.0	187.5
75°	97.2	100.0	104.7	109.2	114.9	123.1	131.0	132.9	135.2	138.9	143.6
77.5°	73.6	76.1	77.8	81.0	85.3	92.0	96.2	99.0	99.5	100.9	105.5
80°	58.3	59.7	61.6	63.9	65.7	71.3	73.7	76.4	77.3	78.7	81.1
82.5°	42.8	44.1	45.3	47.3	50.2	52.4	54.8	57.5	57.7	58.7	59.2
85°	25.0	25.5	24.5	25.5	25.9	26.8	29.2	31.5	31.0	30.6	31.9
87.5°	11.2	11.1	10.5	11.4	10.4	10.6	10.4	10.5	11.0	11.5	11.9
90°	11.9	11.1	10.1	9.0	7.9	6.8	5.6	4.5	3.2	2.0	0.7
92.5°	27.8	26.8	25.4	24.1	22.7	21.4	20.3	19.4	18.6	17.7	16.9
95°	54.8	53.7	52.2	50.6	49.0	47.5	46.5	46.3	45.9	45.7	45.3
97.5°	86.5	85.5	83.4	81.2	79.1	77.0	75.8	75.7	75.5	75.4	75.3
100°	108.1	106.6	104.7	102.6	100.7	98.6	97.6	97.6	97.6	97.6	97.6
102.5°	130.5	129.0	128.0	127.0	125.9	124.9	124.1	123.5	122.9	122.3	121.6
105°	167.6	166.7	165.7	164.8	163.9	162.9	162.1	161.3	160.5	159.8	159.0
107.5°	207.4	207.0	206.3	205.5	204.8	204.1	203.4	202.6	201.8	201.0	200.3
110°	234.8	234.3	233.8	233.4	232.9	232.5	231.8	231.0	230.2	229.5	228.7



TEST NUMBER: P333563-940

CATALOG NUMBER: S125RDIP-S850D810U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	262.4	262.2	261.6	261.0	260.4	259.8	259.3	259.0	258.5	258.2	257.7
115°	304.5	304.7	304.4	304.1	303.8	303.4	303.0	302.4	301.8	301.1	300.5
117.5°	346.1	346.0	345.7	345.4	345.2	344.9	344.6	344.3	344.0	343.8	343.5
120°	374.4	374.4	374.3	374.2	374.0	373.8	373.4	372.6	371.8	371.0	370.2
122.5°	402.2	402.3	401.9	401.5	401.1	400.7	400.4	400.1	399.8	399.6	399.2
125°	443.2	443.4	443.3	443.2	443.0	442.8	442.3	441.4	440.4	439.5	438.5
127.5°	483.5	483.7	483.5	483.2	483.0	482.9	482.5	482.0	481.4	481.0	480.5
130°	510.2	510.4	510.1	509.8	509.4	509.2	508.6	507.8	507.1	506.3	505.5
132.5°	535.9	536.1	536.1	536.2	536.3	536.3	535.7	534.4	533.2	531.9	530.7
135°	575.2	575.2	575.1	575.0	574.8	574.6	574.1	573.2	572.2	571.3	570.3
137.5°	613.5	613.3	613.0	612.6	612.3	612.0	611.4	610.5	609.6	608.7	607.8
140°	637.7	637.3	636.9	636.4	635.9	635.4	634.8	634.1	633.3	632.5	631.8
142.5°	661.5	661.3	660.7	660.1	659.5	659.0	658.4	657.6	657.0	656.4	655.8
145°	695.9	695.9	695.4	694.9	694.5	694.0	693.5	692.9	692.2	691.6	691.0
147.5°	727.2	726.8	726.5	726.1	725.8	725.3	725.0	724.7	724.3	724.0	723.6
150°	747.5	747.5	746.9	746.3	745.6	745.0	744.8	744.9	745.1	745.2	745.4
152.5°	765.7	765.4	765.1	764.8	764.6	764.4	764.1	763.9	763.7	763.5	763.2
155°	792.0	791.4	791.2	791.1	790.9	790.8	790.7	790.7	790.7	790.7	790.7
157.5°	815.0	814.4	814.2	814.1	814.0	813.8	813.9	814.2	814.6	814.9	815.3
160°	829.0	828.4	828.2	828.0	827.9	827.8	827.9	828.4	828.8	829.3	829.7
162.5°	842.0	841.2	841.2	841.2	841.1	841.1	841.2	841.6	841.9	842.2	842.6
165°	859.7	859.1	858.9	858.7	858.5	858.4	858.5	858.8	859.2	859.4	859.8
167.5°	872.4	871.5	871.5	871.5	871.5	871.5	871.7	872.4	873.0	873.6	874.2
170°	880.2	879.2	879.2	879.2	879.2	879.2	879.6	880.2	880.8	881.5	882.1
172.5°	885.7	884.8	884.8	884.8	884.8	884.8	885.1	885.7	886.4	887.0	887.6
175°	892.1	891.1	891.1	891.1	891.1	891.1	891.4	892.1	892.7	893.3	893.9
177.5°	895.1	894.3	894.5	894.6	894.7	894.8	895.1	895.6	896.2	896.6	897.2
180°	896.0	896.0	896.0	896.0	896.0	896.0	896.0	896.0	896.0	896.0	896.0



TEST NUMBER: P333563-940

CATALOG NUMBER: S125RDIP-S850D810U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9
2.5°	1133.5	1136.8	1141.7	1147.2	1151.6	1156.5	1159.0	1159.0	1161.3	1166.1	1172.3
5°	1136.8	1148.8	1160.3	1175.2	1186.7	1200.2	1210.3	1220.0	1228.9	1239.9	1251.5
7.5°	1135.8	1155.7	1176.6	1200.0	1225.7	1246.2	1267.2	1283.7	1299.9	1321.2	1338.0
10°	1132.1	1158.0	1186.2	1215.8	1248.3	1276.6	1302.0	1325.2	1347.4	1370.6	1391.3
12.5°	1125.4	1158.4	1192.9	1228.5	1269.4	1301.7	1334.6	1359.2	1385.2	1410.5	1436.2
15°	1115.4	1154.3	1196.0	1245.5	1295.6	1331.7	1364.1	1396.0	1420.0	1448.8	1473.4
17.5°	1094.8	1144.9	1197.3	1251.4	1299.5	1341.5	1375.5	1405.8	1431.5	1463.0	1496.4
20°	1082.5	1136.8	1191.3	1249.2	1295.0	1338.1	1371.0	1402.5	1434.4	1475.6	1516.4
22.5°	1065.5	1123.4	1181.3	1236.3	1284.7	1326.2	1360.2	1398.8	1440.7	1487.5	1536.8
25°	1038.6	1098.3	1155.7	1208.0	1255.3	1297.9	1344.2	1396.0	1447.0	1508.5	1579.4
27.5°	1004.4	1061.9	1113.2	1168.5	1215.4	1269.6	1327.4	1383.6	1457.1	1541.8	1630.2
30°	978.8	1033.5	1082.1	1134.4	1187.7	1247.4	1312.2	1378.4	1465.9	1565.5	1670.6
32.5°	949.2	998.6	1046.9	1097.3	1158.8	1224.4	1293.3	1374.3	1478.9	1592.1	1700.9
35°	897.8	942.3	989.0	1045.0	1110.4	1181.6	1269.6	1368.2	1494.6	1616.4	1714.1
37.5°	843.9	879.0	926.0	985.1	1056.1	1138.6	1238.5	1358.3	1488.2	1597.4	1639.0
40°	802.5	835.3	884.8	946.9	1017.3	1107.5	1219.6	1342.7	1473.4	1549.3	1546.0
42.5°	761.3	794.5	842.2	904.6	978.0	1079.1	1194.4	1322.4	1432.6	1461.5	1401.2
45°	698.2	729.2	776.1	839.0	917.7	1023.8	1145.0	1267.7	1338.1	1291.4	1171.9
47.5°	634.0	664.1	707.5	769.2	855.1	966.1	1080.8	1181.4	1191.3	1090.9	947.6
50°	591.7	620.0	661.2	726.9	810.3	918.6	1029.3	1108.5	1084.0	961.3	813.5
52.5°	550.6	577.7	616.4	678.4	763.6	869.8	968.6	1030.6	973.9	843.5	710.5
55°	489.9	515.8	554.7	611.6	688.9	786.2	872.8	895.5	812.2	680.6	573.2
57.5°	432.2	451.2	489.6	539.9	614.5	700.3	762.3	758.2	666.3	547.9	470.8
60°	394.0	411.2	447.7	494.0	564.9	641.8	685.3	666.7	573.6	476.0	401.9
62.5°	358.5	374.5	405.1	447.7	508.5	575.4	607.1	581.6	493.7	407.9	348.9
65°	304.7	316.2	340.8	380.1	427.8	474.1	502.4	464.8	387.1	322.3	277.8
67.5°	254.4	264.4	286.2	314.5	347.3	379.3	390.7	355.6	295.2	251.5	220.2
70°	221.8	231.0	245.8	272.2	294.0	316.7	322.3	290.8	240.3	207.0	187.5
72.5°	190.6	199.2	212.1	230.8	245.8	259.0	261.5	232.3	193.6	170.7	155.7
75°	145.3	152.8	161.1	168.1	177.8	180.1	179.1	156.5	135.6	120.4	112.1
77.5°	106.8	109.9	115.0	117.8	118.2	118.1	113.3	99.0	88.3	81.9	78.6
80°	82.4	84.7	86.1	87.0	87.5	82.8	77.8	69.0	65.3	61.6	57.4
82.5°	59.8	61.4	62.8	63.0	60.5	56.6	51.9	47.5	44.9	43.1	41.5
85°	32.4	32.9	32.4	30.1	26.8	25.5	24.5	23.6	23.2	22.6	22.6
87.5°	11.9	11.0	9.4	10.0	10.3	10.1	10.3	10.2	10.0	10.2	10.3
90°	2.0	3.2	4.5	5.6	6.8	7.9	9.0	10.1	11.1	11.9	12.7
92.5°	17.7	18.6	19.4	20.3	21.4	22.7	24.1	25.4	26.8	27.8	28.8
95°	45.7	45.9	46.3	46.5	47.5	49.0	50.6	52.2	53.7	54.8	55.8
97.5°	75.4	75.5	75.7	75.8	77.0	79.1	81.2	83.4	85.5	86.5	87.6
100°	97.6	97.6	97.6	97.6	98.6	100.7	102.6	104.7	106.6	108.1	109.5
102.5°	122.3	122.9	123.5	124.1	124.9	125.9	127.0	128.0	129.0	130.5	132.1
105°	159.8	160.5	161.3	162.1	162.9	163.9	164.8	165.7	166.7	167.6	168.5
107.5°	201.0	201.8	202.6	203.4	204.1	204.8	205.5	206.3	207.0	207.4	207.9
110°	229.5	230.2	231.0	231.8	232.5	232.9	233.4	233.8	234.3	234.8	235.2



TEST NUMBER: P333563-940

CATALOG NUMBER: S125RDIP-S850D810U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	258.2	258.5	259.0	259.3	259.8	260.4	261.0	261.6	262.2	262.4	262.6
115°	301.1	301.8	302.4	303.0	303.4	303.8	304.1	304.4	304.7	304.5	304.4
117.5°	343.8	344.0	344.3	344.6	344.9	345.2	345.4	345.7	346.0	346.1	346.3
120°	371.0	371.8	372.6	373.4	373.8	374.0	374.2	374.3	374.4	374.4	374.4
122.5°	399.6	399.8	400.1	400.4	400.7	401.1	401.5	401.9	402.3	402.2	402.1
125°	439.5	440.4	441.4	442.3	442.8	443.0	443.2	443.3	443.4	443.2	442.8
127.5°	481.0	481.4	482.0	482.5	482.9	483.0	483.2	483.5	483.7	483.5	483.3
130°	506.3	507.1	507.8	508.6	509.2	509.4	509.8	510.1	510.4	510.2	510.1
132.5°	531.9	533.2	534.4	535.7	536.3	536.3	536.2	536.1	536.1	535.9	535.7
135°	571.3	572.2	573.2	574.1	574.6	574.8	575.0	575.1	575.2	575.2	575.2
137.5°	608.7	609.6	610.5	611.4	612.0	612.3	612.6	613.0	613.3	613.5	613.7
140°	632.5	633.3	634.1	634.8	635.4	635.9	636.4	636.9	637.3	637.7	637.9
142.5°	656.4	657.0	657.6	658.4	659.0	659.5	660.1	660.7	661.3	661.5	661.6
145°	691.6	692.2	692.9	693.5	694.0	694.5	694.9	695.4	695.9	695.9	695.9
147.5°	724.0	724.3	724.7	725.0	725.3	725.8	726.1	726.5	726.8	727.2	727.5
150°	745.2	745.1	744.9	744.8	745.0	745.6	746.3	746.9	747.5	747.5	747.5
152.5°	763.5	763.7	763.9	764.1	764.4	764.6	764.8	765.1	765.4	765.7	766.1
155°	790.7	790.7	790.7	790.7	790.8	790.9	791.1	791.2	791.4	792.0	792.6
157.5°	814.9	814.6	814.2	813.9	813.8	814.0	814.1	814.2	814.4	815.0	815.6
160°	829.3	828.8	828.4	827.9	827.8	827.9	828.0	828.2	828.4	829.0	829.6
162.5°	842.2	841.9	841.6	841.2	841.1	841.1	841.2	841.2	841.2	842.0	842.7
165°	859.4	859.2	858.8	858.5	858.4	858.5	858.7	858.9	859.1	859.7	860.3
167.5°	873.6	873.0	872.4	871.7	871.5	871.5	871.5	871.5	871.5	872.4	873.3
170°	881.5	880.8	880.2	879.6	879.2	879.2	879.2	879.2	879.2	880.2	881.1
172.5°	887.0	886.4	885.7	885.1	884.8	884.8	884.8	884.8	884.8	885.7	886.7
175°	893.3	892.7	892.1	891.4	891.1	891.1	891.1	891.1	891.1	892.1	893.0
177.5°	896.6	896.2	895.6	895.1	894.8	894.7	894.6	894.5	894.3	895.1	895.8
180°	896.0	896.0	896.0	896.0	896.0	896.0	896.0	896.0	896.0	896.0	896.0



TEST NUMBER: P333563-940

CATALOG NUMBER: S125RDIP-S850D810U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9
2.5°	1177.1	1177.1	1183.5	1183.1	1187.2	1185.7	1186.4
5°	1265.4	1273.3	1280.2	1284.9	1291.8	1293.7	1292.7
7.5°	1356.9	1374.4	1383.0	1394.6	1396.8	1402.8	1402.2
10°	1413.6	1430.7	1443.7	1453.8	1459.0	1465.4	1465.9
12.5°	1458.0	1472.6	1484.1	1493.5	1499.7	1501.7	1503.0
15°	1492.8	1509.0	1522.4	1535.8	1543.7	1549.7	1553.0
17.5°	1527.8	1552.8	1576.5	1594.7	1605.7	1614.9	1614.8
20°	1554.8	1583.5	1613.2	1634.0	1655.3	1664.6	1666.0
22.5°	1583.7	1627.6	1665.8	1698.1	1726.1	1735.7	1739.3
25°	1643.7	1701.1	1760.0	1805.4	1837.7	1856.7	1859.5
27.5°	1716.2	1793.9	1855.8	1897.6	1924.6	1938.7	1941.7
30°	1767.4	1839.2	1894.7	1926.2	1938.7	1940.5	1933.6
32.5°	1790.3	1844.0	1866.2	1864.3	1839.8	1823.5	1817.2
35°	1762.3	1751.1	1696.9	1632.2	1582.6	1551.1	1542.7
37.5°	1603.7	1507.9	1408.2	1310.3	1258.1	1231.6	1186.1
40°	1447.4	1310.8	1207.1	1124.7	1065.9	1018.6	1007.5
42.5°	1271.0	1130.1	1026.4	955.7	908.8	876.4	862.3
45°	1021.5	900.1	814.5	760.3	724.2	700.5	689.9
47.5°	817.0	723.1	660.7	620.5	593.1	572.5	566.8
50°	704.7	629.7	576.9	543.1	522.3	506.6	500.1
52.5°	612.1	551.5	511.0	483.1	463.4	453.6	448.2
55°	505.2	452.8	423.7	401.4	390.3	382.5	378.7
57.5°	413.1	375.3	354.0	338.7	328.4	323.3	321.6
60°	361.6	332.0	312.5	300.5	293.6	287.0	285.3
62.5°	316.0	292.7	277.7	267.2	260.2	257.4	256.4
65°	254.7	239.4	228.3	221.8	216.2	215.3	214.8
67.5°	202.4	193.4	187.6	180.8	178.9	175.7	175.0
70°	173.2	167.1	160.2	157.9	155.6	152.3	152.8
72.5°	146.9	140.9	136.2	133.0	132.2	130.8	132.1
75°	107.5	105.6	103.7	101.4	100.5	100.5	100.0
77.5°	76.7	75.1	73.0	71.7	71.4	69.5	70.2
80°	55.6	53.2	52.3	52.8	51.4	50.9	50.9
82.5°	41.1	40.3	39.3	39.4	39.1	38.7	39.1
85°	22.6	22.2	22.2	21.8	21.8	21.3	21.3
87.5°	10.9	11.4	10.8	10.4	10.6	11.1	11.5
90°	13.5	14.3	14.9	15.3	15.8	16.2	16.8
92.5°	29.9	30.9	31.6	31.9	32.2	32.5	32.9
95°	57.0	58.1	58.8	59.0	59.4	59.7	59.9
97.5°	88.5	89.6	90.2	90.3	90.5	90.8	91.0
100°	110.8	112.3	113.2	113.4	113.7	114.0	114.3
102.5°	133.6	135.1	136.1	136.5	136.9	137.3	137.8
105°	169.4	170.4	171.0	171.6	172.0	172.5	172.9
107.5°	208.3	208.8	209.0	209.0	208.9	208.9	208.9
110°	235.7	236.1	236.3	236.1	235.9	235.9	235.7



TEST NUMBER: P333563-940

CATALOG NUMBER: S125RDIP-S850D810U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	262.8	263.1	263.1	262.7	262.4	262.2	261.9
115°	304.3	304.1	303.9	303.8	303.6	303.4	303.4
117.5°	346.3	346.5	346.3	345.6	345.0	344.4	343.8
120°	374.4	374.4	374.2	373.5	372.9	372.3	371.7
122.5°	402.0	401.8	401.5	401.0	400.6	400.0	399.6
125°	442.6	442.2	442.0	441.8	441.7	441.6	441.4
127.5°	483.1	483.0	482.8	482.5	482.1	481.9	481.5
130°	510.0	509.8	509.5	509.3	508.9	508.6	508.3
132.5°	535.6	535.5	535.1	534.8	534.3	533.9	533.4
135°	575.2	575.2	575.0	574.4	573.7	573.1	572.5
137.5°	613.9	614.0	613.8	613.0	612.2	611.4	610.6
140°	638.2	638.6	638.3	637.6	636.8	636.0	635.3
142.5°	661.8	662.0	661.7	660.9	660.2	659.4	658.6
145°	695.9	695.9	695.6	695.2	694.7	694.3	693.8
147.5°	728.0	728.3	728.0	726.9	725.9	724.9	723.8
150°	747.5	747.5	747.3	747.0	746.7	746.4	746.1
152.5°	766.4	766.8	766.7	766.2	765.6	765.1	764.5
155°	793.3	793.9	793.8	793.0	792.3	791.5	790.7
157.5°	816.3	816.9	816.7	815.6	814.7	813.6	812.6
160°	830.2	830.8	830.8	830.0	829.2	828.4	827.7
162.5°	843.5	844.2	844.1	843.2	842.3	841.4	840.5
165°	860.9	861.5	861.4	860.4	859.5	858.5	857.6
167.5°	874.2	875.2	875.1	874.2	873.3	872.3	871.3
170°	882.1	883.0	882.9	881.8	880.7	879.7	878.6
172.5°	887.6	888.6	888.6	887.6	886.6	885.6	884.7
175°	893.9	894.8	894.7	893.7	892.6	891.5	890.5
177.5°	896.5	897.3	897.2	896.3	895.5	894.7	893.8
180°	896.0	896.0	896.0	896.0	896.0	896.0	896.0

(END OF REPORT)