

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333567-940

Luminaire Tested: **S125RDIP-S850D810U940-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333567-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S850D810U940-4F0-1E-UDD-F4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 810 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5492.0 lumens
Efficiency: N/A
Efficacy: 119.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 45.9
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333567-940

CATALOG NUMBER: S125RDIP-S850D810U940-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P333567-940

CATALOG NUMBER: S125RDIP-S850D810U940-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59	53
1	99	94	91	87	91	88	84	81	75	72	70	63	61	60	52	51	50	45
2	90	83	77	72	83	77	72	67	66	62	58	56	53	50	46	44	42	38
3	82	73	66	60	76	68	61	56	58	53	49	49	46	43	41	39	36	32
4	75	65	57	51	70	60	53	48	52	47	42	44	40	37	37	34	31	28
5	69	58	50	44	64	54	47	41	46	41	37	40	35	32	33	30	28	24
6	64	52	44	38	59	48	41	36	42	36	32	36	32	28	30	27	24	22
7	59	47	39	33	55	44	37	32	38	32	28	33	28	25	28	24	22	19
8	55	43	35	30	51	40	33	28	35	29	25	30	26	22	25	22	20	17
9	51	39	31	26	47	37	30	25	32	26	23	28	23	20	24	20	18	16
10	48	36	29	24	44	34	27	23	29	24	20	26	21	18	22	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7919	7919	7919
5°	7937	7847	7895
10°	7877	7774	7774
15°	7783	7616	7554
20°	7663	7396	7307
25°	7524	7180	7021
30°	7348	6927	6706
35°	7171	6666	6352
40°	7003	6395	6004
45°	6801	6090	5624
50°	6597	5760	5230
55°	6361	5443	4808
60°	6124	5059	4354
65°	5845	4614	3834
70°	5527	4056	3305
75°	5085	3421	2750
80°	4478	2685	2310
85°	3772	2193	2060



TEST NUMBER: P333567-940

CATALOG NUMBER: S125RDIP-S850D810U940-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	115.3	2.1
10°-20°	322.2	5.9
20°-30°	467.2	8.5
30°-40°	532.5	9.7
40°-50°	519.1	9.5
50°-60°	436.9	8.0
60°-70°	306.3	5.6
70°-80°	157.4	2.9
80°-90°	41.7	0.8
90°-100°	250.7	4.6
100°-110°	538.9	9.8
110°-120°	505.7	9.2
120°-130°	409.8	7.5
130°-140°	328.9	6.0
140°-150°	248.2	4.5
150°-160°	174.7	3.2
160°-170°	103.0	1.9
170°-180°	33.5	0.6
0°-30°	904.7	16.5
0°-40°	1437.3	26.2
0°-60°	2393.2	43.6
0°-90°	2898.7	52.8
90°-120°	1295.2	23.6
90°-150°	2282.2	41.6
90°-180°	2593.0	47.2
0°-180°	5492.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1226	1226	1226	1226	1226	
5°	1224	1220	1210	1219	1218	116
15°	1164	1158	1139	1138	1130	328
25°	1056	1041	1008	996	985	486
35°	910	886	846	819	806	569
45°	745	716	667	631	616	574
55°	565	534	483	443	427	505
65°	382	350	302	266	251	379
75°	204	175	137	118	110	216
85°	51	35	30	29	28	57
90°	1	6	11	15	16	4
95°	23	68	618	280	164	24
105°	79	110	506	995	924	83
115°	141	170	406	875	1029	139
125°	195	229	389	696	811	173
135°	229	275	386	583	674	178
145°	266	305	388	483	531	167
155°	304	327	378	427	446	140
165°	332	341	363	385	390	93
175°	345	345	348	352	351	33
180°	346	346	346	346	346	



TEST NUMBER: P333567-940

CATALOG NUMBER: S125RDIP-S850D810U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1226.2	1226.2	1226.2	1226.2	1226.2	1226.2	1226.2	1226.2	1226.2	1226.2	1226.2
2.5°	1228.3	1227.9	1227.4	1226.9	1226.4	1225.3	1223.7	1222.0	1220.4	1218.7	1220.4
5°	1224.3	1223.5	1222.6	1221.8	1221.0	1219.5	1217.2	1215.0	1212.6	1210.4	1212.5
7.5°	1212.3	1211.5	1210.7	1209.9	1209.2	1207.4	1204.7	1201.9	1199.3	1196.5	1197.9
10°	1201.1	1200.5	1199.9	1199.3	1198.6	1196.9	1194.1	1191.1	1188.3	1185.4	1186.0
12.5°	1188.6	1187.8	1187.0	1186.2	1185.4	1183.1	1179.2	1175.4	1171.5	1167.6	1168.1
15°	1164.1	1162.9	1161.6	1160.4	1159.1	1156.4	1152.1	1147.7	1143.4	1139.1	1138.9
17.5°	1136.5	1134.6	1132.7	1130.9	1128.9	1125.2	1119.8	1114.4	1108.9	1103.5	1102.5
20°	1115.0	1112.9	1110.9	1108.8	1106.8	1102.4	1095.9	1089.3	1082.7	1076.1	1075.1
22.5°	1091.3	1089.2	1087.2	1085.1	1083.1	1078.6	1071.7	1064.8	1057.8	1051.0	1048.9
25°	1055.8	1052.7	1049.5	1046.5	1043.4	1038.0	1030.5	1022.8	1015.2	1007.6	1005.0
27.5°	1015.0	1011.3	1007.5	1003.8	1000.1	994.1	986.0	977.8	969.6	961.4	957.7
30°	985.3	981.4	977.6	973.7	969.7	963.4	954.8	946.2	937.5	928.9	924.2
32.5°	956.4	951.9	947.4	942.8	938.2	931.5	922.7	913.9	905.1	896.3	891.1
35°	909.5	904.5	899.6	894.6	889.7	882.5	873.3	864.1	854.8	845.5	839.5
37.5°	863.3	857.3	851.3	845.3	839.3	831.5	822.0	812.3	802.8	793.3	786.1
40°	830.7	824.6	818.3	812.2	806.0	798.0	788.1	778.2	768.4	758.5	750.6
42.5°	796.7	790.3	784.0	777.6	771.2	763.0	752.8	742.6	732.4	722.2	714.7
45°	744.6	738.6	732.6	726.7	720.7	712.0	700.7	689.5	678.1	666.8	658.5
47.5°	690.7	684.4	678.1	671.8	665.5	656.7	645.2	633.8	622.4	611.0	602.5
50°	656.6	649.8	643.0	636.2	629.5	620.2	608.4	596.7	585.0	573.3	564.6
52.5°	619.6	612.6	605.6	598.7	591.7	582.7	571.7	560.6	549.5	538.4	529.1
55°	564.9	558.3	551.8	545.2	538.6	529.5	518.0	506.5	495.0	483.4	474.1
57.5°	509.7	502.7	495.6	488.6	481.6	472.5	461.4	450.2	439.2	428.0	419.0
60°	474.1	467.0	459.8	452.5	445.3	436.2	425.1	413.9	402.9	391.7	382.7
62.5°	436.4	429.5	422.7	415.7	408.8	399.8	388.5	377.3	366.0	354.7	346.3
65°	382.5	375.5	368.5	361.5	354.5	345.5	334.7	323.7	312.8	301.9	293.6
67.5°	329.0	321.9	315.0	308.0	301.0	292.2	281.8	271.3	260.9	250.4	242.9
70°	292.7	285.6	278.7	271.6	264.7	256.0	245.8	235.4	225.2	214.8	208.5
72.5°	257.1	250.2	243.4	236.6	229.8	221.5	211.9	202.2	192.6	183.0	177.1
75°	203.8	197.6	191.4	185.2	179.1	171.7	163.0	154.4	145.7	137.1	132.5
77.5°	150.8	145.8	140.9	136.0	131.0	125.1	118.2	111.3	104.3	97.5	94.3
80°	120.4	115.5	110.5	105.6	100.7	95.3	89.5	83.7	78.0	72.2	70.4
82.5°	90.8	86.3	81.9	77.4	72.9	68.8	64.8	60.9	56.9	53.0	52.1
85°	50.9	47.3	43.5	39.9	36.1	33.7	32.7	31.7	30.7	29.6	29.4
87.5°	17.2	16.1	15.3	14.4	13.6	13.2	13.1	13.3	13.2	13.4	13.5
90°	0.7	1.4	2.8	4.2	5.6	7.0	7.7	9.1	9.7	11.1	11.9
92.5°	8.5	10.3	16.1	24.8	36.8	57.2	95.2	159.1	228.4	224.8	182.0
95°	23.0	23.7	29.2	36.9	52.3	83.6	158.3	311.7	504.1	617.8	604.5
97.5°	38.2	39.1	43.0	50.6	64.4	87.0	136.3	248.8	450.1	659.7	764.8
100°	48.8	50.2	53.0	60.6	73.9	94.8	135.3	225.9	401.6	629.6	803.9
102.5°	60.5	61.3	63.6	71.8	83.9	104.3	140.3	216.4	364.8	576.6	780.5
105°	78.8	78.8	82.3	89.3	100.4	119.9	150.6	212.7	329.1	505.5	705.6
107.5°	96.7	98.0	101.4	107.1	118.7	136.3	165.9	219.1	314.1	456.6	629.2
110°	109.5	110.8	113.6	119.9	130.4	148.5	177.1	225.2	309.6	433.6	585.7



TEST NUMBER: P333567-940

CATALOG NUMBER: S125RDIP-S850D810U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	122.3	123.7	125.9	132.2	142.7	160.2	187.7	233.0	309.6	420.3	553.3
115°	140.8	142.2	144.4	150.6	161.0	178.5	204.3	244.7	311.7	405.8	518.0
117.5°	157.6	159.7	161.9	168.2	180.0	196.9	221.3	258.2	316.3	398.7	497.0
120°	168.7	170.9	173.6	179.9	191.7	209.2	233.5	267.1	320.7	395.3	485.3
122.5°	180.5	182.0	184.2	190.5	203.5	220.9	245.3	277.1	324.6	392.5	475.2
125°	195.2	196.6	200.1	206.3	219.6	237.7	260.7	290.7	331.2	389.1	461.5
127.5°	206.8	208.9	213.4	221.3	235.4	253.5	275.7	303.3	338.6	387.4	449.0
130°	214.0	216.2	221.7	230.8	245.4	263.6	285.2	311.7	343.0	386.3	440.7
132.5°	219.6	222.3	229.0	239.2	254.3	272.5	294.1	318.9	348.0	386.3	434.0
135°	228.7	231.5	239.9	251.0	265.6	284.5	306.1	329.1	354.9	386.3	426.0
137.5°	240.1	242.2	250.0	261.2	275.5	294.9	314.6	336.6	361.1	387.1	418.9
140°	246.8	248.9	257.3	268.4	281.7	300.5	320.7	341.6	363.9	387.6	415.5
142.5°	254.6	256.2	263.9	275.1	287.8	305.5	324.6	344.5	365.6	388.3	412.8
145°	266.4	267.7	274.7	284.5	297.0	313.1	331.2	348.6	367.5	387.6	408.6
147.5°	278.6	279.5	285.4	294.5	305.4	319.5	335.4	351.2	368.1	385.8	404.2
150°	285.9	287.2	292.1	301.2	310.9	322.8	338.1	352.8	368.1	384.1	400.9
152.5°	293.6	294.5	298.8	306.7	316.0	326.7	340.9	353.9	367.6	381.9	397.0
155°	304.0	304.0	308.2	315.1	322.1	331.9	343.8	354.9	366.0	377.9	390.5
157.5°	313.2	313.1	316.4	322.4	328.5	335.9	346.1	355.6	364.3	373.7	384.3
160°	319.3	318.6	321.5	326.3	331.9	338.1	347.2	355.6	362.6	371.0	379.3
162.5°	324.3	323.7	326.5	330.7	335.2	340.4	348.3	355.0	360.9	367.6	374.8
165°	331.9	330.5	332.6	336.1	338.9	343.0	348.6	354.2	358.4	362.6	368.1
167.5°	336.9	336.2	337.4	339.4	341.3	344.0	348.6	352.5	354.5	357.7	361.6
170°	340.3	339.6	340.3	341.6	343.0	345.1	348.6	351.4	352.8	354.9	357.7
172.5°	342.5	341.3	341.9	343.3	344.1	345.1	348.0	350.3	350.5	351.5	353.7
175°	345.1	343.8	344.5	345.1	345.1	345.1	347.2	348.6	347.9	347.9	348.6
177.5°	346.3	345.3	345.3	345.8	345.3	345.3	346.3	347.0	345.8	345.8	346.3
180°	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8



TEST NUMBER: P333567-940

CATALOG NUMBER: S125RDIP-S850D810U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1226.2	1226.2	1226.2	1226.2	1226.2	1226.2	1226.2	1226.2
2.5°	1222.0	1223.7	1225.3	1226.1	1225.9	1225.7	1225.6	1225.4
5°	1214.5	1216.6	1218.6	1219.5	1219.1	1218.6	1218.3	1217.8
7.5°	1199.4	1200.9	1202.3	1202.7	1202.3	1201.8	1201.4	1201.0
10°	1186.6	1187.2	1187.8	1187.8	1187.2	1186.6	1186.0	1185.4
12.5°	1168.5	1168.9	1169.4	1169.2	1168.2	1167.2	1166.4	1165.4
15°	1138.7	1138.4	1138.3	1137.3	1135.4	1133.5	1131.7	1129.8
17.5°	1101.4	1100.5	1099.4	1098.1	1096.6	1095.1	1093.6	1092.1
20°	1074.1	1073.0	1072.0	1070.6	1068.7	1066.8	1065.0	1063.2
22.5°	1046.9	1044.9	1042.9	1041.1	1039.6	1038.0	1036.5	1035.0
25°	1002.3	999.6	996.9	994.4	992.1	989.9	987.7	985.3
27.5°	954.0	950.2	946.5	943.5	941.4	939.1	937.0	934.8
30°	919.4	914.7	909.9	906.7	904.8	902.9	901.1	899.2
32.5°	885.8	880.6	875.4	871.6	869.2	866.9	864.5	862.2
35°	833.6	827.6	821.6	817.3	814.3	811.5	808.6	805.7
37.5°	779.0	771.8	764.6	759.6	756.9	754.0	751.3	748.5
40°	742.8	735.0	727.2	722.0	719.6	717.1	714.6	712.2
42.5°	707.2	699.7	692.2	686.6	683.1	679.4	675.7	672.2
45°	650.3	642.1	633.8	628.2	625.1	622.1	618.9	615.8
47.5°	594.1	585.6	577.1	571.1	567.8	564.4	560.9	557.5
50°	556.0	547.3	538.7	532.8	529.8	526.6	523.5	520.5
52.5°	519.9	510.5	501.2	495.0	492.0	488.8	485.8	482.7
55°	464.9	455.7	446.4	440.1	436.8	433.5	430.3	427.0
57.5°	409.9	400.9	391.8	385.8	382.9	380.0	377.1	374.2
60°	373.6	364.5	355.5	349.5	346.3	343.3	340.2	337.1
62.5°	337.9	329.5	321.1	315.4	312.3	309.2	306.1	303.0
65°	285.4	277.2	268.9	263.3	260.2	257.2	254.0	250.9
67.5°	235.3	227.8	220.3	215.3	212.9	210.4	207.9	205.5
70°	202.1	195.7	189.3	184.9	182.4	179.9	177.5	175.0
72.5°	171.2	165.3	159.4	155.7	154.0	152.4	150.8	149.1
75°	128.0	123.5	119.0	116.0	114.5	113.1	111.6	110.2
77.5°	91.0	87.9	84.7	82.7	81.6	80.5	79.5	78.4
80°	68.6	66.7	64.8	63.7	63.3	62.9	62.4	62.1
82.5°	51.3	50.4	49.5	49.0	48.7	48.5	48.2	48.0
85°	29.2	29.0	28.8	28.6	28.4	28.2	28.0	27.8
87.5°	13.6	13.7	13.9	14.1	13.9	13.7	13.7	13.6
90°	12.6	13.3	13.9	15.3	15.3	15.3	16.1	16.1
92.5°	123.6	89.7	67.5	57.2	48.2	46.5	45.6	44.5
95°	501.3	395.3	309.6	251.0	201.5	180.6	175.0	163.8
97.5°	746.6	672.3	588.7	507.3	464.2	425.2	404.9	396.0
100°	857.6	823.4	751.6	679.1	631.0	580.8	555.0	543.9
102.5°	894.9	916.1	881.5	832.5	781.0	745.3	717.3	708.9
105°	872.9	968.5	999.2	991.5	969.1	946.1	932.2	923.8
107.5°	794.2	921.8	1000.5	1036.9	1048.2	1048.0	1043.5	1037.9
110°	736.3	868.7	967.1	1026.3	1057.7	1070.9	1075.8	1075.8



TEST NUMBER: P333567-940

CATALOG NUMBER: S125RDIP-S850D810U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	690.5	816.3	915.7	985.6	1031.4	1054.2	1066.3	1071.4
115°	633.1	741.2	836.7	912.7	967.1	1000.5	1020.0	1029.1
117.5°	596.0	689.1	771.4	841.2	895.5	930.1	949.5	955.0
120°	575.9	659.6	736.3	797.6	849.2	882.7	901.5	907.0
122.5°	560.9	638.4	706.7	764.2	810.2	840.9	859.7	864.7
125°	539.0	610.1	670.7	720.9	760.0	788.5	803.9	810.8
127.5°	516.7	583.0	639.6	686.6	722.0	747.3	761.8	764.8
130°	502.7	564.1	618.4	663.8	698.7	721.7	735.6	739.8
132.5°	488.7	546.2	595.6	639.2	674.0	697.1	709.9	714.6
135°	470.6	518.7	563.4	603.1	633.7	656.7	669.3	673.5
137.5°	455.3	494.2	531.3	565.0	592.5	613.4	625.0	629.6
140°	446.9	479.7	511.8	541.0	566.9	585.0	595.4	598.9
142.5°	439.7	467.4	495.0	520.4	542.3	557.7	567.6	570.4
145°	430.2	451.8	473.4	492.2	509.0	520.8	528.5	531.3
147.5°	421.2	438.8	455.4	469.7	482.9	492.4	496.9	498.1
150°	416.3	431.6	444.8	457.4	467.9	476.2	479.0	479.7
152.5°	410.6	424.4	436.5	446.2	455.0	461.7	464.5	465.2
155°	402.3	413.5	423.2	430.9	437.8	442.7	444.8	445.5
157.5°	394.0	403.1	410.6	416.7	422.1	426.1	428.1	427.9
160°	388.3	395.3	402.3	407.2	412.1	415.5	417.0	416.3
162.5°	382.2	388.6	394.5	398.8	402.6	405.5	405.8	405.6
165°	373.7	378.6	382.8	386.3	389.1	390.5	390.5	390.5
167.5°	365.6	368.8	372.0	374.5	375.9	377.2	376.7	376.5
170°	361.1	363.3	365.3	366.8	368.1	368.8	368.8	368.1
172.5°	356.1	358.2	359.8	360.6	360.9	362.1	361.1	360.3
175°	350.7	350.7	352.1	352.1	352.1	352.8	351.4	350.7
177.5°	347.0	347.5	347.5	347.5	347.0	347.5	345.8	345.8
180°	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8

(END OF REPORT)