

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331747-930

Luminaire Tested: **SA2XXRDIP-C1005D725U930-4F0-1E-UDD-A**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331747-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C1005D725U930-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 725 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5471.5 lumens
Efficiency: N/A
Efficacy: 90.1 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 60.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331747-930
CATALOG NUMBER: SA2XXRDIP-C1005D725U930-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331747-930

CATALOG NUMBER: SA2XXRDIP-C1005D725U930-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	57
1	100	96	93	89	93	90	87	84	78	75	73	67	65	64	56	55	54	50
2	92	85	79	74	86	80	75	70	69	65	62	60	57	55	51	49	47	43
3	85	76	69	63	79	71	65	60	62	57	54	54	50	47	46	43	41	38
4	78	68	60	54	72	64	57	52	56	51	47	49	45	41	42	39	37	33
5	72	61	53	47	67	57	50	45	50	45	41	44	40	37	38	35	33	30
6	67	55	47	42	62	52	45	40	46	40	36	40	36	33	35	32	29	27
7	62	50	43	37	58	47	41	36	42	37	33	37	33	29	32	29	26	24
8	58	46	38	33	54	43	37	32	39	33	29	34	30	27	30	27	24	22
9	54	42	35	30	51	40	33	29	36	30	27	32	27	24	28	25	22	20
10	51	39	32	27	47	37	31	26	33	28	24	30	25	22	26	23	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	29032	29032	29032	29032
5°	32423	29214	25901	29214
10°	35974	29009	22453	29009
15°	37742	28583	17690	28583
20°	32720	27953	15309	27953
25°	21458	27091	13668	27091
30°	14443	26045	12370	26045
35°	11698	24727	11158	24727
40°	10404	23294	10323	23294
45°	9417	21614	9216	21614
50°	8568	19947	8538	19947
55°	8056	18097	7949	18097
60°	6736	16401	6659	16401
65°	5681	14896	6445	14896
70°	5249	13303	6076	13303
75°	4916	11578	5608	11578
80°	4537	9530	4993	9530
85°	4168	7521	4390	7521



TEST NUMBER: P331747-930

CATALOG NUMBER: SA2XXRDIP-C1005D725U930-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	170.4	3.1
10°-20°	474.9	8.7
20°-30°	612.0	11.2
30°-40°	581.6	10.6
40°-50°	498.2	9.1
50°-60°	379.4	6.9
60°-70°	239.9	4.4
70°-80°	119.8	2.2
80°-90°	33.2	0.6
90°-100°	26.9	0.5
100°-110°	98.6	1.8
110°-120°	263.5	4.8
120°-130°	435.0	8.0
130°-140°	462.7	8.5
140°-150°	430.0	7.9
150°-160°	345.7	6.3
160°-170°	222.8	4.1
170°-180°	76.7	1.4
0°-30°	1257.4	23.0
0°-40°	1839.0	33.6
0°-60°	2716.7	49.7
0°-90°	3109.5	56.8
90°-120°	389.0	7.1
90°-150°	1716.8	31.4
90°-180°	2362.0	43.2
0°-180°	5471.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1798	1798	1798	1798	1798	
5°	2000	1802	1598	1802	2000	197
15°	2258	1710	1058	1710	2258	609
25°	1204	1521	767	1521	1204	572
35°	594	1254	566	1254	594	380
45°	412	947	404	947	412	319
55°	286	643	282	643	286	251
65°	149	390	169	390	149	151
75°	79	186	90	186	79	84
85°	22	41	24	41	22	25
90°	16	1	16	1	16	8
95°	25	38	25	38	25	23
105°	44	177	44	177	44	46
115°	48	335	48	335	48	120
125°	499	474	499	474	499	431
135°	606	587	606	587	606	467
145°	691	681	691	681	691	432
155°	750	749	750	749	750	346
165°	788	790	788	790	788	222
175°	803	808	803	808	803	76
180°	806	806	806	806	806	



TEST NUMBER: P331747-930

CATALOG NUMBER: SA2XXRDIP-C1005D725U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1
2.5°	1871.0	1872.6	1874.0	1870.5	1870.5	1867.5	1861.1	1856.0	1842.1	1840.0	1840.0
5°	2000.5	1999.3	2001.7	1993.7	1982.4	1979.9	1968.1	1952.4	1936.2	1918.1	1914.3
7.5°	2129.2	2127.4	2122.3	2121.0	2112.4	2093.4	2074.4	2054.0	2027.0	2000.7	1987.4
10°	2194.2	2214.8	2202.3	2180.4	2184.8	2155.5	2139.8	2113.0	2090.5	2051.1	2042.4
12.5°	2258.1	2266.3	2262.3	2249.9	2244.3	2223.9	2202.8	2179.5	2138.0	2102.6	2071.8
15°	2257.9	2269.8	2272.9	2269.1	2272.3	2271.0	2259.8	2240.4	2204.2	2165.4	2131.7
17.5°	2091.2	2099.5	2119.9	2133.8	2151.3	2188.3	2206.5	2213.7	2208.3	2186.2	2162.4
20°	1904.3	1890.5	1948.0	1977.4	2002.4	2064.8	2118.6	2139.2	2172.3	2171.7	2165.4
22.5°	1639.4	1642.7	1697.1	1732.0	1805.0	1867.4	1928.7	2006.3	2070.4	2112.7	2137.5
25°	1204.5	1228.3	1282.6	1330.2	1411.4	1527.5	1633.1	1755.6	1871.2	1962.4	2049.3
27.5°	904.7	906.4	949.5	993.4	1041.6	1136.9	1269.7	1416.0	1580.8	1716.8	1873.2
30°	774.7	770.9	789.0	816.0	857.2	930.9	1030.9	1174.6	1338.9	1543.8	1726.2
32.5°	682.7	683.0	696.6	716.5	750.7	800.5	868.9	985.6	1140.9	1342.4	1556.3
35°	593.5	592.9	602.9	617.3	631.6	663.5	710.4	771.6	878.4	1066.5	1285.2
37.5°	529.5	532.3	537.2	546.2	562.1	579.8	607.9	649.0	725.1	836.3	1020.1
40°	493.6	494.8	501.7	509.2	518.5	532.3	555.4	588.6	644.2	732.9	867.2
42.5°	460.6	461.9	466.7	473.7	481.1	494.8	514.0	542.6	587.7	656.9	767.7
45°	412.4	412.4	416.7	419.9	428.0	440.4	456.1	479.8	511.0	562.3	636.0
47.5°	367.1	367.2	370.1	375.5	380.6	390.4	405.7	425.1	447.8	487.5	550.4
50°	341.1	341.8	343.6	348.0	351.1	359.9	371.8	388.6	412.4	443.0	495.5
52.5°	320.2	319.8	322.1	324.0	326.1	332.4	341.3	356.1	377.3	404.0	447.4
55°	286.2	283.6	287.4	290.5	292.4	294.9	299.9	309.2	327.3	349.8	382.4
57.5°	243.7	242.6	245.3	248.2	254.0	260.8	265.1	271.0	280.4	296.5	328.7
60°	208.6	208.6	214.3	216.1	223.1	231.8	240.5	245.6	254.9	265.5	289.3
62.5°	177.7	178.2	180.8	182.7	186.5	197.3	209.5	220.5	229.4	239.5	255.3
65°	148.7	149.9	149.9	151.2	153.7	156.2	161.2	169.9	185.6	199.9	211.8
67.5°	126.2	126.6	126.9	128.2	128.8	131.6	133.5	137.5	141.0	154.7	169.4
70°	111.2	113.1	112.4	113.7	114.3	115.6	118.1	119.9	125.6	128.7	137.5
72.5°	97.2	98.6	98.5	99.2	100.9	101.1	103.1	104.9	108.6	111.2	115.9
75°	78.8	78.1	78.8	80.0	80.6	81.2	81.2	83.7	85.6	88.1	91.2
77.5°	60.7	61.4	61.2	61.4	61.5	62.6	62.5	63.6	65.5	66.7	68.2
80°	48.8	49.3	48.8	49.3	50.0	50.6	50.0	50.6	52.5	53.7	53.7
82.5°	37.7	37.8	38.2	38.4	38.5	38.6	39.5	39.6	41.0	40.8	41.3
85°	22.5	21.9	21.9	21.9	22.5	23.2	22.5	22.5	23.2	23.2	23.2
87.5°	11.2	11.6	11.6	11.5	11.4	11.3	11.3	11.6	10.9	11.3	10.6
90°	15.7	15.5	15.2	15.0	14.7	14.3	13.6	13.0	12.3	11.7	10.6
92.5°	15.7	15.6	15.4	15.2	15.2	14.8	14.5	14.2	13.9	13.5	13.0
95°	25.1	25.2	25.4	25.4	25.6	25.4	24.7	24.1	23.4	22.7	21.9
97.5°	33.5	33.3	33.2	33.0	32.9	32.5	32.0	31.5	31.0	30.4	28.4
100°	39.1	38.8	38.6	38.3	38.1	37.4	36.4	35.3	34.2	33.3	31.1
102.5°	41.9	41.5	41.2	40.8	40.4	39.5	38.2	36.9	35.5	34.2	52.6
105°	44.4	43.8	43.3	42.8	42.2	41.3	39.9	38.4	37.0	35.5	70.9
107.5°	45.6	45.1	44.6	44.0	43.5	44.0	45.4	46.9	48.3	49.8	92.2
110°	46.1	45.6	45.0	44.5	44.0	50.2	63.2	76.1	89.1	102.1	139.5



TEST NUMBER: P331747-930

CATALOG NUMBER: SA2XXRDIP-C1005D725U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	46.6	46.1	45.7	45.3	44.8	68.3	115.6	162.9	210.2	257.4	266.7
115°	47.9	57.2	66.4	75.8	85.1	119.8	179.9	239.9	299.9	359.9	356.6
117.5°	195.3	225.9	256.6	287.2	317.9	340.5	355.0	369.6	384.1	398.6	396.3
120°	355.8	373.2	390.8	408.2	425.7	433.7	432.2	430.6	429.0	427.5	425.2
122.5°	443.9	447.4	450.7	454.1	457.5	458.8	457.8	456.9	455.9	455.0	452.5
125°	498.6	498.2	497.9	497.5	497.1	496.4	495.5	494.6	493.7	492.8	490.3
127.5°	533.2	533.1	533.0	533.0	532.9	532.1	530.8	529.5	528.2	526.8	525.1
130°	554.6	554.7	554.9	555.1	555.1	554.5	553.1	551.6	550.2	548.8	547.4
132.5°	575.6	575.8	575.9	576.0	576.2	575.6	574.4	573.2	571.9	570.7	569.3
135°	605.9	606.2	606.5	606.7	607.0	606.5	605.2	603.9	602.6	601.3	600.1
137.5°	633.6	634.1	634.5	635.0	635.4	635.0	633.7	632.4	631.1	629.9	628.5
140°	650.9	651.5	652.2	652.8	653.5	653.2	652.0	650.9	649.7	648.6	647.1
142.5°	667.6	668.3	669.0	669.6	670.3	670.0	669.0	667.9	666.8	665.8	664.1
145°	691.1	691.8	692.4	693.1	693.7	693.6	692.7	691.8	690.9	689.9	687.7
147.5°	711.8	712.3	712.8	713.4	714.0	713.9	713.2	712.5	711.8	711.2	709.0
150°	724.3	725.0	725.6	726.3	726.9	726.8	726.1	725.3	724.6	723.7	721.7
152.5°	735.1	736.0	736.8	737.7	738.5	738.6	737.8	736.9	736.2	735.4	733.4
155°	750.0	751.1	752.1	753.1	754.2	754.3	753.5	752.8	752.0	751.1	749.6
157.5°	763.7	764.7	765.6	766.7	767.7	767.8	766.9	766.0	765.2	764.3	763.1
160°	771.6	772.5	773.4	774.3	775.2	775.3	774.5	773.7	773.0	772.2	771.4
162.5°	778.1	779.3	780.3	781.5	782.6	782.7	781.8	780.9	780.1	779.2	778.5
165°	787.9	788.8	789.7	790.7	791.6	791.6	790.7	789.7	788.8	787.9	787.5
167.5°	794.1	795.2	796.5	797.6	798.7	798.9	798.0	797.1	796.1	795.2	794.9
170°	797.9	799.0	800.1	801.4	802.5	802.7	801.7	800.8	799.9	799.0	798.7
172.5°	800.6	801.8	803.0	804.1	805.3	805.4	804.5	803.6	802.7	801.8	801.5
175°	803.1	804.4	805.7	807.0	808.3	808.5	807.6	806.7	805.8	804.9	804.5
177.5°	804.6	805.5	806.5	807.4	808.4	808.5	807.7	807.0	806.2	805.5	805.4
180°	806.0	806.0	806.0	806.0	806.0	806.0	806.0	806.0	806.0	806.0	806.0



TEST NUMBER: P331747-930

CATALOG NUMBER: SA2XXRDIP-C1005D725U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1
2.5°	1841.1	1837.0	1833.6	1824.6	1820.1	1810.0	1808.6	1808.1	1795.1	1782.6	1779.1
5°	1904.3	1894.3	1879.3	1861.8	1843.7	1825.0	1812.5	1802.5	1777.4	1753.7	1740.0
7.5°	1968.1	1946.5	1920.7	1887.6	1859.9	1829.0	1806.0	1785.3	1749.9	1715.9	1693.0
10°	2015.5	1980.5	1946.1	1900.5	1864.9	1829.9	1797.5	1769.4	1729.3	1684.4	1652.5
12.5°	2045.0	2006.5	1959.2	1914.6	1868.4	1824.0	1780.5	1744.3	1697.4	1650.9	1613.1
15°	2084.9	2043.6	1986.2	1922.4	1863.0	1805.0	1755.0	1710.0	1648.8	1593.2	1546.9
17.5°	2117.5	2060.8	1999.0	1925.3	1856.6	1782.7	1718.4	1660.9	1592.8	1525.7	1471.2
20°	2127.9	2071.8	2000.5	1926.8	1845.6	1758.8	1689.4	1626.9	1553.8	1480.7	1418.2
22.5°	2121.5	2077.7	1998.5	1910.3	1827.1	1736.3	1657.9	1585.4	1504.3	1429.7	1357.2
25°	2077.4	2062.4	1987.4	1891.2	1796.2	1690.6	1600.0	1520.7	1428.2	1348.3	1269.5
27.5°	1974.5	2006.9	1960.4	1857.9	1752.3	1639.2	1537.3	1447.0	1351.0	1261.0	1182.6
30°	1875.6	1949.9	1929.9	1834.9	1716.9	1605.7	1491.3	1397.0	1294.5	1202.1	1124.6
32.5°	1740.1	1863.0	1882.4	1803.0	1680.9	1558.7	1438.8	1345.0	1238.0	1140.6	1065.1
35°	1524.4	1708.1	1792.4	1741.9	1619.4	1487.6	1363.8	1254.5	1147.0	1050.8	975.9
37.5°	1267.1	1517.4	1657.9	1661.5	1549.1	1412.0	1277.2	1168.7	1058.7	964.3	883.2
40°	1100.2	1371.3	1554.4	1595.1	1500.1	1352.0	1215.8	1105.2	997.8	905.3	812.2
42.5°	950.3	1220.4	1445.4	1516.0	1440.6	1293.6	1156.8	1041.2	936.8	849.3	754.2
45°	768.5	1004.6	1252.6	1378.8	1337.0	1200.8	1056.5	946.6	848.4	772.8	681.6
47.5°	648.2	814.7	1054.8	1225.4	1224.7	1100.3	958.4	853.0	762.1	691.2	617.4
50°	579.8	724.7	927.8	1121.4	1137.7	1033.4	898.4	794.1	709.1	634.8	575.4
52.5°	518.3	637.7	820.4	1006.0	1052.2	961.9	831.0	734.6	652.2	583.8	533.0
55°	438.0	530.4	669.1	842.8	912.8	849.1	732.9	642.9	576.0	518.5	474.8
57.5°	370.5	439.9	551.1	691.0	772.5	732.4	636.5	563.5	506.2	454.2	419.7
60°	328.0	384.8	479.2	596.1	686.0	657.9	576.0	507.9	459.2	414.3	381.7
62.5°	288.0	336.9	417.8	512.6	595.0	583.4	516.6	459.4	416.7	375.8	348.2
65°	231.8	267.4	330.5	404.9	471.1	476.7	428.6	389.9	351.7	319.3	294.9
67.5°	184.6	207.8	252.3	314.9	364.5	382.2	352.9	323.3	293.0	267.9	246.8
70°	155.6	174.3	206.8	257.4	303.0	321.7	304.9	281.8	255.5	234.9	216.8
72.5°	126.0	144.3	168.3	205.5	244.5	264.8	258.9	242.3	221.0	203.9	186.8
75°	95.0	100.6	116.8	141.9	172.4	190.0	194.3	185.6	168.7	155.6	145.5
77.5°	70.2	73.6	81.4	94.5	114.5	130.0	136.5	135.4	123.8	116.2	106.8
80°	56.3	58.1	61.9	67.5	82.5	98.1	102.5	102.5	94.3	91.2	81.9
82.5°	42.7	44.1	46.4	49.5	56.5	70.1	75.0	76.0	70.8	66.7	59.4
85°	24.4	23.7	25.0	26.9	28.1	31.9	39.4	40.6	39.4	34.3	32.4
87.5°	10.4	10.7	10.5	9.8	9.9	10.2	12.4	14.6	12.9	11.7	11.0
90°	9.6	8.6	7.5	6.3	4.9	3.4	2.0	0.6	2.0	3.4	4.9
92.5°	12.5	12.0	11.5	11.3	11.4	11.5	11.7	11.7	11.7	11.5	11.4
95°	21.0	20.1	19.1	20.8	25.1	29.4	33.7	37.9	33.7	29.4	25.1
97.5°	26.3	24.1	22.0	27.0	39.1	51.1	63.2	75.3	63.2	51.1	39.1
100°	28.9	26.7	24.5	32.2	50.0	67.8	85.4	103.2	85.4	67.8	50.0
102.5°	71.0	89.4	107.9	119.0	122.8	126.5	130.3	134.0	130.3	126.5	122.8
105°	106.3	141.7	177.1	192.8	189.0	185.1	181.2	177.3	181.2	185.1	189.0
107.5°	134.7	177.1	219.6	239.2	236.0	232.9	229.8	226.7	229.8	232.9	236.0
110°	177.0	214.4	251.8	269.2	266.5	263.8	261.1	258.4	261.1	263.8	266.5



TEST NUMBER: P331747-930

CATALOG NUMBER: SA2XXRDIP-C1005D725U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	275.9	285.2	294.4	297.8	295.5	293.0	290.7	288.2	290.7	293.0	295.5
115°	353.4	350.1	346.9	344.1	341.9	339.7	337.5	335.3	337.5	339.7	341.9
117.5°	394.1	391.9	389.6	387.3	384.8	382.4	379.9	377.5	379.9	382.4	384.8
120°	422.8	420.5	418.2	416.0	414.1	412.1	410.2	408.2	410.2	412.1	414.1
122.5°	450.0	447.4	444.8	442.5	440.5	438.5	436.4	434.4	436.4	438.5	440.5
125°	487.9	485.4	483.0	480.9	479.2	477.5	475.8	474.2	475.8	477.5	479.2
127.5°	523.2	521.4	519.5	517.6	515.8	514.0	512.1	510.2	512.1	514.0	515.8
130°	545.9	544.5	543.1	541.4	539.2	537.2	535.2	533.0	535.2	537.2	539.2
132.5°	567.9	566.5	565.0	563.5	561.7	559.9	558.2	556.4	558.2	559.9	561.7
135°	598.9	597.8	596.6	595.0	593.0	590.8	588.8	586.7	588.8	590.8	593.0
137.5°	627.2	625.9	624.6	623.2	621.7	620.3	618.8	617.4	618.8	620.3	621.7
140°	645.7	644.2	642.9	641.6	640.6	639.5	638.5	637.5	638.5	639.5	640.6
142.5°	662.5	660.9	659.3	657.9	657.0	656.2	655.2	654.3	655.2	656.2	657.0
145°	685.5	683.3	681.1	680.1	680.2	680.4	680.4	680.6	680.4	680.4	680.2
147.5°	706.8	704.7	702.5	701.6	702.1	702.6	703.1	703.6	703.1	702.6	702.1
150°	719.6	717.5	715.5	714.9	715.8	716.7	717.6	718.5	717.6	716.7	715.8
152.5°	731.5	729.5	727.6	727.1	728.1	729.1	730.1	731.1	730.1	729.1	728.1
155°	748.0	746.5	744.9	744.8	745.9	747.1	748.3	749.4	748.3	747.1	745.9
157.5°	762.1	761.0	759.9	759.9	760.8	761.8	762.8	763.8	762.8	761.8	760.8
160°	770.6	769.8	769.1	769.1	769.8	770.6	771.4	772.2	771.4	770.6	769.8
162.5°	777.8	777.1	776.5	776.5	777.3	778.1	778.9	779.7	778.9	778.1	777.3
165°	787.2	786.8	786.4	786.5	787.3	788.1	788.9	789.7	788.9	788.1	787.3
167.5°	794.5	794.2	793.8	794.0	794.8	795.6	796.4	797.1	796.4	795.6	794.8
170°	798.5	798.3	797.9	798.3	799.0	799.8	800.5	801.4	800.5	799.8	799.0
172.5°	801.3	801.0	800.8	801.0	801.8	802.6	803.3	804.1	803.3	802.6	801.8
175°	804.3	804.0	803.8	804.1	805.0	805.9	806.8	807.7	806.8	805.9	805.0
177.5°	805.4	805.2	805.1	805.4	806.2	806.9	807.6	808.4	807.6	806.9	806.2
180°	806.0	806.0	806.0	806.0	806.0	806.0	806.0	806.0	806.0	806.0	806.0



TEST NUMBER: P331747-930

CATALOG NUMBER: SA2XXRDIP-C1005D725U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1
2.5°	1772.6	1769.1	1762.6	1752.6	1746.6	1736.1	1729.1	1733.1	1734.1	1733.1	1732.1
5°	1725.0	1711.9	1693.8	1676.3	1660.0	1642.5	1632.6	1628.2	1619.4	1614.4	1611.9
7.5°	1667.4	1644.8	1619.2	1588.7	1562.8	1535.7	1521.8	1514.9	1497.1	1487.4	1478.8
10°	1624.4	1588.8	1563.2	1523.2	1498.8	1463.2	1438.8	1439.5	1415.1	1401.3	1391.4
12.5°	1577.0	1537.8	1495.2	1459.2	1425.4	1396.8	1367.3	1355.5	1329.7	1316.4	1289.4
15°	1498.2	1452.6	1407.6	1358.9	1324.5	1280.2	1237.7	1185.9	1143.9	1107.7	1097.7
17.5°	1412.3	1355.8	1310.7	1253.4	1194.6	1120.0	1070.7	1040.6	1015.4	996.3	982.0
20°	1353.2	1295.8	1247.7	1161.5	1082.1	1031.5	995.2	972.2	945.9	925.3	914.0
22.5°	1291.3	1231.3	1165.7	1069.5	1007.6	967.0	934.7	908.2	890.4	874.3	864.1
25°	1203.3	1137.7	1029.6	963.4	913.4	870.9	848.4	832.2	813.4	791.6	781.6
27.5°	1110.4	1006.0	928.4	879.1	831.4	803.8	783.6	759.4	742.6	732.7	722.4
30°	1040.9	936.5	876.0	822.2	788.5	757.8	734.1	720.4	704.1	687.2	680.4
32.5°	963.4	880.0	822.0	777.2	743.0	716.9	698.1	675.9	664.1	653.8	639.4
35°	867.2	804.0	751.0	714.8	682.2	661.0	639.1	626.0	604.8	596.1	590.4
37.5°	785.7	731.0	691.4	653.1	627.4	603.9	590.5	569.6	560.4	548.3	536.5
40°	739.7	686.0	647.9	616.6	587.9	570.4	553.5	536.7	522.9	517.3	503.0
42.5°	692.8	649.0	610.9	576.7	557.4	538.9	517.6	505.2	491.0	481.8	473.0
45°	627.9	589.1	556.7	528.6	507.3	488.0	474.2	453.6	445.5	427.4	419.9
47.5°	571.0	534.9	503.9	477.2	456.5	443.8	423.7	407.6	394.6	383.5	373.9
50°	530.4	500.4	470.4	446.7	428.0	409.9	389.2	381.1	361.1	355.5	349.8
52.5°	493.4	465.0	437.5	414.3	395.5	377.9	359.7	349.1	335.7	330.0	325.9
55°	441.7	414.3	388.0	367.4	348.6	330.5	319.3	306.1	299.9	295.5	290.5
57.5°	389.7	365.0	344.9	324.0	305.2	290.7	277.8	269.9	263.4	257.6	251.7
60°	356.8	333.0	314.9	295.5	276.1	264.2	254.3	244.9	237.4	228.7	226.2
62.5°	321.7	301.0	284.4	265.5	248.7	237.8	228.3	219.4	210.4	197.7	194.2
65°	273.6	257.4	239.9	224.3	209.3	198.7	184.9	175.0	171.2	169.9	169.3
67.5°	230.2	214.8	199.8	183.8	170.2	160.3	153.4	151.8	149.2	148.5	146.7
70°	201.2	186.8	171.8	156.8	143.7	141.9	139.3	136.8	133.7	132.5	131.2
72.5°	175.2	160.3	145.3	133.3	127.7	125.3	122.9	120.3	118.2	117.0	116.2
75°	134.4	120.6	110.6	106.2	103.1	101.2	97.4	95.6	94.3	92.5	91.8
77.5°	96.7	88.9	84.4	81.6	78.4	76.3	74.2	72.3	71.0	70.6	69.6
80°	73.7	70.0	66.9	63.1	61.9	59.4	58.7	56.8	57.5	55.6	55.6
82.5°	57.2	52.5	49.9	48.1	46.9	44.8	44.3	43.4	43.5	42.1	42.1
85°	29.4	28.1	26.9	25.6	25.6	23.7	24.4	23.7	23.7	22.5	21.9
87.5°	10.8	10.5	9.7	9.9	10.1	9.9	9.9	9.6	9.7	9.9	9.5
90°	6.3	7.5	8.6	9.6	10.6	11.7	12.3	13.0	13.6	14.3	14.7
92.5°	11.3	11.5	12.0	12.5	13.0	13.5	13.9	14.2	14.5	14.8	15.2
95°	20.8	19.1	20.1	21.0	21.9	22.7	23.4	24.1	24.7	25.4	25.6
97.5°	27.0	22.0	24.1	26.3	28.4	30.4	31.0	31.5	32.0	32.5	32.9
100°	32.2	24.5	26.7	28.9	31.1	33.3	34.2	35.3	36.4	37.4	38.1
102.5°	119.0	107.9	89.4	71.0	52.6	34.2	35.5	36.9	38.2	39.5	40.4
105°	192.8	177.1	141.7	106.3	70.9	35.5	37.0	38.4	39.9	41.3	42.2
107.5°	239.2	219.6	177.1	134.7	92.2	49.8	48.3	46.9	45.4	44.0	43.5
110°	269.2	251.8	214.4	177.0	139.5	102.1	89.1	76.1	63.2	50.2	44.0



TEST NUMBER: P331747-930

CATALOG NUMBER: SA2XXRDIP-C1005D725U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	297.8	294.4	285.2	275.9	266.7	257.4	210.2	162.9	115.6	68.3	44.8
115°	344.1	346.9	350.1	353.4	356.6	359.9	299.9	239.9	179.9	119.8	85.1
117.5°	387.3	389.6	391.9	394.1	396.3	398.6	384.1	369.6	355.0	340.5	317.9
120°	416.0	418.2	420.5	422.8	425.2	427.5	429.0	430.6	432.2	433.7	425.7
122.5°	442.5	444.8	447.4	450.0	452.5	455.0	455.9	456.9	457.8	458.8	457.5
125°	480.9	483.0	485.4	487.9	490.3	492.8	493.7	494.6	495.5	496.4	497.1
127.5°	517.6	519.5	521.4	523.2	525.1	526.8	528.2	529.5	530.8	532.1	532.9
130°	541.4	543.1	544.5	545.9	547.4	548.8	550.2	551.6	553.1	554.5	555.1
132.5°	563.5	565.0	566.5	567.9	569.3	570.7	571.9	573.2	574.4	575.6	576.2
135°	595.0	596.6	597.8	598.9	600.1	601.3	602.6	603.9	605.2	606.5	607.0
137.5°	623.2	624.6	625.9	627.2	628.5	629.9	631.1	632.4	633.7	635.0	635.4
140°	641.6	642.9	644.2	645.7	647.1	648.6	649.7	650.9	652.0	653.2	653.5
142.5°	657.9	659.3	660.9	662.5	664.1	665.8	666.8	667.9	669.0	670.0	670.3
145°	680.1	681.1	683.3	685.5	687.7	689.9	690.9	691.8	692.7	693.6	693.7
147.5°	701.6	702.5	704.7	706.8	709.0	711.2	711.8	712.5	713.2	713.9	714.0
150°	714.9	715.5	717.5	719.6	721.7	723.7	724.6	725.3	726.1	726.8	726.9
152.5°	727.1	727.6	729.5	731.5	733.4	735.4	736.2	736.9	737.8	738.6	738.5
155°	744.8	744.9	746.5	748.0	749.6	751.1	752.0	752.8	753.5	754.3	754.2
157.5°	759.9	759.9	761.0	762.1	763.1	764.3	765.2	766.0	766.9	767.8	767.7
160°	769.1	769.1	769.8	770.6	771.4	772.2	773.0	773.7	774.5	775.3	775.2
162.5°	776.5	776.5	777.1	777.8	778.5	779.2	780.1	780.9	781.8	782.7	782.6
165°	786.5	786.4	786.8	787.2	787.5	787.9	788.8	789.7	790.7	791.6	791.6
167.5°	794.0	793.8	794.2	794.5	794.9	795.2	796.1	797.1	798.0	798.9	798.7
170°	798.3	797.9	798.3	798.5	798.7	799.0	799.9	800.8	801.7	802.7	802.5
172.5°	801.0	800.8	801.0	801.3	801.5	801.8	802.7	803.6	804.5	805.4	805.3
175°	804.1	803.8	804.0	804.3	804.5	804.9	805.8	806.7	807.6	808.5	808.3
177.5°	805.4	805.1	805.2	805.4	805.4	805.5	806.2	807.0	807.7	808.5	808.4
180°	806.0	806.0	806.0	806.0	806.0	806.0	806.0	806.0	806.0	806.0	806.0



TEST NUMBER: P331747-930
 CATALOG NUMBER: SA2XXRDIP-C1005D725U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1
2.5°	1726.6	1727.6	1726.2	1727.1	1726.2	1727.6	1726.6	1732.1	1733.1	1734.1	1733.1
5°	1608.7	1601.2	1600.0	1598.1	1600.0	1601.2	1608.7	1611.9	1614.4	1619.4	1628.2
7.5°	1468.1	1467.0	1463.9	1459.5	1463.9	1467.0	1468.1	1478.8	1487.4	1497.1	1514.9
10°	1377.6	1374.5	1373.9	1369.5	1373.9	1374.5	1377.6	1391.4	1401.3	1415.1	1439.5
12.5°	1271.6	1251.6	1249.4	1238.5	1249.4	1251.6	1271.6	1289.4	1316.4	1329.7	1355.5
15°	1082.7	1079.0	1066.5	1058.3	1066.5	1079.0	1082.7	1097.7	1107.7	1143.9	1185.9
17.5°	974.8	962.5	958.6	956.9	958.6	962.5	974.8	982.0	996.3	1015.4	1040.6
20°	905.3	894.1	892.2	891.0	892.2	894.1	905.3	914.0	925.3	945.9	972.2
22.5°	857.3	845.5	840.7	836.9	840.7	845.5	857.3	864.1	874.3	890.4	908.2
25°	775.3	770.9	768.5	767.2	768.5	770.9	775.3	781.6	791.6	813.4	832.2
27.5°	711.3	701.6	699.8	696.5	699.8	701.6	711.3	722.4	732.7	742.6	759.4
30°	674.7	671.6	667.2	663.5	667.2	671.6	674.7	680.4	687.2	704.1	720.4
32.5°	631.8	629.2	625.3	623.5	625.3	629.2	631.8	639.4	653.8	664.1	675.9
35°	584.2	575.4	571.7	566.1	571.7	575.4	584.2	590.4	596.1	604.8	626.0
37.5°	533.8	529.2	523.9	525.8	523.9	529.2	533.8	536.5	548.3	560.4	569.6
40°	494.8	491.7	490.5	489.8	490.5	491.7	494.8	503.0	517.3	522.9	536.7
42.5°	463.8	455.2	451.9	451.8	451.9	455.2	463.8	473.0	481.8	491.0	505.2
45°	416.7	408.6	403.0	403.6	403.0	408.6	416.7	419.9	427.4	445.5	453.6
47.5°	368.5	368.3	364.8	365.8	364.8	368.3	368.5	373.9	383.5	394.6	407.6
50°	345.5	341.8	339.2	339.9	339.2	341.8	345.5	349.8	355.5	361.1	381.1
52.5°	323.5	320.2	318.3	320.9	318.3	320.2	323.5	325.9	330.0	335.7	349.1
55°	287.4	283.6	283.0	282.4	283.0	283.6	287.4	290.5	295.5	299.9	306.1
57.5°	247.0	244.5	240.8	239.1	240.8	244.5	247.0	251.7	257.6	263.4	269.9
60°	218.0	213.0	206.8	206.2	206.8	213.0	218.0	226.2	228.7	237.4	244.9
62.5°	191.5	190.5	189.3	189.1	189.3	190.5	191.5	194.2	197.7	210.4	219.4
65°	168.0	167.5	168.0	168.7	168.0	167.5	168.0	169.3	169.9	171.2	175.0
67.5°	146.4	145.3	144.2	144.7	144.2	145.3	146.4	146.7	148.5	149.2	151.8
70°	130.0	129.3	128.7	128.7	128.7	129.3	130.0	131.2	132.5	133.7	136.8
72.5°	114.0	113.8	113.2	112.7	113.2	113.8	114.0	116.2	117.0	118.2	120.3
75°	91.2	89.9	89.9	89.9	89.9	89.9	91.2	91.8	92.5	94.3	95.6
77.5°	69.5	68.8	68.2	67.8	68.2	68.8	69.5	69.6	70.6	71.0	72.3
80°	55.0	54.4	53.7	53.7	53.7	54.4	55.0	55.6	55.6	57.5	56.8
82.5°	42.0	41.3	41.3	40.8	41.3	41.3	42.0	42.1	42.1	43.5	43.4
85°	22.5	23.2	22.5	23.7	22.5	23.2	22.5	21.9	22.5	23.7	23.7
87.5°	9.5	9.0	9.6	9.1	9.6	9.0	9.5	9.5	9.9	9.7	9.6
90°	15.0	15.2	15.5	15.7	15.5	15.2	15.0	14.7	14.3	13.6	13.0
92.5°	15.2	15.4	15.6	15.7	15.6	15.4	15.2	15.2	14.8	14.5	14.2
95°	25.4	25.4	25.2	25.1	25.2	25.4	25.4	25.6	25.4	24.7	24.1
97.5°	33.0	33.2	33.3	33.5	33.3	33.2	33.0	32.9	32.5	32.0	31.5
100°	38.3	38.6	38.8	39.1	38.8	38.6	38.3	38.1	37.4	36.4	35.3
102.5°	40.8	41.2	41.5	41.9	41.5	41.2	40.8	40.4	39.5	38.2	36.9
105°	42.8	43.3	43.8	44.4	43.8	43.3	42.8	42.2	41.3	39.9	38.4
107.5°	44.0	44.6	45.1	45.6	45.1	44.6	44.0	43.5	44.0	45.4	46.9
110°	44.5	45.0	45.6	46.1	45.6	45.0	44.5	44.0	50.2	63.2	76.1



TEST NUMBER: P331747-930

CATALOG NUMBER: SA2XXRDIP-C1005D725U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	45.3	45.7	46.1	46.6	46.1	45.7	45.3	44.8	68.3	115.6	162.9
115°	75.8	66.4	57.2	47.9	57.2	66.4	75.8	85.1	119.8	179.9	239.9
117.5°	287.2	256.6	225.9	195.3	225.9	256.6	287.2	317.9	340.5	355.0	369.6
120°	408.2	390.8	373.2	355.8	373.2	390.8	408.2	425.7	433.7	432.2	430.6
122.5°	454.1	450.7	447.4	443.9	447.4	450.7	454.1	457.5	458.8	457.8	456.9
125°	497.5	497.9	498.2	498.6	498.2	497.9	497.5	497.1	496.4	495.5	494.6
127.5°	533.0	533.0	533.1	533.2	533.1	533.0	533.0	532.9	532.1	530.8	529.5
130°	555.1	554.9	554.7	554.6	554.7	554.9	555.1	555.1	554.5	553.1	551.6
132.5°	576.0	575.9	575.8	575.6	575.8	575.9	576.0	576.2	575.6	574.4	573.2
135°	606.7	606.5	606.2	605.9	606.2	606.5	606.7	607.0	606.5	605.2	603.9
137.5°	635.0	634.5	634.1	633.6	634.1	634.5	635.0	635.4	635.0	633.7	632.4
140°	652.8	652.2	651.5	650.9	651.5	652.2	652.8	653.5	653.2	652.0	650.9
142.5°	669.6	669.0	668.3	667.6	668.3	669.0	669.6	670.3	670.0	669.0	667.9
145°	693.1	692.4	691.8	691.1	691.8	692.4	693.1	693.7	693.6	692.7	691.8
147.5°	713.4	712.8	712.3	711.8	712.3	712.8	713.4	714.0	713.9	713.2	712.5
150°	726.3	725.6	725.0	724.3	725.0	725.6	726.3	726.9	726.8	726.1	725.3
152.5°	737.7	736.8	736.0	735.1	736.0	736.8	737.7	738.5	738.6	737.8	736.9
155°	753.1	752.1	751.1	750.0	751.1	752.1	753.1	754.2	754.3	753.5	752.8
157.5°	766.7	765.6	764.7	763.7	764.7	765.6	766.7	767.7	767.8	766.9	766.0
160°	774.3	773.4	772.5	771.6	772.5	773.4	774.3	775.2	775.3	774.5	773.7
162.5°	781.5	780.3	779.3	778.1	779.3	780.3	781.5	782.6	782.7	781.8	780.9
165°	790.7	789.7	788.8	787.9	788.8	789.7	790.7	791.6	791.6	790.7	789.7
167.5°	797.6	796.5	795.2	794.1	795.2	796.5	797.6	798.7	798.9	798.0	797.1
170°	801.4	800.1	799.0	797.9	799.0	800.1	801.4	802.5	802.7	801.7	800.8
172.5°	804.1	803.0	801.8	800.6	801.8	803.0	804.1	805.3	805.4	804.5	803.6
175°	807.0	805.7	804.4	803.1	804.4	805.7	807.0	808.3	808.5	807.6	806.7
177.5°	807.4	806.5	805.5	804.6	805.5	806.5	807.4	808.4	808.5	807.7	807.0
180°	806.0	806.0	806.0	806.0	806.0	806.0	806.0	806.0	806.0	806.0	806.0



TEST NUMBER: P331747-930

CATALOG NUMBER: SA2XXRDIP-C1005D725U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1
2.5°	1729.1	1736.1	1746.6	1752.6	1762.6	1769.1	1772.6	1779.1	1782.6	1795.1	1808.1
5°	1632.6	1642.5	1660.0	1676.3	1693.8	1711.9	1725.0	1740.0	1753.7	1777.4	1802.5
7.5°	1521.8	1535.7	1562.8	1588.7	1619.2	1644.8	1667.4	1693.0	1715.9	1749.9	1785.3
10°	1438.8	1463.2	1498.8	1523.2	1563.2	1588.8	1624.4	1652.5	1684.4	1729.3	1769.4
12.5°	1367.3	1396.8	1425.4	1459.2	1495.2	1537.8	1577.0	1613.1	1650.9	1697.4	1744.3
15°	1237.7	1280.2	1324.5	1358.9	1407.6	1452.6	1498.2	1546.9	1593.2	1648.8	1710.0
17.5°	1070.7	1120.0	1194.6	1253.4	1310.7	1355.8	1412.3	1471.2	1525.7	1592.8	1660.9
20°	995.2	1031.5	1082.1	1161.5	1247.7	1295.8	1353.2	1418.2	1480.7	1553.8	1626.9
22.5°	934.7	967.0	1007.6	1069.5	1165.7	1231.3	1291.3	1357.2	1429.7	1504.3	1585.4
25°	848.4	870.9	913.4	963.4	1029.6	1137.7	1203.3	1269.5	1348.3	1428.2	1520.7
27.5°	783.6	803.8	831.4	879.1	928.4	1006.0	1110.4	1182.6	1261.0	1351.0	1447.0
30°	734.1	757.8	788.5	822.2	876.0	936.5	1040.9	1124.6	1202.1	1294.5	1397.0
32.5°	698.1	716.9	743.0	777.2	822.0	880.0	963.4	1065.1	1140.6	1238.0	1345.0
35°	639.1	661.0	682.2	714.8	751.0	804.0	867.2	975.9	1050.8	1147.0	1254.5
37.5°	590.5	603.9	627.4	653.1	691.4	731.0	785.7	883.2	964.3	1058.7	1168.7
40°	553.5	570.4	587.9	616.6	647.9	686.0	739.7	812.2	905.3	997.8	1105.2
42.5°	517.6	538.9	557.4	576.7	610.9	649.0	692.8	754.2	849.3	936.8	1041.2
45°	474.2	488.0	507.3	528.6	556.7	589.1	627.9	681.6	772.8	848.4	946.6
47.5°	423.7	443.8	456.5	477.2	503.9	534.9	571.0	617.4	691.2	762.1	853.0
50°	389.2	409.9	428.0	446.7	470.4	500.4	530.4	575.4	634.8	709.1	794.1
52.5°	359.7	377.9	395.5	414.3	437.5	465.0	493.4	533.0	583.8	652.2	734.6
55°	319.3	330.5	348.6	367.4	388.0	414.3	441.7	474.8	518.5	576.0	642.9
57.5°	277.8	290.7	305.2	324.0	344.9	365.0	389.7	419.7	454.2	506.2	563.5
60°	254.3	264.2	276.1	295.5	314.9	333.0	356.8	381.7	414.3	459.2	507.9
62.5°	228.3	237.8	248.7	265.5	284.4	301.0	321.7	348.2	375.8	416.7	459.4
65°	184.9	198.7	209.3	224.3	239.9	257.4	273.6	294.9	319.3	351.7	389.9
67.5°	153.4	160.3	170.2	183.8	199.8	214.8	230.2	246.8	267.9	293.0	323.3
70°	139.3	141.9	143.7	156.8	171.8	186.8	201.2	216.8	234.9	255.5	281.8
72.5°	122.9	125.3	127.7	133.3	145.3	160.3	175.2	186.8	203.9	221.0	242.3
75°	97.4	101.2	103.1	106.2	110.6	120.6	134.4	145.5	155.6	168.7	185.6
77.5°	74.2	76.3	78.4	81.6	84.4	88.9	96.7	106.8	116.2	123.8	135.4
80°	58.7	59.4	61.9	63.1	66.9	70.0	73.7	81.9	91.2	94.3	102.5
82.5°	44.3	44.8	46.9	48.1	49.9	52.5	57.2	59.4	66.7	70.8	76.0
85°	24.4	23.7	25.6	25.6	26.9	28.1	29.4	32.4	34.3	39.4	40.6
87.5°	9.9	9.9	10.1	9.9	9.7	10.5	10.8	11.0	11.7	12.9	14.6
90°	12.3	11.7	10.6	9.6	8.6	7.5	6.3	4.9	3.4	2.0	0.6
92.5°	13.9	13.5	13.0	12.5	12.0	11.5	11.3	11.4	11.5	11.7	11.7
95°	23.4	22.7	21.9	21.0	20.1	19.1	20.8	25.1	29.4	33.7	37.9
97.5°	31.0	30.4	28.4	26.3	24.1	22.0	27.0	39.1	51.1	63.2	75.3
100°	34.2	33.3	31.1	28.9	26.7	24.5	32.2	50.0	67.8	85.4	103.2
102.5°	35.5	34.2	52.6	71.0	89.4	107.9	119.0	122.8	126.5	130.3	134.0
105°	37.0	35.5	70.9	106.3	141.7	177.1	192.8	189.0	185.1	181.2	177.3
107.5°	48.3	49.8	92.2	134.7	177.1	219.6	239.2	236.0	232.9	229.8	226.7
110°	89.1	102.1	139.5	177.0	214.4	251.8	269.2	266.5	263.8	261.1	258.4



TEST NUMBER: P331747-930

CATALOG NUMBER: SA2XXRDIP-C1005D725U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	210.2	257.4	266.7	275.9	285.2	294.4	297.8	295.5	293.0	290.7	288.2
115°	299.9	359.9	356.6	353.4	350.1	346.9	344.1	341.9	339.7	337.5	335.3
117.5°	384.1	398.6	396.3	394.1	391.9	389.6	387.3	384.8	382.4	379.9	377.5
120°	429.0	427.5	425.2	422.8	420.5	418.2	416.0	414.1	412.1	410.2	408.2
122.5°	455.9	455.0	452.5	450.0	447.4	444.8	442.5	440.5	438.5	436.4	434.4
125°	493.7	492.8	490.3	487.9	485.4	483.0	480.9	479.2	477.5	475.8	474.2
127.5°	528.2	526.8	525.1	523.2	521.4	519.5	517.6	515.8	514.0	512.1	510.2
130°	550.2	548.8	547.4	545.9	544.5	543.1	541.4	539.2	537.2	535.2	533.0
132.5°	571.9	570.7	569.3	567.9	566.5	565.0	563.5	561.7	559.9	558.2	556.4
135°	602.6	601.3	600.1	598.9	597.8	596.6	595.0	593.0	590.8	588.8	586.7
137.5°	631.1	629.9	628.5	627.2	625.9	624.6	623.2	621.7	620.3	618.8	617.4
140°	649.7	648.6	647.1	645.7	644.2	642.9	641.6	640.6	639.5	638.5	637.5
142.5°	666.8	665.8	664.1	662.5	660.9	659.3	657.9	657.0	656.2	655.2	654.3
145°	690.9	689.9	687.7	685.5	683.3	681.1	680.1	680.2	680.4	680.4	680.6
147.5°	711.8	711.2	709.0	706.8	704.7	702.5	701.6	702.1	702.6	703.1	703.6
150°	724.6	723.7	721.7	719.6	717.5	715.5	714.9	715.8	716.7	717.6	718.5
152.5°	736.2	735.4	733.4	731.5	729.5	727.6	727.1	728.1	729.1	730.1	731.1
155°	752.0	751.1	749.6	748.0	746.5	744.9	744.8	745.9	747.1	748.3	749.4
157.5°	765.2	764.3	763.1	762.1	761.0	759.9	759.9	760.8	761.8	762.8	763.8
160°	773.0	772.2	771.4	770.6	769.8	769.1	769.1	769.8	770.6	771.4	772.2
162.5°	780.1	779.2	778.5	777.8	777.1	776.5	776.5	777.3	778.1	778.9	779.7
165°	788.8	787.9	787.5	787.2	786.8	786.4	786.5	787.3	788.1	788.9	789.7
167.5°	796.1	795.2	794.9	794.5	794.2	793.8	794.0	794.8	795.6	796.4	797.1
170°	799.9	799.0	798.7	798.5	798.3	797.9	798.3	799.0	799.8	800.5	801.4
172.5°	802.7	801.8	801.5	801.3	801.0	800.8	801.0	801.8	802.6	803.3	804.1
175°	805.8	804.9	804.5	804.3	804.0	803.8	804.1	805.0	805.9	806.8	807.7
177.5°	806.2	805.5	805.4	805.4	805.2	805.1	805.4	806.2	806.9	807.6	808.4
180°	806.0	806.0	806.0	806.0	806.0	806.0	806.0	806.0	806.0	806.0	806.0



TEST NUMBER: P331747-930

CATALOG NUMBER: SA2XXRDIP-C1005D725U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1
2.5°	1808.6	1810.0	1820.1	1824.6	1833.6	1837.0	1841.1	1840.0	1840.0	1842.1	1856.0
5°	1812.5	1825.0	1843.7	1861.8	1879.3	1894.3	1904.3	1914.3	1918.1	1936.2	1952.4
7.5°	1806.0	1829.0	1859.9	1887.6	1920.7	1946.5	1968.1	1987.4	2000.7	2027.0	2054.0
10°	1797.5	1829.9	1864.9	1900.5	1946.1	1980.5	2015.5	2042.4	2051.1	2090.5	2113.0
12.5°	1780.5	1824.0	1868.4	1914.6	1959.2	2006.5	2045.0	2071.8	2102.6	2138.0	2179.5
15°	1755.0	1805.0	1863.0	1922.4	1986.2	2043.6	2084.9	2131.7	2165.4	2204.2	2240.4
17.5°	1718.4	1782.7	1856.6	1925.3	1999.0	2060.8	2117.5	2162.4	2186.2	2208.3	2213.7
20°	1689.4	1758.8	1845.6	1926.8	2000.5	2071.8	2127.9	2165.4	2171.7	2172.3	2139.2
22.5°	1657.9	1736.3	1827.1	1910.3	1998.5	2077.7	2121.5	2137.5	2112.7	2070.4	2006.3
25°	1600.0	1690.6	1796.2	1891.2	1987.4	2062.4	2077.4	2049.3	1962.4	1871.2	1755.6
27.5°	1537.3	1639.2	1752.3	1857.9	1960.4	2006.9	1974.5	1873.2	1716.8	1580.8	1416.0
30°	1491.3	1605.7	1716.9	1834.9	1929.9	1949.9	1875.6	1726.2	1543.8	1338.9	1174.6
32.5°	1438.8	1558.7	1680.9	1803.0	1882.4	1863.0	1740.1	1556.3	1342.4	1140.9	985.6
35°	1363.8	1487.6	1619.4	1741.9	1792.4	1708.1	1524.4	1285.2	1066.5	878.4	771.6
37.5°	1277.2	1412.0	1549.1	1661.5	1657.9	1517.4	1267.1	1020.1	836.3	725.1	649.0
40°	1215.8	1352.0	1500.1	1595.1	1554.4	1371.3	1100.2	867.2	732.9	644.2	588.6
42.5°	1156.8	1293.6	1440.6	1516.0	1445.4	1220.4	950.3	767.7	656.9	587.7	542.6
45°	1056.5	1200.8	1337.0	1378.8	1252.6	1004.6	768.5	636.0	562.3	511.0	479.8
47.5°	958.4	1100.3	1224.7	1225.4	1054.8	814.7	648.2	550.4	487.5	447.8	425.1
50°	898.4	1033.4	1137.7	1121.4	927.8	724.7	579.8	495.5	443.0	412.4	388.6
52.5°	831.0	961.9	1052.2	1006.0	820.4	637.7	518.3	447.4	404.0	377.3	356.1
55°	732.9	849.1	912.8	842.8	669.1	530.4	438.0	382.4	349.8	327.3	309.2
57.5°	636.5	732.4	772.5	691.0	551.1	439.9	370.5	328.7	296.5	280.4	271.0
60°	576.0	657.9	686.0	596.1	479.2	384.8	328.0	289.3	265.5	254.9	245.6
62.5°	516.6	583.4	595.0	512.6	417.8	336.9	288.0	255.3	239.5	229.4	220.5
65°	428.6	476.7	471.1	404.9	330.5	267.4	231.8	211.8	199.9	185.6	169.9
67.5°	352.9	382.2	364.5	314.9	252.3	207.8	184.6	169.4	154.7	141.0	137.5
70°	304.9	321.7	303.0	257.4	206.8	174.3	155.6	137.5	128.7	125.6	119.9
72.5°	258.9	264.8	244.5	205.5	168.3	144.3	126.0	115.9	111.2	108.6	104.9
75°	194.3	190.0	172.4	141.9	116.8	100.6	95.0	91.2	88.1	85.6	83.7
77.5°	136.5	130.0	114.5	94.5	81.4	73.6	70.2	68.2	66.7	65.5	63.6
80°	102.5	98.1	82.5	67.5	61.9	58.1	56.3	53.7	53.7	52.5	50.6
82.5°	75.0	70.1	56.5	49.5	46.4	44.1	42.7	41.3	40.8	41.0	39.6
85°	39.4	31.9	28.1	26.9	25.0	23.7	24.4	23.2	23.2	23.2	22.5
87.5°	12.4	10.2	9.9	9.8	10.5	10.7	10.4	10.6	11.3	10.9	11.6
90°	2.0	3.4	4.9	6.3	7.5	8.6	9.6	10.6	11.7	12.3	13.0
92.5°	11.7	11.5	11.4	11.3	11.5	12.0	12.5	13.0	13.5	13.9	14.2
95°	33.7	29.4	25.1	20.8	19.1	20.1	21.0	21.9	22.7	23.4	24.1
97.5°	63.2	51.1	39.1	27.0	22.0	24.1	26.3	28.4	30.4	31.0	31.5
100°	85.4	67.8	50.0	32.2	24.5	26.7	28.9	31.1	33.3	34.2	35.3
102.5°	130.3	126.5	122.8	119.0	107.9	89.4	71.0	52.6	34.2	35.5	36.9
105°	181.2	185.1	189.0	192.8	177.1	141.7	106.3	70.9	35.5	37.0	38.4
107.5°	229.8	232.9	236.0	239.2	219.6	177.1	134.7	92.2	49.8	48.3	46.9
110°	261.1	263.8	266.5	269.2	251.8	214.4	177.0	139.5	102.1	89.1	76.1



TEST NUMBER: P331747-930

CATALOG NUMBER: SA2XXRDIP-C1005D725U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	290.7	293.0	295.5	297.8	294.4	285.2	275.9	266.7	257.4	210.2	162.9
115°	337.5	339.7	341.9	344.1	346.9	350.1	353.4	356.6	359.9	299.9	239.9
117.5°	379.9	382.4	384.8	387.3	389.6	391.9	394.1	396.3	398.6	384.1	369.6
120°	410.2	412.1	414.1	416.0	418.2	420.5	422.8	425.2	427.5	429.0	430.6
122.5°	436.4	438.5	440.5	442.5	444.8	447.4	450.0	452.5	455.0	455.9	456.9
125°	475.8	477.5	479.2	480.9	483.0	485.4	487.9	490.3	492.8	493.7	494.6
127.5°	512.1	514.0	515.8	517.6	519.5	521.4	523.2	525.1	526.8	528.2	529.5
130°	535.2	537.2	539.2	541.4	543.1	544.5	545.9	547.4	548.8	550.2	551.6
132.5°	558.2	559.9	561.7	563.5	565.0	566.5	567.9	569.3	570.7	571.9	573.2
135°	588.8	590.8	593.0	595.0	596.6	597.8	598.9	600.1	601.3	602.6	603.9
137.5°	618.8	620.3	621.7	623.2	624.6	625.9	627.2	628.5	629.9	631.1	632.4
140°	638.5	639.5	640.6	641.6	642.9	644.2	645.7	647.1	648.6	649.7	650.9
142.5°	655.2	656.2	657.0	657.9	659.3	660.9	662.5	664.1	665.8	666.8	667.9
145°	680.4	680.4	680.2	680.1	681.1	683.3	685.5	687.7	689.9	690.9	691.8
147.5°	703.1	702.6	702.1	701.6	702.5	704.7	706.8	709.0	711.2	711.8	712.5
150°	717.6	716.7	715.8	714.9	715.5	717.5	719.6	721.7	723.7	724.6	725.3
152.5°	730.1	729.1	728.1	727.1	727.6	729.5	731.5	733.4	735.4	736.2	736.9
155°	748.3	747.1	745.9	744.8	744.9	746.5	748.0	749.6	751.1	752.0	752.8
157.5°	762.8	761.8	760.8	759.9	759.9	761.0	762.1	763.1	764.3	765.2	766.0
160°	771.4	770.6	769.8	769.1	769.1	769.8	770.6	771.4	772.2	773.0	773.7
162.5°	778.9	778.1	777.3	776.5	776.5	777.1	777.8	778.5	779.2	780.1	780.9
165°	788.9	788.1	787.3	786.5	786.4	786.8	787.2	787.5	787.9	788.8	789.7
167.5°	796.4	795.6	794.8	794.0	793.8	794.2	794.5	794.9	795.2	796.1	797.1
170°	800.5	799.8	799.0	798.3	797.9	798.3	798.5	798.7	799.0	799.9	800.8
172.5°	803.3	802.6	801.8	801.0	800.8	801.0	801.3	801.5	801.8	802.7	803.6
175°	806.8	805.9	805.0	804.1	803.8	804.0	804.3	804.5	804.9	805.8	806.7
177.5°	807.6	806.9	806.2	805.4	805.1	805.2	805.4	805.4	805.5	806.2	807.0
180°	806.0	806.0	806.0	806.0	806.0	806.0	806.0	806.0	806.0	806.0	806.0



TEST NUMBER: P331747-930

CATALOG NUMBER: SA2XXRDIP-C1005D725U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1
2.5°	1861.1	1867.5	1870.5	1870.5	1874.0	1872.6	1871.0
5°	1968.1	1979.9	1982.4	1993.7	2001.7	1999.3	2000.5
7.5°	2074.4	2093.4	2112.4	2121.0	2122.3	2127.4	2129.2
10°	2139.8	2155.5	2184.8	2180.4	2202.3	2214.8	2194.2
12.5°	2202.8	2223.9	2244.3	2249.9	2262.3	2266.3	2258.1
15°	2259.8	2271.0	2272.3	2269.1	2272.9	2269.8	2257.9
17.5°	2206.5	2188.3	2151.3	2133.8	2119.9	2099.5	2091.2
20°	2118.6	2064.8	2002.4	1977.4	1948.0	1890.5	1904.3
22.5°	1928.7	1867.4	1805.0	1732.0	1697.1	1642.7	1639.4
25°	1633.1	1527.5	1411.4	1330.2	1282.6	1228.3	1204.5
27.5°	1269.7	1136.9	1041.6	993.4	949.5	906.4	904.7
30°	1030.9	930.9	857.2	816.0	789.0	770.9	774.7
32.5°	868.9	800.5	750.7	716.5	696.6	683.0	682.7
35°	710.4	663.5	631.6	617.3	602.9	592.9	593.5
37.5°	607.9	579.8	562.1	546.2	537.2	532.3	529.5
40°	555.4	532.3	518.5	509.2	501.7	494.8	493.6
42.5°	514.0	494.8	481.1	473.7	466.7	461.9	460.6
45°	456.1	440.4	428.0	419.9	416.7	412.4	412.4
47.5°	405.7	390.4	380.6	375.5	370.1	367.2	367.1
50°	371.8	359.9	351.1	348.0	343.6	341.8	341.1
52.5°	341.3	332.4	326.1	324.0	322.1	319.8	320.2
55°	299.9	294.9	292.4	290.5	287.4	283.6	286.2
57.5°	265.1	260.8	254.0	248.2	245.3	242.6	243.7
60°	240.5	231.8	223.1	216.1	214.3	208.6	208.6
62.5°	209.5	197.3	186.5	182.7	180.8	178.2	177.7
65°	161.2	156.2	153.7	151.2	149.9	149.9	148.7
67.5°	133.5	131.6	128.8	128.2	126.9	126.6	126.2
70°	118.1	115.6	114.3	113.7	112.4	113.1	111.2
72.5°	103.1	101.1	100.9	99.2	98.5	98.6	97.2
75°	81.2	81.2	80.6	80.0	78.8	78.1	78.8
77.5°	62.5	62.6	61.5	61.4	61.2	61.4	60.7
80°	50.0	50.6	50.0	49.3	48.8	49.3	48.8
82.5°	39.5	38.6	38.5	38.4	38.2	37.8	37.7
85°	22.5	23.2	22.5	21.9	21.9	21.9	22.5
87.5°	11.3	11.3	11.4	11.5	11.6	11.6	11.2
90°	13.6	14.3	14.7	15.0	15.2	15.5	15.7
92.5°	14.5	14.8	15.2	15.2	15.4	15.6	15.7
95°	24.7	25.4	25.6	25.4	25.4	25.2	25.1
97.5°	32.0	32.5	32.9	33.0	33.2	33.3	33.5
100°	36.4	37.4	38.1	38.3	38.6	38.8	39.1
102.5°	38.2	39.5	40.4	40.8	41.2	41.5	41.9
105°	39.9	41.3	42.2	42.8	43.3	43.8	44.4
107.5°	45.4	44.0	43.5	44.0	44.6	45.1	45.6
110°	63.2	50.2	44.0	44.5	45.0	45.6	46.1



TEST NUMBER: P331747-930

CATALOG NUMBER: SA2XXRDIP-C1005D725U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	115.6	68.3	44.8	45.3	45.7	46.1	46.6
115°	179.9	119.8	85.1	75.8	66.4	57.2	47.9
117.5°	355.0	340.5	317.9	287.2	256.6	225.9	195.3
120°	432.2	433.7	425.7	408.2	390.8	373.2	355.8
122.5°	457.8	458.8	457.5	454.1	450.7	447.4	443.9
125°	495.5	496.4	497.1	497.5	497.9	498.2	498.6
127.5°	530.8	532.1	532.9	533.0	533.0	533.1	533.2
130°	553.1	554.5	555.1	555.1	554.9	554.7	554.6
132.5°	574.4	575.6	576.2	576.0	575.9	575.8	575.6
135°	605.2	606.5	607.0	606.7	606.5	606.2	605.9
137.5°	633.7	635.0	635.4	635.0	634.5	634.1	633.6
140°	652.0	653.2	653.5	652.8	652.2	651.5	650.9
142.5°	669.0	670.0	670.3	669.6	669.0	668.3	667.6
145°	692.7	693.6	693.7	693.1	692.4	691.8	691.1
147.5°	713.2	713.9	714.0	713.4	712.8	712.3	711.8
150°	726.1	726.8	726.9	726.3	725.6	725.0	724.3
152.5°	737.8	738.6	738.5	737.7	736.8	736.0	735.1
155°	753.5	754.3	754.2	753.1	752.1	751.1	750.0
157.5°	766.9	767.8	767.7	766.7	765.6	764.7	763.7
160°	774.5	775.3	775.2	774.3	773.4	772.5	771.6
162.5°	781.8	782.7	782.6	781.5	780.3	779.3	778.1
165°	790.7	791.6	791.6	790.7	789.7	788.8	787.9
167.5°	798.0	798.9	798.7	797.6	796.5	795.2	794.1
170°	801.7	802.7	802.5	801.4	800.1	799.0	797.9
172.5°	804.5	805.4	805.3	804.1	803.0	801.8	800.6
175°	807.6	808.5	808.3	807.0	805.7	804.4	803.1
177.5°	807.7	808.5	808.4	807.4	806.5	805.5	804.6
180°	806.0	806.0	806.0	806.0	806.0	806.0	806.0

(END OF REPORT)