

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331751-930

Luminaire Tested: **SA2XXRDIP-C1005D725U930-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331751-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C1005D725U930-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 725 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4954.3 lumens
Efficiency: N/A
Efficacy: 81.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 60.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331751-930
CATALOG NUMBER: SA2XXRDIP-C1005D725U930-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331751-930

CATALOG NUMBER: SA2XXRDIP-C1005D725U930-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	87	87	87	75	75	75	63	63	63	57
1	100	96	92	89	93	89	86	83	77	75	73	67	65	63	56	55	54	49
2	91	84	78	73	85	79	74	69	69	65	61	59	56	54	50	48	46	42
3	84	75	67	62	78	70	64	59	61	56	52	53	49	46	45	42	40	36
4	77	66	59	53	72	62	55	50	55	49	45	47	43	40	41	38	35	32
5	71	60	52	46	66	56	49	44	49	44	39	43	38	35	37	34	31	28
6	66	54	46	40	61	51	43	38	45	39	35	39	34	31	34	30	28	25
7	61	49	41	35	57	46	39	34	41	35	31	36	31	28	31	27	25	22
8	57	44	37	31	53	42	35	30	37	32	28	33	28	25	29	25	22	20
9	53	41	33	28	49	38	32	27	34	29	25	30	26	23	26	23	20	18
10	49	37	30	26	46	35	29	25	32	26	23	28	24	21	25	21	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	22291	22291	22291
5°	22376	22013	22135
10°	22207	21653	21469
15°	21951	21010	20404
20°	21596	20094	19086
25°	21235	19053	17808
30°	20734	17984	16168
35°	20243	16821	14728
40°	19751	15616	13061
45°	19173	14266	11556
50°	18580	12901	10073
55°	17973	11431	8653
60°	17270	9884	7182
65°	16466	8306	6541
70°	15512	6845	6014
75°	14342	6238	5608
80°	12664	5579	5114
85°	9948	4390	4390



TEST NUMBER: P331751-930

CATALOG NUMBER: SA2XXRDIP-C1005D725U930-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	129.2	2.6
10°-20°	354.8	7.2
20°-30°	498.3	10.1
30°-40°	543.4	11.0
40°-50°	499.6	10.1
50°-60°	392.4	7.9
60°-70°	255.8	5.2
70°-80°	131.9	2.7
80°-90°	37.2	0.8
90°-100°	47.9	1.0
100°-110°	148.6	3.0
110°-120°	254.0	5.1
120°-130°	334.1	6.7
130°-140°	375.0	7.6
140°-150°	367.7	7.4
150°-160°	308.4	6.2
160°-170°	204.5	4.1
170°-180°	71.5	1.4
0°-30°	982.4	19.8
0°-40°	1525.7	30.8
0°-60°	2417.7	48.8
0°-90°	2842.7	57.4
90°-120°	450.5	9.1
90°-150°	1527.2	30.8
90°-180°	2112.0	42.6
0°-180°	4954.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1381	1381	1381	1381	1381	
5°	1381	1374	1358	1369	1366	131
15°	1313	1298	1257	1234	1221	370
25°	1192	1150	1070	1020	1000	548
35°	1027	961	853	778	747	642
45°	840	753	625	539	506	648
55°	638	539	406	334	307	570
65°	431	329	217	177	171	427
75°	230	145	100	92	90	243
85°	54	29	24	24	24	63
90°	1	9	22	21	22	4
95°	33	39	41	41	40	38
105°	137	139	140	141	142	145
115°	255	258	258	257	255	252
125°	371	376	375	373	372	331
135°	480	487	488	487	486	371
145°	582	587	591	591	589	364
155°	666	668	670	673	671	306
165°	725	724	724	728	725	204
175°	754	752	751	755	751	72
180°	755	755	755	755	755	



TEST NUMBER: P331751-930

CATALOG NUMBER: SA2XXRDIP-C1005D725U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1380.6	1380.6	1380.6	1380.6	1380.6	1380.6	1380.6	1380.6	1380.6	1380.6	1380.6
2.5°	1385.7	1384.5	1383.4	1382.3	1381.2	1379.4	1377.0	1374.6	1372.1	1369.7	1371.9
5°	1380.6	1379.2	1377.9	1376.5	1375.1	1372.6	1369.0	1365.4	1361.8	1358.2	1360.7
7.5°	1366.4	1364.7	1363.0	1361.2	1359.5	1356.6	1352.3	1348.1	1343.9	1339.7	1340.4
10°	1354.5	1352.5	1350.5	1348.6	1346.6	1342.9	1337.3	1331.8	1326.2	1320.7	1319.9
12.5°	1339.5	1337.0	1334.6	1332.3	1329.9	1325.1	1318.0	1310.9	1303.8	1296.7	1295.2
15°	1313.2	1310.1	1307.1	1304.0	1301.0	1294.7	1285.3	1275.9	1266.4	1256.9	1251.7
17.5°	1280.9	1276.3	1271.6	1267.0	1262.3	1253.9	1241.8	1229.7	1217.6	1205.5	1199.2
20°	1256.9	1251.4	1245.9	1240.3	1234.8	1225.1	1211.1	1197.3	1183.4	1169.5	1162.5
22.5°	1230.9	1224.7	1218.5	1212.4	1206.1	1195.1	1179.5	1163.8	1148.2	1132.5	1123.6
25°	1192.0	1183.1	1174.2	1165.3	1156.4	1142.9	1124.5	1106.2	1087.9	1069.5	1058.2
27.5°	1145.0	1135.4	1125.7	1116.1	1106.4	1091.2	1070.6	1049.9	1029.2	1008.6	995.3
30°	1112.1	1101.5	1091.0	1080.4	1069.8	1053.4	1031.2	1009.0	986.8	964.6	950.4
32.5°	1080.0	1067.7	1055.4	1043.1	1030.7	1013.3	990.6	967.9	945.3	922.6	906.4
35°	1027.0	1012.9	998.7	984.6	970.5	951.1	926.7	902.3	877.8	853.4	835.9
37.5°	974.1	958.5	943.0	927.4	911.9	891.1	865.0	839.0	812.9	786.9	767.7
40°	937.1	920.5	903.8	887.1	870.5	848.6	821.7	794.8	767.8	740.9	721.2
42.5°	899.1	881.6	864.1	846.4	828.9	806.2	778.4	750.6	722.8	695.0	674.6
45°	839.7	821.0	802.4	783.8	765.2	741.4	712.2	683.1	653.9	624.8	605.0
47.5°	781.6	762.0	742.2	722.5	702.8	677.9	647.8	617.7	587.6	557.5	537.9
50°	739.7	720.0	700.3	680.5	660.8	635.7	605.2	574.6	544.0	513.6	494.4
52.5°	698.7	678.1	657.5	636.9	616.3	591.1	561.2	531.3	501.4	471.6	453.1
55°	638.5	616.9	595.2	573.5	551.9	526.0	496.0	466.0	436.1	406.1	389.4
57.5°	576.7	554.6	532.3	510.1	487.9	462.4	433.6	404.7	375.9	347.1	331.8
60°	534.8	512.6	490.3	468.1	445.9	420.5	391.9	363.3	334.7	306.1	292.0
62.5°	493.8	471.6	449.4	427.1	405.0	380.2	352.9	325.6	298.4	271.2	257.6
65°	431.0	408.5	386.1	363.6	341.1	317.4	292.4	267.4	242.4	217.4	208.0
67.5°	370.6	348.3	326.0	303.6	281.3	258.9	236.4	213.9	191.4	168.9	164.6
70°	328.6	307.0	285.3	263.7	242.0	221.6	202.4	183.3	164.1	145.0	142.2
72.5°	288.6	267.8	247.1	226.3	205.5	187.4	172.1	156.7	141.3	126.0	123.6
75°	229.9	210.4	191.0	171.6	152.1	137.7	128.2	118.9	109.4	100.0	98.0
77.5°	172.2	155.2	138.1	121.1	104.0	93.2	88.6	84.1	79.5	75.0	73.9
80°	136.2	122.1	107.9	93.7	79.6	71.1	68.3	65.6	62.8	60.0	58.9
82.5°	103.2	92.1	81.1	70.0	59.0	52.5	50.6	48.8	46.9	45.0	44.4
85°	53.7	47.9	42.1	36.2	30.4	27.1	26.3	25.4	24.5	23.7	23.7
87.5°	16.1	14.7	13.2	11.8	10.4	9.9	10.6	11.3	11.8	12.5	12.1
90°	0.7	2.4	4.1	5.7	7.4	9.9	13.0	16.1	19.2	22.3	22.0
92.5°	11.3	12.6	13.9	15.1	16.3	17.3	18.0	18.8	19.6	20.3	20.3
95°	33.1	34.6	36.0	37.4	38.8	39.6	39.9	40.2	40.5	40.8	40.8
97.5°	60.6	61.8	63.0	64.2	65.6	66.4	66.9	67.5	68.0	68.6	68.6
100°	81.0	82.1	83.2	84.3	85.4	86.3	86.7	87.1	87.5	88.0	88.0
102.5°	102.3	103.2	104.2	105.1	106.0	106.7	107.2	107.8	108.3	108.8	108.9
105°	137.1	137.5	137.9	138.3	138.7	139.1	139.3	139.7	139.9	140.2	140.5
107.5°	171.9	172.6	173.2	173.8	174.4	174.7	174.7	174.7	174.7	174.7	174.9
110°	194.4	195.2	196.1	196.9	197.8	198.2	198.2	198.2	198.2	198.2	198.2



TEST NUMBER: P331751-930

CATALOG NUMBER: SA2XXRDIP-C1005D725U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	218.8	219.7	220.5	221.4	222.3	222.6	222.5	222.4	222.3	222.2	221.8
115°	254.9	255.8	256.6	257.5	258.3	258.6	258.3	258.0	257.7	257.5	257.3
117.5°	290.8	292.0	293.1	294.2	295.4	295.5	294.7	294.0	293.2	292.4	292.0
120°	314.8	315.9	317.1	318.2	319.4	319.4	318.2	317.1	315.9	314.8	314.8
122.5°	336.7	338.1	339.5	340.8	342.2	342.4	341.7	340.9	340.1	339.2	338.9
125°	370.9	372.2	373.4	374.7	376.0	376.4	376.0	375.5	375.1	374.7	374.3
127.5°	404.1	405.8	407.4	409.0	410.6	411.2	410.7	410.2	409.6	409.1	408.6
130°	425.1	426.9	428.8	430.6	432.4	433.2	432.9	432.6	432.4	432.1	431.8
132.5°	448.5	450.0	451.5	453.0	454.5	455.3	455.3	455.4	455.4	455.5	454.9
135°	479.9	481.4	483.0	484.5	486.1	487.0	487.3	487.5	487.9	488.1	488.0
137.5°	512.9	514.1	515.4	516.7	518.0	518.8	519.2	519.5	519.9	520.2	520.2
140°	532.8	534.0	535.3	536.5	537.9	538.8	539.6	540.3	541.0	541.7	541.7
142.5°	553.2	554.4	555.7	557.0	558.2	559.1	559.6	560.1	560.6	561.1	561.2
145°	582.4	583.4	584.5	585.5	586.4	587.3	588.2	589.1	589.9	590.8	590.9
147.5°	608.6	609.8	611.0	612.1	613.3	614.2	614.8	615.4	616.0	616.5	616.8
150°	626.5	627.3	628.1	629.0	629.8	630.6	631.1	631.7	632.3	632.8	633.2
152.5°	642.2	643.1	643.9	644.8	645.6	646.4	647.1	647.8	648.4	649.1	649.6
155°	665.9	666.3	666.8	667.2	667.6	668.1	668.5	669.0	669.4	669.8	670.5
157.5°	686.2	686.5	686.8	687.1	687.4	687.6	687.9	688.1	688.4	688.6	689.6
160°	698.5	698.7	699.0	699.3	699.6	699.8	699.9	700.1	700.3	700.3	701.2
162.5°	709.6	709.7	709.8	709.8	709.9	710.0	710.1	710.3	710.5	710.5	711.5
165°	724.6	724.5	724.3	724.1	724.0	723.9	723.9	723.9	723.9	723.9	725.0
167.5°	737.0	736.6	736.2	735.8	735.4	735.2	735.2	735.1	735.1	735.0	736.1
170°	743.7	743.3	742.8	742.4	742.0	741.7	741.6	741.4	741.3	741.1	742.2
172.5°	748.3	747.9	747.5	747.0	746.6	746.3	746.2	746.0	745.9	745.8	746.7
175°	753.9	753.5	753.0	752.6	752.2	751.9	751.5	751.3	751.0	750.7	751.7
177.5°	756.2	755.9	755.5	755.1	754.8	754.6	754.3	754.1	753.8	753.7	754.3
180°	755.1	755.1	755.1	755.1	755.1	755.1	755.1	755.1	755.1	755.1	755.1



TEST NUMBER: P331751-930

CATALOG NUMBER: SA2XXRDIP-C1005D725U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1380.6	1380.6	1380.6	1380.6	1380.6	1380.6	1380.6	1380.6
2.5°	1374.1	1376.3	1378.6	1379.4	1379.0	1378.6	1378.1	1377.7
5°	1363.2	1365.7	1368.2	1369.0	1368.2	1367.3	1366.5	1365.7
7.5°	1341.1	1341.8	1342.6	1342.2	1340.8	1339.3	1337.9	1336.4
10°	1319.0	1318.2	1317.4	1316.1	1314.4	1312.8	1311.1	1309.5
12.5°	1293.7	1292.2	1290.7	1288.6	1285.8	1283.0	1280.3	1277.5
15°	1246.4	1241.1	1235.8	1231.8	1229.1	1226.3	1223.5	1220.7
17.5°	1192.9	1186.7	1180.4	1174.8	1170.1	1165.3	1160.5	1155.8
20°	1155.6	1148.7	1141.7	1135.2	1129.1	1123.0	1116.9	1110.8
22.5°	1114.7	1105.7	1096.7	1090.0	1085.5	1080.9	1076.4	1071.8
25°	1046.8	1035.4	1024.0	1016.3	1012.0	1007.9	1003.7	999.6
27.5°	982.0	968.7	955.4	945.5	938.9	932.3	925.7	919.1
30°	936.3	922.1	907.9	897.2	889.7	882.2	874.7	867.2
32.5°	890.3	874.2	857.9	846.4	839.4	832.3	825.2	818.2
35°	818.4	801.0	783.4	771.6	765.5	759.4	753.3	747.2
37.5°	748.4	729.1	709.8	696.7	689.7	682.7	675.7	668.7
40°	701.5	681.8	662.1	648.7	641.4	634.1	627.0	619.7
42.5°	654.2	633.8	613.4	599.7	592.7	585.7	578.8	571.8
45°	585.3	565.6	545.8	532.7	526.0	519.3	512.7	506.1
47.5°	518.3	498.7	479.1	466.3	460.2	454.2	448.1	442.1
50°	475.2	456.1	436.9	424.4	418.6	412.7	406.9	401.0
52.5°	434.6	416.0	397.6	385.6	380.3	374.9	369.5	364.1
55°	372.8	356.1	339.4	328.5	323.2	317.9	312.7	307.4
57.5°	316.6	301.3	286.0	276.1	271.7	267.3	262.9	258.4
60°	277.8	263.7	249.5	240.2	235.7	231.3	226.8	222.4
62.5°	244.2	230.6	217.2	209.0	206.4	203.7	201.1	198.4
65°	198.5	189.1	179.6	174.5	173.7	172.8	172.0	171.2
67.5°	160.3	156.0	151.6	149.0	148.1	147.2	146.3	145.4
70°	139.4	136.6	133.9	131.9	130.8	129.6	128.6	127.4
72.5°	121.3	119.0	116.6	115.1	114.5	113.8	113.1	112.4
75°	96.0	94.2	92.2	91.1	90.8	90.5	90.3	89.9
77.5°	72.7	71.7	70.5	69.7	69.3	68.9	68.4	68.0
80°	57.7	56.7	55.5	55.0	55.0	55.0	55.0	55.0
82.5°	43.6	43.0	42.3	42.0	42.0	42.0	42.0	42.0
85°	23.7	23.7	23.7	23.7	23.7	23.7	23.7	23.7
87.5°	11.9	11.7	11.3	11.3	11.3	11.3	11.3	11.3
90°	21.8	21.4	21.2	21.1	21.3	21.4	21.5	21.7
92.5°	20.4	20.5	20.5	20.5	20.5	20.6	20.6	20.6
95°	40.8	40.8	40.8	40.7	40.4	40.1	39.8	39.5
97.5°	68.6	68.6	68.6	68.6	68.6	68.5	68.5	68.4
100°	88.0	88.0	88.0	87.9	87.7	87.6	87.5	87.3
102.5°	109.1	109.2	109.3	109.3	109.2	109.0	108.8	108.7
105°	140.8	141.0	141.4	141.5	141.5	141.5	141.5	141.5
107.5°	175.0	175.0	175.2	175.0	174.3	173.7	173.0	172.4
110°	198.2	198.2	198.2	198.0	197.5	197.1	196.7	196.2



TEST NUMBER: P331751-930

CATALOG NUMBER: SA2XXRDIP-C1005D725U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	221.4	221.1	220.8	220.5	220.1	219.8	219.6	219.2
115°	257.1	257.1	256.9	256.6	256.2	255.8	255.4	254.9
117.5°	291.7	291.4	291.0	290.7	290.2	289.8	289.3	288.9
120°	314.8	314.8	314.8	314.6	314.1	313.7	313.3	312.9
122.5°	338.6	338.3	337.9	337.6	337.3	337.0	336.6	336.4
125°	373.9	373.4	373.0	372.8	372.6	372.4	372.3	372.2
127.5°	408.1	407.6	407.1	406.6	406.2	405.7	405.3	404.8
130°	431.5	431.2	431.0	430.5	429.9	429.4	428.8	428.3
132.5°	454.3	453.6	453.1	452.5	452.0	451.6	451.1	450.7
135°	487.9	487.7	487.5	487.3	486.9	486.5	486.0	485.6
137.5°	520.1	519.9	519.8	519.5	518.9	518.4	517.8	517.2
140°	541.7	541.7	541.7	541.4	540.9	540.3	539.7	539.2
142.5°	561.3	561.4	561.5	561.3	560.7	560.1	559.6	559.1
145°	591.0	591.2	591.3	591.1	590.5	590.0	589.4	588.8
147.5°	617.1	617.4	617.8	617.7	617.1	616.5	616.0	615.5
150°	633.7	634.1	634.5	634.5	634.1	633.7	633.2	632.8
152.5°	650.2	650.8	651.3	651.3	650.8	650.2	649.6	649.1
155°	671.2	671.9	672.6	672.8	672.3	671.9	671.5	671.1
157.5°	690.6	691.5	692.5	692.6	691.9	691.3	690.6	689.9
160°	702.1	703.0	703.8	703.9	703.4	702.8	702.2	701.6
162.5°	712.5	713.5	714.4	714.5	713.9	713.2	712.5	711.8
165°	725.9	726.9	727.9	728.1	727.3	726.6	725.9	725.2
167.5°	737.0	738.0	739.0	739.2	738.4	737.7	736.9	736.2
170°	743.1	744.1	745.1	745.2	744.4	743.5	742.7	741.8
172.5°	747.7	748.7	749.7	749.7	748.9	748.0	747.2	746.4
175°	752.7	753.7	754.6	754.7	753.9	753.0	752.2	751.4
177.5°	755.0	755.7	756.4	756.4	755.7	755.0	754.3	753.7
180°	755.1	755.1	755.1	755.1	755.1	755.1	755.1	755.1

(END OF REPORT)