

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331644-930

Luminaire Tested: **SA2XXRDIP-C290D1080U930-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331644-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXRDIP-C290D1080U930-4F0-1E-UDD-F4  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1080 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4273.3 lumens  
Efficiency: N/A  
Efficacy: 101.3 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 42.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331644-930

CATALOG NUMBER: SA2XXRDIP-C290D1080U930-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P331644-930

CATALOG NUMBER: SA2XXRDIP-C290D1080U930-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	100	100	100	100	88	88	88	88	67	67	67	47	47	47	28	28	28	20
1	91	87	83	80	80	77	74	71	58	56	55	41	40	39	25	25	24	17
2	83	76	70	66	73	68	63	59	51	48	45	36	34	33	22	21	21	15
3	76	67	60	55	67	60	54	49	45	42	38	32	30	28	20	19	18	13
4	69	59	52	46	61	53	47	42	40	36	33	29	26	24	18	17	15	11
5	64	53	45	40	56	47	41	36	36	32	28	26	23	21	16	15	14	10
6	58	47	40	34	52	42	36	31	32	28	24	23	20	18	15	13	12	9
7	54	42	35	30	48	38	32	27	29	25	21	21	18	16	14	12	11	8
8	50	38	31	26	44	34	28	24	27	22	19	19	16	14	12	11	10	7
9	46	35	28	23	41	31	25	21	24	20	17	18	15	13	11	10	9	6
10	43	32	25	21	38	29	23	19	22	18	15	16	13	11	11	9	8	6

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	6608	6608	6608
5°	6634	6525	6561
10°	6583	6419	6365
15°	6506	6228	6048
20°	6402	5957	5658
25°	6296	5649	5279
30°	6145	5330	4793
35°	6000	4987	4366
40°	5855	4628	3872
45°	5683	4229	3425
50°	5506	3823	2987
55°	5326	3386	2567
60°	5118	2929	2131
65°	4883	2460	1937
70°	4598	2030	1780
75°	4255	1847	1666
80°	3756	1655	1516
85°	2946	1297	1297



TEST NUMBER: P331644-930

CATALOG NUMBER: SA2XXRDIP-C290D1080U930-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	38.3	0.9
10°-20°	105.2	2.5
20°-30°	147.7	3.5
30°-40°	161.1	3.8
40°-50°	148.1	3.5
50°-60°	116.3	2.7
60°-70°	75.8	1.8
70°-80°	39.1	0.9
80°-90°	14.6	0.3
90°-100°	196.9	4.6
100°-110°	668.2	15.6
110°-120°	709.9	16.6
120°-130°	584.4	13.7
130°-140°	469.3	11.0
140°-150°	354.6	8.3
150°-160°	249.2	5.8
160°-170°	146.7	3.4
170°-180°	47.8	1.1
0°-30°	291.2	6.8
0°-40°	452.3	10.6
0°-60°	716.7	16.8
0°-90°	846.2	19.8
90°-120°	1575.1	36.9
90°-150°	2983.4	69.8
90°-180°	3427.0	80.2
0°-180°	4273.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	409	409	409	409	409	
5°	409	407	403	406	405	39
15°	389	385	373	366	362	110
25°	353	341	317	302	296	162
35°	304	285	253	230	222	190
45°	249	223	185	160	150	192
55°	189	160	120	99	91	169
65°	128	98	64	52	51	127
75°	68	43	30	27	27	72
85°	16	8	7	7	7	19
90°	1	13	32	31	31	3
95°	33	81	371	140	108	35
105°	116	174	702	1254	1067	123
115°	204	257	587	1212	1405	202
125°	284	336	564	982	1139	252
135°	333	398	558	825	944	258
145°	381	438	555	689	754	239
155°	433	467	539	609	634	199
165°	472	486	516	547	556	133
175°	492	492	496	502	501	47
180°	492	492	492	492	492	



TEST NUMBER: P331644-930

CATALOG NUMBER: SA2XXRDIP-C290D1080U930-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	409.3	409.3	409.3	409.3	409.3	409.3	409.3	409.3	409.3	409.3	409.3
2.5°	410.7	410.4	410.1	409.8	409.4	408.9	408.1	407.5	406.8	406.0	406.7
5°	409.3	408.9	408.5	408.1	407.6	406.8	405.8	404.7	403.7	402.6	403.3
7.5°	405.0	404.6	404.0	403.5	403.0	402.1	400.9	399.6	398.4	397.1	397.3
10°	401.5	400.9	400.3	399.7	399.2	398.0	396.4	394.8	393.1	391.5	391.3
12.5°	397.1	396.3	395.6	394.9	394.2	392.8	390.7	388.6	386.5	384.3	383.9
15°	389.2	388.3	387.4	386.5	385.6	383.8	381.0	378.2	375.4	372.6	371.0
17.5°	379.7	378.3	376.9	375.5	374.1	371.7	368.1	364.5	360.9	357.3	355.5
20°	372.6	371.0	369.3	367.6	366.0	363.1	359.0	354.9	350.8	346.7	344.6
22.5°	364.9	363.1	361.2	359.4	357.5	354.2	349.6	345.0	340.4	335.7	333.0
25°	353.4	350.7	348.1	345.4	342.8	338.8	333.3	327.9	322.5	317.1	313.6
27.5°	339.4	336.6	333.7	330.8	327.9	323.4	317.3	311.2	305.1	299.0	295.1
30°	329.6	326.5	323.3	320.2	317.2	312.3	305.7	299.1	292.5	285.9	281.8
32.5°	320.2	316.5	312.8	309.2	305.5	300.4	293.7	286.9	280.2	273.5	268.7
35°	304.4	300.3	296.0	291.9	287.6	281.9	274.7	267.4	260.2	253.0	247.8
37.5°	288.8	284.1	279.5	274.9	270.3	264.2	256.4	248.7	241.0	233.3	227.6
40°	277.8	272.9	267.9	262.9	258.0	251.6	243.6	235.6	227.6	219.6	213.8
42.5°	266.5	261.3	256.1	250.9	245.7	239.0	230.7	222.5	214.3	206.0	200.0
45°	248.9	243.4	237.8	232.4	226.8	219.7	211.1	202.4	193.8	185.2	179.4
47.5°	231.7	225.8	220.0	214.2	208.3	201.0	192.0	183.1	174.1	165.3	159.5
50°	219.2	213.4	207.6	201.7	195.9	188.4	179.4	170.3	161.3	152.2	146.5
52.5°	207.1	201.0	194.9	188.8	182.7	175.2	166.3	157.5	148.6	139.7	134.3
55°	189.2	182.9	176.4	170.0	163.5	156.0	147.0	138.1	129.2	120.3	115.4
57.5°	171.0	164.4	157.8	151.2	144.6	137.1	128.5	120.0	111.5	102.9	98.3
60°	158.5	152.0	145.4	138.8	132.2	124.7	116.2	107.7	99.2	90.7	86.5
62.5°	146.3	139.8	133.2	126.6	120.0	112.7	104.6	96.5	88.5	80.4	76.4
65°	127.8	121.1	114.5	107.8	101.1	94.1	86.7	79.2	71.8	64.4	61.6
67.5°	109.8	103.2	96.6	90.0	83.4	76.7	70.0	63.4	56.7	50.1	48.8
70°	97.4	91.0	84.5	78.2	71.7	65.7	60.0	54.3	48.7	43.0	42.2
72.5°	85.5	79.4	73.2	67.1	60.9	55.6	51.0	46.5	41.9	37.3	36.6
75°	68.2	62.4	56.7	50.9	45.1	40.8	38.0	35.2	32.4	29.6	29.0
77.5°	51.0	46.0	40.9	35.9	30.8	27.6	26.3	24.9	23.6	22.3	21.9
80°	40.4	36.2	32.0	27.8	23.6	21.0	20.2	19.4	18.6	17.8	17.4
82.5°	30.6	27.3	24.1	20.8	17.5	15.6	15.0	14.4	13.9	13.4	13.1
85°	15.9	14.2	12.5	10.8	9.0	8.0	7.7	7.5	7.3	7.0	7.0
87.5°	4.9	5.0	5.2	5.1	4.9	5.2	6.2	7.5	8.6	8.8	8.6
90°	1.0	3.8	7.6	9.5	11.3	14.2	18.9	25.6	31.2	32.2	31.2
92.5°	11.6	16.6	23.5	27.6	34.1	43.0	64.4	94.5	121.4	123.1	104.0
95°	33.2	36.9	46.4	55.0	70.1	92.8	136.4	218.7	328.6	371.3	324.9
97.5°	54.0	59.1	69.1	82.0	99.5	125.2	179.9	294.7	477.4	633.8	664.9
100°	72.9	75.7	84.3	99.5	118.4	144.9	195.1	310.6	515.2	748.2	884.6
102.5°	90.3	92.5	100.9	116.1	135.8	162.3	208.7	311.4	500.8	752.0	966.5
105°	115.5	119.4	126.0	140.1	161.0	187.5	232.0	316.3	472.6	701.8	953.7
107.5°	142.8	145.9	152.3	165.3	186.1	212.7	255.9	329.4	458.6	648.0	870.6
110°	161.0	164.8	170.5	182.8	202.7	230.2	271.8	340.0	455.6	622.2	818.3



TEST NUMBER: P331644-930

CATALOG NUMBER: SA2XXRDIP-C290D1080U930-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	177.7	181.5	187.9	199.4	218.6	246.8	287.0	351.4	456.3	605.6	782.0
115°	203.7	208.4	214.0	225.4	244.3	269.9	310.6	368.4	460.3	587.2	736.9
117.5°	230.6	234.3	240.0	250.1	268.2	294.7	332.4	386.6	467.1	578.3	708.4
120°	247.2	250.9	256.7	265.2	284.1	310.6	347.6	398.8	471.7	573.0	693.2
122.5°	263.1	266.1	271.8	281.1	300.0	327.3	362.0	409.4	477.0	570.0	680.4
125°	284.1	287.0	292.7	304.0	322.9	349.5	383.6	426.2	484.9	564.5	662.0
127.5°	300.8	304.6	312.6	325.1	343.2	370.5	403.7	441.9	493.1	561.3	645.0
130°	310.6	314.5	323.9	337.2	356.1	382.6	415.8	451.8	499.1	559.7	633.7
132.5°	319.8	324.3	334.5	348.5	368.3	394.8	426.4	461.6	505.2	559.0	624.5
135°	333.4	337.2	348.5	362.7	384.5	411.1	441.3	474.5	512.4	557.8	611.8
137.5°	346.3	350.8	362.2	377.3	398.9	423.5	453.5	484.4	518.9	557.7	602.9
140°	356.1	359.9	371.3	386.5	407.2	431.9	460.3	489.7	521.9	556.9	597.6
142.5°	366.0	369.0	379.6	394.8	414.8	438.0	465.6	494.2	524.2	556.9	592.3
145°	380.7	384.5	394.0	408.2	427.1	448.0	473.5	500.1	526.6	555.0	585.3
147.5°	396.6	399.5	408.5	421.7	437.4	455.9	480.0	503.3	527.3	551.6	578.1
150°	407.2	410.1	417.7	430.0	444.2	461.2	483.1	504.8	526.6	549.3	572.0
152.5°	417.8	419.2	426.7	437.6	451.0	466.5	486.1	505.6	525.1	545.5	566.7
155°	432.8	433.7	439.4	449.9	460.3	474.5	490.6	506.7	522.8	538.9	556.9
157.5°	445.3	446.3	450.9	459.9	468.2	480.2	493.8	506.7	518.4	532.1	547.6
160°	453.6	454.6	458.4	465.9	473.5	484.0	495.4	506.7	516.2	527.6	540.8
162.5°	462.0	461.5	465.2	471.2	478.1	486.2	496.1	506.0	513.9	523.7	534.8
165°	471.7	470.8	472.6	478.3	483.1	488.7	497.3	503.9	509.6	516.2	524.7
167.5°	479.6	478.5	480.2	483.8	487.2	490.8	497.0	502.6	505.2	509.6	514.9
170°	484.9	483.1	484.0	486.8	488.7	491.5	496.3	501.0	502.9	505.7	509.6
172.5°	488.0	486.8	486.2	489.1	490.2	492.3	495.5	498.7	499.9	501.2	504.3
175°	491.5	490.6	489.7	491.5	491.5	492.5	494.4	496.3	495.4	496.3	497.3
177.5°	493.3	491.7	491.0	492.5	492.5	492.5	493.3	494.8	493.3	492.5	493.3
180°	492.5	492.5	492.5	492.5	492.5	492.5	492.5	492.5	492.5	492.5	492.5



TEST NUMBER: P331644-930

CATALOG NUMBER: SA2XXRDIP-C290D1080U930-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	409.3	409.3	409.3	409.3	409.3	409.3	409.3	409.3
2.5°	407.3	408.0	408.6	408.9	408.8	408.6	408.5	408.4
5°	404.1	404.8	405.5	405.8	405.5	405.3	405.0	404.8
7.5°	397.5	397.8	397.9	397.9	397.5	397.0	396.6	396.2
10°	391.0	390.8	390.5	390.1	389.6	389.1	388.7	388.2
12.5°	383.5	383.0	382.6	382.0	381.2	380.3	379.5	378.7
15°	369.5	367.9	366.3	365.2	364.4	363.5	362.6	361.8
17.5°	353.6	351.7	349.9	348.3	346.8	345.4	344.0	342.6
20°	342.6	340.5	338.4	336.5	334.7	332.9	331.1	329.3
22.5°	330.4	327.8	325.1	323.1	321.7	320.4	319.0	317.7
25°	310.3	306.9	303.5	301.3	300.0	298.7	297.5	296.3
27.5°	291.1	287.1	283.2	280.3	278.3	276.4	274.4	272.5
30°	277.5	273.4	269.1	266.0	263.7	261.5	259.3	257.1
32.5°	263.9	259.1	254.3	250.9	248.8	246.7	244.6	242.6
35°	242.6	237.4	232.2	228.7	226.9	225.1	223.3	221.5
37.5°	221.8	216.1	210.4	206.5	204.5	202.4	200.3	198.2
40°	208.0	202.1	196.2	192.2	190.1	188.0	185.8	183.7
42.5°	193.9	187.8	181.8	177.8	175.7	173.7	171.5	169.5
45°	173.5	167.6	161.8	157.9	156.0	153.9	152.0	150.0
47.5°	153.6	147.8	142.0	138.2	136.4	134.6	132.8	131.0
50°	140.9	135.2	129.5	125.8	124.1	122.4	120.6	118.9
52.5°	128.8	123.4	117.9	114.3	112.8	111.1	109.5	107.9
55°	110.5	105.6	100.6	97.3	95.8	94.2	92.7	91.2
57.5°	93.8	89.3	84.8	81.9	80.6	79.2	77.9	76.6
60°	82.3	78.2	73.9	71.2	69.9	68.6	67.3	66.0
62.5°	72.4	68.4	64.4	62.0	61.1	60.4	59.6	58.8
65°	58.9	56.0	53.2	51.7	51.4	51.2	51.0	50.7
67.5°	47.5	46.2	44.9	44.2	43.9	43.6	43.4	43.1
70°	41.3	40.5	39.7	39.1	38.7	38.4	38.1	37.7
72.5°	36.0	35.2	34.6	34.2	33.9	33.8	33.5	33.3
75°	28.5	27.9	27.3	27.0	26.9	26.8	26.7	26.7
77.5°	21.5	21.2	20.9	20.7	20.5	20.4	20.3	20.1
80°	17.1	16.8	16.5	16.3	16.3	16.3	16.3	16.3
82.5°	13.0	12.7	12.6	12.5	12.5	12.5	12.5	12.5
85°	7.0	7.0	7.0	7.0	7.0	7.0	7.0	7.0
87.5°	8.3	7.8	8.2	8.3	8.3	8.3	8.3	8.3
90°	30.3	28.5	30.3	31.2	31.2	31.2	31.2	31.2
92.5°	82.6	70.8	62.9	57.0	56.3	53.2	54.0	52.5
95°	248.2	190.4	150.6	129.7	117.4	109.9	107.0	107.9
97.5°	579.0	473.8	371.3	302.9	257.6	234.3	220.5	212.5
100°	864.7	747.3	617.5	502.9	424.3	383.6	356.1	339.1
102.5°	1051.9	1025.3	930.4	809.0	723.6	654.1	619.8	596.7
105°	1150.7	1257.8	1270.1	1238.8	1180.1	1121.4	1080.7	1067.4
107.5°	1079.5	1240.7	1339.2	1385.0	1392.4	1389.2	1381.0	1363.4
110°	1018.1	1187.6	1308.9	1386.6	1427.3	1445.3	1453.8	1452.9





TEST NUMBER: P331644-930

CATALOG NUMBER: SA2XXRDIP-C290D1080U930-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	962.1	1124.8	1254.3	1343.4	1400.0	1430.1	1446.3	1451.3
115°	893.2	1039.0	1163.0	1260.6	1327.9	1371.4	1396.0	1404.6
117.5°	841.2	969.3	1081.8	1173.3	1241.9	1287.8	1313.9	1321.0
120°	815.5	932.9	1033.3	1119.5	1185.8	1230.3	1257.8	1267.2
122.5°	795.0	902.6	997.7	1075.5	1135.0	1178.8	1203.2	1211.1
125°	765.2	862.8	946.2	1017.2	1072.1	1108.2	1131.8	1139.4
127.5°	735.9	824.2	902.8	968.3	1016.3	1049.9	1070.4	1076.5
130°	717.0	798.4	873.3	935.7	982.2	1014.4	1033.3	1040.9
132.5°	698.8	774.2	842.9	901.6	947.3	979.5	996.9	1003.7
135°	673.4	735.9	798.4	851.4	892.2	923.4	940.4	944.3
137.5°	653.1	705.4	755.0	801.3	838.4	865.3	880.3	885.9
140°	640.3	685.7	729.3	770.9	801.3	825.9	840.1	845.8
142.5°	629.7	668.3	705.8	740.6	769.4	791.8	804.5	805.6
145°	614.7	646.0	675.3	702.8	725.5	741.6	751.1	753.9
147.5°	603.2	627.8	650.7	670.7	689.5	702.4	708.8	710.5
150°	594.8	615.6	635.5	652.6	666.8	678.2	683.8	684.8
152.5°	586.4	605.8	622.6	637.4	648.6	658.4	662.6	662.8
155°	574.9	590.0	604.2	614.7	625.1	631.7	635.5	633.7
157.5°	561.4	574.1	586.0	594.2	601.6	607.1	608.8	608.8
160°	553.1	563.5	574.0	580.6	587.2	591.9	592.9	592.9
162.5°	544.8	553.7	562.6	567.7	574.3	577.6	578.5	577.7
165°	532.3	538.9	545.5	549.3	553.1	556.9	556.9	556.0
167.5°	520.3	525.5	530.0	533.5	535.1	537.2	537.0	535.9
170°	514.3	517.1	520.9	522.8	523.7	526.6	525.6	523.7
172.5°	507.4	509.6	512.6	513.7	514.7	516.0	515.0	513.9
175°	500.1	501.0	502.0	502.9	502.9	503.9	502.9	501.0
177.5°	494.8	494.8	495.5	495.5	495.5	495.5	494.8	493.3
180°	492.5	492.5	492.5	492.5	492.5	492.5	492.5	492.5

(END OF REPORT)