

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P334363

Luminaire Tested: **S125DP-S1090D935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P334363
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1802-639-12)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DP-S1090D935-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT LED LUMINAIRE, FLUSH SATIN WHITE DIFFUSER
PENDANT/SURFACE/WALL MOUNT, 1090 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3612.2 lumens
Efficiency: N/A
Efficacy: 103.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 34.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P334363

CATALOG NUMBER: S125DP-S1090D935-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P334363

CATALOG NUMBER: S125DP-S1090D935-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	109	104	100	96	106	102	98	95	98	94	92		94	91	89		90	88	86	84
2	99	91	84	79	97	89	83	78	86	80	76		82	78	74		79	76	72	70
3	91	80	72	66	88	79	71	65	76	69	64		73	67	63		70	66	62	59
4	83	71	62	56	81	70	62	55	67	60	55		65	59	54		63	58	53	51
5	76	64	55	48	74	63	54	48	60	53	47		58	52	47		57	51	46	44
6	71	57	49	42	69	56	48	42	55	47	42		53	46	41		51	46	41	39
7	66	52	43	37	64	51	43	37	50	42	37		48	42	37		47	41	36	34
8	61	48	39	33	60	47	39	33	46	38	33		44	38	33		43	37	33	31
9	57	44	36	30	56	43	35	30	42	35	30		41	34	30		40	34	30	28
10	54	40	33	27	52	40	32	27	39	32	27		38	32	27		37	31	27	25

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8964	8964	8964
5°	8984	8898	8955
10°	8929	8835	8885
15°	8832	8729	8766
20°	8693	8580	8595
25°	8544	8403	8395
30°	8360	8213	8172
35°	8163	8007	7895
40°	7961	7785	7674
45°	7742	7582	7431
50°	7501	7337	7116
55°	7269	7060	6862
60°	6992	6779	6538
65°	6661	6443	6226
70°	6345	6054	5846
75°	5782	5589	5397
80°	5144	5066	4943
85°	4476	4557	4313



TEST NUMBER: P334363

CATALOG NUMBER: S125DP-S1090D935-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	131.0	3.6
10°-20°	369.9	10.2
20°-30°	546.1	15.1
30°-40°	637.2	17.6
40°-50°	639.9	17.7
50°-60°	561.8	15.6
60°-70°	418.4	11.6
70°-80°	239.0	6.6
80°-90°	69.0	1.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1047.0	29.0
0°-40°	1684.2	46.6
0°-60°	2885.9	79.9
0°-90°	3612.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3612.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1388	1388	1388	1388	1388	
5°	1386	1384	1372	1382	1381	131
15°	1321	1318	1306	1311	1311	372
25°	1199	1194	1179	1181	1178	552
35°	1035	1031	1016	1010	1001	648
45°	848	843	830	817	814	653
55°	646	642	627	617	609	576
65°	436	434	422	412	407	432
75°	232	230	224	221	216	247
85°	60	62	62	60	58	70
90°	0	0	0	0	0	



TEST NUMBER: P334363

CATALOG NUMBER: S125DP-S1090D935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1387.9	1387.9	1387.9	1387.9	1387.9
2.5°	1392.2	1389.0	1378.0	1389.0	1387.9
5°	1385.7	1383.5	1372.5	1382.4	1381.3
7.5°	1375.8	1373.6	1361.5	1371.4	1370.3
10°	1361.5	1359.3	1347.2	1356.0	1354.9
12.5°	1343.9	1339.5	1328.6	1335.2	1335.2
15°	1320.9	1317.6	1305.5	1311.0	1311.0
17.5°	1296.7	1291.2	1279.2	1285.7	1280.3
20°	1264.9	1262.7	1248.4	1256.1	1250.6
22.5°	1233.0	1228.6	1215.5	1219.9	1216.6
25°	1199.0	1193.5	1179.2	1181.4	1178.1
27.5°	1159.5	1156.2	1141.9	1143.0	1139.7
30°	1121.0	1117.8	1101.3	1099.1	1095.8
32.5°	1079.3	1073.8	1059.6	1055.2	1048.6
35°	1035.4	1031.0	1015.6	1010.1	1001.4
37.5°	990.4	984.9	970.6	962.9	957.4
40°	944.3	938.8	923.4	913.5	910.2
42.5°	894.9	890.5	875.1	866.3	860.8
45°	847.6	843.3	830.1	816.9	813.6
47.5°	796.0	797.1	780.7	767.5	759.8
50°	746.6	743.3	730.2	715.9	708.2
52.5°	696.1	693.9	679.7	667.6	658.8
55°	645.6	642.3	627.0	617.1	609.4
57.5°	591.8	590.7	577.5	564.4	561.1
60°	541.3	536.9	524.8	513.9	506.2
62.5°	488.6	485.3	475.4	463.4	457.9
65°	435.9	433.7	421.6	411.7	407.4
67.5°	384.3	379.9	371.1	362.3	360.1
70°	336.0	330.5	320.6	314.0	309.6
72.5°	283.3	280.0	274.5	266.8	262.4
75°	231.7	229.5	224.0	220.7	216.3
77.5°	183.4	182.3	179.0	176.8	173.5
80°	138.3	138.3	136.2	135.1	132.9
82.5°	98.8	96.6	96.6	94.4	94.4
85°	60.4	61.5	61.5	60.4	58.2
87.5°	29.6	29.6	28.5	28.5	26.4
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)