

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331421-927

Luminaire Tested: **SA2XXDIP-C1005D330U927-4F0-1E-UDD-A1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331421-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C1005D330U927-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 330 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4413.7 lumens
Efficiency: N/A
Efficacy: 88.6 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 49.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331421-927
CATALOG NUMBER: SA2XXDIP-C1005D330U927-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331421-927

CATALOG NUMBER: SA2XXDIP-C1005D330U927-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	114	114	114	114	109	109	109	109	99	99	99	91	91	91	83	83	83	79
1	105	101	97	94	100	97	93	90	89	86	84	81	79	77	74	73	71	68
2	96	89	83	78	92	85	80	75	79	74	70	72	69	66	66	64	61	58
3	88	79	72	66	84	76	69	64	70	65	60	65	60	57	60	56	53	50
4	81	71	63	57	78	68	61	55	63	57	52	58	53	49	54	50	46	44
5	75	63	55	49	72	61	54	48	57	50	46	53	47	43	49	45	41	39
6	70	57	49	43	66	55	48	42	52	45	40	48	43	38	45	40	37	34
7	65	52	44	39	62	51	43	38	47	41	36	44	39	34	41	36	33	31
8	60	48	40	35	58	46	39	34	43	37	32	41	35	31	38	33	30	28
9	56	44	36	31	54	43	36	31	40	34	29	37	32	28	35	30	27	25
10	53	41	33	28	51	39	33	28	37	31	27	35	30	26	33	28	25	23

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	25504	25504	25504	25504
5°	28593	25671	22749	25671
10°	32765	25460	19687	25460
15°	36247	24993	17392	24993
20°	35696	24493	15856	24493
25°	32186	23826	14883	23826
30°	26597	22760	14171	22760
35°	19385	21646	13665	21646
40°	15483	20331	13384	20331
45°	13531	18810	13001	18810
50°	12717	17337	12750	17337
55°	11724	15842	12408	15842
60°	10743	14250	11880	14250
65°	9788	12825	11366	12825
70°	8884	11434	10607	11434
75°	7879	9881	9395	9881
80°	6778	8182	7569	8182
85°	6076	6076	4502	6076



TEST NUMBER: P331421-927

CATALOG NUMBER: SA2XXDIP-C1005D330U927-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	150.4	3.4
10°-20°	437.4	9.9
20°-30°	634.7	14.4
30°-40°	669.8	15.2
40°-50°	593.0	13.4
50°-60°	473.3	10.7
60°-70°	321.7	7.3
70°-80°	164.9	3.7
80°-90°	41.1	0.9
90°-100°	21.0	0.5
100°-110°	65.3	1.5
110°-120°	111.6	2.5
120°-130°	146.7	3.3
130°-140°	164.7	3.7
140°-150°	161.5	3.7
150°-160°	135.4	3.1
160°-170°	89.8	2.0
170°-180°	31.4	0.7
0°-30°	1222.5	27.7
0°-40°	1892.3	42.9
0°-60°	2958.6	67.0
0°-90°	3486.3	79.0
90°-120°	197.9	4.5
90°-150°	670.7	15.2
90°-180°	927.0	21.0
0°-180°	4413.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1580	1580	1580	1580	1580	
5°	1764	1584	1404	1584	1764	176
15°	2168	1495	1040	1495	2168	598
25°	1807	1337	835	1337	1807	817
35°	984	1098	693	1098	984	640
45°	593	824	569	824	593	466
55°	416	563	441	563	416	373
65°	256	336	298	336	256	255
75°	126	158	151	158	126	135
85°	33	33	24	33	33	36
90°	10	0	10	0	10	6
95°	17	15	17	15	17	19
105°	62	60	62	60	62	65
115°	112	112	112	112	112	111
125°	163	163	163	163	163	146
135°	213	211	213	211	213	164
145°	259	256	259	256	259	161
155°	295	292	295	292	295	136
165°	318	318	318	318	318	90
175°	330	331	330	331	330	31
180°	332	332	332	332	332	



TEST NUMBER: P331421-927

CATALOG NUMBER: SA2XXDIP-C1005D330U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6
2.5°	1652.5	1653.0	1653.9	1646.2	1645.2	1645.2	1638.4	1632.6	1625.8	1616.5	1617.6
5°	1764.2	1770.8	1773.3	1766.0	1755.1	1753.9	1743.6	1726.6	1710.8	1698.0	1688.9
7.5°	1897.5	1900.2	1894.3	1884.7	1876.5	1861.9	1842.8	1823.9	1797.6	1773.5	1755.5
10°	1998.5	2002.2	1991.9	1977.9	1966.4	1949.4	1921.4	1892.9	1858.3	1825.0	1798.2
12.5°	2075.3	2084.2	2071.0	2069.2	2049.5	2026.1	1992.8	1978.4	1929.7	1883.2	1854.6
15°	2168.5	2167.9	2169.2	2157.6	2143.0	2139.4	2104.2	2065.9	1997.3	1970.0	1922.6
17.5°	2141.6	2150.8	2155.1	2154.9	2154.6	2152.3	2141.0	2116.8	2082.4	2038.1	1983.5
20°	2077.5	2089.6	2091.4	2105.4	2113.3	2123.6	2127.9	2121.1	2099.9	2062.9	2015.5
22.5°	1978.4	1981.8	1987.5	2009.2	2026.3	2052.2	2065.7	2088.1	2080.0	2061.9	2022.4
25°	1806.7	1800.6	1821.9	1832.8	1872.2	1913.5	1943.3	1976.1	2005.3	2022.8	2011.3
27.5°	1600.5	1591.4	1623.3	1652.3	1684.3	1729.0	1775.4	1830.1	1875.7	1932.6	1952.2
30°	1426.6	1432.1	1462.4	1493.4	1542.0	1605.1	1657.3	1717.5	1782.4	1846.2	1890.5
32.5°	1239.2	1260.2	1279.4	1326.8	1369.6	1440.0	1516.5	1591.7	1672.7	1745.2	1813.8
35°	983.5	1007.7	1034.5	1069.1	1129.2	1199.0	1273.7	1375.1	1485.6	1584.5	1665.9
37.5°	827.8	823.9	839.2	864.3	912.9	969.3	1055.3	1155.4	1285.5	1401.8	1516.5
40°	734.6	732.1	743.1	766.1	803.2	844.5	919.7	1007.7	1128.5	1270.7	1407.2
42.5°	670.5	671.9	678.0	694.3	719.6	753.6	810.0	884.9	995.5	1129.3	1276.1
45°	592.6	596.8	603.5	611.3	625.9	653.9	685.4	738.9	826.2	937.9	1082.4
47.5°	536.4	536.5	543.4	550.2	558.9	574.6	600.4	633.9	695.6	786.6	910.8
50°	506.3	502.1	506.9	512.4	521.5	532.4	549.4	581.0	622.3	695.7	799.5
52.5°	469.4	469.5	473.9	475.9	484.1	495.0	510.6	532.4	569.8	627.2	712.6
55°	416.5	419.5	421.9	425.6	432.8	440.8	452.9	467.5	496.6	539.7	602.9
57.5°	366.7	367.7	370.1	377.0	381.6	388.9	400.4	413.7	432.6	464.5	512.0
60°	332.7	332.7	337.5	340.6	346.7	353.9	363.1	375.8	392.8	418.9	457.2
62.5°	301.6	301.1	303.1	308.0	312.7	319.5	328.5	339.4	355.4	378.6	410.0
65°	256.2	255.0	258.6	259.8	264.7	271.4	278.7	290.2	302.9	320.0	347.8
67.5°	212.5	214.0	215.9	218.2	220.9	227.9	232.7	240.9	251.7	265.8	284.7
70°	188.2	188.2	188.2	190.0	193.7	197.3	202.2	208.8	219.2	231.3	248.3
72.5°	161.0	163.0	164.9	163.8	168.4	170.6	176.4	180.2	190.0	197.8	212.9
75°	126.3	126.3	126.3	129.3	131.1	132.9	136.6	140.2	145.1	154.8	162.7
77.5°	94.2	94.0	94.6	95.3	97.3	99.4	100.5	103.8	108.3	112.8	119.5
80°	72.9	74.1	74.7	75.9	75.9	77.1	77.7	82.0	85.0	88.0	92.3
82.5°	56.3	56.6	56.7	57.0	57.4	58.1	59.7	61.1	62.2	64.7	68.0
85°	32.8	32.2	32.2	33.4	32.8	32.8	34.0	35.2	35.2	35.8	37.6
87.5°	14.5	14.5	15.0	14.5	14.5	15.0	15.0	14.6	15.1	15.5	15.8
90°	9.5	9.4	9.4	9.3	9.3	9.3	9.4	9.6	9.7	9.8	8.4
92.5°	9.0	9.0	9.0	9.0	9.0	9.0	9.0	9.0	9.0	8.9	8.6
95°	17.3	17.5	17.6	17.7	17.8	17.9	17.9	17.9	17.9	17.9	17.8
97.5°	30.0	30.1	30.1	30.1	30.1	30.1	30.1	30.1	30.1	30.1	29.9
100°	38.3	38.4	38.5	38.5	38.6	38.7	38.7	38.7	38.7	38.7	38.4
102.5°	47.8	47.8	47.8	47.9	48.0	48.0	47.9	47.9	47.8	47.8	47.5
105°	62.1	62.1	62.1	62.1	62.1	62.1	61.9	61.8	61.7	61.6	61.5
107.5°	75.7	76.0	76.3	76.5	76.8	76.9	76.9	76.8	76.8	76.8	76.8
110°	86.2	86.4	86.6	86.7	87.0	87.1	87.1	87.1	87.1	87.1	87.1



TEST NUMBER: P331421-927

CATALOG NUMBER: SA2XXDIP-C1005D330U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	96.3	96.4	96.6	96.7	96.8	97.0	97.1	97.3	97.4	97.6	97.6
115°	111.9	112.2	112.3	112.5	112.7	112.8	112.9	113.0	113.0	113.0	113.2
117.5°	126.9	127.1	127.3	127.5	127.6	127.8	127.9	128.1	128.3	128.4	128.7
120°	137.4	137.6	137.8	138.0	138.2	138.2	138.2	138.2	138.2	138.2	138.8
122.5°	147.7	147.8	148.0	148.1	148.3	148.4	148.5	148.7	148.9	149.0	149.3
125°	163.4	163.5	163.6	163.7	163.7	163.8	164.0	164.2	164.4	164.5	164.8
127.5°	177.8	178.0	178.2	178.4	178.6	178.8	179.0	179.3	179.4	179.7	179.9
130°	188.1	188.3	188.5	188.9	189.1	189.3	189.4	189.5	189.6	189.7	189.9
132.5°	198.0	198.1	198.4	198.5	198.8	199.0	199.2	199.5	199.8	200.0	200.0
135°	213.3	213.5	213.7	213.8	214.0	214.1	214.2	214.3	214.3	214.4	214.3
137.5°	227.1	227.4	227.7	227.9	228.1	228.3	228.3	228.4	228.5	228.5	228.3
140°	236.8	237.0	237.3	237.5	237.7	237.9	237.9	237.9	237.9	237.9	237.6
142.5°	245.5	245.7	246.0	246.3	246.5	246.6	246.5	246.5	246.4	246.4	246.2
145°	258.6	258.9	259.1	259.4	259.6	259.7	259.6	259.6	259.5	259.4	259.0
147.5°	270.3	270.5	270.8	271.0	271.2	271.3	271.2	271.0	270.9	270.8	270.5
150°	277.9	278.1	278.3	278.5	278.7	278.7	278.5	278.3	278.1	277.9	277.7
152.5°	285.1	285.3	285.6	285.8	286.1	286.1	285.8	285.6	285.3	285.1	284.8
155°	294.7	294.9	295.1	295.2	295.5	295.4	295.1	294.8	294.5	294.1	294.0
157.5°	303.0	303.3	303.6	303.9	304.2	304.1	303.7	303.2	302.9	302.5	302.3
160°	308.2	308.4	308.6	308.9	309.1	309.1	308.7	308.3	307.9	307.6	307.5
162.5°	312.6	312.9	313.2	313.5	313.8	313.8	313.3	312.9	312.5	312.0	312.0
165°	318.5	318.8	319.1	319.4	319.7	319.6	319.2	318.8	318.4	317.9	317.9
167.5°	323.3	323.6	323.9	324.3	324.6	324.6	324.1	323.7	323.2	322.8	322.8
170°	325.7	326.1	326.5	326.9	327.3	327.3	326.8	326.4	325.9	325.5	325.6
172.5°	327.8	328.2	328.5	328.9	329.3	329.2	328.8	328.4	328.0	327.5	327.6
175°	329.9	330.3	330.7	331.1	331.4	331.4	331.0	330.6	330.1	329.7	329.8
177.5°	331.0	331.3	331.6	331.8	332.2	332.2	331.8	331.6	331.3	331.0	331.1
180°	331.7	331.7	331.7	331.7	331.7	331.7	331.7	331.7	331.7	331.7	331.7



TEST NUMBER: P331421-927

CATALOG NUMBER: SA2XXDIP-C1005D330U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6
2.5°	1621.0	1617.1	1614.6	1605.9	1598.1	1590.3	1587.9	1588.9	1578.2	1568.0	1563.6
5°	1684.1	1671.9	1660.4	1644.0	1624.6	1603.3	1592.4	1583.9	1562.7	1539.6	1526.2
7.5°	1740.7	1723.3	1701.1	1670.2	1642.0	1608.5	1587.3	1568.4	1537.4	1504.8	1484.9
10°	1775.1	1751.4	1722.9	1685.3	1650.7	1610.0	1581.4	1552.9	1516.5	1477.7	1453.3
12.5°	1804.7	1772.8	1744.8	1696.5	1655.5	1604.6	1570.8	1530.6	1492.2	1446.0	1422.3
15°	1875.3	1816.4	1763.0	1708.3	1658.0	1586.9	1549.3	1495.2	1444.9	1387.8	1360.5
17.5°	1929.8	1863.6	1779.5	1710.1	1651.3	1572.6	1517.3	1452.6	1393.1	1327.9	1290.7
20°	1960.9	1885.0	1794.5	1712.0	1641.6	1551.7	1491.6	1425.5	1355.7	1282.1	1242.1
22.5°	1979.3	1899.6	1810.1	1704.7	1622.2	1534.7	1459.0	1386.6	1315.8	1236.5	1194.5
25°	1985.2	1912.3	1817.7	1698.7	1597.8	1498.9	1407.9	1337.4	1251.8	1177.7	1116.4
27.5°	1956.3	1904.1	1813.0	1687.2	1569.8	1454.1	1352.6	1272.8	1182.5	1102.1	1040.5
30°	1920.8	1890.5	1801.8	1675.5	1547.4	1423.0	1311.3	1220.8	1131.0	1049.6	986.5
32.5°	1866.0	1859.4	1781.5	1659.1	1523.7	1383.7	1268.1	1176.6	1077.1	997.2	937.0
35°	1758.2	1787.2	1738.1	1622.2	1478.8	1327.7	1202.6	1098.2	995.1	918.5	862.1
37.5°	1613.7	1686.0	1673.2	1568.1	1418.4	1266.8	1128.7	1019.5	921.2	844.0	788.6
40°	1514.1	1606.4	1619.7	1526.9	1375.7	1219.6	1073.3	964.6	868.7	798.4	742.4
42.5°	1407.2	1515.0	1551.7	1477.3	1329.0	1170.1	1023.8	911.2	816.3	747.8	698.3
45°	1228.1	1370.8	1437.0	1394.5	1251.3	1088.5	937.9	823.8	737.6	673.3	635.0
47.5°	1060.7	1216.6	1305.6	1290.5	1164.7	1003.5	854.7	745.1	661.2	609.9	575.7
50°	942.2	1102.5	1209.9	1214.8	1102.5	942.8	793.4	690.2	613.1	565.2	537.3
52.5°	839.2	992.2	1109.4	1135.1	1033.0	879.6	738.6	635.9	568.0	523.9	498.9
55°	704.8	834.2	964.1	1011.4	929.5	783.8	653.2	562.8	499.0	468.7	446.8
57.5°	586.0	693.8	813.7	866.1	815.6	690.9	568.5	489.9	438.2	411.6	394.8
60°	523.3	608.3	715.2	777.7	734.0	622.9	516.0	441.3	398.9	375.2	359.4
62.5°	465.0	540.3	630.7	687.9	664.0	559.3	463.6	397.7	361.0	338.7	327.3
65°	383.7	443.1	513.0	565.8	550.0	470.5	392.2	335.7	306.6	289.0	279.9
67.5°	315.9	358.9	407.3	453.6	440.8	384.5	321.6	277.7	256.0	240.7	235.3
70°	273.2	305.9	349.1	386.1	375.8	329.6	279.9	242.2	223.4	210.6	205.2
72.5°	232.4	259.4	292.2	322.5	315.5	277.2	235.7	207.2	192.8	181.0	176.6
75°	175.5	196.1	216.1	236.1	234.3	204.6	180.3	158.4	146.9	137.8	136.0
77.5°	129.5	141.1	154.7	166.6	163.3	146.3	127.2	114.7	106.2	100.1	99.2
80°	98.9	105.6	115.3	123.8	119.6	112.3	97.1	88.0	82.0	75.9	73.4
82.5°	71.8	78.4	84.3	88.9	85.6	78.8	69.5	63.3	59.7	55.5	54.5
85°	37.6	41.3	43.7	44.9	43.7	39.5	35.2	32.8	29.8	28.0	27.3
87.5°	16.0	15.7	15.4	16.2	14.6	14.4	12.4	10.8	10.4	10.1	9.3
90°	7.1	5.7	4.4	3.2	2.5	1.7	1.0	0.3	1.0	1.7	2.5
92.5°	8.2	7.9	7.6	7.2	6.7	6.1	5.5	5.0	5.5	6.1	6.7
95°	17.7	17.5	17.4	17.0	16.4	15.8	15.2	14.6	15.2	15.8	16.4
97.5°	29.6	29.4	29.2	28.8	28.2	27.6	27.2	26.6	27.2	27.6	28.2
100°	38.3	38.0	37.9	37.5	37.1	36.5	36.0	35.6	36.0	36.5	37.1
102.5°	47.3	47.1	46.9	46.5	46.1	45.7	45.3	44.9	45.3	45.7	46.1
105°	61.3	61.2	61.1	60.9	60.8	60.5	60.4	60.2	60.4	60.5	60.8
107.5°	76.8	76.8	76.8	76.6	76.4	76.0	75.8	75.5	75.8	76.0	76.4
110°	87.1	87.1	87.1	86.8	86.5	86.1	85.7	85.4	85.7	86.1	86.5



TEST NUMBER: P331421-927

CATALOG NUMBER: SA2XXDIP-C1005D330U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	97.7	97.7	97.8	97.6	97.2	96.9	96.5	96.1	96.5	96.9	97.2
115°	113.3	113.4	113.6	113.4	113.0	112.7	112.3	111.9	112.3	112.7	113.0
117.5°	129.1	129.4	129.8	129.8	129.2	128.7	128.3	127.7	128.3	128.7	129.2
120°	139.3	139.7	140.2	140.2	139.7	139.3	138.8	138.2	138.8	139.3	139.7
122.5°	149.7	150.0	150.4	150.3	149.6	149.1	148.5	147.9	148.5	149.1	149.6
125°	164.9	165.1	165.3	165.1	164.5	164.0	163.4	162.9	163.4	164.0	164.5
127.5°	180.1	180.4	180.5	180.3	179.6	179.0	178.2	177.5	178.2	179.0	179.6
130°	190.0	190.1	190.3	189.9	189.1	188.3	187.5	186.7	187.5	188.3	189.1
132.5°	200.0	199.9	199.9	199.6	198.9	198.3	197.6	197.0	197.6	198.3	198.9
135°	214.1	214.0	213.9	213.5	212.8	212.1	211.4	210.7	211.4	212.1	212.8
137.5°	228.1	228.0	227.8	227.5	227.0	226.3	225.8	225.2	225.8	226.3	227.0
140°	237.3	236.9	236.6	236.2	235.7	235.1	234.6	234.0	234.6	235.1	235.7
142.5°	246.0	245.7	245.6	245.2	244.6	244.1	243.5	243.0	243.5	244.1	244.6
145°	258.7	258.3	257.9	257.5	257.1	256.7	256.3	255.8	256.3	256.7	257.1
147.5°	270.3	270.0	269.7	269.3	268.9	268.3	267.8	267.3	267.8	268.3	268.9
150°	277.4	277.2	276.9	276.6	276.2	275.8	275.5	275.1	275.5	275.8	276.2
152.5°	284.5	284.2	283.9	283.5	283.2	282.8	282.4	282.1	282.4	282.8	283.2
155°	293.7	293.6	293.4	293.2	293.0	292.9	292.6	292.5	292.6	292.9	293.0
157.5°	302.2	302.1	302.0	301.9	301.7	301.6	301.5	301.3	301.5	301.6	301.7
160°	307.4	307.4	307.4	307.2	307.1	307.0	306.9	306.7	306.9	307.0	307.1
162.5°	312.0	311.9	311.8	311.8	311.7	311.7	311.7	311.6	311.7	311.7	311.7
165°	317.9	317.9	317.9	318.0	318.1	318.1	318.1	318.2	318.1	318.1	318.1
167.5°	322.8	322.8	322.9	323.0	323.1	323.4	323.5	323.7	323.5	323.4	323.1
170°	325.6	325.7	325.7	325.9	326.1	326.2	326.5	326.6	326.5	326.2	326.1
172.5°	327.6	327.7	327.7	327.9	328.0	328.3	328.4	328.6	328.4	328.3	328.0
175°	329.9	330.1	330.2	330.3	330.5	330.7	330.9	331.1	330.9	330.7	330.5
177.5°	331.2	331.3	331.4	331.5	331.7	331.8	331.9	332.1	331.9	331.8	331.7
180°	331.7	331.7	331.7	331.7	331.7	331.7	331.7	331.7	331.7	331.7	331.7



TEST NUMBER: P331421-927

CATALOG NUMBER: SA2XXDIP-C1005D330U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6
2.5°	1558.8	1555.8	1545.6	1540.3	1531.6	1523.3	1518.0	1520.4	1522.3	1521.4	1519.9
5°	1514.1	1502.5	1484.9	1469.7	1458.8	1438.8	1430.3	1426.1	1422.4	1418.2	1413.9
7.5°	1460.9	1442.7	1417.5	1395.8	1375.4	1350.5	1336.3	1327.9	1319.1	1309.5	1301.0
10°	1423.0	1397.5	1370.8	1340.5	1316.2	1293.7	1273.7	1260.3	1248.2	1236.7	1228.1
12.5°	1383.2	1353.8	1320.8	1279.3	1252.5	1220.4	1217.3	1193.8	1174.8	1167.7	1157.7
15°	1319.8	1278.5	1236.7	1187.5	1166.3	1137.1	1118.9	1100.7	1084.3	1072.7	1069.7
17.5°	1247.8	1194.4	1152.7	1117.4	1082.6	1052.7	1035.9	1021.4	1007.9	992.4	990.4
20°	1192.9	1146.8	1101.3	1070.3	1034.5	1004.1	983.5	968.9	957.4	948.2	940.4
22.5°	1141.0	1090.4	1048.8	1014.9	979.6	955.1	938.8	924.7	915.1	905.1	897.6
25°	1057.6	1018.1	972.6	934.3	905.1	889.4	876.0	863.9	857.9	851.1	842.6
27.5°	984.6	940.7	898.1	868.5	842.9	828.9	819.4	811.2	805.5	801.6	796.8
30°	933.1	888.7	855.4	826.2	805.0	791.1	785.0	780.1	773.4	771.0	768.6
32.5°	883.5	843.6	815.1	789.8	769.5	760.4	754.9	750.5	745.3	742.8	738.0
35°	813.5	780.1	752.2	738.2	721.8	713.9	709.7	703.6	698.8	696.3	695.7
37.5°	747.6	718.6	700.2	682.2	675.3	670.5	664.6	660.5	659.1	658.7	658.1
40°	704.8	681.1	664.8	650.2	647.1	639.8	635.0	631.4	631.4	632.0	631.4
42.5°	666.0	644.8	630.3	617.7	614.1	609.7	604.9	604.7	605.6	607.7	605.6
45°	607.1	591.9	581.6	575.5	568.9	564.6	564.0	565.8	566.4	567.0	568.9
47.5°	552.9	542.9	533.5	526.8	523.9	523.2	522.4	525.6	528.5	529.7	532.4
50°	520.9	509.4	501.5	497.2	494.8	493.5	494.8	498.4	500.8	503.9	505.7
52.5°	485.0	476.8	471.3	468.1	467.1	467.9	468.1	472.2	476.1	477.2	478.0
55°	435.3	429.2	428.0	422.6	424.9	424.4	427.4	429.8	433.5	437.1	437.7
57.5°	385.7	380.9	377.6	378.1	378.8	381.5	384.0	388.3	392.2	396.1	396.4
60°	352.8	350.3	348.5	348.5	349.7	353.3	356.3	360.6	363.1	365.4	367.3
62.5°	322.6	320.2	318.4	319.3	322.5	324.6	328.2	330.5	333.0	335.3	336.2
65°	275.0	273.8	275.6	276.9	277.4	280.5	284.7	286.5	289.0	290.2	294.5
67.5°	231.2	231.4	231.2	232.9	236.4	237.1	241.1	245.4	245.9	248.2	251.0
70°	201.5	202.8	204.0	205.2	208.3	209.5	212.5	214.3	216.7	218.6	220.4
72.5°	174.4	174.6	175.8	175.5	178.1	180.8	183.3	185.1	187.6	189.9	191.7
75°	134.2	134.2	135.4	136.0	139.0	142.0	141.5	142.7	145.1	147.5	148.8
77.5°	98.0	96.6	98.0	98.6	99.6	102.1	102.6	104.3	107.1	106.2	107.6
80°	74.7	72.9	74.7	75.3	75.3	78.3	78.3	79.5	81.4	79.5	81.4
82.5°	53.3	52.4	53.8	53.9	54.9	55.0	56.0	56.2	58.1	57.2	58.1
85°	26.7	26.1	26.7	26.1	26.7	27.3	27.3	26.7	26.7	28.0	26.1
87.5°	8.9	8.6	8.4	8.7	8.5	8.2	7.8	7.8	7.7	6.7	6.7
90°	3.2	4.4	5.7	7.1	8.4	9.8	9.7	9.6	9.4	9.3	9.3
92.5°	7.2	7.6	7.9	8.2	8.6	8.9	9.0	9.0	9.0	9.0	9.0
95°	17.0	17.4	17.5	17.7	17.8	17.9	17.9	17.9	17.9	17.9	17.8
97.5°	28.8	29.2	29.4	29.6	29.9	30.1	30.1	30.1	30.1	30.1	30.1
100°	37.5	37.9	38.0	38.3	38.4	38.7	38.7	38.7	38.7	38.7	38.6
102.5°	46.5	46.9	47.1	47.3	47.5	47.8	47.8	47.9	47.9	48.0	48.0
105°	60.9	61.1	61.2	61.3	61.5	61.6	61.7	61.8	61.9	62.1	62.1
107.5°	76.6	76.8	76.8	76.8	76.8	76.8	76.8	76.8	76.9	76.9	76.8
110°	86.8	87.1	87.1	87.1	87.1	87.1	87.1	87.1	87.1	87.1	87.0



TEST NUMBER: P331421-927

CATALOG NUMBER: SA2XXDIP-C1005D330U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	97.6	97.8	97.7	97.7	97.6	97.6	97.4	97.3	97.1	97.0	96.8
115°	113.4	113.6	113.4	113.3	113.2	113.0	113.0	113.0	112.9	112.8	112.7
117.5°	129.8	129.8	129.4	129.1	128.7	128.4	128.3	128.1	127.9	127.8	127.6
120°	140.2	140.2	139.7	139.3	138.8	138.2	138.2	138.2	138.2	138.2	138.2
122.5°	150.3	150.4	150.0	149.7	149.3	149.0	148.9	148.7	148.5	148.4	148.3
125°	165.1	165.3	165.1	164.9	164.8	164.5	164.4	164.2	164.0	163.8	163.7
127.5°	180.3	180.5	180.4	180.1	179.9	179.7	179.4	179.3	179.0	178.8	178.6
130°	189.9	190.3	190.1	190.0	189.9	189.7	189.6	189.5	189.4	189.3	189.1
132.5°	199.6	199.9	199.9	200.0	200.0	200.0	199.8	199.5	199.2	199.0	198.8
135°	213.5	213.9	214.0	214.1	214.3	214.4	214.3	214.3	214.2	214.1	214.0
137.5°	227.5	227.8	228.0	228.1	228.3	228.5	228.5	228.4	228.3	228.3	228.1
140°	236.2	236.6	236.9	237.3	237.6	237.9	237.9	237.9	237.9	237.9	237.7
142.5°	245.2	245.6	245.7	246.0	246.2	246.4	246.4	246.5	246.5	246.6	246.5
145°	257.5	257.9	258.3	258.7	259.0	259.4	259.5	259.6	259.6	259.7	259.6
147.5°	269.3	269.7	270.0	270.3	270.5	270.8	270.9	271.0	271.2	271.3	271.2
150°	276.6	276.9	277.2	277.4	277.7	277.9	278.1	278.3	278.5	278.7	278.7
152.5°	283.5	283.9	284.2	284.5	284.8	285.1	285.3	285.6	285.8	286.1	286.1
155°	293.2	293.4	293.6	293.7	294.0	294.1	294.5	294.8	295.1	295.4	295.5
157.5°	301.9	302.0	302.1	302.2	302.3	302.5	302.9	303.2	303.7	304.1	304.2
160°	307.2	307.4	307.4	307.4	307.5	307.6	307.9	308.3	308.7	309.1	309.1
162.5°	311.8	311.8	311.9	312.0	312.0	312.0	312.5	312.9	313.3	313.8	313.8
165°	318.0	317.9	317.9	317.9	317.9	317.9	318.4	318.8	319.2	319.6	319.7
167.5°	323.0	322.9	322.8	322.8	322.8	322.8	323.2	323.7	324.1	324.6	324.6
170°	325.9	325.7	325.7	325.6	325.6	325.5	325.9	326.4	326.8	327.3	327.3
172.5°	327.9	327.7	327.7	327.6	327.6	327.5	328.0	328.4	328.8	329.2	329.3
175°	330.3	330.2	330.1	329.9	329.8	329.7	330.1	330.6	331.0	331.4	331.4
177.5°	331.5	331.4	331.3	331.2	331.1	331.0	331.3	331.6	331.8	332.2	332.2
180°	331.7	331.7	331.7	331.7	331.7	331.7	331.7	331.7	331.7	331.7	331.7



TEST NUMBER: P331421-927
 CATALOG NUMBER: SA2XXDIP-C1005D330U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6
2.5°	1515.0	1514.1	1514.1	1509.7	1514.1	1514.1	1515.0	1519.9	1521.4	1522.3	1520.4
5°	1405.4	1403.6	1400.6	1403.6	1400.6	1403.6	1405.4	1413.9	1418.2	1422.4	1426.1
7.5°	1297.0	1289.7	1288.6	1281.4	1288.6	1289.7	1297.0	1301.0	1309.5	1319.1	1327.9
10°	1217.8	1213.0	1212.4	1200.8	1212.4	1213.0	1217.8	1228.1	1236.7	1248.2	1260.3
12.5°	1157.6	1146.0	1148.3	1141.5	1148.3	1146.0	1157.6	1157.7	1167.7	1174.8	1193.8
15°	1053.3	1053.3	1050.9	1040.5	1050.9	1053.3	1053.3	1069.7	1072.7	1084.3	1100.7
17.5°	978.4	977.2	971.4	974.2	971.4	977.2	978.4	990.4	992.4	1007.9	1021.4
20°	933.7	930.1	922.8	922.8	922.8	930.1	933.7	940.4	948.2	957.4	968.9
22.5°	891.4	891.2	883.4	885.9	883.4	891.2	891.4	897.6	905.1	915.1	924.7
25°	842.0	837.2	833.5	835.4	833.5	837.2	842.0	842.6	851.1	857.9	863.9
27.5°	795.2	792.5	792.3	787.3	792.3	792.5	795.2	796.8	801.6	805.5	811.2
30°	767.9	761.9	763.1	760.1	763.1	761.9	767.9	768.6	771.0	773.4	780.1
32.5°	736.9	734.7	733.5	730.9	733.5	734.7	736.9	738.0	742.8	745.3	750.5
35°	694.5	695.1	692.1	693.3	692.1	695.1	694.5	695.7	696.3	698.8	703.6
37.5°	657.5	659.4	658.0	658.3	658.0	659.4	657.5	658.1	658.7	659.1	660.5
40°	633.2	633.2	633.2	635.0	633.2	633.2	633.2	631.4	632.0	631.4	631.4
42.5°	609.9	609.0	607.9	607.8	607.9	609.0	609.9	605.6	607.7	605.6	604.7
45°	570.1	571.9	572.5	569.4	572.5	571.9	570.1	568.9	567.0	566.4	565.8
47.5°	534.0	534.2	534.0	536.7	534.0	534.2	534.0	532.4	529.7	528.5	525.6
50°	508.7	507.6	508.7	507.6	508.7	507.6	508.7	505.7	503.9	500.8	498.4
52.5°	482.0	482.3	481.6	481.3	481.6	482.3	482.0	478.0	477.2	476.1	472.2
55°	440.1	441.3	440.8	440.8	440.8	441.3	440.1	437.7	437.1	433.5	429.8
57.5°	396.8	397.9	398.7	396.1	398.7	397.9	396.8	396.4	396.1	392.2	388.3
60°	366.7	369.7	369.1	367.9	369.1	369.7	366.7	367.3	365.4	363.1	360.6
62.5°	339.0	340.1	340.0	339.8	340.0	340.1	339.0	336.2	335.3	333.0	330.5
65°	296.3	297.5	295.6	297.5	295.6	297.5	296.3	294.5	290.2	289.0	286.5
67.5°	250.3	250.6	251.9	252.8	251.9	250.6	250.3	251.0	248.2	245.9	245.4
70°	221.6	221.0	222.8	224.7	222.8	221.0	221.6	220.4	218.6	216.7	214.3
72.5°	191.5	192.8	192.2	193.5	192.2	192.8	191.5	191.7	189.9	187.6	185.1
75°	147.5	149.3	148.8	150.6	148.8	149.3	147.5	148.8	147.5	145.1	142.7
77.5°	106.6	106.9	106.6	107.6	106.6	106.9	106.6	107.6	106.2	107.1	104.3
80°	81.4	80.2	78.9	81.4	78.9	80.2	81.4	81.4	79.5	81.4	79.5
82.5°	56.6	57.3	56.1	56.1	56.1	57.3	56.6	58.1	57.2	58.1	56.2
85°	26.1	25.5	24.3	24.3	24.3	25.5	26.1	26.1	28.0	26.7	26.7
87.5°	6.7	6.3	6.3	5.8	6.3	6.3	6.7	6.7	6.7	7.7	7.8
90°	9.3	9.4	9.4	9.5	9.4	9.4	9.3	9.3	9.3	9.4	9.6
92.5°	9.0	9.0	9.0	9.0	9.0	9.0	9.0	9.0	9.0	9.0	9.0
95°	17.7	17.6	17.5	17.3	17.5	17.6	17.7	17.8	17.9	17.9	17.9
97.5°	30.1	30.1	30.1	30.0	30.1	30.1	30.1	30.1	30.1	30.1	30.1
100°	38.5	38.5	38.4	38.3	38.4	38.5	38.5	38.6	38.7	38.7	38.7
102.5°	47.9	47.8	47.8	47.8	47.8	47.8	47.9	48.0	48.0	47.9	47.9
105°	62.1	62.1	62.1	62.1	62.1	62.1	62.1	62.1	62.1	61.9	61.8
107.5°	76.5	76.3	76.0	75.7	76.0	76.3	76.5	76.8	76.9	76.9	76.8
110°	86.7	86.6	86.4	86.2	86.4	86.6	86.7	87.0	87.1	87.1	87.1



TEST NUMBER: P331421-927

CATALOG NUMBER: SA2XXDIP-C1005D330U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	96.7	96.6	96.4	96.3	96.4	96.6	96.7	96.8	97.0	97.1	97.3
115°	112.5	112.3	112.2	111.9	112.2	112.3	112.5	112.7	112.8	112.9	113.0
117.5°	127.5	127.3	127.1	126.9	127.1	127.3	127.5	127.6	127.8	127.9	128.1
120°	138.0	137.8	137.6	137.4	137.6	137.8	138.0	138.2	138.2	138.2	138.2
122.5°	148.1	148.0	147.8	147.7	147.8	148.0	148.1	148.3	148.4	148.5	148.7
125°	163.7	163.6	163.5	163.4	163.5	163.6	163.7	163.7	163.8	164.0	164.2
127.5°	178.4	178.2	178.0	177.8	178.0	178.2	178.4	178.6	178.8	179.0	179.3
130°	188.9	188.5	188.3	188.1	188.3	188.5	188.9	189.1	189.3	189.4	189.5
132.5°	198.5	198.4	198.1	198.0	198.1	198.4	198.5	198.8	199.0	199.2	199.5
135°	213.8	213.7	213.5	213.3	213.5	213.7	213.8	214.0	214.1	214.2	214.3
137.5°	227.9	227.7	227.4	227.1	227.4	227.7	227.9	228.1	228.3	228.3	228.4
140°	237.5	237.3	237.0	236.8	237.0	237.3	237.5	237.7	237.9	237.9	237.9
142.5°	246.3	246.0	245.7	245.5	245.7	246.0	246.3	246.5	246.6	246.5	246.5
145°	259.4	259.1	258.9	258.6	258.9	259.1	259.4	259.6	259.7	259.6	259.6
147.5°	271.0	270.8	270.5	270.3	270.5	270.8	271.0	271.2	271.3	271.2	271.0
150°	278.5	278.3	278.1	277.9	278.1	278.3	278.5	278.7	278.7	278.5	278.3
152.5°	285.8	285.6	285.3	285.1	285.3	285.6	285.8	286.1	286.1	285.8	285.6
155°	295.2	295.1	294.9	294.7	294.9	295.1	295.2	295.5	295.4	295.1	294.8
157.5°	303.9	303.6	303.3	303.0	303.3	303.6	303.9	304.2	304.1	303.7	303.2
160°	308.9	308.6	308.4	308.2	308.4	308.6	308.9	309.1	309.1	308.7	308.3
162.5°	313.5	313.2	312.9	312.6	312.9	313.2	313.5	313.8	313.8	313.3	312.9
165°	319.4	319.1	318.8	318.5	318.8	319.1	319.4	319.7	319.6	319.2	318.8
167.5°	324.3	323.9	323.6	323.3	323.6	323.9	324.3	324.6	324.6	324.1	323.7
170°	326.9	326.5	326.1	325.7	326.1	326.5	326.9	327.3	327.3	326.8	326.4
172.5°	328.9	328.5	328.2	327.8	328.2	328.5	328.9	329.3	329.2	328.8	328.4
175°	331.1	330.7	330.3	329.9	330.3	330.7	331.1	331.4	331.4	331.0	330.6
177.5°	331.8	331.6	331.3	331.0	331.3	331.6	331.8	332.2	332.2	331.8	331.6
180°	331.7	331.7	331.7	331.7	331.7	331.7	331.7	331.7	331.7	331.7	331.7



TEST NUMBER: P331421-927

CATALOG NUMBER: SA2XXDIP-C1005D330U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6
2.5°	1518.0	1523.3	1531.6	1540.3	1545.6	1555.8	1558.8	1563.6	1568.0	1578.2	1588.9
5°	1430.3	1438.8	1458.8	1469.7	1484.9	1502.5	1514.1	1526.2	1539.6	1562.7	1583.9
7.5°	1336.3	1350.5	1375.4	1395.8	1417.5	1442.7	1460.9	1484.9	1504.8	1537.4	1568.4
10°	1273.7	1293.7	1316.2	1340.5	1370.8	1397.5	1423.0	1453.3	1477.7	1516.5	1552.9
12.5°	1217.3	1220.4	1252.5	1279.3	1320.8	1353.8	1383.2	1422.3	1446.0	1492.2	1530.6
15°	1118.9	1137.1	1166.3	1187.5	1236.7	1278.5	1319.8	1360.5	1387.8	1444.9	1495.2
17.5°	1035.9	1052.7	1082.6	1117.4	1152.7	1194.4	1247.8	1290.7	1327.9	1393.1	1452.6
20°	983.5	1004.1	1034.5	1070.3	1101.3	1146.8	1192.9	1242.1	1282.1	1355.7	1425.5
22.5°	938.8	955.1	979.6	1014.9	1048.8	1090.4	1141.0	1194.5	1236.5	1315.8	1386.6
25°	876.0	889.4	905.1	934.3	972.6	1018.1	1057.6	1116.4	1177.7	1251.8	1337.4
27.5°	819.4	828.9	842.9	868.5	898.1	940.7	984.6	1040.5	1102.1	1182.5	1272.8
30°	785.0	791.1	805.0	826.2	855.4	888.7	933.1	986.5	1049.6	1131.0	1220.8
32.5°	754.9	760.4	769.5	789.8	815.1	843.6	883.5	937.0	997.2	1077.1	1176.6
35°	709.7	713.9	721.8	738.2	752.2	780.1	813.5	862.1	918.5	995.1	1098.2
37.5°	664.6	670.5	675.3	682.2	700.2	718.6	747.6	788.6	844.0	921.2	1019.5
40°	635.0	639.8	647.1	650.2	664.8	681.1	704.8	742.4	798.4	868.7	964.6
42.5°	604.9	609.7	614.1	617.7	630.3	644.8	666.0	698.3	747.8	816.3	911.2
45°	564.0	564.6	568.9	575.5	581.6	591.9	607.1	635.0	673.3	737.6	823.8
47.5°	522.4	523.2	523.9	526.8	533.5	542.9	552.9	575.7	609.9	661.2	745.1
50°	494.8	493.5	494.8	497.2	501.5	509.4	520.9	537.3	565.2	613.1	690.2
52.5°	468.1	467.9	467.1	468.1	471.3	476.8	485.0	498.9	523.9	568.0	635.9
55°	427.4	424.4	424.9	422.6	428.0	429.2	435.3	446.8	468.7	499.0	562.8
57.5°	384.0	381.5	378.8	378.1	377.6	380.9	385.7	394.8	411.6	438.2	489.9
60°	356.3	353.3	349.7	348.5	348.5	350.3	352.8	359.4	375.2	398.9	441.3
62.5°	328.2	324.6	322.5	319.3	318.4	320.2	322.6	327.3	338.7	361.0	397.7
65°	284.7	280.5	277.4	276.9	275.6	273.8	275.0	279.9	289.0	306.6	335.7
67.5°	241.1	237.1	236.4	232.9	231.2	231.4	231.2	235.3	240.7	256.0	277.7
70°	212.5	209.5	208.3	205.2	204.0	202.8	201.5	205.2	210.6	223.4	242.2
72.5°	183.3	180.8	178.1	175.5	175.8	174.6	174.4	176.6	181.0	192.8	207.2
75°	141.5	142.0	139.0	136.0	135.4	134.2	134.2	136.0	137.8	146.9	158.4
77.5°	102.6	102.1	99.6	98.6	98.0	96.6	98.0	99.2	100.1	106.2	114.7
80°	78.3	78.3	75.3	75.3	74.7	72.9	74.7	73.4	75.9	82.0	88.0
82.5°	56.0	55.0	54.9	53.9	53.8	52.4	53.3	54.5	55.5	59.7	63.3
85°	27.3	27.3	26.7	26.1	26.7	26.1	26.7	27.3	28.0	29.8	32.8
87.5°	7.8	8.2	8.5	8.7	8.4	8.6	8.9	9.3	10.1	10.4	10.8
90°	9.7	9.8	8.4	7.1	5.7	4.4	3.2	2.5	1.7	1.0	0.3
92.5°	9.0	8.9	8.6	8.2	7.9	7.6	7.2	6.7	6.1	5.5	5.0
95°	17.9	17.9	17.8	17.7	17.5	17.4	17.0	16.4	15.8	15.2	14.6
97.5°	30.1	30.1	29.9	29.6	29.4	29.2	28.8	28.2	27.6	27.2	26.6
100°	38.7	38.7	38.4	38.3	38.0	37.9	37.5	37.1	36.5	36.0	35.6
102.5°	47.8	47.8	47.5	47.3	47.1	46.9	46.5	46.1	45.7	45.3	44.9
105°	61.7	61.6	61.5	61.3	61.2	61.1	60.9	60.8	60.5	60.4	60.2
107.5°	76.8	76.8	76.8	76.8	76.8	76.8	76.6	76.4	76.0	75.8	75.5
110°	87.1	87.1	87.1	87.1	87.1	87.1	86.8	86.5	86.1	85.7	85.4



TEST NUMBER: P331421-927

CATALOG NUMBER: SA2XXDIP-C1005D330U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	97.4	97.6	97.6	97.7	97.7	97.8	97.6	97.2	96.9	96.5	96.1
115°	113.0	113.0	113.2	113.3	113.4	113.6	113.4	113.0	112.7	112.3	111.9
117.5°	128.3	128.4	128.7	129.1	129.4	129.8	129.8	129.2	128.7	128.3	127.7
120°	138.2	138.2	138.8	139.3	139.7	140.2	140.2	139.7	139.3	138.8	138.2
122.5°	148.9	149.0	149.3	149.7	150.0	150.4	150.3	149.6	149.1	148.5	147.9
125°	164.4	164.5	164.8	164.9	165.1	165.3	165.1	164.5	164.0	163.4	162.9
127.5°	179.4	179.7	179.9	180.1	180.4	180.5	180.3	179.6	179.0	178.2	177.5
130°	189.6	189.7	189.9	190.0	190.1	190.3	189.9	189.1	188.3	187.5	186.7
132.5°	199.8	200.0	200.0	200.0	199.9	199.9	199.6	198.9	198.3	197.6	197.0
135°	214.3	214.4	214.3	214.1	214.0	213.9	213.5	212.8	212.1	211.4	210.7
137.5°	228.5	228.5	228.3	228.1	228.0	227.8	227.5	227.0	226.3	225.8	225.2
140°	237.9	237.9	237.6	237.3	236.9	236.6	236.2	235.7	235.1	234.6	234.0
142.5°	246.4	246.4	246.2	246.0	245.7	245.6	245.2	244.6	244.1	243.5	243.0
145°	259.5	259.4	259.0	258.7	258.3	257.9	257.5	257.1	256.7	256.3	255.8
147.5°	270.9	270.8	270.5	270.3	270.0	269.7	269.3	268.9	268.3	267.8	267.3
150°	278.1	277.9	277.7	277.4	277.2	276.9	276.6	276.2	275.8	275.5	275.1
152.5°	285.3	285.1	284.8	284.5	284.2	283.9	283.5	283.2	282.8	282.4	282.1
155°	294.5	294.1	294.0	293.7	293.6	293.4	293.2	293.0	292.9	292.6	292.5
157.5°	302.9	302.5	302.3	302.2	302.1	302.0	301.9	301.7	301.6	301.5	301.3
160°	307.9	307.6	307.5	307.4	307.4	307.4	307.2	307.1	307.0	306.9	306.7
162.5°	312.5	312.0	312.0	312.0	311.9	311.8	311.8	311.7	311.7	311.7	311.6
165°	318.4	317.9	317.9	317.9	317.9	317.9	318.0	318.1	318.1	318.1	318.2
167.5°	323.2	322.8	322.8	322.8	322.8	322.9	323.0	323.1	323.4	323.5	323.7
170°	325.9	325.5	325.6	325.6	325.7	325.7	325.9	326.1	326.2	326.5	326.6
172.5°	328.0	327.5	327.6	327.6	327.7	327.7	327.9	328.0	328.3	328.4	328.6
175°	330.1	329.7	329.8	329.9	330.1	330.2	330.3	330.5	330.7	330.9	331.1
177.5°	331.3	331.0	331.1	331.2	331.3	331.4	331.5	331.7	331.8	331.9	332.1
180°	331.7	331.7	331.7	331.7	331.7	331.7	331.7	331.7	331.7	331.7	331.7



TEST NUMBER: P331421-927
 CATALOG NUMBER: SA2XXDIP-C1005D330U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6
2.5°	1587.9	1590.3	1598.1	1605.9	1614.6	1617.1	1621.0	1617.6	1616.5	1625.8	1632.6
5°	1592.4	1603.3	1624.6	1644.0	1660.4	1671.9	1684.1	1688.9	1698.0	1710.8	1726.6
7.5°	1587.3	1608.5	1642.0	1670.2	1701.1	1723.3	1740.7	1755.5	1773.5	1797.6	1823.9
10°	1581.4	1610.0	1650.7	1685.3	1722.9	1751.4	1775.1	1798.2	1825.0	1858.3	1892.9
12.5°	1570.8	1604.6	1655.5	1696.5	1744.8	1772.8	1804.7	1854.6	1883.2	1929.7	1978.4
15°	1549.3	1586.9	1658.0	1708.3	1763.0	1816.4	1875.3	1922.6	1970.0	1997.3	2065.9
17.5°	1517.3	1572.6	1651.3	1710.1	1779.5	1863.6	1929.8	1983.5	2038.1	2082.4	2116.8
20°	1491.6	1551.7	1641.6	1712.0	1794.5	1885.0	1960.9	2015.5	2062.9	2099.9	2121.1
22.5°	1459.0	1534.7	1622.2	1704.7	1810.1	1899.6	1979.3	2022.4	2061.9	2080.0	2088.1
25°	1407.9	1498.9	1597.8	1698.7	1817.7	1912.3	1985.2	2011.3	2022.8	2005.3	1976.1
27.5°	1352.6	1454.1	1569.8	1687.2	1813.0	1904.1	1956.3	1952.2	1932.6	1875.7	1830.1
30°	1311.3	1423.0	1547.4	1675.5	1801.8	1890.5	1920.8	1890.5	1846.2	1782.4	1717.5
32.5°	1268.1	1383.7	1523.7	1659.1	1781.5	1859.4	1866.0	1813.8	1745.2	1672.7	1591.7
35°	1202.6	1327.7	1478.8	1622.2	1738.1	1787.2	1758.2	1665.9	1584.5	1485.6	1375.1
37.5°	1128.7	1266.8	1418.4	1568.1	1673.2	1686.0	1613.7	1516.5	1401.8	1285.5	1155.4
40°	1073.3	1219.6	1375.7	1526.9	1619.7	1606.4	1514.1	1407.2	1270.7	1128.5	1007.7
42.5°	1023.8	1170.1	1329.0	1477.3	1551.7	1515.0	1407.2	1276.1	1129.3	995.5	884.9
45°	937.9	1088.5	1251.3	1394.5	1437.0	1370.8	1228.1	1082.4	937.9	826.2	738.9
47.5°	854.7	1003.5	1164.7	1290.5	1305.6	1216.6	1060.7	910.8	786.6	695.6	633.9
50°	793.4	942.8	1102.5	1214.8	1209.9	1102.5	942.2	799.5	695.7	622.3	581.0
52.5°	738.6	879.6	1033.0	1135.1	1109.4	992.2	839.2	712.6	627.2	569.8	532.4
55°	653.2	783.8	929.5	1011.4	964.1	834.2	704.8	602.9	539.7	496.6	467.5
57.5°	568.5	690.9	815.6	866.1	813.7	693.8	586.0	512.0	464.5	432.6	413.7
60°	516.0	622.9	734.0	777.7	715.2	608.3	523.3	457.2	418.9	392.8	375.8
62.5°	463.6	559.3	664.0	687.9	630.7	540.3	465.0	410.0	378.6	355.4	339.4
65°	392.2	470.5	550.0	565.8	513.0	443.1	383.7	347.8	320.0	302.9	290.2
67.5°	321.6	384.5	440.8	453.6	407.3	358.9	315.9	284.7	265.8	251.7	240.9
70°	279.9	329.6	375.8	386.1	349.1	305.9	273.2	248.3	231.3	219.2	208.8
72.5°	235.7	277.2	315.5	322.5	292.2	259.4	232.4	212.9	197.8	190.0	180.2
75°	180.3	204.6	234.3	236.1	216.1	196.1	175.5	162.7	154.8	145.1	140.2
77.5°	127.2	146.3	163.3	166.6	154.7	141.1	129.5	119.5	112.8	108.3	103.8
80°	97.1	112.3	119.6	123.8	115.3	105.6	98.9	92.3	88.0	85.0	82.0
82.5°	69.5	78.8	85.6	88.9	84.3	78.4	71.8	68.0	64.7	62.2	61.1
85°	35.2	39.5	43.7	44.9	43.7	41.3	37.6	37.6	35.8	35.2	35.2
87.5°	12.4	14.4	14.6	16.2	15.4	15.7	16.0	15.8	15.5	15.1	14.6
90°	1.0	1.7	2.5	3.2	4.4	5.7	7.1	8.4	9.8	9.7	9.6
92.5°	5.5	6.1	6.7	7.2	7.6	7.9	8.2	8.6	8.9	9.0	9.0
95°	15.2	15.8	16.4	17.0	17.4	17.5	17.7	17.8	17.9	17.9	17.9
97.5°	27.2	27.6	28.2	28.8	29.2	29.4	29.6	29.9	30.1	30.1	30.1
100°	36.0	36.5	37.1	37.5	37.9	38.0	38.3	38.4	38.7	38.7	38.7
102.5°	45.3	45.7	46.1	46.5	46.9	47.1	47.3	47.5	47.8	47.8	47.9
105°	60.4	60.5	60.8	60.9	61.1	61.2	61.3	61.5	61.6	61.7	61.8
107.5°	75.8	76.0	76.4	76.6	76.8	76.8	76.8	76.8	76.8	76.8	76.8
110°	85.7	86.1	86.5	86.8	87.1	87.1	87.1	87.1	87.1	87.1	87.1



TEST NUMBER: P331421-927

CATALOG NUMBER: SA2XXDIP-C1005D330U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	96.5	96.9	97.2	97.6	97.8	97.7	97.7	97.6	97.6	97.4	97.3
115°	112.3	112.7	113.0	113.4	113.6	113.4	113.3	113.2	113.0	113.0	113.0
117.5°	128.3	128.7	129.2	129.8	129.8	129.4	129.1	128.7	128.4	128.3	128.1
120°	138.8	139.3	139.7	140.2	140.2	139.7	139.3	138.8	138.2	138.2	138.2
122.5°	148.5	149.1	149.6	150.3	150.4	150.0	149.7	149.3	149.0	148.9	148.7
125°	163.4	164.0	164.5	165.1	165.3	165.1	164.9	164.8	164.5	164.4	164.2
127.5°	178.2	179.0	179.6	180.3	180.5	180.4	180.1	179.9	179.7	179.4	179.3
130°	187.5	188.3	189.1	189.9	190.3	190.1	190.0	189.9	189.7	189.6	189.5
132.5°	197.6	198.3	198.9	199.6	199.9	199.9	200.0	200.0	200.0	199.8	199.5
135°	211.4	212.1	212.8	213.5	213.9	214.0	214.1	214.3	214.4	214.3	214.3
137.5°	225.8	226.3	227.0	227.5	227.8	228.0	228.1	228.3	228.5	228.5	228.4
140°	234.6	235.1	235.7	236.2	236.6	236.9	237.3	237.6	237.9	237.9	237.9
142.5°	243.5	244.1	244.6	245.2	245.6	245.7	246.0	246.2	246.4	246.4	246.5
145°	256.3	256.7	257.1	257.5	257.9	258.3	258.7	259.0	259.4	259.5	259.6
147.5°	267.8	268.3	268.9	269.3	269.7	270.0	270.3	270.5	270.8	270.9	271.0
150°	275.5	275.8	276.2	276.6	276.9	277.2	277.4	277.7	277.9	278.1	278.3
152.5°	282.4	282.8	283.2	283.5	283.9	284.2	284.5	284.8	285.1	285.3	285.6
155°	292.6	292.9	293.0	293.2	293.4	293.6	293.7	294.0	294.1	294.5	294.8
157.5°	301.5	301.6	301.7	301.9	302.0	302.1	302.2	302.3	302.5	302.9	303.2
160°	306.9	307.0	307.1	307.2	307.4	307.4	307.4	307.5	307.6	307.9	308.3
162.5°	311.7	311.7	311.7	311.8	311.8	311.9	312.0	312.0	312.0	312.5	312.9
165°	318.1	318.1	318.1	318.0	317.9	317.9	317.9	317.9	317.9	318.4	318.8
167.5°	323.5	323.4	323.1	323.0	322.9	322.8	322.8	322.8	322.8	323.2	323.7
170°	326.5	326.2	326.1	325.9	325.7	325.7	325.6	325.6	325.5	325.9	326.4
172.5°	328.4	328.3	328.0	327.9	327.7	327.7	327.6	327.6	327.5	328.0	328.4
175°	330.9	330.7	330.5	330.3	330.2	330.1	329.9	329.8	329.7	330.1	330.6
177.5°	331.9	331.8	331.7	331.5	331.4	331.3	331.2	331.1	331.0	331.3	331.6
180°	331.7	331.7	331.7	331.7	331.7	331.7	331.7	331.7	331.7	331.7	331.7



TEST NUMBER: P331421-927

CATALOG NUMBER: SA2XXDIP-C1005D330U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6
2.5°	1638.4	1645.2	1645.2	1646.2	1653.9	1653.0	1652.5
5°	1743.6	1753.9	1755.1	1766.0	1773.3	1770.8	1764.2
7.5°	1842.8	1861.9	1876.5	1884.7	1894.3	1900.2	1897.5
10°	1921.4	1949.4	1966.4	1977.9	1991.9	2002.2	1998.5
12.5°	1992.8	2026.1	2049.5	2069.2	2071.0	2084.2	2075.3
15°	2104.2	2139.4	2143.0	2157.6	2169.2	2167.9	2168.5
17.5°	2141.0	2152.3	2154.6	2154.9	2155.1	2150.8	2141.6
20°	2127.9	2123.6	2113.3	2105.4	2091.4	2089.6	2077.5
22.5°	2065.7	2052.2	2026.3	2009.2	1987.5	1981.8	1978.4
25°	1943.3	1913.5	1872.2	1832.8	1821.9	1800.6	1806.7
27.5°	1775.4	1729.0	1684.3	1652.3	1623.3	1591.4	1600.5
30°	1657.3	1605.1	1542.0	1493.4	1462.4	1432.1	1426.6
32.5°	1516.5	1440.0	1369.6	1326.8	1279.4	1260.2	1239.2
35°	1273.7	1199.0	1129.2	1069.1	1034.5	1007.7	983.5
37.5°	1055.3	969.3	912.9	864.3	839.2	823.9	827.8
40°	919.7	844.5	803.2	766.1	743.1	732.1	734.6
42.5°	810.0	753.6	719.6	694.3	678.0	671.9	670.5
45°	685.4	653.9	625.9	611.3	603.5	596.8	592.6
47.5°	600.4	574.6	558.9	550.2	543.4	536.5	536.4
50°	549.4	532.4	521.5	512.4	506.9	502.1	506.3
52.5°	510.6	495.0	484.1	475.9	473.9	469.5	469.4
55°	452.9	440.8	432.8	425.6	421.9	419.5	416.5
57.5°	400.4	388.9	381.6	377.0	370.1	367.7	366.7
60°	363.1	353.9	346.7	340.6	337.5	332.7	332.7
62.5°	328.5	319.5	312.7	308.0	303.1	301.1	301.6
65°	278.7	271.4	264.7	259.8	258.6	255.0	256.2
67.5°	232.7	227.9	220.9	218.2	215.9	214.0	212.5
70°	202.2	197.3	193.7	190.0	188.2	188.2	188.2
72.5°	176.4	170.6	168.4	163.8	164.9	163.0	161.0
75°	136.6	132.9	131.1	129.3	126.3	126.3	126.3
77.5°	100.5	99.4	97.3	95.3	94.6	94.0	94.2
80°	77.7	77.1	75.9	75.9	74.7	74.1	72.9
82.5°	59.7	58.1	57.4	57.0	56.7	56.6	56.3
85°	34.0	32.8	32.8	33.4	32.2	32.2	32.8
87.5°	15.0	15.0	14.5	14.5	15.0	14.5	14.5
90°	9.4	9.3	9.3	9.3	9.4	9.4	9.5
92.5°	9.0	9.0	9.0	9.0	9.0	9.0	9.0
95°	17.9	17.9	17.8	17.7	17.6	17.5	17.3
97.5°	30.1	30.1	30.1	30.1	30.1	30.1	30.0
100°	38.7	38.7	38.6	38.5	38.5	38.4	38.3
102.5°	47.9	48.0	48.0	47.9	47.8	47.8	47.8
105°	61.9	62.1	62.1	62.1	62.1	62.1	62.1
107.5°	76.9	76.9	76.8	76.5	76.3	76.0	75.7
110°	87.1	87.1	87.0	86.7	86.6	86.4	86.2



TEST NUMBER: P331421-927

CATALOG NUMBER: SA2XXDIP-C1005D330U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	97.1	97.0	96.8	96.7	96.6	96.4	96.3
115°	112.9	112.8	112.7	112.5	112.3	112.2	111.9
117.5°	127.9	127.8	127.6	127.5	127.3	127.1	126.9
120°	138.2	138.2	138.2	138.0	137.8	137.6	137.4
122.5°	148.5	148.4	148.3	148.1	148.0	147.8	147.7
125°	164.0	163.8	163.7	163.7	163.6	163.5	163.4
127.5°	179.0	178.8	178.6	178.4	178.2	178.0	177.8
130°	189.4	189.3	189.1	188.9	188.5	188.3	188.1
132.5°	199.2	199.0	198.8	198.5	198.4	198.1	198.0
135°	214.2	214.1	214.0	213.8	213.7	213.5	213.3
137.5°	228.3	228.3	228.1	227.9	227.7	227.4	227.1
140°	237.9	237.9	237.7	237.5	237.3	237.0	236.8
142.5°	246.5	246.6	246.5	246.3	246.0	245.7	245.5
145°	259.6	259.7	259.6	259.4	259.1	258.9	258.6
147.5°	271.2	271.3	271.2	271.0	270.8	270.5	270.3
150°	278.5	278.7	278.7	278.5	278.3	278.1	277.9
152.5°	285.8	286.1	286.1	285.8	285.6	285.3	285.1
155°	295.1	295.4	295.5	295.2	295.1	294.9	294.7
157.5°	303.7	304.1	304.2	303.9	303.6	303.3	303.0
160°	308.7	309.1	309.1	308.9	308.6	308.4	308.2
162.5°	313.3	313.8	313.8	313.5	313.2	312.9	312.6
165°	319.2	319.6	319.7	319.4	319.1	318.8	318.5
167.5°	324.1	324.6	324.6	324.3	323.9	323.6	323.3
170°	326.8	327.3	327.3	326.9	326.5	326.1	325.7
172.5°	328.8	329.2	329.3	328.9	328.5	328.2	327.8
175°	331.0	331.4	331.4	331.1	330.7	330.3	329.9
177.5°	331.8	332.2	332.2	331.8	331.6	331.3	331.0
180°	331.7	331.7	331.7	331.7	331.7	331.7	331.7

(END OF REPORT)