

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331428-927

Luminaire Tested: **SA2XXDIP-C1005D330U927-4F0-1E-UDD-F4**


Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331428-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXDIP-C1005D330U927-4F0-1E-UDD-F4  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 330 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4226.4 lumens  
Efficiency: N/A  
Efficacy: 84.9 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Direct  
  
Input Watts (W): 49.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331428-927  
CATALOG NUMBER: SA2XXDIP-C1005D330U927-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P331428-927

CATALOG NUMBER: SA2XXDIP-C1005D330U927-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	113	113	113	113	108	108	108	108	98	98	98	89	89	89	80	80	80	76
1	104	99	95	91	98	95	91	88	86	83	81	78	76	74	71	69	68	64
2	94	87	80	75	90	83	77	72	75	71	67	69	65	62	62	60	57	54
3	86	76	69	62	82	73	66	60	67	61	56	61	56	52	55	52	49	45
4	79	68	59	53	75	65	57	51	59	53	48	54	49	45	49	45	42	39
5	73	60	52	46	69	58	50	44	53	47	42	49	43	39	45	40	37	34
6	67	54	46	40	64	52	44	39	48	41	36	44	39	34	40	36	32	30
7	62	49	41	35	59	47	40	34	44	37	32	40	35	30	37	32	29	26
8	58	45	37	31	55	43	36	30	40	33	29	37	31	27	34	29	26	24
9	54	41	33	28	51	40	32	27	37	30	26	34	29	25	31	27	23	21
10	50	38	30	25	48	37	29	25	34	28	24	32	26	22	29	25	21	19

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	20386	20386	20386
5°	20464	20169	20285
10°	20341	19964	20064
15°	20090	19704	19686
20°	19734	19316	19295
25°	19379	18838	18838
30°	18921	18401	18243
35°	18496	17875	17611
40°	17962	17351	17015
45°	17438	16826	16411
50°	16865	16284	15707
55°	16268	15651	15071
60°	15603	14899	14347
65°	14888	14147	13498
70°	13983	13237	12609
75°	12726	12190	11890
80°	11288	10953	10386
85°	9207	8781	7873



TEST NUMBER: P331428-927

CATALOG NUMBER: SA2XXDIP-C1005D330U927-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	118.7	2.8
10°-20°	334.1	7.9
20°-30°	491.0	11.6
30°-40°	570.4	13.5
40°-50°	569.8	13.5
50°-60°	496.9	11.8
60°-70°	367.4	8.7
70°-80°	208.1	4.9
80°-90°	57.3	1.4
90°-100°	58.2	1.4
100°-110°	197.5	4.7
110°-120°	209.8	5.0
120°-130°	172.7	4.1
130°-140°	138.7	3.3
140°-150°	104.8	2.5
150°-160°	73.7	1.7
160°-170°	43.4	1.0
170°-180°	14.1	0.3
0°-30°	943.8	22.3
0°-40°	1514.2	35.8
0°-60°	2580.8	61.1
0°-90°	3213.6	76.0
90°-120°	465.5	11.0
90°-150°	881.7	20.9
90°-180°	1013.0	24.0
0°-180°	4226.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1263	1263	1263	1263	1263	
5°	1263	1257	1244	1253	1252	120
15°	1202	1194	1179	1183	1178	338
25°	1088	1078	1057	1060	1057	500
35°	938	926	907	900	894	586
45°	764	755	737	724	719	589
55°	578	570	556	542	535	517
65°	390	382	370	360	353	385
75°	204	201	195	189	191	218
85°	50	49	47	44	42	57
90°	0	4	10	9	9	3
95°	10	24	110	41	32	10
105°	34	52	207	371	315	36
115°	60	76	174	358	415	60
125°	84	99	167	290	337	75
135°	98	118	165	244	279	76
145°	112	129	164	204	223	71
155°	128	138	159	180	187	59
165°	139	144	153	162	164	39
175°	145	145	147	148	148	14
180°	146	146	146	146	146	



TEST NUMBER: P331428-927

CATALOG NUMBER: SA2XXDIP-C1005D330U927-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6
2.5°	1268.4	1267.3	1266.3	1265.2	1264.1	1262.4	1260.0	1257.7	1255.3	1252.9	1255.1
5°	1262.6	1261.6	1260.4	1259.3	1258.3	1256.2	1253.3	1250.3	1247.4	1244.4	1246.6
7.5°	1251.4	1249.7	1248.1	1246.4	1244.8	1242.4	1239.4	1236.4	1233.3	1230.3	1232.5
10°	1240.7	1238.9	1237.0	1235.1	1233.2	1230.7	1227.4	1224.2	1220.9	1217.7	1219.9
12.5°	1226.2	1224.5	1222.8	1221.1	1219.5	1217.0	1213.8	1210.5	1207.4	1204.1	1205.6
15°	1201.9	1200.3	1198.7	1197.1	1195.4	1192.9	1189.4	1185.8	1182.3	1178.8	1180.0
17.5°	1170.8	1169.2	1167.6	1165.9	1164.3	1161.7	1158.2	1154.6	1151.0	1147.6	1148.7
20°	1148.5	1146.8	1145.3	1143.6	1142.0	1139.3	1135.5	1131.8	1128.0	1124.2	1125.0
22.5°	1126.2	1123.9	1121.7	1119.4	1117.1	1114.2	1110.6	1107.1	1103.5	1099.9	1100.1
25°	1087.8	1085.6	1083.5	1081.3	1079.2	1075.8	1071.2	1066.6	1062.0	1057.4	1058.0
27.5°	1044.1	1042.1	1040.2	1038.2	1036.3	1033.6	1029.9	1026.3	1022.7	1019.1	1018.3
30°	1014.9	1012.8	1010.6	1008.4	1006.3	1003.2	999.2	995.1	991.1	987.0	986.2
32.5°	983.9	982.1	980.4	978.7	976.9	974.0	969.7	965.4	961.2	956.9	955.5
35°	938.4	935.7	933.0	930.3	927.6	924.2	919.8	915.5	911.2	906.9	905.3
37.5°	887.2	884.9	882.5	880.1	877.7	874.4	870.1	865.8	861.4	857.1	855.1
40°	852.2	850.1	848.0	845.8	843.6	840.4	836.1	831.8	827.4	823.2	820.7
42.5°	818.2	816.1	814.0	811.8	809.6	806.4	802.1	797.7	793.4	789.1	786.5
45°	763.7	761.8	759.9	758.0	756.1	753.1	749.1	745.0	741.0	736.9	734.0
47.5°	709.2	707.5	705.7	703.9	702.1	699.1	694.9	690.7	686.5	682.3	679.1
50°	671.4	670.0	668.7	667.3	666.0	663.4	659.7	655.8	652.0	648.3	644.5
52.5°	634.5	632.7	630.9	629.2	627.3	624.6	621.1	617.5	614.0	610.5	607.3
55°	577.9	576.2	574.6	573.1	571.4	568.9	565.8	562.5	559.3	556.0	552.8
57.5°	521.1	519.8	518.5	517.2	515.9	513.5	509.9	506.4	502.8	499.2	496.1
60°	483.2	482.1	481.0	480.0	478.9	476.4	472.7	468.9	465.1	461.4	458.4
62.5°	446.3	444.6	442.8	441.1	439.3	437.0	434.1	431.3	428.3	425.4	422.6
65°	389.7	388.1	386.5	384.8	383.3	381.0	378.3	375.7	373.0	370.3	367.9
67.5°	332.2	330.9	329.5	328.3	327.0	325.1	322.7	320.3	317.8	315.4	313.5
70°	296.2	295.2	294.1	293.0	291.9	290.2	287.7	285.3	282.9	280.4	278.5
72.5°	259.3	258.3	257.1	256.1	255.0	253.7	252.2	250.6	249.0	247.4	245.5
75°	204.0	203.4	202.9	202.3	201.8	200.8	199.5	198.1	196.8	195.4	193.8
77.5°	154.4	153.5	152.6	151.7	150.8	150.0	149.5	148.9	148.4	147.9	147.0
80°	121.4	121.1	120.9	120.6	120.3	119.9	119.4	118.8	118.3	117.8	116.9
82.5°	90.3	90.3	90.2	90.2	90.1	89.9	89.6	89.3	89.0	88.6	87.6
85°	49.7	49.5	49.3	49.0	48.7	48.4	48.2	47.8	47.6	47.4	46.5
87.5°	17.5	17.3	17.0	16.7	16.4	16.2	16.0	16.0	15.8	15.5	14.8
90°	0.3	1.1	2.2	2.8	3.3	4.2	5.6	7.5	9.3	9.5	9.3
92.5°	3.4	4.9	7.0	8.2	10.1	12.7	19.0	28.0	35.9	36.4	30.7
95°	9.8	10.9	13.7	16.2	20.7	27.4	40.3	64.6	97.1	109.7	96.0
97.5°	15.9	17.4	20.4	24.2	29.4	37.0	53.2	87.1	141.1	187.3	196.5
100°	21.5	22.4	24.9	29.4	35.0	42.9	57.7	91.8	152.3	221.1	261.4
102.5°	26.7	27.3	29.9	34.3	40.2	48.0	61.7	92.1	148.0	222.2	285.6
105°	34.1	35.3	37.2	41.4	47.6	55.5	68.6	93.5	139.7	207.4	281.9
107.5°	42.2	43.1	45.0	48.9	55.0	62.9	75.7	97.4	135.5	191.5	257.3
110°	47.6	48.7	50.4	54.0	59.9	68.0	80.3	100.4	134.7	183.9	241.9



TEST NUMBER: P331428-927

CATALOG NUMBER: SA2XXDIP-C1005D330U927-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	52.5	53.6	55.5	58.9	64.6	73.0	84.8	103.9	134.8	179.0	231.1
115°	60.2	61.6	63.3	66.6	72.2	79.8	91.8	108.8	136.0	173.6	217.8
117.5°	68.1	69.2	70.9	73.9	79.3	87.1	98.2	114.2	138.1	170.9	209.4
120°	73.0	74.1	75.9	78.3	84.0	91.8	102.7	117.9	139.4	169.4	204.9
122.5°	77.8	78.7	80.3	83.1	88.6	96.7	106.9	121.0	140.9	168.4	201.1
125°	84.0	84.8	86.5	89.8	95.5	103.3	113.4	126.0	143.3	166.8	195.7
127.5°	88.9	90.0	92.4	96.1	101.4	109.5	119.3	130.6	145.7	165.9	190.6
130°	91.8	92.9	95.7	99.7	105.3	113.0	122.9	133.5	147.5	165.4	187.3
132.5°	94.5	95.9	98.9	103.0	108.8	116.7	126.0	136.4	149.3	165.2	184.6
135°	98.5	99.7	103.0	107.2	113.7	121.4	130.5	140.2	151.5	164.9	180.8
137.5°	102.3	103.7	107.0	111.5	117.9	125.2	134.0	143.1	153.4	164.8	178.2
140°	105.3	106.4	109.7	114.2	120.3	127.6	136.0	144.7	154.2	164.6	176.6
142.5°	108.1	109.1	112.2	116.7	122.6	129.4	137.6	146.1	154.9	164.6	175.1
145°	112.5	113.7	116.5	120.6	126.3	132.4	140.0	147.8	155.6	164.0	173.0
147.5°	117.2	118.0	120.7	124.6	129.3	134.8	141.9	148.8	155.8	163.0	170.9
150°	120.3	121.2	123.4	127.1	131.3	136.3	142.8	149.2	155.6	162.3	169.1
152.5°	123.5	123.9	126.1	129.3	133.3	137.8	143.6	149.4	155.2	161.2	167.5
155°	127.9	128.2	129.8	132.9	136.0	140.2	145.0	149.7	154.5	159.2	164.6
157.5°	131.6	131.9	133.2	135.9	138.4	141.9	145.9	149.7	153.2	157.2	161.8
160°	134.0	134.4	135.5	137.7	140.0	143.1	146.4	149.7	152.6	155.9	159.8
162.5°	136.6	136.3	137.5	139.3	141.3	143.7	146.6	149.5	151.9	154.8	158.0
165°	139.4	139.1	139.7	141.3	142.8	144.4	146.9	148.9	150.6	152.6	155.0
167.5°	141.7	141.4	141.9	143.0	144.0	145.0	146.9	148.5	149.3	150.6	152.2
170°	143.3	142.8	143.1	143.9	144.4	145.3	146.6	148.1	148.6	149.5	150.6
172.5°	144.2	143.9	143.7	144.6	144.9	145.5	146.5	147.4	147.7	148.1	149.0
175°	145.3	145.0	144.7	145.3	145.3	145.5	146.1	146.6	146.4	146.6	146.9
177.5°	145.8	145.3	145.1	145.5	145.5	145.5	145.8	146.2	145.8	145.5	145.8
180°	145.5	145.5	145.5	145.5	145.5	145.5	145.5	145.5	145.5	145.5	145.5



TEST NUMBER: P331428-927

CATALOG NUMBER: SA2XXDIP-C1005D330U927-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6
2.5°	1257.2	1259.3	1261.6	1262.4	1261.9	1261.6	1261.1	1260.7
5°	1248.7	1250.9	1253.0	1253.9	1253.3	1252.8	1252.2	1251.6
7.5°	1234.6	1236.8	1239.0	1239.8	1239.1	1238.6	1237.9	1237.4
10°	1222.0	1224.2	1226.3	1227.0	1226.2	1225.3	1224.6	1223.8
12.5°	1207.1	1208.6	1210.1	1210.6	1210.0	1209.4	1208.8	1208.2
15°	1181.0	1182.1	1183.1	1183.0	1181.7	1180.4	1179.0	1177.7
17.5°	1150.0	1151.3	1152.5	1152.5	1151.1	1149.9	1148.6	1147.2
20°	1125.8	1126.6	1127.4	1127.3	1126.2	1125.1	1124.1	1123.0
22.5°	1100.3	1100.4	1100.6	1100.3	1099.7	1099.1	1098.4	1097.7
25°	1058.5	1059.1	1059.6	1059.6	1059.1	1058.5	1058.0	1057.4
27.5°	1017.5	1016.6	1015.8	1014.8	1013.5	1012.2	1010.9	1009.6
30°	985.4	984.6	983.8	982.9	981.8	980.6	979.6	978.5
32.5°	954.0	952.5	951.1	949.8	948.7	947.7	946.6	945.5
35°	903.6	902.1	900.4	899.0	897.6	896.3	894.8	893.5
37.5°	853.1	851.1	849.1	847.5	846.2	844.9	843.6	842.3
40°	818.2	815.9	813.4	811.7	810.6	809.5	808.4	807.3
42.5°	783.9	781.2	778.6	776.5	775.0	773.5	772.0	770.4
45°	731.0	728.0	725.1	723.0	721.9	720.9	719.8	718.7
47.5°	676.0	672.9	669.8	667.4	665.8	664.3	662.7	661.2
50°	640.7	637.0	633.2	630.7	629.3	628.0	626.6	625.3
52.5°	604.2	601.0	597.9	595.5	593.7	591.9	590.1	588.4
55°	549.5	546.3	543.1	540.8	539.5	538.1	536.8	535.4
57.5°	492.8	489.6	486.5	484.3	483.4	482.4	481.3	480.3
60°	455.4	452.4	449.5	447.6	446.8	446.0	445.1	444.3
62.5°	419.9	417.2	414.4	412.5	411.5	410.4	409.4	408.4
65°	365.4	363.0	360.6	358.7	357.4	356.0	354.7	353.3
67.5°	311.6	309.7	307.8	306.3	305.3	304.2	303.2	302.1
70°	276.6	274.8	272.9	271.4	270.3	269.3	268.2	267.1
72.5°	243.7	241.8	239.9	238.5	237.7	236.8	235.9	235.0
75°	192.3	190.6	189.0	188.5	189.0	189.5	190.0	190.6
77.5°	146.2	145.4	144.7	143.9	143.1	142.4	141.6	140.9
80°	116.1	115.3	114.5	113.8	113.3	112.8	112.3	111.7
82.5°	86.6	85.6	84.5	84.0	83.8	83.7	83.7	83.5
85°	45.7	44.9	44.1	43.6	43.3	43.0	42.8	42.5
87.5°	14.1	13.3	12.8	12.4	12.2	12.0	11.8	11.6
90°	9.0	8.4	9.0	9.3	9.3	9.3	9.3	9.3
92.5°	24.4	20.9	18.6	16.9	16.6	15.8	15.9	15.5
95°	73.4	56.2	44.5	38.3	34.7	32.5	31.6	31.9
97.5°	171.1	140.0	109.7	89.5	76.1	69.2	65.2	62.8
100°	255.6	220.9	182.5	148.6	125.4	113.4	105.3	100.2
102.5°	310.9	303.0	275.0	239.1	213.8	193.3	183.2	176.3
105°	340.1	371.7	375.3	366.1	348.7	331.4	319.3	315.4
107.5°	319.0	366.7	395.8	409.3	411.5	410.6	408.1	403.0
110°	300.9	351.0	386.8	409.8	421.8	427.1	429.7	429.4





TEST NUMBER: P331428-927

CATALOG NUMBER: SA2XXDIP-C1005D330U927-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	284.3	332.4	370.7	397.0	413.8	422.6	427.4	428.9
115°	264.0	307.0	343.7	372.6	392.4	405.3	412.6	415.1
117.5°	248.6	286.5	319.7	346.7	367.0	380.6	388.2	390.4
120°	241.0	275.7	305.4	330.8	350.5	363.6	371.7	374.5
122.5°	235.0	266.7	294.9	317.8	335.4	348.4	355.6	357.9
125°	226.2	255.0	279.6	300.6	316.9	327.5	334.5	336.8
127.5°	217.5	243.6	266.8	286.1	300.3	310.3	316.3	318.1
130°	211.9	236.0	258.1	276.6	290.3	299.8	305.4	307.6
132.5°	206.5	228.8	249.1	266.5	280.0	289.5	294.6	296.7
135°	199.0	217.5	236.0	251.6	263.6	272.9	278.0	279.1
137.5°	193.1	208.5	223.2	236.8	247.8	255.7	260.2	261.8
140°	189.2	202.6	215.6	227.8	236.8	244.1	248.3	249.9
142.5°	186.1	197.5	208.6	218.9	227.4	234.0	237.7	238.1
145°	181.6	190.9	199.6	207.7	214.4	219.2	222.0	222.8
147.5°	178.2	185.5	192.3	198.2	203.7	207.6	209.5	210.0
150°	175.8	182.0	187.8	192.8	197.0	200.4	202.1	202.4
152.5°	173.3	179.0	184.0	188.4	191.7	194.6	195.8	195.9
155°	169.9	174.4	178.6	181.6	184.7	186.7	187.8	187.3
157.5°	166.0	169.7	173.2	175.6	177.8	179.4	179.9	179.9
160°	163.4	166.5	169.6	171.6	173.6	174.9	175.2	175.2
162.5°	161.0	163.7	166.3	167.8	169.8	170.7	171.0	170.7
165°	157.3	159.2	161.2	162.3	163.4	164.6	164.6	164.3
167.5°	153.8	155.3	156.6	157.6	158.1	158.8	158.7	158.4
170°	152.0	152.8	153.9	154.5	154.8	155.6	155.3	154.8
172.5°	150.0	150.6	151.5	151.8	152.1	152.5	152.2	151.9
175°	147.8	148.1	148.4	148.6	148.6	148.9	148.6	148.1
177.5°	146.2	146.2	146.5	146.5	146.5	146.5	146.2	145.8
180°	145.5	145.5	145.5	145.5	145.5	145.5	145.5	145.5

(END OF REPORT)