

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331651-930

Luminaire Tested: **SA2XXRDIP-C485D530U930-4F0-1E-UDD-A**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331651-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C485D530U930-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 530 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3239.0 lumens
Efficiency: N/A
Efficacy: 98.8 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 32.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331651-930

CATALOG NUMBER: SA2XXRDIP-C485D530U930-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331651-930

CATALOG NUMBER: SA2XXRDIP-C485D530U930-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	53	53	53	47
1	98	94	90	87	90	86	83	81	73	70	68	60	58	57	48	47	46	41
2	90	83	77	72	82	76	71	67	64	61	58	53	51	49	43	42	40	35
3	82	73	67	61	75	68	62	57	58	53	50	48	45	42	39	37	35	31
4	76	66	58	52	69	61	54	49	52	47	43	43	40	37	35	33	31	27
5	70	59	51	46	64	55	48	43	47	42	38	39	36	33	32	30	28	24
6	65	53	45	40	59	49	43	38	42	37	33	36	32	29	30	27	25	22
7	60	48	41	35	55	45	38	33	39	34	30	33	29	26	27	25	22	20
8	56	44	37	32	51	41	35	30	36	30	27	30	26	23	25	23	20	18
9	52	40	33	28	48	38	31	27	33	28	24	28	24	21	24	21	19	16
10	49	37	30	26	45	35	29	24	30	25	22	26	22	20	22	19	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	14149	14149	14149	14149
5°	15801	14237	12624	14237
10°	17531	14137	10942	14137
15°	18392	13929	8622	13929
20°	15945	13622	7459	13622
25°	10457	13201	6661	13201
30°	7040	12693	6027	12693
35°	5702	12051	5436	12051
40°	5069	11352	5031	11352
45°	4590	10533	4491	10533
50°	4175	9718	4160	9718
55°	3924	8819	3873	8819
60°	3284	7992	3242	7992
65°	2770	7259	3140	7259
70°	2559	6482	2960	6482
75°	2395	5639	2739	5639
80°	2204	4640	2436	4640
85°	2019	3668	2149	3668



TEST NUMBER: P331651-930

CATALOG NUMBER: SA2XXRDIP-C485D530U930-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	83.1	2.6
10°-20°	231.5	7.1
20°-30°	298.2	9.2
30°-40°	283.4	8.8
40°-50°	242.8	7.5
50°-60°	184.9	5.7
60°-70°	116.9	3.6
70°-80°	58.4	1.8
80°-90°	16.6	0.5
90°-100°	19.6	0.6
100°-110°	71.9	2.2
110°-120°	192.3	5.9
120°-130°	317.4	9.8
130°-140°	337.5	10.4
140°-150°	313.7	9.7
150°-160°	252.2	7.8
160°-170°	162.5	5.0
170°-180°	55.9	1.7
0°-30°	612.8	18.9
0°-40°	896.2	27.7
0°-60°	1323.9	40.9
0°-90°	1515.8	46.8
90°-120°	283.8	8.8
90°-150°	1252.5	38.7
90°-180°	1723.0	53.2
0°-180°	3239.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	876	876	876	876	876	
5°	975	878	779	878	975	96
15°	1100	833	516	833	1100	297
25°	587	741	374	741	587	279
35°	289	611	276	611	289	185
45°	201	461	197	461	201	156
55°	139	313	138	313	139	122
65°	72	190	82	190	72	74
75°	38	90	44	90	38	41
85°	11	20	12	20	11	12
90°	12	0	12	0	12	6
95°	18	28	18	28	18	17
105°	32	129	32	129	32	34
115°	35	245	35	245	35	87
125°	364	346	364	346	364	315
135°	442	428	442	428	442	341
145°	504	496	504	496	504	315
155°	547	547	547	547	547	252
165°	575	576	575	576	575	162
175°	586	589	586	589	586	56
180°	588	588	588	588	588	



TEST NUMBER: P331651-930
 CATALOG NUMBER: SA2XXRDIP-C485D530U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3
2.5°	911.8	912.6	913.3	911.6	911.6	910.1	906.9	904.5	897.6	896.7	896.7
5°	974.9	974.3	975.5	971.5	966.0	964.8	959.0	951.5	943.5	934.7	932.9
7.5°	1037.6	1036.7	1034.3	1033.6	1029.4	1020.2	1010.9	1000.9	987.8	974.9	968.5
10°	1069.3	1079.3	1073.3	1062.6	1064.7	1050.4	1042.8	1029.7	1018.7	999.6	995.3
12.5°	1100.4	1104.4	1102.4	1096.4	1093.7	1083.8	1073.5	1062.1	1041.9	1024.7	1009.7
15°	1100.3	1106.1	1107.7	1105.8	1107.3	1106.7	1101.2	1091.8	1074.2	1055.2	1038.9
17.5°	1019.1	1023.1	1033.1	1039.8	1048.4	1066.4	1075.3	1078.8	1076.1	1065.4	1053.8
20°	928.0	921.3	949.3	963.6	975.8	1006.2	1032.4	1042.4	1058.6	1058.3	1055.2
22.5°	798.9	800.5	827.0	844.0	879.6	910.0	939.9	977.7	1008.9	1029.6	1041.6
25°	587.0	598.6	625.1	648.2	687.8	744.4	795.9	855.6	911.8	956.3	998.7
27.5°	440.8	441.7	462.7	484.1	507.6	554.0	618.8	690.1	770.4	836.6	912.8
30°	377.6	375.7	384.6	397.6	417.8	453.6	502.4	572.4	652.5	752.4	841.2
32.5°	332.7	332.8	339.5	349.2	365.8	390.0	423.5	480.3	556.0	654.2	758.4
35°	289.3	288.9	293.8	300.8	307.8	323.3	346.2	376.0	428.1	519.8	626.3
37.5°	258.0	259.4	261.8	266.2	273.9	282.5	296.3	316.3	353.4	407.6	497.1
40°	240.5	241.2	244.5	248.2	252.7	259.4	270.7	286.8	313.9	357.1	422.6
42.5°	224.5	225.0	227.5	230.8	234.4	241.2	250.5	264.4	286.4	320.1	374.1
45°	201.0	201.0	203.1	204.6	208.6	214.7	222.3	233.8	249.1	274.0	310.0
47.5°	178.9	179.0	180.3	183.0	185.5	190.2	197.7	207.2	218.3	237.6	268.2
50°	166.2	166.6	167.5	169.6	171.1	175.4	181.2	189.4	201.0	215.9	241.4
52.5°	156.0	155.8	156.9	157.9	158.9	162.0	166.3	173.6	183.9	196.9	218.1
55°	139.4	138.2	140.1	141.5	142.5	143.7	146.1	150.7	159.6	170.5	186.3
57.5°	118.7	118.2	119.5	120.9	123.8	127.1	129.1	132.1	136.6	144.5	160.2
60°	101.7	101.7	104.4	105.3	108.7	112.9	117.2	119.7	124.3	129.4	141.0
62.5°	86.6	86.8	88.1	89.0	90.9	96.1	102.2	107.5	111.8	116.8	124.4
65°	72.5	73.1	73.1	73.7	74.9	76.1	78.5	82.8	90.4	97.4	103.2
67.5°	61.5	61.7	61.9	62.5	62.8	64.1	65.1	67.0	68.7	75.4	82.6
70°	54.2	55.1	54.8	55.4	55.7	56.3	57.6	58.5	61.2	62.7	67.0
72.5°	47.4	48.0	48.0	48.3	49.2	49.2	50.2	51.1	52.9	54.2	56.5
75°	38.4	38.1	38.4	39.0	39.3	39.5	39.5	40.8	41.7	43.0	44.4
77.5°	29.6	29.9	29.8	29.9	29.9	30.5	30.4	31.0	31.9	32.5	33.3
80°	23.7	24.1	23.7	24.1	24.4	24.6	24.4	24.6	25.6	26.2	26.2
82.5°	18.4	18.4	18.7	18.7	18.8	18.8	19.2	19.3	20.0	19.8	20.1
85°	10.9	10.7	10.7	10.7	10.9	11.3	10.9	10.9	11.3	11.3	11.3
87.5°	6.2	6.4	6.4	6.4	6.3	6.2	6.1	6.3	6.0	6.1	5.7
90°	11.5	11.3	11.1	10.9	10.8	10.4	9.9	9.5	9.0	8.5	7.7
92.5°	11.5	11.4	11.3	11.2	11.0	10.8	10.6	10.4	10.1	9.9	9.5
95°	18.3	18.4	18.5	18.6	18.7	18.5	18.0	17.5	17.0	16.6	15.9
97.5°	24.5	24.3	24.2	24.1	24.0	23.7	23.3	23.0	22.6	22.2	20.7
100°	28.5	28.3	28.1	28.0	27.7	27.3	26.5	25.8	25.0	24.2	22.7
102.5°	30.6	30.2	30.0	29.8	29.5	28.9	27.9	26.9	25.9	24.9	38.4
105°	32.4	32.0	31.6	31.2	30.8	30.1	29.1	28.0	27.0	25.9	51.8
107.5°	33.3	32.9	32.5	32.1	31.8	32.1	33.2	34.2	35.3	36.4	67.3
110°	33.6	33.3	32.9	32.4	32.1	36.6	46.1	55.5	65.0	74.4	101.7



TEST NUMBER: P331651-930

CATALOG NUMBER: SA2XXRDIP-C485D530U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	33.9	33.7	33.3	33.0	32.8	49.8	84.3	118.8	153.3	187.8	194.5
115°	34.9	41.7	48.5	55.3	62.1	87.4	131.2	175.0	218.7	262.5	260.2
117.5°	142.4	164.9	187.2	209.5	232.0	248.4	259.0	269.6	280.2	290.7	289.2
120°	259.5	272.3	285.1	297.8	310.6	316.4	315.3	314.1	313.0	311.9	310.1
122.5°	323.8	326.4	328.8	331.3	333.8	334.7	334.0	333.3	332.6	332.0	330.1
125°	363.8	363.5	363.2	363.0	362.6	362.2	361.5	360.9	360.2	359.5	357.8
127.5°	389.0	388.9	388.9	388.8	388.7	388.2	387.3	386.3	385.3	384.4	383.0
130°	404.6	404.7	404.8	404.9	405.0	404.6	403.5	402.4	401.5	400.4	399.3
132.5°	420.0	420.0	420.1	420.2	420.3	420.0	419.1	418.2	417.3	416.4	415.3
135°	442.1	442.3	442.5	442.6	442.9	442.5	441.5	440.6	439.6	438.6	437.8
137.5°	462.3	462.6	462.8	463.2	463.5	463.3	462.3	461.4	460.5	459.5	458.5
140°	474.8	475.3	475.8	476.2	476.7	476.5	475.6	474.8	474.0	473.1	472.1
142.5°	487.1	487.5	488.0	488.5	489.0	488.9	488.0	487.3	486.5	485.8	484.5
145°	504.2	504.7	505.2	505.6	506.1	506.0	505.3	504.7	504.0	503.4	501.7
147.5°	519.3	519.7	520.1	520.5	520.8	520.8	520.3	519.8	519.3	518.9	517.2
150°	528.5	528.9	529.4	529.9	530.4	530.3	529.7	529.1	528.6	528.0	526.5
152.5°	536.3	536.9	537.5	538.2	538.7	538.8	538.3	537.7	537.1	536.5	535.1
155°	547.1	548.0	548.7	549.4	550.2	550.3	549.8	549.2	548.6	548.0	546.9
157.5°	557.1	557.8	558.6	559.3	560.1	560.1	559.5	558.8	558.2	557.6	556.8
160°	562.9	563.5	564.3	564.9	565.6	565.6	565.0	564.4	563.9	563.4	562.8
162.5°	567.7	568.5	569.3	570.1	571.0	571.0	570.4	569.7	569.1	568.4	567.9
165°	574.8	575.5	576.2	576.8	577.5	577.5	576.8	576.2	575.5	574.8	574.5
167.5°	579.4	580.2	581.1	581.9	582.8	582.9	582.2	581.5	580.8	580.2	579.9
170°	582.0	582.9	583.8	584.6	585.5	585.5	584.9	584.2	583.6	582.9	582.7
172.5°	584.1	585.0	585.8	586.7	587.5	587.6	586.9	586.3	585.6	585.0	584.7
175°	585.9	586.9	587.7	588.7	589.7	589.8	589.1	588.5	587.8	587.2	586.9
177.5°	587.0	587.7	588.3	589.1	589.7	589.8	589.3	588.7	588.2	587.7	587.6
180°	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0



TEST NUMBER: P331651-930

CATALOG NUMBER: SA2XXRDIP-C485D530U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3
2.5°	897.2	895.3	893.6	889.2	887.0	882.1	881.3	881.1	874.8	868.7	867.0
5°	928.0	923.2	915.8	907.3	898.5	889.3	883.2	878.4	866.2	854.6	847.9
7.5°	959.0	948.6	936.0	919.8	906.4	891.3	880.1	870.0	852.7	836.2	825.0
10°	982.2	965.2	948.4	926.2	908.8	891.8	876.0	862.3	842.8	820.8	805.3
12.5°	996.5	977.8	954.7	933.0	910.5	888.8	867.6	850.0	827.2	804.5	786.0
15°	1016.0	995.9	967.9	936.9	907.9	879.6	855.2	833.3	803.5	776.4	753.8
17.5°	1031.9	1004.2	974.1	938.2	904.7	868.8	837.4	809.3	776.2	743.5	717.0
20°	1037.0	1009.6	974.9	939.0	899.4	857.0	823.3	792.8	757.2	721.5	691.1
22.5°	1033.8	1012.5	973.9	930.9	890.4	846.1	808.0	772.6	733.1	696.8	661.5
25°	1012.4	1005.0	968.5	921.6	875.3	823.9	779.8	741.0	696.0	657.0	618.6
27.5°	962.2	978.0	955.4	905.4	853.9	798.7	749.2	705.2	658.4	614.5	576.3
30°	914.0	950.2	940.4	894.2	836.7	782.4	726.8	680.8	630.9	585.8	548.0
32.5°	848.0	907.8	917.4	878.6	819.1	759.5	701.2	655.4	603.3	555.8	519.0
35°	742.9	832.4	873.5	848.8	789.1	725.0	664.6	611.4	559.0	512.1	475.6
37.5°	617.5	739.4	808.0	809.7	754.9	688.1	622.5	569.6	515.9	469.9	430.4
40°	536.1	668.3	757.5	777.3	731.0	658.8	592.5	538.6	486.2	441.2	395.8
42.5°	463.1	594.8	704.4	738.8	702.1	630.4	563.8	507.4	456.5	413.8	367.5
45°	374.5	489.6	610.4	672.0	651.6	585.1	514.9	461.3	413.4	376.6	332.2
47.5°	315.9	397.1	514.0	597.2	596.8	536.2	467.1	415.7	371.4	336.9	300.8
50°	282.5	353.2	452.2	546.5	554.4	503.6	437.8	386.9	345.6	309.3	280.4
52.5°	252.6	310.8	399.7	490.2	512.7	468.7	405.0	358.0	317.8	284.5	259.7
55°	213.4	258.4	326.1	410.7	444.8	413.8	357.1	313.3	280.7	252.7	231.4
57.5°	180.5	214.3	268.6	336.7	376.4	356.9	310.2	274.6	246.7	221.4	204.6
60°	159.9	187.5	233.5	290.5	334.3	320.6	280.7	247.5	223.8	201.9	186.1
62.5°	140.4	164.2	203.6	249.8	290.0	284.3	251.8	223.9	203.1	183.1	169.7
65°	112.9	130.3	161.0	197.3	229.6	232.3	208.9	190.0	171.4	155.6	143.7
67.5°	89.9	101.3	122.9	153.4	177.7	186.3	171.9	157.5	142.8	130.5	120.3
70°	75.8	85.0	100.8	125.5	147.7	156.8	148.5	137.3	124.5	114.5	105.7
72.5°	61.5	70.4	82.0	100.1	119.2	129.1	126.2	118.1	107.7	99.4	91.1
75°	46.3	49.0	56.9	69.1	84.1	92.5	94.7	90.4	82.2	75.8	70.9
77.5°	34.2	35.9	39.6	46.1	55.8	63.3	66.5	66.0	60.3	56.7	52.1
80°	27.4	28.3	30.2	32.9	40.2	47.8	49.9	49.9	46.0	44.4	39.9
82.5°	20.8	21.5	22.6	24.1	27.6	34.2	36.5	37.0	34.5	32.5	28.9
85°	11.9	11.6	12.1	13.1	13.7	15.5	19.2	19.8	19.2	16.7	15.8
87.5°	5.5	5.6	5.5	5.1	5.1	5.1	6.1	7.2	6.4	5.9	5.5
90°	7.0	6.3	5.5	4.6	3.5	2.5	1.5	0.4	1.5	2.5	3.5
92.5°	9.1	8.7	8.4	8.2	8.3	8.4	8.5	8.6	8.5	8.4	8.3
95°	15.2	14.6	13.9	15.2	18.3	21.4	24.5	27.6	24.5	21.4	18.3
97.5°	19.2	17.6	16.1	19.7	28.5	37.3	46.1	54.9	46.1	37.3	28.5
100°	21.0	19.4	17.9	23.5	36.4	49.4	62.4	75.3	62.4	49.4	36.4
102.5°	51.9	65.3	78.7	86.8	89.5	92.3	95.1	97.8	95.1	92.3	89.5
105°	77.6	103.4	129.2	140.7	137.9	135.0	132.2	129.3	132.2	135.0	137.9
107.5°	98.2	129.2	160.1	174.5	172.2	169.9	167.6	165.3	167.6	169.9	172.2
110°	129.1	156.5	183.8	196.4	194.4	192.5	190.5	188.5	190.5	192.5	194.4



TEST NUMBER: P331651-930

CATALOG NUMBER: SA2XXRDIP-C485D530U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	201.3	208.1	214.8	217.3	215.6	213.8	212.1	210.3	212.1	213.8	215.6
115°	257.8	255.4	253.1	251.1	249.5	247.9	246.2	244.7	246.2	247.9	249.5
117.5°	287.6	285.9	284.3	282.6	280.8	279.0	277.2	275.4	277.2	279.0	280.8
120°	308.5	306.8	305.1	303.5	302.1	300.7	299.2	297.8	299.2	300.7	302.1
122.5°	328.2	326.4	324.6	322.9	321.4	319.9	318.4	316.9	318.4	319.9	321.4
125°	356.0	354.2	352.4	350.8	349.6	348.4	347.2	345.9	347.2	348.4	349.6
127.5°	381.7	380.3	379.0	377.6	376.3	375.0	373.6	372.2	373.6	375.0	376.3
130°	398.3	397.3	396.2	394.9	393.5	391.9	390.4	388.9	390.4	391.9	393.5
132.5°	414.3	413.3	412.2	411.1	409.8	408.5	407.2	405.9	407.2	408.5	409.8
135°	437.0	436.1	435.3	434.1	432.6	431.0	429.6	428.0	429.6	431.0	432.6
137.5°	457.6	456.6	455.7	454.6	453.6	452.5	451.4	450.5	451.4	452.5	453.6
140°	471.1	470.0	469.0	468.1	467.3	466.6	465.8	465.0	465.8	466.6	467.3
142.5°	483.3	482.2	480.9	480.0	479.3	478.7	478.0	477.3	478.0	478.7	479.3
145°	500.1	498.6	496.9	496.2	496.3	496.4	496.4	496.5	496.4	496.4	496.3
147.5°	515.7	514.0	512.5	511.8	512.3	512.6	512.9	513.3	512.9	512.6	512.3
150°	525.0	523.5	522.0	521.5	522.2	522.9	523.5	524.2	523.5	522.9	522.2
152.5°	533.7	532.2	530.8	530.4	531.2	531.9	532.6	533.4	532.6	531.9	531.2
155°	545.8	544.6	543.5	543.3	544.2	545.0	545.9	546.7	545.9	545.0	544.2
157.5°	556.0	555.1	554.4	554.3	555.1	555.8	556.5	557.2	556.5	555.8	555.1
160°	562.2	561.7	561.1	561.1	561.7	562.2	562.8	563.4	562.8	562.2	561.7
162.5°	567.4	567.0	566.5	566.6	567.0	567.6	568.2	568.8	568.2	567.6	567.0
165°	574.2	574.0	573.7	573.8	574.4	574.9	575.5	576.1	575.5	574.9	574.4
167.5°	579.7	579.4	579.1	579.3	579.8	580.4	581.0	581.6	581.0	580.4	579.8
170°	582.5	582.4	582.1	582.4	582.9	583.5	584.1	584.6	584.1	583.5	582.9
172.5°	584.6	584.4	584.2	584.4	585.0	585.5	586.1	586.7	586.1	585.5	585.0
175°	586.8	586.6	586.4	586.6	587.3	588.0	588.6	589.3	588.6	588.0	587.3
177.5°	587.5	587.4	587.3	587.6	588.2	588.6	589.2	589.7	589.2	588.6	588.2
180°	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0



TEST NUMBER: P331651-930

CATALOG NUMBER: SA2XXRDIP-C485D530U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3
2.5°	863.8	862.1	858.9	854.1	851.2	846.0	842.6	844.6	845.1	844.6	844.1
5°	840.7	834.2	825.4	816.8	808.9	800.5	795.6	793.4	789.1	786.8	785.5
7.5°	812.5	801.5	789.0	774.2	761.6	748.4	741.6	738.3	729.5	724.8	720.6
10°	791.6	774.2	761.7	742.2	730.4	713.1	701.2	701.5	689.6	682.9	678.0
12.5°	768.5	749.4	728.6	711.1	694.6	680.7	666.3	660.6	647.9	641.5	628.4
15°	730.1	707.8	686.0	662.2	645.5	623.9	603.2	577.9	557.5	539.8	534.9
17.5°	688.2	660.7	638.7	610.8	582.1	545.8	521.8	507.1	494.8	485.5	478.6
20°	659.5	631.4	608.1	566.0	527.3	502.6	485.0	473.8	461.0	450.9	445.4
22.5°	629.2	600.1	568.1	521.1	491.1	471.2	455.5	442.5	433.9	426.1	421.1
25°	586.4	554.4	501.7	469.4	445.2	424.4	413.4	405.5	396.4	385.7	380.9
27.5°	541.1	490.2	452.4	428.4	405.2	391.8	381.9	370.1	361.9	357.1	352.0
30°	507.2	456.4	426.9	400.6	384.3	369.3	357.8	351.1	343.2	334.9	331.6
32.5°	469.4	428.8	400.6	378.8	362.1	349.4	340.2	329.4	323.7	318.6	311.6
35°	422.6	391.8	366.0	348.3	332.5	322.1	311.4	305.1	294.7	290.5	287.7
37.5°	382.9	356.2	336.9	318.3	305.7	294.3	287.8	277.6	273.1	267.2	261.4
40°	360.4	334.3	315.8	300.5	286.5	277.9	269.8	261.5	254.9	252.1	245.1
42.5°	337.6	316.3	297.7	281.0	271.7	262.6	252.3	246.2	239.2	234.8	230.5
45°	306.0	287.1	271.3	257.6	247.2	237.8	231.1	221.0	217.1	208.2	204.6
47.5°	278.2	260.7	245.6	232.5	222.4	216.3	206.5	198.6	192.3	186.9	182.2
50°	258.4	243.9	229.3	217.7	208.6	199.7	189.7	185.7	175.9	173.3	170.5
52.5°	240.4	226.6	213.2	201.9	192.7	184.2	175.3	170.2	163.5	160.8	158.8
55°	215.2	201.9	189.1	179.0	169.9	161.0	155.6	149.2	146.1	144.0	141.5
57.5°	189.9	177.9	168.0	157.9	148.7	141.7	135.3	131.5	128.3	125.6	122.6
60°	173.8	162.2	153.4	144.0	134.6	128.8	123.9	119.4	115.7	111.5	110.2
62.5°	156.8	146.7	138.6	129.4	121.2	115.9	111.3	107.0	102.6	96.4	94.7
65°	133.4	125.5	116.9	109.3	102.0	96.9	90.1	85.3	83.4	82.8	82.5
67.5°	112.2	104.7	97.3	89.6	82.9	78.1	74.7	73.9	72.7	72.3	71.5
70°	98.0	91.1	83.7	76.4	70.0	69.1	67.9	66.7	65.1	64.6	63.9
72.5°	85.4	78.1	70.8	65.0	62.2	61.1	59.8	58.6	57.6	57.0	56.7
75°	65.5	58.8	53.9	51.8	50.2	49.3	47.5	46.6	46.0	45.1	44.8
77.5°	47.1	43.4	41.1	39.8	38.2	37.2	36.2	35.2	34.6	34.4	33.9
80°	36.0	34.1	32.6	30.7	30.2	28.9	28.6	27.7	28.0	27.1	27.1
82.5°	27.9	25.6	24.3	23.5	22.8	21.9	21.5	21.1	21.2	20.5	20.5
85°	14.3	13.7	13.1	12.5	12.5	11.6	11.9	11.6	11.6	10.9	10.7
87.5°	5.5	5.5	5.1	5.3	5.5	5.4	5.5	5.3	5.4	5.5	5.3
90°	4.6	5.5	6.3	7.0	7.7	8.5	9.0	9.5	9.9	10.4	10.8
92.5°	8.2	8.4	8.7	9.1	9.5	9.9	10.1	10.4	10.6	10.8	11.0
95°	15.2	13.9	14.6	15.2	15.9	16.6	17.0	17.5	18.0	18.5	18.7
97.5°	19.7	16.1	17.6	19.2	20.7	22.2	22.6	23.0	23.3	23.7	24.0
100°	23.5	17.9	19.4	21.0	22.7	24.2	25.0	25.8	26.5	27.3	27.7
102.5°	86.8	78.7	65.3	51.9	38.4	24.9	25.9	26.9	27.9	28.9	29.5
105°	140.7	129.2	103.4	77.6	51.8	25.9	27.0	28.0	29.1	30.1	30.8
107.5°	174.5	160.1	129.2	98.2	67.3	36.4	35.3	34.2	33.2	32.1	31.8
110°	196.4	183.8	156.5	129.1	101.7	74.4	65.0	55.5	46.1	36.6	32.1



TEST NUMBER: P331651-930

CATALOG NUMBER: SA2XXRDIP-C485D530U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	217.3	214.8	208.1	201.3	194.5	187.8	153.3	118.8	84.3	49.8	32.8
115°	251.1	253.1	255.4	257.8	260.2	262.5	218.7	175.0	131.2	87.4	62.1
117.5°	282.6	284.3	285.9	287.6	289.2	290.7	280.2	269.6	259.0	248.4	232.0
120°	303.5	305.1	306.8	308.5	310.1	311.9	313.0	314.1	315.3	316.4	310.6
122.5°	322.9	324.6	326.4	328.2	330.1	332.0	332.6	333.3	334.0	334.7	333.8
125°	350.8	352.4	354.2	356.0	357.8	359.5	360.2	360.9	361.5	362.2	362.6
127.5°	377.6	379.0	380.3	381.7	383.0	384.4	385.3	386.3	387.3	388.2	388.7
130°	394.9	396.2	397.3	398.3	399.3	400.4	401.5	402.4	403.5	404.6	405.0
132.5°	411.1	412.2	413.3	414.3	415.3	416.4	417.3	418.2	419.1	420.0	420.3
135°	434.1	435.3	436.1	437.0	437.8	438.6	439.6	440.6	441.5	442.5	442.9
137.5°	454.6	455.7	456.6	457.6	458.5	459.5	460.5	461.4	462.3	463.3	463.5
140°	468.1	469.0	470.0	471.1	472.1	473.1	474.0	474.8	475.6	476.5	476.7
142.5°	480.0	480.9	482.2	483.3	484.5	485.8	486.5	487.3	488.0	488.9	489.0
145°	496.2	496.9	498.6	500.1	501.7	503.4	504.0	504.7	505.3	506.0	506.1
147.5°	511.8	512.5	514.0	515.7	517.2	518.9	519.3	519.8	520.3	520.8	520.8
150°	521.5	522.0	523.5	525.0	526.5	528.0	528.6	529.1	529.7	530.3	530.4
152.5°	530.4	530.8	532.2	533.7	535.1	536.5	537.1	537.7	538.3	538.8	538.7
155°	543.3	543.5	544.6	545.8	546.9	548.0	548.6	549.2	549.8	550.3	550.2
157.5°	554.3	554.4	555.1	556.0	556.8	557.6	558.2	558.8	559.5	560.1	560.1
160°	561.1	561.1	561.7	562.2	562.8	563.4	563.9	564.4	565.0	565.6	565.6
162.5°	566.6	566.5	567.0	567.4	567.9	568.4	569.1	569.7	570.4	571.0	571.0
165°	573.8	573.7	574.0	574.2	574.5	574.8	575.5	576.2	576.8	577.5	577.5
167.5°	579.3	579.1	579.4	579.7	579.9	580.2	580.8	581.5	582.2	582.9	582.8
170°	582.4	582.1	582.4	582.5	582.7	582.9	583.6	584.2	584.9	585.5	585.5
172.5°	584.4	584.2	584.4	584.6	584.7	585.0	585.6	586.3	586.9	587.6	587.5
175°	586.6	586.4	586.6	586.8	586.9	587.2	587.8	588.5	589.1	589.8	589.7
177.5°	587.6	587.3	587.4	587.5	587.6	587.7	588.2	588.7	589.3	589.8	589.7
180°	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0



TEST NUMBER: P331651-930
 CATALOG NUMBER: SA2XXRDIP-C485D530U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3
2.5°	841.4	841.9	841.1	841.6	841.1	841.9	841.4	844.1	844.6	845.1	844.6
5°	784.0	780.3	779.8	778.9	779.8	780.3	784.0	785.5	786.8	789.1	793.4
7.5°	715.4	714.9	713.4	711.2	713.4	714.9	715.4	720.6	724.8	729.5	738.3
10°	671.3	669.8	669.5	667.4	669.5	669.8	671.3	678.0	682.9	689.6	701.5
12.5°	619.7	609.9	608.9	603.6	608.9	609.9	619.7	628.4	641.5	647.9	660.6
15°	527.7	525.8	519.8	515.8	519.8	525.8	527.7	534.9	539.8	557.5	577.9
17.5°	475.0	469.0	467.2	466.4	467.2	469.0	475.0	478.6	485.5	494.8	507.1
20°	441.2	435.7	434.8	434.1	434.8	435.7	441.2	445.4	450.9	461.0	473.8
22.5°	417.8	412.1	409.7	407.9	409.7	412.1	417.8	421.1	426.1	433.9	442.5
25°	377.8	375.7	374.5	373.9	374.5	375.7	377.8	380.9	385.7	396.4	405.5
27.5°	346.6	341.9	341.0	339.4	341.0	341.9	346.6	352.0	357.1	361.9	370.1
30°	328.8	327.3	325.1	323.3	325.1	327.3	328.8	331.6	334.9	343.2	351.1
32.5°	307.9	306.6	304.7	303.9	304.7	306.6	307.9	311.6	318.6	323.7	329.4
35°	284.7	280.4	278.6	275.8	278.6	280.4	284.7	287.7	290.5	294.7	305.1
37.5°	260.2	257.9	255.4	256.2	255.4	257.9	260.2	261.4	267.2	273.1	277.6
40°	241.2	239.6	239.0	238.7	239.0	239.6	241.2	245.1	252.1	254.9	261.5
42.5°	226.0	221.8	220.2	220.2	220.2	221.8	226.0	230.5	234.8	239.2	246.2
45°	203.1	199.1	196.4	196.7	196.4	199.1	203.1	204.6	208.2	217.1	221.0
47.5°	179.6	179.4	177.7	178.3	177.7	179.4	179.6	182.2	186.9	192.3	198.6
50°	168.4	166.6	165.3	165.6	165.3	166.6	168.4	170.5	173.3	175.9	185.7
52.5°	157.7	156.0	155.1	156.4	155.1	156.0	157.7	158.8	160.8	163.5	170.2
55°	140.1	138.2	137.9	137.6	137.9	138.2	140.1	141.5	144.0	146.1	149.2
57.5°	120.4	119.2	117.3	116.6	117.3	119.2	120.4	122.6	125.6	128.3	131.5
60°	106.2	103.8	100.8	100.4	100.8	103.8	106.2	110.2	111.5	115.7	119.4
62.5°	93.4	92.9	92.3	92.2	92.3	92.9	93.4	94.7	96.4	102.6	107.0
65°	81.9	81.6	81.9	82.2	81.9	81.6	81.9	82.5	82.8	83.4	85.3
67.5°	71.3	70.8	70.3	70.5	70.3	70.8	71.3	71.5	72.3	72.7	73.9
70°	63.3	63.0	62.7	62.7	62.7	63.0	63.3	63.9	64.6	65.1	66.7
72.5°	55.5	55.4	55.2	55.0	55.2	55.4	55.5	56.7	57.0	57.6	58.6
75°	44.4	43.9	43.9	43.9	43.9	43.9	44.4	44.8	45.1	46.0	46.6
77.5°	33.8	33.6	33.3	33.0	33.3	33.6	33.8	33.9	34.4	34.6	35.2
80°	26.8	26.5	26.2	26.2	26.2	26.5	26.8	27.1	27.1	28.0	27.7
82.5°	20.5	20.1	20.1	19.8	20.1	20.1	20.5	20.5	20.5	21.2	21.1
85°	10.9	11.3	10.9	11.6	10.9	11.3	10.9	10.7	10.9	11.6	11.6
87.5°	5.4	5.1	5.5	5.2	5.5	5.1	5.4	5.3	5.5	5.4	5.3
90°	10.9	11.1	11.3	11.5	11.3	11.1	10.9	10.8	10.4	9.9	9.5
92.5°	11.2	11.3	11.4	11.5	11.4	11.3	11.2	11.0	10.8	10.6	10.4
95°	18.6	18.5	18.4	18.3	18.4	18.5	18.6	18.7	18.5	18.0	17.5
97.5°	24.1	24.2	24.3	24.5	24.3	24.2	24.1	24.0	23.7	23.3	23.0
100°	28.0	28.1	28.3	28.5	28.3	28.1	28.0	27.7	27.3	26.5	25.8
102.5°	29.8	30.0	30.2	30.6	30.2	30.0	29.8	29.5	28.9	27.9	26.9
105°	31.2	31.6	32.0	32.4	32.0	31.6	31.2	30.8	30.1	29.1	28.0
107.5°	32.1	32.5	32.9	33.3	32.9	32.5	32.1	31.8	32.1	33.2	34.2
110°	32.4	32.9	33.3	33.6	33.3	32.9	32.4	32.1	36.6	46.1	55.5



TEST NUMBER: P331651-930

CATALOG NUMBER: SA2XXRDIP-C485D530U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	33.0	33.3	33.7	33.9	33.7	33.3	33.0	32.8	49.8	84.3	118.8
115°	55.3	48.5	41.7	34.9	41.7	48.5	55.3	62.1	87.4	131.2	175.0
117.5°	209.5	187.2	164.9	142.4	164.9	187.2	209.5	232.0	248.4	259.0	269.6
120°	297.8	285.1	272.3	259.5	272.3	285.1	297.8	310.6	316.4	315.3	314.1
122.5°	331.3	328.8	326.4	323.8	326.4	328.8	331.3	333.8	334.7	334.0	333.3
125°	363.0	363.2	363.5	363.8	363.5	363.2	363.0	362.6	362.2	361.5	360.9
127.5°	388.8	388.9	388.9	389.0	388.9	388.9	388.8	388.7	388.2	387.3	386.3
130°	404.9	404.8	404.7	404.6	404.7	404.8	404.9	405.0	404.6	403.5	402.4
132.5°	420.2	420.1	420.0	420.0	420.0	420.1	420.2	420.3	420.0	419.1	418.2
135°	442.6	442.5	442.3	442.1	442.3	442.5	442.6	442.9	442.5	441.5	440.6
137.5°	463.2	462.8	462.6	462.3	462.6	462.8	463.2	463.5	463.3	462.3	461.4
140°	476.2	475.8	475.3	474.8	475.3	475.8	476.2	476.7	476.5	475.6	474.8
142.5°	488.5	488.0	487.5	487.1	487.5	488.0	488.5	489.0	488.9	488.0	487.3
145°	505.6	505.2	504.7	504.2	504.7	505.2	505.6	506.1	506.0	505.3	504.7
147.5°	520.5	520.1	519.7	519.3	519.7	520.1	520.5	520.8	520.8	520.3	519.8
150°	529.9	529.4	528.9	528.5	528.9	529.4	529.9	530.4	530.3	529.7	529.1
152.5°	538.2	537.5	536.9	536.3	536.9	537.5	538.2	538.7	538.8	538.3	537.7
155°	549.4	548.7	548.0	547.1	548.0	548.7	549.4	550.2	550.3	549.8	549.2
157.5°	559.3	558.6	557.8	557.1	557.8	558.6	559.3	560.1	560.1	559.5	558.8
160°	564.9	564.3	563.5	562.9	563.5	564.3	564.9	565.6	565.6	565.0	564.4
162.5°	570.1	569.3	568.5	567.7	568.5	569.3	570.1	571.0	571.0	570.4	569.7
165°	576.8	576.2	575.5	574.8	575.5	576.2	576.8	577.5	577.5	576.8	576.2
167.5°	581.9	581.1	580.2	579.4	580.2	581.1	581.9	582.8	582.9	582.2	581.5
170°	584.6	583.8	582.9	582.0	582.9	583.8	584.6	585.5	585.5	584.9	584.2
172.5°	586.7	585.8	585.0	584.1	585.0	585.8	586.7	587.5	587.6	586.9	586.3
175°	588.7	587.7	586.9	585.9	586.9	587.7	588.7	589.7	589.8	589.1	588.5
177.5°	589.1	588.3	587.7	587.0	587.7	588.3	589.1	589.7	589.8	589.3	588.7
180°	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0



TEST NUMBER: P331651-930

CATALOG NUMBER: SA2XXRDIP-C485D530U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3
2.5°	842.6	846.0	851.2	854.1	858.9	862.1	863.8	867.0	868.7	874.8	881.1
5°	795.6	800.5	808.9	816.8	825.4	834.2	840.7	847.9	854.6	866.2	878.4
7.5°	741.6	748.4	761.6	774.2	789.0	801.5	812.5	825.0	836.2	852.7	870.0
10°	701.2	713.1	730.4	742.2	761.7	774.2	791.6	805.3	820.8	842.8	862.3
12.5°	666.3	680.7	694.6	711.1	728.6	749.4	768.5	786.0	804.5	827.2	850.0
15°	603.2	623.9	645.5	662.2	686.0	707.8	730.1	753.8	776.4	803.5	833.3
17.5°	521.8	545.8	582.1	610.8	638.7	660.7	688.2	717.0	743.5	776.2	809.3
20°	485.0	502.6	527.3	566.0	608.1	631.4	659.5	691.1	721.5	757.2	792.8
22.5°	455.5	471.2	491.1	521.1	568.1	600.1	629.2	661.5	696.8	733.1	772.6
25°	413.4	424.4	445.2	469.4	501.7	554.4	586.4	618.6	657.0	696.0	741.0
27.5°	381.9	391.8	405.2	428.4	452.4	490.2	541.1	576.3	614.5	658.4	705.2
30°	357.8	369.3	384.3	400.6	426.9	456.4	507.2	548.0	585.8	630.9	680.8
32.5°	340.2	349.4	362.1	378.8	400.6	428.8	469.4	519.0	555.8	603.3	655.4
35°	311.4	322.1	332.5	348.3	366.0	391.8	422.6	475.6	512.1	559.0	611.4
37.5°	287.8	294.3	305.7	318.3	336.9	356.2	382.9	430.4	469.9	515.9	569.6
40°	269.8	277.9	286.5	300.5	315.8	334.3	360.4	395.8	441.2	486.2	538.6
42.5°	252.3	262.6	271.7	281.0	297.7	316.3	337.6	367.5	413.8	456.5	507.4
45°	231.1	237.8	247.2	257.6	271.3	287.1	306.0	332.2	376.6	413.4	461.3
47.5°	206.5	216.3	222.4	232.5	245.6	260.7	278.2	300.8	336.9	371.4	415.7
50°	189.7	199.7	208.6	217.7	229.3	243.9	258.4	280.4	309.3	345.6	386.9
52.5°	175.3	184.2	192.7	201.9	213.2	226.6	240.4	259.7	284.5	317.8	358.0
55°	155.6	161.0	169.9	179.0	189.1	201.9	215.2	231.4	252.7	280.7	313.3
57.5°	135.3	141.7	148.7	157.9	168.0	177.9	189.9	204.6	221.4	246.7	274.6
60°	123.9	128.8	134.6	144.0	153.4	162.2	173.8	186.1	201.9	223.8	247.5
62.5°	111.3	115.9	121.2	129.4	138.6	146.7	156.8	169.7	183.1	203.1	223.9
65°	90.1	96.9	102.0	109.3	116.9	125.5	133.4	143.7	155.6	171.4	190.0
67.5°	74.7	78.1	82.9	89.6	97.3	104.7	112.2	120.3	130.5	142.8	157.5
70°	67.9	69.1	70.0	76.4	83.7	91.1	98.0	105.7	114.5	124.5	137.3
72.5°	59.8	61.1	62.2	65.0	70.8	78.1	85.4	91.1	99.4	107.7	118.1
75°	47.5	49.3	50.2	51.8	53.9	58.8	65.5	70.9	75.8	82.2	90.4
77.5°	36.2	37.2	38.2	39.8	41.1	43.4	47.1	52.1	56.7	60.3	66.0
80°	28.6	28.9	30.2	30.7	32.6	34.1	36.0	39.9	44.4	46.0	49.9
82.5°	21.5	21.9	22.8	23.5	24.3	25.6	27.9	28.9	32.5	34.5	37.0
85°	11.9	11.6	12.5	12.5	13.1	13.7	14.3	15.8	16.7	19.2	19.8
87.5°	5.5	5.4	5.5	5.3	5.1	5.5	5.5	5.5	5.9	6.4	7.2
90°	9.0	8.5	7.7	7.0	6.3	5.5	4.6	3.5	2.5	1.5	0.4
92.5°	10.1	9.9	9.5	9.1	8.7	8.4	8.2	8.3	8.4	8.5	8.6
95°	17.0	16.6	15.9	15.2	14.6	13.9	15.2	18.3	21.4	24.5	27.6
97.5°	22.6	22.2	20.7	19.2	17.6	16.1	19.7	28.5	37.3	46.1	54.9
100°	25.0	24.2	22.7	21.0	19.4	17.9	23.5	36.4	49.4	62.4	75.3
102.5°	25.9	24.9	38.4	51.9	65.3	78.7	86.8	89.5	92.3	95.1	97.8
105°	27.0	25.9	51.8	77.6	103.4	129.2	140.7	137.9	135.0	132.2	129.3
107.5°	35.3	36.4	67.3	98.2	129.2	160.1	174.5	172.2	169.9	167.6	165.3
110°	65.0	74.4	101.7	129.1	156.5	183.8	196.4	194.4	192.5	190.5	188.5



TEST NUMBER: P331651-930

CATALOG NUMBER: SA2XXRDIP-C485D530U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	153.3	187.8	194.5	201.3	208.1	214.8	217.3	215.6	213.8	212.1	210.3
115°	218.7	262.5	260.2	257.8	255.4	253.1	251.1	249.5	247.9	246.2	244.7
117.5°	280.2	290.7	289.2	287.6	285.9	284.3	282.6	280.8	279.0	277.2	275.4
120°	313.0	311.9	310.1	308.5	306.8	305.1	303.5	302.1	300.7	299.2	297.8
122.5°	332.6	332.0	330.1	328.2	326.4	324.6	322.9	321.4	319.9	318.4	316.9
125°	360.2	359.5	357.8	356.0	354.2	352.4	350.8	349.6	348.4	347.2	345.9
127.5°	385.3	384.4	383.0	381.7	380.3	379.0	377.6	376.3	375.0	373.6	372.2
130°	401.5	400.4	399.3	398.3	397.3	396.2	394.9	393.5	391.9	390.4	388.9
132.5°	417.3	416.4	415.3	414.3	413.3	412.2	411.1	409.8	408.5	407.2	405.9
135°	439.6	438.6	437.8	437.0	436.1	435.3	434.1	432.6	431.0	429.6	428.0
137.5°	460.5	459.5	458.5	457.6	456.6	455.7	454.6	453.6	452.5	451.4	450.5
140°	474.0	473.1	472.1	471.1	470.0	469.0	468.1	467.3	466.6	465.8	465.0
142.5°	486.5	485.8	484.5	483.3	482.2	480.9	480.0	479.3	478.7	478.0	477.3
145°	504.0	503.4	501.7	500.1	498.6	496.9	496.2	496.3	496.4	496.4	496.5
147.5°	519.3	518.9	517.2	515.7	514.0	512.5	511.8	512.3	512.6	512.9	513.3
150°	528.6	528.0	526.5	525.0	523.5	522.0	521.5	522.2	522.9	523.5	524.2
152.5°	537.1	536.5	535.1	533.7	532.2	530.8	530.4	531.2	531.9	532.6	533.4
155°	548.6	548.0	546.9	545.8	544.6	543.5	543.3	544.2	545.0	545.9	546.7
157.5°	558.2	557.6	556.8	556.0	555.1	554.4	554.3	555.1	555.8	556.5	557.2
160°	563.9	563.4	562.8	562.2	561.7	561.1	561.1	561.7	562.2	562.8	563.4
162.5°	569.1	568.4	567.9	567.4	567.0	566.5	566.6	567.0	567.6	568.2	568.8
165°	575.5	574.8	574.5	574.2	574.0	573.7	573.8	574.4	574.9	575.5	576.1
167.5°	580.8	580.2	579.9	579.7	579.4	579.1	579.3	579.8	580.4	581.0	581.6
170°	583.6	582.9	582.7	582.5	582.4	582.1	582.4	582.9	583.5	584.1	584.6
172.5°	585.6	585.0	584.7	584.6	584.4	584.2	584.4	585.0	585.5	586.1	586.7
175°	587.8	587.2	586.9	586.8	586.6	586.4	586.6	587.3	588.0	588.6	589.3
177.5°	588.2	587.7	587.6	587.5	587.4	587.3	587.6	588.2	588.6	589.2	589.7
180°	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0



TEST NUMBER: P331651-930

CATALOG NUMBER: SA2XXRDIP-C485D530U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3
2.5°	881.3	882.1	887.0	889.2	893.6	895.3	897.2	896.7	896.7	897.6	904.5
5°	883.2	889.3	898.5	907.3	915.8	923.2	928.0	932.9	934.7	943.5	951.5
7.5°	880.1	891.3	906.4	919.8	936.0	948.6	959.0	968.5	974.9	987.8	1000.9
10°	876.0	891.8	908.8	926.2	948.4	965.2	982.2	995.3	999.6	1018.7	1029.7
12.5°	867.6	888.8	910.5	933.0	954.7	977.8	996.5	1009.7	1024.7	1041.9	1062.1
15°	855.2	879.6	907.9	936.9	967.9	995.9	1016.0	1038.9	1055.2	1074.2	1091.8
17.5°	837.4	868.8	904.7	938.2	974.1	1004.2	1031.9	1053.8	1065.4	1076.1	1078.8
20°	823.3	857.0	899.4	939.0	974.9	1009.6	1037.0	1055.2	1058.3	1058.6	1042.4
22.5°	808.0	846.1	890.4	930.9	973.9	1012.5	1033.8	1041.6	1029.6	1008.9	977.7
25°	779.8	823.9	875.3	921.6	968.5	1005.0	1012.4	998.7	956.3	911.8	855.6
27.5°	749.2	798.7	853.9	905.4	955.4	978.0	962.2	912.8	836.6	770.4	690.1
30°	726.8	782.4	836.7	894.2	940.4	950.2	914.0	841.2	752.4	652.5	572.4
32.5°	701.2	759.5	819.1	878.6	917.4	907.8	848.0	758.4	654.2	556.0	480.3
35°	664.6	725.0	789.1	848.8	873.5	832.4	742.9	626.3	519.8	428.1	376.0
37.5°	622.5	688.1	754.9	809.7	808.0	739.4	617.5	497.1	407.6	353.4	316.3
40°	592.5	658.8	731.0	777.3	757.5	668.3	536.1	422.6	357.1	313.9	286.8
42.5°	563.8	630.4	702.1	738.8	704.4	594.8	463.1	374.1	320.1	286.4	264.4
45°	514.9	585.1	651.6	672.0	610.4	489.6	374.5	310.0	274.0	249.1	233.8
47.5°	467.1	536.2	596.8	597.2	514.0	397.1	315.9	268.2	237.6	218.3	207.2
50°	437.8	503.6	554.4	546.5	452.2	353.2	282.5	241.4	215.9	201.0	189.4
52.5°	405.0	468.7	512.7	490.2	399.7	310.8	252.6	218.1	196.9	183.9	173.6
55°	357.1	413.8	444.8	410.7	326.1	258.4	213.4	186.3	170.5	159.6	150.7
57.5°	310.2	356.9	376.4	336.7	268.6	214.3	180.5	160.2	144.5	136.6	132.1
60°	280.7	320.6	334.3	290.5	233.5	187.5	159.9	141.0	129.4	124.3	119.7
62.5°	251.8	284.3	290.0	249.8	203.6	164.2	140.4	124.4	116.8	111.8	107.5
65°	208.9	232.3	229.6	197.3	161.0	130.3	112.9	103.2	97.4	90.4	82.8
67.5°	171.9	186.3	177.7	153.4	122.9	101.3	89.9	82.6	75.4	68.7	67.0
70°	148.5	156.8	147.7	125.5	100.8	85.0	75.8	67.0	62.7	61.2	58.5
72.5°	126.2	129.1	119.2	100.1	82.0	70.4	61.5	56.5	54.2	52.9	51.1
75°	94.7	92.5	84.1	69.1	56.9	49.0	46.3	44.4	43.0	41.7	40.8
77.5°	66.5	63.3	55.8	46.1	39.6	35.9	34.2	33.3	32.5	31.9	31.0
80°	49.9	47.8	40.2	32.9	30.2	28.3	27.4	26.2	26.2	25.6	24.6
82.5°	36.5	34.2	27.6	24.1	22.6	21.5	20.8	20.1	19.8	20.0	19.3
85°	19.2	15.5	13.7	13.1	12.1	11.6	11.9	11.3	11.3	11.3	10.9
87.5°	6.1	5.1	5.1	5.1	5.5	5.6	5.5	5.7	6.1	6.0	6.3
90°	1.5	2.5	3.5	4.6	5.5	6.3	7.0	7.7	8.5	9.0	9.5
92.5°	8.5	8.4	8.3	8.2	8.4	8.7	9.1	9.5	9.9	10.1	10.4
95°	24.5	21.4	18.3	15.2	13.9	14.6	15.2	15.9	16.6	17.0	17.5
97.5°	46.1	37.3	28.5	19.7	16.1	17.6	19.2	20.7	22.2	22.6	23.0
100°	62.4	49.4	36.4	23.5	17.9	19.4	21.0	22.7	24.2	25.0	25.8
102.5°	95.1	92.3	89.5	86.8	78.7	65.3	51.9	38.4	24.9	25.9	26.9
105°	132.2	135.0	137.9	140.7	129.2	103.4	77.6	51.8	25.9	27.0	28.0
107.5°	167.6	169.9	172.2	174.5	160.1	129.2	98.2	67.3	36.4	35.3	34.2
110°	190.5	192.5	194.4	196.4	183.8	156.5	129.1	101.7	74.4	65.0	55.5



TEST NUMBER: P331651-930

CATALOG NUMBER: SA2XXRDIP-C485D530U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	212.1	213.8	215.6	217.3	214.8	208.1	201.3	194.5	187.8	153.3	118.8
115°	246.2	247.9	249.5	251.1	253.1	255.4	257.8	260.2	262.5	218.7	175.0
117.5°	277.2	279.0	280.8	282.6	284.3	285.9	287.6	289.2	290.7	280.2	269.6
120°	299.2	300.7	302.1	303.5	305.1	306.8	308.5	310.1	311.9	313.0	314.1
122.5°	318.4	319.9	321.4	322.9	324.6	326.4	328.2	330.1	332.0	332.6	333.3
125°	347.2	348.4	349.6	350.8	352.4	354.2	356.0	357.8	359.5	360.2	360.9
127.5°	373.6	375.0	376.3	377.6	379.0	380.3	381.7	383.0	384.4	385.3	386.3
130°	390.4	391.9	393.5	394.9	396.2	397.3	398.3	399.3	400.4	401.5	402.4
132.5°	407.2	408.5	409.8	411.1	412.2	413.3	414.3	415.3	416.4	417.3	418.2
135°	429.6	431.0	432.6	434.1	435.3	436.1	437.0	437.8	438.6	439.6	440.6
137.5°	451.4	452.5	453.6	454.6	455.7	456.6	457.6	458.5	459.5	460.5	461.4
140°	465.8	466.6	467.3	468.1	469.0	470.0	471.1	472.1	473.1	474.0	474.8
142.5°	478.0	478.7	479.3	480.0	480.9	482.2	483.3	484.5	485.8	486.5	487.3
145°	496.4	496.4	496.3	496.2	496.9	498.6	500.1	501.7	503.4	504.0	504.7
147.5°	512.9	512.6	512.3	511.8	512.5	514.0	515.7	517.2	518.9	519.3	519.8
150°	523.5	522.9	522.2	521.5	522.0	523.5	525.0	526.5	528.0	528.6	529.1
152.5°	532.6	531.9	531.2	530.4	530.8	532.2	533.7	535.1	536.5	537.1	537.7
155°	545.9	545.0	544.2	543.3	543.5	544.6	545.8	546.9	548.0	548.6	549.2
157.5°	556.5	555.8	555.1	554.3	554.4	555.1	556.0	556.8	557.6	558.2	558.8
160°	562.8	562.2	561.7	561.1	561.1	561.7	562.2	562.8	563.4	563.9	564.4
162.5°	568.2	567.6	567.0	566.6	566.5	567.0	567.4	567.9	568.4	569.1	569.7
165°	575.5	574.9	574.4	573.8	573.7	574.0	574.2	574.5	574.8	575.5	576.2
167.5°	581.0	580.4	579.8	579.3	579.1	579.4	579.7	579.9	580.2	580.8	581.5
170°	584.1	583.5	582.9	582.4	582.1	582.4	582.5	582.7	582.9	583.6	584.2
172.5°	586.1	585.5	585.0	584.4	584.2	584.4	584.6	584.7	585.0	585.6	586.3
175°	588.6	588.0	587.3	586.6	586.4	586.6	586.8	586.9	587.2	587.8	588.5
177.5°	589.2	588.6	588.2	587.6	587.3	587.4	587.5	587.6	587.7	588.2	588.7
180°	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0



TEST NUMBER: P331651-930

CATALOG NUMBER: SA2XXRDIP-C485D530U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	876.3	876.3	876.3	876.3	876.3	876.3	876.3
2.5°	906.9	910.1	911.6	911.6	913.3	912.6	911.8
5°	959.0	964.8	966.0	971.5	975.5	974.3	974.9
7.5°	1010.9	1020.2	1029.4	1033.6	1034.3	1036.7	1037.6
10°	1042.8	1050.4	1064.7	1062.6	1073.3	1079.3	1069.3
12.5°	1073.5	1083.8	1093.7	1096.4	1102.4	1104.4	1100.4
15°	1101.2	1106.7	1107.3	1105.8	1107.7	1106.1	1100.3
17.5°	1075.3	1066.4	1048.4	1039.8	1033.1	1023.1	1019.1
20°	1032.4	1006.2	975.8	963.6	949.3	921.3	928.0
22.5°	939.9	910.0	879.6	844.0	827.0	800.5	798.9
25°	795.9	744.4	687.8	648.2	625.1	598.6	587.0
27.5°	618.8	554.0	507.6	484.1	462.7	441.7	440.8
30°	502.4	453.6	417.8	397.6	384.6	375.7	377.6
32.5°	423.5	390.0	365.8	349.2	339.5	332.8	332.7
35°	346.2	323.3	307.8	300.8	293.8	288.9	289.3
37.5°	296.3	282.5	273.9	266.2	261.8	259.4	258.0
40°	270.7	259.4	252.7	248.2	244.5	241.2	240.5
42.5°	250.5	241.2	234.4	230.8	227.5	225.0	224.5
45°	222.3	214.7	208.6	204.6	203.1	201.0	201.0
47.5°	197.7	190.2	185.5	183.0	180.3	179.0	178.9
50°	181.2	175.4	171.1	169.6	167.5	166.6	166.2
52.5°	166.3	162.0	158.9	157.9	156.9	155.8	156.0
55°	146.1	143.7	142.5	141.5	140.1	138.2	139.4
57.5°	129.1	127.1	123.8	120.9	119.5	118.2	118.7
60°	117.2	112.9	108.7	105.3	104.4	101.7	101.7
62.5°	102.2	96.1	90.9	89.0	88.1	86.8	86.6
65°	78.5	76.1	74.9	73.7	73.1	73.1	72.5
67.5°	65.1	64.1	62.8	62.5	61.9	61.7	61.5
70°	57.6	56.3	55.7	55.4	54.8	55.1	54.2
72.5°	50.2	49.2	49.2	48.3	48.0	48.0	47.4
75°	39.5	39.5	39.3	39.0	38.4	38.1	38.4
77.5°	30.4	30.5	29.9	29.9	29.8	29.9	29.6
80°	24.4	24.6	24.4	24.1	23.7	24.1	23.7
82.5°	19.2	18.8	18.8	18.7	18.7	18.4	18.4
85°	10.9	11.3	10.9	10.7	10.7	10.7	10.9
87.5°	6.1	6.2	6.3	6.4	6.4	6.4	6.2
90°	9.9	10.4	10.8	10.9	11.1	11.3	11.5
92.5°	10.6	10.8	11.0	11.2	11.3	11.4	11.5
95°	18.0	18.5	18.7	18.6	18.5	18.4	18.3
97.5°	23.3	23.7	24.0	24.1	24.2	24.3	24.5
100°	26.5	27.3	27.7	28.0	28.1	28.3	28.5
102.5°	27.9	28.9	29.5	29.8	30.0	30.2	30.6
105°	29.1	30.1	30.8	31.2	31.6	32.0	32.4
107.5°	33.2	32.1	31.8	32.1	32.5	32.9	33.3
110°	46.1	36.6	32.1	32.4	32.9	33.3	33.6



TEST NUMBER: P331651-930

CATALOG NUMBER: SA2XXRDIP-C485D530U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	84.3	49.8	32.8	33.0	33.3	33.7	33.9
115°	131.2	87.4	62.1	55.3	48.5	41.7	34.9
117.5°	259.0	248.4	232.0	209.5	187.2	164.9	142.4
120°	315.3	316.4	310.6	297.8	285.1	272.3	259.5
122.5°	334.0	334.7	333.8	331.3	328.8	326.4	323.8
125°	361.5	362.2	362.6	363.0	363.2	363.5	363.8
127.5°	387.3	388.2	388.7	388.8	388.9	388.9	389.0
130°	403.5	404.6	405.0	404.9	404.8	404.7	404.6
132.5°	419.1	420.0	420.3	420.2	420.1	420.0	420.0
135°	441.5	442.5	442.9	442.6	442.5	442.3	442.1
137.5°	462.3	463.3	463.5	463.2	462.8	462.6	462.3
140°	475.6	476.5	476.7	476.2	475.8	475.3	474.8
142.5°	488.0	488.9	489.0	488.5	488.0	487.5	487.1
145°	505.3	506.0	506.1	505.6	505.2	504.7	504.2
147.5°	520.3	520.8	520.8	520.5	520.1	519.7	519.3
150°	529.7	530.3	530.4	529.9	529.4	528.9	528.5
152.5°	538.3	538.8	538.7	538.2	537.5	536.9	536.3
155°	549.8	550.3	550.2	549.4	548.7	548.0	547.1
157.5°	559.5	560.1	560.1	559.3	558.6	557.8	557.1
160°	565.0	565.6	565.6	564.9	564.3	563.5	562.9
162.5°	570.4	571.0	571.0	570.1	569.3	568.5	567.7
165°	576.8	577.5	577.5	576.8	576.2	575.5	574.8
167.5°	582.2	582.9	582.8	581.9	581.1	580.2	579.4
170°	584.9	585.5	585.5	584.6	583.8	582.9	582.0
172.5°	586.9	587.6	587.5	586.7	585.8	585.0	584.1
175°	589.1	589.8	589.7	588.7	587.7	586.9	585.9
177.5°	589.3	589.8	589.7	589.1	588.3	587.7	587.0
180°	588.0	588.0	588.0	588.0	588.0	588.0	588.0

(END OF REPORT)