

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331657-930

Luminaire Tested: **SA2XXRDIP-C485D725U930-4F0-1E-UDD-A**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331657-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C485D725U930-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 725 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3878.4 lumens
Efficiency: N/A
Efficacy: 101.0 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 38.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331657-930
CATALOG NUMBER: SA2XXRDIP-C485D725U930-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331657-930

CATALOG NUMBER: SA2XXRDIP-C485D725U930-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46	39				
1	96	92	88	85	87	84	81	78	69	66	65	55	53	52	42	41	40	34				
2	88	81	75	70	80	74	69	65	61	57	54	49	46	44	37	36	35	30				
3	81	72	65	59	73	66	60	55	54	50	47	44	41	38	34	32	30	26				
4	74	64	57	51	67	59	52	47	49	44	40	39	36	33	31	28	27	23				
5	68	57	50	44	62	53	46	41	44	39	35	36	32	29	28	26	24	20				
6	63	52	44	38	57	47	41	36	40	35	31	32	29	26	26	23	21	18				
7	58	47	39	34	53	43	37	32	36	31	28	30	26	23	24	21	19	17				
8	54	43	35	30	49	39	33	28	33	28	25	27	24	21	22	19	17	15				
9	51	39	32	27	46	36	30	25	31	26	22	25	22	19	20	18	16	14				
10	47	36	29	24	43	33	27	23	28	23	20	23	20	17	19	16	15	13				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	14149	14149	14149	14149
5°	15801	14237	12624	14237
10°	17531	14137	10942	14137
15°	18392	13929	8622	13929
20°	15945	13622	7459	13622
25°	10457	13201	6661	13201
30°	7040	12693	6027	12693
35°	5702	12051	5436	12051
40°	5069	11352	5031	11352
45°	4590	10533	4491	10533
50°	4175	9718	4160	9718
55°	3924	8819	3873	8819
60°	3284	7992	3242	7992
65°	2770	7259	3140	7259
70°	2559	6482	2960	6482
75°	2395	5639	2739	5639
80°	2204	4640	2436	4640
85°	2019	3668	2149	3668



TEST NUMBER: P331657-930

CATALOG NUMBER: SA2XXRDIP-C485D725U930-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	83.1	2.1
10°-20°	231.5	6.0
20°-30°	298.2	7.7
30°-40°	283.4	7.3
40°-50°	242.8	6.3
50°-60°	184.9	4.8
60°-70°	116.9	3.0
70°-80°	58.4	1.5
80°-90°	17.2	0.4
90°-100°	26.9	0.7
100°-110°	98.6	2.5
110°-120°	263.5	6.8
120°-130°	435.0	11.2
130°-140°	462.7	11.9
140°-150°	430.0	11.1
150°-160°	345.7	8.9
160°-170°	222.8	5.7
170°-180°	76.7	2.0
0°-30°	612.8	15.8
0°-40°	896.2	23.1
0°-60°	1323.9	34.1
0°-90°	1516.3	39.1
90°-120°	389.0	10.0
90°-150°	1716.8	44.3
90°-180°	2362.0	60.9
0°-180°	3878.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	876	876	876	876	876	
5°	975	878	779	878	975	96
15°	1100	833	516	833	1100	297
25°	587	741	374	741	587	279
35°	289	611	276	611	289	185
45°	201	461	197	461	201	156
55°	139	313	138	313	139	122
65°	72	190	82	190	72	74
75°	38	90	44	90	38	41
85°	11	20	12	20	11	12
90°	16	1	16	1	16	7
95°	25	38	25	38	25	23
105°	44	177	44	177	44	46
115°	48	335	48	335	48	120
125°	499	474	499	474	499	431
135°	606	587	606	587	606	467
145°	691	681	691	681	691	432
155°	750	749	750	749	750	346
165°	788	790	788	790	788	222
175°	803	808	803	808	803	76
180°	806	806	806	806	806	



TEST NUMBER: P331657-930

CATALOG NUMBER: SA2XXRDIP-C485D725U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3
2.5°	911.8	912.6	913.3	911.6	911.6	910.1	906.9	904.5	897.6	896.7	896.7
5°	974.9	974.3	975.5	971.5	966.0	964.8	959.0	951.5	943.5	934.7	932.9
7.5°	1037.6	1036.7	1034.3	1033.6	1029.4	1020.2	1010.9	1000.9	987.8	974.9	968.5
10°	1069.3	1079.3	1073.3	1062.6	1064.7	1050.4	1042.8	1029.7	1018.7	999.6	995.3
12.5°	1100.4	1104.4	1102.4	1096.4	1093.7	1083.8	1073.5	1062.1	1041.9	1024.7	1009.7
15°	1100.3	1106.1	1107.7	1105.8	1107.3	1106.7	1101.2	1091.8	1074.2	1055.2	1038.9
17.5°	1019.1	1023.1	1033.1	1039.8	1048.4	1066.4	1075.3	1078.8	1076.1	1065.4	1053.8
20°	928.0	921.3	949.3	963.6	975.8	1006.2	1032.4	1042.4	1058.6	1058.3	1055.2
22.5°	798.9	800.5	827.0	844.0	879.6	910.0	939.9	977.7	1008.9	1029.6	1041.6
25°	587.0	598.6	625.1	648.2	687.8	744.4	795.9	855.6	911.8	956.3	998.7
27.5°	440.8	441.7	462.7	484.1	507.6	554.0	618.8	690.1	770.4	836.6	912.8
30°	377.6	375.7	384.6	397.6	417.8	453.6	502.4	572.4	652.5	752.4	841.2
32.5°	332.7	332.8	339.5	349.2	365.8	390.0	423.5	480.3	556.0	654.2	758.4
35°	289.3	288.9	293.8	300.8	307.8	323.3	346.2	376.0	428.1	519.8	626.3
37.5°	258.0	259.4	261.8	266.2	273.9	282.5	296.3	316.3	353.4	407.6	497.1
40°	240.5	241.2	244.5	248.2	252.7	259.4	270.7	286.8	313.9	357.1	422.6
42.5°	224.5	225.0	227.5	230.8	234.4	241.2	250.5	264.4	286.4	320.1	374.1
45°	201.0	201.0	203.1	204.6	208.6	214.7	222.3	233.8	249.1	274.0	310.0
47.5°	178.9	179.0	180.3	183.0	185.5	190.2	197.7	207.2	218.3	237.6	268.2
50°	166.2	166.6	167.5	169.6	171.1	175.4	181.2	189.4	201.0	215.9	241.4
52.5°	156.0	155.8	156.9	157.9	158.9	162.0	166.3	173.6	183.9	196.9	218.1
55°	139.4	138.2	140.1	141.5	142.5	143.7	146.1	150.7	159.6	170.5	186.3
57.5°	118.7	118.2	119.5	120.9	123.8	127.1	129.1	132.1	136.6	144.5	160.2
60°	101.7	101.7	104.4	105.3	108.7	112.9	117.2	119.7	124.3	129.4	141.0
62.5°	86.6	86.8	88.1	89.0	90.9	96.1	102.2	107.5	111.8	116.8	124.4
65°	72.5	73.1	73.1	73.7	74.9	76.1	78.5	82.8	90.4	97.4	103.2
67.5°	61.5	61.7	61.9	62.5	62.8	64.1	65.1	67.0	68.7	75.4	82.6
70°	54.2	55.1	54.8	55.4	55.7	56.3	57.6	58.5	61.2	62.7	67.0
72.5°	47.4	48.0	48.0	48.3	49.2	49.2	50.2	51.1	52.9	54.2	56.5
75°	38.4	38.1	38.4	39.0	39.3	39.5	39.5	40.8	41.7	43.0	44.4
77.5°	29.6	29.9	29.8	29.9	29.9	30.5	30.4	31.0	31.9	32.5	33.3
80°	23.7	24.1	23.7	24.1	24.4	24.6	24.4	24.6	25.6	26.2	26.2
82.5°	18.4	18.4	18.7	18.7	18.8	18.8	19.2	19.3	20.0	19.8	20.1
85°	10.9	10.7	10.7	10.7	10.9	11.3	10.9	10.9	11.3	11.3	11.3
87.5°	7.0	7.3	7.2	7.2	7.1	7.0	6.8	7.0	6.6	6.7	6.3
90°	15.7	15.5	15.2	15.0	14.7	14.3	13.6	13.0	12.3	11.7	10.6
92.5°	15.7	15.6	15.4	15.2	15.2	14.8	14.5	14.2	13.9	13.5	13.0
95°	25.1	25.2	25.4	25.4	25.6	25.4	24.7	24.1	23.4	22.7	21.9
97.5°	33.5	33.3	33.2	33.0	32.9	32.5	32.0	31.5	31.0	30.4	28.4
100°	39.1	38.8	38.6	38.3	38.1	37.4	36.4	35.3	34.2	33.3	31.1
102.5°	41.9	41.5	41.2	40.8	40.4	39.5	38.2	36.9	35.5	34.2	52.6
105°	44.4	43.8	43.3	42.8	42.2	41.3	39.9	38.4	37.0	35.5	70.9
107.5°	45.6	45.1	44.6	44.0	43.5	44.0	45.4	46.9	48.3	49.8	92.2
110°	46.1	45.6	45.0	44.5	44.0	50.2	63.2	76.1	89.1	102.1	139.5



TEST NUMBER: P331657-930

CATALOG NUMBER: SA2XXRDIP-C485D725U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	46.6	46.1	45.7	45.3	44.8	68.3	115.6	162.9	210.2	257.4	266.7
115°	47.9	57.2	66.4	75.8	85.1	119.8	179.9	239.9	299.9	359.9	356.6
117.5°	195.3	225.9	256.6	287.2	317.9	340.5	355.0	369.6	384.1	398.6	396.3
120°	355.8	373.2	390.8	408.2	425.7	433.7	432.2	430.6	429.0	427.5	425.2
122.5°	443.9	447.4	450.7	454.1	457.5	458.8	457.8	456.9	455.9	455.0	452.5
125°	498.6	498.2	497.9	497.5	497.1	496.4	495.5	494.6	493.7	492.8	490.3
127.5°	533.2	533.1	533.0	533.0	532.9	532.1	530.8	529.5	528.2	526.8	525.1
130°	554.6	554.7	554.9	555.1	555.1	554.5	553.1	551.6	550.2	548.8	547.4
132.5°	575.6	575.8	575.9	576.0	576.2	575.6	574.4	573.2	571.9	570.7	569.3
135°	605.9	606.2	606.5	606.7	607.0	606.5	605.2	603.9	602.6	601.3	600.1
137.5°	633.6	634.1	634.5	635.0	635.4	635.0	633.7	632.4	631.1	629.9	628.5
140°	650.9	651.5	652.2	652.8	653.5	653.2	652.0	650.9	649.7	648.6	647.1
142.5°	667.6	668.3	669.0	669.6	670.3	670.0	669.0	667.9	666.8	665.8	664.1
145°	691.1	691.8	692.4	693.1	693.7	693.6	692.7	691.8	690.9	689.9	687.7
147.5°	711.8	712.3	712.8	713.4	714.0	713.9	713.2	712.5	711.8	711.2	709.0
150°	724.3	725.0	725.6	726.3	726.9	726.8	726.1	725.3	724.6	723.7	721.7
152.5°	735.1	736.0	736.8	737.7	738.5	738.6	737.8	736.9	736.2	735.4	733.4
155°	750.0	751.1	752.1	753.1	754.2	754.3	753.5	752.8	752.0	751.1	749.6
157.5°	763.7	764.7	765.6	766.7	767.7	767.8	766.9	766.0	765.2	764.3	763.1
160°	771.6	772.5	773.4	774.3	775.2	775.3	774.5	773.7	773.0	772.2	771.4
162.5°	778.1	779.3	780.3	781.5	782.6	782.7	781.8	780.9	780.1	779.2	778.5
165°	787.9	788.8	789.7	790.7	791.6	791.6	790.7	789.7	788.8	787.9	787.5
167.5°	794.1	795.2	796.5	797.6	798.7	798.9	798.0	797.1	796.1	795.2	794.9
170°	797.9	799.0	800.1	801.4	802.5	802.7	801.7	800.8	799.9	799.0	798.7
172.5°	800.6	801.8	803.0	804.1	805.3	805.4	804.5	803.6	802.7	801.8	801.5
175°	803.1	804.4	805.7	807.0	808.3	808.5	807.6	806.7	805.8	804.9	804.5
177.5°	804.6	805.5	806.5	807.4	808.4	808.5	807.7	807.0	806.2	805.5	805.4
180°	806.0	806.0	806.0	806.0	806.0	806.0	806.0	806.0	806.0	806.0	806.0



TEST NUMBER: P331657-930

CATALOG NUMBER: SA2XXRDIP-C485D725U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3
2.5°	897.2	895.3	893.6	889.2	887.0	882.1	881.3	881.1	874.8	868.7	867.0
5°	928.0	923.2	915.8	907.3	898.5	889.3	883.2	878.4	866.2	854.6	847.9
7.5°	959.0	948.6	936.0	919.8	906.4	891.3	880.1	870.0	852.7	836.2	825.0
10°	982.2	965.2	948.4	926.2	908.8	891.8	876.0	862.3	842.8	820.8	805.3
12.5°	996.5	977.8	954.7	933.0	910.5	888.8	867.6	850.0	827.2	804.5	786.0
15°	1016.0	995.9	967.9	936.9	907.9	879.6	855.2	833.3	803.5	776.4	753.8
17.5°	1031.9	1004.2	974.1	938.2	904.7	868.8	837.4	809.3	776.2	743.5	717.0
20°	1037.0	1009.6	974.9	939.0	899.4	857.0	823.3	792.8	757.2	721.5	691.1
22.5°	1033.8	1012.5	973.9	930.9	890.4	846.1	808.0	772.6	733.1	696.8	661.5
25°	1012.4	1005.0	968.5	921.6	875.3	823.9	779.8	741.0	696.0	657.0	618.6
27.5°	962.2	978.0	955.4	905.4	853.9	798.7	749.2	705.2	658.4	614.5	576.3
30°	914.0	950.2	940.4	894.2	836.7	782.4	726.8	680.8	630.9	585.8	548.0
32.5°	848.0	907.8	917.4	878.6	819.1	759.5	701.2	655.4	603.3	555.8	519.0
35°	742.9	832.4	873.5	848.8	789.1	725.0	664.6	611.4	559.0	512.1	475.6
37.5°	617.5	739.4	808.0	809.7	754.9	688.1	622.5	569.6	515.9	469.9	430.4
40°	536.1	668.3	757.5	777.3	731.0	658.8	592.5	538.6	486.2	441.2	395.8
42.5°	463.1	594.8	704.4	738.8	702.1	630.4	563.8	507.4	456.5	413.8	367.5
45°	374.5	489.6	610.4	672.0	651.6	585.1	514.9	461.3	413.4	376.6	332.2
47.5°	315.9	397.1	514.0	597.2	596.8	536.2	467.1	415.7	371.4	336.9	300.8
50°	282.5	353.2	452.2	546.5	554.4	503.6	437.8	386.9	345.6	309.3	280.4
52.5°	252.6	310.8	399.7	490.2	512.7	468.7	405.0	358.0	317.8	284.5	259.7
55°	213.4	258.4	326.1	410.7	444.8	413.8	357.1	313.3	280.7	252.7	231.4
57.5°	180.5	214.3	268.6	336.7	376.4	356.9	310.2	274.6	246.7	221.4	204.6
60°	159.9	187.5	233.5	290.5	334.3	320.6	280.7	247.5	223.8	201.9	186.1
62.5°	140.4	164.2	203.6	249.8	290.0	284.3	251.8	223.9	203.1	183.1	169.7
65°	112.9	130.3	161.0	197.3	229.6	232.3	208.9	190.0	171.4	155.6	143.7
67.5°	89.9	101.3	122.9	153.4	177.7	186.3	171.9	157.5	142.8	130.5	120.3
70°	75.8	85.0	100.8	125.5	147.7	156.8	148.5	137.3	124.5	114.5	105.7
72.5°	61.5	70.4	82.0	100.1	119.2	129.1	126.2	118.1	107.7	99.4	91.1
75°	46.3	49.0	56.9	69.1	84.1	92.5	94.7	90.4	82.2	75.8	70.9
77.5°	34.2	35.9	39.6	46.1	55.8	63.3	66.5	66.0	60.3	56.7	52.1
80°	27.4	28.3	30.2	32.9	40.2	47.8	49.9	49.9	46.0	44.4	39.9
82.5°	20.8	21.5	22.6	24.1	27.6	34.2	36.5	37.0	34.5	32.5	28.9
85°	11.9	11.6	12.1	13.1	13.7	15.5	19.2	19.8	19.2	16.7	15.8
87.5°	6.0	6.1	5.9	5.4	5.4	5.3	6.3	7.2	6.5	6.0	5.9
90°	9.6	8.6	7.5	6.3	4.9	3.4	2.0	0.6	2.0	3.4	4.9
92.5°	12.5	12.0	11.5	11.3	11.4	11.5	11.7	11.7	11.7	11.5	11.4
95°	21.0	20.1	19.1	20.8	25.1	29.4	33.7	37.9	33.7	29.4	25.1
97.5°	26.3	24.1	22.0	27.0	39.1	51.1	63.2	75.3	63.2	51.1	39.1
100°	28.9	26.7	24.5	32.2	50.0	67.8	85.4	103.2	85.4	67.8	50.0
102.5°	71.0	89.4	107.9	119.0	122.8	126.5	130.3	134.0	130.3	126.5	122.8
105°	106.3	141.7	177.1	192.8	189.0	185.1	181.2	177.3	181.2	185.1	189.0
107.5°	134.7	177.1	219.6	239.2	236.0	232.9	229.8	226.7	229.8	232.9	236.0
110°	177.0	214.4	251.8	269.2	266.5	263.8	261.1	258.4	261.1	263.8	266.5



TEST NUMBER: P331657-930

CATALOG NUMBER: SA2XXRDIP-C485D725U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	275.9	285.2	294.4	297.8	295.5	293.0	290.7	288.2	290.7	293.0	295.5
115°	353.4	350.1	346.9	344.1	341.9	339.7	337.5	335.3	337.5	339.7	341.9
117.5°	394.1	391.9	389.6	387.3	384.8	382.4	379.9	377.5	379.9	382.4	384.8
120°	422.8	420.5	418.2	416.0	414.1	412.1	410.2	408.2	410.2	412.1	414.1
122.5°	450.0	447.4	444.8	442.5	440.5	438.5	436.4	434.4	436.4	438.5	440.5
125°	487.9	485.4	483.0	480.9	479.2	477.5	475.8	474.2	475.8	477.5	479.2
127.5°	523.2	521.4	519.5	517.6	515.8	514.0	512.1	510.2	512.1	514.0	515.8
130°	545.9	544.5	543.1	541.4	539.2	537.2	535.2	533.0	535.2	537.2	539.2
132.5°	567.9	566.5	565.0	563.5	561.7	559.9	558.2	556.4	558.2	559.9	561.7
135°	598.9	597.8	596.6	595.0	593.0	590.8	588.8	586.7	588.8	590.8	593.0
137.5°	627.2	625.9	624.6	623.2	621.7	620.3	618.8	617.4	618.8	620.3	621.7
140°	645.7	644.2	642.9	641.6	640.6	639.5	638.5	637.5	638.5	639.5	640.6
142.5°	662.5	660.9	659.3	657.9	657.0	656.2	655.2	654.3	655.2	656.2	657.0
145°	685.5	683.3	681.1	680.1	680.2	680.4	680.4	680.6	680.4	680.4	680.2
147.5°	706.8	704.7	702.5	701.6	702.1	702.6	703.1	703.6	703.1	702.6	702.1
150°	719.6	717.5	715.5	714.9	715.8	716.7	717.6	718.5	717.6	716.7	715.8
152.5°	731.5	729.5	727.6	727.1	728.1	729.1	730.1	731.1	730.1	729.1	728.1
155°	748.0	746.5	744.9	744.8	745.9	747.1	748.3	749.4	748.3	747.1	745.9
157.5°	762.1	761.0	759.9	759.9	760.8	761.8	762.8	763.8	762.8	761.8	760.8
160°	770.6	769.8	769.1	769.1	769.8	770.6	771.4	772.2	771.4	770.6	769.8
162.5°	777.8	777.1	776.5	776.5	777.3	778.1	778.9	779.7	778.9	778.1	777.3
165°	787.2	786.8	786.4	786.5	787.3	788.1	788.9	789.7	788.9	788.1	787.3
167.5°	794.5	794.2	793.8	794.0	794.8	795.6	796.4	797.1	796.4	795.6	794.8
170°	798.5	798.3	797.9	798.3	799.0	799.8	800.5	801.4	800.5	799.8	799.0
172.5°	801.3	801.0	800.8	801.0	801.8	802.6	803.3	804.1	803.3	802.6	801.8
175°	804.3	804.0	803.8	804.1	805.0	805.9	806.8	807.7	806.8	805.9	805.0
177.5°	805.4	805.2	805.1	805.4	806.2	806.9	807.6	808.4	807.6	806.9	806.2
180°	806.0	806.0	806.0	806.0	806.0	806.0	806.0	806.0	806.0	806.0	806.0



TEST NUMBER: P331657-930

CATALOG NUMBER: SA2XXRDIP-C485D725U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3
2.5°	863.8	862.1	858.9	854.1	851.2	846.0	842.6	844.6	845.1	844.6	844.1
5°	840.7	834.2	825.4	816.8	808.9	800.5	795.6	793.4	789.1	786.8	785.5
7.5°	812.5	801.5	789.0	774.2	761.6	748.4	741.6	738.3	729.5	724.8	720.6
10°	791.6	774.2	761.7	742.2	730.4	713.1	701.2	701.5	689.6	682.9	678.0
12.5°	768.5	749.4	728.6	711.1	694.6	680.7	666.3	660.6	647.9	641.5	628.4
15°	730.1	707.8	686.0	662.2	645.5	623.9	603.2	577.9	557.5	539.8	534.9
17.5°	688.2	660.7	638.7	610.8	582.1	545.8	521.8	507.1	494.8	485.5	478.6
20°	659.5	631.4	608.1	566.0	527.3	502.6	485.0	473.8	461.0	450.9	445.4
22.5°	629.2	600.1	568.1	521.1	491.1	471.2	455.5	442.5	433.9	426.1	421.1
25°	586.4	554.4	501.7	469.4	445.2	424.4	413.4	405.5	396.4	385.7	380.9
27.5°	541.1	490.2	452.4	428.4	405.2	391.8	381.9	370.1	361.9	357.1	352.0
30°	507.2	456.4	426.9	400.6	384.3	369.3	357.8	351.1	343.2	334.9	331.6
32.5°	469.4	428.8	400.6	378.8	362.1	349.4	340.2	329.4	323.7	318.6	311.6
35°	422.6	391.8	366.0	348.3	332.5	322.1	311.4	305.1	294.7	290.5	287.7
37.5°	382.9	356.2	336.9	318.3	305.7	294.3	287.8	277.6	273.1	267.2	261.4
40°	360.4	334.3	315.8	300.5	286.5	277.9	269.8	261.5	254.9	252.1	245.1
42.5°	337.6	316.3	297.7	281.0	271.7	262.6	252.3	246.2	239.2	234.8	230.5
45°	306.0	287.1	271.3	257.6	247.2	237.8	231.1	221.0	217.1	208.2	204.6
47.5°	278.2	260.7	245.6	232.5	222.4	216.3	206.5	198.6	192.3	186.9	182.2
50°	258.4	243.9	229.3	217.7	208.6	199.7	189.7	185.7	175.9	173.3	170.5
52.5°	240.4	226.6	213.2	201.9	192.7	184.2	175.3	170.2	163.5	160.8	158.8
55°	215.2	201.9	189.1	179.0	169.9	161.0	155.6	149.2	146.1	144.0	141.5
57.5°	189.9	177.9	168.0	157.9	148.7	141.7	135.3	131.5	128.3	125.6	122.6
60°	173.8	162.2	153.4	144.0	134.6	128.8	123.9	119.4	115.7	111.5	110.2
62.5°	156.8	146.7	138.6	129.4	121.2	115.9	111.3	107.0	102.6	96.4	94.7
65°	133.4	125.5	116.9	109.3	102.0	96.9	90.1	85.3	83.4	82.8	82.5
67.5°	112.2	104.7	97.3	89.6	82.9	78.1	74.7	73.9	72.7	72.3	71.5
70°	98.0	91.1	83.7	76.4	70.0	69.1	67.9	66.7	65.1	64.6	63.9
72.5°	85.4	78.1	70.8	65.0	62.2	61.1	59.8	58.6	57.6	57.0	56.7
75°	65.5	58.8	53.9	51.8	50.2	49.3	47.5	46.6	46.0	45.1	44.8
77.5°	47.1	43.4	41.1	39.8	38.2	37.2	36.2	35.2	34.6	34.4	33.9
80°	36.0	34.1	32.6	30.7	30.2	28.9	28.6	27.7	28.0	27.1	27.1
82.5°	27.9	25.6	24.3	23.5	22.8	21.9	21.5	21.1	21.2	20.5	20.5
85°	14.3	13.7	13.1	12.5	12.5	11.6	11.9	11.6	11.6	10.9	10.7
87.5°	5.9	5.9	5.6	5.8	6.0	6.0	6.1	6.0	6.1	6.3	6.1
90°	6.3	7.5	8.6	9.6	10.6	11.7	12.3	13.0	13.6	14.3	14.7
92.5°	11.3	11.5	12.0	12.5	13.0	13.5	13.9	14.2	14.5	14.8	15.2
95°	20.8	19.1	20.1	21.0	21.9	22.7	23.4	24.1	24.7	25.4	25.6
97.5°	27.0	22.0	24.1	26.3	28.4	30.4	31.0	31.5	32.0	32.5	32.9
100°	32.2	24.5	26.7	28.9	31.1	33.3	34.2	35.3	36.4	37.4	38.1
102.5°	119.0	107.9	89.4	71.0	52.6	34.2	35.5	36.9	38.2	39.5	40.4
105°	192.8	177.1	141.7	106.3	70.9	35.5	37.0	38.4	39.9	41.3	42.2
107.5°	239.2	219.6	177.1	134.7	92.2	49.8	48.3	46.9	45.4	44.0	43.5
110°	269.2	251.8	214.4	177.0	139.5	102.1	89.1	76.1	63.2	50.2	44.0



TEST NUMBER: P331657-930

CATALOG NUMBER: SA2XXRDIP-C485D725U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	297.8	294.4	285.2	275.9	266.7	257.4	210.2	162.9	115.6	68.3	44.8
115°	344.1	346.9	350.1	353.4	356.6	359.9	299.9	239.9	179.9	119.8	85.1
117.5°	387.3	389.6	391.9	394.1	396.3	398.6	384.1	369.6	355.0	340.5	317.9
120°	416.0	418.2	420.5	422.8	425.2	427.5	429.0	430.6	432.2	433.7	425.7
122.5°	442.5	444.8	447.4	450.0	452.5	455.0	455.9	456.9	457.8	458.8	457.5
125°	480.9	483.0	485.4	487.9	490.3	492.8	493.7	494.6	495.5	496.4	497.1
127.5°	517.6	519.5	521.4	523.2	525.1	526.8	528.2	529.5	530.8	532.1	532.9
130°	541.4	543.1	544.5	545.9	547.4	548.8	550.2	551.6	553.1	554.5	555.1
132.5°	563.5	565.0	566.5	567.9	569.3	570.7	571.9	573.2	574.4	575.6	576.2
135°	595.0	596.6	597.8	598.9	600.1	601.3	602.6	603.9	605.2	606.5	607.0
137.5°	623.2	624.6	625.9	627.2	628.5	629.9	631.1	632.4	633.7	635.0	635.4
140°	641.6	642.9	644.2	645.7	647.1	648.6	649.7	650.9	652.0	653.2	653.5
142.5°	657.9	659.3	660.9	662.5	664.1	665.8	666.8	667.9	669.0	670.0	670.3
145°	680.1	681.1	683.3	685.5	687.7	689.9	690.9	691.8	692.7	693.6	693.7
147.5°	701.6	702.5	704.7	706.8	709.0	711.2	711.8	712.5	713.2	713.9	714.0
150°	714.9	715.5	717.5	719.6	721.7	723.7	724.6	725.3	726.1	726.8	726.9
152.5°	727.1	727.6	729.5	731.5	733.4	735.4	736.2	736.9	737.8	738.6	738.5
155°	744.8	744.9	746.5	748.0	749.6	751.1	752.0	752.8	753.5	754.3	754.2
157.5°	759.9	759.9	761.0	762.1	763.1	764.3	765.2	766.0	766.9	767.8	767.7
160°	769.1	769.1	769.8	770.6	771.4	772.2	773.0	773.7	774.5	775.3	775.2
162.5°	776.5	776.5	777.1	777.8	778.5	779.2	780.1	780.9	781.8	782.7	782.6
165°	786.5	786.4	786.8	787.2	787.5	787.9	788.8	789.7	790.7	791.6	791.6
167.5°	794.0	793.8	794.2	794.5	794.9	795.2	796.1	797.1	798.0	798.9	798.7
170°	798.3	797.9	798.3	798.5	798.7	799.0	799.9	800.8	801.7	802.7	802.5
172.5°	801.0	800.8	801.0	801.3	801.5	801.8	802.7	803.6	804.5	805.4	805.3
175°	804.1	803.8	804.0	804.3	804.5	804.9	805.8	806.7	807.6	808.5	808.3
177.5°	805.4	805.1	805.2	805.4	805.4	805.5	806.2	807.0	807.7	808.5	808.4
180°	806.0	806.0	806.0	806.0	806.0	806.0	806.0	806.0	806.0	806.0	806.0



TEST NUMBER: P331657-930

CATALOG NUMBER: SA2XXRDIP-C485D725U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3
2.5°	841.4	841.9	841.1	841.6	841.1	841.9	841.4	844.1	844.6	845.1	844.6
5°	784.0	780.3	779.8	778.9	779.8	780.3	784.0	785.5	786.8	789.1	793.4
7.5°	715.4	714.9	713.4	711.2	713.4	714.9	715.4	720.6	724.8	729.5	738.3
10°	671.3	669.8	669.5	667.4	669.5	669.8	671.3	678.0	682.9	689.6	701.5
12.5°	619.7	609.9	608.9	603.6	608.9	609.9	619.7	628.4	641.5	647.9	660.6
15°	527.7	525.8	519.8	515.8	519.8	525.8	527.7	534.9	539.8	557.5	577.9
17.5°	475.0	469.0	467.2	466.4	467.2	469.0	475.0	478.6	485.5	494.8	507.1
20°	441.2	435.7	434.8	434.1	434.8	435.7	441.2	445.4	450.9	461.0	473.8
22.5°	417.8	412.1	409.7	407.9	409.7	412.1	417.8	421.1	426.1	433.9	442.5
25°	377.8	375.7	374.5	373.9	374.5	375.7	377.8	380.9	385.7	396.4	405.5
27.5°	346.6	341.9	341.0	339.4	341.0	341.9	346.6	352.0	357.1	361.9	370.1
30°	328.8	327.3	325.1	323.3	325.1	327.3	328.8	331.6	334.9	343.2	351.1
32.5°	307.9	306.6	304.7	303.9	304.7	306.6	307.9	311.6	318.6	323.7	329.4
35°	284.7	280.4	278.6	275.8	278.6	280.4	284.7	287.7	290.5	294.7	305.1
37.5°	260.2	257.9	255.4	256.2	255.4	257.9	260.2	261.4	267.2	273.1	277.6
40°	241.2	239.6	239.0	238.7	239.0	239.6	241.2	245.1	252.1	254.9	261.5
42.5°	226.0	221.8	220.2	220.2	220.2	221.8	226.0	230.5	234.8	239.2	246.2
45°	203.1	199.1	196.4	196.7	196.4	199.1	203.1	204.6	208.2	217.1	221.0
47.5°	179.6	179.4	177.7	178.3	177.7	179.4	179.6	182.2	186.9	192.3	198.6
50°	168.4	166.6	165.3	165.6	165.3	166.6	168.4	170.5	173.3	175.9	185.7
52.5°	157.7	156.0	155.1	156.4	155.1	156.0	157.7	158.8	160.8	163.5	170.2
55°	140.1	138.2	137.9	137.6	137.9	138.2	140.1	141.5	144.0	146.1	149.2
57.5°	120.4	119.2	117.3	116.6	117.3	119.2	120.4	122.6	125.6	128.3	131.5
60°	106.2	103.8	100.8	100.4	100.8	103.8	106.2	110.2	111.5	115.7	119.4
62.5°	93.4	92.9	92.3	92.2	92.3	92.9	93.4	94.7	96.4	102.6	107.0
65°	81.9	81.6	81.9	82.2	81.9	81.6	81.9	82.5	82.8	83.4	85.3
67.5°	71.3	70.8	70.3	70.5	70.3	70.8	71.3	71.5	72.3	72.7	73.9
70°	63.3	63.0	62.7	62.7	62.7	63.0	63.3	63.9	64.6	65.1	66.7
72.5°	55.5	55.4	55.2	55.0	55.2	55.4	55.5	56.7	57.0	57.6	58.6
75°	44.4	43.9	43.9	43.9	43.9	43.9	44.4	44.8	45.1	46.0	46.6
77.5°	33.8	33.6	33.3	33.0	33.3	33.6	33.8	33.9	34.4	34.6	35.2
80°	26.8	26.5	26.2	26.2	26.2	26.5	26.8	27.1	27.1	28.0	27.7
82.5°	20.5	20.1	20.1	19.8	20.1	20.1	20.5	20.5	20.5	21.2	21.1
85°	10.9	11.3	10.9	11.6	10.9	11.3	10.9	10.7	10.9	11.6	11.6
87.5°	6.2	6.0	6.3	6.0	6.3	6.0	6.2	6.1	6.3	6.1	6.0
90°	15.0	15.2	15.5	15.7	15.5	15.2	15.0	14.7	14.3	13.6	13.0
92.5°	15.2	15.4	15.6	15.7	15.6	15.4	15.2	15.2	14.8	14.5	14.2
95°	25.4	25.4	25.2	25.1	25.2	25.4	25.4	25.6	25.4	24.7	24.1
97.5°	33.0	33.2	33.3	33.5	33.3	33.2	33.0	32.9	32.5	32.0	31.5
100°	38.3	38.6	38.8	39.1	38.8	38.6	38.3	38.1	37.4	36.4	35.3
102.5°	40.8	41.2	41.5	41.9	41.5	41.2	40.8	40.4	39.5	38.2	36.9
105°	42.8	43.3	43.8	44.4	43.8	43.3	42.8	42.2	41.3	39.9	38.4
107.5°	44.0	44.6	45.1	45.6	45.1	44.6	44.0	43.5	44.0	45.4	46.9
110°	44.5	45.0	45.6	46.1	45.6	45.0	44.5	44.0	50.2	63.2	76.1



TEST NUMBER: P331657-930

CATALOG NUMBER: SA2XXRDIP-C485D725U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	45.3	45.7	46.1	46.6	46.1	45.7	45.3	44.8	68.3	115.6	162.9
115°	75.8	66.4	57.2	47.9	57.2	66.4	75.8	85.1	119.8	179.9	239.9
117.5°	287.2	256.6	225.9	195.3	225.9	256.6	287.2	317.9	340.5	355.0	369.6
120°	408.2	390.8	373.2	355.8	373.2	390.8	408.2	425.7	433.7	432.2	430.6
122.5°	454.1	450.7	447.4	443.9	447.4	450.7	454.1	457.5	458.8	457.8	456.9
125°	497.5	497.9	498.2	498.6	498.2	497.9	497.5	497.1	496.4	495.5	494.6
127.5°	533.0	533.0	533.1	533.2	533.1	533.0	533.0	532.9	532.1	530.8	529.5
130°	555.1	554.9	554.7	554.6	554.7	554.9	555.1	555.1	554.5	553.1	551.6
132.5°	576.0	575.9	575.8	575.6	575.8	575.9	576.0	576.2	575.6	574.4	573.2
135°	606.7	606.5	606.2	605.9	606.2	606.5	606.7	607.0	606.5	605.2	603.9
137.5°	635.0	634.5	634.1	633.6	634.1	634.5	635.0	635.4	635.0	633.7	632.4
140°	652.8	652.2	651.5	650.9	651.5	652.2	652.8	653.5	653.2	652.0	650.9
142.5°	669.6	669.0	668.3	667.6	668.3	669.0	669.6	670.3	670.0	669.0	667.9
145°	693.1	692.4	691.8	691.1	691.8	692.4	693.1	693.7	693.6	692.7	691.8
147.5°	713.4	712.8	712.3	711.8	712.3	712.8	713.4	714.0	713.9	713.2	712.5
150°	726.3	725.6	725.0	724.3	725.0	725.6	726.3	726.9	726.8	726.1	725.3
152.5°	737.7	736.8	736.0	735.1	736.0	736.8	737.7	738.5	738.6	737.8	736.9
155°	753.1	752.1	751.1	750.0	751.1	752.1	753.1	754.2	754.3	753.5	752.8
157.5°	766.7	765.6	764.7	763.7	764.7	765.6	766.7	767.7	767.8	766.9	766.0
160°	774.3	773.4	772.5	771.6	772.5	773.4	774.3	775.2	775.3	774.5	773.7
162.5°	781.5	780.3	779.3	778.1	779.3	780.3	781.5	782.6	782.7	781.8	780.9
165°	790.7	789.7	788.8	787.9	788.8	789.7	790.7	791.6	791.6	790.7	789.7
167.5°	797.6	796.5	795.2	794.1	795.2	796.5	797.6	798.7	798.9	798.0	797.1
170°	801.4	800.1	799.0	797.9	799.0	800.1	801.4	802.5	802.7	801.7	800.8
172.5°	804.1	803.0	801.8	800.6	801.8	803.0	804.1	805.3	805.4	804.5	803.6
175°	807.0	805.7	804.4	803.1	804.4	805.7	807.0	808.3	808.5	807.6	806.7
177.5°	807.4	806.5	805.5	804.6	805.5	806.5	807.4	808.4	808.5	807.7	807.0
180°	806.0	806.0	806.0	806.0	806.0	806.0	806.0	806.0	806.0	806.0	806.0



TEST NUMBER: P331657-930
 CATALOG NUMBER: SA2XXRDIP-C485D725U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3
2.5°	842.6	846.0	851.2	854.1	858.9	862.1	863.8	867.0	868.7	874.8	881.1
5°	795.6	800.5	808.9	816.8	825.4	834.2	840.7	847.9	854.6	866.2	878.4
7.5°	741.6	748.4	761.6	774.2	789.0	801.5	812.5	825.0	836.2	852.7	870.0
10°	701.2	713.1	730.4	742.2	761.7	774.2	791.6	805.3	820.8	842.8	862.3
12.5°	666.3	680.7	694.6	711.1	728.6	749.4	768.5	786.0	804.5	827.2	850.0
15°	603.2	623.9	645.5	662.2	686.0	707.8	730.1	753.8	776.4	803.5	833.3
17.5°	521.8	545.8	582.1	610.8	638.7	660.7	688.2	717.0	743.5	776.2	809.3
20°	485.0	502.6	527.3	566.0	608.1	631.4	659.5	691.1	721.5	757.2	792.8
22.5°	455.5	471.2	491.1	521.1	568.1	600.1	629.2	661.5	696.8	733.1	772.6
25°	413.4	424.4	445.2	469.4	501.7	554.4	586.4	618.6	657.0	696.0	741.0
27.5°	381.9	391.8	405.2	428.4	452.4	490.2	541.1	576.3	614.5	658.4	705.2
30°	357.8	369.3	384.3	400.6	426.9	456.4	507.2	548.0	585.8	630.9	680.8
32.5°	340.2	349.4	362.1	378.8	400.6	428.8	469.4	519.0	555.8	603.3	655.4
35°	311.4	322.1	332.5	348.3	366.0	391.8	422.6	475.6	512.1	559.0	611.4
37.5°	287.8	294.3	305.7	318.3	336.9	356.2	382.9	430.4	469.9	515.9	569.6
40°	269.8	277.9	286.5	300.5	315.8	334.3	360.4	395.8	441.2	486.2	538.6
42.5°	252.3	262.6	271.7	281.0	297.7	316.3	337.6	367.5	413.8	456.5	507.4
45°	231.1	237.8	247.2	257.6	271.3	287.1	306.0	332.2	376.6	413.4	461.3
47.5°	206.5	216.3	222.4	232.5	245.6	260.7	278.2	300.8	336.9	371.4	415.7
50°	189.7	199.7	208.6	217.7	229.3	243.9	258.4	280.4	309.3	345.6	386.9
52.5°	175.3	184.2	192.7	201.9	213.2	226.6	240.4	259.7	284.5	317.8	358.0
55°	155.6	161.0	169.9	179.0	189.1	201.9	215.2	231.4	252.7	280.7	313.3
57.5°	135.3	141.7	148.7	157.9	168.0	177.9	189.9	204.6	221.4	246.7	274.6
60°	123.9	128.8	134.6	144.0	153.4	162.2	173.8	186.1	201.9	223.8	247.5
62.5°	111.3	115.9	121.2	129.4	138.6	146.7	156.8	169.7	183.1	203.1	223.9
65°	90.1	96.9	102.0	109.3	116.9	125.5	133.4	143.7	155.6	171.4	190.0
67.5°	74.7	78.1	82.9	89.6	97.3	104.7	112.2	120.3	130.5	142.8	157.5
70°	67.9	69.1	70.0	76.4	83.7	91.1	98.0	105.7	114.5	124.5	137.3
72.5°	59.8	61.1	62.2	65.0	70.8	78.1	85.4	91.1	99.4	107.7	118.1
75°	47.5	49.3	50.2	51.8	53.9	58.8	65.5	70.9	75.8	82.2	90.4
77.5°	36.2	37.2	38.2	39.8	41.1	43.4	47.1	52.1	56.7	60.3	66.0
80°	28.6	28.9	30.2	30.7	32.6	34.1	36.0	39.9	44.4	46.0	49.9
82.5°	21.5	21.9	22.8	23.5	24.3	25.6	27.9	28.9	32.5	34.5	37.0
85°	11.9	11.6	12.5	12.5	13.1	13.7	14.3	15.8	16.7	19.2	19.8
87.5°	6.1	6.0	6.0	5.8	5.6	5.9	5.9	5.9	6.0	6.5	7.2
90°	12.3	11.7	10.6	9.6	8.6	7.5	6.3	4.9	3.4	2.0	0.6
92.5°	13.9	13.5	13.0	12.5	12.0	11.5	11.3	11.4	11.5	11.7	11.7
95°	23.4	22.7	21.9	21.0	20.1	19.1	20.8	25.1	29.4	33.7	37.9
97.5°	31.0	30.4	28.4	26.3	24.1	22.0	27.0	39.1	51.1	63.2	75.3
100°	34.2	33.3	31.1	28.9	26.7	24.5	32.2	50.0	67.8	85.4	103.2
102.5°	35.5	34.2	52.6	71.0	89.4	107.9	119.0	122.8	126.5	130.3	134.0
105°	37.0	35.5	70.9	106.3	141.7	177.1	192.8	189.0	185.1	181.2	177.3
107.5°	48.3	49.8	92.2	134.7	177.1	219.6	239.2	236.0	232.9	229.8	226.7
110°	89.1	102.1	139.5	177.0	214.4	251.8	269.2	266.5	263.8	261.1	258.4



TEST NUMBER: P331657-930

CATALOG NUMBER: SA2XXRDIP-C485D725U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	210.2	257.4	266.7	275.9	285.2	294.4	297.8	295.5	293.0	290.7	288.2
115°	299.9	359.9	356.6	353.4	350.1	346.9	344.1	341.9	339.7	337.5	335.3
117.5°	384.1	398.6	396.3	394.1	391.9	389.6	387.3	384.8	382.4	379.9	377.5
120°	429.0	427.5	425.2	422.8	420.5	418.2	416.0	414.1	412.1	410.2	408.2
122.5°	455.9	455.0	452.5	450.0	447.4	444.8	442.5	440.5	438.5	436.4	434.4
125°	493.7	492.8	490.3	487.9	485.4	483.0	480.9	479.2	477.5	475.8	474.2
127.5°	528.2	526.8	525.1	523.2	521.4	519.5	517.6	515.8	514.0	512.1	510.2
130°	550.2	548.8	547.4	545.9	544.5	543.1	541.4	539.2	537.2	535.2	533.0
132.5°	571.9	570.7	569.3	567.9	566.5	565.0	563.5	561.7	559.9	558.2	556.4
135°	602.6	601.3	600.1	598.9	597.8	596.6	595.0	593.0	590.8	588.8	586.7
137.5°	631.1	629.9	628.5	627.2	625.9	624.6	623.2	621.7	620.3	618.8	617.4
140°	649.7	648.6	647.1	645.7	644.2	642.9	641.6	640.6	639.5	638.5	637.5
142.5°	666.8	665.8	664.1	662.5	660.9	659.3	657.9	657.0	656.2	655.2	654.3
145°	690.9	689.9	687.7	685.5	683.3	681.1	680.1	680.2	680.4	680.4	680.6
147.5°	711.8	711.2	709.0	706.8	704.7	702.5	701.6	702.1	702.6	703.1	703.6
150°	724.6	723.7	721.7	719.6	717.5	715.5	714.9	715.8	716.7	717.6	718.5
152.5°	736.2	735.4	733.4	731.5	729.5	727.6	727.1	728.1	729.1	730.1	731.1
155°	752.0	751.1	749.6	748.0	746.5	744.9	744.8	745.9	747.1	748.3	749.4
157.5°	765.2	764.3	763.1	762.1	761.0	759.9	759.9	760.8	761.8	762.8	763.8
160°	773.0	772.2	771.4	770.6	769.8	769.1	769.1	769.8	770.6	771.4	772.2
162.5°	780.1	779.2	778.5	777.8	777.1	776.5	776.5	777.3	778.1	778.9	779.7
165°	788.8	787.9	787.5	787.2	786.8	786.4	786.5	787.3	788.1	788.9	789.7
167.5°	796.1	795.2	794.9	794.5	794.2	793.8	794.0	794.8	795.6	796.4	797.1
170°	799.9	799.0	798.7	798.5	798.3	797.9	798.3	799.0	799.8	800.5	801.4
172.5°	802.7	801.8	801.5	801.3	801.0	800.8	801.0	801.8	802.6	803.3	804.1
175°	805.8	804.9	804.5	804.3	804.0	803.8	804.1	805.0	805.9	806.8	807.7
177.5°	806.2	805.5	805.4	805.4	805.2	805.1	805.4	806.2	806.9	807.6	808.4
180°	806.0	806.0	806.0	806.0	806.0	806.0	806.0	806.0	806.0	806.0	806.0



TEST NUMBER: P331657-930

CATALOG NUMBER: SA2XXRDIP-C485D725U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3
2.5°	881.3	882.1	887.0	889.2	893.6	895.3	897.2	896.7	896.7	897.6	904.5
5°	883.2	889.3	898.5	907.3	915.8	923.2	928.0	932.9	934.7	943.5	951.5
7.5°	880.1	891.3	906.4	919.8	936.0	948.6	959.0	968.5	974.9	987.8	1000.9
10°	876.0	891.8	908.8	926.2	948.4	965.2	982.2	995.3	999.6	1018.7	1029.7
12.5°	867.6	888.8	910.5	933.0	954.7	977.8	996.5	1009.7	1024.7	1041.9	1062.1
15°	855.2	879.6	907.9	936.9	967.9	995.9	1016.0	1038.9	1055.2	1074.2	1091.8
17.5°	837.4	868.8	904.7	938.2	974.1	1004.2	1031.9	1053.8	1065.4	1076.1	1078.8
20°	823.3	857.0	899.4	939.0	974.9	1009.6	1037.0	1055.2	1058.3	1058.6	1042.4
22.5°	808.0	846.1	890.4	930.9	973.9	1012.5	1033.8	1041.6	1029.6	1008.9	977.7
25°	779.8	823.9	875.3	921.6	968.5	1005.0	1012.4	998.7	956.3	911.8	855.6
27.5°	749.2	798.7	853.9	905.4	955.4	978.0	962.2	912.8	836.6	770.4	690.1
30°	726.8	782.4	836.7	894.2	940.4	950.2	914.0	841.2	752.4	652.5	572.4
32.5°	701.2	759.5	819.1	878.6	917.4	907.8	848.0	758.4	654.2	556.0	480.3
35°	664.6	725.0	789.1	848.8	873.5	832.4	742.9	626.3	519.8	428.1	376.0
37.5°	622.5	688.1	754.9	809.7	808.0	739.4	617.5	497.1	407.6	353.4	316.3
40°	592.5	658.8	731.0	777.3	757.5	668.3	536.1	422.6	357.1	313.9	286.8
42.5°	563.8	630.4	702.1	738.8	704.4	594.8	463.1	374.1	320.1	286.4	264.4
45°	514.9	585.1	651.6	672.0	610.4	489.6	374.5	310.0	274.0	249.1	233.8
47.5°	467.1	536.2	596.8	597.2	514.0	397.1	315.9	268.2	237.6	218.3	207.2
50°	437.8	503.6	554.4	546.5	452.2	353.2	282.5	241.4	215.9	201.0	189.4
52.5°	405.0	468.7	512.7	490.2	399.7	310.8	252.6	218.1	196.9	183.9	173.6
55°	357.1	413.8	444.8	410.7	326.1	258.4	213.4	186.3	170.5	159.6	150.7
57.5°	310.2	356.9	376.4	336.7	268.6	214.3	180.5	160.2	144.5	136.6	132.1
60°	280.7	320.6	334.3	290.5	233.5	187.5	159.9	141.0	129.4	124.3	119.7
62.5°	251.8	284.3	290.0	249.8	203.6	164.2	140.4	124.4	116.8	111.8	107.5
65°	208.9	232.3	229.6	197.3	161.0	130.3	112.9	103.2	97.4	90.4	82.8
67.5°	171.9	186.3	177.7	153.4	122.9	101.3	89.9	82.6	75.4	68.7	67.0
70°	148.5	156.8	147.7	125.5	100.8	85.0	75.8	67.0	62.7	61.2	58.5
72.5°	126.2	129.1	119.2	100.1	82.0	70.4	61.5	56.5	54.2	52.9	51.1
75°	94.7	92.5	84.1	69.1	56.9	49.0	46.3	44.4	43.0	41.7	40.8
77.5°	66.5	63.3	55.8	46.1	39.6	35.9	34.2	33.3	32.5	31.9	31.0
80°	49.9	47.8	40.2	32.9	30.2	28.3	27.4	26.2	26.2	25.6	24.6
82.5°	36.5	34.2	27.6	24.1	22.6	21.5	20.8	20.1	19.8	20.0	19.3
85°	19.2	15.5	13.7	13.1	12.1	11.6	11.9	11.3	11.3	11.3	10.9
87.5°	6.3	5.3	5.4	5.4	5.9	6.1	6.0	6.3	6.7	6.6	7.0
90°	2.0	3.4	4.9	6.3	7.5	8.6	9.6	10.6	11.7	12.3	13.0
92.5°	11.7	11.5	11.4	11.3	11.5	12.0	12.5	13.0	13.5	13.9	14.2
95°	33.7	29.4	25.1	20.8	19.1	20.1	21.0	21.9	22.7	23.4	24.1
97.5°	63.2	51.1	39.1	27.0	22.0	24.1	26.3	28.4	30.4	31.0	31.5
100°	85.4	67.8	50.0	32.2	24.5	26.7	28.9	31.1	33.3	34.2	35.3
102.5°	130.3	126.5	122.8	119.0	107.9	89.4	71.0	52.6	34.2	35.5	36.9
105°	181.2	185.1	189.0	192.8	177.1	141.7	106.3	70.9	35.5	37.0	38.4
107.5°	229.8	232.9	236.0	239.2	219.6	177.1	134.7	92.2	49.8	48.3	46.9
110°	261.1	263.8	266.5	269.2	251.8	214.4	177.0	139.5	102.1	89.1	76.1



TEST NUMBER: P331657-930

CATALOG NUMBER: SA2XXRDIP-C485D725U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	290.7	293.0	295.5	297.8	294.4	285.2	275.9	266.7	257.4	210.2	162.9
115°	337.5	339.7	341.9	344.1	346.9	350.1	353.4	356.6	359.9	299.9	239.9
117.5°	379.9	382.4	384.8	387.3	389.6	391.9	394.1	396.3	398.6	384.1	369.6
120°	410.2	412.1	414.1	416.0	418.2	420.5	422.8	425.2	427.5	429.0	430.6
122.5°	436.4	438.5	440.5	442.5	444.8	447.4	450.0	452.5	455.0	455.9	456.9
125°	475.8	477.5	479.2	480.9	483.0	485.4	487.9	490.3	492.8	493.7	494.6
127.5°	512.1	514.0	515.8	517.6	519.5	521.4	523.2	525.1	526.8	528.2	529.5
130°	535.2	537.2	539.2	541.4	543.1	544.5	545.9	547.4	548.8	550.2	551.6
132.5°	558.2	559.9	561.7	563.5	565.0	566.5	567.9	569.3	570.7	571.9	573.2
135°	588.8	590.8	593.0	595.0	596.6	597.8	598.9	600.1	601.3	602.6	603.9
137.5°	618.8	620.3	621.7	623.2	624.6	625.9	627.2	628.5	629.9	631.1	632.4
140°	638.5	639.5	640.6	641.6	642.9	644.2	645.7	647.1	648.6	649.7	650.9
142.5°	655.2	656.2	657.0	657.9	659.3	660.9	662.5	664.1	665.8	666.8	667.9
145°	680.4	680.4	680.2	680.1	681.1	683.3	685.5	687.7	689.9	690.9	691.8
147.5°	703.1	702.6	702.1	701.6	702.5	704.7	706.8	709.0	711.2	711.8	712.5
150°	717.6	716.7	715.8	714.9	715.5	717.5	719.6	721.7	723.7	724.6	725.3
152.5°	730.1	729.1	728.1	727.1	727.6	729.5	731.5	733.4	735.4	736.2	736.9
155°	748.3	747.1	745.9	744.8	744.9	746.5	748.0	749.6	751.1	752.0	752.8
157.5°	762.8	761.8	760.8	759.9	759.9	761.0	762.1	763.1	764.3	765.2	766.0
160°	771.4	770.6	769.8	769.1	769.1	769.8	770.6	771.4	772.2	773.0	773.7
162.5°	778.9	778.1	777.3	776.5	776.5	777.1	777.8	778.5	779.2	780.1	780.9
165°	788.9	788.1	787.3	786.5	786.4	786.8	787.2	787.5	787.9	788.8	789.7
167.5°	796.4	795.6	794.8	794.0	793.8	794.2	794.5	794.9	795.2	796.1	797.1
170°	800.5	799.8	799.0	798.3	797.9	798.3	798.5	798.7	799.0	799.9	800.8
172.5°	803.3	802.6	801.8	801.0	800.8	801.0	801.3	801.5	801.8	802.7	803.6
175°	806.8	805.9	805.0	804.1	803.8	804.0	804.3	804.5	804.9	805.8	806.7
177.5°	807.6	806.9	806.2	805.4	805.1	805.2	805.4	805.4	805.5	806.2	807.0
180°	806.0	806.0	806.0	806.0	806.0	806.0	806.0	806.0	806.0	806.0	806.0



TEST NUMBER: P331657-930

CATALOG NUMBER: SA2XXRDIP-C485D725U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	876.3	876.3	876.3	876.3	876.3	876.3	876.3
2.5°	906.9	910.1	911.6	911.6	913.3	912.6	911.8
5°	959.0	964.8	966.0	971.5	975.5	974.3	974.9
7.5°	1010.9	1020.2	1029.4	1033.6	1034.3	1036.7	1037.6
10°	1042.8	1050.4	1064.7	1062.6	1073.3	1079.3	1069.3
12.5°	1073.5	1083.8	1093.7	1096.4	1102.4	1104.4	1100.4
15°	1101.2	1106.7	1107.3	1105.8	1107.7	1106.1	1100.3
17.5°	1075.3	1066.4	1048.4	1039.8	1033.1	1023.1	1019.1
20°	1032.4	1006.2	975.8	963.6	949.3	921.3	928.0
22.5°	939.9	910.0	879.6	844.0	827.0	800.5	798.9
25°	795.9	744.4	687.8	648.2	625.1	598.6	587.0
27.5°	618.8	554.0	507.6	484.1	462.7	441.7	440.8
30°	502.4	453.6	417.8	397.6	384.6	375.7	377.6
32.5°	423.5	390.0	365.8	349.2	339.5	332.8	332.7
35°	346.2	323.3	307.8	300.8	293.8	288.9	289.3
37.5°	296.3	282.5	273.9	266.2	261.8	259.4	258.0
40°	270.7	259.4	252.7	248.2	244.5	241.2	240.5
42.5°	250.5	241.2	234.4	230.8	227.5	225.0	224.5
45°	222.3	214.7	208.6	204.6	203.1	201.0	201.0
47.5°	197.7	190.2	185.5	183.0	180.3	179.0	178.9
50°	181.2	175.4	171.1	169.6	167.5	166.6	166.2
52.5°	166.3	162.0	158.9	157.9	156.9	155.8	156.0
55°	146.1	143.7	142.5	141.5	140.1	138.2	139.4
57.5°	129.1	127.1	123.8	120.9	119.5	118.2	118.7
60°	117.2	112.9	108.7	105.3	104.4	101.7	101.7
62.5°	102.2	96.1	90.9	89.0	88.1	86.8	86.6
65°	78.5	76.1	74.9	73.7	73.1	73.1	72.5
67.5°	65.1	64.1	62.8	62.5	61.9	61.7	61.5
70°	57.6	56.3	55.7	55.4	54.8	55.1	54.2
72.5°	50.2	49.2	49.2	48.3	48.0	48.0	47.4
75°	39.5	39.5	39.3	39.0	38.4	38.1	38.4
77.5°	30.4	30.5	29.9	29.9	29.8	29.9	29.6
80°	24.4	24.6	24.4	24.1	23.7	24.1	23.7
82.5°	19.2	18.8	18.8	18.7	18.7	18.4	18.4
85°	10.9	11.3	10.9	10.7	10.7	10.7	10.9
87.5°	6.8	7.0	7.1	7.2	7.2	7.3	7.0
90°	13.6	14.3	14.7	15.0	15.2	15.5	15.7
92.5°	14.5	14.8	15.2	15.2	15.4	15.6	15.7
95°	24.7	25.4	25.6	25.4	25.4	25.2	25.1
97.5°	32.0	32.5	32.9	33.0	33.2	33.3	33.5
100°	36.4	37.4	38.1	38.3	38.6	38.8	39.1
102.5°	38.2	39.5	40.4	40.8	41.2	41.5	41.9
105°	39.9	41.3	42.2	42.8	43.3	43.8	44.4
107.5°	45.4	44.0	43.5	44.0	44.6	45.1	45.6
110°	63.2	50.2	44.0	44.5	45.0	45.6	46.1



TEST NUMBER: P331657-930

CATALOG NUMBER: SA2XXRDIP-C485D725U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	115.6	68.3	44.8	45.3	45.7	46.1	46.6
115°	179.9	119.8	85.1	75.8	66.4	57.2	47.9
117.5°	355.0	340.5	317.9	287.2	256.6	225.9	195.3
120°	432.2	433.7	425.7	408.2	390.8	373.2	355.8
122.5°	457.8	458.8	457.5	454.1	450.7	447.4	443.9
125°	495.5	496.4	497.1	497.5	497.9	498.2	498.6
127.5°	530.8	532.1	532.9	533.0	533.0	533.1	533.2
130°	553.1	554.5	555.1	555.1	554.9	554.7	554.6
132.5°	574.4	575.6	576.2	576.0	575.9	575.8	575.6
135°	605.2	606.5	607.0	606.7	606.5	606.2	605.9
137.5°	633.7	635.0	635.4	635.0	634.5	634.1	633.6
140°	652.0	653.2	653.5	652.8	652.2	651.5	650.9
142.5°	669.0	670.0	670.3	669.6	669.0	668.3	667.6
145°	692.7	693.6	693.7	693.1	692.4	691.8	691.1
147.5°	713.2	713.9	714.0	713.4	712.8	712.3	711.8
150°	726.1	726.8	726.9	726.3	725.6	725.0	724.3
152.5°	737.8	738.6	738.5	737.7	736.8	736.0	735.1
155°	753.5	754.3	754.2	753.1	752.1	751.1	750.0
157.5°	766.9	767.8	767.7	766.7	765.6	764.7	763.7
160°	774.5	775.3	775.2	774.3	773.4	772.5	771.6
162.5°	781.8	782.7	782.6	781.5	780.3	779.3	778.1
165°	790.7	791.6	791.6	790.7	789.7	788.8	787.9
167.5°	798.0	798.9	798.7	797.6	796.5	795.2	794.1
170°	801.7	802.7	802.5	801.4	800.1	799.0	797.9
172.5°	804.5	805.4	805.3	804.1	803.0	801.8	800.6
175°	807.6	808.5	808.3	807.0	805.7	804.4	803.1
177.5°	807.7	808.5	808.4	807.4	806.5	805.5	804.6
180°	806.0	806.0	806.0	806.0	806.0	806.0	806.0

(END OF REPORT)