

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331435-927

Luminaire Tested: **SA2XXDIP-C1005D530U927-4F0-1E-UDD-F**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331435-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C1005D530U927-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 530 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4888.0 lumens
Efficiency: N/A
Efficacy: 88.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 55.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331435-927

CATALOG NUMBER: SA2XXDIP-C1005D530U927-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331435-927

CATALOG NUMBER: SA2XXDIP-C1005D530U927-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	71	71	71	66
1	101	97	93	89	95	91	88	85	81	78	76	71	69	67	62	61	60	55
2	92	85	78	73	87	80	74	70	71	67	63	63	59	56	55	52	50	46
3	84	74	67	61	79	70	64	58	63	57	53	55	51	48	49	46	43	39
4	77	66	58	52	72	62	55	49	56	50	45	49	45	41	44	40	37	34
5	71	59	51	44	66	56	48	43	50	44	39	44	39	36	39	35	32	29
6	65	53	45	39	61	50	43	37	45	39	34	40	35	31	36	32	28	26
7	61	48	40	34	57	45	38	33	41	35	30	37	32	28	33	28	25	23
8	56	44	36	30	53	41	34	29	37	31	27	34	28	25	30	26	23	20
9	52	40	32	27	49	38	31	26	34	28	24	31	26	22	28	24	20	18
10	49	37	29	24	46	35	28	24	32	26	22	29	24	20	26	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	20386	20386	20386
5°	20464	20169	20285
10°	20341	19964	20064
15°	20090	19704	19686
20°	19734	19316	19295
25°	19379	18838	18838
30°	18921	18401	18243
35°	18496	17875	17611
40°	17962	17351	17015
45°	17438	16826	16411
50°	16865	16284	15707
55°	16268	15651	15071
60°	15603	14899	14347
65°	14888	14147	13498
70°	13983	13237	12609
75°	12726	12190	11890
80°	11288	10953	10386
85°	9207	8781	7873



TEST NUMBER: P331435-927

CATALOG NUMBER: SA2XXDIP-C1005D530U927-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	118.7	2.4
10°-20°	334.1	6.8
20°-30°	491.0	10.0
30°-40°	570.4	11.7
40°-50°	569.8	11.7
50°-60°	496.9	10.2
60°-70°	367.4	7.5
70°-80°	208.1	4.3
80°-90°	57.4	1.2
90°-100°	19.1	0.4
100°-110°	69.9	1.4
110°-120°	186.8	3.8
120°-130°	308.4	6.3
130°-140°	328.0	6.7
140°-150°	304.8	6.2
150°-160°	245.1	5.0
160°-170°	157.9	3.2
170°-180°	54.4	1.1
0°-30°	943.8	19.3
0°-40°	1514.2	31.0
0°-60°	2580.8	52.8
0°-90°	3213.7	65.7
90°-120°	275.8	5.6
90°-150°	1217.0	24.9
90°-180°	1674.0	34.2
0°-180°	4888.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1263	1263	1263	1263	1263	
5°	1263	1257	1244	1253	1252	120
15°	1202	1194	1179	1183	1178	338
25°	1088	1078	1057	1060	1057	500
35°	938	926	907	900	894	586
45°	764	755	737	724	719	589
55°	578	570	556	542	535	517
65°	390	382	370	360	353	385
75°	204	201	195	189	191	218
85°	50	49	47	44	42	57
90°	0	5	8	10	11	4
95°	27	14	16	18	18	33
105°	126	131	25	30	31	134
115°	238	245	255	73	34	234
125°	336	342	349	352	354	300
135°	416	422	426	430	430	321
145°	482	482	489	492	490	302
155°	531	528	532	535	532	245
165°	560	558	558	561	558	158
175°	573	570	570	573	569	54
180°	571	571	571	571	571	



TEST NUMBER: P331435-927

CATALOG NUMBER: SA2XXDIP-C1005D530U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6
2.5°	1268.4	1267.3	1266.3	1265.2	1264.1	1262.4	1260.0	1257.7	1255.3	1252.9	1255.1
5°	1262.6	1261.6	1260.4	1259.3	1258.3	1256.2	1253.3	1250.3	1247.4	1244.4	1246.6
7.5°	1251.4	1249.7	1248.1	1246.4	1244.8	1242.4	1239.4	1236.4	1233.3	1230.3	1232.5
10°	1240.7	1238.9	1237.0	1235.1	1233.2	1230.7	1227.4	1224.2	1220.9	1217.7	1219.9
12.5°	1226.2	1224.5	1222.8	1221.1	1219.5	1217.0	1213.8	1210.5	1207.4	1204.1	1205.6
15°	1201.9	1200.3	1198.7	1197.1	1195.4	1192.9	1189.4	1185.8	1182.3	1178.8	1180.0
17.5°	1170.8	1169.2	1167.6	1165.9	1164.3	1161.7	1158.2	1154.6	1151.0	1147.6	1148.7
20°	1148.5	1146.8	1145.3	1143.6	1142.0	1139.3	1135.5	1131.8	1128.0	1124.2	1125.0
22.5°	1126.2	1123.9	1121.7	1119.4	1117.1	1114.2	1110.6	1107.1	1103.5	1099.9	1100.1
25°	1087.8	1085.6	1083.5	1081.3	1079.2	1075.8	1071.2	1066.6	1062.0	1057.4	1058.0
27.5°	1044.1	1042.1	1040.2	1038.2	1036.3	1033.6	1029.9	1026.3	1022.7	1019.1	1018.3
30°	1014.9	1012.8	1010.6	1008.4	1006.3	1003.2	999.2	995.1	991.1	987.0	986.2
32.5°	983.9	982.1	980.4	978.7	976.9	974.0	969.7	965.4	961.2	956.9	955.5
35°	938.4	935.7	933.0	930.3	927.6	924.2	919.8	915.5	911.2	906.9	905.3
37.5°	887.2	884.9	882.5	880.1	877.7	874.4	870.1	865.8	861.4	857.1	855.1
40°	852.2	850.1	848.0	845.8	843.6	840.4	836.1	831.8	827.4	823.2	820.7
42.5°	818.2	816.1	814.0	811.8	809.6	806.4	802.1	797.7	793.4	789.1	786.5
45°	763.7	761.8	759.9	758.0	756.1	753.1	749.1	745.0	741.0	736.9	734.0
47.5°	709.2	707.5	705.7	703.9	702.1	699.1	694.9	690.7	686.5	682.3	679.1
50°	671.4	670.0	668.7	667.3	666.0	663.4	659.7	655.8	652.0	648.3	644.5
52.5°	634.5	632.7	630.9	629.2	627.3	624.6	621.1	617.5	614.0	610.5	607.3
55°	577.9	576.2	574.6	573.1	571.4	568.9	565.8	562.5	559.3	556.0	552.8
57.5°	521.1	519.8	518.5	517.2	515.9	513.5	509.9	506.4	502.8	499.2	496.1
60°	483.2	482.1	481.0	480.0	478.9	476.4	472.7	468.9	465.1	461.4	458.4
62.5°	446.3	444.6	442.8	441.1	439.3	437.0	434.1	431.3	428.3	425.4	422.6
65°	389.7	388.1	386.5	384.8	383.3	381.0	378.3	375.7	373.0	370.3	367.9
67.5°	332.2	330.9	329.5	328.3	327.0	325.1	322.7	320.3	317.8	315.4	313.5
70°	296.2	295.2	294.1	293.0	291.9	290.2	287.7	285.3	282.9	280.4	278.5
72.5°	259.3	258.3	257.1	256.1	255.0	253.7	252.2	250.6	249.0	247.4	245.5
75°	204.0	203.4	202.9	202.3	201.8	200.8	199.5	198.1	196.8	195.4	193.8
77.5°	154.4	153.5	152.6	151.7	150.8	150.0	149.5	148.9	148.4	147.9	147.0
80°	121.4	121.1	120.9	120.6	120.3	119.9	119.4	118.8	118.3	117.8	116.9
82.5°	90.3	90.3	90.2	90.2	90.1	89.9	89.6	89.3	89.0	88.6	87.6
85°	49.7	49.5	49.3	49.0	48.7	48.4	48.2	47.8	47.6	47.4	46.5
87.5°	17.6	17.3	17.1	16.9	16.6	16.4	16.1	15.8	15.5	15.3	14.7
90°	0.4	1.4	2.5	3.4	4.4	5.3	6.1	6.8	7.5	8.2	8.7
92.5°	8.3	8.2	8.2	8.1	8.0	8.2	8.5	8.9	9.2	9.6	9.8
95°	26.9	23.8	20.8	17.7	14.7	13.5	14.2	14.8	15.4	16.2	16.6
97.5°	53.3	44.8	36.3	27.7	19.2	15.6	17.1	18.6	20.1	21.5	21.9
100°	73.2	60.6	48.0	35.4	22.8	17.3	18.9	20.4	22.0	23.5	24.3
102.5°	95.0	92.4	89.7	87.0	84.4	76.4	63.5	50.4	37.3	24.2	25.2
105°	125.6	128.4	131.2	134.0	136.7	125.6	100.4	75.4	50.3	25.2	26.2
107.5°	160.7	162.9	165.1	167.3	169.5	155.6	125.6	95.5	65.4	35.3	34.3
110°	183.2	185.1	187.0	188.9	190.8	178.6	152.0	125.5	98.9	72.3	63.1



TEST NUMBER: P331435-927

CATALOG NUMBER: SA2XXDIP-C1005D530U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	204.3	206.0	207.7	209.5	211.1	208.7	202.2	195.6	189.0	182.5	148.9
115°	237.7	239.2	240.8	242.4	244.0	245.9	248.2	250.5	252.8	255.1	212.5
117.5°	267.6	269.3	271.1	272.8	274.6	276.2	277.8	279.4	281.0	282.5	272.3
120°	289.4	290.7	292.2	293.5	294.9	296.4	298.1	299.8	301.3	303.0	304.1
122.5°	307.9	309.3	310.9	312.3	313.7	315.4	317.1	318.9	320.8	322.6	323.2
125°	336.1	337.3	338.5	339.7	340.9	342.4	344.1	345.9	347.6	349.4	350.0
127.5°	361.6	363.0	364.3	365.6	366.9	368.3	369.6	370.9	372.2	373.5	374.4
130°	377.9	379.3	380.8	382.3	383.7	385.0	386.0	387.0	388.0	389.0	390.1
132.5°	394.4	395.6	396.9	398.2	399.4	400.5	401.6	402.6	403.5	404.6	405.4
135°	415.9	417.4	418.8	420.3	421.8	422.9	423.7	424.6	425.4	426.2	427.1
137.5°	437.7	438.6	439.7	440.7	441.7	442.8	443.7	444.7	445.5	446.5	447.4
140°	451.9	452.6	453.4	454.1	454.8	455.7	456.7	457.7	458.7	459.7	460.6
142.5°	463.7	464.5	465.1	465.7	466.4	467.3	468.5	469.6	470.8	472.0	472.7
145°	482.4	482.4	482.3	482.2	482.1	482.8	484.4	485.9	487.5	489.1	489.7
147.5°	498.8	498.4	498.0	497.7	497.3	498.0	499.5	501.1	502.6	504.1	504.6
150°	509.3	508.7	508.0	507.4	506.8	507.2	508.7	510.1	511.6	513.0	513.6
152.5°	518.2	517.5	516.8	516.1	515.4	515.7	517.1	518.6	519.9	521.3	521.9
155°	531.2	530.4	529.6	528.8	527.9	528.1	529.2	530.3	531.4	532.5	533.1
157.5°	541.4	540.7	540.0	539.3	538.6	538.7	539.4	540.2	541.0	541.8	542.3
160°	547.4	546.8	546.3	545.7	545.2	545.2	545.7	546.3	546.8	547.4	548.0
162.5°	552.6	552.1	551.5	551.0	550.5	550.4	550.9	551.4	551.8	552.3	552.9
165°	559.8	559.2	558.6	558.1	557.5	557.5	557.7	557.9	558.3	558.5	559.2
167.5°	565.1	564.5	564.0	563.4	562.8	562.7	562.9	563.2	563.5	563.7	564.4
170°	568.0	567.5	567.0	566.4	565.9	565.6	565.9	566.0	566.2	566.4	567.0
172.5°	570.1	569.5	568.9	568.4	567.8	567.6	567.8	568.0	568.2	568.4	569.0
175°	572.6	572.0	571.3	570.7	570.0	569.8	570.0	570.1	570.3	570.5	571.2
177.5°	573.0	572.5	572.0	571.5	570.9	570.7	570.8	570.8	570.9	571.0	571.6
180°	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3



TEST NUMBER: P331435-927

CATALOG NUMBER: SA2XXDIP-C1005D530U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6
2.5°	1257.2	1259.3	1261.6	1262.4	1261.9	1261.6	1261.1	1260.7
5°	1248.7	1250.9	1253.0	1253.9	1253.3	1252.8	1252.2	1251.6
7.5°	1234.6	1236.8	1239.0	1239.8	1239.1	1238.6	1237.9	1237.4
10°	1222.0	1224.2	1226.3	1227.0	1226.2	1225.3	1224.6	1223.8
12.5°	1207.1	1208.6	1210.1	1210.6	1210.0	1209.4	1208.8	1208.2
15°	1181.0	1182.1	1183.1	1183.0	1181.7	1180.4	1179.0	1177.7
17.5°	1150.0	1151.3	1152.5	1152.5	1151.1	1149.9	1148.6	1147.2
20°	1125.8	1126.6	1127.4	1127.3	1126.2	1125.1	1124.1	1123.0
22.5°	1100.3	1100.4	1100.6	1100.3	1099.7	1099.1	1098.4	1097.7
25°	1058.5	1059.1	1059.6	1059.6	1059.1	1058.5	1058.0	1057.4
27.5°	1017.5	1016.6	1015.8	1014.8	1013.5	1012.2	1010.9	1009.6
30°	985.4	984.6	983.8	982.9	981.8	980.6	979.6	978.5
32.5°	954.0	952.5	951.1	949.8	948.7	947.7	946.6	945.5
35°	903.6	902.1	900.4	899.0	897.6	896.3	894.8	893.5
37.5°	853.1	851.1	849.1	847.5	846.2	844.9	843.6	842.3
40°	818.2	815.9	813.4	811.7	810.6	809.5	808.4	807.3
42.5°	783.9	781.2	778.6	776.5	775.0	773.5	772.0	770.4
45°	731.0	728.0	725.1	723.0	721.9	720.9	719.8	718.7
47.5°	676.0	672.9	669.8	667.4	665.8	664.3	662.7	661.2
50°	640.7	637.0	633.2	630.7	629.3	628.0	626.6	625.3
52.5°	604.2	601.0	597.9	595.5	593.7	591.9	590.1	588.4
55°	549.5	546.3	543.1	540.8	539.5	538.1	536.8	535.4
57.5°	492.8	489.6	486.5	484.3	483.4	482.4	481.3	480.3
60°	455.4	452.4	449.5	447.6	446.8	446.0	445.1	444.3
62.5°	419.9	417.2	414.4	412.5	411.5	410.4	409.4	408.4
65°	365.4	363.0	360.6	358.7	357.4	356.0	354.7	353.3
67.5°	311.6	309.7	307.8	306.3	305.3	304.2	303.2	302.1
70°	276.6	274.8	272.9	271.4	270.3	269.3	268.2	267.1
72.5°	243.7	241.8	239.9	238.5	237.7	236.8	235.9	235.0
75°	192.3	190.6	189.0	188.5	189.0	189.5	190.0	190.6
77.5°	146.2	145.4	144.7	143.9	143.1	142.4	141.6	140.9
80°	116.1	115.3	114.5	113.8	113.3	112.8	112.3	111.7
82.5°	86.6	85.6	84.5	84.0	83.8	83.7	83.7	83.5
85°	45.7	44.9	44.1	43.6	43.3	43.0	42.8	42.5
87.5°	14.1	13.5	13.0	12.7	12.5	12.3	12.1	12.0
90°	9.2	9.7	10.1	10.5	10.6	10.8	11.0	11.2
92.5°	10.1	10.3	10.5	10.7	10.9	10.9	11.1	11.2
95°	17.0	17.5	18.0	18.1	18.1	18.0	17.9	17.7
97.5°	22.3	22.7	23.1	23.3	23.4	23.5	23.6	23.8
100°	25.0	25.7	26.5	26.9	27.2	27.3	27.5	27.7
102.5°	26.1	27.1	28.0	28.7	28.9	29.2	29.4	29.7
105°	27.3	28.3	29.2	29.9	30.3	30.7	31.1	31.4
107.5°	33.3	32.2	31.2	30.9	31.2	31.6	31.9	32.3
110°	53.9	44.8	35.6	31.2	31.5	31.9	32.3	32.6



TEST NUMBER: P331435-927

CATALOG NUMBER: SA2XXDIP-C1005D530U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	115.4	81.9	48.4	31.8	32.1	32.4	32.7	33.0
115°	170.0	127.5	84.9	60.4	53.7	47.1	40.5	33.9
117.5°	262.0	251.7	241.4	225.4	203.6	181.9	160.2	138.4
120°	305.2	306.3	307.4	301.8	289.4	277.0	264.6	252.2
122.5°	323.8	324.6	325.2	324.3	321.9	319.5	317.1	314.7
125°	350.6	351.3	351.9	352.4	352.7	352.9	353.2	353.5
127.5°	375.3	376.3	377.2	377.7	377.8	377.9	377.9	378.0
130°	391.0	392.1	393.1	393.6	393.4	393.3	393.2	393.2
132.5°	406.3	407.2	408.1	408.4	408.3	408.2	408.1	408.1
135°	428.1	429.0	429.9	430.3	430.1	429.9	429.8	429.5
137.5°	448.3	449.2	450.1	450.4	450.0	449.7	449.5	449.2
140°	461.4	462.2	463.0	463.2	462.7	462.3	461.8	461.4
142.5°	473.5	474.2	475.0	475.2	474.7	474.2	473.7	473.2
145°	490.4	491.0	491.6	491.7	491.3	490.8	490.4	489.9
147.5°	505.1	505.6	506.0	506.0	505.7	505.3	504.9	504.5
150°	514.1	514.7	515.2	515.3	514.8	514.4	513.9	513.5
152.5°	522.4	523.0	523.6	523.5	522.9	522.3	521.7	521.1
155°	533.6	534.2	534.7	534.6	533.9	533.1	532.4	531.6
157.5°	543.0	543.6	544.2	544.2	543.4	542.7	542.0	541.3
160°	548.4	549.0	549.5	549.5	548.9	548.3	547.6	546.9
162.5°	553.6	554.2	554.8	554.8	554.0	553.2	552.4	551.6
165°	559.8	560.5	561.1	561.1	560.5	559.8	559.2	558.5
167.5°	565.0	565.7	566.3	566.3	565.4	564.6	563.7	562.9
170°	567.7	568.3	568.9	568.9	568.0	567.2	566.4	565.5
172.5°	569.7	570.3	570.9	570.8	570.1	569.2	568.4	567.5
175°	571.8	572.4	573.1	573.0	572.0	571.1	570.2	569.3
177.5°	572.0	572.6	573.1	573.0	572.4	571.6	571.0	570.4
180°	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3

(END OF REPORT)