

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331436-927

Luminaire Tested: **SA2XXDIP-C1005D530U927-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331436-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C1005D530U927-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 530 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4711.2 lumens
Efficiency: N/A
Efficacy: 85.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 55.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331436-927
CATALOG NUMBER: SA2XXDIP-C1005D530U927-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331436-927

CATALOG NUMBER: SA2XXDIP-C1005D530U927-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	105	105	105	105	93	93	93	83	83	83	73	73	73	68
1	102	97	93	90	96	92	89	85	82	79	77	73	71	69	64	63	62	57
2	93	85	79	73	87	81	75	70	72	68	64	64	61	58	57	54	52	48
3	85	75	67	61	80	71	64	59	64	58	54	57	52	49	50	47	44	41
4	78	66	58	52	73	63	56	50	57	51	46	51	46	42	45	41	38	35
5	71	59	51	45	67	56	49	43	51	44	40	45	40	36	41	36	33	30
6	66	53	45	39	62	51	43	37	46	39	35	41	36	32	37	33	29	27
7	61	48	40	34	57	46	38	33	42	35	31	37	32	28	34	29	26	24
8	57	44	36	30	53	42	35	29	38	32	27	34	29	25	31	27	23	21
9	53	40	32	27	50	38	31	26	35	29	25	32	27	23	29	24	21	19
10	49	37	30	25	47	35	28	24	32	26	22	29	24	21	27	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	20386	20386	20386
5°	20464	20169	20285
10°	20341	19964	20064
15°	20090	19704	19686
20°	19734	19316	19295
25°	19379	18838	18838
30°	18921	18401	18243
35°	18496	17875	17611
40°	17962	17351	17015
45°	17438	16826	16411
50°	16865	16284	15707
55°	16268	15651	15071
60°	15603	14899	14347
65°	14888	14147	13498
70°	13983	13237	12609
75°	12726	12190	11890
80°	11288	10953	10386
85°	9207	8781	7873



TEST NUMBER: P331436-927

CATALOG NUMBER: SA2XXDIP-C1005D530U927-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	118.7	2.5
10°-20°	334.1	7.1
20°-30°	491.0	10.4
30°-40°	570.4	12.1
40°-50°	569.8	12.1
50°-60°	496.9	10.5
60°-70°	367.4	7.8
70°-80°	208.1	4.4
80°-90°	58.1	1.2
90°-100°	33.9	0.7
100°-110°	105.4	2.2
110°-120°	180.1	3.8
120°-130°	236.8	5.0
130°-140°	265.8	5.6
140°-150°	260.6	5.5
150°-160°	218.6	4.6
160°-170°	145.0	3.1
170°-180°	50.7	1.1
0°-30°	943.8	20.0
0°-40°	1514.2	32.1
0°-60°	2580.8	54.8
0°-90°	3214.4	68.2
90°-120°	319.4	6.8
90°-150°	1082.6	23.0
90°-180°	1497.0	31.8
0°-180°	4711.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1263	1263	1263	1263	1263	
5°	1263	1257	1244	1253	1252	120
15°	1202	1194	1179	1183	1178	338
25°	1088	1078	1057	1060	1057	500
35°	938	926	907	900	894	586
45°	764	755	737	724	719	589
55°	578	570	556	542	535	517
65°	390	382	370	360	353	385
75°	204	201	195	189	191	218
85°	50	49	47	44	42	57
90°	0	6	16	15	15	4
95°	24	28	29	29	28	27
105°	97	98	99	100	100	103
115°	181	183	182	182	181	179
125°	263	267	266	264	264	235
135°	340	345	346	346	344	263
145°	413	416	419	419	417	258
155°	472	473	475	477	476	217
165°	514	513	513	516	514	145
175°	534	533	532	535	533	51
180°	535	535	535	535	535	



TEST NUMBER: P331436-927

CATALOG NUMBER: SA2XXDIP-C1005D530U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6
2.5°	1268.4	1267.3	1266.3	1265.2	1264.1	1262.4	1260.0	1257.7	1255.3	1252.9	1255.1
5°	1262.6	1261.6	1260.4	1259.3	1258.3	1256.2	1253.3	1250.3	1247.4	1244.4	1246.6
7.5°	1251.4	1249.7	1248.1	1246.4	1244.8	1242.4	1239.4	1236.4	1233.3	1230.3	1232.5
10°	1240.7	1238.9	1237.0	1235.1	1233.2	1230.7	1227.4	1224.2	1220.9	1217.7	1219.9
12.5°	1226.2	1224.5	1222.8	1221.1	1219.5	1217.0	1213.8	1210.5	1207.4	1204.1	1205.6
15°	1201.9	1200.3	1198.7	1197.1	1195.4	1192.9	1189.4	1185.8	1182.3	1178.8	1180.0
17.5°	1170.8	1169.2	1167.6	1165.9	1164.3	1161.7	1158.2	1154.6	1151.0	1147.6	1148.7
20°	1148.5	1146.8	1145.3	1143.6	1142.0	1139.3	1135.5	1131.8	1128.0	1124.2	1125.0
22.5°	1126.2	1123.9	1121.7	1119.4	1117.1	1114.2	1110.6	1107.1	1103.5	1099.9	1100.1
25°	1087.8	1085.6	1083.5	1081.3	1079.2	1075.8	1071.2	1066.6	1062.0	1057.4	1058.0
27.5°	1044.1	1042.1	1040.2	1038.2	1036.3	1033.6	1029.9	1026.3	1022.7	1019.1	1018.3
30°	1014.9	1012.8	1010.6	1008.4	1006.3	1003.2	999.2	995.1	991.1	987.0	986.2
32.5°	983.9	982.1	980.4	978.7	976.9	974.0	969.7	965.4	961.2	956.9	955.5
35°	938.4	935.7	933.0	930.3	927.6	924.2	919.8	915.5	911.2	906.9	905.3
37.5°	887.2	884.9	882.5	880.1	877.7	874.4	870.1	865.8	861.4	857.1	855.1
40°	852.2	850.1	848.0	845.8	843.6	840.4	836.1	831.8	827.4	823.2	820.7
42.5°	818.2	816.1	814.0	811.8	809.6	806.4	802.1	797.7	793.4	789.1	786.5
45°	763.7	761.8	759.9	758.0	756.1	753.1	749.1	745.0	741.0	736.9	734.0
47.5°	709.2	707.5	705.7	703.9	702.1	699.1	694.9	690.7	686.5	682.3	679.1
50°	671.4	670.0	668.7	667.3	666.0	663.4	659.7	655.8	652.0	648.3	644.5
52.5°	634.5	632.7	630.9	629.2	627.3	624.6	621.1	617.5	614.0	610.5	607.3
55°	577.9	576.2	574.6	573.1	571.4	568.9	565.8	562.5	559.3	556.0	552.8
57.5°	521.1	519.8	518.5	517.2	515.9	513.5	509.9	506.4	502.8	499.2	496.1
60°	483.2	482.1	481.0	480.0	478.9	476.4	472.7	468.9	465.1	461.4	458.4
62.5°	446.3	444.6	442.8	441.1	439.3	437.0	434.1	431.3	428.3	425.4	422.6
65°	389.7	388.1	386.5	384.8	383.3	381.0	378.3	375.7	373.0	370.3	367.9
67.5°	332.2	330.9	329.5	328.3	327.0	325.1	322.7	320.3	317.8	315.4	313.5
70°	296.2	295.2	294.1	293.0	291.9	290.2	287.7	285.3	282.9	280.4	278.5
72.5°	259.3	258.3	257.1	256.1	255.0	253.7	252.2	250.6	249.0	247.4	245.5
75°	204.0	203.4	202.9	202.3	201.8	200.8	199.5	198.1	196.8	195.4	193.8
77.5°	154.4	153.5	152.6	151.7	150.8	150.0	149.5	148.9	148.4	147.9	147.0
80°	121.4	121.1	120.9	120.6	120.3	119.9	119.4	118.8	118.3	117.8	116.9
82.5°	90.3	90.3	90.2	90.2	90.1	89.9	89.6	89.3	89.0	88.6	87.6
85°	49.7	49.5	49.3	49.0	48.7	48.4	48.2	47.8	47.6	47.4	46.5
87.5°	17.6	17.3	17.2	17.0	16.8	16.7	16.7	16.7	16.7	16.8	16.1
90°	0.5	1.7	2.9	4.0	5.3	7.0	9.2	11.4	13.6	15.8	15.6
92.5°	8.1	9.0	9.8	10.7	11.6	12.3	12.8	13.3	13.9	14.3	14.4
95°	23.5	24.5	25.5	26.5	27.5	28.1	28.3	28.5	28.7	28.9	28.9
97.5°	42.9	43.8	44.7	45.6	46.4	47.1	47.5	47.8	48.2	48.6	48.6
100°	57.4	58.1	58.9	59.8	60.6	61.2	61.5	61.7	62.0	62.3	62.3
102.5°	72.6	73.2	73.8	74.5	75.1	75.7	76.0	76.4	76.8	77.2	77.2
105°	97.1	97.4	97.8	98.0	98.3	98.5	98.8	98.9	99.2	99.4	99.6
107.5°	121.9	122.3	122.8	123.2	123.7	123.9	123.9	123.9	123.9	123.9	124.0
110°	137.8	138.4	138.9	139.6	140.2	140.5	140.5	140.5	140.5	140.5	140.5



TEST NUMBER: P331436-927

CATALOG NUMBER: SA2XXDIP-C1005D530U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	155.1	155.7	156.3	156.9	157.6	157.8	157.7	157.6	157.6	157.5	157.2
115°	180.7	181.3	181.9	182.5	183.1	183.3	183.1	182.9	182.7	182.5	182.4
117.5°	206.2	207.0	207.8	208.6	209.4	209.5	209.0	208.3	207.8	207.2	207.0
120°	223.2	223.9	224.7	225.5	226.4	226.4	225.5	224.7	223.9	223.2	223.2
122.5°	238.7	239.6	240.7	241.6	242.6	242.7	242.2	241.6	241.1	240.5	240.3
125°	262.9	263.8	264.7	265.6	266.5	266.8	266.5	266.3	265.9	265.6	265.3
127.5°	286.5	287.6	288.8	289.9	291.0	291.4	291.1	290.7	290.4	290.0	289.6
130°	301.3	302.6	303.9	305.2	306.5	307.0	306.9	306.7	306.5	306.3	306.1
132.5°	317.9	319.0	320.0	321.2	322.2	322.7	322.8	322.8	322.9	322.9	322.5
135°	340.2	341.3	342.4	343.5	344.6	345.2	345.4	345.6	345.9	346.0	345.9
137.5°	363.5	364.5	365.4	366.3	367.2	367.7	368.0	368.3	368.5	368.8	368.7
140°	377.6	378.6	379.5	380.3	381.3	382.0	382.5	382.9	383.5	384.0	384.0
142.5°	392.1	393.0	394.0	394.8	395.7	396.3	396.7	397.0	397.4	397.7	397.8
145°	412.9	413.6	414.3	415.0	415.7	416.4	416.9	417.6	418.2	418.7	418.8
147.5°	431.4	432.2	433.1	434.0	434.7	435.4	435.8	436.2	436.6	437.0	437.2
150°	444.1	444.7	445.3	445.8	446.5	446.9	447.3	447.7	448.1	448.6	448.9
152.5°	455.3	455.9	456.5	457.1	457.6	458.2	458.7	459.1	459.6	460.2	460.5
155°	472.1	472.4	472.7	472.9	473.2	473.6	473.9	474.2	474.4	474.8	475.3
157.5°	486.4	486.6	486.8	487.0	487.3	487.4	487.6	487.8	488.0	488.1	488.9
160°	495.1	495.3	495.5	495.7	495.9	496.1	496.1	496.2	496.4	496.5	497.1
162.5°	503.0	503.1	503.1	503.2	503.2	503.3	503.4	503.5	503.6	503.7	504.4
165°	513.7	513.5	513.4	513.3	513.3	513.2	513.2	513.2	513.2	513.2	513.9
167.5°	522.4	522.2	521.9	521.6	521.3	521.1	521.1	521.1	521.0	521.0	521.7
170°	527.2	526.9	526.6	526.2	526.0	525.8	525.7	525.5	525.5	525.4	526.1
172.5°	530.4	530.1	529.8	529.5	529.3	529.0	528.9	528.9	528.7	528.6	529.3
175°	534.4	534.1	533.8	533.5	533.2	533.0	532.7	532.6	532.3	532.1	532.8
177.5°	536.1	535.8	535.5	535.3	535.0	534.9	534.7	534.6	534.4	534.2	534.7
180°	535.3	535.3	535.3	535.3	535.3	535.3	535.3	535.3	535.3	535.3	535.3



TEST NUMBER: P331436-927

CATALOG NUMBER: SA2XXDIP-C1005D530U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6
2.5°	1257.2	1259.3	1261.6	1262.4	1261.9	1261.6	1261.1	1260.7
5°	1248.7	1250.9	1253.0	1253.9	1253.3	1252.8	1252.2	1251.6
7.5°	1234.6	1236.8	1239.0	1239.8	1239.1	1238.6	1237.9	1237.4
10°	1222.0	1224.2	1226.3	1227.0	1226.2	1225.3	1224.6	1223.8
12.5°	1207.1	1208.6	1210.1	1210.6	1210.0	1209.4	1208.8	1208.2
15°	1181.0	1182.1	1183.1	1183.0	1181.7	1180.4	1179.0	1177.7
17.5°	1150.0	1151.3	1152.5	1152.5	1151.1	1149.9	1148.6	1147.2
20°	1125.8	1126.6	1127.4	1127.3	1126.2	1125.1	1124.1	1123.0
22.5°	1100.3	1100.4	1100.6	1100.3	1099.7	1099.1	1098.4	1097.7
25°	1058.5	1059.1	1059.6	1059.6	1059.1	1058.5	1058.0	1057.4
27.5°	1017.5	1016.6	1015.8	1014.8	1013.5	1012.2	1010.9	1009.6
30°	985.4	984.6	983.8	982.9	981.8	980.6	979.6	978.5
32.5°	954.0	952.5	951.1	949.8	948.7	947.7	946.6	945.5
35°	903.6	902.1	900.4	899.0	897.6	896.3	894.8	893.5
37.5°	853.1	851.1	849.1	847.5	846.2	844.9	843.6	842.3
40°	818.2	815.9	813.4	811.7	810.6	809.5	808.4	807.3
42.5°	783.9	781.2	778.6	776.5	775.0	773.5	772.0	770.4
45°	731.0	728.0	725.1	723.0	721.9	720.9	719.8	718.7
47.5°	676.0	672.9	669.8	667.4	665.8	664.3	662.7	661.2
50°	640.7	637.0	633.2	630.7	629.3	628.0	626.6	625.3
52.5°	604.2	601.0	597.9	595.5	593.7	591.9	590.1	588.4
55°	549.5	546.3	543.1	540.8	539.5	538.1	536.8	535.4
57.5°	492.8	489.6	486.5	484.3	483.4	482.4	481.3	480.3
60°	455.4	452.4	449.5	447.6	446.8	446.0	445.1	444.3
62.5°	419.9	417.2	414.4	412.5	411.5	410.4	409.4	408.4
65°	365.4	363.0	360.6	358.7	357.4	356.0	354.7	353.3
67.5°	311.6	309.7	307.8	306.3	305.3	304.2	303.2	302.1
70°	276.6	274.8	272.9	271.4	270.3	269.3	268.2	267.1
72.5°	243.7	241.8	239.9	238.5	237.7	236.8	235.9	235.0
75°	192.3	190.6	189.0	188.5	189.0	189.5	190.0	190.6
77.5°	146.2	145.4	144.7	143.9	143.1	142.4	141.6	140.9
80°	116.1	115.3	114.5	113.8	113.3	112.8	112.3	111.7
82.5°	86.6	85.6	84.5	84.0	83.8	83.7	83.7	83.5
85°	45.7	44.9	44.1	43.6	43.3	43.0	42.8	42.5
87.5°	15.4	14.7	14.0	13.5	13.4	13.2	13.0	12.8
90°	15.4	15.2	15.0	15.0	15.1	15.1	15.3	15.4
92.5°	14.4	14.5	14.5	14.6	14.6	14.6	14.7	14.7
95°	28.9	28.9	28.9	28.8	28.6	28.4	28.2	28.0
97.5°	48.6	48.6	48.6	48.6	48.6	48.6	48.6	48.5
100°	62.3	62.3	62.3	62.3	62.2	62.1	62.0	61.9
102.5°	77.3	77.4	77.5	77.5	77.4	77.2	77.2	77.1
105°	99.8	100.0	100.2	100.3	100.3	100.3	100.3	100.3
107.5°	124.1	124.1	124.2	124.0	123.5	123.1	122.6	122.2
110°	140.5	140.5	140.5	140.4	140.1	139.7	139.4	139.1



TEST NUMBER: P331436-927

CATALOG NUMBER: SA2XXDIP-C1005D530U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	157.0	156.8	156.5	156.3	156.1	155.8	155.6	155.4
115°	182.3	182.2	182.1	181.9	181.6	181.3	181.0	180.7
117.5°	206.8	206.5	206.3	206.0	205.7	205.4	205.1	204.8
120°	223.2	223.2	223.2	223.0	222.7	222.4	222.1	221.8
122.5°	240.0	239.8	239.6	239.3	239.1	238.8	238.7	238.4
125°	265.0	264.7	264.4	264.2	264.1	264.0	263.9	263.8
127.5°	289.3	288.9	288.6	288.2	287.9	287.6	287.2	286.9
130°	305.9	305.7	305.5	305.1	304.8	304.4	304.0	303.6
132.5°	322.0	321.5	321.2	320.8	320.4	320.1	319.8	319.5
135°	345.9	345.7	345.6	345.4	345.2	344.8	344.5	344.2
137.5°	368.6	368.5	368.4	368.2	367.8	367.4	367.0	366.6
140°	384.0	384.0	384.0	383.8	383.3	382.9	382.5	382.1
142.5°	397.8	397.9	398.0	397.8	397.4	397.0	396.6	396.2
145°	419.0	419.1	419.1	419.0	418.6	418.2	417.8	417.4
147.5°	437.4	437.7	437.9	437.8	437.4	437.0	436.7	436.3
150°	449.2	449.5	449.8	449.8	449.5	449.2	448.9	448.6
152.5°	460.9	461.3	461.7	461.7	461.3	460.9	460.5	460.2
155°	475.8	476.3	476.8	476.9	476.6	476.3	475.9	475.7
157.5°	489.5	490.2	490.9	491.0	490.5	490.0	489.6	489.0
160°	497.6	498.3	498.8	499.0	498.6	498.2	497.7	497.3
162.5°	505.0	505.7	506.4	506.5	506.0	505.6	505.1	504.6
165°	514.6	515.3	515.9	516.1	515.6	515.1	514.6	514.0
167.5°	522.4	523.2	523.9	523.9	523.4	522.9	522.4	521.8
170°	526.8	527.5	528.1	528.2	527.6	527.0	526.4	525.9
172.5°	530.0	530.8	531.4	531.5	530.9	530.3	529.7	529.1
175°	533.5	534.2	535.0	535.0	534.4	533.8	533.2	532.6
177.5°	535.2	535.7	536.1	536.1	535.7	535.2	534.7	534.2
180°	535.3	535.3	535.3	535.3	535.3	535.3	535.3	535.3

(END OF REPORT)