

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331443-927

Luminaire Tested: **SA2XXDIP-C1005D725U927-4F0-1E-UDD-D4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331443-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C1005D725U927-4F0-1E-UDD-D4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, DROP SATIN WHITE DIFFUSER
UPLIGHT 725 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5439.5 lumens
Efficiency: N/A
Efficacy: 89.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.32 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.08')
CIE Type: General Diffuse

Input Watts (W): 60.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331443-927
CATALOG NUMBER: SA2XXDIP-C1005D725U927-4F0-1E-UDD-D4

Luminous Intensity Polar Plot





TEST NUMBER: P331443-927

CATALOG NUMBER: SA2XXDIP-C1005D725U927-4F0-1E-UDD-D4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	58	58	58	52
1	97	92	87	83	89	85	81	77	72	69	66	60	58	56	49	47	46	41
2	87	79	72	67	80	73	67	62	62	57	54	52	48	45	42	40	38	33
3	79	69	61	55	73	64	57	51	54	49	44	45	41	38	37	34	31	27
4	72	61	52	46	66	56	49	43	48	42	37	40	35	32	33	29	27	23
5	66	54	45	39	61	50	42	37	43	37	32	36	31	27	29	26	23	20
6	61	48	40	34	56	45	37	32	38	32	28	32	27	24	26	23	20	17
7	56	43	35	29	52	40	33	28	35	29	24	29	24	21	24	20	18	15
8	52	39	31	26	48	37	29	24	31	26	21	27	22	18	22	18	16	13
9	49	36	28	23	45	33	26	22	29	23	19	24	20	17	20	17	14	12
10	45	33	25	20	42	31	24	19	27	21	17	23	18	15	19	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13525	13525	13525
5°	13591	13020	12971
10°	13506	12635	12493
15°	13320	12228	11990
20°	13085	11791	11506
25°	12852	11370	11066
30°	12525	10939	10626
35°	12192	10521	10314
40°	11845	10165	10004
45°	11515	9846	9739
50°	11159	9559	9477
55°	10787	9249	9211
60°	10329	8927	8928
65°	9856	8551	8595
70°	9323	8147	8233
75°	8642	7750	7901
80°	7567	7345	7563
85°	6539	6995	7303



TEST NUMBER: P331443-927

CATALOG NUMBER: SA2XXDIP-C1005D725U927-4F0-1E-UDD-D4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	79.4	1.5
10°-20°	227.6	4.2
20°-30°	344.9	6.3
30°-40°	420.1	7.7
40°-50°	452.0	8.3
50°-60°	438.9	8.1
60°-70°	383.2	7.0
70°-80°	295.0	5.4
80°-90°	200.9	3.7
90°-100°	265.2	4.9
100°-110°	536.5	9.9
110°-120°	530.0	9.7
120°-130°	418.8	7.7
130°-140°	322.2	5.9
140°-150°	234.6	4.3
150°-160°	163.0	3.0
160°-170°	95.9	1.8
170°-180°	31.2	0.6
0°-30°	651.9	12.0
0°-40°	1072.0	19.7
0°-60°	1962.9	36.1
0°-90°	2842.1	52.2
90°-120°	1331.7	24.5
90°-150°	2307.3	42.4
90°-180°	2597.0	47.7
0°-180°	5439.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	838	838	838	838	838	
5°	840	836	829	836	835	80
15°	801	804	804	814	813	226
25°	728	737	748	762	766	335
35°	628	648	671	697	706	392
45°	515	548	590	626	640	397
55°	395	439	501	544	561	353
65°	270	330	401	449	466	268
75°	149	218	295	345	363	158
85°	44	119	197	246	265	47
90°	13	91	181	227	244	9
95°	31	121	382	276	271	31
105°	82	157	563	966	858	87
115°	138	189	457	900	1041	136
125°	188	224	410	715	830	167
135°	219	262	378	577	666	170
145°	249	286	363	458	506	156
155°	283	306	352	398	414	130
165°	308	318	338	358	364	87
175°	321	322	324	328	328	31
180°	322	322	322	322	322	



TEST NUMBER: P331443-927

CATALOG NUMBER: SA2XXDIP-C1005D725U927-4F0-1E-UDD-D4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	837.7	837.7	837.7	837.7	837.7	837.7	837.7	837.7	837.7	837.7	837.7
2.5°	842.6	841.9	841.2	840.6	840.0	838.8	837.3	835.8	834.3	832.8	833.9
5°	840.1	839.3	838.5	837.7	836.9	835.7	834.1	832.4	830.8	829.2	830.8
7.5°	832.6	832.0	831.5	831.0	830.4	829.6	828.3	827.0	825.9	824.6	826.5
10°	826.8	826.2	825.7	825.1	824.6	823.9	823.2	822.3	821.5	820.7	822.8
12.5°	817.1	817.1	817.3	817.4	817.5	817.2	816.7	816.0	815.5	814.8	817.1
15°	801.3	801.8	802.3	802.9	803.4	803.7	803.7	803.7	803.7	803.7	806.1
17.5°	780.9	782.0	783.2	784.3	785.4	786.4	787.3	788.1	789.0	789.9	792.4
20°	767.3	768.7	770.0	771.3	772.7	773.9	775.0	776.0	777.1	778.2	781.2
22.5°	752.7	754.2	755.8	757.4	759.0	760.5	762.0	763.5	765.0	766.5	769.5
25°	728.4	730.3	732.2	734.1	736.0	738.2	740.5	743.0	745.4	747.8	751.1
27.5°	699.3	702.3	705.4	708.5	711.6	714.5	717.4	720.3	723.1	726.0	730.1
30°	679.9	683.3	686.9	690.4	693.9	697.4	700.9	704.4	707.9	711.5	715.7
32.5°	658.5	662.4	666.4	670.3	674.2	678.3	682.5	686.6	690.8	694.9	699.9
35°	627.6	632.2	636.8	641.4	646.0	650.9	656.0	661.1	666.2	671.4	677.3
37.5°	594.1	599.4	604.8	610.0	615.3	621.2	627.9	634.5	641.2	647.8	654.4
40°	571.8	577.7	583.7	589.6	595.6	602.1	609.4	616.7	624.0	631.3	638.3
42.5°	550.5	556.3	562.3	568.2	574.2	581.3	589.7	598.1	606.4	614.8	622.4
45°	514.8	522.0	529.3	536.6	543.9	552.2	561.7	571.2	580.6	590.0	598.4
47.5°	479.6	487.5	495.4	503.4	511.3	520.8	531.9	542.9	554.0	565.0	573.8
50°	455.3	463.7	472.0	480.4	488.7	499.0	511.1	523.2	535.4	547.6	556.7
52.5°	432.0	440.8	449.6	458.4	467.1	477.9	490.7	503.5	516.3	529.1	538.4
55°	394.6	404.3	414.0	423.7	433.4	445.3	459.3	473.3	487.4	501.4	511.1
57.5°	357.7	368.6	379.5	390.5	401.5	414.1	428.4	442.7	457.0	471.3	481.7
60°	331.4	343.0	354.7	366.2	377.9	391.3	406.7	422.1	437.4	452.8	463.1
62.5°	308.2	320.1	332.2	344.2	356.2	369.9	385.3	400.7	416.1	431.5	442.4
65°	269.5	282.7	296.0	309.2	322.4	337.0	352.9	368.8	384.7	400.6	411.7
67.5°	234.1	247.9	261.7	275.5	289.3	304.4	320.7	337.0	353.2	369.6	380.7
70°	208.8	222.8	236.9	250.9	264.9	280.3	297.1	313.8	330.5	347.2	358.8
72.5°	185.5	199.9	214.4	228.9	243.4	259.0	276.0	292.9	309.9	326.9	338.2
75°	149.3	164.5	179.5	194.6	209.8	225.9	243.2	260.5	277.7	295.0	306.6
77.5°	114.4	130.2	146.0	161.8	177.6	194.2	211.8	229.3	246.8	264.4	276.0
80°	91.0	107.5	124.0	140.5	156.9	173.9	191.4	209.0	226.5	244.0	255.3
82.5°	71.6	87.9	104.1	120.3	136.6	153.6	171.3	189.1	206.8	224.6	235.9
85°	43.7	60.4	77.2	93.9	110.6	127.6	144.9	162.2	179.4	196.7	208.0
87.5°	23.9	40.4	57.0	73.3	89.6	106.6	124.5	142.7	160.7	178.1	188.9
90°	12.8	30.3	48.4	65.3	82.1	100.4	120.8	142.4	163.4	181.3	191.5
92.5°	18.7	36.6	55.7	73.0	91.7	113.1	143.8	180.1	214.3	232.0	230.0
95°	31.4	46.6	65.4	83.7	106.2	135.5	180.2	250.3	338.3	382.4	362.3
97.5°	43.8	58.4	76.3	95.9	118.6	148.9	200.2	290.8	425.7	543.6	573.9
100°	56.2	68.0	83.6	103.5	125.8	155.7	203.7	294.3	443.1	610.6	709.8
102.5°	66.6	77.1	91.8	110.8	132.8	162.0	207.1	288.8	427.4	606.3	756.2
105°	81.6	91.9	104.1	121.2	142.7	170.9	214.0	283.2	399.4	563.2	737.4
107.5°	99.2	107.4	118.0	132.7	152.5	179.8	221.5	283.0	380.9	518.2	672.7
110°	110.1	118.0	127.1	140.5	159.0	186.2	226.7	284.5	373.3	495.5	632.3



TEST NUMBER: P331443-927

CATALOG NUMBER: SA2XXDIP-C1005D725U927-4F0-1E-UDD-D4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	121.0	128.0	136.8	148.9	165.9	192.9	231.7	286.5	367.6	477.8	601.7
115°	138.0	144.1	150.8	161.1	176.5	200.7	239.6	289.5	361.6	456.8	562.7
117.5°	154.4	158.8	164.5	172.9	186.8	210.7	246.6	293.2	357.1	441.0	534.1
120°	165.2	168.8	173.6	180.3	193.8	217.0	251.9	296.2	354.7	431.7	517.9
122.5°	175.7	178.1	182.2	188.7	201.5	224.7	257.5	298.6	352.9	423.9	503.4
125°	188.2	190.0	193.8	201.2	213.6	235.3	266.2	302.7	349.7	410.4	481.4
127.5°	199.1	201.3	206.2	214.1	225.8	246.9	275.6	307.5	347.9	399.5	461.0
130°	205.6	207.7	213.7	222.0	234.2	254.2	281.5	310.8	347.4	392.7	447.4
132.5°	211.5	214.2	220.6	229.5	242.1	261.5	286.5	313.9	346.8	386.3	435.5
135°	219.2	221.7	229.1	238.4	252.6	271.3	293.8	318.2	345.7	378.1	419.1
137.5°	227.6	230.5	237.9	247.8	261.8	278.5	299.3	320.6	344.4	370.9	405.5
140°	234.1	236.2	243.4	253.0	266.4	282.7	301.7	321.5	343.1	366.5	397.5
142.5°	240.5	242.2	248.9	258.5	271.4	286.4	304.6	323.4	343.1	364.6	391.2
145°	248.9	251.4	257.6	266.9	279.2	292.9	309.7	326.9	344.3	362.9	384.3
147.5°	259.4	261.2	267.1	275.7	286.0	298.1	313.9	329.1	344.8	360.7	378.2
150°	266.3	268.2	273.1	281.1	290.4	301.6	315.8	330.0	344.3	359.2	374.0
152.5°	273.2	274.1	279.0	286.1	294.9	305.1	317.8	330.6	343.3	356.7	370.6
155°	283.0	283.6	287.3	294.1	301.0	310.2	320.8	331.3	341.8	352.4	364.1
157.5°	291.2	291.8	294.8	300.7	306.2	313.9	322.9	331.3	339.0	347.9	358.1
160°	296.6	297.2	299.7	304.7	309.7	316.4	323.8	331.3	337.5	344.9	353.6
162.5°	302.1	301.7	304.2	308.2	312.6	317.9	324.4	330.8	336.0	342.5	349.6
165°	308.4	307.8	309.0	312.8	315.8	319.6	325.1	329.5	333.2	337.5	343.1
167.5°	313.6	312.8	313.9	316.3	318.5	320.9	325.0	328.6	330.3	333.2	336.6
170°	317.0	315.8	316.4	318.3	319.6	321.4	324.5	327.6	328.8	330.7	333.2
172.5°	319.0	318.3	317.9	319.8	320.5	321.9	324.0	326.1	326.9	327.7	329.7
175°	321.4	320.8	320.1	321.4	321.4	322.0	323.2	324.5	323.8	324.5	325.1
177.5°	322.5	321.5	321.0	322.0	322.0	322.0	322.5	323.5	322.5	322.0	322.5
180°	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0



TEST NUMBER: P331443-927

CATALOG NUMBER: SA2XXDIP-C1005D725U927-4F0-1E-UDD-D4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	837.7	837.7	837.7	837.7	837.7	837.7	837.7	837.7
2.5°	835.0	836.1	837.2	837.5	837.0	836.6	836.1	835.8
5°	832.4	834.1	835.7	836.3	836.1	835.8	835.5	835.3
7.5°	828.5	830.4	832.3	833.2	832.9	832.7	832.3	832.1
10°	825.0	827.2	829.3	830.3	830.0	829.7	829.5	829.2
12.5°	819.2	821.3	823.5	824.4	824.2	823.9	823.6	823.4
15°	808.6	811.0	813.4	814.5	814.2	814.0	813.7	813.4
17.5°	795.0	797.5	800.0	801.3	801.3	801.3	801.3	801.3
20°	784.1	787.1	790.0	791.5	791.5	791.5	791.5	791.5
22.5°	772.5	775.5	778.4	780.1	780.5	781.0	781.4	781.9
25°	754.3	757.6	760.8	762.8	763.7	764.5	765.2	766.0
27.5°	734.2	738.3	742.4	744.7	745.4	745.9	746.6	747.1
30°	720.1	724.4	728.7	731.3	732.1	732.8	733.7	734.5
32.5°	704.9	709.8	714.8	718.0	719.5	720.9	722.4	723.8
35°	683.3	689.2	695.1	699.0	700.9	702.8	704.7	706.5
37.5°	661.0	667.6	674.1	678.4	680.4	682.5	684.4	686.4
40°	645.3	652.4	659.3	664.1	666.5	668.9	671.4	673.8
42.5°	630.1	637.8	645.5	650.5	652.9	655.4	657.7	660.2
45°	606.7	615.1	623.4	629.0	631.7	634.4	637.1	639.8
47.5°	582.5	591.2	600.0	605.9	608.8	611.8	614.7	617.7
50°	565.9	575.0	584.2	590.3	593.3	596.2	599.2	602.1
52.5°	547.9	557.2	566.6	572.9	576.1	579.3	582.5	585.7
55°	520.9	530.5	540.3	546.8	550.3	553.9	557.4	560.9
57.5°	492.3	502.7	513.2	520.1	523.7	527.3	530.8	534.4
60°	473.3	483.6	493.8	500.9	504.6	508.4	512.2	515.9
62.5°	453.3	464.1	475.1	482.3	485.8	489.4	493.0	496.5
65°	422.8	433.8	444.9	452.2	455.7	459.1	462.7	466.2
67.5°	391.9	403.1	414.2	421.7	425.3	429.0	432.7	436.3
70°	370.4	382.0	393.6	401.0	404.3	407.5	410.7	414.0
72.5°	349.6	361.0	372.3	380.0	383.9	387.8	391.7	395.5
75°	318.2	329.8	341.4	349.0	352.4	356.0	359.5	363.0
77.5°	287.5	299.0	310.6	318.3	322.0	325.8	329.6	333.4
80°	266.6	278.1	289.4	296.9	300.7	304.4	308.2	312.0
82.5°	247.2	258.6	269.9	277.3	280.9	284.5	288.0	291.6
85°	219.4	230.7	242.0	249.5	253.3	257.1	260.9	264.7
87.5°	199.9	210.6	221.8	229.2	232.7	236.1	239.6	243.0
90°	201.7	211.2	223.2	230.8	234.1	237.3	240.6	243.8
92.5°	226.6	229.6	235.0	238.0	240.7	242.0	245.7	248.0
95°	322.3	294.9	279.1	272.2	267.4	265.7	267.0	270.9
97.5°	527.8	468.9	411.9	373.8	347.3	335.3	329.4	327.4
100°	706.7	639.9	565.1	496.6	448.2	424.5	409.6	401.4
102.5°	821.9	814.3	762.0	689.0	636.1	593.7	574.2	562.1
105°	875.7	955.1	972.6	958.4	923.0	887.5	863.9	858.2
107.5°	818.4	932.9	1006.3	1042.4	1050.1	1051.0	1048.6	1040.1
110°	771.6	891.0	979.0	1035.5	1065.2	1079.9	1088.4	1090.8



TEST NUMBER: P331443-927

CATALOG NUMBER: SA2XXDIP-C1005D725U927-4F0-1E-UDD-D4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	728.1	843.1	936.5	1000.5	1040.5	1063.2	1076.7	1083.0
115°	673.0	776.4	865.6	934.9	981.9	1013.4	1032.5	1040.9
117.5°	628.9	720.6	802.2	867.4	914.9	947.8	967.5	974.9
120°	605.3	689.7	762.9	824.5	870.8	902.9	923.8	933.0
122.5°	585.7	663.4	732.9	788.8	830.2	861.3	879.8	887.6
125°	556.2	627.2	689.0	740.4	778.7	804.6	822.5	830.0
127.5°	527.0	591.4	649.6	697.0	730.6	755.1	770.8	777.1
130°	508.4	568.2	623.5	668.8	701.2	724.5	739.0	746.1
132.5°	490.3	545.8	597.1	639.7	671.7	694.9	708.4	715.0
135°	465.0	511.5	558.0	596.7	625.4	648.0	661.3	666.0
137.5°	443.3	482.4	519.8	553.4	579.6	599.0	610.6	616.2
140°	429.7	463.7	496.5	526.7	548.2	565.9	576.8	582.1
142.5°	419.1	447.8	475.8	501.0	521.2	537.3	546.9	549.1
145°	405.1	427.2	448.0	467.5	483.6	495.5	503.0	506.3
147.5°	394.7	411.1	426.3	439.8	452.7	461.8	466.7	468.4
150°	388.9	402.5	415.5	426.7	435.9	443.4	447.1	447.7
152.5°	383.4	396.1	407.1	416.8	424.1	430.5	433.2	433.3
155°	375.9	385.8	395.1	401.9	408.7	413.0	415.5	414.3
157.5°	367.1	375.4	383.2	388.5	393.3	397.0	398.1	398.1
160°	361.6	368.4	375.3	379.6	384.0	387.1	387.6	387.6
162.5°	356.2	362.0	367.8	371.2	375.5	377.6	378.3	377.7
165°	348.0	352.4	356.7	359.2	361.6	364.1	364.1	363.5
167.5°	340.2	343.6	346.5	348.8	349.9	351.3	351.1	350.4
170°	336.3	338.1	340.6	341.8	342.5	344.3	343.6	342.5
172.5°	331.8	333.2	335.2	335.9	336.5	337.4	336.8	336.0
175°	326.9	327.6	328.2	328.8	328.8	329.5	328.8	327.6
177.5°	323.5	323.5	324.0	324.0	324.0	324.0	323.5	322.5
180°	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0

(END OF REPORT)