

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331684-930

Luminaire Tested: **SA2XXRDIP-C675D530U930-4F0-1E-UDD-F**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331684-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXRDIP-C675D530U930-4F0-1E-UDD-F  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 530 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3616.2 lumens  
Efficiency: N/A  
Efficacy: 89.7 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 40.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331684-930  
CATALOG NUMBER: SA2XXRDIP-C675D530U930-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P331684-930

CATALOG NUMBER: SA2XXRDIP-C675D530U930-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	58	58	58	52				
1	99	95	91	88	91	88	85	82	75	73	71	63	62	60	52	51	50	45				
2	90	83	77	72	83	77	72	68	66	62	59	56	53	51	47	45	43	39				
3	83	74	67	61	76	69	62	57	59	54	50	50	47	44	42	39	37	33				
4	76	65	58	52	70	61	54	49	53	47	43	45	41	38	38	35	32	29				
5	70	59	51	45	65	55	48	42	47	42	38	41	36	33	34	31	29	26				
6	65	53	45	39	60	49	42	37	43	37	33	37	33	29	31	28	25	23				
7	60	48	40	35	55	45	38	33	39	34	29	34	29	26	29	25	23	20				
8	56	44	36	31	52	41	34	29	36	30	26	31	27	23	26	23	21	18				
9	52	40	33	28	48	37	31	26	33	28	24	29	24	21	24	21	19	17				
10	49	37	30	25	45	35	28	24	30	25	22	26	22	19	23	19	17	15				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	14849	14849	14849
5°	14906	14663	14744
10°	14791	14423	14300
15°	14621	13996	13593
20°	14387	13385	12713
25°	14145	12691	11863
30°	13811	11979	10769
35°	13484	11203	9810
40°	13156	10404	8701
45°	12771	9501	7695
50°	12376	8593	6712
55°	11972	7614	5762
60°	11502	6584	4782
65°	10968	5532	4359
70°	10334	4556	4008
75°	9551	4155	3737
80°	8433	3710	3403
85°	6632	2927	2927



TEST NUMBER: P331684-930

CATALOG NUMBER: SA2XXRDIP-C675D530U930-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	86.1	2.4
10°-20°	236.4	6.5
20°-30°	331.9	9.2
30°-40°	361.9	10.0
40°-50°	332.8	9.2
50°-60°	261.4	7.2
60°-70°	170.4	4.7
70°-80°	87.9	2.4
80°-90°	24.2	0.7
90°-100°	19.6	0.5
100°-110°	71.9	2.0
110°-120°	192.3	5.3
120°-130°	317.4	8.8
130°-140°	337.5	9.3
140°-150°	313.7	8.7
150°-160°	252.2	7.0
160°-170°	162.5	4.5
170°-180°	55.9	1.5
0°-30°	654.4	18.1
0°-40°	1016.3	28.1
0°-60°	1610.5	44.5
0°-90°	1893.0	52.3
90°-120°	283.8	7.8
90°-150°	1252.5	34.6
90°-180°	1723.0	47.6
0°-180°	3616.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	920	920	920	920	920	
5°	920	915	905	912	910	87
15°	875	864	837	822	813	246
25°	794	766	712	680	666	365
35°	684	640	568	518	498	428
45°	559	502	416	359	337	432
55°	425	359	270	222	205	380
65°	287	219	145	118	114	285
75°	153	96	67	61	60	162
85°	36	19	16	16	16	42
90°	0	5	8	11	12	3
95°	28	15	17	19	18	34
105°	129	135	26	30	32	138
115°	245	252	262	75	35	241
125°	346	352	360	362	364	308
135°	428	435	439	443	442	330
145°	496	497	503	506	504	310
155°	547	543	548	550	547	252
165°	576	574	575	578	575	163
175°	589	586	587	590	586	56
180°	588	588	588	588	588	



TEST NUMBER: P331684-930

CATALOG NUMBER: SA2XXRDIP-C675D530U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	919.7	919.7	919.7	919.7	919.7	919.7	919.7	919.7	919.7	919.7	919.7
2.5°	923.0	922.3	921.5	920.8	920.1	918.8	917.2	915.6	914.0	912.4	913.9
5°	919.7	918.8	917.9	916.9	916.0	914.4	911.9	909.5	907.1	904.7	906.4
7.5°	910.2	909.1	907.9	906.8	905.6	903.6	900.8	898.1	895.2	892.4	892.8
10°	902.2	900.9	899.6	898.3	897.0	894.5	890.8	887.1	883.5	879.7	879.2
12.5°	892.2	890.6	889.0	887.5	885.8	882.7	878.0	873.3	868.5	863.7	862.7
15°	874.7	872.7	870.7	868.6	866.6	862.4	856.1	849.9	843.6	837.3	833.8
17.5°	853.3	850.2	847.1	843.9	840.8	835.3	827.2	819.1	811.1	803.0	798.8
20°	837.3	833.6	829.9	826.2	822.5	816.0	806.7	797.5	788.3	779.0	774.4
22.5°	819.9	815.9	811.7	807.6	803.4	796.1	785.7	775.3	764.8	754.4	748.4
25°	794.0	788.1	782.2	776.2	770.4	761.2	749.1	736.9	724.6	712.4	704.8
27.5°	762.7	756.3	749.8	743.4	736.9	726.8	713.1	699.4	685.6	671.8	663.0
30°	740.8	733.7	726.7	719.7	712.7	701.7	686.9	672.1	657.3	642.5	633.1
32.5°	719.4	711.2	703.0	694.8	686.6	674.9	659.8	644.7	629.7	614.6	603.8
35°	684.1	674.7	665.3	655.8	646.5	633.6	617.3	601.0	584.7	568.4	556.8
37.5°	648.9	638.5	628.1	617.8	607.4	593.5	576.3	558.9	541.5	524.2	511.4
40°	624.2	613.1	602.0	590.9	579.8	565.3	547.4	529.5	511.5	493.6	480.5
42.5°	598.9	587.3	575.5	563.9	552.2	537.0	518.5	500.0	481.4	462.9	449.3
45°	559.3	546.9	534.5	522.1	509.7	493.8	474.4	455.0	435.5	416.1	403.0
47.5°	520.7	507.5	494.4	481.3	468.1	451.6	431.5	411.5	391.4	371.4	358.3
50°	492.7	479.6	466.4	453.3	440.2	423.5	403.1	382.8	362.4	342.1	329.3
52.5°	465.5	451.7	438.0	424.3	410.5	393.7	373.8	353.9	334.0	314.1	301.8
55°	425.3	410.9	396.5	382.0	367.6	350.4	330.4	310.5	290.5	270.5	259.4
57.5°	384.2	369.4	354.6	339.8	325.0	308.0	288.8	269.6	250.4	231.2	221.0
60°	356.2	341.4	326.6	311.9	297.0	280.1	261.1	242.0	223.0	203.9	194.4
62.5°	328.9	314.1	299.3	284.5	269.7	253.2	235.1	217.0	198.8	180.6	171.6
65°	287.1	272.1	257.1	242.2	227.2	211.4	194.8	178.1	161.4	144.8	138.5
67.5°	246.9	232.0	217.1	202.3	187.4	172.4	157.4	142.5	127.5	112.5	109.7
70°	218.9	204.5	190.0	175.6	161.2	147.6	134.9	122.1	109.3	96.5	94.7
72.5°	192.2	178.4	164.6	150.7	136.9	124.9	114.6	104.4	94.2	83.9	82.3
75°	153.1	140.2	127.3	114.3	101.3	91.7	85.4	79.2	72.9	66.6	65.3
77.5°	114.7	103.3	92.0	80.6	69.3	62.0	59.0	56.0	53.0	50.0	49.2
80°	90.7	81.3	71.8	62.5	53.0	47.4	45.5	43.6	41.8	39.9	39.2
82.5°	68.7	61.4	54.1	46.6	39.3	35.0	33.8	32.4	31.2	30.0	29.5
85°	35.8	31.9	28.0	24.1	20.2	18.0	17.4	17.0	16.4	15.8	15.8
87.5°	10.8	9.8	8.8	7.8	6.8	6.4	6.6	6.7	6.8	7.0	7.0
90°	0.4	1.5	2.5	3.5	4.6	5.5	6.3	7.0	7.7	8.5	9.0
92.5°	8.6	8.5	8.4	8.3	8.2	8.4	8.7	9.1	9.5	9.9	10.1
95°	27.6	24.5	21.4	18.3	15.2	13.9	14.6	15.2	15.9	16.6	17.0
97.5°	54.9	46.1	37.3	28.5	19.7	16.1	17.6	19.2	20.7	22.2	22.6
100°	75.3	62.4	49.4	36.4	23.5	17.9	19.4	21.0	22.7	24.2	25.0
102.5°	97.8	95.1	92.3	89.5	86.8	78.7	65.3	51.9	38.4	24.9	25.9
105°	129.3	132.2	135.0	137.9	140.7	129.2	103.4	77.6	51.8	25.9	27.0
107.5°	165.3	167.6	169.9	172.2	174.5	160.1	129.2	98.2	67.3	36.4	35.3
110°	188.5	190.5	192.5	194.4	196.4	183.8	156.5	129.1	101.7	74.4	65.0



TEST NUMBER: P331684-930

CATALOG NUMBER: SA2XXRDIP-C675D530U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	210.3	212.1	213.8	215.6	217.3	214.8	208.1	201.3	194.5	187.8	153.3
115°	244.7	246.2	247.9	249.5	251.1	253.1	255.4	257.8	260.2	262.5	218.7
117.5°	275.4	277.2	279.0	280.8	282.6	284.3	285.9	287.6	289.2	290.7	280.2
120°	297.8	299.2	300.7	302.1	303.5	305.1	306.8	308.5	310.1	311.9	313.0
122.5°	316.9	318.4	319.9	321.4	322.9	324.6	326.4	328.2	330.1	332.0	332.6
125°	345.9	347.2	348.4	349.6	350.8	352.4	354.2	356.0	357.8	359.5	360.2
127.5°	372.2	373.6	375.0	376.3	377.6	379.0	380.3	381.7	383.0	384.4	385.3
130°	388.9	390.4	391.9	393.5	394.9	396.2	397.3	398.3	399.3	400.4	401.5
132.5°	405.9	407.2	408.5	409.8	411.1	412.2	413.3	414.3	415.3	416.4	417.3
135°	428.0	429.6	431.0	432.6	434.1	435.3	436.1	437.0	437.8	438.6	439.6
137.5°	450.5	451.4	452.5	453.6	454.6	455.7	456.6	457.6	458.5	459.5	460.5
140°	465.0	465.8	466.6	467.3	468.1	469.0	470.0	471.1	472.1	473.1	474.0
142.5°	477.3	478.0	478.7	479.3	480.0	480.9	482.2	483.3	484.5	485.8	486.5
145°	496.5	496.4	496.4	496.3	496.2	496.9	498.6	500.1	501.7	503.4	504.0
147.5°	513.3	512.9	512.6	512.3	511.8	512.5	514.0	515.7	517.2	518.9	519.3
150°	524.2	523.5	522.9	522.2	521.5	522.0	523.5	525.0	526.5	528.0	528.6
152.5°	533.4	532.6	531.9	531.2	530.4	530.8	532.2	533.7	535.1	536.5	537.1
155°	546.7	545.9	545.0	544.2	543.3	543.5	544.6	545.8	546.9	548.0	548.6
157.5°	557.2	556.5	555.8	555.1	554.3	554.4	555.1	556.0	556.8	557.6	558.2
160°	563.4	562.8	562.2	561.7	561.1	561.1	561.7	562.2	562.8	563.4	563.9
162.5°	568.8	568.2	567.6	567.0	566.6	566.5	567.0	567.4	567.9	568.4	569.1
165°	576.1	575.5	574.9	574.4	573.8	573.7	574.0	574.2	574.5	574.8	575.5
167.5°	581.6	581.0	580.4	579.8	579.3	579.1	579.4	579.7	579.9	580.2	580.8
170°	584.6	584.1	583.5	582.9	582.4	582.1	582.4	582.5	582.7	582.9	583.6
172.5°	586.7	586.1	585.5	585.0	584.4	584.2	584.4	584.6	584.7	585.0	585.6
175°	589.3	588.6	588.0	587.3	586.6	586.4	586.6	586.8	586.9	587.2	587.8
177.5°	589.7	589.2	588.6	588.2	587.6	587.3	587.4	587.5	587.6	587.7	588.2
180°	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0



TEST NUMBER: P331684-930

CATALOG NUMBER: SA2XXRDIP-C675D530U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	919.7	919.7	919.7	919.7	919.7	919.7	919.7	919.7
2.5°	915.3	916.8	918.3	918.8	918.6	918.3	918.0	917.7
5°	908.0	909.7	911.3	911.9	911.3	910.8	910.3	909.7
7.5°	893.3	893.8	894.3	894.1	893.1	892.2	891.2	890.2
10°	878.6	878.1	877.5	876.7	875.5	874.5	873.3	872.2
12.5°	861.8	860.8	859.7	858.3	856.5	854.7	852.8	850.9
15°	830.3	826.7	823.2	820.5	818.7	816.8	815.0	813.2
17.5°	794.7	790.4	786.3	782.6	779.4	776.2	773.1	769.9
20°	769.8	765.2	760.5	756.2	752.1	748.0	744.0	739.9
22.5°	742.5	736.5	730.6	726.1	723.0	720.0	717.0	714.0
25°	697.2	689.7	682.1	676.9	674.2	671.4	668.6	665.9
27.5°	654.1	645.3	636.5	629.8	625.4	621.0	616.6	612.2
30°	623.7	614.2	604.8	597.6	592.6	587.6	582.6	577.6
32.5°	593.0	582.3	571.5	563.8	559.1	554.4	549.7	545.0
35°	545.2	533.5	521.9	514.0	509.9	505.8	501.8	497.7
37.5°	498.5	485.7	472.9	464.1	459.4	454.8	450.1	445.5
40°	467.2	454.1	441.0	432.0	427.2	422.4	417.6	412.8
42.5°	435.8	422.2	408.6	399.5	394.8	390.2	385.6	380.8
45°	389.9	376.7	363.6	354.8	350.4	345.9	341.5	337.0
47.5°	345.3	332.2	319.1	310.6	306.6	302.6	298.5	294.5
50°	316.6	303.8	291.1	282.7	278.8	274.9	271.1	267.2
52.5°	289.5	277.1	264.8	256.9	253.3	249.7	246.1	242.6
55°	248.3	237.2	226.1	218.8	215.3	211.7	208.2	204.7
57.5°	210.8	200.7	190.5	183.9	181.0	178.1	175.0	172.1
60°	185.1	175.6	166.2	160.0	157.0	154.1	151.1	148.1
62.5°	162.7	153.6	144.6	139.3	137.5	135.7	134.0	132.2
65°	132.2	126.0	119.7	116.3	115.7	115.1	114.5	114.1
67.5°	106.7	103.9	101.0	99.2	98.7	98.1	97.5	96.9
70°	92.9	91.0	89.1	87.9	87.1	86.3	85.6	84.9
72.5°	80.8	79.2	77.7	76.7	76.2	75.8	75.3	74.9
75°	64.0	62.7	61.4	60.7	60.5	60.3	60.1	59.9
77.5°	48.4	47.7	47.0	46.5	46.1	45.9	45.6	45.2
80°	38.5	37.7	37.0	36.6	36.6	36.6	36.6	36.6
82.5°	29.1	28.6	28.2	28.0	28.0	28.0	28.0	28.0
85°	15.8	15.8	15.8	15.8	15.8	15.8	15.8	15.8
87.5°	6.9	6.8	6.8	6.8	6.8	6.8	6.9	6.9
90°	9.5	9.9	10.4	10.8	10.9	11.1	11.3	11.5
92.5°	10.4	10.6	10.8	11.0	11.2	11.3	11.4	11.5
95°	17.5	18.0	18.5	18.7	18.6	18.5	18.4	18.3
97.5°	23.0	23.3	23.7	24.0	24.1	24.2	24.3	24.5
100°	25.8	26.5	27.3	27.7	28.0	28.1	28.3	28.5
102.5°	26.9	27.9	28.9	29.5	29.8	30.0	30.2	30.6
105°	28.0	29.1	30.1	30.8	31.2	31.6	32.0	32.4
107.5°	34.2	33.2	32.1	31.8	32.1	32.5	32.9	33.3
110°	55.5	46.1	36.6	32.1	32.4	32.9	33.3	33.6





TEST NUMBER: P331684-930

CATALOG NUMBER: SA2XXRDIP-C675D530U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	118.8	84.3	49.8	32.8	33.0	33.3	33.7	33.9
115°	175.0	131.2	87.4	62.1	55.3	48.5	41.7	34.9
117.5°	269.6	259.0	248.4	232.0	209.5	187.2	164.9	142.4
120°	314.1	315.3	316.4	310.6	297.8	285.1	272.3	259.5
122.5°	333.3	334.0	334.7	333.8	331.3	328.8	326.4	323.8
125°	360.9	361.5	362.2	362.6	363.0	363.2	363.5	363.8
127.5°	386.3	387.3	388.2	388.7	388.8	388.9	388.9	389.0
130°	402.4	403.5	404.6	405.0	404.9	404.8	404.7	404.6
132.5°	418.2	419.1	420.0	420.3	420.2	420.1	420.0	420.0
135°	440.6	441.5	442.5	442.9	442.6	442.5	442.3	442.1
137.5°	461.4	462.3	463.3	463.5	463.2	462.8	462.6	462.3
140°	474.8	475.6	476.5	476.7	476.2	475.8	475.3	474.8
142.5°	487.3	488.0	488.9	489.0	488.5	488.0	487.5	487.1
145°	504.7	505.3	506.0	506.1	505.6	505.2	504.7	504.2
147.5°	519.8	520.3	520.8	520.8	520.5	520.1	519.7	519.3
150°	529.1	529.7	530.3	530.4	529.9	529.4	528.9	528.5
152.5°	537.7	538.3	538.8	538.7	538.2	537.5	536.9	536.3
155°	549.2	549.8	550.3	550.2	549.4	548.7	548.0	547.1
157.5°	558.8	559.5	560.1	560.1	559.3	558.6	557.8	557.1
160°	564.4	565.0	565.6	565.6	564.9	564.3	563.5	562.9
162.5°	569.7	570.4	571.0	571.0	570.1	569.3	568.5	567.7
165°	576.2	576.8	577.5	577.5	576.8	576.2	575.5	574.8
167.5°	581.5	582.2	582.9	582.8	581.9	581.1	580.2	579.4
170°	584.2	584.9	585.5	585.5	584.6	583.8	582.9	582.0
172.5°	586.3	586.9	587.6	587.5	586.7	585.8	585.0	584.1
175°	588.5	589.1	589.8	589.7	588.7	587.7	586.9	585.9
177.5°	588.7	589.3	589.8	589.7	589.1	588.3	587.7	587.0
180°	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0

(END OF REPORT)