

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331444-927

Luminaire Tested: **SA2XXDIP-C1005D725U927-4F0-1E-UDD-F**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331444-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXDIP-C1005D725U927-4F0-1E-UDD-F  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 725 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5509.2 lumens  
Efficiency: N/A  
Efficacy: 90.8 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 60.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331444-927

CATALOG NUMBER: SA2XXDIP-C1005D725U927-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P331444-927

CATALOG NUMBER: SA2XXDIP-C1005D725U927-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	64	64	64	58
1	100	95	91	88	93	89	86	82	77	75	72	66	65	63	56	55	54	49
2	91	83	77	72	84	78	72	68	68	63	60	58	55	52	50	47	45	41
3	83	73	66	60	77	68	62	57	60	55	50	52	48	44	44	41	39	35
4	76	65	57	51	70	61	54	48	53	47	43	46	42	38	39	36	33	30
5	70	58	50	43	65	54	47	41	48	42	37	41	37	33	35	32	29	26
6	64	52	44	38	60	49	41	36	43	37	32	37	33	29	32	28	26	23
7	59	47	39	33	55	44	37	32	39	33	29	34	29	26	29	26	23	20
8	55	43	35	29	51	40	33	28	36	30	25	31	26	23	27	23	20	18
9	51	39	31	26	48	37	30	25	33	27	23	29	24	21	25	21	18	16
10	48	36	28	24	45	34	27	23	30	25	21	27	22	19	23	19	17	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	20386	20386	20386
5°	20464	20169	20285
10°	20341	19964	20064
15°	20090	19704	19686
20°	19734	19316	19295
25°	19379	18838	18838
30°	18921	18401	18243
35°	18496	17875	17611
40°	17962	17351	17015
45°	17438	16826	16411
50°	16865	16284	15707
55°	16268	15651	15071
60°	15603	14899	14347
65°	14888	14147	13498
70°	13983	13237	12609
75°	12726	12190	11890
80°	11288	10953	10386
85°	9207	8781	7873



TEST NUMBER: P331444-927

CATALOG NUMBER: SA2XXDIP-C1005D725U927-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	118.7	2.2
10°-20°	334.1	6.1
20°-30°	491.0	8.9
30°-40°	570.4	10.4
40°-50°	569.8	10.3
50°-60°	496.9	9.0
60°-70°	367.4	6.7
70°-80°	208.1	3.8
80°-90°	57.9	1.1
90°-100°	26.1	0.5
100°-110°	95.8	1.7
110°-120°	256.1	4.6
120°-130°	422.7	7.7
130°-140°	449.6	8.2
140°-150°	417.8	7.6
150°-160°	335.9	6.1
160°-170°	216.5	3.9
170°-180°	74.5	1.4
0°-30°	943.8	17.1
0°-40°	1514.2	27.5
0°-60°	2580.8	46.8
0°-90°	3214.2	58.3
90°-120°	378.0	6.9
90°-150°	1668.1	30.3
90°-180°	2295.0	41.7
0°-180°	5509.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1263	1263	1263	1263	1263	
5°	1263	1257	1244	1253	1252	120
15°	1202	1194	1179	1183	1178	338
25°	1088	1078	1057	1060	1057	500
35°	938	926	907	900	894	586
45°	764	755	737	724	719	589
55°	578	570	556	542	535	517
65°	390	382	370	360	353	385
75°	204	201	195	189	191	218
85°	50	49	47	44	42	57
90°	1	7	11	14	15	4
95°	37	19	22	25	24	45
105°	172	180	34	41	43	184
115°	326	336	350	100	46	321
125°	461	468	479	483	484	411
135°	570	579	584	590	589	440
145°	661	661	670	674	672	413
155°	728	724	730	733	729	335
165°	767	764	766	769	766	217
175°	785	781	782	785	780	75
180°	783	783	783	783	783	



TEST NUMBER: P331444-927

CATALOG NUMBER: SA2XXDIP-C1005D725U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6
2.5°	1268.4	1267.3	1266.3	1265.2	1264.1	1262.4	1260.0	1257.7	1255.3	1252.9	1255.1
5°	1262.6	1261.6	1260.4	1259.3	1258.3	1256.2	1253.3	1250.3	1247.4	1244.4	1246.6
7.5°	1251.4	1249.7	1248.1	1246.4	1244.8	1242.4	1239.4	1236.4	1233.3	1230.3	1232.5
10°	1240.7	1238.9	1237.0	1235.1	1233.2	1230.7	1227.4	1224.2	1220.9	1217.7	1219.9
12.5°	1226.2	1224.5	1222.8	1221.1	1219.5	1217.0	1213.8	1210.5	1207.4	1204.1	1205.6
15°	1201.9	1200.3	1198.7	1197.1	1195.4	1192.9	1189.4	1185.8	1182.3	1178.8	1180.0
17.5°	1170.8	1169.2	1167.6	1165.9	1164.3	1161.7	1158.2	1154.6	1151.0	1147.6	1148.7
20°	1148.5	1146.8	1145.3	1143.6	1142.0	1139.3	1135.5	1131.8	1128.0	1124.2	1125.0
22.5°	1126.2	1123.9	1121.7	1119.4	1117.1	1114.2	1110.6	1107.1	1103.5	1099.9	1100.1
25°	1087.8	1085.6	1083.5	1081.3	1079.2	1075.8	1071.2	1066.6	1062.0	1057.4	1058.0
27.5°	1044.1	1042.1	1040.2	1038.2	1036.3	1033.6	1029.9	1026.3	1022.7	1019.1	1018.3
30°	1014.9	1012.8	1010.6	1008.4	1006.3	1003.2	999.2	995.1	991.1	987.0	986.2
32.5°	983.9	982.1	980.4	978.7	976.9	974.0	969.7	965.4	961.2	956.9	955.5
35°	938.4	935.7	933.0	930.3	927.6	924.2	919.8	915.5	911.2	906.9	905.3
37.5°	887.2	884.9	882.5	880.1	877.7	874.4	870.1	865.8	861.4	857.1	855.1
40°	852.2	850.1	848.0	845.8	843.6	840.4	836.1	831.8	827.4	823.2	820.7
42.5°	818.2	816.1	814.0	811.8	809.6	806.4	802.1	797.7	793.4	789.1	786.5
45°	763.7	761.8	759.9	758.0	756.1	753.1	749.1	745.0	741.0	736.9	734.0
47.5°	709.2	707.5	705.7	703.9	702.1	699.1	694.9	690.7	686.5	682.3	679.1
50°	671.4	670.0	668.7	667.3	666.0	663.4	659.7	655.8	652.0	648.3	644.5
52.5°	634.5	632.7	630.9	629.2	627.3	624.6	621.1	617.5	614.0	610.5	607.3
55°	577.9	576.2	574.6	573.1	571.4	568.9	565.8	562.5	559.3	556.0	552.8
57.5°	521.1	519.8	518.5	517.2	515.9	513.5	509.9	506.4	502.8	499.2	496.1
60°	483.2	482.1	481.0	480.0	478.9	476.4	472.7	468.9	465.1	461.4	458.4
62.5°	446.3	444.6	442.8	441.1	439.3	437.0	434.1	431.3	428.3	425.4	422.6
65°	389.7	388.1	386.5	384.8	383.3	381.0	378.3	375.7	373.0	370.3	367.9
67.5°	332.2	330.9	329.5	328.3	327.0	325.1	322.7	320.3	317.8	315.4	313.5
70°	296.2	295.2	294.1	293.0	291.9	290.2	287.7	285.3	282.9	280.4	278.5
72.5°	259.3	258.3	257.1	256.1	255.0	253.7	252.2	250.6	249.0	247.4	245.5
75°	204.0	203.4	202.9	202.3	201.8	200.8	199.5	198.1	196.8	195.4	193.8
77.5°	154.4	153.5	152.6	151.7	150.8	150.0	149.5	148.9	148.4	147.9	147.0
80°	121.4	121.1	120.9	120.6	120.3	119.9	119.4	118.8	118.3	117.8	116.9
82.5°	90.3	90.3	90.2	90.2	90.1	89.9	89.6	89.3	89.0	88.6	87.6
85°	49.7	49.5	49.3	49.0	48.7	48.4	48.2	47.8	47.6	47.4	46.5
87.5°	17.6	17.4	17.3	17.1	17.0	16.8	16.6	16.3	16.1	15.8	15.4
90°	0.6	2.0	3.3	4.8	6.1	7.3	8.3	9.3	10.3	11.3	12.0
92.5°	11.4	11.3	11.2	11.1	10.9	11.2	11.6	12.1	12.7	13.2	13.5
95°	36.8	32.7	28.5	24.4	20.2	18.5	19.5	20.4	21.2	22.1	22.7
97.5°	73.1	61.4	49.7	37.9	26.2	21.4	23.4	25.5	27.6	29.5	30.1
100°	100.3	83.0	65.8	48.6	31.3	23.8	25.9	28.0	30.2	32.3	33.3
102.5°	130.2	126.6	122.9	119.3	115.6	104.8	86.9	69.0	51.1	33.2	34.5
105°	172.3	176.0	179.8	183.6	187.4	172.1	137.7	103.3	68.9	34.5	36.0
107.5°	220.2	223.2	226.3	229.3	232.4	213.3	172.1	130.9	89.6	48.4	47.0
110°	251.0	253.7	256.4	259.0	261.6	244.7	208.3	172.0	135.5	99.2	86.6



TEST NUMBER: P331444-927

CATALOG NUMBER: SA2XXDIP-C1005D725U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	280.0	282.4	284.7	287.1	289.4	286.1	277.1	268.1	259.1	250.1	204.2
115°	325.8	328.0	330.1	332.2	334.4	337.1	340.2	343.3	346.5	349.7	291.4
117.5°	366.8	369.2	371.5	373.9	376.3	378.6	380.8	382.9	385.1	387.3	373.2
120°	396.6	398.5	400.4	402.3	404.3	406.3	408.6	410.8	413.1	415.3	416.8
122.5°	422.1	424.1	426.0	428.0	430.0	432.2	434.7	437.2	439.7	442.1	443.0
125°	460.7	462.3	464.0	465.6	467.2	469.3	471.7	474.0	476.4	478.9	479.7
127.5°	495.7	497.6	499.4	501.1	503.0	504.8	506.6	508.3	510.2	511.9	513.3
130°	517.9	520.0	522.0	523.9	526.0	527.7	529.1	530.4	531.9	533.2	534.6
132.5°	540.6	542.3	544.1	545.7	547.5	549.0	550.4	551.8	553.2	554.5	555.7
135°	570.1	572.1	574.1	576.2	578.1	579.7	580.8	581.9	583.1	584.2	585.5
137.5°	599.9	601.3	602.7	604.1	605.5	606.9	608.2	609.4	610.7	612.0	613.2
140°	619.4	620.4	621.4	622.4	623.4	624.6	626.0	627.4	628.8	630.2	631.3
142.5°	635.7	636.6	637.5	638.4	639.3	640.6	642.1	643.7	645.3	646.9	647.9
145°	661.3	661.2	661.1	660.9	660.8	661.8	663.9	666.1	668.2	670.3	671.3
147.5°	683.7	683.2	682.7	682.2	681.8	682.5	684.7	686.7	688.9	691.0	691.7
150°	698.2	697.3	696.4	695.5	694.6	695.2	697.2	699.2	701.2	703.2	704.0
152.5°	710.3	709.4	708.4	707.4	706.5	706.9	708.8	710.7	712.6	714.5	715.3
155°	728.2	727.1	725.9	724.8	723.7	723.8	725.3	726.8	728.3	729.8	730.6
157.5°	742.1	741.2	740.2	739.3	738.3	738.3	739.4	740.5	741.5	742.6	743.5
160°	750.3	749.5	748.8	748.0	747.3	747.3	748.0	748.8	749.5	750.3	751.1
162.5°	757.6	756.8	756.1	755.3	754.5	754.5	755.1	755.7	756.5	757.1	758.0
165°	767.3	766.5	765.8	765.0	764.2	764.1	764.5	764.9	765.2	765.6	766.4
167.5°	774.5	773.8	773.0	772.3	771.5	771.3	771.7	772.0	772.4	772.7	773.6
170°	778.6	777.8	777.1	776.3	775.6	775.3	775.6	775.9	776.1	776.3	777.2
172.5°	781.3	780.5	779.8	779.0	778.3	778.1	778.3	778.6	778.8	779.0	780.0
175°	784.8	783.9	783.1	782.2	781.3	781.0	781.3	781.5	781.7	782.0	782.9
177.5°	785.4	784.7	784.0	783.3	782.6	782.3	782.4	782.5	782.6	782.7	783.4
180°	783.2	783.2	783.2	783.2	783.2	783.2	783.2	783.2	783.2	783.2	783.2



TEST NUMBER: P331444-927

CATALOG NUMBER: SA2XXDIP-C1005D725U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6
2.5°	1257.2	1259.3	1261.6	1262.4	1261.9	1261.6	1261.1	1260.7
5°	1248.7	1250.9	1253.0	1253.9	1253.3	1252.8	1252.2	1251.6
7.5°	1234.6	1236.8	1239.0	1239.8	1239.1	1238.6	1237.9	1237.4
10°	1222.0	1224.2	1226.3	1227.0	1226.2	1225.3	1224.6	1223.8
12.5°	1207.1	1208.6	1210.1	1210.6	1210.0	1209.4	1208.8	1208.2
15°	1181.0	1182.1	1183.1	1183.0	1181.7	1180.4	1179.0	1177.7
17.5°	1150.0	1151.3	1152.5	1152.5	1151.1	1149.9	1148.6	1147.2
20°	1125.8	1126.6	1127.4	1127.3	1126.2	1125.1	1124.1	1123.0
22.5°	1100.3	1100.4	1100.6	1100.3	1099.7	1099.1	1098.4	1097.7
25°	1058.5	1059.1	1059.6	1059.6	1059.1	1058.5	1058.0	1057.4
27.5°	1017.5	1016.6	1015.8	1014.8	1013.5	1012.2	1010.9	1009.6
30°	985.4	984.6	983.8	982.9	981.8	980.6	979.6	978.5
32.5°	954.0	952.5	951.1	949.8	948.7	947.7	946.6	945.5
35°	903.6	902.1	900.4	899.0	897.6	896.3	894.8	893.5
37.5°	853.1	851.1	849.1	847.5	846.2	844.9	843.6	842.3
40°	818.2	815.9	813.4	811.7	810.6	809.5	808.4	807.3
42.5°	783.9	781.2	778.6	776.5	775.0	773.5	772.0	770.4
45°	731.0	728.0	725.1	723.0	721.9	720.9	719.8	718.7
47.5°	676.0	672.9	669.8	667.4	665.8	664.3	662.7	661.2
50°	640.7	637.0	633.2	630.7	629.3	628.0	626.6	625.3
52.5°	604.2	601.0	597.9	595.5	593.7	591.9	590.1	588.4
55°	549.5	546.3	543.1	540.8	539.5	538.1	536.8	535.4
57.5°	492.8	489.6	486.5	484.3	483.4	482.4	481.3	480.3
60°	455.4	452.4	449.5	447.6	446.8	446.0	445.1	444.3
62.5°	419.9	417.2	414.4	412.5	411.5	410.4	409.4	408.4
65°	365.4	363.0	360.6	358.7	357.4	356.0	354.7	353.3
67.5°	311.6	309.7	307.8	306.3	305.3	304.2	303.2	302.1
70°	276.6	274.8	272.9	271.4	270.3	269.3	268.2	267.1
72.5°	243.7	241.8	239.9	238.5	237.7	236.8	235.9	235.0
75°	192.3	190.6	189.0	188.5	189.0	189.5	190.0	190.6
77.5°	146.2	145.4	144.7	143.9	143.1	142.4	141.6	140.9
80°	116.1	115.3	114.5	113.8	113.3	112.8	112.3	111.7
82.5°	86.6	85.6	84.5	84.0	83.8	83.7	83.7	83.5
85°	45.7	44.9	44.1	43.6	43.3	43.0	42.8	42.5
87.5°	14.8	14.3	13.8	13.5	13.2	13.1	12.9	12.8
90°	12.6	13.2	13.9	14.3	14.6	14.8	15.1	15.3
92.5°	13.8	14.1	14.4	14.7	14.8	15.0	15.1	15.3
95°	23.4	24.0	24.6	24.9	24.7	24.6	24.5	24.4
97.5°	30.6	31.1	31.6	31.9	32.1	32.2	32.4	32.6
100°	34.3	35.3	36.4	37.0	37.2	37.5	37.7	37.9
102.5°	35.8	37.2	38.4	39.3	39.6	40.0	40.3	40.7
105°	37.3	38.7	40.1	41.0	41.6	42.1	42.5	43.1
107.5°	45.6	44.1	42.8	42.3	42.8	43.3	43.8	44.3
110°	74.0	61.4	48.8	42.8	43.3	43.7	44.3	44.8





TEST NUMBER: P331444-927

CATALOG NUMBER: SA2XXDIP-C1005D725U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	158.3	112.3	66.4	43.6	44.0	44.4	44.8	45.2
115°	233.1	174.8	116.5	82.7	73.7	64.6	55.5	46.5
117.5°	359.1	344.9	330.8	308.9	279.1	249.3	219.5	189.7
120°	418.4	419.9	421.4	413.7	396.6	379.7	362.7	345.7
122.5°	443.9	444.8	445.8	444.6	441.2	437.9	434.7	431.3
125°	480.6	481.5	482.4	483.0	483.4	483.8	484.1	484.5
127.5°	514.5	515.8	517.1	517.8	517.8	517.9	518.0	518.1
130°	536.0	537.4	538.8	539.4	539.3	539.2	539.0	538.9
132.5°	556.9	558.1	559.3	559.8	559.7	559.6	559.4	559.3
135°	586.8	588.0	589.3	589.8	589.5	589.3	589.0	588.7
137.5°	614.5	615.7	617.0	617.3	617.0	616.5	616.1	615.6
140°	632.4	633.5	634.7	634.9	634.3	633.7	633.0	632.4
142.5°	649.0	650.0	651.0	651.3	650.6	650.0	649.4	648.7
145°	672.2	673.0	673.9	674.0	673.4	672.8	672.2	671.5
147.5°	692.3	693.0	693.6	693.7	693.2	692.6	692.1	691.6
150°	704.7	705.5	706.2	706.3	705.7	705.0	704.4	703.8
152.5°	716.1	716.8	717.6	717.6	716.8	715.9	715.1	714.2
155°	731.4	732.1	732.9	732.8	731.7	730.8	729.8	728.7
157.5°	744.3	745.1	746.0	745.9	745.0	743.9	743.0	742.0
160°	751.8	752.6	753.3	753.2	752.3	751.5	750.6	749.7
162.5°	758.8	759.6	760.5	760.4	759.3	758.2	757.2	756.1
165°	767.3	768.3	769.1	769.1	768.3	767.3	766.4	765.6
167.5°	774.5	775.4	776.3	776.1	775.0	773.9	772.7	771.6
170°	778.1	779.0	779.9	779.7	778.6	777.4	776.3	775.2
172.5°	780.9	781.7	782.6	782.4	781.3	780.2	779.0	777.9
175°	783.8	784.7	785.5	785.4	784.1	782.8	781.6	780.3
177.5°	784.1	784.8	785.5	785.4	784.5	783.6	782.7	781.8
180°	783.2	783.2	783.2	783.2	783.2	783.2	783.2	783.2

(END OF REPORT)