

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331445-927

Luminaire Tested: **SA2XXDIP-C1005D725U927-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331445-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C1005D725U927-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 725 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5266.9 lumens
Efficiency: N/A
Efficacy: 86.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 60.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331445-927
CATALOG NUMBER: SA2XXDIP-C1005D725U927-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331445-927

CATALOG NUMBER: SA2XXDIP-C1005D725U927-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	89	89	89	77	77	77	66	66	66	61
1	100	96	92	88	94	90	86	83	79	76	74	68	66	64	59	57	56	51
2	91	84	77	72	85	79	73	68	69	65	61	60	57	54	52	49	47	43
3	83	74	66	60	78	69	63	57	61	56	51	53	49	46	46	43	40	36
4	76	65	57	51	71	61	54	49	54	48	44	47	43	39	41	37	35	31
5	70	58	50	44	65	55	47	42	48	42	38	42	38	34	37	33	30	27
6	65	52	44	38	60	49	42	36	44	38	33	38	34	30	33	30	27	24
7	60	47	39	33	56	45	37	32	40	34	29	35	30	26	31	27	24	21
8	56	43	35	30	52	41	33	28	36	30	26	32	27	24	28	24	21	19
9	52	39	32	27	48	37	30	25	33	27	23	29	25	21	26	22	19	17
10	48	36	29	24	45	34	27	23	31	25	21	27	23	19	24	20	17	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	20386	20386	20386
5°	20464	20169	20285
10°	20341	19964	20064
15°	20090	19704	19686
20°	19734	19316	19295
25°	19379	18838	18838
30°	18921	18401	18243
35°	18496	17875	17611
40°	17962	17351	17015
45°	17438	16826	16411
50°	16865	16284	15707
55°	16268	15651	15071
60°	15603	14899	14347
65°	14888	14147	13498
70°	13983	13237	12609
75°	12726	12190	11890
80°	11288	10953	10386
85°	9207	8781	7873



TEST NUMBER: P331445-927

CATALOG NUMBER: SA2XXDIP-C1005D725U927-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	118.7	2.3
10°-20°	334.1	6.3
20°-30°	491.0	9.3
30°-40°	570.4	10.8
40°-50°	569.8	10.8
50°-60°	496.9	9.4
60°-70°	367.4	7.0
70°-80°	208.1	4.0
80°-90°	58.9	1.1
90°-100°	46.5	0.9
100°-110°	144.4	2.7
110°-120°	246.8	4.7
120°-130°	324.6	6.2
130°-140°	364.3	6.9
140°-150°	357.2	6.8
150°-160°	299.6	5.7
160°-170°	198.7	3.8
170°-180°	69.5	1.3
0°-30°	943.8	17.9
0°-40°	1514.2	28.7
0°-60°	2580.8	49.0
0°-90°	3215.2	61.0
90°-120°	437.7	8.3
90°-150°	1483.9	28.2
90°-180°	2052.0	39.0
0°-180°	5266.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1263	1263	1263	1263	1263	
5°	1263	1257	1244	1253	1252	120
15°	1202	1194	1179	1183	1178	338
25°	1088	1078	1057	1060	1057	500
35°	938	926	907	900	894	586
45°	764	755	737	724	719	589
55°	578	570	556	542	535	517
65°	390	382	370	360	353	385
75°	204	201	195	189	191	218
85°	50	49	47	44	42	57
90°	1	8	22	21	21	4
95°	32	38	40	40	38	37
105°	133	135	136	137	137	141
115°	248	251	250	249	248	245
125°	360	366	364	362	362	322
135°	466	473	474	474	472	360
145°	566	570	574	574	572	353
155°	647	649	651	654	652	298
165°	704	703	703	707	705	198
175°	732	731	729	733	730	70
180°	734	734	734	734	734	



TEST NUMBER: P331445-927

CATALOG NUMBER: SA2XXDIP-C1005D725U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6
2.5°	1268.4	1267.3	1266.3	1265.2	1264.1	1262.4	1260.0	1257.7	1255.3	1252.9	1255.1
5°	1262.6	1261.6	1260.4	1259.3	1258.3	1256.2	1253.3	1250.3	1247.4	1244.4	1246.6
7.5°	1251.4	1249.7	1248.1	1246.4	1244.8	1242.4	1239.4	1236.4	1233.3	1230.3	1232.5
10°	1240.7	1238.9	1237.0	1235.1	1233.2	1230.7	1227.4	1224.2	1220.9	1217.7	1219.9
12.5°	1226.2	1224.5	1222.8	1221.1	1219.5	1217.0	1213.8	1210.5	1207.4	1204.1	1205.6
15°	1201.9	1200.3	1198.7	1197.1	1195.4	1192.9	1189.4	1185.8	1182.3	1178.8	1180.0
17.5°	1170.8	1169.2	1167.6	1165.9	1164.3	1161.7	1158.2	1154.6	1151.0	1147.6	1148.7
20°	1148.5	1146.8	1145.3	1143.6	1142.0	1139.3	1135.5	1131.8	1128.0	1124.2	1125.0
22.5°	1126.2	1123.9	1121.7	1119.4	1117.1	1114.2	1110.6	1107.1	1103.5	1099.9	1100.1
25°	1087.8	1085.6	1083.5	1081.3	1079.2	1075.8	1071.2	1066.6	1062.0	1057.4	1058.0
27.5°	1044.1	1042.1	1040.2	1038.2	1036.3	1033.6	1029.9	1026.3	1022.7	1019.1	1018.3
30°	1014.9	1012.8	1010.6	1008.4	1006.3	1003.2	999.2	995.1	991.1	987.0	986.2
32.5°	983.9	982.1	980.4	978.7	976.9	974.0	969.7	965.4	961.2	956.9	955.5
35°	938.4	935.7	933.0	930.3	927.6	924.2	919.8	915.5	911.2	906.9	905.3
37.5°	887.2	884.9	882.5	880.1	877.7	874.4	870.1	865.8	861.4	857.1	855.1
40°	852.2	850.1	848.0	845.8	843.6	840.4	836.1	831.8	827.4	823.2	820.7
42.5°	818.2	816.1	814.0	811.8	809.6	806.4	802.1	797.7	793.4	789.1	786.5
45°	763.7	761.8	759.9	758.0	756.1	753.1	749.1	745.0	741.0	736.9	734.0
47.5°	709.2	707.5	705.7	703.9	702.1	699.1	694.9	690.7	686.5	682.3	679.1
50°	671.4	670.0	668.7	667.3	666.0	663.4	659.7	655.8	652.0	648.3	644.5
52.5°	634.5	632.7	630.9	629.2	627.3	624.6	621.1	617.5	614.0	610.5	607.3
55°	577.9	576.2	574.6	573.1	571.4	568.9	565.8	562.5	559.3	556.0	552.8
57.5°	521.1	519.8	518.5	517.2	515.9	513.5	509.9	506.4	502.8	499.2	496.1
60°	483.2	482.1	481.0	480.0	478.9	476.4	472.7	468.9	465.1	461.4	458.4
62.5°	446.3	444.6	442.8	441.1	439.3	437.0	434.1	431.3	428.3	425.4	422.6
65°	389.7	388.1	386.5	384.8	383.3	381.0	378.3	375.7	373.0	370.3	367.9
67.5°	332.2	330.9	329.5	328.3	327.0	325.1	322.7	320.3	317.8	315.4	313.5
70°	296.2	295.2	294.1	293.0	291.9	290.2	287.7	285.3	282.9	280.4	278.5
72.5°	259.3	258.3	257.1	256.1	255.0	253.7	252.2	250.6	249.0	247.4	245.5
75°	204.0	203.4	202.9	202.3	201.8	200.8	199.5	198.1	196.8	195.4	193.8
77.5°	154.4	153.5	152.6	151.7	150.8	150.0	149.5	148.9	148.4	147.9	147.0
80°	121.4	121.1	120.9	120.6	120.3	119.9	119.4	118.8	118.3	117.8	116.9
82.5°	90.3	90.3	90.2	90.2	90.1	89.9	89.6	89.3	89.0	88.6	87.6
85°	49.7	49.5	49.3	49.0	48.7	48.4	48.2	47.8	47.6	47.4	46.5
87.5°	17.6	17.5	17.4	17.3	17.2	17.3	17.4	17.6	17.7	17.9	17.2
90°	0.6	2.3	4.0	5.5	7.2	9.6	12.6	15.6	18.6	21.7	21.4
92.5°	11.0	12.2	13.5	14.7	15.8	16.8	17.5	18.2	19.0	19.7	19.7
95°	32.2	33.6	34.9	36.4	37.7	38.5	38.8	39.1	39.4	39.6	39.6
97.5°	58.9	60.0	61.2	62.4	63.7	64.6	65.0	65.6	66.1	66.6	66.6
100°	78.7	79.8	80.8	81.9	83.0	83.8	84.2	84.6	85.0	85.5	85.5
102.5°	99.4	100.3	101.2	102.1	103.0	103.7	104.2	104.7	105.2	105.8	105.8
105°	133.2	133.6	134.0	134.4	134.8	135.1	135.4	135.7	135.9	136.3	136.5
107.5°	167.1	167.7	168.3	168.9	169.4	169.8	169.8	169.8	169.8	169.8	169.9
110°	188.9	189.6	190.5	191.3	192.2	192.6	192.6	192.6	192.6	192.6	192.6



TEST NUMBER: P331445-927

CATALOG NUMBER: SA2XXDIP-C1005D725U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	212.6	213.5	214.3	215.1	215.9	216.3	216.2	216.1	215.9	215.9	215.6
115°	247.7	248.5	249.3	250.2	251.0	251.3	251.0	250.7	250.4	250.2	250.0
117.5°	282.6	283.7	284.8	285.9	287.0	287.2	286.4	285.7	284.9	284.1	283.8
120°	305.9	307.0	308.1	309.2	310.3	310.3	309.2	308.1	307.0	305.9	305.9
122.5°	327.2	328.5	329.9	331.1	332.5	332.7	332.0	331.2	330.4	329.6	329.3
125°	360.4	361.6	362.8	364.1	365.4	365.8	365.4	364.9	364.5	364.1	363.7
127.5°	392.7	394.3	395.9	397.4	398.9	399.5	399.0	398.5	398.0	397.5	397.0
130°	413.0	414.8	416.6	418.4	420.2	420.9	420.6	420.3	420.1	419.9	419.5
132.5°	435.8	437.3	438.7	440.1	441.6	442.4	442.4	442.5	442.5	442.6	442.0
135°	466.3	467.8	469.3	470.8	472.3	473.2	473.5	473.7	474.0	474.3	474.2
137.5°	498.4	499.6	500.8	502.1	503.3	504.1	504.5	504.8	505.2	505.5	505.4
140°	517.7	518.9	520.1	521.3	522.6	523.6	524.3	525.0	525.6	526.3	526.3
142.5°	537.5	538.7	540.0	541.2	542.4	543.3	543.8	544.2	544.7	545.2	545.3
145°	565.9	566.9	567.9	568.9	569.8	570.7	571.6	572.4	573.1	574.0	574.2
147.5°	591.4	592.5	593.7	594.8	596.0	596.8	597.4	597.9	598.5	599.0	599.3
150°	608.7	609.5	610.3	611.2	612.0	612.7	613.2	613.8	614.3	614.9	615.3
152.5°	624.0	624.9	625.7	626.5	627.3	628.0	628.8	629.4	630.0	630.7	631.2
155°	647.1	647.5	647.9	648.3	648.7	649.1	649.5	650.0	650.4	650.8	651.5
157.5°	666.8	667.0	667.3	667.6	667.9	668.1	668.4	668.6	668.8	669.1	670.0
160°	678.7	678.9	679.2	679.5	679.8	679.9	680.1	680.2	680.4	680.5	681.4
162.5°	689.5	689.6	689.7	689.7	689.8	689.8	690.0	690.1	690.3	690.4	691.3
165°	704.0	703.9	703.8	703.6	703.5	703.4	703.4	703.4	703.4	703.4	704.4
167.5°	716.1	715.7	715.3	714.9	714.5	714.3	714.3	714.2	714.2	714.2	715.2
170°	722.6	722.2	721.8	721.4	721.0	720.6	720.6	720.4	720.3	720.1	721.1
172.5°	727.1	726.7	726.3	725.8	725.4	725.2	725.0	724.8	724.8	724.6	725.6
175°	732.5	732.1	731.7	731.3	730.9	730.6	730.2	730.0	729.7	729.4	730.4
177.5°	734.7	734.4	734.1	733.7	733.4	733.2	732.9	732.7	732.5	732.3	732.9
180°	733.7	733.7	733.7	733.7	733.7	733.7	733.7	733.7	733.7	733.7	733.7



TEST NUMBER: P331445-927

CATALOG NUMBER: SA2XXDIP-C1005D725U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6
2.5°	1257.2	1259.3	1261.6	1262.4	1261.9	1261.6	1261.1	1260.7
5°	1248.7	1250.9	1253.0	1253.9	1253.3	1252.8	1252.2	1251.6
7.5°	1234.6	1236.8	1239.0	1239.8	1239.1	1238.6	1237.9	1237.4
10°	1222.0	1224.2	1226.3	1227.0	1226.2	1225.3	1224.6	1223.8
12.5°	1207.1	1208.6	1210.1	1210.6	1210.0	1209.4	1208.8	1208.2
15°	1181.0	1182.1	1183.1	1183.0	1181.7	1180.4	1179.0	1177.7
17.5°	1150.0	1151.3	1152.5	1152.5	1151.1	1149.9	1148.6	1147.2
20°	1125.8	1126.6	1127.4	1127.3	1126.2	1125.1	1124.1	1123.0
22.5°	1100.3	1100.4	1100.6	1100.3	1099.7	1099.1	1098.4	1097.7
25°	1058.5	1059.1	1059.6	1059.6	1059.1	1058.5	1058.0	1057.4
27.5°	1017.5	1016.6	1015.8	1014.8	1013.5	1012.2	1010.9	1009.6
30°	985.4	984.6	983.8	982.9	981.8	980.6	979.6	978.5
32.5°	954.0	952.5	951.1	949.8	948.7	947.7	946.6	945.5
35°	903.6	902.1	900.4	899.0	897.6	896.3	894.8	893.5
37.5°	853.1	851.1	849.1	847.5	846.2	844.9	843.6	842.3
40°	818.2	815.9	813.4	811.7	810.6	809.5	808.4	807.3
42.5°	783.9	781.2	778.6	776.5	775.0	773.5	772.0	770.4
45°	731.0	728.0	725.1	723.0	721.9	720.9	719.8	718.7
47.5°	676.0	672.9	669.8	667.4	665.8	664.3	662.7	661.2
50°	640.7	637.0	633.2	630.7	629.3	628.0	626.6	625.3
52.5°	604.2	601.0	597.9	595.5	593.7	591.9	590.1	588.4
55°	549.5	546.3	543.1	540.8	539.5	538.1	536.8	535.4
57.5°	492.8	489.6	486.5	484.3	483.4	482.4	481.3	480.3
60°	455.4	452.4	449.5	447.6	446.8	446.0	445.1	444.3
62.5°	419.9	417.2	414.4	412.5	411.5	410.4	409.4	408.4
65°	365.4	363.0	360.6	358.7	357.4	356.0	354.7	353.3
67.5°	311.6	309.7	307.8	306.3	305.3	304.2	303.2	302.1
70°	276.6	274.8	272.9	271.4	270.3	269.3	268.2	267.1
72.5°	243.7	241.8	239.9	238.5	237.7	236.8	235.9	235.0
75°	192.3	190.6	189.0	188.5	189.0	189.5	190.0	190.6
77.5°	146.2	145.4	144.7	143.9	143.1	142.4	141.6	140.9
80°	116.1	115.3	114.5	113.8	113.3	112.8	112.3	111.7
82.5°	86.6	85.6	84.5	84.0	83.8	83.7	83.7	83.5
85°	45.7	44.9	44.1	43.6	43.3	43.0	42.8	42.5
87.5°	16.6	15.8	15.1	14.7	14.5	14.3	14.1	13.9
90°	21.2	20.8	20.6	20.5	20.7	20.8	20.9	21.1
92.5°	19.8	19.9	19.9	20.0	20.0	20.0	20.0	20.0
95°	39.6	39.6	39.6	39.5	39.2	39.0	38.7	38.4
97.5°	66.6	66.6	66.6	66.6	66.6	66.5	66.5	66.5
100°	85.5	85.5	85.5	85.4	85.2	85.1	85.0	84.8
102.5°	106.0	106.1	106.2	106.2	106.1	105.9	105.8	105.6
105°	136.8	137.0	137.4	137.4	137.4	137.4	137.4	137.4
107.5°	170.0	170.1	170.2	170.0	169.4	168.7	168.1	167.5
110°	192.6	192.6	192.6	192.3	191.9	191.5	191.2	190.7



TEST NUMBER: P331445-927

CATALOG NUMBER: SA2XXDIP-C1005D725U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	215.2	214.8	214.5	214.2	213.9	213.6	213.3	213.0
115°	249.9	249.8	249.6	249.3	248.9	248.5	248.1	247.7
117.5°	283.4	283.1	282.7	282.4	282.0	281.5	281.1	280.7
120°	305.9	305.9	305.9	305.7	305.2	304.8	304.4	304.0
122.5°	329.0	328.7	328.4	328.0	327.7	327.4	327.1	326.9
125°	363.3	362.8	362.4	362.2	362.0	361.9	361.8	361.6
127.5°	396.6	396.0	395.5	395.1	394.7	394.2	393.8	393.3
130°	419.3	419.0	418.7	418.3	417.7	417.2	416.7	416.1
132.5°	441.4	440.8	440.2	439.7	439.2	438.8	438.3	437.9
135°	474.0	473.9	473.7	473.5	473.1	472.7	472.2	471.8
137.5°	505.3	505.2	505.1	504.8	504.2	503.7	503.1	502.6
140°	526.3	526.3	526.3	526.0	525.5	525.0	524.4	523.9
142.5°	545.3	545.5	545.6	545.3	544.8	544.2	543.8	543.2
145°	574.3	574.4	574.6	574.3	573.8	573.2	572.7	572.1
147.5°	599.6	599.9	600.2	600.2	599.6	599.0	598.6	598.0
150°	615.7	616.1	616.6	616.6	616.1	615.7	615.3	614.9
152.5°	631.8	632.3	632.8	632.8	632.3	631.8	631.2	630.7
155°	652.1	652.8	653.6	653.7	653.2	652.8	652.4	652.0
157.5°	671.0	671.9	672.9	673.0	672.3	671.7	671.0	670.3
160°	682.1	683.0	683.8	684.0	683.4	682.9	682.3	681.8
162.5°	692.3	693.2	694.2	694.3	693.6	693.0	692.3	691.7
165°	705.4	706.3	707.3	707.4	706.7	706.0	705.4	704.6
167.5°	716.1	717.1	718.0	718.2	717.5	716.8	716.1	715.3
170°	722.1	723.0	724.0	724.1	723.3	722.4	721.6	720.7
172.5°	726.5	727.5	728.4	728.5	727.7	726.8	726.0	725.2
175°	731.3	732.3	733.2	733.3	732.5	731.7	730.9	730.1
177.5°	733.6	734.3	734.9	734.9	734.3	733.6	732.9	732.3
180°	733.7	733.7	733.7	733.7	733.7	733.7	733.7	733.7

(END OF REPORT)