

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331688-930

Luminaire Tested: **SA2XXRDIP-C675D725U930-4F0-1E-UDD-A1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331688-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C675D725U930-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 725 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4184.6 lumens
Efficiency: N/A
Efficacy: 91.2 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 45.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331688-930
CATALOG NUMBER: SA2XXRDIP-C675D725U930-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331688-930

CATALOG NUMBER: SA2XXRDIP-C675D725U930-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	50				
1	98	94	91	88	91	87	84	81	74	72	70	62	60	59	50	49	48	43				
2	90	83	78	73	83	77	72	68	66	62	59	55	53	50	45	44	42	37				
3	83	74	67	62	76	69	63	58	59	54	51	50	46	44	41	39	37	33				
4	76	66	59	53	70	62	55	50	53	48	44	45	41	38	37	35	32	29				
5	70	59	52	46	65	55	49	43	48	43	39	41	37	34	34	31	29	26				
6	65	54	46	40	60	50	43	38	43	38	34	37	33	30	31	28	26	23				
7	60	49	41	36	56	46	39	34	40	34	30	34	30	27	29	26	23	21				
8	56	45	37	32	52	42	35	31	36	31	27	31	27	24	27	24	21	19				
9	53	41	34	29	49	38	32	28	34	28	25	29	25	22	25	22	20	17				
10	49	38	31	26	46	35	29	25	31	26	23	27	23	20	23	20	18	16				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	19339	19339	19339	19339
5°	21598	19460	17253	19460
10°	23963	19323	14955	19323
15°	25142	19041	11784	19041
20°	21795	18620	10198	18620
25°	14295	18045	9103	18045
30°	9622	17350	8240	17350
35°	7792	16472	7433	16472
40°	6930	15517	6877	15517
45°	6272	14397	6140	14397
50°	5707	13288	5687	13288
55°	5365	12056	5295	12056
60°	4489	10924	4434	10924
65°	3786	9922	4290	9922
70°	3498	8861	4050	8861
75°	3269	7711	3737	7711
80°	3013	6341	3329	6341
85°	2779	5020	2927	5020



TEST NUMBER: P331688-930

CATALOG NUMBER: SA2XXRDIP-C675D725U930-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	113.5	2.7
10°-20°	316.4	7.6
20°-30°	407.7	9.7
30°-40°	387.4	9.3
40°-50°	331.9	7.9
50°-60°	252.7	6.0
60°-70°	159.8	3.8
70°-80°	79.8	1.9
80°-90°	23.8	0.6
90°-100°	47.9	1.1
100°-110°	148.6	3.6
110°-120°	254.0	6.1
120°-130°	334.1	8.0
130°-140°	375.0	9.0
140°-150°	367.7	8.8
150°-160°	308.4	7.4
160°-170°	204.5	4.9
170°-180°	71.5	1.7
0°-30°	837.6	20.0
0°-40°	1225.0	29.3
0°-60°	1809.6	43.2
0°-90°	2073.0	49.5
90°-120°	450.5	10.8
90°-150°	1527.2	36.5
90°-180°	2112.0	50.5
0°-180°	4184.6	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1198	1198	1198	1198	1198	
5°	1333	1201	1064	1201	1333	132
15°	1504	1139	705	1139	1504	406
25°	802	1013	511	1013	802	381
35°	395	836	377	836	395	253
45°	275	630	269	630	275	213
55°	191	428	188	428	191	167
65°	99	260	112	260	99	101
75°	52	124	60	124	52	56
85°	15	27	16	27	15	17
90°	22	1	22	1	22	10
95°	40	33	40	33	40	44
105°	142	137	142	137	142	149
115°	255	255	255	255	255	252
125°	372	371	372	371	372	332
135°	486	480	486	480	486	374
145°	589	582	589	582	589	368
155°	671	666	671	666	671	309
165°	725	725	725	725	725	205
175°	751	754	751	754	751	71
180°	755	755	755	755	755	



TEST NUMBER: P331688-930

CATALOG NUMBER: SA2XXRDIP-C675D725U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8
2.5°	1246.3	1247.3	1248.4	1246.0	1246.0	1244.0	1239.7	1236.4	1227.0	1225.7	1225.7
5°	1332.6	1331.7	1333.4	1328.0	1320.5	1318.8	1310.9	1300.6	1289.7	1277.7	1275.1
7.5°	1418.3	1417.1	1413.7	1412.8	1407.0	1394.5	1381.8	1368.2	1350.2	1332.7	1323.9
10°	1461.6	1475.4	1467.0	1452.5	1455.4	1435.8	1425.4	1407.5	1392.5	1366.3	1360.5
12.5°	1504.2	1509.6	1507.0	1498.7	1494.9	1481.4	1467.4	1451.8	1424.2	1400.6	1380.1
15°	1504.1	1512.0	1514.0	1511.6	1513.6	1512.8	1505.3	1492.4	1468.3	1442.4	1420.0
17.5°	1393.0	1398.5	1412.2	1421.4	1433.1	1457.7	1469.8	1474.6	1471.0	1456.3	1440.5
20°	1268.5	1259.3	1297.6	1317.2	1333.8	1375.4	1411.2	1425.0	1447.0	1446.6	1442.4
22.5°	1092.0	1094.2	1130.5	1153.7	1202.3	1243.9	1284.7	1336.4	1379.1	1407.3	1423.8
25°	802.4	818.2	854.4	886.1	940.1	1017.6	1087.9	1169.5	1246.4	1307.2	1365.1
27.5°	602.6	603.8	632.5	661.7	693.8	757.2	845.8	943.2	1053.0	1143.5	1247.7
30°	516.1	513.6	525.6	543.6	571.0	620.1	686.6	782.4	891.9	1028.3	1149.9
32.5°	454.8	454.9	464.1	477.3	500.1	533.2	578.8	656.6	760.0	894.2	1036.7
35°	395.3	394.9	401.6	411.2	420.8	442.0	473.2	514.0	585.1	710.4	856.1
37.5°	352.8	354.6	357.8	363.8	374.4	386.2	405.0	432.4	483.0	557.1	679.6
40°	328.8	329.6	334.2	339.2	345.4	354.6	370.0	392.0	429.1	488.2	577.6
42.5°	306.8	307.6	310.9	315.5	320.4	329.6	342.3	361.4	391.4	437.6	511.4
45°	274.7	274.7	277.6	279.6	285.1	293.4	303.8	319.6	340.5	374.5	423.6
47.5°	244.5	244.6	246.5	250.1	253.6	260.0	270.3	283.2	298.3	324.7	366.6
50°	227.2	227.6	228.9	231.8	233.9	239.7	247.6	258.9	274.7	295.1	330.0
52.5°	213.3	213.0	214.6	215.8	217.3	221.4	227.3	237.3	251.4	269.1	298.1
55°	190.6	188.9	191.4	193.6	194.8	196.4	199.7	206.0	218.1	233.1	254.7
57.5°	162.3	161.7	163.4	165.3	169.3	173.7	176.5	180.5	186.8	197.5	219.0
60°	139.0	139.0	142.8	144.0	148.5	154.4	160.2	163.5	169.8	176.8	192.7
62.5°	118.4	118.7	120.4	121.7	124.3	131.4	139.6	146.9	152.8	159.6	170.1
65°	99.1	99.9	99.9	100.7	102.4	104.0	107.4	113.2	123.6	133.1	141.0
67.5°	84.1	84.3	84.5	85.4	85.9	87.6	88.9	91.6	94.0	103.1	112.8
70°	74.1	75.3	74.9	75.7	76.1	77.0	78.7	79.9	83.6	85.8	91.6
72.5°	64.7	65.6	65.6	66.1	67.2	67.3	68.6	70.0	72.3	74.1	77.2
75°	52.4	52.0	52.4	53.2	53.6	54.1	54.1	55.8	57.0	58.7	60.7
77.5°	40.4	40.8	40.8	40.8	40.9	41.7	41.6	42.4	43.6	44.4	45.4
80°	32.4	32.9	32.4	32.9	33.3	33.7	33.3	33.7	35.0	35.8	35.8
82.5°	25.1	25.2	25.4	25.5	25.6	25.7	26.3	26.4	27.3	27.1	27.5
85°	15.0	14.6	14.6	14.6	15.0	15.4	15.0	15.0	15.4	15.4	15.4
87.5°	9.6	9.9	9.9	9.9	9.9	9.9	9.9	10.4	10.0	10.4	9.5
90°	21.7	21.5	21.4	21.3	21.1	21.2	21.4	21.8	22.0	22.3	19.2
92.5°	20.6	20.6	20.6	20.5	20.5	20.5	20.5	20.4	20.3	20.3	19.6
95°	39.5	39.8	40.1	40.4	40.7	40.8	40.8	40.8	40.8	40.8	40.5
97.5°	68.4	68.5	68.5	68.6	68.6	68.6	68.6	68.6	68.6	68.6	68.0
100°	87.3	87.5	87.6	87.7	87.9	88.0	88.0	88.0	88.0	88.0	87.5
102.5°	108.7	108.8	109.0	109.2	109.3	109.3	109.2	109.1	108.9	108.8	108.3
105°	141.5	141.5	141.5	141.5	141.5	141.4	141.0	140.8	140.5	140.2	139.9
107.5°	172.4	173.0	173.7	174.3	175.0	175.2	175.0	175.0	174.9	174.7	174.7
110°	196.2	196.7	197.1	197.5	198.0	198.2	198.2	198.2	198.2	198.2	198.2



TEST NUMBER: P331688-930

CATALOG NUMBER: SA2XXRDIP-C675D725U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	219.2	219.6	219.8	220.1	220.5	220.8	221.1	221.4	221.8	222.2	222.3
115°	254.9	255.4	255.8	256.2	256.6	256.9	257.1	257.1	257.3	257.5	257.7
117.5°	288.9	289.3	289.8	290.2	290.7	291.0	291.4	291.7	292.0	292.4	293.2
120°	312.9	313.3	313.7	314.1	314.6	314.8	314.8	314.8	314.8	314.8	315.9
122.5°	336.4	336.6	337.0	337.3	337.6	337.9	338.3	338.6	338.9	339.2	340.1
125°	372.2	372.3	372.4	372.6	372.8	373.0	373.4	373.9	374.3	374.7	375.1
127.5°	404.8	405.3	405.7	406.2	406.6	407.1	407.6	408.1	408.6	409.1	409.6
130°	428.3	428.8	429.4	429.9	430.5	431.0	431.2	431.5	431.8	432.1	432.4
132.5°	450.7	451.1	451.6	452.0	452.5	453.1	453.6	454.3	454.9	455.5	455.4
135°	485.6	486.0	486.5	486.9	487.3	487.5	487.7	487.9	488.0	488.1	487.9
137.5°	517.2	517.8	518.4	518.9	519.5	519.8	519.9	520.1	520.2	520.2	519.9
140°	539.2	539.7	540.3	540.9	541.4	541.7	541.7	541.7	541.7	541.7	541.0
142.5°	559.1	559.6	560.1	560.7	561.3	561.5	561.4	561.3	561.2	561.1	560.6
145°	588.8	589.4	590.0	590.5	591.1	591.3	591.2	591.0	590.9	590.8	589.9
147.5°	615.5	616.0	616.5	617.1	617.7	617.8	617.4	617.1	616.8	616.5	616.0
150°	632.8	633.2	633.7	634.1	634.5	634.5	634.1	633.7	633.2	632.8	632.3
152.5°	649.1	649.6	650.2	650.8	651.3	651.3	650.8	650.2	649.6	649.1	648.4
155°	671.1	671.5	671.9	672.3	672.8	672.6	671.9	671.2	670.5	669.8	669.4
157.5°	689.9	690.6	691.3	691.9	692.6	692.5	691.5	690.6	689.6	688.6	688.4
160°	701.6	702.2	702.8	703.4	703.9	703.8	703.0	702.1	701.2	700.3	700.3
162.5°	711.8	712.5	713.2	713.9	714.5	714.4	713.5	712.5	711.5	710.5	710.5
165°	725.2	725.9	726.6	727.3	728.1	727.9	726.9	725.9	725.0	723.9	723.9
167.5°	736.2	736.9	737.7	738.4	739.2	739.0	738.0	737.0	736.1	735.0	735.1
170°	741.8	742.7	743.5	744.4	745.2	745.1	744.1	743.1	742.2	741.1	741.3
172.5°	746.4	747.2	748.0	748.9	749.7	749.7	748.7	747.7	746.7	745.8	745.9
175°	751.4	752.2	753.0	753.9	754.7	754.6	753.7	752.7	751.7	750.7	751.0
177.5°	753.7	754.3	755.0	755.7	756.4	756.4	755.7	755.0	754.3	753.7	753.8
180°	755.1	755.1	755.1	755.1	755.1	755.1	755.1	755.1	755.1	755.1	755.1



TEST NUMBER: P331688-930

CATALOG NUMBER: SA2XXRDIP-C675D725U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8
2.5°	1226.4	1223.7	1221.4	1215.4	1212.4	1205.7	1204.8	1204.4	1195.7	1187.4	1185.1
5°	1268.5	1261.8	1251.8	1240.2	1228.1	1215.6	1207.3	1200.7	1184.0	1168.2	1159.0
7.5°	1310.9	1296.7	1279.4	1257.4	1238.9	1218.3	1203.0	1189.3	1165.6	1143.0	1127.7
10°	1342.6	1319.2	1296.4	1266.0	1242.3	1219.0	1197.3	1178.6	1151.9	1122.0	1100.7
12.5°	1362.2	1336.6	1305.0	1275.3	1244.6	1215.0	1186.0	1162.0	1130.7	1099.7	1074.5
15°	1388.8	1361.3	1323.0	1280.6	1241.0	1202.3	1169.1	1139.1	1098.3	1061.3	1030.5
17.5°	1410.5	1372.7	1331.5	1282.5	1236.7	1187.5	1144.6	1106.4	1060.9	1016.3	980.0
20°	1417.5	1380.1	1332.6	1283.4	1229.4	1171.5	1125.4	1083.7	1035.0	986.3	944.7
22.5°	1413.2	1384.1	1331.2	1272.5	1217.1	1156.5	1104.3	1056.1	1002.1	952.4	904.1
25°	1383.8	1373.8	1323.9	1259.7	1196.5	1126.2	1065.8	1012.9	951.4	898.1	845.6
27.5°	1315.2	1336.8	1305.9	1237.6	1167.3	1091.8	1024.0	963.8	899.9	840.0	787.7
30°	1249.4	1298.9	1285.6	1222.3	1143.6	1069.6	993.4	930.6	862.3	800.7	749.1
32.5°	1159.1	1241.0	1253.9	1201.0	1119.7	1038.3	958.5	895.9	824.7	759.8	709.5
35°	1015.5	1137.8	1194.0	1160.3	1078.7	990.9	908.5	835.7	764.1	700.0	650.0
37.5°	844.1	1010.7	1104.3	1106.8	1031.8	940.5	850.8	778.5	705.2	642.3	588.3
40°	732.9	913.5	1035.4	1062.5	999.2	900.6	809.8	736.2	664.6	603.0	541.0
42.5°	633.0	812.9	962.9	1009.9	959.6	861.6	770.6	693.6	624.0	565.7	502.4
45°	511.9	669.2	834.5	918.5	890.6	799.9	703.8	630.5	565.2	514.8	454.0
47.5°	431.8	542.7	702.5	816.3	815.8	733.0	638.4	568.3	507.7	460.5	411.2
50°	386.2	482.7	618.0	747.1	757.8	688.4	598.4	529.0	472.4	422.8	383.3
52.5°	345.3	424.9	546.4	670.1	700.9	640.7	553.5	489.3	434.4	388.9	355.0
55°	291.7	353.4	445.7	561.4	608.1	565.6	488.2	428.3	383.7	345.4	316.3
57.5°	246.8	293.0	367.1	460.3	514.5	487.9	424.0	375.3	337.2	302.6	279.6
60°	218.5	256.3	319.2	397.1	457.0	438.2	383.7	338.3	305.9	275.9	254.3
62.5°	191.8	224.4	278.3	341.4	396.4	388.7	344.1	306.1	277.6	250.3	232.0
65°	154.4	178.1	220.1	269.7	313.8	317.6	285.5	259.7	234.3	212.6	196.4
67.5°	122.9	138.4	168.0	209.8	242.8	254.6	235.1	215.3	195.2	178.5	164.4
70°	103.6	116.1	137.8	171.5	201.9	214.3	203.1	187.7	170.2	156.5	144.4
72.5°	84.0	96.1	112.1	136.8	162.9	176.3	172.4	161.4	147.2	135.8	124.4
75°	63.3	67.0	77.9	94.5	114.9	126.5	129.5	123.6	112.3	103.6	96.9
77.5°	46.8	49.0	54.2	62.9	76.2	86.7	90.9	90.3	82.5	77.4	71.2
80°	37.4	38.7	41.2	44.9	55.0	65.3	68.2	68.2	62.9	60.7	54.5
82.5°	28.5	29.4	30.9	32.9	37.6	46.7	50.0	50.6	47.2	44.4	39.5
85°	16.2	15.8	16.6	17.9	18.8	21.2	26.3	27.1	26.3	22.9	21.6
87.5°	8.9	8.6	8.0	7.2	7.2	7.1	8.5	9.8	8.8	8.2	7.8
90°	16.1	13.0	9.9	7.4	5.7	4.1	2.4	0.7	2.4	4.1	5.7
92.5°	18.8	18.0	17.3	16.3	15.1	13.9	12.6	11.3	12.6	13.9	15.1
95°	40.2	39.9	39.6	38.8	37.4	36.0	34.6	33.1	34.6	36.0	37.4
97.5°	67.5	66.9	66.4	65.6	64.2	63.0	61.8	60.6	61.8	63.0	64.2
100°	87.1	86.7	86.3	85.4	84.3	83.2	82.1	81.0	82.1	83.2	84.3
102.5°	107.8	107.2	106.7	106.0	105.1	104.2	103.2	102.3	103.2	104.2	105.1
105°	139.7	139.3	139.1	138.7	138.3	137.9	137.5	137.1	137.5	137.9	138.3
107.5°	174.7	174.7	174.7	174.4	173.8	173.2	172.6	171.9	172.6	173.2	173.8
110°	198.2	198.2	198.2	197.8	196.9	196.1	195.2	194.4	195.2	196.1	196.9



TEST NUMBER: P331688-930
 CATALOG NUMBER: SA2XXRDIP-C675D725U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	222.4	222.5	222.6	222.3	221.4	220.5	219.7	218.8	219.7	220.5	221.4
115°	258.0	258.3	258.6	258.3	257.5	256.6	255.8	254.9	255.8	256.6	257.5
117.5°	294.0	294.7	295.5	295.4	294.2	293.1	292.0	290.8	292.0	293.1	294.2
120°	317.1	318.2	319.4	319.4	318.2	317.1	315.9	314.8	315.9	317.1	318.2
122.5°	340.9	341.7	342.4	342.2	340.8	339.5	338.1	336.7	338.1	339.5	340.8
125°	375.5	376.0	376.4	376.0	374.7	373.4	372.2	370.9	372.2	373.4	374.7
127.5°	410.2	410.7	411.2	410.6	409.0	407.4	405.8	404.1	405.8	407.4	409.0
130°	432.6	432.9	433.2	432.4	430.6	428.8	426.9	425.1	426.9	428.8	430.6
132.5°	455.4	455.3	455.3	454.5	453.0	451.5	450.0	448.5	450.0	451.5	453.0
135°	487.5	487.3	487.0	486.1	484.5	483.0	481.4	479.9	481.4	483.0	484.5
137.5°	519.5	519.2	518.8	518.0	516.7	515.4	514.1	512.9	514.1	515.4	516.7
140°	540.3	539.6	538.8	537.9	536.5	535.3	534.0	532.8	534.0	535.3	536.5
142.5°	560.1	559.6	559.1	558.2	557.0	555.7	554.4	553.2	554.4	555.7	557.0
145°	589.1	588.2	587.3	586.4	585.5	584.5	583.4	582.4	583.4	584.5	585.5
147.5°	615.4	614.8	614.2	613.3	612.1	611.0	609.8	608.6	609.8	611.0	612.1
150°	631.7	631.1	630.6	629.8	629.0	628.1	627.3	626.5	627.3	628.1	629.0
152.5°	647.8	647.1	646.4	645.6	644.8	643.9	643.1	642.2	643.1	643.9	644.8
155°	669.0	668.5	668.1	667.6	667.2	666.8	666.3	665.9	666.3	666.8	667.2
157.5°	688.1	687.9	687.6	687.4	687.1	686.8	686.5	686.2	686.5	686.8	687.1
160°	700.1	699.9	699.8	699.6	699.3	699.0	698.7	698.5	698.7	699.0	699.3
162.5°	710.3	710.1	710.0	709.9	709.8	709.8	709.7	709.6	709.7	709.8	709.8
165°	723.9	723.9	723.9	724.0	724.1	724.3	724.5	724.6	724.5	724.3	724.1
167.5°	735.1	735.2	735.2	735.4	735.8	736.2	736.6	737.0	736.6	736.2	735.8
170°	741.4	741.6	741.7	742.0	742.4	742.8	743.3	743.7	743.3	742.8	742.4
172.5°	746.0	746.2	746.3	746.6	747.0	747.5	747.9	748.3	747.9	747.5	747.0
175°	751.3	751.5	751.9	752.2	752.6	753.0	753.5	753.9	753.5	753.0	752.6
177.5°	754.1	754.3	754.6	754.8	755.1	755.5	755.9	756.2	755.9	755.5	755.1
180°	755.1	755.1	755.1	755.1	755.1	755.1	755.1	755.1	755.1	755.1	755.1



TEST NUMBER: P331688-930

CATALOG NUMBER: SA2XXRDIP-C675D725U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8
2.5°	1180.8	1178.4	1174.1	1167.4	1163.4	1156.4	1151.8	1154.5	1155.1	1154.5	1153.8
5°	1149.1	1140.3	1128.2	1116.6	1105.8	1094.1	1087.4	1084.5	1078.7	1075.4	1073.7
7.5°	1110.7	1095.6	1078.6	1058.3	1041.0	1023.0	1013.7	1009.1	997.2	990.8	985.0
10°	1082.1	1058.3	1041.3	1014.6	998.4	974.7	958.5	958.9	942.6	933.4	926.8
12.5°	1050.4	1024.3	996.0	972.0	949.4	930.4	910.9	902.9	885.7	876.9	858.9
15°	998.0	967.6	937.7	905.1	882.3	852.7	824.4	789.9	762.0	737.8	731.2
17.5°	940.7	903.1	873.0	834.9	795.7	746.0	713.2	693.2	676.4	663.7	654.1
20°	901.4	863.2	831.1	773.6	720.8	687.1	663.0	647.6	630.1	616.4	608.9
22.5°	860.1	820.2	776.5	712.4	671.2	644.2	622.6	605.0	593.1	582.4	575.6
25°	801.5	757.8	685.8	641.7	608.5	580.2	565.2	554.3	541.8	527.3	520.7
27.5°	739.6	670.1	618.4	585.6	553.8	535.4	522.0	505.8	494.6	488.1	481.2
30°	693.3	623.9	583.5	547.7	525.2	504.8	489.0	479.9	469.0	457.8	453.2
32.5°	641.7	586.2	547.6	517.7	494.9	477.5	465.0	450.2	442.4	435.5	425.9
35°	577.6	535.7	500.3	476.1	454.4	440.3	425.7	417.0	402.8	397.1	393.3
37.5°	523.3	486.9	460.6	435.0	417.9	402.3	393.4	379.4	373.3	365.3	357.3
40°	492.8	457.0	431.5	410.7	391.6	379.9	368.8	357.5	348.3	344.6	335.0
42.5°	461.5	432.4	406.9	384.1	371.3	359.0	344.8	336.6	327.0	321.0	315.0
45°	418.2	392.5	370.8	352.0	337.9	325.1	315.8	302.1	296.8	284.6	279.6
47.5°	380.3	356.3	335.7	317.9	304.0	295.6	282.3	271.5	262.9	255.4	249.1
50°	353.4	333.4	313.4	297.6	285.1	273.0	259.3	253.9	240.5	236.8	233.1
52.5°	328.7	309.7	291.4	275.9	263.4	251.7	239.6	232.5	223.6	219.8	217.1
55°	294.2	275.9	258.4	244.7	232.2	220.1	212.6	203.9	199.7	196.8	193.6
57.5°	259.6	243.1	229.8	215.8	203.3	193.7	185.0	179.8	175.5	171.6	167.6
60°	237.7	221.8	209.8	196.8	183.9	176.0	169.4	163.1	158.2	152.3	150.7
62.5°	214.3	200.5	189.5	176.8	165.7	158.4	152.1	146.2	140.1	131.7	129.3
65°	182.3	171.5	159.8	149.4	139.4	132.3	123.2	116.5	114.1	113.2	112.8
67.5°	153.4	143.1	133.1	122.5	113.3	106.8	102.2	101.1	99.4	98.9	97.8
70°	134.0	124.4	114.5	104.4	95.7	94.5	92.8	91.2	89.0	88.2	87.4
72.5°	116.7	106.8	96.8	88.8	85.0	83.5	81.9	80.1	78.8	77.9	77.4
75°	89.4	80.3	73.7	70.8	68.6	67.4	64.9	63.7	62.9	61.6	61.1
77.5°	64.4	59.3	56.2	54.4	52.2	50.9	49.4	48.2	47.3	47.0	46.4
80°	49.1	46.6	44.5	42.1	41.2	39.5	39.1	37.9	38.3	37.0	37.0
82.5°	38.2	35.0	33.2	32.0	31.2	29.9	29.4	28.9	28.9	28.0	28.0
85°	19.6	18.8	17.9	17.0	17.0	15.8	16.2	15.8	15.8	15.0	14.6
87.5°	7.8	8.0	7.9	8.6	9.1	9.5	9.4	9.0	9.0	8.9	8.6
90°	7.4	9.9	13.0	16.1	19.2	22.3	22.0	21.8	21.4	21.2	21.1
92.5°	16.3	17.3	18.0	18.8	19.6	20.3	20.3	20.4	20.5	20.5	20.5
95°	38.8	39.6	39.9	40.2	40.5	40.8	40.8	40.8	40.8	40.8	40.7
97.5°	65.6	66.4	66.9	67.5	68.0	68.6	68.6	68.6	68.6	68.6	68.6
100°	85.4	86.3	86.7	87.1	87.5	88.0	88.0	88.0	88.0	88.0	87.9
102.5°	106.0	106.7	107.2	107.8	108.3	108.8	108.9	109.1	109.2	109.3	109.3
105°	138.7	139.1	139.3	139.7	139.9	140.2	140.5	140.8	141.0	141.4	141.5
107.5°	174.4	174.7	174.7	174.7	174.7	174.7	174.9	175.0	175.0	175.2	175.0
110°	197.8	198.2	198.2	198.2	198.2	198.2	198.2	198.2	198.2	198.2	198.0



TEST NUMBER: P331688-930

CATALOG NUMBER: SA2XXRDIP-C675D725U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	222.3	222.6	222.5	222.4	222.3	222.2	221.8	221.4	221.1	220.8	220.5
115°	258.3	258.6	258.3	258.0	257.7	257.5	257.3	257.1	257.1	256.9	256.6
117.5°	295.4	295.5	294.7	294.0	293.2	292.4	292.0	291.7	291.4	291.0	290.7
120°	319.4	319.4	318.2	317.1	315.9	314.8	314.8	314.8	314.8	314.8	314.6
122.5°	342.2	342.4	341.7	340.9	340.1	339.2	338.9	338.6	338.3	337.9	337.6
125°	376.0	376.4	376.0	375.5	375.1	374.7	374.3	373.9	373.4	373.0	372.8
127.5°	410.6	411.2	410.7	410.2	409.6	409.1	408.6	408.1	407.6	407.1	406.6
130°	432.4	433.2	432.9	432.6	432.4	432.1	431.8	431.5	431.2	431.0	430.5
132.5°	454.5	455.3	455.3	455.4	455.4	455.5	454.9	454.3	453.6	453.1	452.5
135°	486.1	487.0	487.3	487.5	487.9	488.1	488.0	487.9	487.7	487.5	487.3
137.5°	518.0	518.8	519.2	519.5	519.9	520.2	520.2	520.1	519.9	519.8	519.5
140°	537.9	538.8	539.6	540.3	541.0	541.7	541.7	541.7	541.7	541.7	541.4
142.5°	558.2	559.1	559.6	560.1	560.6	561.1	561.2	561.3	561.4	561.5	561.3
145°	586.4	587.3	588.2	589.1	589.9	590.8	590.9	591.0	591.2	591.3	591.1
147.5°	613.3	614.2	614.8	615.4	616.0	616.5	616.8	617.1	617.4	617.8	617.7
150°	629.8	630.6	631.1	631.7	632.3	632.8	633.2	633.7	634.1	634.5	634.5
152.5°	645.6	646.4	647.1	647.8	648.4	649.1	649.6	650.2	650.8	651.3	651.3
155°	667.6	668.1	668.5	669.0	669.4	669.8	670.5	671.2	671.9	672.6	672.8
157.5°	687.4	687.6	687.9	688.1	688.4	688.6	689.6	690.6	691.5	692.5	692.6
160°	699.6	699.8	699.9	700.1	700.3	700.3	701.2	702.1	703.0	703.8	703.9
162.5°	709.9	710.0	710.1	710.3	710.5	710.5	711.5	712.5	713.5	714.4	714.5
165°	724.0	723.9	723.9	723.9	723.9	723.9	725.0	725.9	726.9	727.9	728.1
167.5°	735.4	735.2	735.2	735.1	735.1	735.0	736.1	737.0	738.0	739.0	739.2
170°	742.0	741.7	741.6	741.4	741.3	741.1	742.2	743.1	744.1	745.1	745.2
172.5°	746.6	746.3	746.2	746.0	745.9	745.8	746.7	747.7	748.7	749.7	749.7
175°	752.2	751.9	751.5	751.3	751.0	750.7	751.7	752.7	753.7	754.6	754.7
177.5°	754.8	754.6	754.3	754.1	753.8	753.7	754.3	755.0	755.7	756.4	756.4
180°	755.1	755.1	755.1	755.1	755.1	755.1	755.1	755.1	755.1	755.1	755.1



TEST NUMBER: P331688-930
 CATALOG NUMBER: SA2XXRDIP-C675D725U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8
2.5°	1150.1	1150.8	1149.8	1150.5	1149.8	1150.8	1150.1	1153.8	1154.5	1155.1	1154.5
5°	1071.6	1066.7	1065.8	1064.5	1065.8	1066.7	1071.6	1073.7	1075.4	1078.7	1084.5
7.5°	978.0	977.1	975.1	972.2	975.1	977.1	978.0	985.0	990.8	997.2	1009.1
10°	917.6	915.6	915.2	912.2	915.2	915.6	917.6	926.8	933.4	942.6	958.9
12.5°	847.1	833.6	832.3	825.0	832.3	833.6	847.1	858.9	876.9	885.7	902.9
15°	721.2	718.8	710.4	705.0	710.4	718.8	721.2	731.2	737.8	762.0	789.9
17.5°	649.3	641.2	638.5	637.4	638.5	641.2	649.3	654.1	663.7	676.4	693.2
20°	603.0	595.6	594.3	593.5	594.3	595.6	603.0	608.9	616.4	630.1	647.6
22.5°	571.0	563.2	560.0	557.5	560.0	563.2	571.0	575.6	582.4	593.1	605.0
25°	516.5	513.6	511.9	511.0	511.9	513.6	516.5	520.7	527.3	541.8	554.3
27.5°	473.8	467.3	466.1	464.0	466.1	467.3	473.8	481.2	488.1	494.6	505.8
30°	449.5	447.4	444.5	442.0	444.5	447.4	449.5	453.2	457.8	469.0	479.9
32.5°	420.9	419.1	416.5	415.3	416.5	419.1	420.9	425.9	435.5	442.4	450.2
35°	389.1	383.3	380.8	377.1	380.8	383.3	389.1	393.3	397.1	402.8	417.0
37.5°	355.6	352.5	349.0	350.3	349.0	352.5	355.6	357.3	365.3	373.3	379.4
40°	329.6	327.5	326.7	326.3	326.7	327.5	329.6	335.0	344.6	348.3	357.5
42.5°	309.0	303.2	301.1	301.0	301.1	303.2	309.0	315.0	321.0	327.0	336.6
45°	277.6	272.1	268.4	268.9	268.4	272.1	277.6	279.6	284.6	296.8	302.1
47.5°	245.5	245.3	243.0	243.7	243.0	245.3	245.5	249.1	255.4	262.9	271.5
50°	230.2	227.6	226.0	226.4	226.0	227.6	230.2	233.1	236.8	240.5	253.9
52.5°	215.5	213.4	212.0	213.8	212.0	213.4	215.5	217.1	219.8	223.6	232.5
55°	191.4	188.9	188.5	188.1	188.5	188.9	191.4	193.6	196.8	199.7	203.9
57.5°	164.5	162.9	160.4	159.3	160.4	162.9	164.5	167.6	171.6	175.5	179.8
60°	145.2	141.9	137.8	137.3	137.8	141.9	145.2	150.7	152.3	158.2	163.1
62.5°	127.6	126.9	126.1	126.0	126.1	126.9	127.6	129.3	131.7	140.1	146.2
65°	111.9	111.5	111.9	112.3	111.9	111.5	111.9	112.8	113.2	114.1	116.5
67.5°	97.6	96.8	96.0	96.4	96.0	96.8	97.6	97.8	98.9	99.4	101.1
70°	86.6	86.2	85.8	85.8	85.8	86.2	86.6	87.4	88.2	89.0	91.2
72.5°	75.9	75.8	75.4	75.1	75.4	75.8	75.9	77.4	77.9	78.8	80.1
75°	60.7	59.9	59.9	59.9	59.9	59.9	60.7	61.1	61.6	62.9	63.7
77.5°	46.3	45.9	45.4	45.1	45.4	45.9	46.3	46.4	47.0	47.3	48.2
80°	36.6	36.2	35.8	35.8	35.8	36.2	36.6	37.0	37.0	38.3	37.9
82.5°	28.0	27.6	27.5	27.1	27.5	27.6	28.0	28.0	28.0	28.9	28.9
85°	15.0	15.4	15.0	15.8	15.0	15.4	15.0	14.6	15.0	15.8	15.8
87.5°	8.6	8.2	8.6	8.3	8.6	8.2	8.6	8.6	8.9	9.0	9.0
90°	21.3	21.4	21.5	21.7	21.5	21.4	21.3	21.1	21.2	21.4	21.8
92.5°	20.5	20.6	20.6	20.6	20.6	20.6	20.5	20.5	20.5	20.5	20.4
95°	40.4	40.1	39.8	39.5	39.8	40.1	40.4	40.7	40.8	40.8	40.8
97.5°	68.6	68.5	68.5	68.4	68.5	68.5	68.6	68.6	68.6	68.6	68.6
100°	87.7	87.6	87.5	87.3	87.5	87.6	87.7	87.9	88.0	88.0	88.0
102.5°	109.2	109.0	108.8	108.7	108.8	109.0	109.2	109.3	109.3	109.2	109.1
105°	141.5	141.5	141.5	141.5	141.5	141.5	141.5	141.5	141.4	141.0	140.8
107.5°	174.3	173.7	173.0	172.4	173.0	173.7	174.3	175.0	175.2	175.0	175.0
110°	197.5	197.1	196.7	196.2	196.7	197.1	197.5	198.0	198.2	198.2	198.2



TEST NUMBER: P331688-930

CATALOG NUMBER: SA2XXRDIP-C675D725U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	220.1	219.8	219.6	219.2	219.6	219.8	220.1	220.5	220.8	221.1	221.4
115°	256.2	255.8	255.4	254.9	255.4	255.8	256.2	256.6	256.9	257.1	257.1
117.5°	290.2	289.8	289.3	288.9	289.3	289.8	290.2	290.7	291.0	291.4	291.7
120°	314.1	313.7	313.3	312.9	313.3	313.7	314.1	314.6	314.8	314.8	314.8
122.5°	337.3	337.0	336.6	336.4	336.6	337.0	337.3	337.6	337.9	338.3	338.6
125°	372.6	372.4	372.3	372.2	372.3	372.4	372.6	372.8	373.0	373.4	373.9
127.5°	406.2	405.7	405.3	404.8	405.3	405.7	406.2	406.6	407.1	407.6	408.1
130°	429.9	429.4	428.8	428.3	428.8	429.4	429.9	430.5	431.0	431.2	431.5
132.5°	452.0	451.6	451.1	450.7	451.1	451.6	452.0	452.5	453.1	453.6	454.3
135°	486.9	486.5	486.0	485.6	486.0	486.5	486.9	487.3	487.5	487.7	487.9
137.5°	518.9	518.4	517.8	517.2	517.8	518.4	518.9	519.5	519.8	519.9	520.1
140°	540.9	540.3	539.7	539.2	539.7	540.3	540.9	541.4	541.7	541.7	541.7
142.5°	560.7	560.1	559.6	559.1	559.6	560.1	560.7	561.3	561.5	561.4	561.3
145°	590.5	590.0	589.4	588.8	589.4	590.0	590.5	591.1	591.3	591.2	591.0
147.5°	617.1	616.5	616.0	615.5	616.0	616.5	617.1	617.7	617.8	617.4	617.1
150°	634.1	633.7	633.2	632.8	633.2	633.7	634.1	634.5	634.5	634.1	633.7
152.5°	650.8	650.2	649.6	649.1	649.6	650.2	650.8	651.3	651.3	650.8	650.2
155°	672.3	671.9	671.5	671.1	671.5	671.9	672.3	672.8	672.6	671.9	671.2
157.5°	691.9	691.3	690.6	689.9	690.6	691.3	691.9	692.6	692.5	691.5	690.6
160°	703.4	702.8	702.2	701.6	702.2	702.8	703.4	703.9	703.8	703.0	702.1
162.5°	713.9	713.2	712.5	711.8	712.5	713.2	713.9	714.5	714.4	713.5	712.5
165°	727.3	726.6	725.9	725.2	725.9	726.6	727.3	728.1	727.9	726.9	725.9
167.5°	738.4	737.7	736.9	736.2	736.9	737.7	738.4	739.2	739.0	738.0	737.0
170°	744.4	743.5	742.7	741.8	742.7	743.5	744.4	745.2	745.1	744.1	743.1
172.5°	748.9	748.0	747.2	746.4	747.2	748.0	748.9	749.7	749.7	748.7	747.7
175°	753.9	753.0	752.2	751.4	752.2	753.0	753.9	754.7	754.6	753.7	752.7
177.5°	755.7	755.0	754.3	753.7	754.3	755.0	755.7	756.4	756.4	755.7	755.0
180°	755.1	755.1	755.1	755.1	755.1	755.1	755.1	755.1	755.1	755.1	755.1



TEST NUMBER: P331688-930

CATALOG NUMBER: SA2XXRDIP-C675D725U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8
2.5°	1151.8	1156.4	1163.4	1167.4	1174.1	1178.4	1180.8	1185.1	1187.4	1195.7	1204.4
5°	1087.4	1094.1	1105.8	1116.6	1128.2	1140.3	1149.1	1159.0	1168.2	1184.0	1200.7
7.5°	1013.7	1023.0	1041.0	1058.3	1078.6	1095.6	1110.7	1127.7	1143.0	1165.6	1189.3
10°	958.5	974.7	998.4	1014.6	1041.3	1058.3	1082.1	1100.7	1122.0	1151.9	1178.6
12.5°	910.9	930.4	949.4	972.0	996.0	1024.3	1050.4	1074.5	1099.7	1130.7	1162.0
15°	824.4	852.7	882.3	905.1	937.7	967.6	998.0	1030.5	1061.3	1098.3	1139.1
17.5°	713.2	746.0	795.7	834.9	873.0	903.1	940.7	980.0	1016.3	1060.9	1106.4
20°	663.0	687.1	720.8	773.6	831.1	863.2	901.4	944.7	986.3	1035.0	1083.7
22.5°	622.6	644.2	671.2	712.4	776.5	820.2	860.1	904.1	952.4	1002.1	1056.1
25°	565.2	580.2	608.5	641.7	685.8	757.8	801.5	845.6	898.1	951.4	1012.9
27.5°	522.0	535.4	553.8	585.6	618.4	670.1	739.6	787.7	840.0	899.9	963.8
30°	489.0	504.8	525.2	547.7	583.5	623.9	693.3	749.1	800.7	862.3	930.6
32.5°	465.0	477.5	494.9	517.7	547.6	586.2	641.7	709.5	759.8	824.7	895.9
35°	425.7	440.3	454.4	476.1	500.3	535.7	577.6	650.0	700.0	764.1	835.7
37.5°	393.4	402.3	417.9	435.0	460.6	486.9	523.3	588.3	642.3	705.2	778.5
40°	368.8	379.9	391.6	410.7	431.5	457.0	492.8	541.0	603.0	664.6	736.2
42.5°	344.8	359.0	371.3	384.1	406.9	432.4	461.5	502.4	565.7	624.0	693.6
45°	315.8	325.1	337.9	352.0	370.8	392.5	418.2	454.0	514.8	565.2	630.5
47.5°	282.3	295.6	304.0	317.9	335.7	356.3	380.3	411.2	460.5	507.7	568.3
50°	259.3	273.0	285.1	297.6	313.4	333.4	353.4	383.3	422.8	472.4	529.0
52.5°	239.6	251.7	263.4	275.9	291.4	309.7	328.7	355.0	388.9	434.4	489.3
55°	212.6	220.1	232.2	244.7	258.4	275.9	294.2	316.3	345.4	383.7	428.3
57.5°	185.0	193.7	203.3	215.8	229.8	243.1	259.6	279.6	302.6	337.2	375.3
60°	169.4	176.0	183.9	196.8	209.8	221.8	237.7	254.3	275.9	305.9	338.3
62.5°	152.1	158.4	165.7	176.8	189.5	200.5	214.3	232.0	250.3	277.6	306.1
65°	123.2	132.3	139.4	149.4	159.8	171.5	182.3	196.4	212.6	234.3	259.7
67.5°	102.2	106.8	113.3	122.5	133.1	143.1	153.4	164.4	178.5	195.2	215.3
70°	92.8	94.5	95.7	104.4	114.5	124.4	134.0	144.4	156.5	170.2	187.7
72.5°	81.9	83.5	85.0	88.8	96.8	106.8	116.7	124.4	135.8	147.2	161.4
75°	64.9	67.4	68.6	70.8	73.7	80.3	89.4	96.9	103.6	112.3	123.6
77.5°	49.4	50.9	52.2	54.4	56.2	59.3	64.4	71.2	77.4	82.5	90.3
80°	39.1	39.5	41.2	42.1	44.5	46.6	49.1	54.5	60.7	62.9	68.2
82.5°	29.4	29.9	31.2	32.0	33.2	35.0	38.2	39.5	44.4	47.2	50.6
85°	16.2	15.8	17.0	17.0	17.9	18.8	19.6	21.6	22.9	26.3	27.1
87.5°	9.4	9.5	9.1	8.6	7.9	8.0	7.8	7.8	8.2	8.8	9.8
90°	22.0	22.3	19.2	16.1	13.0	9.9	7.4	5.7	4.1	2.4	0.7
92.5°	20.3	20.3	19.6	18.8	18.0	17.3	16.3	15.1	13.9	12.6	11.3
95°	40.8	40.8	40.5	40.2	39.9	39.6	38.8	37.4	36.0	34.6	33.1
97.5°	68.6	68.6	68.0	67.5	66.9	66.4	65.6	64.2	63.0	61.8	60.6
100°	88.0	88.0	87.5	87.1	86.7	86.3	85.4	84.3	83.2	82.1	81.0
102.5°	108.9	108.8	108.3	107.8	107.2	106.7	106.0	105.1	104.2	103.2	102.3
105°	140.5	140.2	139.9	139.7	139.3	139.1	138.7	138.3	137.9	137.5	137.1
107.5°	174.9	174.7	174.7	174.7	174.7	174.7	174.4	173.8	173.2	172.6	171.9
110°	198.2	198.2	198.2	198.2	198.2	198.2	197.8	196.9	196.1	195.2	194.4



TEST NUMBER: P331688-930

CATALOG NUMBER: SA2XXRDIP-C675D725U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	221.8	222.2	222.3	222.4	222.5	222.6	222.3	221.4	220.5	219.7	218.8
115°	257.3	257.5	257.7	258.0	258.3	258.6	258.3	257.5	256.6	255.8	254.9
117.5°	292.0	292.4	293.2	294.0	294.7	295.5	295.4	294.2	293.1	292.0	290.8
120°	314.8	314.8	315.9	317.1	318.2	319.4	319.4	318.2	317.1	315.9	314.8
122.5°	338.9	339.2	340.1	340.9	341.7	342.4	342.2	340.8	339.5	338.1	336.7
125°	374.3	374.7	375.1	375.5	376.0	376.4	376.0	374.7	373.4	372.2	370.9
127.5°	408.6	409.1	409.6	410.2	410.7	411.2	410.6	409.0	407.4	405.8	404.1
130°	431.8	432.1	432.4	432.6	432.9	433.2	432.4	430.6	428.8	426.9	425.1
132.5°	454.9	455.5	455.4	455.4	455.3	455.3	454.5	453.0	451.5	450.0	448.5
135°	488.0	488.1	487.9	487.5	487.3	487.0	486.1	484.5	483.0	481.4	479.9
137.5°	520.2	520.2	519.9	519.5	519.2	518.8	518.0	516.7	515.4	514.1	512.9
140°	541.7	541.7	541.0	540.3	539.6	538.8	537.9	536.5	535.3	534.0	532.8
142.5°	561.2	561.1	560.6	560.1	559.6	559.1	558.2	557.0	555.7	554.4	553.2
145°	590.9	590.8	589.9	589.1	588.2	587.3	586.4	585.5	584.5	583.4	582.4
147.5°	616.8	616.5	616.0	615.4	614.8	614.2	613.3	612.1	611.0	609.8	608.6
150°	633.2	632.8	632.3	631.7	631.1	630.6	629.8	629.0	628.1	627.3	626.5
152.5°	649.6	649.1	648.4	647.8	647.1	646.4	645.6	644.8	643.9	643.1	642.2
155°	670.5	669.8	669.4	669.0	668.5	668.1	667.6	667.2	666.8	666.3	665.9
157.5°	689.6	688.6	688.4	688.1	687.9	687.6	687.4	687.1	686.8	686.5	686.2
160°	701.2	700.3	700.3	700.1	699.9	699.8	699.6	699.3	699.0	698.7	698.5
162.5°	711.5	710.5	710.5	710.3	710.1	710.0	709.9	709.8	709.8	709.7	709.6
165°	725.0	723.9	723.9	723.9	723.9	723.9	724.0	724.1	724.3	724.5	724.6
167.5°	736.1	735.0	735.1	735.1	735.2	735.2	735.4	735.8	736.2	736.6	737.0
170°	742.2	741.1	741.3	741.4	741.6	741.7	742.0	742.4	742.8	743.3	743.7
172.5°	746.7	745.8	745.9	746.0	746.2	746.3	746.6	747.0	747.5	747.9	748.3
175°	751.7	750.7	751.0	751.3	751.5	751.9	752.2	752.6	753.0	753.5	753.9
177.5°	754.3	753.7	753.8	754.1	754.3	754.6	754.8	755.1	755.5	755.9	756.2
180°	755.1	755.1	755.1	755.1	755.1	755.1	755.1	755.1	755.1	755.1	755.1



TEST NUMBER: P331688-930

CATALOG NUMBER: SA2XXRDIP-C675D725U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8
2.5°	1204.8	1205.7	1212.4	1215.4	1221.4	1223.7	1226.4	1225.7	1225.7	1227.0	1236.4
5°	1207.3	1215.6	1228.1	1240.2	1251.8	1261.8	1268.5	1275.1	1277.7	1289.7	1300.6
7.5°	1203.0	1218.3	1238.9	1257.4	1279.4	1296.7	1310.9	1323.9	1332.7	1350.2	1368.2
10°	1197.3	1219.0	1242.3	1266.0	1296.4	1319.2	1342.6	1360.5	1366.3	1392.5	1407.5
12.5°	1186.0	1215.0	1244.6	1275.3	1305.0	1336.6	1362.2	1380.1	1400.6	1424.2	1451.8
15°	1169.1	1202.3	1241.0	1280.6	1323.0	1361.3	1388.8	1420.0	1442.4	1468.3	1492.4
17.5°	1144.6	1187.5	1236.7	1282.5	1331.5	1372.7	1410.5	1440.5	1456.3	1471.0	1474.6
20°	1125.4	1171.5	1229.4	1283.4	1332.6	1380.1	1417.5	1442.4	1446.6	1447.0	1425.0
22.5°	1104.3	1156.5	1217.1	1272.5	1331.2	1384.1	1413.2	1423.8	1407.3	1379.1	1336.4
25°	1065.8	1126.2	1196.5	1259.7	1323.9	1373.8	1383.8	1365.1	1307.2	1246.4	1169.5
27.5°	1024.0	1091.8	1167.3	1237.6	1305.9	1336.8	1315.2	1247.7	1143.5	1053.0	943.2
30°	993.4	1069.6	1143.6	1222.3	1285.6	1298.9	1249.4	1149.9	1028.3	891.9	782.4
32.5°	958.5	1038.3	1119.7	1201.0	1253.9	1241.0	1159.1	1036.7	894.2	760.0	656.6
35°	908.5	990.9	1078.7	1160.3	1194.0	1137.8	1015.5	856.1	710.4	585.1	514.0
37.5°	850.8	940.5	1031.8	1106.8	1104.3	1010.7	844.1	679.6	557.1	483.0	432.4
40°	809.8	900.6	999.2	1062.5	1035.4	913.5	732.9	577.6	488.2	429.1	392.0
42.5°	770.6	861.6	959.6	1009.9	962.9	812.9	633.0	511.4	437.6	391.4	361.4
45°	703.8	799.9	890.6	918.5	834.5	669.2	511.9	423.6	374.5	340.5	319.6
47.5°	638.4	733.0	815.8	816.3	702.5	542.7	431.8	366.6	324.7	298.3	283.2
50°	598.4	688.4	757.8	747.1	618.0	482.7	386.2	330.0	295.1	274.7	258.9
52.5°	553.5	640.7	700.9	670.1	546.4	424.9	345.3	298.1	269.1	251.4	237.3
55°	488.2	565.6	608.1	561.4	445.7	353.4	291.7	254.7	233.1	218.1	206.0
57.5°	424.0	487.9	514.5	460.3	367.1	293.0	246.8	219.0	197.5	186.8	180.5
60°	383.7	438.2	457.0	397.1	319.2	256.3	218.5	192.7	176.8	169.8	163.5
62.5°	344.1	388.7	396.4	341.4	278.3	224.4	191.8	170.1	159.6	152.8	146.9
65°	285.5	317.6	313.8	269.7	220.1	178.1	154.4	141.0	133.1	123.6	113.2
67.5°	235.1	254.6	242.8	209.8	168.0	138.4	122.9	112.8	103.1	94.0	91.6
70°	203.1	214.3	201.9	171.5	137.8	116.1	103.6	91.6	85.8	83.6	79.9
72.5°	172.4	176.3	162.9	136.8	112.1	96.1	84.0	77.2	74.1	72.3	70.0
75°	129.5	126.5	114.9	94.5	77.9	67.0	63.3	60.7	58.7	57.0	55.8
77.5°	90.9	86.7	76.2	62.9	54.2	49.0	46.8	45.4	44.4	43.6	42.4
80°	68.2	65.3	55.0	44.9	41.2	38.7	37.4	35.8	35.8	35.0	33.7
82.5°	50.0	46.7	37.6	32.9	30.9	29.4	28.5	27.5	27.1	27.3	26.4
85°	26.3	21.2	18.8	17.9	16.6	15.8	16.2	15.4	15.4	15.4	15.0
87.5°	8.5	7.1	7.2	7.2	8.0	8.6	8.9	9.5	10.4	10.0	10.4
90°	2.4	4.1	5.7	7.4	9.9	13.0	16.1	19.2	22.3	22.0	21.8
92.5°	12.6	13.9	15.1	16.3	17.3	18.0	18.8	19.6	20.3	20.3	20.4
95°	34.6	36.0	37.4	38.8	39.6	39.9	40.2	40.5	40.8	40.8	40.8
97.5°	61.8	63.0	64.2	65.6	66.4	66.9	67.5	68.0	68.6	68.6	68.6
100°	82.1	83.2	84.3	85.4	86.3	86.7	87.1	87.5	88.0	88.0	88.0
102.5°	103.2	104.2	105.1	106.0	106.7	107.2	107.8	108.3	108.8	108.9	109.1
105°	137.5	137.9	138.3	138.7	139.1	139.3	139.7	139.9	140.2	140.5	140.8
107.5°	172.6	173.2	173.8	174.4	174.7	174.7	174.7	174.7	174.7	174.9	175.0
110°	195.2	196.1	196.9	197.8	198.2	198.2	198.2	198.2	198.2	198.2	198.2



TEST NUMBER: P331688-930

CATALOG NUMBER: SA2XXRDIP-C675D725U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	219.7	220.5	221.4	222.3	222.6	222.5	222.4	222.3	222.2	221.8	221.4
115°	255.8	256.6	257.5	258.3	258.6	258.3	258.0	257.7	257.5	257.3	257.1
117.5°	292.0	293.1	294.2	295.4	295.5	294.7	294.0	293.2	292.4	292.0	291.7
120°	315.9	317.1	318.2	319.4	319.4	318.2	317.1	315.9	314.8	314.8	314.8
122.5°	338.1	339.5	340.8	342.2	342.4	341.7	340.9	340.1	339.2	338.9	338.6
125°	372.2	373.4	374.7	376.0	376.4	376.0	375.5	375.1	374.7	374.3	373.9
127.5°	405.8	407.4	409.0	410.6	411.2	410.7	410.2	409.6	409.1	408.6	408.1
130°	426.9	428.8	430.6	432.4	433.2	432.9	432.6	432.4	432.1	431.8	431.5
132.5°	450.0	451.5	453.0	454.5	455.3	455.3	455.4	455.4	455.5	454.9	454.3
135°	481.4	483.0	484.5	486.1	487.0	487.3	487.5	487.9	488.1	488.0	487.9
137.5°	514.1	515.4	516.7	518.0	518.8	519.2	519.5	519.9	520.2	520.2	520.1
140°	534.0	535.3	536.5	537.9	538.8	539.6	540.3	541.0	541.7	541.7	541.7
142.5°	554.4	555.7	557.0	558.2	559.1	559.6	560.1	560.6	561.1	561.2	561.3
145°	583.4	584.5	585.5	586.4	587.3	588.2	589.1	589.9	590.8	590.9	591.0
147.5°	609.8	611.0	612.1	613.3	614.2	614.8	615.4	616.0	616.5	616.8	617.1
150°	627.3	628.1	629.0	629.8	630.6	631.1	631.7	632.3	632.8	633.2	633.7
152.5°	643.1	643.9	644.8	645.6	646.4	647.1	647.8	648.4	649.1	649.6	650.2
155°	666.3	666.8	667.2	667.6	668.1	668.5	669.0	669.4	669.8	670.5	671.2
157.5°	686.5	686.8	687.1	687.4	687.6	687.9	688.1	688.4	688.6	689.6	690.6
160°	698.7	699.0	699.3	699.6	699.8	699.9	700.1	700.3	700.3	701.2	702.1
162.5°	709.7	709.8	709.8	709.9	710.0	710.1	710.3	710.5	710.5	711.5	712.5
165°	724.5	724.3	724.1	724.0	723.9	723.9	723.9	723.9	723.9	725.0	725.9
167.5°	736.6	736.2	735.8	735.4	735.2	735.2	735.1	735.1	735.0	736.1	737.0
170°	743.3	742.8	742.4	742.0	741.7	741.6	741.4	741.3	741.1	742.2	743.1
172.5°	747.9	747.5	747.0	746.6	746.3	746.2	746.0	745.9	745.8	746.7	747.7
175°	753.5	753.0	752.6	752.2	751.9	751.5	751.3	751.0	750.7	751.7	752.7
177.5°	755.9	755.5	755.1	754.8	754.6	754.3	754.1	753.8	753.7	754.3	755.0
180°	755.1	755.1	755.1	755.1	755.1	755.1	755.1	755.1	755.1	755.1	755.1



TEST NUMBER: P331688-930

CATALOG NUMBER: SA2XXRDIP-C675D725U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8
2.5°	1239.7	1244.0	1246.0	1246.0	1248.4	1247.3	1246.3
5°	1310.9	1318.8	1320.5	1328.0	1333.4	1331.7	1332.6
7.5°	1381.8	1394.5	1407.0	1412.8	1413.7	1417.1	1418.3
10°	1425.4	1435.8	1455.4	1452.5	1467.0	1475.4	1461.6
12.5°	1467.4	1481.4	1494.9	1498.7	1507.0	1509.6	1504.2
15°	1505.3	1512.8	1513.6	1511.6	1514.0	1512.0	1504.1
17.5°	1469.8	1457.7	1433.1	1421.4	1412.2	1398.5	1393.0
20°	1411.2	1375.4	1333.8	1317.2	1297.6	1259.3	1268.5
22.5°	1284.7	1243.9	1202.3	1153.7	1130.5	1094.2	1092.0
25°	1087.9	1017.6	940.1	886.1	854.4	818.2	802.4
27.5°	845.8	757.2	693.8	661.7	632.5	603.8	602.6
30°	686.6	620.1	571.0	543.6	525.6	513.6	516.1
32.5°	578.8	533.2	500.1	477.3	464.1	454.9	454.8
35°	473.2	442.0	420.8	411.2	401.6	394.9	395.3
37.5°	405.0	386.2	374.4	363.8	357.8	354.6	352.8
40°	370.0	354.6	345.4	339.2	334.2	329.6	328.8
42.5°	342.3	329.6	320.4	315.5	310.9	307.6	306.8
45°	303.8	293.4	285.1	279.6	277.6	274.7	274.7
47.5°	270.3	260.0	253.6	250.1	246.5	244.6	244.5
50°	247.6	239.7	233.9	231.8	228.9	227.6	227.2
52.5°	227.3	221.4	217.3	215.8	214.6	213.0	213.3
55°	199.7	196.4	194.8	193.6	191.4	188.9	190.6
57.5°	176.5	173.7	169.3	165.3	163.4	161.7	162.3
60°	160.2	154.4	148.5	144.0	142.8	139.0	139.0
62.5°	139.6	131.4	124.3	121.7	120.4	118.7	118.4
65°	107.4	104.0	102.4	100.7	99.9	99.9	99.1
67.5°	88.9	87.6	85.9	85.4	84.5	84.3	84.1
70°	78.7	77.0	76.1	75.7	74.9	75.3	74.1
72.5°	68.6	67.3	67.2	66.1	65.6	65.6	64.7
75°	54.1	54.1	53.6	53.2	52.4	52.0	52.4
77.5°	41.6	41.7	40.9	40.8	40.8	40.8	40.4
80°	33.3	33.7	33.3	32.9	32.4	32.9	32.4
82.5°	26.3	25.7	25.6	25.5	25.4	25.2	25.1
85°	15.0	15.4	15.0	14.6	14.6	14.6	15.0
87.5°	9.9	9.9	9.9	9.9	9.9	9.9	9.6
90°	21.4	21.2	21.1	21.3	21.4	21.5	21.7
92.5°	20.5	20.5	20.5	20.5	20.6	20.6	20.6
95°	40.8	40.8	40.7	40.4	40.1	39.8	39.5
97.5°	68.6	68.6	68.6	68.6	68.5	68.5	68.4
100°	88.0	88.0	87.9	87.7	87.6	87.5	87.3
102.5°	109.2	109.3	109.3	109.2	109.0	108.8	108.7
105°	141.0	141.4	141.5	141.5	141.5	141.5	141.5
107.5°	175.0	175.2	175.0	174.3	173.7	173.0	172.4
110°	198.2	198.2	198.0	197.5	197.1	196.7	196.2



TEST NUMBER: P331688-930

CATALOG NUMBER: SA2XXRDIP-C675D725U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	221.1	220.8	220.5	220.1	219.8	219.6	219.2
115°	257.1	256.9	256.6	256.2	255.8	255.4	254.9
117.5°	291.4	291.0	290.7	290.2	289.8	289.3	288.9
120°	314.8	314.8	314.6	314.1	313.7	313.3	312.9
122.5°	338.3	337.9	337.6	337.3	337.0	336.6	336.4
125°	373.4	373.0	372.8	372.6	372.4	372.3	372.2
127.5°	407.6	407.1	406.6	406.2	405.7	405.3	404.8
130°	431.2	431.0	430.5	429.9	429.4	428.8	428.3
132.5°	453.6	453.1	452.5	452.0	451.6	451.1	450.7
135°	487.7	487.5	487.3	486.9	486.5	486.0	485.6
137.5°	519.9	519.8	519.5	518.9	518.4	517.8	517.2
140°	541.7	541.7	541.4	540.9	540.3	539.7	539.2
142.5°	561.4	561.5	561.3	560.7	560.1	559.6	559.1
145°	591.2	591.3	591.1	590.5	590.0	589.4	588.8
147.5°	617.4	617.8	617.7	617.1	616.5	616.0	615.5
150°	634.1	634.5	634.5	634.1	633.7	633.2	632.8
152.5°	650.8	651.3	651.3	650.8	650.2	649.6	649.1
155°	671.9	672.6	672.8	672.3	671.9	671.5	671.1
157.5°	691.5	692.5	692.6	691.9	691.3	690.6	689.9
160°	703.0	703.8	703.9	703.4	702.8	702.2	701.6
162.5°	713.5	714.4	714.5	713.9	713.2	712.5	711.8
165°	726.9	727.9	728.1	727.3	726.6	725.9	725.2
167.5°	738.0	739.0	739.2	738.4	737.7	736.9	736.2
170°	744.1	745.1	745.2	744.4	743.5	742.7	741.8
172.5°	748.7	749.7	749.7	748.9	748.0	747.2	746.4
175°	753.7	754.6	754.7	753.9	753.0	752.2	751.4
177.5°	755.7	756.4	756.4	755.7	755.0	754.3	753.7
180°	755.1	755.1	755.1	755.1	755.1	755.1	755.1

(END OF REPORT)