

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331691-930

Luminaire Tested: **SA2XXRDIP-C675D725U930-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331691-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C675D725U930-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 725 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4006.2 lumens
Efficiency: N/A
Efficacy: 87.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 45.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331691-930
CATALOG NUMBER: SA2XXRDIP-C675D725U930-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331691-930

CATALOG NUMBER: SA2XXRDIP-C675D725U930-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	54	54	54	47				47
1	98	93	90	86	90	86	83	80	72	70	68	60	58	57	48	47	46				41	
2	89	82	76	71	82	76	71	66	64	60	57	53	50	48	43	41	40				35	
3	82	73	66	60	75	67	61	56	57	52	48	47	44	41	38	36	34				30	
4	75	65	57	51	69	60	53	48	51	46	42	42	39	36	35	32	30				26	
5	69	58	50	44	63	54	47	41	46	40	36	38	34	31	31	29	26				23	
6	64	52	44	38	58	48	41	36	41	36	32	35	31	28	29	26	23				20	
7	59	47	39	34	54	44	37	32	38	32	28	32	28	25	26	23	21				18	
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19				17	
9	51	39	32	27	47	37	30	25	32	26	23	27	23	20	22	19	17				15	
10	48	36	29	24	44	34	27	23	29	24	21	25	21	18	21	18	16				14	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14849	14849	14849
5°	14906	14663	14744
10°	14791	14423	14300
15°	14621	13996	13593
20°	14387	13385	12713
25°	14145	12691	11863
30°	13811	11979	10769
35°	13484	11203	9810
40°	13156	10404	8701
45°	12771	9501	7695
50°	12376	8593	6712
55°	11972	7614	5762
60°	11502	6584	4782
65°	10968	5532	4359
70°	10334	4556	4008
75°	9551	4155	3737
80°	8433	3710	3403
85°	6632	2927	2927



TEST NUMBER: P331691-930

CATALOG NUMBER: SA2XXRDIP-C675D725U930-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	86.1	2.1
10°-20°	236.4	5.9
20°-30°	331.9	8.3
30°-40°	361.9	9.0
40°-50°	332.8	8.3
50°-60°	261.4	6.5
60°-70°	170.4	4.3
70°-80°	87.9	2.2
80°-90°	25.8	0.6
90°-100°	47.9	1.2
100°-110°	148.6	3.7
110°-120°	254.0	6.3
120°-130°	334.1	8.3
130°-140°	375.0	9.4
140°-150°	367.7	9.2
150°-160°	308.4	7.7
160°-170°	204.5	5.1
170°-180°	71.5	1.8
0°-30°	654.4	16.3
0°-40°	1016.3	25.4
0°-60°	1610.5	40.2
0°-90°	1894.6	47.3
90°-120°	450.5	11.2
90°-150°	1527.2	38.1
90°-180°	2112.0	52.7
0°-180°	4006.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	920	920	920	920	920	
5°	920	915	905	912	910	87
15°	875	864	837	822	813	246
25°	794	766	712	680	666	365
35°	684	640	568	518	498	428
45°	559	502	416	359	337	432
55°	425	359	270	222	205	380
65°	287	219	145	118	114	285
75°	153	96	67	61	60	162
85°	36	19	16	16	16	42
90°	1	9	22	21	22	3
95°	33	39	41	41	40	38
105°	137	139	140	141	142	145
115°	255	258	258	257	255	252
125°	371	376	375	373	372	331
135°	480	487	488	487	486	371
145°	582	587	591	591	589	364
155°	666	668	670	673	671	306
165°	725	724	724	728	725	204
175°	754	752	751	755	751	72
180°	755	755	755	755	755	



TEST NUMBER: P331691-930

CATALOG NUMBER: SA2XXRDIP-C675D725U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	919.7	919.7	919.7	919.7	919.7	919.7	919.7	919.7	919.7	919.7	919.7
2.5°	923.0	922.3	921.5	920.8	920.1	918.8	917.2	915.6	914.0	912.4	913.9
5°	919.7	918.8	917.9	916.9	916.0	914.4	911.9	909.5	907.1	904.7	906.4
7.5°	910.2	909.1	907.9	906.8	905.6	903.6	900.8	898.1	895.2	892.4	892.8
10°	902.2	900.9	899.6	898.3	897.0	894.5	890.8	887.1	883.5	879.7	879.2
12.5°	892.2	890.6	889.0	887.5	885.8	882.7	878.0	873.3	868.5	863.7	862.7
15°	874.7	872.7	870.7	868.6	866.6	862.4	856.1	849.9	843.6	837.3	833.8
17.5°	853.3	850.2	847.1	843.9	840.8	835.3	827.2	819.1	811.1	803.0	798.8
20°	837.3	833.6	829.9	826.2	822.5	816.0	806.7	797.5	788.3	779.0	774.4
22.5°	819.9	815.9	811.7	807.6	803.4	796.1	785.7	775.3	764.8	754.4	748.4
25°	794.0	788.1	782.2	776.2	770.4	761.2	749.1	736.9	724.6	712.4	704.8
27.5°	762.7	756.3	749.8	743.4	736.9	726.8	713.1	699.4	685.6	671.8	663.0
30°	740.8	733.7	726.7	719.7	712.7	701.7	686.9	672.1	657.3	642.5	633.1
32.5°	719.4	711.2	703.0	694.8	686.6	674.9	659.8	644.7	629.7	614.6	603.8
35°	684.1	674.7	665.3	655.8	646.5	633.6	617.3	601.0	584.7	568.4	556.8
37.5°	648.9	638.5	628.1	617.8	607.4	593.5	576.3	558.9	541.5	524.2	511.4
40°	624.2	613.1	602.0	590.9	579.8	565.3	547.4	529.5	511.5	493.6	480.5
42.5°	598.9	587.3	575.5	563.9	552.2	537.0	518.5	500.0	481.4	462.9	449.3
45°	559.3	546.9	534.5	522.1	509.7	493.8	474.4	455.0	435.5	416.1	403.0
47.5°	520.7	507.5	494.4	481.3	468.1	451.6	431.5	411.5	391.4	371.4	358.3
50°	492.7	479.6	466.4	453.3	440.2	423.5	403.1	382.8	362.4	342.1	329.3
52.5°	465.5	451.7	438.0	424.3	410.5	393.7	373.8	353.9	334.0	314.1	301.8
55°	425.3	410.9	396.5	382.0	367.6	350.4	330.4	310.5	290.5	270.5	259.4
57.5°	384.2	369.4	354.6	339.8	325.0	308.0	288.8	269.6	250.4	231.2	221.0
60°	356.2	341.4	326.6	311.9	297.0	280.1	261.1	242.0	223.0	203.9	194.4
62.5°	328.9	314.1	299.3	284.5	269.7	253.2	235.1	217.0	198.8	180.6	171.6
65°	287.1	272.1	257.1	242.2	227.2	211.4	194.8	178.1	161.4	144.8	138.5
67.5°	246.9	232.0	217.1	202.3	187.4	172.4	157.4	142.5	127.5	112.5	109.7
70°	218.9	204.5	190.0	175.6	161.2	147.6	134.9	122.1	109.3	96.5	94.7
72.5°	192.2	178.4	164.6	150.7	136.9	124.9	114.6	104.4	94.2	83.9	82.3
75°	153.1	140.2	127.3	114.3	101.3	91.7	85.4	79.2	72.9	66.6	65.3
77.5°	114.7	103.3	92.0	80.6	69.3	62.0	59.0	56.0	53.0	50.0	49.2
80°	90.7	81.3	71.8	62.5	53.0	47.4	45.5	43.6	41.8	39.9	39.2
82.5°	68.7	61.4	54.1	46.6	39.3	35.0	33.8	32.4	31.2	30.0	29.5
85°	35.8	31.9	28.0	24.1	20.2	18.0	17.4	17.0	16.4	15.8	15.8
87.5°	10.8	9.9	9.1	8.2	7.4	7.3	7.9	8.6	9.1	9.8	9.6
90°	0.7	2.4	4.1	5.7	7.4	9.9	13.0	16.1	19.2	22.3	22.0
92.5°	11.3	12.6	13.9	15.1	16.3	17.3	18.0	18.8	19.6	20.3	20.3
95°	33.1	34.6	36.0	37.4	38.8	39.6	39.9	40.2	40.5	40.8	40.8
97.5°	60.6	61.8	63.0	64.2	65.6	66.4	66.9	67.5	68.0	68.6	68.6
100°	81.0	82.1	83.2	84.3	85.4	86.3	86.7	87.1	87.5	88.0	88.0
102.5°	102.3	103.2	104.2	105.1	106.0	106.7	107.2	107.8	108.3	108.8	108.9
105°	137.1	137.5	137.9	138.3	138.7	139.1	139.3	139.7	139.9	140.2	140.5
107.5°	171.9	172.6	173.2	173.8	174.4	174.7	174.7	174.7	174.7	174.7	174.9
110°	194.4	195.2	196.1	196.9	197.8	198.2	198.2	198.2	198.2	198.2	198.2



TEST NUMBER: P331691-930

CATALOG NUMBER: SA2XXRDIP-C675D725U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	218.8	219.7	220.5	221.4	222.3	222.6	222.5	222.4	222.3	222.2	221.8
115°	254.9	255.8	256.6	257.5	258.3	258.6	258.3	258.0	257.7	257.5	257.3
117.5°	290.8	292.0	293.1	294.2	295.4	295.5	294.7	294.0	293.2	292.4	292.0
120°	314.8	315.9	317.1	318.2	319.4	319.4	318.2	317.1	315.9	314.8	314.8
122.5°	336.7	338.1	339.5	340.8	342.2	342.4	341.7	340.9	340.1	339.2	338.9
125°	370.9	372.2	373.4	374.7	376.0	376.4	376.0	375.5	375.1	374.7	374.3
127.5°	404.1	405.8	407.4	409.0	410.6	411.2	410.7	410.2	409.6	409.1	408.6
130°	425.1	426.9	428.8	430.6	432.4	433.2	432.9	432.6	432.4	432.1	431.8
132.5°	448.5	450.0	451.5	453.0	454.5	455.3	455.3	455.4	455.4	455.5	454.9
135°	479.9	481.4	483.0	484.5	486.1	487.0	487.3	487.5	487.9	488.1	488.0
137.5°	512.9	514.1	515.4	516.7	518.0	518.8	519.2	519.5	519.9	520.2	520.2
140°	532.8	534.0	535.3	536.5	537.9	538.8	539.6	540.3	541.0	541.7	541.7
142.5°	553.2	554.4	555.7	557.0	558.2	559.1	559.6	560.1	560.6	561.1	561.2
145°	582.4	583.4	584.5	585.5	586.4	587.3	588.2	589.1	589.9	590.8	590.9
147.5°	608.6	609.8	611.0	612.1	613.3	614.2	614.8	615.4	616.0	616.5	616.8
150°	626.5	627.3	628.1	629.0	629.8	630.6	631.1	631.7	632.3	632.8	633.2
152.5°	642.2	643.1	643.9	644.8	645.6	646.4	647.1	647.8	648.4	649.1	649.6
155°	665.9	666.3	666.8	667.2	667.6	668.1	668.5	669.0	669.4	669.8	670.5
157.5°	686.2	686.5	686.8	687.1	687.4	687.6	687.9	688.1	688.4	688.6	689.6
160°	698.5	698.7	699.0	699.3	699.6	699.8	699.9	700.1	700.3	700.3	701.2
162.5°	709.6	709.7	709.8	709.8	709.9	710.0	710.1	710.3	710.5	710.5	711.5
165°	724.6	724.5	724.3	724.1	724.0	723.9	723.9	723.9	723.9	723.9	725.0
167.5°	737.0	736.6	736.2	735.8	735.4	735.2	735.2	735.1	735.1	735.0	736.1
170°	743.7	743.3	742.8	742.4	742.0	741.7	741.6	741.4	741.3	741.1	742.2
172.5°	748.3	747.9	747.5	747.0	746.6	746.3	746.2	746.0	745.9	745.8	746.7
175°	753.9	753.5	753.0	752.6	752.2	751.9	751.5	751.3	751.0	750.7	751.7
177.5°	756.2	755.9	755.5	755.1	754.8	754.6	754.3	754.1	753.8	753.7	754.3
180°	755.1	755.1	755.1	755.1	755.1	755.1	755.1	755.1	755.1	755.1	755.1



TEST NUMBER: P331691-930

CATALOG NUMBER: SA2XXRDIP-C675D725U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	919.7	919.7	919.7	919.7	919.7	919.7	919.7	919.7
2.5°	915.3	916.8	918.3	918.8	918.6	918.3	918.0	917.7
5°	908.0	909.7	911.3	911.9	911.3	910.8	910.3	909.7
7.5°	893.3	893.8	894.3	894.1	893.1	892.2	891.2	890.2
10°	878.6	878.1	877.5	876.7	875.5	874.5	873.3	872.2
12.5°	861.8	860.8	859.7	858.3	856.5	854.7	852.8	850.9
15°	830.3	826.7	823.2	820.5	818.7	816.8	815.0	813.2
17.5°	794.7	790.4	786.3	782.6	779.4	776.2	773.1	769.9
20°	769.8	765.2	760.5	756.2	752.1	748.0	744.0	739.9
22.5°	742.5	736.5	730.6	726.1	723.0	720.0	717.0	714.0
25°	697.2	689.7	682.1	676.9	674.2	671.4	668.6	665.9
27.5°	654.1	645.3	636.5	629.8	625.4	621.0	616.6	612.2
30°	623.7	614.2	604.8	597.6	592.6	587.6	582.6	577.6
32.5°	593.0	582.3	571.5	563.8	559.1	554.4	549.7	545.0
35°	545.2	533.5	521.9	514.0	509.9	505.8	501.8	497.7
37.5°	498.5	485.7	472.9	464.1	459.4	454.8	450.1	445.5
40°	467.2	454.1	441.0	432.0	427.2	422.4	417.6	412.8
42.5°	435.8	422.2	408.6	399.5	394.8	390.2	385.6	380.8
45°	389.9	376.7	363.6	354.8	350.4	345.9	341.5	337.0
47.5°	345.3	332.2	319.1	310.6	306.6	302.6	298.5	294.5
50°	316.6	303.8	291.1	282.7	278.8	274.9	271.1	267.2
52.5°	289.5	277.1	264.8	256.9	253.3	249.7	246.1	242.6
55°	248.3	237.2	226.1	218.8	215.3	211.7	208.2	204.7
57.5°	210.8	200.7	190.5	183.9	181.0	178.1	175.0	172.1
60°	185.1	175.6	166.2	160.0	157.0	154.1	151.1	148.1
62.5°	162.7	153.6	144.6	139.3	137.5	135.7	134.0	132.2
65°	132.2	126.0	119.7	116.3	115.7	115.1	114.5	114.1
67.5°	106.7	103.9	101.0	99.2	98.7	98.1	97.5	96.9
70°	92.9	91.0	89.1	87.9	87.1	86.3	85.6	84.9
72.5°	80.8	79.2	77.7	76.7	76.2	75.8	75.3	74.9
75°	64.0	62.7	61.4	60.7	60.5	60.3	60.1	59.9
77.5°	48.4	47.7	47.0	46.5	46.1	45.9	45.6	45.2
80°	38.5	37.7	37.0	36.6	36.6	36.6	36.6	36.6
82.5°	29.1	28.6	28.2	28.0	28.0	28.0	28.0	28.0
85°	15.8	15.8	15.8	15.8	15.8	15.8	15.8	15.8
87.5°	9.4	9.2	9.0	8.9	8.9	9.0	9.0	9.0
90°	21.8	21.4	21.2	21.1	21.3	21.4	21.5	21.7
92.5°	20.4	20.5	20.5	20.5	20.5	20.6	20.6	20.6
95°	40.8	40.8	40.8	40.7	40.4	40.1	39.8	39.5
97.5°	68.6	68.6	68.6	68.6	68.6	68.5	68.5	68.4
100°	88.0	88.0	88.0	87.9	87.7	87.6	87.5	87.3
102.5°	109.1	109.2	109.3	109.3	109.2	109.0	108.8	108.7
105°	140.8	141.0	141.4	141.5	141.5	141.5	141.5	141.5
107.5°	175.0	175.0	175.2	175.0	174.3	173.7	173.0	172.4
110°	198.2	198.2	198.2	198.0	197.5	197.1	196.7	196.2



TEST NUMBER: P331691-930

CATALOG NUMBER: SA2XXRDIP-C675D725U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	221.4	221.1	220.8	220.5	220.1	219.8	219.6	219.2
115°	257.1	257.1	256.9	256.6	256.2	255.8	255.4	254.9
117.5°	291.7	291.4	291.0	290.7	290.2	289.8	289.3	288.9
120°	314.8	314.8	314.8	314.6	314.1	313.7	313.3	312.9
122.5°	338.6	338.3	337.9	337.6	337.3	337.0	336.6	336.4
125°	373.9	373.4	373.0	372.8	372.6	372.4	372.3	372.2
127.5°	408.1	407.6	407.1	406.6	406.2	405.7	405.3	404.8
130°	431.5	431.2	431.0	430.5	429.9	429.4	428.8	428.3
132.5°	454.3	453.6	453.1	452.5	452.0	451.6	451.1	450.7
135°	487.9	487.7	487.5	487.3	486.9	486.5	486.0	485.6
137.5°	520.1	519.9	519.8	519.5	518.9	518.4	517.8	517.2
140°	541.7	541.7	541.7	541.4	540.9	540.3	539.7	539.2
142.5°	561.3	561.4	561.5	561.3	560.7	560.1	559.6	559.1
145°	591.0	591.2	591.3	591.1	590.5	590.0	589.4	588.8
147.5°	617.1	617.4	617.8	617.7	617.1	616.5	616.0	615.5
150°	633.7	634.1	634.5	634.5	634.1	633.7	633.2	632.8
152.5°	650.2	650.8	651.3	651.3	650.8	650.2	649.6	649.1
155°	671.2	671.9	672.6	672.8	672.3	671.9	671.5	671.1
157.5°	690.6	691.5	692.5	692.6	691.9	691.3	690.6	689.9
160°	702.1	703.0	703.8	703.9	703.4	702.8	702.2	701.6
162.5°	712.5	713.5	714.4	714.5	713.9	713.2	712.5	711.8
165°	725.9	726.9	727.9	728.1	727.3	726.6	725.9	725.2
167.5°	737.0	738.0	739.0	739.2	738.4	737.7	736.9	736.2
170°	743.1	744.1	745.1	745.2	744.4	743.5	742.7	741.8
172.5°	747.7	748.7	749.7	749.7	748.9	748.0	747.2	746.4
175°	752.7	753.7	754.6	754.7	753.9	753.0	752.2	751.4
177.5°	755.0	755.7	756.4	756.4	755.7	755.0	754.3	753.7
180°	755.1	755.1	755.1	755.1	755.1	755.1	755.1	755.1

(END OF REPORT)