

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331447-927

Luminaire Tested: **SA2XXDIP-C1005D925U927-4F0-1E-UDD-A**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331447-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXDIP-C1005D925U927-4F0-1E-UDD-A  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1005 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 925 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6417.6 lumens  
Efficiency: N/A  
Efficacy: 96.1 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 66.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331447-927  
CATALOG NUMBER: SA2XXDIP-C1005D925U927-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P331447-927

CATALOG NUMBER: SA2XXDIP-C1005D925U927-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	86	86	86	72	72	72	60	60	60	54
1	99	95	91	88	92	88	85	82	76	74	72	65	63	61	54	53	52	47
2	91	84	78	73	84	78	73	68	67	63	60	57	54	52	48	46	44	40
3	83	74	67	61	77	69	63	58	60	55	51	51	48	45	43	41	38	35
4	76	66	58	52	71	62	55	50	53	48	44	46	42	39	39	36	34	30
5	70	59	51	45	65	55	48	43	48	43	38	41	37	34	35	32	30	27
6	65	53	45	40	60	50	43	38	44	38	34	38	33	30	32	29	26	24
7	60	48	40	35	56	45	38	33	40	34	30	34	30	27	30	26	24	21
8	56	44	36	31	52	41	34	30	36	31	27	32	27	24	27	24	21	19
9	52	40	33	28	49	38	31	27	33	28	24	29	25	22	25	22	19	17
10	49	37	30	25	46	35	28	24	31	26	22	27	23	20	24	20	18	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	25504	25504	25504	25504
5°	28593	25671	22749	25671
10°	32765	25460	19687	25460
15°	36247	24993	17392	24993
20°	35696	24493	15856	24493
25°	32186	23826	14883	23826
30°	26597	22760	14171	22760
35°	19385	21646	13665	21646
40°	15483	20331	13384	20331
45°	13531	18810	13001	18810
50°	12717	17337	12750	17337
55°	11724	15842	12408	15842
60°	10743	14250	11880	14250
65°	9788	12825	11366	12825
70°	8884	11434	10607	11434
75°	7879	9881	9395	9881
80°	6778	8182	7569	8182
85°	6076	6076	4502	6076



TEST NUMBER: P331447-927

CATALOG NUMBER: SA2XXDIP-C1005D925U927-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	150.4	2.3
10°-20°	437.4	6.8
20°-30°	634.7	9.9
30°-40°	669.8	10.4
40°-50°	593.0	9.2
50°-60°	473.3	7.4
60°-70°	321.7	5.0
70°-80°	164.9	2.6
80°-90°	42.2	0.7
90°-100°	33.4	0.5
100°-110°	122.3	1.9
110°-120°	326.9	5.1
120°-130°	539.7	8.4
130°-140°	574.0	8.9
140°-150°	533.5	8.3
150°-160°	428.9	6.7
160°-170°	276.4	4.3
170°-180°	95.1	1.5
0°-30°	1222.5	19.0
0°-40°	1892.3	29.5
0°-60°	2958.6	46.1
0°-90°	3487.5	54.3
90°-120°	482.6	7.5
90°-150°	2129.7	33.2
90°-180°	2930.0	45.7
0°-180°	6417.6	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1580	1580	1580	1580	1580	
5°	1764	1584	1404	1584	1764	176
15°	2168	1495	1040	1495	2168	598
25°	1807	1337	835	1337	1807	817
35°	984	1098	693	1098	984	640
45°	593	824	569	824	593	466
55°	416	563	441	563	416	373
65°	256	336	298	336	256	255
75°	126	158	151	158	126	135
85°	33	33	24	33	33	36
90°	20	1	20	1	20	10
95°	31	47	31	47	31	29
105°	55	220	55	220	55	57
115°	59	416	59	416	59	149
125°	619	588	619	588	619	535
135°	752	728	752	728	752	579
145°	857	844	857	844	857	536
155°	930	930	930	930	930	429
165°	978	980	978	980	978	276
175°	996	1002	996	1002	996	95
180°	1000	1000	1000	1000	1000	



TEST NUMBER: P331447-927

CATALOG NUMBER: SA2XXDIP-C1005D925U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6
2.5°	1652.5	1653.0	1653.9	1646.2	1645.2	1645.2	1638.4	1632.6	1625.8	1616.5	1617.6
5°	1764.2	1770.8	1773.3	1766.0	1755.1	1753.9	1743.6	1726.6	1710.8	1698.0	1688.9
7.5°	1897.5	1900.2	1894.3	1884.7	1876.5	1861.9	1842.8	1823.9	1797.6	1773.5	1755.5
10°	1998.5	2002.2	1991.9	1977.9	1966.4	1949.4	1921.4	1892.9	1858.3	1825.0	1798.2
12.5°	2075.3	2084.2	2071.0	2069.2	2049.5	2026.1	1992.8	1978.4	1929.7	1883.2	1854.6
15°	2168.5	2167.9	2169.2	2157.6	2143.0	2139.4	2104.2	2065.9	1997.3	1970.0	1922.6
17.5°	2141.6	2150.8	2155.1	2154.9	2154.6	2152.3	2141.0	2116.8	2082.4	2038.1	1983.5
20°	2077.5	2089.6	2091.4	2105.4	2113.3	2123.6	2127.9	2121.1	2099.9	2062.9	2015.5
22.5°	1978.4	1981.8	1987.5	2009.2	2026.3	2052.2	2065.7	2088.1	2080.0	2061.9	2022.4
25°	1806.7	1800.6	1821.9	1832.8	1872.2	1913.5	1943.3	1976.1	2005.3	2022.8	2011.3
27.5°	1600.5	1591.4	1623.3	1652.3	1684.3	1729.0	1775.4	1830.1	1875.7	1932.6	1952.2
30°	1426.6	1432.1	1462.4	1493.4	1542.0	1605.1	1657.3	1717.5	1782.4	1846.2	1890.5
32.5°	1239.2	1260.2	1279.4	1326.8	1369.6	1440.0	1516.5	1591.7	1672.7	1745.2	1813.8
35°	983.5	1007.7	1034.5	1069.1	1129.2	1199.0	1273.7	1375.1	1485.6	1584.5	1665.9
37.5°	827.8	823.9	839.2	864.3	912.9	969.3	1055.3	1155.4	1285.5	1401.8	1516.5
40°	734.6	732.1	743.1	766.1	803.2	844.5	919.7	1007.7	1128.5	1270.7	1407.2
42.5°	670.5	671.9	678.0	694.3	719.6	753.6	810.0	884.9	995.5	1129.3	1276.1
45°	592.6	596.8	603.5	611.3	625.9	653.9	685.4	738.9	826.2	937.9	1082.4
47.5°	536.4	536.5	543.4	550.2	558.9	574.6	600.4	633.9	695.6	786.6	910.8
50°	506.3	502.1	506.9	512.4	521.5	532.4	549.4	581.0	622.3	695.7	799.5
52.5°	469.4	469.5	473.9	475.9	484.1	495.0	510.6	532.4	569.8	627.2	712.6
55°	416.5	419.5	421.9	425.6	432.8	440.8	452.9	467.5	496.6	539.7	602.9
57.5°	366.7	367.7	370.1	377.0	381.6	388.9	400.4	413.7	432.6	464.5	512.0
60°	332.7	332.7	337.5	340.6	346.7	353.9	363.1	375.8	392.8	418.9	457.2
62.5°	301.6	301.1	303.1	308.0	312.7	319.5	328.5	339.4	355.4	378.6	410.0
65°	256.2	255.0	258.6	259.8	264.7	271.4	278.7	290.2	302.9	320.0	347.8
67.5°	212.5	214.0	215.9	218.2	220.9	227.9	232.7	240.9	251.7	265.8	284.7
70°	188.2	188.2	188.2	190.0	193.7	197.3	202.2	208.8	219.2	231.3	248.3
72.5°	161.0	163.0	164.9	163.8	168.4	170.6	176.4	180.2	190.0	197.8	212.9
75°	126.3	126.3	126.3	129.3	131.1	132.9	136.6	140.2	145.1	154.8	162.7
77.5°	94.2	94.0	94.6	95.3	97.3	99.4	100.5	103.8	108.3	112.8	119.5
80°	72.9	74.1	74.7	75.9	75.9	77.1	77.7	82.0	85.0	88.0	92.3
82.5°	56.3	56.6	56.7	57.0	57.4	58.1	59.7	61.1	62.2	64.7	68.0
85°	32.8	32.2	32.2	33.4	32.8	32.8	34.0	35.2	35.2	35.8	37.6
87.5°	16.6	16.5	16.9	16.3	16.2	16.6	16.5	15.8	16.2	16.5	16.7
90°	19.6	19.3	18.9	18.5	18.2	17.7	16.9	16.1	15.3	14.5	13.2
92.5°	19.6	19.3	19.2	18.9	18.8	18.5	18.1	17.6	17.2	16.8	16.2
95°	31.1	31.3	31.4	31.6	31.8	31.4	30.7	29.8	29.0	28.2	27.1
97.5°	41.5	41.4	41.1	41.0	40.7	40.3	39.7	39.1	38.4	37.8	35.2
100°	48.5	48.2	47.8	47.5	47.2	46.4	45.1	43.8	42.5	41.3	38.5
102.5°	52.0	51.5	51.0	50.6	50.1	49.1	47.5	45.7	44.0	42.4	65.3
105°	55.0	54.3	53.7	53.1	52.4	51.2	49.4	47.7	45.9	44.1	88.0
107.5°	56.6	55.9	55.3	54.7	54.0	54.6	56.4	58.1	60.0	61.8	114.4
110°	57.2	56.5	55.8	55.2	54.6	62.3	78.3	94.4	110.5	126.6	173.1



TEST NUMBER: P331447-927

CATALOG NUMBER: SA2XXDIP-C1005D925U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	57.8	57.2	56.7	56.2	55.7	84.8	143.4	202.1	260.7	319.3	330.8
115°	59.3	70.9	82.5	94.0	105.6	148.6	223.1	297.5	371.9	446.4	442.4
117.5°	242.2	280.3	318.3	356.3	394.3	422.4	440.5	458.4	476.4	494.4	491.7
120°	441.3	463.0	484.7	506.4	528.1	538.1	536.1	534.2	532.3	530.3	527.4
122.5°	550.7	554.9	559.1	563.4	567.6	569.1	567.9	566.8	565.6	564.5	561.3
125°	618.6	618.1	617.6	617.1	616.6	615.8	614.7	613.6	612.5	611.3	608.3
127.5°	661.4	661.3	661.2	661.2	661.0	660.2	658.5	656.9	655.2	653.6	651.3
130°	688.0	688.2	688.3	688.6	688.7	687.9	686.1	684.4	682.5	680.8	679.1
132.5°	714.1	714.2	714.4	714.5	714.7	714.1	712.6	711.1	709.6	708.0	706.2
135°	751.7	752.0	752.3	752.7	753.0	752.3	750.8	749.2	747.5	745.9	744.5
137.5°	786.0	786.6	787.1	787.7	788.2	787.7	786.1	784.5	782.9	781.4	779.7
140°	807.4	808.3	809.1	809.8	810.6	810.3	808.9	807.4	806.0	804.5	802.8
142.5°	828.2	829.1	829.9	830.7	831.5	831.2	829.9	828.5	827.3	825.9	823.9
145°	857.4	858.2	859.0	859.8	860.5	860.4	859.3	858.2	857.0	855.9	853.2
147.5°	883.0	883.6	884.3	884.9	885.7	885.6	884.7	883.9	883.0	882.3	879.6
150°	898.6	899.4	900.2	901.0	901.8	901.7	900.8	899.8	898.8	897.9	895.3
152.5°	911.9	913.0	914.0	915.0	916.2	916.2	915.2	914.3	913.3	912.4	909.9
155°	930.4	931.7	933.0	934.3	935.6	935.7	934.8	933.8	932.8	931.8	929.9
157.5°	947.4	948.6	949.8	951.1	952.4	952.4	951.3	950.2	949.2	948.1	946.7
160°	957.2	958.3	959.4	960.5	961.7	961.8	960.8	959.8	958.9	957.9	957.0
162.5°	965.3	966.7	968.0	969.5	970.8	971.0	969.9	968.8	967.7	966.6	965.7
165°	977.5	978.6	979.7	980.8	981.9	981.9	980.8	979.7	978.6	977.5	977.0
167.5°	985.1	986.6	988.0	989.4	990.9	991.1	989.9	988.8	987.7	986.6	986.1
170°	989.8	991.2	992.6	994.1	995.5	995.7	994.6	993.5	992.3	991.2	990.9
172.5°	993.2	994.7	996.1	997.5	999.0	999.2	998.1	996.9	995.8	994.7	994.3
175°	996.2	997.8	999.5	1001.1	1002.7	1002.9	1001.8	1000.7	999.6	998.4	998.1
177.5°	998.1	999.3	1000.4	1001.6	1002.7	1002.9	1002.0	1001.1	1000.2	999.3	999.2
180°	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9



TEST NUMBER: P331447-927

CATALOG NUMBER: SA2XXDIP-C1005D925U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6
2.5°	1621.0	1617.1	1614.6	1605.9	1598.1	1590.3	1587.9	1588.9	1578.2	1568.0	1563.6
5°	1684.1	1671.9	1660.4	1644.0	1624.6	1603.3	1592.4	1583.9	1562.7	1539.6	1526.2
7.5°	1740.7	1723.3	1701.1	1670.2	1642.0	1608.5	1587.3	1568.4	1537.4	1504.8	1484.9
10°	1775.1	1751.4	1722.9	1685.3	1650.7	1610.0	1581.4	1552.9	1516.5	1477.7	1453.3
12.5°	1804.7	1772.8	1744.8	1696.5	1655.5	1604.6	1570.8	1530.6	1492.2	1446.0	1422.3
15°	1875.3	1816.4	1763.0	1708.3	1658.0	1586.9	1549.3	1495.2	1444.9	1387.8	1360.5
17.5°	1929.8	1863.6	1779.5	1710.1	1651.3	1572.6	1517.3	1452.6	1393.1	1327.9	1290.7
20°	1960.9	1885.0	1794.5	1712.0	1641.6	1551.7	1491.6	1425.5	1355.7	1282.1	1242.1
22.5°	1979.3	1899.6	1810.1	1704.7	1622.2	1534.7	1459.0	1386.6	1315.8	1236.5	1194.5
25°	1985.2	1912.3	1817.7	1698.7	1597.8	1498.9	1407.9	1337.4	1251.8	1177.7	1116.4
27.5°	1956.3	1904.1	1813.0	1687.2	1569.8	1454.1	1352.6	1272.8	1182.5	1102.1	1040.5
30°	1920.8	1890.5	1801.8	1675.5	1547.4	1423.0	1311.3	1220.8	1131.0	1049.6	986.5
32.5°	1866.0	1859.4	1781.5	1659.1	1523.7	1383.7	1268.1	1176.6	1077.1	997.2	937.0
35°	1758.2	1787.2	1738.1	1622.2	1478.8	1327.7	1202.6	1098.2	995.1	918.5	862.1
37.5°	1613.7	1686.0	1673.2	1568.1	1418.4	1266.8	1128.7	1019.5	921.2	844.0	788.6
40°	1514.1	1606.4	1619.7	1526.9	1375.7	1219.6	1073.3	964.6	868.7	798.4	742.4
42.5°	1407.2	1515.0	1551.7	1477.3	1329.0	1170.1	1023.8	911.2	816.3	747.8	698.3
45°	1228.1	1370.8	1437.0	1394.5	1251.3	1088.5	937.9	823.8	737.6	673.3	635.0
47.5°	1060.7	1216.6	1305.6	1290.5	1164.7	1003.5	854.7	745.1	661.2	609.9	575.7
50°	942.2	1102.5	1209.9	1214.8	1102.5	942.8	793.4	690.2	613.1	565.2	537.3
52.5°	839.2	992.2	1109.4	1135.1	1033.0	879.6	738.6	635.9	568.0	523.9	498.9
55°	704.8	834.2	964.1	1011.4	929.5	783.8	653.2	562.8	499.0	468.7	446.8
57.5°	586.0	693.8	813.7	866.1	815.6	690.9	568.5	489.9	438.2	411.6	394.8
60°	523.3	608.3	715.2	777.7	734.0	622.9	516.0	441.3	398.9	375.2	359.4
62.5°	465.0	540.3	630.7	687.9	664.0	559.3	463.6	397.7	361.0	338.7	327.3
65°	383.7	443.1	513.0	565.8	550.0	470.5	392.2	335.7	306.6	289.0	279.9
67.5°	315.9	358.9	407.3	453.6	440.8	384.5	321.6	277.7	256.0	240.7	235.3
70°	273.2	305.9	349.1	386.1	375.8	329.6	279.9	242.2	223.4	210.6	205.2
72.5°	232.4	259.4	292.2	322.5	315.5	277.2	235.7	207.2	192.8	181.0	176.6
75°	175.5	196.1	216.1	236.1	234.3	204.6	180.3	158.4	146.9	137.8	136.0
77.5°	129.5	141.1	154.7	166.6	163.3	146.3	127.2	114.7	106.2	100.1	99.2
80°	98.9	105.6	115.3	123.8	119.6	112.3	97.1	88.0	82.0	75.9	73.4
82.5°	71.8	78.4	84.3	88.9	85.6	78.8	69.5	63.3	59.7	55.5	54.5
85°	37.6	41.3	43.7	44.9	43.7	39.5	35.2	32.8	29.8	28.0	27.3
87.5°	17.0	16.7	16.4	17.1	15.3	15.0	12.7	10.9	10.7	10.5	10.0
90°	11.9	10.6	9.3	7.8	6.0	4.3	2.5	0.7	2.5	4.3	6.0
92.5°	15.5	14.9	14.2	13.9	14.1	14.3	14.4	14.6	14.4	14.3	14.1
95°	26.0	24.9	23.7	25.8	31.1	36.4	41.7	47.1	41.7	36.4	31.1
97.5°	32.6	29.9	27.3	33.5	48.5	63.5	78.3	93.3	78.3	63.5	48.5
100°	35.8	33.0	30.3	39.9	61.9	84.0	106.0	128.1	106.0	84.0	61.9
102.5°	88.1	111.0	133.9	147.6	152.3	156.9	161.6	166.3	161.6	156.9	152.3
105°	131.9	175.8	219.7	239.2	234.4	229.6	224.7	219.9	224.7	229.6	234.4
107.5°	167.1	219.7	272.4	296.8	292.8	288.9	285.0	281.1	285.0	288.9	292.8
110°	219.5	266.0	312.4	334.0	330.7	327.3	323.9	320.5	323.9	327.3	330.7





TEST NUMBER: P331447-927

CATALOG NUMBER: SA2XXDIP-C1005D925U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	342.3	353.8	365.3	369.5	366.5	363.5	360.5	357.5	360.5	363.5	366.5
115°	438.4	434.4	430.3	426.9	424.2	421.4	418.7	416.0	418.7	421.4	424.2
117.5°	488.9	486.2	483.4	480.5	477.4	474.4	471.3	468.3	471.3	474.4	477.4
120°	524.5	521.7	518.7	516.1	513.7	511.3	508.8	506.4	508.8	511.3	513.7
122.5°	558.2	555.0	551.8	549.0	546.4	543.9	541.4	538.8	541.4	543.9	546.4
125°	605.2	602.2	599.1	596.6	594.5	592.4	590.3	588.2	590.3	592.4	594.5
127.5°	649.0	646.7	644.4	642.1	639.8	637.5	635.3	632.9	635.3	637.5	639.8
130°	677.2	675.5	673.8	671.5	669.0	666.4	663.8	661.3	663.8	666.4	669.0
132.5°	704.5	702.7	700.9	698.9	696.8	694.6	692.4	690.2	692.4	694.6	696.8
135°	743.1	741.6	740.1	738.2	735.5	733.0	730.4	727.9	730.4	733.0	735.5
137.5°	778.1	776.4	774.8	773.1	771.3	769.5	767.7	765.9	767.7	769.5	771.3
140°	801.0	799.2	797.5	795.9	794.6	793.4	792.1	790.8	792.1	793.4	794.6
142.5°	821.9	819.8	817.8	816.3	815.1	814.0	812.8	811.6	812.8	814.0	815.1
145°	850.4	847.7	844.9	843.7	843.8	844.0	844.1	844.3	844.1	844.0	843.8
147.5°	876.9	874.1	871.4	870.4	871.0	871.6	872.2	872.8	872.2	871.6	871.0
150°	892.7	890.2	887.6	886.8	888.0	889.1	890.3	891.4	890.3	889.1	888.0
152.5°	907.4	905.0	902.5	902.0	903.2	904.4	905.7	907.0	905.7	904.4	903.2
155°	928.0	926.1	924.2	923.9	925.3	926.8	928.3	929.7	928.3	926.8	925.3
157.5°	945.4	944.0	942.7	942.6	943.8	945.1	946.3	947.5	946.3	945.1	943.8
160°	956.0	955.0	954.0	954.0	955.0	956.0	957.0	957.9	957.0	956.0	955.0
162.5°	964.9	964.1	963.2	963.3	964.2	965.3	966.2	967.2	966.2	965.3	964.2
165°	976.4	976.0	975.5	975.7	976.7	977.7	978.7	979.6	978.7	977.7	976.7
167.5°	985.6	985.2	984.8	985.0	986.0	987.0	987.9	988.9	987.9	987.0	986.0
170°	990.5	990.2	989.9	990.2	991.2	992.1	993.1	994.1	993.1	992.1	991.2
172.5°	994.0	993.7	993.4	993.7	994.7	995.6	996.6	997.5	996.6	995.6	994.7
175°	997.8	997.4	997.1	997.5	998.6	999.8	1000.9	1002.0	1000.9	999.8	998.6
177.5°	999.0	998.9	998.8	999.2	1000.1	1001.0	1001.9	1002.7	1001.9	1001.0	1000.1
180°	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9



TEST NUMBER: P331447-927

CATALOG NUMBER: SA2XXDIP-C1005D925U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6
2.5°	1558.8	1555.8	1545.6	1540.3	1531.6	1523.3	1518.0	1520.4	1522.3	1521.4	1519.9
5°	1514.1	1502.5	1484.9	1469.7	1458.8	1438.8	1430.3	1426.1	1422.4	1418.2	1413.9
7.5°	1460.9	1442.7	1417.5	1395.8	1375.4	1350.5	1336.3	1327.9	1319.1	1309.5	1301.0
10°	1423.0	1397.5	1370.8	1340.5	1316.2	1293.7	1273.7	1260.3	1248.2	1236.7	1228.1
12.5°	1383.2	1353.8	1320.8	1279.3	1252.5	1220.4	1217.3	1193.8	1174.8	1167.7	1157.7
15°	1319.8	1278.5	1236.7	1187.5	1166.3	1137.1	1118.9	1100.7	1084.3	1072.7	1069.7
17.5°	1247.8	1194.4	1152.7	1117.4	1082.6	1052.7	1035.9	1021.4	1007.9	992.4	990.4
20°	1192.9	1146.8	1101.3	1070.3	1034.5	1004.1	983.5	968.9	957.4	948.2	940.4
22.5°	1141.0	1090.4	1048.8	1014.9	979.6	955.1	938.8	924.7	915.1	905.1	897.6
25°	1057.6	1018.1	972.6	934.3	905.1	889.4	876.0	863.9	857.9	851.1	842.6
27.5°	984.6	940.7	898.1	868.5	842.9	828.9	819.4	811.2	805.5	801.6	796.8
30°	933.1	888.7	855.4	826.2	805.0	791.1	785.0	780.1	773.4	771.0	768.6
32.5°	883.5	843.6	815.1	789.8	769.5	760.4	754.9	750.5	745.3	742.8	738.0
35°	813.5	780.1	752.2	738.2	721.8	713.9	709.7	703.6	698.8	696.3	695.7
37.5°	747.6	718.6	700.2	682.2	675.3	670.5	664.6	660.5	659.1	658.7	658.1
40°	704.8	681.1	664.8	650.2	647.1	639.8	635.0	631.4	631.4	632.0	631.4
42.5°	666.0	644.8	630.3	617.7	614.1	609.7	604.9	604.7	605.6	607.7	605.6
45°	607.1	591.9	581.6	575.5	568.9	564.6	564.0	565.8	566.4	567.0	568.9
47.5°	552.9	542.9	533.5	526.8	523.9	523.2	522.4	525.6	528.5	529.7	532.4
50°	520.9	509.4	501.5	497.2	494.8	493.5	494.8	498.4	500.8	503.9	505.7
52.5°	485.0	476.8	471.3	468.1	467.1	467.9	468.1	472.2	476.1	477.2	478.0
55°	435.3	429.2	428.0	422.6	424.9	424.4	427.4	429.8	433.5	437.1	437.7
57.5°	385.7	380.9	377.6	378.1	378.8	381.5	384.0	388.3	392.2	396.1	396.4
60°	352.8	350.3	348.5	348.5	349.7	353.3	356.3	360.6	363.1	365.4	367.3
62.5°	322.6	320.2	318.4	319.3	322.5	324.6	328.2	330.5	333.0	335.3	336.2
65°	275.0	273.8	275.6	276.9	277.4	280.5	284.7	286.5	289.0	290.2	294.5
67.5°	231.2	231.4	231.2	232.9	236.4	237.1	241.1	245.4	245.9	248.2	251.0
70°	201.5	202.8	204.0	205.2	208.3	209.5	212.5	214.3	216.7	218.6	220.4
72.5°	174.4	174.6	175.8	175.5	178.1	180.8	183.3	185.1	187.6	189.9	191.7
75°	134.2	134.2	135.4	136.0	139.0	142.0	141.5	142.7	145.1	147.5	148.8
77.5°	98.0	96.6	98.0	98.6	99.6	102.1	102.6	104.3	107.1	106.2	107.6
80°	74.7	72.9	74.7	75.3	75.3	78.3	78.3	79.5	81.4	79.5	81.4
82.5°	53.3	52.4	53.8	53.9	54.9	55.0	56.0	56.2	58.1	57.2	58.1
85°	26.7	26.1	26.7	26.1	26.7	27.3	27.3	26.7	26.7	28.0	26.1
87.5°	9.8	9.7	9.4	9.7	9.4	9.2	8.9	9.0	9.2	8.4	8.5
90°	7.8	9.3	10.6	11.9	13.2	14.5	15.3	16.1	16.9	17.7	18.2
92.5°	13.9	14.2	14.9	15.5	16.2	16.8	17.2	17.6	18.1	18.5	18.8
95°	25.8	23.7	24.9	26.0	27.1	28.2	29.0	29.8	30.7	31.4	31.8
97.5°	33.5	27.3	29.9	32.6	35.2	37.8	38.4	39.1	39.7	40.3	40.7
100°	39.9	30.3	33.0	35.8	38.5	41.3	42.5	43.8	45.1	46.4	47.2
102.5°	147.6	133.9	111.0	88.1	65.3	42.4	44.0	45.7	47.5	49.1	50.1
105°	239.2	219.7	175.8	131.9	88.0	44.1	45.9	47.7	49.4	51.2	52.4
107.5°	296.8	272.4	219.7	167.1	114.4	61.8	60.0	58.1	56.4	54.6	54.0
110°	334.0	312.4	266.0	219.5	173.1	126.6	110.5	94.4	78.3	62.3	54.6



TEST NUMBER: P331447-927

CATALOG NUMBER: SA2XXDIP-C1005D925U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	369.5	365.3	353.8	342.3	330.8	319.3	260.7	202.1	143.4	84.8	55.7
115°	426.9	430.3	434.4	438.4	442.4	446.4	371.9	297.5	223.1	148.6	105.6
117.5°	480.5	483.4	486.2	488.9	491.7	494.4	476.4	458.4	440.5	422.4	394.3
120°	516.1	518.7	521.7	524.5	527.4	530.3	532.3	534.2	536.1	538.1	528.1
122.5°	549.0	551.8	555.0	558.2	561.3	564.5	565.6	566.8	567.9	569.1	567.6
125°	596.6	599.1	602.2	605.2	608.3	611.3	612.5	613.6	614.7	615.8	616.6
127.5°	642.1	644.4	646.7	649.0	651.3	653.6	655.2	656.9	658.5	660.2	661.0
130°	671.5	673.8	675.5	677.2	679.1	680.8	682.5	684.4	686.1	687.9	688.7
132.5°	698.9	700.9	702.7	704.5	706.2	708.0	709.6	711.1	712.6	714.1	714.7
135°	738.2	740.1	741.6	743.1	744.5	745.9	747.5	749.2	750.8	752.3	753.0
137.5°	773.1	774.8	776.4	778.1	779.7	781.4	782.9	784.5	786.1	787.7	788.2
140°	795.9	797.5	799.2	801.0	802.8	804.5	806.0	807.4	808.9	810.3	810.6
142.5°	816.3	817.8	819.8	821.9	823.9	825.9	827.3	828.5	829.9	831.2	831.5
145°	843.7	844.9	847.7	850.4	853.2	855.9	857.0	858.2	859.3	860.4	860.5
147.5°	870.4	871.4	874.1	876.9	879.6	882.3	883.0	883.9	884.7	885.6	885.7
150°	886.8	887.6	890.2	892.7	895.3	897.9	898.8	899.8	900.8	901.7	901.8
152.5°	902.0	902.5	905.0	907.4	909.9	912.4	913.3	914.3	915.2	916.2	916.2
155°	923.9	924.2	926.1	928.0	929.9	931.8	932.8	933.8	934.8	935.7	935.6
157.5°	942.6	942.7	944.0	945.4	946.7	948.1	949.2	950.2	951.3	952.4	952.4
160°	954.0	954.0	955.0	956.0	957.0	957.9	958.9	959.8	960.8	961.8	961.7
162.5°	963.3	963.2	964.1	964.9	965.7	966.6	967.7	968.8	969.9	971.0	970.8
165°	975.7	975.5	976.0	976.4	977.0	977.5	978.6	979.7	980.8	981.9	981.9
167.5°	985.0	984.8	985.2	985.6	986.1	986.6	987.7	988.8	989.9	991.1	990.9
170°	990.2	989.9	990.2	990.5	990.9	991.2	992.3	993.5	994.6	995.7	995.5
172.5°	993.7	993.4	993.7	994.0	994.3	994.7	995.8	996.9	998.1	999.2	999.0
175°	997.5	997.1	997.4	997.8	998.1	998.4	999.6	1000.7	1001.8	1002.9	1002.7
177.5°	999.2	998.8	998.9	999.0	999.2	999.3	1000.2	1001.1	1002.0	1002.9	1002.7
180°	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9



TEST NUMBER: P331447-927

CATALOG NUMBER: SA2XXDIP-C1005D925U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6
2.5°	1515.0	1514.1	1514.1	1509.7	1514.1	1514.1	1515.0	1519.9	1521.4	1522.3	1520.4
5°	1405.4	1403.6	1400.6	1403.6	1400.6	1403.6	1405.4	1413.9	1418.2	1422.4	1426.1
7.5°	1297.0	1289.7	1288.6	1281.4	1288.6	1289.7	1297.0	1301.0	1309.5	1319.1	1327.9
10°	1217.8	1213.0	1212.4	1200.8	1212.4	1213.0	1217.8	1228.1	1236.7	1248.2	1260.3
12.5°	1157.6	1146.0	1148.3	1141.5	1148.3	1146.0	1157.6	1157.7	1167.7	1174.8	1193.8
15°	1053.3	1053.3	1050.9	1040.5	1050.9	1053.3	1053.3	1069.7	1072.7	1084.3	1100.7
17.5°	978.4	977.2	971.4	974.2	971.4	977.2	978.4	990.4	992.4	1007.9	1021.4
20°	933.7	930.1	922.8	922.8	922.8	930.1	933.7	940.4	948.2	957.4	968.9
22.5°	891.4	891.2	883.4	885.9	883.4	891.2	891.4	897.6	905.1	915.1	924.7
25°	842.0	837.2	833.5	835.4	833.5	837.2	842.0	842.6	851.1	857.9	863.9
27.5°	795.2	792.5	792.3	787.3	792.3	792.5	795.2	796.8	801.6	805.5	811.2
30°	767.9	761.9	763.1	760.1	763.1	761.9	767.9	768.6	771.0	773.4	780.1
32.5°	736.9	734.7	733.5	730.9	733.5	734.7	736.9	738.0	742.8	745.3	750.5
35°	694.5	695.1	692.1	693.3	692.1	695.1	694.5	695.7	696.3	698.8	703.6
37.5°	657.5	659.4	658.0	658.3	658.0	659.4	657.5	658.1	658.7	659.1	660.5
40°	633.2	633.2	633.2	635.0	633.2	633.2	633.2	631.4	632.0	631.4	631.4
42.5°	609.9	609.0	607.9	607.8	607.9	609.0	609.9	605.6	607.7	605.6	604.7
45°	570.1	571.9	572.5	569.4	572.5	571.9	570.1	568.9	567.0	566.4	565.8
47.5°	534.0	534.2	534.0	536.7	534.0	534.2	534.0	532.4	529.7	528.5	525.6
50°	508.7	507.6	508.7	507.6	508.7	507.6	508.7	505.7	503.9	500.8	498.4
52.5°	482.0	482.3	481.6	481.3	481.6	482.3	482.0	478.0	477.2	476.1	472.2
55°	440.1	441.3	440.8	440.8	440.8	441.3	440.1	437.7	437.1	433.5	429.8
57.5°	396.8	397.9	398.7	396.1	398.7	397.9	396.8	396.4	396.1	392.2	388.3
60°	366.7	369.7	369.1	367.9	369.1	369.7	366.7	367.3	365.4	363.1	360.6
62.5°	339.0	340.1	340.0	339.8	340.0	340.1	339.0	336.2	335.3	333.0	330.5
65°	296.3	297.5	295.6	297.5	295.6	297.5	296.3	294.5	290.2	289.0	286.5
67.5°	250.3	250.6	251.9	252.8	251.9	250.6	250.3	251.0	248.2	245.9	245.4
70°	221.6	221.0	222.8	224.7	222.8	221.0	221.6	220.4	218.6	216.7	214.3
72.5°	191.5	192.8	192.2	193.5	192.2	192.8	191.5	191.7	189.9	187.6	185.1
75°	147.5	149.3	148.8	150.6	148.8	149.3	147.5	148.8	147.5	145.1	142.7
77.5°	106.6	106.9	106.6	107.6	106.6	106.9	106.6	107.6	106.2	107.1	104.3
80°	81.4	80.2	78.9	81.4	78.9	80.2	81.4	81.4	79.5	81.4	79.5
82.5°	56.6	57.3	56.1	56.1	56.1	57.3	56.6	58.1	57.2	58.1	56.2
85°	26.1	25.5	24.3	24.3	24.3	25.5	26.1	26.1	28.0	26.7	26.7
87.5°	8.6	8.2	8.2	7.8	8.2	8.2	8.6	8.5	8.4	9.2	9.0
90°	18.5	18.9	19.3	19.6	19.3	18.9	18.5	18.2	17.7	16.9	16.1
92.5°	18.9	19.2	19.3	19.6	19.3	19.2	18.9	18.8	18.5	18.1	17.6
95°	31.6	31.4	31.3	31.1	31.3	31.4	31.6	31.8	31.4	30.7	29.8
97.5°	41.0	41.1	41.4	41.5	41.4	41.1	41.0	40.7	40.3	39.7	39.1
100°	47.5	47.8	48.2	48.5	48.2	47.8	47.5	47.2	46.4	45.1	43.8
102.5°	50.6	51.0	51.5	52.0	51.5	51.0	50.6	50.1	49.1	47.5	45.7
105°	53.1	53.7	54.3	55.0	54.3	53.7	53.1	52.4	51.2	49.4	47.7
107.5°	54.7	55.3	55.9	56.6	55.9	55.3	54.7	54.0	54.6	56.4	58.1
110°	55.2	55.8	56.5	57.2	56.5	55.8	55.2	54.6	62.3	78.3	94.4



TEST NUMBER: P331447-927

CATALOG NUMBER: SA2XXDIP-C1005D925U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	56.2	56.7	57.2	57.8	57.2	56.7	56.2	55.7	84.8	143.4	202.1
115°	94.0	82.5	70.9	59.3	70.9	82.5	94.0	105.6	148.6	223.1	297.5
117.5°	356.3	318.3	280.3	242.2	280.3	318.3	356.3	394.3	422.4	440.5	458.4
120°	506.4	484.7	463.0	441.3	463.0	484.7	506.4	528.1	538.1	536.1	534.2
122.5°	563.4	559.1	554.9	550.7	554.9	559.1	563.4	567.6	569.1	567.9	566.8
125°	617.1	617.6	618.1	618.6	618.1	617.6	617.1	616.6	615.8	614.7	613.6
127.5°	661.2	661.2	661.3	661.4	661.3	661.2	661.2	661.0	660.2	658.5	656.9
130°	688.6	688.3	688.2	688.0	688.2	688.3	688.6	688.7	687.9	686.1	684.4
132.5°	714.5	714.4	714.2	714.1	714.2	714.4	714.5	714.7	714.1	712.6	711.1
135°	752.7	752.3	752.0	751.7	752.0	752.3	752.7	753.0	752.3	750.8	749.2
137.5°	787.7	787.1	786.6	786.0	786.6	787.1	787.7	788.2	787.7	786.1	784.5
140°	809.8	809.1	808.3	807.4	808.3	809.1	809.8	810.6	810.3	808.9	807.4
142.5°	830.7	829.9	829.1	828.2	829.1	829.9	830.7	831.5	831.2	829.9	828.5
145°	859.8	859.0	858.2	857.4	858.2	859.0	859.8	860.5	860.4	859.3	858.2
147.5°	884.9	884.3	883.6	883.0	883.6	884.3	884.9	885.7	885.6	884.7	883.9
150°	901.0	900.2	899.4	898.6	899.4	900.2	901.0	901.8	901.7	900.8	899.8
152.5°	915.0	914.0	913.0	911.9	913.0	914.0	915.0	916.2	916.2	915.2	914.3
155°	934.3	933.0	931.7	930.4	931.7	933.0	934.3	935.6	935.7	934.8	933.8
157.5°	951.1	949.8	948.6	947.4	948.6	949.8	951.1	952.4	952.4	951.3	950.2
160°	960.5	959.4	958.3	957.2	958.3	959.4	960.5	961.7	961.8	960.8	959.8
162.5°	969.5	968.0	966.7	965.3	966.7	968.0	969.5	970.8	971.0	969.9	968.8
165°	980.8	979.7	978.6	977.5	978.6	979.7	980.8	981.9	981.9	980.8	979.7
167.5°	989.4	988.0	986.6	985.1	986.6	988.0	989.4	990.9	991.1	989.9	988.8
170°	994.1	992.6	991.2	989.8	991.2	992.6	994.1	995.5	995.7	994.6	993.5
172.5°	997.5	996.1	994.7	993.2	994.7	996.1	997.5	999.0	999.2	998.1	996.9
175°	1001.1	999.5	997.8	996.2	997.8	999.5	1001.1	1002.7	1002.9	1001.8	1000.7
177.5°	1001.6	1000.4	999.3	998.1	999.3	1000.4	1001.6	1002.7	1002.9	1002.0	1001.1
180°	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9



TEST NUMBER: P331447-927

CATALOG NUMBER: SA2XXDIP-C1005D925U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6
2.5°	1518.0	1523.3	1531.6	1540.3	1545.6	1555.8	1558.8	1563.6	1568.0	1578.2	1588.9
5°	1430.3	1438.8	1458.8	1469.7	1484.9	1502.5	1514.1	1526.2	1539.6	1562.7	1583.9
7.5°	1336.3	1350.5	1375.4	1395.8	1417.5	1442.7	1460.9	1484.9	1504.8	1537.4	1568.4
10°	1273.7	1293.7	1316.2	1340.5	1370.8	1397.5	1423.0	1453.3	1477.7	1516.5	1552.9
12.5°	1217.3	1220.4	1252.5	1279.3	1320.8	1353.8	1383.2	1422.3	1446.0	1492.2	1530.6
15°	1118.9	1137.1	1166.3	1187.5	1236.7	1278.5	1319.8	1360.5	1387.8	1444.9	1495.2
17.5°	1035.9	1052.7	1082.6	1117.4	1152.7	1194.4	1247.8	1290.7	1327.9	1393.1	1452.6
20°	983.5	1004.1	1034.5	1070.3	1101.3	1146.8	1192.9	1242.1	1282.1	1355.7	1425.5
22.5°	938.8	955.1	979.6	1014.9	1048.8	1090.4	1141.0	1194.5	1236.5	1315.8	1386.6
25°	876.0	889.4	905.1	934.3	972.6	1018.1	1057.6	1116.4	1177.7	1251.8	1337.4
27.5°	819.4	828.9	842.9	868.5	898.1	940.7	984.6	1040.5	1102.1	1182.5	1272.8
30°	785.0	791.1	805.0	826.2	855.4	888.7	933.1	986.5	1049.6	1131.0	1220.8
32.5°	754.9	760.4	769.5	789.8	815.1	843.6	883.5	937.0	997.2	1077.1	1176.6
35°	709.7	713.9	721.8	738.2	752.2	780.1	813.5	862.1	918.5	995.1	1098.2
37.5°	664.6	670.5	675.3	682.2	700.2	718.6	747.6	788.6	844.0	921.2	1019.5
40°	635.0	639.8	647.1	650.2	664.8	681.1	704.8	742.4	798.4	868.7	964.6
42.5°	604.9	609.7	614.1	617.7	630.3	644.8	666.0	698.3	747.8	816.3	911.2
45°	564.0	564.6	568.9	575.5	581.6	591.9	607.1	635.0	673.3	737.6	823.8
47.5°	522.4	523.2	523.9	526.8	533.5	542.9	552.9	575.7	609.9	661.2	745.1
50°	494.8	493.5	494.8	497.2	501.5	509.4	520.9	537.3	565.2	613.1	690.2
52.5°	468.1	467.9	467.1	468.1	471.3	476.8	485.0	498.9	523.9	568.0	635.9
55°	427.4	424.4	424.9	422.6	428.0	429.2	435.3	446.8	468.7	499.0	562.8
57.5°	384.0	381.5	378.8	378.1	377.6	380.9	385.7	394.8	411.6	438.2	489.9
60°	356.3	353.3	349.7	348.5	348.5	350.3	352.8	359.4	375.2	398.9	441.3
62.5°	328.2	324.6	322.5	319.3	318.4	320.2	322.6	327.3	338.7	361.0	397.7
65°	284.7	280.5	277.4	276.9	275.6	273.8	275.0	279.9	289.0	306.6	335.7
67.5°	241.1	237.1	236.4	232.9	231.2	231.4	231.2	235.3	240.7	256.0	277.7
70°	212.5	209.5	208.3	205.2	204.0	202.8	201.5	205.2	210.6	223.4	242.2
72.5°	183.3	180.8	178.1	175.5	175.8	174.6	174.4	176.6	181.0	192.8	207.2
75°	141.5	142.0	139.0	136.0	135.4	134.2	134.2	136.0	137.8	146.9	158.4
77.5°	102.6	102.1	99.6	98.6	98.0	96.6	98.0	99.2	100.1	106.2	114.7
80°	78.3	78.3	75.3	75.3	74.7	72.9	74.7	73.4	75.9	82.0	88.0
82.5°	56.0	55.0	54.9	53.9	53.8	52.4	53.3	54.5	55.5	59.7	63.3
85°	27.3	27.3	26.7	26.1	26.7	26.1	26.7	27.3	28.0	29.8	32.8
87.5°	8.9	9.2	9.4	9.7	9.4	9.7	9.8	10.0	10.5	10.7	10.9
90°	15.3	14.5	13.2	11.9	10.6	9.3	7.8	6.0	4.3	2.5	0.7
92.5°	17.2	16.8	16.2	15.5	14.9	14.2	13.9	14.1	14.3	14.4	14.6
95°	29.0	28.2	27.1	26.0	24.9	23.7	25.8	31.1	36.4	41.7	47.1
97.5°	38.4	37.8	35.2	32.6	29.9	27.3	33.5	48.5	63.5	78.3	93.3
100°	42.5	41.3	38.5	35.8	33.0	30.3	39.9	61.9	84.0	106.0	128.1
102.5°	44.0	42.4	65.3	88.1	111.0	133.9	147.6	152.3	156.9	161.6	166.3
105°	45.9	44.1	88.0	131.9	175.8	219.7	239.2	234.4	229.6	224.7	219.9
107.5°	60.0	61.8	114.4	167.1	219.7	272.4	296.8	292.8	288.9	285.0	281.1
110°	110.5	126.6	173.1	219.5	266.0	312.4	334.0	330.7	327.3	323.9	320.5



TEST NUMBER: P331447-927

CATALOG NUMBER: SA2XXDIP-C1005D925U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	260.7	319.3	330.8	342.3	353.8	365.3	369.5	366.5	363.5	360.5	357.5
115°	371.9	446.4	442.4	438.4	434.4	430.3	426.9	424.2	421.4	418.7	416.0
117.5°	476.4	494.4	491.7	488.9	486.2	483.4	480.5	477.4	474.4	471.3	468.3
120°	532.3	530.3	527.4	524.5	521.7	518.7	516.1	513.7	511.3	508.8	506.4
122.5°	565.6	564.5	561.3	558.2	555.0	551.8	549.0	546.4	543.9	541.4	538.8
125°	612.5	611.3	608.3	605.2	602.2	599.1	596.6	594.5	592.4	590.3	588.2
127.5°	655.2	653.6	651.3	649.0	646.7	644.4	642.1	639.8	637.5	635.3	632.9
130°	682.5	680.8	679.1	677.2	675.5	673.8	671.5	669.0	666.4	663.8	661.3
132.5°	709.6	708.0	706.2	704.5	702.7	700.9	698.9	696.8	694.6	692.4	690.2
135°	747.5	745.9	744.5	743.1	741.6	740.1	738.2	735.5	733.0	730.4	727.9
137.5°	782.9	781.4	779.7	778.1	776.4	774.8	773.1	771.3	769.5	767.7	765.9
140°	806.0	804.5	802.8	801.0	799.2	797.5	795.9	794.6	793.4	792.1	790.8
142.5°	827.3	825.9	823.9	821.9	819.8	817.8	816.3	815.1	814.0	812.8	811.6
145°	857.0	855.9	853.2	850.4	847.7	844.9	843.7	843.8	844.0	844.1	844.3
147.5°	883.0	882.3	879.6	876.9	874.1	871.4	870.4	871.0	871.6	872.2	872.8
150°	898.8	897.9	895.3	892.7	890.2	887.6	886.8	888.0	889.1	890.3	891.4
152.5°	913.3	912.4	909.9	907.4	905.0	902.5	902.0	903.2	904.4	905.7	907.0
155°	932.8	931.8	929.9	928.0	926.1	924.2	923.9	925.3	926.8	928.3	929.7
157.5°	949.2	948.1	946.7	945.4	944.0	942.7	942.6	943.8	945.1	946.3	947.5
160°	958.9	957.9	957.0	956.0	955.0	954.0	954.0	955.0	956.0	957.0	957.9
162.5°	967.7	966.6	965.7	964.9	964.1	963.2	963.3	964.2	965.3	966.2	967.2
165°	978.6	977.5	977.0	976.4	976.0	975.5	975.7	976.7	977.7	978.7	979.6
167.5°	987.7	986.6	986.1	985.6	985.2	984.8	985.0	986.0	987.0	987.9	988.9
170°	992.3	991.2	990.9	990.5	990.2	989.9	990.2	991.2	992.1	993.1	994.1
172.5°	995.8	994.7	994.3	994.0	993.7	993.4	993.7	994.7	995.6	996.6	997.5
175°	999.6	998.4	998.1	997.8	997.4	997.1	997.5	998.6	999.8	1000.9	1002.0
177.5°	1000.2	999.3	999.2	999.0	998.9	998.8	999.2	1000.1	1001.0	1001.9	1002.7
180°	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9



TEST NUMBER: P331447-927

CATALOG NUMBER: SA2XXDIP-C1005D925U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6
2.5°	1587.9	1590.3	1598.1	1605.9	1614.6	1617.1	1621.0	1617.6	1616.5	1625.8	1632.6
5°	1592.4	1603.3	1624.6	1644.0	1660.4	1671.9	1684.1	1688.9	1698.0	1710.8	1726.6
7.5°	1587.3	1608.5	1642.0	1670.2	1701.1	1723.3	1740.7	1755.5	1773.5	1797.6	1823.9
10°	1581.4	1610.0	1650.7	1685.3	1722.9	1751.4	1775.1	1798.2	1825.0	1858.3	1892.9
12.5°	1570.8	1604.6	1655.5	1696.5	1744.8	1772.8	1804.7	1854.6	1883.2	1929.7	1978.4
15°	1549.3	1586.9	1658.0	1708.3	1763.0	1816.4	1875.3	1922.6	1970.0	1997.3	2065.9
17.5°	1517.3	1572.6	1651.3	1710.1	1779.5	1863.6	1929.8	1983.5	2038.1	2082.4	2116.8
20°	1491.6	1551.7	1641.6	1712.0	1794.5	1885.0	1960.9	2015.5	2062.9	2099.9	2121.1
22.5°	1459.0	1534.7	1622.2	1704.7	1810.1	1899.6	1979.3	2022.4	2061.9	2080.0	2088.1
25°	1407.9	1498.9	1597.8	1698.7	1817.7	1912.3	1985.2	2011.3	2022.8	2005.3	1976.1
27.5°	1352.6	1454.1	1569.8	1687.2	1813.0	1904.1	1956.3	1952.2	1932.6	1875.7	1830.1
30°	1311.3	1423.0	1547.4	1675.5	1801.8	1890.5	1920.8	1890.5	1846.2	1782.4	1717.5
32.5°	1268.1	1383.7	1523.7	1659.1	1781.5	1859.4	1866.0	1813.8	1745.2	1672.7	1591.7
35°	1202.6	1327.7	1478.8	1622.2	1738.1	1787.2	1758.2	1665.9	1584.5	1485.6	1375.1
37.5°	1128.7	1266.8	1418.4	1568.1	1673.2	1686.0	1613.7	1516.5	1401.8	1285.5	1155.4
40°	1073.3	1219.6	1375.7	1526.9	1619.7	1606.4	1514.1	1407.2	1270.7	1128.5	1007.7
42.5°	1023.8	1170.1	1329.0	1477.3	1551.7	1515.0	1407.2	1276.1	1129.3	995.5	884.9
45°	937.9	1088.5	1251.3	1394.5	1437.0	1370.8	1228.1	1082.4	937.9	826.2	738.9
47.5°	854.7	1003.5	1164.7	1290.5	1305.6	1216.6	1060.7	910.8	786.6	695.6	633.9
50°	793.4	942.8	1102.5	1214.8	1209.9	1102.5	942.2	799.5	695.7	622.3	581.0
52.5°	738.6	879.6	1033.0	1135.1	1109.4	992.2	839.2	712.6	627.2	569.8	532.4
55°	653.2	783.8	929.5	1011.4	964.1	834.2	704.8	602.9	539.7	496.6	467.5
57.5°	568.5	690.9	815.6	866.1	813.7	693.8	586.0	512.0	464.5	432.6	413.7
60°	516.0	622.9	734.0	777.7	715.2	608.3	523.3	457.2	418.9	392.8	375.8
62.5°	463.6	559.3	664.0	687.9	630.7	540.3	465.0	410.0	378.6	355.4	339.4
65°	392.2	470.5	550.0	565.8	513.0	443.1	383.7	347.8	320.0	302.9	290.2
67.5°	321.6	384.5	440.8	453.6	407.3	358.9	315.9	284.7	265.8	251.7	240.9
70°	279.9	329.6	375.8	386.1	349.1	305.9	273.2	248.3	231.3	219.2	208.8
72.5°	235.7	277.2	315.5	322.5	292.2	259.4	232.4	212.9	197.8	190.0	180.2
75°	180.3	204.6	234.3	236.1	216.1	196.1	175.5	162.7	154.8	145.1	140.2
77.5°	127.2	146.3	163.3	166.6	154.7	141.1	129.5	119.5	112.8	108.3	103.8
80°	97.1	112.3	119.6	123.8	115.3	105.6	98.9	92.3	88.0	85.0	82.0
82.5°	69.5	78.8	85.6	88.9	84.3	78.4	71.8	68.0	64.7	62.2	61.1
85°	35.2	39.5	43.7	44.9	43.7	41.3	37.6	37.6	35.8	35.2	35.2
87.5°	12.7	15.0	15.3	17.1	16.4	16.7	17.0	16.7	16.5	16.2	15.8
90°	2.5	4.3	6.0	7.8	9.3	10.6	11.9	13.2	14.5	15.3	16.1
92.5°	14.4	14.3	14.1	13.9	14.2	14.9	15.5	16.2	16.8	17.2	17.6
95°	41.7	36.4	31.1	25.8	23.7	24.9	26.0	27.1	28.2	29.0	29.8
97.5°	78.3	63.5	48.5	33.5	27.3	29.9	32.6	35.2	37.8	38.4	39.1
100°	106.0	84.0	61.9	39.9	30.3	33.0	35.8	38.5	41.3	42.5	43.8
102.5°	161.6	156.9	152.3	147.6	133.9	111.0	88.1	65.3	42.4	44.0	45.7
105°	224.7	229.6	234.4	239.2	219.7	175.8	131.9	88.0	44.1	45.9	47.7
107.5°	285.0	288.9	292.8	296.8	272.4	219.7	167.1	114.4	61.8	60.0	58.1
110°	323.9	327.3	330.7	334.0	312.4	266.0	219.5	173.1	126.6	110.5	94.4





TEST NUMBER: P331447-927

CATALOG NUMBER: SA2XXDIP-C1005D925U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	360.5	363.5	366.5	369.5	365.3	353.8	342.3	330.8	319.3	260.7	202.1
115°	418.7	421.4	424.2	426.9	430.3	434.4	438.4	442.4	446.4	371.9	297.5
117.5°	471.3	474.4	477.4	480.5	483.4	486.2	488.9	491.7	494.4	476.4	458.4
120°	508.8	511.3	513.7	516.1	518.7	521.7	524.5	527.4	530.3	532.3	534.2
122.5°	541.4	543.9	546.4	549.0	551.8	555.0	558.2	561.3	564.5	565.6	566.8
125°	590.3	592.4	594.5	596.6	599.1	602.2	605.2	608.3	611.3	612.5	613.6
127.5°	635.3	637.5	639.8	642.1	644.4	646.7	649.0	651.3	653.6	655.2	656.9
130°	663.8	666.4	669.0	671.5	673.8	675.5	677.2	679.1	680.8	682.5	684.4
132.5°	692.4	694.6	696.8	698.9	700.9	702.7	704.5	706.2	708.0	709.6	711.1
135°	730.4	733.0	735.5	738.2	740.1	741.6	743.1	744.5	745.9	747.5	749.2
137.5°	767.7	769.5	771.3	773.1	774.8	776.4	778.1	779.7	781.4	782.9	784.5
140°	792.1	793.4	794.6	795.9	797.5	799.2	801.0	802.8	804.5	806.0	807.4
142.5°	812.8	814.0	815.1	816.3	817.8	819.8	821.9	823.9	825.9	827.3	828.5
145°	844.1	844.0	843.8	843.7	844.9	847.7	850.4	853.2	855.9	857.0	858.2
147.5°	872.2	871.6	871.0	870.4	871.4	874.1	876.9	879.6	882.3	883.0	883.9
150°	890.3	889.1	888.0	886.8	887.6	890.2	892.7	895.3	897.9	898.8	899.8
152.5°	905.7	904.4	903.2	902.0	902.5	905.0	907.4	909.9	912.4	913.3	914.3
155°	928.3	926.8	925.3	923.9	924.2	926.1	928.0	929.9	931.8	932.8	933.8
157.5°	946.3	945.1	943.8	942.6	942.7	944.0	945.4	946.7	948.1	949.2	950.2
160°	957.0	956.0	955.0	954.0	954.0	955.0	956.0	957.0	957.9	958.9	959.8
162.5°	966.2	965.3	964.2	963.3	963.2	964.1	964.9	965.7	966.6	967.7	968.8
165°	978.7	977.7	976.7	975.7	975.5	976.0	976.4	977.0	977.5	978.6	979.7
167.5°	987.9	987.0	986.0	985.0	984.8	985.2	985.6	986.1	986.6	987.7	988.8
170°	993.1	992.1	991.2	990.2	989.9	990.2	990.5	990.9	991.2	992.3	993.5
172.5°	996.6	995.6	994.7	993.7	993.4	993.7	994.0	994.3	994.7	995.8	996.9
175°	1000.9	999.8	998.6	997.5	997.1	997.4	997.8	998.1	998.4	999.6	1000.7
177.5°	1001.9	1001.0	1000.1	999.2	998.8	998.9	999.0	999.2	999.3	1000.2	1001.1
180°	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9



TEST NUMBER: P331447-927

CATALOG NUMBER: SA2XXDIP-C1005D925U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6
2.5°	1638.4	1645.2	1645.2	1646.2	1653.9	1653.0	1652.5
5°	1743.6	1753.9	1755.1	1766.0	1773.3	1770.8	1764.2
7.5°	1842.8	1861.9	1876.5	1884.7	1894.3	1900.2	1897.5
10°	1921.4	1949.4	1966.4	1977.9	1991.9	2002.2	1998.5
12.5°	1992.8	2026.1	2049.5	2069.2	2071.0	2084.2	2075.3
15°	2104.2	2139.4	2143.0	2157.6	2169.2	2167.9	2168.5
17.5°	2141.0	2152.3	2154.6	2154.9	2155.1	2150.8	2141.6
20°	2127.9	2123.6	2113.3	2105.4	2091.4	2089.6	2077.5
22.5°	2065.7	2052.2	2026.3	2009.2	1987.5	1981.8	1978.4
25°	1943.3	1913.5	1872.2	1832.8	1821.9	1800.6	1806.7
27.5°	1775.4	1729.0	1684.3	1652.3	1623.3	1591.4	1600.5
30°	1657.3	1605.1	1542.0	1493.4	1462.4	1432.1	1426.6
32.5°	1516.5	1440.0	1369.6	1326.8	1279.4	1260.2	1239.2
35°	1273.7	1199.0	1129.2	1069.1	1034.5	1007.7	983.5
37.5°	1055.3	969.3	912.9	864.3	839.2	823.9	827.8
40°	919.7	844.5	803.2	766.1	743.1	732.1	734.6
42.5°	810.0	753.6	719.6	694.3	678.0	671.9	670.5
45°	685.4	653.9	625.9	611.3	603.5	596.8	592.6
47.5°	600.4	574.6	558.9	550.2	543.4	536.5	536.4
50°	549.4	532.4	521.5	512.4	506.9	502.1	506.3
52.5°	510.6	495.0	484.1	475.9	473.9	469.5	469.4
55°	452.9	440.8	432.8	425.6	421.9	419.5	416.5
57.5°	400.4	388.9	381.6	377.0	370.1	367.7	366.7
60°	363.1	353.9	346.7	340.6	337.5	332.7	332.7
62.5°	328.5	319.5	312.7	308.0	303.1	301.1	301.6
65°	278.7	271.4	264.7	259.8	258.6	255.0	256.2
67.5°	232.7	227.9	220.9	218.2	215.9	214.0	212.5
70°	202.2	197.3	193.7	190.0	188.2	188.2	188.2
72.5°	176.4	170.6	168.4	163.8	164.9	163.0	161.0
75°	136.6	132.9	131.1	129.3	126.3	126.3	126.3
77.5°	100.5	99.4	97.3	95.3	94.6	94.0	94.2
80°	77.7	77.1	75.9	75.9	74.7	74.1	72.9
82.5°	59.7	58.1	57.4	57.0	56.7	56.6	56.3
85°	34.0	32.8	32.8	33.4	32.2	32.2	32.8
87.5°	16.5	16.6	16.2	16.3	16.9	16.5	16.6
90°	16.9	17.7	18.2	18.5	18.9	19.3	19.6
92.5°	18.1	18.5	18.8	18.9	19.2	19.3	19.6
95°	30.7	31.4	31.8	31.6	31.4	31.3	31.1
97.5°	39.7	40.3	40.7	41.0	41.1	41.4	41.5
100°	45.1	46.4	47.2	47.5	47.8	48.2	48.5
102.5°	47.5	49.1	50.1	50.6	51.0	51.5	52.0
105°	49.4	51.2	52.4	53.1	53.7	54.3	55.0
107.5°	56.4	54.6	54.0	54.7	55.3	55.9	56.6
110°	78.3	62.3	54.6	55.2	55.8	56.5	57.2



TEST NUMBER: P331447-927

CATALOG NUMBER: SA2XXDIP-C1005D925U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	143.4	84.8	55.7	56.2	56.7	57.2	57.8
115°	223.1	148.6	105.6	94.0	82.5	70.9	59.3
117.5°	440.5	422.4	394.3	356.3	318.3	280.3	242.2
120°	536.1	538.1	528.1	506.4	484.7	463.0	441.3
122.5°	567.9	569.1	567.6	563.4	559.1	554.9	550.7
125°	614.7	615.8	616.6	617.1	617.6	618.1	618.6
127.5°	658.5	660.2	661.0	661.2	661.2	661.3	661.4
130°	686.1	687.9	688.7	688.6	688.3	688.2	688.0
132.5°	712.6	714.1	714.7	714.5	714.4	714.2	714.1
135°	750.8	752.3	753.0	752.7	752.3	752.0	751.7
137.5°	786.1	787.7	788.2	787.7	787.1	786.6	786.0
140°	808.9	810.3	810.6	809.8	809.1	808.3	807.4
142.5°	829.9	831.2	831.5	830.7	829.9	829.1	828.2
145°	859.3	860.4	860.5	859.8	859.0	858.2	857.4
147.5°	884.7	885.6	885.7	884.9	884.3	883.6	883.0
150°	900.8	901.7	901.8	901.0	900.2	899.4	898.6
152.5°	915.2	916.2	916.2	915.0	914.0	913.0	911.9
155°	934.8	935.7	935.6	934.3	933.0	931.7	930.4
157.5°	951.3	952.4	952.4	951.1	949.8	948.6	947.4
160°	960.8	961.8	961.7	960.5	959.4	958.3	957.2
162.5°	969.9	971.0	970.8	969.5	968.0	966.7	965.3
165°	980.8	981.9	981.9	980.8	979.7	978.6	977.5
167.5°	989.9	991.1	990.9	989.4	988.0	986.6	985.1
170°	994.6	995.7	995.5	994.1	992.6	991.2	989.8
172.5°	998.1	999.2	999.0	997.5	996.1	994.7	993.2
175°	1001.8	1002.9	1002.7	1001.1	999.5	997.8	996.2
177.5°	1002.0	1002.9	1002.7	1001.6	1000.4	999.3	998.1
180°	999.9	999.9	999.9	999.9	999.9	999.9	999.9

(END OF REPORT)