

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331448-927

Luminaire Tested: **SA2XXDIP-C1005D925U927-4F0-1E-UDD-A1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331448-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C1005D925U927-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 925 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6108.3 lumens
Efficiency: N/A
Efficacy: 91.4 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 66.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331448-927
CATALOG NUMBER: SA2XXDIP-C1005D925U927-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331448-927

CATALOG NUMBER: SA2XXDIP-C1005D925U927-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	63	63	63	57
1	100	96	92	89	93	89	86	83	77	75	73	66	65	63	56	55	54	49
2	91	84	78	73	85	79	74	69	68	65	61	59	56	54	50	48	46	42
3	84	75	67	62	78	70	64	58	61	56	52	53	49	46	45	42	40	36
4	77	66	59	53	71	62	55	50	54	49	45	47	43	40	41	37	35	32
5	71	59	52	46	66	56	49	43	49	43	39	43	38	35	37	34	31	28
6	65	54	46	40	61	50	43	38	44	39	35	39	34	31	34	30	27	25
7	61	49	41	35	57	46	39	34	41	35	31	36	31	28	31	27	25	22
8	56	44	37	31	53	42	35	30	37	31	27	33	28	25	28	25	22	20
9	53	41	33	28	49	38	32	27	34	29	25	30	26	23	26	23	20	18
10	49	37	30	26	46	35	29	25	32	26	22	28	24	20	25	21	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	25504	25504	25504	25504
5°	28593	25671	22749	25671
10°	32765	25460	19687	25460
15°	36247	24993	17392	24993
20°	35696	24493	15856	24493
25°	32186	23826	14883	23826
30°	26597	22760	14171	22760
35°	19385	21646	13665	21646
40°	15483	20331	13384	20331
45°	13531	18810	13001	18810
50°	12717	17337	12750	17337
55°	11724	15842	12408	15842
60°	10743	14250	11880	14250
65°	9788	12825	11366	12825
70°	8884	11434	10607	11434
75°	7879	9881	9395	9881
80°	6778	8182	7569	8182
85°	6076	6076	4502	6076



TEST NUMBER: P331448-927

CATALOG NUMBER: SA2XXDIP-C1005D925U927-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	150.4	2.5
10°-20°	437.4	7.2
20°-30°	634.7	10.4
30°-40°	669.8	11.0
40°-50°	593.0	9.7
50°-60°	473.3	7.7
60°-70°	321.7	5.3
70°-80°	164.9	2.7
80°-90°	43.5	0.7
90°-100°	59.4	1.0
100°-110°	184.4	3.0
110°-120°	315.1	5.2
120°-130°	414.4	6.8
130°-140°	465.2	7.6
140°-150°	456.1	7.5
150°-160°	382.5	6.3
160°-170°	253.7	4.2
170°-180°	88.7	1.5
0°-30°	1222.5	20.0
0°-40°	1892.3	31.0
0°-60°	2958.6	48.4
0°-90°	3488.8	57.1
90°-120°	558.9	9.1
90°-150°	1894.5	31.0
90°-180°	2620.0	42.9
0°-180°	6108.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1580	1580	1580	1580	1580	
5°	1764	1584	1404	1584	1764	176
15°	2168	1495	1040	1495	2168	598
25°	1807	1337	835	1337	1807	817
35°	984	1098	693	1098	984	640
45°	593	824	569	824	593	466
55°	416	563	441	563	416	373
65°	256	336	298	336	256	255
75°	126	158	151	158	126	135
85°	33	33	24	33	33	37
90°	27	1	27	1	27	13
95°	49	41	49	41	49	55
105°	176	170	176	170	176	185
115°	316	316	316	316	316	312
125°	462	460	462	460	462	412
135°	602	595	602	595	602	464
145°	730	722	730	722	730	456
155°	832	826	832	826	832	383
165°	900	899	900	899	900	254
175°	932	935	932	935	932	89
180°	937	937	937	937	937	



TEST NUMBER: P331448-927

CATALOG NUMBER: SA2XXDIP-C1005D925U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6
2.5°	1652.5	1653.0	1653.9	1646.2	1645.2	1645.2	1638.4	1632.6	1625.8	1616.5	1617.6
5°	1764.2	1770.8	1773.3	1766.0	1755.1	1753.9	1743.6	1726.6	1710.8	1698.0	1688.9
7.5°	1897.5	1900.2	1894.3	1884.7	1876.5	1861.9	1842.8	1823.9	1797.6	1773.5	1755.5
10°	1998.5	2002.2	1991.9	1977.9	1966.4	1949.4	1921.4	1892.9	1858.3	1825.0	1798.2
12.5°	2075.3	2084.2	2071.0	2069.2	2049.5	2026.1	1992.8	1978.4	1929.7	1883.2	1854.6
15°	2168.5	2167.9	2169.2	2157.6	2143.0	2139.4	2104.2	2065.9	1997.3	1970.0	1922.6
17.5°	2141.6	2150.8	2155.1	2154.9	2154.6	2152.3	2141.0	2116.8	2082.4	2038.1	1983.5
20°	2077.5	2089.6	2091.4	2105.4	2113.3	2123.6	2127.9	2121.1	2099.9	2062.9	2015.5
22.5°	1978.4	1981.8	1987.5	2009.2	2026.3	2052.2	2065.7	2088.1	2080.0	2061.9	2022.4
25°	1806.7	1800.6	1821.9	1832.8	1872.2	1913.5	1943.3	1976.1	2005.3	2022.8	2011.3
27.5°	1600.5	1591.4	1623.3	1652.3	1684.3	1729.0	1775.4	1830.1	1875.7	1932.6	1952.2
30°	1426.6	1432.1	1462.4	1493.4	1542.0	1605.1	1657.3	1717.5	1782.4	1846.2	1890.5
32.5°	1239.2	1260.2	1279.4	1326.8	1369.6	1440.0	1516.5	1591.7	1672.7	1745.2	1813.8
35°	983.5	1007.7	1034.5	1069.1	1129.2	1199.0	1273.7	1375.1	1485.6	1584.5	1665.9
37.5°	827.8	823.9	839.2	864.3	912.9	969.3	1055.3	1155.4	1285.5	1401.8	1516.5
40°	734.6	732.1	743.1	766.1	803.2	844.5	919.7	1007.7	1128.5	1270.7	1407.2
42.5°	670.5	671.9	678.0	694.3	719.6	753.6	810.0	884.9	995.5	1129.3	1276.1
45°	592.6	596.8	603.5	611.3	625.9	653.9	685.4	738.9	826.2	937.9	1082.4
47.5°	536.4	536.5	543.4	550.2	558.9	574.6	600.4	633.9	695.6	786.6	910.8
50°	506.3	502.1	506.9	512.4	521.5	532.4	549.4	581.0	622.3	695.7	799.5
52.5°	469.4	469.5	473.9	475.9	484.1	495.0	510.6	532.4	569.8	627.2	712.6
55°	416.5	419.5	421.9	425.6	432.8	440.8	452.9	467.5	496.6	539.7	602.9
57.5°	366.7	367.7	370.1	377.0	381.6	388.9	400.4	413.7	432.6	464.5	512.0
60°	332.7	332.7	337.5	340.6	346.7	353.9	363.1	375.8	392.8	418.9	457.2
62.5°	301.6	301.1	303.1	308.0	312.7	319.5	328.5	339.4	355.4	378.6	410.0
65°	256.2	255.0	258.6	259.8	264.7	271.4	278.7	290.2	302.9	320.0	347.8
67.5°	212.5	214.0	215.9	218.2	220.9	227.9	232.7	240.9	251.7	265.8	284.7
70°	188.2	188.2	188.2	190.0	193.7	197.3	202.2	208.8	219.2	231.3	248.3
72.5°	161.0	163.0	164.9	163.8	168.4	170.6	176.4	180.2	190.0	197.8	212.9
75°	126.3	126.3	126.3	129.3	131.1	132.9	136.6	140.2	145.1	154.8	162.7
77.5°	94.2	94.0	94.6	95.3	97.3	99.4	100.5	103.8	108.3	112.8	119.5
80°	72.9	74.1	74.7	75.9	75.9	77.1	77.7	82.0	85.0	88.0	92.3
82.5°	56.3	56.6	56.7	57.0	57.4	58.1	59.7	61.1	62.2	64.7	68.0
85°	32.8	32.2	32.2	33.4	32.8	32.8	34.0	35.2	35.2	35.8	37.6
87.5°	18.0	18.0	18.5	17.9	17.8	18.4	18.5	18.0	18.6	19.2	18.9
90°	26.9	26.7	26.5	26.4	26.1	26.3	26.6	26.9	27.3	27.6	23.8
92.5°	25.6	25.6	25.5	25.5	25.5	25.4	25.3	25.3	25.2	25.1	24.2
95°	49.0	49.4	49.7	50.1	50.4	50.6	50.6	50.6	50.6	50.6	50.2
97.5°	84.9	84.9	85.0	85.0	85.1	85.1	85.1	85.1	85.1	85.1	84.4
100°	108.3	108.4	108.7	108.8	109.0	109.1	109.1	109.1	109.1	109.1	108.6
102.5°	134.9	135.1	135.2	135.4	135.5	135.6	135.5	135.3	135.1	135.1	134.4
105°	175.5	175.5	175.5	175.5	175.5	175.3	175.0	174.6	174.3	173.9	173.6
107.5°	213.7	214.6	215.4	216.2	217.0	217.3	217.2	217.1	216.9	216.7	216.7
110°	243.5	244.0	244.5	245.1	245.6	245.9	245.9	245.9	245.9	245.9	245.9



TEST NUMBER: P331448-927

CATALOG NUMBER: SA2XXDIP-C1005D925U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	272.0	272.4	272.7	273.1	273.5	273.9	274.3	274.7	275.2	275.6	275.8
115°	316.2	316.7	317.3	317.8	318.3	318.7	318.9	319.0	319.2	319.4	319.7
117.5°	358.5	358.9	359.5	360.0	360.5	361.0	361.5	361.9	362.3	362.7	363.7
120°	388.2	388.7	389.2	389.8	390.3	390.5	390.5	390.5	390.5	390.5	392.0
122.5°	417.2	417.6	418.0	418.4	418.8	419.2	419.6	420.0	420.5	420.9	421.9
125°	461.7	461.8	462.0	462.2	462.4	462.7	463.3	463.8	464.3	464.9	465.4
127.5°	502.2	502.7	503.3	503.8	504.4	505.0	505.6	506.3	506.9	507.6	508.2
130°	531.2	532.0	532.7	533.4	534.1	534.6	535.0	535.3	535.7	536.0	536.4
132.5°	559.1	559.7	560.2	560.8	561.3	562.0	562.8	563.6	564.4	565.1	565.0
135°	602.4	602.9	603.5	604.0	604.5	604.8	605.1	605.2	605.4	605.5	605.2
137.5°	641.6	642.3	643.0	643.7	644.4	644.8	645.0	645.2	645.3	645.4	645.0
140°	668.8	669.6	670.2	670.9	671.6	672.0	672.0	672.0	672.0	672.0	671.1
142.5°	693.5	694.2	694.9	695.6	696.3	696.6	696.4	696.3	696.2	696.0	695.4
145°	730.5	731.2	731.9	732.6	733.3	733.6	733.4	733.2	733.0	732.8	731.8
147.5°	763.5	764.2	764.9	765.6	766.2	766.4	766.0	765.6	765.2	764.8	764.1
150°	785.1	785.5	786.1	786.6	787.1	787.1	786.6	786.1	785.5	785.1	784.3
152.5°	805.3	806.0	806.6	807.2	807.9	807.9	807.2	806.6	806.0	805.3	804.4
155°	832.4	833.0	833.5	834.0	834.6	834.4	833.5	832.7	831.8	830.8	830.4
157.5°	855.9	856.7	857.5	858.4	859.2	859.0	857.9	856.7	855.5	854.3	854.0
160°	870.4	871.1	871.8	872.5	873.2	873.1	872.0	870.9	869.9	868.8	868.6
162.5°	883.0	883.9	884.7	885.6	886.5	886.2	885.0	883.8	882.6	881.5	881.3
165°	899.7	900.6	901.4	902.3	903.2	903.0	901.7	900.6	899.3	898.1	898.1
167.5°	913.2	914.2	915.0	916.0	916.9	916.7	915.5	914.3	913.1	911.8	911.9
170°	920.2	921.2	922.3	923.4	924.4	924.3	923.1	921.9	920.7	919.4	919.6
172.5°	925.9	926.9	928.0	929.1	930.1	930.0	928.8	927.6	926.4	925.1	925.3
175°	932.1	933.1	934.1	935.3	936.3	936.2	934.9	933.7	932.5	931.3	931.6
177.5°	934.9	935.7	936.6	937.5	938.3	938.3	937.5	936.6	935.7	934.9	935.2
180°	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8



TEST NUMBER: P331448-927

CATALOG NUMBER: SA2XXDIP-C1005D925U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6
2.5°	1621.0	1617.1	1614.6	1605.9	1598.1	1590.3	1587.9	1588.9	1578.2	1568.0	1563.6
5°	1684.1	1671.9	1660.4	1644.0	1624.6	1603.3	1592.4	1583.9	1562.7	1539.6	1526.2
7.5°	1740.7	1723.3	1701.1	1670.2	1642.0	1608.5	1587.3	1568.4	1537.4	1504.8	1484.9
10°	1775.1	1751.4	1722.9	1685.3	1650.7	1610.0	1581.4	1552.9	1516.5	1477.7	1453.3
12.5°	1804.7	1772.8	1744.8	1696.5	1655.5	1604.6	1570.8	1530.6	1492.2	1446.0	1422.3
15°	1875.3	1816.4	1763.0	1708.3	1658.0	1586.9	1549.3	1495.2	1444.9	1387.8	1360.5
17.5°	1929.8	1863.6	1779.5	1710.1	1651.3	1572.6	1517.3	1452.6	1393.1	1327.9	1290.7
20°	1960.9	1885.0	1794.5	1712.0	1641.6	1551.7	1491.6	1425.5	1355.7	1282.1	1242.1
22.5°	1979.3	1899.6	1810.1	1704.7	1622.2	1534.7	1459.0	1386.6	1315.8	1236.5	1194.5
25°	1985.2	1912.3	1817.7	1698.7	1597.8	1498.9	1407.9	1337.4	1251.8	1177.7	1116.4
27.5°	1956.3	1904.1	1813.0	1687.2	1569.8	1454.1	1352.6	1272.8	1182.5	1102.1	1040.5
30°	1920.8	1890.5	1801.8	1675.5	1547.4	1423.0	1311.3	1220.8	1131.0	1049.6	986.5
32.5°	1866.0	1859.4	1781.5	1659.1	1523.7	1383.7	1268.1	1176.6	1077.1	997.2	937.0
35°	1758.2	1787.2	1738.1	1622.2	1478.8	1327.7	1202.6	1098.2	995.1	918.5	862.1
37.5°	1613.7	1686.0	1673.2	1568.1	1418.4	1266.8	1128.7	1019.5	921.2	844.0	788.6
40°	1514.1	1606.4	1619.7	1526.9	1375.7	1219.6	1073.3	964.6	868.7	798.4	742.4
42.5°	1407.2	1515.0	1551.7	1477.3	1329.0	1170.1	1023.8	911.2	816.3	747.8	698.3
45°	1228.1	1370.8	1437.0	1394.5	1251.3	1088.5	937.9	823.8	737.6	673.3	635.0
47.5°	1060.7	1216.6	1305.6	1290.5	1164.7	1003.5	854.7	745.1	661.2	609.9	575.7
50°	942.2	1102.5	1209.9	1214.8	1102.5	942.8	793.4	690.2	613.1	565.2	537.3
52.5°	839.2	992.2	1109.4	1135.1	1033.0	879.6	738.6	635.9	568.0	523.9	498.9
55°	704.8	834.2	964.1	1011.4	929.5	783.8	653.2	562.8	499.0	468.7	446.8
57.5°	586.0	693.8	813.7	866.1	815.6	690.9	568.5	489.9	438.2	411.6	394.8
60°	523.3	608.3	715.2	777.7	734.0	622.9	516.0	441.3	398.9	375.2	359.4
62.5°	465.0	540.3	630.7	687.9	664.0	559.3	463.6	397.7	361.0	338.7	327.3
65°	383.7	443.1	513.0	565.8	550.0	470.5	392.2	335.7	306.6	289.0	279.9
67.5°	315.9	358.9	407.3	453.6	440.8	384.5	321.6	277.7	256.0	240.7	235.3
70°	273.2	305.9	349.1	386.1	375.8	329.6	279.9	242.2	223.4	210.6	205.2
72.5°	232.4	259.4	292.2	322.5	315.5	277.2	235.7	207.2	192.8	181.0	176.6
75°	175.5	196.1	216.1	236.1	234.3	204.6	180.3	158.4	146.9	137.8	136.0
77.5°	129.5	141.1	154.7	166.6	163.3	146.3	127.2	114.7	106.2	100.1	99.2
80°	98.9	105.6	115.3	123.8	119.6	112.3	97.1	88.0	82.0	75.9	73.4
82.5°	71.8	78.4	84.3	88.9	85.6	78.8	69.5	63.3	59.7	55.5	54.5
85°	37.6	41.3	43.7	44.9	43.7	39.5	35.2	32.8	29.8	28.0	27.3
87.5°	18.5	17.8	17.0	17.3	15.5	15.1	12.8	10.9	10.8	10.7	10.1
90°	20.0	16.1	12.2	9.2	7.1	5.0	2.9	0.8	2.9	5.0	7.1
92.5°	23.3	22.4	21.5	20.3	18.7	17.2	15.6	14.1	15.6	17.2	18.7
95°	49.9	49.5	49.2	48.2	46.3	44.6	42.9	41.1	42.9	44.6	46.3
97.5°	83.7	83.1	82.4	81.3	79.8	78.2	76.7	75.1	76.7	78.2	79.8
100°	108.1	107.5	107.0	106.0	104.6	103.2	101.8	100.4	101.8	103.2	104.6
102.5°	133.7	133.0	132.4	131.4	130.3	129.2	128.1	127.0	128.1	129.2	130.3
105°	173.3	172.9	172.5	172.1	171.6	171.0	170.5	170.0	170.5	171.0	171.6
107.5°	216.7	216.7	216.7	216.4	215.6	214.8	214.0	213.3	214.0	214.8	215.6
110°	245.9	245.9	245.9	245.3	244.3	243.2	242.2	241.1	242.2	243.2	244.3



TEST NUMBER: P331448-927

CATALOG NUMBER: SA2XXDIP-C1005D925U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	275.8	276.0	276.2	275.7	274.6	273.6	272.5	271.5	272.5	273.6	274.6
115°	320.1	320.4	320.8	320.4	319.4	318.3	317.3	316.2	317.3	318.3	319.4
117.5°	364.6	365.7	366.6	366.5	365.0	363.6	362.2	360.8	362.2	363.6	365.0
120°	393.3	394.7	396.2	396.2	394.7	393.3	392.0	390.5	392.0	393.3	394.7
122.5°	422.9	423.8	424.8	424.5	422.8	421.1	419.4	417.7	419.4	421.1	422.8
125°	465.9	466.4	467.0	466.4	464.9	463.3	461.7	460.1	461.7	463.3	464.9
127.5°	508.8	509.5	510.1	509.4	507.4	505.4	503.4	501.4	503.4	505.4	507.4
130°	536.7	537.0	537.4	536.5	534.2	531.9	529.6	527.3	529.6	531.9	534.2
132.5°	565.0	564.9	564.8	563.9	562.0	560.2	558.3	556.4	558.3	560.2	562.0
135°	604.8	604.5	604.2	603.0	601.1	599.1	597.2	595.3	597.2	599.1	601.1
137.5°	644.5	644.0	643.6	642.5	641.0	639.4	637.8	636.3	637.8	639.4	641.0
140°	670.2	669.3	668.4	667.3	665.7	664.1	662.5	660.9	662.5	664.1	665.7
142.5°	694.8	694.2	693.6	692.5	690.9	689.4	687.8	686.2	687.8	689.4	690.9
145°	730.7	729.7	728.6	727.5	726.3	725.0	723.8	722.5	723.8	725.0	726.3
147.5°	763.3	762.7	762.0	760.9	759.4	758.0	756.5	754.9	756.5	758.0	759.4
150°	783.6	782.9	782.2	781.3	780.3	779.2	778.2	777.1	778.2	779.2	780.3
152.5°	803.6	802.7	801.9	801.0	799.9	798.8	797.8	796.7	797.8	798.8	799.9
155°	829.8	829.3	828.8	828.2	827.8	827.2	826.6	826.2	826.6	827.2	827.8
157.5°	853.7	853.3	853.0	852.7	852.3	852.0	851.6	851.3	851.6	852.0	852.3
160°	868.5	868.3	868.2	867.8	867.5	867.1	866.8	866.5	866.8	867.1	867.5
162.5°	881.1	881.0	880.7	880.7	880.6	880.5	880.4	880.4	880.4	880.5	880.6
165°	898.1	898.1	898.1	898.2	898.3	898.5	898.7	898.9	898.7	898.5	898.3
167.5°	911.9	912.0	912.0	912.3	912.8	913.3	913.9	914.3	913.9	913.3	912.8
170°	919.8	920.0	920.1	920.4	921.0	921.5	922.0	922.6	922.0	921.5	921.0
172.5°	925.4	925.7	925.8	926.1	926.7	927.2	927.7	928.3	927.7	927.2	926.7
175°	932.0	932.3	932.7	933.1	933.7	934.1	934.7	935.3	934.7	934.1	933.7
177.5°	935.5	935.7	936.0	936.4	936.8	937.2	937.6	938.1	937.6	937.2	936.8
180°	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8



TEST NUMBER: P331448-927

CATALOG NUMBER: SA2XXDIP-C1005D925U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6
2.5°	1558.8	1555.8	1545.6	1540.3	1531.6	1523.3	1518.0	1520.4	1522.3	1521.4	1519.9
5°	1514.1	1502.5	1484.9	1469.7	1458.8	1438.8	1430.3	1426.1	1422.4	1418.2	1413.9
7.5°	1460.9	1442.7	1417.5	1395.8	1375.4	1350.5	1336.3	1327.9	1319.1	1309.5	1301.0
10°	1423.0	1397.5	1370.8	1340.5	1316.2	1293.7	1273.7	1260.3	1248.2	1236.7	1228.1
12.5°	1383.2	1353.8	1320.8	1279.3	1252.5	1220.4	1217.3	1193.8	1174.8	1167.7	1157.7
15°	1319.8	1278.5	1236.7	1187.5	1166.3	1137.1	1118.9	1100.7	1084.3	1072.7	1069.7
17.5°	1247.8	1194.4	1152.7	1117.4	1082.6	1052.7	1035.9	1021.4	1007.9	992.4	990.4
20°	1192.9	1146.8	1101.3	1070.3	1034.5	1004.1	983.5	968.9	957.4	948.2	940.4
22.5°	1141.0	1090.4	1048.8	1014.9	979.6	955.1	938.8	924.7	915.1	905.1	897.6
25°	1057.6	1018.1	972.6	934.3	905.1	889.4	876.0	863.9	857.9	851.1	842.6
27.5°	984.6	940.7	898.1	868.5	842.9	828.9	819.4	811.2	805.5	801.6	796.8
30°	933.1	888.7	855.4	826.2	805.0	791.1	785.0	780.1	773.4	771.0	768.6
32.5°	883.5	843.6	815.1	789.8	769.5	760.4	754.9	750.5	745.3	742.8	738.0
35°	813.5	780.1	752.2	738.2	721.8	713.9	709.7	703.6	698.8	696.3	695.7
37.5°	747.6	718.6	700.2	682.2	675.3	670.5	664.6	660.5	659.1	658.7	658.1
40°	704.8	681.1	664.8	650.2	647.1	639.8	635.0	631.4	631.4	632.0	631.4
42.5°	666.0	644.8	630.3	617.7	614.1	609.7	604.9	604.7	605.6	607.7	605.6
45°	607.1	591.9	581.6	575.5	568.9	564.6	564.0	565.8	566.4	567.0	568.9
47.5°	552.9	542.9	533.5	526.8	523.9	523.2	522.4	525.6	528.5	529.7	532.4
50°	520.9	509.4	501.5	497.2	494.8	493.5	494.8	498.4	500.8	503.9	505.7
52.5°	485.0	476.8	471.3	468.1	467.1	467.9	468.1	472.2	476.1	477.2	478.0
55°	435.3	429.2	428.0	422.6	424.9	424.4	427.4	429.8	433.5	437.1	437.7
57.5°	385.7	380.9	377.6	378.1	378.8	381.5	384.0	388.3	392.2	396.1	396.4
60°	352.8	350.3	348.5	348.5	349.7	353.3	356.3	360.6	363.1	365.4	367.3
62.5°	322.6	320.2	318.4	319.3	322.5	324.6	328.2	330.5	333.0	335.3	336.2
65°	275.0	273.8	275.6	276.9	277.4	280.5	284.7	286.5	289.0	290.2	294.5
67.5°	231.2	231.4	231.2	232.9	236.4	237.1	241.1	245.4	245.9	248.2	251.0
70°	201.5	202.8	204.0	205.2	208.3	209.5	212.5	214.3	216.7	218.6	220.4
72.5°	174.4	174.6	175.8	175.5	178.1	180.8	183.3	185.1	187.6	189.9	191.7
75°	134.2	134.2	135.4	136.0	139.0	142.0	141.5	142.7	145.1	147.5	148.8
77.5°	98.0	96.6	98.0	98.6	99.6	102.1	102.6	104.3	107.1	106.2	107.6
80°	74.7	72.9	74.7	75.3	75.3	78.3	78.3	79.5	81.4	79.5	81.4
82.5°	53.3	52.4	53.8	53.9	54.9	55.0	56.0	56.2	58.1	57.2	58.1
85°	26.7	26.1	26.7	26.1	26.7	27.3	27.3	26.7	26.7	28.0	26.1
87.5°	10.1	10.2	10.5	11.2	11.6	11.9	11.3	11.2	11.2	10.1	10.1
90°	9.2	12.2	16.1	20.0	23.8	27.6	27.3	26.9	26.6	26.3	26.1
92.5°	20.3	21.5	22.4	23.3	24.2	25.1	25.2	25.3	25.3	25.4	25.5
95°	48.2	49.2	49.5	49.9	50.2	50.6	50.6	50.6	50.6	50.6	50.4
97.5°	81.3	82.4	83.1	83.7	84.4	85.1	85.1	85.1	85.1	85.1	85.1
100°	106.0	107.0	107.5	108.1	108.6	109.1	109.1	109.1	109.1	109.1	109.0
102.5°	131.4	132.4	133.0	133.7	134.4	135.1	135.1	135.3	135.5	135.6	135.5
105°	172.1	172.5	172.9	173.3	173.6	173.9	174.3	174.6	175.0	175.3	175.5
107.5°	216.4	216.7	216.7	216.7	216.7	216.7	216.9	217.1	217.2	217.3	217.0
110°	245.3	245.9	245.9	245.9	245.9	245.9	245.9	245.9	245.9	245.9	245.6



TEST NUMBER: P331448-927

CATALOG NUMBER: SA2XXDIP-C1005D925U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	275.7	276.2	276.0	275.8	275.8	275.6	275.2	274.7	274.3	273.9	273.5
115°	320.4	320.8	320.4	320.1	319.7	319.4	319.2	319.0	318.9	318.7	318.3
117.5°	366.5	366.6	365.7	364.6	363.7	362.7	362.3	361.9	361.5	361.0	360.5
120°	396.2	396.2	394.7	393.3	392.0	390.5	390.5	390.5	390.5	390.5	390.3
122.5°	424.5	424.8	423.8	422.9	421.9	420.9	420.5	420.0	419.6	419.2	418.8
125°	466.4	467.0	466.4	465.9	465.4	464.9	464.3	463.8	463.3	462.7	462.4
127.5°	509.4	510.1	509.5	508.8	508.2	507.6	506.9	506.3	505.6	505.0	504.4
130°	536.5	537.4	537.0	536.7	536.4	536.0	535.7	535.3	535.0	534.6	534.1
132.5°	563.9	564.8	564.9	565.0	565.0	565.1	564.4	563.6	562.8	562.0	561.3
135°	603.0	604.2	604.5	604.8	605.2	605.5	605.4	605.2	605.1	604.8	604.5
137.5°	642.5	643.6	644.0	644.5	645.0	645.4	645.3	645.2	645.0	644.8	644.4
140°	667.3	668.4	669.3	670.2	671.1	672.0	672.0	672.0	672.0	672.0	671.6
142.5°	692.5	693.6	694.2	694.8	695.4	696.0	696.2	696.3	696.4	696.6	696.3
145°	727.5	728.6	729.7	730.7	731.8	732.8	733.0	733.2	733.4	733.6	733.3
147.5°	760.9	762.0	762.7	763.3	764.1	764.8	765.2	765.6	766.0	766.4	766.2
150°	781.3	782.2	782.9	783.6	784.3	785.1	785.5	786.1	786.6	787.1	787.1
152.5°	801.0	801.9	802.7	803.6	804.4	805.3	806.0	806.6	807.2	807.9	807.9
155°	828.2	828.8	829.3	829.8	830.4	830.8	831.8	832.7	833.5	834.4	834.6
157.5°	852.7	853.0	853.3	853.7	854.0	854.3	855.5	856.7	857.9	859.0	859.2
160°	867.8	868.2	868.3	868.5	868.6	868.8	869.9	870.9	872.0	873.1	873.2
162.5°	880.7	880.7	881.0	881.1	881.3	881.5	882.6	883.8	885.0	886.2	886.5
165°	898.2	898.1	898.1	898.1	898.1	898.1	899.3	900.6	901.7	903.0	903.2
167.5°	912.3	912.0	912.0	911.9	911.9	911.8	913.1	914.3	915.5	916.7	916.9
170°	920.4	920.1	920.0	919.8	919.6	919.4	920.7	921.9	923.1	924.3	924.4
172.5°	926.1	925.8	925.7	925.4	925.3	925.1	926.4	927.6	928.8	930.0	930.1
175°	933.1	932.7	932.3	932.0	931.6	931.3	932.5	933.7	934.9	936.2	936.3
177.5°	936.4	936.0	935.7	935.5	935.2	934.9	935.7	936.6	937.5	938.3	938.3
180°	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8



TEST NUMBER: P331448-927

CATALOG NUMBER: SA2XXDIP-C1005D925U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6
2.5°	1515.0	1514.1	1514.1	1509.7	1514.1	1514.1	1515.0	1519.9	1521.4	1522.3	1520.4
5°	1405.4	1403.6	1400.6	1403.6	1400.6	1403.6	1405.4	1413.9	1418.2	1422.4	1426.1
7.5°	1297.0	1289.7	1288.6	1281.4	1288.6	1289.7	1297.0	1301.0	1309.5	1319.1	1327.9
10°	1217.8	1213.0	1212.4	1200.8	1212.4	1213.0	1217.8	1228.1	1236.7	1248.2	1260.3
12.5°	1157.6	1146.0	1148.3	1141.5	1148.3	1146.0	1157.6	1157.7	1167.7	1174.8	1193.8
15°	1053.3	1053.3	1050.9	1040.5	1050.9	1053.3	1053.3	1069.7	1072.7	1084.3	1100.7
17.5°	978.4	977.2	971.4	974.2	971.4	977.2	978.4	990.4	992.4	1007.9	1021.4
20°	933.7	930.1	922.8	922.8	922.8	930.1	933.7	940.4	948.2	957.4	968.9
22.5°	891.4	891.2	883.4	885.9	883.4	891.2	891.4	897.6	905.1	915.1	924.7
25°	842.0	837.2	833.5	835.4	833.5	837.2	842.0	842.6	851.1	857.9	863.9
27.5°	795.2	792.5	792.3	787.3	792.3	792.5	795.2	796.8	801.6	805.5	811.2
30°	767.9	761.9	763.1	760.1	763.1	761.9	767.9	768.6	771.0	773.4	780.1
32.5°	736.9	734.7	733.5	730.9	733.5	734.7	736.9	738.0	742.8	745.3	750.5
35°	694.5	695.1	692.1	693.3	692.1	695.1	694.5	695.7	696.3	698.8	703.6
37.5°	657.5	659.4	658.0	658.3	658.0	659.4	657.5	658.1	658.7	659.1	660.5
40°	633.2	633.2	633.2	635.0	633.2	633.2	633.2	631.4	632.0	631.4	631.4
42.5°	609.9	609.0	607.9	607.8	607.9	609.0	609.9	605.6	607.7	605.6	604.7
45°	570.1	571.9	572.5	569.4	572.5	571.9	570.1	568.9	567.0	566.4	565.8
47.5°	534.0	534.2	534.0	536.7	534.0	534.2	534.0	532.4	529.7	528.5	525.6
50°	508.7	507.6	508.7	507.6	508.7	507.6	508.7	505.7	503.9	500.8	498.4
52.5°	482.0	482.3	481.6	481.3	481.6	482.3	482.0	478.0	477.2	476.1	472.2
55°	440.1	441.3	440.8	440.8	440.8	441.3	440.1	437.7	437.1	433.5	429.8
57.5°	396.8	397.9	398.7	396.1	398.7	397.9	396.8	396.4	396.1	392.2	388.3
60°	366.7	369.7	369.1	367.9	369.1	369.7	366.7	367.3	365.4	363.1	360.6
62.5°	339.0	340.1	340.0	339.8	340.0	340.1	339.0	336.2	335.3	333.0	330.5
65°	296.3	297.5	295.6	297.5	295.6	297.5	296.3	294.5	290.2	289.0	286.5
67.5°	250.3	250.6	251.9	252.8	251.9	250.6	250.3	251.0	248.2	245.9	245.4
70°	221.6	221.0	222.8	224.7	222.8	221.0	221.6	220.4	218.6	216.7	214.3
72.5°	191.5	192.8	192.2	193.5	192.2	192.8	191.5	191.7	189.9	187.6	185.1
75°	147.5	149.3	148.8	150.6	148.8	149.3	147.5	148.8	147.5	145.1	142.7
77.5°	106.6	106.9	106.6	107.6	106.6	106.9	106.6	107.6	106.2	107.1	104.3
80°	81.4	80.2	78.9	81.4	78.9	80.2	81.4	81.4	79.5	81.4	79.5
82.5°	56.6	57.3	56.1	56.1	56.1	57.3	56.6	58.1	57.2	58.1	56.2
85°	26.1	25.5	24.3	24.3	24.3	25.5	26.1	26.1	28.0	26.7	26.7
87.5°	10.1	9.7	9.7	9.3	9.7	9.7	10.1	10.1	10.1	11.2	11.2
90°	26.4	26.5	26.7	26.9	26.7	26.5	26.4	26.1	26.3	26.6	26.9
92.5°	25.5	25.5	25.6	25.6	25.6	25.5	25.5	25.5	25.4	25.3	25.3
95°	50.1	49.7	49.4	49.0	49.4	49.7	50.1	50.4	50.6	50.6	50.6
97.5°	85.0	85.0	84.9	84.9	84.9	85.0	85.0	85.1	85.1	85.1	85.1
100°	108.8	108.7	108.4	108.3	108.4	108.7	108.8	109.0	109.1	109.1	109.1
102.5°	135.4	135.2	135.1	134.9	135.1	135.2	135.4	135.5	135.6	135.5	135.3
105°	175.5	175.5	175.5	175.5	175.5	175.5	175.5	175.5	175.3	175.0	174.6
107.5°	216.2	215.4	214.6	213.7	214.6	215.4	216.2	217.0	217.3	217.2	217.1
110°	245.1	244.5	244.0	243.5	244.0	244.5	245.1	245.6	245.9	245.9	245.9



TEST NUMBER: P331448-927

CATALOG NUMBER: SA2XXDIP-C1005D925U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	273.1	272.7	272.4	272.0	272.4	272.7	273.1	273.5	273.9	274.3	274.7
115°	317.8	317.3	316.7	316.2	316.7	317.3	317.8	318.3	318.7	318.9	319.0
117.5°	360.0	359.5	358.9	358.5	358.9	359.5	360.0	360.5	361.0	361.5	361.9
120°	389.8	389.2	388.7	388.2	388.7	389.2	389.8	390.3	390.5	390.5	390.5
122.5°	418.4	418.0	417.6	417.2	417.6	418.0	418.4	418.8	419.2	419.6	420.0
125°	462.2	462.0	461.8	461.7	461.8	462.0	462.2	462.4	462.7	463.3	463.8
127.5°	503.8	503.3	502.7	502.2	502.7	503.3	503.8	504.4	505.0	505.6	506.3
130°	533.4	532.7	532.0	531.2	532.0	532.7	533.4	534.1	534.6	535.0	535.3
132.5°	560.8	560.2	559.7	559.1	559.7	560.2	560.8	561.3	562.0	562.8	563.6
135°	604.0	603.5	602.9	602.4	602.9	603.5	604.0	604.5	604.8	605.1	605.2
137.5°	643.7	643.0	642.3	641.6	642.3	643.0	643.7	644.4	644.8	645.0	645.2
140°	670.9	670.2	669.6	668.8	669.6	670.2	670.9	671.6	672.0	672.0	672.0
142.5°	695.6	694.9	694.2	693.5	694.2	694.9	695.6	696.3	696.6	696.4	696.3
145°	732.6	731.9	731.2	730.5	731.2	731.9	732.6	733.3	733.6	733.4	733.2
147.5°	765.6	764.9	764.2	763.5	764.2	764.9	765.6	766.2	766.4	766.0	765.6
150°	786.6	786.1	785.5	785.1	785.5	786.1	786.6	787.1	787.1	786.6	786.1
152.5°	807.2	806.6	806.0	805.3	806.0	806.6	807.2	807.9	807.9	807.2	806.6
155°	834.0	833.5	833.0	832.4	833.0	833.5	834.0	834.6	834.4	833.5	832.7
157.5°	858.4	857.5	856.7	855.9	856.7	857.5	858.4	859.2	859.0	857.9	856.7
160°	872.5	871.8	871.1	870.4	871.1	871.8	872.5	873.2	873.1	872.0	870.9
162.5°	885.6	884.7	883.9	883.0	883.9	884.7	885.6	886.5	886.2	885.0	883.8
165°	902.3	901.4	900.6	899.7	900.6	901.4	902.3	903.2	903.0	901.7	900.6
167.5°	916.0	915.0	914.2	913.2	914.2	915.0	916.0	916.9	916.7	915.5	914.3
170°	923.4	922.3	921.2	920.2	921.2	922.3	923.4	924.4	924.3	923.1	921.9
172.5°	929.1	928.0	926.9	925.9	926.9	928.0	929.1	930.1	930.0	928.8	927.6
175°	935.3	934.1	933.1	932.1	933.1	934.1	935.3	936.3	936.2	934.9	933.7
177.5°	937.5	936.6	935.7	934.9	935.7	936.6	937.5	938.3	938.3	937.5	936.6
180°	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8



TEST NUMBER: P331448-927

CATALOG NUMBER: SA2XXDIP-C1005D925U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6
2.5°	1518.0	1523.3	1531.6	1540.3	1545.6	1555.8	1558.8	1563.6	1568.0	1578.2	1588.9
5°	1430.3	1438.8	1458.8	1469.7	1484.9	1502.5	1514.1	1526.2	1539.6	1562.7	1583.9
7.5°	1336.3	1350.5	1375.4	1395.8	1417.5	1442.7	1460.9	1484.9	1504.8	1537.4	1568.4
10°	1273.7	1293.7	1316.2	1340.5	1370.8	1397.5	1423.0	1453.3	1477.7	1516.5	1552.9
12.5°	1217.3	1220.4	1252.5	1279.3	1320.8	1353.8	1383.2	1422.3	1446.0	1492.2	1530.6
15°	1118.9	1137.1	1166.3	1187.5	1236.7	1278.5	1319.8	1360.5	1387.8	1444.9	1495.2
17.5°	1035.9	1052.7	1082.6	1117.4	1152.7	1194.4	1247.8	1290.7	1327.9	1393.1	1452.6
20°	983.5	1004.1	1034.5	1070.3	1101.3	1146.8	1192.9	1242.1	1282.1	1355.7	1425.5
22.5°	938.8	955.1	979.6	1014.9	1048.8	1090.4	1141.0	1194.5	1236.5	1315.8	1386.6
25°	876.0	889.4	905.1	934.3	972.6	1018.1	1057.6	1116.4	1177.7	1251.8	1337.4
27.5°	819.4	828.9	842.9	868.5	898.1	940.7	984.6	1040.5	1102.1	1182.5	1272.8
30°	785.0	791.1	805.0	826.2	855.4	888.7	933.1	986.5	1049.6	1131.0	1220.8
32.5°	754.9	760.4	769.5	789.8	815.1	843.6	883.5	937.0	997.2	1077.1	1176.6
35°	709.7	713.9	721.8	738.2	752.2	780.1	813.5	862.1	918.5	995.1	1098.2
37.5°	664.6	670.5	675.3	682.2	700.2	718.6	747.6	788.6	844.0	921.2	1019.5
40°	635.0	639.8	647.1	650.2	664.8	681.1	704.8	742.4	798.4	868.7	964.6
42.5°	604.9	609.7	614.1	617.7	630.3	644.8	666.0	698.3	747.8	816.3	911.2
45°	564.0	564.6	568.9	575.5	581.6	591.9	607.1	635.0	673.3	737.6	823.8
47.5°	522.4	523.2	523.9	526.8	533.5	542.9	552.9	575.7	609.9	661.2	745.1
50°	494.8	493.5	494.8	497.2	501.5	509.4	520.9	537.3	565.2	613.1	690.2
52.5°	468.1	467.9	467.1	468.1	471.3	476.8	485.0	498.9	523.9	568.0	635.9
55°	427.4	424.4	424.9	422.6	428.0	429.2	435.3	446.8	468.7	499.0	562.8
57.5°	384.0	381.5	378.8	378.1	377.6	380.9	385.7	394.8	411.6	438.2	489.9
60°	356.3	353.3	349.7	348.5	348.5	350.3	352.8	359.4	375.2	398.9	441.3
62.5°	328.2	324.6	322.5	319.3	318.4	320.2	322.6	327.3	338.7	361.0	397.7
65°	284.7	280.5	277.4	276.9	275.6	273.8	275.0	279.9	289.0	306.6	335.7
67.5°	241.1	237.1	236.4	232.9	231.2	231.4	231.2	235.3	240.7	256.0	277.7
70°	212.5	209.5	208.3	205.2	204.0	202.8	201.5	205.2	210.6	223.4	242.2
72.5°	183.3	180.8	178.1	175.5	175.8	174.6	174.4	176.6	181.0	192.8	207.2
75°	141.5	142.0	139.0	136.0	135.4	134.2	134.2	136.0	137.8	146.9	158.4
77.5°	102.6	102.1	99.6	98.6	98.0	96.6	98.0	99.2	100.1	106.2	114.7
80°	78.3	78.3	75.3	75.3	74.7	72.9	74.7	73.4	75.9	82.0	88.0
82.5°	56.0	55.0	54.9	53.9	53.8	52.4	53.3	54.5	55.5	59.7	63.3
85°	27.3	27.3	26.7	26.1	26.7	26.1	26.7	27.3	28.0	29.8	32.8
87.5°	11.3	11.9	11.6	11.2	10.5	10.2	10.1	10.1	10.7	10.8	10.9
90°	27.3	27.6	23.8	20.0	16.1	12.2	9.2	7.1	5.0	2.9	0.8
92.5°	25.2	25.1	24.2	23.3	22.4	21.5	20.3	18.7	17.2	15.6	14.1
95°	50.6	50.6	50.2	49.9	49.5	49.2	48.2	46.3	44.6	42.9	41.1
97.5°	85.1	85.1	84.4	83.7	83.1	82.4	81.3	79.8	78.2	76.7	75.1
100°	109.1	109.1	108.6	108.1	107.5	107.0	106.0	104.6	103.2	101.8	100.4
102.5°	135.1	135.1	134.4	133.7	133.0	132.4	131.4	130.3	129.2	128.1	127.0
105°	174.3	173.9	173.6	173.3	172.9	172.5	172.1	171.6	171.0	170.5	170.0
107.5°	216.9	216.7	216.7	216.7	216.7	216.7	216.4	215.6	214.8	214.0	213.3
110°	245.9	245.9	245.9	245.9	245.9	245.9	245.3	244.3	243.2	242.2	241.1



TEST NUMBER: P331448-927

CATALOG NUMBER: SA2XXDIP-C1005D925U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	275.2	275.6	275.8	275.8	276.0	276.2	275.7	274.6	273.6	272.5	271.5
115°	319.2	319.4	319.7	320.1	320.4	320.8	320.4	319.4	318.3	317.3	316.2
117.5°	362.3	362.7	363.7	364.6	365.7	366.6	366.5	365.0	363.6	362.2	360.8
120°	390.5	390.5	392.0	393.3	394.7	396.2	396.2	394.7	393.3	392.0	390.5
122.5°	420.5	420.9	421.9	422.9	423.8	424.8	424.5	422.8	421.1	419.4	417.7
125°	464.3	464.9	465.4	465.9	466.4	467.0	466.4	464.9	463.3	461.7	460.1
127.5°	506.9	507.6	508.2	508.8	509.5	510.1	509.4	507.4	505.4	503.4	501.4
130°	535.7	536.0	536.4	536.7	537.0	537.4	536.5	534.2	531.9	529.6	527.3
132.5°	564.4	565.1	565.0	565.0	564.9	564.8	563.9	562.0	560.2	558.3	556.4
135°	605.4	605.5	605.2	604.8	604.5	604.2	603.0	601.1	599.1	597.2	595.3
137.5°	645.3	645.4	645.0	644.5	644.0	643.6	642.5	641.0	639.4	637.8	636.3
140°	672.0	672.0	671.1	670.2	669.3	668.4	667.3	665.7	664.1	662.5	660.9
142.5°	696.2	696.0	695.4	694.8	694.2	693.6	692.5	690.9	689.4	687.8	686.2
145°	733.0	732.8	731.8	730.7	729.7	728.6	727.5	726.3	725.0	723.8	722.5
147.5°	765.2	764.8	764.1	763.3	762.7	762.0	760.9	759.4	758.0	756.5	754.9
150°	785.5	785.1	784.3	783.6	782.9	782.2	781.3	780.3	779.2	778.2	777.1
152.5°	806.0	805.3	804.4	803.6	802.7	801.9	801.0	799.9	798.8	797.8	796.7
155°	831.8	830.8	830.4	829.8	829.3	828.8	828.2	827.8	827.2	826.6	826.2
157.5°	855.5	854.3	854.0	853.7	853.3	853.0	852.7	852.3	852.0	851.6	851.3
160°	869.9	868.8	868.6	868.5	868.3	868.2	867.8	867.5	867.1	866.8	866.5
162.5°	882.6	881.5	881.3	881.1	881.0	880.7	880.7	880.6	880.5	880.4	880.4
165°	899.3	898.1	898.1	898.1	898.1	898.1	898.2	898.3	898.5	898.7	898.9
167.5°	913.1	911.8	911.9	911.9	912.0	912.0	912.3	912.8	913.3	913.9	914.3
170°	920.7	919.4	919.6	919.8	920.0	920.1	920.4	921.0	921.5	922.0	922.6
172.5°	926.4	925.1	925.3	925.4	925.7	925.8	926.1	926.7	927.2	927.7	928.3
175°	932.5	931.3	931.6	932.0	932.3	932.7	933.1	933.7	934.1	934.7	935.3
177.5°	935.7	934.9	935.2	935.5	935.7	936.0	936.4	936.8	937.2	937.6	938.1
180°	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8



TEST NUMBER: P331448-927

CATALOG NUMBER: SA2XXDIP-C1005D925U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6
2.5°	1587.9	1590.3	1598.1	1605.9	1614.6	1617.1	1621.0	1617.6	1616.5	1625.8	1632.6
5°	1592.4	1603.3	1624.6	1644.0	1660.4	1671.9	1684.1	1688.9	1698.0	1710.8	1726.6
7.5°	1587.3	1608.5	1642.0	1670.2	1701.1	1723.3	1740.7	1755.5	1773.5	1797.6	1823.9
10°	1581.4	1610.0	1650.7	1685.3	1722.9	1751.4	1775.1	1798.2	1825.0	1858.3	1892.9
12.5°	1570.8	1604.6	1655.5	1696.5	1744.8	1772.8	1804.7	1854.6	1883.2	1929.7	1978.4
15°	1549.3	1586.9	1658.0	1708.3	1763.0	1816.4	1875.3	1922.6	1970.0	1997.3	2065.9
17.5°	1517.3	1572.6	1651.3	1710.1	1779.5	1863.6	1929.8	1983.5	2038.1	2082.4	2116.8
20°	1491.6	1551.7	1641.6	1712.0	1794.5	1885.0	1960.9	2015.5	2062.9	2099.9	2121.1
22.5°	1459.0	1534.7	1622.2	1704.7	1810.1	1899.6	1979.3	2022.4	2061.9	2080.0	2088.1
25°	1407.9	1498.9	1597.8	1698.7	1817.7	1912.3	1985.2	2011.3	2022.8	2005.3	1976.1
27.5°	1352.6	1454.1	1569.8	1687.2	1813.0	1904.1	1956.3	1952.2	1932.6	1875.7	1830.1
30°	1311.3	1423.0	1547.4	1675.5	1801.8	1890.5	1920.8	1890.5	1846.2	1782.4	1717.5
32.5°	1268.1	1383.7	1523.7	1659.1	1781.5	1859.4	1866.0	1813.8	1745.2	1672.7	1591.7
35°	1202.6	1327.7	1478.8	1622.2	1738.1	1787.2	1758.2	1665.9	1584.5	1485.6	1375.1
37.5°	1128.7	1266.8	1418.4	1568.1	1673.2	1686.0	1613.7	1516.5	1401.8	1285.5	1155.4
40°	1073.3	1219.6	1375.7	1526.9	1619.7	1606.4	1514.1	1407.2	1270.7	1128.5	1007.7
42.5°	1023.8	1170.1	1329.0	1477.3	1551.7	1515.0	1407.2	1276.1	1129.3	995.5	884.9
45°	937.9	1088.5	1251.3	1394.5	1437.0	1370.8	1228.1	1082.4	937.9	826.2	738.9
47.5°	854.7	1003.5	1164.7	1290.5	1305.6	1216.6	1060.7	910.8	786.6	695.6	633.9
50°	793.4	942.8	1102.5	1214.8	1209.9	1102.5	942.2	799.5	695.7	622.3	581.0
52.5°	738.6	879.6	1033.0	1135.1	1109.4	992.2	839.2	712.6	627.2	569.8	532.4
55°	653.2	783.8	929.5	1011.4	964.1	834.2	704.8	602.9	539.7	496.6	467.5
57.5°	568.5	690.9	815.6	866.1	813.7	693.8	586.0	512.0	464.5	432.6	413.7
60°	516.0	622.9	734.0	777.7	715.2	608.3	523.3	457.2	418.9	392.8	375.8
62.5°	463.6	559.3	664.0	687.9	630.7	540.3	465.0	410.0	378.6	355.4	339.4
65°	392.2	470.5	550.0	565.8	513.0	443.1	383.7	347.8	320.0	302.9	290.2
67.5°	321.6	384.5	440.8	453.6	407.3	358.9	315.9	284.7	265.8	251.7	240.9
70°	279.9	329.6	375.8	386.1	349.1	305.9	273.2	248.3	231.3	219.2	208.8
72.5°	235.7	277.2	315.5	322.5	292.2	259.4	232.4	212.9	197.8	190.0	180.2
75°	180.3	204.6	234.3	236.1	216.1	196.1	175.5	162.7	154.8	145.1	140.2
77.5°	127.2	146.3	163.3	166.6	154.7	141.1	129.5	119.5	112.8	108.3	103.8
80°	97.1	112.3	119.6	123.8	115.3	105.6	98.9	92.3	88.0	85.0	82.0
82.5°	69.5	78.8	85.6	88.9	84.3	78.4	71.8	68.0	64.7	62.2	61.1
85°	35.2	39.5	43.7	44.9	43.7	41.3	37.6	37.6	35.8	35.2	35.2
87.5°	12.8	15.1	15.5	17.3	17.0	17.8	18.5	18.9	19.2	18.6	18.0
90°	2.9	5.0	7.1	9.2	12.2	16.1	20.0	23.8	27.6	27.3	26.9
92.5°	15.6	17.2	18.7	20.3	21.5	22.4	23.3	24.2	25.1	25.2	25.3
95°	42.9	44.6	46.3	48.2	49.2	49.5	49.9	50.2	50.6	50.6	50.6
97.5°	76.7	78.2	79.8	81.3	82.4	83.1	83.7	84.4	85.1	85.1	85.1
100°	101.8	103.2	104.6	106.0	107.0	107.5	108.1	108.6	109.1	109.1	109.1
102.5°	128.1	129.2	130.3	131.4	132.4	133.0	133.7	134.4	135.1	135.1	135.3
105°	170.5	171.0	171.6	172.1	172.5	172.9	173.3	173.6	173.9	174.3	174.6
107.5°	214.0	214.8	215.6	216.4	216.7	216.7	216.7	216.7	216.7	216.9	217.1
110°	242.2	243.2	244.3	245.3	245.9	245.9	245.9	245.9	245.9	245.9	245.9



TEST NUMBER: P331448-927

CATALOG NUMBER: SA2XXDIP-C1005D925U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	272.5	273.6	274.6	275.7	276.2	276.0	275.8	275.8	275.6	275.2	274.7
115°	317.3	318.3	319.4	320.4	320.8	320.4	320.1	319.7	319.4	319.2	319.0
117.5°	362.2	363.6	365.0	366.5	366.6	365.7	364.6	363.7	362.7	362.3	361.9
120°	392.0	393.3	394.7	396.2	396.2	394.7	393.3	392.0	390.5	390.5	390.5
122.5°	419.4	421.1	422.8	424.5	424.8	423.8	422.9	421.9	420.9	420.5	420.0
125°	461.7	463.3	464.9	466.4	467.0	466.4	465.9	465.4	464.9	464.3	463.8
127.5°	503.4	505.4	507.4	509.4	510.1	509.5	508.8	508.2	507.6	506.9	506.3
130°	529.6	531.9	534.2	536.5	537.4	537.0	536.7	536.4	536.0	535.7	535.3
132.5°	558.3	560.2	562.0	563.9	564.8	564.9	565.0	565.0	565.1	564.4	563.6
135°	597.2	599.1	601.1	603.0	604.2	604.5	604.8	605.2	605.5	605.4	605.2
137.5°	637.8	639.4	641.0	642.5	643.6	644.0	644.5	645.0	645.4	645.3	645.2
140°	662.5	664.1	665.7	667.3	668.4	669.3	670.2	671.1	672.0	672.0	672.0
142.5°	687.8	689.4	690.9	692.5	693.6	694.2	694.8	695.4	696.0	696.2	696.3
145°	723.8	725.0	726.3	727.5	728.6	729.7	730.7	731.8	732.8	733.0	733.2
147.5°	756.5	758.0	759.4	760.9	762.0	762.7	763.3	764.1	764.8	765.2	765.6
150°	778.2	779.2	780.3	781.3	782.2	782.9	783.6	784.3	785.1	785.5	786.1
152.5°	797.8	798.8	799.9	801.0	801.9	802.7	803.6	804.4	805.3	806.0	806.6
155°	826.6	827.2	827.8	828.2	828.8	829.3	829.8	830.4	830.8	831.8	832.7
157.5°	851.6	852.0	852.3	852.7	853.0	853.3	853.7	854.0	854.3	855.5	856.7
160°	866.8	867.1	867.5	867.8	868.2	868.3	868.5	868.6	868.8	869.9	870.9
162.5°	880.4	880.5	880.6	880.7	880.7	881.0	881.1	881.3	881.5	882.6	883.8
165°	898.7	898.5	898.3	898.2	898.1	898.1	898.1	898.1	898.1	899.3	900.6
167.5°	913.9	913.3	912.8	912.3	912.0	912.0	911.9	911.9	911.8	913.1	914.3
170°	922.0	921.5	921.0	920.4	920.1	920.0	919.8	919.6	919.4	920.7	921.9
172.5°	927.7	927.2	926.7	926.1	925.8	925.7	925.4	925.3	925.1	926.4	927.6
175°	934.7	934.1	933.7	933.1	932.7	932.3	932.0	931.6	931.3	932.5	933.7
177.5°	937.6	937.2	936.8	936.4	936.0	935.7	935.5	935.2	934.9	935.7	936.6
180°	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8



TEST NUMBER: P331448-927

CATALOG NUMBER: SA2XXDIP-C1005D925U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6
2.5°	1638.4	1645.2	1645.2	1646.2	1653.9	1653.0	1652.5
5°	1743.6	1753.9	1755.1	1766.0	1773.3	1770.8	1764.2
7.5°	1842.8	1861.9	1876.5	1884.7	1894.3	1900.2	1897.5
10°	1921.4	1949.4	1966.4	1977.9	1991.9	2002.2	1998.5
12.5°	1992.8	2026.1	2049.5	2069.2	2071.0	2084.2	2075.3
15°	2104.2	2139.4	2143.0	2157.6	2169.2	2167.9	2168.5
17.5°	2141.0	2152.3	2154.6	2154.9	2155.1	2150.8	2141.6
20°	2127.9	2123.6	2113.3	2105.4	2091.4	2089.6	2077.5
22.5°	2065.7	2052.2	2026.3	2009.2	1987.5	1981.8	1978.4
25°	1943.3	1913.5	1872.2	1832.8	1821.9	1800.6	1806.7
27.5°	1775.4	1729.0	1684.3	1652.3	1623.3	1591.4	1600.5
30°	1657.3	1605.1	1542.0	1493.4	1462.4	1432.1	1426.6
32.5°	1516.5	1440.0	1369.6	1326.8	1279.4	1260.2	1239.2
35°	1273.7	1199.0	1129.2	1069.1	1034.5	1007.7	983.5
37.5°	1055.3	969.3	912.9	864.3	839.2	823.9	827.8
40°	919.7	844.5	803.2	766.1	743.1	732.1	734.6
42.5°	810.0	753.6	719.6	694.3	678.0	671.9	670.5
45°	685.4	653.9	625.9	611.3	603.5	596.8	592.6
47.5°	600.4	574.6	558.9	550.2	543.4	536.5	536.4
50°	549.4	532.4	521.5	512.4	506.9	502.1	506.3
52.5°	510.6	495.0	484.1	475.9	473.9	469.5	469.4
55°	452.9	440.8	432.8	425.6	421.9	419.5	416.5
57.5°	400.4	388.9	381.6	377.0	370.1	367.7	366.7
60°	363.1	353.9	346.7	340.6	337.5	332.7	332.7
62.5°	328.5	319.5	312.7	308.0	303.1	301.1	301.6
65°	278.7	271.4	264.7	259.8	258.6	255.0	256.2
67.5°	232.7	227.9	220.9	218.2	215.9	214.0	212.5
70°	202.2	197.3	193.7	190.0	188.2	188.2	188.2
72.5°	176.4	170.6	168.4	163.8	164.9	163.0	161.0
75°	136.6	132.9	131.1	129.3	126.3	126.3	126.3
77.5°	100.5	99.4	97.3	95.3	94.6	94.0	94.2
80°	77.7	77.1	75.9	75.9	74.7	74.1	72.9
82.5°	59.7	58.1	57.4	57.0	56.7	56.6	56.3
85°	34.0	32.8	32.8	33.4	32.2	32.2	32.8
87.5°	18.5	18.4	17.8	17.9	18.5	18.0	18.0
90°	26.6	26.3	26.1	26.4	26.5	26.7	26.9
92.5°	25.3	25.4	25.5	25.5	25.5	25.6	25.6
95°	50.6	50.6	50.4	50.1	49.7	49.4	49.0
97.5°	85.1	85.1	85.1	85.0	85.0	84.9	84.9
100°	109.1	109.1	109.0	108.8	108.7	108.4	108.3
102.5°	135.5	135.6	135.5	135.4	135.2	135.1	134.9
105°	175.0	175.3	175.5	175.5	175.5	175.5	175.5
107.5°	217.2	217.3	217.0	216.2	215.4	214.6	213.7
110°	245.9	245.9	245.6	245.1	244.5	244.0	243.5



TEST NUMBER: P331448-927

CATALOG NUMBER: SA2XXDIP-C1005D925U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	274.3	273.9	273.5	273.1	272.7	272.4	272.0
115°	318.9	318.7	318.3	317.8	317.3	316.7	316.2
117.5°	361.5	361.0	360.5	360.0	359.5	358.9	358.5
120°	390.5	390.5	390.3	389.8	389.2	388.7	388.2
122.5°	419.6	419.2	418.8	418.4	418.0	417.6	417.2
125°	463.3	462.7	462.4	462.2	462.0	461.8	461.7
127.5°	505.6	505.0	504.4	503.8	503.3	502.7	502.2
130°	535.0	534.6	534.1	533.4	532.7	532.0	531.2
132.5°	562.8	562.0	561.3	560.8	560.2	559.7	559.1
135°	605.1	604.8	604.5	604.0	603.5	602.9	602.4
137.5°	645.0	644.8	644.4	643.7	643.0	642.3	641.6
140°	672.0	672.0	671.6	670.9	670.2	669.6	668.8
142.5°	696.4	696.6	696.3	695.6	694.9	694.2	693.5
145°	733.4	733.6	733.3	732.6	731.9	731.2	730.5
147.5°	766.0	766.4	766.2	765.6	764.9	764.2	763.5
150°	786.6	787.1	787.1	786.6	786.1	785.5	785.1
152.5°	807.2	807.9	807.9	807.2	806.6	806.0	805.3
155°	833.5	834.4	834.6	834.0	833.5	833.0	832.4
157.5°	857.9	859.0	859.2	858.4	857.5	856.7	855.9
160°	872.0	873.1	873.2	872.5	871.8	871.1	870.4
162.5°	885.0	886.2	886.5	885.6	884.7	883.9	883.0
165°	901.7	903.0	903.2	902.3	901.4	900.6	899.7
167.5°	915.5	916.7	916.9	916.0	915.0	914.2	913.2
170°	923.1	924.3	924.4	923.4	922.3	921.2	920.2
172.5°	928.8	930.0	930.1	929.1	928.0	926.9	925.9
175°	934.9	936.2	936.3	935.3	934.1	933.1	932.1
177.5°	937.5	938.3	938.3	937.5	936.6	935.7	934.9
180°	936.8	936.8	936.8	936.8	936.8	936.8	936.8

(END OF REPORT)