

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331453-927

Luminaire Tested: **SA2XXDIP-C1005D925U927-4F0-1E-UDD-F**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331453-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXDIP-C1005D925U927-4F0-1E-UDD-F  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 925 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6144.9 lumens  
Efficiency: N/A  
Efficacy: 92.0 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 66.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331453-927  
CATALOG NUMBER: SA2XXDIP-C1005D925U927-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P331453-927

CATALOG NUMBER: SA2XXDIP-C1005D925U927-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	58	58	58	52				
1	98	94	90	87	91	87	84	81	74	72	69	62	61	59	51	50	49	44				
2	90	82	76	71	83	76	71	66	65	61	58	55	52	49	45	43	41	37				
3	82	72	65	59	75	67	61	55	57	52	48	48	45	42	40	38	35	31				
4	75	64	56	50	69	59	52	47	51	46	41	43	39	36	36	33	30	27				
5	69	57	49	43	63	53	46	40	46	40	36	39	34	31	32	29	27	23				
6	63	51	43	37	58	48	40	35	41	35	31	35	31	27	29	26	23	20				
7	58	46	38	33	54	43	36	31	37	32	27	32	27	24	27	23	21	18				
8	54	42	34	29	50	39	32	27	34	28	24	29	25	21	25	21	19	16				
9	51	38	31	26	47	36	29	24	31	26	22	27	22	19	23	19	17	15				
10	47	35	28	23	44	33	26	22	29	23	20	25	21	17	21	18	15	13				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	20386	20386	20386
5°	20464	20169	20285
10°	20341	19964	20064
15°	20090	19704	19686
20°	19734	19316	19295
25°	19379	18838	18838
30°	18921	18401	18243
35°	18496	17875	17611
40°	17962	17351	17015
45°	17438	16826	16411
50°	16865	16284	15707
55°	16268	15651	15071
60°	15603	14899	14347
65°	14888	14147	13498
70°	13983	13237	12609
75°	12726	12190	11890
80°	11288	10953	10386
85°	9207	8781	7873



TEST NUMBER: P331453-927

CATALOG NUMBER: SA2XXDIP-C1005D925U927-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	118.7	1.9
10°-20°	334.1	5.4
20°-30°	491.0	8.0
30°-40°	570.4	9.3
40°-50°	569.8	9.3
50°-60°	496.9	8.1
60°-70°	367.4	6.0
70°-80°	208.1	3.4
80°-90°	58.4	1.0
90°-100°	33.4	0.5
100°-110°	122.3	2.0
110°-120°	326.9	5.3
120°-130°	539.7	8.8
130°-140°	574.0	9.3
140°-150°	533.5	8.7
150°-160°	428.9	7.0
160°-170°	276.4	4.5
170°-180°	95.1	1.5
0°-30°	943.8	15.4
0°-40°	1514.2	24.6
0°-60°	2580.8	42.0
0°-90°	3214.7	52.3
90°-120°	482.6	7.9
90°-150°	2129.7	34.7
90°-180°	2930.0	47.7
0°-180°	6144.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1263	1263	1263	1263	1263	
5°	1263	1257	1244	1253	1252	120
15°	1202	1194	1179	1183	1178	338
25°	1088	1078	1057	1060	1057	500
35°	938	926	907	900	894	586
45°	764	755	737	724	719	589
55°	578	570	556	542	535	517
65°	390	382	370	360	353	385
75°	204	201	195	189	191	218
85°	50	49	47	44	42	57
90°	1	9	14	18	20	5
95°	47	25	28	32	31	58
105°	220	229	44	52	55	235
115°	416	429	446	127	59	409
125°	588	598	611	616	619	524
135°	728	739	746	753	752	562
145°	844	844	856	860	857	528
155°	930	924	932	936	930	428
165°	980	976	978	982	978	277
175°	1002	997	998	1003	996	95
180°	1000	1000	1000	1000	1000	



TEST NUMBER: P331453-927

CATALOG NUMBER: SA2XXDIP-C1005D925U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6
2.5°	1268.4	1267.3	1266.3	1265.2	1264.1	1262.4	1260.0	1257.7	1255.3	1252.9	1255.1
5°	1262.6	1261.6	1260.4	1259.3	1258.3	1256.2	1253.3	1250.3	1247.4	1244.4	1246.6
7.5°	1251.4	1249.7	1248.1	1246.4	1244.8	1242.4	1239.4	1236.4	1233.3	1230.3	1232.5
10°	1240.7	1238.9	1237.0	1235.1	1233.2	1230.7	1227.4	1224.2	1220.9	1217.7	1219.9
12.5°	1226.2	1224.5	1222.8	1221.1	1219.5	1217.0	1213.8	1210.5	1207.4	1204.1	1205.6
15°	1201.9	1200.3	1198.7	1197.1	1195.4	1192.9	1189.4	1185.8	1182.3	1178.8	1180.0
17.5°	1170.8	1169.2	1167.6	1165.9	1164.3	1161.7	1158.2	1154.6	1151.0	1147.6	1148.7
20°	1148.5	1146.8	1145.3	1143.6	1142.0	1139.3	1135.5	1131.8	1128.0	1124.2	1125.0
22.5°	1126.2	1123.9	1121.7	1119.4	1117.1	1114.2	1110.6	1107.1	1103.5	1099.9	1100.1
25°	1087.8	1085.6	1083.5	1081.3	1079.2	1075.8	1071.2	1066.6	1062.0	1057.4	1058.0
27.5°	1044.1	1042.1	1040.2	1038.2	1036.3	1033.6	1029.9	1026.3	1022.7	1019.1	1018.3
30°	1014.9	1012.8	1010.6	1008.4	1006.3	1003.2	999.2	995.1	991.1	987.0	986.2
32.5°	983.9	982.1	980.4	978.7	976.9	974.0	969.7	965.4	961.2	956.9	955.5
35°	938.4	935.7	933.0	930.3	927.6	924.2	919.8	915.5	911.2	906.9	905.3
37.5°	887.2	884.9	882.5	880.1	877.7	874.4	870.1	865.8	861.4	857.1	855.1
40°	852.2	850.1	848.0	845.8	843.6	840.4	836.1	831.8	827.4	823.2	820.7
42.5°	818.2	816.1	814.0	811.8	809.6	806.4	802.1	797.7	793.4	789.1	786.5
45°	763.7	761.8	759.9	758.0	756.1	753.1	749.1	745.0	741.0	736.9	734.0
47.5°	709.2	707.5	705.7	703.9	702.1	699.1	694.9	690.7	686.5	682.3	679.1
50°	671.4	670.0	668.7	667.3	666.0	663.4	659.7	655.8	652.0	648.3	644.5
52.5°	634.5	632.7	630.9	629.2	627.3	624.6	621.1	617.5	614.0	610.5	607.3
55°	577.9	576.2	574.6	573.1	571.4	568.9	565.8	562.5	559.3	556.0	552.8
57.5°	521.1	519.8	518.5	517.2	515.9	513.5	509.9	506.4	502.8	499.2	496.1
60°	483.2	482.1	481.0	480.0	478.9	476.4	472.7	468.9	465.1	461.4	458.4
62.5°	446.3	444.6	442.8	441.1	439.3	437.0	434.1	431.3	428.3	425.4	422.6
65°	389.7	388.1	386.5	384.8	383.3	381.0	378.3	375.7	373.0	370.3	367.9
67.5°	332.2	330.9	329.5	328.3	327.0	325.1	322.7	320.3	317.8	315.4	313.5
70°	296.2	295.2	294.1	293.0	291.9	290.2	287.7	285.3	282.9	280.4	278.5
72.5°	259.3	258.3	257.1	256.1	255.0	253.7	252.2	250.6	249.0	247.4	245.5
75°	204.0	203.4	202.9	202.3	201.8	200.8	199.5	198.1	196.8	195.4	193.8
77.5°	154.4	153.5	152.6	151.7	150.8	150.0	149.5	148.9	148.4	147.9	147.0
80°	121.4	121.1	120.9	120.6	120.3	119.9	119.4	118.8	118.3	117.8	116.9
82.5°	90.3	90.3	90.2	90.2	90.1	89.9	89.6	89.3	89.0	88.6	87.6
85°	49.7	49.5	49.3	49.0	48.7	48.4	48.2	47.8	47.6	47.4	46.5
87.5°	17.7	17.6	17.5	17.4	17.3	17.2	17.0	16.9	16.6	16.5	16.0
90°	0.7	2.5	4.3	6.0	7.8	9.3	10.6	11.9	13.2	14.5	15.3
92.5°	14.6	14.4	14.3	14.1	13.9	14.2	14.9	15.5	16.2	16.8	17.2
95°	47.1	41.7	36.4	31.1	25.8	23.7	24.9	26.0	27.1	28.2	29.0
97.5°	93.3	78.3	63.5	48.5	33.5	27.3	29.9	32.6	35.2	37.8	38.4
100°	128.1	106.0	84.0	61.9	39.9	30.3	33.0	35.8	38.5	41.3	42.5
102.5°	166.3	161.6	156.9	152.3	147.6	133.9	111.0	88.1	65.3	42.4	44.0
105°	219.9	224.7	229.6	234.4	239.2	219.7	175.8	131.9	88.0	44.1	45.9
107.5°	281.1	285.0	288.9	292.8	296.8	272.4	219.7	167.1	114.4	61.8	60.0
110°	320.5	323.9	327.3	330.7	334.0	312.4	266.0	219.5	173.1	126.6	110.5



TEST NUMBER: P331453-927

CATALOG NUMBER: SA2XXDIP-C1005D925U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	357.5	360.5	363.5	366.5	369.5	365.3	353.8	342.3	330.8	319.3	260.7
115°	416.0	418.7	421.4	424.2	426.9	430.3	434.4	438.4	442.4	446.4	371.9
117.5°	468.3	471.3	474.4	477.4	480.5	483.4	486.2	488.9	491.7	494.4	476.4
120°	506.4	508.8	511.3	513.7	516.1	518.7	521.7	524.5	527.4	530.3	532.3
122.5°	538.8	541.4	543.9	546.4	549.0	551.8	555.0	558.2	561.3	564.5	565.6
125°	588.2	590.3	592.4	594.5	596.6	599.1	602.2	605.2	608.3	611.3	612.5
127.5°	632.9	635.3	637.5	639.8	642.1	644.4	646.7	649.0	651.3	653.6	655.2
130°	661.3	663.8	666.4	669.0	671.5	673.8	675.5	677.2	679.1	680.8	682.5
132.5°	690.2	692.4	694.6	696.8	698.9	700.9	702.7	704.5	706.2	708.0	709.6
135°	727.9	730.4	733.0	735.5	738.2	740.1	741.6	743.1	744.5	745.9	747.5
137.5°	765.9	767.7	769.5	771.3	773.1	774.8	776.4	778.1	779.7	781.4	782.9
140°	790.8	792.1	793.4	794.6	795.9	797.5	799.2	801.0	802.8	804.5	806.0
142.5°	811.6	812.8	814.0	815.1	816.3	817.8	819.8	821.9	823.9	825.9	827.3
145°	844.3	844.1	844.0	843.8	843.7	844.9	847.7	850.4	853.2	855.9	857.0
147.5°	872.8	872.2	871.6	871.0	870.4	871.4	874.1	876.9	879.6	882.3	883.0
150°	891.4	890.3	889.1	888.0	886.8	887.6	890.2	892.7	895.3	897.9	898.8
152.5°	907.0	905.7	904.4	903.2	902.0	902.5	905.0	907.4	909.9	912.4	913.3
155°	929.7	928.3	926.8	925.3	923.9	924.2	926.1	928.0	929.9	931.8	932.8
157.5°	947.5	946.3	945.1	943.8	942.6	942.7	944.0	945.4	946.7	948.1	949.2
160°	957.9	957.0	956.0	955.0	954.0	954.0	955.0	956.0	957.0	957.9	958.9
162.5°	967.2	966.2	965.3	964.2	963.3	963.2	964.1	964.9	965.7	966.6	967.7
165°	979.6	978.7	977.7	976.7	975.7	975.5	976.0	976.4	977.0	977.5	978.6
167.5°	988.9	987.9	987.0	986.0	985.0	984.8	985.2	985.6	986.1	986.6	987.7
170°	994.1	993.1	992.1	991.2	990.2	989.9	990.2	990.5	990.9	991.2	992.3
172.5°	997.5	996.6	995.6	994.7	993.7	993.4	993.7	994.0	994.3	994.7	995.8
175°	1002.0	1000.9	999.8	998.6	997.5	997.1	997.4	997.8	998.1	998.4	999.6
177.5°	1002.7	1001.9	1001.0	1000.1	999.2	998.8	998.9	999.0	999.2	999.3	1000.2
180°	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9



TEST NUMBER: P331453-927

CATALOG NUMBER: SA2XXDIP-C1005D925U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6
2.5°	1257.2	1259.3	1261.6	1262.4	1261.9	1261.6	1261.1	1260.7
5°	1248.7	1250.9	1253.0	1253.9	1253.3	1252.8	1252.2	1251.6
7.5°	1234.6	1236.8	1239.0	1239.8	1239.1	1238.6	1237.9	1237.4
10°	1222.0	1224.2	1226.3	1227.0	1226.2	1225.3	1224.6	1223.8
12.5°	1207.1	1208.6	1210.1	1210.6	1210.0	1209.4	1208.8	1208.2
15°	1181.0	1182.1	1183.1	1183.0	1181.7	1180.4	1179.0	1177.7
17.5°	1150.0	1151.3	1152.5	1152.5	1151.1	1149.9	1148.6	1147.2
20°	1125.8	1126.6	1127.4	1127.3	1126.2	1125.1	1124.1	1123.0
22.5°	1100.3	1100.4	1100.6	1100.3	1099.7	1099.1	1098.4	1097.7
25°	1058.5	1059.1	1059.6	1059.6	1059.1	1058.5	1058.0	1057.4
27.5°	1017.5	1016.6	1015.8	1014.8	1013.5	1012.2	1010.9	1009.6
30°	985.4	984.6	983.8	982.9	981.8	980.6	979.6	978.5
32.5°	954.0	952.5	951.1	949.8	948.7	947.7	946.6	945.5
35°	903.6	902.1	900.4	899.0	897.6	896.3	894.8	893.5
37.5°	853.1	851.1	849.1	847.5	846.2	844.9	843.6	842.3
40°	818.2	815.9	813.4	811.7	810.6	809.5	808.4	807.3
42.5°	783.9	781.2	778.6	776.5	775.0	773.5	772.0	770.4
45°	731.0	728.0	725.1	723.0	721.9	720.9	719.8	718.7
47.5°	676.0	672.9	669.8	667.4	665.8	664.3	662.7	661.2
50°	640.7	637.0	633.2	630.7	629.3	628.0	626.6	625.3
52.5°	604.2	601.0	597.9	595.5	593.7	591.9	590.1	588.4
55°	549.5	546.3	543.1	540.8	539.5	538.1	536.8	535.4
57.5°	492.8	489.6	486.5	484.3	483.4	482.4	481.3	480.3
60°	455.4	452.4	449.5	447.6	446.8	446.0	445.1	444.3
62.5°	419.9	417.2	414.4	412.5	411.5	410.4	409.4	408.4
65°	365.4	363.0	360.6	358.7	357.4	356.0	354.7	353.3
67.5°	311.6	309.7	307.8	306.3	305.3	304.2	303.2	302.1
70°	276.6	274.8	272.9	271.4	270.3	269.3	268.2	267.1
72.5°	243.7	241.8	239.9	238.5	237.7	236.8	235.9	235.0
75°	192.3	190.6	189.0	188.5	189.0	189.5	190.0	190.6
77.5°	146.2	145.4	144.7	143.9	143.1	142.4	141.6	140.9
80°	116.1	115.3	114.5	113.8	113.3	112.8	112.3	111.7
82.5°	86.6	85.6	84.5	84.0	83.8	83.7	83.7	83.5
85°	45.7	44.9	44.1	43.6	43.3	43.0	42.8	42.5
87.5°	15.5	15.1	14.6	14.3	14.1	13.9	13.8	13.6
90°	16.1	16.9	17.7	18.2	18.5	18.9	19.3	19.6
92.5°	17.6	18.1	18.5	18.8	18.9	19.2	19.3	19.6
95°	29.8	30.7	31.4	31.8	31.6	31.4	31.3	31.1
97.5°	39.1	39.7	40.3	40.7	41.0	41.1	41.4	41.5
100°	43.8	45.1	46.4	47.2	47.5	47.8	48.2	48.5
102.5°	45.7	47.5	49.1	50.1	50.6	51.0	51.5	52.0
105°	47.7	49.4	51.2	52.4	53.1	53.7	54.3	55.0
107.5°	58.1	56.4	54.6	54.0	54.7	55.3	55.9	56.6
110°	94.4	78.3	62.3	54.6	55.2	55.8	56.5	57.2





TEST NUMBER: P331453-927

CATALOG NUMBER: SA2XXDIP-C1005D925U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	202.1	143.4	84.8	55.7	56.2	56.7	57.2	57.8
115°	297.5	223.1	148.6	105.6	94.0	82.5	70.9	59.3
117.5°	458.4	440.5	422.4	394.3	356.3	318.3	280.3	242.2
120°	534.2	536.1	538.1	528.1	506.4	484.7	463.0	441.3
122.5°	566.8	567.9	569.1	567.6	563.4	559.1	554.9	550.7
125°	613.6	614.7	615.8	616.6	617.1	617.6	618.1	618.6
127.5°	656.9	658.5	660.2	661.0	661.2	661.2	661.3	661.4
130°	684.4	686.1	687.9	688.7	688.6	688.3	688.2	688.0
132.5°	711.1	712.6	714.1	714.7	714.5	714.4	714.2	714.1
135°	749.2	750.8	752.3	753.0	752.7	752.3	752.0	751.7
137.5°	784.5	786.1	787.7	788.2	787.7	787.1	786.6	786.0
140°	807.4	808.9	810.3	810.6	809.8	809.1	808.3	807.4
142.5°	828.5	829.9	831.2	831.5	830.7	829.9	829.1	828.2
145°	858.2	859.3	860.4	860.5	859.8	859.0	858.2	857.4
147.5°	883.9	884.7	885.6	885.7	884.9	884.3	883.6	883.0
150°	899.8	900.8	901.7	901.8	901.0	900.2	899.4	898.6
152.5°	914.3	915.2	916.2	916.2	915.0	914.0	913.0	911.9
155°	933.8	934.8	935.7	935.6	934.3	933.0	931.7	930.4
157.5°	950.2	951.3	952.4	952.4	951.1	949.8	948.6	947.4
160°	959.8	960.8	961.8	961.7	960.5	959.4	958.3	957.2
162.5°	968.8	969.9	971.0	970.8	969.5	968.0	966.7	965.3
165°	979.7	980.8	981.9	981.9	980.8	979.7	978.6	977.5
167.5°	988.8	989.9	991.1	990.9	989.4	988.0	986.6	985.1
170°	993.5	994.6	995.7	995.5	994.1	992.6	991.2	989.8
172.5°	996.9	998.1	999.2	999.0	997.5	996.1	994.7	993.2
175°	1000.7	1001.8	1002.9	1002.7	1001.1	999.5	997.8	996.2
177.5°	1001.1	1002.0	1002.9	1002.7	1001.6	1000.4	999.3	998.1
180°	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9

(END OF REPORT)