

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331282-927

Luminaire Tested: **SA2XXDIP-C290D1080U927-4F0-1E-UDD-F**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331282-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXDIP-C290D1080U927-4F0-1E-UDD-F  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1080 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4365.7 lumens  
Efficiency: N/A  
Efficacy: 103.5 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 42.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331282-927

CATALOG NUMBER: SA2XXDIP-C290D1080U927-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P331282-927

CATALOG NUMBER: SA2XXDIP-C290D1080U927-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	100	100	100	100	89	89	89	89	68	68	68	48	48	48	30	30	30	22				
1	91	87	84	80	81	78	74	72	59	57	55	42	41	40	27	26	25	18				
2	83	76	70	65	74	68	63	59	52	49	46	37	35	33	23	22	21	15				
3	76	67	60	54	67	59	54	49	46	42	38	33	30	28	21	19	18	13				
4	69	59	52	46	61	53	46	41	40	36	33	29	26	24	19	17	16	11				
5	63	52	45	39	56	47	40	35	36	31	28	26	23	21	17	15	14	10				
6	58	47	39	34	51	42	35	30	32	28	24	23	20	18	15	13	12	9				
7	54	42	35	29	47	38	31	26	29	24	21	21	18	16	14	12	11	8				
8	50	38	31	26	44	34	28	23	26	22	19	19	16	14	13	11	9	7				
9	46	35	27	23	41	31	25	21	24	20	16	18	15	12	12	10	8	6				
10	43	32	25	20	38	28	22	18	22	18	15	16	13	11	11	9	8	6				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	6042	6042	6042
5°	6065	5977	6015
10°	6030	5917	5946
15°	5954	5840	5835
20°	5849	5727	5720
25°	5744	5585	5585
30°	5610	5455	5407
35°	5483	5298	5219
40°	5324	5143	5044
45°	5167	4987	4864
50°	4999	4828	4657
55°	4822	4642	4467
60°	4624	4414	4253
65°	4413	4195	4000
70°	4145	3923	3734
75°	3768	3612	3525
80°	3347	3245	3078
85°	2723	2594	2334



TEST NUMBER: P331282-927

CATALOG NUMBER: SA2XXDIP-C290D1080U927-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	35.2	0.8
10°-20°	99.0	2.3
20°-30°	145.6	3.3
30°-40°	169.1	3.9
40°-50°	168.9	3.9
50°-60°	147.3	3.4
60°-70°	108.9	2.5
70°-80°	61.7	1.4
80°-90°	19.5	0.4
90°-100°	38.8	0.9
100°-110°	142.4	3.3
110°-120°	380.6	8.7
120°-130°	628.2	14.4
130°-140°	668.1	15.3
140°-150°	620.9	14.2
150°-160°	499.2	11.4
160°-170°	321.7	7.4
170°-180°	110.7	2.5
0°-30°	279.8	6.4
0°-40°	448.8	10.3
0°-60°	765.0	17.5
0°-90°	955.0	21.9
90°-120°	561.7	12.9
90°-150°	2478.9	56.8
90°-180°	3411.0	78.1
0°-180°	4365.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	374	374	374	374	374	
5°	374	373	369	372	371	35
15°	356	354	349	351	349	100
25°	322	319	314	314	314	148
35°	278	274	269	267	265	174
45°	226	224	218	215	213	175
55°	171	169	165	161	159	153
65°	116	113	110	107	105	114
75°	60	60	58	56	56	65
85°	15	14	14	13	13	17
90°	1	10	17	21	23	3
95°	55	29	33	37	36	67
105°	256	267	51	60	64	274
115°	484	499	520	148	69	477
125°	685	696	712	717	720	610
135°	847	860	868	876	875	654
145°	983	983	996	1002	998	614
155°	1082	1076	1085	1089	1083	498
165°	1140	1136	1138	1143	1138	322
175°	1166	1161	1162	1167	1160	111
180°	1164	1164	1164	1164	1164	



TEST NUMBER: P331282-927

CATALOG NUMBER: SA2XXDIP-C290D1080U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	374.2	374.2	374.2	374.2	374.2	374.2	374.2	374.2	374.2	374.2	374.2
2.5°	376.0	375.7	375.3	375.0	374.7	374.2	373.5	372.8	372.1	371.4	372.0
5°	374.2	373.9	373.6	373.3	373.0	372.4	371.5	370.7	369.7	368.8	369.5
7.5°	371.0	370.4	369.9	369.5	369.0	368.3	367.4	366.5	365.6	364.7	365.4
10°	367.8	367.3	366.7	366.1	365.5	364.8	363.8	362.9	361.9	360.9	361.6
12.5°	363.5	363.0	362.5	361.9	361.5	360.8	359.8	358.9	357.9	357.0	357.4
15°	356.2	355.8	355.3	354.8	354.3	353.6	352.5	351.5	350.5	349.4	349.7
17.5°	347.1	346.6	346.1	345.6	345.2	344.4	343.3	342.2	341.2	340.2	340.5
20°	340.4	339.9	339.5	339.0	338.5	337.7	336.6	335.5	334.4	333.3	333.5
22.5°	333.8	333.1	332.5	331.8	331.1	330.3	329.2	328.1	327.1	326.1	326.1
25°	322.4	321.8	321.2	320.5	319.9	318.9	317.5	316.2	314.8	313.5	313.6
27.5°	309.5	309.0	308.3	307.8	307.2	306.3	305.3	304.2	303.2	302.1	301.8
30°	300.9	300.2	299.6	299.0	298.3	297.4	296.2	295.0	293.7	292.6	292.3
32.5°	291.6	291.1	290.7	290.1	289.6	288.7	287.4	286.2	284.9	283.7	283.2
35°	278.2	277.3	276.6	275.8	275.0	273.9	272.7	271.4	270.1	268.8	268.3
37.5°	263.0	262.3	261.6	260.9	260.2	259.2	257.9	256.7	255.3	254.1	253.5
40°	252.6	252.0	251.4	250.7	250.1	249.1	247.8	246.5	245.3	244.0	243.3
42.5°	242.6	241.9	241.3	240.7	240.0	239.0	237.7	236.5	235.2	233.9	233.1
45°	226.3	225.8	225.2	224.7	224.1	223.2	222.0	220.9	219.7	218.4	217.5
47.5°	210.2	209.7	209.2	208.7	208.1	207.2	206.0	204.8	203.5	202.2	201.3
50°	199.0	198.6	198.2	197.8	197.4	196.6	195.5	194.4	193.3	192.2	191.1
52.5°	188.1	187.5	187.0	186.5	185.9	185.1	184.1	183.1	182.0	180.9	180.0
55°	171.3	170.8	170.3	169.8	169.4	168.7	167.7	166.8	165.8	164.9	163.8
57.5°	154.5	154.1	153.7	153.3	152.9	152.2	151.1	150.1	149.0	148.0	147.0
60°	143.2	142.9	142.6	142.3	142.0	141.2	140.1	139.0	137.8	136.7	135.9
62.5°	132.3	131.7	131.3	130.8	130.2	129.5	128.7	127.9	127.0	126.1	125.2
65°	115.5	115.0	114.5	114.1	113.6	113.0	112.2	111.4	110.6	109.8	109.0
67.5°	98.5	98.1	97.7	97.3	97.0	96.4	95.6	94.9	94.2	93.5	92.9
70°	87.8	87.5	87.1	86.8	86.5	86.0	85.3	84.6	83.8	83.1	82.5
72.5°	76.8	76.5	76.2	75.9	75.6	75.2	74.7	74.3	73.8	73.4	72.8
75°	60.4	60.3	60.1	60.0	59.8	59.6	59.2	58.7	58.3	57.9	57.4
77.5°	45.8	45.5	45.2	45.0	44.7	44.4	44.3	44.1	44.0	43.8	43.6
80°	36.0	35.9	35.8	35.7	35.6	35.6	35.4	35.3	35.1	34.9	34.7
82.5°	26.8	26.8	26.8	26.7	26.7	26.6	26.5	26.5	26.4	26.3	26.0
85°	14.7	14.7	14.6	14.5	14.4	14.3	14.3	14.2	14.1	14.0	13.8
87.5°	5.4	5.6	5.9	6.2	6.5	6.7	6.9	7.1	7.2	7.4	7.4
90°	0.9	2.9	5.0	7.1	9.1	10.9	12.4	13.9	15.4	16.9	17.7
92.5°	17.0	16.8	16.6	16.5	16.2	16.6	17.3	18.1	18.8	19.6	20.0
95°	54.7	48.6	42.4	36.2	30.0	27.6	28.9	30.3	31.5	32.9	33.7
97.5°	108.6	91.3	73.8	56.4	39.1	31.8	34.9	37.9	41.0	44.0	44.7
100°	149.1	123.4	97.8	72.2	46.5	35.3	38.4	41.7	44.8	48.0	49.5
102.5°	193.5	188.1	182.7	177.2	171.8	155.8	129.2	102.6	76.0	49.4	51.3
105°	256.0	261.7	267.2	272.8	278.5	255.7	204.6	153.5	102.4	51.3	53.4
107.5°	327.3	331.8	336.3	340.8	345.4	317.0	255.7	194.5	133.2	71.9	69.8
110°	373.0	377.0	381.0	384.8	388.8	363.7	309.6	255.6	201.5	147.3	128.7



TEST NUMBER: P331282-927

CATALOG NUMBER: SA2XXDIP-C290D1080U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	416.2	419.7	423.1	426.6	430.1	425.2	411.8	398.5	385.1	371.7	303.5
115°	484.3	487.4	490.6	493.8	496.9	500.9	505.6	510.2	514.9	519.6	432.9
117.5°	545.0	548.6	552.2	555.7	559.3	562.6	565.9	569.1	572.3	575.5	554.5
120°	589.5	592.3	595.1	597.9	600.7	603.8	607.2	610.5	613.9	617.3	619.5
122.5°	627.2	630.2	633.1	636.1	639.1	642.4	646.0	649.7	653.4	657.0	658.4
125°	684.7	687.1	689.5	692.0	694.3	697.4	700.9	704.5	708.1	711.6	712.9
127.5°	736.7	739.4	742.1	744.8	747.5	750.1	752.8	755.4	758.1	760.8	762.7
130°	769.7	772.7	775.7	778.7	781.6	784.2	786.2	788.3	790.4	792.4	794.5
132.5°	803.4	806.0	808.5	811.0	813.6	815.9	817.9	820.0	822.0	824.1	825.9
135°	847.2	850.2	853.2	856.2	859.1	861.5	863.2	864.8	866.6	868.2	870.1
137.5°	891.4	893.6	895.6	897.8	899.8	901.8	903.8	905.7	907.6	909.5	911.3
140°	920.4	921.9	923.4	925.0	926.5	928.2	930.3	932.3	934.4	936.4	938.1
142.5°	944.7	946.0	947.4	948.7	950.1	952.0	954.3	956.6	959.0	961.4	962.9
145°	982.8	982.5	982.4	982.2	982.0	983.5	986.7	989.8	993.1	996.2	997.5
147.5°	1016.0	1015.3	1014.5	1013.8	1013.1	1014.3	1017.5	1020.6	1023.7	1026.9	1027.9
150°	1037.5	1036.2	1034.9	1033.6	1032.3	1033.1	1036.1	1039.1	1042.1	1045.0	1046.2
152.5°	1055.7	1054.2	1052.7	1051.3	1049.9	1050.5	1053.4	1056.2	1059.1	1061.9	1063.0
155°	1082.1	1080.5	1078.8	1077.1	1075.4	1075.7	1077.9	1080.1	1082.4	1084.7	1085.8
157.5°	1102.9	1101.5	1100.0	1098.6	1097.2	1097.3	1098.8	1100.3	1101.9	1103.5	1104.8
160°	1115.0	1113.9	1112.7	1111.6	1110.5	1110.5	1111.6	1112.7	1113.9	1115.0	1116.1
162.5°	1125.8	1124.7	1123.5	1122.4	1121.3	1121.2	1122.1	1123.2	1124.1	1125.1	1126.3
165°	1140.3	1139.1	1138.0	1136.9	1135.8	1135.4	1136.0	1136.6	1137.2	1137.7	1139.0
167.5°	1151.0	1149.9	1148.7	1147.6	1146.5	1146.2	1146.8	1147.2	1147.8	1148.3	1149.6
170°	1157.1	1156.0	1154.8	1153.7	1152.6	1152.2	1152.6	1152.9	1153.3	1153.7	1155.0
172.5°	1161.1	1160.0	1158.9	1157.8	1156.7	1156.3	1156.7	1157.0	1157.4	1157.8	1159.0
175°	1166.3	1165.1	1163.7	1162.4	1161.1	1160.6	1161.0	1161.4	1161.7	1162.1	1163.5
177.5°	1167.2	1166.2	1165.1	1164.0	1163.0	1162.5	1162.7	1162.8	1163.0	1163.2	1164.2
180°	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8



TEST NUMBER: P331282-927

CATALOG NUMBER: SA2XXDIP-C290D1080U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	374.2	374.2	374.2	374.2	374.2	374.2	374.2	374.2
2.5°	372.6	373.3	373.9	374.2	374.1	373.9	373.8	373.7
5°	370.2	370.8	371.5	371.7	371.5	371.4	371.2	371.1
7.5°	366.0	366.6	367.3	367.5	367.3	367.1	366.9	366.8
10°	362.3	362.9	363.5	363.7	363.5	363.2	363.0	362.7
12.5°	357.8	358.2	358.7	358.9	358.7	358.5	358.3	358.1
15°	350.1	350.4	350.7	350.7	350.3	349.9	349.5	349.1
17.5°	340.9	341.3	341.6	341.6	341.2	340.9	340.5	340.1
20°	333.7	334.0	334.2	334.1	333.8	333.5	333.2	332.9
22.5°	326.1	326.2	326.2	326.1	326.0	325.7	325.6	325.4
25°	313.8	313.9	314.1	314.1	313.9	313.8	313.6	313.5
27.5°	301.6	301.3	301.1	300.8	300.4	300.0	299.7	299.3
30°	292.1	291.8	291.6	291.4	291.0	290.7	290.4	290.0
32.5°	282.8	282.3	281.9	281.5	281.2	280.9	280.6	280.3
35°	267.8	267.4	266.9	266.5	266.1	265.7	265.3	264.8
37.5°	252.9	252.3	251.7	251.2	250.8	250.4	250.1	249.7
40°	242.6	241.9	241.1	240.6	240.3	240.0	239.6	239.3
42.5°	232.3	231.6	230.8	230.1	229.7	229.3	228.9	228.4
45°	216.7	215.8	214.9	214.3	214.0	213.7	213.3	213.0
47.5°	200.4	199.5	198.5	197.8	197.4	196.9	196.5	196.0
50°	190.0	188.8	187.7	187.0	186.6	186.2	185.8	185.4
52.5°	179.1	178.2	177.2	176.5	175.9	175.5	174.9	174.4
55°	162.9	161.9	161.0	160.3	159.9	159.5	159.1	158.7
57.5°	146.1	145.1	144.2	143.5	143.3	143.0	142.7	142.4
60°	135.0	134.1	133.2	132.7	132.5	132.2	132.0	131.7
62.5°	124.5	123.7	122.9	122.3	122.0	121.7	121.4	121.0
65°	108.3	107.6	106.9	106.3	105.9	105.5	105.1	104.7
67.5°	92.4	91.8	91.3	90.8	90.5	90.2	89.8	89.5
70°	82.0	81.4	80.9	80.5	80.2	79.8	79.5	79.1
72.5°	72.2	71.7	71.1	70.7	70.4	70.2	69.9	69.6
75°	57.0	56.5	56.0	55.8	56.0	56.2	56.3	56.5
77.5°	43.3	43.1	42.9	42.6	42.4	42.2	42.0	41.7
80°	34.5	34.2	34.0	33.7	33.6	33.4	33.3	33.1
82.5°	25.7	25.3	25.0	24.9	24.9	24.8	24.8	24.8
85°	13.5	13.3	13.1	12.9	12.8	12.8	12.7	12.6
87.5°	7.4	7.4	7.4	7.4	7.4	7.4	7.4	7.4
90°	18.7	19.6	20.6	21.2	21.6	22.0	22.3	22.7
92.5°	20.5	21.0	21.5	21.9	22.1	22.3	22.5	22.7
95°	34.7	35.6	36.6	37.0	36.8	36.6	36.4	36.2
97.5°	45.5	46.2	47.0	47.5	47.7	47.9	48.1	48.3
100°	51.0	52.5	54.0	54.9	55.3	55.7	56.1	56.4
102.5°	53.2	55.2	57.1	58.4	58.9	59.4	60.0	60.4
105°	55.5	57.5	59.6	61.0	61.8	62.5	63.2	64.0
107.5°	67.7	65.6	63.5	62.9	63.6	64.3	65.1	65.8
110°	110.0	91.3	72.5	63.5	64.2	65.0	65.8	66.5





TEST NUMBER: P331282-927

CATALOG NUMBER: SA2XXDIP-C290D1080U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	235.2	166.9	98.6	64.8	65.4	66.0	66.6	67.2
115°	346.3	259.7	173.0	122.9	109.5	96.0	82.5	69.1
117.5°	533.6	512.6	491.7	459.1	414.8	370.5	326.2	281.9
120°	621.8	624.0	626.3	614.7	589.5	564.2	538.9	513.7
122.5°	659.7	661.1	662.4	660.6	655.8	650.9	645.9	641.0
125°	714.2	715.5	716.8	717.8	718.4	718.9	719.5	720.0
127.5°	764.6	766.5	768.4	769.4	769.5	769.7	769.8	769.8
130°	796.5	798.6	800.7	801.6	801.5	801.2	801.1	800.9
132.5°	827.6	829.4	831.2	831.9	831.7	831.6	831.4	831.2
135°	872.0	873.9	875.7	876.5	876.1	875.7	875.4	875.0
137.5°	913.1	915.0	916.8	917.4	916.8	916.2	915.5	914.9
140°	939.8	941.5	943.2	943.6	942.6	941.7	940.7	939.8
142.5°	964.4	966.0	967.5	967.8	966.9	965.9	965.0	964.1
145°	998.9	1000.1	1001.5	1001.6	1000.8	999.8	998.9	997.9
147.5°	1028.8	1029.8	1030.8	1030.9	1030.1	1029.3	1028.5	1027.7
150°	1047.3	1048.5	1049.6	1049.6	1048.7	1047.8	1046.9	1045.9
152.5°	1064.1	1065.3	1066.4	1066.4	1065.1	1063.9	1062.6	1061.4
155°	1086.9	1088.1	1089.2	1088.9	1087.4	1086.0	1084.5	1083.0
157.5°	1106.0	1107.3	1108.6	1108.5	1107.1	1105.6	1104.1	1102.6
160°	1117.2	1118.3	1119.4	1119.4	1118.1	1116.7	1115.5	1114.1
162.5°	1127.6	1128.9	1130.2	1130.0	1128.4	1126.8	1125.1	1123.6
165°	1140.3	1141.6	1143.0	1143.0	1141.6	1140.3	1139.0	1137.7
167.5°	1151.0	1152.2	1153.6	1153.3	1151.7	1150.0	1148.3	1146.6
170°	1156.3	1157.6	1159.0	1158.7	1157.1	1155.4	1153.7	1152.0
172.5°	1160.4	1161.7	1163.0	1162.8	1161.1	1159.4	1157.8	1156.0
175°	1164.7	1166.1	1167.4	1167.1	1165.2	1163.3	1161.5	1159.6
177.5°	1165.2	1166.3	1167.4	1167.2	1165.9	1164.5	1163.2	1161.8
180°	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8

(END OF REPORT)