

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331457

Luminaire Tested: **SA2XXDIP-C1005D1080U835-4F0-1E-UDD-A1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331457
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C1005D1080U835-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1080 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8253.6 lumens
Efficiency: N/A
Efficacy: 115.1 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 71.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331457

CATALOG NUMBER: SA2XXDIP-C1005D1080U835-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331457

CATALOG NUMBER: SA2XXDIP-C1005D1080U835-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59	53
1	99	95	91	88	92	88	85	82	75	73	71	64	62	61	53	52	51	46
2	91	83	78	73	84	78	72	68	67	63	60	57	54	51	47	45	44	39
3	83	74	67	61	77	69	63	58	59	55	51	51	47	44	42	40	38	34
4	76	66	58	52	70	61	55	49	53	48	44	45	41	38	38	35	33	30
5	70	59	51	45	65	55	48	43	48	42	38	41	37	34	35	32	29	26
6	65	53	45	39	60	50	43	37	43	38	34	37	33	30	32	28	26	23
7	60	48	40	35	56	45	38	33	39	34	30	34	30	26	29	26	23	21
8	56	44	36	31	52	41	34	29	36	31	27	31	27	24	27	23	21	19
9	52	40	33	28	48	38	31	26	33	28	24	29	25	22	25	22	19	17
10	49	37	30	25	45	35	28	24	31	25	22	27	23	20	23	20	17	16

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	32195	32195	32195	32195
5°	36094	32405	28716	32405
10°	41361	32139	24851	32139
15°	45757	31550	21956	31550
20°	45060	30917	20015	30917
25°	40631	30077	18786	30077
30°	33575	28732	17889	28732
35°	24471	27325	17251	27325
40°	19545	25665	16895	25665
45°	17080	23745	16413	23745
50°	16053	21886	16093	21886
55°	14798	19997	15662	19997
60°	13563	17990	14996	17990
65°	12355	16191	14346	16191
70°	11216	14436	13388	14436
75°	9944	12477	11859	12477
80°	8554	10330	9549	10330
85°	7669	7669	5687	7669



TEST NUMBER: P331457

CATALOG NUMBER: SA2XXDIP-C1005D1080U835-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	189.9	2.3
10°-20°	552.1	6.7
20°-30°	801.2	9.7
30°-40°	845.5	10.2
40°-50°	748.6	9.1
50°-60°	597.4	7.2
60°-70°	406.1	4.9
70°-80°	208.2	2.5
80°-90°	55.7	0.7
90°-100°	87.2	1.1
100°-110°	270.9	3.3
110°-120°	463.1	5.6
120°-130°	608.9	7.4
130°-140°	683.5	8.3
140°-150°	670.1	8.1
150°-160°	562.1	6.8
160°-170°	372.8	4.5
170°-180°	130.3	1.6
0°-30°	1543.2	18.7
0°-40°	2388.7	28.9
0°-60°	3734.8	45.3
0°-90°	4404.8	53.4
90°-120°	821.2	9.9
90°-150°	2783.7	33.7
90°-180°	3849.0	46.6
0°-180°	8253.6	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1994	1994	1994	1994	1994	
5°	2227	1999	1772	1999	2227	222
15°	2737	1888	1314	1888	2737	755
25°	2281	1688	1054	1688	2281	1031
35°	1242	1386	875	1386	1242	807
45°	748	1040	719	1040	748	588
55°	526	710	556	710	526	471
65°	323	424	376	424	323	322
75°	159	200	190	200	159	170
85°	41	41	31	41	41	46
90°	40	1	40	1	40	19
95°	72	60	72	60	72	80
105°	258	250	258	250	258	271
115°	465	465	465	465	465	459
125°	678	676	678	676	678	605
135°	885	875	885	875	885	681
145°	1073	1062	1073	1062	1073	670
155°	1223	1214	1223	1214	1223	563
165°	1322	1321	1322	1321	1322	373
175°	1370	1374	1370	1374	1370	130
180°	1376	1376	1376	1376	1376	



TEST NUMBER: P331457

CATALOG NUMBER: SA2XXDIP-C1005D1080U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0
2.5°	2086.0	2086.6	2087.8	2078.0	2076.8	2076.8	2068.2	2060.9	2052.3	2040.6	2041.9
5°	2227.0	2235.4	2238.5	2229.3	2215.5	2214.0	2201.0	2179.5	2159.6	2143.5	2132.0
7.5°	2395.3	2398.7	2391.2	2379.1	2368.8	2350.4	2326.2	2302.4	2269.2	2238.7	2216.0
10°	2522.8	2527.4	2514.4	2496.8	2482.2	2460.8	2425.5	2389.5	2345.8	2303.7	2269.9
12.5°	2619.7	2631.0	2614.3	2612.0	2587.1	2557.6	2515.6	2497.4	2435.9	2377.2	2341.1
15°	2737.4	2736.6	2738.2	2723.6	2705.2	2700.6	2656.2	2607.9	2521.3	2486.8	2427.0
17.5°	2703.4	2715.0	2720.4	2720.2	2719.8	2716.9	2702.6	2672.1	2628.7	2572.8	2503.8
20°	2622.5	2637.8	2640.1	2657.7	2667.7	2680.7	2686.1	2677.6	2650.8	2604.1	2544.3
22.5°	2497.4	2501.7	2508.9	2536.3	2557.9	2590.6	2607.6	2635.9	2625.7	2602.8	2552.9
25°	2280.7	2273.0	2299.8	2313.6	2363.4	2415.5	2453.1	2494.5	2531.3	2553.5	2538.9
27.5°	2020.4	2008.9	2049.1	2085.7	2126.2	2182.6	2241.1	2310.2	2367.7	2439.6	2464.3
30°	1800.9	1807.8	1846.1	1885.2	1946.5	2026.2	2092.1	2168.0	2250.0	2330.5	2386.4
32.5°	1564.3	1590.8	1615.0	1674.9	1728.9	1817.8	1914.3	2009.2	2111.5	2203.0	2289.6
35°	1241.5	1272.1	1305.9	1349.5	1425.4	1513.5	1607.8	1735.8	1875.3	2000.2	2102.9
37.5°	1045.0	1040.1	1059.4	1091.0	1152.4	1223.6	1332.1	1458.5	1622.7	1769.5	1914.3
40°	927.3	924.2	938.0	967.1	1013.9	1066.0	1161.0	1272.1	1424.6	1604.0	1776.4
42.5°	846.4	848.2	855.9	876.4	908.4	951.3	1022.5	1117.0	1256.7	1425.6	1610.9
45°	748.0	753.3	761.8	771.7	790.1	825.4	865.2	932.7	1043.0	1184.0	1366.4
47.5°	677.1	677.3	685.9	694.6	705.5	725.4	757.9	800.2	878.1	992.9	1149.7
50°	639.1	633.8	639.9	646.8	658.3	672.1	693.5	733.4	785.5	878.2	1009.3
52.5°	592.5	592.7	598.2	600.8	611.1	624.9	644.5	672.1	719.3	791.8	899.5
55°	525.7	529.5	532.6	537.2	546.4	556.4	571.7	590.1	626.9	681.3	761.0
57.5°	462.9	464.1	467.2	475.9	481.7	490.9	505.5	522.2	546.1	586.4	646.3
60°	420.0	420.0	426.1	429.9	437.6	446.8	458.3	474.4	495.8	528.8	577.1
62.5°	380.7	380.1	382.6	388.8	394.7	403.3	414.7	428.4	448.6	477.9	517.6
65°	323.4	321.9	326.5	328.0	334.1	342.6	351.8	366.3	382.4	403.9	439.1
67.5°	268.2	270.1	272.5	275.4	278.8	287.7	293.8	304.1	317.7	335.5	359.4
70°	237.6	237.6	237.6	239.9	244.5	249.1	255.2	263.6	276.7	292.0	313.4
72.5°	203.2	205.7	208.1	206.8	212.6	215.3	222.7	227.5	239.9	249.7	268.7
75°	159.4	159.4	159.4	163.2	165.5	167.8	172.4	177.0	183.2	195.4	205.4
77.5°	118.9	118.6	119.4	120.3	122.8	125.5	126.9	131.0	136.7	142.4	150.8
80°	92.0	93.5	94.3	95.8	95.8	97.3	98.1	103.5	107.3	111.1	116.5
82.5°	71.1	71.4	71.6	71.9	72.5	73.4	75.4	77.1	78.5	81.7	85.8
85°	41.4	40.6	40.6	42.1	41.4	41.4	42.9	44.4	44.4	45.2	47.5
87.5°	23.8	23.8	24.3	23.7	23.6	24.3	24.4	23.9	24.6	25.3	24.8
90°	39.5	39.2	39.0	38.7	38.5	38.6	39.1	39.6	40.1	40.7	35.0
92.5°	37.6	37.6	37.5	37.5	37.4	37.4	37.2	37.1	37.0	36.9	35.6
95°	72.0	72.5	73.1	73.6	74.1	74.3	74.3	74.3	74.3	74.3	73.8
97.5°	124.8	124.8	124.9	124.9	125.0	125.0	125.0	125.0	125.0	125.0	124.0
100°	159.1	159.4	159.7	159.9	160.2	160.3	160.3	160.3	160.3	160.3	159.5
102.5°	198.2	198.4	198.7	198.9	199.2	199.2	199.0	198.8	198.6	198.4	197.4
105°	257.9	257.9	257.9	257.9	257.9	257.6	257.1	256.6	256.1	255.5	255.0
107.5°	314.1	315.3	316.5	317.7	318.8	319.3	319.1	318.9	318.7	318.5	318.5
110°	357.8	358.5	359.3	360.1	360.9	361.3	361.3	361.3	361.3	361.3	361.3



TEST NUMBER: P331457

CATALOG NUMBER: SA2XXDIP-C1005D1080U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	399.6	400.2	400.7	401.3	401.9	402.5	403.1	403.7	404.3	404.9	405.1
115°	464.6	465.4	466.2	467.0	467.7	468.2	468.5	468.8	469.0	469.3	469.8
117.5°	526.7	527.4	528.2	529.0	529.8	530.5	531.1	531.7	532.3	532.9	534.4
120°	570.3	571.1	571.9	572.7	573.4	573.8	573.8	573.8	573.8	573.8	575.9
122.5°	613.1	613.7	614.2	614.8	615.4	615.9	616.6	617.2	617.8	618.4	619.9
125°	678.4	678.6	678.9	679.1	679.4	679.9	680.7	681.5	682.2	683.0	683.8
127.5°	737.8	738.7	739.5	740.3	741.1	742.0	742.9	743.9	744.8	745.7	746.7
130°	780.6	781.6	782.6	783.7	784.7	785.5	786.0	786.5	787.0	787.6	788.1
132.5°	821.5	822.3	823.1	824.0	824.8	825.8	826.9	828.0	829.2	830.3	830.2
135°	885.1	885.9	886.7	887.4	888.2	888.7	889.0	889.3	889.5	889.8	889.3
137.5°	942.7	943.8	944.8	945.8	946.9	947.5	947.7	947.9	948.1	948.3	947.6
140°	982.7	983.7	984.8	985.8	986.8	987.3	987.3	987.3	987.3	987.3	986.1
142.5°	1018.9	1020.0	1021.0	1022.0	1023.1	1023.5	1023.3	1023.1	1022.9	1022.7	1021.8
145°	1073.3	1074.3	1075.4	1076.4	1077.4	1077.8	1077.6	1077.3	1077.0	1076.8	1075.2
147.5°	1121.9	1122.8	1123.8	1124.8	1125.8	1126.0	1125.4	1124.9	1124.3	1123.7	1122.7
150°	1153.5	1154.2	1155.0	1155.8	1156.6	1156.6	1155.8	1155.0	1154.2	1153.5	1152.4
152.5°	1183.2	1184.2	1185.2	1186.1	1187.1	1187.1	1186.1	1185.2	1184.2	1183.2	1182.0
155°	1223.1	1223.9	1224.7	1225.5	1226.2	1226.0	1224.7	1223.4	1222.1	1220.8	1220.1
157.5°	1257.5	1258.8	1260.0	1261.2	1262.5	1262.2	1260.5	1258.7	1257.0	1255.2	1254.7
160°	1278.9	1279.9	1281.0	1282.0	1283.0	1282.8	1281.2	1279.7	1278.1	1276.6	1276.3
162.5°	1297.5	1298.7	1300.0	1301.2	1302.4	1302.2	1300.4	1298.7	1296.9	1295.2	1294.9
165°	1321.9	1323.2	1324.5	1325.8	1327.0	1326.8	1325.0	1323.2	1321.4	1319.6	1319.6
167.5°	1341.9	1343.2	1344.5	1345.9	1347.2	1347.0	1345.2	1343.4	1341.6	1339.8	1339.8
170°	1352.1	1353.6	1355.2	1356.7	1358.3	1358.1	1356.3	1354.5	1352.7	1350.9	1351.2
172.5°	1360.4	1362.0	1363.5	1365.1	1366.6	1366.5	1364.7	1362.9	1361.1	1359.3	1359.5
175°	1369.5	1371.1	1372.6	1374.2	1375.7	1375.6	1373.8	1372.0	1370.2	1368.3	1368.9
177.5°	1373.7	1374.9	1376.2	1377.4	1378.6	1378.6	1377.4	1376.2	1374.9	1373.7	1374.1
180°	1376.5	1376.5	1376.5	1376.5	1376.5	1376.5	1376.5	1376.5	1376.5	1376.5	1376.5



TEST NUMBER: P331457

CATALOG NUMBER: SA2XXDIP-C1005D1080U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0
2.5°	2046.2	2041.3	2038.2	2027.2	2017.3	2007.5	2004.5	2005.7	1992.2	1979.3	1973.8
5°	2125.9	2110.5	2096.0	2075.3	2050.8	2023.9	2010.1	1999.4	1972.6	1943.5	1926.6
7.5°	2197.3	2175.4	2147.3	2108.4	2072.7	2030.5	2003.7	1979.9	1940.7	1899.6	1874.5
10°	2240.8	2210.9	2174.9	2127.4	2083.7	2032.4	1996.3	1960.3	1914.3	1865.3	1834.6
12.5°	2278.2	2237.9	2202.5	2141.5	2089.8	2025.6	1982.9	1932.1	1883.7	1825.4	1795.4
15°	2367.3	2292.9	2225.5	2156.5	2092.9	2003.2	1955.7	1887.5	1823.9	1751.9	1717.4
17.5°	2436.1	2352.5	2246.3	2158.7	2084.5	1985.2	1915.4	1833.7	1758.5	1676.2	1629.3
20°	2475.3	2379.5	2265.3	2161.1	2072.2	1958.8	1882.9	1799.4	1711.3	1618.5	1568.0
22.5°	2498.6	2397.9	2285.0	2151.9	2047.7	1937.3	1841.8	1750.3	1661.0	1560.9	1507.9
25°	2506.0	2414.0	2294.5	2144.3	2017.0	1892.1	1777.2	1688.3	1580.2	1486.7	1409.3
27.5°	2469.5	2403.6	2288.6	2129.8	1981.6	1835.6	1707.4	1606.7	1492.7	1391.2	1313.4
30°	2424.7	2386.4	2274.5	2115.1	1953.4	1796.3	1655.3	1541.1	1427.7	1325.0	1245.3
32.5°	2355.5	2347.2	2248.8	2094.3	1923.4	1746.7	1600.8	1485.3	1359.7	1258.8	1182.8
35°	2219.4	2256.1	2194.1	2047.7	1866.8	1676.0	1518.1	1386.3	1256.1	1159.5	1088.2
37.5°	2037.0	2128.3	2112.1	1979.5	1790.5	1599.1	1424.8	1287.0	1162.9	1065.4	995.5
40°	1911.3	2027.8	2044.6	1927.4	1736.6	1539.6	1354.9	1217.7	1096.6	1007.8	937.2
42.5°	1776.4	1912.5	1958.8	1864.8	1677.7	1477.1	1292.4	1150.3	1030.4	944.0	881.5
45°	1550.3	1730.4	1814.0	1760.3	1579.5	1374.1	1184.0	1039.9	931.1	849.9	801.6
47.5°	1339.0	1535.8	1648.1	1629.1	1470.2	1266.8	1078.9	940.6	834.7	769.9	726.7
50°	1189.4	1391.7	1527.3	1533.5	1391.7	1190.1	1001.6	871.3	774.0	713.5	678.2
52.5°	1059.4	1252.5	1400.4	1432.9	1304.0	1110.4	932.3	802.7	717.0	661.4	629.8
55°	889.7	1053.0	1217.0	1276.7	1173.3	989.4	824.6	710.4	629.9	591.6	564.0
57.5°	739.7	875.8	1027.2	1093.3	1029.5	872.1	717.6	618.4	553.2	519.6	498.4
60°	660.6	767.9	902.8	981.7	926.5	786.3	651.4	557.1	503.5	473.6	453.7
62.5°	587.0	682.1	796.1	868.3	838.2	706.0	585.2	502.0	455.7	427.6	413.2
65°	484.3	559.4	647.6	714.2	694.3	593.9	495.1	423.8	387.0	364.8	353.3
67.5°	398.8	453.1	514.2	572.6	556.5	485.4	406.0	350.5	323.1	303.9	297.0
70°	344.9	386.2	440.7	487.4	474.4	416.1	353.3	305.8	282.0	265.9	259.0
72.5°	293.4	327.4	368.9	407.1	398.3	349.9	297.5	261.6	243.4	228.5	222.9
75°	221.5	247.5	272.8	298.1	295.8	258.3	227.6	200.0	185.5	174.0	171.7
77.5°	163.5	178.1	195.3	210.3	206.1	184.7	160.6	144.8	134.1	126.4	125.2
80°	124.9	133.3	145.6	156.3	151.0	141.8	122.6	111.1	103.5	95.8	92.7
82.5°	90.6	99.0	106.4	112.2	108.1	99.5	87.7	79.9	75.3	70.0	68.8
85°	47.5	52.1	55.2	56.7	55.2	49.8	44.4	41.4	37.6	35.3	34.5
87.5°	24.3	23.1	22.0	22.3	19.9	19.3	16.2	13.7	13.7	13.7	13.1
90°	29.3	23.6	17.9	13.6	10.5	7.4	4.3	1.2	4.3	7.4	10.5
92.5°	34.3	32.9	31.6	29.8	27.5	25.2	22.9	20.7	22.9	25.2	27.5
95°	73.3	72.8	72.3	70.7	68.1	65.6	63.0	60.4	63.0	65.6	68.1
97.5°	123.0	122.0	121.1	119.4	117.2	114.9	112.6	110.4	112.6	114.9	117.2
100°	158.7	158.0	157.2	155.8	153.7	151.7	149.6	147.5	149.6	151.7	153.7
102.5°	196.4	195.5	194.5	193.2	191.5	189.9	188.2	186.6	188.2	189.9	191.5
105°	254.5	254.0	253.5	252.8	252.1	251.3	250.5	249.7	250.5	251.3	252.1
107.5°	318.5	318.5	318.5	317.9	316.8	315.7	314.5	313.4	314.5	315.7	316.8
110°	361.3	361.3	361.3	360.5	358.9	357.4	355.8	354.3	355.8	357.4	358.9



TEST NUMBER: P331457

CATALOG NUMBER: SA2XXDIP-C1005D1080U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	405.3	405.5	405.8	405.1	403.5	402.0	400.4	398.9	400.4	402.0	403.5
115°	470.3	470.8	471.3	470.8	469.3	467.7	466.2	464.6	466.2	467.7	469.3
117.5°	535.8	537.3	538.7	538.4	536.3	534.3	532.2	530.1	532.2	534.3	536.3
120°	578.0	580.0	582.1	582.1	580.0	578.0	575.9	573.8	575.9	578.0	580.0
122.5°	621.3	622.8	624.2	623.7	621.2	618.7	616.3	613.8	616.3	618.7	621.2
125°	684.6	685.3	686.1	685.3	683.0	680.7	678.4	676.0	678.4	680.7	683.0
127.5°	747.6	748.5	749.5	748.4	745.5	742.6	739.6	736.7	739.6	742.6	745.5
130°	788.6	789.1	789.6	788.2	784.8	781.5	778.1	774.8	778.1	781.5	784.8
132.5°	830.1	830.0	829.9	828.5	825.7	823.0	820.3	817.5	820.3	823.0	825.7
135°	888.7	888.2	887.7	886.0	883.2	880.4	877.5	874.7	877.5	880.4	883.2
137.5°	947.0	946.3	945.6	944.1	941.8	939.5	937.2	934.8	937.2	939.5	941.8
140°	984.8	983.5	982.2	980.4	978.1	975.7	973.4	971.1	973.4	975.7	978.1
142.5°	1020.9	1020.0	1019.1	1017.5	1015.2	1012.9	1010.6	1008.3	1010.6	1012.9	1015.2
145°	1073.7	1072.1	1070.6	1068.9	1067.1	1065.3	1063.5	1061.7	1063.5	1065.3	1067.1
147.5°	1121.7	1120.6	1119.6	1118.0	1115.8	1113.6	1111.5	1109.3	1111.5	1113.6	1115.8
150°	1151.4	1150.4	1149.3	1148.0	1146.5	1144.9	1143.4	1141.8	1143.4	1144.9	1146.5
152.5°	1180.7	1179.5	1178.2	1176.8	1175.3	1173.7	1172.2	1170.6	1172.2	1173.7	1175.3
155°	1219.3	1218.5	1217.7	1217.0	1216.2	1215.4	1214.6	1213.9	1214.6	1215.4	1216.2
157.5°	1254.3	1253.8	1253.3	1252.9	1252.3	1251.8	1251.3	1250.8	1251.3	1251.8	1252.3
160°	1276.1	1275.8	1275.5	1275.2	1274.6	1274.1	1273.6	1273.1	1273.6	1274.1	1274.6
162.5°	1294.6	1294.4	1294.1	1294.0	1293.8	1293.7	1293.6	1293.5	1293.6	1293.7	1293.8
165°	1319.6	1319.6	1319.6	1319.7	1319.9	1320.2	1320.5	1320.7	1320.5	1320.2	1319.9
167.5°	1339.9	1339.9	1340.0	1340.4	1341.2	1341.9	1342.7	1343.5	1342.7	1341.9	1341.2
170°	1351.4	1351.7	1352.0	1352.5	1353.2	1354.0	1354.8	1355.6	1354.8	1354.0	1353.2
172.5°	1359.8	1360.1	1360.3	1360.8	1361.6	1362.4	1363.2	1363.9	1363.2	1362.4	1361.6
175°	1369.4	1369.9	1370.4	1371.1	1371.8	1372.6	1373.4	1374.2	1373.4	1372.6	1371.8
177.5°	1374.5	1374.9	1375.3	1375.9	1376.5	1377.1	1377.7	1378.3	1377.7	1377.1	1376.5
180°	1376.5	1376.5	1376.5	1376.5	1376.5	1376.5	1376.5	1376.5	1376.5	1376.5	1376.5



TEST NUMBER: P331457

CATALOG NUMBER: SA2XXDIP-C1005D1080U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0
2.5°	1967.7	1964.0	1951.1	1944.4	1933.4	1922.9	1916.2	1919.3	1921.7	1920.5	1918.6
5°	1911.3	1896.7	1874.5	1855.3	1841.5	1816.3	1805.5	1800.2	1795.6	1790.2	1784.8
7.5°	1844.1	1821.2	1789.3	1762.0	1736.2	1704.8	1686.9	1676.2	1665.1	1653.0	1642.3
10°	1796.3	1764.1	1730.4	1692.1	1661.5	1633.1	1607.8	1590.9	1575.6	1561.1	1550.3
12.5°	1746.1	1709.0	1667.3	1614.9	1581.1	1540.5	1536.7	1507.0	1483.0	1474.0	1461.4
15°	1666.0	1613.9	1561.1	1499.0	1472.2	1435.4	1412.4	1389.4	1368.7	1354.1	1350.3
17.5°	1575.2	1507.7	1455.1	1410.5	1366.6	1328.9	1307.7	1289.3	1272.3	1252.8	1250.2
20°	1505.9	1447.6	1390.2	1351.1	1305.9	1267.5	1241.5	1223.1	1208.5	1197.0	1187.1
22.5°	1440.3	1376.5	1323.9	1281.2	1236.6	1205.6	1185.1	1167.3	1155.2	1142.5	1133.1
25°	1335.0	1285.2	1227.7	1179.4	1142.6	1122.7	1105.8	1090.5	1082.9	1074.4	1063.7
27.5°	1242.9	1187.5	1133.7	1096.3	1064.0	1046.4	1034.4	1024.0	1016.8	1011.9	1005.8
30°	1177.9	1121.9	1079.8	1043.0	1016.2	998.6	990.9	984.8	976.3	973.3	970.2
32.5°	1115.3	1064.9	1028.9	997.0	971.4	959.9	952.9	947.4	940.8	937.7	931.6
35°	1026.9	984.8	949.5	931.9	911.2	901.2	895.9	888.2	882.1	879.0	878.2
37.5°	943.7	907.1	883.9	861.2	852.5	846.4	839.0	833.8	832.0	831.5	830.7
40°	889.7	859.8	839.2	820.8	816.9	807.7	801.6	797.0	797.0	797.8	797.0
42.5°	840.7	813.9	795.6	779.7	775.2	769.7	763.6	763.3	764.5	767.1	764.5
45°	766.4	747.2	734.2	726.5	718.1	712.7	711.9	714.2	715.0	715.8	718.1
47.5°	698.0	685.3	673.5	665.0	661.4	660.4	659.5	663.5	667.2	668.6	672.1
50°	657.5	643.0	633.0	627.6	624.6	623.0	624.6	629.2	632.2	636.1	638.4
52.5°	612.2	601.9	595.0	590.9	589.6	590.6	590.9	596.1	601.0	602.4	603.4
55°	549.5	541.8	540.3	533.4	536.4	535.7	539.5	542.6	547.2	551.8	552.5
57.5°	486.9	480.8	476.7	477.3	478.2	481.6	484.8	490.2	495.1	500.0	500.4
60°	445.3	442.2	439.9	439.9	441.4	446.0	449.8	455.2	458.3	461.3	463.6
62.5°	407.2	404.2	401.9	403.1	407.1	409.8	414.3	417.2	420.3	423.3	424.4
65°	347.2	345.6	347.9	349.5	350.2	354.1	359.4	361.7	364.8	366.3	371.7
67.5°	291.8	292.1	291.8	294.0	298.4	299.3	304.4	309.8	310.4	313.3	316.8
70°	254.4	256.0	257.5	259.0	262.9	264.4	268.2	270.5	273.6	275.9	278.2
72.5°	220.1	220.4	221.9	221.6	224.8	228.2	231.4	233.7	236.8	239.7	242.0
75°	169.4	169.4	170.9	171.7	175.5	179.3	178.6	180.1	183.2	186.2	187.8
77.5°	123.7	122.0	123.7	124.5	125.7	128.9	129.5	131.7	135.2	134.1	135.8
80°	94.3	92.0	94.3	95.0	95.0	98.9	98.9	100.4	102.7	100.4	102.7
82.5°	67.3	66.2	67.9	68.1	69.3	69.4	70.7	71.0	73.3	72.2	73.3
85°	33.7	33.0	33.7	33.0	33.7	34.5	34.5	33.7	33.7	35.3	33.0
87.5°	13.1	13.4	13.9	15.1	15.6	16.1	15.4	15.3	15.2	13.8	13.8
90°	13.6	17.9	23.6	29.3	35.0	40.7	40.1	39.6	39.1	38.6	38.5
92.5°	29.8	31.6	32.9	34.3	35.6	36.9	37.0	37.1	37.2	37.4	37.4
95°	70.7	72.3	72.8	73.3	73.8	74.3	74.3	74.3	74.3	74.3	74.1
97.5°	119.4	121.1	122.0	123.0	124.0	125.0	125.0	125.0	125.0	125.0	125.0
100°	155.8	157.2	158.0	158.7	159.5	160.3	160.3	160.3	160.3	160.3	160.2
102.5°	193.2	194.5	195.5	196.4	197.4	198.4	198.6	198.8	199.0	199.2	199.2
105°	252.8	253.5	254.0	254.5	255.0	255.5	256.1	256.6	257.1	257.6	257.9
107.5°	317.9	318.5	318.5	318.5	318.5	318.5	318.7	318.9	319.1	319.3	318.8
110°	360.5	361.3	361.3	361.3	361.3	361.3	361.3	361.3	361.3	361.3	360.9



TEST NUMBER: P331457

CATALOG NUMBER: SA2XXDIP-C1005D1080U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	405.1	405.8	405.5	405.3	405.1	404.9	404.3	403.7	403.1	402.5	401.9
115°	470.8	471.3	470.8	470.3	469.8	469.3	469.0	468.8	468.5	468.2	467.7
117.5°	538.4	538.7	537.3	535.8	534.4	532.9	532.3	531.7	531.1	530.5	529.8
120°	582.1	582.1	580.0	578.0	575.9	573.8	573.8	573.8	573.8	573.8	573.4
122.5°	623.7	624.2	622.8	621.3	619.9	618.4	617.8	617.2	616.6	615.9	615.4
125°	685.3	686.1	685.3	684.6	683.8	683.0	682.2	681.5	680.7	679.9	679.4
127.5°	748.4	749.5	748.5	747.6	746.7	745.7	744.8	743.9	742.9	742.0	741.1
130°	788.2	789.6	789.1	788.6	788.1	787.6	787.0	786.5	786.0	785.5	784.7
132.5°	828.5	829.9	830.0	830.1	830.2	830.3	829.2	828.0	826.9	825.8	824.8
135°	886.0	887.7	888.2	888.7	889.3	889.8	889.5	889.3	889.0	888.7	888.2
137.5°	944.1	945.6	946.3	947.0	947.6	948.3	948.1	947.9	947.7	947.5	946.9
140°	980.4	982.2	983.5	984.8	986.1	987.3	987.3	987.3	987.3	987.3	986.8
142.5°	1017.5	1019.1	1020.0	1020.9	1021.8	1022.7	1022.9	1023.1	1023.3	1023.5	1023.1
145°	1068.9	1070.6	1072.1	1073.7	1075.2	1076.8	1077.0	1077.3	1077.6	1077.8	1077.4
147.5°	1118.0	1119.6	1120.6	1121.7	1122.7	1123.7	1124.3	1124.9	1125.4	1126.0	1125.8
150°	1148.0	1149.3	1150.4	1151.4	1152.4	1153.5	1154.2	1155.0	1155.8	1156.6	1156.6
152.5°	1176.8	1178.2	1179.5	1180.7	1182.0	1183.2	1184.2	1185.2	1186.1	1187.1	1187.1
155°	1217.0	1217.7	1218.5	1219.3	1220.1	1220.8	1222.1	1223.4	1224.7	1226.0	1226.2
157.5°	1252.9	1253.3	1253.8	1254.3	1254.7	1255.2	1257.0	1258.7	1260.5	1262.2	1262.5
160°	1275.2	1275.5	1275.8	1276.1	1276.3	1276.6	1278.1	1279.7	1281.2	1282.8	1283.0
162.5°	1294.0	1294.1	1294.4	1294.6	1294.9	1295.2	1296.9	1298.7	1300.4	1302.2	1302.4
165°	1319.7	1319.6	1319.6	1319.6	1319.6	1319.6	1321.4	1323.2	1325.0	1326.8	1327.0
167.5°	1340.4	1340.0	1339.9	1339.9	1339.8	1339.8	1341.6	1343.4	1345.2	1347.0	1347.2
170°	1352.5	1352.0	1351.7	1351.4	1351.2	1350.9	1352.7	1354.5	1356.3	1358.1	1358.3
172.5°	1360.8	1360.3	1360.1	1359.8	1359.5	1359.3	1361.1	1362.9	1364.7	1366.5	1366.6
175°	1371.1	1370.4	1369.9	1369.4	1368.9	1368.3	1370.2	1372.0	1373.8	1375.6	1375.7
177.5°	1375.9	1375.3	1374.9	1374.5	1374.1	1373.7	1374.9	1376.2	1377.4	1378.6	1378.6
180°	1376.5	1376.5	1376.5	1376.5	1376.5	1376.5	1376.5	1376.5	1376.5	1376.5	1376.5



TEST NUMBER: P331457

CATALOG NUMBER: SA2XXDIP-C1005D1080U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0
2.5°	1912.5	1911.3	1911.3	1905.8	1911.3	1911.3	1912.5	1918.6	1920.5	1921.7	1919.3
5°	1774.1	1771.8	1768.0	1771.8	1768.0	1771.8	1774.1	1784.8	1790.2	1795.6	1800.2
7.5°	1637.2	1628.0	1626.7	1617.6	1626.7	1628.0	1637.2	1642.3	1653.0	1665.1	1676.2
10°	1537.3	1531.2	1530.4	1515.8	1530.4	1531.2	1537.3	1550.3	1561.1	1575.6	1590.9
12.5°	1461.3	1446.6	1449.5	1441.0	1449.5	1446.6	1461.3	1461.4	1474.0	1483.0	1507.0
15°	1329.6	1329.6	1326.6	1313.5	1326.6	1329.6	1329.6	1350.3	1354.1	1368.7	1389.4
17.5°	1235.1	1233.5	1226.2	1229.8	1226.2	1233.5	1235.1	1250.2	1252.8	1272.3	1289.3
20°	1178.6	1174.1	1164.9	1164.9	1164.9	1174.1	1178.6	1187.1	1197.0	1208.5	1223.1
22.5°	1125.3	1125.0	1115.2	1118.3	1115.2	1125.0	1125.3	1133.1	1142.5	1155.2	1167.3
25°	1062.9	1056.8	1052.2	1054.5	1052.2	1056.8	1062.9	1063.7	1074.4	1082.9	1090.5
27.5°	1003.8	1000.4	1000.1	993.8	1000.1	1000.4	1003.8	1005.8	1011.9	1016.8	1024.0
30°	969.4	961.8	963.3	959.5	963.3	961.8	969.4	970.2	973.3	976.3	984.8
32.5°	930.2	927.4	925.9	922.7	925.9	927.4	930.2	931.6	937.7	940.8	947.4
35°	876.7	877.5	873.6	875.2	873.6	877.5	876.7	878.2	879.0	882.1	888.2
37.5°	830.0	832.4	830.6	831.0	830.6	832.4	830.0	830.7	831.5	832.0	833.8
40°	799.3	799.3	799.3	801.6	799.3	799.3	799.3	797.0	797.8	797.0	797.0
42.5°	769.9	768.7	767.4	767.3	767.4	768.7	769.9	764.5	767.1	764.5	763.3
45°	719.6	721.9	722.7	718.8	722.7	721.9	719.6	718.1	715.8	715.0	714.2
47.5°	674.1	674.4	674.1	677.5	674.1	674.4	674.1	672.1	668.6	667.2	663.5
50°	642.2	640.7	642.2	640.7	642.2	640.7	642.2	638.4	636.1	632.2	629.2
52.5°	608.5	608.8	607.9	607.6	607.9	608.8	608.5	603.4	602.4	601.0	596.1
55°	555.6	557.1	556.4	556.4	556.4	557.1	555.6	552.5	551.8	547.2	542.6
57.5°	500.9	502.3	503.3	500.0	503.3	502.3	500.9	500.4	500.0	495.1	490.2
60°	462.9	466.7	465.9	464.4	465.9	466.7	462.9	463.6	461.3	458.3	455.2
62.5°	427.9	429.3	429.2	428.9	429.2	429.3	427.9	424.4	423.3	420.3	417.2
65°	374.0	375.5	373.2	375.5	373.2	375.5	374.0	371.7	366.3	364.8	361.7
67.5°	315.9	316.4	318.0	319.1	318.0	316.4	315.9	316.8	313.3	310.4	309.8
70°	279.7	279.0	281.3	283.6	281.3	279.0	279.7	278.2	275.9	273.6	270.5
72.5°	241.7	243.4	242.6	244.3	242.6	243.4	241.7	242.0	239.7	236.8	233.7
75°	186.2	188.5	187.8	190.1	187.8	188.5	186.2	187.8	186.2	183.2	180.1
77.5°	134.6	134.9	134.6	135.8	134.6	134.9	134.6	135.8	134.1	135.2	131.7
80°	102.7	101.2	99.6	102.7	99.6	101.2	102.7	102.7	100.4	102.7	100.4
82.5°	71.4	72.3	70.8	70.8	70.8	72.3	71.4	73.3	72.2	73.3	71.0
85°	33.0	32.2	30.7	30.7	30.7	32.2	33.0	33.0	35.3	33.7	33.7
87.5°	13.9	13.3	13.4	12.8	13.4	13.3	13.9	13.8	13.8	15.2	15.3
90°	38.7	39.0	39.2	39.5	39.2	39.0	38.7	38.5	38.6	39.1	39.6
92.5°	37.5	37.5	37.6	37.6	37.6	37.5	37.5	37.4	37.4	37.2	37.1
95°	73.6	73.1	72.5	72.0	72.5	73.1	73.6	74.1	74.3	74.3	74.3
97.5°	124.9	124.9	124.8	124.8	124.8	124.9	124.9	125.0	125.0	125.0	125.0
100°	159.9	159.7	159.4	159.1	159.4	159.7	159.9	160.2	160.3	160.3	160.3
102.5°	198.9	198.7	198.4	198.2	198.4	198.7	198.9	199.2	199.2	199.0	198.8
105°	257.9	257.9	257.9	257.9	257.9	257.9	257.9	257.9	257.6	257.1	256.6
107.5°	317.7	316.5	315.3	314.1	315.3	316.5	317.7	318.8	319.3	319.1	318.9
110°	360.1	359.3	358.5	357.8	358.5	359.3	360.1	360.9	361.3	361.3	361.3



TEST NUMBER: P331457

CATALOG NUMBER: SA2XXDIP-C1005D1080U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	401.3	400.7	400.2	399.6	400.2	400.7	401.3	401.9	402.5	403.1	403.7
115°	467.0	466.2	465.4	464.6	465.4	466.2	467.0	467.7	468.2	468.5	468.8
117.5°	529.0	528.2	527.4	526.7	527.4	528.2	529.0	529.8	530.5	531.1	531.7
120°	572.7	571.9	571.1	570.3	571.1	571.9	572.7	573.4	573.8	573.8	573.8
122.5°	614.8	614.2	613.7	613.1	613.7	614.2	614.8	615.4	615.9	616.6	617.2
125°	679.1	678.9	678.6	678.4	678.6	678.9	679.1	679.4	679.9	680.7	681.5
127.5°	740.3	739.5	738.7	737.8	738.7	739.5	740.3	741.1	742.0	742.9	743.9
130°	783.7	782.6	781.6	780.6	781.6	782.6	783.7	784.7	785.5	786.0	786.5
132.5°	824.0	823.1	822.3	821.5	822.3	823.1	824.0	824.8	825.8	826.9	828.0
135°	887.4	886.7	885.9	885.1	885.9	886.7	887.4	888.2	888.7	889.0	889.3
137.5°	945.8	944.8	943.8	942.7	943.8	944.8	945.8	946.9	947.5	947.7	947.9
140°	985.8	984.8	983.7	982.7	983.7	984.8	985.8	986.8	987.3	987.3	987.3
142.5°	1022.0	1021.0	1020.0	1018.9	1020.0	1021.0	1022.0	1023.1	1023.5	1023.3	1023.1
145°	1076.4	1075.4	1074.3	1073.3	1074.3	1075.4	1076.4	1077.4	1077.8	1077.6	1077.3
147.5°	1124.8	1123.8	1122.8	1121.9	1122.8	1123.8	1124.8	1125.8	1126.0	1125.4	1124.9
150°	1155.8	1155.0	1154.2	1153.5	1154.2	1155.0	1155.8	1156.6	1156.6	1155.8	1155.0
152.5°	1186.1	1185.2	1184.2	1183.2	1184.2	1185.2	1186.1	1187.1	1187.1	1186.1	1185.2
155°	1225.5	1224.7	1223.9	1223.1	1223.9	1224.7	1225.5	1226.2	1226.0	1224.7	1223.4
157.5°	1261.2	1260.0	1258.8	1257.5	1258.8	1260.0	1261.2	1262.5	1262.2	1260.5	1258.7
160°	1282.0	1281.0	1279.9	1278.9	1279.9	1281.0	1282.0	1283.0	1282.8	1281.2	1279.7
162.5°	1301.2	1300.0	1298.7	1297.5	1298.7	1300.0	1301.2	1302.4	1302.2	1300.4	1298.7
165°	1325.8	1324.5	1323.2	1321.9	1323.2	1324.5	1325.8	1327.0	1326.8	1325.0	1323.2
167.5°	1345.9	1344.5	1343.2	1341.9	1343.2	1344.5	1345.9	1347.2	1347.0	1345.2	1343.4
170°	1356.7	1355.2	1353.6	1352.1	1353.6	1355.2	1356.7	1358.3	1358.1	1356.3	1354.5
172.5°	1365.1	1363.5	1362.0	1360.4	1362.0	1363.5	1365.1	1366.6	1366.5	1364.7	1362.9
175°	1374.2	1372.6	1371.1	1369.5	1371.1	1372.6	1374.2	1375.7	1375.6	1373.8	1372.0
177.5°	1377.4	1376.2	1374.9	1373.7	1374.9	1376.2	1377.4	1378.6	1378.6	1377.4	1376.2
180°	1376.5	1376.5	1376.5	1376.5	1376.5	1376.5	1376.5	1376.5	1376.5	1376.5	1376.5



TEST NUMBER: P331457

CATALOG NUMBER: SA2XXDIP-C1005D1080U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0
2.5°	1916.2	1922.9	1933.4	1944.4	1951.1	1964.0	1967.7	1973.8	1979.3	1992.2	2005.7
5°	1805.5	1816.3	1841.5	1855.3	1874.5	1896.7	1911.3	1926.6	1943.5	1972.6	1999.4
7.5°	1686.9	1704.8	1736.2	1762.0	1789.3	1821.2	1844.1	1874.5	1899.6	1940.7	1979.9
10°	1607.8	1633.1	1661.5	1692.1	1730.4	1764.1	1796.3	1834.6	1865.3	1914.3	1960.3
12.5°	1536.7	1540.5	1581.1	1614.9	1667.3	1709.0	1746.1	1795.4	1825.4	1883.7	1932.1
15°	1412.4	1435.4	1472.2	1499.0	1561.1	1613.9	1666.0	1717.4	1751.9	1823.9	1887.5
17.5°	1307.7	1328.9	1366.6	1410.5	1455.1	1507.7	1575.2	1629.3	1676.2	1758.5	1833.7
20°	1241.5	1267.5	1305.9	1351.1	1390.2	1447.6	1505.9	1568.0	1618.5	1711.3	1799.4
22.5°	1185.1	1205.6	1236.6	1281.2	1323.9	1376.5	1440.3	1507.9	1560.9	1661.0	1750.3
25°	1105.8	1122.7	1142.6	1179.4	1227.7	1285.2	1335.0	1409.3	1486.7	1580.2	1688.3
27.5°	1034.4	1046.4	1064.0	1096.3	1133.7	1187.5	1242.9	1313.4	1391.2	1492.7	1606.7
30°	990.9	998.6	1016.2	1043.0	1079.8	1121.9	1177.9	1245.3	1325.0	1427.7	1541.1
32.5°	952.9	959.9	971.4	997.0	1028.9	1064.9	1115.3	1182.8	1258.8	1359.7	1485.3
35°	895.9	901.2	911.2	931.9	949.5	984.8	1026.9	1088.2	1159.5	1256.1	1386.3
37.5°	839.0	846.4	852.5	861.2	883.9	907.1	943.7	995.5	1065.4	1162.9	1287.0
40°	801.6	807.7	816.9	820.8	839.2	859.8	889.7	937.2	1007.8	1096.6	1217.7
42.5°	763.6	769.7	775.2	779.7	795.6	813.9	840.7	881.5	944.0	1030.4	1150.3
45°	711.9	712.7	718.1	726.5	734.2	747.2	766.4	801.6	849.9	931.1	1039.9
47.5°	659.5	660.4	661.4	665.0	673.5	685.3	698.0	726.7	769.9	834.7	940.6
50°	624.6	623.0	624.6	627.6	633.0	643.0	657.5	678.2	713.5	774.0	871.3
52.5°	590.9	590.6	589.6	590.9	595.0	601.9	612.2	629.8	661.4	717.0	802.7
55°	539.5	535.7	536.4	533.4	540.3	541.8	549.5	564.0	591.6	629.9	710.4
57.5°	484.8	481.6	478.2	477.3	476.7	480.8	486.9	498.4	519.6	553.2	618.4
60°	449.8	446.0	441.4	439.9	439.9	442.2	445.3	453.7	473.6	503.5	557.1
62.5°	414.3	409.8	407.1	403.1	401.9	404.2	407.2	413.2	427.6	455.7	502.0
65°	359.4	354.1	350.2	349.5	347.9	345.6	347.2	353.3	364.8	387.0	423.8
67.5°	304.4	299.3	298.4	294.0	291.8	292.1	291.8	297.0	303.9	323.1	350.5
70°	268.2	264.4	262.9	259.0	257.5	256.0	254.4	259.0	265.9	282.0	305.8
72.5°	231.4	228.2	224.8	221.6	221.9	220.4	220.1	222.9	228.5	243.4	261.6
75°	178.6	179.3	175.5	171.7	170.9	169.4	169.4	171.7	174.0	185.5	200.0
77.5°	129.5	128.9	125.7	124.5	123.7	122.0	123.7	125.2	126.4	134.1	144.8
80°	98.9	98.9	95.0	95.0	94.3	92.0	94.3	92.7	95.8	103.5	111.1
82.5°	70.7	69.4	69.3	68.1	67.9	66.2	67.3	68.8	70.0	75.3	79.9
85°	34.5	34.5	33.7	33.0	33.7	33.0	33.7	34.5	35.3	37.6	41.4
87.5°	15.4	16.1	15.6	15.1	13.9	13.4	13.1	13.1	13.7	13.7	13.7
90°	40.1	40.7	35.0	29.3	23.6	17.9	13.6	10.5	7.4	4.3	1.2
92.5°	37.0	36.9	35.6	34.3	32.9	31.6	29.8	27.5	25.2	22.9	20.7
95°	74.3	74.3	73.8	73.3	72.8	72.3	70.7	68.1	65.6	63.0	60.4
97.5°	125.0	125.0	124.0	123.0	122.0	121.1	119.4	117.2	114.9	112.6	110.4
100°	160.3	160.3	159.5	158.7	158.0	157.2	155.8	153.7	151.7	149.6	147.5
102.5°	198.6	198.4	197.4	196.4	195.5	194.5	193.2	191.5	189.9	188.2	186.6
105°	256.1	255.5	255.0	254.5	254.0	253.5	252.8	252.1	251.3	250.5	249.7
107.5°	318.7	318.5	318.5	318.5	318.5	318.5	317.9	316.8	315.7	314.5	313.4
110°	361.3	361.3	361.3	361.3	361.3	361.3	360.5	358.9	357.4	355.8	354.3



TEST NUMBER: P331457

CATALOG NUMBER: SA2XXDIP-C1005D1080U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	404.3	404.9	405.1	405.3	405.5	405.8	405.1	403.5	402.0	400.4	398.9
115°	469.0	469.3	469.8	470.3	470.8	471.3	470.8	469.3	467.7	466.2	464.6
117.5°	532.3	532.9	534.4	535.8	537.3	538.7	538.4	536.3	534.3	532.2	530.1
120°	573.8	573.8	575.9	578.0	580.0	582.1	582.1	580.0	578.0	575.9	573.8
122.5°	617.8	618.4	619.9	621.3	622.8	624.2	623.7	621.2	618.7	616.3	613.8
125°	682.2	683.0	683.8	684.6	685.3	686.1	685.3	683.0	680.7	678.4	676.0
127.5°	744.8	745.7	746.7	747.6	748.5	749.5	748.4	745.5	742.6	739.6	736.7
130°	787.0	787.6	788.1	788.6	789.1	789.6	788.2	784.8	781.5	778.1	774.8
132.5°	829.2	830.3	830.2	830.1	830.0	829.9	828.5	825.7	823.0	820.3	817.5
135°	889.5	889.8	889.3	888.7	888.2	887.7	886.0	883.2	880.4	877.5	874.7
137.5°	948.1	948.3	947.6	947.0	946.3	945.6	944.1	941.8	939.5	937.2	934.8
140°	987.3	987.3	986.1	984.8	983.5	982.2	980.4	978.1	975.7	973.4	971.1
142.5°	1022.9	1022.7	1021.8	1020.9	1020.0	1019.1	1017.5	1015.2	1012.9	1010.6	1008.3
145°	1077.0	1076.8	1075.2	1073.7	1072.1	1070.6	1068.9	1067.1	1065.3	1063.5	1061.7
147.5°	1124.3	1123.7	1122.7	1121.7	1120.6	1119.6	1118.0	1115.8	1113.6	1111.5	1109.3
150°	1154.2	1153.5	1152.4	1151.4	1150.4	1149.3	1148.0	1146.5	1144.9	1143.4	1141.8
152.5°	1184.2	1183.2	1182.0	1180.7	1179.5	1178.2	1176.8	1175.3	1173.7	1172.2	1170.6
155°	1222.1	1220.8	1220.1	1219.3	1218.5	1217.7	1217.0	1216.2	1215.4	1214.6	1213.9
157.5°	1257.0	1255.2	1254.7	1254.3	1253.8	1253.3	1252.9	1252.3	1251.8	1251.3	1250.8
160°	1278.1	1276.6	1276.3	1276.1	1275.8	1275.5	1275.2	1274.6	1274.1	1273.6	1273.1
162.5°	1296.9	1295.2	1294.9	1294.6	1294.4	1294.1	1294.0	1293.8	1293.7	1293.6	1293.5
165°	1321.4	1319.6	1319.6	1319.6	1319.6	1319.6	1319.7	1319.9	1320.2	1320.5	1320.7
167.5°	1341.6	1339.8	1339.8	1339.9	1339.9	1340.0	1340.4	1341.2	1341.9	1342.7	1343.5
170°	1352.7	1350.9	1351.2	1351.4	1351.7	1352.0	1352.5	1353.2	1354.0	1354.8	1355.6
172.5°	1361.1	1359.3	1359.5	1359.8	1360.1	1360.3	1360.8	1361.6	1362.4	1363.2	1363.9
175°	1370.2	1368.3	1368.9	1369.4	1369.9	1370.4	1371.1	1371.8	1372.6	1373.4	1374.2
177.5°	1374.9	1373.7	1374.1	1374.5	1374.9	1375.3	1375.9	1376.5	1377.1	1377.7	1378.3
180°	1376.5	1376.5	1376.5	1376.5	1376.5	1376.5	1376.5	1376.5	1376.5	1376.5	1376.5



TEST NUMBER: P331457

CATALOG NUMBER: SA2XXDIP-C1005D1080U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0
2.5°	2004.5	2007.5	2017.3	2027.2	2038.2	2041.3	2046.2	2041.9	2040.6	2052.3	2060.9
5°	2010.1	2023.9	2050.8	2075.3	2096.0	2110.5	2125.9	2132.0	2143.5	2159.6	2179.5
7.5°	2003.7	2030.5	2072.7	2108.4	2147.3	2175.4	2197.3	2216.0	2238.7	2269.2	2302.4
10°	1996.3	2032.4	2083.7	2127.4	2174.9	2210.9	2240.8	2269.9	2303.7	2345.8	2389.5
12.5°	1982.9	2025.6	2089.8	2141.5	2202.5	2237.9	2278.2	2341.1	2377.2	2435.9	2497.4
15°	1955.7	2003.2	2092.9	2156.5	2225.5	2292.9	2367.3	2427.0	2486.8	2521.3	2607.9
17.5°	1915.4	1985.2	2084.5	2158.7	2246.3	2352.5	2436.1	2503.8	2572.8	2628.7	2672.1
20°	1882.9	1958.8	2072.2	2161.1	2265.3	2379.5	2475.3	2544.3	2604.1	2650.8	2677.6
22.5°	1841.8	1937.3	2047.7	2151.9	2285.0	2397.9	2498.6	2552.9	2602.8	2625.7	2635.9
25°	1777.2	1892.1	2017.0	2144.3	2294.5	2414.0	2506.0	2538.9	2553.5	2531.3	2494.5
27.5°	1707.4	1835.6	1981.6	2129.8	2288.6	2403.6	2469.5	2464.3	2439.6	2367.7	2310.2
30°	1655.3	1796.3	1953.4	2115.1	2274.5	2386.4	2424.7	2386.4	2330.5	2250.0	2168.0
32.5°	1600.8	1746.7	1923.4	2094.3	2248.8	2347.2	2355.5	2289.6	2203.0	2111.5	2009.2
35°	1518.1	1676.0	1866.8	2047.7	2194.1	2256.1	2219.4	2102.9	2000.2	1875.3	1735.8
37.5°	1424.8	1599.1	1790.5	1979.5	2112.1	2128.3	2037.0	1914.3	1769.5	1622.7	1458.5
40°	1354.9	1539.6	1736.6	1927.4	2044.6	2027.8	1911.3	1776.4	1604.0	1424.6	1272.1
42.5°	1292.4	1477.1	1677.7	1864.8	1958.8	1912.5	1776.4	1610.9	1425.6	1256.7	1117.0
45°	1184.0	1374.1	1579.5	1760.3	1814.0	1730.4	1550.3	1366.4	1184.0	1043.0	932.7
47.5°	1078.9	1266.8	1470.2	1629.1	1648.1	1535.8	1339.0	1149.7	992.9	878.1	800.2
50°	1001.6	1190.1	1391.7	1533.5	1527.3	1391.7	1189.4	1009.3	878.2	785.5	733.4
52.5°	932.3	1110.4	1304.0	1432.9	1400.4	1252.5	1059.4	899.5	791.8	719.3	672.1
55°	824.6	989.4	1173.3	1276.7	1217.0	1053.0	889.7	761.0	681.3	626.9	590.1
57.5°	717.6	872.1	1029.5	1093.3	1027.2	875.8	739.7	646.3	586.4	546.1	522.2
60°	651.4	786.3	926.5	981.7	902.8	767.9	660.6	577.1	528.8	495.8	474.4
62.5°	585.2	706.0	838.2	868.3	796.1	682.1	587.0	517.6	477.9	448.6	428.4
65°	495.1	593.9	694.3	714.2	647.6	559.4	484.3	439.1	403.9	382.4	366.3
67.5°	406.0	485.4	556.5	572.6	514.2	453.1	398.8	359.4	335.5	317.7	304.1
70°	353.3	416.1	474.4	487.4	440.7	386.2	344.9	313.4	292.0	276.7	263.6
72.5°	297.5	349.9	398.3	407.1	368.9	327.4	293.4	268.7	249.7	239.9	227.5
75°	227.6	258.3	295.8	298.1	272.8	247.5	221.5	205.4	195.4	183.2	177.0
77.5°	160.6	184.7	206.1	210.3	195.3	178.1	163.5	150.8	142.4	136.7	131.0
80°	122.6	141.8	151.0	156.3	145.6	133.3	124.9	116.5	111.1	107.3	103.5
82.5°	87.7	99.5	108.1	112.2	106.4	99.0	90.6	85.8	81.7	78.5	77.1
85°	44.4	49.8	55.2	56.7	55.2	52.1	47.5	47.5	45.2	44.4	44.4
87.5°	16.2	19.3	19.9	22.3	22.0	23.1	24.3	24.8	25.3	24.6	23.9
90°	4.3	7.4	10.5	13.6	17.9	23.6	29.3	35.0	40.7	40.1	39.6
92.5°	22.9	25.2	27.5	29.8	31.6	32.9	34.3	35.6	36.9	37.0	37.1
95°	63.0	65.6	68.1	70.7	72.3	72.8	73.3	73.8	74.3	74.3	74.3
97.5°	112.6	114.9	117.2	119.4	121.1	122.0	123.0	124.0	125.0	125.0	125.0
100°	149.6	151.7	153.7	155.8	157.2	158.0	158.7	159.5	160.3	160.3	160.3
102.5°	188.2	189.9	191.5	193.2	194.5	195.5	196.4	197.4	198.4	198.6	198.8
105°	250.5	251.3	252.1	252.8	253.5	254.0	254.5	255.0	255.5	256.1	256.6
107.5°	314.5	315.7	316.8	317.9	318.5	318.5	318.5	318.5	318.5	318.7	318.9
110°	355.8	357.4	358.9	360.5	361.3	361.3	361.3	361.3	361.3	361.3	361.3



TEST NUMBER: P331457

CATALOG NUMBER: SA2XXDIP-C1005D1080U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	400.4	402.0	403.5	405.1	405.8	405.5	405.3	405.1	404.9	404.3	403.7
115°	466.2	467.7	469.3	470.8	471.3	470.8	470.3	469.8	469.3	469.0	468.8
117.5°	532.2	534.3	536.3	538.4	538.7	537.3	535.8	534.4	532.9	532.3	531.7
120°	575.9	578.0	580.0	582.1	582.1	580.0	578.0	575.9	573.8	573.8	573.8
122.5°	616.3	618.7	621.2	623.7	624.2	622.8	621.3	619.9	618.4	617.8	617.2
125°	678.4	680.7	683.0	685.3	686.1	685.3	684.6	683.8	683.0	682.2	681.5
127.5°	739.6	742.6	745.5	748.4	749.5	748.5	747.6	746.7	745.7	744.8	743.9
130°	778.1	781.5	784.8	788.2	789.6	789.1	788.6	788.1	787.6	787.0	786.5
132.5°	820.3	823.0	825.7	828.5	829.9	830.0	830.1	830.2	830.3	829.2	828.0
135°	877.5	880.4	883.2	886.0	887.7	888.2	888.7	889.3	889.8	889.5	889.3
137.5°	937.2	939.5	941.8	944.1	945.6	946.3	947.0	947.6	948.3	948.1	947.9
140°	973.4	975.7	978.1	980.4	982.2	983.5	984.8	986.1	987.3	987.3	987.3
142.5°	1010.6	1012.9	1015.2	1017.5	1019.1	1020.0	1020.9	1021.8	1022.7	1022.9	1023.1
145°	1063.5	1065.3	1067.1	1068.9	1070.6	1072.1	1073.7	1075.2	1076.8	1077.0	1077.3
147.5°	1111.5	1113.6	1115.8	1118.0	1119.6	1120.6	1121.7	1122.7	1123.7	1124.3	1124.9
150°	1143.4	1144.9	1146.5	1148.0	1149.3	1150.4	1151.4	1152.4	1153.5	1154.2	1155.0
152.5°	1172.2	1173.7	1175.3	1176.8	1178.2	1179.5	1180.7	1182.0	1183.2	1184.2	1185.2
155°	1214.6	1215.4	1216.2	1217.0	1217.7	1218.5	1219.3	1220.1	1220.8	1222.1	1223.4
157.5°	1251.3	1251.8	1252.3	1252.9	1253.3	1253.8	1254.3	1254.7	1255.2	1257.0	1258.7
160°	1273.6	1274.1	1274.6	1275.2	1275.5	1275.8	1276.1	1276.3	1276.6	1278.1	1279.7
162.5°	1293.6	1293.7	1293.8	1294.0	1294.1	1294.4	1294.6	1294.9	1295.2	1296.9	1298.7
165°	1320.5	1320.2	1319.9	1319.7	1319.6	1319.6	1319.6	1319.6	1319.6	1321.4	1323.2
167.5°	1342.7	1341.9	1341.2	1340.4	1340.0	1339.9	1339.9	1339.8	1339.8	1341.6	1343.4
170°	1354.8	1354.0	1353.2	1352.5	1352.0	1351.7	1351.4	1351.2	1350.9	1352.7	1354.5
172.5°	1363.2	1362.4	1361.6	1360.8	1360.3	1360.1	1359.8	1359.5	1359.3	1361.1	1362.9
175°	1373.4	1372.6	1371.8	1371.1	1370.4	1369.9	1369.4	1368.9	1368.3	1370.2	1372.0
177.5°	1377.7	1377.1	1376.5	1375.9	1375.3	1374.9	1374.5	1374.1	1373.7	1374.9	1376.2
180°	1376.5	1376.5	1376.5	1376.5	1376.5	1376.5	1376.5	1376.5	1376.5	1376.5	1376.5



TEST NUMBER: P331457

CATALOG NUMBER: SA2XXDIP-C1005D1080U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0	1994.0
2.5°	2068.2	2076.8	2076.8	2078.0	2087.8	2086.6	2086.0
5°	2201.0	2214.0	2215.5	2229.3	2238.5	2235.4	2227.0
7.5°	2326.2	2350.4	2368.8	2379.1	2391.2	2398.7	2395.3
10°	2425.5	2460.8	2482.2	2496.8	2514.4	2527.4	2522.8
12.5°	2515.6	2557.6	2587.1	2612.0	2614.3	2631.0	2619.7
15°	2656.2	2700.6	2705.2	2723.6	2738.2	2736.6	2737.4
17.5°	2702.6	2716.9	2719.8	2720.2	2720.4	2715.0	2703.4
20°	2686.1	2680.7	2667.7	2657.7	2640.1	2637.8	2622.5
22.5°	2607.6	2590.6	2557.9	2536.3	2508.9	2501.7	2497.4
25°	2453.1	2415.5	2363.4	2313.6	2299.8	2273.0	2280.7
27.5°	2241.1	2182.6	2126.2	2085.7	2049.1	2008.9	2020.4
30°	2092.1	2026.2	1946.5	1885.2	1846.1	1807.8	1800.9
32.5°	1914.3	1817.8	1728.9	1674.9	1615.0	1590.8	1564.3
35°	1607.8	1513.5	1425.4	1349.5	1305.9	1272.1	1241.5
37.5°	1332.1	1223.6	1152.4	1091.0	1059.4	1040.1	1045.0
40°	1161.0	1066.0	1013.9	967.1	938.0	924.2	927.3
42.5°	1022.5	951.3	908.4	876.4	855.9	848.2	846.4
45°	865.2	825.4	790.1	771.7	761.8	753.3	748.0
47.5°	757.9	725.4	705.5	694.6	685.9	677.3	677.1
50°	693.5	672.1	658.3	646.8	639.9	633.8	639.1
52.5°	644.5	624.9	611.1	600.8	598.2	592.7	592.5
55°	571.7	556.4	546.4	537.2	532.6	529.5	525.7
57.5°	505.5	490.9	481.7	475.9	467.2	464.1	462.9
60°	458.3	446.8	437.6	429.9	426.1	420.0	420.0
62.5°	414.7	403.3	394.7	388.8	382.6	380.1	380.7
65°	351.8	342.6	334.1	328.0	326.5	321.9	323.4
67.5°	293.8	287.7	278.8	275.4	272.5	270.1	268.2
70°	255.2	249.1	244.5	239.9	237.6	237.6	237.6
72.5°	222.7	215.3	212.6	206.8	208.1	205.7	203.2
75°	172.4	167.8	165.5	163.2	159.4	159.4	159.4
77.5°	126.9	125.5	122.8	120.3	119.4	118.6	118.9
80°	98.1	97.3	95.8	95.8	94.3	93.5	92.0
82.5°	75.4	73.4	72.5	71.9	71.6	71.4	71.1
85°	42.9	41.4	41.4	42.1	40.6	40.6	41.4
87.5°	24.4	24.3	23.6	23.7	24.3	23.8	23.8
90°	39.1	38.6	38.5	38.7	39.0	39.2	39.5
92.5°	37.2	37.4	37.4	37.5	37.5	37.6	37.6
95°	74.3	74.3	74.1	73.6	73.1	72.5	72.0
97.5°	125.0	125.0	125.0	124.9	124.9	124.8	124.8
100°	160.3	160.3	160.2	159.9	159.7	159.4	159.1
102.5°	199.0	199.2	199.2	198.9	198.7	198.4	198.2
105°	257.1	257.6	257.9	257.9	257.9	257.9	257.9
107.5°	319.1	319.3	318.8	317.7	316.5	315.3	314.1
110°	361.3	361.3	360.9	360.1	359.3	358.5	357.8



TEST NUMBER: P331457

CATALOG NUMBER: SA2XXDIP-C1005D1080U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	403.1	402.5	401.9	401.3	400.7	400.2	399.6
115°	468.5	468.2	467.7	467.0	466.2	465.4	464.6
117.5°	531.1	530.5	529.8	529.0	528.2	527.4	526.7
120°	573.8	573.8	573.4	572.7	571.9	571.1	570.3
122.5°	616.6	615.9	615.4	614.8	614.2	613.7	613.1
125°	680.7	679.9	679.4	679.1	678.9	678.6	678.4
127.5°	742.9	742.0	741.1	740.3	739.5	738.7	737.8
130°	786.0	785.5	784.7	783.7	782.6	781.6	780.6
132.5°	826.9	825.8	824.8	824.0	823.1	822.3	821.5
135°	889.0	888.7	888.2	887.4	886.7	885.9	885.1
137.5°	947.7	947.5	946.9	945.8	944.8	943.8	942.7
140°	987.3	987.3	986.8	985.8	984.8	983.7	982.7
142.5°	1023.3	1023.5	1023.1	1022.0	1021.0	1020.0	1018.9
145°	1077.6	1077.8	1077.4	1076.4	1075.4	1074.3	1073.3
147.5°	1125.4	1126.0	1125.8	1124.8	1123.8	1122.8	1121.9
150°	1155.8	1156.6	1156.6	1155.8	1155.0	1154.2	1153.5
152.5°	1186.1	1187.1	1187.1	1186.1	1185.2	1184.2	1183.2
155°	1224.7	1226.0	1226.2	1225.5	1224.7	1223.9	1223.1
157.5°	1260.5	1262.2	1262.5	1261.2	1260.0	1258.8	1257.5
160°	1281.2	1282.8	1283.0	1282.0	1281.0	1279.9	1278.9
162.5°	1300.4	1302.2	1302.4	1301.2	1300.0	1298.7	1297.5
165°	1325.0	1326.8	1327.0	1325.8	1324.5	1323.2	1321.9
167.5°	1345.2	1347.0	1347.2	1345.9	1344.5	1343.2	1341.9
170°	1356.3	1358.1	1358.3	1356.7	1355.2	1353.6	1352.1
172.5°	1364.7	1366.5	1366.6	1365.1	1363.5	1362.0	1360.4
175°	1373.8	1375.6	1375.7	1374.2	1372.6	1371.1	1369.5
177.5°	1377.4	1378.6	1378.6	1377.4	1376.2	1374.9	1373.7
180°	1376.5	1376.5	1376.5	1376.5	1376.5	1376.5	1376.5

(END OF REPORT)