

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331435

Luminaire Tested: **SA2XXDIP-C1005D530U835-4F0-1E-UDD-F**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331435  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXDIP-C1005D530U835-4F0-1E-UDD-F  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 530 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6170.3 lumens  
Efficiency: N/A  
Efficacy: 112.0 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 55.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331435  
CATALOG NUMBER: SA2XXDIP-C1005D530U835-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P331435

CATALOG NUMBER: SA2XXDIP-C1005D530U835-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	71	71	71	66
1	101	97	93	89	95	91	88	85	81	78	76	71	69	67	62	61	60	55
2	92	85	78	73	87	80	74	70	71	67	63	63	59	56	55	52	50	46
3	84	74	67	61	79	70	64	58	63	57	53	55	51	48	49	46	43	39
4	77	66	58	52	72	62	55	49	56	50	45	49	45	41	44	40	37	34
5	71	59	51	44	66	56	48	43	50	44	39	44	39	36	39	35	32	29
6	65	53	45	39	61	50	43	37	45	39	34	40	35	31	36	32	28	26
7	61	48	40	34	57	45	38	33	41	35	30	37	32	28	33	28	25	23
8	56	44	36	30	53	41	34	29	37	31	27	34	28	25	30	26	23	20
9	52	40	32	27	49	38	31	26	34	28	24	31	26	22	28	24	20	18
10	49	37	29	24	46	35	28	24	32	26	22	29	24	20	26	22	19	17

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	25733	25733	25733
5°	25832	25459	25608
10°	25678	25201	25327
15°	25361	24874	24849
20°	24911	24383	24357
25°	24464	23779	23779
30°	23886	23228	23029
35°	23349	22565	22231
40°	22675	21901	21479
45°	22012	21240	20717
50°	21288	20557	19826
55°	20535	19758	19023
60°	19695	18807	18112
65°	18793	17857	17039
70°	17651	16711	15918
75°	16064	15390	15009
80°	14254	13826	13110
85°	11634	11078	9930



TEST NUMBER: P331435

CATALOG NUMBER: SA2XXDIP-C1005D530U835-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	149.9	2.4
10°-20°	421.7	6.8
20°-30°	619.8	10.0
30°-40°	720.0	11.7
40°-50°	719.2	11.7
50°-60°	627.2	10.2
60°-70°	463.8	7.5
70°-80°	262.7	4.3
80°-90°	72.4	1.2
90°-100°	24.1	0.4
100°-110°	88.2	1.4
110°-120°	235.8	3.8
120°-130°	389.3	6.3
130°-140°	414.0	6.7
140°-150°	384.8	6.2
150°-160°	309.4	5.0
160°-170°	199.4	3.2
170°-180°	68.6	1.1
0°-30°	1191.4	19.3
0°-40°	1911.4	31.0
0°-60°	3257.9	52.8
0°-90°	4056.7	65.7
90°-120°	348.1	5.6
90°-150°	1536.2	24.9
90°-180°	2114.0	34.3
0°-180°	6170.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1594	1594	1594	1594	1594	
5°	1594	1587	1571	1582	1580	151
15°	1517	1507	1488	1493	1487	427
25°	1373	1360	1335	1338	1335	631
35°	1185	1169	1145	1136	1128	739
45°	964	953	930	914	907	744
55°	730	720	702	684	676	652
65°	492	482	467	454	446	486
75°	258	254	247	238	241	275
85°	63	61	60	55	54	72
90°	0	6	10	13	14	5
95°	34	18	20	23	22	41
105°	159	166	32	37	40	170
115°	300	309	322	92	43	295
125°	424	431	441	444	446	378
135°	525	533	538	543	542	405
145°	609	609	617	621	618	381
155°	671	666	672	675	671	309
165°	707	704	705	708	705	200
175°	723	719	720	723	719	69
180°	721	721	721	721	721	



TEST NUMBER: P331435

CATALOG NUMBER: SA2XXDIP-C1005D530U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8
2.5°	1601.2	1599.8	1598.5	1597.1	1595.7	1593.6	1590.6	1587.6	1584.6	1581.6	1584.3
5°	1593.8	1592.5	1591.1	1589.7	1588.4	1585.8	1582.1	1578.3	1574.6	1570.8	1573.6
7.5°	1579.7	1577.6	1575.5	1573.4	1571.3	1568.3	1564.5	1560.7	1556.9	1553.1	1555.8
10°	1566.2	1563.9	1561.5	1559.1	1556.7	1553.5	1549.4	1545.3	1541.2	1537.1	1539.9
12.5°	1547.9	1545.7	1543.6	1541.5	1539.4	1536.3	1532.2	1528.1	1524.1	1520.0	1521.9
15°	1517.2	1515.2	1513.1	1511.1	1509.0	1505.8	1501.4	1496.9	1492.5	1488.1	1489.5
17.5°	1478.0	1475.9	1473.9	1471.8	1469.8	1466.5	1462.0	1457.5	1453.0	1448.6	1450.1
20°	1449.8	1447.7	1445.7	1443.6	1441.6	1438.2	1433.4	1428.7	1423.9	1419.1	1420.1
22.5°	1421.6	1418.7	1415.9	1413.0	1410.1	1406.5	1402.0	1397.5	1393.0	1388.5	1388.7
25°	1373.2	1370.4	1367.7	1365.0	1362.3	1358.0	1352.2	1346.4	1340.6	1334.8	1335.5
27.5°	1318.0	1315.5	1313.1	1310.6	1308.2	1304.7	1300.1	1295.5	1291.0	1286.4	1285.4
30°	1281.2	1278.5	1275.7	1273.0	1270.3	1266.4	1261.3	1256.2	1251.1	1245.9	1244.9
32.5°	1242.0	1239.8	1237.6	1235.4	1233.2	1229.5	1224.1	1218.7	1213.3	1207.9	1206.1
35°	1184.6	1181.2	1177.8	1174.4	1171.0	1166.6	1161.1	1155.7	1150.3	1144.8	1142.8
37.5°	1120.0	1117.0	1114.0	1111.0	1108.0	1103.8	1098.3	1092.9	1087.4	1082.0	1079.4
40°	1075.8	1073.1	1070.4	1067.7	1064.9	1060.9	1055.4	1050.0	1044.5	1039.1	1036.0
42.5°	1032.9	1030.2	1027.5	1024.8	1022.0	1017.9	1012.5	1007.0	1001.6	996.1	992.8
45°	964.0	961.6	959.2	956.8	954.4	950.7	945.6	940.5	935.4	930.2	926.5
47.5°	895.3	893.1	890.8	888.6	886.3	882.5	877.2	871.9	866.6	861.3	857.3
50°	847.5	845.8	844.1	842.4	840.7	837.4	832.7	827.9	823.1	818.4	813.6
52.5°	800.9	798.7	796.4	794.2	791.9	788.5	784.0	779.5	775.1	770.6	766.6
55°	729.5	727.4	725.4	723.4	721.3	718.2	714.2	710.1	706.0	701.9	697.8
57.5°	657.8	656.1	654.5	652.9	651.2	648.2	643.7	639.2	634.7	630.2	626.2
60°	609.9	608.6	607.2	605.9	604.5	601.4	596.7	591.9	587.1	582.4	578.6
62.5°	563.4	561.2	559.0	556.8	554.6	551.7	548.0	544.4	540.7	537.0	533.5
65°	491.9	489.9	487.9	485.8	483.8	481.0	477.6	474.2	470.8	467.4	464.4
67.5°	419.3	417.7	416.0	414.4	412.8	410.4	407.3	404.3	401.2	398.2	395.8
70°	373.9	372.6	371.2	369.9	368.5	366.3	363.2	360.1	357.1	354.0	351.6
72.5°	327.3	326.0	324.6	323.3	321.9	320.2	318.3	316.3	314.3	312.3	309.9
75°	257.5	256.8	256.1	255.4	254.7	253.5	251.8	250.1	248.4	246.7	244.7
77.5°	194.9	193.8	192.6	191.5	190.3	189.4	188.7	188.0	187.3	186.7	185.6
80°	153.3	152.9	152.6	152.2	151.9	151.4	150.7	150.0	149.3	148.7	147.6
82.5°	114.0	114.0	113.9	113.8	113.7	113.5	113.1	112.7	112.3	111.9	110.6
85°	62.8	62.5	62.2	61.8	61.5	61.1	60.8	60.4	60.1	59.8	58.7
87.5°	22.2	21.9	21.6	21.3	21.0	20.7	20.3	20.0	19.6	19.3	18.6
90°	0.5	1.8	3.1	4.3	5.6	6.7	7.7	8.6	9.5	10.4	11.0
92.5°	10.5	10.4	10.3	10.2	10.1	10.3	10.7	11.2	11.6	12.1	12.4
95°	33.9	30.1	26.3	22.4	18.6	17.1	17.9	18.7	19.5	20.4	20.9
97.5°	67.3	56.5	45.8	35.0	24.2	19.7	21.6	23.5	25.4	27.2	27.7
100°	92.4	76.5	60.6	44.7	28.8	21.9	23.8	25.8	27.8	29.7	30.7
102.5°	119.9	116.6	113.2	109.8	106.5	96.5	80.1	63.6	47.1	30.6	31.8
105°	158.6	162.1	165.6	169.1	172.6	158.5	126.8	95.2	63.5	31.8	33.1
107.5°	202.8	205.6	208.4	211.2	214.0	196.4	158.5	120.5	82.5	44.6	43.3
110°	231.2	233.6	236.1	238.5	240.9	225.4	191.9	158.4	124.8	91.3	79.7



TEST NUMBER: P331435

CATALOG NUMBER: SA2XXDIP-C1005D530U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	257.9	260.1	262.2	264.4	266.5	263.5	255.2	246.9	238.6	230.4	188.0
115°	300.1	302.0	304.0	306.0	308.0	310.4	313.3	316.2	319.1	322.0	268.3
117.5°	337.8	340.0	342.2	344.4	346.6	348.7	350.7	352.7	354.7	356.6	343.7
120°	365.3	367.0	368.8	370.5	372.3	374.2	376.3	378.4	380.4	382.5	383.9
122.5°	388.7	390.5	392.4	394.2	396.0	398.1	400.3	402.6	404.9	407.2	408.0
125°	424.3	425.8	427.3	428.8	430.3	432.2	434.4	436.6	438.8	441.0	441.8
127.5°	456.5	458.2	459.9	461.5	463.2	464.9	466.5	468.2	469.8	471.5	472.6
130°	477.0	478.8	480.7	482.6	484.4	486.0	487.3	488.5	489.8	491.1	492.4
132.5°	497.9	499.4	501.0	502.6	504.2	505.6	506.9	508.2	509.4	510.7	511.8
135°	525.0	526.9	528.7	530.6	532.4	533.9	534.9	536.0	537.0	538.0	539.2
137.5°	552.5	553.7	555.0	556.3	557.6	558.9	560.1	561.3	562.4	563.6	564.8
140°	570.4	571.3	572.3	573.2	574.1	575.2	576.5	577.8	579.0	580.3	581.4
142.5°	585.4	586.3	587.1	587.9	588.8	589.9	591.4	592.8	594.3	595.8	596.7
145°	609.0	608.9	608.8	608.7	608.6	609.5	611.5	613.4	615.4	617.4	618.2
147.5°	629.6	629.1	628.7	628.3	627.8	628.6	630.5	632.5	634.4	636.4	637.0
150°	642.9	642.1	641.3	640.5	639.7	640.2	642.1	643.9	645.8	647.6	648.3
152.5°	654.2	653.3	652.4	651.5	650.6	651.0	652.8	654.6	656.3	658.1	658.8
155°	670.6	669.6	668.5	667.5	666.4	666.6	668.0	669.4	670.8	672.2	672.9
157.5°	683.4	682.6	681.7	680.8	679.9	680.0	680.9	681.9	682.9	683.9	684.6
160°	691.0	690.3	689.6	688.9	688.2	688.2	688.9	689.6	690.3	691.0	691.7
162.5°	697.6	696.9	696.2	695.5	694.9	694.8	695.4	696.0	696.6	697.2	698.0
165°	706.6	705.9	705.2	704.5	703.8	703.7	704.0	704.3	704.7	705.0	705.9
167.5°	713.3	712.6	711.9	711.2	710.5	710.3	710.6	711.0	711.3	711.6	712.4
170°	717.0	716.4	715.7	715.0	714.3	714.0	714.3	714.5	714.7	715.0	715.8
172.5°	719.6	718.9	718.2	717.5	716.8	716.5	716.8	717.0	717.2	717.5	718.3
175°	722.8	722.0	721.2	720.4	719.5	719.3	719.5	719.7	719.9	720.2	721.0
177.5°	723.3	722.7	722.0	721.4	720.7	720.4	720.5	720.6	720.7	720.8	721.5
180°	721.2	721.2	721.2	721.2	721.2	721.2	721.2	721.2	721.2	721.2	721.2



TEST NUMBER: P331435

CATALOG NUMBER: SA2XXDIP-C1005D530U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8
2.5°	1587.0	1589.7	1592.5	1593.6	1593.0	1592.5	1591.9	1591.4
5°	1576.3	1579.0	1581.7	1582.8	1582.1	1581.4	1580.7	1580.0
7.5°	1558.5	1561.2	1564.0	1565.0	1564.2	1563.5	1562.7	1562.0
10°	1542.6	1545.3	1548.0	1548.9	1547.9	1546.8	1545.8	1544.8
12.5°	1523.8	1525.7	1527.6	1528.2	1527.4	1526.7	1525.9	1525.2
15°	1490.8	1492.2	1493.5	1493.4	1491.7	1490.0	1488.3	1486.6
17.5°	1451.7	1453.3	1454.8	1454.8	1453.1	1451.5	1449.9	1448.2
20°	1421.2	1422.2	1423.2	1423.0	1421.7	1420.3	1419.0	1417.6
22.5°	1388.9	1389.1	1389.3	1389.0	1388.2	1387.4	1386.5	1385.7
25°	1336.2	1336.9	1337.6	1337.6	1336.9	1336.2	1335.5	1334.8
27.5°	1284.4	1283.3	1282.3	1281.0	1279.4	1277.7	1276.1	1274.5
30°	1243.9	1242.9	1241.9	1240.7	1239.3	1237.9	1236.6	1235.2
32.5°	1204.3	1202.4	1200.6	1199.0	1197.6	1196.3	1194.9	1193.5
35°	1140.7	1138.7	1136.6	1134.8	1133.1	1131.4	1129.6	1127.9
37.5°	1076.9	1074.4	1071.9	1069.8	1068.2	1066.5	1064.9	1063.3
40°	1032.9	1029.9	1026.8	1024.6	1023.2	1021.9	1020.5	1019.1
42.5°	989.5	986.1	982.8	980.2	978.3	976.4	974.5	972.5
45°	922.8	919.0	915.3	912.7	911.3	910.0	908.6	907.3
47.5°	853.4	849.4	845.5	842.5	840.5	838.6	836.6	834.6
50°	808.8	804.1	799.3	796.1	794.4	792.7	791.0	789.3
52.5°	762.7	758.7	754.8	751.7	749.4	747.2	744.9	742.7
55°	693.7	689.6	685.6	682.7	681.0	679.3	677.6	675.8
57.5°	622.1	618.1	614.1	611.4	610.2	608.9	607.6	606.3
60°	574.9	571.1	567.4	565.0	564.0	563.0	561.9	560.9
62.5°	530.1	526.6	523.1	520.7	519.4	518.1	516.8	515.5
65°	461.3	458.2	455.2	452.8	451.1	449.4	447.7	446.0
67.5°	393.4	391.0	388.6	386.7	385.4	384.0	382.7	381.3
70°	349.2	346.9	344.5	342.6	341.2	339.9	338.5	337.2
72.5°	307.6	305.2	302.8	301.1	300.0	298.9	297.8	296.7
75°	242.7	240.6	238.6	237.9	238.6	239.2	239.9	240.6
77.5°	184.6	183.6	182.6	181.6	180.6	179.7	178.7	177.8
80°	146.6	145.6	144.6	143.7	143.0	142.4	141.7	141.0
82.5°	109.3	108.0	106.7	106.0	105.8	105.7	105.6	105.4
85°	57.7	56.7	55.7	55.0	54.7	54.3	54.0	53.6
87.5°	17.8	17.1	16.4	16.0	15.8	15.5	15.3	15.1
90°	11.6	12.2	12.8	13.2	13.4	13.6	13.9	14.1
92.5°	12.7	13.0	13.3	13.5	13.7	13.8	14.0	14.1
95°	21.5	22.1	22.7	22.9	22.8	22.7	22.6	22.4
97.5°	28.2	28.6	29.1	29.4	29.5	29.7	29.8	30.0
100°	31.6	32.5	33.5	34.0	34.3	34.5	34.7	35.0
102.5°	33.0	34.2	35.4	36.2	36.5	36.8	37.1	37.5
105°	34.4	35.7	36.9	37.8	38.3	38.7	39.2	39.7
107.5°	42.0	40.7	39.4	39.0	39.4	39.9	40.3	40.8
110°	68.1	56.5	44.9	39.4	39.8	40.3	40.8	41.2





TEST NUMBER: P331435

CATALOG NUMBER: SA2XXDIP-C1005D530U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	145.7	103.4	61.1	40.2	40.5	40.9	41.3	41.6
115°	214.6	160.9	107.2	76.2	67.8	59.5	51.1	42.8
117.5°	330.7	317.7	304.7	284.5	257.0	229.6	202.2	174.7
120°	385.3	386.7	388.1	381.0	365.3	349.7	334.0	318.3
122.5°	408.8	409.7	410.5	409.4	406.4	403.3	400.3	397.2
125°	442.6	443.4	444.2	444.8	445.2	445.5	445.9	446.2
127.5°	473.8	475.0	476.2	476.8	476.9	477.0	477.0	477.1
130°	493.6	494.9	496.2	496.8	496.6	496.5	496.4	496.3
132.5°	512.9	514.0	515.1	515.5	515.4	515.3	515.2	515.1
135°	540.4	541.5	542.7	543.2	542.9	542.7	542.5	542.2
137.5°	565.9	567.0	568.2	568.5	568.1	567.7	567.4	567.0
140°	582.4	583.4	584.5	584.7	584.1	583.6	583.0	582.4
142.5°	597.7	598.6	599.6	599.8	599.2	598.6	598.0	597.4
145°	619.0	619.8	620.6	620.7	620.2	619.6	619.0	618.4
147.5°	637.6	638.2	638.8	638.8	638.4	637.9	637.4	636.9
150°	649.0	649.7	650.4	650.5	649.9	649.3	648.7	648.2
152.5°	659.5	660.2	660.9	660.8	660.1	659.3	658.5	657.8
155°	673.6	674.3	675.0	674.8	673.9	673.0	672.1	671.1
157.5°	685.4	686.2	687.0	687.0	686.0	685.1	684.2	683.3
160°	692.3	693.0	693.7	693.7	692.9	692.1	691.2	690.4
162.5°	698.8	699.6	700.4	700.3	699.3	698.3	697.3	696.3
165°	706.7	707.5	708.3	708.3	707.5	706.7	705.9	705.0
167.5°	713.2	714.1	714.9	714.8	713.7	712.7	711.6	710.6
170°	716.6	717.4	718.2	718.1	717.0	716.0	715.0	713.9
172.5°	719.1	719.9	720.7	720.6	719.6	718.5	717.5	716.4
175°	721.8	722.6	723.4	723.3	722.1	720.9	719.8	718.6
177.5°	722.1	722.8	723.4	723.3	722.5	721.6	720.8	720.0
180°	721.2	721.2	721.2	721.2	721.2	721.2	721.2	721.2

(END OF REPORT)