

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331328-927

Luminaire Tested: **SA2XXDIP-C485D1080U927-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331328-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C485D1080U927-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1080 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4618.8 lumens
Efficiency: N/A
Efficacy: 93.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 49.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331328-927

CATALOG NUMBER: SA2XXDIP-C485D1080U927-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331328-927

CATALOG NUMBER: SA2XXDIP-C485D1080U927-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	34				
1	94	90	86	83	85	81	78	75	65	63	61	50	49	47	37	36	35	29				
2	86	78	73	67	77	71	66	62	57	53	50	44	42	40	32	31	29	24				
3	78	69	62	56	70	62	56	51	50	46	42	39	36	33	28	27	25	20				
4	71	61	53	47	64	55	49	44	45	40	36	35	31	29	25	23	22	17				
5	65	54	46	40	59	49	42	37	40	35	31	31	28	25	23	21	19	15				
6	60	48	41	35	54	44	37	32	36	31	27	28	24	22	21	18	16	13				
7	56	44	36	31	50	40	33	28	32	27	24	25	22	19	19	16	15	12				
8	52	40	32	27	46	36	29	25	29	24	21	23	20	17	17	15	13	11				
9	48	36	29	24	43	33	26	22	27	22	19	21	18	15	16	14	12	10				
10	45	33	26	21	40	30	24	20	25	20	17	20	16	14	15	12	11	9				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9935	9935	9935
5°	9972	9828	9887
10°	9914	9729	9778
15°	9790	9603	9593
20°	9617	9414	9402
25°	9444	9180	9180
30°	9221	8968	8889
35°	9014	8712	8584
40°	8753	8456	8292
45°	8499	8200	7996
50°	8219	7935	7654
55°	7927	7626	7344
60°	7601	7259	6991
65°	7255	6896	6575
70°	6812	6453	6146
75°	6201	5939	5795
80°	5504	5337	5058
85°	4483	4279	3835



TEST NUMBER: P331328-927

CATALOG NUMBER: SA2XXDIP-C485D1080U927-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	57.9	1.3
10°-20°	162.8	3.5
20°-30°	239.3	5.2
30°-40°	278.0	6.0
40°-50°	277.7	6.0
50°-60°	242.1	5.2
60°-70°	179.0	3.9
70°-80°	101.4	2.2
80°-90°	31.6	0.7
90°-100°	69.1	1.5
100°-110°	214.6	4.6
110°-120°	366.8	7.9
120°-130°	482.4	10.4
130°-140°	541.4	11.7
140°-150°	530.9	11.5
150°-160°	445.3	9.6
160°-170°	295.3	6.4
170°-180°	103.2	2.2
0°-30°	459.9	10.0
0°-40°	737.9	16.0
0°-60°	1257.7	27.2
0°-90°	1569.8	34.0
90°-120°	650.5	14.1
90°-150°	2205.2	47.7
90°-180°	3049.0	66.0
0°-180°	4618.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	615	615	615	615	615	
5°	615	613	606	611	610	58
15°	586	582	574	577	574	165
25°	530	525	515	516	515	244
35°	457	451	442	438	436	285
45°	372	368	359	353	350	287
55°	282	278	271	264	261	252
65°	190	186	180	175	172	188
75°	99	98	95	92	93	106
85°	24	24	23	21	21	28
90°	1	12	32	31	31	4
95°	48	57	59	59	57	55
105°	198	201	202	204	204	209
115°	368	373	372	371	368	364
125°	536	543	541	538	537	478
135°	693	703	705	704	701	535
145°	841	847	853	854	850	525
155°	962	964	967	971	969	442
165°	1046	1045	1045	1051	1047	295
175°	1089	1086	1084	1090	1085	103
180°	1090	1090	1090	1090	1090	



TEST NUMBER: P331328-927

CATALOG NUMBER: SA2XXDIP-C485D1080U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	615.3	615.3	615.3	615.3	615.3	615.3	615.3	615.3	615.3	615.3	615.3
2.5°	618.1	617.6	617.1	616.6	616.0	615.2	614.0	612.9	611.7	610.5	611.6
5°	615.3	614.7	614.3	613.7	613.2	612.2	610.8	609.3	607.8	606.4	607.4
7.5°	609.8	609.0	608.2	607.4	606.6	605.5	604.0	602.5	601.0	599.5	600.6
10°	604.7	603.7	602.8	601.9	600.9	599.7	598.1	596.6	595.0	593.4	594.5
12.5°	597.5	596.8	595.9	595.1	594.3	593.1	591.5	589.9	588.4	586.8	587.5
15°	585.7	584.9	584.2	583.4	582.6	581.3	579.6	577.9	576.2	574.5	575.0
17.5°	570.5	569.8	569.0	568.2	567.4	566.2	564.4	562.7	560.9	559.2	559.8
20°	559.7	558.9	558.1	557.3	556.5	555.2	553.3	551.5	549.7	547.9	548.3
22.5°	548.8	547.7	546.6	545.5	544.4	543.0	541.2	539.5	537.7	536.0	536.1
25°	530.1	529.0	528.0	527.0	525.9	524.3	522.0	519.8	517.5	515.3	515.6
27.5°	508.8	507.9	506.9	506.0	505.0	503.7	501.9	500.1	498.4	496.6	496.2
30°	494.6	493.5	492.5	491.5	490.4	488.9	486.9	485.0	483.0	481.0	480.6
32.5°	479.4	478.6	477.8	476.9	476.1	474.6	472.5	470.5	468.4	466.4	465.6
35°	457.3	456.0	454.7	453.4	452.1	450.4	448.3	446.2	444.0	442.0	441.2
37.5°	432.4	431.2	430.1	428.9	427.7	426.1	424.0	421.9	419.8	417.7	416.7
40°	415.3	414.2	413.2	412.2	411.1	409.6	407.4	405.4	403.2	401.2	400.0
42.5°	398.8	397.7	396.6	395.6	394.6	393.0	390.9	388.8	386.7	384.5	383.3
45°	372.2	371.2	370.3	369.4	368.4	367.0	365.0	363.1	361.1	359.1	357.7
47.5°	345.6	344.8	343.9	343.0	342.1	340.7	338.7	336.6	334.5	332.5	331.0
50°	327.2	326.5	325.8	325.2	324.6	323.3	321.5	319.6	317.7	315.9	314.1
52.5°	309.2	308.3	307.4	306.6	305.7	304.4	302.7	301.0	299.2	297.5	296.0
55°	281.6	280.8	280.0	279.2	278.5	277.3	275.7	274.1	272.5	270.9	269.4
57.5°	253.9	253.3	252.6	252.1	251.4	250.3	248.5	246.8	245.0	243.3	241.7
60°	235.4	235.0	234.4	233.9	233.4	232.2	230.4	228.5	226.6	224.8	223.4
62.5°	217.5	216.7	215.8	214.9	214.1	213.0	211.6	210.2	208.7	207.3	206.0
65°	189.9	189.1	188.3	187.5	186.8	185.7	184.4	183.1	181.7	180.5	179.3
67.5°	161.8	161.2	160.6	159.9	159.3	158.4	157.2	156.1	154.9	153.7	152.8
70°	144.3	143.9	143.3	142.8	142.3	141.4	140.2	139.0	137.8	136.7	135.8
72.5°	126.4	125.9	125.3	124.8	124.3	123.7	122.9	122.1	121.4	120.6	119.6
75°	99.4	99.1	98.9	98.6	98.3	97.9	97.2	96.6	95.9	95.2	94.4
77.5°	75.3	74.8	74.4	73.9	73.4	73.1	72.9	72.6	72.3	72.1	71.7
80°	59.2	59.0	58.9	58.8	58.6	58.5	58.1	57.9	57.7	57.4	57.0
82.5°	44.0	44.0	44.0	44.0	43.9	43.8	43.6	43.5	43.3	43.2	42.7
85°	24.2	24.2	24.0	23.8	23.8	23.6	23.4	23.4	23.2	23.1	22.7
87.5°	8.7	9.0	9.3	9.5	9.8	10.3	11.0	11.7	12.4	13.1	12.7
90°	1.0	3.4	5.9	8.3	10.8	14.2	18.7	23.2	27.7	32.2	31.8
92.5°	16.4	18.1	20.0	21.8	23.6	25.0	26.1	27.2	28.2	29.2	29.3
95°	47.8	49.9	52.0	53.9	56.0	57.3	57.7	58.1	58.5	58.9	58.9
97.5°	87.5	89.2	91.0	92.8	94.6	95.9	96.6	97.4	98.2	99.0	99.0
100°	116.8	118.5	120.2	121.8	123.4	124.5	125.2	125.7	126.4	127.0	127.0
102.5°	147.8	149.1	150.4	151.7	153.0	154.1	154.9	155.6	156.4	157.2	157.3
105°	197.8	198.4	199.1	199.7	200.3	200.8	201.2	201.6	202.0	202.4	202.9
107.5°	248.3	249.1	250.1	251.0	251.8	252.3	252.3	252.3	252.3	252.3	252.5
110°	280.7	281.9	283.1	284.3	285.6	286.2	286.2	286.2	286.2	286.2	286.2



TEST NUMBER: P331328-927

CATALOG NUMBER: SA2XXDIP-C485D1080U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	316.0	317.2	318.5	319.6	320.9	321.5	321.2	321.1	320.9	320.8	320.3
115°	368.0	369.3	370.5	371.8	373.0	373.4	373.0	372.6	372.2	371.8	371.5
117.5°	419.9	421.6	423.3	424.8	426.5	426.7	425.6	424.5	423.3	422.2	421.7
120°	454.6	456.2	457.9	459.5	461.1	461.1	459.5	457.9	456.2	454.6	454.6
122.5°	486.2	488.2	490.1	492.1	494.1	494.5	493.4	492.2	491.1	489.9	489.4
125°	535.5	537.4	539.2	541.1	542.9	543.5	542.9	542.3	541.7	541.1	540.4
127.5°	583.6	585.9	588.3	590.6	592.9	593.7	592.9	592.2	591.5	590.7	590.0
130°	613.8	616.4	619.1	621.7	624.4	625.5	625.1	624.7	624.3	623.9	623.4
132.5°	647.6	649.8	652.0	654.1	656.3	657.4	657.5	657.6	657.7	657.7	656.9
135°	692.9	695.1	697.4	699.7	701.9	703.2	703.6	704.0	704.5	704.9	704.6
137.5°	740.5	742.4	744.3	746.1	747.9	749.1	749.6	750.2	750.7	751.2	751.1
140°	769.3	771.1	772.9	774.8	776.7	778.1	779.1	780.1	781.2	782.1	782.1
142.5°	798.8	800.6	802.4	804.2	806.0	807.3	808.0	808.7	809.5	810.2	810.3
145°	841.1	842.5	843.9	845.3	846.8	848.1	849.3	850.6	851.8	853.0	853.2
147.5°	878.8	880.5	882.2	883.9	885.7	886.9	887.7	888.6	889.4	890.2	890.7
150°	904.5	905.8	907.0	908.2	909.4	910.5	911.3	912.1	912.9	913.8	914.3
152.5°	927.3	928.6	929.8	931.1	932.2	933.3	934.4	935.3	936.4	937.3	938.1
155°	961.6	962.2	962.8	963.5	964.1	964.6	965.3	965.9	966.5	967.1	968.1
157.5°	990.9	991.3	991.7	992.0	992.5	992.8	993.2	993.6	994.0	994.3	995.8
160°	1008.5	1008.9	1009.3	1009.7	1010.2	1010.4	1010.7	1010.9	1011.1	1011.3	1012.5
162.5°	1024.7	1024.8	1024.8	1024.9	1025.1	1025.2	1025.4	1025.6	1025.8	1026.0	1027.4
165°	1046.2	1046.1	1045.8	1045.6	1045.4	1045.4	1045.4	1045.4	1045.4	1045.4	1046.8
167.5°	1064.3	1063.7	1063.0	1062.5	1061.8	1061.5	1061.4	1061.4	1061.4	1061.4	1062.8
170°	1073.9	1073.2	1072.6	1072.0	1071.4	1071.0	1070.8	1070.6	1070.4	1070.2	1071.6
172.5°	1080.5	1079.9	1079.3	1078.6	1078.0	1077.6	1077.4	1077.2	1077.0	1076.8	1078.2
175°	1088.6	1088.0	1087.3	1086.7	1086.2	1085.6	1085.2	1084.8	1084.4	1083.9	1085.4
177.5°	1091.9	1091.4	1090.9	1090.4	1090.0	1089.5	1089.2	1088.9	1088.5	1088.2	1089.2
180°	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4



TEST NUMBER: P331328-927

CATALOG NUMBER: SA2XXDIP-C485D1080U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	615.3	615.3	615.3	615.3	615.3	615.3	615.3	615.3
2.5°	612.7	613.7	614.7	615.2	615.0	614.7	614.6	614.3
5°	608.6	609.6	610.6	611.0	610.8	610.5	610.2	610.0
7.5°	601.7	602.7	603.8	604.1	603.9	603.6	603.2	603.0
10°	595.5	596.6	597.6	597.9	597.5	597.1	596.8	596.4
12.5°	588.3	589.0	589.7	589.9	589.6	589.4	589.1	588.7
15°	575.5	576.1	576.6	576.5	575.8	575.2	574.6	573.9
17.5°	560.4	561.0	561.7	561.6	560.9	560.4	559.8	559.1
20°	548.7	549.1	549.5	549.4	548.8	548.3	547.8	547.2
22.5°	536.1	536.2	536.3	536.2	535.9	535.6	535.3	535.0
25°	515.9	516.1	516.3	516.3	516.1	515.9	515.6	515.3
27.5°	495.8	495.4	495.0	494.6	493.9	493.3	492.7	492.0
30°	480.2	479.8	479.4	479.0	478.4	477.9	477.4	476.8
32.5°	464.9	464.2	463.5	462.9	462.3	461.8	461.3	460.7
35°	440.4	439.6	438.8	438.1	437.4	436.7	436.1	435.5
37.5°	415.7	414.8	413.8	413.0	412.3	411.7	411.1	410.5
40°	398.8	397.6	396.4	395.5	395.0	394.5	394.0	393.4
42.5°	382.0	380.7	379.4	378.4	377.6	376.9	376.2	375.4
45°	356.2	354.8	353.3	352.4	351.8	351.3	350.8	350.2
47.5°	329.5	327.9	326.4	325.3	324.5	323.8	323.0	322.2
50°	312.3	310.4	308.6	307.3	306.7	306.0	305.3	304.7
52.5°	294.5	292.9	291.4	290.2	289.3	288.4	287.6	286.7
55°	267.8	266.3	264.7	263.6	262.8	262.2	261.6	260.9
57.5°	240.2	238.6	237.1	236.1	235.5	235.0	234.6	234.0
60°	221.9	220.5	219.0	218.1	217.7	217.3	216.9	216.5
62.5°	204.6	203.3	201.9	201.1	200.5	200.0	199.6	199.0
65°	178.1	176.9	175.7	174.8	174.1	173.5	172.9	172.1
67.5°	151.9	150.9	150.0	149.3	148.8	148.2	147.7	147.2
70°	134.8	133.9	133.0	132.3	131.7	131.2	130.7	130.2
72.5°	118.7	117.8	116.9	116.2	115.8	115.3	114.9	114.5
75°	93.6	92.9	92.1	91.8	92.1	92.4	92.6	92.9
77.5°	71.3	70.9	70.5	70.1	69.7	69.4	69.0	68.6
80°	56.6	56.2	55.8	55.5	55.2	55.0	54.7	54.4
82.5°	42.2	41.7	41.2	40.9	40.9	40.8	40.7	40.7
85°	22.3	21.9	21.5	21.2	21.1	21.0	20.8	20.7
87.5°	12.3	11.9	11.5	11.2	11.2	11.1	11.1	11.0
90°	31.4	31.0	30.6	30.5	30.7	30.9	31.1	31.3
92.5°	29.4	29.5	29.6	29.6	29.7	29.7	29.8	29.8
95°	58.9	58.9	58.9	58.7	58.3	57.9	57.4	57.0
97.5°	99.0	99.0	99.0	99.0	98.9	98.9	98.9	98.9
100°	127.0	127.0	127.0	126.9	126.7	126.5	126.3	126.0
102.5°	157.5	157.6	157.8	157.8	157.6	157.4	157.2	157.0
105°	203.3	203.7	204.1	204.3	204.3	204.3	204.3	204.3
107.5°	252.6	252.8	252.9	252.5	251.7	250.7	249.8	248.8
110°	286.2	286.2	286.2	285.9	285.3	284.6	284.0	283.4



TEST NUMBER: P331328-927

CATALOG NUMBER: SA2XXDIP-C485D1080U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	319.8	319.3	318.9	318.4	317.9	317.4	317.0	316.6
115°	371.4	371.1	370.9	370.5	369.9	369.3	368.7	368.0
117.5°	421.2	420.7	420.3	419.7	419.1	418.4	417.8	417.2
120°	454.6	454.6	454.6	454.2	453.7	453.0	452.4	451.8
122.5°	488.9	488.5	487.9	487.5	487.0	486.6	486.2	485.7
125°	539.9	539.2	538.6	538.2	538.0	537.8	537.6	537.4
127.5°	589.3	588.5	587.8	587.1	586.5	585.8	585.2	584.5
130°	623.1	622.7	622.3	621.6	620.8	620.0	619.2	618.4
132.5°	655.9	655.1	654.2	653.4	652.8	652.0	651.4	650.8
135°	704.5	704.3	704.0	703.6	703.0	702.4	701.8	701.2
137.5°	750.9	750.8	750.6	750.1	749.2	748.5	747.7	746.8
140°	782.1	782.1	782.1	781.7	780.9	780.1	779.3	778.5
142.5°	810.5	810.6	810.8	810.5	809.6	808.8	808.0	807.2
145°	853.4	853.7	853.8	853.5	852.7	851.9	851.0	850.2
147.5°	891.1	891.5	892.0	891.8	891.0	890.3	889.5	888.7
150°	915.0	915.6	916.2	916.2	915.6	915.0	914.3	913.8
152.5°	938.9	939.6	940.4	940.4	939.6	938.9	938.1	937.3
155°	969.2	970.2	971.2	971.4	970.8	970.2	969.6	968.9
157.5°	997.1	998.5	999.9	1000.1	999.1	998.1	997.2	996.2
160°	1013.8	1014.9	1016.2	1016.4	1015.6	1014.8	1013.9	1013.1
162.5°	1028.8	1030.2	1031.6	1031.7	1030.8	1029.8	1028.8	1027.9
165°	1048.2	1049.6	1051.1	1051.2	1050.3	1049.2	1048.2	1047.2
167.5°	1064.2	1065.6	1067.1	1067.2	1066.2	1065.1	1064.1	1063.0
170°	1073.0	1074.4	1075.9	1076.0	1074.8	1073.6	1072.3	1071.1
172.5°	1079.7	1081.1	1082.5	1082.6	1081.4	1080.1	1079.0	1077.7
175°	1086.9	1088.3	1089.7	1089.8	1088.6	1087.3	1086.2	1084.9
177.5°	1090.2	1091.2	1092.1	1092.1	1091.2	1090.2	1089.2	1088.2
180°	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4

(END OF REPORT)