

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331297-927

Luminaire Tested: **SA2XXDIP-C485D530U927-4F0-1E-UDD-D**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331297-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C485D530U927-4F0-1E-UDD-D
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, DROP SATIN WHITE DIFFUSER
UPLIGHT 530 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3233.2 lumens
Efficiency: N/A
Efficacy: 98.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.32 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.08')
CIE Type: General Diffuse

Input Watts (W): 32.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331297-927
CATALOG NUMBER: SA2XXDIP-C485D530U927-4F0-1E-UDD-D

Luminous Intensity Polar Plot





TEST NUMBER: P331297-927

CATALOG NUMBER: SA2XXDIP-C485D530U927-4F0-1E-UDD-D

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	50	50	50	43				
1	95	90	86	82	86	82	79	75	68	65	62	54	52	50	42	40	39	33				
2	86	78	71	66	78	71	65	61	58	54	51	47	44	41	36	34	32	27				
3	78	68	60	54	71	62	55	50	51	46	42	41	37	34	31	29	27	22				
4	71	60	52	45	64	55	48	42	45	40	35	36	32	29	28	25	23	19				
5	65	53	45	39	59	49	41	36	40	35	30	32	28	25	25	22	20	16				
6	60	47	39	33	54	44	36	31	36	30	26	29	25	22	23	19	17	14				
7	55	43	35	29	50	39	32	27	33	27	23	26	22	19	20	17	15	12				
8	51	39	31	25	46	36	28	24	30	24	20	24	20	17	19	16	13	11				
9	48	35	28	22	43	32	26	21	27	22	18	22	18	15	17	14	12	10				
10	44	32	25	20	40	30	23	19	25	20	16	20	16	13	16	13	11	9				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6591	6591	6591
5°	6623	6345	6320
10°	6581	6158	6088
15°	6491	5959	5843
20°	6376	5745	5607
25°	6263	5540	5394
30°	6103	5330	5178
35°	5943	5127	5028
40°	5773	4954	4876
45°	5612	4799	4746
50°	5439	4657	4618
55°	5257	4507	4488
60°	5033	4351	4351
65°	4802	4169	4189
70°	4546	3970	4013
75°	4214	3778	3850
80°	3692	3579	3685
85°	3187	3410	3559



TEST NUMBER: P331297-927

CATALOG NUMBER: SA2XXDIP-C485D530U927-4F0-1E-UDD-D

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	38.7	1.2
10°-20°	110.9	3.4
20°-30°	168.1	5.2
30°-40°	204.7	6.3
40°-50°	220.3	6.8
50°-60°	213.9	6.6
60°-70°	186.8	5.8
70°-80°	143.8	4.4
80°-90°	97.9	3.0
90°-100°	85.5	2.6
100°-110°	118.4	3.7
110°-120°	218.9	6.8
120°-130°	326.3	10.1
130°-140°	335.5	10.4
140°-150°	306.1	9.5
150°-160°	245.1	7.6
160°-170°	157.9	4.9
170°-180°	54.4	1.7
0°-30°	317.7	9.8
0°-40°	522.4	16.2
0°-60°	956.6	29.6
0°-90°	1385.0	42.8
90°-120°	422.8	13.1
90°-150°	1390.8	43.0
90°-180°	1848.0	57.2
0°-180°	3233.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	408	408	408	408	408	
5°	409	408	404	407	407	39
15°	390	392	392	397	396	110
25°	355	359	364	371	373	163
35°	306	316	327	340	344	191
45°	251	267	288	305	312	194
55°	192	214	244	265	273	172
65°	131	161	195	219	227	130
75°	73	106	144	168	177	77
85°	21	58	96	120	129	23
90°	6	45	86	111	120	5
95°	32	47	84	108	115	37
105°	129	152	76	100	110	138
115°	240	255	291	125	94	236
125°	337	344	370	388	395	301
135°	416	423	433	449	453	322
145°	482	482	489	495	496	302
155°	531	528	532	535	532	245
165°	560	558	558	561	558	158
175°	573	570	570	573	569	54
180°	571	571	571	571	571	



TEST NUMBER: P331297-927

CATALOG NUMBER: SA2XXDIP-C485D530U927-4F0-1E-UDD-D

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	408.2	408.2	408.2	408.2	408.2	408.2	408.2	408.2	408.2	408.2	408.2
2.5°	410.6	410.3	410.0	409.6	409.3	408.8	408.1	407.3	406.6	405.8	406.4
5°	409.4	409.0	408.6	408.2	407.8	407.3	406.5	405.7	404.9	404.1	404.9
7.5°	405.8	405.4	405.2	405.0	404.7	404.3	403.6	403.1	402.4	401.8	402.7
10°	402.9	402.7	402.3	402.1	401.9	401.6	401.2	400.8	400.4	400.0	401.0
12.5°	398.2	398.2	398.3	398.3	398.4	398.2	398.0	397.7	397.4	397.1	398.2
15°	390.5	390.7	391.0	391.3	391.5	391.7	391.7	391.7	391.7	391.7	392.8
17.5°	380.6	381.1	381.7	382.2	382.8	383.3	383.7	384.0	384.5	384.9	386.1
20°	373.9	374.5	375.3	375.9	376.5	377.2	377.6	378.2	378.7	379.2	380.6
22.5°	366.8	367.6	368.4	369.1	369.9	370.6	371.4	372.1	372.8	373.6	375.0
25°	355.0	355.9	356.8	357.7	358.6	359.7	360.9	362.1	363.3	364.4	366.0
27.5°	340.8	342.3	343.8	345.3	346.7	348.2	349.6	351.0	352.4	353.8	355.8
30°	331.3	333.0	334.7	336.4	338.2	339.8	341.6	343.3	345.0	346.7	348.8
32.5°	320.9	322.8	324.7	326.7	328.6	330.6	332.6	334.6	336.6	338.7	341.0
35°	305.9	308.1	310.4	312.6	314.8	317.2	319.6	322.2	324.6	327.2	330.0
37.5°	289.5	292.2	294.7	297.3	299.8	302.8	306.0	309.2	312.4	315.7	318.9
40°	278.7	281.5	284.5	287.3	290.3	293.4	297.0	300.6	304.1	307.7	311.1
42.5°	268.2	271.2	274.0	276.9	279.8	283.3	287.4	291.4	295.6	299.6	303.3
45°	250.9	254.4	257.9	261.5	265.1	269.1	273.7	278.3	283.0	287.6	291.6
47.5°	233.7	237.6	241.5	245.3	249.1	253.8	259.2	264.6	270.0	275.4	279.6
50°	221.9	225.9	230.0	234.1	238.1	243.1	249.1	255.0	260.9	266.8	271.3
52.5°	210.5	214.8	219.0	223.4	227.7	232.9	239.2	245.3	251.6	257.9	262.4
55°	192.3	197.0	201.8	206.4	211.2	217.0	223.9	230.7	237.5	244.3	249.1
57.5°	174.3	179.7	185.0	190.3	195.7	201.8	208.7	215.7	222.7	229.7	234.8
60°	161.5	167.2	172.9	178.5	184.1	190.7	198.2	205.7	213.2	220.7	225.7
62.5°	150.1	156.0	161.9	167.8	173.6	180.3	187.7	195.3	202.8	210.2	215.6
65°	131.3	137.8	144.3	150.7	157.1	164.2	172.0	179.7	187.5	195.3	200.7
67.5°	114.1	120.8	127.5	134.3	141.0	148.3	156.3	164.2	172.1	180.1	185.5
70°	101.8	108.6	115.4	122.2	129.1	136.6	144.7	152.9	161.1	169.2	174.8
72.5°	90.4	97.4	104.5	111.5	118.6	126.3	134.5	142.8	151.0	159.2	164.9
75°	72.8	80.2	87.5	94.8	102.2	110.1	118.5	126.9	135.4	143.8	149.4
77.5°	55.8	63.5	71.1	78.8	86.6	94.7	103.2	111.8	120.3	128.9	134.5
80°	44.4	52.4	60.4	68.4	76.4	84.8	93.3	101.8	110.4	118.9	124.5
82.5°	34.9	42.9	50.7	58.6	66.5	74.9	83.5	92.1	100.8	109.5	114.9
85°	21.3	29.5	37.6	45.8	53.9	62.2	70.6	79.0	87.5	95.9	101.4
87.5°	11.6	19.7	27.7	35.8	43.8	52.1	60.7	69.2	77.8	86.3	91.8
90°	6.3	15.0	23.6	32.2	40.9	49.7	58.9	68.0	77.2	86.3	92.1
92.5°	13.8	20.8	27.8	34.9	41.8	49.6	58.1	66.5	74.9	83.4	88.8
95°	31.6	34.8	37.9	41.0	44.2	50.1	58.5	67.1	75.7	84.1	89.6
97.5°	57.4	54.4	51.4	48.3	45.3	48.3	57.4	66.4	75.5	84.5	89.8
100°	77.3	69.6	61.9	54.2	46.4	47.1	55.9	64.9	73.8	82.7	88.3
102.5°	98.7	100.4	102.2	104.0	105.8	103.7	97.8	91.9	86.0	80.1	85.8
105°	128.7	135.2	141.8	148.4	155.0	149.1	130.9	112.6	94.3	76.1	81.7
107.5°	163.5	168.7	174.0	179.4	184.6	175.5	151.9	128.4	104.9	81.4	84.7
110°	185.5	190.0	194.6	199.2	203.7	196.0	175.9	155.7	135.6	115.5	110.6



TEST NUMBER: P331297-927

CATALOG NUMBER: SA2XXDIP-C485D530U927-4F0-1E-UDD-D

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	206.7	210.6	214.5	218.4	222.4	224.1	223.6	223.2	222.8	222.4	193.1
115°	240.1	243.1	246.1	249.1	252.2	257.7	265.9	274.2	282.3	290.6	252.0
117.5°	269.3	272.0	274.7	277.4	280.1	284.9	292.0	299.0	306.1	313.1	306.8
120°	291.1	293.1	295.0	296.9	298.8	303.2	310.1	317.0	323.9	330.8	335.6
122.5°	309.7	311.3	313.0	314.7	316.3	320.5	327.3	334.1	340.8	347.5	351.7
125°	337.3	338.5	339.7	340.9	342.1	345.6	351.6	357.5	363.5	369.5	373.7
127.5°	362.8	364.0	365.2	366.4	367.6	370.6	375.3	379.9	384.6	389.4	393.6
130°	379.1	380.4	381.8	383.1	384.4	387.0	390.7	394.5	398.2	402.0	406.2
132.5°	395.6	396.7	397.8	398.9	400.1	402.2	405.4	408.4	411.6	414.7	418.7
135°	416.5	418.0	419.5	420.9	422.4	424.1	426.4	428.5	430.6	432.8	436.4
137.5°	438.2	439.3	440.2	441.2	442.3	443.5	445.0	446.6	448.1	449.6	452.9
140°	452.5	453.0	453.7	454.2	454.9	455.8	457.1	458.4	459.6	460.9	463.8
142.5°	464.4	464.9	465.4	466.0	466.5	467.4	468.6	469.8	471.0	472.2	474.6
145°	482.4	482.4	482.3	482.2	482.1	482.8	484.4	485.9	487.5	489.1	490.5
147.5°	498.8	498.4	498.0	497.7	497.3	498.0	499.5	501.1	502.6	504.1	504.7
150°	509.3	508.7	508.0	507.4	506.8	507.2	508.7	510.1	511.6	513.0	513.6
152.5°	518.2	517.5	516.8	516.1	515.4	515.7	517.1	518.6	519.9	521.3	521.9
155°	531.2	530.4	529.6	528.8	527.9	528.1	529.2	530.3	531.4	532.5	533.1
157.5°	541.4	540.7	540.0	539.3	538.6	538.7	539.4	540.2	541.0	541.8	542.3
160°	547.4	546.8	546.3	545.7	545.2	545.2	545.7	546.3	546.8	547.4	548.0
162.5°	552.6	552.1	551.5	551.0	550.5	550.4	550.9	551.4	551.8	552.3	552.9
165°	559.8	559.2	558.6	558.1	557.5	557.5	557.7	557.9	558.3	558.5	559.2
167.5°	565.1	564.5	564.0	563.4	562.8	562.7	562.9	563.2	563.5	563.7	564.4
170°	568.0	567.5	567.0	566.4	565.9	565.6	565.9	566.0	566.2	566.4	567.0
172.5°	570.1	569.5	568.9	568.4	567.8	567.6	567.8	568.0	568.2	568.4	569.0
175°	572.6	572.0	571.3	570.7	570.0	569.8	570.0	570.1	570.3	570.5	571.2
177.5°	573.0	572.5	572.0	571.5	570.9	570.7	570.8	570.8	570.9	571.0	571.6
180°	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3



TEST NUMBER: P331297-927

CATALOG NUMBER: SA2XXDIP-C485D530U927-4F0-1E-UDD-D

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	408.2	408.2	408.2	408.2	408.2	408.2	408.2	408.2
2.5°	406.9	407.4	408.0	408.1	407.9	407.7	407.5	407.3
5°	405.7	406.5	407.3	407.6	407.4	407.3	407.2	407.0
7.5°	403.7	404.6	405.6	406.0	405.9	405.8	405.6	405.5
10°	402.0	403.1	404.2	404.6	404.5	404.3	404.3	404.1
12.5°	399.2	400.3	401.3	401.8	401.6	401.5	401.4	401.2
15°	394.0	395.2	396.4	396.9	396.8	396.6	396.5	396.4
17.5°	387.4	388.6	389.8	390.5	390.5	390.5	390.5	390.5
20°	382.1	383.6	385.0	385.7	385.7	385.7	385.7	385.7
22.5°	376.4	377.9	379.4	380.2	380.4	380.6	380.8	381.0
25°	367.6	369.2	370.7	371.8	372.2	372.6	373.0	373.4
27.5°	357.8	359.8	361.8	362.9	363.2	363.5	363.8	364.1
30°	350.9	353.0	355.1	356.3	356.7	357.1	357.5	357.9
32.5°	343.5	345.9	348.3	349.9	350.6	351.3	352.0	352.8
35°	333.0	335.9	338.7	340.6	341.6	342.5	343.4	344.4
37.5°	322.1	325.3	328.5	330.6	331.6	332.6	333.5	334.5
40°	314.5	317.9	321.3	323.6	324.8	326.0	327.2	328.4
42.5°	307.0	310.8	314.5	317.0	318.1	319.3	320.5	321.7
45°	295.7	299.8	303.8	306.5	307.8	309.2	310.5	311.8
47.5°	283.8	288.1	292.4	295.2	296.7	298.1	299.6	301.0
50°	275.8	280.2	284.7	287.6	289.1	290.6	292.0	293.4
52.5°	267.0	271.6	276.2	279.2	280.7	282.3	283.8	285.4
55°	253.8	258.6	263.2	266.5	268.2	269.9	271.6	273.3
57.5°	239.9	244.9	250.1	253.5	255.2	257.0	258.7	260.5
60°	230.7	235.7	240.7	244.1	245.9	247.8	249.6	251.4
62.5°	220.9	226.2	231.5	235.0	236.8	238.5	240.3	242.0
65°	206.0	211.4	216.8	220.4	222.0	223.8	225.5	227.2
67.5°	191.0	196.4	201.8	205.5	207.2	209.1	210.9	212.6
70°	180.5	186.2	191.8	195.4	197.0	198.6	200.2	201.8
72.5°	170.4	175.9	181.5	185.2	187.0	188.9	190.8	192.7
75°	155.1	160.7	166.4	170.1	171.7	173.5	175.2	176.9
77.5°	140.1	145.8	151.4	155.1	156.9	158.8	160.7	162.5
80°	130.0	135.5	141.0	144.7	146.6	148.4	150.2	152.0
82.5°	120.5	126.0	131.5	135.1	136.9	138.6	140.4	142.1
85°	106.9	112.4	118.0	121.6	123.4	125.3	127.1	129.0
87.5°	97.3	102.7	108.2	111.8	113.5	115.3	116.9	118.7
90°	97.8	103.5	109.2	113.0	114.7	116.5	118.3	120.0
92.5°	94.2	99.6	105.0	108.5	110.2	111.9	113.6	115.3
95°	95.1	100.5	106.0	109.5	110.9	112.4	113.9	115.4
97.5°	95.0	100.2	105.4	108.9	110.6	112.3	113.9	115.6
100°	94.0	99.5	105.1	108.8	110.4	112.0	113.6	115.3
102.5°	91.5	97.2	102.9	106.6	108.4	110.0	111.8	113.4
105°	87.3	92.9	98.5	102.3	104.1	105.9	107.7	109.5
107.5°	88.1	91.5	94.9	97.5	99.3	101.1	102.9	104.7
110°	105.6	100.6	95.6	94.0	95.9	97.7	99.5	101.3



TEST NUMBER: P331297-927

CATALOG NUMBER: SA2XXDIP-C485D530U927-4F0-1E-UDD-D

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	163.7	134.4	105.1	91.3	93.1	94.8	96.6	98.3
115°	213.4	174.8	136.2	114.3	109.2	104.0	98.8	93.6
117.5°	300.4	294.0	287.6	274.2	253.8	233.4	213.0	192.6
120°	340.4	345.2	350.0	346.9	336.0	325.0	314.0	303.1
122.5°	356.0	360.2	364.5	366.0	364.8	363.7	362.5	361.3
125°	377.9	382.1	386.2	389.0	390.5	392.0	393.4	394.9
127.5°	397.8	402.0	406.2	408.8	410.0	411.2	412.5	413.7
130°	410.4	414.5	418.7	421.3	422.2	423.2	424.1	425.1
132.5°	422.6	426.5	430.4	432.8	433.8	434.7	435.7	436.7
135°	440.1	443.8	447.4	449.7	450.6	451.5	452.3	453.2
137.5°	456.2	459.5	462.9	464.8	465.4	466.0	466.5	467.1
140°	466.8	469.7	472.6	474.3	474.6	474.9	475.2	475.5
142.5°	477.1	479.5	482.0	483.2	483.5	483.7	483.9	484.2
145°	491.9	493.4	494.8	495.6	495.8	496.0	496.2	496.4
147.5°	505.3	505.9	506.4	506.7	506.6	506.6	506.5	506.4
150°	514.1	514.7	515.2	515.3	514.8	514.4	513.9	513.5
152.5°	522.4	523.0	523.6	523.5	522.9	522.3	521.7	521.1
155°	533.6	534.2	534.7	534.6	533.9	533.1	532.4	531.6
157.5°	543.0	543.6	544.2	544.2	543.4	542.7	542.0	541.3
160°	548.4	549.0	549.5	549.5	548.9	548.3	547.6	546.9
162.5°	553.6	554.2	554.8	554.8	554.0	553.2	552.4	551.6
165°	559.8	560.5	561.1	561.1	560.5	559.8	559.2	558.5
167.5°	565.0	565.7	566.3	566.3	565.4	564.6	563.7	562.9
170°	567.7	568.3	568.9	568.9	568.0	567.2	566.4	565.5
172.5°	569.7	570.3	570.9	570.8	570.1	569.2	568.4	567.5
175°	571.8	572.4	573.1	573.0	572.0	571.1	570.2	569.3
177.5°	572.0	572.6	573.1	573.0	572.4	571.6	571.0	570.4
180°	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3

(END OF REPORT)