

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331454

Luminaire Tested: **SA2XXDIP-C1005D925U835-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331454
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C1005D925U835-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 925 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7366.4 lumens
Efficiency: N/A
Efficacy: 110.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 66.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331454
CATALOG NUMBER: SA2XXDIP-C1005D925U835-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331454

CATALOG NUMBER: SA2XXDIP-C1005D925U835-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	55				
1	99	95	91	87	92	88	85	81	76	73	71	64	62	61	54	52	51	46				
2	90	83	76	71	83	77	71	67	66	62	59	56	53	51	47	45	43	39				
3	82	73	65	59	76	68	61	56	58	53	49	50	46	43	42	39	37	33				
4	75	64	56	50	70	60	53	47	52	46	42	44	40	37	37	34	32	28				
5	69	57	49	43	64	54	46	41	47	41	36	40	35	32	34	30	28	25				
6	64	51	43	37	59	48	41	35	42	36	32	36	32	28	31	27	24	22				
7	59	46	38	33	55	44	36	31	38	32	28	33	28	25	28	24	22	19				
8	55	42	34	29	51	40	33	28	35	29	25	30	25	22	26	22	19	17				
9	51	39	31	26	47	36	29	25	32	26	22	28	23	20	24	20	18	15				
10	48	35	28	23	44	33	27	22	29	24	20	26	21	18	22	19	16	14				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	25733	25733	25733
5°	25832	25459	25608
10°	25678	25201	25327
15°	25361	24874	24849
20°	24911	24383	24357
25°	24464	23779	23779
30°	23886	23228	23029
35°	23349	22565	22231
40°	22675	21901	21479
45°	22012	21240	20717
50°	21288	20557	19826
55°	20535	19758	19023
60°	19695	18807	18112
65°	18793	17857	17039
70°	17651	16711	15918
75°	16064	15390	15009
80°	14254	13826	13110
85°	11634	11078	9930



TEST NUMBER: P331454

CATALOG NUMBER: SA2XXDIP-C1005D925U835-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	149.9	2.0
10°-20°	421.7	5.7
20°-30°	619.8	8.4
30°-40°	720.0	9.8
40°-50°	719.2	9.8
50°-60°	627.2	8.5
60°-70°	463.8	6.3
70°-80°	262.7	3.6
80°-90°	75.4	1.0
90°-100°	74.9	1.0
100°-110°	232.7	3.2
110°-120°	397.8	5.4
120°-130°	523.2	7.1
130°-140°	587.2	8.0
140°-150°	575.7	7.8
150°-160°	482.9	6.6
160°-170°	320.3	4.3
170°-180°	111.9	1.5
0°-30°	1191.4	16.2
0°-40°	1911.4	25.9
0°-60°	3257.9	44.2
0°-90°	4059.7	55.1
90°-120°	705.5	9.6
90°-150°	2391.6	32.5
90°-180°	3307.0	44.9
0°-180°	7366.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1594	1594	1594	1594	1594	
5°	1594	1587	1571	1582	1580	151
15°	1517	1507	1488	1493	1487	427
25°	1373	1360	1335	1338	1335	631
35°	1185	1169	1145	1136	1128	739
45°	964	953	930	914	907	744
55°	730	720	702	684	676	652
65°	492	482	467	454	446	486
75°	258	254	247	238	241	275
85°	63	61	60	55	54	72
90°	1	14	35	33	34	6
95°	52	61	64	64	62	60
105°	215	218	220	221	222	227
115°	399	405	403	402	399	395
125°	581	589	587	584	583	519
135°	752	762	764	763	760	580
145°	912	919	925	926	922	570
155°	1043	1046	1049	1053	1051	480
165°	1135	1134	1134	1140	1136	320
175°	1181	1178	1176	1182	1177	112
180°	1183	1183	1183	1183	1183	



TEST NUMBER: P331454

CATALOG NUMBER: SA2XXDIP-C1005D925U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8
2.5°	1601.2	1599.8	1598.5	1597.1	1595.7	1593.6	1590.6	1587.6	1584.6	1581.6	1584.3
5°	1593.8	1592.5	1591.1	1589.7	1588.4	1585.8	1582.1	1578.3	1574.6	1570.8	1573.6
7.5°	1579.7	1577.6	1575.5	1573.4	1571.3	1568.3	1564.5	1560.7	1556.9	1553.1	1555.8
10°	1566.2	1563.9	1561.5	1559.1	1556.7	1553.5	1549.4	1545.3	1541.2	1537.1	1539.9
12.5°	1547.9	1545.7	1543.6	1541.5	1539.4	1536.3	1532.2	1528.1	1524.1	1520.0	1521.9
15°	1517.2	1515.2	1513.1	1511.1	1509.0	1505.8	1501.4	1496.9	1492.5	1488.1	1489.5
17.5°	1478.0	1475.9	1473.9	1471.8	1469.8	1466.5	1462.0	1457.5	1453.0	1448.6	1450.1
20°	1449.8	1447.7	1445.7	1443.6	1441.6	1438.2	1433.4	1428.7	1423.9	1419.1	1420.1
22.5°	1421.6	1418.7	1415.9	1413.0	1410.1	1406.5	1402.0	1397.5	1393.0	1388.5	1388.7
25°	1373.2	1370.4	1367.7	1365.0	1362.3	1358.0	1352.2	1346.4	1340.6	1334.8	1335.5
27.5°	1318.0	1315.5	1313.1	1310.6	1308.2	1304.7	1300.1	1295.5	1291.0	1286.4	1285.4
30°	1281.2	1278.5	1275.7	1273.0	1270.3	1266.4	1261.3	1256.2	1251.1	1245.9	1244.9
32.5°	1242.0	1239.8	1237.6	1235.4	1233.2	1229.5	1224.1	1218.7	1213.3	1207.9	1206.1
35°	1184.6	1181.2	1177.8	1174.4	1171.0	1166.6	1161.1	1155.7	1150.3	1144.8	1142.8
37.5°	1120.0	1117.0	1114.0	1111.0	1108.0	1103.8	1098.3	1092.9	1087.4	1082.0	1079.4
40°	1075.8	1073.1	1070.4	1067.7	1064.9	1060.9	1055.4	1050.0	1044.5	1039.1	1036.0
42.5°	1032.9	1030.2	1027.5	1024.8	1022.0	1017.9	1012.5	1007.0	1001.6	996.1	992.8
45°	964.0	961.6	959.2	956.8	954.4	950.7	945.6	940.5	935.4	930.2	926.5
47.5°	895.3	893.1	890.8	888.6	886.3	882.5	877.2	871.9	866.6	861.3	857.3
50°	847.5	845.8	844.1	842.4	840.7	837.4	832.7	827.9	823.1	818.4	813.6
52.5°	800.9	798.7	796.4	794.2	791.9	788.5	784.0	779.5	775.1	770.6	766.6
55°	729.5	727.4	725.4	723.4	721.3	718.2	714.2	710.1	706.0	701.9	697.8
57.5°	657.8	656.1	654.5	652.9	651.2	648.2	643.7	639.2	634.7	630.2	626.2
60°	609.9	608.6	607.2	605.9	604.5	601.4	596.7	591.9	587.1	582.4	578.6
62.5°	563.4	561.2	559.0	556.8	554.6	551.7	548.0	544.4	540.7	537.0	533.5
65°	491.9	489.9	487.9	485.8	483.8	481.0	477.6	474.2	470.8	467.4	464.4
67.5°	419.3	417.7	416.0	414.4	412.8	410.4	407.3	404.3	401.2	398.2	395.8
70°	373.9	372.6	371.2	369.9	368.5	366.3	363.2	360.1	357.1	354.0	351.6
72.5°	327.3	326.0	324.6	323.3	321.9	320.2	318.3	316.3	314.3	312.3	309.9
75°	257.5	256.8	256.1	255.4	254.7	253.5	251.8	250.1	248.4	246.7	244.7
77.5°	194.9	193.8	192.6	191.5	190.3	189.4	188.7	188.0	187.3	186.7	185.6
80°	153.3	152.9	152.6	152.2	151.9	151.4	150.7	150.0	149.3	148.7	147.6
82.5°	114.0	114.0	113.9	113.8	113.7	113.5	113.1	112.7	112.3	111.9	110.6
85°	62.8	62.5	62.2	61.8	61.5	61.1	60.8	60.4	60.1	59.8	58.7
87.5°	22.3	22.3	22.2	22.2	22.2	22.4	22.9	23.3	23.7	24.2	23.2
90°	1.0	3.7	6.3	9.0	11.6	15.4	20.3	25.2	30.0	34.9	34.5
92.5°	17.8	19.7	21.7	23.6	25.6	27.1	28.3	29.4	30.6	31.7	31.8
95°	51.9	54.1	56.3	58.5	60.8	62.1	62.5	63.0	63.4	63.9	63.9
97.5°	94.8	96.8	98.7	100.7	102.6	104.0	104.9	105.7	106.5	107.4	107.4
100°	126.7	128.5	130.3	132.1	133.8	135.1	135.7	136.4	137.1	137.7	137.7
102.5°	160.3	161.7	163.1	164.5	165.9	167.1	167.9	168.8	169.6	170.5	170.6
105°	214.6	215.2	215.9	216.6	217.2	217.8	218.2	218.7	219.1	219.5	220.0
107.5°	269.2	270.2	271.2	272.2	273.2	273.6	273.6	273.6	273.6	273.6	273.8
110°	304.4	305.7	307.0	308.4	309.7	310.4	310.4	310.4	310.4	310.4	310.4



TEST NUMBER: P331454

CATALOG NUMBER: SA2XXDIP-C1005D925U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	342.7	344.0	345.4	346.7	348.0	348.6	348.4	348.2	348.1	347.9	347.4
115°	399.2	400.5	401.8	403.2	404.5	404.9	404.5	404.1	403.6	403.2	403.0
117.5°	455.5	457.2	459.0	460.8	462.6	462.8	461.6	460.3	459.1	457.9	457.3
120°	493.0	494.8	496.5	498.3	500.1	500.1	498.3	496.5	494.8	493.0	493.0
122.5°	527.3	529.4	531.6	533.7	535.8	536.3	535.0	533.8	532.6	531.3	530.8
125°	580.8	582.8	584.8	586.8	588.8	589.5	588.8	588.1	587.5	586.8	586.1
127.5°	632.9	635.4	638.0	640.5	643.0	643.9	643.1	642.3	641.5	640.7	639.9
130°	665.6	668.5	671.4	674.3	677.2	678.4	677.9	677.5	677.1	676.6	676.2
132.5°	702.4	704.7	707.1	709.4	711.8	713.0	713.1	713.2	713.2	713.3	712.4
135°	751.5	753.9	756.3	758.8	761.2	762.7	763.1	763.5	764.0	764.4	764.2
137.5°	803.2	805.1	807.1	809.1	811.1	812.4	813.0	813.6	814.2	814.7	814.6
140°	834.3	836.3	838.3	840.3	842.3	843.8	844.9	846.0	847.2	848.3	848.3
142.5°	866.2	868.2	870.2	872.2	874.2	875.6	876.3	877.1	877.8	878.6	878.8
145°	912.1	913.7	915.2	916.8	918.3	919.8	921.1	922.4	923.8	925.1	925.3
147.5°	953.0	954.9	956.8	958.6	960.5	961.9	962.8	963.6	964.5	965.4	965.9
150°	981.0	982.3	983.6	985.0	986.3	987.4	988.3	989.2	990.1	991.0	991.6
152.5°	1005.7	1007.1	1008.4	1009.7	1011.1	1012.3	1013.3	1014.4	1015.4	1016.5	1017.4
155°	1042.9	1043.5	1044.2	1044.9	1045.5	1046.2	1046.9	1047.5	1048.2	1048.8	1050.0
157.5°	1074.6	1075.0	1075.5	1075.9	1076.4	1076.8	1077.2	1077.6	1078.0	1078.4	1079.9
160°	1093.8	1094.2	1094.6	1095.1	1095.5	1095.9	1096.1	1096.3	1096.5	1096.7	1098.1
162.5°	1111.3	1111.4	1111.5	1111.6	1111.7	1111.8	1112.1	1112.3	1112.5	1112.7	1114.2
165°	1134.7	1134.5	1134.2	1134.0	1133.8	1133.7	1133.7	1133.7	1133.7	1133.7	1135.2
167.5°	1154.2	1153.6	1152.9	1152.2	1151.6	1151.2	1151.2	1151.1	1151.1	1151.0	1152.6
170°	1164.6	1163.9	1163.3	1162.6	1161.9	1161.5	1161.3	1161.1	1160.8	1160.6	1162.2
172.5°	1171.8	1171.1	1170.5	1169.8	1169.1	1168.7	1168.5	1168.2	1168.0	1167.8	1169.4
175°	1180.6	1179.9	1179.2	1178.6	1177.9	1177.4	1176.9	1176.5	1176.0	1175.6	1177.1
177.5°	1184.2	1183.6	1183.1	1182.6	1182.0	1181.6	1181.2	1180.9	1180.5	1180.2	1181.2
180°	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6



TEST NUMBER: P331454

CATALOG NUMBER: SA2XXDIP-C1005D925U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8
2.5°	1587.0	1589.7	1592.5	1593.6	1593.0	1592.5	1591.9	1591.4
5°	1576.3	1579.0	1581.7	1582.8	1582.1	1581.4	1580.7	1580.0
7.5°	1558.5	1561.2	1564.0	1565.0	1564.2	1563.5	1562.7	1562.0
10°	1542.6	1545.3	1548.0	1548.9	1547.9	1546.8	1545.8	1544.8
12.5°	1523.8	1525.7	1527.6	1528.2	1527.4	1526.7	1525.9	1525.2
15°	1490.8	1492.2	1493.5	1493.4	1491.7	1490.0	1488.3	1486.6
17.5°	1451.7	1453.3	1454.8	1454.8	1453.1	1451.5	1449.9	1448.2
20°	1421.2	1422.2	1423.2	1423.0	1421.7	1420.3	1419.0	1417.6
22.5°	1388.9	1389.1	1389.3	1389.0	1388.2	1387.4	1386.5	1385.7
25°	1336.2	1336.9	1337.6	1337.6	1336.9	1336.2	1335.5	1334.8
27.5°	1284.4	1283.3	1282.3	1281.0	1279.4	1277.7	1276.1	1274.5
30°	1243.9	1242.9	1241.9	1240.7	1239.3	1237.9	1236.6	1235.2
32.5°	1204.3	1202.4	1200.6	1199.0	1197.6	1196.3	1194.9	1193.5
35°	1140.7	1138.7	1136.6	1134.8	1133.1	1131.4	1129.6	1127.9
37.5°	1076.9	1074.4	1071.9	1069.8	1068.2	1066.5	1064.9	1063.3
40°	1032.9	1029.9	1026.8	1024.6	1023.2	1021.9	1020.5	1019.1
42.5°	989.5	986.1	982.8	980.2	978.3	976.4	974.5	972.5
45°	922.8	919.0	915.3	912.7	911.3	910.0	908.6	907.3
47.5°	853.4	849.4	845.5	842.5	840.5	838.6	836.6	834.6
50°	808.8	804.1	799.3	796.1	794.4	792.7	791.0	789.3
52.5°	762.7	758.7	754.8	751.7	749.4	747.2	744.9	742.7
55°	693.7	689.6	685.6	682.7	681.0	679.3	677.6	675.8
57.5°	622.1	618.1	614.1	611.4	610.2	608.9	607.6	606.3
60°	574.9	571.1	567.4	565.0	564.0	563.0	561.9	560.9
62.5°	530.1	526.6	523.1	520.7	519.4	518.1	516.8	515.5
65°	461.3	458.2	455.2	452.8	451.1	449.4	447.7	446.0
67.5°	393.4	391.0	388.6	386.7	385.4	384.0	382.7	381.3
70°	349.2	346.9	344.5	342.6	341.2	339.9	338.5	337.2
72.5°	307.6	305.2	302.8	301.1	300.0	298.9	297.8	296.7
75°	242.7	240.6	238.6	237.9	238.6	239.2	239.9	240.6
77.5°	184.6	183.6	182.6	181.6	180.6	179.7	178.7	177.8
80°	146.6	145.6	144.6	143.7	143.0	142.4	141.7	141.0
82.5°	109.3	108.0	106.7	106.0	105.8	105.7	105.6	105.4
85°	57.7	56.7	55.7	55.0	54.7	54.3	54.0	53.6
87.5°	22.3	21.4	20.5	20.0	19.7	19.5	19.3	19.0
90°	34.0	33.6	33.2	33.0	33.3	33.5	33.7	33.9
92.5°	31.9	32.0	32.1	32.2	32.2	32.2	32.3	32.3
95°	63.9	63.9	63.9	63.6	63.2	62.8	62.3	61.9
97.5°	107.4	107.4	107.4	107.4	107.3	107.3	107.2	107.2
100°	137.7	137.7	137.7	137.6	137.4	137.2	136.9	136.7
102.5°	170.8	171.0	171.2	171.1	170.9	170.7	170.5	170.3
105°	220.4	220.9	221.3	221.5	221.5	221.5	221.5	221.5
107.5°	274.0	274.2	274.3	273.9	272.9	271.9	270.9	269.8
110°	310.4	310.4	310.4	310.0	309.4	308.7	308.0	307.4



TEST NUMBER: P331454

CATALOG NUMBER: SA2XXDIP-C1005D925U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	346.8	346.3	345.8	345.2	344.8	344.3	343.8	343.3
115°	402.7	402.5	402.3	401.8	401.2	400.5	399.8	399.2
117.5°	456.8	456.3	455.7	455.1	454.5	453.8	453.1	452.5
120°	493.0	493.0	493.0	492.7	492.0	491.3	490.7	490.0
122.5°	530.2	529.7	529.2	528.7	528.2	527.7	527.2	526.7
125°	585.5	584.8	584.1	583.7	583.5	583.2	583.0	582.8
127.5°	639.1	638.3	637.5	636.7	636.0	635.3	634.6	633.9
130°	675.7	675.3	674.8	674.2	673.3	672.4	671.5	670.6
132.5°	711.4	710.4	709.4	708.6	707.9	707.2	706.5	705.8
135°	764.0	763.8	763.5	763.1	762.4	761.8	761.1	760.4
137.5°	814.4	814.2	814.0	813.5	812.6	811.7	810.8	809.9
140°	848.3	848.3	848.3	847.8	846.9	846.0	845.2	844.3
142.5°	879.0	879.1	879.3	879.0	878.1	877.2	876.3	875.4
145°	925.5	925.8	926.0	925.7	924.8	923.9	923.0	922.1
147.5°	966.4	966.9	967.4	967.2	966.4	965.5	964.7	963.8
150°	992.3	993.0	993.6	993.6	993.0	992.3	991.6	991.0
152.5°	1018.2	1019.0	1019.9	1019.9	1019.0	1018.2	1017.4	1016.5
155°	1051.1	1052.2	1053.3	1053.5	1052.8	1052.2	1051.5	1050.8
157.5°	1081.4	1082.9	1084.4	1084.6	1083.6	1082.5	1081.4	1080.4
160°	1099.4	1100.7	1102.1	1102.3	1101.4	1100.5	1099.6	1098.7
162.5°	1115.7	1117.2	1118.7	1119.0	1117.9	1116.8	1115.8	1114.7
165°	1136.8	1138.3	1139.9	1140.1	1139.0	1137.9	1136.8	1135.7
167.5°	1154.1	1155.7	1157.2	1157.4	1156.3	1155.1	1154.0	1152.8
170°	1163.7	1165.3	1166.8	1166.9	1165.6	1164.3	1162.9	1161.6
172.5°	1170.9	1172.5	1174.0	1174.1	1172.8	1171.5	1170.1	1168.8
175°	1178.7	1180.2	1181.8	1181.9	1180.6	1179.2	1177.9	1176.6
177.5°	1182.3	1183.4	1184.4	1184.4	1183.4	1182.3	1181.2	1180.2
180°	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6

(END OF REPORT)