

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331455

Luminaire Tested: **SA2XXDIP-C1005D925U835-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331455
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C1005D925U835-4F0-1E-UDD-F4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 925 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7671.0 lumens
Efficiency: N/A
Efficacy: 114.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 66.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331455
CATALOG NUMBER: SA2XXDIP-C1005D925U835-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P331455

CATALOG NUMBER: SA2XXDIP-C1005D925U835-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59	53
1	98	94	90	87	91	87	84	81	74	72	70	63	61	59	52	51	50	45
2	90	82	76	71	83	76	71	66	65	61	58	55	52	50	46	44	42	37
3	82	72	65	59	75	67	61	55	58	53	49	49	45	42	41	38	36	32
4	75	64	56	50	69	60	52	47	51	46	41	43	39	36	36	33	31	27
5	69	57	49	43	63	53	46	40	46	40	36	39	35	31	33	29	27	24
6	63	51	43	37	58	48	40	35	41	36	31	35	31	27	30	26	24	21
7	59	46	38	33	54	43	36	31	37	32	28	32	28	24	27	24	21	18
8	54	42	34	29	50	39	32	27	34	29	24	29	25	22	25	21	19	16
9	51	38	31	26	47	36	29	24	31	26	22	27	23	19	23	20	17	15
10	47	35	28	23	44	33	26	22	29	23	20	25	21	18	21	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	25733	25733	25733
5°	25832	25459	25608
10°	25678	25201	25327
15°	25361	24874	24849
20°	24911	24383	24357
25°	24464	23779	23779
30°	23886	23228	23029
35°	23349	22565	22231
40°	22675	21901	21479
45°	22012	21240	20717
50°	21288	20557	19826
55°	20535	19758	19023
60°	19695	18807	18112
65°	18793	17857	17039
70°	17651	16711	15918
75°	16064	15390	15009
80°	14254	13826	13110
85°	11634	11078	9930



TEST NUMBER: P331455

CATALOG NUMBER: SA2XXDIP-C1005D925U835-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	149.9	2.0
10°-20°	421.7	5.5
20°-30°	619.8	8.1
30°-40°	720.0	9.4
40°-50°	719.2	9.4
50°-60°	627.2	8.2
60°-70°	463.8	6.0
70°-80°	262.7	3.4
80°-90°	75.3	1.0
90°-100°	207.5	2.7
100°-110°	704.2	9.2
110°-120°	748.1	9.8
120°-130°	615.8	8.0
130°-140°	494.5	6.4
140°-150°	373.7	4.9
150°-160°	262.6	3.4
160°-170°	154.6	2.0
170°-180°	50.3	0.7
0°-30°	1191.4	15.5
0°-40°	1911.4	24.9
0°-60°	3257.9	42.5
0°-90°	4059.6	52.9
90°-120°	1659.8	21.6
90°-150°	3143.8	41.0
90°-180°	3611.0	47.1
0°-180°	7671.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1594	1594	1594	1594	1594	
5°	1594	1587	1571	1582	1580	151
15°	1517	1507	1488	1493	1487	427
25°	1373	1360	1335	1338	1335	631
35°	1185	1169	1145	1136	1128	739
45°	964	953	930	914	907	744
55°	730	720	702	684	676	652
65°	492	482	467	454	446	486
75°	258	254	247	238	241	275
85°	63	61	60	55	54	72
90°	1	14	34	32	33	5
95°	35	86	391	148	114	37
105°	122	184	740	1322	1125	129
115°	215	271	619	1277	1480	213
125°	299	354	595	1034	1201	266
135°	351	419	588	869	995	271
145°	401	461	585	726	794	252
155°	456	492	568	642	668	210
165°	497	512	544	577	586	140
175°	518	518	523	530	528	49
180°	519	519	519	519	519	



TEST NUMBER: P331455

CATALOG NUMBER: SA2XXDIP-C1005D925U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8
2.5°	1601.2	1599.8	1598.5	1597.1	1595.7	1593.6	1590.6	1587.6	1584.6	1581.6	1584.3
5°	1593.8	1592.5	1591.1	1589.7	1588.4	1585.8	1582.1	1578.3	1574.6	1570.8	1573.6
7.5°	1579.7	1577.6	1575.5	1573.4	1571.3	1568.3	1564.5	1560.7	1556.9	1553.1	1555.8
10°	1566.2	1563.9	1561.5	1559.1	1556.7	1553.5	1549.4	1545.3	1541.2	1537.1	1539.9
12.5°	1547.9	1545.7	1543.6	1541.5	1539.4	1536.3	1532.2	1528.1	1524.1	1520.0	1521.9
15°	1517.2	1515.2	1513.1	1511.1	1509.0	1505.8	1501.4	1496.9	1492.5	1488.1	1489.5
17.5°	1478.0	1475.9	1473.9	1471.8	1469.8	1466.5	1462.0	1457.5	1453.0	1448.6	1450.1
20°	1449.8	1447.7	1445.7	1443.6	1441.6	1438.2	1433.4	1428.7	1423.9	1419.1	1420.1
22.5°	1421.6	1418.7	1415.9	1413.0	1410.1	1406.5	1402.0	1397.5	1393.0	1388.5	1388.7
25°	1373.2	1370.4	1367.7	1365.0	1362.3	1358.0	1352.2	1346.4	1340.6	1334.8	1335.5
27.5°	1318.0	1315.5	1313.1	1310.6	1308.2	1304.7	1300.1	1295.5	1291.0	1286.4	1285.4
30°	1281.2	1278.5	1275.7	1273.0	1270.3	1266.4	1261.3	1256.2	1251.1	1245.9	1244.9
32.5°	1242.0	1239.8	1237.6	1235.4	1233.2	1229.5	1224.1	1218.7	1213.3	1207.9	1206.1
35°	1184.6	1181.2	1177.8	1174.4	1171.0	1166.6	1161.1	1155.7	1150.3	1144.8	1142.8
37.5°	1120.0	1117.0	1114.0	1111.0	1108.0	1103.8	1098.3	1092.9	1087.4	1082.0	1079.4
40°	1075.8	1073.1	1070.4	1067.7	1064.9	1060.9	1055.4	1050.0	1044.5	1039.1	1036.0
42.5°	1032.9	1030.2	1027.5	1024.8	1022.0	1017.9	1012.5	1007.0	1001.6	996.1	992.8
45°	964.0	961.6	959.2	956.8	954.4	950.7	945.6	940.5	935.4	930.2	926.5
47.5°	895.3	893.1	890.8	888.6	886.3	882.5	877.2	871.9	866.6	861.3	857.3
50°	847.5	845.8	844.1	842.4	840.7	837.4	832.7	827.9	823.1	818.4	813.6
52.5°	800.9	798.7	796.4	794.2	791.9	788.5	784.0	779.5	775.1	770.6	766.6
55°	729.5	727.4	725.4	723.4	721.3	718.2	714.2	710.1	706.0	701.9	697.8
57.5°	657.8	656.1	654.5	652.9	651.2	648.2	643.7	639.2	634.7	630.2	626.2
60°	609.9	608.6	607.2	605.9	604.5	601.4	596.7	591.9	587.1	582.4	578.6
62.5°	563.4	561.2	559.0	556.8	554.6	551.7	548.0	544.4	540.7	537.0	533.5
65°	491.9	489.9	487.9	485.8	483.8	481.0	477.6	474.2	470.8	467.4	464.4
67.5°	419.3	417.7	416.0	414.4	412.8	410.4	407.3	404.3	401.2	398.2	395.8
70°	373.9	372.6	371.2	369.9	368.5	366.3	363.2	360.1	357.1	354.0	351.6
72.5°	327.3	326.0	324.6	323.3	321.9	320.2	318.3	316.3	314.3	312.3	309.9
75°	257.5	256.8	256.1	255.4	254.7	253.5	251.8	250.1	248.4	246.7	244.7
77.5°	194.9	193.8	192.6	191.5	190.3	189.4	188.7	188.0	187.3	186.7	185.6
80°	153.3	152.9	152.6	152.2	151.9	151.4	150.7	150.0	149.3	148.7	147.6
82.5°	114.0	114.0	113.9	113.8	113.7	113.5	113.1	112.7	112.3	111.9	110.6
85°	62.8	62.5	62.2	61.8	61.5	61.1	60.8	60.4	60.1	59.8	58.7
87.5°	22.3	22.3	22.6	22.4	22.3	22.3	22.8	23.6	24.3	24.0	22.9
90°	1.0	4.0	8.0	10.0	12.0	15.0	20.0	26.9	32.9	33.9	32.9
92.5°	12.2	17.6	24.8	29.1	35.9	45.3	67.9	99.6	127.9	129.7	109.6
95°	34.9	38.9	48.9	57.9	73.9	97.8	143.7	230.5	346.3	391.2	342.3
97.5°	56.9	62.3	72.9	86.4	104.8	131.9	189.6	310.6	503.0	667.9	700.6
100°	76.8	79.8	88.8	104.8	124.8	152.7	205.6	327.4	542.9	788.4	932.2
102.5°	95.2	97.4	106.4	122.4	143.1	171.1	220.0	328.2	527.8	792.4	1018.4
105°	121.8	125.8	132.7	147.7	169.7	197.6	244.5	333.3	498.0	739.5	1005.0
107.5°	150.5	153.7	160.5	174.3	196.0	224.2	269.7	347.1	483.2	682.9	917.4
110°	169.7	173.7	179.6	192.6	213.6	242.5	286.4	358.3	480.1	655.7	862.3



TEST NUMBER: P331455

CATALOG NUMBER: SA2XXDIP-C1005D925U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	187.2	191.2	198.0	210.2	230.3	260.1	302.4	370.3	480.8	638.1	824.0
115°	214.6	219.6	225.6	237.5	257.5	284.4	327.4	388.2	485.0	618.8	776.5
117.5°	242.9	246.9	252.9	263.5	282.6	310.6	350.3	407.4	492.2	609.4	746.5
120°	260.5	264.5	270.5	279.4	299.4	327.4	366.3	420.2	497.0	603.8	730.6
122.5°	277.3	280.4	286.4	296.2	316.2	344.9	381.4	431.3	502.6	600.6	717.0
125°	299.4	302.4	308.4	320.4	340.3	368.3	404.2	449.1	511.0	594.8	697.6
127.5°	317.0	321.0	329.3	342.5	361.7	390.4	425.4	465.7	519.6	591.4	679.7
130°	327.4	331.3	341.3	355.3	375.3	403.2	438.1	476.1	526.0	589.8	667.7
132.5°	336.9	341.7	352.5	367.3	388.0	416.0	449.3	486.4	532.3	589.0	658.1
135°	351.3	355.3	367.3	382.2	405.2	433.1	465.1	500.0	539.9	587.8	644.7
137.5°	364.9	369.7	381.6	397.6	420.4	446.3	477.9	510.4	546.7	587.6	635.3
140°	375.3	379.3	391.2	407.2	429.2	455.1	485.0	516.0	549.9	586.8	629.8
142.5°	385.6	388.8	400.0	416.0	437.1	461.5	490.6	520.8	552.3	586.8	624.2
145°	401.2	405.2	415.2	430.2	450.1	472.1	499.0	527.0	554.9	584.8	616.8
147.5°	418.0	421.0	430.5	444.3	460.9	480.5	505.8	530.4	555.7	581.3	609.2
150°	429.2	432.1	440.1	453.1	468.1	486.0	509.0	531.9	554.9	578.9	602.8
152.5°	440.3	441.7	449.7	461.1	475.3	491.6	512.2	532.7	553.3	574.9	597.2
155°	456.1	457.1	463.1	474.1	485.0	500.0	517.0	533.9	550.9	567.9	586.8
157.5°	469.3	470.3	475.1	484.6	493.4	506.0	520.4	533.9	546.3	560.7	577.1
160°	478.1	479.1	483.0	491.0	499.0	510.0	522.0	533.9	543.9	555.9	569.9
162.5°	486.8	486.2	490.2	496.6	503.8	512.4	522.8	533.1	541.5	551.9	563.5
165°	497.0	496.0	498.0	504.0	509.0	515.0	524.0	531.0	536.9	543.9	552.9
167.5°	505.4	504.2	506.0	509.8	513.4	517.2	523.8	529.6	532.3	536.9	542.5
170°	511.0	509.0	510.0	513.0	515.0	518.0	523.0	528.0	530.0	532.9	536.9
172.5°	514.2	513.0	512.4	515.4	516.6	518.8	522.2	525.6	526.8	528.2	531.4
175°	518.0	517.0	516.0	518.0	518.0	519.0	521.0	523.0	522.0	523.0	524.0
177.5°	519.8	518.2	517.4	519.0	519.0	519.0	519.8	521.4	519.8	519.0	519.8
180°	519.0	519.0	519.0	519.0	519.0	519.0	519.0	519.0	519.0	519.0	519.0



TEST NUMBER: P331455

CATALOG NUMBER: SA2XXDIP-C1005D925U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8
2.5°	1587.0	1589.7	1592.5	1593.6	1593.0	1592.5	1591.9	1591.4
5°	1576.3	1579.0	1581.7	1582.8	1582.1	1581.4	1580.7	1580.0
7.5°	1558.5	1561.2	1564.0	1565.0	1564.2	1563.5	1562.7	1562.0
10°	1542.6	1545.3	1548.0	1548.9	1547.9	1546.8	1545.8	1544.8
12.5°	1523.8	1525.7	1527.6	1528.2	1527.4	1526.7	1525.9	1525.2
15°	1490.8	1492.2	1493.5	1493.4	1491.7	1490.0	1488.3	1486.6
17.5°	1451.7	1453.3	1454.8	1454.8	1453.1	1451.5	1449.9	1448.2
20°	1421.2	1422.2	1423.2	1423.0	1421.7	1420.3	1419.0	1417.6
22.5°	1388.9	1389.1	1389.3	1389.0	1388.2	1387.4	1386.5	1385.7
25°	1336.2	1336.9	1337.6	1337.6	1336.9	1336.2	1335.5	1334.8
27.5°	1284.4	1283.3	1282.3	1281.0	1279.4	1277.7	1276.1	1274.5
30°	1243.9	1242.9	1241.9	1240.7	1239.3	1237.9	1236.6	1235.2
32.5°	1204.3	1202.4	1200.6	1199.0	1197.6	1196.3	1194.9	1193.5
35°	1140.7	1138.7	1136.6	1134.8	1133.1	1131.4	1129.6	1127.9
37.5°	1076.9	1074.4	1071.9	1069.8	1068.2	1066.5	1064.9	1063.3
40°	1032.9	1029.9	1026.8	1024.6	1023.2	1021.9	1020.5	1019.1
42.5°	989.5	986.1	982.8	980.2	978.3	976.4	974.5	972.5
45°	922.8	919.0	915.3	912.7	911.3	910.0	908.6	907.3
47.5°	853.4	849.4	845.5	842.5	840.5	838.6	836.6	834.6
50°	808.8	804.1	799.3	796.1	794.4	792.7	791.0	789.3
52.5°	762.7	758.7	754.8	751.7	749.4	747.2	744.9	742.7
55°	693.7	689.6	685.6	682.7	681.0	679.3	677.6	675.8
57.5°	622.1	618.1	614.1	611.4	610.2	608.9	607.6	606.3
60°	574.9	571.1	567.4	565.0	564.0	563.0	561.9	560.9
62.5°	530.1	526.6	523.1	520.7	519.4	518.1	516.8	515.5
65°	461.3	458.2	455.2	452.8	451.1	449.4	447.7	446.0
67.5°	393.4	391.0	388.6	386.7	385.4	384.0	382.7	381.3
70°	349.2	346.9	344.5	342.6	341.2	339.9	338.5	337.2
72.5°	307.6	305.2	302.8	301.1	300.0	298.9	297.8	296.7
75°	242.7	240.6	238.6	237.9	238.6	239.2	239.9	240.6
77.5°	184.6	183.6	182.6	181.6	180.6	179.7	178.7	177.8
80°	146.6	145.6	144.6	143.7	143.0	142.4	141.7	141.0
82.5°	109.3	108.0	106.7	106.0	105.8	105.7	105.6	105.4
85°	57.7	56.7	55.7	55.0	54.7	54.3	54.0	53.6
87.5°	21.9	20.7	20.3	19.9	19.7	19.4	19.1	18.8
90°	31.9	29.9	31.9	32.9	32.9	32.9	32.9	32.9
92.5°	87.0	74.7	66.3	60.1	59.3	56.1	56.9	55.3
95°	261.5	200.6	158.7	136.7	123.8	115.8	112.8	113.8
97.5°	610.2	499.2	391.2	319.2	271.5	246.9	232.3	224.0
100°	911.2	787.4	650.7	530.0	447.1	404.2	375.3	357.3
102.5°	1108.4	1080.5	980.5	852.5	762.5	689.2	653.1	628.8
105°	1212.6	1325.4	1338.4	1305.4	1243.5	1181.7	1138.7	1124.8
107.5°	1137.6	1307.4	1411.2	1459.5	1467.3	1463.9	1455.3	1436.8
110°	1072.9	1251.5	1379.3	1461.1	1504.0	1523.0	1532.0	1531.0



TEST NUMBER: P331455

CATALOG NUMBER: SA2XXDIP-C1005D925U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	1013.8	1185.3	1321.8	1415.6	1475.3	1507.0	1524.0	1529.4
115°	941.1	1094.8	1225.6	1328.4	1399.2	1445.1	1471.1	1480.1
117.5°	886.4	1021.4	1139.9	1236.4	1308.6	1357.1	1384.5	1392.0
120°	859.3	983.1	1088.8	1179.7	1249.5	1296.4	1325.4	1335.4
122.5°	837.7	951.1	1051.3	1133.4	1196.0	1242.1	1267.9	1276.3
125°	806.4	909.2	997.0	1071.9	1129.8	1167.7	1192.6	1200.6
127.5°	775.5	868.5	951.3	1020.4	1070.9	1106.4	1128.0	1134.4
130°	755.5	841.3	920.2	986.1	1035.0	1068.9	1088.8	1096.8
132.5°	736.3	815.8	888.2	950.1	998.2	1032.2	1050.5	1057.7
135°	709.6	775.5	841.3	897.2	940.1	973.1	991.0	995.0
137.5°	688.2	743.3	795.6	844.3	883.5	911.8	927.6	933.6
140°	674.7	722.6	768.5	812.4	844.3	870.3	885.3	891.2
142.5°	663.5	704.2	743.7	780.5	810.8	834.4	847.7	848.9
145°	647.7	680.7	711.6	740.5	764.5	781.5	791.4	794.4
147.5°	635.5	661.5	685.6	706.8	726.6	740.1	746.9	748.7
150°	626.8	648.7	669.7	687.6	702.6	714.6	720.6	721.6
152.5°	618.0	638.3	656.1	671.7	683.4	693.8	698.2	698.4
155°	605.8	621.8	636.7	647.7	658.7	665.7	669.7	667.7
157.5°	591.6	605.0	617.6	626.2	633.9	639.7	641.5	641.5
160°	582.8	593.8	604.8	611.8	618.8	623.8	624.8	624.8
162.5°	574.1	583.4	592.8	598.2	605.2	608.6	609.6	608.8
165°	560.9	567.9	574.9	578.9	582.8	586.8	586.8	585.8
167.5°	548.3	553.7	558.5	562.1	563.9	566.1	565.9	564.7
170°	541.9	544.9	548.9	550.9	551.9	554.9	553.9	551.9
172.5°	534.7	536.9	540.1	541.3	542.3	543.7	542.7	541.5
175°	527.0	528.0	529.0	530.0	530.0	531.0	530.0	528.0
177.5°	521.4	521.4	522.2	522.2	522.2	522.2	521.4	519.8
180°	519.0	519.0	519.0	519.0	519.0	519.0	519.0	519.0

(END OF REPORT)