

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331284

Luminaire Tested: **SA2XXDIP-C290D1080U835-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331284  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXDIP-C290D1080U835-4F0-1E-UDD-F4  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1080 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5410.9 lumens  
Efficiency: N/A  
Efficacy: 128.2 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Indirect

Input Watts (W): 42.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331284  
CATALOG NUMBER: SA2XXDIP-C290D1080U835-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P331284

CATALOG NUMBER: SA2XXDIP-C290D1080U835-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	101	101	101	101	89	89	89	89	68	68	68	49	49	49	31	31	31	22				
1	92	87	84	80	81	78	75	72	59	57	55	43	41	40	27	26	26	19				
2	83	76	70	65	74	68	63	59	52	49	46	37	35	33	24	23	22	16				
3	76	67	60	54	67	60	54	49	46	42	38	33	30	28	21	20	18	13				
4	69	59	52	46	61	53	46	41	41	36	33	29	26	24	19	17	16	11				
5	64	52	45	39	56	47	40	35	36	32	28	26	23	21	17	15	14	10				
6	58	47	39	34	52	42	35	30	32	28	24	24	20	18	15	13	12	9				
7	54	42	35	29	48	38	31	27	29	25	21	21	18	16	14	12	11	8				
8	50	38	31	26	44	34	28	23	27	22	19	19	16	14	13	11	10	7				
9	46	35	27	23	41	31	25	21	24	20	17	18	15	13	12	10	9	6				
10	43	32	25	20	38	28	22	18	22	18	15	16	13	11	11	9	8	6				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	7627	7627	7627
5°	7656	7546	7592
10°	7612	7470	7507
15°	7517	7373	7366
20°	7383	7228	7220
25°	7251	7049	7049
30°	7081	6885	6825
35°	6922	6688	6589
40°	6721	6492	6367
45°	6524	6295	6140
50°	6310	6094	5878
55°	6086	5858	5638
60°	5838	5574	5370
65°	5570	5295	5051
70°	5231	4952	4716
75°	4760	4560	4448
80°	4221	4100	3887
85°	3446	3279	2946



TEST NUMBER: P331284

CATALOG NUMBER: SA2XXDIP-C290D1080U835-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	44.4	0.8
10°-20°	125.0	2.3
20°-30°	183.7	3.4
30°-40°	213.4	3.9
40°-50°	213.2	3.9
50°-60°	185.9	3.4
60°-70°	137.5	2.5
70°-80°	77.9	1.4
80°-90°	26.4	0.5
90°-100°	241.5	4.5
100°-110°	819.6	15.1
110°-120°	870.7	16.1
120°-130°	716.8	13.2
130°-140°	575.6	10.6
140°-150°	435.0	8.0
150°-160°	305.7	5.6
160°-170°	180.0	3.3
170°-180°	58.6	1.1
0°-30°	353.2	6.5
0°-40°	566.6	10.5
0°-60°	965.7	17.8
0°-90°	1207.4	22.3
90°-120°	1931.9	35.7
90°-150°	3659.3	67.6
90°-180°	4204.0	77.7
0°-180°	5410.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	472	472	472	472	472	
5°	472	470	466	469	468	45
15°	450	447	441	443	441	127
25°	407	403	396	396	396	187
35°	351	346	339	337	334	219
45°	286	282	276	271	269	220
55°	216	213	208	203	200	193
65°	146	143	139	135	132	144
75°	76	75	73	71	71	82
85°	19	18	18	16	16	21
90°	1	16	40	38	38	3
95°	41	100	455	172	132	43
105°	142	214	861	1539	1309	151
115°	250	315	720	1486	1723	248
125°	348	412	692	1204	1398	309
135°	409	488	684	1012	1158	316
145°	467	537	681	845	925	293
155°	531	573	661	748	777	244
165°	578	596	633	671	682	163
175°	603	604	609	616	614	57
180°	604	604	604	604	604	



TEST NUMBER: P331284

CATALOG NUMBER: SA2XXDIP-C290D1080U835-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	472.4	472.4	472.4	472.4	472.4	472.4	472.4	472.4	472.4	472.4	472.4
2.5°	474.6	474.2	473.8	473.4	473.0	472.4	471.5	470.6	469.7	468.8	469.6
5°	472.4	472.0	471.6	471.2	470.8	470.1	469.0	467.9	466.7	465.6	466.4
7.5°	468.3	467.6	467.0	466.4	465.8	464.9	463.8	462.6	461.5	460.4	461.2
10°	464.3	463.6	462.9	462.2	461.4	460.5	459.3	458.1	456.9	455.6	456.4
12.5°	458.8	458.2	457.6	456.9	456.3	455.4	454.2	453.0	451.8	450.6	451.1
15°	449.7	449.1	448.5	447.9	447.3	446.4	445.0	443.7	442.4	441.1	441.5
17.5°	438.1	437.5	436.9	436.3	435.7	434.7	433.4	432.0	430.7	429.4	429.8
20°	429.7	429.1	428.5	427.9	427.3	426.3	424.9	423.5	422.1	420.7	421.0
22.5°	421.4	420.5	419.7	418.8	418.0	416.9	415.6	414.2	412.9	411.6	411.6
25°	407.0	406.2	405.4	404.6	403.8	402.5	400.8	399.1	397.4	395.7	395.9
27.5°	390.7	390.0	389.2	388.5	387.8	386.7	385.4	384.0	382.7	381.3	381.0
30°	379.8	379.0	378.2	377.4	376.5	375.4	373.9	372.4	370.8	369.3	369.0
32.5°	368.1	367.5	366.9	366.2	365.6	364.4	362.8	361.3	359.7	358.1	357.5
35°	351.2	350.1	349.1	348.1	347.1	345.8	344.2	342.6	341.0	339.3	338.7
37.5°	332.0	331.1	330.2	329.3	328.4	327.2	325.6	324.0	322.3	320.7	320.0
40°	318.9	318.1	317.3	316.5	315.7	314.5	312.8	311.2	309.6	308.0	307.1
42.5°	306.2	305.4	304.6	303.8	303.0	301.7	300.1	298.5	296.9	295.3	294.3
45°	285.7	285.0	284.3	283.6	282.9	281.8	280.3	278.8	277.3	275.7	274.6
47.5°	265.4	264.7	264.1	263.4	262.7	261.6	260.0	258.5	256.9	255.3	254.1
50°	251.2	250.7	250.2	249.7	249.2	248.2	246.8	245.4	244.0	242.6	241.2
52.5°	237.4	236.7	236.1	235.4	234.7	233.7	232.4	231.1	229.7	228.4	227.2
55°	216.2	215.6	215.0	214.4	213.8	212.9	211.7	210.5	209.3	208.1	206.8
57.5°	195.0	194.5	194.0	193.5	193.0	192.1	190.8	189.5	188.1	186.8	185.6
60°	180.8	180.4	180.0	179.6	179.2	178.3	176.9	175.5	174.0	172.6	171.5
62.5°	167.0	166.3	165.7	165.1	164.4	163.5	162.4	161.4	160.3	159.2	158.1
65°	145.8	145.2	144.6	144.0	143.4	142.6	141.6	140.6	139.6	138.6	137.6
67.5°	124.3	123.8	123.3	122.8	122.4	121.7	120.7	119.8	118.9	118.0	117.3
70°	110.8	110.4	110.0	109.6	109.2	108.6	107.7	106.8	105.8	104.9	104.2
72.5°	97.0	96.6	96.2	95.8	95.4	94.9	94.3	93.8	93.2	92.6	91.9
75°	76.3	76.1	75.9	75.7	75.5	75.2	74.7	74.1	73.6	73.1	72.5
77.5°	57.8	57.4	57.1	56.8	56.4	56.1	55.9	55.7	55.5	55.3	55.0
80°	45.4	45.3	45.2	45.1	45.0	44.9	44.7	44.5	44.3	44.1	43.8
82.5°	33.8	33.8	33.8	33.7	33.7	33.6	33.5	33.4	33.3	33.2	32.8
85°	18.6	18.5	18.4	18.3	18.2	18.1	18.0	17.9	17.8	17.7	17.4
87.5°	6.8	7.3	8.1	8.4	8.7	9.2	10.2	11.7	12.9	13.0	12.5
90°	1.2	4.6	9.3	11.6	13.9	17.4	23.2	31.4	38.3	39.5	38.3
92.5°	14.2	20.4	28.8	33.9	41.8	52.7	79.0	115.9	148.9	151.0	127.6
95°	40.7	45.3	56.9	67.4	86.0	113.8	167.3	268.3	403.1	455.4	398.5
97.5°	66.2	72.5	84.8	100.6	122.0	153.6	220.7	361.5	585.5	777.4	815.5
100°	89.4	92.9	103.4	122.0	145.2	177.7	239.3	381.0	631.9	917.7	1085.0
102.5°	110.8	113.4	123.8	142.4	166.6	199.1	256.0	382.0	614.3	922.4	1185.4
105°	141.7	146.4	154.5	171.9	197.5	230.0	284.6	388.0	579.7	860.8	1169.8
107.5°	175.2	178.9	186.8	202.8	228.2	260.9	313.9	404.0	562.5	794.8	1067.8
110°	197.5	202.1	209.1	224.2	248.6	282.3	333.4	417.0	558.8	763.2	1003.7



TEST NUMBER: P331284

CATALOG NUMBER: SA2XXDIP-C290D1080U835-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	217.9	222.6	230.5	244.6	268.1	302.7	352.0	431.0	559.7	742.8	959.1
115°	249.8	255.6	262.5	276.5	299.7	331.1	381.0	451.9	564.6	720.2	903.8
117.5°	282.8	287.4	294.4	306.7	329.0	361.5	407.7	474.2	572.9	709.3	868.9
120°	303.2	307.8	314.8	325.3	348.5	381.0	426.3	489.1	578.5	702.8	850.3
122.5°	322.7	326.4	333.4	344.8	368.0	401.5	444.0	502.1	585.0	699.1	834.5
125°	348.5	352.0	359.0	372.9	396.1	428.7	470.5	522.8	594.8	692.4	812.0
127.5°	368.9	373.6	383.4	398.7	421.0	454.4	495.1	542.0	604.8	688.4	791.1
130°	381.0	385.7	397.3	413.6	436.8	469.3	510.0	554.1	612.2	686.5	777.2
132.5°	392.2	397.8	410.3	427.5	451.7	484.2	523.0	566.2	619.6	685.6	766.0
135°	408.9	413.6	427.5	444.9	471.6	504.2	541.3	582.0	628.5	684.2	750.4
137.5°	424.7	430.3	444.2	462.8	489.3	519.5	556.2	594.1	636.4	684.0	739.5
140°	436.8	441.4	455.4	474.0	499.5	529.7	564.6	600.6	640.1	683.1	733.0
142.5°	448.9	452.6	465.6	484.2	508.8	537.2	571.1	606.2	642.9	683.1	726.5
145°	467.0	471.6	483.3	500.7	523.9	549.5	580.8	613.4	645.9	680.7	717.9
147.5°	486.5	490.0	501.1	517.2	536.5	559.2	588.7	617.3	646.8	676.6	709.1
150°	499.5	503.0	512.3	527.4	544.8	565.7	592.5	619.2	645.9	673.8	701.6
152.5°	512.5	514.2	523.4	536.7	553.2	572.2	596.2	620.1	644.0	669.1	695.1
155°	530.9	532.0	539.0	551.8	564.6	582.0	601.7	621.5	641.2	661.0	683.1
157.5°	546.2	547.4	553.0	564.1	574.3	589.0	605.7	621.5	635.9	652.6	671.7
160°	556.4	557.6	562.2	571.5	580.8	593.6	607.6	621.5	633.1	647.1	663.3
162.5°	566.7	566.0	570.6	578.0	586.4	596.4	608.5	620.6	630.3	642.4	655.9
165°	578.5	577.4	579.7	586.6	592.5	599.4	609.9	618.0	625.0	633.1	643.6
167.5°	588.3	586.9	589.0	593.4	597.6	602.0	609.6	616.4	619.6	625.0	631.5
170°	594.8	592.5	593.6	597.1	599.4	602.9	608.7	614.5	616.8	620.3	625.0
172.5°	598.5	597.1	596.4	599.9	601.3	603.8	607.8	611.7	613.1	614.8	618.5
175°	602.9	601.7	600.6	602.9	602.9	604.1	606.4	608.7	607.6	608.7	609.9
177.5°	605.0	603.1	602.2	604.1	604.1	604.1	605.0	606.9	605.0	604.1	605.0
180°	604.1	604.1	604.1	604.1	604.1	604.1	604.1	604.1	604.1	604.1	604.1



TEST NUMBER: P331284

CATALOG NUMBER: SA2XXDIP-C290D1080U835-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	472.4	472.4	472.4	472.4	472.4	472.4	472.4	472.4
2.5°	470.4	471.2	472.0	472.4	472.2	472.0	471.9	471.7
5°	467.3	468.1	468.9	469.2	469.0	468.8	468.6	468.4
7.5°	462.0	462.8	463.6	463.9	463.7	463.4	463.2	463.0
10°	457.3	458.1	458.9	459.1	458.8	458.5	458.2	457.9
12.5°	451.7	452.2	452.8	453.0	452.8	452.5	452.3	452.1
15°	441.9	442.3	442.7	442.7	442.2	441.7	441.2	440.7
17.5°	430.3	430.8	431.2	431.2	430.7	430.3	429.8	429.3
20°	421.3	421.6	421.9	421.8	421.4	421.0	420.6	420.2
22.5°	411.7	411.8	411.8	411.7	411.5	411.2	411.0	410.8
25°	396.1	396.3	396.5	396.5	396.3	396.1	395.9	395.7
27.5°	380.7	380.4	380.1	379.7	379.2	378.7	378.3	377.8
30°	368.7	368.4	368.1	367.8	367.4	367.0	366.6	366.1
32.5°	357.0	356.4	355.9	355.4	355.0	354.6	354.2	353.8
35°	338.1	337.5	336.9	336.4	335.9	335.4	334.9	334.3
37.5°	319.2	318.5	317.7	317.1	316.6	316.1	315.7	315.2
40°	306.2	305.3	304.4	303.7	303.3	302.9	302.5	302.1
42.5°	293.3	292.3	291.3	290.5	290.0	289.4	288.9	288.3
45°	273.5	272.4	271.3	270.5	270.1	269.7	269.3	268.9
47.5°	253.0	251.8	250.6	249.7	249.2	248.6	248.0	247.4
50°	239.8	238.3	236.9	236.0	235.5	235.0	234.5	234.0
52.5°	226.1	224.9	223.7	222.8	222.1	221.5	220.8	220.1
55°	205.6	204.4	203.2	202.4	201.9	201.3	200.8	200.3
57.5°	184.4	183.2	182.0	181.2	180.9	180.5	180.1	179.7
60°	170.4	169.3	168.2	167.5	167.2	166.9	166.6	166.3
62.5°	157.1	156.1	155.1	154.4	154.0	153.6	153.2	152.8
65°	136.7	135.8	134.9	134.2	133.7	133.2	132.7	132.2
67.5°	116.6	115.9	115.2	114.6	114.2	113.8	113.4	113.0
70°	103.5	102.8	102.1	101.6	101.2	100.7	100.3	99.9
72.5°	91.2	90.5	89.8	89.2	88.9	88.6	88.3	87.9
75°	71.9	71.3	70.7	70.5	70.7	70.9	71.1	71.3
77.5°	54.7	54.4	54.1	53.8	53.5	53.3	53.0	52.7
80°	43.5	43.2	42.9	42.6	42.4	42.2	42.0	41.8
82.5°	32.4	32.0	31.6	31.4	31.4	31.3	31.3	31.3
85°	17.1	16.8	16.5	16.3	16.2	16.1	16.0	15.9
87.5°	12.0	11.3	11.6	11.6	11.5	11.5	11.4	11.3
90°	37.2	34.9	37.2	38.3	38.3	38.3	38.3	38.3
92.5°	101.3	86.9	77.1	69.9	69.0	65.3	66.2	64.4
95°	304.4	233.5	184.7	159.1	144.0	134.8	131.3	132.4
97.5°	710.2	581.1	455.4	371.5	316.0	287.4	270.4	260.7
100°	1060.6	916.6	757.4	616.8	520.4	470.5	436.8	415.9
102.5°	1290.2	1257.6	1141.2	992.3	887.5	802.3	760.2	731.9
105°	1411.4	1542.7	1557.8	1519.5	1447.4	1375.4	1325.5	1309.2
107.5°	1324.1	1521.8	1642.6	1698.8	1707.9	1703.9	1693.9	1672.3
110°	1248.8	1456.7	1605.4	1700.7	1750.6	1772.7	1783.2	1782.0





TEST NUMBER: P331284

CATALOG NUMBER: SA2XXDIP-C290D1080U835-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	1180.0	1379.6	1538.5	1647.7	1717.2	1754.1	1773.9	1780.1
115°	1095.5	1274.4	1426.5	1546.2	1628.7	1682.1	1712.3	1722.8
117.5°	1031.8	1188.9	1326.9	1439.1	1523.2	1579.6	1611.5	1620.3
120°	1000.2	1144.2	1267.4	1373.1	1454.4	1509.0	1542.7	1554.3
122.5°	975.1	1107.1	1223.7	1319.2	1392.1	1445.8	1475.8	1485.5
125°	938.6	1058.3	1160.5	1247.6	1315.0	1359.2	1388.2	1397.5
127.5°	902.6	1010.9	1107.3	1187.7	1246.5	1287.8	1312.9	1320.4
130°	879.4	979.3	1071.1	1147.7	1204.7	1244.2	1267.4	1276.7
132.5°	857.1	949.6	1033.9	1105.9	1161.9	1201.4	1222.8	1231.1
135°	825.9	902.6	979.3	1044.3	1094.3	1132.6	1153.5	1158.2
137.5°	801.1	865.2	926.1	982.8	1028.3	1061.3	1079.7	1086.6
140°	785.3	841.1	894.5	945.6	982.8	1013.0	1030.4	1037.4
142.5°	772.3	819.7	865.7	908.4	943.7	971.2	986.7	988.1
145°	753.9	792.3	828.3	862.0	889.8	909.6	921.2	924.7
147.5°	739.8	770.0	798.1	822.7	845.7	861.5	869.4	871.5
150°	729.5	755.1	779.5	800.4	817.8	831.8	838.7	839.9
152.5°	719.3	743.0	763.7	781.8	795.5	807.6	812.7	812.9
155°	705.1	723.7	741.1	753.9	766.7	774.8	779.5	777.2
157.5°	688.6	704.2	718.8	728.8	737.9	744.6	746.7	746.7
160°	678.4	691.2	704.0	712.1	720.2	726.0	727.2	727.2
162.5°	668.2	679.1	690.0	696.3	704.4	708.4	709.5	708.6
165°	652.9	661.0	669.1	673.8	678.4	683.1	683.1	681.9
167.5°	638.2	644.5	650.1	654.3	656.3	658.9	658.7	657.3
170°	630.8	634.3	638.9	641.2	642.4	645.9	644.7	642.4
172.5°	622.4	625.0	628.7	630.1	631.3	632.9	631.7	630.3
175°	613.4	614.5	615.7	616.8	616.8	618.0	616.8	614.5
177.5°	606.9	606.9	607.8	607.8	607.8	607.8	606.9	605.0
180°	604.1	604.1	604.1	604.1	604.1	604.1	604.1	604.1

(END OF REPORT)