

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331320-927

Luminaire Tested: **SA2XXDIP-C485D925U927-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331320-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXDIP-C485D925U927-4F0-1E-UDD-F4  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 925 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4430.0 lumens  
Efficiency: N/A  
Efficacy: 99.6 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 44.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331320-927

CATALOG NUMBER: SA2XXDIP-C485D925U927-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P331320-927

CATALOG NUMBER: SA2XXDIP-C485D925U927-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	43	43	43	35				
1	95	90	86	83	85	82	79	76	66	64	62	51	50	48	38	37	36	30				
2	86	79	73	68	78	71	66	62	58	54	51	45	43	40	33	32	30	25				
3	78	69	62	56	71	63	57	52	51	46	43	40	37	34	29	27	26	21				
4	72	61	53	48	65	56	49	44	45	40	36	35	32	29	26	24	22	18				
5	66	54	46	41	59	50	43	37	40	35	31	32	28	25	24	21	19	16				
6	60	49	41	35	54	44	37	32	36	31	27	29	25	22	21	19	17	14				
7	56	44	36	31	50	40	33	28	33	28	24	26	22	19	20	17	15	12				
8	52	40	32	27	47	36	30	25	30	25	21	24	20	17	18	15	14	11				
9	48	36	29	24	43	33	27	22	27	22	19	22	18	15	17	14	12	10				
10	45	33	26	21	41	30	24	20	25	20	17	20	16	14	15	13	11	9				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	9935	9935	9935
5°	9972	9828	9887
10°	9914	9729	9778
15°	9790	9603	9593
20°	9617	9414	9402
25°	9444	9180	9180
30°	9221	8968	8889
35°	9014	8712	8584
40°	8753	8456	8292
45°	8499	8200	7996
50°	8219	7935	7654
55°	7927	7626	7344
60°	7601	7259	6991
65°	7255	6896	6575
70°	6812	6453	6146
75°	6201	5939	5795
80°	5504	5337	5058
85°	4483	4279	3835



TEST NUMBER: P331320-927

CATALOG NUMBER: SA2XXDIP-C485D925U927-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	57.9	1.3
10°-20°	162.8	3.7
20°-30°	239.3	5.4
30°-40°	278.0	6.3
40°-50°	277.7	6.3
50°-60°	242.1	5.5
60°-70°	179.0	4.0
70°-80°	101.4	2.3
80°-90°	31.0	0.7
90°-100°	164.4	3.7
100°-110°	557.8	12.6
110°-120°	592.6	13.4
120°-130°	487.8	11.0
130°-140°	391.8	8.8
140°-150°	296.0	6.7
150°-160°	208.1	4.7
160°-170°	122.5	2.8
170°-180°	39.9	0.9
0°-30°	459.9	10.4
0°-40°	737.9	16.7
0°-60°	1257.7	28.4
0°-90°	1569.1	35.4
90°-120°	1314.8	29.7
90°-150°	2490.5	56.2
90°-180°	2861.0	64.6
0°-180°	4430.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	615	615	615	615	615	
5°	615	613	606	611	610	58
15°	586	582	574	577	574	165
25°	530	525	515	516	515	244
35°	457	451	442	438	436	285
45°	372	368	359	353	350	287
55°	282	278	271	264	261	252
65°	190	186	180	175	172	188
75°	99	98	95	92	93	106
85°	24	24	23	21	21	28
90°	1	11	27	26	26	3
95°	28	68	310	117	90	29
105°	96	145	586	1047	891	102
115°	170	215	490	1012	1172	169
125°	237	281	471	819	951	211
135°	278	332	466	689	788	215
145°	318	365	463	575	629	199
155°	361	390	450	509	529	166
165°	394	406	431	457	464	111
175°	410	411	414	420	418	39
180°	411	411	411	411	411	



TEST NUMBER: P331320-927

CATALOG NUMBER: SA2XXDIP-C485D925U927-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	615.3	615.3	615.3	615.3	615.3	615.3	615.3	615.3	615.3	615.3	615.3
2.5°	618.1	617.6	617.1	616.6	616.0	615.2	614.0	612.9	611.7	610.5	611.6
5°	615.3	614.7	614.3	613.7	613.2	612.2	610.8	609.3	607.8	606.4	607.4
7.5°	609.8	609.0	608.2	607.4	606.6	605.5	604.0	602.5	601.0	599.5	600.6
10°	604.7	603.7	602.8	601.9	600.9	599.7	598.1	596.6	595.0	593.4	594.5
12.5°	597.5	596.8	595.9	595.1	594.3	593.1	591.5	589.9	588.4	586.8	587.5
15°	585.7	584.9	584.2	583.4	582.6	581.3	579.6	577.9	576.2	574.5	575.0
17.5°	570.5	569.8	569.0	568.2	567.4	566.2	564.4	562.7	560.9	559.2	559.8
20°	559.7	558.9	558.1	557.3	556.5	555.2	553.3	551.5	549.7	547.9	548.3
22.5°	548.8	547.7	546.6	545.5	544.4	543.0	541.2	539.5	537.7	536.0	536.1
25°	530.1	529.0	528.0	527.0	525.9	524.3	522.0	519.8	517.5	515.3	515.6
27.5°	508.8	507.9	506.9	506.0	505.0	503.7	501.9	500.1	498.4	496.6	496.2
30°	494.6	493.5	492.5	491.5	490.4	488.9	486.9	485.0	483.0	481.0	480.6
32.5°	479.4	478.6	477.8	476.9	476.1	474.6	472.5	470.5	468.4	466.4	465.6
35°	457.3	456.0	454.7	453.4	452.1	450.4	448.3	446.2	444.0	442.0	441.2
37.5°	432.4	431.2	430.1	428.9	427.7	426.1	424.0	421.9	419.8	417.7	416.7
40°	415.3	414.2	413.2	412.2	411.1	409.6	407.4	405.4	403.2	401.2	400.0
42.5°	398.8	397.7	396.6	395.6	394.6	393.0	390.9	388.8	386.7	384.5	383.3
45°	372.2	371.2	370.3	369.4	368.4	367.0	365.0	363.1	361.1	359.1	357.7
47.5°	345.6	344.8	343.9	343.0	342.1	340.7	338.7	336.6	334.5	332.5	331.0
50°	327.2	326.5	325.8	325.2	324.6	323.3	321.5	319.6	317.7	315.9	314.1
52.5°	309.2	308.3	307.4	306.6	305.7	304.4	302.7	301.0	299.2	297.5	296.0
55°	281.6	280.8	280.0	279.2	278.5	277.3	275.7	274.1	272.5	270.9	269.4
57.5°	253.9	253.3	252.6	252.1	251.4	250.3	248.5	246.8	245.0	243.3	241.7
60°	235.4	235.0	234.4	233.9	233.4	232.2	230.4	228.5	226.6	224.8	223.4
62.5°	217.5	216.7	215.8	214.9	214.1	213.0	211.6	210.2	208.7	207.3	206.0
65°	189.9	189.1	188.3	187.5	186.8	185.7	184.4	183.1	181.7	180.5	179.3
67.5°	161.8	161.2	160.6	159.9	159.3	158.4	157.2	156.1	154.9	153.7	152.8
70°	144.3	143.9	143.3	142.8	142.3	141.4	140.2	139.0	137.8	136.7	135.8
72.5°	126.4	125.9	125.3	124.8	124.3	123.7	122.9	122.1	121.4	120.6	119.6
75°	99.4	99.1	98.9	98.6	98.3	97.9	97.2	96.6	95.9	95.2	94.4
77.5°	75.3	74.8	74.4	73.9	73.4	73.1	72.9	72.6	72.3	72.1	71.7
80°	59.2	59.0	58.9	58.8	58.6	58.5	58.1	57.9	57.7	57.4	57.0
82.5°	44.0	44.0	44.0	44.0	43.9	43.8	43.6	43.5	43.3	43.2	42.7
85°	24.2	24.2	24.0	23.8	23.8	23.6	23.4	23.4	23.2	23.1	22.7
87.5°	8.7	9.0	9.3	9.5	9.6	9.8	10.5	11.3	12.0	12.0	11.6
90°	0.8	3.2	6.3	7.9	9.5	11.9	15.8	21.3	26.1	26.9	26.1
92.5°	9.7	13.9	19.6	23.1	28.4	35.9	53.8	78.9	101.3	102.7	86.8
95°	27.6	30.8	38.7	45.9	58.5	77.5	113.8	182.6	274.3	309.9	271.2
97.5°	45.1	49.4	57.8	68.4	83.0	104.5	150.2	246.1	398.5	529.1	555.0
100°	60.8	63.2	70.3	83.0	98.9	121.0	162.9	259.4	430.1	624.6	738.5
102.5°	75.4	77.2	84.3	97.0	113.4	135.5	174.3	260.0	418.1	627.7	806.8
105°	96.5	99.7	105.1	117.0	134.4	156.5	193.7	264.0	394.5	585.8	796.1
107.5°	119.2	121.8	127.1	138.1	155.3	177.6	213.7	275.0	382.8	541.0	726.7
110°	134.4	137.6	142.3	152.6	169.2	192.1	226.9	283.8	380.3	519.4	683.1



TEST NUMBER: P331320-927

CATALOG NUMBER: SA2XXDIP-C485D925U927-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	148.3	151.5	156.9	166.5	182.4	206.0	239.6	293.3	380.9	505.5	652.8
115°	170.0	174.0	178.7	188.1	204.0	225.3	259.4	307.5	384.2	490.2	615.1
117.5°	192.4	195.6	200.3	208.7	223.9	246.1	277.5	322.7	389.9	482.8	591.4
120°	206.4	209.5	214.3	221.3	237.2	259.4	290.2	332.9	393.7	478.3	578.8
122.5°	219.7	222.1	226.9	234.6	250.5	273.2	302.1	341.7	398.2	475.8	568.0
125°	237.2	239.6	244.3	253.8	269.6	291.8	320.2	355.8	404.8	471.2	552.6
127.5°	251.1	254.3	260.9	271.3	286.5	309.3	337.0	368.9	411.6	468.5	538.4
130°	259.4	262.4	270.4	281.5	297.3	319.4	347.1	377.2	416.7	467.2	528.9
132.5°	266.9	270.7	279.2	291.0	307.4	329.5	355.9	385.3	421.7	466.6	521.3
135°	278.3	281.5	291.0	302.8	321.0	343.1	368.4	396.1	427.7	465.6	510.7
137.5°	289.1	292.9	302.3	315.0	333.0	353.6	378.6	404.3	433.1	465.5	503.3
140°	297.3	300.5	309.9	322.6	340.0	360.5	384.2	408.8	435.6	464.9	498.9
142.5°	305.5	308.0	316.9	329.5	346.3	365.6	388.6	412.6	437.5	464.9	494.5
145°	317.8	321.0	328.9	340.8	356.6	374.0	395.3	417.5	439.6	463.3	488.6
147.5°	331.1	333.5	341.0	352.0	365.1	380.6	400.7	420.2	440.2	460.5	482.6
150°	340.0	342.3	348.6	358.9	370.8	385.0	403.2	421.4	439.6	458.6	477.5
152.5°	348.8	349.9	356.2	365.3	376.5	389.4	405.8	422.0	438.3	455.4	473.1
155°	361.3	362.1	366.9	375.6	384.2	396.1	409.6	422.9	436.4	449.9	464.9
157.5°	371.8	372.6	376.4	383.9	390.9	400.8	412.3	422.9	432.8	444.2	457.2
160°	378.7	379.5	382.6	389.0	395.3	404.0	413.5	422.9	430.9	440.4	451.5
162.5°	385.6	385.2	388.3	393.4	399.1	405.9	414.2	422.3	429.0	437.2	446.4
165°	393.7	392.9	394.5	399.3	403.2	408.0	415.1	420.6	425.3	430.9	438.0
167.5°	400.4	399.4	400.8	403.9	406.7	409.7	414.9	419.5	421.7	425.3	429.8
170°	404.8	403.2	404.0	406.4	408.0	410.4	414.3	418.3	419.9	422.2	425.3
172.5°	407.3	406.4	405.9	408.3	409.2	411.0	413.7	416.4	417.3	418.4	421.0
175°	410.4	409.6	408.8	410.4	410.4	411.1	412.7	414.3	413.5	414.3	415.1
177.5°	411.8	410.5	409.9	411.1	411.1	411.1	411.8	413.0	411.8	411.1	411.8
180°	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1



TEST NUMBER: P331320-927

CATALOG NUMBER: SA2XXDIP-C485D925U927-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	615.3	615.3	615.3	615.3	615.3	615.3	615.3	615.3
2.5°	612.7	613.7	614.7	615.2	615.0	614.7	614.6	614.3
5°	608.6	609.6	610.6	611.0	610.8	610.5	610.2	610.0
7.5°	601.7	602.7	603.8	604.1	603.9	603.6	603.2	603.0
10°	595.5	596.6	597.6	597.9	597.5	597.1	596.8	596.4
12.5°	588.3	589.0	589.7	589.9	589.6	589.4	589.1	588.7
15°	575.5	576.1	576.6	576.5	575.8	575.2	574.6	573.9
17.5°	560.4	561.0	561.7	561.6	560.9	560.4	559.8	559.1
20°	548.7	549.1	549.5	549.4	548.8	548.3	547.8	547.2
22.5°	536.1	536.2	536.3	536.2	535.9	535.6	535.3	535.0
25°	515.9	516.1	516.3	516.3	516.1	515.9	515.6	515.3
27.5°	495.8	495.4	495.0	494.6	493.9	493.3	492.7	492.0
30°	480.2	479.8	479.4	479.0	478.4	477.9	477.4	476.8
32.5°	464.9	464.2	463.5	462.9	462.3	461.8	461.3	460.7
35°	440.4	439.6	438.8	438.1	437.4	436.7	436.1	435.5
37.5°	415.7	414.8	413.8	413.0	412.3	411.7	411.1	410.5
40°	398.8	397.6	396.4	395.5	395.0	394.5	394.0	393.4
42.5°	382.0	380.7	379.4	378.4	377.6	376.9	376.2	375.4
45°	356.2	354.8	353.3	352.4	351.8	351.3	350.8	350.2
47.5°	329.5	327.9	326.4	325.3	324.5	323.8	323.0	322.2
50°	312.3	310.4	308.6	307.3	306.7	306.0	305.3	304.7
52.5°	294.5	292.9	291.4	290.2	289.3	288.4	287.6	286.7
55°	267.8	266.3	264.7	263.6	262.8	262.2	261.6	260.9
57.5°	240.2	238.6	237.1	236.1	235.5	235.0	234.6	234.0
60°	221.9	220.5	219.0	218.1	217.7	217.3	216.9	216.5
62.5°	204.6	203.3	201.9	201.1	200.5	200.0	199.6	199.0
65°	178.1	176.9	175.7	174.8	174.1	173.5	172.9	172.1
67.5°	151.9	150.9	150.0	149.3	148.8	148.2	147.7	147.2
70°	134.8	133.9	133.0	132.3	131.7	131.2	130.7	130.2
72.5°	118.7	117.8	116.9	116.2	115.8	115.3	114.9	114.5
75°	93.6	92.9	92.1	91.8	92.1	92.4	92.6	92.9
77.5°	71.3	70.9	70.5	70.1	69.7	69.4	69.0	68.6
80°	56.6	56.2	55.8	55.5	55.2	55.0	54.7	54.4
82.5°	42.2	41.7	41.2	40.9	40.9	40.8	40.7	40.7
85°	22.3	21.9	21.5	21.2	21.1	21.0	20.8	20.7
87.5°	11.1	10.5	10.5	10.4	10.3	10.1	10.1	10.0
90°	25.3	23.7	25.3	26.1	26.1	26.1	26.1	26.1
92.5°	68.9	59.2	52.5	47.6	47.0	44.4	45.1	43.8
95°	207.2	158.9	125.7	108.3	98.1	91.7	89.4	90.2
97.5°	483.4	395.5	309.9	252.9	215.1	195.6	184.0	177.4
100°	721.8	623.8	515.5	419.9	354.2	320.2	297.3	283.0
102.5°	878.1	856.0	776.7	675.3	604.0	546.0	517.4	498.1
105°	960.6	1050.0	1060.3	1034.1	985.1	936.1	902.1	891.0
107.5°	901.2	1035.7	1117.9	1156.2	1162.4	1159.7	1152.9	1138.2
110°	849.9	991.4	1092.7	1157.5	1191.4	1206.5	1213.6	1212.8





TEST NUMBER: P331320-927

CATALOG NUMBER: SA2XXDIP-C485D925U927-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	803.1	939.0	1047.1	1121.4	1168.7	1193.8	1207.3	1211.6
115°	745.5	867.3	970.9	1052.3	1108.4	1144.8	1165.4	1172.5
117.5°	702.2	809.1	903.0	979.5	1036.6	1075.1	1096.8	1102.7
120°	680.7	778.8	862.5	934.5	989.8	1027.0	1050.0	1057.9
122.5°	663.6	753.4	832.8	897.9	947.5	984.0	1004.4	1011.1
125°	638.8	720.3	789.8	849.1	895.0	925.0	944.8	951.1
127.5°	614.3	688.0	753.6	808.3	848.3	876.5	893.6	898.7
130°	598.5	666.5	729.0	781.2	819.9	846.8	862.5	868.9
132.5°	583.3	646.3	703.6	752.7	790.8	817.7	832.2	837.9
135°	562.1	614.3	666.5	710.7	744.7	770.9	785.1	788.2
137.5°	545.2	588.8	630.3	668.8	699.9	722.3	734.8	739.6
140°	534.5	572.4	608.8	643.6	668.8	689.4	701.3	706.0
142.5°	525.6	557.9	589.1	618.3	642.3	661.0	671.5	672.5
145°	513.1	539.2	563.7	586.6	605.6	619.1	626.9	629.3
147.5°	503.4	524.0	543.1	559.9	575.6	586.3	591.7	593.1
150°	496.5	513.9	530.5	544.7	556.6	566.1	570.8	571.6
152.5°	489.6	505.6	519.8	532.1	541.4	549.6	553.1	553.3
155°	479.9	492.6	504.4	513.1	521.8	527.4	530.5	528.9
157.5°	468.7	479.3	489.3	496.1	502.2	506.8	508.2	508.2
160°	461.7	470.4	479.1	484.7	490.2	494.2	495.0	495.0
162.5°	454.8	462.2	469.6	473.9	479.4	482.1	482.9	482.3
165°	444.3	449.9	455.4	458.6	461.7	464.9	464.9	464.1
167.5°	434.4	438.6	442.4	445.3	446.7	448.5	448.3	447.3
170°	429.3	431.7	434.8	436.4	437.2	439.6	438.8	437.2
172.5°	423.6	425.3	427.9	428.8	429.6	430.7	429.9	429.0
175°	417.5	418.3	419.1	419.9	419.9	420.6	419.9	418.3
177.5°	413.0	413.0	413.7	413.7	413.7	413.7	413.0	411.8
180°	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1

(END OF REPORT)