

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331264

Luminaire Tested: **SA2XXDIP-C290D725U835-4F0-1E-UDD-F**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331264
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C290D725U835-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 725 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4101.5 lumens
Efficiency: N/A
Efficacy: 131.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 31.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331264
CATALOG NUMBER: SA2XXDIP-C290D725U835-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331264

CATALOG NUMBER: SA2XXDIP-C290D725U835-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	37	37	37	29
1	93	89	85	82	83	80	77	74	63	61	59	47	46	45	33	32	31	25
2	85	78	72	67	76	70	65	61	55	52	49	41	39	37	29	28	26	21
3	77	68	61	55	69	61	55	51	48	44	41	37	34	31	26	24	22	18
4	71	60	53	47	63	54	48	43	43	38	35	33	29	27	23	21	19	15
5	65	54	46	40	58	48	42	36	38	34	30	29	26	23	21	18	17	13
6	60	48	40	34	53	43	36	32	34	30	26	26	23	20	19	16	15	11
7	55	43	35	30	49	39	32	28	31	26	23	24	20	18	17	15	13	10
8	51	39	32	26	45	35	29	24	28	23	20	22	18	16	16	13	12	9
9	47	35	28	23	42	32	26	21	26	21	18	20	17	14	14	12	11	8
10	44	32	25	21	39	29	23	19	24	19	16	18	15	13	13	11	10	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7627	7627	7627
5°	7656	7546	7592
10°	7612	7470	7507
15°	7517	7373	7366
20°	7383	7228	7220
25°	7251	7049	7049
30°	7081	6885	6825
35°	6922	6688	6589
40°	6721	6492	6367
45°	6524	6295	6140
50°	6310	6094	5878
55°	6086	5858	5638
60°	5838	5574	5370
65°	5570	5295	5051
70°	5231	4952	4716
75°	4760	4560	4448
80°	4221	4100	3887
85°	3446	3279	2946



TEST NUMBER: P331264

CATALOG NUMBER: SA2XXDIP-C290D725U835-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.4	1.1
10°-20°	125.0	3.0
20°-30°	183.7	4.5
30°-40°	213.4	5.2
40°-50°	213.2	5.2
50°-60°	185.9	4.5
60°-70°	137.5	3.4
70°-80°	77.9	1.9
80°-90°	23.4	0.6
90°-100°	33.0	0.8
100°-110°	120.9	2.9
110°-120°	323.3	7.9
120°-130°	533.6	13.0
130°-140°	567.5	13.8
140°-150°	527.5	12.9
150°-160°	424.1	10.3
160°-170°	273.3	6.7
170°-180°	94.1	2.3
0°-30°	353.2	8.6
0°-40°	566.6	13.8
0°-60°	965.7	23.5
0°-90°	1204.4	29.4
90°-120°	477.2	11.6
90°-150°	2105.7	51.3
90°-180°	2897.0	70.6
0°-180°	4101.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	472	472	472	472	472	
5°	472	470	466	469	468	45
15°	450	447	441	443	441	127
25°	407	403	396	396	396	187
35°	351	346	339	337	334	219
45°	286	282	276	271	269	220
55°	216	213	208	203	200	193
65°	146	143	139	135	132	144
75°	76	75	73	71	71	82
85°	19	18	18	16	16	21
90°	1	8	14	18	19	3
95°	46	24	28	31	31	57
105°	218	227	44	51	54	232
115°	411	424	441	126	59	405
125°	582	591	604	609	612	518
135°	720	731	738	744	743	556
145°	835	835	846	851	848	522
155°	919	914	921	925	920	423
165°	969	965	966	971	966	274
175°	991	986	987	992	985	94
180°	989	989	989	989	989	



TEST NUMBER: P331264

CATALOG NUMBER: SA2XXDIP-C290D725U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	472.4	472.4	472.4	472.4	472.4	472.4	472.4	472.4	472.4	472.4	472.4
2.5°	474.6	474.2	473.8	473.4	473.0	472.4	471.5	470.6	469.7	468.8	469.6
5°	472.4	472.0	471.6	471.2	470.8	470.1	469.0	467.9	466.7	465.6	466.4
7.5°	468.3	467.6	467.0	466.4	465.8	464.9	463.8	462.6	461.5	460.4	461.2
10°	464.3	463.6	462.9	462.2	461.4	460.5	459.3	458.1	456.9	455.6	456.4
12.5°	458.8	458.2	457.6	456.9	456.3	455.4	454.2	453.0	451.8	450.6	451.1
15°	449.7	449.1	448.5	447.9	447.3	446.4	445.0	443.7	442.4	441.1	441.5
17.5°	438.1	437.5	436.9	436.3	435.7	434.7	433.4	432.0	430.7	429.4	429.8
20°	429.7	429.1	428.5	427.9	427.3	426.3	424.9	423.5	422.1	420.7	421.0
22.5°	421.4	420.5	419.7	418.8	418.0	416.9	415.6	414.2	412.9	411.6	411.6
25°	407.0	406.2	405.4	404.6	403.8	402.5	400.8	399.1	397.4	395.7	395.9
27.5°	390.7	390.0	389.2	388.5	387.8	386.7	385.4	384.0	382.7	381.3	381.0
30°	379.8	379.0	378.2	377.4	376.5	375.4	373.9	372.4	370.8	369.3	369.0
32.5°	368.1	367.5	366.9	366.2	365.6	364.4	362.8	361.3	359.7	358.1	357.5
35°	351.2	350.1	349.1	348.1	347.1	345.8	344.2	342.6	341.0	339.3	338.7
37.5°	332.0	331.1	330.2	329.3	328.4	327.2	325.6	324.0	322.3	320.7	320.0
40°	318.9	318.1	317.3	316.5	315.7	314.5	312.8	311.2	309.6	308.0	307.1
42.5°	306.2	305.4	304.6	303.8	303.0	301.7	300.1	298.5	296.9	295.3	294.3
45°	285.7	285.0	284.3	283.6	282.9	281.8	280.3	278.8	277.3	275.7	274.6
47.5°	265.4	264.7	264.1	263.4	262.7	261.6	260.0	258.5	256.9	255.3	254.1
50°	251.2	250.7	250.2	249.7	249.2	248.2	246.8	245.4	244.0	242.6	241.2
52.5°	237.4	236.7	236.1	235.4	234.7	233.7	232.4	231.1	229.7	228.4	227.2
55°	216.2	215.6	215.0	214.4	213.8	212.9	211.7	210.5	209.3	208.1	206.8
57.5°	195.0	194.5	194.0	193.5	193.0	192.1	190.8	189.5	188.1	186.8	185.6
60°	180.8	180.4	180.0	179.6	179.2	178.3	176.9	175.5	174.0	172.6	171.5
62.5°	167.0	166.3	165.7	165.1	164.4	163.5	162.4	161.4	160.3	159.2	158.1
65°	145.8	145.2	144.6	144.0	143.4	142.6	141.6	140.6	139.6	138.6	137.6
67.5°	124.3	123.8	123.3	122.8	122.4	121.7	120.7	119.8	118.9	118.0	117.3
70°	110.8	110.4	110.0	109.6	109.2	108.6	107.7	106.8	105.8	104.9	104.2
72.5°	97.0	96.6	96.2	95.8	95.4	94.9	94.3	93.8	93.2	92.6	91.9
75°	76.3	76.1	75.9	75.7	75.5	75.2	74.7	74.1	73.6	73.1	72.5
77.5°	57.8	57.4	57.1	56.8	56.4	56.1	55.9	55.7	55.5	55.3	55.0
80°	45.4	45.3	45.2	45.1	45.0	44.9	44.7	44.5	44.3	44.1	43.8
82.5°	33.8	33.8	33.8	33.7	33.7	33.6	33.5	33.4	33.3	33.2	32.8
85°	18.6	18.5	18.4	18.3	18.2	18.1	18.0	17.9	17.8	17.7	17.4
87.5°	6.7	6.9	7.1	7.2	7.4	7.6	7.7	7.8	7.9	7.9	7.9
90°	0.7	2.5	4.2	6.0	7.7	9.2	10.5	11.8	13.0	14.3	15.1
92.5°	14.4	14.3	14.1	14.0	13.8	14.1	14.7	15.3	16.0	16.6	17.0
95°	46.5	41.3	36.0	30.8	25.5	23.4	24.6	25.7	26.8	27.9	28.7
97.5°	92.3	77.5	62.7	47.9	33.1	27.0	29.6	32.2	34.8	37.3	38.0
100°	126.6	104.8	83.1	61.3	39.5	30.0	32.7	35.4	38.1	40.8	42.0
102.5°	164.4	159.8	155.2	150.6	145.9	132.3	109.7	87.1	64.5	41.9	43.6
105°	217.5	222.2	227.0	231.8	236.5	217.2	173.8	130.4	87.0	43.6	45.4
107.5°	278.0	281.8	285.7	289.5	293.4	269.3	217.2	165.2	113.1	61.1	59.3
110°	316.9	320.2	323.6	326.9	330.2	308.9	263.0	217.1	171.1	125.2	109.3



TEST NUMBER: P331264

CATALOG NUMBER: SA2XXDIP-C290D725U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	353.5	356.5	359.4	362.4	365.3	361.1	349.8	338.4	327.1	315.7	257.8
115°	411.3	414.0	416.7	419.4	422.1	425.5	429.4	433.4	437.4	441.4	367.8
117.5°	463.0	466.0	469.0	472.0	475.0	477.9	480.7	483.4	486.1	488.9	471.1
120°	500.7	503.1	505.5	507.9	510.3	512.9	515.8	518.6	521.5	524.3	526.2
122.5°	532.8	535.3	537.8	540.3	542.8	545.6	548.8	551.9	555.0	558.1	559.2
125°	581.6	583.6	585.7	587.8	589.8	592.4	595.4	598.4	601.4	604.5	605.6
127.5°	625.8	628.1	630.4	632.6	634.9	637.2	639.5	641.7	644.0	646.2	647.9
130°	653.8	656.4	658.9	661.4	664.0	666.1	667.9	669.6	671.4	673.1	674.9
132.5°	682.4	684.6	686.8	688.9	691.1	693.0	694.8	696.5	698.3	700.0	701.5
135°	719.6	722.2	724.7	727.3	729.8	731.8	733.2	734.6	736.1	737.5	739.1
137.5°	757.3	759.0	760.8	762.6	764.4	766.1	767.7	769.3	770.9	772.6	774.1
140°	781.9	783.1	784.4	785.7	786.9	788.5	790.2	792.0	793.7	795.5	796.9
142.5°	802.5	803.6	804.8	805.9	807.0	808.6	810.6	812.6	814.6	816.6	817.9
145°	834.8	834.6	834.5	834.3	834.2	835.4	838.1	840.8	843.5	846.2	847.4
147.5°	863.0	862.4	861.8	861.2	860.6	861.6	864.3	866.9	869.6	872.3	873.1
150°	881.3	880.2	879.1	878.0	876.8	877.6	880.1	882.6	885.2	887.7	888.7
152.5°	896.7	895.5	894.3	893.0	891.8	892.4	894.8	897.2	899.6	902.0	903.0
155°	919.2	917.8	916.3	914.9	913.5	913.7	915.6	917.5	919.4	921.3	922.3
157.5°	936.8	935.6	934.4	933.2	932.0	932.0	933.4	934.7	936.0	937.4	938.5
160°	947.1	946.1	945.2	944.2	943.3	943.3	944.2	945.2	946.1	947.1	948.1
162.5°	956.3	955.3	954.4	953.4	952.4	952.4	953.2	954.0	954.9	955.7	956.8
165°	968.6	967.6	966.7	965.7	964.7	964.5	965.0	965.5	965.9	966.4	967.5
167.5°	977.7	976.8	975.8	974.9	973.9	973.6	974.1	974.5	975.0	975.4	976.5
170°	982.9	981.9	981.0	980.0	979.1	978.7	979.1	979.4	979.7	980.0	981.1
172.5°	986.3	985.3	984.4	983.4	982.5	982.2	982.5	982.8	983.1	983.4	984.6
175°	990.7	989.6	988.5	987.4	986.3	985.9	986.2	986.5	986.8	987.2	988.3
177.5°	991.5	990.6	989.7	988.8	987.9	987.5	987.6	987.8	987.9	988.0	988.9
180°	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6



TEST NUMBER: P331264

CATALOG NUMBER: SA2XXDIP-C290D725U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	472.4	472.4	472.4	472.4	472.4	472.4	472.4	472.4
2.5°	470.4	471.2	472.0	472.4	472.2	472.0	471.9	471.7
5°	467.3	468.1	468.9	469.2	469.0	468.8	468.6	468.4
7.5°	462.0	462.8	463.6	463.9	463.7	463.4	463.2	463.0
10°	457.3	458.1	458.9	459.1	458.8	458.5	458.2	457.9
12.5°	451.7	452.2	452.8	453.0	452.8	452.5	452.3	452.1
15°	441.9	442.3	442.7	442.7	442.2	441.7	441.2	440.7
17.5°	430.3	430.8	431.2	431.2	430.7	430.3	429.8	429.3
20°	421.3	421.6	421.9	421.8	421.4	421.0	420.6	420.2
22.5°	411.7	411.8	411.8	411.7	411.5	411.2	411.0	410.8
25°	396.1	396.3	396.5	396.5	396.3	396.1	395.9	395.7
27.5°	380.7	380.4	380.1	379.7	379.2	378.7	378.3	377.8
30°	368.7	368.4	368.1	367.8	367.4	367.0	366.6	366.1
32.5°	357.0	356.4	355.9	355.4	355.0	354.6	354.2	353.8
35°	338.1	337.5	336.9	336.4	335.9	335.4	334.9	334.3
37.5°	319.2	318.5	317.7	317.1	316.6	316.1	315.7	315.2
40°	306.2	305.3	304.4	303.7	303.3	302.9	302.5	302.1
42.5°	293.3	292.3	291.3	290.5	290.0	289.4	288.9	288.3
45°	273.5	272.4	271.3	270.5	270.1	269.7	269.3	268.9
47.5°	253.0	251.8	250.6	249.7	249.2	248.6	248.0	247.4
50°	239.8	238.3	236.9	236.0	235.5	235.0	234.5	234.0
52.5°	226.1	224.9	223.7	222.8	222.1	221.5	220.8	220.1
55°	205.6	204.4	203.2	202.4	201.9	201.3	200.8	200.3
57.5°	184.4	183.2	182.0	181.2	180.9	180.5	180.1	179.7
60°	170.4	169.3	168.2	167.5	167.2	166.9	166.6	166.3
62.5°	157.1	156.1	155.1	154.4	154.0	153.6	153.2	152.8
65°	136.7	135.8	134.9	134.2	133.7	133.2	132.7	132.2
67.5°	116.6	115.9	115.2	114.6	114.2	113.8	113.4	113.0
70°	103.5	102.8	102.1	101.6	101.2	100.7	100.3	99.9
72.5°	91.2	90.5	89.8	89.2	88.9	88.6	88.3	87.9
75°	71.9	71.3	70.7	70.5	70.7	70.9	71.1	71.3
77.5°	54.7	54.4	54.1	53.8	53.5	53.3	53.0	52.7
80°	43.5	43.2	42.9	42.6	42.4	42.2	42.0	41.8
82.5°	32.4	32.0	31.6	31.4	31.4	31.3	31.3	31.3
85°	17.1	16.8	16.5	16.3	16.2	16.1	16.0	15.9
87.5°	7.8	7.7	7.6	7.6	7.5	7.5	7.5	7.5
90°	15.9	16.7	17.5	18.0	18.4	18.7	19.0	19.3
92.5°	17.4	17.8	18.2	18.6	18.7	18.9	19.1	19.3
95°	29.5	30.3	31.1	31.4	31.2	31.1	30.9	30.8
97.5°	38.6	39.2	39.9	40.3	40.5	40.7	40.9	41.1
100°	43.3	44.6	45.9	46.7	47.0	47.3	47.6	47.9
102.5°	45.2	46.9	48.5	49.6	50.0	50.5	50.9	51.4
105°	47.1	48.9	50.6	51.8	52.5	53.1	53.7	54.4
107.5°	57.5	55.7	54.0	53.4	54.0	54.7	55.3	55.9
110°	93.4	77.5	61.6	54.0	54.6	55.2	55.9	56.5



TEST NUMBER: P331264

CATALOG NUMBER: SA2XXDIP-C290D725U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	199.8	141.8	83.8	55.0	55.6	56.1	56.6	57.1
115°	294.2	220.6	147.0	104.4	93.0	81.5	70.1	58.7
117.5°	453.3	435.4	417.6	389.9	352.3	314.7	277.1	239.5
120°	528.2	530.1	532.0	522.2	500.7	479.3	457.8	436.4
122.5°	560.4	561.5	562.7	561.2	557.0	552.8	548.7	544.5
125°	606.7	607.8	608.9	609.7	610.2	610.7	611.1	611.6
127.5°	649.5	651.1	652.7	653.6	653.7	653.8	653.9	654.0
130°	676.6	678.4	680.1	680.9	680.8	680.6	680.4	680.3
132.5°	703.0	704.5	706.0	706.7	706.5	706.4	706.2	706.0
135°	740.7	742.3	743.9	744.5	744.2	743.9	743.5	743.2
137.5°	775.7	777.2	778.8	779.3	778.8	778.2	777.7	777.1
140°	798.3	799.7	801.2	801.5	800.7	799.9	799.1	798.3
142.5°	819.2	820.5	821.8	822.1	821.3	820.5	819.7	818.9
145°	848.5	849.6	850.7	850.8	850.1	849.3	848.5	847.7
147.5°	873.9	874.8	875.6	875.7	875.0	874.3	873.7	873.0
150°	889.6	890.6	891.5	891.6	890.8	890.0	889.2	888.4
152.5°	903.9	904.9	905.9	905.8	904.8	903.7	902.7	901.6
155°	923.3	924.2	925.2	925.0	923.7	922.5	921.2	919.9
157.5°	939.5	940.6	941.7	941.6	940.4	939.1	937.9	936.7
160°	949.0	950.0	950.9	950.8	949.7	948.6	947.5	946.4
162.5°	957.8	958.9	960.0	959.9	958.5	957.1	955.8	954.4
165°	968.6	969.8	970.9	970.9	969.8	968.6	967.5	966.4
167.5°	977.7	978.8	979.9	979.7	978.3	976.9	975.4	974.0
170°	982.2	983.3	984.5	984.3	982.9	981.4	980.0	978.6
172.5°	985.7	986.8	987.9	987.7	986.3	984.9	983.4	982.0
175°	989.4	990.5	991.6	991.4	989.8	988.2	986.6	985.0
177.5°	989.8	990.7	991.6	991.5	990.3	989.2	988.0	986.9
180°	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6

(END OF REPORT)