

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331358-927

Luminaire Tested: **SA2XXDIP-C675D925U927-4F0-1E-UDD-A1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331358-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C675D925U927-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 925 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4944.7 lumens
Efficiency: N/A
Efficacy: 95.1 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 52
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331358-927

CATALOG NUMBER: SA2XXDIP-C675D925U927-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331358-927

CATALOG NUMBER: SA2XXDIP-C675D925U927-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	53	53	53	47
1	98	93	90	86	90	86	83	80	72	70	68	60	58	57	48	47	46	40
2	89	82	76	71	82	76	71	66	64	60	57	53	50	48	43	41	39	35
3	82	73	65	60	75	67	61	56	57	52	48	47	44	41	38	36	34	30
4	75	64	57	51	69	60	53	48	51	46	42	42	39	36	34	32	30	26
5	69	58	50	44	63	53	47	41	46	40	36	38	34	31	31	28	26	23
6	64	52	44	38	58	48	41	36	41	36	32	35	31	27	29	26	23	20
7	59	47	39	34	54	44	37	32	37	32	28	32	28	24	26	23	21	18
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19	16
9	51	39	32	27	47	36	30	25	31	26	23	27	23	20	22	19	17	15
10	48	36	29	24	44	34	27	23	29	24	20	25	21	18	21	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	16990	16990	16990	16990
5°	19047	17099	15152	17099
10°	21827	16959	13114	16959
15°	24145	16649	11587	16649
20°	23778	16314	10562	16314
25°	21440	15871	9912	15871
30°	17717	15163	9439	15163
35°	12912	14420	9102	14420
40°	10313	13544	8916	13544
45°	9012	12529	8661	12529
50°	8470	11549	8493	11549
55°	7809	10553	8265	10553
60°	7156	9494	7915	9494
65°	6518	8542	7568	8542
70°	5915	7619	7062	7619
75°	5246	6581	6257	6581
80°	4519	5449	5040	5449
85°	4057	4057	3001	4057



TEST NUMBER: P331358-927

CATALOG NUMBER: SA2XXDIP-C675D925U927-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.2	2.0
10°-20°	291.3	5.9
20°-30°	422.8	8.6
30°-40°	446.2	9.0
40°-50°	395.0	8.0
50°-60°	315.3	6.4
60°-70°	214.3	4.3
70°-80°	109.9	2.2
80°-90°	30.2	0.6
90°-100°	59.4	1.2
100°-110°	184.4	3.7
110°-120°	315.1	6.4
120°-130°	414.4	8.4
130°-140°	465.2	9.4
140°-150°	456.1	9.2
150°-160°	382.5	7.7
160°-170°	253.7	5.1
170°-180°	88.7	1.8
0°-30°	814.3	16.5
0°-40°	1260.5	25.5
0°-60°	1970.8	39.9
0°-90°	2325.2	47.0
90°-120°	558.9	11.3
90°-150°	1894.5	38.3
90°-180°	2620.0	53.0
0°-180°	4944.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1052	1052	1052	1052	1052	
5°	1175	1055	935	1055	1175	117
15°	1444	996	693	996	1444	399
25°	1204	891	556	891	1204	544
35°	655	732	462	732	655	426
45°	395	549	379	549	395	310
55°	277	375	294	375	277	249
65°	171	224	198	224	171	170
75°	84	106	100	106	84	90
85°	22	22	16	22	22	25
90°	27	1	27	1	27	13
95°	49	41	49	41	49	55
105°	176	170	176	170	176	185
115°	316	316	316	316	316	312
125°	462	460	462	460	462	412
135°	602	595	602	595	602	464
145°	730	722	730	722	730	456
155°	832	826	832	826	832	383
165°	900	899	900	899	900	254
175°	932	935	932	935	932	89
180°	937	937	937	937	937	



TEST NUMBER: P331358-927

CATALOG NUMBER: SA2XXDIP-C675D925U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3
2.5°	1100.7	1101.1	1101.8	1096.5	1095.9	1095.9	1091.4	1087.5	1083.0	1076.8	1077.4
5°	1175.2	1179.6	1181.2	1176.4	1169.1	1168.3	1161.4	1150.1	1139.6	1131.1	1125.1
7.5°	1264.0	1265.7	1261.8	1255.4	1250.0	1240.3	1227.5	1215.0	1197.4	1181.3	1169.3
10°	1331.3	1333.7	1326.8	1317.6	1309.9	1298.5	1279.9	1260.9	1237.9	1215.6	1197.8
12.5°	1382.4	1388.4	1379.6	1378.3	1365.2	1349.6	1327.5	1317.9	1285.4	1254.4	1235.3
15°	1444.5	1444.1	1444.9	1437.3	1427.5	1425.1	1401.6	1376.2	1330.5	1312.2	1280.7
17.5°	1426.6	1432.7	1435.5	1435.4	1435.2	1433.7	1426.2	1410.1	1387.2	1357.6	1321.2
20°	1383.9	1391.9	1393.1	1402.5	1407.7	1414.6	1417.4	1412.9	1398.8	1374.1	1342.6
22.5°	1317.9	1320.1	1323.9	1338.4	1349.8	1367.0	1376.0	1391.0	1385.5	1373.5	1347.1
25°	1203.5	1199.4	1213.6	1220.8	1247.1	1274.6	1294.5	1316.3	1335.7	1347.4	1339.7
27.5°	1066.1	1060.1	1081.2	1100.6	1122.0	1151.8	1182.6	1219.1	1249.4	1287.4	1300.4
30°	950.3	953.9	974.2	994.8	1027.1	1069.2	1104.0	1144.1	1187.3	1229.8	1259.3
32.5°	825.5	839.5	852.2	883.8	912.3	959.3	1010.2	1060.3	1114.2	1162.4	1208.2
35°	655.1	671.3	689.1	712.2	752.2	798.7	848.4	915.9	989.6	1055.5	1109.7
37.5°	551.4	548.8	559.0	575.7	608.2	645.6	702.9	769.7	856.3	933.7	1010.2
40°	489.3	487.7	495.0	510.3	535.0	562.5	612.7	671.3	751.8	846.4	937.4
42.5°	446.6	447.6	451.6	462.5	479.3	502.0	539.6	589.5	663.1	752.3	850.0
45°	394.7	397.5	402.0	407.3	416.9	435.5	456.5	492.2	550.4	624.8	721.0
47.5°	357.4	357.4	361.9	366.5	372.3	382.8	400.0	422.2	463.3	523.9	606.7
50°	337.2	334.5	337.7	341.3	347.4	354.7	366.0	387.0	414.5	463.4	532.6
52.5°	312.7	312.8	315.7	317.0	322.5	329.7	340.1	354.7	379.5	417.8	474.7
55°	277.4	279.4	281.1	283.4	288.4	293.6	301.7	311.4	330.8	359.5	401.6
57.5°	244.2	244.9	246.5	251.1	254.2	259.0	266.7	275.5	288.2	309.4	341.0
60°	221.6	221.6	224.8	226.9	230.9	235.8	241.9	250.3	261.7	279.0	304.5
62.5°	200.9	200.6	201.8	205.2	208.3	212.8	218.9	226.1	236.7	252.2	273.1
65°	170.6	169.8	172.3	173.1	176.3	180.8	185.6	193.3	201.8	213.1	231.7
67.5°	141.6	142.5	143.8	145.4	147.1	151.8	155.0	160.5	167.6	177.1	189.6
70°	125.3	125.3	125.3	126.6	129.0	131.4	134.7	139.1	146.0	154.1	165.4
72.5°	107.3	108.5	109.8	109.1	112.2	113.6	117.5	120.0	126.6	131.7	141.8
75°	84.1	84.1	84.1	86.1	87.4	88.6	91.0	93.4	96.6	103.1	108.4
77.5°	62.7	62.6	63.0	63.5	64.8	66.2	66.9	69.2	72.2	75.1	79.6
80°	48.6	49.4	49.7	50.5	50.5	51.3	51.7	54.6	56.6	58.6	61.5
82.5°	37.5	37.7	37.8	37.9	38.3	38.7	39.8	40.7	41.4	43.1	45.3
85°	21.9	21.5	21.5	22.3	21.9	21.9	22.7	23.4	23.4	23.8	25.0
87.5°	13.8	13.8	14.0	13.7	13.6	14.0	14.0	13.8	14.2	14.6	14.2
90°	26.9	26.7	26.5	26.4	26.1	26.3	26.6	26.9	27.3	27.6	23.8
92.5°	25.6	25.6	25.5	25.5	25.5	25.4	25.3	25.3	25.2	25.1	24.2
95°	49.0	49.4	49.7	50.1	50.4	50.6	50.6	50.6	50.6	50.6	50.2
97.5°	84.9	84.9	85.0	85.0	85.1	85.1	85.1	85.1	85.1	85.1	84.4
100°	108.3	108.4	108.7	108.8	109.0	109.1	109.1	109.1	109.1	109.1	108.6
102.5°	134.9	135.1	135.2	135.4	135.5	135.6	135.5	135.3	135.1	135.1	134.4
105°	175.5	175.5	175.5	175.5	175.5	175.3	175.0	174.6	174.3	173.9	173.6
107.5°	213.7	214.6	215.4	216.2	217.0	217.3	217.2	217.1	216.9	216.7	216.7
110°	243.5	244.0	244.5	245.1	245.6	245.9	245.9	245.9	245.9	245.9	245.9



TEST NUMBER: P331358-927

CATALOG NUMBER: SA2XXDIP-C675D925U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	272.0	272.4	272.7	273.1	273.5	273.9	274.3	274.7	275.2	275.6	275.8
115°	316.2	316.7	317.3	317.8	318.3	318.7	318.9	319.0	319.2	319.4	319.7
117.5°	358.5	358.9	359.5	360.0	360.5	361.0	361.5	361.9	362.3	362.7	363.7
120°	388.2	388.7	389.2	389.8	390.3	390.5	390.5	390.5	390.5	390.5	392.0
122.5°	417.2	417.6	418.0	418.4	418.8	419.2	419.6	420.0	420.5	420.9	421.9
125°	461.7	461.8	462.0	462.2	462.4	462.7	463.3	463.8	464.3	464.9	465.4
127.5°	502.2	502.7	503.3	503.8	504.4	505.0	505.6	506.3	506.9	507.6	508.2
130°	531.2	532.0	532.7	533.4	534.1	534.6	535.0	535.3	535.7	536.0	536.4
132.5°	559.1	559.7	560.2	560.8	561.3	562.0	562.8	563.6	564.4	565.1	565.0
135°	602.4	602.9	603.5	604.0	604.5	604.8	605.1	605.2	605.4	605.5	605.2
137.5°	641.6	642.3	643.0	643.7	644.4	644.8	645.0	645.2	645.3	645.4	645.0
140°	668.8	669.6	670.2	670.9	671.6	672.0	672.0	672.0	672.0	672.0	671.1
142.5°	693.5	694.2	694.9	695.6	696.3	696.6	696.4	696.3	696.2	696.0	695.4
145°	730.5	731.2	731.9	732.6	733.3	733.6	733.4	733.2	733.0	732.8	731.8
147.5°	763.5	764.2	764.9	765.6	766.2	766.4	766.0	765.6	765.2	764.8	764.1
150°	785.1	785.5	786.1	786.6	787.1	787.1	786.6	786.1	785.5	785.1	784.3
152.5°	805.3	806.0	806.6	807.2	807.9	807.9	807.2	806.6	806.0	805.3	804.4
155°	832.4	833.0	833.5	834.0	834.6	834.4	833.5	832.7	831.8	830.8	830.4
157.5°	855.9	856.7	857.5	858.4	859.2	859.0	857.9	856.7	855.5	854.3	854.0
160°	870.4	871.1	871.8	872.5	873.2	873.1	872.0	870.9	869.9	868.8	868.6
162.5°	883.0	883.9	884.7	885.6	886.5	886.2	885.0	883.8	882.6	881.5	881.3
165°	899.7	900.6	901.4	902.3	903.2	903.0	901.7	900.6	899.3	898.1	898.1
167.5°	913.2	914.2	915.0	916.0	916.9	916.7	915.5	914.3	913.1	911.8	911.9
170°	920.2	921.2	922.3	923.4	924.4	924.3	923.1	921.9	920.7	919.4	919.6
172.5°	925.9	926.9	928.0	929.1	930.1	930.0	928.8	927.6	926.4	925.1	925.3
175°	932.1	933.1	934.1	935.3	936.3	936.2	934.9	933.7	932.5	931.3	931.6
177.5°	934.9	935.7	936.6	937.5	938.3	938.3	937.5	936.6	935.7	934.9	935.2
180°	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8



TEST NUMBER: P331358-927

CATALOG NUMBER: SA2XXDIP-C675D925U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3
2.5°	1079.7	1077.1	1075.5	1069.7	1064.5	1059.4	1057.7	1058.4	1051.3	1044.5	1041.6
5°	1121.8	1113.7	1106.0	1095.1	1082.2	1068.0	1060.7	1055.0	1040.9	1025.6	1016.7
7.5°	1159.5	1148.0	1133.1	1112.5	1093.8	1071.5	1057.3	1044.8	1024.1	1002.4	989.1
10°	1182.5	1166.6	1147.6	1122.6	1099.5	1072.5	1053.4	1034.4	1010.2	984.3	968.1
12.5°	1202.2	1180.9	1162.2	1130.0	1102.8	1068.9	1046.3	1019.5	994.0	963.3	947.5
15°	1249.2	1210.0	1174.3	1138.0	1104.4	1057.1	1032.1	996.0	962.4	924.5	906.3
17.5°	1285.5	1241.4	1185.3	1139.1	1099.9	1047.6	1010.7	967.7	928.0	884.5	859.8
20°	1306.2	1255.6	1195.4	1140.4	1093.4	1033.6	993.6	949.5	903.0	854.1	827.4
22.5°	1318.5	1265.4	1205.8	1135.5	1080.5	1022.3	971.9	923.6	876.5	823.7	795.7
25°	1322.4	1273.8	1210.8	1131.5	1064.4	998.5	937.8	890.9	833.9	784.5	743.7
27.5°	1303.1	1268.4	1207.7	1123.9	1045.7	968.6	901.0	847.9	787.7	734.1	693.1
30°	1279.5	1259.3	1200.2	1116.1	1030.8	947.9	873.5	813.3	753.4	699.2	657.1
32.5°	1242.9	1238.6	1186.7	1105.1	1014.9	921.7	844.7	783.8	717.5	664.2	624.2
35°	1171.2	1190.6	1157.8	1080.5	985.1	884.4	801.1	731.6	662.8	611.9	574.3
37.5°	1074.9	1123.1	1114.5	1044.6	944.8	843.8	751.9	679.1	613.6	562.2	525.3
40°	1008.5	1070.0	1079.0	1017.1	916.4	812.5	714.9	642.6	578.7	531.8	494.6
42.5°	937.4	1009.2	1033.6	984.0	885.3	779.4	682.0	607.0	543.8	498.1	465.2
45°	818.1	913.1	957.2	928.9	833.5	725.1	624.8	548.7	491.3	448.5	423.0
47.5°	706.5	810.4	869.7	859.7	775.8	668.4	569.3	496.4	440.5	406.2	383.4
50°	627.6	734.4	806.0	809.2	734.4	628.0	528.5	459.8	408.4	376.5	357.9
52.5°	559.0	660.9	739.0	756.1	688.1	586.0	492.0	423.6	378.3	349.0	332.3
55°	469.5	555.6	642.1	673.8	619.1	522.0	435.1	374.9	332.4	312.2	297.6
57.5°	390.3	462.2	542.1	576.9	543.3	460.2	378.7	326.4	291.9	274.2	263.0
60°	348.6	405.2	476.3	518.0	488.9	414.9	343.7	294.0	265.7	249.9	239.4
62.5°	309.7	359.9	420.1	458.2	442.4	372.6	308.8	264.9	240.4	225.6	218.1
65°	255.6	295.2	341.7	376.9	366.4	313.4	261.3	223.6	204.2	192.5	186.4
67.5°	210.5	239.1	271.3	302.1	293.7	256.1	214.3	185.0	170.5	160.4	156.8
70°	182.0	203.8	232.5	257.2	250.3	219.6	186.4	161.4	148.9	140.3	136.7
72.5°	154.8	172.8	194.6	214.8	210.2	184.7	157.0	138.1	128.4	120.6	117.6
75°	116.8	130.6	143.9	157.3	156.1	136.3	120.1	105.5	97.8	91.8	90.5
77.5°	86.3	94.0	103.1	111.0	108.8	97.4	84.8	76.4	70.7	66.7	66.1
80°	65.9	70.3	76.8	82.5	79.7	74.8	64.7	58.6	54.6	50.5	49.0
82.5°	47.8	52.3	56.2	59.2	57.0	52.5	46.3	42.1	39.7	37.0	36.3
85°	25.0	27.5	29.2	29.9	29.2	26.3	23.4	21.9	19.8	18.6	18.2
87.5°	13.7	12.9	12.1	12.2	10.8	10.4	8.6	7.3	7.4	7.4	7.2
90°	20.0	16.1	12.2	9.2	7.1	5.0	2.9	0.8	2.9	5.0	7.1
92.5°	23.3	22.4	21.5	20.3	18.7	17.2	15.6	14.1	15.6	17.2	18.7
95°	49.9	49.5	49.2	48.2	46.3	44.6	42.9	41.1	42.9	44.6	46.3
97.5°	83.7	83.1	82.4	81.3	79.8	78.2	76.7	75.1	76.7	78.2	79.8
100°	108.1	107.5	107.0	106.0	104.6	103.2	101.8	100.4	101.8	103.2	104.6
102.5°	133.7	133.0	132.4	131.4	130.3	129.2	128.1	127.0	128.1	129.2	130.3
105°	173.3	172.9	172.5	172.1	171.6	171.0	170.5	170.0	170.5	171.0	171.6
107.5°	216.7	216.7	216.7	216.4	215.6	214.8	214.0	213.3	214.0	214.8	215.6
110°	245.9	245.9	245.9	245.3	244.3	243.2	242.2	241.1	242.2	243.2	244.3



TEST NUMBER: P331358-927

CATALOG NUMBER: SA2XXDIP-C675D925U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	275.8	276.0	276.2	275.7	274.6	273.6	272.5	271.5	272.5	273.6	274.6
115°	320.1	320.4	320.8	320.4	319.4	318.3	317.3	316.2	317.3	318.3	319.4
117.5°	364.6	365.7	366.6	366.5	365.0	363.6	362.2	360.8	362.2	363.6	365.0
120°	393.3	394.7	396.2	396.2	394.7	393.3	392.0	390.5	392.0	393.3	394.7
122.5°	422.9	423.8	424.8	424.5	422.8	421.1	419.4	417.7	419.4	421.1	422.8
125°	465.9	466.4	467.0	466.4	464.9	463.3	461.7	460.1	461.7	463.3	464.9
127.5°	508.8	509.5	510.1	509.4	507.4	505.4	503.4	501.4	503.4	505.4	507.4
130°	536.7	537.0	537.4	536.5	534.2	531.9	529.6	527.3	529.6	531.9	534.2
132.5°	565.0	564.9	564.8	563.9	562.0	560.2	558.3	556.4	558.3	560.2	562.0
135°	604.8	604.5	604.2	603.0	601.1	599.1	597.2	595.3	597.2	599.1	601.1
137.5°	644.5	644.0	643.6	642.5	641.0	639.4	637.8	636.3	637.8	639.4	641.0
140°	670.2	669.3	668.4	667.3	665.7	664.1	662.5	660.9	662.5	664.1	665.7
142.5°	694.8	694.2	693.6	692.5	690.9	689.4	687.8	686.2	687.8	689.4	690.9
145°	730.7	729.7	728.6	727.5	726.3	725.0	723.8	722.5	723.8	725.0	726.3
147.5°	763.3	762.7	762.0	760.9	759.4	758.0	756.5	754.9	756.5	758.0	759.4
150°	783.6	782.9	782.2	781.3	780.3	779.2	778.2	777.1	778.2	779.2	780.3
152.5°	803.6	802.7	801.9	801.0	799.9	798.8	797.8	796.7	797.8	798.8	799.9
155°	829.8	829.3	828.8	828.2	827.8	827.2	826.6	826.2	826.6	827.2	827.8
157.5°	853.7	853.3	853.0	852.7	852.3	852.0	851.6	851.3	851.6	852.0	852.3
160°	868.5	868.3	868.2	867.8	867.5	867.1	866.8	866.5	866.8	867.1	867.5
162.5°	881.1	881.0	880.7	880.7	880.6	880.5	880.4	880.4	880.4	880.5	880.6
165°	898.1	898.1	898.1	898.2	898.3	898.5	898.7	898.9	898.7	898.5	898.3
167.5°	911.9	912.0	912.0	912.3	912.8	913.3	913.9	914.3	913.9	913.3	912.8
170°	919.8	920.0	920.1	920.4	921.0	921.5	922.0	922.6	922.0	921.5	921.0
172.5°	925.4	925.7	925.8	926.1	926.7	927.2	927.7	928.3	927.7	927.2	926.7
175°	932.0	932.3	932.7	933.1	933.7	934.1	934.7	935.3	934.7	934.1	933.7
177.5°	935.5	935.7	936.0	936.4	936.8	937.2	937.6	938.1	937.6	937.2	936.8
180°	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8



TEST NUMBER: P331358-927

CATALOG NUMBER: SA2XXDIP-C675D925U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3
2.5°	1038.3	1036.4	1029.6	1026.0	1020.2	1014.7	1011.1	1012.8	1014.1	1013.4	1012.4
5°	1008.5	1000.8	989.1	979.1	971.8	958.4	952.8	949.9	947.5	944.7	941.8
7.5°	973.1	961.0	944.2	929.8	916.2	899.6	890.2	884.5	878.7	872.3	866.6
10°	947.9	930.9	913.1	892.9	876.7	861.7	848.4	839.6	831.5	823.8	818.1
12.5°	921.4	901.8	879.8	852.2	834.3	812.9	810.9	795.2	782.6	777.8	771.2
15°	879.2	851.7	823.8	791.0	776.8	757.4	745.3	733.2	722.2	714.5	712.6
17.5°	831.2	795.6	767.9	744.3	721.1	701.2	690.1	680.3	671.4	661.1	659.7
20°	794.6	763.9	733.6	713.0	689.1	668.8	655.1	645.4	637.7	631.7	626.4
22.5°	760.0	726.4	698.6	676.0	652.5	636.2	625.3	616.0	609.6	602.9	597.9
25°	704.5	678.2	647.8	622.3	602.9	592.5	583.5	575.4	571.4	567.0	561.3
27.5°	655.8	626.6	598.3	578.5	561.5	552.2	545.8	540.3	536.5	533.9	530.8
30°	621.5	592.0	569.8	550.4	536.2	527.0	522.9	519.7	515.2	513.6	512.0
32.5°	588.6	562.0	543.0	526.1	512.6	506.5	502.8	499.9	496.5	494.8	491.5
35°	541.9	519.7	501.1	491.7	480.9	475.5	472.8	468.7	465.5	463.8	463.4
37.5°	498.0	478.6	466.4	454.5	449.9	446.6	442.8	440.0	439.0	438.8	438.4
40°	469.5	453.8	442.8	433.1	431.1	426.2	423.0	420.6	420.6	421.0	420.6
42.5°	443.6	429.4	419.9	411.5	409.1	406.2	402.9	402.7	403.5	404.8	403.5
45°	404.4	394.3	387.4	383.3	378.9	376.0	375.7	376.9	377.3	377.7	378.9
47.5°	368.3	361.6	355.4	350.9	349.0	348.5	348.0	350.1	352.0	352.8	354.7
50°	347.0	339.3	334.1	331.2	329.5	328.8	329.5	332.0	333.6	335.6	336.8
52.5°	323.1	317.6	313.9	311.8	311.2	311.6	311.8	314.6	317.1	317.8	318.5
55°	289.9	285.9	285.1	281.5	283.0	282.7	284.7	286.3	288.8	291.1	291.6
57.5°	257.0	253.7	251.5	251.8	252.3	254.1	255.8	258.6	261.3	263.8	264.0
60°	235.0	233.3	232.1	232.1	232.9	235.4	237.4	240.2	241.9	243.4	244.6
62.5°	214.9	213.3	212.1	212.7	214.8	216.3	218.6	220.1	221.7	223.4	223.9
65°	183.2	182.4	183.6	184.4	184.8	186.8	189.6	190.8	192.5	193.3	196.1
67.5°	154.0	154.2	154.0	155.1	157.5	158.0	160.7	163.4	163.7	165.3	167.2
70°	134.3	135.1	135.9	136.7	138.7	139.5	141.6	142.8	144.3	145.6	146.8
72.5°	116.1	116.3	117.1	116.9	118.7	120.4	122.2	123.3	124.9	126.5	127.7
75°	89.4	89.4	90.2	90.5	92.6	94.7	94.2	95.1	96.6	98.2	99.1
77.5°	65.3	64.4	65.3	65.7	66.3	68.0	68.4	69.5	71.3	70.7	71.7
80°	49.7	48.6	49.7	50.1	50.1	52.2	52.2	53.0	54.2	53.0	54.2
82.5°	35.5	34.9	35.8	35.9	36.5	36.6	37.3	37.5	38.7	38.1	38.7
85°	17.8	17.4	17.8	17.4	17.8	18.2	18.2	17.8	17.8	18.6	17.4
87.5°	7.4	7.6	8.1	8.9	9.3	9.7	9.3	9.3	9.2	8.5	8.5
90°	9.2	12.2	16.1	20.0	23.8	27.6	27.3	26.9	26.6	26.3	26.1
92.5°	20.3	21.5	22.4	23.3	24.2	25.1	25.2	25.3	25.3	25.4	25.5
95°	48.2	49.2	49.5	49.9	50.2	50.6	50.6	50.6	50.6	50.6	50.4
97.5°	81.3	82.4	83.1	83.7	84.4	85.1	85.1	85.1	85.1	85.1	85.1
100°	106.0	107.0	107.5	108.1	108.6	109.1	109.1	109.1	109.1	109.1	109.0
102.5°	131.4	132.4	133.0	133.7	134.4	135.1	135.1	135.3	135.5	135.6	135.5
105°	172.1	172.5	172.9	173.3	173.6	173.9	174.3	174.6	175.0	175.3	175.5
107.5°	216.4	216.7	216.7	216.7	216.7	216.7	216.9	217.1	217.2	217.3	217.0
110°	245.3	245.9	245.9	245.9	245.9	245.9	245.9	245.9	245.9	245.9	245.6



TEST NUMBER: P331358-927

CATALOG NUMBER: SA2XXDIP-C675D925U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	275.7	276.2	276.0	275.8	275.8	275.6	275.2	274.7	274.3	273.9	273.5
115°	320.4	320.8	320.4	320.1	319.7	319.4	319.2	319.0	318.9	318.7	318.3
117.5°	366.5	366.6	365.7	364.6	363.7	362.7	362.3	361.9	361.5	361.0	360.5
120°	396.2	396.2	394.7	393.3	392.0	390.5	390.5	390.5	390.5	390.5	390.3
122.5°	424.5	424.8	423.8	422.9	421.9	420.9	420.5	420.0	419.6	419.2	418.8
125°	466.4	467.0	466.4	465.9	465.4	464.9	464.3	463.8	463.3	462.7	462.4
127.5°	509.4	510.1	509.5	508.8	508.2	507.6	506.9	506.3	505.6	505.0	504.4
130°	536.5	537.4	537.0	536.7	536.4	536.0	535.7	535.3	535.0	534.6	534.1
132.5°	563.9	564.8	564.9	565.0	565.0	565.1	564.4	563.6	562.8	562.0	561.3
135°	603.0	604.2	604.5	604.8	605.2	605.5	605.4	605.2	605.1	604.8	604.5
137.5°	642.5	643.6	644.0	644.5	645.0	645.4	645.3	645.2	645.0	644.8	644.4
140°	667.3	668.4	669.3	670.2	671.1	672.0	672.0	672.0	672.0	672.0	671.6
142.5°	692.5	693.6	694.2	694.8	695.4	696.0	696.2	696.3	696.4	696.6	696.3
145°	727.5	728.6	729.7	730.7	731.8	732.8	733.0	733.2	733.4	733.6	733.3
147.5°	760.9	762.0	762.7	763.3	764.1	764.8	765.2	765.6	766.0	766.4	766.2
150°	781.3	782.2	782.9	783.6	784.3	785.1	785.5	786.1	786.6	787.1	787.1
152.5°	801.0	801.9	802.7	803.6	804.4	805.3	806.0	806.6	807.2	807.9	807.9
155°	828.2	828.8	829.3	829.8	830.4	830.8	831.8	832.7	833.5	834.4	834.6
157.5°	852.7	853.0	853.3	853.7	854.0	854.3	855.5	856.7	857.9	859.0	859.2
160°	867.8	868.2	868.3	868.5	868.6	868.8	869.9	870.9	872.0	873.1	873.2
162.5°	880.7	880.7	881.0	881.1	881.3	881.5	882.6	883.8	885.0	886.2	886.5
165°	898.2	898.1	898.1	898.1	898.1	898.1	899.3	900.6	901.7	903.0	903.2
167.5°	912.3	912.0	912.0	911.9	911.9	911.8	913.1	914.3	915.5	916.7	916.9
170°	920.4	920.1	920.0	919.8	919.6	919.4	920.7	921.9	923.1	924.3	924.4
172.5°	926.1	925.8	925.7	925.4	925.3	925.1	926.4	927.6	928.8	930.0	930.1
175°	933.1	932.7	932.3	932.0	931.6	931.3	932.5	933.7	934.9	936.2	936.3
177.5°	936.4	936.0	935.7	935.5	935.2	934.9	935.7	936.6	937.5	938.3	938.3
180°	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8



TEST NUMBER: P331358-927

CATALOG NUMBER: SA2XXDIP-C675D925U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3
2.5°	1009.2	1008.5	1008.5	1005.7	1008.5	1008.5	1009.2	1012.4	1013.4	1014.1	1012.8
5°	936.2	934.9	933.0	934.9	933.0	934.9	936.2	941.8	944.7	947.5	949.9
7.5°	864.0	859.1	858.4	853.6	858.4	859.1	864.0	866.6	872.3	878.7	884.5
10°	811.2	807.9	807.6	799.9	807.6	807.9	811.2	818.1	823.8	831.5	839.6
12.5°	771.1	763.3	764.9	760.4	764.9	763.3	771.1	771.2	777.8	782.6	795.2
15°	701.6	701.6	700.0	693.2	700.0	701.6	701.6	712.6	714.5	722.2	733.2
17.5°	651.7	650.9	647.1	649.0	647.1	650.9	651.7	659.7	661.1	671.4	680.3
20°	621.9	619.6	614.7	614.7	614.7	619.6	621.9	626.4	631.7	637.7	645.4
22.5°	593.8	593.7	588.5	590.1	588.5	593.7	593.8	597.9	602.9	609.6	616.0
25°	560.9	557.7	555.2	556.4	555.2	557.7	560.9	561.3	567.0	571.4	575.4
27.5°	529.7	527.9	527.8	524.4	527.8	527.9	529.7	530.8	533.9	536.5	540.3
30°	511.6	507.6	508.3	506.3	508.3	507.6	511.6	512.0	513.6	515.2	519.7
32.5°	490.8	489.4	488.6	486.9	488.6	489.4	490.8	491.5	494.8	496.5	499.9
35°	462.6	463.0	461.1	461.8	461.1	463.0	462.6	463.4	463.8	465.5	468.7
37.5°	438.0	439.3	438.3	438.6	438.3	439.3	438.0	438.4	438.8	439.0	440.0
40°	421.8	421.8	421.8	423.0	421.8	421.8	421.8	420.6	421.0	420.6	420.6
42.5°	406.2	405.6	405.0	404.9	405.0	405.6	406.2	403.5	404.8	403.5	402.7
45°	379.7	381.0	381.4	379.3	381.4	381.0	379.7	378.9	377.7	377.3	376.9
47.5°	355.7	355.8	355.7	357.5	355.7	355.8	355.7	354.7	352.8	352.0	350.1
50°	338.9	338.1	338.9	338.1	338.9	338.1	338.9	336.8	335.6	333.6	332.0
52.5°	321.1	321.2	320.8	320.6	320.8	321.2	321.1	318.5	317.8	317.1	314.6
55°	293.2	294.0	293.6	293.6	293.6	294.0	293.2	291.6	291.1	288.8	286.3
57.5°	264.4	265.1	265.6	263.8	265.6	265.1	264.4	264.0	263.8	261.3	258.6
60°	244.2	246.3	245.9	245.1	245.9	246.3	244.2	244.6	243.4	241.9	240.2
62.5°	225.9	226.6	226.5	226.3	226.5	226.6	225.9	223.9	223.4	221.7	220.1
65°	197.3	198.1	196.9	198.1	196.9	198.1	197.3	196.1	193.3	192.5	190.8
67.5°	166.7	166.9	167.9	168.4	167.9	166.9	166.7	167.2	165.3	163.7	163.4
70°	147.6	147.2	148.4	149.6	148.4	147.2	147.6	146.8	145.6	144.3	142.8
72.5°	127.5	128.4	128.0	128.9	128.0	128.4	127.5	127.7	126.5	124.9	123.3
75°	98.2	99.5	99.1	100.3	99.1	99.5	98.2	99.1	98.2	96.6	95.1
77.5°	71.0	71.1	71.0	71.7	71.0	71.1	71.0	71.7	70.7	71.3	69.5
80°	54.2	53.4	52.6	54.2	52.6	53.4	54.2	54.2	53.0	54.2	53.0
82.5°	37.7	38.2	37.4	37.4	37.4	38.2	37.7	38.7	38.1	38.7	37.5
85°	17.4	17.0	16.2	16.2	16.2	17.0	17.4	17.4	18.6	17.8	17.8
87.5°	8.5	8.2	8.2	8.0	8.2	8.2	8.5	8.5	8.5	9.2	9.3
90°	26.4	26.5	26.7	26.9	26.7	26.5	26.4	26.1	26.3	26.6	26.9
92.5°	25.5	25.5	25.6	25.6	25.6	25.5	25.5	25.5	25.4	25.3	25.3
95°	50.1	49.7	49.4	49.0	49.4	49.7	50.1	50.4	50.6	50.6	50.6
97.5°	85.0	85.0	84.9	84.9	84.9	85.0	85.0	85.1	85.1	85.1	85.1
100°	108.8	108.7	108.4	108.3	108.4	108.7	108.8	109.0	109.1	109.1	109.1
102.5°	135.4	135.2	135.1	134.9	135.1	135.2	135.4	135.5	135.6	135.5	135.3
105°	175.5	175.5	175.5	175.5	175.5	175.5	175.5	175.5	175.3	175.0	174.6
107.5°	216.2	215.4	214.6	213.7	214.6	215.4	216.2	217.0	217.3	217.2	217.1
110°	245.1	244.5	244.0	243.5	244.0	244.5	245.1	245.6	245.9	245.9	245.9



TEST NUMBER: P331358-927

CATALOG NUMBER: SA2XXDIP-C675D925U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	273.1	272.7	272.4	272.0	272.4	272.7	273.1	273.5	273.9	274.3	274.7
115°	317.8	317.3	316.7	316.2	316.7	317.3	317.8	318.3	318.7	318.9	319.0
117.5°	360.0	359.5	358.9	358.5	358.9	359.5	360.0	360.5	361.0	361.5	361.9
120°	389.8	389.2	388.7	388.2	388.7	389.2	389.8	390.3	390.5	390.5	390.5
122.5°	418.4	418.0	417.6	417.2	417.6	418.0	418.4	418.8	419.2	419.6	420.0
125°	462.2	462.0	461.8	461.7	461.8	462.0	462.2	462.4	462.7	463.3	463.8
127.5°	503.8	503.3	502.7	502.2	502.7	503.3	503.8	504.4	505.0	505.6	506.3
130°	533.4	532.7	532.0	531.2	532.0	532.7	533.4	534.1	534.6	535.0	535.3
132.5°	560.8	560.2	559.7	559.1	559.7	560.2	560.8	561.3	562.0	562.8	563.6
135°	604.0	603.5	602.9	602.4	602.9	603.5	604.0	604.5	604.8	605.1	605.2
137.5°	643.7	643.0	642.3	641.6	642.3	643.0	643.7	644.4	644.8	645.0	645.2
140°	670.9	670.2	669.6	668.8	669.6	670.2	670.9	671.6	672.0	672.0	672.0
142.5°	695.6	694.9	694.2	693.5	694.2	694.9	695.6	696.3	696.6	696.4	696.3
145°	732.6	731.9	731.2	730.5	731.2	731.9	732.6	733.3	733.6	733.4	733.2
147.5°	765.6	764.9	764.2	763.5	764.2	764.9	765.6	766.2	766.4	766.0	765.6
150°	786.6	786.1	785.5	785.1	785.5	786.1	786.6	787.1	787.1	786.6	786.1
152.5°	807.2	806.6	806.0	805.3	806.0	806.6	807.2	807.9	807.9	807.2	806.6
155°	834.0	833.5	833.0	832.4	833.0	833.5	834.0	834.6	834.4	833.5	832.7
157.5°	858.4	857.5	856.7	855.9	856.7	857.5	858.4	859.2	859.0	857.9	856.7
160°	872.5	871.8	871.1	870.4	871.1	871.8	872.5	873.2	873.1	872.0	870.9
162.5°	885.6	884.7	883.9	883.0	883.9	884.7	885.6	886.5	886.2	885.0	883.8
165°	902.3	901.4	900.6	899.7	900.6	901.4	902.3	903.2	903.0	901.7	900.6
167.5°	916.0	915.0	914.2	913.2	914.2	915.0	916.0	916.9	916.7	915.5	914.3
170°	923.4	922.3	921.2	920.2	921.2	922.3	923.4	924.4	924.3	923.1	921.9
172.5°	929.1	928.0	926.9	925.9	926.9	928.0	929.1	930.1	930.0	928.8	927.6
175°	935.3	934.1	933.1	932.1	933.1	934.1	935.3	936.3	936.2	934.9	933.7
177.5°	937.5	936.6	935.7	934.9	935.7	936.6	937.5	938.3	938.3	937.5	936.6
180°	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8



TEST NUMBER: P331358-927

CATALOG NUMBER: SA2XXDIP-C675D925U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3
2.5°	1011.1	1014.7	1020.2	1026.0	1029.6	1036.4	1038.3	1041.6	1044.5	1051.3	1058.4
5°	952.8	958.4	971.8	979.1	989.1	1000.8	1008.5	1016.7	1025.6	1040.9	1055.0
7.5°	890.2	899.6	916.2	929.8	944.2	961.0	973.1	989.1	1002.4	1024.1	1044.8
10°	848.4	861.7	876.7	892.9	913.1	930.9	947.9	968.1	984.3	1010.2	1034.4
12.5°	810.9	812.9	834.3	852.2	879.8	901.8	921.4	947.5	963.3	994.0	1019.5
15°	745.3	757.4	776.8	791.0	823.8	851.7	879.2	906.3	924.5	962.4	996.0
17.5°	690.1	701.2	721.1	744.3	767.9	795.6	831.2	859.8	884.5	928.0	967.7
20°	655.1	668.8	689.1	713.0	733.6	763.9	794.6	827.4	854.1	903.0	949.5
22.5°	625.3	636.2	652.5	676.0	698.6	726.4	760.0	795.7	823.7	876.5	923.6
25°	583.5	592.5	602.9	622.3	647.8	678.2	704.5	743.7	784.5	833.9	890.9
27.5°	545.8	552.2	561.5	578.5	598.3	626.6	655.8	693.1	734.1	787.7	847.9
30°	522.9	527.0	536.2	550.4	569.8	592.0	621.5	657.1	699.2	753.4	813.3
32.5°	502.8	506.5	512.6	526.1	543.0	562.0	588.6	624.2	664.2	717.5	783.8
35°	472.8	475.5	480.9	491.7	501.1	519.7	541.9	574.3	611.9	662.8	731.6
37.5°	442.8	446.6	449.9	454.5	466.4	478.6	498.0	525.3	562.2	613.6	679.1
40°	423.0	426.2	431.1	433.1	442.8	453.8	469.5	494.6	531.8	578.7	642.6
42.5°	402.9	406.2	409.1	411.5	419.9	429.4	443.6	465.2	498.1	543.8	607.0
45°	375.7	376.0	378.9	383.3	387.4	394.3	404.4	423.0	448.5	491.3	548.7
47.5°	348.0	348.5	349.0	350.9	355.4	361.6	368.3	383.4	406.2	440.5	496.4
50°	329.5	328.8	329.5	331.2	334.1	339.3	347.0	357.9	376.5	408.4	459.8
52.5°	311.8	311.6	311.2	311.8	313.9	317.6	323.1	332.3	349.0	378.3	423.6
55°	284.7	282.7	283.0	281.5	285.1	285.9	289.9	297.6	312.2	332.4	374.9
57.5°	255.8	254.1	252.3	251.8	251.5	253.7	257.0	263.0	274.2	291.9	326.4
60°	237.4	235.4	232.9	232.1	232.1	233.3	235.0	239.4	249.9	265.7	294.0
62.5°	218.6	216.3	214.8	212.7	212.1	213.3	214.9	218.1	225.6	240.4	264.9
65°	189.6	186.8	184.8	184.4	183.6	182.4	183.2	186.4	192.5	204.2	223.6
67.5°	160.7	158.0	157.5	155.1	154.0	154.2	154.0	156.8	160.4	170.5	185.0
70°	141.6	139.5	138.7	136.7	135.9	135.1	134.3	136.7	140.3	148.9	161.4
72.5°	122.2	120.4	118.7	116.9	117.1	116.3	116.1	117.6	120.6	128.4	138.1
75°	94.2	94.7	92.6	90.5	90.2	89.4	89.4	90.5	91.8	97.8	105.5
77.5°	68.4	68.0	66.3	65.7	65.3	64.4	65.3	66.1	66.7	70.7	76.4
80°	52.2	52.2	50.1	50.1	49.7	48.6	49.7	49.0	50.5	54.6	58.6
82.5°	37.3	36.6	36.5	35.9	35.8	34.9	35.5	36.3	37.0	39.7	42.1
85°	18.2	18.2	17.8	17.4	17.8	17.4	17.8	18.2	18.6	19.8	21.9
87.5°	9.3	9.7	9.3	8.9	8.1	7.6	7.4	7.2	7.4	7.4	7.3
90°	27.3	27.6	23.8	20.0	16.1	12.2	9.2	7.1	5.0	2.9	0.8
92.5°	25.2	25.1	24.2	23.3	22.4	21.5	20.3	18.7	17.2	15.6	14.1
95°	50.6	50.6	50.2	49.9	49.5	49.2	48.2	46.3	44.6	42.9	41.1
97.5°	85.1	85.1	84.4	83.7	83.1	82.4	81.3	79.8	78.2	76.7	75.1
100°	109.1	109.1	108.6	108.1	107.5	107.0	106.0	104.6	103.2	101.8	100.4
102.5°	135.1	135.1	134.4	133.7	133.0	132.4	131.4	130.3	129.2	128.1	127.0
105°	174.3	173.9	173.6	173.3	172.9	172.5	172.1	171.6	171.0	170.5	170.0
107.5°	216.9	216.7	216.7	216.7	216.7	216.7	216.4	215.6	214.8	214.0	213.3
110°	245.9	245.9	245.9	245.9	245.9	245.9	245.3	244.3	243.2	242.2	241.1



TEST NUMBER: P331358-927

CATALOG NUMBER: SA2XXDIP-C675D925U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	275.2	275.6	275.8	275.8	276.0	276.2	275.7	274.6	273.6	272.5	271.5
115°	319.2	319.4	319.7	320.1	320.4	320.8	320.4	319.4	318.3	317.3	316.2
117.5°	362.3	362.7	363.7	364.6	365.7	366.6	366.5	365.0	363.6	362.2	360.8
120°	390.5	390.5	392.0	393.3	394.7	396.2	396.2	394.7	393.3	392.0	390.5
122.5°	420.5	420.9	421.9	422.9	423.8	424.8	424.5	422.8	421.1	419.4	417.7
125°	464.3	464.9	465.4	465.9	466.4	467.0	466.4	464.9	463.3	461.7	460.1
127.5°	506.9	507.6	508.2	508.8	509.5	510.1	509.4	507.4	505.4	503.4	501.4
130°	535.7	536.0	536.4	536.7	537.0	537.4	536.5	534.2	531.9	529.6	527.3
132.5°	564.4	565.1	565.0	565.0	564.9	564.8	563.9	562.0	560.2	558.3	556.4
135°	605.4	605.5	605.2	604.8	604.5	604.2	603.0	601.1	599.1	597.2	595.3
137.5°	645.3	645.4	645.0	644.5	644.0	643.6	642.5	641.0	639.4	637.8	636.3
140°	672.0	672.0	671.1	670.2	669.3	668.4	667.3	665.7	664.1	662.5	660.9
142.5°	696.2	696.0	695.4	694.8	694.2	693.6	692.5	690.9	689.4	687.8	686.2
145°	733.0	732.8	731.8	730.7	729.7	728.6	727.5	726.3	725.0	723.8	722.5
147.5°	765.2	764.8	764.1	763.3	762.7	762.0	760.9	759.4	758.0	756.5	754.9
150°	785.5	785.1	784.3	783.6	782.9	782.2	781.3	780.3	779.2	778.2	777.1
152.5°	806.0	805.3	804.4	803.6	802.7	801.9	801.0	799.9	798.8	797.8	796.7
155°	831.8	830.8	830.4	829.8	829.3	828.8	828.2	827.8	827.2	826.6	826.2
157.5°	855.5	854.3	854.0	853.7	853.3	853.0	852.7	852.3	852.0	851.6	851.3
160°	869.9	868.8	868.6	868.5	868.3	868.2	867.8	867.5	867.1	866.8	866.5
162.5°	882.6	881.5	881.3	881.1	881.0	880.7	880.7	880.6	880.5	880.4	880.4
165°	899.3	898.1	898.1	898.1	898.1	898.1	898.2	898.3	898.5	898.7	898.9
167.5°	913.1	911.8	911.9	911.9	912.0	912.0	912.3	912.8	913.3	913.9	914.3
170°	920.7	919.4	919.6	919.8	920.0	920.1	920.4	921.0	921.5	922.0	922.6
172.5°	926.4	925.1	925.3	925.4	925.7	925.8	926.1	926.7	927.2	927.7	928.3
175°	932.5	931.3	931.6	932.0	932.3	932.7	933.1	933.7	934.1	934.7	935.3
177.5°	935.7	934.9	935.2	935.5	935.7	936.0	936.4	936.8	937.2	937.6	938.1
180°	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8



TEST NUMBER: P331358-927

CATALOG NUMBER: SA2XXDIP-C675D925U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3
2.5°	1057.7	1059.4	1064.5	1069.7	1075.5	1077.1	1079.7	1077.4	1076.8	1083.0	1087.5
5°	1060.7	1068.0	1082.2	1095.1	1106.0	1113.7	1121.8	1125.1	1131.1	1139.6	1150.1
7.5°	1057.3	1071.5	1093.8	1112.5	1133.1	1148.0	1159.5	1169.3	1181.3	1197.4	1215.0
10°	1053.4	1072.5	1099.5	1122.6	1147.6	1166.6	1182.5	1197.8	1215.6	1237.9	1260.9
12.5°	1046.3	1068.9	1102.8	1130.0	1162.2	1180.9	1202.2	1235.3	1254.4	1285.4	1317.9
15°	1032.1	1057.1	1104.4	1138.0	1174.3	1210.0	1249.2	1280.7	1312.2	1330.5	1376.2
17.5°	1010.7	1047.6	1099.9	1139.1	1185.3	1241.4	1285.5	1321.2	1357.6	1387.2	1410.1
20°	993.6	1033.6	1093.4	1140.4	1195.4	1255.6	1306.2	1342.6	1374.1	1398.8	1412.9
22.5°	971.9	1022.3	1080.5	1135.5	1205.8	1265.4	1318.5	1347.1	1373.5	1385.5	1391.0
25°	937.8	998.5	1064.4	1131.5	1210.8	1273.8	1322.4	1339.7	1347.4	1335.7	1316.3
27.5°	901.0	968.6	1045.7	1123.9	1207.7	1268.4	1303.1	1300.4	1287.4	1249.4	1219.1
30°	873.5	947.9	1030.8	1116.1	1200.2	1259.3	1279.5	1259.3	1229.8	1187.3	1144.1
32.5°	844.7	921.7	1014.9	1105.1	1186.7	1238.6	1242.9	1208.2	1162.4	1114.2	1060.3
35°	801.1	884.4	985.1	1080.5	1157.8	1190.6	1171.2	1109.7	1055.5	989.6	915.9
37.5°	751.9	843.8	944.8	1044.6	1114.5	1123.1	1074.9	1010.2	933.7	856.3	769.7
40°	714.9	812.5	916.4	1017.1	1079.0	1070.0	1008.5	937.4	846.4	751.8	671.3
42.5°	682.0	779.4	885.3	984.0	1033.6	1009.2	937.4	850.0	752.3	663.1	589.5
45°	624.8	725.1	833.5	928.9	957.2	913.1	818.1	721.0	624.8	550.4	492.2
47.5°	569.3	668.4	775.8	859.7	869.7	810.4	706.5	606.7	523.9	463.3	422.2
50°	528.5	628.0	734.4	809.2	806.0	734.4	627.6	532.6	463.4	414.5	387.0
52.5°	492.0	586.0	688.1	756.1	739.0	660.9	559.0	474.7	417.8	379.5	354.7
55°	435.1	522.0	619.1	673.8	642.1	555.6	469.5	401.6	359.5	330.8	311.4
57.5°	378.7	460.2	543.3	576.9	542.1	462.2	390.3	341.0	309.4	288.2	275.5
60°	343.7	414.9	488.9	518.0	476.3	405.2	348.6	304.5	279.0	261.7	250.3
62.5°	308.8	372.6	442.4	458.2	420.1	359.9	309.7	273.1	252.2	236.7	226.1
65°	261.3	313.4	366.4	376.9	341.7	295.2	255.6	231.7	213.1	201.8	193.3
67.5°	214.3	256.1	293.7	302.1	271.3	239.1	210.5	189.6	177.1	167.6	160.5
70°	186.4	219.6	250.3	257.2	232.5	203.8	182.0	165.4	154.1	146.0	139.1
72.5°	157.0	184.7	210.2	214.8	194.6	172.8	154.8	141.8	131.7	126.6	120.0
75°	120.1	136.3	156.1	157.3	143.9	130.6	116.8	108.4	103.1	96.6	93.4
77.5°	84.8	97.4	108.8	111.0	103.1	94.0	86.3	79.6	75.1	72.2	69.2
80°	64.7	74.8	79.7	82.5	76.8	70.3	65.9	61.5	58.6	56.6	54.6
82.5°	46.3	52.5	57.0	59.2	56.2	52.3	47.8	45.3	43.1	41.4	40.7
85°	23.4	26.3	29.2	29.9	29.2	27.5	25.0	25.0	23.8	23.4	23.4
87.5°	8.6	10.4	10.8	12.2	12.1	12.9	13.7	14.2	14.6	14.2	13.8
90°	2.9	5.0	7.1	9.2	12.2	16.1	20.0	23.8	27.6	27.3	26.9
92.5°	15.6	17.2	18.7	20.3	21.5	22.4	23.3	24.2	25.1	25.2	25.3
95°	42.9	44.6	46.3	48.2	49.2	49.5	49.9	50.2	50.6	50.6	50.6
97.5°	76.7	78.2	79.8	81.3	82.4	83.1	83.7	84.4	85.1	85.1	85.1
100°	101.8	103.2	104.6	106.0	107.0	107.5	108.1	108.6	109.1	109.1	109.1
102.5°	128.1	129.2	130.3	131.4	132.4	133.0	133.7	134.4	135.1	135.1	135.3
105°	170.5	171.0	171.6	172.1	172.5	172.9	173.3	173.6	173.9	174.3	174.6
107.5°	214.0	214.8	215.6	216.4	216.7	216.7	216.7	216.7	216.7	216.9	217.1
110°	242.2	243.2	244.3	245.3	245.9	245.9	245.9	245.9	245.9	245.9	245.9



TEST NUMBER: P331358-927

CATALOG NUMBER: SA2XXDIP-C675D925U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	272.5	273.6	274.6	275.7	276.2	276.0	275.8	275.8	275.6	275.2	274.7
115°	317.3	318.3	319.4	320.4	320.8	320.4	320.1	319.7	319.4	319.2	319.0
117.5°	362.2	363.6	365.0	366.5	366.6	365.7	364.6	363.7	362.7	362.3	361.9
120°	392.0	393.3	394.7	396.2	396.2	394.7	393.3	392.0	390.5	390.5	390.5
122.5°	419.4	421.1	422.8	424.5	424.8	423.8	422.9	421.9	420.9	420.5	420.0
125°	461.7	463.3	464.9	466.4	467.0	466.4	465.9	465.4	464.9	464.3	463.8
127.5°	503.4	505.4	507.4	509.4	510.1	509.5	508.8	508.2	507.6	506.9	506.3
130°	529.6	531.9	534.2	536.5	537.4	537.0	536.7	536.4	536.0	535.7	535.3
132.5°	558.3	560.2	562.0	563.9	564.8	564.9	565.0	565.0	565.1	564.4	563.6
135°	597.2	599.1	601.1	603.0	604.2	604.5	604.8	605.2	605.5	605.4	605.2
137.5°	637.8	639.4	641.0	642.5	643.6	644.0	644.5	645.0	645.4	645.3	645.2
140°	662.5	664.1	665.7	667.3	668.4	669.3	670.2	671.1	672.0	672.0	672.0
142.5°	687.8	689.4	690.9	692.5	693.6	694.2	694.8	695.4	696.0	696.2	696.3
145°	723.8	725.0	726.3	727.5	728.6	729.7	730.7	731.8	732.8	733.0	733.2
147.5°	756.5	758.0	759.4	760.9	762.0	762.7	763.3	764.1	764.8	765.2	765.6
150°	778.2	779.2	780.3	781.3	782.2	782.9	783.6	784.3	785.1	785.5	786.1
152.5°	797.8	798.8	799.9	801.0	801.9	802.7	803.6	804.4	805.3	806.0	806.6
155°	826.6	827.2	827.8	828.2	828.8	829.3	829.8	830.4	830.8	831.8	832.7
157.5°	851.6	852.0	852.3	852.7	853.0	853.3	853.7	854.0	854.3	855.5	856.7
160°	866.8	867.1	867.5	867.8	868.2	868.3	868.5	868.6	868.8	869.9	870.9
162.5°	880.4	880.5	880.6	880.7	880.7	881.0	881.1	881.3	881.5	882.6	883.8
165°	898.7	898.5	898.3	898.2	898.1	898.1	898.1	898.1	898.1	899.3	900.6
167.5°	913.9	913.3	912.8	912.3	912.0	912.0	911.9	911.9	911.8	913.1	914.3
170°	922.0	921.5	921.0	920.4	920.1	920.0	919.8	919.6	919.4	920.7	921.9
172.5°	927.7	927.2	926.7	926.1	925.8	925.7	925.4	925.3	925.1	926.4	927.6
175°	934.7	934.1	933.7	933.1	932.7	932.3	932.0	931.6	931.3	932.5	933.7
177.5°	937.6	937.2	936.8	936.4	936.0	935.7	935.5	935.2	934.9	935.7	936.6
180°	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8



TEST NUMBER: P331358-927

CATALOG NUMBER: SA2XXDIP-C675D925U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3
2.5°	1091.4	1095.9	1095.9	1096.5	1101.8	1101.1	1100.7
5°	1161.4	1168.3	1169.1	1176.4	1181.2	1179.6	1175.2
7.5°	1227.5	1240.3	1250.0	1255.4	1261.8	1265.7	1264.0
10°	1279.9	1298.5	1309.9	1317.6	1326.8	1333.7	1331.3
12.5°	1327.5	1349.6	1365.2	1378.3	1379.6	1388.4	1382.4
15°	1401.6	1425.1	1427.5	1437.3	1444.9	1444.1	1444.5
17.5°	1426.2	1433.7	1435.2	1435.4	1435.5	1432.7	1426.6
20°	1417.4	1414.6	1407.7	1402.5	1393.1	1391.9	1383.9
22.5°	1376.0	1367.0	1349.8	1338.4	1323.9	1320.1	1317.9
25°	1294.5	1274.6	1247.1	1220.8	1213.6	1199.4	1203.5
27.5°	1182.6	1151.8	1122.0	1100.6	1081.2	1060.1	1066.1
30°	1104.0	1069.2	1027.1	994.8	974.2	953.9	950.3
32.5°	1010.2	959.3	912.3	883.8	852.2	839.5	825.5
35°	848.4	798.7	752.2	712.2	689.1	671.3	655.1
37.5°	702.9	645.6	608.2	575.7	559.0	548.8	551.4
40°	612.7	562.5	535.0	510.3	495.0	487.7	489.3
42.5°	539.6	502.0	479.3	462.5	451.6	447.6	446.6
45°	456.5	435.5	416.9	407.3	402.0	397.5	394.7
47.5°	400.0	382.8	372.3	366.5	361.9	357.4	357.4
50°	366.0	354.7	347.4	341.3	337.7	334.5	337.2
52.5°	340.1	329.7	322.5	317.0	315.7	312.8	312.7
55°	301.7	293.6	288.4	283.4	281.1	279.4	277.4
57.5°	266.7	259.0	254.2	251.1	246.5	244.9	244.2
60°	241.9	235.8	230.9	226.9	224.8	221.6	221.6
62.5°	218.9	212.8	208.3	205.2	201.8	200.6	200.9
65°	185.6	180.8	176.3	173.1	172.3	169.8	170.6
67.5°	155.0	151.8	147.1	145.4	143.8	142.5	141.6
70°	134.7	131.4	129.0	126.6	125.3	125.3	125.3
72.5°	117.5	113.6	112.2	109.1	109.8	108.5	107.3
75°	91.0	88.6	87.4	86.1	84.1	84.1	84.1
77.5°	66.9	66.2	64.8	63.5	63.0	62.6	62.7
80°	51.7	51.3	50.5	50.5	49.7	49.4	48.6
82.5°	39.8	38.7	38.3	37.9	37.8	37.7	37.5
85°	22.7	21.9	21.9	22.3	21.5	21.5	21.9
87.5°	14.0	14.0	13.6	13.7	14.0	13.8	13.8
90°	26.6	26.3	26.1	26.4	26.5	26.7	26.9
92.5°	25.3	25.4	25.5	25.5	25.5	25.6	25.6
95°	50.6	50.6	50.4	50.1	49.7	49.4	49.0
97.5°	85.1	85.1	85.1	85.0	85.0	84.9	84.9
100°	109.1	109.1	109.0	108.8	108.7	108.4	108.3
102.5°	135.5	135.6	135.5	135.4	135.2	135.1	134.9
105°	175.0	175.3	175.5	175.5	175.5	175.5	175.5
107.5°	217.2	217.3	217.0	216.2	215.4	214.6	213.7
110°	245.9	245.9	245.6	245.1	244.5	244.0	243.5



TEST NUMBER: P331358-927

CATALOG NUMBER: SA2XXDIP-C675D925U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	274.3	273.9	273.5	273.1	272.7	272.4	272.0
115°	318.9	318.7	318.3	317.8	317.3	316.7	316.2
117.5°	361.5	361.0	360.5	360.0	359.5	358.9	358.5
120°	390.5	390.5	390.3	389.8	389.2	388.7	388.2
122.5°	419.6	419.2	418.8	418.4	418.0	417.6	417.2
125°	463.3	462.7	462.4	462.2	462.0	461.8	461.7
127.5°	505.6	505.0	504.4	503.8	503.3	502.7	502.2
130°	535.0	534.6	534.1	533.4	532.7	532.0	531.2
132.5°	562.8	562.0	561.3	560.8	560.2	559.7	559.1
135°	605.1	604.8	604.5	604.0	603.5	602.9	602.4
137.5°	645.0	644.8	644.4	643.7	643.0	642.3	641.6
140°	672.0	672.0	671.6	670.9	670.2	669.6	668.8
142.5°	696.4	696.6	696.3	695.6	694.9	694.2	693.5
145°	733.4	733.6	733.3	732.6	731.9	731.2	730.5
147.5°	766.0	766.4	766.2	765.6	764.9	764.2	763.5
150°	786.6	787.1	787.1	786.6	786.1	785.5	785.1
152.5°	807.2	807.9	807.9	807.2	806.6	806.0	805.3
155°	833.5	834.4	834.6	834.0	833.5	833.0	832.4
157.5°	857.9	859.0	859.2	858.4	857.5	856.7	855.9
160°	872.0	873.1	873.2	872.5	871.8	871.1	870.4
162.5°	885.0	886.2	886.5	885.6	884.7	883.9	883.0
165°	901.7	903.0	903.2	902.3	901.4	900.6	899.7
167.5°	915.5	916.7	916.9	916.0	915.0	914.2	913.2
170°	923.1	924.3	924.4	923.4	922.3	921.2	920.2
172.5°	928.8	930.0	930.1	929.1	928.0	926.9	925.9
175°	934.9	936.2	936.3	935.3	934.1	933.1	932.1
177.5°	937.5	938.3	938.3	937.5	936.6	935.7	934.9
180°	936.8	936.8	936.8	936.8	936.8	936.8	936.8

(END OF REPORT)