

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331321

Luminaire Tested: **SA2XXDIP-C485D1080U835-4F0-1E-UDD-A**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331321  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXDIP-C485D1080U835-4F0-1E-UDD-A  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 485 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1080 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6452.8 lumens  
Efficiency: N/A  
Efficacy: 130.6 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: Semi-Indirect

Input Watts (W): 49.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331321  
CATALOG NUMBER: SA2XXDIP-C485D1080U835-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P331321

CATALOG NUMBER: SA2XXDIP-C485D1080U835-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	33
1	94	90	87	83	85	82	78	76	65	63	61	50	49	48	36	36	35	29
2	86	79	73	68	77	72	67	63	58	54	51	45	42	40	32	31	30	24
3	79	70	63	57	71	63	57	53	51	47	43	40	37	34	29	27	26	21
4	72	62	54	49	65	56	50	45	45	41	37	35	32	30	26	24	23	18
5	66	55	47	42	60	50	44	39	41	36	32	32	29	26	24	22	20	16
6	61	50	42	36	55	45	38	34	37	32	28	29	25	23	22	19	18	14
7	56	45	37	32	51	41	34	29	33	28	25	26	23	20	20	17	16	13
8	52	41	33	28	47	37	31	26	30	26	22	24	21	18	18	16	14	12
9	49	37	30	25	44	34	28	23	28	23	20	22	19	16	17	15	13	11
10	45	34	27	22	41	31	25	21	26	21	18	21	17	15	16	13	12	10

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	15689	15689	15689	15689
5°	17590	15793	13994	15793
10°	20156	15662	12111	15662
15°	22298	15375	10700	15375
20°	21959	15067	9754	15067
25°	19800	14656	9155	14656
30°	16362	14001	8718	14001
35°	11925	13316	8406	13316
40°	9525	12507	8233	12507
45°	8323	11572	7999	11572
50°	7824	10665	7842	10665
55°	7212	9745	7631	9745
60°	6610	8767	7308	8767
65°	6021	7889	6991	7889
70°	5467	7034	6524	7034
75°	4847	6082	5777	6082
80°	4166	5040	4649	5040
85°	3742	3742	2760	3742



TEST NUMBER: P331321

CATALOG NUMBER: SA2XXDIP-C485D1080U835-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	92.5	1.4
10°-20°	269.0	4.2
20°-30°	390.5	6.1
30°-40°	412.0	6.4
40°-50°	364.8	5.7
50°-60°	291.1	4.5
60°-70°	197.9	3.1
70°-80°	101.5	1.6
80°-90°	28.1	0.4
90°-100°	49.0	0.8
100°-110°	179.7	2.8
110°-120°	480.4	7.4
120°-130°	793.0	12.3
130°-140°	843.3	13.1
140°-150°	783.8	12.1
150°-160°	630.2	9.8
160°-170°	406.1	6.3
170°-180°	139.8	2.2
0°-30°	752.0	11.7
0°-40°	1164.1	18.0
0°-60°	1820.1	28.2
0°-90°	2147.5	33.3
90°-120°	709.1	11.0
90°-150°	3129.2	48.5
90°-180°	4305.0	66.7
0°-180°	6452.8	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	972	972	972	972	972	
5°	1085	974	863	974	1085	108
15°	1334	920	640	920	1334	368
25°	1111	823	514	823	1111	502
35°	605	676	426	676	605	393
45°	364	507	350	507	364	287
55°	256	346	271	346	256	230
65°	158	206	183	206	158	157
75°	78	98	93	98	78	83
85°	20	20	15	20	20	23
90°	29	1	29	1	29	14
95°	46	69	46	69	46	43
105°	81	323	81	323	81	84
115°	87	611	87	611	87	218
125°	909	864	909	864	909	786
135°	1104	1069	1104	1069	1104	851
145°	1260	1241	1260	1241	1260	788
155°	1367	1366	1367	1366	1367	631
165°	1436	1439	1436	1439	1436	405
175°	1464	1472	1464	1472	1464	139
180°	1469	1469	1469	1469	1469	



TEST NUMBER: P331321

CATALOG NUMBER: SA2XXDIP-C485D1080U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7
2.5°	1016.6	1016.9	1017.4	1012.7	1012.1	1012.1	1007.9	1004.3	1000.1	994.4	995.0
5°	1085.3	1089.4	1090.9	1086.4	1079.7	1078.9	1072.6	1062.1	1052.4	1044.6	1039.0
7.5°	1167.3	1168.9	1165.3	1159.4	1154.4	1145.4	1133.6	1122.0	1105.8	1090.9	1079.9
10°	1229.4	1231.7	1225.3	1216.7	1209.6	1199.2	1182.0	1164.4	1143.2	1122.6	1106.2
12.5°	1276.6	1282.2	1274.0	1272.9	1260.7	1246.4	1225.9	1217.0	1187.1	1158.5	1140.8
15°	1334.0	1333.6	1334.4	1327.3	1318.3	1316.1	1294.4	1270.9	1228.7	1211.9	1182.7
17.5°	1317.4	1323.1	1325.7	1325.6	1325.4	1324.0	1317.0	1302.2	1281.0	1253.8	1220.2
20°	1278.0	1285.4	1286.6	1295.2	1300.0	1306.4	1309.0	1304.9	1291.8	1269.0	1239.9
22.5°	1217.0	1219.1	1222.6	1236.0	1246.5	1262.4	1270.7	1284.5	1279.5	1268.4	1244.1
25°	1111.4	1107.7	1120.7	1127.5	1151.7	1177.1	1195.4	1215.6	1233.5	1244.4	1237.3
27.5°	984.6	979.0	998.6	1016.4	1036.1	1063.6	1092.1	1125.8	1153.8	1188.9	1200.9
30°	877.6	881.0	899.7	918.7	948.6	987.4	1019.5	1056.5	1096.5	1135.7	1162.9
32.5°	762.3	775.2	787.0	816.2	842.5	885.8	932.9	979.1	1029.0	1073.5	1115.7
35°	605.0	619.9	636.4	657.7	694.6	737.6	783.5	845.9	913.9	974.7	1024.8
37.5°	509.2	506.9	516.3	531.7	561.6	596.3	649.1	710.8	790.8	862.3	932.9
40°	451.9	450.4	457.1	471.3	494.1	519.5	565.8	619.9	694.3	781.6	865.7
42.5°	412.4	413.3	417.1	427.1	442.7	463.6	498.3	544.4	612.4	694.7	785.0
45°	364.5	367.1	371.2	376.1	385.0	402.2	421.6	454.5	508.3	577.0	665.9
47.5°	330.0	330.1	334.2	338.5	343.8	353.5	369.4	390.0	427.9	483.9	560.3
50°	311.5	308.8	311.8	315.2	320.8	327.5	338.0	357.4	382.8	428.0	491.8
52.5°	288.8	288.8	291.5	292.8	297.8	304.5	314.1	327.5	350.5	385.9	438.4
55°	256.2	258.1	259.6	261.8	266.3	271.1	278.6	287.6	305.5	332.0	370.8
57.5°	225.6	226.2	227.7	231.9	234.8	239.2	246.3	254.5	266.1	285.8	315.0
60°	204.7	204.7	207.6	209.5	213.2	217.7	223.3	231.2	241.6	257.7	281.2
62.5°	185.5	185.2	186.4	189.5	192.3	196.5	202.1	208.8	218.6	232.9	252.2
65°	157.6	156.9	159.1	159.8	162.8	166.9	171.4	178.5	186.4	196.8	214.0
67.5°	130.7	131.6	132.8	134.2	135.9	140.2	143.2	148.2	154.8	163.5	175.2
70°	115.8	115.8	115.8	116.9	119.1	121.4	124.4	128.5	134.8	142.3	152.7
72.5°	99.0	100.2	101.4	100.8	103.6	104.9	108.5	110.8	116.9	121.7	130.9
75°	77.7	77.7	77.7	79.5	80.7	81.8	84.0	86.3	89.3	95.2	100.1
77.5°	58.0	57.8	58.2	58.6	59.8	61.2	61.8	63.9	66.6	69.4	73.5
80°	44.8	45.6	45.9	46.7	46.7	47.4	47.8	50.4	52.3	54.2	56.8
82.5°	34.7	34.8	34.9	35.0	35.3	35.8	36.7	37.6	38.2	39.8	41.8
85°	20.2	19.8	19.8	20.5	20.2	20.2	20.9	21.7	21.7	22.0	23.2
87.5°	13.5	13.4	13.6	13.2	13.1	13.3	13.0	12.5	12.6	12.6	12.5
90°	28.7	28.2	27.8	27.3	26.8	26.0	24.8	23.6	22.4	21.3	19.4
92.5°	28.7	28.4	28.1	27.9	27.6	27.1	26.5	25.9	25.3	24.7	23.7
95°	45.7	45.9	46.2	46.4	46.7	46.2	45.0	43.8	42.6	41.5	39.8
97.5°	61.0	60.7	60.5	60.2	59.9	59.3	58.3	57.4	56.4	55.5	51.7
100°	71.2	70.8	70.3	69.8	69.3	68.2	66.3	64.4	62.5	60.6	56.6
102.5°	76.3	75.7	75.0	74.3	73.7	72.1	69.7	67.2	64.8	62.3	59.9
105°	80.8	79.8	78.9	78.0	77.0	75.2	72.6	70.0	67.4	64.8	62.3
107.5°	83.1	82.2	81.2	80.3	79.4	80.2	82.8	85.5	88.1	90.8	95.9
110°	84.0	83.0	82.1	81.1	80.2	91.5	115.2	138.8	162.4	186.0	254.3



TEST NUMBER: P331321

CATALOG NUMBER: SA2XXDIP-C485D1080U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	84.8	84.1	83.3	82.6	81.8	124.5	210.7	296.9	383.1	469.2	486.1
115°	87.2	104.2	121.2	138.2	155.2	218.4	327.8	437.1	546.5	655.9	650.0
117.5°	355.9	411.8	467.7	523.6	579.5	620.7	647.1	673.6	700.0	726.5	722.4
120°	648.5	680.3	712.2	744.1	776.0	790.6	787.7	784.9	782.0	779.2	775.0
122.5°	809.2	815.4	821.6	827.8	833.9	836.2	834.5	832.8	831.1	829.4	824.8
125°	908.9	908.2	907.5	906.8	906.1	904.9	903.2	901.6	899.9	898.3	893.8
127.5°	971.8	971.7	971.6	971.4	971.3	970.0	967.6	965.2	962.8	960.4	957.0
130°	1011.0	1011.2	1011.4	1011.7	1011.9	1010.7	1008.1	1005.5	1002.9	1000.3	997.7
132.5°	1049.2	1049.5	1049.7	1049.9	1050.2	1049.2	1047.0	1044.7	1042.5	1040.3	1037.7
135°	1104.5	1105.0	1105.4	1105.9	1106.4	1105.4	1103.1	1100.7	1098.4	1096.0	1093.9
137.5°	1154.9	1155.7	1156.5	1157.3	1158.1	1157.3	1155.0	1152.7	1150.4	1148.1	1145.7
140°	1186.4	1187.5	1188.7	1189.9	1191.1	1190.6	1188.5	1186.4	1184.2	1182.1	1179.5
142.5°	1217.0	1218.2	1219.3	1220.5	1221.7	1221.3	1219.4	1217.4	1215.5	1213.6	1210.6
145°	1259.7	1260.9	1262.1	1263.3	1264.4	1264.2	1262.5	1260.9	1259.2	1257.6	1253.6
147.5°	1297.3	1298.3	1299.3	1300.3	1301.3	1301.2	1300.0	1298.7	1297.5	1296.3	1292.3
150°	1320.3	1321.5	1322.7	1323.8	1325.0	1324.9	1323.5	1322.1	1320.7	1319.2	1315.5
152.5°	1339.9	1341.4	1343.0	1344.5	1346.1	1346.2	1344.8	1343.3	1341.9	1340.5	1336.9
155°	1367.1	1369.0	1370.9	1372.7	1374.6	1374.9	1373.5	1372.0	1370.6	1369.2	1366.4
157.5°	1391.9	1393.8	1395.6	1397.5	1399.3	1399.4	1397.8	1396.2	1394.6	1393.0	1391.0
160°	1406.4	1408.1	1409.7	1411.4	1413.0	1413.1	1411.7	1410.3	1408.9	1407.5	1406.1
162.5°	1418.3	1420.3	1422.4	1424.4	1426.4	1426.7	1425.0	1423.4	1421.8	1420.2	1419.0
165°	1436.2	1437.8	1439.5	1441.1	1442.8	1442.8	1441.1	1439.5	1437.8	1436.2	1435.5
167.5°	1447.4	1449.6	1451.7	1453.8	1455.9	1456.2	1454.5	1452.9	1451.2	1449.6	1448.9
170°	1454.2	1456.4	1458.5	1460.6	1462.7	1463.0	1461.3	1459.7	1458.0	1456.4	1455.9
172.5°	1459.3	1461.5	1463.6	1465.7	1467.9	1468.1	1466.4	1464.8	1463.1	1461.5	1461.0
175°	1463.8	1466.2	1468.5	1470.9	1473.3	1473.6	1472.0	1470.3	1468.7	1467.0	1466.5
177.5°	1466.6	1468.3	1470.0	1471.7	1473.4	1473.6	1472.2	1470.9	1469.6	1468.3	1468.1
180°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1



TEST NUMBER: P331321

CATALOG NUMBER: SA2XXDIP-C485D1080U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7
2.5°	997.1	994.7	993.2	987.9	983.1	978.3	976.8	977.4	970.8	964.6	961.9
5°	1036.0	1028.5	1021.4	1011.3	999.4	986.3	979.6	974.4	961.3	947.1	938.9
7.5°	1070.8	1060.1	1046.4	1027.5	1010.1	989.5	976.4	964.9	945.7	925.7	913.5
10°	1092.0	1077.4	1059.9	1036.7	1015.4	990.4	972.9	955.3	932.9	909.0	894.1
12.5°	1110.2	1090.6	1073.3	1043.6	1018.4	987.1	966.3	941.6	918.0	889.6	874.9
15°	1153.6	1117.4	1084.5	1050.9	1019.9	976.2	953.1	919.8	888.8	853.7	836.9
17.5°	1187.1	1146.4	1094.7	1052.0	1015.8	967.4	933.4	893.6	856.9	816.8	794.0
20°	1206.3	1159.6	1103.9	1053.2	1009.8	954.6	917.6	876.9	833.9	788.7	764.1
22.5°	1217.6	1168.6	1113.5	1048.7	997.9	944.1	897.6	853.0	809.4	760.7	734.8
25°	1221.2	1176.4	1118.1	1044.9	982.9	922.1	866.0	822.7	770.1	724.5	686.8
27.5°	1203.4	1171.3	1115.3	1037.9	965.7	894.5	832.1	783.0	727.4	678.0	640.0
30°	1181.6	1162.9	1108.4	1030.7	951.9	875.4	806.7	751.0	695.8	645.7	606.9
32.5°	1147.9	1143.8	1095.9	1020.6	937.3	851.2	780.1	723.8	662.6	613.4	576.4
35°	1081.5	1099.5	1069.2	997.9	909.7	816.8	739.8	675.6	612.1	565.0	530.3
37.5°	992.7	1037.2	1029.3	964.6	872.5	779.3	694.3	627.2	566.7	519.2	485.1
40°	931.4	988.2	996.4	939.2	846.3	750.3	660.3	593.4	534.4	491.1	456.7
42.5°	865.7	932.0	954.6	908.8	817.6	719.8	629.8	560.6	502.2	460.0	429.6
45°	755.5	843.3	884.0	857.8	769.7	669.6	577.0	506.8	453.8	414.2	390.6
47.5°	652.5	748.4	803.2	793.9	716.4	617.3	525.8	458.4	406.8	375.2	354.1
50°	579.6	678.2	744.3	747.3	678.2	580.0	488.1	424.6	377.2	347.7	330.5
52.5°	516.3	610.4	682.5	698.3	635.5	541.1	454.3	391.2	349.4	322.3	306.9
55°	433.6	513.1	593.1	622.2	571.8	482.1	401.8	346.2	307.0	288.3	274.9
57.5°	360.5	426.8	500.6	532.8	501.7	425.0	349.7	301.4	269.6	253.2	242.9
60°	321.9	374.2	439.9	478.4	451.5	383.2	317.4	271.5	245.4	230.8	221.1
62.5°	286.1	332.4	387.9	423.1	408.5	344.0	285.2	244.6	222.1	208.4	201.4
65°	236.0	272.6	315.6	348.1	338.4	289.4	241.3	206.5	188.6	177.8	172.2
67.5°	194.3	220.8	250.6	279.0	271.2	236.5	197.9	170.8	157.4	148.1	144.8
70°	168.1	188.2	214.7	237.5	231.2	202.8	172.2	149.0	137.4	129.6	126.2
72.5°	143.0	159.5	179.8	198.4	194.1	170.5	145.0	127.5	118.6	111.4	108.6
75°	107.9	120.6	133.0	145.3	144.2	125.9	110.9	97.5	90.4	84.8	83.7
77.5°	79.7	86.8	95.2	102.5	100.5	90.0	78.3	70.6	65.4	61.6	61.0
80°	60.9	65.0	71.0	76.2	73.6	69.1	59.8	54.2	50.4	46.7	45.2
82.5°	44.1	48.3	51.8	54.7	52.7	48.5	42.7	38.9	36.7	34.1	33.5
85°	23.2	25.4	26.9	27.6	26.9	24.3	21.7	20.2	18.3	17.2	16.8
87.5°	12.5	12.1	11.7	11.9	10.4	9.9	8.2	6.8	7.0	7.2	7.1
90°	17.5	15.6	13.7	11.5	8.9	6.3	3.7	1.1	3.7	6.3	8.9
92.5°	22.8	21.8	20.9	20.5	20.8	21.0	21.2	21.5	21.2	21.0	20.8
95°	38.2	36.5	34.8	37.9	45.7	53.5	61.3	69.1	61.3	53.5	45.7
97.5°	47.8	44.0	40.2	49.3	71.2	93.2	115.2	137.1	115.2	93.2	71.2
100°	52.6	48.5	44.5	58.7	91.1	123.4	155.8	188.2	155.8	123.4	91.1
102.5°	129.5	163.1	196.7	216.9	223.7	230.6	237.4	244.3	237.4	230.6	223.7
105°	193.8	258.3	322.8	351.5	344.4	337.3	330.3	323.2	330.3	337.3	344.4
107.5°	245.5	322.8	400.2	436.0	430.2	424.5	418.8	413.1	418.8	424.5	430.2
110°	322.6	390.8	459.1	490.8	485.8	480.9	475.9	470.9	475.9	480.9	485.8





TEST NUMBER: P331321

CATALOG NUMBER: SA2XXDIP-C485D1080U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	503.0	519.8	536.7	542.9	538.5	534.1	529.8	525.4	529.8	534.1	538.5
115°	644.1	638.2	632.3	627.3	623.3	619.3	615.3	611.3	615.3	619.3	623.3
117.5°	718.4	714.3	710.2	706.0	701.5	697.0	692.5	688.0	692.5	697.0	701.5
120°	770.7	766.5	762.2	758.3	754.8	751.2	747.7	744.1	747.7	751.2	754.8
122.5°	820.1	815.5	810.9	806.7	803.0	799.2	795.5	791.8	795.5	799.2	803.0
125°	889.3	884.8	880.3	876.5	873.5	870.4	867.3	864.3	867.3	870.4	873.5
127.5°	953.6	950.3	946.9	943.6	940.2	936.8	933.4	930.0	933.4	936.8	940.2
130°	995.1	992.5	989.9	986.7	983.0	979.2	975.4	971.6	975.4	979.2	983.0
132.5°	1035.1	1032.5	1029.9	1027.0	1023.8	1020.6	1017.4	1014.1	1017.4	1020.6	1023.8
135°	1091.7	1089.6	1087.5	1084.5	1080.8	1077.0	1073.2	1069.4	1073.2	1077.0	1080.8
137.5°	1143.3	1140.9	1138.4	1135.9	1133.3	1130.6	1128.0	1125.3	1128.0	1130.6	1133.3
140°	1176.9	1174.3	1171.7	1169.5	1167.6	1165.7	1163.8	1161.9	1163.8	1165.7	1167.6
142.5°	1207.6	1204.6	1201.7	1199.3	1197.6	1195.9	1194.2	1192.5	1194.2	1195.9	1197.6
145°	1249.5	1245.5	1241.5	1239.6	1239.9	1240.1	1240.3	1240.6	1240.3	1240.1	1239.9
147.5°	1288.3	1284.4	1280.4	1278.9	1279.8	1280.7	1281.6	1282.5	1281.6	1280.7	1279.8
150°	1311.7	1307.9	1304.1	1303.1	1304.7	1306.4	1308.0	1309.7	1308.0	1306.4	1304.7
152.5°	1333.3	1329.7	1326.1	1325.3	1327.1	1328.9	1330.8	1332.6	1330.8	1328.9	1327.1
155°	1363.5	1360.7	1357.9	1357.5	1359.6	1361.8	1363.9	1366.0	1363.9	1361.8	1359.6
157.5°	1389.0	1387.1	1385.1	1385.0	1386.8	1388.6	1390.4	1392.2	1390.4	1388.6	1386.8
160°	1404.6	1403.2	1401.8	1401.8	1403.2	1404.6	1406.1	1407.5	1406.1	1404.6	1403.2
162.5°	1417.8	1416.5	1415.3	1415.4	1416.8	1418.2	1419.7	1421.1	1419.7	1418.2	1416.8
165°	1434.8	1434.0	1433.3	1433.7	1435.1	1436.5	1437.9	1439.4	1437.9	1436.5	1435.1
167.5°	1448.2	1447.6	1446.9	1447.3	1448.7	1450.1	1451.6	1453.0	1451.6	1450.1	1448.7
170°	1455.4	1455.0	1454.5	1455.0	1456.4	1457.8	1459.2	1460.6	1459.2	1457.8	1456.4
172.5°	1460.5	1460.1	1459.6	1460.1	1461.5	1462.9	1464.3	1465.7	1464.3	1462.9	1461.5
175°	1466.1	1465.6	1465.1	1465.7	1467.4	1469.0	1470.7	1472.3	1470.7	1469.0	1467.4
177.5°	1467.9	1467.7	1467.5	1468.1	1469.4	1470.7	1472.1	1473.4	1472.1	1470.7	1469.4
180°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1



TEST NUMBER: P331321

CATALOG NUMBER: SA2XXDIP-C485D1080U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7
2.5°	958.9	957.1	950.8	947.5	942.2	937.1	933.8	935.3	936.5	935.9	935.0
5°	931.4	924.3	913.5	904.1	897.4	885.1	879.9	877.3	875.0	872.4	869.8
7.5°	898.7	887.5	872.0	858.7	846.1	830.8	822.1	816.8	811.4	805.5	800.3
10°	875.4	859.7	843.3	824.6	809.7	795.8	783.5	775.3	767.8	760.7	755.5
12.5°	850.9	832.8	812.5	787.0	770.5	750.7	748.9	734.4	722.7	718.3	712.2
15°	811.9	786.5	760.7	730.5	717.4	699.5	688.3	677.1	667.0	659.9	658.0
17.5°	767.6	734.7	709.1	687.4	666.0	647.6	637.3	628.3	620.0	610.5	609.3
20°	733.8	705.5	677.5	658.4	636.4	617.7	605.0	596.0	588.9	583.3	578.5
22.5°	701.9	670.8	645.2	624.3	602.6	587.5	577.5	568.9	563.0	556.8	552.2
25°	650.6	626.3	598.3	574.8	556.8	547.1	538.9	531.4	527.7	523.6	518.4
27.5°	605.7	578.7	552.5	534.3	518.5	509.9	504.1	499.0	495.5	493.1	490.1
30°	574.0	546.7	526.2	508.3	495.2	486.6	482.9	479.9	475.8	474.3	472.8
32.5°	543.5	519.0	501.4	485.9	473.4	467.8	464.4	461.7	458.5	457.0	454.0
35°	500.4	479.9	462.7	454.1	444.0	439.2	436.6	432.8	429.9	428.4	428.0
37.5°	459.9	442.0	430.7	419.7	415.4	412.4	408.9	406.3	405.4	405.2	404.8
40°	433.6	419.0	408.9	400.0	398.1	393.6	390.6	388.4	388.4	388.8	388.4
42.5°	409.7	396.6	387.7	380.0	377.8	375.1	372.1	372.0	372.6	373.8	372.6
45°	373.5	364.1	357.8	354.0	349.9	347.3	346.9	348.1	348.4	348.8	349.9
47.5°	340.1	333.9	328.2	324.1	322.3	321.8	321.4	323.3	325.1	325.8	327.5
50°	320.4	313.3	308.5	305.9	304.4	303.6	304.4	306.6	308.1	310.0	311.1
52.5°	298.3	293.3	290.0	287.9	287.3	287.8	287.9	290.5	292.9	293.5	294.1
55°	267.8	264.0	263.3	259.9	261.4	261.0	262.9	264.4	266.6	268.9	269.3
57.5°	237.3	234.3	232.3	232.6	233.0	234.7	236.2	238.9	241.3	243.6	243.9
60°	217.0	215.5	214.4	214.4	215.1	217.4	219.2	221.8	223.3	224.8	225.9
62.5°	198.5	197.0	195.8	196.4	198.4	199.7	201.9	203.3	204.8	206.3	206.8
65°	169.2	168.4	169.6	170.3	170.7	172.5	175.2	176.3	177.8	178.5	181.1
67.5°	142.2	142.4	142.2	143.3	145.4	145.9	148.3	151.0	151.3	152.7	154.4
70°	124.0	124.7	125.5	126.2	128.1	128.8	130.7	131.8	133.3	134.4	135.6
72.5°	107.3	107.4	108.2	108.0	109.6	111.2	112.8	113.9	115.4	116.8	117.9
75°	82.5	82.5	83.3	83.7	85.5	87.4	87.0	87.8	89.3	90.8	91.5
77.5°	60.3	59.5	60.3	60.6	61.2	62.8	63.1	64.2	65.9	65.4	66.2
80°	45.9	44.8	45.9	46.3	46.3	48.2	48.2	48.9	50.0	48.9	50.0
82.5°	32.8	32.3	33.1	33.2	33.8	33.8	34.4	34.6	35.7	35.2	35.7
85°	16.4	16.1	16.4	16.1	16.4	16.8	16.8	16.4	16.4	17.2	16.1
87.5°	7.4	7.5	7.6	8.0	8.1	8.1	8.1	8.3	8.5	8.2	8.4
90°	11.5	13.7	15.6	17.5	19.4	21.3	22.4	23.6	24.8	26.0	26.8
92.5°	20.5	20.9	21.8	22.8	23.7	24.7	25.3	25.9	26.5	27.1	27.6
95°	37.9	34.8	36.5	38.2	39.8	41.5	42.6	43.8	45.0	46.2	46.7
97.5°	49.3	40.2	44.0	47.8	51.7	55.5	56.4	57.4	58.3	59.3	59.9
100°	58.7	44.5	48.5	52.6	56.6	60.6	62.5	64.4	66.3	68.2	69.3
102.5°	216.9	196.7	163.1	129.5	95.9	62.3	64.8	67.2	69.7	72.1	73.7
105°	351.5	322.8	258.3	193.8	129.3	64.8	67.4	70.0	72.6	75.2	77.0
107.5°	436.0	400.2	322.8	245.5	168.1	90.8	88.1	85.5	82.8	80.2	79.4
110°	490.8	459.1	390.8	322.6	254.3	186.0	162.4	138.8	115.2	91.5	80.2



TEST NUMBER: P331321

CATALOG NUMBER: SA2XXDIP-C485D1080U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	542.9	536.7	519.8	503.0	486.1	469.2	383.1	296.9	210.7	124.5	81.8
115°	627.3	632.3	638.2	644.1	650.0	655.9	546.5	437.1	327.8	218.4	155.2
117.5°	706.0	710.2	714.3	718.4	722.4	726.5	700.0	673.6	647.1	620.7	579.5
120°	758.3	762.2	766.5	770.7	775.0	779.2	782.0	784.9	787.7	790.6	776.0
122.5°	806.7	810.9	815.5	820.1	824.8	829.4	831.1	832.8	834.5	836.2	833.9
125°	876.5	880.3	884.8	889.3	893.8	898.3	899.9	901.6	903.2	904.9	906.1
127.5°	943.6	946.9	950.3	953.6	957.0	960.4	962.8	965.2	967.6	970.0	971.3
130°	986.7	989.9	992.5	995.1	997.7	1000.3	1002.9	1005.5	1008.1	1010.7	1011.9
132.5°	1027.0	1029.9	1032.5	1035.1	1037.7	1040.3	1042.5	1044.7	1047.0	1049.2	1050.2
135°	1084.5	1087.5	1089.6	1091.7	1093.9	1096.0	1098.4	1100.7	1103.1	1105.4	1106.4
137.5°	1135.9	1138.4	1140.9	1143.3	1145.7	1148.1	1150.4	1152.7	1155.0	1157.3	1158.1
140°	1169.5	1171.7	1174.3	1176.9	1179.5	1182.1	1184.2	1186.4	1188.5	1190.6	1191.1
142.5°	1199.3	1201.7	1204.6	1207.6	1210.6	1213.6	1215.5	1217.4	1219.4	1221.3	1221.7
145°	1239.6	1241.5	1245.5	1249.5	1253.6	1257.6	1259.2	1260.9	1262.5	1264.2	1264.4
147.5°	1278.9	1280.4	1284.4	1288.3	1292.3	1296.3	1297.5	1298.7	1300.0	1301.2	1301.3
150°	1303.1	1304.1	1307.9	1311.7	1315.5	1319.2	1320.7	1322.1	1323.5	1324.9	1325.0
152.5°	1325.3	1326.1	1329.7	1333.3	1336.9	1340.5	1341.9	1343.3	1344.8	1346.2	1346.1
155°	1357.5	1357.9	1360.7	1363.5	1366.4	1369.2	1370.6	1372.0	1373.5	1374.9	1374.6
157.5°	1385.0	1385.1	1387.1	1389.0	1391.0	1393.0	1394.6	1396.2	1397.8	1399.4	1399.3
160°	1401.8	1401.8	1403.2	1404.6	1406.1	1407.5	1408.9	1410.3	1411.7	1413.1	1413.0
162.5°	1415.4	1415.3	1416.5	1417.8	1419.0	1420.2	1421.8	1423.4	1425.0	1426.7	1426.4
165°	1433.7	1433.3	1434.0	1434.8	1435.5	1436.2	1437.8	1439.5	1441.1	1442.8	1442.8
167.5°	1447.3	1446.9	1447.6	1448.2	1448.9	1449.6	1451.2	1452.9	1454.5	1456.2	1455.9
170°	1455.0	1454.5	1455.0	1455.4	1455.9	1456.4	1458.0	1459.7	1461.3	1463.0	1462.7
172.5°	1460.1	1459.6	1460.1	1460.5	1461.0	1461.5	1463.1	1464.8	1466.4	1468.1	1467.9
175°	1465.7	1465.1	1465.6	1466.1	1466.5	1467.0	1468.7	1470.3	1472.0	1473.6	1473.3
177.5°	1468.1	1467.5	1467.7	1467.9	1468.1	1468.3	1469.6	1470.9	1472.2	1473.6	1473.4
180°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1



TEST NUMBER: P331321

CATALOG NUMBER: SA2XXDIP-C485D1080U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7
2.5°	932.0	931.4	931.4	928.7	931.4	931.4	932.0	935.0	935.9	936.5	935.3
5°	864.6	863.4	861.6	863.4	861.6	863.4	864.6	869.8	872.4	875.0	877.3
7.5°	797.9	793.4	792.7	788.3	792.7	793.4	797.9	800.3	805.5	811.4	816.8
10°	749.2	746.2	745.8	738.7	745.8	746.2	749.2	755.5	760.7	767.8	775.3
12.5°	712.1	704.9	706.4	702.3	706.4	704.9	712.1	712.2	718.3	722.7	734.4
15°	647.9	647.9	646.5	640.1	646.5	647.9	647.9	658.0	659.9	667.0	677.1
17.5°	601.9	601.1	597.5	599.3	597.5	601.1	601.9	609.3	610.5	620.0	628.3
20°	574.4	572.1	567.7	567.7	567.7	572.1	574.4	578.5	583.3	588.9	596.0
22.5°	548.4	548.2	543.5	545.0	543.5	548.2	548.4	552.2	556.8	563.0	568.9
25°	518.0	515.0	512.8	513.9	512.8	515.0	518.0	518.4	523.6	527.7	531.4
27.5°	489.2	487.5	487.4	484.3	487.4	487.5	489.2	490.1	493.1	495.5	499.0
30°	472.4	468.7	469.4	467.6	469.4	468.7	472.4	472.8	474.3	475.8	479.9
32.5°	453.3	452.0	451.2	449.6	451.2	452.0	453.3	454.0	457.0	458.5	461.7
35°	427.2	427.6	425.7	426.5	425.7	427.6	427.2	428.0	428.4	429.9	432.8
37.5°	404.5	405.7	404.8	405.0	404.8	405.7	404.5	404.8	405.2	405.4	406.3
40°	389.5	389.5	389.5	390.6	389.5	389.5	389.5	388.4	388.8	388.4	388.4
42.5°	375.2	374.6	374.0	373.9	374.0	374.6	375.2	372.6	373.8	372.6	372.0
45°	350.7	351.8	352.2	350.3	352.2	351.8	350.7	349.9	348.8	348.4	348.1
47.5°	328.5	328.6	328.5	330.1	328.5	328.6	328.5	327.5	325.8	325.1	323.3
50°	313.0	312.2	313.0	312.2	313.0	312.2	313.0	311.1	310.0	308.1	306.6
52.5°	296.5	296.7	296.2	296.1	296.2	296.7	296.5	294.1	293.5	292.9	290.5
55°	270.8	271.5	271.1	271.1	271.1	271.5	270.8	269.3	268.9	266.6	264.4
57.5°	244.1	244.8	245.3	243.6	245.3	244.8	244.1	243.9	243.6	241.3	238.9
60°	225.6	227.4	227.1	226.3	227.1	227.4	225.6	225.9	224.8	223.3	221.8
62.5°	208.5	209.2	209.1	209.0	209.1	209.2	208.5	206.8	206.3	204.8	203.3
65°	182.2	183.0	181.9	183.0	181.9	183.0	182.2	181.1	178.5	177.8	176.3
67.5°	153.9	154.2	155.0	155.5	155.0	154.2	153.9	154.4	152.7	151.3	151.0
70°	136.3	135.9	137.1	138.2	137.1	135.9	136.3	135.6	134.4	133.3	131.8
72.5°	117.8	118.6	118.2	119.1	118.2	118.6	117.8	117.9	116.8	115.4	113.9
75°	90.8	91.9	91.5	92.6	91.5	91.9	90.8	91.5	90.8	89.3	87.8
77.5°	65.6	65.7	65.6	66.2	65.6	65.7	65.6	66.2	65.4	65.9	64.2
80°	50.0	49.3	48.5	50.0	48.5	49.3	50.0	50.0	48.9	50.0	48.9
82.5°	34.8	35.3	34.5	34.5	34.5	35.3	34.8	35.7	35.2	35.7	34.6
85°	16.1	15.7	14.9	14.9	14.9	15.7	16.1	16.1	17.2	16.4	16.4
87.5°	8.4	8.2	8.3	8.1	8.3	8.2	8.4	8.4	8.2	8.5	8.3
90°	27.3	27.8	28.2	28.7	28.2	27.8	27.3	26.8	26.0	24.8	23.6
92.5°	27.9	28.1	28.4	28.7	28.4	28.1	27.9	27.6	27.1	26.5	25.9
95°	46.4	46.2	45.9	45.7	45.9	46.2	46.4	46.7	46.2	45.0	43.8
97.5°	60.2	60.5	60.7	61.0	60.7	60.5	60.2	59.9	59.3	58.3	57.4
100°	69.8	70.3	70.8	71.2	70.8	70.3	69.8	69.3	68.2	66.3	64.4
102.5°	74.3	75.0	75.7	76.3	75.7	75.0	74.3	73.7	72.1	69.7	67.2
105°	78.0	78.9	79.8	80.8	79.8	78.9	78.0	77.0	75.2	72.6	70.0
107.5°	80.3	81.2	82.2	83.1	82.2	81.2	80.3	79.4	80.2	82.8	85.5
110°	81.1	82.1	83.0	84.0	83.0	82.1	81.1	80.2	91.5	115.2	138.8



TEST NUMBER: P331321

CATALOG NUMBER: SA2XXDIP-C485D1080U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	82.6	83.3	84.1	84.8	84.1	83.3	82.6	81.8	124.5	210.7	296.9
115°	138.2	121.2	104.2	87.2	104.2	121.2	138.2	155.2	218.4	327.8	437.1
117.5°	523.6	467.7	411.8	355.9	411.8	467.7	523.6	579.5	620.7	647.1	673.6
120°	744.1	712.2	680.3	648.5	680.3	712.2	744.1	776.0	790.6	787.7	784.9
122.5°	827.8	821.6	815.4	809.2	815.4	821.6	827.8	833.9	836.2	834.5	832.8
125°	906.8	907.5	908.2	908.9	908.2	907.5	906.8	906.1	904.9	903.2	901.6
127.5°	971.4	971.6	971.7	971.8	971.7	971.6	971.4	971.3	970.0	967.6	965.2
130°	1011.7	1011.4	1011.2	1011.0	1011.2	1011.4	1011.7	1011.9	1010.7	1008.1	1005.5
132.5°	1049.9	1049.7	1049.5	1049.2	1049.5	1049.7	1049.9	1050.2	1049.2	1047.0	1044.7
135°	1105.9	1105.4	1105.0	1104.5	1105.0	1105.4	1105.9	1106.4	1105.4	1103.1	1100.7
137.5°	1157.3	1156.5	1155.7	1154.9	1155.7	1156.5	1157.3	1158.1	1157.3	1155.0	1152.7
140°	1189.9	1188.7	1187.5	1186.4	1187.5	1188.7	1189.9	1191.1	1190.6	1188.5	1186.4
142.5°	1220.5	1219.3	1218.2	1217.0	1218.2	1219.3	1220.5	1221.7	1221.3	1219.4	1217.4
145°	1263.3	1262.1	1260.9	1259.7	1260.9	1262.1	1263.3	1264.4	1264.2	1262.5	1260.9
147.5°	1300.3	1299.3	1298.3	1297.3	1298.3	1299.3	1300.3	1301.3	1301.2	1300.0	1298.7
150°	1323.8	1322.7	1321.5	1320.3	1321.5	1322.7	1323.8	1325.0	1324.9	1323.5	1322.1
152.5°	1344.5	1343.0	1341.4	1339.9	1341.4	1343.0	1344.5	1346.1	1346.2	1344.8	1343.3
155°	1372.7	1370.9	1369.0	1367.1	1369.0	1370.9	1372.7	1374.6	1374.9	1373.5	1372.0
157.5°	1397.5	1395.6	1393.8	1391.9	1393.8	1395.6	1397.5	1399.3	1399.4	1397.8	1396.2
160°	1411.4	1409.7	1408.1	1406.4	1408.1	1409.7	1411.4	1413.0	1413.1	1411.7	1410.3
162.5°	1424.4	1422.4	1420.3	1418.3	1420.3	1422.4	1424.4	1426.4	1426.7	1425.0	1423.4
165°	1441.1	1439.5	1437.8	1436.2	1437.8	1439.5	1441.1	1442.8	1442.8	1441.1	1439.5
167.5°	1453.8	1451.7	1449.6	1447.4	1449.6	1451.7	1453.8	1455.9	1456.2	1454.5	1452.9
170°	1460.6	1458.5	1456.4	1454.2	1456.4	1458.5	1460.6	1462.7	1463.0	1461.3	1459.7
172.5°	1465.7	1463.6	1461.5	1459.3	1461.5	1463.6	1465.7	1467.9	1468.1	1466.4	1464.8
175°	1470.9	1468.5	1466.2	1463.8	1466.2	1468.5	1470.9	1473.3	1473.6	1472.0	1470.3
177.5°	1471.7	1470.0	1468.3	1466.6	1468.3	1470.0	1471.7	1473.4	1473.6	1472.2	1470.9
180°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1



TEST NUMBER: P331321

CATALOG NUMBER: SA2XXDIP-C485D1080U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7
2.5°	933.8	937.1	942.2	947.5	950.8	957.1	958.9	961.9	964.6	970.8	977.4
5°	879.9	885.1	897.4	904.1	913.5	924.3	931.4	938.9	947.1	961.3	974.4
7.5°	822.1	830.8	846.1	858.7	872.0	887.5	898.7	913.5	925.7	945.7	964.9
10°	783.5	795.8	809.7	824.6	843.3	859.7	875.4	894.1	909.0	932.9	955.3
12.5°	748.9	750.7	770.5	787.0	812.5	832.8	850.9	874.9	889.6	918.0	941.6
15°	688.3	699.5	717.4	730.5	760.7	786.5	811.9	836.9	853.7	888.8	919.8
17.5°	637.3	647.6	666.0	687.4	709.1	734.7	767.6	794.0	816.8	856.9	893.6
20°	605.0	617.7	636.4	658.4	677.5	705.5	733.8	764.1	788.7	833.9	876.9
22.5°	577.5	587.5	602.6	624.3	645.2	670.8	701.9	734.8	760.7	809.4	853.0
25°	538.9	547.1	556.8	574.8	598.3	626.3	650.6	686.8	724.5	770.1	822.7
27.5°	504.1	509.9	518.5	534.3	552.5	578.7	605.7	640.0	678.0	727.4	783.0
30°	482.9	486.6	495.2	508.3	526.2	546.7	574.0	606.9	645.7	695.8	751.0
32.5°	464.4	467.8	473.4	485.9	501.4	519.0	543.5	576.4	613.4	662.6	723.8
35°	436.6	439.2	444.0	454.1	462.7	479.9	500.4	530.3	565.0	612.1	675.6
37.5°	408.9	412.4	415.4	419.7	430.7	442.0	459.9	485.1	519.2	566.7	627.2
40°	390.6	393.6	398.1	400.0	408.9	419.0	433.6	456.7	491.1	534.4	593.4
42.5°	372.1	375.1	377.8	380.0	387.7	396.6	409.7	429.6	460.0	502.2	560.6
45°	346.9	347.3	349.9	354.0	357.8	364.1	373.5	390.6	414.2	453.8	506.8
47.5°	321.4	321.8	322.3	324.1	328.2	333.9	340.1	354.1	375.2	406.8	458.4
50°	304.4	303.6	304.4	305.9	308.5	313.3	320.4	330.5	347.7	377.2	424.6
52.5°	287.9	287.8	287.3	287.9	290.0	293.3	298.3	306.9	322.3	349.4	391.2
55°	262.9	261.0	261.4	259.9	263.3	264.0	267.8	274.9	288.3	307.0	346.2
57.5°	236.2	234.7	233.0	232.6	232.3	234.3	237.3	242.9	253.2	269.6	301.4
60°	219.2	217.4	215.1	214.4	214.4	215.5	217.0	221.1	230.8	245.4	271.5
62.5°	201.9	199.7	198.4	196.4	195.8	197.0	198.5	201.4	208.4	222.1	244.6
65°	175.2	172.5	170.7	170.3	169.6	168.4	169.2	172.2	177.8	188.6	206.5
67.5°	148.3	145.9	145.4	143.3	142.2	142.4	142.2	144.8	148.1	157.4	170.8
70°	130.7	128.8	128.1	126.2	125.5	124.7	124.0	126.2	129.6	137.4	149.0
72.5°	112.8	111.2	109.6	108.0	108.2	107.4	107.3	108.6	111.4	118.6	127.5
75°	87.0	87.4	85.5	83.7	83.3	82.5	82.5	83.7	84.8	90.4	97.5
77.5°	63.1	62.8	61.2	60.6	60.3	59.5	60.3	61.0	61.6	65.4	70.6
80°	48.2	48.2	46.3	46.3	45.9	44.8	45.9	45.2	46.7	50.4	54.2
82.5°	34.4	33.8	33.8	33.2	33.1	32.3	32.8	33.5	34.1	36.7	38.9
85°	16.8	16.8	16.4	16.1	16.4	16.1	16.4	16.8	17.2	18.3	20.2
87.5°	8.1	8.1	8.1	8.0	7.6	7.5	7.4	7.1	7.2	7.0	6.8
90°	22.4	21.3	19.4	17.5	15.6	13.7	11.5	8.9	6.3	3.7	1.1
92.5°	25.3	24.7	23.7	22.8	21.8	20.9	20.5	20.8	21.0	21.2	21.5
95°	42.6	41.5	39.8	38.2	36.5	34.8	37.9	45.7	53.5	61.3	69.1
97.5°	56.4	55.5	51.7	47.8	44.0	40.2	49.3	71.2	93.2	115.2	137.1
100°	62.5	60.6	56.6	52.6	48.5	44.5	58.7	91.1	123.4	155.8	188.2
102.5°	64.8	62.3	95.9	129.5	163.1	196.7	216.9	223.7	230.6	237.4	244.3
105°	67.4	64.8	129.3	193.8	258.3	322.8	351.5	344.4	337.3	330.3	323.2
107.5°	88.1	90.8	168.1	245.5	322.8	400.2	436.0	430.2	424.5	418.8	413.1
110°	162.4	186.0	254.3	322.6	390.8	459.1	490.8	485.8	480.9	475.9	470.9



TEST NUMBER: P331321

CATALOG NUMBER: SA2XXDIP-C485D1080U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	383.1	469.2	486.1	503.0	519.8	536.7	542.9	538.5	534.1	529.8	525.4
115°	546.5	655.9	650.0	644.1	638.2	632.3	627.3	623.3	619.3	615.3	611.3
117.5°	700.0	726.5	722.4	718.4	714.3	710.2	706.0	701.5	697.0	692.5	688.0
120°	782.0	779.2	775.0	770.7	766.5	762.2	758.3	754.8	751.2	747.7	744.1
122.5°	831.1	829.4	824.8	820.1	815.5	810.9	806.7	803.0	799.2	795.5	791.8
125°	899.9	898.3	893.8	889.3	884.8	880.3	876.5	873.5	870.4	867.3	864.3
127.5°	962.8	960.4	957.0	953.6	950.3	946.9	943.6	940.2	936.8	933.4	930.0
130°	1002.9	1000.3	997.7	995.1	992.5	989.9	986.7	983.0	979.2	975.4	971.6
132.5°	1042.5	1040.3	1037.7	1035.1	1032.5	1029.9	1027.0	1023.8	1020.6	1017.4	1014.1
135°	1098.4	1096.0	1093.9	1091.7	1089.6	1087.5	1084.5	1080.8	1077.0	1073.2	1069.4
137.5°	1150.4	1148.1	1145.7	1143.3	1140.9	1138.4	1135.9	1133.3	1130.6	1128.0	1125.3
140°	1184.2	1182.1	1179.5	1176.9	1174.3	1171.7	1169.5	1167.6	1165.7	1163.8	1161.9
142.5°	1215.5	1213.6	1210.6	1207.6	1204.6	1201.7	1199.3	1197.6	1195.9	1194.2	1192.5
145°	1259.2	1257.6	1253.6	1249.5	1245.5	1241.5	1239.6	1239.9	1240.1	1240.3	1240.6
147.5°	1297.5	1296.3	1292.3	1288.3	1284.4	1280.4	1278.9	1279.8	1280.7	1281.6	1282.5
150°	1320.7	1319.2	1315.5	1311.7	1307.9	1304.1	1303.1	1304.7	1306.4	1308.0	1309.7
152.5°	1341.9	1340.5	1336.9	1333.3	1329.7	1326.1	1325.3	1327.1	1328.9	1330.8	1332.6
155°	1370.6	1369.2	1366.4	1363.5	1360.7	1357.9	1357.5	1359.6	1361.8	1363.9	1366.0
157.5°	1394.6	1393.0	1391.0	1389.0	1387.1	1385.1	1385.0	1386.8	1388.6	1390.4	1392.2
160°	1408.9	1407.5	1406.1	1404.6	1403.2	1401.8	1401.8	1403.2	1404.6	1406.1	1407.5
162.5°	1421.8	1420.2	1419.0	1417.8	1416.5	1415.3	1415.4	1416.8	1418.2	1419.7	1421.1
165°	1437.8	1436.2	1435.5	1434.8	1434.0	1433.3	1433.7	1435.1	1436.5	1437.9	1439.4
167.5°	1451.2	1449.6	1448.9	1448.2	1447.6	1446.9	1447.3	1448.7	1450.1	1451.6	1453.0
170°	1458.0	1456.4	1455.9	1455.4	1455.0	1454.5	1455.0	1456.4	1457.8	1459.2	1460.6
172.5°	1463.1	1461.5	1461.0	1460.5	1460.1	1459.6	1460.1	1461.5	1462.9	1464.3	1465.7
175°	1468.7	1467.0	1466.5	1466.1	1465.6	1465.1	1465.7	1467.4	1469.0	1470.7	1472.3
177.5°	1469.6	1468.3	1468.1	1467.9	1467.7	1467.5	1468.1	1469.4	1470.7	1472.1	1473.4
180°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1



TEST NUMBER: P331321

CATALOG NUMBER: SA2XXDIP-C485D1080U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7
2.5°	976.8	978.3	983.1	987.9	993.2	994.7	997.1	995.0	994.4	1000.1	1004.3
5°	979.6	986.3	999.4	1011.3	1021.4	1028.5	1036.0	1039.0	1044.6	1052.4	1062.1
7.5°	976.4	989.5	1010.1	1027.5	1046.4	1060.1	1070.8	1079.9	1090.9	1105.8	1122.0
10°	972.9	990.4	1015.4	1036.7	1059.9	1077.4	1092.0	1106.2	1122.6	1143.2	1164.4
12.5°	966.3	987.1	1018.4	1043.6	1073.3	1090.6	1110.2	1140.8	1158.5	1187.1	1217.0
15°	953.1	976.2	1019.9	1050.9	1084.5	1117.4	1153.6	1182.7	1211.9	1228.7	1270.9
17.5°	933.4	967.4	1015.8	1052.0	1094.7	1146.4	1187.1	1220.2	1253.8	1281.0	1302.2
20°	917.6	954.6	1009.8	1053.2	1103.9	1159.6	1206.3	1239.9	1269.0	1291.8	1304.9
22.5°	897.6	944.1	997.9	1048.7	1113.5	1168.6	1217.6	1244.1	1268.4	1279.5	1284.5
25°	866.0	922.1	982.9	1044.9	1118.1	1176.4	1221.2	1237.3	1244.4	1233.5	1215.6
27.5°	832.1	894.5	965.7	1037.9	1115.3	1171.3	1203.4	1200.9	1188.9	1153.8	1125.8
30°	806.7	875.4	951.9	1030.7	1108.4	1162.9	1181.6	1162.9	1135.7	1096.5	1056.5
32.5°	780.1	851.2	937.3	1020.6	1095.9	1143.8	1147.9	1115.7	1073.5	1029.0	979.1
35°	739.8	816.8	909.7	997.9	1069.2	1099.5	1081.5	1024.8	974.7	913.9	845.9
37.5°	694.3	779.3	872.5	964.6	1029.3	1037.2	992.7	932.9	862.3	790.8	710.8
40°	660.3	750.3	846.3	939.2	996.4	988.2	931.4	865.7	781.6	694.3	619.9
42.5°	629.8	719.8	817.6	908.8	954.6	932.0	865.7	785.0	694.7	612.4	544.4
45°	577.0	669.6	769.7	857.8	884.0	843.3	755.5	665.9	577.0	508.3	454.5
47.5°	525.8	617.3	716.4	793.9	803.2	748.4	652.5	560.3	483.9	427.9	390.0
50°	488.1	580.0	678.2	747.3	744.3	678.2	579.6	491.8	428.0	382.8	357.4
52.5°	454.3	541.1	635.5	698.3	682.5	610.4	516.3	438.4	385.9	350.5	327.5
55°	401.8	482.1	571.8	622.2	593.1	513.1	433.6	370.8	332.0	305.5	287.6
57.5°	349.7	425.0	501.7	532.8	500.6	426.8	360.5	315.0	285.8	266.1	254.5
60°	317.4	383.2	451.5	478.4	439.9	374.2	321.9	281.2	257.7	241.6	231.2
62.5°	285.2	344.0	408.5	423.1	387.9	332.4	286.1	252.2	232.9	218.6	208.8
65°	241.3	289.4	338.4	348.1	315.6	272.6	236.0	214.0	196.8	186.4	178.5
67.5°	197.9	236.5	271.2	279.0	250.6	220.8	194.3	175.2	163.5	154.8	148.2
70°	172.2	202.8	231.2	237.5	214.7	188.2	168.1	152.7	142.3	134.8	128.5
72.5°	145.0	170.5	194.1	198.4	179.8	159.5	143.0	130.9	121.7	116.9	110.8
75°	110.9	125.9	144.2	145.3	133.0	120.6	107.9	100.1	95.2	89.3	86.3
77.5°	78.3	90.0	100.5	102.5	95.2	86.8	79.7	73.5	69.4	66.6	63.9
80°	59.8	69.1	73.6	76.2	71.0	65.0	60.9	56.8	54.2	52.3	50.4
82.5°	42.7	48.5	52.7	54.7	51.8	48.3	44.1	41.8	39.8	38.2	37.6
85°	21.7	24.3	26.9	27.6	26.9	25.4	23.2	23.2	22.0	21.7	21.7
87.5°	8.2	9.9	10.4	11.9	11.7	12.1	12.5	12.5	12.6	12.6	12.5
90°	3.7	6.3	8.9	11.5	13.7	15.6	17.5	19.4	21.3	22.4	23.6
92.5°	21.2	21.0	20.8	20.5	20.9	21.8	22.8	23.7	24.7	25.3	25.9
95°	61.3	53.5	45.7	37.9	34.8	36.5	38.2	39.8	41.5	42.6	43.8
97.5°	115.2	93.2	71.2	49.3	40.2	44.0	47.8	51.7	55.5	56.4	57.4
100°	155.8	123.4	91.1	58.7	44.5	48.5	52.6	56.6	60.6	62.5	64.4
102.5°	237.4	230.6	223.7	216.9	196.7	163.1	129.5	95.9	62.3	64.8	67.2
105°	330.3	337.3	344.4	351.5	322.8	258.3	193.8	129.3	64.8	67.4	70.0
107.5°	418.8	424.5	430.2	436.0	400.2	322.8	245.5	168.1	90.8	88.1	85.5
110°	475.9	480.9	485.8	490.8	459.1	390.8	322.6	254.3	186.0	162.4	138.8





TEST NUMBER: P331321

CATALOG NUMBER: SA2XXDIP-C485D1080U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	529.8	534.1	538.5	542.9	536.7	519.8	503.0	486.1	469.2	383.1	296.9
115°	615.3	619.3	623.3	627.3	632.3	638.2	644.1	650.0	655.9	546.5	437.1
117.5°	692.5	697.0	701.5	706.0	710.2	714.3	718.4	722.4	726.5	700.0	673.6
120°	747.7	751.2	754.8	758.3	762.2	766.5	770.7	775.0	779.2	782.0	784.9
122.5°	795.5	799.2	803.0	806.7	810.9	815.5	820.1	824.8	829.4	831.1	832.8
125°	867.3	870.4	873.5	876.5	880.3	884.8	889.3	893.8	898.3	899.9	901.6
127.5°	933.4	936.8	940.2	943.6	946.9	950.3	953.6	957.0	960.4	962.8	965.2
130°	975.4	979.2	983.0	986.7	989.9	992.5	995.1	997.7	1000.3	1002.9	1005.5
132.5°	1017.4	1020.6	1023.8	1027.0	1029.9	1032.5	1035.1	1037.7	1040.3	1042.5	1044.7
135°	1073.2	1077.0	1080.8	1084.5	1087.5	1089.6	1091.7	1093.9	1096.0	1098.4	1100.7
137.5°	1128.0	1130.6	1133.3	1135.9	1138.4	1140.9	1143.3	1145.7	1148.1	1150.4	1152.7
140°	1163.8	1165.7	1167.6	1169.5	1171.7	1174.3	1176.9	1179.5	1182.1	1184.2	1186.4
142.5°	1194.2	1195.9	1197.6	1199.3	1201.7	1204.6	1207.6	1210.6	1213.6	1215.5	1217.4
145°	1240.3	1240.1	1239.9	1239.6	1241.5	1245.5	1249.5	1253.6	1257.6	1259.2	1260.9
147.5°	1281.6	1280.7	1279.8	1278.9	1280.4	1284.4	1288.3	1292.3	1296.3	1297.5	1298.7
150°	1308.0	1306.4	1304.7	1303.1	1304.1	1307.9	1311.7	1315.5	1319.2	1320.7	1322.1
152.5°	1330.8	1328.9	1327.1	1325.3	1326.1	1329.7	1333.3	1336.9	1340.5	1341.9	1343.3
155°	1363.9	1361.8	1359.6	1357.5	1357.9	1360.7	1363.5	1366.4	1369.2	1370.6	1372.0
157.5°	1390.4	1388.6	1386.8	1385.0	1385.1	1387.1	1389.0	1391.0	1393.0	1394.6	1396.2
160°	1406.1	1404.6	1403.2	1401.8	1401.8	1403.2	1404.6	1406.1	1407.5	1408.9	1410.3
162.5°	1419.7	1418.2	1416.8	1415.4	1415.3	1416.5	1417.8	1419.0	1420.2	1421.8	1423.4
165°	1437.9	1436.5	1435.1	1433.7	1433.3	1434.0	1434.8	1435.5	1436.2	1437.8	1439.5
167.5°	1451.6	1450.1	1448.7	1447.3	1446.9	1447.6	1448.2	1448.9	1449.6	1451.2	1452.9
170°	1459.2	1457.8	1456.4	1455.0	1454.5	1455.0	1455.4	1455.9	1456.4	1458.0	1459.7
172.5°	1464.3	1462.9	1461.5	1460.1	1459.6	1460.1	1460.5	1461.0	1461.5	1463.1	1464.8
175°	1470.7	1469.0	1467.4	1465.7	1465.1	1465.6	1466.1	1466.5	1467.0	1468.7	1470.3
177.5°	1472.1	1470.7	1469.4	1468.1	1467.5	1467.7	1467.9	1468.1	1468.3	1469.6	1470.9
180°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1



TEST NUMBER: P331321

CATALOG NUMBER: SA2XXDIP-C485D1080U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	971.7	971.7	971.7	971.7	971.7	971.7	971.7
2.5°	1007.9	1012.1	1012.1	1012.7	1017.4	1016.9	1016.6
5°	1072.6	1078.9	1079.7	1086.4	1090.9	1089.4	1085.3
7.5°	1133.6	1145.4	1154.4	1159.4	1165.3	1168.9	1167.3
10°	1182.0	1199.2	1209.6	1216.7	1225.3	1231.7	1229.4
12.5°	1225.9	1246.4	1260.7	1272.9	1274.0	1282.2	1276.6
15°	1294.4	1316.1	1318.3	1327.3	1334.4	1333.6	1334.0
17.5°	1317.0	1324.0	1325.4	1325.6	1325.7	1323.1	1317.4
20°	1309.0	1306.4	1300.0	1295.2	1286.6	1285.4	1278.0
22.5°	1270.7	1262.4	1246.5	1236.0	1222.6	1219.1	1217.0
25°	1195.4	1177.1	1151.7	1127.5	1120.7	1107.7	1111.4
27.5°	1092.1	1063.6	1036.1	1016.4	998.6	979.0	984.6
30°	1019.5	987.4	948.6	918.7	899.7	881.0	877.6
32.5°	932.9	885.8	842.5	816.2	787.0	775.2	762.3
35°	783.5	737.6	694.6	657.7	636.4	619.9	605.0
37.5°	649.1	596.3	561.6	531.7	516.3	506.9	509.2
40°	565.8	519.5	494.1	471.3	457.1	450.4	451.9
42.5°	498.3	463.6	442.7	427.1	417.1	413.3	412.4
45°	421.6	402.2	385.0	376.1	371.2	367.1	364.5
47.5°	369.4	353.5	343.8	338.5	334.2	330.1	330.0
50°	338.0	327.5	320.8	315.2	311.8	308.8	311.5
52.5°	314.1	304.5	297.8	292.8	291.5	288.8	288.8
55°	278.6	271.1	266.3	261.8	259.6	258.1	256.2
57.5°	246.3	239.2	234.8	231.9	227.7	226.2	225.6
60°	223.3	217.7	213.2	209.5	207.6	204.7	204.7
62.5°	202.1	196.5	192.3	189.5	186.4	185.2	185.5
65°	171.4	166.9	162.8	159.8	159.1	156.9	157.6
67.5°	143.2	140.2	135.9	134.2	132.8	131.6	130.7
70°	124.4	121.4	119.1	116.9	115.8	115.8	115.8
72.5°	108.5	104.9	103.6	100.8	101.4	100.2	99.0
75°	84.0	81.8	80.7	79.5	77.7	77.7	77.7
77.5°	61.8	61.2	59.8	58.6	58.2	57.8	58.0
80°	47.8	47.4	46.7	46.7	45.9	45.6	44.8
82.5°	36.7	35.8	35.3	35.0	34.9	34.8	34.7
85°	20.9	20.2	20.2	20.5	19.8	19.8	20.2
87.5°	13.0	13.3	13.1	13.2	13.6	13.4	13.5
90°	24.8	26.0	26.8	27.3	27.8	28.2	28.7
92.5°	26.5	27.1	27.6	27.9	28.1	28.4	28.7
95°	45.0	46.2	46.7	46.4	46.2	45.9	45.7
97.5°	58.3	59.3	59.9	60.2	60.5	60.7	61.0
100°	66.3	68.2	69.3	69.8	70.3	70.8	71.2
102.5°	69.7	72.1	73.7	74.3	75.0	75.7	76.3
105°	72.6	75.2	77.0	78.0	78.9	79.8	80.8
107.5°	82.8	80.2	79.4	80.3	81.2	82.2	83.1
110°	115.2	91.5	80.2	81.1	82.1	83.0	84.0



TEST NUMBER: P331321

CATALOG NUMBER: SA2XXDIP-C485D1080U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	210.7	124.5	81.8	82.6	83.3	84.1	84.8
115°	327.8	218.4	155.2	138.2	121.2	104.2	87.2
117.5°	647.1	620.7	579.5	523.6	467.7	411.8	355.9
120°	787.7	790.6	776.0	744.1	712.2	680.3	648.5
122.5°	834.5	836.2	833.9	827.8	821.6	815.4	809.2
125°	903.2	904.9	906.1	906.8	907.5	908.2	908.9
127.5°	967.6	970.0	971.3	971.4	971.6	971.7	971.8
130°	1008.1	1010.7	1011.9	1011.7	1011.4	1011.2	1011.0
132.5°	1047.0	1049.2	1050.2	1049.9	1049.7	1049.5	1049.2
135°	1103.1	1105.4	1106.4	1105.9	1105.4	1105.0	1104.5
137.5°	1155.0	1157.3	1158.1	1157.3	1156.5	1155.7	1154.9
140°	1188.5	1190.6	1191.1	1189.9	1188.7	1187.5	1186.4
142.5°	1219.4	1221.3	1221.7	1220.5	1219.3	1218.2	1217.0
145°	1262.5	1264.2	1264.4	1263.3	1262.1	1260.9	1259.7
147.5°	1300.0	1301.2	1301.3	1300.3	1299.3	1298.3	1297.3
150°	1323.5	1324.9	1325.0	1323.8	1322.7	1321.5	1320.3
152.5°	1344.8	1346.2	1346.1	1344.5	1343.0	1341.4	1339.9
155°	1373.5	1374.9	1374.6	1372.7	1370.9	1369.0	1367.1
157.5°	1397.8	1399.4	1399.3	1397.5	1395.6	1393.8	1391.9
160°	1411.7	1413.1	1413.0	1411.4	1409.7	1408.1	1406.4
162.5°	1425.0	1426.7	1426.4	1424.4	1422.4	1420.3	1418.3
165°	1441.1	1442.8	1442.8	1441.1	1439.5	1437.8	1436.2
167.5°	1454.5	1456.2	1455.9	1453.8	1451.7	1449.6	1447.4
170°	1461.3	1463.0	1462.7	1460.6	1458.5	1456.4	1454.2
172.5°	1466.4	1468.1	1467.9	1465.7	1463.6	1461.5	1459.3
175°	1472.0	1473.6	1473.3	1470.9	1468.5	1466.2	1463.8
177.5°	1472.2	1473.6	1473.4	1471.7	1470.0	1468.3	1466.6
180°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1

(END OF REPORT)